

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333522-930

Luminaire Tested: **S125RDIP-S610D365U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333522-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D365U930-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3027.2 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65																				
1	102	97	94	90	95	92	88	86	81	79	76	71	70	68	62	61	60	56																				
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51	47																				
3	85	76	69	63	80	72	65	60	64	59	54	56	52	49	50	47	44	41																				
4	78	67	60	54	73	64	57	51	57	51	47	51	46	43	45	41	38	35																				
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	40	37	34	31																				
6	66	54	46	40	62	52	44	39	46	40	36	41	36	33	37	33	30	27																				
7	62	49	41	36	58	47	39	34	42	36	32	38	33	29	34	30	27	24																				
8	57	45	37	32	54	43	35	30	38	32	28	35	30	26	31	27	24	22																				
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20																				
10	50	38	30	26	47	36	29	25	33	27	23	29	25	21	26	23	20	18																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4873	4873	4873	4873
5°	5606	4879	4309	4879
10°	6431	4854	3802	4854
15°	6946	4804	3380	4804
20°	7659	4746	3120	4746
25°	8863	4670	2895	4670
30°	9645	4589	2748	4589
35°	8136	4495	2613	4495
40°	5681	4326	2496	4326
45°	4215	4098	2382	4098
50°	3361	3861	2284	3861
55°	2852	3567	2197	3567
60°	2465	3304	2056	3304
65°	2196	3020	1771	3020
70°	1930	2766	1613	2766
75°	1669	2395	1515	2395
80°	1268	2016	1268	2016
85°	1060	1586	1193	1586



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.3	2.4
10°-20°	212.0	7.0
20°-30°	336.2	11.1
30°-40°	405.4	13.4
40°-50°	362.0	12.0
50°-60°	277.6	9.2
60°-70°	180.4	6.0
70°-80°	87.7	2.9
80°-90°	21.7	0.7
90°-100°	103.6	3.4
100°-110°	222.7	7.4
110°-120°	209.0	6.9
120°-130°	169.4	5.6
130°-140°	135.9	4.5
140°-150°	102.6	3.4
150°-160°	72.2	2.4
160°-170°	42.6	1.4
170°-180°	13.8	0.5
0°-30°	620.5	20.5
0°-40°	1025.9	33.9
0°-60°	1665.6	55.0
0°-90°	1955.5	64.6
90°-120°	535.3	17.7
90°-150°	943.1	31.2
90°-180°	1072.0	35.4
0°-180°	3027.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	754	754	754	754	754	
5°	865	753	665	753	865	86
15°	1039	718	506	718	1039	298
25°	1244	655	406	655	1244	571
35°	1032	570	331	570	1032	623
45°	462	449	261	449	462	368
55°	253	317	195	317	253	230
65°	144	198	116	198	144	143
75°	67	96	61	96	67	71
85°	14	21	16	21	14	17
90°	7	0	7	0	7	5
95°	68	10	68	10	68	96
105°	382	32	382	32	382	380
115°	425	58	425	58	425	416
125°	335	81	335	81	335	303
135°	278	94	278	94	278	216
145°	220	110	220	110	220	140
155°	184	126	184	126	184	86
165°	161	137	161	137	161	46
175°	145	143	145	143	145	14
180°	143	143	143	143	143	



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	793.6	793.1	794.1	791.3	791.7	787.4	787.4	784.2	780.0	776.7	775.3
5°	864.7	865.4	864.1	859.4	856.3	851.7	846.4	837.1	829.4	822.0	816.1
7.5°	937.9	938.3	934.3	932.9	925.0	919.3	907.7	895.0	883.8	869.5	858.7
10°	980.6	980.2	975.9	972.5	965.6	957.0	945.5	930.7	916.7	901.2	886.4
12.5°	1005.3	1004.5	1003.1	999.0	992.7	985.0	975.3	960.7	943.5	926.5	909.2
15°	1038.8	1036.6	1032.6	1027.3	1018.3	1009.3	998.5	985.5	969.1	949.9	933.8
17.5°	1080.1	1080.2	1074.0	1066.7	1054.5	1038.6	1021.9	1000.9	978.6	957.5	940.4
20°	1114.4	1113.4	1107.2	1093.0	1079.0	1059.2	1040.0	1014.3	987.1	959.4	938.1
22.5°	1163.4	1161.0	1154.5	1135.8	1114.2	1088.7	1059.3	1027.9	995.0	963.7	935.6
25°	1243.8	1241.9	1229.2	1207.5	1177.2	1137.8	1099.4	1056.4	1009.0	967.8	933.8
27.5°	1298.8	1296.7	1287.4	1269.3	1241.3	1200.0	1147.9	1090.5	1031.3	974.6	925.4
30°	1293.3	1298.0	1296.7	1288.4	1267.3	1230.1	1182.2	1117.4	1047.1	980.6	922.0
32.5°	1215.5	1219.7	1230.6	1247.0	1248.2	1233.4	1197.5	1137.8	1064.9	989.2	919.2
35°	1031.9	1037.5	1058.6	1091.7	1135.1	1171.3	1178.8	1146.6	1081.2	999.7	915.2
37.5°	793.4	823.9	841.6	876.4	941.9	1008.6	1072.7	1096.3	1068.5	995.4	908.6
40°	673.9	681.3	713.0	752.3	807.4	876.8	968.2	1034.1	1036.2	985.5	898.1
42.5°	576.8	586.2	607.9	639.3	686.5	755.9	850.2	937.3	977.5	958.2	884.5
45°	461.5	468.6	484.4	508.5	544.8	602.1	683.2	783.9	863.8	895.0	848.0
47.5°	379.1	382.9	396.6	415.1	441.9	483.6	546.4	633.8	729.7	796.9	790.3
50°	334.5	338.8	349.4	363.3	385.9	421.2	471.4	544.1	642.9	725.0	741.4
52.5°	299.8	303.4	310.0	323.2	341.8	368.9	409.4	475.3	564.2	651.4	689.4
55°	253.3	255.8	261.1	268.5	283.4	302.9	337.9	383.4	455.3	543.2	599.0
57.5°	215.1	216.3	219.6	226.5	236.8	251.0	276.3	315.0	366.5	445.6	507.2
60°	190.8	192.0	196.3	201.0	209.0	222.1	241.9	268.8	318.4	383.8	446.0
62.5°	171.5	172.2	174.1	178.7	185.7	195.8	211.4	233.4	272.8	330.2	389.0
65°	143.7	144.0	144.6	148.4	152.7	160.1	170.3	185.8	215.6	258.9	311.0
67.5°	117.1	117.5	119.7	121.0	125.5	129.4	135.4	147.2	168.2	197.4	237.8
70°	102.2	101.9	104.0	105.6	107.1	111.8	115.9	125.4	138.4	160.8	194.5
72.5°	88.3	87.6	88.5	89.0	91.1	94.2	98.2	104.1	114.1	129.6	155.3
75°	66.9	67.2	67.2	67.8	69.4	70.6	71.8	74.9	80.6	90.7	104.7
77.5°	47.0	46.5	47.8	47.9	48.8	50.2	51.3	52.5	54.8	59.0	66.2
80°	34.1	34.1	34.4	35.3	35.0	35.6	37.2	38.4	41.2	43.7	46.1
82.5°	26.2	25.9	26.2	26.4	26.3	26.9	27.5	27.7	28.8	30.0	31.8
85°	14.3	14.3	14.6	14.6	14.8	14.8	15.2	15.2	15.2	15.5	15.8
87.5°	6.8	6.5	6.2	6.2	6.4	6.8	6.5	6.3	6.2	6.1	6.3
90°	6.6	6.6	6.4	6.4	6.4	5.8	5.5	5.2	4.9	4.6	4.0
92.5°	18.3	18.8	19.2	20.0	23.6	27.9	37.0	51.0	75.2	92.9	94.4
95°	67.8	72.3	74.6	83.2	103.7	127.9	163.4	207.2	249.8	255.3	208.3
97.5°	163.6	167.4	175.7	191.8	209.6	243.3	277.9	308.5	316.1	272.6	186.1
100°	224.8	229.3	240.0	260.7	280.6	310.6	340.3	354.4	332.2	260.2	166.0
102.5°	293.0	296.4	308.0	322.8	344.1	364.4	378.5	369.8	322.5	238.3	150.7
105°	381.8	385.2	391.0	400.5	409.8	412.9	400.2	360.8	291.6	208.9	136.0
107.5°	428.9	431.2	433.2	433.2	428.5	413.4	380.9	328.2	260.0	188.7	129.8
110°	444.6	444.6	442.5	437.1	424.1	399.7	359.1	304.3	242.1	179.2	127.9



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	442.8	440.7	435.7	426.2	407.3	378.5	337.4	285.4	228.7	173.7	127.9
115°	425.3	421.5	413.4	399.7	377.2	345.8	306.3	261.6	214.1	167.7	128.8
117.5°	394.7	392.4	384.4	370.1	347.6	318.8	284.8	246.3	205.4	164.8	130.7
120°	374.9	372.6	364.8	351.0	329.6	304.3	272.6	238.0	200.6	163.4	132.6
122.5°	357.3	355.3	347.5	334.8	315.8	292.0	263.8	231.8	196.4	162.2	134.1
125°	335.1	332.2	325.9	314.1	297.9	277.2	252.1	222.7	190.8	160.8	136.9
127.5°	316.1	314.8	308.8	298.4	283.7	264.3	240.9	213.5	185.6	160.1	139.9
130°	305.7	304.0	298.2	288.7	274.3	255.6	233.1	207.7	182.1	159.6	141.8
132.5°	295.3	293.3	288.0	278.6	264.2	246.1	225.8	201.9	179.4	159.6	143.8
135°	278.3	276.6	271.4	262.0	249.2	232.8	214.3	194.5	176.0	159.6	146.7
137.5°	260.2	258.3	253.5	244.8	233.5	219.6	204.2	188.2	173.1	160.0	149.3
140°	247.5	246.1	241.7	234.2	223.6	211.5	198.2	184.7	171.7	160.2	150.4
142.5°	235.8	234.6	230.5	224.1	215.1	204.6	193.1	181.7	170.6	160.5	151.1
145°	219.6	218.4	215.2	210.3	203.4	195.7	186.7	177.8	168.8	160.2	151.8
147.5°	205.9	205.3	203.5	199.6	194.1	188.3	181.3	174.1	167.1	159.5	152.1
150°	198.2	198.0	196.8	193.3	189.0	183.8	178.4	172.0	165.7	158.7	152.1
152.5°	192.2	191.9	190.8	188.0	184.4	180.3	175.4	169.7	164.0	157.8	151.9
155°	184.1	183.8	183.0	180.9	178.1	174.9	170.9	166.2	161.3	156.2	151.2
157.5°	176.8	176.9	176.1	174.5	172.2	169.7	166.6	162.8	158.8	154.4	150.5
160°	172.0	172.3	171.7	170.3	168.3	166.2	163.4	160.5	156.8	153.3	149.9
162.5°	167.6	167.7	167.5	166.4	164.9	163.1	160.6	157.9	154.9	151.9	149.1
165°	161.3	161.3	161.3	160.8	159.6	158.2	156.5	154.4	152.1	149.9	148.1
167.5°	155.6	155.6	155.9	155.4	154.8	153.8	152.5	151.1	149.4	147.8	146.5
170°	152.1	152.5	152.5	152.1	151.6	151.0	150.1	149.3	147.8	146.7	145.8
172.5°	148.9	149.2	149.7	149.1	149.0	148.7	148.1	147.2	146.2	145.3	144.9
175°	145.0	145.2	145.8	145.5	145.5	145.5	145.0	145.0	144.1	143.8	143.8
177.5°	142.9	142.9	143.6	143.4	143.6	143.6	143.6	143.4	143.2	142.9	142.9
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	775.3	773.6	770.3	767.4	763.6	760.4	758.1	755.5	752.0	747.8	744.3
5°	809.6	802.7	793.8	786.0	776.2	768.4	760.3	752.6	744.9	734.9	726.3
7.5°	847.6	833.6	819.9	802.7	787.0	773.1	759.7	746.2	732.9	718.8	705.2
10°	870.9	853.9	834.9	813.3	793.4	774.6	757.2	740.2	722.3	706.5	689.4
12.5°	892.7	870.7	849.1	821.7	797.9	774.9	752.8	731.6	712.3	691.9	673.5
15°	912.4	890.7	866.6	833.2	800.0	772.1	746.1	718.5	694.7	671.7	651.3
17.5°	920.0	897.3	869.2	837.1	800.9	765.8	732.3	702.1	674.0	647.3	624.3
20°	917.0	895.0	866.3	835.6	796.9	760.3	724.1	690.6	659.3	631.2	606.7
22.5°	909.9	887.1	859.3	827.0	790.2	751.4	712.7	677.0	644.2	615.1	588.4
25°	899.1	868.1	839.6	808.0	773.1	734.7	694.7	655.3	620.4	590.6	561.5
27.5°	887.9	849.2	813.0	781.5	744.6	710.4	671.8	631.5	594.7	564.4	534.6
30°	877.8	834.4	794.4	758.8	723.8	691.3	654.7	615.4	577.6	546.3	516.0
32.5°	865.1	819.0	775.1	734.0	700.3	668.0	634.9	597.3	560.5	528.2	497.4
35°	849.2	790.4	742.7	699.0	661.5	630.2	600.5	570.1	533.3	499.9	469.9
37.5°	828.4	761.7	706.5	658.8	619.4	587.9	564.5	536.7	503.1	471.1	443.2
40°	815.8	740.9	680.4	633.3	591.8	558.7	536.7	513.1	482.5	452.5	424.6
42.5°	798.9	721.8	654.2	605.1	563.4	531.5	509.2	488.7	462.9	434.6	404.8
45°	765.9	684.8	613.8	561.2	519.1	487.8	467.0	448.7	429.3	403.2	377.2
47.5°	722.9	646.2	571.9	514.5	473.2	444.2	424.0	409.6	395.7	373.6	348.3
50°	688.5	614.5	542.0	486.2	442.3	414.7	395.8	384.3	371.6	351.6	330.4
52.5°	647.8	581.8	510.8	453.8	412.3	386.5	368.3	356.9	346.3	330.0	309.9
55°	583.8	525.9	460.8	409.1	371.0	345.0	327.7	316.8	310.6	296.7	280.9
57.5°	509.9	468.4	411.1	361.2	327.5	301.7	289.1	279.9	272.9	263.0	251.8
60°	458.4	429.3	377.8	330.4	299.5	275.0	263.6	255.8	249.3	240.9	232.3
62.5°	406.1	384.9	340.2	299.5	271.0	250.5	239.8	232.8	225.3	219.6	211.2
65°	336.1	317.2	286.2	254.3	228.0	211.6	203.8	197.6	193.0	186.8	180.8
67.5°	261.4	253.7	232.4	210.3	191.4	176.8	170.2	165.8	160.2	156.5	152.5
70°	215.6	211.8	196.7	182.1	164.4	154.6	148.4	146.5	139.7	136.0	133.1
72.5°	175.0	173.2	164.4	154.3	141.9	133.2	127.5	125.4	121.1	118.1	116.3
75°	119.8	120.5	119.0	112.4	107.8	102.2	97.3	96.0	92.9	90.4	88.9
77.5°	75.8	79.0	79.1	78.8	77.0	73.5	71.5	70.5	67.5	66.6	66.2
80°	52.0	55.4	58.5	58.2	57.6	56.7	55.1	54.2	52.7	51.7	51.1
82.5°	34.7	37.8	40.4	42.2	42.0	41.1	40.0	39.5	39.3	38.6	38.5
85°	16.4	17.0	17.9	20.1	21.7	22.0	21.7	21.4	20.5	20.8	21.0
87.5°	6.4	6.4	6.5	6.4	6.0	7.2	7.8	8.0	7.6	7.2	6.8
90°	3.8	3.2	2.9	2.3	1.7	1.1	0.6	0.3	0.6	1.1	1.7
92.5°	65.7	39.4	23.6	15.2	10.3	6.7	4.2	3.5	4.2	6.7	10.3
95°	128.8	65.4	34.6	21.6	15.2	12.1	9.8	9.5	9.8	12.1	15.2
97.5°	102.8	56.3	36.0	26.7	21.0	17.8	16.1	15.8	16.1	17.8	21.0
100°	93.4	55.9	39.2	30.6	25.0	21.9	20.7	20.1	20.7	21.9	25.0
102.5°	89.4	58.0	43.1	34.7	29.7	26.3	25.4	25.0	25.4	26.3	29.7
105°	87.9	62.2	49.6	41.5	36.9	34.0	32.5	32.5	32.5	34.0	36.9
107.5°	90.5	68.6	56.3	49.1	44.3	41.9	40.5	39.9	40.5	41.9	44.3
110°	93.1	73.2	61.4	53.9	49.6	47.0	45.8	45.2	45.8	47.0	49.6





TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	96.3	77.5	66.2	58.9	54.6	52.0	51.1	50.5	51.1	52.0	54.6
115°	101.1	84.5	73.8	66.5	62.2	59.7	58.8	58.2	58.8	59.7	62.2
117.5°	106.6	91.5	81.4	74.4	69.5	66.9	66.0	65.1	66.0	66.9	69.5
120°	110.4	96.5	86.4	79.2	74.4	71.7	70.6	69.7	70.6	71.7	74.4
122.5°	114.5	101.3	91.3	84.1	78.8	76.1	75.2	74.6	75.2	76.1	78.8
125°	120.2	107.8	98.2	90.7	85.3	82.7	81.3	80.7	81.3	82.7	85.3
127.5°	125.3	113.9	104.8	97.3	91.5	88.1	86.3	85.4	86.3	88.1	91.5
130°	128.8	117.8	108.9	101.4	95.4	91.6	89.4	88.5	89.4	91.6	95.4
132.5°	131.8	121.6	112.6	105.1	98.8	94.7	91.9	90.7	91.9	94.7	98.8
135°	136.0	126.5	117.6	109.8	103.7	99.1	95.6	94.5	95.6	99.1	103.7
137.5°	139.1	130.0	121.9	113.9	107.9	103.3	100.1	99.2	100.1	103.3	107.9
140°	141.2	132.6	124.2	116.4	111.0	106.3	102.9	102.0	102.9	106.3	111.0
142.5°	142.4	134.1	126.3	119.0	113.7	109.1	105.8	105.3	105.8	109.1	113.7
145°	144.1	136.9	129.4	122.8	117.6	113.5	110.6	110.1	110.6	113.5	117.6
147.5°	145.1	138.6	132.0	126.2	121.7	118.0	115.4	115.1	115.4	118.0	121.7
150°	145.8	139.7	133.4	128.5	124.5	120.7	118.7	118.1	118.7	120.7	124.5
152.5°	146.3	140.9	135.0	130.6	126.8	123.5	121.7	121.4	121.7	123.5	126.8
155°	146.7	142.0	137.1	133.1	130.2	127.3	125.6	125.6	125.6	127.3	130.2
157.5°	146.9	143.0	138.8	135.7	133.2	130.8	129.4	129.5	129.4	130.8	133.2
160°	146.9	143.5	139.7	137.1	134.9	132.8	131.7	132.0	131.7	132.8	134.9
162.5°	146.8	144.0	140.6	138.5	136.7	134.9	133.8	134.0	133.8	134.9	136.7
165°	146.3	144.1	141.8	140.1	138.8	137.5	136.6	137.1	136.6	137.5	138.8
167.5°	145.7	144.1	142.2	141.0	140.2	139.5	138.9	139.3	138.9	139.5	140.2
170°	145.2	144.1	142.6	141.8	141.2	140.6	140.3	140.6	140.3	140.6	141.2
172.5°	144.8	143.8	142.6	142.2	141.9	141.3	141.0	141.5	141.0	141.3	141.9
175°	144.1	143.5	142.6	142.6	142.6	142.4	142.0	142.6	142.0	142.4	142.6
177.5°	143.4	143.2	142.7	142.7	142.9	142.7	142.7	143.2	142.7	142.7	142.9
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	741.8	738.3	735.9	730.9	727.4	725.9	723.3	722.5	725.2	723.3	723.0
5°	719.7	710.8	703.7	696.5	688.8	683.9	676.4	675.1	673.3	670.5	669.9
7.5°	693.3	681.6	672.5	660.6	650.4	642.2	632.9	628.5	626.1	622.5	617.7
10°	675.5	661.5	649.1	637.4	624.7	614.5	605.2	598.0	593.4	589.1	587.2
12.5°	657.9	643.7	627.9	613.6	599.4	587.9	577.6	573.0	567.9	562.8	558.5
15°	630.6	611.6	594.4	577.9	565.8	553.4	543.6	536.7	529.0	526.8	518.4
17.5°	601.6	583.0	562.7	545.4	531.5	517.8	507.0	499.2	493.3	485.3	481.5
20°	583.5	561.5	541.7	525.9	510.4	494.3	483.1	476.6	471.1	464.6	461.5
22.5°	564.2	542.7	522.4	503.9	488.1	472.2	464.3	457.5	451.3	445.2	441.2
25°	535.8	514.1	492.8	473.5	457.1	445.6	436.3	428.6	425.3	419.3	415.0
27.5°	507.8	484.7	462.5	443.4	430.5	419.1	411.6	405.4	399.3	394.1	390.4
30°	489.7	466.1	442.0	426.8	413.1	402.4	394.0	388.1	383.4	378.8	376.0
32.5°	471.6	447.3	425.8	409.4	396.6	387.2	378.6	372.9	368.0	362.9	359.6
35°	442.5	417.8	400.5	384.3	371.6	363.0	357.1	349.0	345.0	341.3	337.9
37.5°	415.6	392.6	373.8	359.7	348.7	340.1	332.5	328.1	323.2	319.8	317.0
40°	395.8	374.7	357.8	342.8	334.8	325.2	318.0	312.5	308.8	304.4	301.3
42.5°	378.0	358.4	341.9	328.5	318.5	310.3	303.5	297.9	293.2	290.1	287.5
45°	352.8	333.2	317.2	304.8	295.5	287.7	280.6	277.8	271.6	267.9	266.7
47.5°	326.7	309.2	293.7	282.3	272.7	265.4	258.7	253.1	249.6	246.0	244.0
50°	309.1	292.4	277.8	266.7	257.4	249.3	243.1	239.4	234.7	231.4	228.9
52.5°	291.5	276.0	261.5	250.8	242.7	234.7	227.8	224.0	219.6	217.4	215.7
55°	266.4	250.0	237.6	227.0	218.7	211.2	204.7	201.0	198.2	196.1	195.4
57.5°	237.8	224.9	213.4	203.8	195.2	188.2	182.5	179.0	176.5	176.2	174.3
60°	219.2	207.5	197.0	186.8	179.3	172.8	167.9	163.9	161.3	161.0	160.5
62.5°	200.7	189.4	179.6	170.6	164.0	157.7	153.0	148.5	147.0	145.4	144.1
65°	173.1	162.9	154.8	147.7	140.6	135.3	130.7	127.9	124.5	122.6	119.3
67.5°	146.0	138.1	130.4	124.4	118.8	113.8	110.0	105.8	103.5	102.0	99.5
70°	128.2	122.1	114.3	107.8	103.5	99.4	96.3	91.6	90.1	88.9	87.6
72.5°	111.4	105.9	99.4	94.2	89.8	86.0	82.4	80.3	78.8	77.5	76.7
75°	87.6	82.3	76.8	73.1	70.0	66.9	65.1	63.5	62.9	62.5	61.3
77.5°	64.3	61.6	57.1	54.1	52.1	50.9	49.2	48.3	48.3	47.0	46.6
80°	49.2	47.7	43.9	42.7	41.2	39.9	39.1	37.5	36.0	35.3	34.4
82.5°	36.6	35.1	33.6	31.6	30.3	29.5	28.6	28.0	28.2	27.4	26.9
85°	19.5	17.9	17.4	17.0	16.4	17.0	16.7	16.4	16.1	15.8	16.1
87.5°	6.7	6.8	6.6	7.2	6.5	6.8	6.9	6.8	6.8	6.8	6.7
90°	2.3	2.9	3.2	3.8	4.0	4.6	4.9	5.2	5.5	5.8	6.4
92.5°	15.2	23.6	39.4	65.7	94.4	92.9	75.2	51.0	37.0	27.9	23.6
95°	21.6	34.6	65.4	128.8	208.3	255.3	249.8	207.2	163.4	127.9	103.7
97.5°	26.7	36.0	56.3	102.8	186.1	272.6	316.1	308.5	277.9	243.3	209.6
100°	30.6	39.2	55.9	93.4	166.0	260.2	332.2	354.4	340.3	310.6	280.6
102.5°	34.7	43.1	58.0	89.4	150.7	238.3	322.5	369.8	378.5	364.4	344.1
105°	41.5	49.6	62.2	87.9	136.0	208.9	291.6	360.8	400.2	412.9	409.8
107.5°	49.1	56.3	68.6	90.5	129.8	188.7	260.0	328.2	380.9	413.4	428.5
110°	53.9	61.4	73.2	93.1	127.9	179.2	242.1	304.3	359.1	399.7	424.1



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	58.9	66.2	77.5	96.3	127.9	173.7	228.7	285.4	337.4	378.5	407.3
115°	66.5	73.8	84.5	101.1	128.8	167.7	214.1	261.6	306.3	345.8	377.2
117.5°	74.4	81.4	91.5	106.6	130.7	164.8	205.4	246.3	284.8	318.8	347.6
120°	79.2	86.4	96.5	110.4	132.6	163.4	200.6	238.0	272.6	304.3	329.6
122.5°	84.1	91.3	101.3	114.5	134.1	162.2	196.4	231.8	263.8	292.0	315.8
125°	90.7	98.2	107.8	120.2	136.9	160.8	190.8	222.7	252.1	277.2	297.9
127.5°	97.3	104.8	113.9	125.3	139.9	160.1	185.6	213.5	240.9	264.3	283.7
130°	101.4	108.9	117.8	128.8	141.8	159.6	182.1	207.7	233.1	255.6	274.3
132.5°	105.1	112.6	121.6	131.8	143.8	159.6	179.4	201.9	225.8	246.1	264.2
135°	109.8	117.6	126.5	136.0	146.7	159.6	176.0	194.5	214.3	232.8	249.2
137.5°	113.9	121.9	130.0	139.1	149.3	160.0	173.1	188.2	204.2	219.6	233.5
140°	116.4	124.2	132.6	141.2	150.4	160.2	171.7	184.7	198.2	211.5	223.6
142.5°	119.0	126.3	134.1	142.4	151.1	160.5	170.6	181.7	193.1	204.6	215.1
145°	122.8	129.4	136.9	144.1	151.8	160.2	168.8	177.8	186.7	195.7	203.4
147.5°	126.2	132.0	138.6	145.1	152.1	159.5	167.1	174.1	181.3	188.3	194.1
150°	128.5	133.4	139.7	145.8	152.1	158.7	165.7	172.0	178.4	183.8	189.0
152.5°	130.6	135.0	140.9	146.3	151.9	157.8	164.0	169.7	175.4	180.3	184.4
155°	133.1	137.1	142.0	146.7	151.2	156.2	161.3	166.2	170.9	174.9	178.1
157.5°	135.7	138.8	143.0	146.9	150.5	154.4	158.8	162.8	166.6	169.7	172.2
160°	137.1	139.7	143.5	146.9	149.9	153.3	156.8	160.5	163.4	166.2	168.3
162.5°	138.5	140.6	144.0	146.8	149.1	151.9	154.9	157.9	160.6	163.1	164.9
165°	140.1	141.8	144.1	146.3	148.1	149.9	152.1	154.4	156.5	158.2	159.6
167.5°	141.0	142.2	144.1	145.7	146.5	147.8	149.4	151.1	152.5	153.8	154.8
170°	141.8	142.6	144.1	145.2	145.8	146.7	147.8	149.3	150.1	151.0	151.6
172.5°	142.2	142.6	143.8	144.8	144.9	145.3	146.2	147.2	148.1	148.7	149.0
175°	142.6	142.6	143.5	144.1	143.8	143.8	144.1	145.0	145.0	145.5	145.5
177.5°	142.7	142.7	143.2	143.4	142.9	142.9	143.2	143.4	143.6	143.6	143.6
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	722.8	720.0	719.3	720.2	719.3	720.0	722.8	723.0	723.3	725.2	722.5
5°	666.8	663.7	665.3	664.6	665.3	663.7	666.8	669.9	670.5	673.3	675.1
7.5°	617.6	613.8	609.7	611.0	609.7	613.8	617.6	617.7	622.5	626.1	628.5
10°	583.2	580.1	578.2	579.8	578.2	580.1	583.2	587.2	589.1	593.4	598.0
12.5°	554.2	552.4	550.7	550.1	550.7	552.4	554.2	558.5	562.8	567.9	573.0
15°	514.7	511.0	509.5	505.5	509.5	511.0	514.7	518.4	526.8	529.0	536.7
17.5°	478.3	477.1	473.1	471.4	473.1	477.1	478.3	481.5	485.3	493.3	499.2
20°	456.8	455.6	451.6	454.0	451.6	455.6	456.8	461.5	464.6	471.1	476.6
22.5°	439.0	436.3	435.0	434.2	435.0	436.3	439.0	441.2	445.2	451.3	457.5
25°	413.8	409.8	408.2	406.3	408.2	409.8	413.8	415.0	419.3	425.3	428.6
27.5°	388.7	386.5	384.4	383.9	384.4	386.5	388.7	390.4	394.1	399.3	405.4
30°	372.3	370.1	368.5	368.5	368.5	370.1	372.3	376.0	378.8	383.4	388.1
32.5°	357.7	356.0	354.4	354.2	354.4	356.0	357.7	359.6	362.9	368.0	372.9
35°	336.3	333.9	333.2	331.4	333.2	333.9	336.3	337.9	341.3	345.0	349.0
37.5°	314.2	312.2	312.1	311.9	312.1	312.2	314.2	317.0	319.8	323.2	328.1
40°	300.1	298.6	298.2	296.1	298.2	298.6	300.1	301.3	304.4	308.8	312.5
42.5°	285.0	284.2	283.2	282.2	283.2	284.2	285.0	287.5	290.1	293.2	297.9
45°	264.5	262.4	262.4	260.8	262.4	262.4	264.5	266.7	267.9	271.6	277.8
47.5°	243.3	241.7	241.8	240.2	241.8	241.7	243.3	244.0	246.0	249.6	253.1
50°	229.2	228.3	228.0	227.3	228.0	228.3	229.2	228.9	231.4	234.7	239.4
52.5°	215.1	214.7	215.8	214.4	215.8	214.7	215.1	215.7	217.4	219.6	224.0
55°	196.1	195.1	197.0	195.1	197.0	195.1	196.1	195.4	196.1	198.2	201.0
57.5°	174.1	173.3	175.0	174.1	175.0	173.3	174.1	174.3	176.2	176.5	179.0
60°	159.8	157.9	158.9	159.2	158.9	157.9	159.8	160.5	161.0	161.3	163.9
62.5°	142.7	141.6	142.3	140.9	142.3	141.6	142.7	144.1	145.4	147.0	148.5
65°	118.6	117.7	116.4	115.9	116.4	117.7	118.6	119.3	122.6	124.5	127.9
67.5°	99.6	97.4	97.3	97.8	97.3	97.4	99.6	99.5	102.0	103.5	105.8
70°	85.8	85.8	85.4	85.4	85.4	85.8	85.8	87.6	88.9	90.1	91.6
72.5°	76.1	75.9	75.3	75.1	75.3	75.9	76.1	76.7	77.5	78.8	80.3
75°	61.3	61.6	61.0	60.7	61.0	61.6	61.3	61.3	62.5	62.9	63.5
77.5°	45.2	43.9	44.7	43.9	44.7	43.9	45.2	46.6	47.0	48.3	48.3
80°	34.4	34.1	35.0	34.1	35.0	34.1	34.4	34.4	35.3	36.0	37.5
82.5°	27.2	26.9	27.3	26.7	27.3	26.9	27.2	26.9	27.4	28.2	28.0
85°	16.4	16.1	15.8	16.1	15.8	16.1	16.4	16.1	15.8	16.1	16.4
87.5°	6.9	6.7	6.8	6.8	6.8	6.7	6.9	6.7	6.8	6.8	6.8
90°	6.4	6.4	6.6	6.6	6.6	6.4	6.4	6.4	5.8	5.5	5.2
92.5°	20.0	19.2	18.8	18.3	18.8	19.2	20.0	23.6	27.9	37.0	51.0
95°	83.2	74.6	72.3	67.8	72.3	74.6	83.2	103.7	127.9	163.4	207.2
97.5°	191.8	175.7	167.4	163.6	167.4	175.7	191.8	209.6	243.3	277.9	308.5
100°	260.7	240.0	229.3	224.8	229.3	240.0	260.7	280.6	310.6	340.3	354.4
102.5°	322.8	308.0	296.4	293.0	296.4	308.0	322.8	344.1	364.4	378.5	369.8
105°	400.5	391.0	385.2	381.8	385.2	391.0	400.5	409.8	412.9	400.2	360.8
107.5°	433.2	433.2	431.2	428.9	431.2	433.2	433.2	428.5	413.4	380.9	328.2
110°	437.1	442.5	444.6	444.6	444.6	442.5	437.1	424.1	399.7	359.1	304.3



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	426.2	435.7	440.7	442.8	440.7	435.7	426.2	407.3	378.5	337.4	285.4
115°	399.7	413.4	421.5	425.3	421.5	413.4	399.7	377.2	345.8	306.3	261.6
117.5°	370.1	384.4	392.4	394.7	392.4	384.4	370.1	347.6	318.8	284.8	246.3
120°	351.0	364.8	372.6	374.9	372.6	364.8	351.0	329.6	304.3	272.6	238.0
122.5°	334.8	347.5	355.3	357.3	355.3	347.5	334.8	315.8	292.0	263.8	231.8
125°	314.1	325.9	332.2	335.1	332.2	325.9	314.1	297.9	277.2	252.1	222.7
127.5°	298.4	308.8	314.8	316.1	314.8	308.8	298.4	283.7	264.3	240.9	213.5
130°	288.7	298.2	304.0	305.7	304.0	298.2	288.7	274.3	255.6	233.1	207.7
132.5°	278.6	288.0	293.3	295.3	293.3	288.0	278.6	264.2	246.1	225.8	201.9
135°	262.0	271.4	276.6	278.3	276.6	271.4	262.0	249.2	232.8	214.3	194.5
137.5°	244.8	253.5	258.3	260.2	258.3	253.5	244.8	233.5	219.6	204.2	188.2
140°	234.2	241.7	246.1	247.5	246.1	241.7	234.2	223.6	211.5	198.2	184.7
142.5°	224.1	230.5	234.6	235.8	234.6	230.5	224.1	215.1	204.6	193.1	181.7
145°	210.3	215.2	218.4	219.6	218.4	215.2	210.3	203.4	195.7	186.7	177.8
147.5°	199.6	203.5	205.3	205.9	205.3	203.5	199.6	194.1	188.3	181.3	174.1
150°	193.3	196.8	198.0	198.2	198.0	196.8	193.3	189.0	183.8	178.4	172.0
152.5°	188.0	190.8	191.9	192.2	191.9	190.8	188.0	184.4	180.3	175.4	169.7
155°	180.9	183.0	183.8	184.1	183.8	183.0	180.9	178.1	174.9	170.9	166.2
157.5°	174.5	176.1	176.9	176.8	176.9	176.1	174.5	172.2	169.7	166.6	162.8
160°	170.3	171.7	172.3	172.0	172.3	171.7	170.3	168.3	166.2	163.4	160.5
162.5°	166.4	167.5	167.7	167.6	167.7	167.5	166.4	164.9	163.1	160.6	157.9
165°	160.8	161.3	161.3	161.3	161.3	161.3	160.8	159.6	158.2	156.5	154.4
167.5°	155.4	155.9	155.6	155.6	155.6	155.9	155.4	154.8	153.8	152.5	151.1
170°	152.1	152.5	152.5	152.1	152.5	152.5	152.1	151.6	151.0	150.1	149.3
172.5°	149.1	149.7	149.2	148.9	149.2	149.7	149.1	149.0	148.7	148.1	147.2
175°	145.5	145.8	145.2	145.0	145.2	145.8	145.5	145.5	145.5	145.0	145.0
177.5°	143.4	143.6	142.9	142.9	142.9	143.6	143.4	143.6	143.6	143.6	143.4
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	723.3	725.9	727.4	730.9	735.9	738.3	741.8	744.3	747.8	752.0	755.5
5°	676.4	683.9	688.8	696.5	703.7	710.8	719.7	726.3	734.9	744.9	752.6
7.5°	632.9	642.2	650.4	660.6	672.5	681.6	693.3	705.2	718.8	732.9	746.2
10°	605.2	614.5	624.7	637.4	649.1	661.5	675.5	689.4	706.5	722.3	740.2
12.5°	577.6	587.9	599.4	613.6	627.9	643.7	657.9	673.5	691.9	712.3	731.6
15°	543.6	553.4	565.8	577.9	594.4	611.6	630.6	651.3	671.7	694.7	718.5
17.5°	507.0	517.8	531.5	545.4	562.7	583.0	601.6	624.3	647.3	674.0	702.1
20°	483.1	494.3	510.4	525.9	541.7	561.5	583.5	606.7	631.2	659.3	690.6
22.5°	464.3	472.2	488.1	503.9	522.4	542.7	564.2	588.4	615.1	644.2	677.0
25°	436.3	445.6	457.1	473.5	492.8	514.1	535.8	561.5	590.6	620.4	655.3
27.5°	411.6	419.1	430.5	443.4	462.5	484.7	507.8	534.6	564.4	594.7	631.5
30°	394.0	402.4	413.1	426.8	442.0	466.1	489.7	516.0	546.3	577.6	615.4
32.5°	378.6	387.2	396.6	409.4	425.8	447.3	471.6	497.4	528.2	560.5	597.3
35°	357.1	363.0	371.6	384.3	400.5	417.8	442.5	469.9	499.9	533.3	570.1
37.5°	332.5	340.1	348.7	359.7	373.8	392.6	415.6	443.2	471.1	503.1	536.7
40°	318.0	325.2	334.8	342.8	357.8	374.7	395.8	424.6	452.5	482.5	513.1
42.5°	303.5	310.3	318.5	328.5	341.9	358.4	378.0	404.8	434.6	462.9	488.7
45°	280.6	287.7	295.5	304.8	317.2	333.2	352.8	377.2	403.2	429.3	448.7
47.5°	258.7	265.4	272.7	282.3	293.7	309.2	326.7	348.3	373.6	395.7	409.6
50°	243.1	249.3	257.4	266.7	277.8	292.4	309.1	330.4	351.6	371.6	384.3
52.5°	227.8	234.7	242.7	250.8	261.5	276.0	291.5	309.9	330.0	346.3	356.9
55°	204.7	211.2	218.7	227.0	237.6	250.0	266.4	280.9	296.7	310.6	316.8
57.5°	182.5	188.2	195.2	203.8	213.4	224.9	237.8	251.8	263.0	272.9	279.9
60°	167.9	172.8	179.3	186.8	197.0	207.5	219.2	232.3	240.9	249.3	255.8
62.5°	153.0	157.7	164.0	170.6	179.6	189.4	200.7	211.2	219.6	225.3	232.8
65°	130.7	135.3	140.6	147.7	154.8	162.9	173.1	180.8	186.8	193.0	197.6
67.5°	110.0	113.8	118.8	124.4	130.4	138.1	146.0	152.5	156.5	160.2	165.8
70°	96.3	99.4	103.5	107.8	114.3	122.1	128.2	133.1	136.0	139.7	146.5
72.5°	82.4	86.0	89.8	94.2	99.4	105.9	111.4	116.3	118.1	121.1	125.4
75°	65.1	66.9	70.0	73.1	76.8	82.3	87.6	88.9	90.4	92.9	96.0
77.5°	49.2	50.9	52.1	54.1	57.1	61.6	64.3	66.2	66.6	67.5	70.5
80°	39.1	39.9	41.2	42.7	43.9	47.7	49.2	51.1	51.7	52.7	54.2
82.5°	28.6	29.5	30.3	31.6	33.6	35.1	36.6	38.5	38.6	39.3	39.5
85°	16.7	17.0	16.4	17.0	17.4	17.9	19.5	21.0	20.8	20.5	21.4
87.5°	6.9	6.8	6.5	7.2	6.6	6.8	6.7	6.8	7.2	7.6	8.0
90°	4.9	4.6	4.0	3.8	3.2	2.9	2.3	1.7	1.1	0.6	0.3
92.5°	75.2	92.9	94.4	65.7	39.4	23.6	15.2	10.3	6.7	4.2	3.5
95°	249.8	255.3	208.3	128.8	65.4	34.6	21.6	15.2	12.1	9.8	9.5
97.5°	316.1	272.6	186.1	102.8	56.3	36.0	26.7	21.0	17.8	16.1	15.8
100°	332.2	260.2	166.0	93.4	55.9	39.2	30.6	25.0	21.9	20.7	20.1
102.5°	322.5	238.3	150.7	89.4	58.0	43.1	34.7	29.7	26.3	25.4	25.0
105°	291.6	208.9	136.0	87.9	62.2	49.6	41.5	36.9	34.0	32.5	32.5
107.5°	260.0	188.7	129.8	90.5	68.6	56.3	49.1	44.3	41.9	40.5	39.9
110°	242.1	179.2	127.9	93.1	73.2	61.4	53.9	49.6	47.0	45.8	45.2



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	228.7	173.7	127.9	96.3	77.5	66.2	58.9	54.6	52.0	51.1	50.5
115°	214.1	167.7	128.8	101.1	84.5	73.8	66.5	62.2	59.7	58.8	58.2
117.5°	205.4	164.8	130.7	106.6	91.5	81.4	74.4	69.5	66.9	66.0	65.1
120°	200.6	163.4	132.6	110.4	96.5	86.4	79.2	74.4	71.7	70.6	69.7
122.5°	196.4	162.2	134.1	114.5	101.3	91.3	84.1	78.8	76.1	75.2	74.6
125°	190.8	160.8	136.9	120.2	107.8	98.2	90.7	85.3	82.7	81.3	80.7
127.5°	185.6	160.1	139.9	125.3	113.9	104.8	97.3	91.5	88.1	86.3	85.4
130°	182.1	159.6	141.8	128.8	117.8	108.9	101.4	95.4	91.6	89.4	88.5
132.5°	179.4	159.6	143.8	131.8	121.6	112.6	105.1	98.8	94.7	91.9	90.7
135°	176.0	159.6	146.7	136.0	126.5	117.6	109.8	103.7	99.1	95.6	94.5
137.5°	173.1	160.0	149.3	139.1	130.0	121.9	113.9	107.9	103.3	100.1	99.2
140°	171.7	160.2	150.4	141.2	132.6	124.2	116.4	111.0	106.3	102.9	102.0
142.5°	170.6	160.5	151.1	142.4	134.1	126.3	119.0	113.7	109.1	105.8	105.3
145°	168.8	160.2	151.8	144.1	136.9	129.4	122.8	117.6	113.5	110.6	110.1
147.5°	167.1	159.5	152.1	145.1	138.6	132.0	126.2	121.7	118.0	115.4	115.1
150°	165.7	158.7	152.1	145.8	139.7	133.4	128.5	124.5	120.7	118.7	118.1
152.5°	164.0	157.8	151.9	146.3	140.9	135.0	130.6	126.8	123.5	121.7	121.4
155°	161.3	156.2	151.2	146.7	142.0	137.1	133.1	130.2	127.3	125.6	125.6
157.5°	158.8	154.4	150.5	146.9	143.0	138.8	135.7	133.2	130.8	129.4	129.5
160°	156.8	153.3	149.9	146.9	143.5	139.7	137.1	134.9	132.8	131.7	132.0
162.5°	154.9	151.9	149.1	146.8	144.0	140.6	138.5	136.7	134.9	133.8	134.0
165°	152.1	149.9	148.1	146.3	144.1	141.8	140.1	138.8	137.5	136.6	137.1
167.5°	149.4	147.8	146.5	145.7	144.1	142.2	141.0	140.2	139.5	138.9	139.3
170°	147.8	146.7	145.8	145.2	144.1	142.6	141.8	141.2	140.6	140.3	140.6
172.5°	146.2	145.3	144.9	144.8	143.8	142.6	142.2	141.9	141.3	141.0	141.5
175°	144.1	143.8	143.8	144.1	143.5	142.6	142.6	142.6	142.4	142.0	142.6
177.5°	143.2	142.9	142.9	143.4	143.2	142.7	142.7	142.9	142.7	142.7	143.2
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	758.1	760.4	763.6	767.4	770.3	773.6	775.3	775.3	776.7	780.0	784.2
5°	760.3	768.4	776.2	786.0	793.8	802.7	809.6	816.1	822.0	829.4	837.1
7.5°	759.7	773.1	787.0	802.7	819.9	833.6	847.6	858.7	869.5	883.8	895.0
10°	757.2	774.6	793.4	813.3	834.9	853.9	870.9	886.4	901.2	916.7	930.7
12.5°	752.8	774.9	797.9	821.7	849.1	870.7	892.7	909.2	926.5	943.5	960.7
15°	746.1	772.1	800.0	833.2	866.6	890.7	912.4	933.8	949.9	969.1	985.5
17.5°	732.3	765.8	800.9	837.1	869.2	897.3	920.0	940.4	957.5	978.6	1000.9
20°	724.1	760.3	796.9	835.6	866.3	895.0	917.0	938.1	959.4	987.1	1014.3
22.5°	712.7	751.4	790.2	827.0	859.3	887.1	909.9	935.6	963.7	995.0	1027.9
25°	694.7	734.7	773.1	808.0	839.6	868.1	899.1	933.8	967.8	1009.0	1056.4
27.5°	671.8	710.4	744.6	781.5	813.0	849.2	887.9	925.4	974.6	1031.3	1090.5
30°	654.7	691.3	723.8	758.8	794.4	834.4	877.8	922.0	980.6	1047.1	1117.4
32.5°	634.9	668.0	700.3	734.0	775.1	819.0	865.1	919.2	989.2	1064.9	1137.8
35°	600.5	630.2	661.5	699.0	742.7	790.4	849.2	915.2	999.7	1081.2	1146.6
37.5°	564.5	587.9	619.4	658.8	706.5	761.7	828.4	908.6	995.4	1068.5	1096.3
40°	536.7	558.7	591.8	633.3	680.4	740.9	815.8	898.1	985.5	1036.2	1034.1
42.5°	509.2	531.5	563.4	605.1	654.2	721.8	798.9	884.5	958.2	977.5	937.3
45°	467.0	487.8	519.1	561.2	613.8	684.8	765.9	848.0	895.0	863.8	783.9
47.5°	424.0	444.2	473.2	514.5	571.9	646.2	722.9	790.3	796.9	729.7	633.8
50°	395.8	414.7	442.3	486.2	542.0	614.5	688.5	741.4	725.0	642.9	544.1
52.5°	368.3	386.5	412.3	453.8	510.8	581.8	647.8	689.4	651.4	564.2	475.3
55°	327.7	345.0	371.0	409.1	460.8	525.9	583.8	599.0	543.2	455.3	383.4
57.5°	289.1	301.7	327.5	361.2	411.1	468.4	509.9	507.2	445.6	366.5	315.0
60°	263.6	275.0	299.5	330.4	377.8	429.3	458.4	446.0	383.8	318.4	268.8
62.5°	239.8	250.5	271.0	299.5	340.2	384.9	406.1	389.0	330.2	272.8	233.4
65°	203.8	211.6	228.0	254.3	286.2	317.2	336.1	311.0	258.9	215.6	185.8
67.5°	170.2	176.8	191.4	210.3	232.4	253.7	261.4	237.8	197.4	168.2	147.2
70°	148.4	154.6	164.4	182.1	196.7	211.8	215.6	194.5	160.8	138.4	125.4
72.5°	127.5	133.2	141.9	154.3	164.4	173.2	175.0	155.3	129.6	114.1	104.1
75°	97.3	102.2	107.8	112.4	119.0	120.5	119.8	104.7	90.7	80.6	74.9
77.5°	71.5	73.5	77.0	78.8	79.1	79.0	75.8	66.2	59.0	54.8	52.5
80°	55.1	56.7	57.6	58.2	58.5	55.4	52.0	46.1	43.7	41.2	38.4
82.5°	40.0	41.1	42.0	42.2	40.4	37.8	34.7	31.8	30.0	28.8	27.7
85°	21.7	22.0	21.7	20.1	17.9	17.0	16.4	15.8	15.5	15.2	15.2
87.5°	7.8	7.2	6.0	6.4	6.5	6.4	6.4	6.3	6.1	6.2	6.3
90°	0.6	1.1	1.7	2.3	2.9	3.2	3.8	4.0	4.6	4.9	5.2
92.5°	4.2	6.7	10.3	15.2	23.6	39.4	65.7	94.4	92.9	75.2	51.0
95°	9.8	12.1	15.2	21.6	34.6	65.4	128.8	208.3	255.3	249.8	207.2
97.5°	16.1	17.8	21.0	26.7	36.0	56.3	102.8	186.1	272.6	316.1	308.5
100°	20.7	21.9	25.0	30.6	39.2	55.9	93.4	166.0	260.2	332.2	354.4
102.5°	25.4	26.3	29.7	34.7	43.1	58.0	89.4	150.7	238.3	322.5	369.8
105°	32.5	34.0	36.9	41.5	49.6	62.2	87.9	136.0	208.9	291.6	360.8
107.5°	40.5	41.9	44.3	49.1	56.3	68.6	90.5	129.8	188.7	260.0	328.2
110°	45.8	47.0	49.6	53.9	61.4	73.2	93.1	127.9	179.2	242.1	304.3





TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	51.1	52.0	54.6	58.9	66.2	77.5	96.3	127.9	173.7	228.7	285.4
115°	58.8	59.7	62.2	66.5	73.8	84.5	101.1	128.8	167.7	214.1	261.6
117.5°	66.0	66.9	69.5	74.4	81.4	91.5	106.6	130.7	164.8	205.4	246.3
120°	70.6	71.7	74.4	79.2	86.4	96.5	110.4	132.6	163.4	200.6	238.0
122.5°	75.2	76.1	78.8	84.1	91.3	101.3	114.5	134.1	162.2	196.4	231.8
125°	81.3	82.7	85.3	90.7	98.2	107.8	120.2	136.9	160.8	190.8	222.7
127.5°	86.3	88.1	91.5	97.3	104.8	113.9	125.3	139.9	160.1	185.6	213.5
130°	89.4	91.6	95.4	101.4	108.9	117.8	128.8	141.8	159.6	182.1	207.7
132.5°	91.9	94.7	98.8	105.1	112.6	121.6	131.8	143.8	159.6	179.4	201.9
135°	95.6	99.1	103.7	109.8	117.6	126.5	136.0	146.7	159.6	176.0	194.5
137.5°	100.1	103.3	107.9	113.9	121.9	130.0	139.1	149.3	160.0	173.1	188.2
140°	102.9	106.3	111.0	116.4	124.2	132.6	141.2	150.4	160.2	171.7	184.7
142.5°	105.8	109.1	113.7	119.0	126.3	134.1	142.4	151.1	160.5	170.6	181.7
145°	110.6	113.5	117.6	122.8	129.4	136.9	144.1	151.8	160.2	168.8	177.8
147.5°	115.4	118.0	121.7	126.2	132.0	138.6	145.1	152.1	159.5	167.1	174.1
150°	118.7	120.7	124.5	128.5	133.4	139.7	145.8	152.1	158.7	165.7	172.0
152.5°	121.7	123.5	126.8	130.6	135.0	140.9	146.3	151.9	157.8	164.0	169.7
155°	125.6	127.3	130.2	133.1	137.1	142.0	146.7	151.2	156.2	161.3	166.2
157.5°	129.4	130.8	133.2	135.7	138.8	143.0	146.9	150.5	154.4	158.8	162.8
160°	131.7	132.8	134.9	137.1	139.7	143.5	146.9	149.9	153.3	156.8	160.5
162.5°	133.8	134.9	136.7	138.5	140.6	144.0	146.8	149.1	151.9	154.9	157.9
165°	136.6	137.5	138.8	140.1	141.8	144.1	146.3	148.1	149.9	152.1	154.4
167.5°	138.9	139.5	140.2	141.0	142.2	144.1	145.7	146.5	147.8	149.4	151.1
170°	140.3	140.6	141.2	141.8	142.6	144.1	145.2	145.8	146.7	147.8	149.3
172.5°	141.0	141.3	141.9	142.2	142.6	143.8	144.8	144.9	145.3	146.2	147.2
175°	142.0	142.4	142.6	142.6	142.6	143.5	144.1	143.8	143.8	144.1	145.0
177.5°	142.7	142.7	142.9	142.7	142.7	143.2	143.4	142.9	142.9	143.2	143.4
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	787.4	787.4	791.7	791.3	794.1	793.1	793.6
5°	846.4	851.7	856.3	859.4	864.1	865.4	864.7
7.5°	907.7	919.3	925.0	932.9	934.3	938.3	937.9
10°	945.5	957.0	965.6	972.5	975.9	980.2	980.6
12.5°	975.3	985.0	992.7	999.0	1003.1	1004.5	1005.3
15°	998.5	1009.3	1018.3	1027.3	1032.6	1036.6	1038.8
17.5°	1021.9	1038.6	1054.5	1066.7	1074.0	1080.2	1080.1
20°	1040.0	1059.2	1079.0	1093.0	1107.2	1113.4	1114.4
22.5°	1059.3	1088.7	1114.2	1135.8	1154.5	1161.0	1163.4
25°	1099.4	1137.8	1177.2	1207.5	1229.2	1241.9	1243.8
27.5°	1147.9	1200.0	1241.3	1269.3	1287.4	1296.7	1298.8
30°	1182.2	1230.1	1267.3	1288.4	1296.7	1298.0	1293.3
32.5°	1197.5	1233.4	1248.2	1247.0	1230.6	1219.7	1215.5
35°	1178.8	1171.3	1135.1	1091.7	1058.6	1037.5	1031.9
37.5°	1072.7	1008.6	941.9	876.4	841.6	823.9	793.4
40°	968.2	876.8	807.4	752.3	713.0	681.3	673.9
42.5°	850.2	755.9	686.5	639.3	607.9	586.2	576.8
45°	683.2	602.1	544.8	508.5	484.4	468.6	461.5
47.5°	546.4	483.6	441.9	415.1	396.6	382.9	379.1
50°	471.4	421.2	385.9	363.3	349.4	338.8	334.5
52.5°	409.4	368.9	341.8	323.2	310.0	303.4	299.8
55°	337.9	302.9	283.4	268.5	261.1	255.8	253.3
57.5°	276.3	251.0	236.8	226.5	219.6	216.3	215.1
60°	241.9	222.1	209.0	201.0	196.3	192.0	190.8
62.5°	211.4	195.8	185.7	178.7	174.1	172.2	171.5
65°	170.3	160.1	152.7	148.4	144.6	144.0	143.7
67.5°	135.4	129.4	125.5	121.0	119.7	117.5	117.1
70°	115.9	111.8	107.1	105.6	104.0	101.9	102.2
72.5°	98.2	94.2	91.1	89.0	88.5	87.6	88.3
75°	71.8	70.6	69.4	67.8	67.2	67.2	66.9
77.5°	51.3	50.2	48.8	47.9	47.8	46.5	47.0
80°	37.2	35.6	35.0	35.3	34.4	34.1	34.1
82.5°	27.5	26.9	26.3	26.4	26.2	25.9	26.2
85°	15.2	14.8	14.8	14.6	14.6	14.3	14.3
87.5°	6.5	6.8	6.4	6.2	6.2	6.5	6.8
90°	5.5	5.8	6.4	6.4	6.4	6.6	6.6
92.5°	37.0	27.9	23.6	20.0	19.2	18.8	18.3
95°	163.4	127.9	103.7	83.2	74.6	72.3	67.8
97.5°	277.9	243.3	209.6	191.8	175.7	167.4	163.6
100°	340.3	310.6	280.6	260.7	240.0	229.3	224.8
102.5°	378.5	364.4	344.1	322.8	308.0	296.4	293.0
105°	400.2	412.9	409.8	400.5	391.0	385.2	381.8
107.5°	380.9	413.4	428.5	433.2	433.2	431.2	428.9
110°	359.1	399.7	424.1	437.1	442.5	444.6	444.6



TEST NUMBER: P333522-930

CATALOG NUMBER: S125RDIP-S610D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	337.4	378.5	407.3	426.2	435.7	440.7	442.8
115°	306.3	345.8	377.2	399.7	413.4	421.5	425.3
117.5°	284.8	318.8	347.6	370.1	384.4	392.4	394.7
120°	272.6	304.3	329.6	351.0	364.8	372.6	374.9
122.5°	263.8	292.0	315.8	334.8	347.5	355.3	357.3
125°	252.1	277.2	297.9	314.1	325.9	332.2	335.1
127.5°	240.9	264.3	283.7	298.4	308.8	314.8	316.1
130°	233.1	255.6	274.3	288.7	298.2	304.0	305.7
132.5°	225.8	246.1	264.2	278.6	288.0	293.3	295.3
135°	214.3	232.8	249.2	262.0	271.4	276.6	278.3
137.5°	204.2	219.6	233.5	244.8	253.5	258.3	260.2
140°	198.2	211.5	223.6	234.2	241.7	246.1	247.5
142.5°	193.1	204.6	215.1	224.1	230.5	234.6	235.8
145°	186.7	195.7	203.4	210.3	215.2	218.4	219.6
147.5°	181.3	188.3	194.1	199.6	203.5	205.3	205.9
150°	178.4	183.8	189.0	193.3	196.8	198.0	198.2
152.5°	175.4	180.3	184.4	188.0	190.8	191.9	192.2
155°	170.9	174.9	178.1	180.9	183.0	183.8	184.1
157.5°	166.6	169.7	172.2	174.5	176.1	176.9	176.8
160°	163.4	166.2	168.3	170.3	171.7	172.3	172.0
162.5°	160.6	163.1	164.9	166.4	167.5	167.7	167.6
165°	156.5	158.2	159.6	160.8	161.3	161.3	161.3
167.5°	152.5	153.8	154.8	155.4	155.9	155.6	155.6
170°	150.1	151.0	151.6	152.1	152.5	152.5	152.1
172.5°	148.1	148.7	149.0	149.1	149.7	149.2	148.9
175°	145.0	145.5	145.5	145.5	145.8	145.2	145.0
177.5°	143.6	143.6	143.6	143.4	143.6	142.9	142.9
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9

(END OF REPORT)