

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333528-930

Luminaire Tested: **S125RDIP-S610D590U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333528-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D590U930-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3685.8 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	84	77	72	68	66	63	59	56	54	51	47	45	43	39
3	83	74	66	61	76	68	62	57	59	54	50	50	47	44	42	39	37	33
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	52	44	39	59	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	47	40	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4873	4873	4873	4873
5°	5606	4879	4309	4879
10°	6431	4854	3802	4854
15°	6946	4804	3380	4804
20°	7659	4746	3120	4746
25°	8863	4670	2895	4670
30°	9645	4589	2748	4589
35°	8136	4495	2613	4495
40°	5681	4326	2496	4326
45°	4215	4098	2382	4098
50°	3361	3861	2284	3861
55°	2852	3567	2197	3567
60°	2465	3304	2056	3304
65°	2196	3020	1771	3020
70°	1930	2766	1613	2766
75°	1669	2395	1515	2395
80°	1268	2016	1268	2016
85°	1060	1586	1193	1586



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	2.0
10°-20°	212.0	5.8
20°-30°	336.2	9.1
30°-40°	405.4	11.0
40°-50°	362.0	9.8
50°-60°	277.6	7.5
60°-70°	180.4	4.9
70°-80°	87.7	2.4
80°-90°	22.2	0.6
90°-100°	167.2	4.5
100°-110°	359.4	9.8
110°-120°	337.3	9.2
120°-130°	273.4	7.4
130°-140°	219.4	6.0
140°-150°	165.6	4.5
150°-160°	116.5	3.2
160°-170°	68.7	1.9
170°-180°	22.3	0.6
0°-30°	620.5	16.8
0°-40°	1025.9	27.8
0°-60°	1665.6	45.2
0°-90°	1955.9	53.1
90°-120°	864.0	23.4
90°-150°	1522.3	41.3
90°-180°	1730.0	46.9
0°-180°	3685.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	754	754	754	754	754	
5°	865	753	665	753	865	86
15°	1039	718	506	718	1039	298
25°	1244	655	406	655	1244	571
35°	1032	570	331	570	1032	623
45°	462	449	261	449	462	368
55°	253	317	195	317	253	230
65°	144	198	116	198	144	143
75°	67	96	61	96	67	71
85°	14	21	16	21	14	17
90°	11	0	11	0	11	8
95°	109	15	109	15	109	155
105°	616	53	616	53	616	613
115°	686	94	686	94	686	671
125°	541	130	541	130	541	489
135°	449	152	449	152	449	348
145°	354	178	354	178	354	225
155°	297	203	297	203	297	139
165°	260	221	260	221	260	74
175°	234	230	234	230	234	23
180°	231	231	231	231	231	



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	793.6	793.1	794.1	791.3	791.7	787.4	787.4	784.2	780.0	776.7	775.3
5°	864.7	865.4	864.1	859.4	856.3	851.7	846.4	837.1	829.4	822.0	816.1
7.5°	937.9	938.3	934.3	932.9	925.0	919.3	907.7	895.0	883.8	869.5	858.7
10°	980.6	980.2	975.9	972.5	965.6	957.0	945.5	930.7	916.7	901.2	886.4
12.5°	1005.3	1004.5	1003.1	999.0	992.7	985.0	975.3	960.7	943.5	926.5	909.2
15°	1038.8	1036.6	1032.6	1027.3	1018.3	1009.3	998.5	985.5	969.1	949.9	933.8
17.5°	1080.1	1080.2	1074.0	1066.7	1054.5	1038.6	1021.9	1000.9	978.6	957.5	940.4
20°	1114.4	1113.4	1107.2	1093.0	1079.0	1059.2	1040.0	1014.3	987.1	959.4	938.1
22.5°	1163.4	1161.0	1154.5	1135.8	1114.2	1088.7	1059.3	1027.9	995.0	963.7	935.6
25°	1243.8	1241.9	1229.2	1207.5	1177.2	1137.8	1099.4	1056.4	1009.0	967.8	933.8
27.5°	1298.8	1296.7	1287.4	1269.3	1241.3	1200.0	1147.9	1090.5	1031.3	974.6	925.4
30°	1293.3	1298.0	1296.7	1288.4	1267.3	1230.1	1182.2	1117.4	1047.1	980.6	922.0
32.5°	1215.5	1219.7	1230.6	1247.0	1248.2	1233.4	1197.5	1137.8	1064.9	989.2	919.2
35°	1031.9	1037.5	1058.6	1091.7	1135.1	1171.3	1178.8	1146.6	1081.2	999.7	915.2
37.5°	793.4	823.9	841.6	876.4	941.9	1008.6	1072.7	1096.3	1068.5	995.4	908.6
40°	673.9	681.3	713.0	752.3	807.4	876.8	968.2	1034.1	1036.2	985.5	898.1
42.5°	576.8	586.2	607.9	639.3	686.5	755.9	850.2	937.3	977.5	958.2	884.5
45°	461.5	468.6	484.4	508.5	544.8	602.1	683.2	783.9	863.8	895.0	848.0
47.5°	379.1	382.9	396.6	415.1	441.9	483.6	546.4	633.8	729.7	796.9	790.3
50°	334.5	338.8	349.4	363.3	385.9	421.2	471.4	544.1	642.9	725.0	741.4
52.5°	299.8	303.4	310.0	323.2	341.8	368.9	409.4	475.3	564.2	651.4	689.4
55°	253.3	255.8	261.1	268.5	283.4	302.9	337.9	383.4	455.3	543.2	599.0
57.5°	215.1	216.3	219.6	226.5	236.8	251.0	276.3	315.0	366.5	445.6	507.2
60°	190.8	192.0	196.3	201.0	209.0	222.1	241.9	268.8	318.4	383.8	446.0
62.5°	171.5	172.2	174.1	178.7	185.7	195.8	211.4	233.4	272.8	330.2	389.0
65°	143.7	144.0	144.6	148.4	152.7	160.1	170.3	185.8	215.6	258.9	311.0
67.5°	117.1	117.5	119.7	121.0	125.5	129.4	135.4	147.2	168.2	197.4	237.8
70°	102.2	101.9	104.0	105.6	107.1	111.8	115.9	125.4	138.4	160.8	194.5
72.5°	88.3	87.6	88.5	89.0	91.1	94.2	98.2	104.1	114.1	129.6	155.3
75°	66.9	67.2	67.2	67.8	69.4	70.6	71.8	74.9	80.6	90.7	104.7
77.5°	47.0	46.5	47.8	47.9	48.8	50.2	51.3	52.5	54.8	59.0	66.2
80°	34.1	34.1	34.4	35.3	35.0	35.6	37.2	38.4	41.2	43.7	46.1
82.5°	26.2	25.9	26.2	26.4	26.3	26.9	27.5	27.7	28.8	30.0	31.8
85°	14.3	14.3	14.6	14.6	14.8	14.8	15.2	15.2	15.2	15.5	15.8
87.5°	7.6	7.3	7.0	7.0	7.3	7.6	7.3	6.8	6.8	6.7	6.8
90°	10.7	10.7	10.2	10.2	10.2	9.3	8.8	8.4	7.9	7.4	6.5
92.5°	29.7	30.4	31.1	32.2	38.2	45.0	59.8	82.4	121.4	149.9	152.4
95°	109.3	116.8	120.4	134.4	167.5	206.5	263.7	334.4	403.2	412.1	336.2
97.5°	264.2	270.1	283.6	309.7	338.3	392.7	448.4	498.0	510.2	440.0	300.3
100°	362.7	370.2	387.4	420.9	453.0	501.3	549.3	572.0	536.2	420.0	267.9
102.5°	472.9	478.5	497.2	521.0	555.3	588.0	611.0	597.0	520.6	384.6	243.3
105°	616.2	621.8	631.1	646.5	661.3	666.4	646.0	582.3	470.7	337.2	219.5
107.5°	692.3	696.0	699.1	699.2	691.6	667.4	614.8	529.8	419.7	304.5	209.5
110°	717.6	717.6	714.4	705.5	684.6	645.1	579.5	491.1	390.7	289.3	206.5



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	714.6	711.3	703.2	688.0	657.5	610.8	544.5	460.6	369.1	280.4	206.5
115°	686.5	680.4	667.4	645.1	608.8	558.1	494.4	422.2	345.5	270.7	207.9
117.5°	637.1	633.3	620.4	597.4	561.1	514.5	459.7	397.5	331.5	266.0	210.9
120°	605.0	601.4	588.8	566.5	532.1	491.1	439.9	384.2	323.7	263.7	213.9
122.5°	576.7	573.4	560.8	540.4	509.7	471.4	425.8	374.1	317.0	261.9	216.5
125°	540.9	536.2	526.0	507.0	480.9	447.4	406.9	359.5	307.9	259.5	220.9
127.5°	510.2	508.1	498.5	481.6	458.0	426.6	388.9	344.6	299.5	258.4	225.8
130°	493.4	490.6	481.4	466.0	442.7	412.5	376.3	335.3	293.9	257.6	228.9
132.5°	476.7	473.5	465.0	449.6	426.4	397.3	364.4	326.0	289.4	257.6	232.2
135°	449.2	446.5	438.1	422.7	402.3	375.8	346.0	313.9	284.1	257.6	236.7
137.5°	420.0	416.9	409.2	395.2	376.9	354.4	329.6	303.7	279.4	258.2	240.9
140°	399.5	397.1	390.2	378.1	360.9	341.4	320.0	298.1	277.2	258.6	242.8
142.5°	380.5	378.5	371.9	361.7	347.2	330.2	311.8	293.3	275.3	258.9	243.9
145°	354.4	352.5	347.4	339.5	328.3	315.8	301.3	287.0	272.6	258.6	245.1
147.5°	332.2	331.4	328.4	322.1	313.2	303.8	292.7	281.0	269.6	257.4	245.6
150°	320.0	319.5	317.6	312.1	305.1	296.7	287.9	277.6	267.4	256.2	245.6
152.5°	310.3	309.8	307.9	303.5	297.7	291.1	283.1	273.9	264.8	254.8	245.2
155°	297.2	296.7	295.3	292.0	287.4	282.3	275.8	268.3	260.4	252.1	244.2
157.5°	285.4	285.5	284.2	281.5	277.9	273.9	268.9	262.8	256.3	249.2	243.0
160°	277.6	278.1	277.2	274.8	271.6	268.3	263.7	259.0	253.0	247.4	241.8
162.5°	270.6	270.7	270.5	268.6	266.0	263.1	259.3	254.9	250.1	245.2	240.8
165°	260.4	260.4	260.4	259.5	257.6	255.4	252.5	249.2	245.6	241.8	239.0
167.5°	251.1	251.2	251.6	250.8	249.8	248.2	246.1	243.9	241.2	238.6	236.4
170°	245.6	246.1	246.1	245.6	244.6	243.7	242.3	240.9	238.6	236.7	235.3
172.5°	240.4	240.8	241.6	240.8	240.5	239.9	239.0	237.6	235.9	234.5	233.8
175°	233.9	234.4	235.3	234.9	234.9	234.9	233.9	233.9	232.5	232.0	232.0
177.5°	230.6	230.6	231.8	231.4	231.8	231.8	231.8	231.4	231.1	230.6	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	775.3	773.6	770.3	767.4	763.6	760.4	758.1	755.5	752.0	747.8	744.3
5°	809.6	802.7	793.8	786.0	776.2	768.4	760.3	752.6	744.9	734.9	726.3
7.5°	847.6	833.6	819.9	802.7	787.0	773.1	759.7	746.2	732.9	718.8	705.2
10°	870.9	853.9	834.9	813.3	793.4	774.6	757.2	740.2	722.3	706.5	689.4
12.5°	892.7	870.7	849.1	821.7	797.9	774.9	752.8	731.6	712.3	691.9	673.5
15°	912.4	890.7	866.6	833.2	800.0	772.1	746.1	718.5	694.7	671.7	651.3
17.5°	920.0	897.3	869.2	837.1	800.9	765.8	732.3	702.1	674.0	647.3	624.3
20°	917.0	895.0	866.3	835.6	796.9	760.3	724.1	690.6	659.3	631.2	606.7
22.5°	909.9	887.1	859.3	827.0	790.2	751.4	712.7	677.0	644.2	615.1	588.4
25°	899.1	868.1	839.6	808.0	773.1	734.7	694.7	655.3	620.4	590.6	561.5
27.5°	887.9	849.2	813.0	781.5	744.6	710.4	671.8	631.5	594.7	564.4	534.6
30°	877.8	834.4	794.4	758.8	723.8	691.3	654.7	615.4	577.6	546.3	516.0
32.5°	865.1	819.0	775.1	734.0	700.3	668.0	634.9	597.3	560.5	528.2	497.4
35°	849.2	790.4	742.7	699.0	661.5	630.2	600.5	570.1	533.3	499.9	469.9
37.5°	828.4	761.7	706.5	658.8	619.4	587.9	564.5	536.7	503.1	471.1	443.2
40°	815.8	740.9	680.4	633.3	591.8	558.7	536.7	513.1	482.5	452.5	424.6
42.5°	798.9	721.8	654.2	605.1	563.4	531.5	509.2	488.7	462.9	434.6	404.8
45°	765.9	684.8	613.8	561.2	519.1	487.8	467.0	448.7	429.3	403.2	377.2
47.5°	722.9	646.2	571.9	514.5	473.2	444.2	424.0	409.6	395.7	373.6	348.3
50°	688.5	614.5	542.0	486.2	442.3	414.7	395.8	384.3	371.6	351.6	330.4
52.5°	647.8	581.8	510.8	453.8	412.3	386.5	368.3	356.9	346.3	330.0	309.9
55°	583.8	525.9	460.8	409.1	371.0	345.0	327.7	316.8	310.6	296.7	280.9
57.5°	509.9	468.4	411.1	361.2	327.5	301.7	289.1	279.9	272.9	263.0	251.8
60°	458.4	429.3	377.8	330.4	299.5	275.0	263.6	255.8	249.3	240.9	232.3
62.5°	406.1	384.9	340.2	299.5	271.0	250.5	239.8	232.8	225.3	219.6	211.2
65°	336.1	317.2	286.2	254.3	228.0	211.6	203.8	197.6	193.0	186.8	180.8
67.5°	261.4	253.7	232.4	210.3	191.4	176.8	170.2	165.8	160.2	156.5	152.5
70°	215.6	211.8	196.7	182.1	164.4	154.6	148.4	146.5	139.7	136.0	133.1
72.5°	175.0	173.2	164.4	154.3	141.9	133.2	127.5	125.4	121.1	118.1	116.3
75°	119.8	120.5	119.0	112.4	107.8	102.2	97.3	96.0	92.9	90.4	88.9
77.5°	75.8	79.0	79.1	78.8	77.0	73.5	71.5	70.5	67.5	66.6	66.2
80°	52.0	55.4	58.5	58.2	57.6	56.7	55.1	54.2	52.7	51.7	51.1
82.5°	34.7	37.8	40.4	42.2	42.0	41.1	40.0	39.5	39.3	38.6	38.5
85°	16.4	17.0	17.9	20.1	21.7	22.0	21.7	21.4	20.5	20.8	21.0
87.5°	6.9	6.7	6.8	6.7	6.3	7.3	7.8	8.0	7.6	7.3	7.0
90°	6.0	5.1	4.6	3.8	2.8	1.9	0.9	0.5	0.9	1.9	2.8
92.5°	106.2	63.5	38.2	24.5	16.6	10.8	6.8	5.7	6.8	10.8	16.6
95°	207.9	105.6	55.8	34.9	24.6	19.6	15.8	15.3	15.8	19.6	24.6
97.5°	165.9	91.0	58.0	43.0	33.8	28.6	26.0	25.5	26.0	28.6	33.8
100°	150.7	90.3	63.3	49.3	40.4	35.4	33.5	32.5	33.5	35.4	40.4
102.5°	144.4	93.6	69.5	56.0	47.9	42.4	40.9	40.4	40.9	42.4	47.9
105°	141.9	100.4	80.0	66.9	59.5	54.9	52.6	52.6	52.6	54.9	59.5
107.5°	146.1	110.7	90.9	79.2	71.4	67.6	65.4	64.5	65.4	67.6	71.4
110°	150.2	118.1	99.1	87.0	80.0	75.8	73.9	73.1	73.9	75.8	80.0



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	155.4	125.2	106.9	95.1	88.2	84.0	82.5	81.6	82.5	84.0	88.2
115°	163.2	136.2	119.0	107.5	100.4	96.3	94.9	93.9	94.9	96.3	100.4
117.5°	172.2	147.7	131.3	120.1	112.2	108.0	106.5	105.1	106.5	108.0	112.2
120°	178.1	155.8	139.5	127.9	120.0	115.8	114.0	112.5	114.0	115.8	120.0
122.5°	184.8	163.6	147.3	135.7	127.0	122.9	121.4	120.3	121.4	122.9	127.0
125°	194.0	173.9	158.6	146.5	137.6	133.5	131.2	130.2	131.2	133.5	137.6
127.5°	202.3	183.8	169.1	157.0	147.7	142.4	139.3	137.9	139.3	142.4	147.7
130°	207.9	190.2	175.8	163.7	153.9	147.9	144.1	142.8	144.1	147.9	153.9
132.5°	212.7	196.2	181.7	169.7	159.6	152.7	148.3	146.5	148.3	152.7	159.6
135°	219.5	204.2	189.7	177.2	167.5	160.0	154.4	152.5	154.4	160.0	167.5
137.5°	224.5	209.9	196.7	183.8	174.2	166.8	161.6	160.2	161.6	166.8	174.2
140°	227.9	213.9	200.5	187.9	179.0	171.6	166.0	164.6	166.0	171.6	179.0
142.5°	229.8	216.5	203.8	192.0	183.5	176.1	170.9	169.8	170.9	176.1	183.5
145°	232.5	220.9	208.8	198.1	189.7	183.2	178.6	177.7	178.6	183.2	189.7
147.5°	234.2	223.7	213.1	203.7	196.4	190.4	186.4	185.8	186.4	190.4	196.4
150°	235.3	225.6	215.3	207.4	200.9	194.9	191.6	190.7	191.6	194.9	200.9
152.5°	236.0	227.4	217.9	210.8	204.6	199.3	196.4	195.9	196.4	199.3	204.6
155°	236.7	229.3	221.4	214.8	210.2	205.5	202.8	202.8	202.8	205.5	210.2
157.5°	237.2	230.9	224.0	219.2	215.1	211.1	208.8	208.9	208.8	211.1	215.1
160°	237.2	231.6	225.6	221.4	217.7	214.4	212.5	213.0	212.5	214.4	217.7
162.5°	236.8	232.4	227.1	223.6	220.6	217.8	215.9	216.4	215.9	217.8	220.6
165°	236.3	232.5	228.9	226.0	224.1	221.8	220.5	221.4	220.5	221.8	224.1
167.5°	235.1	232.5	229.4	227.7	226.4	225.1	224.3	224.7	224.3	225.1	226.4
170°	234.4	232.5	230.2	228.9	227.9	227.0	226.5	227.0	226.5	227.0	227.9
172.5°	233.7	232.2	230.2	229.6	229.0	228.0	227.6	228.4	227.6	228.0	229.0
175°	232.5	231.6	230.2	230.2	230.2	229.8	229.3	230.2	229.3	229.8	230.2
177.5°	231.4	231.1	230.3	230.3	230.6	230.3	230.3	231.1	230.3	230.3	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	741.8	738.3	735.9	730.9	727.4	725.9	723.3	722.5	725.2	723.3	723.0
5°	719.7	710.8	703.7	696.5	688.8	683.9	676.4	675.1	673.3	670.5	669.9
7.5°	693.3	681.6	672.5	660.6	650.4	642.2	632.9	628.5	626.1	622.5	617.7
10°	675.5	661.5	649.1	637.4	624.7	614.5	605.2	598.0	593.4	589.1	587.2
12.5°	657.9	643.7	627.9	613.6	599.4	587.9	577.6	573.0	567.9	562.8	558.5
15°	630.6	611.6	594.4	577.9	565.8	553.4	543.6	536.7	529.0	526.8	518.4
17.5°	601.6	583.0	562.7	545.4	531.5	517.8	507.0	499.2	493.3	485.3	481.5
20°	583.5	561.5	541.7	525.9	510.4	494.3	483.1	476.6	471.1	464.6	461.5
22.5°	564.2	542.7	522.4	503.9	488.1	472.2	464.3	457.5	451.3	445.2	441.2
25°	535.8	514.1	492.8	473.5	457.1	445.6	436.3	428.6	425.3	419.3	415.0
27.5°	507.8	484.7	462.5	443.4	430.5	419.1	411.6	405.4	399.3	394.1	390.4
30°	489.7	466.1	442.0	426.8	413.1	402.4	394.0	388.1	383.4	378.8	376.0
32.5°	471.6	447.3	425.8	409.4	396.6	387.2	378.6	372.9	368.0	362.9	359.6
35°	442.5	417.8	400.5	384.3	371.6	363.0	357.1	349.0	345.0	341.3	337.9
37.5°	415.6	392.6	373.8	359.7	348.7	340.1	332.5	328.1	323.2	319.8	317.0
40°	395.8	374.7	357.8	342.8	334.8	325.2	318.0	312.5	308.8	304.4	301.3
42.5°	378.0	358.4	341.9	328.5	318.5	310.3	303.5	297.9	293.2	290.1	287.5
45°	352.8	333.2	317.2	304.8	295.5	287.7	280.6	277.8	271.6	267.9	266.7
47.5°	326.7	309.2	293.7	282.3	272.7	265.4	258.7	253.1	249.6	246.0	244.0
50°	309.1	292.4	277.8	266.7	257.4	249.3	243.1	239.4	234.7	231.4	228.9
52.5°	291.5	276.0	261.5	250.8	242.7	234.7	227.8	224.0	219.6	217.4	215.7
55°	266.4	250.0	237.6	227.0	218.7	211.2	204.7	201.0	198.2	196.1	195.4
57.5°	237.8	224.9	213.4	203.8	195.2	188.2	182.5	179.0	176.5	176.2	174.3
60°	219.2	207.5	197.0	186.8	179.3	172.8	167.9	163.9	161.3	161.0	160.5
62.5°	200.7	189.4	179.6	170.6	164.0	157.7	153.0	148.5	147.0	145.4	144.1
65°	173.1	162.9	154.8	147.7	140.6	135.3	130.7	127.9	124.5	122.6	119.3
67.5°	146.0	138.1	130.4	124.4	118.8	113.8	110.0	105.8	103.5	102.0	99.5
70°	128.2	122.1	114.3	107.8	103.5	99.4	96.3	91.6	90.1	88.9	87.6
72.5°	111.4	105.9	99.4	94.2	89.8	86.0	82.4	80.3	78.8	77.5	76.7
75°	87.6	82.3	76.8	73.1	70.0	66.9	65.1	63.5	62.9	62.5	61.3
77.5°	64.3	61.6	57.1	54.1	52.1	50.9	49.2	48.3	48.3	47.0	46.6
80°	49.2	47.7	43.9	42.7	41.2	39.9	39.1	37.5	36.0	35.3	34.4
82.5°	36.6	35.1	33.6	31.6	30.3	29.5	28.6	28.0	28.2	27.4	26.9
85°	19.5	17.9	17.4	17.0	16.4	17.0	16.7	16.4	16.1	15.8	16.1
87.5°	6.9	7.1	6.9	7.7	7.0	7.4	7.5	7.3	7.5	7.6	7.5
90°	3.8	4.6	5.1	6.0	6.5	7.4	7.9	8.4	8.8	9.3	10.2
92.5°	24.5	38.2	63.5	106.2	152.4	149.9	121.4	82.4	59.8	45.0	38.2
95°	34.9	55.8	105.6	207.9	336.2	412.1	403.2	334.4	263.7	206.5	167.5
97.5°	43.0	58.0	91.0	165.9	300.3	440.0	510.2	498.0	448.4	392.7	338.3
100°	49.3	63.3	90.3	150.7	267.9	420.0	536.2	572.0	549.3	501.3	453.0
102.5°	56.0	69.5	93.6	144.4	243.3	384.6	520.6	597.0	611.0	588.0	555.3
105°	66.9	80.0	100.4	141.9	219.5	337.2	470.7	582.3	646.0	666.4	661.3
107.5°	79.2	90.9	110.7	146.1	209.5	304.5	419.7	529.8	614.8	667.4	691.6
110°	87.0	99.1	118.1	150.2	206.5	289.3	390.7	491.1	579.5	645.1	684.6



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	95.1	106.9	125.2	155.4	206.5	280.4	369.1	460.6	544.5	610.8	657.5
115°	107.5	119.0	136.2	163.2	207.9	270.7	345.5	422.2	494.4	558.1	608.8
117.5°	120.1	131.3	147.7	172.2	210.9	266.0	331.5	397.5	459.7	514.5	561.1
120°	127.9	139.5	155.8	178.1	213.9	263.7	323.7	384.2	439.9	491.1	532.1
122.5°	135.7	147.3	163.6	184.8	216.5	261.9	317.0	374.1	425.8	471.4	509.7
125°	146.5	158.6	173.9	194.0	220.9	259.5	307.9	359.5	406.9	447.4	480.9
127.5°	157.0	169.1	183.8	202.3	225.8	258.4	299.5	344.6	388.9	426.6	458.0
130°	163.7	175.8	190.2	207.9	228.9	257.6	293.9	335.3	376.3	412.5	442.7
132.5°	169.7	181.7	196.2	212.7	232.2	257.6	289.4	326.0	364.4	397.3	426.4
135°	177.2	189.7	204.2	219.5	236.7	257.6	284.1	313.9	346.0	375.8	402.3
137.5°	183.8	196.7	209.9	224.5	240.9	258.2	279.4	303.7	329.6	354.4	376.9
140°	187.9	200.5	213.9	227.9	242.8	258.6	277.2	298.1	320.0	341.4	360.9
142.5°	192.0	203.8	216.5	229.8	243.9	258.9	275.3	293.3	311.8	330.2	347.2
145°	198.1	208.8	220.9	232.5	245.1	258.6	272.6	287.0	301.3	315.8	328.3
147.5°	203.7	213.1	223.7	234.2	245.6	257.4	269.6	281.0	292.7	303.8	313.2
150°	207.4	215.3	225.6	235.3	245.6	256.2	267.4	277.6	287.9	296.7	305.1
152.5°	210.8	217.9	227.4	236.0	245.2	254.8	264.8	273.9	283.1	291.1	297.7
155°	214.8	221.4	229.3	236.7	244.2	252.1	260.4	268.3	275.8	282.3	287.4
157.5°	219.2	224.0	230.9	237.2	243.0	249.2	256.3	262.8	268.9	273.9	277.9
160°	221.4	225.6	231.6	237.2	241.8	247.4	253.0	259.0	263.7	268.3	271.6
162.5°	223.6	227.1	232.4	236.8	240.8	245.2	250.1	254.9	259.3	263.1	266.0
165°	226.0	228.9	232.5	236.3	239.0	241.8	245.6	249.2	252.5	255.4	257.6
167.5°	227.7	229.4	232.5	235.1	236.4	238.6	241.2	243.9	246.1	248.2	249.8
170°	228.9	230.2	232.5	234.4	235.3	236.7	238.6	240.9	242.3	243.7	244.6
172.5°	229.6	230.2	232.2	233.7	233.8	234.5	235.9	237.6	239.0	239.9	240.5
175°	230.2	230.2	231.6	232.5	232.0	232.0	232.5	233.9	233.9	234.9	234.9
177.5°	230.3	230.3	231.1	231.4	230.6	230.6	231.1	231.4	231.8	231.8	231.8
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	722.8	720.0	719.3	720.2	719.3	720.0	722.8	723.0	723.3	725.2	722.5
5°	666.8	663.7	665.3	664.6	665.3	663.7	666.8	669.9	670.5	673.3	675.1
7.5°	617.6	613.8	609.7	611.0	609.7	613.8	617.6	617.7	622.5	626.1	628.5
10°	583.2	580.1	578.2	579.8	578.2	580.1	583.2	587.2	589.1	593.4	598.0
12.5°	554.2	552.4	550.7	550.1	550.7	552.4	554.2	558.5	562.8	567.9	573.0
15°	514.7	511.0	509.5	505.5	509.5	511.0	514.7	518.4	526.8	529.0	536.7
17.5°	478.3	477.1	473.1	471.4	473.1	477.1	478.3	481.5	485.3	493.3	499.2
20°	456.8	455.6	451.6	454.0	451.6	455.6	456.8	461.5	464.6	471.1	476.6
22.5°	439.0	436.3	435.0	434.2	435.0	436.3	439.0	441.2	445.2	451.3	457.5
25°	413.8	409.8	408.2	406.3	408.2	409.8	413.8	415.0	419.3	425.3	428.6
27.5°	388.7	386.5	384.4	383.9	384.4	386.5	388.7	390.4	394.1	399.3	405.4
30°	372.3	370.1	368.5	368.5	368.5	370.1	372.3	376.0	378.8	383.4	388.1
32.5°	357.7	356.0	354.4	354.2	354.4	356.0	357.7	359.6	362.9	368.0	372.9
35°	336.3	333.9	333.2	331.4	333.2	333.9	336.3	337.9	341.3	345.0	349.0
37.5°	314.2	312.2	312.1	311.9	312.1	312.2	314.2	317.0	319.8	323.2	328.1
40°	300.1	298.6	298.2	296.1	298.2	298.6	300.1	301.3	304.4	308.8	312.5
42.5°	285.0	284.2	283.2	282.2	283.2	284.2	285.0	287.5	290.1	293.2	297.9
45°	264.5	262.4	262.4	260.8	262.4	262.4	264.5	266.7	267.9	271.6	277.8
47.5°	243.3	241.7	241.8	240.2	241.8	241.7	243.3	244.0	246.0	249.6	253.1
50°	229.2	228.3	228.0	227.3	228.0	228.3	229.2	228.9	231.4	234.7	239.4
52.5°	215.1	214.7	215.8	214.4	215.8	214.7	215.1	215.7	217.4	219.6	224.0
55°	196.1	195.1	197.0	195.1	197.0	195.1	196.1	195.4	196.1	198.2	201.0
57.5°	174.1	173.3	175.0	174.1	175.0	173.3	174.1	174.3	176.2	176.5	179.0
60°	159.8	157.9	158.9	159.2	158.9	157.9	159.8	160.5	161.0	161.3	163.9
62.5°	142.7	141.6	142.3	140.9	142.3	141.6	142.7	144.1	145.4	147.0	148.5
65°	118.6	117.7	116.4	115.9	116.4	117.7	118.6	119.3	122.6	124.5	127.9
67.5°	99.6	97.4	97.3	97.8	97.3	97.4	99.6	99.5	102.0	103.5	105.8
70°	85.8	85.8	85.4	85.4	85.4	85.8	85.8	87.6	88.9	90.1	91.6
72.5°	76.1	75.9	75.3	75.1	75.3	75.9	76.1	76.7	77.5	78.8	80.3
75°	61.3	61.6	61.0	60.7	61.0	61.6	61.3	61.3	62.5	62.9	63.5
77.5°	45.2	43.9	44.7	43.9	44.7	43.9	45.2	46.6	47.0	48.3	48.3
80°	34.4	34.1	35.0	34.1	35.0	34.1	34.4	34.4	35.3	36.0	37.5
82.5°	27.2	26.9	27.3	26.7	27.3	26.9	27.2	26.9	27.4	28.2	28.0
85°	16.4	16.1	15.8	16.1	15.8	16.1	16.4	16.1	15.8	16.1	16.4
87.5°	7.7	7.5	7.6	7.6	7.6	7.5	7.7	7.5	7.6	7.5	7.3
90°	10.2	10.2	10.7	10.7	10.7	10.2	10.2	10.2	9.3	8.8	8.4
92.5°	32.2	31.1	30.4	29.7	30.4	31.1	32.2	38.2	45.0	59.8	82.4
95°	134.4	120.4	116.8	109.3	116.8	120.4	134.4	167.5	206.5	263.7	334.4
97.5°	309.7	283.6	270.1	264.2	270.1	283.6	309.7	338.3	392.7	448.4	498.0
100°	420.9	387.4	370.2	362.7	370.2	387.4	420.9	453.0	501.3	549.3	572.0
102.5°	521.0	497.2	478.5	472.9	478.5	497.2	521.0	555.3	588.0	611.0	597.0
105°	646.5	631.1	621.8	616.2	621.8	631.1	646.5	661.3	666.4	646.0	582.3
107.5°	699.2	699.1	696.0	692.3	696.0	699.1	699.2	691.6	667.4	614.8	529.8
110°	705.5	714.4	717.6	717.6	717.6	714.4	705.5	684.6	645.1	579.5	491.1



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	688.0	703.2	711.3	714.6	711.3	703.2	688.0	657.5	610.8	544.5	460.6
115°	645.1	667.4	680.4	686.5	680.4	667.4	645.1	608.8	558.1	494.4	422.2
117.5°	597.4	620.4	633.3	637.1	633.3	620.4	597.4	561.1	514.5	459.7	397.5
120°	566.5	588.8	601.4	605.0	601.4	588.8	566.5	532.1	491.1	439.9	384.2
122.5°	540.4	560.8	573.4	576.7	573.4	560.8	540.4	509.7	471.4	425.8	374.1
125°	507.0	526.0	536.2	540.9	536.2	526.0	507.0	480.9	447.4	406.9	359.5
127.5°	481.6	498.5	508.1	510.2	508.1	498.5	481.6	458.0	426.6	388.9	344.6
130°	466.0	481.4	490.6	493.4	490.6	481.4	466.0	442.7	412.5	376.3	335.3
132.5°	449.6	465.0	473.5	476.7	473.5	465.0	449.6	426.4	397.3	364.4	326.0
135°	422.7	438.1	446.5	449.2	446.5	438.1	422.7	402.3	375.8	346.0	313.9
137.5°	395.2	409.2	416.9	420.0	416.9	409.2	395.2	376.9	354.4	329.6	303.7
140°	378.1	390.2	397.1	399.5	397.1	390.2	378.1	360.9	341.4	320.0	298.1
142.5°	361.7	371.9	378.5	380.5	378.5	371.9	361.7	347.2	330.2	311.8	293.3
145°	339.5	347.4	352.5	354.4	352.5	347.4	339.5	328.3	315.8	301.3	287.0
147.5°	322.1	328.4	331.4	332.2	331.4	328.4	322.1	313.2	303.8	292.7	281.0
150°	312.1	317.6	319.5	320.0	319.5	317.6	312.1	305.1	296.7	287.9	277.6
152.5°	303.5	307.9	309.8	310.3	309.8	307.9	303.5	297.7	291.1	283.1	273.9
155°	292.0	295.3	296.7	297.2	296.7	295.3	292.0	287.4	282.3	275.8	268.3
157.5°	281.5	284.2	285.5	285.4	285.5	284.2	281.5	277.9	273.9	268.9	262.8
160°	274.8	277.2	278.1	277.6	278.1	277.2	274.8	271.6	268.3	263.7	259.0
162.5°	268.6	270.5	270.7	270.6	270.7	270.5	268.6	266.0	263.1	259.3	254.9
165°	259.5	260.4	260.4	260.4	260.4	260.4	259.5	257.6	255.4	252.5	249.2
167.5°	250.8	251.6	251.2	251.1	251.2	251.6	250.8	249.8	248.2	246.1	243.9
170°	245.6	246.1	246.1	245.6	246.1	246.1	245.6	244.6	243.7	242.3	240.9
172.5°	240.8	241.6	240.8	240.4	240.8	241.6	240.8	240.5	239.9	239.0	237.6
175°	234.9	235.3	234.4	233.9	234.4	235.3	234.9	234.9	234.9	233.9	233.9
177.5°	231.4	231.8	230.6	230.6	230.6	231.8	231.4	231.8	231.8	231.8	231.4
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	723.3	725.9	727.4	730.9	735.9	738.3	741.8	744.3	747.8	752.0	755.5
5°	676.4	683.9	688.8	696.5	703.7	710.8	719.7	726.3	734.9	744.9	752.6
7.5°	632.9	642.2	650.4	660.6	672.5	681.6	693.3	705.2	718.8	732.9	746.2
10°	605.2	614.5	624.7	637.4	649.1	661.5	675.5	689.4	706.5	722.3	740.2
12.5°	577.6	587.9	599.4	613.6	627.9	643.7	657.9	673.5	691.9	712.3	731.6
15°	543.6	553.4	565.8	577.9	594.4	611.6	630.6	651.3	671.7	694.7	718.5
17.5°	507.0	517.8	531.5	545.4	562.7	583.0	601.6	624.3	647.3	674.0	702.1
20°	483.1	494.3	510.4	525.9	541.7	561.5	583.5	606.7	631.2	659.3	690.6
22.5°	464.3	472.2	488.1	503.9	522.4	542.7	564.2	588.4	615.1	644.2	677.0
25°	436.3	445.6	457.1	473.5	492.8	514.1	535.8	561.5	590.6	620.4	655.3
27.5°	411.6	419.1	430.5	443.4	462.5	484.7	507.8	534.6	564.4	594.7	631.5
30°	394.0	402.4	413.1	426.8	442.0	466.1	489.7	516.0	546.3	577.6	615.4
32.5°	378.6	387.2	396.6	409.4	425.8	447.3	471.6	497.4	528.2	560.5	597.3
35°	357.1	363.0	371.6	384.3	400.5	417.8	442.5	469.9	499.9	533.3	570.1
37.5°	332.5	340.1	348.7	359.7	373.8	392.6	415.6	443.2	471.1	503.1	536.7
40°	318.0	325.2	334.8	342.8	357.8	374.7	395.8	424.6	452.5	482.5	513.1
42.5°	303.5	310.3	318.5	328.5	341.9	358.4	378.0	404.8	434.6	462.9	488.7
45°	280.6	287.7	295.5	304.8	317.2	333.2	352.8	377.2	403.2	429.3	448.7
47.5°	258.7	265.4	272.7	282.3	293.7	309.2	326.7	348.3	373.6	395.7	409.6
50°	243.1	249.3	257.4	266.7	277.8	292.4	309.1	330.4	351.6	371.6	384.3
52.5°	227.8	234.7	242.7	250.8	261.5	276.0	291.5	309.9	330.0	346.3	356.9
55°	204.7	211.2	218.7	227.0	237.6	250.0	266.4	280.9	296.7	310.6	316.8
57.5°	182.5	188.2	195.2	203.8	213.4	224.9	237.8	251.8	263.0	272.9	279.9
60°	167.9	172.8	179.3	186.8	197.0	207.5	219.2	232.3	240.9	249.3	255.8
62.5°	153.0	157.7	164.0	170.6	179.6	189.4	200.7	211.2	219.6	225.3	232.8
65°	130.7	135.3	140.6	147.7	154.8	162.9	173.1	180.8	186.8	193.0	197.6
67.5°	110.0	113.8	118.8	124.4	130.4	138.1	146.0	152.5	156.5	160.2	165.8
70°	96.3	99.4	103.5	107.8	114.3	122.1	128.2	133.1	136.0	139.7	146.5
72.5°	82.4	86.0	89.8	94.2	99.4	105.9	111.4	116.3	118.1	121.1	125.4
75°	65.1	66.9	70.0	73.1	76.8	82.3	87.6	88.9	90.4	92.9	96.0
77.5°	49.2	50.9	52.1	54.1	57.1	61.6	64.3	66.2	66.6	67.5	70.5
80°	39.1	39.9	41.2	42.7	43.9	47.7	49.2	51.1	51.7	52.7	54.2
82.5°	28.6	29.5	30.3	31.6	33.6	35.1	36.6	38.5	38.6	39.3	39.5
85°	16.7	17.0	16.4	17.0	17.4	17.9	19.5	21.0	20.8	20.5	21.4
87.5°	7.5	7.4	7.0	7.7	6.9	7.1	6.9	7.0	7.3	7.6	8.0
90°	7.9	7.4	6.5	6.0	5.1	4.6	3.8	2.8	1.9	0.9	0.5
92.5°	121.4	149.9	152.4	106.2	63.5	38.2	24.5	16.6	10.8	6.8	5.7
95°	403.2	412.1	336.2	207.9	105.6	55.8	34.9	24.6	19.6	15.8	15.3
97.5°	510.2	440.0	300.3	165.9	91.0	58.0	43.0	33.8	28.6	26.0	25.5
100°	536.2	420.0	267.9	150.7	90.3	63.3	49.3	40.4	35.4	33.5	32.5
102.5°	520.6	384.6	243.3	144.4	93.6	69.5	56.0	47.9	42.4	40.9	40.4
105°	470.7	337.2	219.5	141.9	100.4	80.0	66.9	59.5	54.9	52.6	52.6
107.5°	419.7	304.5	209.5	146.1	110.7	90.9	79.2	71.4	67.6	65.4	64.5
110°	390.7	289.3	206.5	150.2	118.1	99.1	87.0	80.0	75.8	73.9	73.1



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	369.1	280.4	206.5	155.4	125.2	106.9	95.1	88.2	84.0	82.5	81.6
115°	345.5	270.7	207.9	163.2	136.2	119.0	107.5	100.4	96.3	94.9	93.9
117.5°	331.5	266.0	210.9	172.2	147.7	131.3	120.1	112.2	108.0	106.5	105.1
120°	323.7	263.7	213.9	178.1	155.8	139.5	127.9	120.0	115.8	114.0	112.5
122.5°	317.0	261.9	216.5	184.8	163.6	147.3	135.7	127.0	122.9	121.4	120.3
125°	307.9	259.5	220.9	194.0	173.9	158.6	146.5	137.6	133.5	131.2	130.2
127.5°	299.5	258.4	225.8	202.3	183.8	169.1	157.0	147.7	142.4	139.3	137.9
130°	293.9	257.6	228.9	207.9	190.2	175.8	163.7	153.9	147.9	144.1	142.8
132.5°	289.4	257.6	232.2	212.7	196.2	181.7	169.7	159.6	152.7	148.3	146.5
135°	284.1	257.6	236.7	219.5	204.2	189.7	177.2	167.5	160.0	154.4	152.5
137.5°	279.4	258.2	240.9	224.5	209.9	196.7	183.8	174.2	166.8	161.6	160.2
140°	277.2	258.6	242.8	227.9	213.9	200.5	187.9	179.0	171.6	166.0	164.6
142.5°	275.3	258.9	243.9	229.8	216.5	203.8	192.0	183.5	176.1	170.9	169.8
145°	272.6	258.6	245.1	232.5	220.9	208.8	198.1	189.7	183.2	178.6	177.7
147.5°	269.6	257.4	245.6	234.2	223.7	213.1	203.7	196.4	190.4	186.4	185.8
150°	267.4	256.2	245.6	235.3	225.6	215.3	207.4	200.9	194.9	191.6	190.7
152.5°	264.8	254.8	245.2	236.0	227.4	217.9	210.8	204.6	199.3	196.4	195.9
155°	260.4	252.1	244.2	236.7	229.3	221.4	214.8	210.2	205.5	202.8	202.8
157.5°	256.3	249.2	243.0	237.2	230.9	224.0	219.2	215.1	211.1	208.8	208.9
160°	253.0	247.4	241.8	237.2	231.6	225.6	221.4	217.7	214.4	212.5	213.0
162.5°	250.1	245.2	240.8	236.8	232.4	227.1	223.6	220.6	217.8	215.9	216.4
165°	245.6	241.8	239.0	236.3	232.5	228.9	226.0	224.1	221.8	220.5	221.4
167.5°	241.2	238.6	236.4	235.1	232.5	229.4	227.7	226.4	225.1	224.3	224.7
170°	238.6	236.7	235.3	234.4	232.5	230.2	228.9	227.9	227.0	226.5	227.0
172.5°	235.9	234.5	233.8	233.7	232.2	230.2	229.6	229.0	228.0	227.6	228.4
175°	232.5	232.0	232.0	232.5	231.6	230.2	230.2	230.2	229.8	229.3	230.2
177.5°	231.1	230.6	230.6	231.4	231.1	230.3	230.3	230.6	230.3	230.3	231.1
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	758.1	760.4	763.6	767.4	770.3	773.6	775.3	775.3	776.7	780.0	784.2
5°	760.3	768.4	776.2	786.0	793.8	802.7	809.6	816.1	822.0	829.4	837.1
7.5°	759.7	773.1	787.0	802.7	819.9	833.6	847.6	858.7	869.5	883.8	895.0
10°	757.2	774.6	793.4	813.3	834.9	853.9	870.9	886.4	901.2	916.7	930.7
12.5°	752.8	774.9	797.9	821.7	849.1	870.7	892.7	909.2	926.5	943.5	960.7
15°	746.1	772.1	800.0	833.2	866.6	890.7	912.4	933.8	949.9	969.1	985.5
17.5°	732.3	765.8	800.9	837.1	869.2	897.3	920.0	940.4	957.5	978.6	1000.9
20°	724.1	760.3	796.9	835.6	866.3	895.0	917.0	938.1	959.4	987.1	1014.3
22.5°	712.7	751.4	790.2	827.0	859.3	887.1	909.9	935.6	963.7	995.0	1027.9
25°	694.7	734.7	773.1	808.0	839.6	868.1	899.1	933.8	967.8	1009.0	1056.4
27.5°	671.8	710.4	744.6	781.5	813.0	849.2	887.9	925.4	974.6	1031.3	1090.5
30°	654.7	691.3	723.8	758.8	794.4	834.4	877.8	922.0	980.6	1047.1	1117.4
32.5°	634.9	668.0	700.3	734.0	775.1	819.0	865.1	919.2	989.2	1064.9	1137.8
35°	600.5	630.2	661.5	699.0	742.7	790.4	849.2	915.2	999.7	1081.2	1146.6
37.5°	564.5	587.9	619.4	658.8	706.5	761.7	828.4	908.6	995.4	1068.5	1096.3
40°	536.7	558.7	591.8	633.3	680.4	740.9	815.8	898.1	985.5	1036.2	1034.1
42.5°	509.2	531.5	563.4	605.1	654.2	721.8	798.9	884.5	958.2	977.5	937.3
45°	467.0	487.8	519.1	561.2	613.8	684.8	765.9	848.0	895.0	863.8	783.9
47.5°	424.0	444.2	473.2	514.5	571.9	646.2	722.9	790.3	796.9	729.7	633.8
50°	395.8	414.7	442.3	486.2	542.0	614.5	688.5	741.4	725.0	642.9	544.1
52.5°	368.3	386.5	412.3	453.8	510.8	581.8	647.8	689.4	651.4	564.2	475.3
55°	327.7	345.0	371.0	409.1	460.8	525.9	583.8	599.0	543.2	455.3	383.4
57.5°	289.1	301.7	327.5	361.2	411.1	468.4	509.9	507.2	445.6	366.5	315.0
60°	263.6	275.0	299.5	330.4	377.8	429.3	458.4	446.0	383.8	318.4	268.8
62.5°	239.8	250.5	271.0	299.5	340.2	384.9	406.1	389.0	330.2	272.8	233.4
65°	203.8	211.6	228.0	254.3	286.2	317.2	336.1	311.0	258.9	215.6	185.8
67.5°	170.2	176.8	191.4	210.3	232.4	253.7	261.4	237.8	197.4	168.2	147.2
70°	148.4	154.6	164.4	182.1	196.7	211.8	215.6	194.5	160.8	138.4	125.4
72.5°	127.5	133.2	141.9	154.3	164.4	173.2	175.0	155.3	129.6	114.1	104.1
75°	97.3	102.2	107.8	112.4	119.0	120.5	119.8	104.7	90.7	80.6	74.9
77.5°	71.5	73.5	77.0	78.8	79.1	79.0	75.8	66.2	59.0	54.8	52.5
80°	55.1	56.7	57.6	58.2	58.5	55.4	52.0	46.1	43.7	41.2	38.4
82.5°	40.0	41.1	42.0	42.2	40.4	37.8	34.7	31.8	30.0	28.8	27.7
85°	21.7	22.0	21.7	20.1	17.9	17.0	16.4	15.8	15.5	15.2	15.2
87.5°	7.8	7.3	6.3	6.7	6.8	6.7	6.9	6.8	6.7	6.8	6.8
90°	0.9	1.9	2.8	3.8	4.6	5.1	6.0	6.5	7.4	7.9	8.4
92.5°	6.8	10.8	16.6	24.5	38.2	63.5	106.2	152.4	149.9	121.4	82.4
95°	15.8	19.6	24.6	34.9	55.8	105.6	207.9	336.2	412.1	403.2	334.4
97.5°	26.0	28.6	33.8	43.0	58.0	91.0	165.9	300.3	440.0	510.2	498.0
100°	33.5	35.4	40.4	49.3	63.3	90.3	150.7	267.9	420.0	536.2	572.0
102.5°	40.9	42.4	47.9	56.0	69.5	93.6	144.4	243.3	384.6	520.6	597.0
105°	52.6	54.9	59.5	66.9	80.0	100.4	141.9	219.5	337.2	470.7	582.3
107.5°	65.4	67.6	71.4	79.2	90.9	110.7	146.1	209.5	304.5	419.7	529.8
110°	73.9	75.8	80.0	87.0	99.1	118.1	150.2	206.5	289.3	390.7	491.1



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	82.5	84.0	88.2	95.1	106.9	125.2	155.4	206.5	280.4	369.1	460.6
115°	94.9	96.3	100.4	107.5	119.0	136.2	163.2	207.9	270.7	345.5	422.2
117.5°	106.5	108.0	112.2	120.1	131.3	147.7	172.2	210.9	266.0	331.5	397.5
120°	114.0	115.8	120.0	127.9	139.5	155.8	178.1	213.9	263.7	323.7	384.2
122.5°	121.4	122.9	127.0	135.7	147.3	163.6	184.8	216.5	261.9	317.0	374.1
125°	131.2	133.5	137.6	146.5	158.6	173.9	194.0	220.9	259.5	307.9	359.5
127.5°	139.3	142.4	147.7	157.0	169.1	183.8	202.3	225.8	258.4	299.5	344.6
130°	144.1	147.9	153.9	163.7	175.8	190.2	207.9	228.9	257.6	293.9	335.3
132.5°	148.3	152.7	159.6	169.7	181.7	196.2	212.7	232.2	257.6	289.4	326.0
135°	154.4	160.0	167.5	177.2	189.7	204.2	219.5	236.7	257.6	284.1	313.9
137.5°	161.6	166.8	174.2	183.8	196.7	209.9	224.5	240.9	258.2	279.4	303.7
140°	166.0	171.6	179.0	187.9	200.5	213.9	227.9	242.8	258.6	277.2	298.1
142.5°	170.9	176.1	183.5	192.0	203.8	216.5	229.8	243.9	258.9	275.3	293.3
145°	178.6	183.2	189.7	198.1	208.8	220.9	232.5	245.1	258.6	272.6	287.0
147.5°	186.4	190.4	196.4	203.7	213.1	223.7	234.2	245.6	257.4	269.6	281.0
150°	191.6	194.9	200.9	207.4	215.3	225.6	235.3	245.6	256.2	267.4	277.6
152.5°	196.4	199.3	204.6	210.8	217.9	227.4	236.0	245.2	254.8	264.8	273.9
155°	202.8	205.5	210.2	214.8	221.4	229.3	236.7	244.2	252.1	260.4	268.3
157.5°	208.8	211.1	215.1	219.2	224.0	230.9	237.2	243.0	249.2	256.3	262.8
160°	212.5	214.4	217.7	221.4	225.6	231.6	237.2	241.8	247.4	253.0	259.0
162.5°	215.9	217.8	220.6	223.6	227.1	232.4	236.8	240.8	245.2	250.1	254.9
165°	220.5	221.8	224.1	226.0	228.9	232.5	236.3	239.0	241.8	245.6	249.2
167.5°	224.3	225.1	226.4	227.7	229.4	232.5	235.1	236.4	238.6	241.2	243.9
170°	226.5	227.0	227.9	228.9	230.2	232.5	234.4	235.3	236.7	238.6	240.9
172.5°	227.6	228.0	229.0	229.6	230.2	232.2	233.7	233.8	234.5	235.9	237.6
175°	229.3	229.8	230.2	230.2	230.2	231.6	232.5	232.0	232.0	232.5	233.9
177.5°	230.3	230.3	230.6	230.3	230.3	231.1	231.4	230.6	230.6	231.1	231.4
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	787.4	787.4	791.7	791.3	794.1	793.1	793.6
5°	846.4	851.7	856.3	859.4	864.1	865.4	864.7
7.5°	907.7	919.3	925.0	932.9	934.3	938.3	937.9
10°	945.5	957.0	965.6	972.5	975.9	980.2	980.6
12.5°	975.3	985.0	992.7	999.0	1003.1	1004.5	1005.3
15°	998.5	1009.3	1018.3	1027.3	1032.6	1036.6	1038.8
17.5°	1021.9	1038.6	1054.5	1066.7	1074.0	1080.2	1080.1
20°	1040.0	1059.2	1079.0	1093.0	1107.2	1113.4	1114.4
22.5°	1059.3	1088.7	1114.2	1135.8	1154.5	1161.0	1163.4
25°	1099.4	1137.8	1177.2	1207.5	1229.2	1241.9	1243.8
27.5°	1147.9	1200.0	1241.3	1269.3	1287.4	1296.7	1298.8
30°	1182.2	1230.1	1267.3	1288.4	1296.7	1298.0	1293.3
32.5°	1197.5	1233.4	1248.2	1247.0	1230.6	1219.7	1215.5
35°	1178.8	1171.3	1135.1	1091.7	1058.6	1037.5	1031.9
37.5°	1072.7	1008.6	941.9	876.4	841.6	823.9	793.4
40°	968.2	876.8	807.4	752.3	713.0	681.3	673.9
42.5°	850.2	755.9	686.5	639.3	607.9	586.2	576.8
45°	683.2	602.1	544.8	508.5	484.4	468.6	461.5
47.5°	546.4	483.6	441.9	415.1	396.6	382.9	379.1
50°	471.4	421.2	385.9	363.3	349.4	338.8	334.5
52.5°	409.4	368.9	341.8	323.2	310.0	303.4	299.8
55°	337.9	302.9	283.4	268.5	261.1	255.8	253.3
57.5°	276.3	251.0	236.8	226.5	219.6	216.3	215.1
60°	241.9	222.1	209.0	201.0	196.3	192.0	190.8
62.5°	211.4	195.8	185.7	178.7	174.1	172.2	171.5
65°	170.3	160.1	152.7	148.4	144.6	144.0	143.7
67.5°	135.4	129.4	125.5	121.0	119.7	117.5	117.1
70°	115.9	111.8	107.1	105.6	104.0	101.9	102.2
72.5°	98.2	94.2	91.1	89.0	88.5	87.6	88.3
75°	71.8	70.6	69.4	67.8	67.2	67.2	66.9
77.5°	51.3	50.2	48.8	47.9	47.8	46.5	47.0
80°	37.2	35.6	35.0	35.3	34.4	34.1	34.1
82.5°	27.5	26.9	26.3	26.4	26.2	25.9	26.2
85°	15.2	14.8	14.8	14.6	14.6	14.3	14.3
87.5°	7.3	7.6	7.3	7.0	7.0	7.3	7.6
90°	8.8	9.3	10.2	10.2	10.2	10.7	10.7
92.5°	59.8	45.0	38.2	32.2	31.1	30.4	29.7
95°	263.7	206.5	167.5	134.4	120.4	116.8	109.3
97.5°	448.4	392.7	338.3	309.7	283.6	270.1	264.2
100°	549.3	501.3	453.0	420.9	387.4	370.2	362.7
102.5°	611.0	588.0	555.3	521.0	497.2	478.5	472.9
105°	646.0	666.4	661.3	646.5	631.1	621.8	616.2
107.5°	614.8	667.4	691.6	699.2	699.1	696.0	692.3
110°	579.5	645.1	684.6	705.5	714.4	717.6	717.6



TEST NUMBER: P333528-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	544.5	610.8	657.5	688.0	703.2	711.3	714.6
115°	494.4	558.1	608.8	645.1	667.4	680.4	686.5
117.5°	459.7	514.5	561.1	597.4	620.4	633.3	637.1
120°	439.9	491.1	532.1	566.5	588.8	601.4	605.0
122.5°	425.8	471.4	509.7	540.4	560.8	573.4	576.7
125°	406.9	447.4	480.9	507.0	526.0	536.2	540.9
127.5°	388.9	426.6	458.0	481.6	498.5	508.1	510.2
130°	376.3	412.5	442.7	466.0	481.4	490.6	493.4
132.5°	364.4	397.3	426.4	449.6	465.0	473.5	476.7
135°	346.0	375.8	402.3	422.7	438.1	446.5	449.2
137.5°	329.6	354.4	376.9	395.2	409.2	416.9	420.0
140°	320.0	341.4	360.9	378.1	390.2	397.1	399.5
142.5°	311.8	330.2	347.2	361.7	371.9	378.5	380.5
145°	301.3	315.8	328.3	339.5	347.4	352.5	354.4
147.5°	292.7	303.8	313.2	322.1	328.4	331.4	332.2
150°	287.9	296.7	305.1	312.1	317.6	319.5	320.0
152.5°	283.1	291.1	297.7	303.5	307.9	309.8	310.3
155°	275.8	282.3	287.4	292.0	295.3	296.7	297.2
157.5°	268.9	273.9	277.9	281.5	284.2	285.5	285.4
160°	263.7	268.3	271.6	274.8	277.2	278.1	277.6
162.5°	259.3	263.1	266.0	268.6	270.5	270.7	270.6
165°	252.5	255.4	257.6	259.5	260.4	260.4	260.4
167.5°	246.1	248.2	249.8	250.8	251.6	251.2	251.1
170°	242.3	243.7	244.6	245.6	246.1	246.1	245.6
172.5°	239.0	239.9	240.5	240.8	241.6	240.8	240.4
175°	233.9	234.9	234.9	234.9	235.3	234.4	233.9
177.5°	231.8	231.8	231.8	231.4	231.8	230.6	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6

(END OF REPORT)