

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333570-930

Luminaire Tested: **S125RDIP-S850D1035U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333570-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1035U930-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5701.4 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47				47
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46				40	
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	42	41	39				34	
3	81	72	65	60	75	67	61	56	56	52	48	47	44	41	38	36	34				29	
4	75	64	56	51	68	59	53	47	50	45	41	42	38	35	34	31	29				26	
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26				22	
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23				20	
7	58	46	39	33	54	43	36	31	37	31	28	31	27	24	26	23	20				18	
8	54	42	35	29	50	39	32	28	34	28	24	28	24	21	23	20	18				16	
9	51	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16				14	
10	47	35	28	23	43	33	27	22	28	23	20	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6660	6660	6660	6660
5°	7662	6669	5890	6669
10°	8790	6635	5197	6635
15°	9494	6567	4619	6567
20°	10469	6488	4265	6488
25°	12115	6383	3958	6383
30°	13184	6272	3757	6272
35°	11121	6144	3572	6144
40°	7766	5914	3412	5914
45°	5761	5602	3255	5602
50°	4594	5279	3122	5279
55°	3899	4877	3003	4877
60°	3369	4517	2811	4517
65°	3001	4128	2419	4128
70°	2638	3780	2206	3780
75°	2283	3276	2071	3276
80°	1733	2756	1733	2756
85°	1445	2164	1630	2164



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.9	1.7
10°-20°	289.8	5.1
20°-30°	459.5	8.1
30°-40°	554.1	9.7
40°-50°	494.9	8.7
50°-60°	379.5	6.7
60°-70°	246.6	4.3
70°-80°	119.9	2.1
80°-90°	30.9	0.5
90°-100°	292.6	5.1
100°-110°	629.0	11.0
110°-120°	590.3	10.4
120°-130°	478.4	8.4
130°-140°	383.9	6.7
140°-150°	289.7	5.1
150°-160°	203.9	3.6
160°-170°	120.2	2.1
170°-180°	39.1	0.7
0°-30°	848.2	14.9
0°-40°	1402.4	24.6
0°-60°	2276.7	39.9
0°-90°	2674.1	46.9
90°-120°	1512.0	26.5
90°-150°	2664.1	46.7
90°-180°	3027.0	53.1
0°-180°	5701.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1031	1031	1031	1031	1031	
5°	1182	1029	908	1029	1182	118
15°	1420	982	691	982	1420	407
25°	1700	896	556	896	1700	781
35°	1410	779	453	779	1410	852
45°	631	613	356	613	631	503
55°	346	433	267	433	346	314
65°	196	270	158	270	196	195
75°	92	131	83	131	92	97
85°	20	29	22	29	20	23
90°	19	1	19	1	19	14
95°	191	27	191	27	191	271
105°	1078	92	1078	92	1078	1072
115°	1201	164	1201	164	1201	1174
125°	947	228	947	228	947	856
135°	786	267	786	267	786	609
145°	620	311	620	311	620	394
155°	520	355	520	355	520	242
165°	456	387	456	387	456	130
175°	409	403	409	403	409	40
180°	404	404	404	404	404	



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1084.8	1084.1	1085.5	1081.7	1082.1	1076.3	1076.3	1071.9	1066.2	1061.8	1059.7
5°	1181.9	1182.8	1181.1	1174.8	1170.5	1164.2	1157.0	1144.3	1133.7	1123.6	1115.5
7.5°	1282.1	1282.6	1277.1	1275.1	1264.4	1256.6	1240.6	1223.4	1208.0	1188.5	1173.7
10°	1340.3	1339.9	1334.0	1329.3	1320.0	1308.1	1292.5	1272.1	1253.1	1231.9	1211.6
12.5°	1374.2	1373.0	1371.2	1365.5	1356.9	1346.4	1333.1	1313.1	1289.6	1266.5	1242.8
15°	1419.9	1416.9	1411.4	1404.2	1392.0	1379.6	1364.9	1347.1	1324.6	1298.4	1276.4
17.5°	1476.4	1476.5	1468.1	1458.1	1441.4	1419.8	1396.9	1368.2	1337.7	1308.8	1285.3
20°	1523.2	1521.9	1513.4	1494.0	1475.0	1447.8	1421.6	1386.4	1349.2	1311.5	1282.3
22.5°	1590.2	1587.0	1578.2	1552.6	1523.1	1488.2	1448.0	1405.1	1360.0	1317.3	1279.0
25°	1700.1	1697.6	1680.3	1650.7	1609.2	1555.3	1502.8	1444.1	1379.2	1323.0	1276.4
27.5°	1775.3	1772.5	1759.7	1735.0	1696.8	1640.2	1569.1	1490.5	1409.7	1332.2	1265.0
30°	1767.9	1774.3	1772.5	1761.1	1732.3	1681.6	1615.9	1527.5	1431.3	1340.3	1260.3
32.5°	1661.5	1667.2	1682.1	1704.5	1706.3	1686.0	1636.9	1555.2	1455.7	1352.2	1256.5
35°	1410.5	1418.2	1447.0	1492.3	1551.5	1601.1	1611.3	1567.2	1477.9	1366.5	1251.0
37.5°	1084.4	1126.1	1150.3	1198.0	1287.5	1378.7	1466.3	1498.5	1460.5	1360.7	1241.9
40°	921.2	931.3	974.5	1028.3	1103.7	1198.5	1323.4	1413.6	1416.5	1347.1	1227.7
42.5°	788.4	801.3	831.0	873.8	938.4	1033.2	1162.1	1281.2	1336.3	1309.9	1209.1
45°	630.8	640.5	662.1	695.1	744.7	823.0	933.9	1071.5	1180.7	1223.4	1159.1
47.5°	518.2	523.4	542.3	567.4	604.1	661.1	747.0	866.4	997.4	1089.2	1080.2
50°	457.2	463.2	477.5	496.6	527.5	575.8	644.3	743.8	878.9	991.1	1013.5
52.5°	409.8	414.7	423.7	441.7	467.2	504.3	559.6	649.6	771.2	890.5	942.3
55°	346.3	349.7	356.9	367.0	387.3	414.0	461.9	524.1	622.3	742.6	818.7
57.5°	294.0	295.6	300.3	309.7	323.7	343.2	377.7	430.5	500.9	609.2	693.2
60°	260.8	262.4	268.4	274.8	285.8	303.5	330.6	367.5	435.2	524.5	609.6
62.5°	234.4	235.4	237.9	244.3	253.9	267.7	288.9	319.0	372.9	451.3	531.7
65°	196.4	196.9	197.7	202.8	208.7	218.9	232.8	254.0	294.6	353.9	425.0
67.5°	160.0	160.6	163.5	165.3	171.5	176.8	185.1	201.3	229.9	269.9	325.1
70°	139.7	139.3	142.3	144.4	146.5	152.8	158.3	171.5	189.2	219.7	265.9
72.5°	120.7	119.6	120.9	121.6	124.5	128.8	134.3	142.4	156.0	177.0	212.4
75°	91.5	91.9	91.9	92.7	94.8	96.5	98.2	102.5	110.1	124.0	143.1
77.5°	64.2	63.5	65.3	65.6	66.8	68.6	70.1	71.8	74.9	80.7	90.5
80°	46.6	46.6	47.0	48.3	47.9	48.7	50.8	52.5	56.3	59.7	63.1
82.5°	35.7	35.4	35.8	36.0	36.0	36.9	37.6	37.9	39.4	41.1	43.5
85°	19.5	19.5	19.9	19.9	20.3	20.3	20.7	20.7	20.7	21.2	21.6
87.5°	11.2	10.8	10.4	10.4	10.7	11.0	10.5	10.0	9.9	9.7	9.7
90°	18.8	18.8	17.9	17.9	17.9	16.3	15.5	14.7	13.9	13.0	11.4
92.5°	51.9	53.2	54.4	56.3	66.8	78.8	104.7	144.2	212.4	262.4	266.6
95°	191.3	204.3	210.8	235.2	293.0	361.3	461.5	585.2	705.6	721.1	588.5
97.5°	462.3	472.7	496.3	541.9	592.2	687.2	784.7	871.6	892.8	770.1	525.5
100°	634.9	647.8	678.0	736.5	792.7	877.3	961.2	1001.1	938.4	734.9	468.8
102.5°	827.5	837.3	870.1	911.7	971.8	1029.1	1069.3	1044.7	911.1	673.1	425.8
105°	1078.4	1088.2	1104.5	1131.3	1157.3	1166.3	1130.5	1019.0	823.7	590.0	384.2
107.5°	1211.5	1218.1	1223.4	1223.6	1210.4	1167.9	1076.0	927.2	734.4	533.0	366.6
110°	1255.8	1255.8	1250.1	1234.7	1198.1	1128.9	1014.1	859.5	683.6	506.2	361.3



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1250.6	1244.8	1230.6	1204.0	1150.6	1068.9	952.9	806.1	645.9	490.6	361.3
115°	1201.3	1190.7	1167.9	1128.9	1065.4	976.6	865.2	739.0	604.7	473.7	363.8
117.5°	1114.8	1108.3	1085.7	1045.4	981.9	900.5	804.5	695.7	580.2	465.4	369.2
120°	1058.9	1052.4	1030.4	991.3	931.1	859.5	770.0	672.3	566.5	461.5	374.4
122.5°	1009.4	1003.6	981.5	945.7	892.0	824.9	745.2	654.7	554.7	458.2	379.0
125°	946.6	938.4	920.5	887.1	841.6	782.9	712.2	629.2	538.8	454.1	386.6
127.5°	892.8	889.2	872.3	842.9	801.5	746.7	680.6	603.1	524.2	452.2	395.3
130°	863.6	858.7	842.4	815.5	774.9	721.9	658.4	586.9	514.4	450.9	400.5
132.5°	834.2	828.7	813.8	786.8	746.2	695.2	637.6	570.5	506.5	450.9	406.3
135°	786.2	781.3	766.7	739.8	704.0	657.6	605.5	549.3	497.3	450.9	414.3
137.5°	734.9	729.6	716.1	691.6	659.6	620.2	576.9	531.5	489.0	451.8	421.6
140°	699.1	695.0	682.9	661.7	631.6	597.4	559.9	521.7	485.1	452.5	424.9
142.5°	665.9	662.5	650.9	633.1	607.5	577.9	545.6	513.2	481.8	453.1	426.8
145°	620.2	616.9	608.0	594.1	574.6	552.6	527.4	502.1	477.0	452.5	428.9
147.5°	581.5	580.0	574.8	563.7	548.2	531.7	512.3	491.8	471.9	450.4	429.7
150°	559.9	559.1	555.9	546.1	533.9	519.3	503.8	485.9	468.0	448.4	429.7
152.5°	543.0	542.2	539.0	531.2	520.9	509.5	495.3	479.4	463.4	445.9	429.1
155°	520.1	519.3	516.8	511.1	503.0	494.1	482.7	469.6	455.8	441.2	427.3
157.5°	499.5	499.7	497.4	492.8	486.4	479.4	470.6	459.8	448.6	436.3	425.2
160°	485.9	486.7	485.1	481.0	475.3	469.6	461.5	453.3	442.8	433.0	423.2
162.5°	473.5	473.7	473.4	469.9	465.5	460.5	453.6	446.2	437.6	429.1	421.3
165°	455.8	455.8	455.8	454.1	450.9	446.9	442.0	436.3	429.7	423.2	418.3
167.5°	439.5	439.7	440.3	438.9	437.2	434.3	430.6	426.8	422.1	417.5	413.8
170°	429.7	430.6	430.6	429.7	428.1	426.5	424.0	421.6	417.5	414.3	411.8
172.5°	420.6	421.4	422.7	421.3	420.9	420.0	418.2	415.7	412.9	410.3	409.2
175°	409.4	410.2	411.8	411.0	411.0	411.0	409.4	409.4	406.9	406.1	406.1
177.5°	403.7	403.7	405.6	405.0	405.6	405.6	405.6	405.0	404.3	403.7	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1059.7	1057.4	1053.0	1048.9	1043.8	1039.4	1036.3	1032.7	1027.8	1022.1	1017.4
5°	1106.6	1097.3	1085.0	1074.5	1060.9	1050.4	1039.3	1028.7	1018.1	1004.6	992.7
7.5°	1158.6	1139.4	1120.7	1097.1	1075.8	1056.7	1038.4	1019.9	1001.8	982.6	964.0
10°	1190.4	1167.2	1141.3	1111.7	1084.6	1058.7	1035.1	1011.8	987.2	965.6	942.3
12.5°	1220.3	1190.2	1160.7	1123.2	1090.7	1059.2	1029.0	1000.0	973.7	945.7	920.7
15°	1247.2	1217.6	1184.5	1138.8	1093.5	1055.4	1019.9	982.2	949.6	918.3	890.3
17.5°	1257.6	1226.5	1188.1	1144.2	1094.7	1046.8	1000.9	959.6	921.3	884.8	853.4
20°	1253.5	1223.4	1184.1	1142.2	1089.2	1039.3	989.8	944.0	901.3	862.7	829.3
22.5°	1243.7	1212.6	1174.6	1130.3	1080.1	1027.1	974.2	925.4	880.6	840.7	804.3
25°	1229.0	1186.7	1147.7	1104.5	1056.6	1004.2	949.6	895.8	848.0	807.3	767.5
27.5°	1213.7	1160.8	1111.3	1068.4	1017.8	970.9	918.4	863.2	812.9	771.5	730.7
30°	1199.8	1140.5	1085.9	1037.2	989.4	944.9	895.0	841.1	789.5	746.8	705.3
32.5°	1182.5	1119.5	1059.5	1003.3	957.2	913.1	867.9	816.4	766.1	722.0	679.9
35°	1160.8	1080.4	1015.2	955.4	904.2	861.5	820.8	779.3	729.0	683.3	642.2
37.5°	1132.4	1041.1	965.6	900.7	846.6	803.6	771.6	733.7	687.7	643.9	605.8
40°	1115.1	1012.6	930.1	865.8	809.0	763.7	733.7	701.5	659.6	618.5	580.4
42.5°	1092.1	986.6	894.2	827.1	770.1	726.4	696.0	668.0	632.8	594.1	553.3
45°	1046.9	936.0	839.1	767.1	709.6	666.8	638.4	613.4	586.8	551.2	515.6
47.5°	988.1	883.3	781.8	703.3	646.9	607.2	579.7	559.9	540.9	510.6	476.1
50°	941.1	839.9	740.9	664.6	604.5	566.9	541.0	525.4	508.0	480.5	451.7
52.5°	885.6	795.2	698.1	620.3	563.5	528.2	503.4	487.8	473.4	451.0	423.6
55°	798.0	718.8	629.9	559.2	507.2	471.6	447.9	433.1	424.6	405.5	384.0
57.5°	697.0	640.3	561.8	493.7	447.7	412.5	395.2	382.5	373.0	359.5	344.3
60°	626.6	586.8	516.5	451.7	409.4	375.9	360.3	349.7	340.8	329.4	317.5
62.5°	555.1	526.1	465.0	409.4	370.4	342.4	327.8	318.2	307.9	300.3	288.7
65°	459.3	433.5	391.2	347.6	311.6	289.1	278.6	270.1	263.7	255.3	247.2
67.5°	357.3	346.8	317.6	287.6	261.7	241.7	232.6	226.7	219.1	213.9	208.5
70°	294.6	289.6	268.8	248.9	224.8	211.2	202.8	200.2	190.9	185.9	182.1
72.5°	239.1	236.8	224.8	211.0	194.0	182.1	174.3	171.5	165.5	161.4	159.0
75°	163.8	164.7	162.6	153.7	147.3	139.7	132.9	131.3	127.0	123.6	121.5
77.5°	103.6	107.9	108.1	107.7	105.2	100.5	97.7	96.4	92.3	91.0	90.5
80°	71.1	75.7	80.0	79.6	78.8	77.5	75.3	74.1	72.0	70.7	69.9
82.5°	47.5	51.8	55.3	57.6	57.4	56.2	54.7	54.1	53.6	52.7	52.6
85°	22.4	23.3	24.5	27.6	29.6	30.1	29.6	29.2	28.0	28.4	28.8
87.5°	9.9	9.6	9.8	9.5	8.8	10.1	10.8	11.0	10.5	10.1	9.8
90°	10.6	9.0	8.2	6.5	4.9	3.3	1.6	0.8	1.6	3.3	4.9
92.5°	185.7	111.2	66.8	43.0	28.9	18.9	12.1	9.9	12.1	18.9	28.9
95°	363.8	184.7	97.7	61.1	43.1	34.2	27.6	26.8	27.6	34.2	43.1
97.5°	290.4	159.2	101.6	75.2	59.1	50.1	45.6	44.6	45.6	50.1	59.1
100°	263.7	157.9	110.7	86.3	70.8	61.9	58.6	57.0	58.6	61.9	70.8
102.5°	252.7	163.8	121.7	98.0	83.8	74.2	71.6	70.7	71.6	74.2	83.8
105°	248.3	175.8	140.0	117.2	104.2	96.0	92.0	92.0	92.0	96.0	104.2
107.5°	255.8	193.7	159.1	138.5	125.0	118.3	114.5	112.8	114.5	118.3	125.0
110°	262.9	206.8	173.3	152.2	140.0	132.6	129.4	127.8	129.4	132.6	140.0



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	272.0	219.1	187.0	166.5	154.3	147.0	144.4	142.8	144.4	147.0	154.3
115°	285.7	238.5	208.4	188.0	175.8	168.4	166.0	164.4	166.0	168.4	175.8
117.5°	301.3	258.4	229.8	210.2	196.3	189.0	186.4	183.9	186.4	189.0	196.3
120°	311.7	272.6	244.2	223.8	210.0	202.7	199.4	197.0	199.4	202.7	210.0
122.5°	323.4	286.3	257.9	237.5	222.3	215.0	212.4	210.7	212.4	215.0	222.3
125°	339.4	304.4	277.5	256.4	240.9	233.6	229.5	227.9	229.5	233.6	240.9
127.5°	354.0	321.8	296.0	274.8	258.4	249.1	243.9	241.4	243.9	249.1	258.4
130°	363.8	332.9	307.6	286.5	269.4	258.9	252.3	249.9	252.3	258.9	269.4
132.5°	372.3	343.3	318.0	296.9	279.2	267.3	259.4	256.4	259.4	267.3	279.2
135°	384.2	357.3	332.1	310.1	293.0	280.0	270.2	266.9	270.2	280.0	293.0
137.5°	393.0	367.2	344.3	321.6	304.9	291.9	282.7	280.3	282.7	291.9	304.9
140°	398.8	374.4	350.8	328.8	313.3	300.4	290.6	288.1	290.6	300.4	313.3
142.5°	402.0	379.0	356.6	336.0	321.1	308.1	299.1	297.3	299.1	308.1	321.1
145°	406.9	386.6	365.4	346.7	332.1	320.7	312.5	310.9	312.5	320.7	332.1
147.5°	409.9	391.5	372.9	356.4	343.8	333.2	326.2	325.2	326.2	333.2	343.8
150°	411.8	394.8	376.8	363.0	351.6	341.0	335.3	333.7	335.3	341.0	351.6
152.5°	413.1	398.0	381.4	368.8	358.1	348.9	343.8	342.8	343.8	348.9	358.1
155°	414.3	401.2	387.4	376.0	367.9	359.7	354.8	354.8	354.8	359.7	367.9
157.5°	415.1	404.0	392.2	383.5	376.3	369.3	365.4	365.6	365.4	369.3	376.3
160°	415.1	405.3	394.8	387.4	380.9	375.2	371.9	372.8	371.9	375.2	380.9
162.5°	414.4	406.6	397.4	391.3	386.1	381.1	377.8	378.6	377.8	381.1	386.1
165°	413.4	406.9	400.5	395.6	392.3	388.2	385.8	387.4	385.8	388.2	392.3
167.5°	411.5	406.9	401.5	398.5	396.2	394.0	392.5	393.3	392.5	394.0	396.2
170°	410.2	406.9	402.8	400.5	398.8	397.2	396.4	397.2	396.4	397.2	398.8
172.5°	408.9	406.3	402.8	401.7	400.7	399.2	398.4	399.8	398.4	399.2	400.7
175°	406.9	405.3	402.8	402.8	402.8	402.0	401.2	402.8	401.2	402.0	402.8
177.5°	405.0	404.3	403.0	403.0	403.7	403.0	403.0	404.3	403.0	403.0	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1014.0	1009.3	1005.8	999.1	994.3	992.3	988.6	987.6	991.3	988.6	988.2
5°	983.8	971.6	961.8	952.1	941.5	934.7	924.5	922.9	920.3	916.6	915.7
7.5°	947.7	931.7	919.2	903.1	889.1	877.8	865.1	859.2	855.8	850.9	844.3
10°	923.3	904.2	887.3	871.2	853.9	839.9	827.2	817.5	811.1	805.2	802.7
12.5°	899.3	879.9	858.2	838.7	819.4	803.6	789.6	783.3	776.2	769.3	763.4
15°	861.9	836.1	812.4	789.9	773.5	756.5	743.0	733.7	723.1	720.1	708.7
17.5°	822.3	797.0	769.2	745.6	726.4	707.8	692.9	682.3	674.4	663.5	658.2
20°	797.6	767.5	740.5	718.8	697.7	675.6	660.4	651.5	643.9	635.0	630.8
22.5°	771.2	741.8	714.0	688.7	667.2	645.6	634.7	625.4	616.8	608.6	603.0
25°	732.4	702.8	673.5	647.3	624.8	609.2	596.5	585.9	581.2	573.2	567.3
27.5°	694.1	662.5	632.2	606.1	588.5	573.0	562.6	554.2	545.8	538.7	533.6
30°	669.3	637.2	604.1	583.3	564.8	549.9	538.5	530.4	524.1	517.7	514.0
32.5°	644.6	611.4	582.1	559.6	542.0	529.3	517.5	509.8	503.1	496.1	491.6
35°	605.0	571.1	547.4	525.4	508.0	496.2	488.1	477.1	471.6	466.5	461.9
37.5°	568.1	536.6	510.9	491.7	476.6	464.8	454.4	448.5	441.7	437.2	433.3
40°	541.0	512.3	488.9	468.6	457.6	444.5	434.8	427.1	422.1	416.1	411.9
42.5°	516.7	489.9	467.2	449.0	435.3	424.2	414.8	407.2	400.7	396.5	393.0
45°	482.2	455.5	433.5	416.5	403.9	393.3	383.5	379.8	371.3	366.2	364.5
47.5°	446.5	422.7	401.5	385.8	372.8	362.8	353.7	345.8	341.2	336.2	333.5
50°	422.5	399.7	379.8	364.5	351.8	340.8	332.3	327.3	320.9	316.3	312.8
52.5°	398.4	377.3	357.4	342.8	331.8	320.8	311.4	306.2	300.3	297.3	294.9
55°	364.1	341.6	324.7	310.3	298.9	288.7	279.8	274.8	270.9	268.0	267.1
57.5°	325.1	307.4	291.6	278.7	266.8	257.2	249.4	244.6	241.2	240.8	238.2
60°	299.7	283.6	269.2	255.3	245.1	236.2	229.4	224.0	220.5	220.1	219.3
62.5°	274.3	258.9	245.6	233.3	224.1	215.6	209.1	202.9	200.9	198.8	197.0
65°	236.7	222.7	211.7	201.9	192.2	185.0	178.6	174.8	170.2	167.6	163.0
67.5°	199.7	188.8	178.2	170.0	162.4	155.6	150.3	144.6	141.5	139.4	136.1
70°	175.3	166.8	156.2	147.3	141.4	135.9	131.7	125.3	123.2	121.5	119.8
72.5°	152.2	144.8	135.9	128.7	122.8	117.6	112.7	109.7	107.6	105.9	104.9
75°	119.8	112.6	105.0	99.9	95.7	91.5	88.9	86.7	85.9	85.5	83.8
77.5°	88.0	84.1	78.0	74.0	71.2	69.5	67.3	66.1	66.0	64.2	63.6
80°	67.3	65.2	60.1	58.5	56.3	54.6	53.3	51.2	49.1	48.3	47.0
82.5°	50.1	47.9	45.9	43.2	41.4	40.4	39.1	38.3	38.6	37.4	36.9
85°	26.7	24.5	23.7	23.3	22.4	23.3	22.8	22.4	22.0	21.6	22.0
87.5°	9.8	10.1	9.9	10.9	10.0	10.8	10.9	10.7	10.8	11.0	11.0
90°	6.5	8.2	9.0	10.6	11.4	13.0	13.9	14.7	15.5	16.3	17.9
92.5°	43.0	66.8	111.2	185.7	266.6	262.4	212.4	144.2	104.7	78.8	66.8
95°	61.1	97.7	184.7	363.8	588.5	721.1	705.6	585.2	461.5	361.3	293.0
97.5°	75.2	101.6	159.2	290.4	525.5	770.1	892.8	871.6	784.7	687.2	592.2
100°	86.3	110.7	157.9	263.7	468.8	734.9	938.4	1001.1	961.2	877.3	792.7
102.5°	98.0	121.7	163.8	252.7	425.8	673.1	911.1	1044.7	1069.3	1029.1	971.8
105°	117.2	140.0	175.8	248.3	384.2	590.0	823.7	1019.0	1130.5	1166.3	1157.3
107.5°	138.5	159.1	193.7	255.8	366.6	533.0	734.4	927.2	1076.0	1167.9	1210.4
110°	152.2	173.3	206.8	262.9	361.3	506.2	683.6	859.5	1014.1	1128.9	1198.1



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	166.5	187.0	219.1	272.0	361.3	490.6	645.9	806.1	952.9	1068.9	1150.6
115°	188.0	208.4	238.5	285.7	363.8	473.7	604.7	739.0	865.2	976.6	1065.4
117.5°	210.2	229.8	258.4	301.3	369.2	465.4	580.2	695.7	804.5	900.5	981.9
120°	223.8	244.2	272.6	311.7	374.4	461.5	566.5	672.3	770.0	859.5	931.1
122.5°	237.5	257.9	286.3	323.4	379.0	458.2	554.7	654.7	745.2	824.9	892.0
125°	256.4	277.5	304.4	339.4	386.6	454.1	538.8	629.2	712.2	782.9	841.6
127.5°	274.8	296.0	321.8	354.0	395.3	452.2	524.2	603.1	680.6	746.7	801.5
130°	286.5	307.6	332.9	363.8	400.5	450.9	514.4	586.9	658.4	721.9	774.9
132.5°	296.9	318.0	343.3	372.3	406.3	450.9	506.5	570.5	637.6	695.2	746.2
135°	310.1	332.1	357.3	384.2	414.3	450.9	497.3	549.3	605.5	657.6	704.0
137.5°	321.6	344.3	367.2	393.0	421.6	451.8	489.0	531.5	576.9	620.2	659.6
140°	328.8	350.8	374.4	398.8	424.9	452.5	485.1	521.7	559.9	597.4	631.6
142.5°	336.0	356.6	379.0	402.0	426.8	453.1	481.8	513.2	545.6	577.9	607.5
145°	346.7	365.4	386.6	406.9	428.9	452.5	477.0	502.1	527.4	552.6	574.6
147.5°	356.4	372.9	391.5	409.9	429.7	450.4	471.9	491.8	512.3	531.7	548.2
150°	363.0	376.8	394.8	411.8	429.7	448.4	468.0	485.9	503.8	519.3	533.9
152.5°	368.8	381.4	398.0	413.1	429.1	445.9	463.4	479.4	495.3	509.5	520.9
155°	376.0	387.4	401.2	414.3	427.3	441.2	455.8	469.6	482.7	494.1	503.0
157.5°	383.5	392.2	404.0	415.1	425.2	436.3	448.6	459.8	470.6	479.4	486.4
160°	387.4	394.8	405.3	415.1	423.2	433.0	442.8	453.3	461.5	469.6	475.3
162.5°	391.3	397.4	406.6	414.4	421.3	429.1	437.6	446.2	453.6	460.5	465.5
165°	395.6	400.5	406.9	413.4	418.3	423.2	429.7	436.3	442.0	446.9	450.9
167.5°	398.5	401.5	406.9	411.5	413.8	417.5	422.1	426.8	430.6	434.3	437.2
170°	400.5	402.8	406.9	410.2	411.8	414.3	417.5	421.6	424.0	426.5	428.1
172.5°	401.7	402.8	406.3	408.9	409.2	410.3	412.9	415.7	418.2	420.0	420.9
175°	402.8	402.8	405.3	406.9	406.1	406.1	406.9	409.4	409.4	411.0	411.0
177.5°	403.0	403.0	404.3	405.0	403.7	403.7	404.3	405.0	405.6	405.6	405.6
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	987.9	984.2	983.2	984.6	983.2	984.2	987.9	988.2	988.6	991.3	987.6
5°	911.4	907.3	909.3	908.5	909.3	907.3	911.4	915.7	916.6	920.3	922.9
7.5°	844.2	838.9	833.4	835.2	833.4	838.9	844.2	844.3	850.9	855.8	859.2
10°	797.1	793.0	790.4	792.5	790.4	793.0	797.1	802.7	805.2	811.1	817.5
12.5°	757.5	755.0	752.8	751.9	752.8	755.0	757.5	763.4	769.3	776.2	783.3
15°	703.6	698.5	696.4	690.9	696.4	698.5	703.6	708.7	720.1	723.1	733.7
17.5°	653.9	652.2	646.7	644.3	646.7	652.2	653.9	658.2	663.5	674.4	682.3
20°	624.4	622.7	617.3	620.6	617.3	622.7	624.4	630.8	635.0	643.9	651.5
22.5°	600.1	596.3	594.5	593.5	594.5	596.3	600.1	603.0	608.6	616.8	625.4
25°	565.6	560.1	558.0	555.5	558.0	560.1	565.6	567.3	573.2	581.2	585.9
27.5°	531.2	528.2	525.5	524.8	525.5	528.2	531.2	533.6	538.7	545.8	554.2
30°	508.8	505.9	503.8	503.8	503.8	505.9	508.8	514.0	517.7	524.1	530.4
32.5°	488.9	486.6	484.5	484.1	484.5	486.6	488.9	491.6	496.1	503.1	509.8
35°	459.7	456.4	455.5	453.0	455.5	456.4	459.7	461.9	466.5	471.6	477.1
37.5°	429.5	426.7	426.6	426.4	426.6	426.7	429.5	433.3	437.2	441.7	448.5
40°	410.3	408.1	407.6	404.7	407.6	408.1	410.3	411.9	416.1	422.1	427.1
42.5°	389.6	388.5	387.0	385.7	387.0	388.5	389.6	393.0	396.5	400.7	407.2
45°	361.5	358.6	358.6	356.4	358.6	358.6	361.5	364.5	366.2	371.3	379.8
47.5°	332.6	330.3	330.5	328.3	330.5	330.3	332.6	333.5	336.2	341.2	345.8
50°	313.2	312.0	311.6	310.7	311.6	312.0	313.2	312.8	316.3	320.9	327.3
52.5°	294.0	293.3	295.0	293.1	295.0	293.3	294.0	294.9	297.3	300.3	306.2
55°	268.0	266.7	269.2	266.7	269.2	266.7	268.0	267.1	268.0	270.9	274.8
57.5°	238.1	236.9	239.2	237.9	239.2	236.9	238.1	238.2	240.8	241.2	244.6
60°	218.4	215.9	217.2	217.6	217.2	215.9	218.4	219.3	220.1	220.5	224.0
62.5°	195.1	193.6	194.4	192.6	194.4	193.6	195.1	197.0	198.8	200.9	202.9
65°	162.2	160.9	159.1	158.3	159.1	160.9	162.2	163.0	167.6	170.2	174.8
67.5°	136.2	133.2	133.1	133.8	133.1	133.2	136.2	136.1	139.4	141.5	144.6
70°	117.2	117.2	116.8	116.8	116.8	117.2	117.2	119.8	121.5	123.2	125.3
72.5°	104.0	103.7	103.0	102.6	103.0	103.7	104.0	104.9	105.9	107.6	109.7
75°	83.8	84.2	83.4	83.0	83.4	84.2	83.8	83.8	85.5	85.9	86.7
77.5°	61.9	60.1	61.1	60.1	61.1	60.1	61.9	63.6	64.2	66.0	66.1
80°	47.0	46.6	47.9	46.6	47.9	46.6	47.0	47.0	48.3	49.1	51.2
82.5°	37.2	36.8	37.3	36.4	37.3	36.8	37.2	36.9	37.4	38.6	38.3
85°	22.4	22.0	21.6	22.0	21.6	22.0	22.4	22.0	21.6	22.0	22.4
87.5°	11.3	11.0	11.2	11.2	11.2	11.0	11.3	11.0	11.0	10.8	10.7
90°	17.9	17.9	18.8	18.8	18.8	17.9	17.9	17.9	16.3	15.5	14.7
92.5°	56.3	54.4	53.2	51.9	53.2	54.4	56.3	66.8	78.8	104.7	144.2
95°	235.2	210.8	204.3	191.3	204.3	210.8	235.2	293.0	361.3	461.5	585.2
97.5°	541.9	496.3	472.7	462.3	472.7	496.3	541.9	592.2	687.2	784.7	871.6
100°	736.5	678.0	647.8	634.9	647.8	678.0	736.5	792.7	877.3	961.2	1001.1
102.5°	911.7	870.1	837.3	827.5	837.3	870.1	911.7	971.8	1029.1	1069.3	1044.7
105°	1131.3	1104.5	1088.2	1078.4	1088.2	1104.5	1131.3	1157.3	1166.3	1130.5	1019.0
107.5°	1223.6	1223.4	1218.1	1211.5	1218.1	1223.4	1223.6	1210.4	1167.9	1076.0	927.2
110°	1234.7	1250.1	1255.8	1255.8	1255.8	1250.1	1234.7	1198.1	1128.9	1014.1	859.5



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1204.0	1230.6	1244.8	1250.6	1244.8	1230.6	1204.0	1150.6	1068.9	952.9	806.1
115°	1128.9	1167.9	1190.7	1201.3	1190.7	1167.9	1128.9	1065.4	976.6	865.2	739.0
117.5°	1045.4	1085.7	1108.3	1114.8	1108.3	1085.7	1045.4	981.9	900.5	804.5	695.7
120°	991.3	1030.4	1052.4	1058.9	1052.4	1030.4	991.3	931.1	859.5	770.0	672.3
122.5°	945.7	981.5	1003.6	1009.4	1003.6	981.5	945.7	892.0	824.9	745.2	654.7
125°	887.1	920.5	938.4	946.6	938.4	920.5	887.1	841.6	782.9	712.2	629.2
127.5°	842.9	872.3	889.2	892.8	889.2	872.3	842.9	801.5	746.7	680.6	603.1
130°	815.5	842.4	858.7	863.6	858.7	842.4	815.5	774.9	721.9	658.4	586.9
132.5°	786.8	813.8	828.7	834.2	828.7	813.8	786.8	746.2	695.2	637.6	570.5
135°	739.8	766.7	781.3	786.2	781.3	766.7	739.8	704.0	657.6	605.5	549.3
137.5°	691.6	716.1	729.6	734.9	729.6	716.1	691.6	659.6	620.2	576.9	531.5
140°	661.7	682.9	695.0	699.1	695.0	682.9	661.7	631.6	597.4	559.9	521.7
142.5°	633.1	650.9	662.5	665.9	662.5	650.9	633.1	607.5	577.9	545.6	513.2
145°	594.1	608.0	616.9	620.2	616.9	608.0	594.1	574.6	552.6	527.4	502.1
147.5°	563.7	574.8	580.0	581.5	580.0	574.8	563.7	548.2	531.7	512.3	491.8
150°	546.1	555.9	559.1	559.9	559.1	555.9	546.1	533.9	519.3	503.8	485.9
152.5°	531.2	539.0	542.2	543.0	542.2	539.0	531.2	520.9	509.5	495.3	479.4
155°	511.1	516.8	519.3	520.1	519.3	516.8	511.1	503.0	494.1	482.7	469.6
157.5°	492.8	497.4	499.7	499.5	499.7	497.4	492.8	486.4	479.4	470.6	459.8
160°	481.0	485.1	486.7	485.9	486.7	485.1	481.0	475.3	469.6	461.5	453.3
162.5°	469.9	473.4	473.7	473.5	473.7	473.4	469.9	465.5	460.5	453.6	446.2
165°	454.1	455.8	455.8	455.8	455.8	455.8	454.1	450.9	446.9	442.0	436.3
167.5°	438.9	440.3	439.7	439.5	439.7	440.3	438.9	437.2	434.3	430.6	426.8
170°	429.7	430.6	430.6	429.7	430.6	430.6	429.7	428.1	426.5	424.0	421.6
172.5°	421.3	422.7	421.4	420.6	421.4	422.7	421.3	420.9	420.0	418.2	415.7
175°	411.0	411.8	410.2	409.4	410.2	411.8	411.0	411.0	411.0	409.4	409.4
177.5°	405.0	405.6	403.7	403.7	403.7	405.6	405.0	405.6	405.6	405.6	405.0
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	988.6	992.3	994.3	999.1	1005.8	1009.3	1014.0	1017.4	1022.1	1027.8	1032.7
5°	924.5	934.7	941.5	952.1	961.8	971.6	983.8	992.7	1004.6	1018.1	1028.7
7.5°	865.1	877.8	889.1	903.1	919.2	931.7	947.7	964.0	982.6	1001.8	1019.9
10°	827.2	839.9	853.9	871.2	887.3	904.2	923.3	942.3	965.6	987.2	1011.8
12.5°	789.6	803.6	819.4	838.7	858.2	879.9	899.3	920.7	945.7	973.7	1000.0
15°	743.0	756.5	773.5	789.9	812.4	836.1	861.9	890.3	918.3	949.6	982.2
17.5°	692.9	707.8	726.4	745.6	769.2	797.0	822.3	853.4	884.8	921.3	959.6
20°	660.4	675.6	697.7	718.8	740.5	767.5	797.6	829.3	862.7	901.3	944.0
22.5°	634.7	645.6	667.2	688.7	714.0	741.8	771.2	804.3	840.7	880.6	925.4
25°	596.5	609.2	624.8	647.3	673.5	702.8	732.4	767.5	807.3	848.0	895.8
27.5°	562.6	573.0	588.5	606.1	632.2	662.5	694.1	730.7	771.5	812.9	863.2
30°	538.5	549.9	564.8	583.3	604.1	637.2	669.3	705.3	746.8	789.5	841.1
32.5°	517.5	529.3	542.0	559.6	582.1	611.4	644.6	679.9	722.0	766.1	816.4
35°	488.1	496.2	508.0	525.4	547.4	571.1	605.0	642.2	683.3	729.0	779.3
37.5°	454.4	464.8	476.6	491.7	510.9	536.6	568.1	605.8	643.9	687.7	733.7
40°	434.8	444.5	457.6	468.6	488.9	512.3	541.0	580.4	618.5	659.6	701.5
42.5°	414.8	424.2	435.3	449.0	467.2	489.9	516.7	553.3	594.1	632.8	668.0
45°	383.5	393.3	403.9	416.5	433.5	455.5	482.2	515.6	551.2	586.8	613.4
47.5°	353.7	362.8	372.8	385.8	401.5	422.7	446.5	476.1	510.6	540.9	559.9
50°	332.3	340.8	351.8	364.5	379.8	399.7	422.5	451.7	480.5	508.0	525.4
52.5°	311.4	320.8	331.8	342.8	357.4	377.3	398.4	423.6	451.0	473.4	487.8
55°	279.8	288.7	298.9	310.3	324.7	341.6	364.1	384.0	405.5	424.6	433.1
57.5°	249.4	257.2	266.8	278.7	291.6	307.4	325.1	344.3	359.5	373.0	382.5
60°	229.4	236.2	245.1	255.3	269.2	283.6	299.7	317.5	329.4	340.8	349.7
62.5°	209.1	215.6	224.1	233.3	245.6	258.9	274.3	288.7	300.3	307.9	318.2
65°	178.6	185.0	192.2	201.9	211.7	222.7	236.7	247.2	255.3	263.7	270.1
67.5°	150.3	155.6	162.4	170.0	178.2	188.8	199.7	208.5	213.9	219.1	226.7
70°	131.7	135.9	141.4	147.3	156.2	166.8	175.3	182.1	185.9	190.9	200.2
72.5°	112.7	117.6	122.8	128.7	135.9	144.8	152.2	159.0	161.4	165.5	171.5
75°	88.9	91.5	95.7	99.9	105.0	112.6	119.8	121.5	123.6	127.0	131.3
77.5°	67.3	69.5	71.2	74.0	78.0	84.1	88.0	90.5	91.0	92.3	96.4
80°	53.3	54.6	56.3	58.5	60.1	65.2	67.3	69.9	70.7	72.0	74.1
82.5°	39.1	40.4	41.4	43.2	45.9	47.9	50.1	52.6	52.7	53.6	54.1
85°	22.8	23.3	22.4	23.3	23.7	24.5	26.7	28.8	28.4	28.0	29.2
87.5°	10.9	10.8	10.0	10.9	9.9	10.1	9.8	9.8	10.1	10.5	11.0
90°	13.9	13.0	11.4	10.6	9.0	8.2	6.5	4.9	3.3	1.6	0.8
92.5°	212.4	262.4	266.6	185.7	111.2	66.8	43.0	28.9	18.9	12.1	9.9
95°	705.6	721.1	588.5	363.8	184.7	97.7	61.1	43.1	34.2	27.6	26.8
97.5°	892.8	770.1	525.5	290.4	159.2	101.6	75.2	59.1	50.1	45.6	44.6
100°	938.4	734.9	468.8	263.7	157.9	110.7	86.3	70.8	61.9	58.6	57.0
102.5°	911.1	673.1	425.8	252.7	163.8	121.7	98.0	83.8	74.2	71.6	70.7
105°	823.7	590.0	384.2	248.3	175.8	140.0	117.2	104.2	96.0	92.0	92.0
107.5°	734.4	533.0	366.6	255.8	193.7	159.1	138.5	125.0	118.3	114.5	112.8
110°	683.6	506.2	361.3	262.9	206.8	173.3	152.2	140.0	132.6	129.4	127.8



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	645.9	490.6	361.3	272.0	219.1	187.0	166.5	154.3	147.0	144.4	142.8
115°	604.7	473.7	363.8	285.7	238.5	208.4	188.0	175.8	168.4	166.0	164.4
117.5°	580.2	465.4	369.2	301.3	258.4	229.8	210.2	196.3	189.0	186.4	183.9
120°	566.5	461.5	374.4	311.7	272.6	244.2	223.8	210.0	202.7	199.4	197.0
122.5°	554.7	458.2	379.0	323.4	286.3	257.9	237.5	222.3	215.0	212.4	210.7
125°	538.8	454.1	386.6	339.4	304.4	277.5	256.4	240.9	233.6	229.5	227.9
127.5°	524.2	452.2	395.3	354.0	321.8	296.0	274.8	258.4	249.1	243.9	241.4
130°	514.4	450.9	400.5	363.8	332.9	307.6	286.5	269.4	258.9	252.3	249.9
132.5°	506.5	450.9	406.3	372.3	343.3	318.0	296.9	279.2	267.3	259.4	256.4
135°	497.3	450.9	414.3	384.2	357.3	332.1	310.1	293.0	280.0	270.2	266.9
137.5°	489.0	451.8	421.6	393.0	367.2	344.3	321.6	304.9	291.9	282.7	280.3
140°	485.1	452.5	424.9	398.8	374.4	350.8	328.8	313.3	300.4	290.6	288.1
142.5°	481.8	453.1	426.8	402.0	379.0	356.6	336.0	321.1	308.1	299.1	297.3
145°	477.0	452.5	428.9	406.9	386.6	365.4	346.7	332.1	320.7	312.5	310.9
147.5°	471.9	450.4	429.7	409.9	391.5	372.9	356.4	343.8	333.2	326.2	325.2
150°	468.0	448.4	429.7	411.8	394.8	376.8	363.0	351.6	341.0	335.3	333.7
152.5°	463.4	445.9	429.1	413.1	398.0	381.4	368.8	358.1	348.9	343.8	342.8
155°	455.8	441.2	427.3	414.3	401.2	387.4	376.0	367.9	359.7	354.8	354.8
157.5°	448.6	436.3	425.2	415.1	404.0	392.2	383.5	376.3	369.3	365.4	365.6
160°	442.8	433.0	423.2	415.1	405.3	394.8	387.4	380.9	375.2	371.9	372.8
162.5°	437.6	429.1	421.3	414.4	406.6	397.4	391.3	386.1	381.1	377.8	378.6
165°	429.7	423.2	418.3	413.4	406.9	400.5	395.6	392.3	388.2	385.8	387.4
167.5°	422.1	417.5	413.8	411.5	406.9	401.5	398.5	396.2	394.0	392.5	393.3
170°	417.5	414.3	411.8	410.2	406.9	402.8	400.5	398.8	397.2	396.4	397.2
172.5°	412.9	410.3	409.2	408.9	406.3	402.8	401.7	400.7	399.2	398.4	399.8
175°	406.9	406.1	406.1	406.9	405.3	402.8	402.8	402.8	402.0	401.2	402.8
177.5°	404.3	403.7	403.7	405.0	404.3	403.0	403.0	403.7	403.0	403.0	404.3
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1036.3	1039.4	1043.8	1048.9	1053.0	1057.4	1059.7	1059.7	1061.8	1066.2	1071.9
5°	1039.3	1050.4	1060.9	1074.5	1085.0	1097.3	1106.6	1115.5	1123.6	1133.7	1144.3
7.5°	1038.4	1056.7	1075.8	1097.1	1120.7	1139.4	1158.6	1173.7	1188.5	1208.0	1223.4
10°	1035.1	1058.7	1084.6	1111.7	1141.3	1167.2	1190.4	1211.6	1231.9	1253.1	1272.1
12.5°	1029.0	1059.2	1090.7	1123.2	1160.7	1190.2	1220.3	1242.8	1266.5	1289.6	1313.1
15°	1019.9	1055.4	1093.5	1138.8	1184.5	1217.6	1247.2	1276.4	1298.4	1324.6	1347.1
17.5°	1000.9	1046.8	1094.7	1144.2	1188.1	1226.5	1257.6	1285.3	1308.8	1337.7	1368.2
20°	989.8	1039.3	1089.2	1142.2	1184.1	1223.4	1253.5	1282.3	1311.5	1349.2	1386.4
22.5°	974.2	1027.1	1080.1	1130.3	1174.6	1212.6	1243.7	1279.0	1317.3	1360.0	1405.1
25°	949.6	1004.2	1056.6	1104.5	1147.7	1186.7	1229.0	1276.4	1323.0	1379.2	1444.1
27.5°	918.4	970.9	1017.8	1068.4	1111.3	1160.8	1213.7	1265.0	1332.2	1409.7	1490.5
30°	895.0	944.9	989.4	1037.2	1085.9	1140.5	1199.8	1260.3	1340.3	1431.3	1527.5
32.5°	867.9	913.1	957.2	1003.3	1059.5	1119.5	1182.5	1256.5	1352.2	1455.7	1555.2
35°	820.8	861.5	904.2	955.4	1015.2	1080.4	1160.8	1251.0	1366.5	1477.9	1567.2
37.5°	771.6	803.6	846.6	900.7	965.6	1041.1	1132.4	1241.9	1360.7	1460.5	1498.5
40°	733.7	763.7	809.0	865.8	930.1	1012.6	1115.1	1227.7	1347.1	1416.5	1413.6
42.5°	696.0	726.4	770.1	827.1	894.2	986.6	1092.1	1209.1	1309.9	1336.3	1281.2
45°	638.4	666.8	709.6	767.1	839.1	936.0	1046.9	1159.1	1223.4	1180.7	1071.5
47.5°	579.7	607.2	646.9	703.3	781.8	883.3	988.1	1080.2	1089.2	997.4	866.4
50°	541.0	566.9	604.5	664.6	740.9	839.9	941.1	1013.5	991.1	878.9	743.8
52.5°	503.4	528.2	563.5	620.3	698.1	795.2	885.6	942.3	890.5	771.2	649.6
55°	447.9	471.6	507.2	559.2	629.9	718.8	798.0	818.7	742.6	622.3	524.1
57.5°	395.2	412.5	447.7	493.7	561.8	640.3	697.0	693.2	609.2	500.9	430.5
60°	360.3	375.9	409.4	451.7	516.5	586.8	626.6	609.6	524.5	435.2	367.5
62.5°	327.8	342.4	370.4	409.4	465.0	526.1	555.1	531.7	451.3	372.9	319.0
65°	278.6	289.1	311.6	347.6	391.2	433.5	459.3	425.0	353.9	294.6	254.0
67.5°	232.6	241.7	261.7	287.6	317.6	346.8	357.3	325.1	269.9	229.9	201.3
70°	202.8	211.2	224.8	248.9	268.8	289.6	294.6	265.9	219.7	189.2	171.5
72.5°	174.3	182.1	194.0	211.0	224.8	236.8	239.1	212.4	177.0	156.0	142.4
75°	132.9	139.7	147.3	153.7	162.6	164.7	163.8	143.1	124.0	110.1	102.5
77.5°	97.7	100.5	105.2	107.7	108.1	107.9	103.6	90.5	80.7	74.9	71.8
80°	75.3	77.5	78.8	79.6	80.0	75.7	71.1	63.1	59.7	56.3	52.5
82.5°	54.7	56.2	57.4	57.6	55.3	51.8	47.5	43.5	41.1	39.4	37.9
85°	29.6	30.1	29.6	27.6	24.5	23.3	22.4	21.6	21.2	20.7	20.7
87.5°	10.8	10.1	8.8	9.5	9.8	9.6	9.9	9.7	9.7	9.9	10.0
90°	1.6	3.3	4.9	6.5	8.2	9.0	10.6	11.4	13.0	13.9	14.7
92.5°	12.1	18.9	28.9	43.0	66.8	111.2	185.7	266.6	262.4	212.4	144.2
95°	27.6	34.2	43.1	61.1	97.7	184.7	363.8	588.5	721.1	705.6	585.2
97.5°	45.6	50.1	59.1	75.2	101.6	159.2	290.4	525.5	770.1	892.8	871.6
100°	58.6	61.9	70.8	86.3	110.7	157.9	263.7	468.8	734.9	938.4	1001.1
102.5°	71.6	74.2	83.8	98.0	121.7	163.8	252.7	425.8	673.1	911.1	1044.7
105°	92.0	96.0	104.2	117.2	140.0	175.8	248.3	384.2	590.0	823.7	1019.0
107.5°	114.5	118.3	125.0	138.5	159.1	193.7	255.8	366.6	533.0	734.4	927.2
110°	129.4	132.6	140.0	152.2	173.3	206.8	262.9	361.3	506.2	683.6	859.5



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.4	147.0	154.3	166.5	187.0	219.1	272.0	361.3	490.6	645.9	806.1
115°	166.0	168.4	175.8	188.0	208.4	238.5	285.7	363.8	473.7	604.7	739.0
117.5°	186.4	189.0	196.3	210.2	229.8	258.4	301.3	369.2	465.4	580.2	695.7
120°	199.4	202.7	210.0	223.8	244.2	272.6	311.7	374.4	461.5	566.5	672.3
122.5°	212.4	215.0	222.3	237.5	257.9	286.3	323.4	379.0	458.2	554.7	654.7
125°	229.5	233.6	240.9	256.4	277.5	304.4	339.4	386.6	454.1	538.8	629.2
127.5°	243.9	249.1	258.4	274.8	296.0	321.8	354.0	395.3	452.2	524.2	603.1
130°	252.3	258.9	269.4	286.5	307.6	332.9	363.8	400.5	450.9	514.4	586.9
132.5°	259.4	267.3	279.2	296.9	318.0	343.3	372.3	406.3	450.9	506.5	570.5
135°	270.2	280.0	293.0	310.1	332.1	357.3	384.2	414.3	450.9	497.3	549.3
137.5°	282.7	291.9	304.9	321.6	344.3	367.2	393.0	421.6	451.8	489.0	531.5
140°	290.6	300.4	313.3	328.8	350.8	374.4	398.8	424.9	452.5	485.1	521.7
142.5°	299.1	308.1	321.1	336.0	356.6	379.0	402.0	426.8	453.1	481.8	513.2
145°	312.5	320.7	332.1	346.7	365.4	386.6	406.9	428.9	452.5	477.0	502.1
147.5°	326.2	333.2	343.8	356.4	372.9	391.5	409.9	429.7	450.4	471.9	491.8
150°	335.3	341.0	351.6	363.0	376.8	394.8	411.8	429.7	448.4	468.0	485.9
152.5°	343.8	348.9	358.1	368.8	381.4	398.0	413.1	429.1	445.9	463.4	479.4
155°	354.8	359.7	367.9	376.0	387.4	401.2	414.3	427.3	441.2	455.8	469.6
157.5°	365.4	369.3	376.3	383.5	392.2	404.0	415.1	425.2	436.3	448.6	459.8
160°	371.9	375.2	380.9	387.4	394.8	405.3	415.1	423.2	433.0	442.8	453.3
162.5°	377.8	381.1	386.1	391.3	397.4	406.6	414.4	421.3	429.1	437.6	446.2
165°	385.8	388.2	392.3	395.6	400.5	406.9	413.4	418.3	423.2	429.7	436.3
167.5°	392.5	394.0	396.2	398.5	401.5	406.9	411.5	413.8	417.5	422.1	426.8
170°	396.4	397.2	398.8	400.5	402.8	406.9	410.2	411.8	414.3	417.5	421.6
172.5°	398.4	399.2	400.7	401.7	402.8	406.3	408.9	409.2	410.3	412.9	415.7
175°	401.2	402.0	402.8	402.8	402.8	405.3	406.9	406.1	406.1	406.9	409.4
177.5°	403.0	403.0	403.7	403.0	403.0	404.3	405.0	403.7	403.7	404.3	405.0
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1076.3	1076.3	1082.1	1081.7	1085.5	1084.1	1084.8
5°	1157.0	1164.2	1170.5	1174.8	1181.1	1182.8	1181.9
7.5°	1240.6	1256.6	1264.4	1275.1	1277.1	1282.6	1282.1
10°	1292.5	1308.1	1320.0	1329.3	1334.0	1339.9	1340.3
12.5°	1333.1	1346.4	1356.9	1365.5	1371.2	1373.0	1374.2
15°	1364.9	1379.6	1392.0	1404.2	1411.4	1416.9	1419.9
17.5°	1396.9	1419.8	1441.4	1458.1	1468.1	1476.5	1476.4
20°	1421.6	1447.8	1475.0	1494.0	1513.4	1521.9	1523.2
22.5°	1448.0	1488.2	1523.1	1552.6	1578.2	1587.0	1590.2
25°	1502.8	1555.3	1609.2	1650.7	1680.3	1697.6	1700.1
27.5°	1569.1	1640.2	1696.8	1735.0	1759.7	1772.5	1775.3
30°	1615.9	1681.6	1732.3	1761.1	1772.5	1774.3	1767.9
32.5°	1636.9	1686.0	1706.3	1704.5	1682.1	1667.2	1661.5
35°	1611.3	1601.1	1551.5	1492.3	1447.0	1418.2	1410.5
37.5°	1466.3	1378.7	1287.5	1198.0	1150.3	1126.1	1084.4
40°	1323.4	1198.5	1103.7	1028.3	974.5	931.3	921.2
42.5°	1162.1	1033.2	938.4	873.8	831.0	801.3	788.4
45°	933.9	823.0	744.7	695.1	662.1	640.5	630.8
47.5°	747.0	661.1	604.1	567.4	542.3	523.4	518.2
50°	644.3	575.8	527.5	496.6	477.5	463.2	457.2
52.5°	559.6	504.3	467.2	441.7	423.7	414.7	409.8
55°	461.9	414.0	387.3	367.0	356.9	349.7	346.3
57.5°	377.7	343.2	323.7	309.7	300.3	295.6	294.0
60°	330.6	303.5	285.8	274.8	268.4	262.4	260.8
62.5°	288.9	267.7	253.9	244.3	237.9	235.4	234.4
65°	232.8	218.9	208.7	202.8	197.7	196.9	196.4
67.5°	185.1	176.8	171.5	165.3	163.5	160.6	160.0
70°	158.3	152.8	146.5	144.4	142.3	139.3	139.7
72.5°	134.3	128.8	124.5	121.6	120.9	119.6	120.7
75°	98.2	96.5	94.8	92.7	91.9	91.9	91.5
77.5°	70.1	68.6	66.8	65.6	65.3	63.5	64.2
80°	50.8	48.7	47.9	48.3	47.0	46.6	46.6
82.5°	37.6	36.9	36.0	36.0	35.8	35.4	35.7
85°	20.7	20.3	20.3	19.9	19.9	19.5	19.5
87.5°	10.5	11.0	10.7	10.4	10.4	10.8	11.2
90°	15.5	16.3	17.9	17.9	17.9	18.8	18.8
92.5°	104.7	78.8	66.8	56.3	54.4	53.2	51.9
95°	461.5	361.3	293.0	235.2	210.8	204.3	191.3
97.5°	784.7	687.2	592.2	541.9	496.3	472.7	462.3
100°	961.2	877.3	792.7	736.5	678.0	647.8	634.9
102.5°	1069.3	1029.1	971.8	911.7	870.1	837.3	827.5
105°	1130.5	1166.3	1157.3	1131.3	1104.5	1088.2	1078.4
107.5°	1076.0	1167.9	1210.4	1223.6	1223.4	1218.1	1211.5
110°	1014.1	1128.9	1198.1	1234.7	1250.1	1255.8	1255.8



TEST NUMBER: P333570-930

CATALOG NUMBER: S125RDIP-S850D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	952.9	1068.9	1150.6	1204.0	1230.6	1244.8	1250.6
115°	865.2	976.6	1065.4	1128.9	1167.9	1190.7	1201.3
117.5°	804.5	900.5	981.9	1045.4	1085.7	1108.3	1114.8
120°	770.0	859.5	931.1	991.3	1030.4	1052.4	1058.9
122.5°	745.2	824.9	892.0	945.7	981.5	1003.6	1009.4
125°	712.2	782.9	841.6	887.1	920.5	938.4	946.6
127.5°	680.6	746.7	801.5	842.9	872.3	889.2	892.8
130°	658.4	721.9	774.9	815.5	842.4	858.7	863.6
132.5°	637.6	695.2	746.2	786.8	813.8	828.7	834.2
135°	605.5	657.6	704.0	739.8	766.7	781.3	786.2
137.5°	576.9	620.2	659.6	691.6	716.1	729.6	734.9
140°	559.9	597.4	631.6	661.7	682.9	695.0	699.1
142.5°	545.6	577.9	607.5	633.1	650.9	662.5	665.9
145°	527.4	552.6	574.6	594.1	608.0	616.9	620.2
147.5°	512.3	531.7	548.2	563.7	574.8	580.0	581.5
150°	503.8	519.3	533.9	546.1	555.9	559.1	559.9
152.5°	495.3	509.5	520.9	531.2	539.0	542.2	543.0
155°	482.7	494.1	503.0	511.1	516.8	519.3	520.1
157.5°	470.6	479.4	486.4	492.8	497.4	499.7	499.5
160°	461.5	469.6	475.3	481.0	485.1	486.7	485.9
162.5°	453.6	460.5	465.5	469.9	473.4	473.7	473.5
165°	442.0	446.9	450.9	454.1	455.8	455.8	455.8
167.5°	430.6	434.3	437.2	438.9	440.3	439.7	439.5
170°	424.0	426.5	428.1	429.7	430.6	430.6	429.7
172.5°	418.2	420.0	420.9	421.3	422.7	421.4	420.6
175°	409.4	411.0	411.0	411.0	411.8	410.2	409.4
177.5°	405.6	405.6	405.6	405.0	405.6	403.7	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7

(END OF REPORT)