

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333324

Luminaire Tested: **S125DIP-S1270D1035U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333324
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D1035U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8898.3 lumens
Efficiency: N/A
Efficacy: 133.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58																				
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	56	54	50																				
2	91	84	78	73	85	78	73	69	68	64	61	59	56	53	50	48	46	42																				
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	45	42	40	36																				
4	76	66	58	52	71	61	54	49	54	48	44	47	42	39	40	37	34	31																				
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	33	30	27																				
6	65	53	44	39	60	49	42	37	44	38	33	38	33	30	33	29	26	24																				
7	60	47	39	34	56	45	37	32	39	34	29	35	30	26	30	26	23	21																				
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19																				
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	22	19	17																				
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	24	20	17	15																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11861	11861	11861	11861
5°	13736	11902	10421	11902
10°	15980	11840	9130	11840
15°	17690	11753	8423	11753
20°	19801	11615	7854	11615
25°	23197	11460	7577	11460
30°	25055	11307	7337	11307
35°	20601	11020	7179	11020
40°	14643	10620	7006	10620
45°	11249	10082	6906	10082
50°	9602	9414	6893	9414
55°	8550	8760	6952	8760
60°	7713	8045	7129	8045
65°	7124	7326	7314	7326
70°	6477	6579	7419	6579
75°	5719	5797	7354	5797
80°	4813	4727	6724	4727
85°	3809	3409	5432	3409



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.8	2.0
10°-20°	526.4	5.9
20°-30°	854.8	9.6
30°-40°	1042.7	11.7
40°-50°	948.5	10.7
50°-60°	755.5	8.5
60°-70°	526.2	5.9
70°-80°	280.6	3.2
80°-90°	73.6	0.8
90°-100°	358.9	4.0
100°-110°	771.5	8.7
110°-120°	724.1	8.1
120°-130°	586.8	6.6
130°-140°	470.9	5.3
140°-150°	355.4	4.0
150°-160°	250.1	2.8
160°-170°	147.4	1.7
170°-180°	48.0	0.5
0°-30°	1558.0	17.5
0°-40°	2600.7	29.2
0°-60°	4304.7	48.4
0°-90°	5185.2	58.3
90°-120°	1854.5	20.8
90°-150°	3267.6	36.7
90°-180°	3713.0	41.7
0°-180°	8898.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1837	1837	1837	1837	1837	
5°	2119	1836	1607	1836	2119	214
15°	2646	1758	1260	1758	2646	757
25°	3255	1608	1063	1608	3255	1487
35°	2613	1398	910	1398	2613	1599
45°	1232	1104	756	1104	1232	986
55°	759	778	617	778	759	684
65°	466	479	479	479	466	463
75°	229	232	295	232	229	247
85°	51	46	73	46	51	60
90°	23	1	23	1	23	18
95°	235	33	235	33	235	332
105°	1323	113	1323	113	1323	1315
115°	1474	202	1474	202	1474	1440
125°	1161	280	1161	280	1161	1050
135°	964	327	964	327	964	747
145°	761	381	761	381	761	483
155°	638	435	638	435	638	297
165°	559	475	559	475	559	160
175°	502	494	502	494	502	49
180°	495	495	495	495	495	



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1942.6	1940.1	1937.6	1932.6	1936.3	1925.7	1920.7	1912.0	1901.4	1897.7	1893.3
5°	2118.7	2122.6	2126.5	2110.2	2111.7	2100.8	2075.9	2055.6	2039.2	2018.2	2003.4
7.5°	2330.8	2321.6	2320.8	2310.2	2292.0	2277.3	2251.1	2217.7	2185.5	2148.7	2118.3
10°	2436.8	2437.6	2430.6	2418.1	2398.6	2384.6	2350.3	2317.5	2277.8	2231.0	2197.5
12.5°	2516.6	2519.9	2511.0	2494.2	2484.6	2453.2	2426.3	2387.4	2340.1	2302.7	2251.7
15°	2645.7	2637.1	2630.9	2609.8	2593.5	2560.7	2517.9	2477.3	2425.9	2378.3	2330.8
17.5°	2770.1	2777.0	2765.3	2746.1	2695.3	2657.1	2599.6	2544.0	2480.0	2416.2	2359.5
20°	2881.1	2887.4	2869.4	2835.9	2775.1	2736.9	2661.3	2589.6	2515.5	2433.7	2371.3
22.5°	3019.6	3014.6	2990.4	2939.4	2886.7	2816.1	2734.3	2646.9	2554.2	2461.7	2378.8
25°	3255.3	3222.5	3207.7	3144.6	3075.2	2971.5	2859.3	2731.4	2616.1	2493.7	2387.7
27.5°	3385.9	3375.6	3359.1	3315.2	3242.2	3131.3	2999.0	2843.2	2680.5	2526.0	2387.2
30°	3359.7	3361.3	3362.9	3348.8	3302.1	3218.6	3086.9	2919.3	2726.0	2552.2	2391.6
32.5°	3127.8	3156.1	3183.3	3215.4	3228.5	3212.4	3129.9	2978.6	2779.6	2582.1	2389.1
35°	2613.0	2621.5	2709.6	2796.9	2915.4	3007.4	3069.0	3001.9	2834.3	2607.5	2386.1
37.5°	2037.4	2079.5	2140.4	2239.1	2410.1	2563.2	2760.1	2850.7	2796.6	2615.8	2380.7
40°	1736.8	1775.8	1815.5	1916.1	2060.3	2245.8	2469.5	2660.5	2704.9	2589.6	2362.0
42.5°	1504.8	1535.7	1579.8	1655.4	1775.9	1940.2	2154.0	2403.6	2557.1	2513.5	2322.7
45°	1231.6	1251.1	1285.4	1345.5	1432.8	1561.4	1750.0	2022.9	2260.6	2339.3	2229.4
47.5°	1054.2	1054.1	1080.7	1122.2	1185.2	1294.5	1434.0	1647.8	1901.7	2089.6	2080.9
50°	955.7	951.8	972.8	1008.7	1058.6	1131.1	1264.4	1435.1	1679.1	1891.9	1951.1
52.5°	870.9	871.3	884.3	910.8	952.6	1014.5	1114.1	1268.0	1476.4	1694.8	1806.5
55°	759.3	756.1	770.9	788.9	819.3	859.8	931.5	1049.2	1218.4	1433.5	1578.5
57.5°	657.0	665.6	671.5	684.0	709.2	736.3	796.8	883.2	1017.4	1202.0	1355.3
60°	597.1	605.7	610.4	622.8	643.1	666.5	713.3	783.4	896.5	1055.5	1207.5
62.5°	543.5	550.2	551.7	563.0	579.5	602.3	639.1	698.0	787.3	926.4	1075.3
65°	466.2	466.2	469.3	481.0	488.8	509.0	537.1	580.0	651.7	760.0	887.1
67.5°	391.6	395.4	394.6	399.7	406.9	422.7	442.8	478.2	531.3	610.4	712.0
70°	343.0	346.1	345.3	349.2	357.0	367.2	383.5	417.0	455.2	523.1	610.4
72.5°	299.3	300.6	298.6	303.7	308.4	317.3	335.5	353.4	389.1	446.4	518.1
75°	229.2	230.7	232.3	235.4	240.1	244.8	254.1	272.1	295.4	338.3	384.3
77.5°	171.8	168.8	172.6	172.1	174.8	178.4	186.6	196.1	215.3	242.4	278.0
80°	129.4	130.2	130.2	131.0	134.9	137.2	144.2	151.2	166.0	186.3	211.3
82.5°	94.5	96.5	95.3	96.7	99.9	101.6	105.5	111.3	119.9	135.8	153.9
85°	51.4	47.6	49.1	50.7	50.7	51.4	54.6	56.9	61.6	67.8	74.8
87.5°	19.6	20.8	21.2	21.2	21.9	21.5	23.7	23.5	25.2	26.9	29.0
90°	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0	17.0	16.0	14.0
92.5°	63.7	65.3	66.7	69.1	81.9	96.6	128.4	176.9	260.5	321.8	327.0
95°	234.6	250.6	258.6	288.5	359.4	443.2	566.0	717.8	865.5	884.5	721.8
97.5°	567.0	579.8	608.7	664.7	726.3	842.9	962.5	1069.0	1095.1	944.6	644.5
100°	778.7	794.6	831.6	903.4	972.3	1076.1	1179.0	1227.9	1151.0	901.4	575.0
102.5°	1015.0	1027.0	1067.2	1118.3	1191.9	1262.2	1311.5	1281.4	1117.5	825.6	522.3
105°	1322.7	1334.7	1354.7	1387.6	1419.5	1430.5	1386.6	1249.8	1010.3	723.7	471.2
107.5°	1486.0	1494.0	1500.6	1500.8	1484.6	1432.5	1319.7	1137.2	900.8	653.7	449.6
110°	1540.3	1540.3	1533.3	1514.4	1469.5	1384.6	1243.8	1054.2	838.5	620.9	443.2



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1533.9	1526.8	1509.4	1476.8	1411.2	1311.1	1168.8	988.7	792.2	601.8	443.2
115°	1473.5	1460.5	1432.5	1384.6	1306.7	1197.9	1061.2	906.4	741.7	581.0	446.2
117.5°	1367.4	1359.4	1331.7	1282.2	1204.3	1104.5	986.7	853.3	711.6	570.8	452.8
120°	1298.8	1290.8	1263.8	1215.9	1142.0	1054.2	944.4	824.6	694.8	566.0	459.2
122.5°	1238.1	1230.9	1203.9	1160.0	1094.1	1011.8	914.0	803.0	680.4	562.0	464.8
125°	1161.0	1151.0	1129.0	1088.1	1032.2	960.3	873.5	771.7	660.9	557.0	474.2
127.5°	1095.1	1090.7	1069.9	1033.8	983.1	915.8	834.8	739.7	642.9	554.6	484.8
130°	1059.2	1053.2	1033.2	1000.3	950.4	885.5	807.6	719.8	630.9	553.0	491.2
132.5°	1023.2	1016.4	998.1	965.1	915.2	852.7	782.0	699.8	621.3	553.0	498.3
135°	964.3	958.3	940.4	907.4	863.5	806.6	742.7	673.8	609.9	553.0	508.1
137.5°	901.4	894.9	878.3	848.3	809.0	760.7	707.6	651.9	599.8	554.2	517.1
140°	857.5	852.5	837.6	811.6	774.7	732.7	686.8	639.9	595.0	555.0	521.1
142.5°	816.8	812.6	798.4	776.5	745.1	708.8	669.2	629.5	591.0	555.8	523.5
145°	760.7	756.7	745.7	728.7	704.8	677.8	646.9	615.9	585.0	555.0	526.1
147.5°	713.2	711.4	705.0	691.4	672.4	652.1	628.3	603.2	578.8	552.4	527.1
150°	686.8	685.8	681.8	669.8	654.9	636.9	617.9	596.0	574.0	550.0	527.1
152.5°	666.0	665.0	661.1	651.5	638.9	624.9	607.5	588.0	568.4	546.9	526.3
155°	637.9	636.9	633.9	626.9	616.9	606.0	592.0	576.0	559.0	541.1	524.1
157.5°	612.7	612.9	610.1	604.4	596.6	588.0	577.2	564.0	550.2	535.1	521.5
160°	596.0	597.0	595.0	590.0	583.0	576.0	566.0	556.0	543.1	531.1	519.1
162.5°	580.8	581.0	580.6	576.4	571.0	564.8	556.4	547.3	536.7	526.3	516.7
165°	559.0	559.0	559.0	557.0	553.0	548.1	542.1	535.1	527.1	519.1	513.1
167.5°	539.1	539.3	540.1	538.3	536.3	532.7	528.1	523.5	517.7	512.1	507.5
170°	527.1	528.1	528.1	527.1	525.1	523.1	520.1	517.1	512.1	508.1	505.1
172.5°	515.9	516.9	518.5	516.7	516.3	515.1	512.9	509.9	506.5	503.3	501.9
175°	502.1	503.1	505.1	504.1	504.1	504.1	502.1	502.1	499.1	498.1	498.1
177.5°	495.1	495.1	497.5	496.7	497.5	497.5	497.5	496.7	495.9	495.1	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1889.6	1885.2	1880.2	1871.5	1860.9	1855.3	1846.5	1840.9	1829.7	1820.3	1810.4
5°	1985.4	1965.2	1946.5	1922.3	1895.8	1878.6	1858.4	1835.8	1812.4	1788.2	1761.7
7.5°	2084.8	2048.9	2009.9	1968.0	1927.0	1889.2	1853.2	1817.8	1784.8	1744.9	1711.1
10°	2151.5	2106.3	2057.9	2001.0	1945.7	1897.4	1848.2	1805.4	1761.7	1714.9	1673.6
12.5°	2218.2	2158.0	2089.7	2027.2	1960.7	1902.3	1844.5	1789.8	1734.9	1683.1	1635.0
15°	2265.3	2212.3	2149.1	2060.3	1985.4	1905.2	1828.8	1757.8	1691.6	1633.9	1573.1
17.5°	2296.3	2228.0	2160.2	2074.9	1976.9	1887.1	1800.5	1719.3	1644.6	1571.5	1512.9
20°	2301.9	2231.8	2160.8	2077.4	1976.9	1874.0	1787.4	1690.0	1609.7	1534.1	1462.4
22.5°	2300.1	2220.5	2143.4	2057.5	1959.4	1864.6	1760.0	1660.7	1573.5	1499.2	1424.3
25°	2282.4	2197.5	2100.8	2014.3	1917.6	1817.1	1711.1	1608.2	1519.3	1434.3	1360.3
27.5°	2267.8	2157.6	2048.1	1947.2	1853.9	1761.7	1660.2	1554.8	1456.3	1370.2	1300.4
30°	2249.7	2128.9	2005.7	1900.5	1804.6	1714.9	1619.1	1516.2	1413.3	1329.1	1254.3
32.5°	2233.5	2092.7	1962.7	1848.1	1746.6	1659.4	1571.0	1473.1	1372.1	1286.7	1211.8
35°	2202.2	2039.2	1890.3	1760.9	1652.6	1562.9	1488.9	1397.7	1304.9	1222.3	1150.6
37.5°	2162.4	1969.1	1809.3	1673.6	1554.8	1460.4	1391.4	1321.4	1232.4	1152.8	1087.9
40°	2131.2	1919.2	1750.0	1611.3	1488.1	1389.9	1326.0	1259.7	1185.7	1111.6	1043.0
42.5°	2091.9	1874.3	1690.2	1540.8	1418.9	1323.2	1256.1	1199.8	1134.5	1065.5	1001.8
45°	2019.7	1792.9	1593.3	1432.8	1309.6	1215.3	1145.9	1103.8	1054.7	989.2	935.4
47.5°	1913.6	1695.1	1488.7	1323.0	1195.9	1108.5	1043.5	1003.1	968.5	919.8	871.0
50°	1819.4	1622.2	1413.3	1248.8	1121.7	1033.6	973.6	937.0	907.4	869.9	828.6
52.5°	1714.0	1530.5	1339.1	1176.5	1050.6	963.8	905.0	872.8	848.1	821.3	780.6
55°	1546.6	1390.7	1212.9	1058.6	942.4	857.5	806.0	778.0	757.7	737.4	712.5
57.5°	1362.1	1240.2	1082.8	941.7	834.7	757.4	709.4	682.1	666.3	655.9	641.2
60°	1232.4	1128.0	992.3	863.7	759.3	690.7	643.9	622.8	609.6	601.0	590.1
62.5°	1112.1	1026.3	900.7	783.3	691.9	627.0	585.3	564.8	552.2	548.0	539.0
65°	934.6	868.4	764.7	667.3	589.3	534.0	498.9	479.4	471.6	466.9	467.7
67.5°	759.9	719.5	636.2	553.1	490.9	444.5	416.4	401.5	397.6	391.3	391.2
70°	653.2	622.8	552.7	480.2	424.8	389.0	364.0	348.4	344.5	341.4	340.7
72.5°	559.1	532.4	471.6	413.5	363.7	332.2	311.7	302.3	295.9	294.0	293.9
75°	420.2	405.4	357.0	311.0	276.7	254.9	240.9	232.3	227.6	226.8	227.6
77.5°	298.7	285.8	255.1	222.5	200.8	184.3	172.4	169.5	164.2	164.3	163.5
80°	224.5	215.9	196.4	170.7	152.8	138.8	132.5	127.1	125.5	123.2	125.5
82.5°	162.8	153.6	140.3	123.9	109.1	100.7	94.5	92.8	91.8	90.7	91.2
85°	80.3	81.1	73.3	60.8	54.6	49.9	46.0	46.0	45.2	44.4	45.2
87.5°	30.0	28.4	25.7	23.4	19.9	17.6	16.6	17.0	15.4	15.1	16.2
90°	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0	2.0	4.0	6.0
92.5°	227.8	136.4	81.9	52.7	35.5	23.2	14.8	12.2	14.8	23.2	35.5
95°	446.2	226.6	119.8	74.9	52.9	41.9	33.9	32.9	33.9	41.9	52.9
97.5°	356.2	195.3	124.6	92.2	72.5	61.5	55.9	54.7	55.9	61.5	72.5
100°	323.4	193.7	135.8	105.8	86.8	75.9	71.9	69.9	71.9	75.9	86.8
102.5°	309.9	200.9	149.3	120.2	102.8	91.0	87.8	86.7	87.8	91.0	102.8
105°	304.5	215.6	171.7	143.8	127.8	117.8	112.8	112.8	112.8	117.8	127.8
107.5°	313.7	237.6	195.1	169.9	153.3	145.1	140.4	138.4	140.4	145.1	153.3
110°	322.4	253.6	212.6	186.7	171.7	162.7	158.7	156.7	158.7	162.7	171.7



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	333.6	268.7	229.4	204.2	189.3	180.3	177.1	175.1	177.1	180.3	189.3
115°	350.4	292.5	255.6	230.6	215.6	206.6	203.6	201.7	203.6	206.6	215.6
117.5°	369.6	316.9	281.9	257.8	240.8	231.8	228.6	225.6	228.6	231.8	240.8
120°	382.3	334.4	299.5	274.5	257.6	248.6	244.6	241.6	244.6	248.6	257.6
122.5°	396.7	351.2	316.3	291.3	272.7	263.7	260.5	258.4	260.5	263.7	272.7
125°	416.3	373.4	340.4	314.5	295.5	286.5	281.5	279.5	281.5	286.5	295.5
127.5°	434.2	394.7	363.0	337.0	316.9	305.5	299.1	296.1	299.1	305.5	316.9
130°	446.2	408.3	377.3	351.4	330.4	317.5	309.5	306.5	309.5	317.5	330.4
132.5°	456.6	421.1	390.1	364.2	342.4	327.8	318.2	314.5	318.2	327.8	342.4
135°	471.2	438.2	407.3	380.3	359.4	343.4	331.4	327.4	331.4	343.4	359.4
137.5°	482.0	450.4	422.3	394.5	374.0	358.0	346.8	343.8	346.8	358.0	374.0
140°	489.2	459.2	430.3	403.3	384.3	368.4	356.4	353.4	356.4	368.4	384.3
142.5°	493.1	464.8	437.4	412.1	393.9	377.9	366.8	364.6	366.8	377.9	393.9
145°	499.1	474.2	448.2	425.3	407.3	393.3	383.3	381.3	383.3	393.3	407.3
147.5°	502.7	480.2	457.4	437.2	421.7	408.7	400.1	398.9	400.1	408.7	421.7
150°	505.1	484.2	462.2	445.2	431.3	418.3	411.3	409.3	411.3	418.3	431.3
152.5°	506.7	488.2	467.8	452.4	439.2	427.9	421.7	420.5	421.7	427.9	439.2
155°	508.1	492.1	475.2	461.2	451.2	441.2	435.2	435.2	435.2	441.2	451.2
157.5°	509.1	495.5	481.0	470.4	461.6	453.0	448.2	448.4	448.2	453.0	461.6
160°	509.1	497.1	484.2	475.2	467.2	460.2	456.2	457.2	456.2	460.2	467.2
162.5°	508.3	498.7	487.4	480.0	473.6	467.4	463.4	464.4	463.4	467.4	473.6
165°	507.1	499.1	491.2	485.2	481.2	476.2	473.2	475.2	473.2	476.2	481.2
167.5°	504.7	499.1	492.5	488.8	486.0	483.2	481.4	482.4	481.4	483.2	486.0
170°	503.1	499.1	494.1	491.2	489.2	487.2	486.2	487.2	486.2	487.2	489.2
172.5°	501.5	498.3	494.1	492.7	491.5	489.6	488.6	490.4	488.6	489.6	491.5
175°	499.1	497.1	494.1	494.1	494.1	493.1	492.1	494.1	492.1	493.1	494.1
177.5°	496.7	495.9	494.3	494.3	495.1	494.3	494.3	495.9	494.3	494.3	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1804.7	1797.9	1792.3	1779.8	1772.9	1763.6	1756.1	1764.2	1755.5	1759.2	1753.6
5°	1748.5	1726.6	1711.1	1688.4	1669.0	1651.0	1637.8	1635.4	1629.2	1626.1	1616.7
7.5°	1680.8	1653.5	1626.7	1597.1	1572.1	1546.7	1530.5	1517.1	1508.2	1496.5	1488.6
10°	1640.9	1604.3	1573.1	1537.2	1506.0	1478.8	1456.9	1446.0	1435.9	1421.1	1415.6
12.5°	1591.6	1553.7	1515.7	1477.4	1447.4	1417.0	1398.3	1381.8	1374.8	1358.1	1356.4
15°	1532.5	1475.6	1438.2	1399.2	1357.9	1333.0	1317.4	1299.5	1291.7	1280.0	1271.4
17.5°	1462.1	1411.2	1364.5	1324.1	1288.7	1267.7	1248.3	1236.0	1222.6	1215.0	1200.9
20°	1410.9	1362.6	1315.8	1273.0	1245.7	1221.5	1205.9	1194.2	1180.2	1176.3	1162.3
22.5°	1367.9	1314.6	1269.7	1233.7	1203.9	1176.6	1159.8	1151.8	1142.2	1130.2	1127.3
25°	1297.9	1242.6	1204.4	1168.5	1142.0	1117.1	1105.4	1095.2	1085.9	1077.3	1074.2
27.5°	1237.4	1188.0	1142.6	1110.2	1087.1	1064.4	1054.1	1041.8	1034.9	1028.0	1019.6
30°	1195.0	1144.3	1104.6	1073.4	1048.5	1028.2	1017.3	1008.7	1002.5	996.2	991.6
32.5°	1151.4	1104.4	1065.9	1035.4	1010.4	995.1	985.5	979.4	972.5	965.0	959.1
35°	1093.7	1042.2	1004.8	978.3	958.8	947.1	936.2	930.7	923.0	923.0	916.7
37.5°	1028.7	984.2	951.2	927.0	909.5	899.1	887.3	883.5	878.5	875.2	873.1
40°	990.0	948.7	917.5	893.3	874.6	866.0	856.7	850.5	847.3	843.4	841.9
42.5°	950.1	910.6	880.7	858.4	842.2	834.9	826.1	821.8	815.5	810.4	809.5
45°	889.4	851.2	824.0	806.0	792.0	783.4	778.0	768.6	765.5	759.3	758.5
47.5°	831.9	795.3	768.5	753.8	741.5	734.5	725.9	716.5	713.0	709.8	709.5
50°	788.9	755.4	730.4	716.4	704.7	694.6	686.0	679.7	677.4	677.4	679.0
52.5°	745.2	716.7	695.5	678.3	667.3	656.5	648.6	644.8	641.2	645.0	647.8
55°	681.3	652.5	636.9	620.5	609.6	597.1	593.2	591.7	589.3	595.6	598.7
57.5°	613.6	593.4	575.1	558.9	549.1	541.9	536.6	535.7	540.1	543.0	553.1
60°	570.6	547.2	530.9	518.4	506.7	502.0	500.5	498.9	502.0	510.6	523.8
62.5°	523.2	504.2	486.6	477.2	468.6	460.9	460.5	461.5	467.7	477.5	490.8
65°	453.7	437.3	425.6	414.7	407.7	403.0	404.6	407.7	414.7	428.0	442.8
67.5°	383.1	371.8	361.4	352.5	345.8	345.8	347.4	352.0	360.3	375.6	389.1
70°	337.5	325.1	316.5	312.6	307.1	304.0	308.7	316.5	323.5	337.5	349.2
72.5°	292.0	281.4	274.7	272.1	269.7	267.2	268.8	277.2	286.7	300.7	314.3
75°	224.5	220.6	215.9	212.8	210.5	212.0	213.6	221.4	229.2	244.0	259.6
77.5°	163.9	159.8	157.0	156.2	155.0	155.7	160.1	165.9	173.5	184.3	196.1
80°	123.9	122.4	120.8	120.0	120.0	120.8	127.1	131.0	138.0	148.1	157.5
82.5°	90.3	89.3	89.0	88.9	89.5	89.6	93.4	98.5	104.3	111.9	120.0
85°	47.6	46.0	48.3	49.1	47.6	49.9	51.4	54.6	56.9	60.8	64.7
87.5°	17.2	18.8	18.4	19.4	19.6	21.3	20.9	23.5	25.0	26.4	26.2
90°	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0	19.0	20.0	22.0
92.5°	52.7	81.9	136.4	227.8	327.0	321.8	260.5	176.9	128.4	96.6	81.9
95°	74.9	119.8	226.6	446.2	721.8	884.5	865.5	717.8	566.0	443.2	359.4
97.5°	92.2	124.6	195.3	356.2	644.5	944.6	1095.1	1069.0	962.5	842.9	726.3
100°	105.8	135.8	193.7	323.4	575.0	901.4	1151.0	1227.9	1179.0	1076.1	972.3
102.5°	120.2	149.3	200.9	309.9	522.3	825.6	1117.5	1281.4	1311.5	1262.2	1191.9
105°	143.8	171.7	215.6	304.5	471.2	723.7	1010.3	1249.8	1386.6	1430.5	1419.5
107.5°	169.9	195.1	237.6	313.7	449.6	653.7	900.8	1137.2	1319.7	1432.5	1484.6
110°	186.7	212.6	253.6	322.4	443.2	620.9	838.5	1054.2	1243.8	1384.6	1469.5



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.2	229.4	268.7	333.6	443.2	601.8	792.2	988.7	1168.8	1311.1	1411.2
115°	230.6	255.6	292.5	350.4	446.2	581.0	741.7	906.4	1061.2	1197.9	1306.7
117.5°	257.8	281.9	316.9	369.6	452.8	570.8	711.6	853.3	986.7	1104.5	1204.3
120°	274.5	299.5	334.4	382.3	459.2	566.0	694.8	824.6	944.4	1054.2	1142.0
122.5°	291.3	316.3	351.2	396.7	464.8	562.0	680.4	803.0	914.0	1011.8	1094.1
125°	314.5	340.4	373.4	416.3	474.2	557.0	660.9	771.7	873.5	960.3	1032.2
127.5°	337.0	363.0	394.7	434.2	484.8	554.6	642.9	739.7	834.8	915.8	983.1
130°	351.4	377.3	408.3	446.2	491.2	553.0	630.9	719.8	807.6	885.5	950.4
132.5°	364.2	390.1	421.1	456.6	498.3	553.0	621.3	699.8	782.0	852.7	915.2
135°	380.3	407.3	438.2	471.2	508.1	553.0	609.9	673.8	742.7	806.6	863.5
137.5°	394.5	422.3	450.4	482.0	517.1	554.2	599.8	651.9	707.6	760.7	809.0
140°	403.3	430.3	459.2	489.2	521.1	555.0	595.0	639.9	686.8	732.7	774.7
142.5°	412.1	437.4	464.8	493.1	523.5	555.8	591.0	629.5	669.2	708.8	745.1
145°	425.3	448.2	474.2	499.1	526.1	555.0	585.0	615.9	646.9	677.8	704.8
147.5°	437.2	457.4	480.2	502.7	527.1	552.4	578.8	603.2	628.3	652.1	672.4
150°	445.2	462.2	484.2	505.1	527.1	550.0	574.0	596.0	617.9	636.9	654.9
152.5°	452.4	467.8	488.2	506.7	526.3	546.9	568.4	588.0	607.5	624.9	638.9
155°	461.2	475.2	492.1	508.1	524.1	541.1	559.0	576.0	592.0	606.0	616.9
157.5°	470.4	481.0	495.5	509.1	521.5	535.1	550.2	564.0	577.2	588.0	596.6
160°	475.2	484.2	497.1	509.1	519.1	531.1	543.1	556.0	566.0	576.0	583.0
162.5°	480.0	487.4	498.7	508.3	516.7	526.3	536.7	547.3	556.4	564.8	571.0
165°	485.2	491.2	499.1	507.1	513.1	519.1	527.1	535.1	542.1	548.1	553.0
167.5°	488.8	492.5	499.1	504.7	507.5	512.1	517.7	523.5	528.1	532.7	536.3
170°	491.2	494.1	499.1	503.1	505.1	508.1	512.1	517.1	520.1	523.1	525.1
172.5°	492.7	494.1	498.3	501.5	501.9	503.3	506.5	509.9	512.9	515.1	516.3
175°	494.1	494.1	497.1	499.1	498.1	498.1	499.1	502.1	502.1	504.1	504.1
177.5°	494.3	494.3	495.9	496.7	495.1	495.1	495.9	496.7	497.5	497.5	497.5
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1749.9	1754.2	1750.5	1755.5	1750.5	1754.2	1749.9	1753.6	1759.2	1755.5	1764.2
5°	1612.8	1605.8	1610.5	1607.4	1610.5	1605.8	1612.8	1616.7	1626.1	1629.2	1635.4
7.5°	1486.2	1479.5	1471.9	1468.3	1471.9	1479.5	1486.2	1488.6	1496.5	1508.2	1517.1
10°	1407.0	1398.5	1397.7	1392.2	1397.7	1398.5	1407.0	1415.6	1421.1	1435.9	1446.0
12.5°	1349.0	1341.1	1332.2	1329.9	1332.2	1341.1	1349.0	1356.4	1358.1	1374.8	1381.8
15°	1266.7	1260.5	1255.0	1259.7	1255.0	1260.5	1266.7	1271.4	1280.0	1291.7	1299.5
17.5°	1198.3	1193.1	1192.2	1186.4	1192.2	1193.1	1198.3	1200.9	1215.0	1222.6	1236.0
20°	1155.3	1151.4	1152.9	1142.8	1152.9	1151.4	1155.3	1162.3	1176.3	1180.2	1194.2
22.5°	1121.0	1113.3	1112.4	1110.4	1112.4	1113.3	1121.0	1127.3	1130.2	1142.2	1151.8
25°	1067.2	1063.3	1059.4	1063.3	1059.4	1063.3	1067.2	1074.2	1077.3	1085.9	1095.2
27.5°	1020.2	1015.6	1014.5	1014.9	1014.5	1015.6	1020.2	1019.6	1028.0	1034.9	1041.8
30°	991.6	983.8	984.5	983.8	984.5	983.8	991.6	991.6	996.2	1002.5	1008.7
32.5°	960.4	955.1	954.0	952.6	954.0	955.1	960.4	959.1	965.0	972.5	979.4
35°	914.4	914.4	910.5	910.5	910.5	914.4	914.4	916.7	923.0	923.0	930.7
37.5°	871.2	870.4	868.1	868.4	868.1	870.4	871.2	873.1	875.2	878.5	883.5
40°	838.8	838.0	835.6	831.0	835.6	838.0	838.8	841.9	843.4	847.3	850.5
42.5°	807.6	804.9	803.8	802.3	803.8	804.9	807.6	809.5	810.4	815.5	821.8
45°	758.5	758.5	756.9	756.1	756.9	758.5	758.5	758.5	759.3	765.5	768.6
47.5°	710.8	712.2	715.1	714.7	715.1	712.2	710.8	709.5	709.8	713.0	716.5
50°	682.1	682.9	685.2	686.0	685.2	682.9	682.1	679.0	677.4	677.4	679.7
52.5°	650.3	654.8	657.8	657.3	657.8	654.8	650.3	647.8	645.0	641.2	644.8
55°	605.7	611.1	616.6	617.4	616.6	611.1	605.7	598.7	595.6	589.3	591.7
57.5°	561.6	569.2	575.0	576.8	575.0	569.2	561.6	553.1	543.0	540.1	535.7
60°	531.6	541.8	548.8	551.9	548.8	541.8	531.6	523.8	510.6	502.0	498.9
62.5°	502.9	514.3	521.3	522.0	521.3	514.3	502.9	490.8	477.5	467.7	461.5
65°	456.0	467.7	473.9	478.6	473.9	467.7	456.0	442.8	428.0	414.7	407.7
67.5°	405.5	417.2	424.1	427.8	424.1	417.2	405.5	389.1	375.6	360.3	352.0
70°	368.7	380.4	389.8	392.9	389.8	380.4	368.7	349.2	337.5	323.5	316.5
72.5°	332.5	343.0	350.5	354.2	350.5	343.0	332.5	314.3	300.7	286.7	277.2
75°	269.7	283.7	290.8	294.7	290.8	283.7	269.7	259.6	244.0	229.2	221.4
77.5°	208.0	220.8	225.0	227.0	225.0	220.8	208.0	196.1	184.3	173.5	165.9
80°	166.8	174.6	180.1	180.8	180.1	174.6	166.8	157.5	148.1	138.0	131.0
82.5°	128.2	134.7	136.4	138.4	136.4	134.7	128.2	120.0	111.9	104.3	98.5
85°	70.2	73.3	74.1	73.3	74.1	73.3	70.2	64.7	60.8	56.9	54.6
87.5°	27.5	26.8	27.0	28.3	27.0	26.8	27.5	26.2	26.4	25.0	23.5
90°	22.0	22.0	23.0	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0
92.5°	69.1	66.7	65.3	63.7	65.3	66.7	69.1	81.9	96.6	128.4	176.9
95°	288.5	258.6	250.6	234.6	250.6	258.6	288.5	359.4	443.2	566.0	717.8
97.5°	664.7	608.7	579.8	567.0	579.8	608.7	664.7	726.3	842.9	962.5	1069.0
100°	903.4	831.6	794.6	778.7	794.6	831.6	903.4	972.3	1076.1	1179.0	1227.9
102.5°	1118.3	1067.2	1027.0	1015.0	1027.0	1067.2	1118.3	1191.9	1262.2	1311.5	1281.4
105°	1387.6	1354.7	1334.7	1322.7	1334.7	1354.7	1387.6	1419.5	1430.5	1386.6	1249.8
107.5°	1500.8	1500.6	1494.0	1486.0	1494.0	1500.6	1500.8	1484.6	1432.5	1319.7	1137.2
110°	1514.4	1533.3	1540.3	1540.3	1540.3	1533.3	1514.4	1469.5	1384.6	1243.8	1054.2



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1476.8	1509.4	1526.8	1533.9	1526.8	1509.4	1476.8	1411.2	1311.1	1168.8	988.7
115°	1384.6	1432.5	1460.5	1473.5	1460.5	1432.5	1384.6	1306.7	1197.9	1061.2	906.4
117.5°	1282.2	1331.7	1359.4	1367.4	1359.4	1331.7	1282.2	1204.3	1104.5	986.7	853.3
120°	1215.9	1263.8	1290.8	1298.8	1290.8	1263.8	1215.9	1142.0	1054.2	944.4	824.6
122.5°	1160.0	1203.9	1230.9	1238.1	1230.9	1203.9	1160.0	1094.1	1011.8	914.0	803.0
125°	1088.1	1129.0	1151.0	1161.0	1151.0	1129.0	1088.1	1032.2	960.3	873.5	771.7
127.5°	1033.8	1069.9	1090.7	1095.1	1090.7	1069.9	1033.8	983.1	915.8	834.8	739.7
130°	1000.3	1033.2	1053.2	1059.2	1053.2	1033.2	1000.3	950.4	885.5	807.6	719.8
132.5°	965.1	998.1	1016.4	1023.2	1016.4	998.1	965.1	915.2	852.7	782.0	699.8
135°	907.4	940.4	958.3	964.3	958.3	940.4	907.4	863.5	806.6	742.7	673.8
137.5°	848.3	878.3	894.9	901.4	894.9	878.3	848.3	809.0	760.7	707.6	651.9
140°	811.6	837.6	852.5	857.5	852.5	837.6	811.6	774.7	732.7	686.8	639.9
142.5°	776.5	798.4	812.6	816.8	812.6	798.4	776.5	745.1	708.8	669.2	629.5
145°	728.7	745.7	756.7	760.7	756.7	745.7	728.7	704.8	677.8	646.9	615.9
147.5°	691.4	705.0	711.4	713.2	711.4	705.0	691.4	672.4	652.1	628.3	603.2
150°	669.8	681.8	685.8	686.8	685.8	681.8	669.8	654.9	636.9	617.9	596.0
152.5°	651.5	661.1	665.0	666.0	665.0	661.1	651.5	638.9	624.9	607.5	588.0
155°	626.9	633.9	636.9	637.9	636.9	633.9	626.9	616.9	606.0	592.0	576.0
157.5°	604.4	610.1	612.9	612.7	612.9	610.1	604.4	596.6	588.0	577.2	564.0
160°	590.0	595.0	597.0	596.0	597.0	595.0	590.0	583.0	576.0	566.0	556.0
162.5°	576.4	580.6	581.0	580.8	581.0	580.6	576.4	571.0	564.8	556.4	547.3
165°	557.0	559.0	559.0	559.0	559.0	559.0	557.0	553.0	548.1	542.1	535.1
167.5°	538.3	540.1	539.3	539.1	539.3	540.1	538.3	536.3	532.7	528.1	523.5
170°	527.1	528.1	528.1	527.1	528.1	528.1	527.1	525.1	523.1	520.1	517.1
172.5°	516.7	518.5	516.9	515.9	516.9	518.5	516.7	516.3	515.1	512.9	509.9
175°	504.1	505.1	503.1	502.1	503.1	505.1	504.1	504.1	504.1	502.1	502.1
177.5°	496.7	497.5	495.1	495.1	495.1	497.5	496.7	497.5	497.5	497.5	496.7
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1756.1	1763.6	1772.9	1779.8	1792.3	1797.9	1804.7	1810.4	1820.3	1829.7	1840.9
5°	1637.8	1651.0	1669.0	1688.4	1711.1	1726.6	1748.5	1761.7	1788.2	1812.4	1835.8
7.5°	1530.5	1546.7	1572.1	1597.1	1626.7	1653.5	1680.8	1711.1	1744.9	1784.8	1817.8
10°	1456.9	1478.8	1506.0	1537.2	1573.1	1604.3	1640.9	1673.6	1714.9	1761.7	1805.4
12.5°	1398.3	1417.0	1447.4	1477.4	1515.7	1553.7	1591.6	1635.0	1683.1	1734.9	1789.8
15°	1317.4	1333.0	1357.9	1399.2	1438.2	1475.6	1532.5	1573.1	1633.9	1691.6	1757.8
17.5°	1248.3	1267.7	1288.7	1324.1	1364.5	1411.2	1462.1	1512.9	1571.5	1644.6	1719.3
20°	1205.9	1221.5	1245.7	1273.0	1315.8	1362.6	1410.9	1462.4	1534.1	1609.7	1690.0
22.5°	1159.8	1176.6	1203.9	1233.7	1269.7	1314.6	1367.9	1424.3	1499.2	1573.5	1660.7
25°	1105.4	1117.1	1142.0	1168.5	1204.4	1242.6	1297.9	1360.3	1434.3	1519.3	1608.2
27.5°	1054.1	1064.4	1087.1	1110.2	1142.6	1188.0	1237.4	1300.4	1370.2	1456.3	1554.8
30°	1017.3	1028.2	1048.5	1073.4	1104.6	1144.3	1195.0	1254.3	1329.1	1413.3	1516.2
32.5°	985.5	995.1	1010.4	1035.4	1065.9	1104.4	1151.4	1211.8	1286.7	1372.1	1473.1
35°	936.2	947.1	958.8	978.3	1004.8	1042.2	1093.7	1150.6	1222.3	1304.9	1397.7
37.5°	887.3	899.1	909.5	927.0	951.2	984.2	1028.7	1087.9	1152.8	1232.4	1321.4
40°	856.7	866.0	874.6	893.3	917.5	948.7	990.0	1043.0	1111.6	1185.7	1259.7
42.5°	826.1	834.9	842.2	858.4	880.7	910.6	950.1	1001.8	1065.5	1134.5	1199.8
45°	778.0	783.4	792.0	806.0	824.0	851.2	889.4	935.4	989.2	1054.7	1103.8
47.5°	725.9	734.5	741.5	753.8	768.5	795.3	831.9	871.0	919.8	968.5	1003.1
50°	686.0	694.6	704.7	716.4	730.4	755.4	788.9	828.6	869.9	907.4	937.0
52.5°	648.6	656.5	667.3	678.3	695.5	716.7	745.2	780.6	821.3	848.1	872.8
55°	593.2	597.1	609.6	620.5	636.9	652.5	681.3	712.5	737.4	757.7	778.0
57.5°	536.6	541.9	549.1	558.9	575.1	593.4	613.6	641.2	655.9	666.3	682.1
60°	500.5	502.0	506.7	518.4	530.9	547.2	570.6	590.1	601.0	609.6	622.8
62.5°	460.5	460.9	468.6	477.2	486.6	504.2	523.2	539.0	548.0	552.2	564.8
65°	404.6	403.0	407.7	414.7	425.6	437.3	453.7	467.7	466.9	471.6	479.4
67.5°	347.4	345.8	345.8	352.5	361.4	371.8	383.1	391.2	391.3	397.6	401.5
70°	308.7	304.0	307.1	312.6	316.5	325.1	337.5	340.7	341.4	344.5	348.4
72.5°	268.8	267.2	269.7	272.1	274.7	281.4	292.0	293.9	294.0	295.9	302.3
75°	213.6	212.0	210.5	212.8	215.9	220.6	224.5	227.6	226.8	227.6	232.3
77.5°	160.1	155.7	155.0	156.2	157.0	159.8	163.9	163.5	164.3	164.2	169.5
80°	127.1	120.8	120.0	120.0	120.8	122.4	123.9	125.5	123.2	125.5	127.1
82.5°	93.4	89.6	89.5	88.9	89.0	89.3	90.3	91.2	90.7	91.8	92.8
85°	51.4	49.9	47.6	49.1	48.3	46.0	47.6	45.2	44.4	45.2	46.0
87.5°	20.9	21.3	19.6	19.4	18.4	18.8	17.2	16.2	15.1	15.4	17.0
90°	17.0	16.0	14.0	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0
92.5°	260.5	321.8	327.0	227.8	136.4	81.9	52.7	35.5	23.2	14.8	12.2
95°	865.5	884.5	721.8	446.2	226.6	119.8	74.9	52.9	41.9	33.9	32.9
97.5°	1095.1	944.6	644.5	356.2	195.3	124.6	92.2	72.5	61.5	55.9	54.7
100°	1151.0	901.4	575.0	323.4	193.7	135.8	105.8	86.8	75.9	71.9	69.9
102.5°	1117.5	825.6	522.3	309.9	200.9	149.3	120.2	102.8	91.0	87.8	86.7
105°	1010.3	723.7	471.2	304.5	215.6	171.7	143.8	127.8	117.8	112.8	112.8
107.5°	900.8	653.7	449.6	313.7	237.6	195.1	169.9	153.3	145.1	140.4	138.4
110°	838.5	620.9	443.2	322.4	253.6	212.6	186.7	171.7	162.7	158.7	156.7



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	792.2	601.8	443.2	333.6	268.7	229.4	204.2	189.3	180.3	177.1	175.1
115°	741.7	581.0	446.2	350.4	292.5	255.6	230.6	215.6	206.6	203.6	201.7
117.5°	711.6	570.8	452.8	369.6	316.9	281.9	257.8	240.8	231.8	228.6	225.6
120°	694.8	566.0	459.2	382.3	334.4	299.5	274.5	257.6	248.6	244.6	241.6
122.5°	680.4	562.0	464.8	396.7	351.2	316.3	291.3	272.7	263.7	260.5	258.4
125°	660.9	557.0	474.2	416.3	373.4	340.4	314.5	295.5	286.5	281.5	279.5
127.5°	642.9	554.6	484.8	434.2	394.7	363.0	337.0	316.9	305.5	299.1	296.1
130°	630.9	553.0	491.2	446.2	408.3	377.3	351.4	330.4	317.5	309.5	306.5
132.5°	621.3	553.0	498.3	456.6	421.1	390.1	364.2	342.4	327.8	318.2	314.5
135°	609.9	553.0	508.1	471.2	438.2	407.3	380.3	359.4	343.4	331.4	327.4
137.5°	599.8	554.2	517.1	482.0	450.4	422.3	394.5	374.0	358.0	346.8	343.8
140°	595.0	555.0	521.1	489.2	459.2	430.3	403.3	384.3	368.4	356.4	353.4
142.5°	591.0	555.8	523.5	493.1	464.8	437.4	412.1	393.9	377.9	366.8	364.6
145°	585.0	555.0	526.1	499.1	474.2	448.2	425.3	407.3	393.3	383.3	381.3
147.5°	578.8	552.4	527.1	502.7	480.2	457.4	437.2	421.7	408.7	400.1	398.9
150°	574.0	550.0	527.1	505.1	484.2	462.2	445.2	431.3	418.3	411.3	409.3
152.5°	568.4	546.9	526.3	506.7	488.2	467.8	452.4	439.2	427.9	421.7	420.5
155°	559.0	541.1	524.1	508.1	492.1	475.2	461.2	451.2	441.2	435.2	435.2
157.5°	550.2	535.1	521.5	509.1	495.5	481.0	470.4	461.6	453.0	448.2	448.4
160°	543.1	531.1	519.1	509.1	497.1	484.2	475.2	467.2	460.2	456.2	457.2
162.5°	536.7	526.3	516.7	508.3	498.7	487.4	480.0	473.6	467.4	463.4	464.4
165°	527.1	519.1	513.1	507.1	499.1	491.2	485.2	481.2	476.2	473.2	475.2
167.5°	517.7	512.1	507.5	504.7	499.1	492.5	488.8	486.0	483.2	481.4	482.4
170°	512.1	508.1	505.1	503.1	499.1	494.1	491.2	489.2	487.2	486.2	487.2
172.5°	506.5	503.3	501.9	501.5	498.3	494.1	492.7	491.5	489.6	488.6	490.4
175°	499.1	498.1	498.1	499.1	497.1	494.1	494.1	494.1	493.1	492.1	494.1
177.5°	495.9	495.1	495.1	496.7	495.9	494.3	494.3	495.1	494.3	494.3	495.9
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1846.5	1855.3	1860.9	1871.5	1880.2	1885.2	1889.6	1893.3	1897.7	1901.4	1912.0
5°	1858.4	1878.6	1895.8	1922.3	1946.5	1965.2	1985.4	2003.4	2018.2	2039.2	2055.6
7.5°	1853.2	1889.2	1927.0	1968.0	2009.9	2048.9	2084.8	2118.3	2148.7	2185.5	2217.7
10°	1848.2	1897.4	1945.7	2001.0	2057.9	2106.3	2151.5	2197.5	2231.0	2277.8	2317.5
12.5°	1844.5	1902.3	1960.7	2027.2	2089.7	2158.0	2218.2	2251.7	2302.7	2340.1	2387.4
15°	1828.8	1905.2	1985.4	2060.3	2149.1	2212.3	2265.3	2330.8	2378.3	2425.9	2477.3
17.5°	1800.5	1887.1	1976.9	2074.9	2160.2	2228.0	2296.3	2359.5	2416.2	2480.0	2544.0
20°	1787.4	1874.0	1976.9	2077.4	2160.8	2231.8	2301.9	2371.3	2433.7	2515.5	2589.6
22.5°	1760.0	1864.6	1959.4	2057.5	2143.4	2220.5	2300.1	2378.8	2461.7	2554.2	2646.9
25°	1711.1	1817.1	1917.6	2014.3	2100.8	2197.5	2282.4	2387.7	2493.7	2616.1	2731.4
27.5°	1660.2	1761.7	1853.9	1947.2	2048.1	2157.6	2267.8	2387.2	2526.0	2680.5	2843.2
30°	1619.1	1714.9	1804.6	1900.5	2005.7	2128.9	2249.7	2391.6	2552.2	2726.0	2919.3
32.5°	1571.0	1659.4	1746.6	1848.1	1962.7	2092.7	2233.5	2389.1	2582.1	2779.6	2978.6
35°	1488.9	1562.9	1652.6	1760.9	1890.3	2039.2	2202.2	2386.1	2607.5	2834.3	3001.9
37.5°	1391.4	1460.4	1554.8	1673.6	1809.3	1969.1	2162.4	2380.7	2615.8	2796.6	2850.7
40°	1326.0	1389.9	1488.1	1611.3	1750.0	1919.2	2131.2	2362.0	2589.6	2704.9	2660.5
42.5°	1256.1	1323.2	1418.9	1540.8	1690.2	1874.3	2091.9	2322.7	2513.5	2557.1	2403.6
45°	1145.9	1215.3	1309.6	1432.8	1593.3	1792.9	2019.7	2229.4	2339.3	2260.6	2022.9
47.5°	1043.5	1108.5	1195.9	1323.0	1488.7	1695.1	1913.6	2080.9	2089.6	1901.7	1647.8
50°	973.6	1033.6	1121.7	1248.8	1413.3	1622.2	1819.4	1951.1	1891.9	1679.1	1435.1
52.5°	905.0	963.8	1050.6	1176.5	1339.1	1530.5	1714.0	1806.5	1694.8	1476.4	1268.0
55°	806.0	857.5	942.4	1058.6	1212.9	1390.7	1546.6	1578.5	1433.5	1218.4	1049.2
57.5°	709.4	757.4	834.7	941.7	1082.8	1240.2	1362.1	1355.3	1202.0	1017.4	883.2
60°	643.9	690.7	759.3	863.7	992.3	1128.0	1232.4	1207.5	1055.5	896.5	783.4
62.5°	585.3	627.0	691.9	783.3	900.7	1026.3	1112.1	1075.3	926.4	787.3	698.0
65°	498.9	534.0	589.3	667.3	764.7	868.4	934.6	887.1	760.0	651.7	580.0
67.5°	416.4	444.5	490.9	553.1	636.2	719.5	759.9	712.0	610.4	531.3	478.2
70°	364.0	389.0	424.8	480.2	552.7	622.8	653.2	610.4	523.1	455.2	417.0
72.5°	311.7	332.2	363.7	413.5	471.6	532.4	559.1	518.1	446.4	389.1	353.4
75°	240.9	254.9	276.7	311.0	357.0	405.4	420.2	384.3	338.3	295.4	272.1
77.5°	172.4	184.3	200.8	222.5	255.1	285.8	298.7	278.0	242.4	215.3	196.1
80°	132.5	138.8	152.8	170.7	196.4	215.9	224.5	211.3	186.3	166.0	151.2
82.5°	94.5	100.7	109.1	123.9	140.3	153.6	162.8	153.9	135.8	119.9	111.3
85°	46.0	49.9	54.6	60.8	73.3	81.1	80.3	74.8	67.8	61.6	56.9
87.5°	16.6	17.6	19.9	23.4	25.7	28.4	30.0	29.0	26.9	25.2	23.5
90°	2.0	4.0	6.0	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0
92.5°	14.8	23.2	35.5	52.7	81.9	136.4	227.8	327.0	321.8	260.5	176.9
95°	33.9	41.9	52.9	74.9	119.8	226.6	446.2	721.8	884.5	865.5	717.8
97.5°	55.9	61.5	72.5	92.2	124.6	195.3	356.2	644.5	944.6	1095.1	1069.0
100°	71.9	75.9	86.8	105.8	135.8	193.7	323.4	575.0	901.4	1151.0	1227.9
102.5°	87.8	91.0	102.8	120.2	149.3	200.9	309.9	522.3	825.6	1117.5	1281.4
105°	112.8	117.8	127.8	143.8	171.7	215.6	304.5	471.2	723.7	1010.3	1249.8
107.5°	140.4	145.1	153.3	169.9	195.1	237.6	313.7	449.6	653.7	900.8	1137.2
110°	158.7	162.7	171.7	186.7	212.6	253.6	322.4	443.2	620.9	838.5	1054.2



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	177.1	180.3	189.3	204.2	229.4	268.7	333.6	443.2	601.8	792.2	988.7
115°	203.6	206.6	215.6	230.6	255.6	292.5	350.4	446.2	581.0	741.7	906.4
117.5°	228.6	231.8	240.8	257.8	281.9	316.9	369.6	452.8	570.8	711.6	853.3
120°	244.6	248.6	257.6	274.5	299.5	334.4	382.3	459.2	566.0	694.8	824.6
122.5°	260.5	263.7	272.7	291.3	316.3	351.2	396.7	464.8	562.0	680.4	803.0
125°	281.5	286.5	295.5	314.5	340.4	373.4	416.3	474.2	557.0	660.9	771.7
127.5°	299.1	305.5	316.9	337.0	363.0	394.7	434.2	484.8	554.6	642.9	739.7
130°	309.5	317.5	330.4	351.4	377.3	408.3	446.2	491.2	553.0	630.9	719.8
132.5°	318.2	327.8	342.4	364.2	390.1	421.1	456.6	498.3	553.0	621.3	699.8
135°	331.4	343.4	359.4	380.3	407.3	438.2	471.2	508.1	553.0	609.9	673.8
137.5°	346.8	358.0	374.0	394.5	422.3	450.4	482.0	517.1	554.2	599.8	651.9
140°	356.4	368.4	384.3	403.3	430.3	459.2	489.2	521.1	555.0	595.0	639.9
142.5°	366.8	377.9	393.9	412.1	437.4	464.8	493.1	523.5	555.8	591.0	629.5
145°	383.3	393.3	407.3	425.3	448.2	474.2	499.1	526.1	555.0	585.0	615.9
147.5°	400.1	408.7	421.7	437.2	457.4	480.2	502.7	527.1	552.4	578.8	603.2
150°	411.3	418.3	431.3	445.2	462.2	484.2	505.1	527.1	550.0	574.0	596.0
152.5°	421.7	427.9	439.2	452.4	467.8	488.2	506.7	526.3	546.9	568.4	588.0
155°	435.2	441.2	451.2	461.2	475.2	492.1	508.1	524.1	541.1	559.0	576.0
157.5°	448.2	453.0	461.6	470.4	481.0	495.5	509.1	521.5	535.1	550.2	564.0
160°	456.2	460.2	467.2	475.2	484.2	497.1	509.1	519.1	531.1	543.1	556.0
162.5°	463.4	467.4	473.6	480.0	487.4	498.7	508.3	516.7	526.3	536.7	547.3
165°	473.2	476.2	481.2	485.2	491.2	499.1	507.1	513.1	519.1	527.1	535.1
167.5°	481.4	483.2	486.0	488.8	492.5	499.1	504.7	507.5	512.1	517.7	523.5
170°	486.2	487.2	489.2	491.2	494.1	499.1	503.1	505.1	508.1	512.1	517.1
172.5°	488.6	489.6	491.5	492.7	494.1	498.3	501.5	501.9	503.3	506.5	509.9
175°	492.1	493.1	494.1	494.1	494.1	497.1	499.1	498.1	498.1	499.1	502.1
177.5°	494.3	494.3	495.1	494.3	494.3	495.9	496.7	495.1	495.1	495.9	496.7
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1920.7	1925.7	1936.3	1932.6	1937.6	1940.1	1942.6
5°	2075.9	2100.8	2111.7	2110.2	2126.5	2122.6	2118.7
7.5°	2251.1	2277.3	2292.0	2310.2	2320.8	2321.6	2330.8
10°	2350.3	2384.6	2398.6	2418.1	2430.6	2437.6	2436.8
12.5°	2426.3	2453.2	2484.6	2494.2	2511.0	2519.9	2516.6
15°	2517.9	2560.7	2593.5	2609.8	2630.9	2637.1	2645.7
17.5°	2599.6	2657.1	2695.3	2746.1	2765.3	2777.0	2770.1
20°	2661.3	2736.9	2775.1	2835.9	2869.4	2887.4	2881.1
22.5°	2734.3	2816.1	2886.7	2939.4	2990.4	3014.6	3019.6
25°	2859.3	2971.5	3075.2	3144.6	3207.7	3222.5	3255.3
27.5°	2999.0	3131.3	3242.2	3315.2	3359.1	3375.6	3385.9
30°	3086.9	3218.6	3302.1	3348.8	3362.9	3361.3	3359.7
32.5°	3129.9	3212.4	3228.5	3215.4	3183.3	3156.1	3127.8
35°	3069.0	3007.4	2915.4	2796.9	2709.6	2621.5	2613.0
37.5°	2760.1	2563.2	2410.1	2239.1	2140.4	2079.5	2037.4
40°	2469.5	2245.8	2060.3	1916.1	1815.5	1775.8	1736.8
42.5°	2154.0	1940.2	1775.9	1655.4	1579.8	1535.7	1504.8
45°	1750.0	1561.4	1432.8	1345.5	1285.4	1251.1	1231.6
47.5°	1434.0	1294.5	1185.2	1122.2	1080.7	1054.1	1054.2
50°	1264.4	1131.1	1058.6	1008.7	972.8	951.8	955.7
52.5°	1114.1	1014.5	952.6	910.8	884.3	871.3	870.9
55°	931.5	859.8	819.3	788.9	770.9	756.1	759.3
57.5°	796.8	736.3	709.2	684.0	671.5	665.6	657.0
60°	713.3	666.5	643.1	622.8	610.4	605.7	597.1
62.5°	639.1	602.3	579.5	563.0	551.7	550.2	543.5
65°	537.1	509.0	488.8	481.0	469.3	466.2	466.2
67.5°	442.8	422.7	406.9	399.7	394.6	395.4	391.6
70°	383.5	367.2	357.0	349.2	345.3	346.1	343.0
72.5°	335.5	317.3	308.4	303.7	298.6	300.6	299.3
75°	254.1	244.8	240.1	235.4	232.3	230.7	229.2
77.5°	186.6	178.4	174.8	172.1	172.6	168.8	171.8
80°	144.2	137.2	134.9	131.0	130.2	130.2	129.4
82.5°	105.5	101.6	99.9	96.7	95.3	96.5	94.5
85°	54.6	51.4	50.7	50.7	49.1	47.6	51.4
87.5°	23.7	21.5	21.9	21.2	21.2	20.8	19.6
90°	19.0	20.0	22.0	22.0	22.0	23.0	23.0
92.5°	128.4	96.6	81.9	69.1	66.7	65.3	63.7
95°	566.0	443.2	359.4	288.5	258.6	250.6	234.6
97.5°	962.5	842.9	726.3	664.7	608.7	579.8	567.0
100°	1179.0	1076.1	972.3	903.4	831.6	794.6	778.7
102.5°	1311.5	1262.2	1191.9	1118.3	1067.2	1027.0	1015.0
105°	1386.6	1430.5	1419.5	1387.6	1354.7	1334.7	1322.7
107.5°	1319.7	1432.5	1484.6	1500.8	1500.6	1494.0	1486.0
110°	1243.8	1384.6	1469.5	1514.4	1533.3	1540.3	1540.3



TEST NUMBER: P333324

CATALOG NUMBER: S125DIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1168.8	1311.1	1411.2	1476.8	1509.4	1526.8	1533.9
115°	1061.2	1197.9	1306.7	1384.6	1432.5	1460.5	1473.5
117.5°	986.7	1104.5	1204.3	1282.2	1331.7	1359.4	1367.4
120°	944.4	1054.2	1142.0	1215.9	1263.8	1290.8	1298.8
122.5°	914.0	1011.8	1094.1	1160.0	1203.9	1230.9	1238.1
125°	873.5	960.3	1032.2	1088.1	1129.0	1151.0	1161.0
127.5°	834.8	915.8	983.1	1033.8	1069.9	1090.7	1095.1
130°	807.6	885.5	950.4	1000.3	1033.2	1053.2	1059.2
132.5°	782.0	852.7	915.2	965.1	998.1	1016.4	1023.2
135°	742.7	806.6	863.5	907.4	940.4	958.3	964.3
137.5°	707.6	760.7	809.0	848.3	878.3	894.9	901.4
140°	686.8	732.7	774.7	811.6	837.6	852.5	857.5
142.5°	669.2	708.8	745.1	776.5	798.4	812.6	816.8
145°	646.9	677.8	704.8	728.7	745.7	756.7	760.7
147.5°	628.3	652.1	672.4	691.4	705.0	711.4	713.2
150°	617.9	636.9	654.9	669.8	681.8	685.8	686.8
152.5°	607.5	624.9	638.9	651.5	661.1	665.0	666.0
155°	592.0	606.0	616.9	626.9	633.9	636.9	637.9
157.5°	577.2	588.0	596.6	604.4	610.1	612.9	612.7
160°	566.0	576.0	583.0	590.0	595.0	597.0	596.0
162.5°	556.4	564.8	571.0	576.4	580.6	581.0	580.8
165°	542.1	548.1	553.0	557.0	559.0	559.0	559.0
167.5°	528.1	532.7	536.3	538.3	540.1	539.3	539.1
170°	520.1	523.1	525.1	527.1	528.1	528.1	527.1
172.5°	512.9	515.1	516.3	516.7	518.5	516.9	515.9
175°	502.1	504.1	504.1	504.1	505.1	503.1	502.1
177.5°	497.5	497.5	497.5	496.7	497.5	495.1	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1

(END OF REPORT)