

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333144

Luminaire Tested: **S125DIP-S375D1035U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333144  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D1035U835-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5252.1 lumens  
Efficiency: N/A  
Efficacy: 140.8 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25				
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21				
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18				
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	15				
5	65	54	46	40	58	49	42	37	39	34	30	29	26	24	21	19	17	13				
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12				
7	55	43	36	30	49	39	33	28	31	27	23	24	21	18	17	15	13	11				
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9				
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	15	12	11	8				
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	13	11	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3516	3516	3516	3516
5°	4071	3528	3089	3528
10°	4737	3510	2706	3510
15°	5243	3484	2497	3484
20°	5869	3443	2328	3443
25°	6876	3397	2246	3397
30°	7427	3351	2175	3351
35°	6106	3266	2128	3266
40°	4340	3148	2076	3148
45°	3335	2988	2047	2988
50°	2846	2790	2043	2790
55°	2535	2597	2061	2597
60°	2286	2384	2113	2384
65°	2112	2172	2168	2172
70°	1920	1951	2200	1951
75°	1694	1719	2178	1719
80°	1428	1402	1993	1402
85°	1134	1008	1608	1008



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.4	1.0
10°-20°	156.0	3.0
20°-30°	253.4	4.8
30°-40°	309.1	5.9
40°-50°	281.2	5.4
50°-60°	224.0	4.3
60°-70°	156.0	3.0
70°-80°	83.2	1.6
80°-90°	23.8	0.5
90°-100°	358.9	6.8
100°-110°	771.5	14.7
110°-120°	724.1	13.8
120°-130°	586.8	11.2
130°-140°	470.9	9.0
140°-150°	355.4	6.8
150°-160°	250.1	4.8
160°-170°	147.4	2.8
170°-180°	48.0	0.9
0°-30°	461.8	8.8
0°-40°	770.9	14.7
0°-60°	1276.0	24.3
0°-90°	1538.9	29.3
90°-120°	1854.5	35.3
90°-150°	3267.6	62.2
90°-180°	3713.0	70.7
0°-180°	5252.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	544	544	544	544	544	
5°	628	544	476	544	628	63
15°	784	521	373	521	784	224
25°	965	477	315	477	965	441
35°	774	414	270	414	774	474
45°	365	327	224	327	365	292
55°	225	231	183	231	225	203
65°	138	142	142	142	138	137
75°	68	69	87	69	68	73
85°	15	14	22	14	15	18
90°	23	1	23	1	23	16
95°	235	33	235	33	235	332
105°	1323	113	1323	113	1323	1315
115°	1474	202	1474	202	1474	1440
125°	1161	280	1161	280	1161	1050
135°	964	327	964	327	964	747
145°	761	381	761	381	761	483
155°	638	435	638	435	638	297
165°	559	475	559	475	559	160
175°	502	494	502	494	502	49
180°	495	495	495	495	495	



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	575.8	575.1	574.3	572.9	574.0	570.8	569.4	566.8	563.6	562.5	561.2
5°	628.0	629.2	630.4	625.5	626.0	622.7	615.3	609.3	604.5	598.2	593.8
7.5°	690.9	688.2	687.9	684.8	679.4	675.0	667.3	657.4	647.8	636.9	627.9
10°	722.3	722.6	720.5	716.8	711.0	706.8	696.7	687.0	675.2	661.3	651.4
12.5°	746.0	747.0	744.3	739.3	736.5	727.2	719.2	707.7	693.7	682.6	667.5
15°	784.2	781.7	779.9	773.6	768.8	759.1	746.4	734.3	719.1	705.0	690.9
17.5°	821.1	823.2	819.7	814.0	798.9	787.6	770.6	754.1	735.1	716.2	699.4
20°	854.0	855.9	850.6	840.6	822.6	811.3	788.9	767.6	745.7	721.4	702.9
22.5°	895.1	893.6	886.4	871.3	855.7	834.8	810.5	784.6	757.1	729.7	705.1
25°	964.9	955.2	950.8	932.1	911.6	880.8	847.6	809.7	775.5	739.2	707.8
27.5°	1003.7	1000.6	995.7	982.7	961.1	928.2	889.0	842.8	794.6	748.8	707.6
30°	995.9	996.4	996.8	992.7	978.8	954.1	915.0	865.4	808.0	756.5	708.9
32.5°	927.1	935.5	943.6	953.1	957.0	952.2	927.8	882.9	823.9	765.4	708.2
35°	774.5	777.1	803.2	829.1	864.2	891.5	909.7	889.8	840.2	772.9	707.3
37.5°	603.9	616.4	634.5	663.7	714.4	759.8	818.2	845.0	829.0	775.4	705.7
40°	514.8	526.4	538.2	568.0	610.7	665.7	732.0	788.6	801.8	767.6	700.1
42.5°	446.1	455.2	468.3	490.7	526.4	575.1	638.5	712.5	758.0	745.1	688.5
45°	365.1	370.9	381.0	398.8	424.7	462.8	518.7	599.6	670.1	693.4	660.9
47.5°	312.5	312.5	320.4	332.6	351.3	383.7	425.1	488.4	563.7	619.4	616.8
50°	283.3	282.1	288.4	299.0	313.8	335.3	374.8	425.4	497.7	560.8	578.4
52.5°	258.1	258.3	262.1	270.0	282.4	300.7	330.2	375.9	437.6	502.4	535.5
55°	225.1	224.1	228.5	233.8	242.9	254.9	276.1	311.0	361.2	424.9	467.9
57.5°	194.7	197.3	199.0	202.7	210.2	218.3	236.2	261.8	301.6	356.3	401.7
60°	177.0	179.5	180.9	184.6	190.6	197.6	211.4	232.2	265.7	312.9	357.9
62.5°	161.1	163.1	163.6	166.9	171.8	178.5	189.4	206.9	233.4	274.6	318.7
65°	138.2	138.2	139.1	142.6	144.9	150.9	159.2	171.9	193.2	225.3	263.0
67.5°	116.1	117.2	117.0	118.5	120.6	125.3	131.2	141.7	157.5	180.9	211.1
70°	101.7	102.6	102.4	103.5	105.8	108.8	113.7	123.6	134.9	155.0	180.9
72.5°	88.7	89.1	88.5	90.0	91.4	94.0	99.5	104.8	115.3	132.3	153.6
75°	67.9	68.4	68.9	69.8	71.2	72.6	75.3	80.6	87.6	100.3	113.9
77.5°	50.9	50.0	51.2	51.0	51.8	52.9	55.3	58.1	63.8	71.9	82.4
80°	38.4	38.6	38.6	38.8	40.0	40.7	42.7	44.8	49.2	55.2	62.6
82.5°	28.0	28.6	28.2	28.7	29.6	30.1	31.3	33.0	35.5	40.3	45.6
85°	15.3	14.1	14.6	15.0	15.0	15.3	16.2	16.9	18.3	20.1	22.2
87.5°	9.0	9.4	9.4	9.4	9.6	9.2	9.7	9.5	9.9	10.2	10.6
90°	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0	17.0	16.0	14.0
92.5°	63.7	65.3	66.7	69.1	81.9	96.6	128.4	176.9	260.5	321.8	327.0
95°	234.6	250.6	258.6	288.5	359.4	443.2	566.0	717.8	865.5	884.5	721.8
97.5°	567.0	579.8	608.7	664.7	726.3	842.9	962.5	1069.0	1095.1	944.6	644.5
100°	778.7	794.6	831.6	903.4	972.3	1076.1	1179.0	1227.9	1151.0	901.4	575.0
102.5°	1015.0	1027.0	1067.2	1118.3	1191.9	1262.2	1311.5	1281.4	1117.5	825.6	522.3
105°	1322.7	1334.7	1354.7	1387.6	1419.5	1430.5	1386.6	1249.8	1010.3	723.7	471.2
107.5°	1486.0	1494.0	1500.6	1500.8	1484.6	1432.5	1319.7	1137.2	900.8	653.7	449.6
110°	1540.3	1540.3	1533.3	1514.4	1469.5	1384.6	1243.8	1054.2	838.5	620.9	443.2



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1533.9	1526.8	1509.4	1476.8	1411.2	1311.1	1168.8	988.7	792.2	601.8	443.2
115°	1473.5	1460.5	1432.5	1384.6	1306.7	1197.9	1061.2	906.4	741.7	581.0	446.2
117.5°	1367.4	1359.4	1331.7	1282.2	1204.3	1104.5	986.7	853.3	711.6	570.8	452.8
120°	1298.8	1290.8	1263.8	1215.9	1142.0	1054.2	944.4	824.6	694.8	566.0	459.2
122.5°	1238.1	1230.9	1203.9	1160.0	1094.1	1011.8	914.0	803.0	680.4	562.0	464.8
125°	1161.0	1151.0	1129.0	1088.1	1032.2	960.3	873.5	771.7	660.9	557.0	474.2
127.5°	1095.1	1090.7	1069.9	1033.8	983.1	915.8	834.8	739.7	642.9	554.6	484.8
130°	1059.2	1053.2	1033.2	1000.3	950.4	885.5	807.6	719.8	630.9	553.0	491.2
132.5°	1023.2	1016.4	998.1	965.1	915.2	852.7	782.0	699.8	621.3	553.0	498.3
135°	964.3	958.3	940.4	907.4	863.5	806.6	742.7	673.8	609.9	553.0	508.1
137.5°	901.4	894.9	878.3	848.3	809.0	760.7	707.6	651.9	599.8	554.2	517.1
140°	857.5	852.5	837.6	811.6	774.7	732.7	686.8	639.9	595.0	555.0	521.1
142.5°	816.8	812.6	798.4	776.5	745.1	708.8	669.2	629.5	591.0	555.8	523.5
145°	760.7	756.7	745.7	728.7	704.8	677.8	646.9	615.9	585.0	555.0	526.1
147.5°	713.2	711.4	705.0	691.4	672.4	652.1	628.3	603.2	578.8	552.4	527.1
150°	686.8	685.8	681.8	669.8	654.9	636.9	617.9	596.0	574.0	550.0	527.1
152.5°	666.0	665.0	661.1	651.5	638.9	624.9	607.5	588.0	568.4	546.9	526.3
155°	637.9	636.9	633.9	626.9	616.9	606.0	592.0	576.0	559.0	541.1	524.1
157.5°	612.7	612.9	610.1	604.4	596.6	588.0	577.2	564.0	550.2	535.1	521.5
160°	596.0	597.0	595.0	590.0	583.0	576.0	566.0	556.0	543.1	531.1	519.1
162.5°	580.8	581.0	580.6	576.4	571.0	564.8	556.4	547.3	536.7	526.3	516.7
165°	559.0	559.0	559.0	557.0	553.0	548.1	542.1	535.1	527.1	519.1	513.1
167.5°	539.1	539.3	540.1	538.3	536.3	532.7	528.1	523.5	517.7	512.1	507.5
170°	527.1	528.1	528.1	527.1	525.1	523.1	520.1	517.1	512.1	508.1	505.1
172.5°	515.9	516.9	518.5	516.7	516.3	515.1	512.9	509.9	506.5	503.3	501.9
175°	502.1	503.1	505.1	504.1	504.1	504.1	502.1	502.1	499.1	498.1	498.1
177.5°	495.1	495.1	497.5	496.7	497.5	497.5	497.5	496.7	495.9	495.1	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	560.1	558.8	557.3	554.7	551.6	549.9	547.4	545.7	542.4	539.6	536.6
5°	588.5	582.5	577.0	569.8	562.0	556.9	550.9	544.2	537.2	530.1	522.2
7.5°	618.0	607.3	595.8	583.4	571.2	560.0	549.3	538.9	529.1	517.2	507.2
10°	637.7	624.3	610.0	593.2	576.7	562.4	547.9	535.2	522.2	508.4	496.1
12.5°	657.5	639.7	619.4	600.9	581.2	563.9	546.8	530.5	514.3	498.9	484.6
15°	671.5	655.8	637.1	610.7	588.5	564.7	542.1	521.1	501.4	484.3	466.3
17.5°	680.7	660.4	640.3	615.1	586.0	559.4	533.7	509.6	487.5	465.8	448.5
20°	682.3	661.5	640.5	615.8	586.0	555.5	529.8	501.0	477.2	454.7	433.5
22.5°	681.8	658.2	635.3	609.9	580.8	552.7	521.7	492.3	466.4	444.4	422.2
25°	676.6	651.4	622.7	597.1	568.4	538.6	507.2	476.7	450.4	425.2	403.2
27.5°	672.2	639.6	607.1	577.2	549.5	522.2	492.1	460.9	431.7	406.2	385.5
30°	666.9	631.0	594.5	563.3	534.9	508.4	479.9	449.4	418.9	394.0	371.8
32.5°	662.1	620.3	581.8	547.8	517.7	491.9	465.7	436.7	406.7	381.4	359.2
35°	652.8	604.5	560.3	522.0	489.9	463.3	441.3	414.3	386.8	362.3	341.1
37.5°	641.0	583.7	536.3	496.1	460.9	432.9	412.5	391.7	365.3	341.7	322.5
40°	631.7	568.9	518.7	477.6	441.1	412.0	393.0	373.4	351.5	329.5	309.2
42.5°	620.1	555.6	501.0	456.7	420.6	392.2	372.3	355.7	336.3	315.8	297.0
45°	598.7	531.5	472.3	424.7	388.2	360.2	339.7	327.2	312.6	293.2	277.3
47.5°	567.2	502.5	441.3	392.2	354.5	328.6	309.3	297.3	287.1	272.7	258.2
50°	539.3	480.9	418.9	370.2	332.5	306.4	288.6	277.7	269.0	257.9	245.6
52.5°	508.1	453.7	396.9	348.7	311.4	285.7	268.3	258.7	251.4	243.5	231.4
55°	458.4	412.2	359.5	313.8	279.4	254.2	238.9	230.6	224.6	218.6	211.2
57.5°	403.8	367.6	321.0	279.1	247.4	224.5	210.3	202.2	197.5	194.4	190.1
60°	365.3	334.4	294.2	256.0	225.1	204.7	190.9	184.6	180.7	178.2	174.9
62.5°	329.6	304.2	267.0	232.2	205.1	185.9	173.5	167.4	163.7	162.4	159.8
65°	277.1	257.4	226.7	197.8	174.7	158.3	147.9	142.1	139.8	138.4	138.6
67.5°	225.2	213.3	188.6	164.0	145.5	131.8	123.4	119.0	117.8	116.0	116.0
70°	193.6	184.6	163.8	142.3	125.9	115.3	107.9	103.3	102.1	101.2	101.0
72.5°	165.7	157.8	139.8	122.6	107.8	98.5	92.4	89.6	87.7	87.2	87.1
75°	124.5	120.2	105.8	92.2	82.0	75.6	71.4	68.9	67.5	67.2	67.5
77.5°	88.5	84.7	75.6	65.9	59.5	54.6	51.1	50.2	48.7	48.7	48.5
80°	66.5	64.0	58.2	50.6	45.3	41.1	39.3	37.7	37.2	36.5	37.2
82.5°	48.2	45.5	41.6	36.7	32.3	29.9	28.0	27.5	27.2	26.9	27.0
85°	23.8	24.0	21.7	18.0	16.2	14.8	13.6	13.6	13.4	13.2	13.4
87.5°	10.7	10.0	9.0	8.1	6.7	5.8	5.2	5.2	4.8	5.1	5.6
90°	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0	2.0	4.0	6.0
92.5°	227.8	136.4	81.9	52.7	35.5	23.2	14.8	12.2	14.8	23.2	35.5
95°	446.2	226.6	119.8	74.9	52.9	41.9	33.9	32.9	33.9	41.9	52.9
97.5°	356.2	195.3	124.6	92.2	72.5	61.5	55.9	54.7	55.9	61.5	72.5
100°	323.4	193.7	135.8	105.8	86.8	75.9	71.9	69.9	71.9	75.9	86.8
102.5°	309.9	200.9	149.3	120.2	102.8	91.0	87.8	86.7	87.8	91.0	102.8
105°	304.5	215.6	171.7	143.8	127.8	117.8	112.8	112.8	112.8	117.8	127.8
107.5°	313.7	237.6	195.1	169.9	153.3	145.1	140.4	138.4	140.4	145.1	153.3
110°	322.4	253.6	212.6	186.7	171.7	162.7	158.7	156.7	158.7	162.7	171.7





TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	333.6	268.7	229.4	204.2	189.3	180.3	177.1	175.1	177.1	180.3	189.3
115°	350.4	292.5	255.6	230.6	215.6	206.6	203.6	201.7	203.6	206.6	215.6
117.5°	369.6	316.9	281.9	257.8	240.8	231.8	228.6	225.6	228.6	231.8	240.8
120°	382.3	334.4	299.5	274.5	257.6	248.6	244.6	241.6	244.6	248.6	257.6
122.5°	396.7	351.2	316.3	291.3	272.7	263.7	260.5	258.4	260.5	263.7	272.7
125°	416.3	373.4	340.4	314.5	295.5	286.5	281.5	279.5	281.5	286.5	295.5
127.5°	434.2	394.7	363.0	337.0	316.9	305.5	299.1	296.1	299.1	305.5	316.9
130°	446.2	408.3	377.3	351.4	330.4	317.5	309.5	306.5	309.5	317.5	330.4
132.5°	456.6	421.1	390.1	364.2	342.4	327.8	318.2	314.5	318.2	327.8	342.4
135°	471.2	438.2	407.3	380.3	359.4	343.4	331.4	327.4	331.4	343.4	359.4
137.5°	482.0	450.4	422.3	394.5	374.0	358.0	346.8	343.8	346.8	358.0	374.0
140°	489.2	459.2	430.3	403.3	384.3	368.4	356.4	353.4	356.4	368.4	384.3
142.5°	493.1	464.8	437.4	412.1	393.9	377.9	366.8	364.6	366.8	377.9	393.9
145°	499.1	474.2	448.2	425.3	407.3	393.3	383.3	381.3	383.3	393.3	407.3
147.5°	502.7	480.2	457.4	437.2	421.7	408.7	400.1	398.9	400.1	408.7	421.7
150°	505.1	484.2	462.2	445.2	431.3	418.3	411.3	409.3	411.3	418.3	431.3
152.5°	506.7	488.2	467.8	452.4	439.2	427.9	421.7	420.5	421.7	427.9	439.2
155°	508.1	492.1	475.2	461.2	451.2	441.2	435.2	435.2	435.2	441.2	451.2
157.5°	509.1	495.5	481.0	470.4	461.6	453.0	448.2	448.4	448.2	453.0	461.6
160°	509.1	497.1	484.2	475.2	467.2	460.2	456.2	457.2	456.2	460.2	467.2
162.5°	508.3	498.7	487.4	480.0	473.6	467.4	463.4	464.4	463.4	467.4	473.6
165°	507.1	499.1	491.2	485.2	481.2	476.2	473.2	475.2	473.2	476.2	481.2
167.5°	504.7	499.1	492.5	488.8	486.0	483.2	481.4	482.4	481.4	483.2	486.0
170°	503.1	499.1	494.1	491.2	489.2	487.2	486.2	487.2	486.2	487.2	489.2
172.5°	501.5	498.3	494.1	492.7	491.5	489.6	488.6	490.4	488.6	489.6	491.5
175°	499.1	497.1	494.1	494.1	494.1	493.1	492.1	494.1	492.1	493.1	494.1
177.5°	496.7	495.9	494.3	494.3	495.1	494.3	494.3	495.9	494.3	494.3	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	535.0	532.9	531.3	527.6	525.5	522.8	520.6	523.0	520.4	521.5	519.8
5°	518.3	511.8	507.2	500.5	494.7	489.4	485.5	484.8	482.9	482.0	479.2
7.5°	498.2	490.1	482.2	473.4	466.0	458.5	453.7	449.7	447.1	443.6	441.2
10°	486.4	475.5	466.3	455.7	446.4	438.3	431.9	428.6	425.6	421.2	419.6
12.5°	471.8	460.6	449.3	437.9	429.0	420.0	414.5	409.6	407.5	402.6	402.1
15°	454.3	437.4	426.3	414.8	402.5	395.1	390.5	385.2	382.9	379.4	376.9
17.5°	433.4	418.3	404.5	392.5	382.0	375.8	370.0	366.4	362.4	360.1	356.0
20°	418.2	403.9	390.0	377.3	369.2	362.1	357.5	354.0	349.8	348.7	344.5
22.5°	405.5	389.7	376.4	365.7	356.9	348.8	343.8	341.4	338.6	335.0	334.2
25°	384.7	368.3	357.0	346.4	338.5	331.1	327.7	324.7	321.9	319.3	318.4
27.5°	366.8	352.1	338.7	329.1	322.2	315.5	312.5	308.8	306.8	304.7	302.2
30°	354.2	339.2	327.4	318.2	310.8	304.8	301.5	299.0	297.2	295.3	293.9
32.5°	341.3	327.4	316.0	306.9	299.5	295.0	292.1	290.3	288.3	286.1	284.3
35°	324.2	308.9	297.8	290.0	284.2	280.7	277.5	275.9	273.6	273.6	271.7
37.5°	304.9	291.7	281.9	274.8	269.6	266.5	263.0	261.9	260.4	259.4	258.8
40°	293.5	281.2	272.0	264.8	259.3	256.7	253.9	252.1	251.2	250.0	249.6
42.5°	281.6	269.9	261.1	254.5	249.6	247.5	244.9	243.6	241.7	240.2	239.9
45°	263.6	252.3	244.2	238.9	234.8	232.2	230.6	227.8	226.9	225.1	224.8
47.5°	246.6	235.7	227.8	223.4	219.8	217.7	215.2	212.4	211.3	210.4	210.3
50°	233.8	223.9	216.5	212.4	208.9	205.9	203.3	201.5	200.8	200.8	201.3
52.5°	220.9	212.4	206.2	201.1	197.8	194.6	192.2	191.1	190.1	191.2	192.0
55°	202.0	193.4	188.8	183.9	180.7	177.0	175.8	175.4	174.7	176.5	177.5
57.5°	181.9	175.9	170.5	165.7	162.8	160.6	159.1	158.8	160.1	161.0	164.0
60°	169.1	162.2	157.4	153.7	150.2	148.8	148.3	147.9	148.8	151.3	155.3
62.5°	155.1	149.5	144.2	141.5	138.9	136.6	136.5	136.8	138.6	141.6	145.5
65°	134.5	129.6	126.2	122.9	120.8	119.5	119.9	120.8	122.9	126.9	131.2
67.5°	113.5	110.2	107.1	104.5	102.5	102.5	103.0	104.4	106.8	111.3	115.3
70°	100.1	96.4	93.8	92.7	91.0	90.1	91.5	93.8	95.9	100.1	103.5
72.5°	86.6	83.4	81.4	80.6	79.9	79.2	79.7	82.2	85.0	89.1	93.2
75°	66.5	65.4	64.0	63.1	62.4	62.9	63.3	65.6	67.9	72.3	76.9
77.5°	48.6	47.4	46.5	46.3	45.9	46.2	47.5	49.2	51.4	54.6	58.1
80°	36.7	36.3	35.8	35.6	35.6	35.8	37.7	38.8	40.9	43.9	46.7
82.5°	26.8	26.5	26.4	26.3	26.5	26.6	27.7	29.2	30.9	33.2	35.6
85°	14.1	13.6	14.3	14.6	14.1	14.8	15.3	16.2	16.9	18.0	19.2
87.5°	6.2	7.0	7.0	7.6	7.8	8.6	8.6	9.5	10.1	10.6	10.9
90°	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0	19.0	20.0	22.0
92.5°	52.7	81.9	136.4	227.8	327.0	321.8	260.5	176.9	128.4	96.6	81.9
95°	74.9	119.8	226.6	446.2	721.8	884.5	865.5	717.8	566.0	443.2	359.4
97.5°	92.2	124.6	195.3	356.2	644.5	944.6	1095.1	1069.0	962.5	842.9	726.3
100°	105.8	135.8	193.7	323.4	575.0	901.4	1151.0	1227.9	1179.0	1076.1	972.3
102.5°	120.2	149.3	200.9	309.9	522.3	825.6	1117.5	1281.4	1311.5	1262.2	1191.9
105°	143.8	171.7	215.6	304.5	471.2	723.7	1010.3	1249.8	1386.6	1430.5	1419.5
107.5°	169.9	195.1	237.6	313.7	449.6	653.7	900.8	1137.2	1319.7	1432.5	1484.6
110°	186.7	212.6	253.6	322.4	443.2	620.9	838.5	1054.2	1243.8	1384.6	1469.5



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.2	229.4	268.7	333.6	443.2	601.8	792.2	988.7	1168.8	1311.1	1411.2
115°	230.6	255.6	292.5	350.4	446.2	581.0	741.7	906.4	1061.2	1197.9	1306.7
117.5°	257.8	281.9	316.9	369.6	452.8	570.8	711.6	853.3	986.7	1104.5	1204.3
120°	274.5	299.5	334.4	382.3	459.2	566.0	694.8	824.6	944.4	1054.2	1142.0
122.5°	291.3	316.3	351.2	396.7	464.8	562.0	680.4	803.0	914.0	1011.8	1094.1
125°	314.5	340.4	373.4	416.3	474.2	557.0	660.9	771.7	873.5	960.3	1032.2
127.5°	337.0	363.0	394.7	434.2	484.8	554.6	642.9	739.7	834.8	915.8	983.1
130°	351.4	377.3	408.3	446.2	491.2	553.0	630.9	719.8	807.6	885.5	950.4
132.5°	364.2	390.1	421.1	456.6	498.3	553.0	621.3	699.8	782.0	852.7	915.2
135°	380.3	407.3	438.2	471.2	508.1	553.0	609.9	673.8	742.7	806.6	863.5
137.5°	394.5	422.3	450.4	482.0	517.1	554.2	599.8	651.9	707.6	760.7	809.0
140°	403.3	430.3	459.2	489.2	521.1	555.0	595.0	639.9	686.8	732.7	774.7
142.5°	412.1	437.4	464.8	493.1	523.5	555.8	591.0	629.5	669.2	708.8	745.1
145°	425.3	448.2	474.2	499.1	526.1	555.0	585.0	615.9	646.9	677.8	704.8
147.5°	437.2	457.4	480.2	502.7	527.1	552.4	578.8	603.2	628.3	652.1	672.4
150°	445.2	462.2	484.2	505.1	527.1	550.0	574.0	596.0	617.9	636.9	654.9
152.5°	452.4	467.8	488.2	506.7	526.3	546.9	568.4	588.0	607.5	624.9	638.9
155°	461.2	475.2	492.1	508.1	524.1	541.1	559.0	576.0	592.0	606.0	616.9
157.5°	470.4	481.0	495.5	509.1	521.5	535.1	550.2	564.0	577.2	588.0	596.6
160°	475.2	484.2	497.1	509.1	519.1	531.1	543.1	556.0	566.0	576.0	583.0
162.5°	480.0	487.4	498.7	508.3	516.7	526.3	536.7	547.3	556.4	564.8	571.0
165°	485.2	491.2	499.1	507.1	513.1	519.1	527.1	535.1	542.1	548.1	553.0
167.5°	488.8	492.5	499.1	504.7	507.5	512.1	517.7	523.5	528.1	532.7	536.3
170°	491.2	494.1	499.1	503.1	505.1	508.1	512.1	517.1	520.1	523.1	525.1
172.5°	492.7	494.1	498.3	501.5	501.9	503.3	506.5	509.9	512.9	515.1	516.3
175°	494.1	494.1	497.1	499.1	498.1	498.1	499.1	502.1	502.1	504.1	504.1
177.5°	494.3	494.3	495.9	496.7	495.1	495.1	495.9	496.7	497.5	497.5	497.5
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	518.7	520.0	518.9	520.4	518.9	520.0	518.7	519.8	521.5	520.4	523.0
5°	478.1	476.0	477.4	476.5	477.4	476.0	478.1	479.2	482.0	482.9	484.8
7.5°	440.6	438.6	436.3	435.2	436.3	438.6	440.6	441.2	443.6	447.1	449.7
10°	417.1	414.5	414.3	412.7	414.3	414.5	417.1	419.6	421.2	425.6	428.6
12.5°	399.9	397.5	394.9	394.2	394.9	397.5	399.9	402.1	402.6	407.5	409.6
15°	375.5	373.6	372.0	373.4	372.0	373.6	375.5	376.9	379.4	382.9	385.2
17.5°	355.2	353.7	353.4	351.7	353.4	353.7	355.2	356.0	360.1	362.4	366.4
20°	342.4	341.3	341.8	338.7	341.8	341.3	342.4	344.5	348.7	349.8	354.0
22.5°	332.3	330.0	329.7	329.1	329.7	330.0	332.3	334.2	335.0	338.6	341.4
25°	316.3	315.2	314.0	315.2	314.0	315.2	316.3	318.4	319.3	321.9	324.7
27.5°	302.4	301.0	300.7	300.9	300.7	301.0	302.4	302.2	304.7	306.8	308.8
30°	293.9	291.6	291.8	291.6	291.8	291.6	293.9	293.9	295.3	297.2	299.0
32.5°	284.7	283.1	282.8	282.4	282.8	283.1	284.7	284.3	286.1	288.3	290.3
35°	271.0	271.0	269.9	269.9	269.9	271.0	271.0	271.7	273.6	273.6	275.9
37.5°	258.2	258.0	257.3	257.4	257.3	258.0	258.2	258.8	259.4	260.4	261.9
40°	248.6	248.4	247.7	246.3	247.7	248.4	248.6	249.6	250.0	251.2	252.1
42.5°	239.4	238.6	238.3	237.8	238.3	238.6	239.4	239.9	240.2	241.7	243.6
45°	224.8	224.8	224.4	224.1	224.4	224.8	224.8	224.8	225.1	226.9	227.8
47.5°	210.7	211.1	212.0	211.8	212.0	211.1	210.7	210.3	210.4	211.3	212.4
50°	202.2	202.4	203.1	203.3	203.1	202.4	202.2	201.3	200.8	200.8	201.5
52.5°	192.8	194.1	195.0	194.8	195.0	194.1	192.8	192.0	191.2	190.1	191.1
55°	179.5	181.2	182.8	183.0	182.8	181.2	179.5	177.5	176.5	174.7	175.4
57.5°	166.5	168.7	170.4	171.0	170.4	168.7	166.5	164.0	161.0	160.1	158.8
60°	157.6	160.6	162.7	163.6	162.7	160.6	157.6	155.3	151.3	148.8	147.9
62.5°	149.1	152.5	154.5	154.7	154.5	152.5	149.1	145.5	141.6	138.6	136.8
65°	135.2	138.6	140.5	141.9	140.5	138.6	135.2	131.2	126.9	122.9	120.8
67.5°	120.2	123.7	125.7	126.8	125.7	123.7	120.2	115.3	111.3	106.8	104.4
70°	109.3	112.8	115.5	116.5	115.5	112.8	109.3	103.5	100.1	95.9	93.8
72.5°	98.6	101.7	103.9	105.0	103.9	101.7	98.6	93.2	89.1	85.0	82.2
75°	79.9	84.1	86.2	87.3	86.2	84.1	79.9	76.9	72.3	67.9	65.6
77.5°	61.6	65.4	66.7	67.3	66.7	65.4	61.6	58.1	54.6	51.4	49.2
80°	49.4	51.8	53.4	53.6	53.4	51.8	49.4	46.7	43.9	40.9	38.8
82.5°	38.0	39.9	40.4	41.0	40.4	39.9	38.0	35.6	33.2	30.9	29.2
85°	20.8	21.7	22.0	21.7	22.0	21.7	20.8	19.2	18.0	16.9	16.2
87.5°	11.2	11.0	11.2	11.6	11.2	11.0	11.2	10.9	10.6	10.1	9.5
90°	22.0	22.0	23.0	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0
92.5°	69.1	66.7	65.3	63.7	65.3	66.7	69.1	81.9	96.6	128.4	176.9
95°	288.5	258.6	250.6	234.6	250.6	258.6	288.5	359.4	443.2	566.0	717.8
97.5°	664.7	608.7	579.8	567.0	579.8	608.7	664.7	726.3	842.9	962.5	1069.0
100°	903.4	831.6	794.6	778.7	794.6	831.6	903.4	972.3	1076.1	1179.0	1227.9
102.5°	1118.3	1067.2	1027.0	1015.0	1027.0	1067.2	1118.3	1191.9	1262.2	1311.5	1281.4
105°	1387.6	1354.7	1334.7	1322.7	1334.7	1354.7	1387.6	1419.5	1430.5	1386.6	1249.8
107.5°	1500.8	1500.6	1494.0	1486.0	1494.0	1500.6	1500.8	1484.6	1432.5	1319.7	1137.2
110°	1514.4	1533.3	1540.3	1540.3	1540.3	1533.3	1514.4	1469.5	1384.6	1243.8	1054.2



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1476.8	1509.4	1526.8	1533.9	1526.8	1509.4	1476.8	1411.2	1311.1	1168.8	988.7
115°	1384.6	1432.5	1460.5	1473.5	1460.5	1432.5	1384.6	1306.7	1197.9	1061.2	906.4
117.5°	1282.2	1331.7	1359.4	1367.4	1359.4	1331.7	1282.2	1204.3	1104.5	986.7	853.3
120°	1215.9	1263.8	1290.8	1298.8	1290.8	1263.8	1215.9	1142.0	1054.2	944.4	824.6
122.5°	1160.0	1203.9	1230.9	1238.1	1230.9	1203.9	1160.0	1094.1	1011.8	914.0	803.0
125°	1088.1	1129.0	1151.0	1161.0	1151.0	1129.0	1088.1	1032.2	960.3	873.5	771.7
127.5°	1033.8	1069.9	1090.7	1095.1	1090.7	1069.9	1033.8	983.1	915.8	834.8	739.7
130°	1000.3	1033.2	1053.2	1059.2	1053.2	1033.2	1000.3	950.4	885.5	807.6	719.8
132.5°	965.1	998.1	1016.4	1023.2	1016.4	998.1	965.1	915.2	852.7	782.0	699.8
135°	907.4	940.4	958.3	964.3	958.3	940.4	907.4	863.5	806.6	742.7	673.8
137.5°	848.3	878.3	894.9	901.4	894.9	878.3	848.3	809.0	760.7	707.6	651.9
140°	811.6	837.6	852.5	857.5	852.5	837.6	811.6	774.7	732.7	686.8	639.9
142.5°	776.5	798.4	812.6	816.8	812.6	798.4	776.5	745.1	708.8	669.2	629.5
145°	728.7	745.7	756.7	760.7	756.7	745.7	728.7	704.8	677.8	646.9	615.9
147.5°	691.4	705.0	711.4	713.2	711.4	705.0	691.4	672.4	652.1	628.3	603.2
150°	669.8	681.8	685.8	686.8	685.8	681.8	669.8	654.9	636.9	617.9	596.0
152.5°	651.5	661.1	665.0	666.0	665.0	661.1	651.5	638.9	624.9	607.5	588.0
155°	626.9	633.9	636.9	637.9	636.9	633.9	626.9	616.9	606.0	592.0	576.0
157.5°	604.4	610.1	612.9	612.7	612.9	610.1	604.4	596.6	588.0	577.2	564.0
160°	590.0	595.0	597.0	596.0	597.0	595.0	590.0	583.0	576.0	566.0	556.0
162.5°	576.4	580.6	581.0	580.8	581.0	580.6	576.4	571.0	564.8	556.4	547.3
165°	557.0	559.0	559.0	559.0	559.0	559.0	557.0	553.0	548.1	542.1	535.1
167.5°	538.3	540.1	539.3	539.1	539.3	540.1	538.3	536.3	532.7	528.1	523.5
170°	527.1	528.1	528.1	527.1	528.1	528.1	527.1	525.1	523.1	520.1	517.1
172.5°	516.7	518.5	516.9	515.9	516.9	518.5	516.7	516.3	515.1	512.9	509.9
175°	504.1	505.1	503.1	502.1	503.1	505.1	504.1	504.1	504.1	502.1	502.1
177.5°	496.7	497.5	495.1	495.1	495.1	497.5	496.7	497.5	497.5	497.5	496.7
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	520.6	522.8	525.5	527.6	531.3	532.9	535.0	536.6	539.6	542.4	545.7
5°	485.5	489.4	494.7	500.5	507.2	511.8	518.3	522.2	530.1	537.2	544.2
7.5°	453.7	458.5	466.0	473.4	482.2	490.1	498.2	507.2	517.2	529.1	538.9
10°	431.9	438.3	446.4	455.7	466.3	475.5	486.4	496.1	508.4	522.2	535.2
12.5°	414.5	420.0	429.0	437.9	449.3	460.6	471.8	484.6	498.9	514.3	530.5
15°	390.5	395.1	402.5	414.8	426.3	437.4	454.3	466.3	484.3	501.4	521.1
17.5°	370.0	375.8	382.0	392.5	404.5	418.3	433.4	448.5	465.8	487.5	509.6
20°	357.5	362.1	369.2	377.3	390.0	403.9	418.2	433.5	454.7	477.2	501.0
22.5°	343.8	348.8	356.9	365.7	376.4	389.7	405.5	422.2	444.4	466.4	492.3
25°	327.7	331.1	338.5	346.4	357.0	368.3	384.7	403.2	425.2	450.4	476.7
27.5°	312.5	315.5	322.2	329.1	338.7	352.1	366.8	385.5	406.2	431.7	460.9
30°	301.5	304.8	310.8	318.2	327.4	339.2	354.2	371.8	394.0	418.9	449.4
32.5°	292.1	295.0	299.5	306.9	316.0	327.4	341.3	359.2	381.4	406.7	436.7
35°	277.5	280.7	284.2	290.0	297.8	308.9	324.2	341.1	362.3	386.8	414.3
37.5°	263.0	266.5	269.6	274.8	281.9	291.7	304.9	322.5	341.7	365.3	391.7
40°	253.9	256.7	259.3	264.8	272.0	281.2	293.5	309.2	329.5	351.5	373.4
42.5°	244.9	247.5	249.6	254.5	261.1	269.9	281.6	297.0	315.8	336.3	355.7
45°	230.6	232.2	234.8	238.9	244.2	252.3	263.6	277.3	293.2	312.6	327.2
47.5°	215.2	217.7	219.8	223.4	227.8	235.7	246.6	258.2	272.7	287.1	297.3
50°	203.3	205.9	208.9	212.4	216.5	223.9	233.8	245.6	257.9	269.0	277.7
52.5°	192.2	194.6	197.8	201.1	206.2	212.4	220.9	231.4	243.5	251.4	258.7
55°	175.8	177.0	180.7	183.9	188.8	193.4	202.0	211.2	218.6	224.6	230.6
57.5°	159.1	160.6	162.8	165.7	170.5	175.9	181.9	190.1	194.4	197.5	202.2
60°	148.3	148.8	150.2	153.7	157.4	162.2	169.1	174.9	178.2	180.7	184.6
62.5°	136.5	136.6	138.9	141.5	144.2	149.5	155.1	159.8	162.4	163.7	167.4
65°	119.9	119.5	120.8	122.9	126.2	129.6	134.5	138.6	138.4	139.8	142.1
67.5°	103.0	102.5	102.5	104.5	107.1	110.2	113.5	116.0	116.0	117.8	119.0
70°	91.5	90.1	91.0	92.7	93.8	96.4	100.1	101.0	101.2	102.1	103.3
72.5°	79.7	79.2	79.9	80.6	81.4	83.4	86.6	87.1	87.2	87.7	89.6
75°	63.3	62.9	62.4	63.1	64.0	65.4	66.5	67.5	67.2	67.5	68.9
77.5°	47.5	46.2	45.9	46.3	46.5	47.4	48.6	48.5	48.7	48.7	50.2
80°	37.7	35.8	35.6	35.6	35.8	36.3	36.7	37.2	36.5	37.2	37.7
82.5°	27.7	26.6	26.5	26.3	26.4	26.5	26.8	27.0	26.9	27.2	27.5
85°	15.3	14.8	14.1	14.6	14.3	13.6	14.1	13.4	13.2	13.4	13.6
87.5°	8.6	8.6	7.8	7.6	7.0	7.0	6.2	5.6	5.1	4.8	5.2
90°	17.0	16.0	14.0	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0
92.5°	260.5	321.8	327.0	227.8	136.4	81.9	52.7	35.5	23.2	14.8	12.2
95°	865.5	884.5	721.8	446.2	226.6	119.8	74.9	52.9	41.9	33.9	32.9
97.5°	1095.1	944.6	644.5	356.2	195.3	124.6	92.2	72.5	61.5	55.9	54.7
100°	1151.0	901.4	575.0	323.4	193.7	135.8	105.8	86.8	75.9	71.9	69.9
102.5°	1117.5	825.6	522.3	309.9	200.9	149.3	120.2	102.8	91.0	87.8	86.7
105°	1010.3	723.7	471.2	304.5	215.6	171.7	143.8	127.8	117.8	112.8	112.8
107.5°	900.8	653.7	449.6	313.7	237.6	195.1	169.9	153.3	145.1	140.4	138.4
110°	838.5	620.9	443.2	322.4	253.6	212.6	186.7	171.7	162.7	158.7	156.7



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	792.2	601.8	443.2	333.6	268.7	229.4	204.2	189.3	180.3	177.1	175.1
115°	741.7	581.0	446.2	350.4	292.5	255.6	230.6	215.6	206.6	203.6	201.7
117.5°	711.6	570.8	452.8	369.6	316.9	281.9	257.8	240.8	231.8	228.6	225.6
120°	694.8	566.0	459.2	382.3	334.4	299.5	274.5	257.6	248.6	244.6	241.6
122.5°	680.4	562.0	464.8	396.7	351.2	316.3	291.3	272.7	263.7	260.5	258.4
125°	660.9	557.0	474.2	416.3	373.4	340.4	314.5	295.5	286.5	281.5	279.5
127.5°	642.9	554.6	484.8	434.2	394.7	363.0	337.0	316.9	305.5	299.1	296.1
130°	630.9	553.0	491.2	446.2	408.3	377.3	351.4	330.4	317.5	309.5	306.5
132.5°	621.3	553.0	498.3	456.6	421.1	390.1	364.2	342.4	327.8	318.2	314.5
135°	609.9	553.0	508.1	471.2	438.2	407.3	380.3	359.4	343.4	331.4	327.4
137.5°	599.8	554.2	517.1	482.0	450.4	422.3	394.5	374.0	358.0	346.8	343.8
140°	595.0	555.0	521.1	489.2	459.2	430.3	403.3	384.3	368.4	356.4	353.4
142.5°	591.0	555.8	523.5	493.1	464.8	437.4	412.1	393.9	377.9	366.8	364.6
145°	585.0	555.0	526.1	499.1	474.2	448.2	425.3	407.3	393.3	383.3	381.3
147.5°	578.8	552.4	527.1	502.7	480.2	457.4	437.2	421.7	408.7	400.1	398.9
150°	574.0	550.0	527.1	505.1	484.2	462.2	445.2	431.3	418.3	411.3	409.3
152.5°	568.4	546.9	526.3	506.7	488.2	467.8	452.4	439.2	427.9	421.7	420.5
155°	559.0	541.1	524.1	508.1	492.1	475.2	461.2	451.2	441.2	435.2	435.2
157.5°	550.2	535.1	521.5	509.1	495.5	481.0	470.4	461.6	453.0	448.2	448.4
160°	543.1	531.1	519.1	509.1	497.1	484.2	475.2	467.2	460.2	456.2	457.2
162.5°	536.7	526.3	516.7	508.3	498.7	487.4	480.0	473.6	467.4	463.4	464.4
165°	527.1	519.1	513.1	507.1	499.1	491.2	485.2	481.2	476.2	473.2	475.2
167.5°	517.7	512.1	507.5	504.7	499.1	492.5	488.8	486.0	483.2	481.4	482.4
170°	512.1	508.1	505.1	503.1	499.1	494.1	491.2	489.2	487.2	486.2	487.2
172.5°	506.5	503.3	501.9	501.5	498.3	494.1	492.7	491.5	489.6	488.6	490.4
175°	499.1	498.1	498.1	499.1	497.1	494.1	494.1	494.1	493.1	492.1	494.1
177.5°	495.9	495.1	495.1	496.7	495.9	494.3	494.3	495.1	494.3	494.3	495.9
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	547.4	549.9	551.6	554.7	557.3	558.8	560.1	561.2	562.5	563.6	566.8
5°	550.9	556.9	562.0	569.8	577.0	582.5	588.5	593.8	598.2	604.5	609.3
7.5°	549.3	560.0	571.2	583.4	595.8	607.3	618.0	627.9	636.9	647.8	657.4
10°	547.9	562.4	576.7	593.2	610.0	624.3	637.7	651.4	661.3	675.2	687.0
12.5°	546.8	563.9	581.2	600.9	619.4	639.7	657.5	667.5	682.6	693.7	707.7
15°	542.1	564.7	588.5	610.7	637.1	655.8	671.5	690.9	705.0	719.1	734.3
17.5°	533.7	559.4	586.0	615.1	640.3	660.4	680.7	699.4	716.2	735.1	754.1
20°	529.8	555.5	586.0	615.8	640.5	661.5	682.3	702.9	721.4	745.7	767.6
22.5°	521.7	552.7	580.8	609.9	635.3	658.2	681.8	705.1	729.7	757.1	784.6
25°	507.2	538.6	568.4	597.1	622.7	651.4	676.6	707.8	739.2	775.5	809.7
27.5°	492.1	522.2	549.5	577.2	607.1	639.6	672.2	707.6	748.8	794.6	842.8
30°	479.9	508.4	534.9	563.3	594.5	631.0	666.9	708.9	756.5	808.0	865.4
32.5°	465.7	491.9	517.7	547.8	581.8	620.3	662.1	708.2	765.4	823.9	882.9
35°	441.3	463.3	489.9	522.0	560.3	604.5	652.8	707.3	772.9	840.2	889.8
37.5°	412.5	432.9	460.9	496.1	536.3	583.7	641.0	705.7	775.4	829.0	845.0
40°	393.0	412.0	441.1	477.6	518.7	568.9	631.7	700.1	767.6	801.8	788.6
42.5°	372.3	392.2	420.6	456.7	501.0	555.6	620.1	688.5	745.1	758.0	712.5
45°	339.7	360.2	388.2	424.7	472.3	531.5	598.7	660.9	693.4	670.1	599.6
47.5°	309.3	328.6	354.5	392.2	441.3	502.5	567.2	616.8	619.4	563.7	488.4
50°	288.6	306.4	332.5	370.2	418.9	480.9	539.3	578.4	560.8	497.7	425.4
52.5°	268.3	285.7	311.4	348.7	396.9	453.7	508.1	535.5	502.4	437.6	375.9
55°	238.9	254.2	279.4	313.8	359.5	412.2	458.4	467.9	424.9	361.2	311.0
57.5°	210.3	224.5	247.4	279.1	321.0	367.6	403.8	401.7	356.3	301.6	261.8
60°	190.9	204.7	225.1	256.0	294.2	334.4	365.3	357.9	312.9	265.7	232.2
62.5°	173.5	185.9	205.1	232.2	267.0	304.2	329.6	318.7	274.6	233.4	206.9
65°	147.9	158.3	174.7	197.8	226.7	257.4	277.1	263.0	225.3	193.2	171.9
67.5°	123.4	131.8	145.5	164.0	188.6	213.3	225.2	211.1	180.9	157.5	141.7
70°	107.9	115.3	125.9	142.3	163.8	184.6	193.6	180.9	155.0	134.9	123.6
72.5°	92.4	98.5	107.8	122.6	139.8	157.8	165.7	153.6	132.3	115.3	104.8
75°	71.4	75.6	82.0	92.2	105.8	120.2	124.5	113.9	100.3	87.6	80.6
77.5°	51.1	54.6	59.5	65.9	75.6	84.7	88.5	82.4	71.9	63.8	58.1
80°	39.3	41.1	45.3	50.6	58.2	64.0	66.5	62.6	55.2	49.2	44.8
82.5°	28.0	29.9	32.3	36.7	41.6	45.5	48.2	45.6	40.3	35.5	33.0
85°	13.6	14.8	16.2	18.0	21.7	24.0	23.8	22.2	20.1	18.3	16.9
87.5°	5.2	5.8	6.7	8.1	9.0	10.0	10.7	10.6	10.2	9.9	9.5
90°	2.0	4.0	6.0	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0
92.5°	14.8	23.2	35.5	52.7	81.9	136.4	227.8	327.0	321.8	260.5	176.9
95°	33.9	41.9	52.9	74.9	119.8	226.6	446.2	721.8	884.5	865.5	717.8
97.5°	55.9	61.5	72.5	92.2	124.6	195.3	356.2	644.5	944.6	1095.1	1069.0
100°	71.9	75.9	86.8	105.8	135.8	193.7	323.4	575.0	901.4	1151.0	1227.9
102.5°	87.8	91.0	102.8	120.2	149.3	200.9	309.9	522.3	825.6	1117.5	1281.4
105°	112.8	117.8	127.8	143.8	171.7	215.6	304.5	471.2	723.7	1010.3	1249.8
107.5°	140.4	145.1	153.3	169.9	195.1	237.6	313.7	449.6	653.7	900.8	1137.2
110°	158.7	162.7	171.7	186.7	212.6	253.6	322.4	443.2	620.9	838.5	1054.2





TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	177.1	180.3	189.3	204.2	229.4	268.7	333.6	443.2	601.8	792.2	988.7
115°	203.6	206.6	215.6	230.6	255.6	292.5	350.4	446.2	581.0	741.7	906.4
117.5°	228.6	231.8	240.8	257.8	281.9	316.9	369.6	452.8	570.8	711.6	853.3
120°	244.6	248.6	257.6	274.5	299.5	334.4	382.3	459.2	566.0	694.8	824.6
122.5°	260.5	263.7	272.7	291.3	316.3	351.2	396.7	464.8	562.0	680.4	803.0
125°	281.5	286.5	295.5	314.5	340.4	373.4	416.3	474.2	557.0	660.9	771.7
127.5°	299.1	305.5	316.9	337.0	363.0	394.7	434.2	484.8	554.6	642.9	739.7
130°	309.5	317.5	330.4	351.4	377.3	408.3	446.2	491.2	553.0	630.9	719.8
132.5°	318.2	327.8	342.4	364.2	390.1	421.1	456.6	498.3	553.0	621.3	699.8
135°	331.4	343.4	359.4	380.3	407.3	438.2	471.2	508.1	553.0	609.9	673.8
137.5°	346.8	358.0	374.0	394.5	422.3	450.4	482.0	517.1	554.2	599.8	651.9
140°	356.4	368.4	384.3	403.3	430.3	459.2	489.2	521.1	555.0	595.0	639.9
142.5°	366.8	377.9	393.9	412.1	437.4	464.8	493.1	523.5	555.8	591.0	629.5
145°	383.3	393.3	407.3	425.3	448.2	474.2	499.1	526.1	555.0	585.0	615.9
147.5°	400.1	408.7	421.7	437.2	457.4	480.2	502.7	527.1	552.4	578.8	603.2
150°	411.3	418.3	431.3	445.2	462.2	484.2	505.1	527.1	550.0	574.0	596.0
152.5°	421.7	427.9	439.2	452.4	467.8	488.2	506.7	526.3	546.9	568.4	588.0
155°	435.2	441.2	451.2	461.2	475.2	492.1	508.1	524.1	541.1	559.0	576.0
157.5°	448.2	453.0	461.6	470.4	481.0	495.5	509.1	521.5	535.1	550.2	564.0
160°	456.2	460.2	467.2	475.2	484.2	497.1	509.1	519.1	531.1	543.1	556.0
162.5°	463.4	467.4	473.6	480.0	487.4	498.7	508.3	516.7	526.3	536.7	547.3
165°	473.2	476.2	481.2	485.2	491.2	499.1	507.1	513.1	519.1	527.1	535.1
167.5°	481.4	483.2	486.0	488.8	492.5	499.1	504.7	507.5	512.1	517.7	523.5
170°	486.2	487.2	489.2	491.2	494.1	499.1	503.1	505.1	508.1	512.1	517.1
172.5°	488.6	489.6	491.5	492.7	494.1	498.3	501.5	501.9	503.3	506.5	509.9
175°	492.1	493.1	494.1	494.1	494.1	497.1	499.1	498.1	498.1	499.1	502.1
177.5°	494.3	494.3	495.1	494.3	494.3	495.9	496.7	495.1	495.1	495.9	496.7
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	569.4	570.8	574.0	572.9	574.3	575.1	575.8
5°	615.3	622.7	626.0	625.5	630.4	629.2	628.0
7.5°	667.3	675.0	679.4	684.8	687.9	688.2	690.9
10°	696.7	706.8	711.0	716.8	720.5	722.6	722.3
12.5°	719.2	727.2	736.5	739.3	744.3	747.0	746.0
15°	746.4	759.1	768.8	773.6	779.9	781.7	784.2
17.5°	770.6	787.6	798.9	814.0	819.7	823.2	821.1
20°	788.9	811.3	822.6	840.6	850.6	855.9	854.0
22.5°	810.5	834.8	855.7	871.3	886.4	893.6	895.1
25°	847.6	880.8	911.6	932.1	950.8	955.2	964.9
27.5°	889.0	928.2	961.1	982.7	995.7	1000.6	1003.7
30°	915.0	954.1	978.8	992.7	996.8	996.4	995.9
32.5°	927.8	952.2	957.0	953.1	943.6	935.5	927.1
35°	909.7	891.5	864.2	829.1	803.2	777.1	774.5
37.5°	818.2	759.8	714.4	663.7	634.5	616.4	603.9
40°	732.0	665.7	610.7	568.0	538.2	526.4	514.8
42.5°	638.5	575.1	526.4	490.7	468.3	455.2	446.1
45°	518.7	462.8	424.7	398.8	381.0	370.9	365.1
47.5°	425.1	383.7	351.3	332.6	320.4	312.5	312.5
50°	374.8	335.3	313.8	299.0	288.4	282.1	283.3
52.5°	330.2	300.7	282.4	270.0	262.1	258.3	258.1
55°	276.1	254.9	242.9	233.8	228.5	224.1	225.1
57.5°	236.2	218.3	210.2	202.7	199.0	197.3	194.7
60°	211.4	197.6	190.6	184.6	180.9	179.5	177.0
62.5°	189.4	178.5	171.8	166.9	163.6	163.1	161.1
65°	159.2	150.9	144.9	142.6	139.1	138.2	138.2
67.5°	131.2	125.3	120.6	118.5	117.0	117.2	116.1
70°	113.7	108.8	105.8	103.5	102.4	102.6	101.7
72.5°	99.5	94.0	91.4	90.0	88.5	89.1	88.7
75°	75.3	72.6	71.2	69.8	68.9	68.4	67.9
77.5°	55.3	52.9	51.8	51.0	51.2	50.0	50.9
80°	42.7	40.7	40.0	38.8	38.6	38.6	38.4
82.5°	31.3	30.1	29.6	28.7	28.2	28.6	28.0
85°	16.2	15.3	15.0	15.0	14.6	14.1	15.3
87.5°	9.7	9.2	9.6	9.4	9.4	9.4	9.0
90°	19.0	20.0	22.0	22.0	22.0	23.0	23.0
92.5°	128.4	96.6	81.9	69.1	66.7	65.3	63.7
95°	566.0	443.2	359.4	288.5	258.6	250.6	234.6
97.5°	962.5	842.9	726.3	664.7	608.7	579.8	567.0
100°	1179.0	1076.1	972.3	903.4	831.6	794.6	778.7
102.5°	1311.5	1262.2	1191.9	1118.3	1067.2	1027.0	1015.0
105°	1386.6	1430.5	1419.5	1387.6	1354.7	1334.7	1322.7
107.5°	1319.7	1432.5	1484.6	1500.8	1500.6	1494.0	1486.0
110°	1243.8	1384.6	1469.5	1514.4	1533.3	1540.3	1540.3



TEST NUMBER: P333144

CATALOG NUMBER: S125DIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1168.8	1311.1	1411.2	1476.8	1509.4	1526.8	1533.9
115°	1061.2	1197.9	1306.7	1384.6	1432.5	1460.5	1473.5
117.5°	986.7	1104.5	1204.3	1282.2	1331.7	1359.4	1367.4
120°	944.4	1054.2	1142.0	1215.9	1263.8	1290.8	1298.8
122.5°	914.0	1011.8	1094.1	1160.0	1203.9	1230.9	1238.1
125°	873.5	960.3	1032.2	1088.1	1129.0	1151.0	1161.0
127.5°	834.8	915.8	983.1	1033.8	1069.9	1090.7	1095.1
130°	807.6	885.5	950.4	1000.3	1033.2	1053.2	1059.2
132.5°	782.0	852.7	915.2	965.1	998.1	1016.4	1023.2
135°	742.7	806.6	863.5	907.4	940.4	958.3	964.3
137.5°	707.6	760.7	809.0	848.3	878.3	894.9	901.4
140°	686.8	732.7	774.7	811.6	837.6	852.5	857.5
142.5°	669.2	708.8	745.1	776.5	798.4	812.6	816.8
145°	646.9	677.8	704.8	728.7	745.7	756.7	760.7
147.5°	628.3	652.1	672.4	691.4	705.0	711.4	713.2
150°	617.9	636.9	654.9	669.8	681.8	685.8	686.8
152.5°	607.5	624.9	638.9	651.5	661.1	665.0	666.0
155°	592.0	606.0	616.9	626.9	633.9	636.9	637.9
157.5°	577.2	588.0	596.6	604.4	610.1	612.9	612.7
160°	566.0	576.0	583.0	590.0	595.0	597.0	596.0
162.5°	556.4	564.8	571.0	576.4	580.6	581.0	580.8
165°	542.1	548.1	553.0	557.0	559.0	559.0	559.0
167.5°	528.1	532.7	536.3	538.3	540.1	539.3	539.1
170°	520.1	523.1	525.1	527.1	528.1	528.1	527.1
172.5°	512.9	515.1	516.3	516.7	518.5	516.9	515.9
175°	502.1	504.1	504.1	504.1	505.1	503.1	502.1
177.5°	497.5	497.5	497.5	496.7	497.5	495.1	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1

(END OF REPORT)