

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333117

Luminaire Tested: **S125DIP-S375D365U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333117
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D365U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2851.7 lumens
Efficiency: N/A
Efficacy: 140.5 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	60	53	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	28	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3516	3516	3516	3516
5°	4071	3528	3089	3528
10°	4737	3510	2706	3510
15°	5243	3484	2497	3484
20°	5869	3443	2328	3443
25°	6876	3397	2246	3397
30°	7427	3351	2175	3351
35°	6106	3266	2128	3266
40°	4340	3148	2076	3148
45°	3335	2988	2047	2988
50°	2846	2790	2043	2790
55°	2535	2597	2061	2597
60°	2286	2384	2113	2384
65°	2112	2172	2168	2172
70°	1920	1951	2200	1951
75°	1694	1719	2178	1719
80°	1428	1402	1993	1402
85°	1134	1008	1608	1008



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	1.8
10°-20°	156.0	5.5
20°-30°	253.4	8.9
30°-40°	309.1	10.8
40°-50°	281.2	9.9
50°-60°	224.0	7.9
60°-70°	156.0	5.5
70°-80°	83.2	2.9
80°-90°	22.0	0.8
90°-100°	127.1	4.5
100°-110°	273.1	9.6
110°-120°	256.3	9.0
120°-130°	207.7	7.3
130°-140°	166.7	5.8
140°-150°	125.8	4.4
150°-160°	88.6	3.1
160°-170°	52.2	1.8
170°-180°	17.0	0.6
0°-30°	461.8	16.2
0°-40°	770.9	27.0
0°-60°	1276.0	44.7
0°-90°	1537.2	53.9
90°-120°	656.5	23.0
90°-150°	1156.8	40.6
90°-180°	1315.0	46.1
0°-180°	2851.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	544	544	544	544	544	
5°	628	544	476	544	628	63
15°	784	521	373	521	784	224
25°	965	477	315	477	965	441
35°	774	414	270	414	774	474
45°	365	327	224	327	365	292
55°	225	231	183	231	225	203
65°	138	142	142	142	138	137
75°	68	69	87	69	68	73
85°	15	14	22	14	15	18
90°	8	0	8	0	8	6
95°	83	12	83	12	83	118
105°	468	40	468	40	468	465
115°	522	71	522	71	522	510
125°	411	99	411	99	411	372
135°	341	116	341	116	341	265
145°	269	135	269	135	269	171
155°	226	154	226	154	226	105
165°	198	168	198	168	198	57
175°	178	175	178	175	178	17
180°	175	175	175	175	175	



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	575.8	575.1	574.3	572.9	574.0	570.8	569.4	566.8	563.6	562.5	561.2
5°	628.0	629.2	630.4	625.5	626.0	622.7	615.3	609.3	604.5	598.2	593.8
7.5°	690.9	688.2	687.9	684.8	679.4	675.0	667.3	657.4	647.8	636.9	627.9
10°	722.3	722.6	720.5	716.8	711.0	706.8	696.7	687.0	675.2	661.3	651.4
12.5°	746.0	747.0	744.3	739.3	736.5	727.2	719.2	707.7	693.7	682.6	667.5
15°	784.2	781.7	779.9	773.6	768.8	759.1	746.4	734.3	719.1	705.0	690.9
17.5°	821.1	823.2	819.7	814.0	798.9	787.6	770.6	754.1	735.1	716.2	699.4
20°	854.0	855.9	850.6	840.6	822.6	811.3	788.9	767.6	745.7	721.4	702.9
22.5°	895.1	893.6	886.4	871.3	855.7	834.8	810.5	784.6	757.1	729.7	705.1
25°	964.9	955.2	950.8	932.1	911.6	880.8	847.6	809.7	775.5	739.2	707.8
27.5°	1003.7	1000.6	995.7	982.7	961.1	928.2	889.0	842.8	794.6	748.8	707.6
30°	995.9	996.4	996.8	992.7	978.8	954.1	915.0	865.4	808.0	756.5	708.9
32.5°	927.1	935.5	943.6	953.1	957.0	952.2	927.8	882.9	823.9	765.4	708.2
35°	774.5	777.1	803.2	829.1	864.2	891.5	909.7	889.8	840.2	772.9	707.3
37.5°	603.9	616.4	634.5	663.7	714.4	759.8	818.2	845.0	829.0	775.4	705.7
40°	514.8	526.4	538.2	568.0	610.7	665.7	732.0	788.6	801.8	767.6	700.1
42.5°	446.1	455.2	468.3	490.7	526.4	575.1	638.5	712.5	758.0	745.1	688.5
45°	365.1	370.9	381.0	398.8	424.7	462.8	518.7	599.6	670.1	693.4	660.9
47.5°	312.5	312.5	320.4	332.6	351.3	383.7	425.1	488.4	563.7	619.4	616.8
50°	283.3	282.1	288.4	299.0	313.8	335.3	374.8	425.4	497.7	560.8	578.4
52.5°	258.1	258.3	262.1	270.0	282.4	300.7	330.2	375.9	437.6	502.4	535.5
55°	225.1	224.1	228.5	233.8	242.9	254.9	276.1	311.0	361.2	424.9	467.9
57.5°	194.7	197.3	199.0	202.7	210.2	218.3	236.2	261.8	301.6	356.3	401.7
60°	177.0	179.5	180.9	184.6	190.6	197.6	211.4	232.2	265.7	312.9	357.9
62.5°	161.1	163.1	163.6	166.9	171.8	178.5	189.4	206.9	233.4	274.6	318.7
65°	138.2	138.2	139.1	142.6	144.9	150.9	159.2	171.9	193.2	225.3	263.0
67.5°	116.1	117.2	117.0	118.5	120.6	125.3	131.2	141.7	157.5	180.9	211.1
70°	101.7	102.6	102.4	103.5	105.8	108.8	113.7	123.6	134.9	155.0	180.9
72.5°	88.7	89.1	88.5	90.0	91.4	94.0	99.5	104.8	115.3	132.3	153.6
75°	67.9	68.4	68.9	69.8	71.2	72.6	75.3	80.6	87.6	100.3	113.9
77.5°	50.9	50.0	51.2	51.0	51.8	52.9	55.3	58.1	63.8	71.9	82.4
80°	38.4	38.6	38.6	38.8	40.0	40.7	42.7	44.8	49.2	55.2	62.6
82.5°	28.0	28.6	28.2	28.7	29.6	30.1	31.3	33.0	35.5	40.3	45.6
85°	15.3	14.1	14.6	15.0	15.0	15.3	16.2	16.9	18.3	20.1	22.2
87.5°	6.1	6.4	6.5	6.5	6.7	6.6	7.3	7.2	7.7	8.2	8.8
90°	8.1	8.1	7.8	7.8	7.8	7.1	6.7	6.4	6.0	5.7	4.9
92.5°	22.5	23.1	23.6	24.5	29.0	34.2	45.4	62.6	92.2	113.9	115.8
95°	83.1	88.7	91.5	102.1	127.2	156.9	200.4	254.1	306.4	313.1	255.5
97.5°	200.7	205.3	215.5	235.3	257.1	298.4	340.8	378.4	387.7	334.4	228.2
100°	275.7	281.3	294.4	319.8	344.2	381.0	417.4	434.7	407.5	319.1	203.6
102.5°	359.4	363.6	377.8	395.9	422.0	446.9	464.3	453.6	395.6	292.3	184.9
105°	468.3	472.5	479.6	491.2	502.6	506.4	490.9	442.5	357.7	256.2	166.8
107.5°	526.1	528.9	531.3	531.3	525.6	507.1	467.2	402.6	318.9	231.4	159.2
110°	545.3	545.3	542.8	536.1	520.2	490.2	440.4	373.2	296.9	219.8	156.9



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	543.1	540.5	534.4	522.8	499.6	464.2	413.8	350.0	280.5	213.0	156.9
115°	521.6	517.0	507.1	490.2	462.6	424.1	375.7	320.9	262.6	205.7	158.0
117.5°	484.1	481.3	471.5	453.9	426.4	391.0	349.3	302.1	251.9	202.1	160.3
120°	459.8	457.0	447.4	430.5	404.3	373.2	334.3	291.9	246.0	200.4	162.6
122.5°	438.3	435.8	426.2	410.7	387.3	358.2	323.6	284.3	240.9	199.0	164.5
125°	411.0	407.5	399.7	385.2	365.4	340.0	309.2	273.2	234.0	197.2	167.9
127.5°	387.7	386.1	378.8	366.0	348.0	324.2	295.5	261.9	227.6	196.4	171.6
130°	375.0	372.9	365.8	354.1	336.5	313.5	285.9	254.8	223.4	195.8	173.9
132.5°	362.2	359.8	353.3	341.7	324.0	301.9	276.9	247.7	220.0	195.8	176.4
135°	341.4	339.3	332.9	321.3	305.7	285.6	262.9	238.6	215.9	195.8	179.9
137.5°	319.1	316.8	310.9	300.3	286.4	269.3	250.5	230.8	212.3	196.2	183.1
140°	303.6	301.8	296.5	287.3	274.2	259.4	243.1	226.5	210.6	196.5	184.5
142.5°	289.2	287.7	282.7	274.9	263.8	250.9	236.9	222.9	209.2	196.8	185.3
145°	269.3	267.9	264.0	258.0	249.5	240.0	229.0	218.1	207.1	196.5	186.2
147.5°	252.5	251.8	249.6	244.8	238.1	230.9	222.4	213.5	204.9	195.6	186.6
150°	243.1	242.8	241.4	237.1	231.8	225.5	218.8	211.0	203.2	194.7	186.6
152.5°	235.8	235.4	234.0	230.6	226.2	221.2	215.1	208.2	201.2	193.6	186.3
155°	225.8	225.5	224.4	221.9	218.4	214.5	209.6	203.9	197.9	191.6	185.5
157.5°	216.9	217.0	216.0	214.0	211.2	208.2	204.3	199.7	194.8	189.4	184.6
160°	211.0	211.3	210.6	208.9	206.4	203.9	200.4	196.9	192.3	188.0	183.8
162.5°	205.6	205.7	205.5	204.1	202.2	200.0	197.0	193.7	190.0	186.3	182.9
165°	197.9	197.9	197.9	197.2	195.8	194.0	191.9	189.4	186.6	183.8	181.7
167.5°	190.8	190.9	191.2	190.6	189.9	188.6	187.0	185.3	183.3	181.3	179.7
170°	186.6	187.0	187.0	186.6	185.9	185.2	184.1	183.1	181.3	179.9	178.8
172.5°	182.6	183.0	183.6	182.9	182.8	182.4	181.6	180.5	179.3	178.2	177.7
175°	177.8	178.1	178.8	178.5	178.5	178.5	177.8	177.8	176.7	176.4	176.4
177.5°	175.3	175.3	176.1	175.9	176.1	176.1	176.1	175.9	175.6	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	560.1	558.8	557.3	554.7	551.6	549.9	547.4	545.7	542.4	539.6	536.6
5°	588.5	582.5	577.0	569.8	562.0	556.9	550.9	544.2	537.2	530.1	522.2
7.5°	618.0	607.3	595.8	583.4	571.2	560.0	549.3	538.9	529.1	517.2	507.2
10°	637.7	624.3	610.0	593.2	576.7	562.4	547.9	535.2	522.2	508.4	496.1
12.5°	657.5	639.7	619.4	600.9	581.2	563.9	546.8	530.5	514.3	498.9	484.6
15°	671.5	655.8	637.1	610.7	588.5	564.7	542.1	521.1	501.4	484.3	466.3
17.5°	680.7	660.4	640.3	615.1	586.0	559.4	533.7	509.6	487.5	465.8	448.5
20°	682.3	661.5	640.5	615.8	586.0	555.5	529.8	501.0	477.2	454.7	433.5
22.5°	681.8	658.2	635.3	609.9	580.8	552.7	521.7	492.3	466.4	444.4	422.2
25°	676.6	651.4	622.7	597.1	568.4	538.6	507.2	476.7	450.4	425.2	403.2
27.5°	672.2	639.6	607.1	577.2	549.5	522.2	492.1	460.9	431.7	406.2	385.5
30°	666.9	631.0	594.5	563.3	534.9	508.4	479.9	449.4	418.9	394.0	371.8
32.5°	662.1	620.3	581.8	547.8	517.7	491.9	465.7	436.7	406.7	381.4	359.2
35°	652.8	604.5	560.3	522.0	489.9	463.3	441.3	414.3	386.8	362.3	341.1
37.5°	641.0	583.7	536.3	496.1	460.9	432.9	412.5	391.7	365.3	341.7	322.5
40°	631.7	568.9	518.7	477.6	441.1	412.0	393.0	373.4	351.5	329.5	309.2
42.5°	620.1	555.6	501.0	456.7	420.6	392.2	372.3	355.7	336.3	315.8	297.0
45°	598.7	531.5	472.3	424.7	388.2	360.2	339.7	327.2	312.6	293.2	277.3
47.5°	567.2	502.5	441.3	392.2	354.5	328.6	309.3	297.3	287.1	272.7	258.2
50°	539.3	480.9	418.9	370.2	332.5	306.4	288.6	277.7	269.0	257.9	245.6
52.5°	508.1	453.7	396.9	348.7	311.4	285.7	268.3	258.7	251.4	243.5	231.4
55°	458.4	412.2	359.5	313.8	279.4	254.2	238.9	230.6	224.6	218.6	211.2
57.5°	403.8	367.6	321.0	279.1	247.4	224.5	210.3	202.2	197.5	194.4	190.1
60°	365.3	334.4	294.2	256.0	225.1	204.7	190.9	184.6	180.7	178.2	174.9
62.5°	329.6	304.2	267.0	232.2	205.1	185.9	173.5	167.4	163.7	162.4	159.8
65°	277.1	257.4	226.7	197.8	174.7	158.3	147.9	142.1	139.8	138.4	138.6
67.5°	225.2	213.3	188.6	164.0	145.5	131.8	123.4	119.0	117.8	116.0	116.0
70°	193.6	184.6	163.8	142.3	125.9	115.3	107.9	103.3	102.1	101.2	101.0
72.5°	165.7	157.8	139.8	122.6	107.8	98.5	92.4	89.6	87.7	87.2	87.1
75°	124.5	120.2	105.8	92.2	82.0	75.6	71.4	68.9	67.5	67.2	67.5
77.5°	88.5	84.7	75.6	65.9	59.5	54.6	51.1	50.2	48.7	48.7	48.5
80°	66.5	64.0	58.2	50.6	45.3	41.1	39.3	37.7	37.2	36.5	37.2
82.5°	48.2	45.5	41.6	36.7	32.3	29.9	28.0	27.5	27.2	26.9	27.0
85°	23.8	24.0	21.7	18.0	16.2	14.8	13.6	13.6	13.4	13.2	13.4
87.5°	9.1	8.5	7.7	7.0	6.0	5.3	4.9	5.1	4.6	4.5	4.9
90°	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	80.6	48.3	29.0	18.7	12.6	8.2	5.2	4.3	5.2	8.2	12.6
95°	158.0	80.2	42.4	26.5	18.7	14.8	12.0	11.7	12.0	14.8	18.7
97.5°	126.1	69.1	44.1	32.7	25.7	21.8	19.8	19.4	19.8	21.8	25.7
100°	114.5	68.6	48.1	37.5	30.7	26.9	25.4	24.7	25.4	26.9	30.7
102.5°	109.7	71.1	52.9	42.6	36.4	32.2	31.1	30.7	31.1	32.2	36.4
105°	107.8	76.3	60.8	50.9	45.2	41.7	39.9	39.9	39.9	41.7	45.2
107.5°	111.0	84.1	69.1	60.2	54.3	51.4	49.7	49.0	49.7	51.4	54.3
110°	114.2	89.8	75.3	66.1	60.8	57.6	56.2	55.5	56.2	57.6	60.8



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	118.1	95.1	81.2	72.3	67.0	63.8	62.7	62.0	62.7	63.8	67.0
115°	124.0	103.6	90.5	81.6	76.3	73.2	72.1	71.4	72.1	73.2	76.3
117.5°	130.8	112.2	99.8	91.3	85.2	82.1	80.9	79.9	80.9	82.1	85.2
120°	135.4	118.4	106.0	97.2	91.2	88.0	86.6	85.5	86.6	88.0	91.2
122.5°	140.4	124.3	112.0	103.1	96.6	93.4	92.2	91.5	92.2	93.4	96.6
125°	147.4	132.2	120.5	111.3	104.6	101.4	99.7	99.0	99.7	101.4	104.6
127.5°	153.7	139.7	128.5	119.3	112.2	108.1	105.9	104.8	105.9	108.1	112.2
130°	158.0	144.5	133.6	124.4	117.0	112.4	109.6	108.5	109.6	112.4	117.0
132.5°	161.7	149.1	138.1	128.9	121.2	116.1	112.7	111.3	112.7	116.1	121.2
135°	166.8	155.1	144.2	134.7	127.2	121.6	117.3	115.9	117.3	121.6	127.2
137.5°	170.6	159.5	149.5	139.7	132.4	126.7	122.8	121.7	122.8	126.7	132.4
140°	173.2	162.6	152.3	142.8	136.1	130.4	126.2	125.1	126.2	130.4	136.1
142.5°	174.6	164.5	154.9	145.9	139.5	133.8	129.8	129.1	129.8	133.8	139.5
145°	176.7	167.9	158.7	150.6	144.2	139.2	135.7	135.0	135.7	139.2	144.2
147.5°	178.0	170.0	161.9	154.8	149.3	144.7	141.6	141.2	141.6	144.7	149.3
150°	178.8	171.4	163.6	157.6	152.7	148.1	145.6	144.9	145.6	148.1	152.7
152.5°	179.4	172.8	165.6	160.2	155.5	151.5	149.3	148.9	149.3	151.5	155.5
155°	179.9	174.2	168.2	163.3	159.7	156.2	154.1	154.1	154.1	156.2	159.7
157.5°	180.2	175.4	170.3	166.5	163.4	160.4	158.7	158.8	158.7	160.4	163.4
160°	180.2	176.0	171.4	168.2	165.4	162.9	161.5	161.9	161.5	162.9	165.4
162.5°	180.0	176.6	172.5	169.9	167.7	165.5	164.1	164.4	164.1	165.5	167.7
165°	179.5	176.7	173.9	171.8	170.3	168.6	167.5	168.2	167.5	168.6	170.3
167.5°	178.7	176.7	174.4	173.0	172.0	171.1	170.4	170.8	170.4	171.1	172.0
170°	178.1	176.7	174.9	173.9	173.2	172.5	172.1	172.5	172.1	172.5	173.2
172.5°	177.6	176.4	174.9	174.4	174.0	173.3	173.0	173.6	173.0	173.3	174.0
175°	176.7	176.0	174.9	174.9	174.9	174.6	174.2	174.9	174.2	174.6	174.9
177.5°	175.9	175.6	175.0	175.0	175.3	175.0	175.0	175.6	175.0	175.0	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	535.0	532.9	531.3	527.6	525.5	522.8	520.6	523.0	520.4	521.5	519.8
5°	518.3	511.8	507.2	500.5	494.7	489.4	485.5	484.8	482.9	482.0	479.2
7.5°	498.2	490.1	482.2	473.4	466.0	458.5	453.7	449.7	447.1	443.6	441.2
10°	486.4	475.5	466.3	455.7	446.4	438.3	431.9	428.6	425.6	421.2	419.6
12.5°	471.8	460.6	449.3	437.9	429.0	420.0	414.5	409.6	407.5	402.6	402.1
15°	454.3	437.4	426.3	414.8	402.5	395.1	390.5	385.2	382.9	379.4	376.9
17.5°	433.4	418.3	404.5	392.5	382.0	375.8	370.0	366.4	362.4	360.1	356.0
20°	418.2	403.9	390.0	377.3	369.2	362.1	357.5	354.0	349.8	348.7	344.5
22.5°	405.5	389.7	376.4	365.7	356.9	348.8	343.8	341.4	338.6	335.0	334.2
25°	384.7	368.3	357.0	346.4	338.5	331.1	327.7	324.7	321.9	319.3	318.4
27.5°	366.8	352.1	338.7	329.1	322.2	315.5	312.5	308.8	306.8	304.7	302.2
30°	354.2	339.2	327.4	318.2	310.8	304.8	301.5	299.0	297.2	295.3	293.9
32.5°	341.3	327.4	316.0	306.9	299.5	295.0	292.1	290.3	288.3	286.1	284.3
35°	324.2	308.9	297.8	290.0	284.2	280.7	277.5	275.9	273.6	273.6	271.7
37.5°	304.9	291.7	281.9	274.8	269.6	266.5	263.0	261.9	260.4	259.4	258.8
40°	293.5	281.2	272.0	264.8	259.3	256.7	253.9	252.1	251.2	250.0	249.6
42.5°	281.6	269.9	261.1	254.5	249.6	247.5	244.9	243.6	241.7	240.2	239.9
45°	263.6	252.3	244.2	238.9	234.8	232.2	230.6	227.8	226.9	225.1	224.8
47.5°	246.6	235.7	227.8	223.4	219.8	217.7	215.2	212.4	211.3	210.4	210.3
50°	233.8	223.9	216.5	212.4	208.9	205.9	203.3	201.5	200.8	200.8	201.3
52.5°	220.9	212.4	206.2	201.1	197.8	194.6	192.2	191.1	190.1	191.2	192.0
55°	202.0	193.4	188.8	183.9	180.7	177.0	175.8	175.4	174.7	176.5	177.5
57.5°	181.9	175.9	170.5	165.7	162.8	160.6	159.1	158.8	160.1	161.0	164.0
60°	169.1	162.2	157.4	153.7	150.2	148.8	148.3	147.9	148.8	151.3	155.3
62.5°	155.1	149.5	144.2	141.5	138.9	136.6	136.5	136.8	138.6	141.6	145.5
65°	134.5	129.6	126.2	122.9	120.8	119.5	119.9	120.8	122.9	126.9	131.2
67.5°	113.5	110.2	107.1	104.5	102.5	102.5	103.0	104.4	106.8	111.3	115.3
70°	100.1	96.4	93.8	92.7	91.0	90.1	91.5	93.8	95.9	100.1	103.5
72.5°	86.6	83.4	81.4	80.6	79.9	79.2	79.7	82.2	85.0	89.1	93.2
75°	66.5	65.4	64.0	63.1	62.4	62.9	63.3	65.6	67.9	72.3	76.9
77.5°	48.6	47.4	46.5	46.3	45.9	46.2	47.5	49.2	51.4	54.6	58.1
80°	36.7	36.3	35.8	35.6	35.6	35.8	37.7	38.8	40.9	43.9	46.7
82.5°	26.8	26.5	26.4	26.3	26.5	26.6	27.7	29.2	30.9	33.2	35.6
85°	14.1	13.6	14.3	14.6	14.1	14.8	15.3	16.2	16.9	18.0	19.2
87.5°	5.2	5.7	5.6	5.9	6.0	6.5	6.4	7.2	7.6	8.1	8.0
90°	2.8	3.5	3.9	4.6	4.9	5.7	6.0	6.4	6.7	7.1	7.8
92.5°	18.7	29.0	48.3	80.6	115.8	113.9	92.2	62.6	45.4	34.2	29.0
95°	26.5	42.4	80.2	158.0	255.5	313.1	306.4	254.1	200.4	156.9	127.2
97.5°	32.7	44.1	69.1	126.1	228.2	334.4	387.7	378.4	340.8	298.4	257.1
100°	37.5	48.1	68.6	114.5	203.6	319.1	407.5	434.7	417.4	381.0	344.2
102.5°	42.6	52.9	71.1	109.7	184.9	292.3	395.6	453.6	464.3	446.9	422.0
105°	50.9	60.8	76.3	107.8	166.8	256.2	357.7	442.5	490.9	506.4	502.6
107.5°	60.2	69.1	84.1	111.0	159.2	231.4	318.9	402.6	467.2	507.1	525.6
110°	66.1	75.3	89.8	114.2	156.9	219.8	296.9	373.2	440.4	490.2	520.2



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	72.3	81.2	95.1	118.1	156.9	213.0	280.5	350.0	413.8	464.2	499.6
115°	81.6	90.5	103.6	124.0	158.0	205.7	262.6	320.9	375.7	424.1	462.6
117.5°	91.3	99.8	112.2	130.8	160.3	202.1	251.9	302.1	349.3	391.0	426.4
120°	97.2	106.0	118.4	135.4	162.6	200.4	246.0	291.9	334.3	373.2	404.3
122.5°	103.1	112.0	124.3	140.4	164.5	199.0	240.9	284.3	323.6	358.2	387.3
125°	111.3	120.5	132.2	147.4	167.9	197.2	234.0	273.2	309.2	340.0	365.4
127.5°	119.3	128.5	139.7	153.7	171.6	196.4	227.6	261.9	295.5	324.2	348.0
130°	124.4	133.6	144.5	158.0	173.9	195.8	223.4	254.8	285.9	313.5	336.5
132.5°	128.9	138.1	149.1	161.7	176.4	195.8	220.0	247.7	276.9	301.9	324.0
135°	134.7	144.2	155.1	166.8	179.9	195.8	215.9	238.6	262.9	285.6	305.7
137.5°	139.7	149.5	159.5	170.6	183.1	196.2	212.3	230.8	250.5	269.3	286.4
140°	142.8	152.3	162.6	173.2	184.5	196.5	210.6	226.5	243.1	259.4	274.2
142.5°	145.9	154.9	164.5	174.6	185.3	196.8	209.2	222.9	236.9	250.9	263.8
145°	150.6	158.7	167.9	176.7	186.2	196.5	207.1	218.1	229.0	240.0	249.5
147.5°	154.8	161.9	170.0	178.0	186.6	195.6	204.9	213.5	222.4	230.9	238.1
150°	157.6	163.6	171.4	178.8	186.6	194.7	203.2	211.0	218.8	225.5	231.8
152.5°	160.2	165.6	172.8	179.4	186.3	193.6	201.2	208.2	215.1	221.2	226.2
155°	163.3	168.2	174.2	179.9	185.5	191.6	197.9	203.9	209.6	214.5	218.4
157.5°	166.5	170.3	175.4	180.2	184.6	189.4	194.8	199.7	204.3	208.2	211.2
160°	168.2	171.4	176.0	180.2	183.8	188.0	192.3	196.9	200.4	203.9	206.4
162.5°	169.9	172.5	176.6	180.0	182.9	186.3	190.0	193.7	197.0	200.0	202.2
165°	171.8	173.9	176.7	179.5	181.7	183.8	186.6	189.4	191.9	194.0	195.8
167.5°	173.0	174.4	176.7	178.7	179.7	181.3	183.3	185.3	187.0	188.6	189.9
170°	173.9	174.9	176.7	178.1	178.8	179.9	181.3	183.1	184.1	185.2	185.9
172.5°	174.4	174.9	176.4	177.6	177.7	178.2	179.3	180.5	181.6	182.4	182.8
175°	174.9	174.9	176.0	176.7	176.4	176.4	176.7	177.8	177.8	178.5	178.5
177.5°	175.0	175.0	175.6	175.9	175.3	175.3	175.6	175.9	176.1	176.1	176.1
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	518.7	520.0	518.9	520.4	518.9	520.0	518.7	519.8	521.5	520.4	523.0
5°	478.1	476.0	477.4	476.5	477.4	476.0	478.1	479.2	482.0	482.9	484.8
7.5°	440.6	438.6	436.3	435.2	436.3	438.6	440.6	441.2	443.6	447.1	449.7
10°	417.1	414.5	414.3	412.7	414.3	414.5	417.1	419.6	421.2	425.6	428.6
12.5°	399.9	397.5	394.9	394.2	394.9	397.5	399.9	402.1	402.6	407.5	409.6
15°	375.5	373.6	372.0	373.4	372.0	373.6	375.5	376.9	379.4	382.9	385.2
17.5°	355.2	353.7	353.4	351.7	353.4	353.7	355.2	356.0	360.1	362.4	366.4
20°	342.4	341.3	341.8	338.7	341.8	341.3	342.4	344.5	348.7	349.8	354.0
22.5°	332.3	330.0	329.7	329.1	329.7	330.0	332.3	334.2	335.0	338.6	341.4
25°	316.3	315.2	314.0	315.2	314.0	315.2	316.3	318.4	319.3	321.9	324.7
27.5°	302.4	301.0	300.7	300.9	300.7	301.0	302.4	302.2	304.7	306.8	308.8
30°	293.9	291.6	291.8	291.6	291.8	291.6	293.9	293.9	295.3	297.2	299.0
32.5°	284.7	283.1	282.8	282.4	282.8	283.1	284.7	284.3	286.1	288.3	290.3
35°	271.0	271.0	269.9	269.9	269.9	271.0	271.0	271.7	273.6	273.6	275.9
37.5°	258.2	258.0	257.3	257.4	257.3	258.0	258.2	258.8	259.4	260.4	261.9
40°	248.6	248.4	247.7	246.3	247.7	248.4	248.6	249.6	250.0	251.2	252.1
42.5°	239.4	238.6	238.3	237.8	238.3	238.6	239.4	239.9	240.2	241.7	243.6
45°	224.8	224.8	224.4	224.1	224.4	224.8	224.8	224.8	225.1	226.9	227.8
47.5°	210.7	211.1	212.0	211.8	212.0	211.1	210.7	210.3	210.4	211.3	212.4
50°	202.2	202.4	203.1	203.3	203.1	202.4	202.2	201.3	200.8	200.8	201.5
52.5°	192.8	194.1	195.0	194.8	195.0	194.1	192.8	192.0	191.2	190.1	191.1
55°	179.5	181.2	182.8	183.0	182.8	181.2	179.5	177.5	176.5	174.7	175.4
57.5°	166.5	168.7	170.4	171.0	170.4	168.7	166.5	164.0	161.0	160.1	158.8
60°	157.6	160.6	162.7	163.6	162.7	160.6	157.6	155.3	151.3	148.8	147.9
62.5°	149.1	152.5	154.5	154.7	154.5	152.5	149.1	145.5	141.6	138.6	136.8
65°	135.2	138.6	140.5	141.9	140.5	138.6	135.2	131.2	126.9	122.9	120.8
67.5°	120.2	123.7	125.7	126.8	125.7	123.7	120.2	115.3	111.3	106.8	104.4
70°	109.3	112.8	115.5	116.5	115.5	112.8	109.3	103.5	100.1	95.9	93.8
72.5°	98.6	101.7	103.9	105.0	103.9	101.7	98.6	93.2	89.1	85.0	82.2
75°	79.9	84.1	86.2	87.3	86.2	84.1	79.9	76.9	72.3	67.9	65.6
77.5°	61.6	65.4	66.7	67.3	66.7	65.4	61.6	58.1	54.6	51.4	49.2
80°	49.4	51.8	53.4	53.6	53.4	51.8	49.4	46.7	43.9	40.9	38.8
82.5°	38.0	39.9	40.4	41.0	40.4	39.9	38.0	35.6	33.2	30.9	29.2
85°	20.8	21.7	22.0	21.7	22.0	21.7	20.8	19.2	18.0	16.9	16.2
87.5°	8.4	8.2	8.3	8.7	8.3	8.2	8.4	8.0	8.1	7.6	7.2
90°	7.8	7.8	8.1	8.1	8.1	7.8	7.8	7.8	7.1	6.7	6.4
92.5°	24.5	23.6	23.1	22.5	23.1	23.6	24.5	29.0	34.2	45.4	62.6
95°	102.1	91.5	88.7	83.1	88.7	91.5	102.1	127.2	156.9	200.4	254.1
97.5°	235.3	215.5	205.3	200.7	205.3	215.5	235.3	257.1	298.4	340.8	378.4
100°	319.8	294.4	281.3	275.7	281.3	294.4	319.8	344.2	381.0	417.4	434.7
102.5°	395.9	377.8	363.6	359.4	363.6	377.8	395.9	422.0	446.9	464.3	453.6
105°	491.2	479.6	472.5	468.3	472.5	479.6	491.2	502.6	506.4	490.9	442.5
107.5°	531.3	531.3	528.9	526.1	528.9	531.3	531.3	525.6	507.1	467.2	402.6
110°	536.1	542.8	545.3	545.3	545.3	542.8	536.1	520.2	490.2	440.4	373.2



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	522.8	534.4	540.5	543.1	540.5	534.4	522.8	499.6	464.2	413.8	350.0
115°	490.2	507.1	517.0	521.6	517.0	507.1	490.2	462.6	424.1	375.7	320.9
117.5°	453.9	471.5	481.3	484.1	481.3	471.5	453.9	426.4	391.0	349.3	302.1
120°	430.5	447.4	457.0	459.8	457.0	447.4	430.5	404.3	373.2	334.3	291.9
122.5°	410.7	426.2	435.8	438.3	435.8	426.2	410.7	387.3	358.2	323.6	284.3
125°	385.2	399.7	407.5	411.0	407.5	399.7	385.2	365.4	340.0	309.2	273.2
127.5°	366.0	378.8	386.1	387.7	386.1	378.8	366.0	348.0	324.2	295.5	261.9
130°	354.1	365.8	372.9	375.0	372.9	365.8	354.1	336.5	313.5	285.9	254.8
132.5°	341.7	353.3	359.8	362.2	359.8	353.3	341.7	324.0	301.9	276.9	247.7
135°	321.3	332.9	339.3	341.4	339.3	332.9	321.3	305.7	285.6	262.9	238.6
137.5°	300.3	310.9	316.8	319.1	316.8	310.9	300.3	286.4	269.3	250.5	230.8
140°	287.3	296.5	301.8	303.6	301.8	296.5	287.3	274.2	259.4	243.1	226.5
142.5°	274.9	282.7	287.7	289.2	287.7	282.7	274.9	263.8	250.9	236.9	222.9
145°	258.0	264.0	267.9	269.3	267.9	264.0	258.0	249.5	240.0	229.0	218.1
147.5°	244.8	249.6	251.8	252.5	251.8	249.6	244.8	238.1	230.9	222.4	213.5
150°	237.1	241.4	242.8	243.1	242.8	241.4	237.1	231.8	225.5	218.8	211.0
152.5°	230.6	234.0	235.4	235.8	235.4	234.0	230.6	226.2	221.2	215.1	208.2
155°	221.9	224.4	225.5	225.8	225.5	224.4	221.9	218.4	214.5	209.6	203.9
157.5°	214.0	216.0	217.0	216.9	217.0	216.0	214.0	211.2	208.2	204.3	199.7
160°	208.9	210.6	211.3	211.0	211.3	210.6	208.9	206.4	203.9	200.4	196.9
162.5°	204.1	205.5	205.7	205.6	205.7	205.5	204.1	202.2	200.0	197.0	193.7
165°	197.2	197.9	197.9	197.9	197.9	197.9	197.2	195.8	194.0	191.9	189.4
167.5°	190.6	191.2	190.9	190.8	190.9	191.2	190.6	189.9	188.6	187.0	185.3
170°	186.6	187.0	187.0	186.6	187.0	187.0	186.6	185.9	185.2	184.1	183.1
172.5°	182.9	183.6	183.0	182.6	183.0	183.6	182.9	182.8	182.4	181.6	180.5
175°	178.5	178.8	178.1	177.8	178.1	178.8	178.5	178.5	178.5	177.8	177.8
177.5°	175.9	176.1	175.3	175.3	175.3	176.1	175.9	176.1	176.1	176.1	175.9
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	520.6	522.8	525.5	527.6	531.3	532.9	535.0	536.6	539.6	542.4	545.7
5°	485.5	489.4	494.7	500.5	507.2	511.8	518.3	522.2	530.1	537.2	544.2
7.5°	453.7	458.5	466.0	473.4	482.2	490.1	498.2	507.2	517.2	529.1	538.9
10°	431.9	438.3	446.4	455.7	466.3	475.5	486.4	496.1	508.4	522.2	535.2
12.5°	414.5	420.0	429.0	437.9	449.3	460.6	471.8	484.6	498.9	514.3	530.5
15°	390.5	395.1	402.5	414.8	426.3	437.4	454.3	466.3	484.3	501.4	521.1
17.5°	370.0	375.8	382.0	392.5	404.5	418.3	433.4	448.5	465.8	487.5	509.6
20°	357.5	362.1	369.2	377.3	390.0	403.9	418.2	433.5	454.7	477.2	501.0
22.5°	343.8	348.8	356.9	365.7	376.4	389.7	405.5	422.2	444.4	466.4	492.3
25°	327.7	331.1	338.5	346.4	357.0	368.3	384.7	403.2	425.2	450.4	476.7
27.5°	312.5	315.5	322.2	329.1	338.7	352.1	366.8	385.5	406.2	431.7	460.9
30°	301.5	304.8	310.8	318.2	327.4	339.2	354.2	371.8	394.0	418.9	449.4
32.5°	292.1	295.0	299.5	306.9	316.0	327.4	341.3	359.2	381.4	406.7	436.7
35°	277.5	280.7	284.2	290.0	297.8	308.9	324.2	341.1	362.3	386.8	414.3
37.5°	263.0	266.5	269.6	274.8	281.9	291.7	304.9	322.5	341.7	365.3	391.7
40°	253.9	256.7	259.3	264.8	272.0	281.2	293.5	309.2	329.5	351.5	373.4
42.5°	244.9	247.5	249.6	254.5	261.1	269.9	281.6	297.0	315.8	336.3	355.7
45°	230.6	232.2	234.8	238.9	244.2	252.3	263.6	277.3	293.2	312.6	327.2
47.5°	215.2	217.7	219.8	223.4	227.8	235.7	246.6	258.2	272.7	287.1	297.3
50°	203.3	205.9	208.9	212.4	216.5	223.9	233.8	245.6	257.9	269.0	277.7
52.5°	192.2	194.6	197.8	201.1	206.2	212.4	220.9	231.4	243.5	251.4	258.7
55°	175.8	177.0	180.7	183.9	188.8	193.4	202.0	211.2	218.6	224.6	230.6
57.5°	159.1	160.6	162.8	165.7	170.5	175.9	181.9	190.1	194.4	197.5	202.2
60°	148.3	148.8	150.2	153.7	157.4	162.2	169.1	174.9	178.2	180.7	184.6
62.5°	136.5	136.6	138.9	141.5	144.2	149.5	155.1	159.8	162.4	163.7	167.4
65°	119.9	119.5	120.8	122.9	126.2	129.6	134.5	138.6	138.4	139.8	142.1
67.5°	103.0	102.5	102.5	104.5	107.1	110.2	113.5	116.0	116.0	117.8	119.0
70°	91.5	90.1	91.0	92.7	93.8	96.4	100.1	101.0	101.2	102.1	103.3
72.5°	79.7	79.2	79.9	80.6	81.4	83.4	86.6	87.1	87.2	87.7	89.6
75°	63.3	62.9	62.4	63.1	64.0	65.4	66.5	67.5	67.2	67.5	68.9
77.5°	47.5	46.2	45.9	46.3	46.5	47.4	48.6	48.5	48.7	48.7	50.2
80°	37.7	35.8	35.6	35.6	35.8	36.3	36.7	37.2	36.5	37.2	37.7
82.5°	27.7	26.6	26.5	26.3	26.4	26.5	26.8	27.0	26.9	27.2	27.5
85°	15.3	14.8	14.1	14.6	14.3	13.6	14.1	13.4	13.2	13.4	13.6
87.5°	6.4	6.5	6.0	5.9	5.6	5.7	5.2	4.9	4.5	4.6	5.1
90°	6.0	5.7	4.9	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4
92.5°	92.2	113.9	115.8	80.6	48.3	29.0	18.7	12.6	8.2	5.2	4.3
95°	306.4	313.1	255.5	158.0	80.2	42.4	26.5	18.7	14.8	12.0	11.7
97.5°	387.7	334.4	228.2	126.1	69.1	44.1	32.7	25.7	21.8	19.8	19.4
100°	407.5	319.1	203.6	114.5	68.6	48.1	37.5	30.7	26.9	25.4	24.7
102.5°	395.6	292.3	184.9	109.7	71.1	52.9	42.6	36.4	32.2	31.1	30.7
105°	357.7	256.2	166.8	107.8	76.3	60.8	50.9	45.2	41.7	39.9	39.9
107.5°	318.9	231.4	159.2	111.0	84.1	69.1	60.2	54.3	51.4	49.7	49.0
110°	296.9	219.8	156.9	114.2	89.8	75.3	66.1	60.8	57.6	56.2	55.5



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	280.5	213.0	156.9	118.1	95.1	81.2	72.3	67.0	63.8	62.7	62.0
115°	262.6	205.7	158.0	124.0	103.6	90.5	81.6	76.3	73.2	72.1	71.4
117.5°	251.9	202.1	160.3	130.8	112.2	99.8	91.3	85.2	82.1	80.9	79.9
120°	246.0	200.4	162.6	135.4	118.4	106.0	97.2	91.2	88.0	86.6	85.5
122.5°	240.9	199.0	164.5	140.4	124.3	112.0	103.1	96.6	93.4	92.2	91.5
125°	234.0	197.2	167.9	147.4	132.2	120.5	111.3	104.6	101.4	99.7	99.0
127.5°	227.6	196.4	171.6	153.7	139.7	128.5	119.3	112.2	108.1	105.9	104.8
130°	223.4	195.8	173.9	158.0	144.5	133.6	124.4	117.0	112.4	109.6	108.5
132.5°	220.0	195.8	176.4	161.7	149.1	138.1	128.9	121.2	116.1	112.7	111.3
135°	215.9	195.8	179.9	166.8	155.1	144.2	134.7	127.2	121.6	117.3	115.9
137.5°	212.3	196.2	183.1	170.6	159.5	149.5	139.7	132.4	126.7	122.8	121.7
140°	210.6	196.5	184.5	173.2	162.6	152.3	142.8	136.1	130.4	126.2	125.1
142.5°	209.2	196.8	185.3	174.6	164.5	154.9	145.9	139.5	133.8	129.8	129.1
145°	207.1	196.5	186.2	176.7	167.9	158.7	150.6	144.2	139.2	135.7	135.0
147.5°	204.9	195.6	186.6	178.0	170.0	161.9	154.8	149.3	144.7	141.6	141.2
150°	203.2	194.7	186.6	178.8	171.4	163.6	157.6	152.7	148.1	145.6	144.9
152.5°	201.2	193.6	186.3	179.4	172.8	165.6	160.2	155.5	151.5	149.3	148.9
155°	197.9	191.6	185.5	179.9	174.2	168.2	163.3	159.7	156.2	154.1	154.1
157.5°	194.8	189.4	184.6	180.2	175.4	170.3	166.5	163.4	160.4	158.7	158.8
160°	192.3	188.0	183.8	180.2	176.0	171.4	168.2	165.4	162.9	161.5	161.9
162.5°	190.0	186.3	182.9	180.0	176.6	172.5	169.9	167.7	165.5	164.1	164.4
165°	186.6	183.8	181.7	179.5	176.7	173.9	171.8	170.3	168.6	167.5	168.2
167.5°	183.3	181.3	179.7	178.7	176.7	174.4	173.0	172.0	171.1	170.4	170.8
170°	181.3	179.9	178.8	178.1	176.7	174.9	173.9	173.2	172.5	172.1	172.5
172.5°	179.3	178.2	177.7	177.6	176.4	174.9	174.4	174.0	173.3	173.0	173.6
175°	176.7	176.4	176.4	176.7	176.0	174.9	174.9	174.9	174.6	174.2	174.9
177.5°	175.6	175.3	175.3	175.9	175.6	175.0	175.0	175.3	175.0	175.0	175.6
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	547.4	549.9	551.6	554.7	557.3	558.8	560.1	561.2	562.5	563.6	566.8
5°	550.9	556.9	562.0	569.8	577.0	582.5	588.5	593.8	598.2	604.5	609.3
7.5°	549.3	560.0	571.2	583.4	595.8	607.3	618.0	627.9	636.9	647.8	657.4
10°	547.9	562.4	576.7	593.2	610.0	624.3	637.7	651.4	661.3	675.2	687.0
12.5°	546.8	563.9	581.2	600.9	619.4	639.7	657.5	667.5	682.6	693.7	707.7
15°	542.1	564.7	588.5	610.7	637.1	655.8	671.5	690.9	705.0	719.1	734.3
17.5°	533.7	559.4	586.0	615.1	640.3	660.4	680.7	699.4	716.2	735.1	754.1
20°	529.8	555.5	586.0	615.8	640.5	661.5	682.3	702.9	721.4	745.7	767.6
22.5°	521.7	552.7	580.8	609.9	635.3	658.2	681.8	705.1	729.7	757.1	784.6
25°	507.2	538.6	568.4	597.1	622.7	651.4	676.6	707.8	739.2	775.5	809.7
27.5°	492.1	522.2	549.5	577.2	607.1	639.6	672.2	707.6	748.8	794.6	842.8
30°	479.9	508.4	534.9	563.3	594.5	631.0	666.9	708.9	756.5	808.0	865.4
32.5°	465.7	491.9	517.7	547.8	581.8	620.3	662.1	708.2	765.4	823.9	882.9
35°	441.3	463.3	489.9	522.0	560.3	604.5	652.8	707.3	772.9	840.2	889.8
37.5°	412.5	432.9	460.9	496.1	536.3	583.7	641.0	705.7	775.4	829.0	845.0
40°	393.0	412.0	441.1	477.6	518.7	568.9	631.7	700.1	767.6	801.8	788.6
42.5°	372.3	392.2	420.6	456.7	501.0	555.6	620.1	688.5	745.1	758.0	712.5
45°	339.7	360.2	388.2	424.7	472.3	531.5	598.7	660.9	693.4	670.1	599.6
47.5°	309.3	328.6	354.5	392.2	441.3	502.5	567.2	616.8	619.4	563.7	488.4
50°	288.6	306.4	332.5	370.2	418.9	480.9	539.3	578.4	560.8	497.7	425.4
52.5°	268.3	285.7	311.4	348.7	396.9	453.7	508.1	535.5	502.4	437.6	375.9
55°	238.9	254.2	279.4	313.8	359.5	412.2	458.4	467.9	424.9	361.2	311.0
57.5°	210.3	224.5	247.4	279.1	321.0	367.6	403.8	401.7	356.3	301.6	261.8
60°	190.9	204.7	225.1	256.0	294.2	334.4	365.3	357.9	312.9	265.7	232.2
62.5°	173.5	185.9	205.1	232.2	267.0	304.2	329.6	318.7	274.6	233.4	206.9
65°	147.9	158.3	174.7	197.8	226.7	257.4	277.1	263.0	225.3	193.2	171.9
67.5°	123.4	131.8	145.5	164.0	188.6	213.3	225.2	211.1	180.9	157.5	141.7
70°	107.9	115.3	125.9	142.3	163.8	184.6	193.6	180.9	155.0	134.9	123.6
72.5°	92.4	98.5	107.8	122.6	139.8	157.8	165.7	153.6	132.3	115.3	104.8
75°	71.4	75.6	82.0	92.2	105.8	120.2	124.5	113.9	100.3	87.6	80.6
77.5°	51.1	54.6	59.5	65.9	75.6	84.7	88.5	82.4	71.9	63.8	58.1
80°	39.3	41.1	45.3	50.6	58.2	64.0	66.5	62.6	55.2	49.2	44.8
82.5°	28.0	29.9	32.3	36.7	41.6	45.5	48.2	45.6	40.3	35.5	33.0
85°	13.6	14.8	16.2	18.0	21.7	24.0	23.8	22.2	20.1	18.3	16.9
87.5°	4.9	5.3	6.0	7.0	7.7	8.5	9.1	8.8	8.2	7.7	7.2
90°	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.7	6.0	6.4
92.5°	5.2	8.2	12.6	18.7	29.0	48.3	80.6	115.8	113.9	92.2	62.6
95°	12.0	14.8	18.7	26.5	42.4	80.2	158.0	255.5	313.1	306.4	254.1
97.5°	19.8	21.8	25.7	32.7	44.1	69.1	126.1	228.2	334.4	387.7	378.4
100°	25.4	26.9	30.7	37.5	48.1	68.6	114.5	203.6	319.1	407.5	434.7
102.5°	31.1	32.2	36.4	42.6	52.9	71.1	109.7	184.9	292.3	395.6	453.6
105°	39.9	41.7	45.2	50.9	60.8	76.3	107.8	166.8	256.2	357.7	442.5
107.5°	49.7	51.4	54.3	60.2	69.1	84.1	111.0	159.2	231.4	318.9	402.6
110°	56.2	57.6	60.8	66.1	75.3	89.8	114.2	156.9	219.8	296.9	373.2



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	62.7	63.8	67.0	72.3	81.2	95.1	118.1	156.9	213.0	280.5	350.0
115°	72.1	73.2	76.3	81.6	90.5	103.6	124.0	158.0	205.7	262.6	320.9
117.5°	80.9	82.1	85.2	91.3	99.8	112.2	130.8	160.3	202.1	251.9	302.1
120°	86.6	88.0	91.2	97.2	106.0	118.4	135.4	162.6	200.4	246.0	291.9
122.5°	92.2	93.4	96.6	103.1	112.0	124.3	140.4	164.5	199.0	240.9	284.3
125°	99.7	101.4	104.6	111.3	120.5	132.2	147.4	167.9	197.2	234.0	273.2
127.5°	105.9	108.1	112.2	119.3	128.5	139.7	153.7	171.6	196.4	227.6	261.9
130°	109.6	112.4	117.0	124.4	133.6	144.5	158.0	173.9	195.8	223.4	254.8
132.5°	112.7	116.1	121.2	128.9	138.1	149.1	161.7	176.4	195.8	220.0	247.7
135°	117.3	121.6	127.2	134.7	144.2	155.1	166.8	179.9	195.8	215.9	238.6
137.5°	122.8	126.7	132.4	139.7	149.5	159.5	170.6	183.1	196.2	212.3	230.8
140°	126.2	130.4	136.1	142.8	152.3	162.6	173.2	184.5	196.5	210.6	226.5
142.5°	129.8	133.8	139.5	145.9	154.9	164.5	174.6	185.3	196.8	209.2	222.9
145°	135.7	139.2	144.2	150.6	158.7	167.9	176.7	186.2	196.5	207.1	218.1
147.5°	141.6	144.7	149.3	154.8	161.9	170.0	178.0	186.6	195.6	204.9	213.5
150°	145.6	148.1	152.7	157.6	163.6	171.4	178.8	186.6	194.7	203.2	211.0
152.5°	149.3	151.5	155.5	160.2	165.6	172.8	179.4	186.3	193.6	201.2	208.2
155°	154.1	156.2	159.7	163.3	168.2	174.2	179.9	185.5	191.6	197.9	203.9
157.5°	158.7	160.4	163.4	166.5	170.3	175.4	180.2	184.6	189.4	194.8	199.7
160°	161.5	162.9	165.4	168.2	171.4	176.0	180.2	183.8	188.0	192.3	196.9
162.5°	164.1	165.5	167.7	169.9	172.5	176.6	180.0	182.9	186.3	190.0	193.7
165°	167.5	168.6	170.3	171.8	173.9	176.7	179.5	181.7	183.8	186.6	189.4
167.5°	170.4	171.1	172.0	173.0	174.4	176.7	178.7	179.7	181.3	183.3	185.3
170°	172.1	172.5	173.2	173.9	174.9	176.7	178.1	178.8	179.9	181.3	183.1
172.5°	173.0	173.3	174.0	174.4	174.9	176.4	177.6	177.7	178.2	179.3	180.5
175°	174.2	174.6	174.9	174.9	174.9	176.0	176.7	176.4	176.4	176.7	177.8
177.5°	175.0	175.0	175.3	175.0	175.0	175.6	175.9	175.3	175.3	175.6	175.9
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	569.4	570.8	574.0	572.9	574.3	575.1	575.8
5°	615.3	622.7	626.0	625.5	630.4	629.2	628.0
7.5°	667.3	675.0	679.4	684.8	687.9	688.2	690.9
10°	696.7	706.8	711.0	716.8	720.5	722.6	722.3
12.5°	719.2	727.2	736.5	739.3	744.3	747.0	746.0
15°	746.4	759.1	768.8	773.6	779.9	781.7	784.2
17.5°	770.6	787.6	798.9	814.0	819.7	823.2	821.1
20°	788.9	811.3	822.6	840.6	850.6	855.9	854.0
22.5°	810.5	834.8	855.7	871.3	886.4	893.6	895.1
25°	847.6	880.8	911.6	932.1	950.8	955.2	964.9
27.5°	889.0	928.2	961.1	982.7	995.7	1000.6	1003.7
30°	915.0	954.1	978.8	992.7	996.8	996.4	995.9
32.5°	927.8	952.2	957.0	953.1	943.6	935.5	927.1
35°	909.7	891.5	864.2	829.1	803.2	777.1	774.5
37.5°	818.2	759.8	714.4	663.7	634.5	616.4	603.9
40°	732.0	665.7	610.7	568.0	538.2	526.4	514.8
42.5°	638.5	575.1	526.4	490.7	468.3	455.2	446.1
45°	518.7	462.8	424.7	398.8	381.0	370.9	365.1
47.5°	425.1	383.7	351.3	332.6	320.4	312.5	312.5
50°	374.8	335.3	313.8	299.0	288.4	282.1	283.3
52.5°	330.2	300.7	282.4	270.0	262.1	258.3	258.1
55°	276.1	254.9	242.9	233.8	228.5	224.1	225.1
57.5°	236.2	218.3	210.2	202.7	199.0	197.3	194.7
60°	211.4	197.6	190.6	184.6	180.9	179.5	177.0
62.5°	189.4	178.5	171.8	166.9	163.6	163.1	161.1
65°	159.2	150.9	144.9	142.6	139.1	138.2	138.2
67.5°	131.2	125.3	120.6	118.5	117.0	117.2	116.1
70°	113.7	108.8	105.8	103.5	102.4	102.6	101.7
72.5°	99.5	94.0	91.4	90.0	88.5	89.1	88.7
75°	75.3	72.6	71.2	69.8	68.9	68.4	67.9
77.5°	55.3	52.9	51.8	51.0	51.2	50.0	50.9
80°	42.7	40.7	40.0	38.8	38.6	38.6	38.4
82.5°	31.3	30.1	29.6	28.7	28.2	28.6	28.0
85°	16.2	15.3	15.0	15.0	14.6	14.1	15.3
87.5°	7.3	6.6	6.7	6.5	6.5	6.4	6.1
90°	6.7	7.1	7.8	7.8	7.8	8.1	8.1
92.5°	45.4	34.2	29.0	24.5	23.6	23.1	22.5
95°	200.4	156.9	127.2	102.1	91.5	88.7	83.1
97.5°	340.8	298.4	257.1	235.3	215.5	205.3	200.7
100°	417.4	381.0	344.2	319.8	294.4	281.3	275.7
102.5°	464.3	446.9	422.0	395.9	377.8	363.6	359.4
105°	490.9	506.4	502.6	491.2	479.6	472.5	468.3
107.5°	467.2	507.1	525.6	531.3	531.3	528.9	526.1
110°	440.4	490.2	520.2	536.1	542.8	545.3	545.3



TEST NUMBER: P333117

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	413.8	464.2	499.6	522.8	534.4	540.5	543.1
115°	375.7	424.1	462.6	490.2	507.1	517.0	521.6
117.5°	349.3	391.0	426.4	453.9	471.5	481.3	484.1
120°	334.3	373.2	404.3	430.5	447.4	457.0	459.8
122.5°	323.6	358.2	387.3	410.7	426.2	435.8	438.3
125°	309.2	340.0	365.4	385.2	399.7	407.5	411.0
127.5°	295.5	324.2	348.0	366.0	378.8	386.1	387.7
130°	285.9	313.5	336.5	354.1	365.8	372.9	375.0
132.5°	276.9	301.9	324.0	341.7	353.3	359.8	362.2
135°	262.9	285.6	305.7	321.3	332.9	339.3	341.4
137.5°	250.5	269.3	286.4	300.3	310.9	316.8	319.1
140°	243.1	259.4	274.2	287.3	296.5	301.8	303.6
142.5°	236.9	250.9	263.8	274.9	282.7	287.7	289.2
145°	229.0	240.0	249.5	258.0	264.0	267.9	269.3
147.5°	222.4	230.9	238.1	244.8	249.6	251.8	252.5
150°	218.8	225.5	231.8	237.1	241.4	242.8	243.1
152.5°	215.1	221.2	226.2	230.6	234.0	235.4	235.8
155°	209.6	214.5	218.4	221.9	224.4	225.5	225.8
157.5°	204.3	208.2	211.2	214.0	216.0	217.0	216.9
160°	200.4	203.9	206.4	208.9	210.6	211.3	211.0
162.5°	197.0	200.0	202.2	204.1	205.5	205.7	205.6
165°	191.9	194.0	195.8	197.2	197.9	197.9	197.9
167.5°	187.0	188.6	189.9	190.6	191.2	190.9	190.8
170°	184.1	185.2	185.9	186.6	187.0	187.0	186.6
172.5°	181.6	182.4	182.8	182.9	183.6	183.0	182.6
175°	177.8	178.5	178.5	178.5	178.8	178.1	177.8
177.5°	176.1	176.1	176.1	175.9	176.1	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3

(END OF REPORT)