

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333135

Luminaire Tested: **S125DIP-S375D810U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333135
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D810U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4446.7 lumens
Efficiency: N/A
Efficacy: 142.5 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	35
1	94	90	87	83	85	82	79	76	66	64	62	51	50	48	37	36	36	29
2	86	79	73	68	78	72	67	62	58	54	51	45	43	40	33	32	30	25
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	24	21	20	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	36	31	50	40	34	29	33	28	24	26	22	20	20	17	15	12
8	52	40	32	27	47	37	30	25	30	25	21	24	20	17	18	15	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3516	3516	3516	3516
5°	4071	3528	3089	3528
10°	4737	3510	2706	3510
15°	5243	3484	2497	3484
20°	5869	3443	2328	3443
25°	6876	3397	2246	3397
30°	7427	3351	2175	3351
35°	6106	3266	2128	3266
40°	4340	3148	2076	3148
45°	3335	2988	2047	2988
50°	2846	2790	2043	2790
55°	2535	2597	2061	2597
60°	2286	2384	2113	2384
65°	2112	2172	2168	2172
70°	1920	1951	2200	1951
75°	1694	1719	2178	1719
80°	1428	1402	1993	1402
85°	1134	1008	1608	1008



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	1.2
10°-20°	156.0	3.5
20°-30°	253.4	5.7
30°-40°	309.1	7.0
40°-50°	281.2	6.3
50°-60°	224.0	5.0
60°-70°	156.0	3.5
70°-80°	83.2	1.9
80°-90°	23.2	0.5
90°-100°	281.1	6.3
100°-110°	604.3	13.6
110°-120°	567.1	12.8
120°-130°	459.6	10.3
130°-140°	368.8	8.3
140°-150°	278.3	6.3
150°-160°	195.9	4.4
160°-170°	115.5	2.6
170°-180°	37.6	0.8
0°-30°	461.8	10.4
0°-40°	770.9	17.3
0°-60°	1276.0	28.7
0°-90°	1538.3	34.6
90°-120°	1452.5	32.7
90°-150°	2559.3	57.6
90°-180°	2908.0	65.4
0°-180°	4446.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	544	544	544	544	544	
5°	628	544	476	544	628	63
15°	784	521	373	521	784	224
25°	965	477	315	477	965	441
35°	774	414	270	414	774	474
45°	365	327	224	327	365	292
55°	225	231	183	231	225	203
65°	138	142	142	142	138	137
75°	68	69	87	69	68	73
85°	15	14	22	14	15	18
90°	18	1	18	1	18	13
95°	184	26	184	26	184	260
105°	1036	88	1036	88	1036	1030
115°	1154	158	1154	158	1154	1128
125°	909	219	909	219	909	823
135°	755	256	755	256	755	585
145°	596	299	596	299	596	379
155°	500	341	500	341	500	233
165°	438	372	438	372	438	125
175°	393	387	393	387	393	38
180°	388	388	388	388	388	



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	575.8	575.1	574.3	572.9	574.0	570.8	569.4	566.8	563.6	562.5	561.2
5°	628.0	629.2	630.4	625.5	626.0	622.7	615.3	609.3	604.5	598.2	593.8
7.5°	690.9	688.2	687.9	684.8	679.4	675.0	667.3	657.4	647.8	636.9	627.9
10°	722.3	722.6	720.5	716.8	711.0	706.8	696.7	687.0	675.2	661.3	651.4
12.5°	746.0	747.0	744.3	739.3	736.5	727.2	719.2	707.7	693.7	682.6	667.5
15°	784.2	781.7	779.9	773.6	768.8	759.1	746.4	734.3	719.1	705.0	690.9
17.5°	821.1	823.2	819.7	814.0	798.9	787.6	770.6	754.1	735.1	716.2	699.4
20°	854.0	855.9	850.6	840.6	822.6	811.3	788.9	767.6	745.7	721.4	702.9
22.5°	895.1	893.6	886.4	871.3	855.7	834.8	810.5	784.6	757.1	729.7	705.1
25°	964.9	955.2	950.8	932.1	911.6	880.8	847.6	809.7	775.5	739.2	707.8
27.5°	1003.7	1000.6	995.7	982.7	961.1	928.2	889.0	842.8	794.6	748.8	707.6
30°	995.9	996.4	996.8	992.7	978.8	954.1	915.0	865.4	808.0	756.5	708.9
32.5°	927.1	935.5	943.6	953.1	957.0	952.2	927.8	882.9	823.9	765.4	708.2
35°	774.5	777.1	803.2	829.1	864.2	891.5	909.7	889.8	840.2	772.9	707.3
37.5°	603.9	616.4	634.5	663.7	714.4	759.8	818.2	845.0	829.0	775.4	705.7
40°	514.8	526.4	538.2	568.0	610.7	665.7	732.0	788.6	801.8	767.6	700.1
42.5°	446.1	455.2	468.3	490.7	526.4	575.1	638.5	712.5	758.0	745.1	688.5
45°	365.1	370.9	381.0	398.8	424.7	462.8	518.7	599.6	670.1	693.4	660.9
47.5°	312.5	312.5	320.4	332.6	351.3	383.7	425.1	488.4	563.7	619.4	616.8
50°	283.3	282.1	288.4	299.0	313.8	335.3	374.8	425.4	497.7	560.8	578.4
52.5°	258.1	258.3	262.1	270.0	282.4	300.7	330.2	375.9	437.6	502.4	535.5
55°	225.1	224.1	228.5	233.8	242.9	254.9	276.1	311.0	361.2	424.9	467.9
57.5°	194.7	197.3	199.0	202.7	210.2	218.3	236.2	261.8	301.6	356.3	401.7
60°	177.0	179.5	180.9	184.6	190.6	197.6	211.4	232.2	265.7	312.9	357.9
62.5°	161.1	163.1	163.6	166.9	171.8	178.5	189.4	206.9	233.4	274.6	318.7
65°	138.2	138.2	139.1	142.6	144.9	150.9	159.2	171.9	193.2	225.3	263.0
67.5°	116.1	117.2	117.0	118.5	120.6	125.3	131.2	141.7	157.5	180.9	211.1
70°	101.7	102.6	102.4	103.5	105.8	108.8	113.7	123.6	134.9	155.0	180.9
72.5°	88.7	89.1	88.5	90.0	91.4	94.0	99.5	104.8	115.3	132.3	153.6
75°	67.9	68.4	68.9	69.8	71.2	72.6	75.3	80.6	87.6	100.3	113.9
77.5°	50.9	50.0	51.2	51.0	51.8	52.9	55.3	58.1	63.8	71.9	82.4
80°	38.4	38.6	38.6	38.8	40.0	40.7	42.7	44.8	49.2	55.2	62.6
82.5°	28.0	28.6	28.2	28.7	29.6	30.1	31.3	33.0	35.5	40.3	45.6
85°	15.3	14.1	14.6	15.0	15.0	15.3	16.2	16.9	18.3	20.1	22.2
87.5°	8.0	8.4	8.4	8.4	8.6	8.3	8.9	8.7	9.1	9.5	10.0
90°	18.0	18.0	17.2	17.2	17.2	15.6	14.9	14.1	13.3	12.5	10.9
92.5°	49.9	51.1	52.2	54.1	64.1	75.7	100.6	138.6	204.1	252.1	256.1
95°	183.7	196.3	202.5	226.0	281.5	347.2	443.3	562.2	677.9	692.8	565.3
97.5°	444.1	454.1	476.8	520.6	568.9	660.2	753.9	837.3	857.7	739.8	504.8
100°	609.9	622.4	651.3	707.6	761.6	842.9	923.4	961.7	901.5	706.1	450.4
102.5°	795.0	804.4	835.8	875.9	933.6	988.6	1027.3	1003.6	875.3	646.6	409.1
105°	1036.0	1045.4	1061.0	1086.8	1111.9	1120.5	1086.1	978.9	791.3	566.9	369.1
107.5°	1163.9	1170.2	1175.3	1175.5	1162.8	1122.0	1033.7	890.7	705.6	512.0	352.2
110°	1206.5	1206.5	1201.0	1186.1	1150.9	1084.5	974.2	825.7	656.8	486.3	347.2



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1201.5	1195.8	1182.2	1156.7	1105.3	1026.9	915.4	774.4	620.5	471.3	347.2
115°	1154.1	1143.9	1122.0	1084.5	1023.5	938.3	831.2	710.0	580.9	455.1	349.5
117.5°	1071.0	1064.8	1043.0	1004.3	943.3	865.1	772.8	668.4	557.3	447.1	354.7
120°	1017.2	1011.0	989.9	952.3	894.5	825.7	739.7	645.8	544.2	443.3	359.7
122.5°	969.7	964.1	943.0	908.6	857.0	792.5	715.9	629.0	532.9	440.2	364.0
125°	909.3	901.5	884.3	852.3	808.5	752.2	684.2	604.4	517.6	436.3	371.4
127.5°	857.7	854.3	838.0	809.7	770.0	717.3	653.8	579.4	503.5	434.4	379.7
130°	829.6	824.9	809.3	783.5	744.4	693.5	632.6	563.7	494.2	433.2	384.7
132.5°	801.4	796.1	781.7	755.9	716.8	667.9	612.5	548.1	486.7	433.2	390.3
135°	755.3	750.6	736.5	710.7	676.3	631.8	581.7	527.8	477.7	433.2	398.0
137.5°	706.1	700.9	687.9	664.5	633.6	595.8	554.2	510.6	469.8	434.1	405.0
140°	671.6	667.7	656.0	635.7	606.7	573.9	537.9	501.2	466.0	434.7	408.1
142.5°	639.7	636.5	625.4	608.2	583.6	555.1	524.2	493.1	462.9	435.4	410.0
145°	595.8	592.7	584.1	570.8	552.0	530.9	506.7	482.4	458.2	434.7	412.1
147.5°	558.6	557.2	552.2	541.5	526.7	510.7	492.1	472.4	453.3	432.7	412.8
150°	537.9	537.2	534.0	524.7	512.9	498.8	484.0	466.8	449.6	430.8	412.8
152.5°	521.7	520.9	517.8	510.3	500.4	489.5	475.9	460.5	445.2	428.3	412.2
155°	499.6	498.8	496.5	491.0	483.2	474.6	463.7	451.2	437.9	423.8	410.5
157.5°	479.9	480.1	477.9	473.4	467.3	460.5	452.1	441.8	431.0	419.1	408.5
160°	466.8	467.6	466.0	462.1	456.6	451.2	443.3	435.5	425.4	416.0	406.6
162.5°	454.9	455.1	454.7	451.5	447.2	442.4	435.8	428.6	420.3	412.2	404.7
165°	437.9	437.9	437.9	436.3	433.2	429.3	424.6	419.1	412.8	406.6	401.9
167.5°	422.2	422.4	423.0	421.6	420.0	417.2	413.6	410.0	405.5	401.1	397.5
170°	412.8	413.6	413.6	412.8	411.3	409.7	407.4	405.0	401.1	398.0	395.6
172.5°	404.1	404.9	406.1	404.7	404.4	403.5	401.7	399.4	396.7	394.2	393.1
175°	393.3	394.1	395.6	394.9	394.9	394.9	393.3	393.3	390.9	390.2	390.2
177.5°	387.8	387.8	389.7	389.1	389.7	389.7	389.7	389.1	388.4	387.8	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	560.1	558.8	557.3	554.7	551.6	549.9	547.4	545.7	542.4	539.6	536.6
5°	588.5	582.5	577.0	569.8	562.0	556.9	550.9	544.2	537.2	530.1	522.2
7.5°	618.0	607.3	595.8	583.4	571.2	560.0	549.3	538.9	529.1	517.2	507.2
10°	637.7	624.3	610.0	593.2	576.7	562.4	547.9	535.2	522.2	508.4	496.1
12.5°	657.5	639.7	619.4	600.9	581.2	563.9	546.8	530.5	514.3	498.9	484.6
15°	671.5	655.8	637.1	610.7	588.5	564.7	542.1	521.1	501.4	484.3	466.3
17.5°	680.7	660.4	640.3	615.1	586.0	559.4	533.7	509.6	487.5	465.8	448.5
20°	682.3	661.5	640.5	615.8	586.0	555.5	529.8	501.0	477.2	454.7	433.5
22.5°	681.8	658.2	635.3	609.9	580.8	552.7	521.7	492.3	466.4	444.4	422.2
25°	676.6	651.4	622.7	597.1	568.4	538.6	507.2	476.7	450.4	425.2	403.2
27.5°	672.2	639.6	607.1	577.2	549.5	522.2	492.1	460.9	431.7	406.2	385.5
30°	666.9	631.0	594.5	563.3	534.9	508.4	479.9	449.4	418.9	394.0	371.8
32.5°	662.1	620.3	581.8	547.8	517.7	491.9	465.7	436.7	406.7	381.4	359.2
35°	652.8	604.5	560.3	522.0	489.9	463.3	441.3	414.3	386.8	362.3	341.1
37.5°	641.0	583.7	536.3	496.1	460.9	432.9	412.5	391.7	365.3	341.7	322.5
40°	631.7	568.9	518.7	477.6	441.1	412.0	393.0	373.4	351.5	329.5	309.2
42.5°	620.1	555.6	501.0	456.7	420.6	392.2	372.3	355.7	336.3	315.8	297.0
45°	598.7	531.5	472.3	424.7	388.2	360.2	339.7	327.2	312.6	293.2	277.3
47.5°	567.2	502.5	441.3	392.2	354.5	328.6	309.3	297.3	287.1	272.7	258.2
50°	539.3	480.9	418.9	370.2	332.5	306.4	288.6	277.7	269.0	257.9	245.6
52.5°	508.1	453.7	396.9	348.7	311.4	285.7	268.3	258.7	251.4	243.5	231.4
55°	458.4	412.2	359.5	313.8	279.4	254.2	238.9	230.6	224.6	218.6	211.2
57.5°	403.8	367.6	321.0	279.1	247.4	224.5	210.3	202.2	197.5	194.4	190.1
60°	365.3	334.4	294.2	256.0	225.1	204.7	190.9	184.6	180.7	178.2	174.9
62.5°	329.6	304.2	267.0	232.2	205.1	185.9	173.5	167.4	163.7	162.4	159.8
65°	277.1	257.4	226.7	197.8	174.7	158.3	147.9	142.1	139.8	138.4	138.6
67.5°	225.2	213.3	188.6	164.0	145.5	131.8	123.4	119.0	117.8	116.0	116.0
70°	193.6	184.6	163.8	142.3	125.9	115.3	107.9	103.3	102.1	101.2	101.0
72.5°	165.7	157.8	139.8	122.6	107.8	98.5	92.4	89.6	87.7	87.2	87.1
75°	124.5	120.2	105.8	92.2	82.0	75.6	71.4	68.9	67.5	67.2	67.5
77.5°	88.5	84.7	75.6	65.9	59.5	54.6	51.1	50.2	48.7	48.7	48.5
80°	66.5	64.0	58.2	50.6	45.3	41.1	39.3	37.7	37.2	36.5	37.2
82.5°	48.2	45.5	41.6	36.7	32.3	29.9	28.0	27.5	27.2	26.9	27.0
85°	23.8	24.0	21.7	18.0	16.2	14.8	13.6	13.6	13.4	13.2	13.4
87.5°	10.2	9.5	8.6	7.7	6.5	5.6	5.1	5.1	4.7	4.9	5.4
90°	10.2	8.6	7.8	6.3	4.7	3.1	1.6	0.8	1.6	3.1	4.7
92.5°	178.4	106.8	64.1	41.3	27.8	18.1	11.6	9.5	11.6	18.1	27.8
95°	349.5	177.5	93.8	58.6	41.4	32.8	26.6	25.8	26.6	32.8	41.4
97.5°	279.0	152.9	97.6	72.2	56.8	48.2	43.8	42.8	43.8	48.2	56.8
100°	253.3	151.7	106.3	82.9	68.0	59.4	56.3	54.7	56.3	59.4	68.0
102.5°	242.7	157.3	117.0	94.1	80.5	71.3	68.8	67.9	68.8	71.3	80.5
105°	238.5	168.9	134.5	112.6	100.1	92.3	88.4	88.4	88.4	92.3	100.1
107.5°	245.7	186.1	152.8	133.1	120.1	113.7	109.9	108.4	109.9	113.7	120.1
110°	252.6	198.6	166.5	146.2	134.5	127.4	124.3	122.8	124.3	127.4	134.5



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.3	210.5	179.7	160.0	148.2	141.2	138.7	137.1	138.7	141.2	148.2
115°	274.4	229.1	200.2	180.6	168.9	161.9	159.5	157.9	159.5	161.9	168.9
117.5°	289.5	248.2	220.8	201.9	188.6	181.6	179.1	176.7	179.1	181.6	188.6
120°	299.5	261.9	234.6	215.0	201.7	194.7	191.6	189.2	191.6	194.7	201.7
122.5°	310.7	275.1	247.7	228.2	213.6	206.6	204.1	202.4	204.1	206.6	213.6
125°	326.0	292.4	266.6	246.3	231.4	224.4	220.5	218.9	220.5	224.4	231.4
127.5°	340.1	309.2	284.3	264.0	248.2	239.3	234.3	231.9	234.3	239.3	248.2
130°	349.5	319.8	295.6	275.2	258.8	248.6	242.4	240.0	242.4	248.6	258.8
132.5°	357.6	329.8	305.6	285.2	268.2	256.8	249.3	246.3	249.3	256.8	268.2
135°	369.1	343.3	319.0	297.9	281.5	269.0	259.6	256.5	259.6	269.0	281.5
137.5°	377.5	352.8	330.7	309.0	292.9	280.4	271.6	269.3	271.6	280.4	292.9
140°	383.1	359.7	337.0	315.9	301.0	288.5	279.1	276.8	279.1	288.5	301.0
142.5°	386.3	364.0	342.6	322.8	308.5	296.0	287.3	285.5	287.3	296.0	308.5
145°	390.9	371.4	351.1	333.1	319.0	308.1	300.2	298.7	300.2	308.1	319.0
147.5°	393.8	376.1	358.3	342.5	330.3	320.1	313.4	312.4	313.4	320.1	330.3
150°	395.6	379.2	362.0	348.7	337.8	327.6	322.1	320.6	322.1	327.6	337.8
152.5°	396.9	382.3	366.4	354.4	344.0	335.1	330.3	329.3	330.3	335.1	344.0
155°	398.0	385.5	372.2	361.2	353.4	345.6	340.9	340.9	340.9	345.6	353.4
157.5°	398.8	388.1	376.7	368.4	361.5	354.8	351.1	351.2	351.1	354.8	361.5
160°	398.8	389.4	379.2	372.2	365.9	360.5	357.3	358.1	357.3	360.5	365.9
162.5°	398.1	390.6	381.7	375.9	370.9	366.1	363.0	363.7	363.0	366.1	370.9
165°	397.2	390.9	384.7	380.0	376.9	373.0	370.6	372.2	370.6	373.0	376.9
167.5°	395.3	390.9	385.8	382.8	380.6	378.4	377.0	377.8	377.0	378.4	380.6
170°	394.1	390.9	387.0	384.7	383.1	381.6	380.8	381.6	380.8	381.6	383.1
172.5°	392.8	390.3	387.0	385.9	385.0	383.4	382.7	384.1	382.7	383.4	385.0
175°	390.9	389.4	387.0	387.0	387.0	386.3	385.5	387.0	385.5	386.3	387.0
177.5°	389.1	388.4	387.2	387.2	387.8	387.2	387.2	388.4	387.2	387.2	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	535.0	532.9	531.3	527.6	525.5	522.8	520.6	523.0	520.4	521.5	519.8
5°	518.3	511.8	507.2	500.5	494.7	489.4	485.5	484.8	482.9	482.0	479.2
7.5°	498.2	490.1	482.2	473.4	466.0	458.5	453.7	449.7	447.1	443.6	441.2
10°	486.4	475.5	466.3	455.7	446.4	438.3	431.9	428.6	425.6	421.2	419.6
12.5°	471.8	460.6	449.3	437.9	429.0	420.0	414.5	409.6	407.5	402.6	402.1
15°	454.3	437.4	426.3	414.8	402.5	395.1	390.5	385.2	382.9	379.4	376.9
17.5°	433.4	418.3	404.5	392.5	382.0	375.8	370.0	366.4	362.4	360.1	356.0
20°	418.2	403.9	390.0	377.3	369.2	362.1	357.5	354.0	349.8	348.7	344.5
22.5°	405.5	389.7	376.4	365.7	356.9	348.8	343.8	341.4	338.6	335.0	334.2
25°	384.7	368.3	357.0	346.4	338.5	331.1	327.7	324.7	321.9	319.3	318.4
27.5°	366.8	352.1	338.7	329.1	322.2	315.5	312.5	308.8	306.8	304.7	302.2
30°	354.2	339.2	327.4	318.2	310.8	304.8	301.5	299.0	297.2	295.3	293.9
32.5°	341.3	327.4	316.0	306.9	299.5	295.0	292.1	290.3	288.3	286.1	284.3
35°	324.2	308.9	297.8	290.0	284.2	280.7	277.5	275.9	273.6	273.6	271.7
37.5°	304.9	291.7	281.9	274.8	269.6	266.5	263.0	261.9	260.4	259.4	258.8
40°	293.5	281.2	272.0	264.8	259.3	256.7	253.9	252.1	251.2	250.0	249.6
42.5°	281.6	269.9	261.1	254.5	249.6	247.5	244.9	243.6	241.7	240.2	239.9
45°	263.6	252.3	244.2	238.9	234.8	232.2	230.6	227.8	226.9	225.1	224.8
47.5°	246.6	235.7	227.8	223.4	219.8	217.7	215.2	212.4	211.3	210.4	210.3
50°	233.8	223.9	216.5	212.4	208.9	205.9	203.3	201.5	200.8	200.8	201.3
52.5°	220.9	212.4	206.2	201.1	197.8	194.6	192.2	191.1	190.1	191.2	192.0
55°	202.0	193.4	188.8	183.9	180.7	177.0	175.8	175.4	174.7	176.5	177.5
57.5°	181.9	175.9	170.5	165.7	162.8	160.6	159.1	158.8	160.1	161.0	164.0
60°	169.1	162.2	157.4	153.7	150.2	148.8	148.3	147.9	148.8	151.3	155.3
62.5°	155.1	149.5	144.2	141.5	138.9	136.6	136.5	136.8	138.6	141.6	145.5
65°	134.5	129.6	126.2	122.9	120.8	119.5	119.9	120.8	122.9	126.9	131.2
67.5°	113.5	110.2	107.1	104.5	102.5	102.5	103.0	104.4	106.8	111.3	115.3
70°	100.1	96.4	93.8	92.7	91.0	90.1	91.5	93.8	95.9	100.1	103.5
72.5°	86.6	83.4	81.4	80.6	79.9	79.2	79.7	82.2	85.0	89.1	93.2
75°	66.5	65.4	64.0	63.1	62.4	62.9	63.3	65.6	67.9	72.3	76.9
77.5°	48.6	47.4	46.5	46.3	45.9	46.2	47.5	49.2	51.4	54.6	58.1
80°	36.7	36.3	35.8	35.6	35.6	35.8	37.7	38.8	40.9	43.9	46.7
82.5°	26.8	26.5	26.4	26.3	26.5	26.6	27.7	29.2	30.9	33.2	35.6
85°	14.1	13.6	14.3	14.6	14.1	14.8	15.3	16.2	16.9	18.0	19.2
87.5°	5.9	6.6	6.5	7.0	7.2	7.9	7.8	8.7	9.3	9.8	9.9
90°	6.3	7.8	8.6	10.2	10.9	12.5	13.3	14.1	14.9	15.6	17.2
92.5°	41.3	64.1	106.8	178.4	256.1	252.1	204.1	138.6	100.6	75.7	64.1
95°	58.6	93.8	177.5	349.5	565.3	692.8	677.9	562.2	443.3	347.2	281.5
97.5°	72.2	97.6	152.9	279.0	504.8	739.8	857.7	837.3	753.9	660.2	568.9
100°	82.9	106.3	151.7	253.3	450.4	706.1	901.5	961.7	923.4	842.9	761.6
102.5°	94.1	117.0	157.3	242.7	409.1	646.6	875.3	1003.6	1027.3	988.6	933.6
105°	112.6	134.5	168.9	238.5	369.1	566.9	791.3	978.9	1086.1	1120.5	1111.9
107.5°	133.1	152.8	186.1	245.7	352.2	512.0	705.6	890.7	1033.7	1122.0	1162.8
110°	146.2	166.5	198.6	252.6	347.2	486.3	656.8	825.7	974.2	1084.5	1150.9



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	160.0	179.7	210.5	261.3	347.2	471.3	620.5	774.4	915.4	1026.9	1105.3
115°	180.6	200.2	229.1	274.4	349.5	455.1	580.9	710.0	831.2	938.3	1023.5
117.5°	201.9	220.8	248.2	289.5	354.7	447.1	557.3	668.4	772.8	865.1	943.3
120°	215.0	234.6	261.9	299.5	359.7	443.3	544.2	645.8	739.7	825.7	894.5
122.5°	228.2	247.7	275.1	310.7	364.0	440.2	532.9	629.0	715.9	792.5	857.0
125°	246.3	266.6	292.4	326.0	371.4	436.3	517.6	604.4	684.2	752.2	808.5
127.5°	264.0	284.3	309.2	340.1	379.7	434.4	503.5	579.4	653.8	717.3	770.0
130°	275.2	295.6	319.8	349.5	384.7	433.2	494.2	563.7	632.6	693.5	744.4
132.5°	285.2	305.6	329.8	357.6	390.3	433.2	486.7	548.1	612.5	667.9	716.8
135°	297.9	319.0	343.3	369.1	398.0	433.2	477.7	527.8	581.7	631.8	676.3
137.5°	309.0	330.7	352.8	377.5	405.0	434.1	469.8	510.6	554.2	595.8	633.6
140°	315.9	337.0	359.7	383.1	408.1	434.7	466.0	501.2	537.9	573.9	606.7
142.5°	322.8	342.6	364.0	386.3	410.0	435.4	462.9	493.1	524.2	555.1	583.6
145°	333.1	351.1	371.4	390.9	412.1	434.7	458.2	482.4	506.7	530.9	552.0
147.5°	342.5	358.3	376.1	393.8	412.8	432.7	453.3	472.4	492.1	510.7	526.7
150°	348.7	362.0	379.2	395.6	412.8	430.8	449.6	466.8	484.0	498.8	512.9
152.5°	354.4	366.4	382.3	396.9	412.2	428.3	445.2	460.5	475.9	489.5	500.4
155°	361.2	372.2	385.5	398.0	410.5	423.8	437.9	451.2	463.7	474.6	483.2
157.5°	368.4	376.7	388.1	398.8	408.5	419.1	431.0	441.8	452.1	460.5	467.3
160°	372.2	379.2	389.4	398.8	406.6	416.0	425.4	435.5	443.3	451.2	456.6
162.5°	375.9	381.7	390.6	398.1	404.7	412.2	420.3	428.6	435.8	442.4	447.2
165°	380.0	384.7	390.9	397.2	401.9	406.6	412.8	419.1	424.6	429.3	433.2
167.5°	382.8	385.8	390.9	395.3	397.5	401.1	405.5	410.0	413.6	417.2	420.0
170°	384.7	387.0	390.9	394.1	395.6	398.0	401.1	405.0	407.4	409.7	411.3
172.5°	385.9	387.0	390.3	392.8	393.1	394.2	396.7	399.4	401.7	403.5	404.4
175°	387.0	387.0	389.4	390.9	390.2	390.2	390.9	393.3	393.3	394.9	394.9
177.5°	387.2	387.2	388.4	389.1	387.8	387.8	388.4	389.1	389.7	389.7	389.7
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	518.7	520.0	518.9	520.4	518.9	520.0	518.7	519.8	521.5	520.4	523.0
5°	478.1	476.0	477.4	476.5	477.4	476.0	478.1	479.2	482.0	482.9	484.8
7.5°	440.6	438.6	436.3	435.2	436.3	438.6	440.6	441.2	443.6	447.1	449.7
10°	417.1	414.5	414.3	412.7	414.3	414.5	417.1	419.6	421.2	425.6	428.6
12.5°	399.9	397.5	394.9	394.2	394.9	397.5	399.9	402.1	402.6	407.5	409.6
15°	375.5	373.6	372.0	373.4	372.0	373.6	375.5	376.9	379.4	382.9	385.2
17.5°	355.2	353.7	353.4	351.7	353.4	353.7	355.2	356.0	360.1	362.4	366.4
20°	342.4	341.3	341.8	338.7	341.8	341.3	342.4	344.5	348.7	349.8	354.0
22.5°	332.3	330.0	329.7	329.1	329.7	330.0	332.3	334.2	335.0	338.6	341.4
25°	316.3	315.2	314.0	315.2	314.0	315.2	316.3	318.4	319.3	321.9	324.7
27.5°	302.4	301.0	300.7	300.9	300.7	301.0	302.4	302.2	304.7	306.8	308.8
30°	293.9	291.6	291.8	291.6	291.8	291.6	293.9	293.9	295.3	297.2	299.0
32.5°	284.7	283.1	282.8	282.4	282.8	283.1	284.7	284.3	286.1	288.3	290.3
35°	271.0	271.0	269.9	269.9	269.9	271.0	271.0	271.7	273.6	273.6	275.9
37.5°	258.2	258.0	257.3	257.4	257.3	258.0	258.2	258.8	259.4	260.4	261.9
40°	248.6	248.4	247.7	246.3	247.7	248.4	248.6	249.6	250.0	251.2	252.1
42.5°	239.4	238.6	238.3	237.8	238.3	238.6	239.4	239.9	240.2	241.7	243.6
45°	224.8	224.8	224.4	224.1	224.4	224.8	224.8	224.8	225.1	226.9	227.8
47.5°	210.7	211.1	212.0	211.8	212.0	211.1	210.7	210.3	210.4	211.3	212.4
50°	202.2	202.4	203.1	203.3	203.1	202.4	202.2	201.3	200.8	200.8	201.5
52.5°	192.8	194.1	195.0	194.8	195.0	194.1	192.8	192.0	191.2	190.1	191.1
55°	179.5	181.2	182.8	183.0	182.8	181.2	179.5	177.5	176.5	174.7	175.4
57.5°	166.5	168.7	170.4	171.0	170.4	168.7	166.5	164.0	161.0	160.1	158.8
60°	157.6	160.6	162.7	163.6	162.7	160.6	157.6	155.3	151.3	148.8	147.9
62.5°	149.1	152.5	154.5	154.7	154.5	152.5	149.1	145.5	141.6	138.6	136.8
65°	135.2	138.6	140.5	141.9	140.5	138.6	135.2	131.2	126.9	122.9	120.8
67.5°	120.2	123.7	125.7	126.8	125.7	123.7	120.2	115.3	111.3	106.8	104.4
70°	109.3	112.8	115.5	116.5	115.5	112.8	109.3	103.5	100.1	95.9	93.8
72.5°	98.6	101.7	103.9	105.0	103.9	101.7	98.6	93.2	89.1	85.0	82.2
75°	79.9	84.1	86.2	87.3	86.2	84.1	79.9	76.9	72.3	67.9	65.6
77.5°	61.6	65.4	66.7	67.3	66.7	65.4	61.6	58.1	54.6	51.4	49.2
80°	49.4	51.8	53.4	53.6	53.4	51.8	49.4	46.7	43.9	40.9	38.8
82.5°	38.0	39.9	40.4	41.0	40.4	39.9	38.0	35.6	33.2	30.9	29.2
85°	20.8	21.7	22.0	21.7	22.0	21.7	20.8	19.2	18.0	16.9	16.2
87.5°	10.3	10.1	10.3	10.6	10.3	10.1	10.3	9.9	9.8	9.3	8.7
90°	17.2	17.2	18.0	18.0	18.0	17.2	17.2	17.2	15.6	14.9	14.1
92.5°	54.1	52.2	51.1	49.9	51.1	52.2	54.1	64.1	75.7	100.6	138.6
95°	226.0	202.5	196.3	183.7	196.3	202.5	226.0	281.5	347.2	443.3	562.2
97.5°	520.6	476.8	454.1	444.1	454.1	476.8	520.6	568.9	660.2	753.9	837.3
100°	707.6	651.3	622.4	609.9	622.4	651.3	707.6	761.6	842.9	923.4	961.7
102.5°	875.9	835.8	804.4	795.0	804.4	835.8	875.9	933.6	988.6	1027.3	1003.6
105°	1086.8	1061.0	1045.4	1036.0	1045.4	1061.0	1086.8	1111.9	1120.5	1086.1	978.9
107.5°	1175.5	1175.3	1170.2	1163.9	1170.2	1175.3	1175.5	1162.8	1122.0	1033.7	890.7
110°	1186.1	1201.0	1206.5	1206.5	1206.5	1201.0	1186.1	1150.9	1084.5	974.2	825.7



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1156.7	1182.2	1195.8	1201.5	1195.8	1182.2	1156.7	1105.3	1026.9	915.4	774.4
115°	1084.5	1122.0	1143.9	1154.1	1143.9	1122.0	1084.5	1023.5	938.3	831.2	710.0
117.5°	1004.3	1043.0	1064.8	1071.0	1064.8	1043.0	1004.3	943.3	865.1	772.8	668.4
120°	952.3	989.9	1011.0	1017.2	1011.0	989.9	952.3	894.5	825.7	739.7	645.8
122.5°	908.6	943.0	964.1	969.7	964.1	943.0	908.6	857.0	792.5	715.9	629.0
125°	852.3	884.3	901.5	909.3	901.5	884.3	852.3	808.5	752.2	684.2	604.4
127.5°	809.7	838.0	854.3	857.7	854.3	838.0	809.7	770.0	717.3	653.8	579.4
130°	783.5	809.3	824.9	829.6	824.9	809.3	783.5	744.4	693.5	632.6	563.7
132.5°	755.9	781.7	796.1	801.4	796.1	781.7	755.9	716.8	667.9	612.5	548.1
135°	710.7	736.5	750.6	755.3	750.6	736.5	710.7	676.3	631.8	581.7	527.8
137.5°	664.5	687.9	700.9	706.1	700.9	687.9	664.5	633.6	595.8	554.2	510.6
140°	635.7	656.0	667.7	671.6	667.7	656.0	635.7	606.7	573.9	537.9	501.2
142.5°	608.2	625.4	636.5	639.7	636.5	625.4	608.2	583.6	555.1	524.2	493.1
145°	570.8	584.1	592.7	595.8	592.7	584.1	570.8	552.0	530.9	506.7	482.4
147.5°	541.5	552.2	557.2	558.6	557.2	552.2	541.5	526.7	510.7	492.1	472.4
150°	524.7	534.0	537.2	537.9	537.2	534.0	524.7	512.9	498.8	484.0	466.8
152.5°	510.3	517.8	520.9	521.7	520.9	517.8	510.3	500.4	489.5	475.9	460.5
155°	491.0	496.5	498.8	499.6	498.8	496.5	491.0	483.2	474.6	463.7	451.2
157.5°	473.4	477.9	480.1	479.9	480.1	477.9	473.4	467.3	460.5	452.1	441.8
160°	462.1	466.0	467.6	466.8	467.6	466.0	462.1	456.6	451.2	443.3	435.5
162.5°	451.5	454.7	455.1	454.9	455.1	454.7	451.5	447.2	442.4	435.8	428.6
165°	436.3	437.9	437.9	437.9	437.9	437.9	436.3	433.2	429.3	424.6	419.1
167.5°	421.6	423.0	422.4	422.2	422.4	423.0	421.6	420.0	417.2	413.6	410.0
170°	412.8	413.6	413.6	412.8	413.6	413.6	412.8	411.3	409.7	407.4	405.0
172.5°	404.7	406.1	404.9	404.1	404.9	406.1	404.7	404.4	403.5	401.7	399.4
175°	394.9	395.6	394.1	393.3	394.1	395.6	394.9	394.9	394.9	393.3	393.3
177.5°	389.1	389.7	387.8	387.8	387.8	389.7	389.1	389.7	389.7	389.7	389.1
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	520.6	522.8	525.5	527.6	531.3	532.9	535.0	536.6	539.6	542.4	545.7
5°	485.5	489.4	494.7	500.5	507.2	511.8	518.3	522.2	530.1	537.2	544.2
7.5°	453.7	458.5	466.0	473.4	482.2	490.1	498.2	507.2	517.2	529.1	538.9
10°	431.9	438.3	446.4	455.7	466.3	475.5	486.4	496.1	508.4	522.2	535.2
12.5°	414.5	420.0	429.0	437.9	449.3	460.6	471.8	484.6	498.9	514.3	530.5
15°	390.5	395.1	402.5	414.8	426.3	437.4	454.3	466.3	484.3	501.4	521.1
17.5°	370.0	375.8	382.0	392.5	404.5	418.3	433.4	448.5	465.8	487.5	509.6
20°	357.5	362.1	369.2	377.3	390.0	403.9	418.2	433.5	454.7	477.2	501.0
22.5°	343.8	348.8	356.9	365.7	376.4	389.7	405.5	422.2	444.4	466.4	492.3
25°	327.7	331.1	338.5	346.4	357.0	368.3	384.7	403.2	425.2	450.4	476.7
27.5°	312.5	315.5	322.2	329.1	338.7	352.1	366.8	385.5	406.2	431.7	460.9
30°	301.5	304.8	310.8	318.2	327.4	339.2	354.2	371.8	394.0	418.9	449.4
32.5°	292.1	295.0	299.5	306.9	316.0	327.4	341.3	359.2	381.4	406.7	436.7
35°	277.5	280.7	284.2	290.0	297.8	308.9	324.2	341.1	362.3	386.8	414.3
37.5°	263.0	266.5	269.6	274.8	281.9	291.7	304.9	322.5	341.7	365.3	391.7
40°	253.9	256.7	259.3	264.8	272.0	281.2	293.5	309.2	329.5	351.5	373.4
42.5°	244.9	247.5	249.6	254.5	261.1	269.9	281.6	297.0	315.8	336.3	355.7
45°	230.6	232.2	234.8	238.9	244.2	252.3	263.6	277.3	293.2	312.6	327.2
47.5°	215.2	217.7	219.8	223.4	227.8	235.7	246.6	258.2	272.7	287.1	297.3
50°	203.3	205.9	208.9	212.4	216.5	223.9	233.8	245.6	257.9	269.0	277.7
52.5°	192.2	194.6	197.8	201.1	206.2	212.4	220.9	231.4	243.5	251.4	258.7
55°	175.8	177.0	180.7	183.9	188.8	193.4	202.0	211.2	218.6	224.6	230.6
57.5°	159.1	160.6	162.8	165.7	170.5	175.9	181.9	190.1	194.4	197.5	202.2
60°	148.3	148.8	150.2	153.7	157.4	162.2	169.1	174.9	178.2	180.7	184.6
62.5°	136.5	136.6	138.9	141.5	144.2	149.5	155.1	159.8	162.4	163.7	167.4
65°	119.9	119.5	120.8	122.9	126.2	129.6	134.5	138.6	138.4	139.8	142.1
67.5°	103.0	102.5	102.5	104.5	107.1	110.2	113.5	116.0	116.0	117.8	119.0
70°	91.5	90.1	91.0	92.7	93.8	96.4	100.1	101.0	101.2	102.1	103.3
72.5°	79.7	79.2	79.9	80.6	81.4	83.4	86.6	87.1	87.2	87.7	89.6
75°	63.3	62.9	62.4	63.1	64.0	65.4	66.5	67.5	67.2	67.5	68.9
77.5°	47.5	46.2	45.9	46.3	46.5	47.4	48.6	48.5	48.7	48.7	50.2
80°	37.7	35.8	35.6	35.6	35.8	36.3	36.7	37.2	36.5	37.2	37.7
82.5°	27.7	26.6	26.5	26.3	26.4	26.5	26.8	27.0	26.9	27.2	27.5
85°	15.3	14.8	14.1	14.6	14.3	13.6	14.1	13.4	13.2	13.4	13.6
87.5°	7.8	7.9	7.2	7.0	6.5	6.6	5.9	5.4	4.9	4.7	5.1
90°	13.3	12.5	10.9	10.2	8.6	7.8	6.3	4.7	3.1	1.6	0.8
92.5°	204.1	252.1	256.1	178.4	106.8	64.1	41.3	27.8	18.1	11.6	9.5
95°	677.9	692.8	565.3	349.5	177.5	93.8	58.6	41.4	32.8	26.6	25.8
97.5°	857.7	739.8	504.8	279.0	152.9	97.6	72.2	56.8	48.2	43.8	42.8
100°	901.5	706.1	450.4	253.3	151.7	106.3	82.9	68.0	59.4	56.3	54.7
102.5°	875.3	646.6	409.1	242.7	157.3	117.0	94.1	80.5	71.3	68.8	67.9
105°	791.3	566.9	369.1	238.5	168.9	134.5	112.6	100.1	92.3	88.4	88.4
107.5°	705.6	512.0	352.2	245.7	186.1	152.8	133.1	120.1	113.7	109.9	108.4
110°	656.8	486.3	347.2	252.6	198.6	166.5	146.2	134.5	127.4	124.3	122.8



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	620.5	471.3	347.2	261.3	210.5	179.7	160.0	148.2	141.2	138.7	137.1
115°	580.9	455.1	349.5	274.4	229.1	200.2	180.6	168.9	161.9	159.5	157.9
117.5°	557.3	447.1	354.7	289.5	248.2	220.8	201.9	188.6	181.6	179.1	176.7
120°	544.2	443.3	359.7	299.5	261.9	234.6	215.0	201.7	194.7	191.6	189.2
122.5°	532.9	440.2	364.0	310.7	275.1	247.7	228.2	213.6	206.6	204.1	202.4
125°	517.6	436.3	371.4	326.0	292.4	266.6	246.3	231.4	224.4	220.5	218.9
127.5°	503.5	434.4	379.7	340.1	309.2	284.3	264.0	248.2	239.3	234.3	231.9
130°	494.2	433.2	384.7	349.5	319.8	295.6	275.2	258.8	248.6	242.4	240.0
132.5°	486.7	433.2	390.3	357.6	329.8	305.6	285.2	268.2	256.8	249.3	246.3
135°	477.7	433.2	398.0	369.1	343.3	319.0	297.9	281.5	269.0	259.6	256.5
137.5°	469.8	434.1	405.0	377.5	352.8	330.7	309.0	292.9	280.4	271.6	269.3
140°	466.0	434.7	408.1	383.1	359.7	337.0	315.9	301.0	288.5	279.1	276.8
142.5°	462.9	435.4	410.0	386.3	364.0	342.6	322.8	308.5	296.0	287.3	285.5
145°	458.2	434.7	412.1	390.9	371.4	351.1	333.1	319.0	308.1	300.2	298.7
147.5°	453.3	432.7	412.8	393.8	376.1	358.3	342.5	330.3	320.1	313.4	312.4
150°	449.6	430.8	412.8	395.6	379.2	362.0	348.7	337.8	327.6	322.1	320.6
152.5°	445.2	428.3	412.2	396.9	382.3	366.4	354.4	344.0	335.1	330.3	329.3
155°	437.9	423.8	410.5	398.0	385.5	372.2	361.2	353.4	345.6	340.9	340.9
157.5°	431.0	419.1	408.5	398.8	388.1	376.7	368.4	361.5	354.8	351.1	351.2
160°	425.4	416.0	406.6	398.8	389.4	379.2	372.2	365.9	360.5	357.3	358.1
162.5°	420.3	412.2	404.7	398.1	390.6	381.7	375.9	370.9	366.1	363.0	363.7
165°	412.8	406.6	401.9	397.2	390.9	384.7	380.0	376.9	373.0	370.6	372.2
167.5°	405.5	401.1	397.5	395.3	390.9	385.8	382.8	380.6	378.4	377.0	377.8
170°	401.1	398.0	395.6	394.1	390.9	387.0	384.7	383.1	381.6	380.8	381.6
172.5°	396.7	394.2	393.1	392.8	390.3	387.0	385.9	385.0	383.4	382.7	384.1
175°	390.9	390.2	390.2	390.9	389.4	387.0	387.0	387.0	386.3	385.5	387.0
177.5°	388.4	387.8	387.8	389.1	388.4	387.2	387.2	387.8	387.2	387.2	388.4
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	547.4	549.9	551.6	554.7	557.3	558.8	560.1	561.2	562.5	563.6	566.8
5°	550.9	556.9	562.0	569.8	577.0	582.5	588.5	593.8	598.2	604.5	609.3
7.5°	549.3	560.0	571.2	583.4	595.8	607.3	618.0	627.9	636.9	647.8	657.4
10°	547.9	562.4	576.7	593.2	610.0	624.3	637.7	651.4	661.3	675.2	687.0
12.5°	546.8	563.9	581.2	600.9	619.4	639.7	657.5	667.5	682.6	693.7	707.7
15°	542.1	564.7	588.5	610.7	637.1	655.8	671.5	690.9	705.0	719.1	734.3
17.5°	533.7	559.4	586.0	615.1	640.3	660.4	680.7	699.4	716.2	735.1	754.1
20°	529.8	555.5	586.0	615.8	640.5	661.5	682.3	702.9	721.4	745.7	767.6
22.5°	521.7	552.7	580.8	609.9	635.3	658.2	681.8	705.1	729.7	757.1	784.6
25°	507.2	538.6	568.4	597.1	622.7	651.4	676.6	707.8	739.2	775.5	809.7
27.5°	492.1	522.2	549.5	577.2	607.1	639.6	672.2	707.6	748.8	794.6	842.8
30°	479.9	508.4	534.9	563.3	594.5	631.0	666.9	708.9	756.5	808.0	865.4
32.5°	465.7	491.9	517.7	547.8	581.8	620.3	662.1	708.2	765.4	823.9	882.9
35°	441.3	463.3	489.9	522.0	560.3	604.5	652.8	707.3	772.9	840.2	889.8
37.5°	412.5	432.9	460.9	496.1	536.3	583.7	641.0	705.7	775.4	829.0	845.0
40°	393.0	412.0	441.1	477.6	518.7	568.9	631.7	700.1	767.6	801.8	788.6
42.5°	372.3	392.2	420.6	456.7	501.0	555.6	620.1	688.5	745.1	758.0	712.5
45°	339.7	360.2	388.2	424.7	472.3	531.5	598.7	660.9	693.4	670.1	599.6
47.5°	309.3	328.6	354.5	392.2	441.3	502.5	567.2	616.8	619.4	563.7	488.4
50°	288.6	306.4	332.5	370.2	418.9	480.9	539.3	578.4	560.8	497.7	425.4
52.5°	268.3	285.7	311.4	348.7	396.9	453.7	508.1	535.5	502.4	437.6	375.9
55°	238.9	254.2	279.4	313.8	359.5	412.2	458.4	467.9	424.9	361.2	311.0
57.5°	210.3	224.5	247.4	279.1	321.0	367.6	403.8	401.7	356.3	301.6	261.8
60°	190.9	204.7	225.1	256.0	294.2	334.4	365.3	357.9	312.9	265.7	232.2
62.5°	173.5	185.9	205.1	232.2	267.0	304.2	329.6	318.7	274.6	233.4	206.9
65°	147.9	158.3	174.7	197.8	226.7	257.4	277.1	263.0	225.3	193.2	171.9
67.5°	123.4	131.8	145.5	164.0	188.6	213.3	225.2	211.1	180.9	157.5	141.7
70°	107.9	115.3	125.9	142.3	163.8	184.6	193.6	180.9	155.0	134.9	123.6
72.5°	92.4	98.5	107.8	122.6	139.8	157.8	165.7	153.6	132.3	115.3	104.8
75°	71.4	75.6	82.0	92.2	105.8	120.2	124.5	113.9	100.3	87.6	80.6
77.5°	51.1	54.6	59.5	65.9	75.6	84.7	88.5	82.4	71.9	63.8	58.1
80°	39.3	41.1	45.3	50.6	58.2	64.0	66.5	62.6	55.2	49.2	44.8
82.5°	28.0	29.9	32.3	36.7	41.6	45.5	48.2	45.6	40.3	35.5	33.0
85°	13.6	14.8	16.2	18.0	21.7	24.0	23.8	22.2	20.1	18.3	16.9
87.5°	5.1	5.6	6.5	7.7	8.6	9.5	10.2	10.0	9.5	9.1	8.7
90°	1.6	3.1	4.7	6.3	7.8	8.6	10.2	10.9	12.5	13.3	14.1
92.5°	11.6	18.1	27.8	41.3	64.1	106.8	178.4	256.1	252.1	204.1	138.6
95°	26.6	32.8	41.4	58.6	93.8	177.5	349.5	565.3	692.8	677.9	562.2
97.5°	43.8	48.2	56.8	72.2	97.6	152.9	279.0	504.8	739.8	857.7	837.3
100°	56.3	59.4	68.0	82.9	106.3	151.7	253.3	450.4	706.1	901.5	961.7
102.5°	68.8	71.3	80.5	94.1	117.0	157.3	242.7	409.1	646.6	875.3	1003.6
105°	88.4	92.3	100.1	112.6	134.5	168.9	238.5	369.1	566.9	791.3	978.9
107.5°	109.9	113.7	120.1	133.1	152.8	186.1	245.7	352.2	512.0	705.6	890.7
110°	124.3	127.4	134.5	146.2	166.5	198.6	252.6	347.2	486.3	656.8	825.7



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	138.7	141.2	148.2	160.0	179.7	210.5	261.3	347.2	471.3	620.5	774.4
115°	159.5	161.9	168.9	180.6	200.2	229.1	274.4	349.5	455.1	580.9	710.0
117.5°	179.1	181.6	188.6	201.9	220.8	248.2	289.5	354.7	447.1	557.3	668.4
120°	191.6	194.7	201.7	215.0	234.6	261.9	299.5	359.7	443.3	544.2	645.8
122.5°	204.1	206.6	213.6	228.2	247.7	275.1	310.7	364.0	440.2	532.9	629.0
125°	220.5	224.4	231.4	246.3	266.6	292.4	326.0	371.4	436.3	517.6	604.4
127.5°	234.3	239.3	248.2	264.0	284.3	309.2	340.1	379.7	434.4	503.5	579.4
130°	242.4	248.6	258.8	275.2	295.6	319.8	349.5	384.7	433.2	494.2	563.7
132.5°	249.3	256.8	268.2	285.2	305.6	329.8	357.6	390.3	433.2	486.7	548.1
135°	259.6	269.0	281.5	297.9	319.0	343.3	369.1	398.0	433.2	477.7	527.8
137.5°	271.6	280.4	292.9	309.0	330.7	352.8	377.5	405.0	434.1	469.8	510.6
140°	279.1	288.5	301.0	315.9	337.0	359.7	383.1	408.1	434.7	466.0	501.2
142.5°	287.3	296.0	308.5	322.8	342.6	364.0	386.3	410.0	435.4	462.9	493.1
145°	300.2	308.1	319.0	333.1	351.1	371.4	390.9	412.1	434.7	458.2	482.4
147.5°	313.4	320.1	330.3	342.5	358.3	376.1	393.8	412.8	432.7	453.3	472.4
150°	322.1	327.6	337.8	348.7	362.0	379.2	395.6	412.8	430.8	449.6	466.8
152.5°	330.3	335.1	344.0	354.4	366.4	382.3	396.9	412.2	428.3	445.2	460.5
155°	340.9	345.6	353.4	361.2	372.2	385.5	398.0	410.5	423.8	437.9	451.2
157.5°	351.1	354.8	361.5	368.4	376.7	388.1	398.8	408.5	419.1	431.0	441.8
160°	357.3	360.5	365.9	372.2	379.2	389.4	398.8	406.6	416.0	425.4	435.5
162.5°	363.0	366.1	370.9	375.9	381.7	390.6	398.1	404.7	412.2	420.3	428.6
165°	370.6	373.0	376.9	380.0	384.7	390.9	397.2	401.9	406.6	412.8	419.1
167.5°	377.0	378.4	380.6	382.8	385.8	390.9	395.3	397.5	401.1	405.5	410.0
170°	380.8	381.6	383.1	384.7	387.0	390.9	394.1	395.6	398.0	401.1	405.0
172.5°	382.7	383.4	385.0	385.9	387.0	390.3	392.8	393.1	394.2	396.7	399.4
175°	385.5	386.3	387.0	387.0	387.0	389.4	390.9	390.2	390.2	390.9	393.3
177.5°	387.2	387.2	387.8	387.2	387.2	388.4	389.1	387.8	387.8	388.4	389.1
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	569.4	570.8	574.0	572.9	574.3	575.1	575.8
5°	615.3	622.7	626.0	625.5	630.4	629.2	628.0
7.5°	667.3	675.0	679.4	684.8	687.9	688.2	690.9
10°	696.7	706.8	711.0	716.8	720.5	722.6	722.3
12.5°	719.2	727.2	736.5	739.3	744.3	747.0	746.0
15°	746.4	759.1	768.8	773.6	779.9	781.7	784.2
17.5°	770.6	787.6	798.9	814.0	819.7	823.2	821.1
20°	788.9	811.3	822.6	840.6	850.6	855.9	854.0
22.5°	810.5	834.8	855.7	871.3	886.4	893.6	895.1
25°	847.6	880.8	911.6	932.1	950.8	955.2	964.9
27.5°	889.0	928.2	961.1	982.7	995.7	1000.6	1003.7
30°	915.0	954.1	978.8	992.7	996.8	996.4	995.9
32.5°	927.8	952.2	957.0	953.1	943.6	935.5	927.1
35°	909.7	891.5	864.2	829.1	803.2	777.1	774.5
37.5°	818.2	759.8	714.4	663.7	634.5	616.4	603.9
40°	732.0	665.7	610.7	568.0	538.2	526.4	514.8
42.5°	638.5	575.1	526.4	490.7	468.3	455.2	446.1
45°	518.7	462.8	424.7	398.8	381.0	370.9	365.1
47.5°	425.1	383.7	351.3	332.6	320.4	312.5	312.5
50°	374.8	335.3	313.8	299.0	288.4	282.1	283.3
52.5°	330.2	300.7	282.4	270.0	262.1	258.3	258.1
55°	276.1	254.9	242.9	233.8	228.5	224.1	225.1
57.5°	236.2	218.3	210.2	202.7	199.0	197.3	194.7
60°	211.4	197.6	190.6	184.6	180.9	179.5	177.0
62.5°	189.4	178.5	171.8	166.9	163.6	163.1	161.1
65°	159.2	150.9	144.9	142.6	139.1	138.2	138.2
67.5°	131.2	125.3	120.6	118.5	117.0	117.2	116.1
70°	113.7	108.8	105.8	103.5	102.4	102.6	101.7
72.5°	99.5	94.0	91.4	90.0	88.5	89.1	88.7
75°	75.3	72.6	71.2	69.8	68.9	68.4	67.9
77.5°	55.3	52.9	51.8	51.0	51.2	50.0	50.9
80°	42.7	40.7	40.0	38.8	38.6	38.6	38.4
82.5°	31.3	30.1	29.6	28.7	28.2	28.6	28.0
85°	16.2	15.3	15.0	15.0	14.6	14.1	15.3
87.5°	8.9	8.3	8.6	8.4	8.4	8.4	8.0
90°	14.9	15.6	17.2	17.2	17.2	18.0	18.0
92.5°	100.6	75.7	64.1	54.1	52.2	51.1	49.9
95°	443.3	347.2	281.5	226.0	202.5	196.3	183.7
97.5°	753.9	660.2	568.9	520.6	476.8	454.1	444.1
100°	923.4	842.9	761.6	707.6	651.3	622.4	609.9
102.5°	1027.3	988.6	933.6	875.9	835.8	804.4	795.0
105°	1086.1	1120.5	1111.9	1086.8	1061.0	1045.4	1036.0
107.5°	1033.7	1122.0	1162.8	1175.5	1175.3	1170.2	1163.9
110°	974.2	1084.5	1150.9	1186.1	1201.0	1206.5	1206.5



TEST NUMBER: P333135

CATALOG NUMBER: S125DIP-S375D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	915.4	1026.9	1105.3	1156.7	1182.2	1195.8	1201.5
115°	831.2	938.3	1023.5	1084.5	1122.0	1143.9	1154.1
117.5°	772.8	865.1	943.3	1004.3	1043.0	1064.8	1071.0
120°	739.7	825.7	894.5	952.3	989.9	1011.0	1017.2
122.5°	715.9	792.5	857.0	908.6	943.0	964.1	969.7
125°	684.2	752.2	808.5	852.3	884.3	901.5	909.3
127.5°	653.8	717.3	770.0	809.7	838.0	854.3	857.7
130°	632.6	693.5	744.4	783.5	809.3	824.9	829.6
132.5°	612.5	667.9	716.8	755.9	781.7	796.1	801.4
135°	581.7	631.8	676.3	710.7	736.5	750.6	755.3
137.5°	554.2	595.8	633.6	664.5	687.9	700.9	706.1
140°	537.9	573.9	606.7	635.7	656.0	667.7	671.6
142.5°	524.2	555.1	583.6	608.2	625.4	636.5	639.7
145°	506.7	530.9	552.0	570.8	584.1	592.7	595.8
147.5°	492.1	510.7	526.7	541.5	552.2	557.2	558.6
150°	484.0	498.8	512.9	524.7	534.0	537.2	537.9
152.5°	475.9	489.5	500.4	510.3	517.8	520.9	521.7
155°	463.7	474.6	483.2	491.0	496.5	498.8	499.6
157.5°	452.1	460.5	467.3	473.4	477.9	480.1	479.9
160°	443.3	451.2	456.6	462.1	466.0	467.6	466.8
162.5°	435.8	442.4	447.2	451.5	454.7	455.1	454.9
165°	424.6	429.3	433.2	436.3	437.9	437.9	437.9
167.5°	413.6	417.2	420.0	421.6	423.0	422.4	422.2
170°	407.4	409.7	411.3	412.8	413.6	413.6	412.8
172.5°	401.7	403.5	404.4	404.7	406.1	404.9	404.1
175°	393.3	394.9	394.9	394.9	395.6	394.1	393.3
177.5°	389.7	389.7	389.7	389.1	389.7	387.8	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8

(END OF REPORT)