

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333162

Luminaire Tested: **S125DIP-S610D365U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333162
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D365U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3841.0 lumens
Efficiency: N/A
Efficacy: 139.7 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	62	60	56
2	93	85	79	74	87	81	75	70	72	67	64	63	60	57	56	53	51	47
3	85	75	68	62	80	71	65	59	63	58	54	56	52	49	50	46	44	40
4	78	67	59	53	73	63	56	50	57	51	46	50	46	42	44	41	38	35
5	71	60	51	45	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	45	40	62	51	43	38	46	40	35	41	36	32	36	32	29	27
7	61	49	40	35	57	46	39	34	42	35	31	37	32	29	33	29	26	24
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	31	26	23	21
9	53	40	33	28	50	39	31	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5780	5780	5780	5780
5°	6694	5800	5078	5800
10°	7788	5770	4450	5770
15°	8620	5727	4105	5727
20°	9649	5660	3827	5660
25°	11305	5585	3693	5585
30°	12210	5510	3575	5510
35°	10039	5370	3498	5370
40°	7136	5176	3414	5176
45°	5482	4913	3366	4913
50°	4679	4588	3359	4588
55°	4166	4269	3388	4269
60°	3759	3920	3475	3920
65°	3472	3570	3564	3570
70°	3155	3206	3616	3206
75°	2787	2825	3583	2825
80°	2347	2302	3277	2302
85°	1860	1660	2645	1660



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	2.2
10°-20°	256.5	6.7
20°-30°	416.6	10.8
30°-40°	508.1	13.2
40°-50°	462.2	12.0
50°-60°	368.2	9.6
60°-70°	256.4	6.7
70°-80°	136.8	3.6
80°-90°	35.5	0.9
90°-100°	127.1	3.3
100°-110°	273.1	7.1
110°-120°	256.3	6.7
120°-130°	207.7	5.4
130°-140°	166.7	4.3
140°-150°	125.8	3.3
150°-160°	88.6	2.3
160°-170°	52.2	1.4
170°-180°	17.0	0.4
0°-30°	759.2	19.8
0°-40°	1267.4	33.0
0°-60°	2097.8	54.6
0°-90°	2526.5	65.8
90°-120°	656.5	17.1
90°-150°	1156.8	30.1
90°-180°	1315.0	34.2
0°-180°	3841.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	895	895	895	895	895	
5°	1032	895	783	895	1032	104
15°	1289	857	614	857	1289	369
25°	1586	784	518	784	1586	725
35°	1273	681	444	681	1273	779
45°	600	538	368	538	600	480
55°	370	379	301	379	370	333
65°	227	234	233	234	227	225
75°	112	113	144	113	112	120
85°	25	22	36	22	25	29
90°	8	0	8	0	8	7
95°	83	12	83	12	83	118
105°	468	40	468	40	468	465
115°	522	71	522	71	522	510
125°	411	99	411	99	411	372
135°	341	116	341	116	341	265
145°	269	135	269	135	269	171
155°	226	154	226	154	226	105
165°	198	168	198	168	198	57
175°	178	175	178	175	178	17
180°	175	175	175	175	175	



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	946.7	945.4	944.2	941.8	943.6	938.4	936.0	931.8	926.6	924.8	922.6
5°	1032.5	1034.4	1036.3	1028.3	1029.1	1023.8	1011.6	1001.7	993.8	983.5	976.3
7.5°	1135.8	1131.3	1131.0	1125.8	1116.9	1109.8	1097.0	1080.7	1065.0	1047.1	1032.3
10°	1187.5	1187.9	1184.5	1178.4	1168.9	1162.0	1145.3	1129.4	1110.0	1087.2	1070.9
12.5°	1226.4	1228.0	1223.7	1215.5	1210.8	1195.5	1182.4	1163.4	1140.4	1122.2	1097.3
15°	1289.3	1285.1	1282.1	1271.8	1263.8	1247.9	1227.0	1207.2	1182.2	1159.0	1135.8
17.5°	1349.9	1353.3	1347.6	1338.2	1313.5	1294.8	1266.8	1239.8	1208.5	1177.5	1149.8
20°	1404.0	1407.1	1398.3	1382.0	1352.4	1333.7	1296.9	1261.9	1225.9	1186.0	1155.6
22.5°	1471.5	1469.1	1457.3	1432.4	1406.8	1372.3	1332.5	1289.9	1244.7	1199.6	1159.2
25°	1586.4	1570.4	1563.2	1532.4	1498.6	1448.1	1393.4	1331.1	1274.9	1215.2	1163.6
27.5°	1650.0	1645.0	1637.0	1615.5	1580.0	1526.0	1461.5	1385.6	1306.2	1231.0	1163.3
30°	1637.3	1638.0	1638.8	1631.9	1609.2	1568.5	1504.3	1422.6	1328.4	1243.7	1165.5
32.5°	1524.2	1538.0	1551.3	1566.9	1573.3	1565.5	1525.3	1451.5	1354.6	1258.3	1164.2
35°	1273.3	1277.5	1320.5	1363.0	1420.7	1465.6	1495.6	1462.9	1381.2	1270.7	1162.8
37.5°	992.8	1013.4	1043.1	1091.2	1174.5	1249.1	1345.1	1389.2	1362.8	1274.7	1160.1
40°	846.4	865.4	884.7	933.7	1004.0	1094.4	1203.4	1296.5	1318.2	1261.9	1151.0
42.5°	733.3	748.4	769.9	806.7	865.4	945.5	1049.7	1171.3	1246.1	1224.9	1131.9
45°	600.2	609.7	626.4	655.7	698.2	760.9	852.8	985.8	1101.6	1140.0	1086.4
47.5°	513.7	513.7	526.7	546.9	577.6	630.8	698.8	803.0	926.7	1018.3	1014.0
50°	465.7	463.8	474.1	491.6	515.9	551.2	616.2	699.4	818.3	922.0	950.8
52.5°	424.4	424.6	430.9	443.8	464.2	494.4	542.9	617.9	719.5	825.9	880.3
55°	370.0	368.5	375.7	384.4	399.3	419.0	454.0	511.3	593.7	698.6	769.2
57.5°	320.2	324.3	327.2	333.3	345.6	358.8	388.3	430.4	495.8	585.8	660.5
60°	291.0	295.2	297.4	303.5	313.4	324.8	347.6	381.8	436.9	514.4	588.4
62.5°	264.8	268.1	268.9	274.3	282.4	293.5	311.4	340.1	383.7	451.4	524.0
65°	227.2	227.2	228.7	234.4	238.2	248.1	261.7	282.6	317.6	370.4	432.3
67.5°	190.8	192.7	192.3	194.8	198.3	206.0	215.8	233.0	258.9	297.4	347.0
70°	167.1	168.7	168.3	170.2	174.0	178.9	186.9	203.2	221.8	254.9	297.4
72.5°	145.9	146.5	145.5	148.0	150.3	154.6	163.5	172.2	189.6	217.5	252.5
75°	111.7	112.4	113.2	114.7	117.0	119.3	123.8	132.6	144.0	164.9	187.3
77.5°	83.7	82.3	84.1	83.9	85.2	86.9	90.9	95.6	104.9	118.1	135.5
80°	63.1	63.4	63.4	63.8	65.7	66.9	70.3	73.7	80.9	90.8	102.9
82.5°	46.0	47.0	46.4	47.1	48.7	49.5	51.4	54.2	58.4	66.2	75.0
85°	25.1	23.2	23.9	24.7	24.7	25.1	26.6	27.7	30.0	33.0	36.5
87.5°	8.9	9.5	9.8	9.8	10.1	9.9	11.1	11.0	11.8	12.7	13.8
90°	8.1	8.1	7.8	7.8	7.8	7.1	6.7	6.4	6.0	5.7	4.9
92.5°	22.5	23.1	23.6	24.5	29.0	34.2	45.4	62.6	92.2	113.9	115.8
95°	83.1	88.7	91.5	102.1	127.2	156.9	200.4	254.1	306.4	313.1	255.5
97.5°	200.7	205.3	215.5	235.3	257.1	298.4	340.8	378.4	387.7	334.4	228.2
100°	275.7	281.3	294.4	319.8	344.2	381.0	417.4	434.7	407.5	319.1	203.6
102.5°	359.4	363.6	377.8	395.9	422.0	446.9	464.3	453.6	395.6	292.3	184.9
105°	468.3	472.5	479.6	491.2	502.6	506.4	490.9	442.5	357.7	256.2	166.8
107.5°	526.1	528.9	531.3	531.3	525.6	507.1	467.2	402.6	318.9	231.4	159.2
110°	545.3	545.3	542.8	536.1	520.2	490.2	440.4	373.2	296.9	219.8	156.9



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	543.1	540.5	534.4	522.8	499.6	464.2	413.8	350.0	280.5	213.0	156.9
115°	521.6	517.0	507.1	490.2	462.6	424.1	375.7	320.9	262.6	205.7	158.0
117.5°	484.1	481.3	471.5	453.9	426.4	391.0	349.3	302.1	251.9	202.1	160.3
120°	459.8	457.0	447.4	430.5	404.3	373.2	334.3	291.9	246.0	200.4	162.6
122.5°	438.3	435.8	426.2	410.7	387.3	358.2	323.6	284.3	240.9	199.0	164.5
125°	411.0	407.5	399.7	385.2	365.4	340.0	309.2	273.2	234.0	197.2	167.9
127.5°	387.7	386.1	378.8	366.0	348.0	324.2	295.5	261.9	227.6	196.4	171.6
130°	375.0	372.9	365.8	354.1	336.5	313.5	285.9	254.8	223.4	195.8	173.9
132.5°	362.2	359.8	353.3	341.7	324.0	301.9	276.9	247.7	220.0	195.8	176.4
135°	341.4	339.3	332.9	321.3	305.7	285.6	262.9	238.6	215.9	195.8	179.9
137.5°	319.1	316.8	310.9	300.3	286.4	269.3	250.5	230.8	212.3	196.2	183.1
140°	303.6	301.8	296.5	287.3	274.2	259.4	243.1	226.5	210.6	196.5	184.5
142.5°	289.2	287.7	282.7	274.9	263.8	250.9	236.9	222.9	209.2	196.8	185.3
145°	269.3	267.9	264.0	258.0	249.5	240.0	229.0	218.1	207.1	196.5	186.2
147.5°	252.5	251.8	249.6	244.8	238.1	230.9	222.4	213.5	204.9	195.6	186.6
150°	243.1	242.8	241.4	237.1	231.8	225.5	218.8	211.0	203.2	194.7	186.6
152.5°	235.8	235.4	234.0	230.6	226.2	221.2	215.1	208.2	201.2	193.6	186.3
155°	225.8	225.5	224.4	221.9	218.4	214.5	209.6	203.9	197.9	191.6	185.5
157.5°	216.9	217.0	216.0	214.0	211.2	208.2	204.3	199.7	194.8	189.4	184.6
160°	211.0	211.3	210.6	208.9	206.4	203.9	200.4	196.9	192.3	188.0	183.8
162.5°	205.6	205.7	205.5	204.1	202.2	200.0	197.0	193.7	190.0	186.3	182.9
165°	197.9	197.9	197.9	197.2	195.8	194.0	191.9	189.4	186.6	183.8	181.7
167.5°	190.8	190.9	191.2	190.6	189.9	188.6	187.0	185.3	183.3	181.3	179.7
170°	186.6	187.0	187.0	186.6	185.9	185.2	184.1	183.1	181.3	179.9	178.8
172.5°	182.6	183.0	183.6	182.9	182.8	182.4	181.6	180.5	179.3	178.2	177.7
175°	177.8	178.1	178.8	178.5	178.5	178.5	177.8	177.8	176.7	176.4	176.4
177.5°	175.3	175.3	176.1	175.9	176.1	176.1	176.1	175.9	175.6	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	920.8	918.7	916.3	912.0	906.8	904.1	899.9	897.1	891.6	887.1	882.2
5°	967.5	957.7	948.6	936.8	923.9	915.5	905.6	894.6	883.2	871.4	858.5
7.5°	1015.9	998.5	979.5	959.0	939.1	920.7	903.1	885.9	869.8	850.3	833.8
10°	1048.5	1026.4	1002.9	975.1	948.2	924.6	900.7	879.8	858.5	835.7	815.6
12.5°	1081.0	1051.6	1018.4	987.9	955.5	927.1	898.9	872.2	845.5	820.2	796.8
15°	1103.9	1078.1	1047.3	1004.0	967.5	928.4	891.2	856.6	824.3	796.2	766.6
17.5°	1119.0	1085.8	1052.7	1011.2	963.4	919.6	877.4	837.9	801.5	765.8	737.3
20°	1121.8	1087.6	1053.0	1012.4	963.4	913.2	871.1	823.6	784.4	747.6	712.6
22.5°	1120.9	1082.1	1044.5	1002.6	954.9	908.7	857.7	809.3	766.8	730.6	694.1
25°	1112.3	1070.9	1023.8	981.6	934.5	885.5	833.8	783.7	740.4	699.0	662.9
27.5°	1105.1	1051.4	998.1	948.9	903.4	858.5	809.1	757.7	709.7	667.7	633.7
30°	1096.3	1037.4	977.4	926.1	879.4	835.7	789.0	738.9	688.7	647.7	611.2
32.5°	1088.4	1019.8	956.5	900.6	851.2	808.7	765.6	717.9	668.7	627.0	590.6
35°	1073.2	993.8	921.2	858.1	805.3	761.7	725.6	681.1	635.9	595.6	560.7
37.5°	1053.8	959.6	881.7	815.6	757.7	711.7	678.1	644.0	600.6	561.8	530.2
40°	1038.6	935.3	852.8	785.2	725.2	677.3	646.2	613.9	577.8	541.7	508.3
42.5°	1019.4	913.4	823.6	750.9	691.5	644.8	612.1	584.7	552.9	519.2	488.2
45°	984.3	873.7	776.5	698.2	638.2	592.2	558.4	537.9	514.0	482.1	455.9
47.5°	932.5	826.1	725.5	644.7	582.8	540.2	508.5	488.8	472.0	448.3	424.5
50°	886.6	790.5	688.7	608.6	546.6	503.7	474.5	456.6	442.2	423.9	403.8
52.5°	835.3	745.8	652.6	573.3	512.0	469.7	441.0	425.3	413.3	400.2	380.4
55°	753.7	677.7	591.1	515.9	459.3	417.9	392.8	379.1	369.2	359.4	347.2
57.5°	663.8	604.4	527.6	458.9	406.8	369.1	345.7	332.4	324.7	319.6	312.5
60°	600.6	549.7	483.6	420.9	370.0	336.6	313.8	303.5	297.1	292.9	287.6
62.5°	541.9	500.1	438.9	381.7	337.2	305.6	285.2	275.3	269.1	267.1	262.6
65°	455.5	423.2	372.7	325.2	287.2	260.2	243.1	233.6	229.8	227.5	227.9
67.5°	370.3	350.6	310.1	269.6	239.2	216.6	202.9	195.6	193.7	190.7	190.6
70°	318.3	303.5	269.3	234.0	207.0	189.6	177.4	169.8	167.9	166.4	166.0
72.5°	272.4	259.5	229.8	201.5	177.3	161.9	151.9	147.3	144.2	143.3	143.2
75°	204.8	197.5	174.0	151.6	134.9	124.2	117.4	113.2	110.9	110.5	110.9
77.5°	145.6	139.3	124.3	108.4	97.9	89.8	84.0	82.6	80.0	80.1	79.7
80°	109.4	105.2	95.7	83.2	74.5	67.6	64.6	61.9	61.2	60.0	61.2
82.5°	79.3	74.8	68.4	60.4	53.2	49.1	46.0	45.2	44.7	44.2	44.4
85°	39.1	39.5	35.7	29.6	26.6	24.3	22.4	22.4	22.0	21.7	22.0
87.5°	14.3	13.5	12.3	11.2	9.5	8.5	8.0	8.3	7.4	7.3	7.7
90°	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	80.6	48.3	29.0	18.7	12.6	8.2	5.2	4.3	5.2	8.2	12.6
95°	158.0	80.2	42.4	26.5	18.7	14.8	12.0	11.7	12.0	14.8	18.7
97.5°	126.1	69.1	44.1	32.7	25.7	21.8	19.8	19.4	19.8	21.8	25.7
100°	114.5	68.6	48.1	37.5	30.7	26.9	25.4	24.7	25.4	26.9	30.7
102.5°	109.7	71.1	52.9	42.6	36.4	32.2	31.1	30.7	31.1	32.2	36.4
105°	107.8	76.3	60.8	50.9	45.2	41.7	39.9	39.9	39.9	41.7	45.2
107.5°	111.0	84.1	69.1	60.2	54.3	51.4	49.7	49.0	49.7	51.4	54.3
110°	114.2	89.8	75.3	66.1	60.8	57.6	56.2	55.5	56.2	57.6	60.8



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	118.1	95.1	81.2	72.3	67.0	63.8	62.7	62.0	62.7	63.8	67.0
115°	124.0	103.6	90.5	81.6	76.3	73.2	72.1	71.4	72.1	73.2	76.3
117.5°	130.8	112.2	99.8	91.3	85.2	82.1	80.9	79.9	80.9	82.1	85.2
120°	135.4	118.4	106.0	97.2	91.2	88.0	86.6	85.5	86.6	88.0	91.2
122.5°	140.4	124.3	112.0	103.1	96.6	93.4	92.2	91.5	92.2	93.4	96.6
125°	147.4	132.2	120.5	111.3	104.6	101.4	99.7	99.0	99.7	101.4	104.6
127.5°	153.7	139.7	128.5	119.3	112.2	108.1	105.9	104.8	105.9	108.1	112.2
130°	158.0	144.5	133.6	124.4	117.0	112.4	109.6	108.5	109.6	112.4	117.0
132.5°	161.7	149.1	138.1	128.9	121.2	116.1	112.7	111.3	112.7	116.1	121.2
135°	166.8	155.1	144.2	134.7	127.2	121.6	117.3	115.9	117.3	121.6	127.2
137.5°	170.6	159.5	149.5	139.7	132.4	126.7	122.8	121.7	122.8	126.7	132.4
140°	173.2	162.6	152.3	142.8	136.1	130.4	126.2	125.1	126.2	130.4	136.1
142.5°	174.6	164.5	154.9	145.9	139.5	133.8	129.8	129.1	129.8	133.8	139.5
145°	176.7	167.9	158.7	150.6	144.2	139.2	135.7	135.0	135.7	139.2	144.2
147.5°	178.0	170.0	161.9	154.8	149.3	144.7	141.6	141.2	141.6	144.7	149.3
150°	178.8	171.4	163.6	157.6	152.7	148.1	145.6	144.9	145.6	148.1	152.7
152.5°	179.4	172.8	165.6	160.2	155.5	151.5	149.3	148.9	149.3	151.5	155.5
155°	179.9	174.2	168.2	163.3	159.7	156.2	154.1	154.1	154.1	156.2	159.7
157.5°	180.2	175.4	170.3	166.5	163.4	160.4	158.7	158.8	158.7	160.4	163.4
160°	180.2	176.0	171.4	168.2	165.4	162.9	161.5	161.9	161.5	162.9	165.4
162.5°	180.0	176.6	172.5	169.9	167.7	165.5	164.1	164.4	164.1	165.5	167.7
165°	179.5	176.7	173.9	171.8	170.3	168.6	167.5	168.2	167.5	168.6	170.3
167.5°	178.7	176.7	174.4	173.0	172.0	171.1	170.4	170.8	170.4	171.1	172.0
170°	178.1	176.7	174.9	173.9	173.2	172.5	172.1	172.5	172.1	172.5	173.2
172.5°	177.6	176.4	174.9	174.4	174.0	173.3	173.0	173.6	173.0	173.3	174.0
175°	176.7	176.0	174.9	174.9	174.9	174.6	174.2	174.9	174.2	174.6	174.9
177.5°	175.9	175.6	175.0	175.0	175.3	175.0	175.0	175.6	175.0	175.0	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	879.5	876.1	873.4	867.3	864.0	859.4	855.8	859.7	855.5	857.3	854.6
5°	852.1	841.4	833.8	822.8	813.3	804.6	798.1	797.0	793.9	792.4	787.9
7.5°	819.1	805.8	792.7	778.3	766.1	753.8	745.8	739.3	735.0	729.3	725.4
10°	799.6	781.8	766.6	749.1	733.9	720.6	710.0	704.7	699.7	692.5	689.9
12.5°	775.6	757.2	738.6	719.9	705.4	690.5	681.4	673.4	670.0	661.8	661.0
15°	746.8	719.1	700.9	681.9	661.7	649.6	642.0	633.3	629.5	623.8	619.6
17.5°	712.5	687.7	664.9	645.3	628.0	617.8	608.3	602.3	595.8	592.1	585.2
20°	687.6	664.0	641.2	620.3	607.0	595.3	587.7	582.0	575.1	573.2	566.4
22.5°	666.6	640.6	618.7	601.2	586.7	573.4	565.2	561.3	556.6	550.7	549.4
25°	632.5	605.5	586.9	569.4	556.5	544.4	538.7	533.7	529.2	525.0	523.5
27.5°	603.0	578.9	556.8	541.0	529.8	518.7	513.7	507.7	504.3	501.0	496.9
30°	582.4	557.7	538.3	523.1	510.9	501.1	495.7	491.6	488.5	485.5	483.2
32.5°	561.1	538.2	519.4	504.6	492.4	485.0	480.2	477.3	473.9	470.3	467.4
35°	533.0	507.9	489.7	476.7	467.2	461.5	456.2	453.6	449.8	449.8	446.7
37.5°	501.3	479.6	463.5	451.7	443.2	438.1	432.4	430.6	428.1	426.5	425.5
40°	482.4	462.3	447.1	435.3	426.2	422.0	417.5	414.4	412.9	411.0	410.3
42.5°	463.0	443.8	429.2	418.3	410.4	406.8	402.6	400.5	397.4	394.9	394.5
45°	433.4	414.8	401.5	392.8	386.0	381.8	379.1	374.6	373.0	370.0	369.6
47.5°	405.4	387.5	374.5	367.3	361.3	357.9	353.7	349.2	347.4	345.9	345.8
50°	384.4	368.1	355.9	349.1	343.4	338.5	334.3	331.3	330.1	330.1	330.9
52.5°	363.2	349.3	338.9	330.6	325.2	319.9	316.1	314.2	312.5	314.3	315.7
55°	332.0	318.0	310.4	302.4	297.1	291.0	289.1	288.3	287.2	290.2	291.7
57.5°	299.0	289.2	280.3	272.4	267.6	264.1	261.5	261.1	263.2	264.6	269.6
60°	278.1	266.7	258.7	252.6	246.9	244.6	243.9	243.1	244.6	248.8	255.3
62.5°	255.0	245.7	237.1	232.6	228.4	224.6	224.4	224.9	227.9	232.7	239.2
65°	221.1	213.1	207.4	202.1	198.7	196.4	197.2	198.7	202.1	208.6	215.8
67.5°	186.7	181.2	176.1	171.8	168.5	168.5	169.3	171.6	175.6	183.0	189.6
70°	164.5	158.4	154.2	152.3	149.7	148.2	150.4	154.2	157.6	164.5	170.2
72.5°	142.3	137.1	133.9	132.6	131.4	130.2	131.0	135.1	139.7	146.6	153.2
75°	109.4	107.5	105.2	103.7	102.6	103.3	104.1	107.9	111.7	118.9	126.5
77.5°	79.9	77.9	76.5	76.1	75.5	75.9	78.0	80.8	84.6	89.8	95.6
80°	60.4	59.6	58.9	58.5	58.5	58.9	61.9	63.8	67.2	72.2	76.7
82.5°	44.0	43.5	43.4	43.3	43.6	43.7	45.5	48.0	50.8	54.6	58.5
85°	23.2	22.4	23.6	23.9	23.2	24.3	25.1	26.6	27.7	29.6	31.5
87.5°	8.2	8.9	8.7	9.1	9.2	9.9	9.7	11.0	11.7	12.4	12.2
90°	2.8	3.5	3.9	4.6	4.9	5.7	6.0	6.4	6.7	7.1	7.8
92.5°	18.7	29.0	48.3	80.6	115.8	113.9	92.2	62.6	45.4	34.2	29.0
95°	26.5	42.4	80.2	158.0	255.5	313.1	306.4	254.1	200.4	156.9	127.2
97.5°	32.7	44.1	69.1	126.1	228.2	334.4	387.7	378.4	340.8	298.4	257.1
100°	37.5	48.1	68.6	114.5	203.6	319.1	407.5	434.7	417.4	381.0	344.2
102.5°	42.6	52.9	71.1	109.7	184.9	292.3	395.6	453.6	464.3	446.9	422.0
105°	50.9	60.8	76.3	107.8	166.8	256.2	357.7	442.5	490.9	506.4	502.6
107.5°	60.2	69.1	84.1	111.0	159.2	231.4	318.9	402.6	467.2	507.1	525.6
110°	66.1	75.3	89.8	114.2	156.9	219.8	296.9	373.2	440.4	490.2	520.2



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	72.3	81.2	95.1	118.1	156.9	213.0	280.5	350.0	413.8	464.2	499.6
115°	81.6	90.5	103.6	124.0	158.0	205.7	262.6	320.9	375.7	424.1	462.6
117.5°	91.3	99.8	112.2	130.8	160.3	202.1	251.9	302.1	349.3	391.0	426.4
120°	97.2	106.0	118.4	135.4	162.6	200.4	246.0	291.9	334.3	373.2	404.3
122.5°	103.1	112.0	124.3	140.4	164.5	199.0	240.9	284.3	323.6	358.2	387.3
125°	111.3	120.5	132.2	147.4	167.9	197.2	234.0	273.2	309.2	340.0	365.4
127.5°	119.3	128.5	139.7	153.7	171.6	196.4	227.6	261.9	295.5	324.2	348.0
130°	124.4	133.6	144.5	158.0	173.9	195.8	223.4	254.8	285.9	313.5	336.5
132.5°	128.9	138.1	149.1	161.7	176.4	195.8	220.0	247.7	276.9	301.9	324.0
135°	134.7	144.2	155.1	166.8	179.9	195.8	215.9	238.6	262.9	285.6	305.7
137.5°	139.7	149.5	159.5	170.6	183.1	196.2	212.3	230.8	250.5	269.3	286.4
140°	142.8	152.3	162.6	173.2	184.5	196.5	210.6	226.5	243.1	259.4	274.2
142.5°	145.9	154.9	164.5	174.6	185.3	196.8	209.2	222.9	236.9	250.9	263.8
145°	150.6	158.7	167.9	176.7	186.2	196.5	207.1	218.1	229.0	240.0	249.5
147.5°	154.8	161.9	170.0	178.0	186.6	195.6	204.9	213.5	222.4	230.9	238.1
150°	157.6	163.6	171.4	178.8	186.6	194.7	203.2	211.0	218.8	225.5	231.8
152.5°	160.2	165.6	172.8	179.4	186.3	193.6	201.2	208.2	215.1	221.2	226.2
155°	163.3	168.2	174.2	179.9	185.5	191.6	197.9	203.9	209.6	214.5	218.4
157.5°	166.5	170.3	175.4	180.2	184.6	189.4	194.8	199.7	204.3	208.2	211.2
160°	168.2	171.4	176.0	180.2	183.8	188.0	192.3	196.9	200.4	203.9	206.4
162.5°	169.9	172.5	176.6	180.0	182.9	186.3	190.0	193.7	197.0	200.0	202.2
165°	171.8	173.9	176.7	179.5	181.7	183.8	186.6	189.4	191.9	194.0	195.8
167.5°	173.0	174.4	176.7	178.7	179.7	181.3	183.3	185.3	187.0	188.6	189.9
170°	173.9	174.9	176.7	178.1	178.8	179.9	181.3	183.1	184.1	185.2	185.9
172.5°	174.4	174.9	176.4	177.6	177.7	178.2	179.3	180.5	181.6	182.4	182.8
175°	174.9	174.9	176.0	176.7	176.4	176.4	176.7	177.8	177.8	178.5	178.5
177.5°	175.0	175.0	175.6	175.9	175.3	175.3	175.6	175.9	176.1	176.1	176.1
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	852.7	854.9	853.1	855.5	853.1	854.9	852.7	854.6	857.3	855.5	859.7
5°	786.0	782.5	784.8	783.3	784.8	782.5	786.0	787.9	792.4	793.9	797.0
7.5°	724.3	721.0	717.3	715.5	717.3	721.0	724.3	725.4	729.3	735.0	739.3
10°	685.7	681.5	681.1	678.5	681.1	681.5	685.7	689.9	692.5	699.7	704.7
12.5°	657.4	653.5	649.2	648.1	649.2	653.5	657.4	661.0	661.8	670.0	673.4
15°	617.3	614.3	611.6	613.9	611.6	614.3	617.3	619.6	623.8	629.5	633.3
17.5°	583.9	581.4	581.0	578.2	581.0	581.4	583.9	585.2	592.1	595.8	602.3
20°	563.0	561.1	561.8	556.9	561.8	561.1	563.0	566.4	573.2	575.1	582.0
22.5°	546.3	542.5	542.1	541.1	542.1	542.5	546.3	549.4	550.7	556.6	561.3
25°	520.1	518.2	516.3	518.2	516.3	518.2	520.1	523.5	525.0	529.2	533.7
27.5°	497.2	494.9	494.4	494.6	494.4	494.9	497.2	496.9	501.0	504.3	507.7
30°	483.2	479.4	479.8	479.4	479.8	479.4	483.2	483.2	485.5	488.5	491.6
32.5°	468.0	465.4	464.9	464.2	464.9	465.4	468.0	467.4	470.3	473.9	477.3
35°	445.6	445.6	443.7	443.7	443.7	445.6	445.6	446.7	449.8	449.8	453.6
37.5°	424.5	424.2	423.0	423.2	423.0	424.2	424.5	425.5	426.5	428.1	430.6
40°	408.7	408.4	407.2	404.9	407.2	408.4	408.7	410.3	411.0	412.9	414.4
42.5°	393.6	392.3	391.7	391.0	391.7	392.3	393.6	394.5	394.9	397.4	400.5
45°	369.6	369.6	368.9	368.5	368.9	369.6	369.6	369.6	370.0	373.0	374.6
47.5°	346.4	347.1	348.5	348.3	348.5	347.1	346.4	345.8	345.9	347.4	349.2
50°	332.4	332.8	333.9	334.3	333.9	332.8	332.4	330.9	330.1	330.1	331.3
52.5°	316.9	319.1	320.5	320.3	320.5	319.1	316.9	315.7	314.3	312.5	314.2
55°	295.2	297.8	300.5	300.9	300.5	297.8	295.2	291.7	290.2	287.2	288.3
57.5°	273.7	277.4	280.2	281.1	280.2	277.4	273.7	269.6	264.6	263.2	261.1
60°	259.1	264.0	267.4	269.0	267.4	264.0	259.1	255.3	248.8	244.6	243.1
62.5°	245.1	250.6	254.1	254.4	254.1	250.6	245.1	239.2	232.7	227.9	224.9
65°	222.2	227.9	231.0	233.2	231.0	227.9	222.2	215.8	208.6	202.1	198.7
67.5°	197.6	203.3	206.7	208.5	206.7	203.3	197.6	189.6	183.0	175.6	171.6
70°	179.7	185.4	189.9	191.5	189.9	185.4	179.7	170.2	164.5	157.6	154.2
72.5°	162.1	167.1	170.8	172.6	170.8	167.1	162.1	153.2	146.6	139.7	135.1
75°	131.4	138.3	141.7	143.6	141.7	138.3	131.4	126.5	118.9	111.7	107.9
77.5°	101.4	107.6	109.6	110.6	109.6	107.6	101.4	95.6	89.8	84.6	80.8
80°	81.3	85.1	87.8	88.1	87.8	85.1	81.3	76.7	72.2	67.2	63.8
82.5°	62.5	65.6	66.5	67.5	66.5	65.6	62.5	58.5	54.6	50.8	48.0
85°	34.2	35.7	36.1	35.7	36.1	35.7	34.2	31.5	29.6	27.7	26.6
87.5°	12.8	12.5	12.6	13.2	12.6	12.5	12.8	12.2	12.4	11.7	11.0
90°	7.8	7.8	8.1	8.1	8.1	7.8	7.8	7.8	7.1	6.7	6.4
92.5°	24.5	23.6	23.1	22.5	23.1	23.6	24.5	29.0	34.2	45.4	62.6
95°	102.1	91.5	88.7	83.1	88.7	91.5	102.1	127.2	156.9	200.4	254.1
97.5°	235.3	215.5	205.3	200.7	205.3	215.5	235.3	257.1	298.4	340.8	378.4
100°	319.8	294.4	281.3	275.7	281.3	294.4	319.8	344.2	381.0	417.4	434.7
102.5°	395.9	377.8	363.6	359.4	363.6	377.8	395.9	422.0	446.9	464.3	453.6
105°	491.2	479.6	472.5	468.3	472.5	479.6	491.2	502.6	506.4	490.9	442.5
107.5°	531.3	531.3	528.9	526.1	528.9	531.3	531.3	525.6	507.1	467.2	402.6
110°	536.1	542.8	545.3	545.3	545.3	542.8	536.1	520.2	490.2	440.4	373.2



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	522.8	534.4	540.5	543.1	540.5	534.4	522.8	499.6	464.2	413.8	350.0
115°	490.2	507.1	517.0	521.6	517.0	507.1	490.2	462.6	424.1	375.7	320.9
117.5°	453.9	471.5	481.3	484.1	481.3	471.5	453.9	426.4	391.0	349.3	302.1
120°	430.5	447.4	457.0	459.8	457.0	447.4	430.5	404.3	373.2	334.3	291.9
122.5°	410.7	426.2	435.8	438.3	435.8	426.2	410.7	387.3	358.2	323.6	284.3
125°	385.2	399.7	407.5	411.0	407.5	399.7	385.2	365.4	340.0	309.2	273.2
127.5°	366.0	378.8	386.1	387.7	386.1	378.8	366.0	348.0	324.2	295.5	261.9
130°	354.1	365.8	372.9	375.0	372.9	365.8	354.1	336.5	313.5	285.9	254.8
132.5°	341.7	353.3	359.8	362.2	359.8	353.3	341.7	324.0	301.9	276.9	247.7
135°	321.3	332.9	339.3	341.4	339.3	332.9	321.3	305.7	285.6	262.9	238.6
137.5°	300.3	310.9	316.8	319.1	316.8	310.9	300.3	286.4	269.3	250.5	230.8
140°	287.3	296.5	301.8	303.6	301.8	296.5	287.3	274.2	259.4	243.1	226.5
142.5°	274.9	282.7	287.7	289.2	287.7	282.7	274.9	263.8	250.9	236.9	222.9
145°	258.0	264.0	267.9	269.3	267.9	264.0	258.0	249.5	240.0	229.0	218.1
147.5°	244.8	249.6	251.8	252.5	251.8	249.6	244.8	238.1	230.9	222.4	213.5
150°	237.1	241.4	242.8	243.1	242.8	241.4	237.1	231.8	225.5	218.8	211.0
152.5°	230.6	234.0	235.4	235.8	235.4	234.0	230.6	226.2	221.2	215.1	208.2
155°	221.9	224.4	225.5	225.8	225.5	224.4	221.9	218.4	214.5	209.6	203.9
157.5°	214.0	216.0	217.0	216.9	217.0	216.0	214.0	211.2	208.2	204.3	199.7
160°	208.9	210.6	211.3	211.0	211.3	210.6	208.9	206.4	203.9	200.4	196.9
162.5°	204.1	205.5	205.7	205.6	205.7	205.5	204.1	202.2	200.0	197.0	193.7
165°	197.2	197.9	197.9	197.9	197.9	197.9	197.2	195.8	194.0	191.9	189.4
167.5°	190.6	191.2	190.9	190.8	190.9	191.2	190.6	189.9	188.6	187.0	185.3
170°	186.6	187.0	187.0	186.6	187.0	187.0	186.6	185.9	185.2	184.1	183.1
172.5°	182.9	183.6	183.0	182.6	183.0	183.6	182.9	182.8	182.4	181.6	180.5
175°	178.5	178.8	178.1	177.8	178.1	178.8	178.5	178.5	178.5	177.8	177.8
177.5°	175.9	176.1	175.3	175.3	175.3	176.1	175.9	176.1	176.1	176.1	175.9
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	855.8	859.4	864.0	867.3	873.4	876.1	879.5	882.2	887.1	891.6	897.1
5°	798.1	804.6	813.3	822.8	833.8	841.4	852.1	858.5	871.4	883.2	894.6
7.5°	745.8	753.8	766.1	778.3	792.7	805.8	819.1	833.8	850.3	869.8	885.9
10°	710.0	720.6	733.9	749.1	766.6	781.8	799.6	815.6	835.7	858.5	879.8
12.5°	681.4	690.5	705.4	719.9	738.6	757.2	775.6	796.8	820.2	845.5	872.2
15°	642.0	649.6	661.7	681.9	700.9	719.1	746.8	766.6	796.2	824.3	856.6
17.5°	608.3	617.8	628.0	645.3	664.9	687.7	712.5	737.3	765.8	801.5	837.9
20°	587.7	595.3	607.0	620.3	641.2	664.0	687.6	712.6	747.6	784.4	823.6
22.5°	565.2	573.4	586.7	601.2	618.7	640.6	666.6	694.1	730.6	766.8	809.3
25°	538.7	544.4	556.5	569.4	586.9	605.5	632.5	662.9	699.0	740.4	783.7
27.5°	513.7	518.7	529.8	541.0	556.8	578.9	603.0	633.7	667.7	709.7	757.7
30°	495.7	501.1	510.9	523.1	538.3	557.7	582.4	611.2	647.7	688.7	738.9
32.5°	480.2	485.0	492.4	504.6	519.4	538.2	561.1	590.6	627.0	668.7	717.9
35°	456.2	461.5	467.2	476.7	489.7	507.9	533.0	560.7	595.6	635.9	681.1
37.5°	432.4	438.1	443.2	451.7	463.5	479.6	501.3	530.2	561.8	600.6	644.0
40°	417.5	422.0	426.2	435.3	447.1	462.3	482.4	508.3	541.7	577.8	613.9
42.5°	402.6	406.8	410.4	418.3	429.2	443.8	463.0	488.2	519.2	552.9	584.7
45°	379.1	381.8	386.0	392.8	401.5	414.8	433.4	455.9	482.1	514.0	537.9
47.5°	353.7	357.9	361.3	367.3	374.5	387.5	405.4	424.5	448.3	472.0	488.8
50°	334.3	338.5	343.4	349.1	355.9	368.1	384.4	403.8	423.9	442.2	456.6
52.5°	316.1	319.9	325.2	330.6	338.9	349.3	363.2	380.4	400.2	413.3	425.3
55°	289.1	291.0	297.1	302.4	310.4	318.0	332.0	347.2	359.4	369.2	379.1
57.5°	261.5	264.1	267.6	272.4	280.3	289.2	299.0	312.5	319.6	324.7	332.4
60°	243.9	244.6	246.9	252.6	258.7	266.7	278.1	287.6	292.9	297.1	303.5
62.5°	224.4	224.6	228.4	232.6	237.1	245.7	255.0	262.6	267.1	269.1	275.3
65°	197.2	196.4	198.7	202.1	207.4	213.1	221.1	227.9	227.5	229.8	233.6
67.5°	169.3	168.5	168.5	171.8	176.1	181.2	186.7	190.6	190.7	193.7	195.6
70°	150.4	148.2	149.7	152.3	154.2	158.4	164.5	166.0	166.4	167.9	169.8
72.5°	131.0	130.2	131.4	132.6	133.9	137.1	142.3	143.2	143.3	144.2	147.3
75°	104.1	103.3	102.6	103.7	105.2	107.5	109.4	110.9	110.5	110.9	113.2
77.5°	78.0	75.9	75.5	76.1	76.5	77.9	79.9	79.7	80.1	80.0	82.6
80°	61.9	58.9	58.5	58.5	58.9	59.6	60.4	61.2	60.0	61.2	61.9
82.5°	45.5	43.7	43.6	43.3	43.4	43.5	44.0	44.4	44.2	44.7	45.2
85°	25.1	24.3	23.2	23.9	23.6	22.4	23.2	22.0	21.7	22.0	22.4
87.5°	9.7	9.9	9.2	9.1	8.7	8.9	8.2	7.7	7.3	7.4	8.3
90°	6.0	5.7	4.9	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4
92.5°	92.2	113.9	115.8	80.6	48.3	29.0	18.7	12.6	8.2	5.2	4.3
95°	306.4	313.1	255.5	158.0	80.2	42.4	26.5	18.7	14.8	12.0	11.7
97.5°	387.7	334.4	228.2	126.1	69.1	44.1	32.7	25.7	21.8	19.8	19.4
100°	407.5	319.1	203.6	114.5	68.6	48.1	37.5	30.7	26.9	25.4	24.7
102.5°	395.6	292.3	184.9	109.7	71.1	52.9	42.6	36.4	32.2	31.1	30.7
105°	357.7	256.2	166.8	107.8	76.3	60.8	50.9	45.2	41.7	39.9	39.9
107.5°	318.9	231.4	159.2	111.0	84.1	69.1	60.2	54.3	51.4	49.7	49.0
110°	296.9	219.8	156.9	114.2	89.8	75.3	66.1	60.8	57.6	56.2	55.5



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	280.5	213.0	156.9	118.1	95.1	81.2	72.3	67.0	63.8	62.7	62.0
115°	262.6	205.7	158.0	124.0	103.6	90.5	81.6	76.3	73.2	72.1	71.4
117.5°	251.9	202.1	160.3	130.8	112.2	99.8	91.3	85.2	82.1	80.9	79.9
120°	246.0	200.4	162.6	135.4	118.4	106.0	97.2	91.2	88.0	86.6	85.5
122.5°	240.9	199.0	164.5	140.4	124.3	112.0	103.1	96.6	93.4	92.2	91.5
125°	234.0	197.2	167.9	147.4	132.2	120.5	111.3	104.6	101.4	99.7	99.0
127.5°	227.6	196.4	171.6	153.7	139.7	128.5	119.3	112.2	108.1	105.9	104.8
130°	223.4	195.8	173.9	158.0	144.5	133.6	124.4	117.0	112.4	109.6	108.5
132.5°	220.0	195.8	176.4	161.7	149.1	138.1	128.9	121.2	116.1	112.7	111.3
135°	215.9	195.8	179.9	166.8	155.1	144.2	134.7	127.2	121.6	117.3	115.9
137.5°	212.3	196.2	183.1	170.6	159.5	149.5	139.7	132.4	126.7	122.8	121.7
140°	210.6	196.5	184.5	173.2	162.6	152.3	142.8	136.1	130.4	126.2	125.1
142.5°	209.2	196.8	185.3	174.6	164.5	154.9	145.9	139.5	133.8	129.8	129.1
145°	207.1	196.5	186.2	176.7	167.9	158.7	150.6	144.2	139.2	135.7	135.0
147.5°	204.9	195.6	186.6	178.0	170.0	161.9	154.8	149.3	144.7	141.6	141.2
150°	203.2	194.7	186.6	178.8	171.4	163.6	157.6	152.7	148.1	145.6	144.9
152.5°	201.2	193.6	186.3	179.4	172.8	165.6	160.2	155.5	151.5	149.3	148.9
155°	197.9	191.6	185.5	179.9	174.2	168.2	163.3	159.7	156.2	154.1	154.1
157.5°	194.8	189.4	184.6	180.2	175.4	170.3	166.5	163.4	160.4	158.7	158.8
160°	192.3	188.0	183.8	180.2	176.0	171.4	168.2	165.4	162.9	161.5	161.9
162.5°	190.0	186.3	182.9	180.0	176.6	172.5	169.9	167.7	165.5	164.1	164.4
165°	186.6	183.8	181.7	179.5	176.7	173.9	171.8	170.3	168.6	167.5	168.2
167.5°	183.3	181.3	179.7	178.7	176.7	174.4	173.0	172.0	171.1	170.4	170.8
170°	181.3	179.9	178.8	178.1	176.7	174.9	173.9	173.2	172.5	172.1	172.5
172.5°	179.3	178.2	177.7	177.6	176.4	174.9	174.4	174.0	173.3	173.0	173.6
175°	176.7	176.4	176.4	176.7	176.0	174.9	174.9	174.9	174.6	174.2	174.9
177.5°	175.6	175.3	175.3	175.9	175.6	175.0	175.0	175.3	175.0	175.0	175.6
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	899.9	904.1	906.8	912.0	916.3	918.7	920.8	922.6	924.8	926.6	931.8
5°	905.6	915.5	923.9	936.8	948.6	957.7	967.5	976.3	983.5	993.8	1001.7
7.5°	903.1	920.7	939.1	959.0	979.5	998.5	1015.9	1032.3	1047.1	1065.0	1080.7
10°	900.7	924.6	948.2	975.1	1002.9	1026.4	1048.5	1070.9	1087.2	1110.0	1129.4
12.5°	898.9	927.1	955.5	987.9	1018.4	1051.6	1081.0	1097.3	1122.2	1140.4	1163.4
15°	891.2	928.4	967.5	1004.0	1047.3	1078.1	1103.9	1135.8	1159.0	1182.2	1207.2
17.5°	877.4	919.6	963.4	1011.2	1052.7	1085.8	1119.0	1149.8	1177.5	1208.5	1239.8
20°	871.1	913.2	963.4	1012.4	1053.0	1087.6	1121.8	1155.6	1186.0	1225.9	1261.9
22.5°	857.7	908.7	954.9	1002.6	1044.5	1082.1	1120.9	1159.2	1199.6	1244.7	1289.9
25°	833.8	885.5	934.5	981.6	1023.8	1070.9	1112.3	1163.6	1215.2	1274.9	1331.1
27.5°	809.1	858.5	903.4	948.9	998.1	1051.4	1105.1	1163.3	1231.0	1306.2	1385.6
30°	789.0	835.7	879.4	926.1	977.4	1037.4	1096.3	1165.5	1243.7	1328.4	1422.6
32.5°	765.6	808.7	851.2	900.6	956.5	1019.8	1088.4	1164.2	1258.3	1354.6	1451.5
35°	725.6	761.7	805.3	858.1	921.2	993.8	1073.2	1162.8	1270.7	1381.2	1462.9
37.5°	678.1	711.7	757.7	815.6	881.7	959.6	1053.8	1160.1	1274.7	1362.8	1389.2
40°	646.2	677.3	725.2	785.2	852.8	935.3	1038.6	1151.0	1261.9	1318.2	1296.5
42.5°	612.1	644.8	691.5	750.9	823.6	913.4	1019.4	1131.9	1224.9	1246.1	1171.3
45°	558.4	592.2	638.2	698.2	776.5	873.7	984.3	1086.4	1140.0	1101.6	985.8
47.5°	508.5	540.2	582.8	644.7	725.5	826.1	932.5	1014.0	1018.3	926.7	803.0
50°	474.5	503.7	546.6	608.6	688.7	790.5	886.6	950.8	922.0	818.3	699.4
52.5°	441.0	469.7	512.0	573.3	652.6	745.8	835.3	880.3	825.9	719.5	617.9
55°	392.8	417.9	459.3	515.9	591.1	677.7	753.7	769.2	698.6	593.7	511.3
57.5°	345.7	369.1	406.8	458.9	527.6	604.4	663.8	660.5	585.8	495.8	430.4
60°	313.8	336.6	370.0	420.9	483.6	549.7	600.6	588.4	514.4	436.9	381.8
62.5°	285.2	305.6	337.2	381.7	438.9	500.1	541.9	524.0	451.4	383.7	340.1
65°	243.1	260.2	287.2	325.2	372.7	423.2	455.5	432.3	370.4	317.6	282.6
67.5°	202.9	216.6	239.2	269.6	310.1	350.6	370.3	347.0	297.4	258.9	233.0
70°	177.4	189.6	207.0	234.0	269.3	303.5	318.3	297.4	254.9	221.8	203.2
72.5°	151.9	161.9	177.3	201.5	229.8	259.5	272.4	252.5	217.5	189.6	172.2
75°	117.4	124.2	134.9	151.6	174.0	197.5	204.8	187.3	164.9	144.0	132.6
77.5°	84.0	89.8	97.9	108.4	124.3	139.3	145.6	135.5	118.1	104.9	95.6
80°	64.6	67.6	74.5	83.2	95.7	105.2	109.4	102.9	90.8	80.9	73.7
82.5°	46.0	49.1	53.2	60.4	68.4	74.8	79.3	75.0	66.2	58.4	54.2
85°	22.4	24.3	26.6	29.6	35.7	39.5	39.1	36.5	33.0	30.0	27.7
87.5°	8.0	8.5	9.5	11.2	12.3	13.5	14.3	13.8	12.7	11.8	11.0
90°	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.7	6.0	6.4
92.5°	5.2	8.2	12.6	18.7	29.0	48.3	80.6	115.8	113.9	92.2	62.6
95°	12.0	14.8	18.7	26.5	42.4	80.2	158.0	255.5	313.1	306.4	254.1
97.5°	19.8	21.8	25.7	32.7	44.1	69.1	126.1	228.2	334.4	387.7	378.4
100°	25.4	26.9	30.7	37.5	48.1	68.6	114.5	203.6	319.1	407.5	434.7
102.5°	31.1	32.2	36.4	42.6	52.9	71.1	109.7	184.9	292.3	395.6	453.6
105°	39.9	41.7	45.2	50.9	60.8	76.3	107.8	166.8	256.2	357.7	442.5
107.5°	49.7	51.4	54.3	60.2	69.1	84.1	111.0	159.2	231.4	318.9	402.6
110°	56.2	57.6	60.8	66.1	75.3	89.8	114.2	156.9	219.8	296.9	373.2



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	62.7	63.8	67.0	72.3	81.2	95.1	118.1	156.9	213.0	280.5	350.0
115°	72.1	73.2	76.3	81.6	90.5	103.6	124.0	158.0	205.7	262.6	320.9
117.5°	80.9	82.1	85.2	91.3	99.8	112.2	130.8	160.3	202.1	251.9	302.1
120°	86.6	88.0	91.2	97.2	106.0	118.4	135.4	162.6	200.4	246.0	291.9
122.5°	92.2	93.4	96.6	103.1	112.0	124.3	140.4	164.5	199.0	240.9	284.3
125°	99.7	101.4	104.6	111.3	120.5	132.2	147.4	167.9	197.2	234.0	273.2
127.5°	105.9	108.1	112.2	119.3	128.5	139.7	153.7	171.6	196.4	227.6	261.9
130°	109.6	112.4	117.0	124.4	133.6	144.5	158.0	173.9	195.8	223.4	254.8
132.5°	112.7	116.1	121.2	128.9	138.1	149.1	161.7	176.4	195.8	220.0	247.7
135°	117.3	121.6	127.2	134.7	144.2	155.1	166.8	179.9	195.8	215.9	238.6
137.5°	122.8	126.7	132.4	139.7	149.5	159.5	170.6	183.1	196.2	212.3	230.8
140°	126.2	130.4	136.1	142.8	152.3	162.6	173.2	184.5	196.5	210.6	226.5
142.5°	129.8	133.8	139.5	145.9	154.9	164.5	174.6	185.3	196.8	209.2	222.9
145°	135.7	139.2	144.2	150.6	158.7	167.9	176.7	186.2	196.5	207.1	218.1
147.5°	141.6	144.7	149.3	154.8	161.9	170.0	178.0	186.6	195.6	204.9	213.5
150°	145.6	148.1	152.7	157.6	163.6	171.4	178.8	186.6	194.7	203.2	211.0
152.5°	149.3	151.5	155.5	160.2	165.6	172.8	179.4	186.3	193.6	201.2	208.2
155°	154.1	156.2	159.7	163.3	168.2	174.2	179.9	185.5	191.6	197.9	203.9
157.5°	158.7	160.4	163.4	166.5	170.3	175.4	180.2	184.6	189.4	194.8	199.7
160°	161.5	162.9	165.4	168.2	171.4	176.0	180.2	183.8	188.0	192.3	196.9
162.5°	164.1	165.5	167.7	169.9	172.5	176.6	180.0	182.9	186.3	190.0	193.7
165°	167.5	168.6	170.3	171.8	173.9	176.7	179.5	181.7	183.8	186.6	189.4
167.5°	170.4	171.1	172.0	173.0	174.4	176.7	178.7	179.7	181.3	183.3	185.3
170°	172.1	172.5	173.2	173.9	174.9	176.7	178.1	178.8	179.9	181.3	183.1
172.5°	173.0	173.3	174.0	174.4	174.9	176.4	177.6	177.7	178.2	179.3	180.5
175°	174.2	174.6	174.9	174.9	174.9	176.0	176.7	176.4	176.4	176.7	177.8
177.5°	175.0	175.0	175.3	175.0	175.0	175.6	175.9	175.3	175.3	175.6	175.9
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	936.0	938.4	943.6	941.8	944.2	945.4	946.7
5°	1011.6	1023.8	1029.1	1028.3	1036.3	1034.4	1032.5
7.5°	1097.0	1109.8	1116.9	1125.8	1131.0	1131.3	1135.8
10°	1145.3	1162.0	1168.9	1178.4	1184.5	1187.9	1187.5
12.5°	1182.4	1195.5	1210.8	1215.5	1223.7	1228.0	1226.4
15°	1227.0	1247.9	1263.8	1271.8	1282.1	1285.1	1289.3
17.5°	1266.8	1294.8	1313.5	1338.2	1347.6	1353.3	1349.9
20°	1296.9	1333.7	1352.4	1382.0	1398.3	1407.1	1404.0
22.5°	1332.5	1372.3	1406.8	1432.4	1457.3	1469.1	1471.5
25°	1393.4	1448.1	1498.6	1532.4	1563.2	1570.4	1586.4
27.5°	1461.5	1526.0	1580.0	1615.5	1637.0	1645.0	1650.0
30°	1504.3	1568.5	1609.2	1631.9	1638.8	1638.0	1637.3
32.5°	1525.3	1565.5	1573.3	1566.9	1551.3	1538.0	1524.2
35°	1495.6	1465.6	1420.7	1363.0	1320.5	1277.5	1273.3
37.5°	1345.1	1249.1	1174.5	1091.2	1043.1	1013.4	992.8
40°	1203.4	1094.4	1004.0	933.7	884.7	865.4	846.4
42.5°	1049.7	945.5	865.4	806.7	769.9	748.4	733.3
45°	852.8	760.9	698.2	655.7	626.4	609.7	600.2
47.5°	698.8	630.8	577.6	546.9	526.7	513.7	513.7
50°	616.2	551.2	515.9	491.6	474.1	463.8	465.7
52.5°	542.9	494.4	464.2	443.8	430.9	424.6	424.4
55°	454.0	419.0	399.3	384.4	375.7	368.5	370.0
57.5°	388.3	358.8	345.6	333.3	327.2	324.3	320.2
60°	347.6	324.8	313.4	303.5	297.4	295.2	291.0
62.5°	311.4	293.5	282.4	274.3	268.9	268.1	264.8
65°	261.7	248.1	238.2	234.4	228.7	227.2	227.2
67.5°	215.8	206.0	198.3	194.8	192.3	192.7	190.8
70°	186.9	178.9	174.0	170.2	168.3	168.7	167.1
72.5°	163.5	154.6	150.3	148.0	145.5	146.5	145.9
75°	123.8	119.3	117.0	114.7	113.2	112.4	111.7
77.5°	90.9	86.9	85.2	83.9	84.1	82.3	83.7
80°	70.3	66.9	65.7	63.8	63.4	63.4	63.1
82.5°	51.4	49.5	48.7	47.1	46.4	47.0	46.0
85°	26.6	25.1	24.7	24.7	23.9	23.2	25.1
87.5°	11.1	9.9	10.1	9.8	9.8	9.5	8.9
90°	6.7	7.1	7.8	7.8	7.8	8.1	8.1
92.5°	45.4	34.2	29.0	24.5	23.6	23.1	22.5
95°	200.4	156.9	127.2	102.1	91.5	88.7	83.1
97.5°	340.8	298.4	257.1	235.3	215.5	205.3	200.7
100°	417.4	381.0	344.2	319.8	294.4	281.3	275.7
102.5°	464.3	446.9	422.0	395.9	377.8	363.6	359.4
105°	490.9	506.4	502.6	491.2	479.6	472.5	468.3
107.5°	467.2	507.1	525.6	531.3	531.3	528.9	526.1
110°	440.4	490.2	520.2	536.1	542.8	545.3	545.3



TEST NUMBER: P333162

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	413.8	464.2	499.6	522.8	534.4	540.5	543.1
115°	375.7	424.1	462.6	490.2	507.1	517.0	521.6
117.5°	349.3	391.0	426.4	453.9	471.5	481.3	484.1
120°	334.3	373.2	404.3	430.5	447.4	457.0	459.8
122.5°	323.6	358.2	387.3	410.7	426.2	435.8	438.3
125°	309.2	340.0	365.4	385.2	399.7	407.5	411.0
127.5°	295.5	324.2	348.0	366.0	378.8	386.1	387.7
130°	285.9	313.5	336.5	354.1	365.8	372.9	375.0
132.5°	276.9	301.9	324.0	341.7	353.3	359.8	362.2
135°	262.9	285.6	305.7	321.3	332.9	339.3	341.4
137.5°	250.5	269.3	286.4	300.3	310.9	316.8	319.1
140°	243.1	259.4	274.2	287.3	296.5	301.8	303.6
142.5°	236.9	250.9	263.8	274.9	282.7	287.7	289.2
145°	229.0	240.0	249.5	258.0	264.0	267.9	269.3
147.5°	222.4	230.9	238.1	244.8	249.6	251.8	252.5
150°	218.8	225.5	231.8	237.1	241.4	242.8	243.1
152.5°	215.1	221.2	226.2	230.6	234.0	235.4	235.8
155°	209.6	214.5	218.4	221.9	224.4	225.5	225.8
157.5°	204.3	208.2	211.2	214.0	216.0	217.0	216.9
160°	200.4	203.9	206.4	208.9	210.6	211.3	211.0
162.5°	197.0	200.0	202.2	204.1	205.5	205.7	205.6
165°	191.9	194.0	195.8	197.2	197.9	197.9	197.9
167.5°	187.0	188.6	189.9	190.6	191.2	190.9	190.8
170°	184.1	185.2	185.9	186.6	187.0	187.0	186.6
172.5°	181.6	182.4	182.8	182.9	183.6	183.0	182.6
175°	177.8	178.5	178.5	178.5	178.8	178.1	177.8
177.5°	176.1	176.1	176.1	175.9	176.1	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3

(END OF REPORT)