

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333171

Luminaire Tested: **S125DIP-S610D590U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333171
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D590U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4648.8 lumens
Efficiency: N/A
Efficacy: 141.7 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	76	73	71	64	62	61	54	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	47	45	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	43	42	40	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	31	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5780	5780	5780	5780
5°	6694	5800	5078	5800
10°	7788	5770	4450	5770
15°	8620	5727	4105	5727
20°	9649	5660	3827	5660
25°	11305	5585	3693	5585
30°	12210	5510	3575	5510
35°	10039	5370	3498	5370
40°	7136	5176	3414	5176
45°	5482	4913	3366	4913
50°	4679	4588	3359	4588
55°	4166	4269	3388	4269
60°	3759	3920	3475	3920
65°	3472	3570	3564	3570
70°	3155	3206	3616	3206
75°	2787	2825	3583	2825
80°	2347	2302	3277	2302
85°	1860	1660	2645	1660



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	1.9
10°-20°	256.5	5.5
20°-30°	416.6	9.0
30°-40°	508.1	10.9
40°-50°	462.2	9.9
50°-60°	368.2	7.9
60°-70°	256.4	5.5
70°-80°	136.8	2.9
80°-90°	36.1	0.8
90°-100°	205.1	4.4
100°-110°	440.9	9.5
110°-120°	413.8	8.9
120°-130°	335.3	7.2
130°-140°	269.1	5.8
140°-150°	203.1	4.4
150°-160°	142.9	3.1
160°-170°	84.3	1.8
170°-180°	27.4	0.6
0°-30°	759.2	16.3
0°-40°	1267.4	27.3
0°-60°	2097.8	45.1
0°-90°	2527.1	54.4
90°-120°	1059.7	22.8
90°-150°	1867.2	40.2
90°-180°	2122.0	45.6
0°-180°	4648.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	895	895	895	895	895	
5°	1032	895	783	895	1032	104
15°	1289	857	614	857	1289	369
25°	1586	784	518	784	1586	725
35°	1273	681	444	681	1273	779
45°	600	538	368	538	600	480
55°	370	379	301	379	370	333
65°	227	234	233	234	227	225
75°	112	113	144	113	112	120
85°	25	22	36	22	25	29
90°	13	1	13	1	13	10
95°	134	19	134	19	134	190
105°	756	64	756	64	756	751
115°	842	115	842	115	842	823
125°	663	160	663	160	663	600
135°	551	187	551	187	551	427
145°	435	218	435	218	435	276
155°	364	249	364	249	364	170
165°	319	272	319	272	319	91
175°	287	282	287	282	287	28
180°	283	283	283	283	283	



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	946.7	945.4	944.2	941.8	943.6	938.4	936.0	931.8	926.6	924.8	922.6
5°	1032.5	1034.4	1036.3	1028.3	1029.1	1023.8	1011.6	1001.7	993.8	983.5	976.3
7.5°	1135.8	1131.3	1131.0	1125.8	1116.9	1109.8	1097.0	1080.7	1065.0	1047.1	1032.3
10°	1187.5	1187.9	1184.5	1178.4	1168.9	1162.0	1145.3	1129.4	1110.0	1087.2	1070.9
12.5°	1226.4	1228.0	1223.7	1215.5	1210.8	1195.5	1182.4	1163.4	1140.4	1122.2	1097.3
15°	1289.3	1285.1	1282.1	1271.8	1263.8	1247.9	1227.0	1207.2	1182.2	1159.0	1135.8
17.5°	1349.9	1353.3	1347.6	1338.2	1313.5	1294.8	1266.8	1239.8	1208.5	1177.5	1149.8
20°	1404.0	1407.1	1398.3	1382.0	1352.4	1333.7	1296.9	1261.9	1225.9	1186.0	1155.6
22.5°	1471.5	1469.1	1457.3	1432.4	1406.8	1372.3	1332.5	1289.9	1244.7	1199.6	1159.2
25°	1586.4	1570.4	1563.2	1532.4	1498.6	1448.1	1393.4	1331.1	1274.9	1215.2	1163.6
27.5°	1650.0	1645.0	1637.0	1615.5	1580.0	1526.0	1461.5	1385.6	1306.2	1231.0	1163.3
30°	1637.3	1638.0	1638.8	1631.9	1609.2	1568.5	1504.3	1422.6	1328.4	1243.7	1165.5
32.5°	1524.2	1538.0	1551.3	1566.9	1573.3	1565.5	1525.3	1451.5	1354.6	1258.3	1164.2
35°	1273.3	1277.5	1320.5	1363.0	1420.7	1465.6	1495.6	1462.9	1381.2	1270.7	1162.8
37.5°	992.8	1013.4	1043.1	1091.2	1174.5	1249.1	1345.1	1389.2	1362.8	1274.7	1160.1
40°	846.4	865.4	884.7	933.7	1004.0	1094.4	1203.4	1296.5	1318.2	1261.9	1151.0
42.5°	733.3	748.4	769.9	806.7	865.4	945.5	1049.7	1171.3	1246.1	1224.9	1131.9
45°	600.2	609.7	626.4	655.7	698.2	760.9	852.8	985.8	1101.6	1140.0	1086.4
47.5°	513.7	513.7	526.7	546.9	577.6	630.8	698.8	803.0	926.7	1018.3	1014.0
50°	465.7	463.8	474.1	491.6	515.9	551.2	616.2	699.4	818.3	922.0	950.8
52.5°	424.4	424.6	430.9	443.8	464.2	494.4	542.9	617.9	719.5	825.9	880.3
55°	370.0	368.5	375.7	384.4	399.3	419.0	454.0	511.3	593.7	698.6	769.2
57.5°	320.2	324.3	327.2	333.3	345.6	358.8	388.3	430.4	495.8	585.8	660.5
60°	291.0	295.2	297.4	303.5	313.4	324.8	347.6	381.8	436.9	514.4	588.4
62.5°	264.8	268.1	268.9	274.3	282.4	293.5	311.4	340.1	383.7	451.4	524.0
65°	227.2	227.2	228.7	234.4	238.2	248.1	261.7	282.6	317.6	370.4	432.3
67.5°	190.8	192.7	192.3	194.8	198.3	206.0	215.8	233.0	258.9	297.4	347.0
70°	167.1	168.7	168.3	170.2	174.0	178.9	186.9	203.2	221.8	254.9	297.4
72.5°	145.9	146.5	145.5	148.0	150.3	154.6	163.5	172.2	189.6	217.5	252.5
75°	111.7	112.4	113.2	114.7	117.0	119.3	123.8	132.6	144.0	164.9	187.3
77.5°	83.7	82.3	84.1	83.9	85.2	86.9	90.9	95.6	104.9	118.1	135.5
80°	63.1	63.4	63.4	63.8	65.7	66.9	70.3	73.7	80.9	90.8	102.9
82.5°	46.0	47.0	46.4	47.1	48.7	49.5	51.4	54.2	58.4	66.2	75.0
85°	25.1	23.2	23.9	24.7	24.7	25.1	26.6	27.7	30.0	33.0	36.5
87.5°	9.9	10.5	10.7	10.7	11.0	10.8	11.9	11.8	12.6	13.4	14.4
90°	13.1	13.1	12.5	12.5	12.5	11.4	10.8	10.3	9.7	9.1	8.0
92.5°	36.4	37.3	38.1	39.5	46.8	55.2	73.4	101.1	148.9	183.9	186.9
95°	134.1	143.2	147.7	164.9	205.4	253.3	323.4	410.1	494.6	505.4	412.4
97.5°	324.0	331.3	347.8	379.8	415.0	481.7	550.0	610.8	625.8	539.7	368.3
100°	444.9	454.1	475.2	516.2	555.6	614.9	673.7	701.6	657.7	515.1	328.6
102.5°	580.0	586.9	609.8	639.0	681.1	721.2	749.4	732.2	638.5	471.7	298.4
105°	755.8	762.7	774.1	792.9	811.1	817.4	792.3	714.2	577.3	413.6	269.2
107.5°	849.1	853.7	857.5	857.6	848.3	818.6	754.1	649.8	514.8	373.5	256.9
110°	880.2	880.2	876.2	865.3	839.7	791.2	710.8	602.4	479.2	354.8	253.3



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	876.5	872.4	862.5	843.9	806.4	749.2	667.9	565.0	452.7	343.9	253.3
115°	842.0	834.5	818.6	791.2	746.7	684.5	606.4	517.9	423.8	332.0	255.0
117.5°	781.4	776.8	761.0	732.7	688.2	631.1	563.8	487.6	406.6	326.2	258.7
120°	742.1	737.6	722.2	694.8	652.6	602.4	539.6	471.2	397.0	323.4	262.4
122.5°	707.4	703.3	687.9	662.8	625.2	578.2	522.3	458.9	388.8	321.2	265.6
125°	663.4	657.7	645.2	621.8	589.8	548.8	499.1	440.9	377.6	318.3	271.0
127.5°	625.8	623.2	611.4	590.7	561.8	523.3	477.0	422.7	367.4	316.9	277.0
130°	605.2	601.8	590.4	571.6	543.0	506.0	461.5	411.3	360.5	316.0	280.7
132.5°	584.7	580.8	570.3	551.5	523.0	487.3	446.9	399.9	355.0	316.0	284.8
135°	551.0	547.6	537.3	518.5	493.4	460.9	424.4	385.0	348.5	316.0	290.3
137.5°	515.1	511.3	501.9	484.7	462.3	434.7	404.3	372.5	342.7	316.7	295.5
140°	490.0	487.1	478.6	463.8	442.7	418.7	392.5	365.6	340.0	317.2	297.8
142.5°	466.7	464.3	456.2	443.7	425.8	405.0	382.4	359.7	337.7	317.6	299.1
145°	434.7	432.4	426.1	416.4	402.7	387.3	369.6	352.0	334.3	317.2	300.6
147.5°	407.5	406.5	402.8	395.1	384.2	372.6	359.0	344.7	330.7	315.7	301.2
150°	392.5	391.9	389.6	382.8	374.2	363.9	353.1	340.5	328.0	314.3	301.2
152.5°	380.6	380.0	377.7	372.3	365.1	357.1	347.2	336.0	324.8	312.5	300.7
155°	364.5	363.9	362.2	358.2	352.5	346.2	338.3	329.1	319.4	309.2	299.5
157.5°	350.1	350.2	348.6	345.3	340.9	336.0	329.8	322.3	314.4	305.7	298.0
160°	340.5	341.1	340.0	337.1	333.1	329.1	323.4	317.7	310.3	303.5	296.6
162.5°	331.9	332.0	331.8	329.4	326.3	322.7	318.0	312.7	306.7	300.7	295.3
165°	319.4	319.4	319.4	318.3	316.0	313.2	309.7	305.7	301.2	296.6	293.2
167.5°	308.0	308.1	308.6	307.6	306.4	304.4	301.8	299.1	295.8	292.6	290.0
170°	301.2	301.8	301.8	301.2	300.0	298.9	297.2	295.5	292.6	290.3	288.6
172.5°	294.8	295.4	296.3	295.3	295.0	294.3	293.1	291.4	289.4	287.6	286.8
175°	286.9	287.5	288.6	288.1	288.1	288.1	286.9	286.9	285.2	284.6	284.6
177.5°	282.9	282.9	284.3	283.8	284.3	284.3	284.3	283.8	283.4	282.9	282.9
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	920.8	918.7	916.3	912.0	906.8	904.1	899.9	897.1	891.6	887.1	882.2
5°	967.5	957.7	948.6	936.8	923.9	915.5	905.6	894.6	883.2	871.4	858.5
7.5°	1015.9	998.5	979.5	959.0	939.1	920.7	903.1	885.9	869.8	850.3	833.8
10°	1048.5	1026.4	1002.9	975.1	948.2	924.6	900.7	879.8	858.5	835.7	815.6
12.5°	1081.0	1051.6	1018.4	987.9	955.5	927.1	898.9	872.2	845.5	820.2	796.8
15°	1103.9	1078.1	1047.3	1004.0	967.5	928.4	891.2	856.6	824.3	796.2	766.6
17.5°	1119.0	1085.8	1052.7	1011.2	963.4	919.6	877.4	837.9	801.5	765.8	737.3
20°	1121.8	1087.6	1053.0	1012.4	963.4	913.2	871.1	823.6	784.4	747.6	712.6
22.5°	1120.9	1082.1	1044.5	1002.6	954.9	908.7	857.7	809.3	766.8	730.6	694.1
25°	1112.3	1070.9	1023.8	981.6	934.5	885.5	833.8	783.7	740.4	699.0	662.9
27.5°	1105.1	1051.4	998.1	948.9	903.4	858.5	809.1	757.7	709.7	667.7	633.7
30°	1096.3	1037.4	977.4	926.1	879.4	835.7	789.0	738.9	688.7	647.7	611.2
32.5°	1088.4	1019.8	956.5	900.6	851.2	808.7	765.6	717.9	668.7	627.0	590.6
35°	1073.2	993.8	921.2	858.1	805.3	761.7	725.6	681.1	635.9	595.6	560.7
37.5°	1053.8	959.6	881.7	815.6	757.7	711.7	678.1	644.0	600.6	561.8	530.2
40°	1038.6	935.3	852.8	785.2	725.2	677.3	646.2	613.9	577.8	541.7	508.3
42.5°	1019.4	913.4	823.6	750.9	691.5	644.8	612.1	584.7	552.9	519.2	488.2
45°	984.3	873.7	776.5	698.2	638.2	592.2	558.4	537.9	514.0	482.1	455.9
47.5°	932.5	826.1	725.5	644.7	582.8	540.2	508.5	488.8	472.0	448.3	424.5
50°	886.6	790.5	688.7	608.6	546.6	503.7	474.5	456.6	442.2	423.9	403.8
52.5°	835.3	745.8	652.6	573.3	512.0	469.7	441.0	425.3	413.3	400.2	380.4
55°	753.7	677.7	591.1	515.9	459.3	417.9	392.8	379.1	369.2	359.4	347.2
57.5°	663.8	604.4	527.6	458.9	406.8	369.1	345.7	332.4	324.7	319.6	312.5
60°	600.6	549.7	483.6	420.9	370.0	336.6	313.8	303.5	297.1	292.9	287.6
62.5°	541.9	500.1	438.9	381.7	337.2	305.6	285.2	275.3	269.1	267.1	262.6
65°	455.5	423.2	372.7	325.2	287.2	260.2	243.1	233.6	229.8	227.5	227.9
67.5°	370.3	350.6	310.1	269.6	239.2	216.6	202.9	195.6	193.7	190.7	190.6
70°	318.3	303.5	269.3	234.0	207.0	189.6	177.4	169.8	167.9	166.4	166.0
72.5°	272.4	259.5	229.8	201.5	177.3	161.9	151.9	147.3	144.2	143.3	143.2
75°	204.8	197.5	174.0	151.6	134.9	124.2	117.4	113.2	110.9	110.5	110.9
77.5°	145.6	139.3	124.3	108.4	97.9	89.8	84.0	82.6	80.0	80.1	79.7
80°	109.4	105.2	95.7	83.2	74.5	67.6	64.6	61.9	61.2	60.0	61.2
82.5°	79.3	74.8	68.4	60.4	53.2	49.1	46.0	45.2	44.7	44.2	44.4
85°	39.1	39.5	35.7	29.6	26.6	24.3	22.4	22.4	22.0	21.7	22.0
87.5°	14.9	14.0	12.7	11.5	9.8	8.7	8.1	8.3	7.5	7.4	8.0
90°	7.4	6.3	5.7	4.6	3.4	2.3	1.1	0.6	1.1	2.3	3.4
92.5°	130.2	77.9	46.8	30.1	20.3	13.2	8.4	7.0	8.4	13.2	20.3
95°	255.0	129.5	68.5	42.8	30.2	24.0	19.4	18.8	19.4	24.0	30.2
97.5°	203.5	111.6	71.2	52.7	41.4	35.1	31.9	31.3	31.9	35.1	41.4
100°	184.8	110.7	77.6	60.5	49.6	43.4	41.1	39.9	41.1	43.4	49.6
102.5°	177.1	114.8	85.3	68.7	58.8	52.0	50.2	49.5	50.2	52.0	58.8
105°	174.0	123.2	98.1	82.1	73.0	67.3	64.5	64.5	64.5	67.3	73.0
107.5°	179.2	135.8	111.5	97.1	87.6	82.9	80.2	79.1	80.2	82.9	87.6
110°	184.2	144.9	121.5	106.7	98.1	93.0	90.7	89.6	90.7	93.0	98.1



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	190.6	153.6	131.1	116.7	108.2	103.0	101.2	100.1	101.2	103.0	108.2
115°	200.2	167.1	146.0	131.8	123.2	118.1	116.4	115.2	116.4	118.1	123.2
117.5°	211.2	181.1	161.1	147.3	137.6	132.5	130.6	128.9	130.6	132.5	137.6
120°	218.5	191.1	171.1	156.9	147.2	142.0	139.8	138.0	139.8	142.0	147.2
122.5°	226.7	200.7	180.7	166.5	155.8	150.7	148.9	147.6	148.9	150.7	155.8
125°	237.9	213.3	194.5	179.7	168.8	163.7	160.9	159.7	160.9	163.7	168.8
127.5°	248.1	225.5	207.4	192.6	181.1	174.6	170.9	169.2	170.9	174.6	181.1
130°	255.0	233.3	215.6	200.8	188.8	181.4	176.8	175.1	176.8	181.4	188.8
132.5°	260.9	240.6	222.9	208.1	195.7	187.3	181.9	179.7	181.9	187.3	195.7
135°	269.2	250.4	232.7	217.3	205.4	196.2	189.4	187.1	189.4	196.2	205.4
137.5°	275.4	257.4	241.3	225.4	213.7	204.6	198.2	196.5	198.2	204.6	213.7
140°	279.5	262.4	245.9	230.5	219.6	210.5	203.6	201.9	203.6	210.5	219.6
142.5°	281.8	265.6	250.0	235.5	225.1	216.0	209.6	208.3	209.6	216.0	225.1
145°	285.2	271.0	256.1	243.0	232.7	224.7	219.0	217.9	219.0	224.7	232.7
147.5°	287.3	274.4	261.4	249.8	240.9	233.5	228.6	227.9	228.6	233.5	240.9
150°	288.6	276.7	264.1	254.4	246.4	239.0	235.0	233.9	235.0	239.0	246.4
152.5°	289.5	278.9	267.3	258.5	251.0	244.5	240.9	240.3	240.9	244.5	251.0
155°	290.3	281.2	271.5	263.5	257.8	252.1	248.7	248.7	248.7	252.1	257.8
157.5°	290.9	283.2	274.8	268.8	263.8	258.9	256.1	256.2	256.1	258.9	263.8
160°	290.9	284.1	276.7	271.5	267.0	263.0	260.7	261.3	260.7	263.0	267.0
162.5°	290.5	285.0	278.5	274.3	270.6	267.1	264.8	265.4	264.8	267.1	270.6
165°	289.8	285.2	280.7	277.2	274.9	272.1	270.4	271.5	270.4	272.1	274.9
167.5°	288.4	285.2	281.4	279.3	277.7	276.1	275.1	275.6	275.1	276.1	277.7
170°	287.5	285.2	282.4	280.7	279.5	278.4	277.8	278.4	277.8	278.4	279.5
172.5°	286.6	284.8	282.4	281.6	280.9	279.7	279.2	280.2	279.2	279.7	280.9
175°	285.2	284.1	282.4	282.4	282.4	281.8	281.2	282.4	281.2	281.8	282.4
177.5°	283.8	283.4	282.5	282.5	282.9	282.5	282.5	283.4	282.5	282.5	282.9
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	879.5	876.1	873.4	867.3	864.0	859.4	855.8	859.7	855.5	857.3	854.6
5°	852.1	841.4	833.8	822.8	813.3	804.6	798.1	797.0	793.9	792.4	787.9
7.5°	819.1	805.8	792.7	778.3	766.1	753.8	745.8	739.3	735.0	729.3	725.4
10°	799.6	781.8	766.6	749.1	733.9	720.6	710.0	704.7	699.7	692.5	689.9
12.5°	775.6	757.2	738.6	719.9	705.4	690.5	681.4	673.4	670.0	661.8	661.0
15°	746.8	719.1	700.9	681.9	661.7	649.6	642.0	633.3	629.5	623.8	619.6
17.5°	712.5	687.7	664.9	645.3	628.0	617.8	608.3	602.3	595.8	592.1	585.2
20°	687.6	664.0	641.2	620.3	607.0	595.3	587.7	582.0	575.1	573.2	566.4
22.5°	666.6	640.6	618.7	601.2	586.7	573.4	565.2	561.3	556.6	550.7	549.4
25°	632.5	605.5	586.9	569.4	556.5	544.4	538.7	533.7	529.2	525.0	523.5
27.5°	603.0	578.9	556.8	541.0	529.8	518.7	513.7	507.7	504.3	501.0	496.9
30°	582.4	557.7	538.3	523.1	510.9	501.1	495.7	491.6	488.5	485.5	483.2
32.5°	561.1	538.2	519.4	504.6	492.4	485.0	480.2	477.3	473.9	470.3	467.4
35°	533.0	507.9	489.7	476.7	467.2	461.5	456.2	453.6	449.8	449.8	446.7
37.5°	501.3	479.6	463.5	451.7	443.2	438.1	432.4	430.6	428.1	426.5	425.5
40°	482.4	462.3	447.1	435.3	426.2	422.0	417.5	414.4	412.9	411.0	410.3
42.5°	463.0	443.8	429.2	418.3	410.4	406.8	402.6	400.5	397.4	394.9	394.5
45°	433.4	414.8	401.5	392.8	386.0	381.8	379.1	374.6	373.0	370.0	369.6
47.5°	405.4	387.5	374.5	367.3	361.3	357.9	353.7	349.2	347.4	345.9	345.8
50°	384.4	368.1	355.9	349.1	343.4	338.5	334.3	331.3	330.1	330.1	330.9
52.5°	363.2	349.3	338.9	330.6	325.2	319.9	316.1	314.2	312.5	314.3	315.7
55°	332.0	318.0	310.4	302.4	297.1	291.0	289.1	288.3	287.2	290.2	291.7
57.5°	299.0	289.2	280.3	272.4	267.6	264.1	261.5	261.1	263.2	264.6	269.6
60°	278.1	266.7	258.7	252.6	246.9	244.6	243.9	243.1	244.6	248.8	255.3
62.5°	255.0	245.7	237.1	232.6	228.4	224.6	224.4	224.9	227.9	232.7	239.2
65°	221.1	213.1	207.4	202.1	198.7	196.4	197.2	198.7	202.1	208.6	215.8
67.5°	186.7	181.2	176.1	171.8	168.5	168.5	169.3	171.6	175.6	183.0	189.6
70°	164.5	158.4	154.2	152.3	149.7	148.2	150.4	154.2	157.6	164.5	170.2
72.5°	142.3	137.1	133.9	132.6	131.4	130.2	131.0	135.1	139.7	146.6	153.2
75°	109.4	107.5	105.2	103.7	102.6	103.3	104.1	107.9	111.7	118.9	126.5
77.5°	79.9	77.9	76.5	76.1	75.5	75.9	78.0	80.8	84.6	89.8	95.6
80°	60.4	59.6	58.9	58.5	58.5	58.9	61.9	63.8	67.2	72.2	76.7
82.5°	44.0	43.5	43.4	43.3	43.6	43.7	45.5	48.0	50.8	54.6	58.5
85°	23.2	22.4	23.6	23.9	23.2	24.3	25.1	26.6	27.7	29.6	31.5
87.5°	8.5	9.3	9.2	9.7	9.8	10.6	10.4	11.8	12.5	13.2	13.1
90°	4.6	5.7	6.3	7.4	8.0	9.1	9.7	10.3	10.8	11.4	12.5
92.5°	30.1	46.8	77.9	130.2	186.9	183.9	148.9	101.1	73.4	55.2	46.8
95°	42.8	68.5	129.5	255.0	412.4	505.4	494.6	410.1	323.4	253.3	205.4
97.5°	52.7	71.2	111.6	203.5	368.3	539.7	625.8	610.8	550.0	481.7	415.0
100°	60.5	77.6	110.7	184.8	328.6	515.1	657.7	701.6	673.7	614.9	555.6
102.5°	68.7	85.3	114.8	177.1	298.4	471.7	638.5	732.2	749.4	721.2	681.1
105°	82.1	98.1	123.2	174.0	269.2	413.6	577.3	714.2	792.3	817.4	811.1
107.5°	97.1	111.5	135.8	179.2	256.9	373.5	514.8	649.8	754.1	818.6	848.3
110°	106.7	121.5	144.9	184.2	253.3	354.8	479.2	602.4	710.8	791.2	839.7



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	116.7	131.1	153.6	190.6	253.3	343.9	452.7	565.0	667.9	749.2	806.4
115°	131.8	146.0	167.1	200.2	255.0	332.0	423.8	517.9	606.4	684.5	746.7
117.5°	147.3	161.1	181.1	211.2	258.7	326.2	406.6	487.6	563.8	631.1	688.2
120°	156.9	171.1	191.1	218.5	262.4	323.4	397.0	471.2	539.6	602.4	652.6
122.5°	166.5	180.7	200.7	226.7	265.6	321.2	388.8	458.9	522.3	578.2	625.2
125°	179.7	194.5	213.3	237.9	271.0	318.3	377.6	440.9	499.1	548.8	589.8
127.5°	192.6	207.4	225.5	248.1	277.0	316.9	367.4	422.7	477.0	523.3	561.8
130°	200.8	215.6	233.3	255.0	280.7	316.0	360.5	411.3	461.5	506.0	543.0
132.5°	208.1	222.9	240.6	260.9	284.8	316.0	355.0	399.9	446.9	487.3	523.0
135°	217.3	232.7	250.4	269.2	290.3	316.0	348.5	385.0	424.4	460.9	493.4
137.5°	225.4	241.3	257.4	275.4	295.5	316.7	342.7	372.5	404.3	434.7	462.3
140°	230.5	245.9	262.4	279.5	297.8	317.2	340.0	365.6	392.5	418.7	442.7
142.5°	235.5	250.0	265.6	281.8	299.1	317.6	337.7	359.7	382.4	405.0	425.8
145°	243.0	256.1	271.0	285.2	300.6	317.2	334.3	352.0	369.6	387.3	402.7
147.5°	249.8	261.4	274.4	287.3	301.2	315.7	330.7	344.7	359.0	372.6	384.2
150°	254.4	264.1	276.7	288.6	301.2	314.3	328.0	340.5	353.1	363.9	374.2
152.5°	258.5	267.3	278.9	289.5	300.7	312.5	324.8	336.0	347.2	357.1	365.1
155°	263.5	271.5	281.2	290.3	299.5	309.2	319.4	329.1	338.3	346.2	352.5
157.5°	268.8	274.8	283.2	290.9	298.0	305.7	314.4	322.3	329.8	336.0	340.9
160°	271.5	276.7	284.1	290.9	296.6	303.5	310.3	317.7	323.4	329.1	333.1
162.5°	274.3	278.5	285.0	290.5	295.3	300.7	306.7	312.7	318.0	322.7	326.3
165°	277.2	280.7	285.2	289.8	293.2	296.6	301.2	305.7	309.7	313.2	316.0
167.5°	279.3	281.4	285.2	288.4	290.0	292.6	295.8	299.1	301.8	304.4	306.4
170°	280.7	282.4	285.2	287.5	288.6	290.3	292.6	295.5	297.2	298.9	300.0
172.5°	281.6	282.4	284.8	286.6	286.8	287.6	289.4	291.4	293.1	294.3	295.0
175°	282.4	282.4	284.1	285.2	284.6	284.6	285.2	286.9	286.9	288.1	288.1
177.5°	282.5	282.5	283.4	283.8	282.9	282.9	283.4	283.8	284.3	284.3	284.3
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	852.7	854.9	853.1	855.5	853.1	854.9	852.7	854.6	857.3	855.5	859.7
5°	786.0	782.5	784.8	783.3	784.8	782.5	786.0	787.9	792.4	793.9	797.0
7.5°	724.3	721.0	717.3	715.5	717.3	721.0	724.3	725.4	729.3	735.0	739.3
10°	685.7	681.5	681.1	678.5	681.1	681.5	685.7	689.9	692.5	699.7	704.7
12.5°	657.4	653.5	649.2	648.1	649.2	653.5	657.4	661.0	661.8	670.0	673.4
15°	617.3	614.3	611.6	613.9	611.6	614.3	617.3	619.6	623.8	629.5	633.3
17.5°	583.9	581.4	581.0	578.2	581.0	581.4	583.9	585.2	592.1	595.8	602.3
20°	563.0	561.1	561.8	556.9	561.8	561.1	563.0	566.4	573.2	575.1	582.0
22.5°	546.3	542.5	542.1	541.1	542.1	542.5	546.3	549.4	550.7	556.6	561.3
25°	520.1	518.2	516.3	518.2	516.3	518.2	520.1	523.5	525.0	529.2	533.7
27.5°	497.2	494.9	494.4	494.6	494.4	494.9	497.2	496.9	501.0	504.3	507.7
30°	483.2	479.4	479.8	479.4	479.8	479.4	483.2	483.2	485.5	488.5	491.6
32.5°	468.0	465.4	464.9	464.2	464.9	465.4	468.0	467.4	470.3	473.9	477.3
35°	445.6	445.6	443.7	443.7	443.7	445.6	445.6	446.7	449.8	449.8	453.6
37.5°	424.5	424.2	423.0	423.2	423.0	424.2	424.5	425.5	426.5	428.1	430.6
40°	408.7	408.4	407.2	404.9	407.2	408.4	408.7	410.3	411.0	412.9	414.4
42.5°	393.6	392.3	391.7	391.0	391.7	392.3	393.6	394.5	394.9	397.4	400.5
45°	369.6	369.6	368.9	368.5	368.9	369.6	369.6	369.6	370.0	373.0	374.6
47.5°	346.4	347.1	348.5	348.3	348.5	347.1	346.4	345.8	345.9	347.4	349.2
50°	332.4	332.8	333.9	334.3	333.9	332.8	332.4	330.9	330.1	330.1	331.3
52.5°	316.9	319.1	320.5	320.3	320.5	319.1	316.9	315.7	314.3	312.5	314.2
55°	295.2	297.8	300.5	300.9	300.5	297.8	295.2	291.7	290.2	287.2	288.3
57.5°	273.7	277.4	280.2	281.1	280.2	277.4	273.7	269.6	264.6	263.2	261.1
60°	259.1	264.0	267.4	269.0	267.4	264.0	259.1	255.3	248.8	244.6	243.1
62.5°	245.1	250.6	254.1	254.4	254.1	250.6	245.1	239.2	232.7	227.9	224.9
65°	222.2	227.9	231.0	233.2	231.0	227.9	222.2	215.8	208.6	202.1	198.7
67.5°	197.6	203.3	206.7	208.5	206.7	203.3	197.6	189.6	183.0	175.6	171.6
70°	179.7	185.4	189.9	191.5	189.9	185.4	179.7	170.2	164.5	157.6	154.2
72.5°	162.1	167.1	170.8	172.6	170.8	167.1	162.1	153.2	146.6	139.7	135.1
75°	131.4	138.3	141.7	143.6	141.7	138.3	131.4	126.5	118.9	111.7	107.9
77.5°	101.4	107.6	109.6	110.6	109.6	107.6	101.4	95.6	89.8	84.6	80.8
80°	81.3	85.1	87.8	88.1	87.8	85.1	81.3	76.7	72.2	67.2	63.8
82.5°	62.5	65.6	66.5	67.5	66.5	65.6	62.5	58.5	54.6	50.8	48.0
85°	34.2	35.7	36.1	35.7	36.1	35.7	34.2	31.5	29.6	27.7	26.6
87.5°	13.8	13.5	13.6	14.2	13.6	13.5	13.8	13.1	13.2	12.5	11.8
90°	12.5	12.5	13.1	13.1	13.1	12.5	12.5	12.5	11.4	10.8	10.3
92.5°	39.5	38.1	37.3	36.4	37.3	38.1	39.5	46.8	55.2	73.4	101.1
95°	164.9	147.7	143.2	134.1	143.2	147.7	164.9	205.4	253.3	323.4	410.1
97.5°	379.8	347.8	331.3	324.0	331.3	347.8	379.8	415.0	481.7	550.0	610.8
100°	516.2	475.2	454.1	444.9	454.1	475.2	516.2	555.6	614.9	673.7	701.6
102.5°	639.0	609.8	586.9	580.0	586.9	609.8	639.0	681.1	721.2	749.4	732.2
105°	792.9	774.1	762.7	755.8	762.7	774.1	792.9	811.1	817.4	792.3	714.2
107.5°	857.6	857.5	853.7	849.1	853.7	857.5	857.6	848.3	818.6	754.1	649.8
110°	865.3	876.2	880.2	880.2	880.2	876.2	865.3	839.7	791.2	710.8	602.4



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	843.9	862.5	872.4	876.5	872.4	862.5	843.9	806.4	749.2	667.9	565.0
115°	791.2	818.6	834.5	842.0	834.5	818.6	791.2	746.7	684.5	606.4	517.9
117.5°	732.7	761.0	776.8	781.4	776.8	761.0	732.7	688.2	631.1	563.8	487.6
120°	694.8	722.2	737.6	742.1	737.6	722.2	694.8	652.6	602.4	539.6	471.2
122.5°	662.8	687.9	703.3	707.4	703.3	687.9	662.8	625.2	578.2	522.3	458.9
125°	621.8	645.2	657.7	663.4	657.7	645.2	621.8	589.8	548.8	499.1	440.9
127.5°	590.7	611.4	623.2	625.8	623.2	611.4	590.7	561.8	523.3	477.0	422.7
130°	571.6	590.4	601.8	605.2	601.8	590.4	571.6	543.0	506.0	461.5	411.3
132.5°	551.5	570.3	580.8	584.7	580.8	570.3	551.5	523.0	487.3	446.9	399.9
135°	518.5	537.3	547.6	551.0	547.6	537.3	518.5	493.4	460.9	424.4	385.0
137.5°	484.7	501.9	511.3	515.1	511.3	501.9	484.7	462.3	434.7	404.3	372.5
140°	463.8	478.6	487.1	490.0	487.1	478.6	463.8	442.7	418.7	392.5	365.6
142.5°	443.7	456.2	464.3	466.7	464.3	456.2	443.7	425.8	405.0	382.4	359.7
145°	416.4	426.1	432.4	434.7	432.4	426.1	416.4	402.7	387.3	369.6	352.0
147.5°	395.1	402.8	406.5	407.5	406.5	402.8	395.1	384.2	372.6	359.0	344.7
150°	382.8	389.6	391.9	392.5	391.9	389.6	382.8	374.2	363.9	353.1	340.5
152.5°	372.3	377.7	380.0	380.6	380.0	377.7	372.3	365.1	357.1	347.2	336.0
155°	358.2	362.2	363.9	364.5	363.9	362.2	358.2	352.5	346.2	338.3	329.1
157.5°	345.3	348.6	350.2	350.1	350.2	348.6	345.3	340.9	336.0	329.8	322.3
160°	337.1	340.0	341.1	340.5	341.1	340.0	337.1	333.1	329.1	323.4	317.7
162.5°	329.4	331.8	332.0	331.9	332.0	331.8	329.4	326.3	322.7	318.0	312.7
165°	318.3	319.4	319.4	319.4	319.4	319.4	318.3	316.0	313.2	309.7	305.7
167.5°	307.6	308.6	308.1	308.0	308.1	308.6	307.6	306.4	304.4	301.8	299.1
170°	301.2	301.8	301.8	301.2	301.8	301.8	301.2	300.0	298.9	297.2	295.5
172.5°	295.3	296.3	295.4	294.8	295.4	296.3	295.3	295.0	294.3	293.1	291.4
175°	288.1	288.6	287.5	286.9	287.5	288.6	288.1	288.1	288.1	286.9	286.9
177.5°	283.8	284.3	282.9	282.9	282.9	284.3	283.8	284.3	284.3	284.3	283.8
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	855.8	859.4	864.0	867.3	873.4	876.1	879.5	882.2	887.1	891.6	897.1
5°	798.1	804.6	813.3	822.8	833.8	841.4	852.1	858.5	871.4	883.2	894.6
7.5°	745.8	753.8	766.1	778.3	792.7	805.8	819.1	833.8	850.3	869.8	885.9
10°	710.0	720.6	733.9	749.1	766.6	781.8	799.6	815.6	835.7	858.5	879.8
12.5°	681.4	690.5	705.4	719.9	738.6	757.2	775.6	796.8	820.2	845.5	872.2
15°	642.0	649.6	661.7	681.9	700.9	719.1	746.8	766.6	796.2	824.3	856.6
17.5°	608.3	617.8	628.0	645.3	664.9	687.7	712.5	737.3	765.8	801.5	837.9
20°	587.7	595.3	607.0	620.3	641.2	664.0	687.6	712.6	747.6	784.4	823.6
22.5°	565.2	573.4	586.7	601.2	618.7	640.6	666.6	694.1	730.6	766.8	809.3
25°	538.7	544.4	556.5	569.4	586.9	605.5	632.5	662.9	699.0	740.4	783.7
27.5°	513.7	518.7	529.8	541.0	556.8	578.9	603.0	633.7	667.7	709.7	757.7
30°	495.7	501.1	510.9	523.1	538.3	557.7	582.4	611.2	647.7	688.7	738.9
32.5°	480.2	485.0	492.4	504.6	519.4	538.2	561.1	590.6	627.0	668.7	717.9
35°	456.2	461.5	467.2	476.7	489.7	507.9	533.0	560.7	595.6	635.9	681.1
37.5°	432.4	438.1	443.2	451.7	463.5	479.6	501.3	530.2	561.8	600.6	644.0
40°	417.5	422.0	426.2	435.3	447.1	462.3	482.4	508.3	541.7	577.8	613.9
42.5°	402.6	406.8	410.4	418.3	429.2	443.8	463.0	488.2	519.2	552.9	584.7
45°	379.1	381.8	386.0	392.8	401.5	414.8	433.4	455.9	482.1	514.0	537.9
47.5°	353.7	357.9	361.3	367.3	374.5	387.5	405.4	424.5	448.3	472.0	488.8
50°	334.3	338.5	343.4	349.1	355.9	368.1	384.4	403.8	423.9	442.2	456.6
52.5°	316.1	319.9	325.2	330.6	338.9	349.3	363.2	380.4	400.2	413.3	425.3
55°	289.1	291.0	297.1	302.4	310.4	318.0	332.0	347.2	359.4	369.2	379.1
57.5°	261.5	264.1	267.6	272.4	280.3	289.2	299.0	312.5	319.6	324.7	332.4
60°	243.9	244.6	246.9	252.6	258.7	266.7	278.1	287.6	292.9	297.1	303.5
62.5°	224.4	224.6	228.4	232.6	237.1	245.7	255.0	262.6	267.1	269.1	275.3
65°	197.2	196.4	198.7	202.1	207.4	213.1	221.1	227.9	227.5	229.8	233.6
67.5°	169.3	168.5	168.5	171.8	176.1	181.2	186.7	190.6	190.7	193.7	195.6
70°	150.4	148.2	149.7	152.3	154.2	158.4	164.5	166.0	166.4	167.9	169.8
72.5°	131.0	130.2	131.4	132.6	133.9	137.1	142.3	143.2	143.3	144.2	147.3
75°	104.1	103.3	102.6	103.7	105.2	107.5	109.4	110.9	110.5	110.9	113.2
77.5°	78.0	75.9	75.5	76.1	76.5	77.9	79.9	79.7	80.1	80.0	82.6
80°	61.9	58.9	58.5	58.5	58.9	59.6	60.4	61.2	60.0	61.2	61.9
82.5°	45.5	43.7	43.6	43.3	43.4	43.5	44.0	44.4	44.2	44.7	45.2
85°	25.1	24.3	23.2	23.9	23.6	22.4	23.2	22.0	21.7	22.0	22.4
87.5°	10.4	10.6	9.8	9.7	9.2	9.3	8.5	8.0	7.4	7.5	8.3
90°	9.7	9.1	8.0	7.4	6.3	5.7	4.6	3.4	2.3	1.1	0.6
92.5°	148.9	183.9	186.9	130.2	77.9	46.8	30.1	20.3	13.2	8.4	7.0
95°	494.6	505.4	412.4	255.0	129.5	68.5	42.8	30.2	24.0	19.4	18.8
97.5°	625.8	539.7	368.3	203.5	111.6	71.2	52.7	41.4	35.1	31.9	31.3
100°	657.7	515.1	328.6	184.8	110.7	77.6	60.5	49.6	43.4	41.1	39.9
102.5°	638.5	471.7	298.4	177.1	114.8	85.3	68.7	58.8	52.0	50.2	49.5
105°	577.3	413.6	269.2	174.0	123.2	98.1	82.1	73.0	67.3	64.5	64.5
107.5°	514.8	373.5	256.9	179.2	135.8	111.5	97.1	87.6	82.9	80.2	79.1
110°	479.2	354.8	253.3	184.2	144.9	121.5	106.7	98.1	93.0	90.7	89.6



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	452.7	343.9	253.3	190.6	153.6	131.1	116.7	108.2	103.0	101.2	100.1
115°	423.8	332.0	255.0	200.2	167.1	146.0	131.8	123.2	118.1	116.4	115.2
117.5°	406.6	326.2	258.7	211.2	181.1	161.1	147.3	137.6	132.5	130.6	128.9
120°	397.0	323.4	262.4	218.5	191.1	171.1	156.9	147.2	142.0	139.8	138.0
122.5°	388.8	321.2	265.6	226.7	200.7	180.7	166.5	155.8	150.7	148.9	147.6
125°	377.6	318.3	271.0	237.9	213.3	194.5	179.7	168.8	163.7	160.9	159.7
127.5°	367.4	316.9	277.0	248.1	225.5	207.4	192.6	181.1	174.6	170.9	169.2
130°	360.5	316.0	280.7	255.0	233.3	215.6	200.8	188.8	181.4	176.8	175.1
132.5°	355.0	316.0	284.8	260.9	240.6	222.9	208.1	195.7	187.3	181.9	179.7
135°	348.5	316.0	290.3	269.2	250.4	232.7	217.3	205.4	196.2	189.4	187.1
137.5°	342.7	316.7	295.5	275.4	257.4	241.3	225.4	213.7	204.6	198.2	196.5
140°	340.0	317.2	297.8	279.5	262.4	245.9	230.5	219.6	210.5	203.6	201.9
142.5°	337.7	317.6	299.1	281.8	265.6	250.0	235.5	225.1	216.0	209.6	208.3
145°	334.3	317.2	300.6	285.2	271.0	256.1	243.0	232.7	224.7	219.0	217.9
147.5°	330.7	315.7	301.2	287.3	274.4	261.4	249.8	240.9	233.5	228.6	227.9
150°	328.0	314.3	301.2	288.6	276.7	264.1	254.4	246.4	239.0	235.0	233.9
152.5°	324.8	312.5	300.7	289.5	278.9	267.3	258.5	251.0	244.5	240.9	240.3
155°	319.4	309.2	299.5	290.3	281.2	271.5	263.5	257.8	252.1	248.7	248.7
157.5°	314.4	305.7	298.0	290.9	283.2	274.8	268.8	263.8	258.9	256.1	256.2
160°	310.3	303.5	296.6	290.9	284.1	276.7	271.5	267.0	263.0	260.7	261.3
162.5°	306.7	300.7	295.3	290.5	285.0	278.5	274.3	270.6	267.1	264.8	265.4
165°	301.2	296.6	293.2	289.8	285.2	280.7	277.2	274.9	272.1	270.4	271.5
167.5°	295.8	292.6	290.0	288.4	285.2	281.4	279.3	277.7	276.1	275.1	275.6
170°	292.6	290.3	288.6	287.5	285.2	282.4	280.7	279.5	278.4	277.8	278.4
172.5°	289.4	287.6	286.8	286.6	284.8	282.4	281.6	280.9	279.7	279.2	280.2
175°	285.2	284.6	284.6	285.2	284.1	282.4	282.4	282.4	281.8	281.2	282.4
177.5°	283.4	282.9	282.9	283.8	283.4	282.5	282.5	282.9	282.5	282.5	283.4
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	899.9	904.1	906.8	912.0	916.3	918.7	920.8	922.6	924.8	926.6	931.8
5°	905.6	915.5	923.9	936.8	948.6	957.7	967.5	976.3	983.5	993.8	1001.7
7.5°	903.1	920.7	939.1	959.0	979.5	998.5	1015.9	1032.3	1047.1	1065.0	1080.7
10°	900.7	924.6	948.2	975.1	1002.9	1026.4	1048.5	1070.9	1087.2	1110.0	1129.4
12.5°	898.9	927.1	955.5	987.9	1018.4	1051.6	1081.0	1097.3	1122.2	1140.4	1163.4
15°	891.2	928.4	967.5	1004.0	1047.3	1078.1	1103.9	1135.8	1159.0	1182.2	1207.2
17.5°	877.4	919.6	963.4	1011.2	1052.7	1085.8	1119.0	1149.8	1177.5	1208.5	1239.8
20°	871.1	913.2	963.4	1012.4	1053.0	1087.6	1121.8	1155.6	1186.0	1225.9	1261.9
22.5°	857.7	908.7	954.9	1002.6	1044.5	1082.1	1120.9	1159.2	1199.6	1244.7	1289.9
25°	833.8	885.5	934.5	981.6	1023.8	1070.9	1112.3	1163.6	1215.2	1274.9	1331.1
27.5°	809.1	858.5	903.4	948.9	998.1	1051.4	1105.1	1163.3	1231.0	1306.2	1385.6
30°	789.0	835.7	879.4	926.1	977.4	1037.4	1096.3	1165.5	1243.7	1328.4	1422.6
32.5°	765.6	808.7	851.2	900.6	956.5	1019.8	1088.4	1164.2	1258.3	1354.6	1451.5
35°	725.6	761.7	805.3	858.1	921.2	993.8	1073.2	1162.8	1270.7	1381.2	1462.9
37.5°	678.1	711.7	757.7	815.6	881.7	959.6	1053.8	1160.1	1274.7	1362.8	1389.2
40°	646.2	677.3	725.2	785.2	852.8	935.3	1038.6	1151.0	1261.9	1318.2	1296.5
42.5°	612.1	644.8	691.5	750.9	823.6	913.4	1019.4	1131.9	1224.9	1246.1	1171.3
45°	558.4	592.2	638.2	698.2	776.5	873.7	984.3	1086.4	1140.0	1101.6	985.8
47.5°	508.5	540.2	582.8	644.7	725.5	826.1	932.5	1014.0	1018.3	926.7	803.0
50°	474.5	503.7	546.6	608.6	688.7	790.5	886.6	950.8	922.0	818.3	699.4
52.5°	441.0	469.7	512.0	573.3	652.6	745.8	835.3	880.3	825.9	719.5	617.9
55°	392.8	417.9	459.3	515.9	591.1	677.7	753.7	769.2	698.6	593.7	511.3
57.5°	345.7	369.1	406.8	458.9	527.6	604.4	663.8	660.5	585.8	495.8	430.4
60°	313.8	336.6	370.0	420.9	483.6	549.7	600.6	588.4	514.4	436.9	381.8
62.5°	285.2	305.6	337.2	381.7	438.9	500.1	541.9	524.0	451.4	383.7	340.1
65°	243.1	260.2	287.2	325.2	372.7	423.2	455.5	432.3	370.4	317.6	282.6
67.5°	202.9	216.6	239.2	269.6	310.1	350.6	370.3	347.0	297.4	258.9	233.0
70°	177.4	189.6	207.0	234.0	269.3	303.5	318.3	297.4	254.9	221.8	203.2
72.5°	151.9	161.9	177.3	201.5	229.8	259.5	272.4	252.5	217.5	189.6	172.2
75°	117.4	124.2	134.9	151.6	174.0	197.5	204.8	187.3	164.9	144.0	132.6
77.5°	84.0	89.8	97.9	108.4	124.3	139.3	145.6	135.5	118.1	104.9	95.6
80°	64.6	67.6	74.5	83.2	95.7	105.2	109.4	102.9	90.8	80.9	73.7
82.5°	46.0	49.1	53.2	60.4	68.4	74.8	79.3	75.0	66.2	58.4	54.2
85°	22.4	24.3	26.6	29.6	35.7	39.5	39.1	36.5	33.0	30.0	27.7
87.5°	8.1	8.7	9.8	11.5	12.7	14.0	14.9	14.4	13.4	12.6	11.8
90°	1.1	2.3	3.4	4.6	5.7	6.3	7.4	8.0	9.1	9.7	10.3
92.5°	8.4	13.2	20.3	30.1	46.8	77.9	130.2	186.9	183.9	148.9	101.1
95°	19.4	24.0	30.2	42.8	68.5	129.5	255.0	412.4	505.4	494.6	410.1
97.5°	31.9	35.1	41.4	52.7	71.2	111.6	203.5	368.3	539.7	625.8	610.8
100°	41.1	43.4	49.6	60.5	77.6	110.7	184.8	328.6	515.1	657.7	701.6
102.5°	50.2	52.0	58.8	68.7	85.3	114.8	177.1	298.4	471.7	638.5	732.2
105°	64.5	67.3	73.0	82.1	98.1	123.2	174.0	269.2	413.6	577.3	714.2
107.5°	80.2	82.9	87.6	97.1	111.5	135.8	179.2	256.9	373.5	514.8	649.8
110°	90.7	93.0	98.1	106.7	121.5	144.9	184.2	253.3	354.8	479.2	602.4



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	101.2	103.0	108.2	116.7	131.1	153.6	190.6	253.3	343.9	452.7	565.0
115°	116.4	118.1	123.2	131.8	146.0	167.1	200.2	255.0	332.0	423.8	517.9
117.5°	130.6	132.5	137.6	147.3	161.1	181.1	211.2	258.7	326.2	406.6	487.6
120°	139.8	142.0	147.2	156.9	171.1	191.1	218.5	262.4	323.4	397.0	471.2
122.5°	148.9	150.7	155.8	166.5	180.7	200.7	226.7	265.6	321.2	388.8	458.9
125°	160.9	163.7	168.8	179.7	194.5	213.3	237.9	271.0	318.3	377.6	440.9
127.5°	170.9	174.6	181.1	192.6	207.4	225.5	248.1	277.0	316.9	367.4	422.7
130°	176.8	181.4	188.8	200.8	215.6	233.3	255.0	280.7	316.0	360.5	411.3
132.5°	181.9	187.3	195.7	208.1	222.9	240.6	260.9	284.8	316.0	355.0	399.9
135°	189.4	196.2	205.4	217.3	232.7	250.4	269.2	290.3	316.0	348.5	385.0
137.5°	198.2	204.6	213.7	225.4	241.3	257.4	275.4	295.5	316.7	342.7	372.5
140°	203.6	210.5	219.6	230.5	245.9	262.4	279.5	297.8	317.2	340.0	365.6
142.5°	209.6	216.0	225.1	235.5	250.0	265.6	281.8	299.1	317.6	337.7	359.7
145°	219.0	224.7	232.7	243.0	256.1	271.0	285.2	300.6	317.2	334.3	352.0
147.5°	228.6	233.5	240.9	249.8	261.4	274.4	287.3	301.2	315.7	330.7	344.7
150°	235.0	239.0	246.4	254.4	264.1	276.7	288.6	301.2	314.3	328.0	340.5
152.5°	240.9	244.5	251.0	258.5	267.3	278.9	289.5	300.7	312.5	324.8	336.0
155°	248.7	252.1	257.8	263.5	271.5	281.2	290.3	299.5	309.2	319.4	329.1
157.5°	256.1	258.9	263.8	268.8	274.8	283.2	290.9	298.0	305.7	314.4	322.3
160°	260.7	263.0	267.0	271.5	276.7	284.1	290.9	296.6	303.5	310.3	317.7
162.5°	264.8	267.1	270.6	274.3	278.5	285.0	290.5	295.3	300.7	306.7	312.7
165°	270.4	272.1	274.9	277.2	280.7	285.2	289.8	293.2	296.6	301.2	305.7
167.5°	275.1	276.1	277.7	279.3	281.4	285.2	288.4	290.0	292.6	295.8	299.1
170°	277.8	278.4	279.5	280.7	282.4	285.2	287.5	288.6	290.3	292.6	295.5
172.5°	279.2	279.7	280.9	281.6	282.4	284.8	286.6	286.8	287.6	289.4	291.4
175°	281.2	281.8	282.4	282.4	282.4	284.1	285.2	284.6	284.6	285.2	286.9
177.5°	282.5	282.5	282.9	282.5	282.5	283.4	283.8	282.9	282.9	283.4	283.8
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	936.0	938.4	943.6	941.8	944.2	945.4	946.7
5°	1011.6	1023.8	1029.1	1028.3	1036.3	1034.4	1032.5
7.5°	1097.0	1109.8	1116.9	1125.8	1131.0	1131.3	1135.8
10°	1145.3	1162.0	1168.9	1178.4	1184.5	1187.9	1187.5
12.5°	1182.4	1195.5	1210.8	1215.5	1223.7	1228.0	1226.4
15°	1227.0	1247.9	1263.8	1271.8	1282.1	1285.1	1289.3
17.5°	1266.8	1294.8	1313.5	1338.2	1347.6	1353.3	1349.9
20°	1296.9	1333.7	1352.4	1382.0	1398.3	1407.1	1404.0
22.5°	1332.5	1372.3	1406.8	1432.4	1457.3	1469.1	1471.5
25°	1393.4	1448.1	1498.6	1532.4	1563.2	1570.4	1586.4
27.5°	1461.5	1526.0	1580.0	1615.5	1637.0	1645.0	1650.0
30°	1504.3	1568.5	1609.2	1631.9	1638.8	1638.0	1637.3
32.5°	1525.3	1565.5	1573.3	1566.9	1551.3	1538.0	1524.2
35°	1495.6	1465.6	1420.7	1363.0	1320.5	1277.5	1273.3
37.5°	1345.1	1249.1	1174.5	1091.2	1043.1	1013.4	992.8
40°	1203.4	1094.4	1004.0	933.7	884.7	865.4	846.4
42.5°	1049.7	945.5	865.4	806.7	769.9	748.4	733.3
45°	852.8	760.9	698.2	655.7	626.4	609.7	600.2
47.5°	698.8	630.8	577.6	546.9	526.7	513.7	513.7
50°	616.2	551.2	515.9	491.6	474.1	463.8	465.7
52.5°	542.9	494.4	464.2	443.8	430.9	424.6	424.4
55°	454.0	419.0	399.3	384.4	375.7	368.5	370.0
57.5°	388.3	358.8	345.6	333.3	327.2	324.3	320.2
60°	347.6	324.8	313.4	303.5	297.4	295.2	291.0
62.5°	311.4	293.5	282.4	274.3	268.9	268.1	264.8
65°	261.7	248.1	238.2	234.4	228.7	227.2	227.2
67.5°	215.8	206.0	198.3	194.8	192.3	192.7	190.8
70°	186.9	178.9	174.0	170.2	168.3	168.7	167.1
72.5°	163.5	154.6	150.3	148.0	145.5	146.5	145.9
75°	123.8	119.3	117.0	114.7	113.2	112.4	111.7
77.5°	90.9	86.9	85.2	83.9	84.1	82.3	83.7
80°	70.3	66.9	65.7	63.8	63.4	63.4	63.1
82.5°	51.4	49.5	48.7	47.1	46.4	47.0	46.0
85°	26.6	25.1	24.7	24.7	23.9	23.2	25.1
87.5°	11.9	10.8	11.0	10.7	10.7	10.5	9.9
90°	10.8	11.4	12.5	12.5	12.5	13.1	13.1
92.5°	73.4	55.2	46.8	39.5	38.1	37.3	36.4
95°	323.4	253.3	205.4	164.9	147.7	143.2	134.1
97.5°	550.0	481.7	415.0	379.8	347.8	331.3	324.0
100°	673.7	614.9	555.6	516.2	475.2	454.1	444.9
102.5°	749.4	721.2	681.1	639.0	609.8	586.9	580.0
105°	792.3	817.4	811.1	792.9	774.1	762.7	755.8
107.5°	754.1	818.6	848.3	857.6	857.5	853.7	849.1
110°	710.8	791.2	839.7	865.3	876.2	880.2	880.2



TEST NUMBER: P333171

CATALOG NUMBER: S125DIP-S610D590U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	667.9	749.2	806.4	843.9	862.5	872.4	876.5
115°	606.4	684.5	746.7	791.2	818.6	834.5	842.0
117.5°	563.8	631.1	688.2	732.7	761.0	776.8	781.4
120°	539.6	602.4	652.6	694.8	722.2	737.6	742.1
122.5°	522.3	578.2	625.2	662.8	687.9	703.3	707.4
125°	499.1	548.8	589.8	621.8	645.2	657.7	663.4
127.5°	477.0	523.3	561.8	590.7	611.4	623.2	625.8
130°	461.5	506.0	543.0	571.6	590.4	601.8	605.2
132.5°	446.9	487.3	523.0	551.5	570.3	580.8	584.7
135°	424.4	460.9	493.4	518.5	537.3	547.6	551.0
137.5°	404.3	434.7	462.3	484.7	501.9	511.3	515.1
140°	392.5	418.7	442.7	463.8	478.6	487.1	490.0
142.5°	382.4	405.0	425.8	443.7	456.2	464.3	466.7
145°	369.6	387.3	402.7	416.4	426.1	432.4	434.7
147.5°	359.0	372.6	384.2	395.1	402.8	406.5	407.5
150°	353.1	363.9	374.2	382.8	389.6	391.9	392.5
152.5°	347.2	357.1	365.1	372.3	377.7	380.0	380.6
155°	338.3	346.2	352.5	358.2	362.2	363.9	364.5
157.5°	329.8	336.0	340.9	345.3	348.6	350.2	350.1
160°	323.4	329.1	333.1	337.1	340.0	341.1	340.5
162.5°	318.0	322.7	326.3	329.4	331.8	332.0	331.9
165°	309.7	313.2	316.0	318.3	319.4	319.4	319.4
167.5°	301.8	304.4	306.4	307.6	308.6	308.1	308.0
170°	297.2	298.9	300.0	301.2	301.8	301.8	301.2
172.5°	293.1	294.3	295.0	295.3	296.3	295.4	294.8
175°	286.9	288.1	288.1	288.1	288.6	287.5	286.9
177.5°	284.3	284.3	284.3	283.8	284.3	282.9	282.9
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9

(END OF REPORT)