

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333603

Luminaire Tested: **S125RDIP-S1090D1035U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333603
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1035U835-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7938.5 lumens
Efficiency: N/A
Efficacy: 131.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333603

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333603

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	53	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	56	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	32	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11544	11544	11544
5°	11570	11439	11509
10°	11482	11332	11332
15°	11346	11102	11012
20°	11171	10781	10652
25°	10967	10467	10236
30°	10712	10097	9775
35°	10452	9717	9260
40°	10209	9321	8752
45°	9913	8878	8199
50°	9616	8396	7623
55°	9272	7935	7007
60°	8928	7375	6347
65°	8520	6725	5590
70°	8055	5914	4817
75°	7411	4986	4007
80°	6527	3916	3362
85°	5498	3201	3001



TEST NUMBER: P333603

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.1	2.1
10°-20°	469.7	5.9
20°-30°	681.1	8.6
30°-40°	776.2	9.8
40°-50°	756.6	9.5
50°-60°	636.9	8.0
60°-70°	446.5	5.6
70°-80°	229.5	2.9
80°-90°	60.7	0.8
90°-100°	358.9	4.5
100°-110°	771.5	9.7
110°-120°	724.1	9.1
120°-130°	586.8	7.4
130°-140°	470.9	5.9
140°-150°	355.4	4.5
150°-160°	250.1	3.2
160°-170°	147.4	1.9
170°-180°	48.0	0.6
0°-30°	1318.9	16.6
0°-40°	2095.1	26.4
0°-60°	3488.6	43.9
0°-90°	4225.3	53.2
90°-120°	1854.5	23.4
90°-150°	3267.6	41.2
90°-180°	3713.0	46.8
0°-180°	7938.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1787	1787	1787	1787	1787	
5°	1785	1779	1764	1777	1775	169
15°	1697	1688	1660	1659	1647	478
25°	1539	1517	1469	1451	1436	708
35°	1326	1292	1232	1194	1174	830
45°	1085	1044	972	920	898	837
55°	824	778	705	646	622	736
65°	558	510	440	388	366	552
75°	297	256	200	171	161	314
85°	74	51	43	42	40	83
90°	1	9	16	21	23	5
95°	33	97	884	401	235	35
105°	113	158	724	1425	1323	119
115°	202	243	581	1252	1474	198
125°	280	327	557	996	1161	248
135°	327	394	553	835	964	254
145°	381	437	555	691	761	239
155°	435	468	541	611	638	200
165°	475	488	519	551	559	134
175°	494	494	498	504	502	47
180°	495	495	495	495	495	



TEST NUMBER: P333603

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1790.6	1789.9	1789.2	1788.4	1787.7	1786.2	1783.8	1781.4	1779.0	1776.6	1779.0
5°	1784.7	1783.5	1782.3	1781.1	1779.9	1777.6	1774.3	1771.0	1767.7	1764.4	1767.4
7.5°	1767.1	1766.0	1764.8	1763.7	1762.5	1760.0	1756.0	1752.1	1748.1	1744.2	1746.3
10°	1750.9	1750.0	1749.1	1748.2	1747.3	1744.8	1740.6	1736.4	1732.2	1728.0	1728.9
12.5°	1732.5	1731.4	1730.3	1729.1	1728.0	1724.6	1719.0	1713.3	1707.7	1702.0	1702.7
15°	1696.9	1695.1	1693.3	1691.5	1689.7	1685.7	1679.4	1673.1	1666.8	1660.5	1660.2
17.5°	1656.7	1653.9	1651.2	1648.4	1645.6	1640.3	1632.4	1624.5	1616.5	1608.6	1607.1
20°	1625.4	1622.4	1619.4	1616.4	1613.4	1607.1	1597.5	1587.9	1578.3	1568.7	1567.2
22.5°	1590.8	1587.8	1584.8	1581.8	1578.8	1572.3	1562.2	1552.1	1542.0	1531.9	1529.0
25°	1539.0	1534.5	1530.0	1525.5	1521.0	1513.2	1502.1	1491.0	1479.9	1468.8	1464.9
27.5°	1479.6	1474.1	1468.6	1463.2	1457.7	1449.1	1437.2	1425.3	1413.4	1401.5	1396.1
30°	1436.4	1430.7	1425.0	1419.3	1413.6	1404.4	1391.8	1379.2	1366.6	1354.0	1347.1
32.5°	1394.2	1387.6	1380.9	1374.3	1367.6	1357.9	1345.0	1332.2	1319.3	1306.5	1298.9
35°	1325.7	1318.5	1311.3	1304.1	1296.9	1286.5	1273.0	1259.5	1246.0	1232.5	1223.8
37.5°	1258.4	1249.7	1240.9	1232.2	1223.4	1212.1	1198.1	1184.2	1170.3	1156.4	1145.9
40°	1210.9	1201.9	1192.9	1183.9	1174.9	1163.2	1148.8	1134.4	1120.0	1105.6	1094.2
42.5°	1161.2	1152.0	1142.8	1133.5	1124.3	1112.2	1097.3	1082.5	1067.6	1052.7	1041.8
45°	1085.4	1076.7	1068.0	1059.3	1050.6	1038.0	1021.5	1005.0	988.5	972.0	960.0
47.5°	1006.8	997.6	988.4	979.3	970.1	957.2	940.6	923.9	907.3	890.7	878.3
50°	957.1	947.2	937.3	927.4	917.5	904.0	886.9	869.8	852.7	835.6	823.0
52.5°	903.1	893.0	882.8	872.7	862.6	849.4	833.3	817.1	801.0	784.9	771.3
55°	823.5	813.9	804.3	794.7	785.1	771.9	755.1	738.3	721.5	704.7	691.2
57.5°	743.0	732.8	722.5	712.2	702.0	688.8	672.6	656.4	640.2	624.0	610.8
60°	691.2	680.7	670.2	659.7	649.2	635.8	619.6	603.4	587.2	571.0	557.8
62.5°	636.1	626.1	616.1	606.0	596.0	582.8	566.4	549.9	533.5	517.0	504.8
65°	557.5	547.3	537.1	526.9	516.7	503.7	487.8	471.9	456.0	440.1	428.1
67.5°	479.5	469.3	459.1	448.9	438.7	426.0	410.7	395.5	380.3	365.0	354.1
70°	426.6	416.4	406.2	396.0	385.8	373.2	358.2	343.2	328.2	313.2	303.9
72.5°	374.8	364.8	354.8	344.9	334.9	322.9	308.9	294.8	280.8	266.8	258.2
75°	297.0	288.0	279.0	270.0	261.0	250.2	237.6	225.0	212.4	199.8	193.2
77.5°	219.8	212.6	205.4	198.2	191.0	182.3	172.3	162.2	152.1	142.0	137.4
80°	175.5	168.3	161.1	153.9	146.7	138.9	130.5	122.1	113.7	105.3	102.6
82.5°	132.3	125.8	119.3	112.9	106.4	100.3	94.5	88.7	83.0	77.2	76.0
85°	74.2	68.8	63.4	58.0	52.6	49.2	47.7	46.2	44.7	43.2	42.9
87.5°	25.0	23.6	22.3	21.0	19.7	19.2	19.1	19.3	19.2	19.4	19.6
90°	1.0	2.0	4.0	6.0	8.0	10.0	11.0	13.0	14.0	16.0	17.0
92.5°	12.2	14.8	23.2	35.5	52.7	81.9	136.4	227.8	327.0	321.8	260.5
95°	32.9	33.9	41.9	52.9	74.9	119.8	226.6	446.2	721.8	884.5	865.5
97.5°	54.7	55.9	61.5	72.5	92.2	124.6	195.3	356.2	644.5	944.6	1095.1
100°	69.9	71.9	75.9	86.8	105.8	135.8	193.7	323.4	575.0	901.4	1151.0
102.5°	86.7	87.8	91.0	102.8	120.2	149.3	200.9	309.9	522.3	825.6	1117.5
105°	112.8	112.8	117.8	127.8	143.8	171.7	215.6	304.5	471.2	723.7	1010.3
107.5°	138.4	140.4	145.1	153.3	169.9	195.1	237.6	313.7	449.6	653.7	900.8
110°	156.7	158.7	162.7	171.7	186.7	212.6	253.6	322.4	443.2	620.9	838.5



TEST NUMBER: P333603

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	175.1	177.1	180.3	189.3	204.2	229.4	268.7	333.6	443.2	601.8	792.2
115°	201.7	203.6	206.6	215.6	230.6	255.6	292.5	350.4	446.2	581.0	741.7
117.5°	225.6	228.6	231.8	240.8	257.8	281.9	316.9	369.6	452.8	570.8	711.6
120°	241.6	244.6	248.6	257.6	274.5	299.5	334.4	382.3	459.2	566.0	694.8
122.5°	258.4	260.5	263.7	272.7	291.3	316.3	351.2	396.7	464.8	562.0	680.4
125°	279.5	281.5	286.5	295.5	314.5	340.4	373.4	416.3	474.2	557.0	660.9
127.5°	296.1	299.1	305.5	316.9	337.0	363.0	394.7	434.2	484.8	554.6	642.9
130°	306.5	309.5	317.5	330.4	351.4	377.3	408.3	446.2	491.2	553.0	630.9
132.5°	314.5	318.2	327.8	342.4	364.2	390.1	421.1	456.6	498.3	553.0	621.3
135°	327.4	331.4	343.4	359.4	380.3	407.3	438.2	471.2	508.1	553.0	609.9
137.5°	343.8	346.8	358.0	374.0	394.5	422.3	450.4	482.0	517.1	554.2	599.8
140°	353.4	356.4	368.4	384.3	403.3	430.3	459.2	489.2	521.1	555.0	595.0
142.5°	364.6	366.8	377.9	393.9	412.1	437.4	464.8	493.1	523.5	555.8	591.0
145°	381.3	383.3	393.3	407.3	425.3	448.2	474.2	499.1	526.1	555.0	585.0
147.5°	398.9	400.1	408.7	421.7	437.2	457.4	480.2	502.7	527.1	552.4	578.8
150°	409.3	411.3	418.3	431.3	445.2	462.2	484.2	505.1	527.1	550.0	574.0
152.5°	420.5	421.7	427.9	439.2	452.4	467.8	488.2	506.7	526.3	546.9	568.4
155°	435.2	435.2	441.2	451.2	461.2	475.2	492.1	508.1	524.1	541.1	559.0
157.5°	448.4	448.2	453.0	461.6	470.4	481.0	495.5	509.1	521.5	535.1	550.2
160°	457.2	456.2	460.2	467.2	475.2	484.2	497.1	509.1	519.1	531.1	543.1
162.5°	464.4	463.4	467.4	473.6	480.0	487.4	498.7	508.3	516.7	526.3	536.7
165°	475.2	473.2	476.2	481.2	485.2	491.2	499.1	507.1	513.1	519.1	527.1
167.5°	482.4	481.4	483.2	486.0	488.8	492.5	499.1	504.7	507.5	512.1	517.7
170°	487.2	486.2	487.2	489.2	491.2	494.1	499.1	503.1	505.1	508.1	512.1
172.5°	490.4	488.6	489.6	491.5	492.7	494.1	498.3	501.5	501.9	503.3	506.5
175°	494.1	492.1	493.1	494.1	494.1	494.1	497.1	499.1	498.1	498.1	499.1
177.5°	495.9	494.3	494.3	495.1	494.3	494.3	495.9	496.7	495.1	495.1	495.9
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333603

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1781.4	1783.8	1786.2	1787.2	1787.0	1786.8	1786.5	1786.3
5°	1770.4	1773.4	1776.4	1777.6	1777.0	1776.4	1775.8	1775.2
7.5°	1748.4	1750.5	1752.6	1753.3	1752.6	1752.0	1751.3	1750.6
10°	1729.8	1730.7	1731.6	1731.6	1730.7	1729.8	1728.9	1728.0
12.5°	1703.4	1704.0	1704.7	1704.3	1702.9	1701.6	1700.2	1698.8
15°	1659.9	1659.6	1659.3	1657.8	1655.1	1652.4	1649.7	1647.0
17.5°	1605.6	1604.1	1602.6	1600.8	1598.5	1596.3	1594.1	1591.9
20°	1565.7	1564.2	1562.7	1560.6	1557.9	1555.2	1552.5	1549.8
22.5°	1526.1	1523.1	1520.2	1517.6	1515.4	1513.2	1510.9	1508.7
25°	1461.0	1457.1	1453.2	1449.6	1446.3	1443.0	1439.7	1436.4
27.5°	1390.6	1385.2	1379.7	1375.4	1372.2	1369.0	1365.8	1362.7
30°	1340.2	1333.3	1326.4	1321.6	1318.9	1316.2	1313.5	1310.8
32.5°	1291.3	1283.6	1276.0	1270.5	1267.1	1263.7	1260.2	1256.8
35°	1215.1	1206.4	1197.7	1191.3	1187.1	1182.9	1178.7	1174.5
37.5°	1135.5	1125.1	1114.6	1107.4	1103.3	1099.2	1095.1	1091.0
40°	1082.8	1071.4	1060.0	1052.5	1048.9	1045.3	1041.7	1038.1
42.5°	1030.9	1019.9	1009.0	1000.9	995.6	990.4	985.1	979.8
45°	948.0	936.0	924.0	915.7	911.2	906.7	902.2	897.7
47.5°	866.0	853.6	841.3	832.6	827.6	822.6	817.7	812.7
50°	810.4	797.8	785.2	776.7	772.2	767.7	763.2	758.7
52.5°	757.8	744.2	730.6	721.6	717.1	712.6	708.1	703.6
55°	677.7	664.2	650.7	641.5	636.7	631.9	627.1	622.3
57.5°	597.6	584.4	571.2	562.4	558.2	553.9	549.6	545.4
60°	544.6	531.4	518.2	509.4	504.9	500.4	495.9	491.4
62.5°	492.6	480.3	468.1	459.7	455.2	450.7	446.2	441.7
65°	416.1	404.1	392.1	383.8	379.3	374.8	370.3	365.8
67.5°	343.1	332.1	321.1	313.8	310.2	306.6	303.0	299.4
70°	294.6	285.3	276.0	269.5	265.9	262.3	258.7	255.1
72.5°	249.6	241.0	232.4	226.9	224.5	222.1	219.7	217.3
75°	186.6	180.0	173.4	169.0	166.9	164.8	162.7	160.6
77.5°	132.8	128.2	123.5	120.4	118.9	117.3	115.8	114.2
80°	99.9	97.2	94.5	92.8	92.2	91.6	91.0	90.4
82.5°	74.7	73.4	72.2	71.4	71.0	70.6	70.3	69.9
85°	42.6	42.3	42.0	41.7	41.4	41.1	40.8	40.5
87.5°	19.8	20.0	20.2	20.5	20.2	20.0	20.0	19.7
90°	18.0	19.0	20.0	22.0	22.0	22.0	23.0	23.0
92.5°	176.9	128.4	96.6	81.9	69.1	66.7	65.3	63.7
95°	717.8	566.0	443.2	359.4	288.5	258.6	250.6	234.6
97.5°	1069.0	962.5	842.9	726.3	664.7	608.7	579.8	567.0
100°	1227.9	1179.0	1076.1	972.3	903.4	831.6	794.6	778.7
102.5°	1281.4	1311.5	1262.2	1191.9	1118.3	1067.2	1027.0	1015.0
105°	1249.8	1386.6	1430.5	1419.5	1387.6	1354.7	1334.7	1322.7
107.5°	1137.2	1319.7	1432.5	1484.6	1500.8	1500.6	1494.0	1486.0
110°	1054.2	1243.8	1384.6	1469.5	1514.4	1533.3	1540.3	1540.3



TEST NUMBER: P333603

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	988.7	1168.8	1311.1	1411.2	1476.8	1509.4	1526.8	1533.9
115°	906.4	1061.2	1197.9	1306.7	1384.6	1432.5	1460.5	1473.5
117.5°	853.3	986.7	1104.5	1204.3	1282.2	1331.7	1359.4	1367.4
120°	824.6	944.4	1054.2	1142.0	1215.9	1263.8	1290.8	1298.8
122.5°	803.0	914.0	1011.8	1094.1	1160.0	1203.9	1230.9	1238.1
125°	771.7	873.5	960.3	1032.2	1088.1	1129.0	1151.0	1161.0
127.5°	739.7	834.8	915.8	983.1	1033.8	1069.9	1090.7	1095.1
130°	719.8	807.6	885.5	950.4	1000.3	1033.2	1053.2	1059.2
132.5°	699.8	782.0	852.7	915.2	965.1	998.1	1016.4	1023.2
135°	673.8	742.7	806.6	863.5	907.4	940.4	958.3	964.3
137.5°	651.9	707.6	760.7	809.0	848.3	878.3	894.9	901.4
140°	639.9	686.8	732.7	774.7	811.6	837.6	852.5	857.5
142.5°	629.5	669.2	708.8	745.1	776.5	798.4	812.6	816.8
145°	615.9	646.9	677.8	704.8	728.7	745.7	756.7	760.7
147.5°	603.2	628.3	652.1	672.4	691.4	705.0	711.4	713.2
150°	596.0	617.9	636.9	654.9	669.8	681.8	685.8	686.8
152.5°	588.0	607.5	624.9	638.9	651.5	661.1	665.0	666.0
155°	576.0	592.0	606.0	616.9	626.9	633.9	636.9	637.9
157.5°	564.0	577.2	588.0	596.6	604.4	610.1	612.9	612.7
160°	556.0	566.0	576.0	583.0	590.0	595.0	597.0	596.0
162.5°	547.3	556.4	564.8	571.0	576.4	580.6	581.0	580.8
165°	535.1	542.1	548.1	553.0	557.0	559.0	559.0	559.0
167.5°	523.5	528.1	532.7	536.3	538.3	540.1	539.3	539.1
170°	517.1	520.1	523.1	525.1	527.1	528.1	528.1	527.1
172.5°	509.9	512.9	515.1	516.3	516.7	518.5	516.9	515.9
175°	502.1	502.1	504.1	504.1	504.1	505.1	503.1	502.1
177.5°	496.7	497.5	497.5	497.5	496.7	497.5	495.1	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1

(END OF REPORT)