

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333606

Luminaire Tested: **S125RDIP-S1090D1205U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333606
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8585.0 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43
2	90	83	77	72	83	76	71	67	65	61	58	54	52	49	44	43	41	36
3	82	73	66	60	75	68	61	56	58	53	49	48	45	42	40	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	25	21	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10619	10619	10619	10619
5°	12217	10633	9390	10633
10°	14014	10579	8286	10579
15°	15136	10470	7365	10470
20°	16690	10344	6801	10344
25°	19316	10177	6310	10177
30°	21020	10001	5990	10001
35°	17731	9797	5694	9797
40°	12382	9429	5440	9429
45°	9186	8933	5191	8933
50°	7324	8416	4977	8416
55°	6217	7775	4788	7775
60°	5371	7201	4481	7201
65°	4786	6580	3857	6580
70°	4205	6027	3518	6027
75°	3638	5220	3301	5220
80°	2760	4392	2760	4392
85°	2297	3453	2601	3453



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	1.8
10°-20°	462.1	5.4
20°-30°	732.6	8.5
30°-40°	883.5	10.3
40°-50°	789.0	9.2
50°-60°	605.0	7.0
60°-70°	393.2	4.6
70°-80°	191.2	2.2
80°-90°	48.8	0.6
90°-100°	417.8	4.9
100°-110°	898.0	10.5
110°-120°	842.8	9.8
120°-130°	683.0	8.0
130°-140°	548.1	6.4
140°-150°	413.6	4.8
150°-160°	291.2	3.4
160°-170°	171.6	2.0
170°-180°	55.8	0.7
0°-30°	1352.3	15.8
0°-40°	2235.8	26.0
0°-60°	3629.8	42.3
0°-90°	4263.0	49.7
90°-120°	2158.6	25.1
90°-150°	3803.4	44.3
90°-180°	4322.0	50.3
0°-180°	8585.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1884	1640	1448	1640	1884	188
15°	2264	1566	1102	1566	2264	649
25°	2711	1428	886	1428	2711	1245
35°	2249	1243	722	1243	2249	1358
45°	1006	978	568	978	1006	802
55°	552	690	425	690	552	501
65°	313	431	252	431	313	312
75°	146	209	132	209	146	155
85°	31	47	35	47	31	36
90°	27	1	27	1	27	20
95°	273	38	273	38	273	387
105°	1540	131	1540	131	1540	1530
115°	1715	235	1715	235	1715	1676
125°	1351	325	1351	325	1351	1223
135°	1122	381	1122	381	1122	870
145°	885	444	885	444	885	563
155°	742	507	742	507	742	346
165°	651	553	651	553	651	186
175°	584	575	584	575	584	57
180°	576	576	576	576	576	



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1729.5	1728.4	1730.6	1724.6	1725.2	1716.0	1716.0	1709.0	1699.8	1692.8	1689.5
5°	1884.4	1885.8	1883.1	1873.0	1866.2	1856.1	1844.6	1824.4	1807.5	1791.3	1778.5
7.5°	2044.0	2044.9	2036.0	2032.9	2015.9	2003.5	1978.0	1950.4	1926.0	1895.0	1871.2
10°	2136.9	2136.2	2126.7	2119.3	2104.5	2085.6	2060.6	2028.2	1997.8	1964.1	1931.7
12.5°	2190.9	2189.1	2186.1	2177.1	2163.3	2146.6	2125.4	2093.5	2056.1	2019.2	1981.4
15°	2263.8	2259.0	2250.3	2238.8	2219.2	2199.6	2176.0	2147.7	2111.9	2070.0	2035.0
17.5°	2353.9	2354.1	2340.6	2324.6	2298.0	2263.5	2227.0	2181.3	2132.7	2086.7	2049.3
20°	2428.4	2426.4	2412.9	2381.9	2351.5	2308.3	2266.5	2210.4	2151.0	2091.0	2044.4
22.5°	2535.4	2530.1	2516.0	2475.3	2428.2	2372.6	2308.6	2240.1	2168.3	2100.1	2039.0
25°	2710.6	2706.5	2678.8	2631.6	2565.5	2479.7	2396.0	2302.2	2199.0	2109.2	2035.0
27.5°	2830.4	2826.0	2805.5	2766.2	2705.2	2615.0	2501.7	2376.3	2247.4	2123.9	2016.9
30°	2818.6	2828.7	2826.0	2807.8	2761.9	2680.9	2576.3	2435.2	2282.0	2136.9	2009.3
32.5°	2649.0	2658.1	2681.8	2717.6	2720.3	2687.9	2609.7	2479.5	2320.9	2155.8	2003.4
35°	2248.9	2261.1	2307.0	2379.2	2473.7	2552.6	2568.8	2498.6	2356.2	2178.7	1994.5
37.5°	1728.9	1795.3	1834.0	1910.0	2052.8	2198.0	2337.7	2389.2	2328.5	2169.3	1980.0
40°	1468.7	1484.9	1553.7	1639.4	1759.6	1910.8	2109.9	2253.6	2258.4	2147.7	1957.3
42.5°	1257.0	1277.5	1324.8	1393.2	1496.1	1647.3	1852.9	2042.5	2130.4	2088.3	1927.6
45°	1005.7	1021.2	1055.6	1108.3	1187.2	1312.1	1488.9	1708.3	1882.4	1950.6	1848.0
47.5°	826.1	834.5	864.5	904.6	963.0	1054.0	1190.9	1381.3	1590.2	1736.6	1722.2
50°	728.9	738.4	761.3	791.7	841.0	917.9	1027.3	1185.9	1401.2	1580.0	1615.8
52.5°	653.3	661.2	675.5	704.2	744.9	804.0	892.3	1035.8	1229.5	1419.7	1502.4
55°	552.1	557.5	569.0	585.2	617.6	660.1	736.4	835.6	992.2	1183.8	1305.3
57.5°	468.7	471.4	478.7	493.7	516.1	547.1	602.2	686.3	798.6	971.2	1105.3
60°	415.8	418.5	427.9	438.0	455.6	483.9	527.1	585.8	693.8	836.3	971.9
62.5°	373.6	375.3	379.3	389.4	404.8	426.7	460.7	508.6	594.5	719.6	847.7
65°	313.2	313.8	315.2	323.3	332.7	348.9	371.2	405.0	469.8	564.3	677.6
67.5°	255.1	256.1	260.8	263.6	273.5	282.0	295.1	320.9	366.5	430.2	518.4
70°	222.7	222.1	226.8	230.2	233.5	243.7	252.4	273.4	301.7	350.3	423.9
72.5°	192.5	190.7	192.8	194.0	198.4	205.3	214.1	226.9	248.8	282.3	338.6
75°	145.8	146.5	146.5	147.8	151.2	153.9	156.6	163.3	175.5	197.8	228.1
77.5°	102.3	101.2	104.1	104.5	106.5	109.5	111.8	114.5	119.5	128.6	144.3
80°	74.2	74.2	74.9	76.9	76.3	77.6	81.0	83.7	89.8	95.2	100.6
82.5°	57.0	56.4	57.1	57.5	57.4	58.7	59.9	60.5	62.8	65.5	69.2
85°	31.0	31.0	31.7	31.7	32.4	32.4	33.1	33.1	33.1	33.7	34.4
87.5°	17.2	16.7	15.9	15.9	16.5	17.1	16.3	15.5	15.3	15.1	15.1
90°	26.7	26.7	25.6	25.6	25.6	23.2	22.1	20.9	19.8	18.6	16.3
92.5°	74.1	76.0	77.6	80.4	95.3	112.5	149.4	205.9	303.3	374.6	380.7
95°	273.1	291.7	300.9	335.8	418.3	515.9	658.8	835.4	1007.4	1029.5	840.1
97.5°	660.0	674.9	708.6	773.6	845.4	981.2	1120.4	1244.2	1274.7	1099.4	750.2
100°	906.3	924.9	967.9	1051.6	1131.7	1252.6	1372.3	1429.2	1339.7	1049.2	669.3
102.5°	1181.5	1195.4	1242.1	1301.6	1387.4	1469.2	1526.6	1491.5	1300.7	960.9	607.9
105°	1539.6	1553.5	1576.8	1615.1	1652.3	1665.1	1614.0	1454.8	1175.9	842.4	548.4
107.5°	1729.7	1739.0	1746.7	1746.9	1728.1	1667.4	1536.1	1323.7	1048.6	760.8	523.3
110°	1792.9	1792.9	1784.8	1762.7	1710.4	1611.6	1447.8	1227.0	976.0	722.7	515.9



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1785.5	1777.1	1756.9	1719.0	1642.5	1526.1	1360.4	1150.8	922.1	700.4	515.9
115°	1715.0	1699.9	1667.4	1611.6	1521.0	1394.3	1235.2	1055.1	863.3	676.3	519.4
117.5°	1591.6	1582.4	1550.1	1492.4	1401.8	1285.6	1148.5	993.2	828.2	664.4	527.1
120°	1511.7	1502.4	1471.0	1415.3	1329.3	1227.0	1099.2	959.8	808.7	658.8	534.5
122.5°	1441.1	1432.7	1401.3	1350.2	1273.5	1177.8	1063.9	934.7	792.0	654.2	541.0
125°	1351.4	1339.7	1314.2	1266.5	1201.5	1117.8	1016.7	898.2	769.2	648.4	551.9
127.5°	1274.7	1269.6	1245.4	1203.3	1144.3	1066.0	971.6	861.0	748.3	645.6	564.2
130°	1232.8	1225.9	1202.6	1164.3	1106.2	1030.7	940.0	837.8	734.4	643.7	571.7
132.5°	1191.0	1183.1	1161.7	1123.4	1065.3	992.5	910.3	814.5	723.2	643.7	580.0
135°	1122.5	1115.5	1094.6	1056.2	1005.1	938.9	864.5	784.3	710.0	643.7	591.4
137.5°	1049.2	1041.6	1022.3	987.4	941.7	885.4	823.6	758.8	698.1	645.1	601.9
140°	998.1	992.3	974.9	944.7	901.7	852.9	799.4	744.8	692.5	646.0	606.5
142.5°	950.7	945.8	929.3	903.8	867.3	825.0	779.0	732.7	687.9	647.0	609.3
145°	885.4	880.8	868.0	848.2	820.3	789.0	752.9	716.9	680.9	646.0	612.4
147.5°	830.1	828.0	820.6	804.8	782.7	759.0	731.3	702.1	673.7	643.0	613.5
150°	799.4	798.3	793.6	779.7	762.2	741.3	719.3	693.7	668.1	640.2	613.5
152.5°	775.3	774.1	769.4	758.3	743.7	727.4	707.2	684.4	661.6	636.5	612.6
155°	742.5	741.3	737.8	729.7	718.1	705.3	689.0	670.4	650.7	629.8	610.0
157.5°	713.2	713.4	710.2	703.4	694.4	684.4	671.8	656.5	640.5	622.8	607.0
160°	693.7	694.9	692.5	686.7	678.6	670.4	658.8	647.2	632.1	618.2	604.2
162.5°	676.0	676.3	675.8	670.9	664.6	657.4	647.7	637.0	624.7	612.6	601.4
165°	650.7	650.7	650.7	648.4	643.7	637.9	630.9	622.8	613.5	604.2	597.2
167.5°	627.5	627.7	628.6	626.5	624.2	620.0	614.7	609.3	602.6	596.1	590.7
170°	613.5	614.7	614.7	613.5	611.2	608.9	605.4	601.9	596.1	591.4	588.0
172.5°	600.5	601.7	603.5	601.4	601.0	599.6	597.0	593.5	589.6	585.9	584.2
175°	584.5	585.6	588.0	586.8	586.8	586.8	584.5	584.5	581.0	579.8	579.8
177.5°	576.3	576.3	579.1	578.2	579.1	579.1	579.1	578.2	577.3	576.3	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1689.5	1685.7	1678.7	1672.2	1664.1	1657.1	1652.3	1646.3	1638.8	1629.6	1622.0
5°	1764.3	1749.4	1729.9	1713.0	1691.4	1674.5	1657.0	1640.1	1623.2	1601.6	1582.7
7.5°	1847.2	1816.5	1786.7	1749.2	1715.2	1684.8	1655.6	1626.1	1597.2	1566.5	1537.0
10°	1897.9	1860.8	1819.6	1772.4	1729.2	1688.0	1650.2	1613.1	1574.0	1539.5	1502.4
12.5°	1945.5	1897.5	1850.4	1790.8	1738.9	1688.6	1640.5	1594.2	1552.4	1507.7	1467.9
15°	1988.4	1941.1	1888.5	1815.6	1743.4	1682.6	1625.9	1565.9	1513.9	1463.9	1419.4
17.5°	2005.0	1955.4	1894.3	1824.2	1745.3	1668.9	1595.8	1530.0	1468.8	1410.6	1360.5
20°	1998.5	1950.6	1887.8	1821.0	1736.6	1657.0	1578.0	1505.1	1437.0	1375.5	1322.2
22.5°	1982.8	1933.3	1872.7	1802.1	1722.0	1637.5	1553.2	1475.4	1404.0	1340.4	1282.3
25°	1959.4	1891.9	1829.8	1760.9	1684.7	1601.0	1513.9	1428.2	1351.9	1287.1	1223.7
27.5°	1934.9	1850.7	1771.7	1703.3	1622.7	1548.0	1464.1	1376.2	1296.0	1230.0	1164.9
30°	1912.8	1818.3	1731.2	1653.6	1577.3	1506.5	1426.8	1341.1	1258.8	1190.6	1124.5
32.5°	1885.2	1784.8	1689.1	1599.6	1526.0	1455.7	1383.6	1301.7	1221.5	1151.2	1084.0
35°	1850.7	1722.5	1618.5	1523.3	1441.7	1373.5	1308.7	1242.6	1162.3	1089.4	1023.9
37.5°	1805.3	1659.8	1539.5	1435.9	1349.7	1281.3	1230.1	1169.7	1096.4	1026.6	965.8
40°	1777.8	1614.5	1482.8	1380.3	1289.8	1217.6	1169.7	1118.4	1051.6	986.1	925.3
42.5°	1741.1	1572.9	1425.6	1318.7	1227.7	1158.2	1109.7	1064.9	1008.9	947.2	882.1
45°	1669.1	1492.3	1337.7	1223.0	1131.2	1063.0	1017.8	978.0	935.5	878.8	822.1
47.5°	1575.4	1408.2	1246.5	1121.2	1031.3	968.0	924.1	892.7	862.3	814.1	759.0
50°	1500.4	1339.1	1181.1	1059.7	963.8	903.7	862.6	837.6	809.9	766.1	720.2
52.5°	1411.8	1267.8	1113.1	988.9	898.5	842.2	802.6	777.7	754.9	719.1	675.3
55°	1272.3	1146.1	1004.3	891.6	808.6	751.9	714.1	690.5	677.0	646.6	612.2
57.5°	1111.2	1020.8	895.8	787.1	713.7	657.7	630.0	609.9	594.6	573.2	548.9
60°	998.9	935.5	823.4	720.2	652.7	599.3	574.4	557.5	543.3	525.1	506.2
62.5°	885.0	838.8	741.4	652.7	590.6	545.9	522.5	507.3	491.0	478.7	460.3
65°	732.3	691.1	623.6	554.1	496.8	461.0	444.1	430.6	420.5	407.0	394.2
67.5°	569.7	552.9	506.3	458.4	417.2	385.4	370.8	361.4	349.2	341.1	332.3
70°	469.8	461.7	428.6	396.9	358.4	336.8	323.3	319.2	304.4	296.3	290.2
72.5°	381.2	377.4	358.4	336.4	309.3	290.4	277.9	273.4	263.9	257.4	253.5
75°	261.2	262.6	259.2	245.0	234.9	222.7	211.9	209.2	202.5	197.1	193.7
77.5°	165.2	172.1	172.4	171.7	167.7	160.2	155.8	153.8	147.1	145.1	144.3
80°	113.4	120.8	127.6	126.9	125.5	123.5	120.1	118.1	114.7	112.7	111.4
82.5°	75.6	82.5	88.1	91.8	91.5	89.5	87.2	86.3	85.6	84.1	83.8
85°	35.8	37.1	39.1	43.9	47.2	47.9	47.2	46.6	44.5	45.2	45.9
87.5°	15.4	15.0	15.3	14.8	13.8	16.0	17.2	17.5	16.7	16.0	15.4
90°	15.1	12.8	11.6	9.3	7.0	4.6	2.3	1.2	2.3	4.6	7.0
92.5°	265.2	158.7	95.3	61.4	41.4	27.0	17.2	14.2	17.2	27.0	41.4
95°	519.4	263.8	139.4	87.1	61.6	48.8	39.5	38.3	39.5	48.8	61.6
97.5°	414.6	227.3	145.0	107.4	84.4	71.6	65.1	63.7	65.1	71.6	84.4
100°	376.5	225.4	158.0	123.2	101.1	88.3	83.7	81.3	83.7	88.3	101.1
102.5°	360.7	233.8	173.8	139.9	119.7	106.0	102.3	100.9	102.3	106.0	119.7
105°	354.4	251.0	199.9	167.3	148.7	137.1	131.3	131.3	131.3	137.1	148.7
107.5°	365.1	276.5	227.0	197.8	178.5	168.9	163.4	161.0	163.4	168.9	178.5
110°	375.3	295.1	247.5	217.3	199.9	189.4	184.8	182.4	184.8	189.4	199.9



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	388.3	312.8	267.0	237.7	220.3	209.8	206.1	203.8	206.1	209.8	220.3
115°	407.8	340.5	297.5	268.4	251.0	240.5	237.0	234.7	237.0	240.5	251.0
117.5°	430.2	368.8	328.1	300.0	280.3	269.8	266.1	262.6	266.1	269.8	280.3
120°	445.0	389.3	348.6	319.5	299.8	289.3	284.7	281.2	284.7	289.3	299.8
122.5°	461.8	408.8	368.1	339.1	317.4	307.0	303.3	300.7	303.3	307.0	317.4
125°	484.5	434.6	396.2	366.0	343.9	333.5	327.7	325.3	327.7	333.5	343.9
127.5°	505.5	459.4	422.5	392.3	368.8	355.6	348.1	344.6	348.1	355.6	368.8
130°	519.4	475.2	439.2	409.0	384.6	369.5	360.2	356.7	360.2	369.5	384.6
132.5°	531.5	490.1	454.1	423.9	398.6	381.6	370.4	366.0	370.4	381.6	398.6
135°	548.4	510.1	474.1	442.7	418.3	399.7	385.8	381.1	385.8	399.7	418.3
137.5°	561.0	524.3	491.5	459.2	435.3	416.7	403.7	400.2	403.7	416.7	435.3
140°	569.4	534.5	500.8	469.4	447.4	428.8	414.8	411.3	414.8	428.8	447.4
142.5°	574.0	541.0	509.2	479.7	458.5	439.9	426.9	424.3	426.9	439.9	458.5
145°	581.0	551.9	521.7	495.0	474.1	457.8	446.2	443.9	446.2	457.8	474.1
147.5°	585.2	558.9	532.4	508.9	490.8	475.7	465.7	464.3	465.7	475.7	490.8
150°	588.0	563.5	538.0	518.2	502.0	486.9	478.7	476.4	478.7	486.9	502.0
152.5°	589.8	568.2	544.5	526.6	511.3	498.0	490.8	489.4	490.8	498.0	511.3
155°	591.4	572.8	553.1	536.8	525.2	513.6	506.6	506.6	506.6	513.6	525.2
157.5°	592.6	576.8	559.8	547.5	537.3	527.3	521.7	522.0	521.7	527.3	537.3
160°	592.6	578.7	563.5	553.1	543.8	535.7	531.0	532.2	531.0	535.7	543.8
162.5°	591.7	580.5	567.3	558.7	551.2	544.0	539.4	540.5	539.4	544.0	551.2
165°	590.3	581.0	571.7	564.7	560.1	554.3	550.8	553.1	550.8	554.3	560.1
167.5°	587.5	581.0	573.3	568.9	565.6	562.4	560.3	561.5	560.3	562.4	565.6
170°	585.6	581.0	575.2	571.7	569.4	567.0	565.9	567.0	565.9	567.0	569.4
172.5°	583.8	580.0	575.2	573.5	572.1	569.8	568.7	570.8	568.7	569.8	572.1
175°	581.0	578.7	575.2	575.2	575.2	574.0	572.8	575.2	572.8	574.0	575.2
177.5°	578.2	577.3	575.4	575.4	576.3	575.4	575.4	577.3	575.4	575.4	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1616.6	1609.1	1603.7	1592.9	1585.3	1582.1	1576.1	1574.5	1580.4	1576.1	1575.6
5°	1568.6	1549.0	1533.5	1517.9	1501.1	1490.3	1474.1	1471.4	1467.3	1461.2	1459.9
7.5°	1510.9	1485.4	1465.4	1439.8	1417.5	1399.6	1379.3	1369.7	1364.5	1356.6	1346.1
10°	1472.0	1441.7	1414.7	1389.0	1361.4	1339.1	1318.8	1303.3	1293.2	1283.7	1279.7
12.5°	1433.7	1402.8	1368.2	1337.2	1306.3	1281.3	1258.9	1248.8	1237.6	1226.5	1217.1
15°	1374.2	1333.0	1295.2	1259.4	1233.1	1206.1	1184.5	1169.7	1152.8	1148.1	1129.9
17.5°	1311.0	1270.6	1226.4	1188.7	1158.2	1128.5	1104.7	1087.9	1075.2	1057.8	1049.4
20°	1271.6	1223.7	1180.5	1146.1	1112.3	1077.2	1052.9	1038.7	1026.6	1012.4	1005.7
22.5°	1229.5	1182.6	1138.4	1098.0	1063.7	1029.2	1011.9	997.2	983.4	970.3	961.4
25°	1167.6	1120.4	1073.8	1032.0	996.2	971.2	951.0	934.1	926.7	913.9	904.4
27.5°	1106.5	1056.3	1008.0	966.2	938.2	913.5	896.9	883.5	870.1	858.9	850.7
30°	1067.1	1015.8	963.1	930.1	900.4	876.7	858.5	845.7	835.6	825.5	819.4
32.5°	1027.7	974.8	928.0	892.3	864.2	843.8	825.0	812.8	802.1	790.9	783.7
35°	964.5	910.5	872.7	837.6	809.9	791.0	778.2	760.7	751.9	743.8	736.4
37.5°	905.8	855.6	814.7	783.9	759.8	741.1	724.5	715.0	704.2	696.9	690.7
40°	862.6	816.7	779.6	747.2	729.6	708.7	693.2	681.0	672.9	663.5	656.7
42.5°	823.7	781.0	745.0	715.8	694.0	676.3	661.3	649.2	638.9	632.2	626.5
45°	768.8	726.2	691.1	664.1	643.9	627.0	611.5	605.4	591.9	583.8	581.1
47.5°	711.9	673.9	640.0	615.1	594.4	578.4	563.8	551.4	544.0	536.0	531.7
50°	673.6	637.1	605.4	581.1	560.9	543.3	529.8	521.7	511.6	504.2	498.8
52.5°	635.3	601.5	569.8	546.6	529.0	511.5	496.4	488.3	478.7	473.9	470.2
55°	580.5	544.7	517.7	494.7	476.5	460.3	446.1	438.0	432.0	427.2	425.9
57.5°	518.4	490.0	464.9	444.2	425.3	410.1	397.7	390.0	384.6	383.9	379.9
60°	477.9	452.2	429.3	407.0	390.8	376.6	365.8	357.0	351.6	351.0	349.6
62.5°	437.4	412.8	391.5	371.9	357.3	343.7	333.4	323.6	320.3	317.0	314.0
65°	377.3	355.0	337.5	321.9	306.4	294.9	284.8	278.8	271.3	267.3	259.9
67.5°	318.3	301.0	284.2	271.1	258.9	248.0	239.6	230.6	225.6	222.3	216.9
70°	279.4	265.9	249.1	234.9	225.4	216.7	209.9	199.8	196.4	193.7	191.0
72.5°	242.7	230.8	216.7	205.2	195.7	187.5	179.7	174.9	171.6	168.9	167.3
75°	191.0	179.5	167.4	159.3	152.5	145.8	141.7	138.4	137.0	136.3	133.6
77.5°	140.3	134.2	124.5	118.0	113.5	110.8	107.2	105.4	105.3	102.3	101.4
80°	107.3	103.9	95.8	93.1	89.8	87.1	85.0	81.7	78.3	76.9	74.9
82.5°	79.8	76.4	73.2	68.8	66.0	64.4	62.4	61.1	61.6	59.7	58.7
85°	42.5	39.1	37.8	37.1	35.8	37.1	36.4	35.8	35.1	34.4	35.1
87.5°	15.4	15.8	15.5	17.1	15.7	16.7	16.9	16.6	16.8	17.1	17.0
90°	9.3	11.6	12.8	15.1	16.3	18.6	19.8	20.9	22.1	23.2	25.6
92.5°	61.4	95.3	158.7	265.2	380.7	374.6	303.3	205.9	149.4	112.5	95.3
95°	87.1	139.4	263.8	519.4	840.1	1029.5	1007.4	835.4	658.8	515.9	418.3
97.5°	107.4	145.0	227.3	414.6	750.2	1099.4	1274.7	1244.2	1120.4	981.2	845.4
100°	123.2	158.0	225.4	376.5	669.3	1049.2	1339.7	1429.2	1372.3	1252.6	1131.7
102.5°	139.9	173.8	233.8	360.7	607.9	960.9	1300.7	1491.5	1526.6	1469.2	1387.4
105°	167.3	199.9	251.0	354.4	548.4	842.4	1175.9	1454.8	1614.0	1665.1	1652.3
107.5°	197.8	227.0	276.5	365.1	523.3	760.8	1048.6	1323.7	1536.1	1667.4	1728.1
110°	217.3	247.5	295.1	375.3	515.9	722.7	976.0	1227.0	1447.8	1611.6	1710.4



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	237.7	267.0	312.8	388.3	515.9	700.4	922.1	1150.8	1360.4	1526.1	1642.5
115°	268.4	297.5	340.5	407.8	519.4	676.3	863.3	1055.1	1235.2	1394.3	1521.0
117.5°	300.0	328.1	368.8	430.2	527.1	664.4	828.2	993.2	1148.5	1285.6	1401.8
120°	319.5	348.6	389.3	445.0	534.5	658.8	808.7	959.8	1099.2	1227.0	1329.3
122.5°	339.1	368.1	408.8	461.8	541.0	654.2	792.0	934.7	1063.9	1177.8	1273.5
125°	366.0	396.2	434.6	484.5	551.9	648.4	769.2	898.2	1016.7	1117.8	1201.5
127.5°	392.3	422.5	459.4	505.5	564.2	645.6	748.3	861.0	971.6	1066.0	1144.3
130°	409.0	439.2	475.2	519.4	571.7	643.7	734.4	837.8	940.0	1030.7	1106.2
132.5°	423.9	454.1	490.1	531.5	580.0	643.7	723.2	814.5	910.3	992.5	1065.3
135°	442.7	474.1	510.1	548.4	591.4	643.7	710.0	784.3	864.5	938.9	1005.1
137.5°	459.2	491.5	524.3	561.0	601.9	645.1	698.1	758.8	823.6	885.4	941.7
140°	469.4	500.8	534.5	569.4	606.5	646.0	692.5	744.8	799.4	852.9	901.7
142.5°	479.7	509.2	541.0	574.0	609.3	647.0	687.9	732.7	779.0	825.0	867.3
145°	495.0	521.7	551.9	581.0	612.4	646.0	680.9	716.9	752.9	789.0	820.3
147.5°	508.9	532.4	558.9	585.2	613.5	643.0	673.7	702.1	731.3	759.0	782.7
150°	518.2	538.0	563.5	588.0	613.5	640.2	668.1	693.7	719.3	741.3	762.2
152.5°	526.6	544.5	568.2	589.8	612.6	636.5	661.6	684.4	707.2	727.4	743.7
155°	536.8	553.1	572.8	591.4	610.0	629.8	650.7	670.4	689.0	705.3	718.1
157.5°	547.5	559.8	576.8	592.6	607.0	622.8	640.5	656.5	671.8	684.4	694.4
160°	553.1	563.5	578.7	592.6	604.2	618.2	632.1	647.2	658.8	670.4	678.6
162.5°	558.7	567.3	580.5	591.7	601.4	612.6	624.7	637.0	647.7	657.4	664.6
165°	564.7	571.7	581.0	590.3	597.2	604.2	613.5	622.8	630.9	637.9	643.7
167.5°	568.9	573.3	581.0	587.5	590.7	596.1	602.6	609.3	614.7	620.0	624.2
170°	571.7	575.2	581.0	585.6	588.0	591.4	596.1	601.9	605.4	608.9	611.2
172.5°	573.5	575.2	580.0	583.8	584.2	585.9	589.6	593.5	597.0	599.6	601.0
175°	575.2	575.2	578.7	581.0	579.8	579.8	581.0	584.5	584.5	586.8	586.8
177.5°	575.4	575.4	577.3	578.2	576.3	576.3	577.3	578.2	579.1	579.1	579.1
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1575.0	1569.1	1567.5	1569.6	1567.5	1569.1	1575.0	1575.6	1576.1	1580.4	1574.5
5°	1453.2	1446.4	1449.8	1448.4	1449.8	1446.4	1453.2	1459.9	1461.2	1467.3	1471.4
7.5°	1346.0	1337.6	1328.7	1331.5	1328.7	1337.6	1346.0	1346.1	1356.6	1364.5	1369.7
10°	1270.9	1264.2	1260.1	1263.5	1260.1	1264.2	1270.9	1279.7	1283.7	1293.2	1303.3
12.5°	1207.7	1203.7	1200.2	1198.7	1200.2	1203.7	1207.7	1217.1	1226.5	1237.6	1248.8
15°	1121.8	1113.7	1110.3	1101.5	1110.3	1113.7	1121.8	1129.9	1148.1	1152.8	1169.7
17.5°	1042.5	1039.8	1031.0	1027.3	1031.0	1039.8	1042.5	1049.4	1057.8	1075.2	1087.9
20°	995.5	992.8	984.1	989.5	984.1	992.8	995.5	1005.7	1012.4	1026.6	1038.7
22.5°	956.7	950.7	947.9	946.3	947.9	950.7	956.7	961.4	970.3	983.4	997.2
25°	901.7	892.9	889.6	885.5	889.6	892.9	901.7	904.4	913.9	926.7	934.1
27.5°	846.9	842.2	837.7	836.7	837.7	842.2	846.9	850.7	858.9	870.1	883.5
30°	811.3	806.6	803.2	803.2	803.2	806.6	811.3	819.4	825.5	835.6	845.7
32.5°	779.4	775.8	772.4	771.9	772.4	775.8	779.4	783.7	790.9	802.1	812.8
35°	733.0	727.6	726.2	722.2	726.2	727.6	733.0	736.4	743.8	751.9	760.7
37.5°	684.8	680.3	680.2	679.8	680.2	680.3	684.8	690.7	696.9	704.2	715.0
40°	654.0	650.6	650.0	645.2	650.0	650.6	654.0	656.7	663.5	672.9	681.0
42.5°	621.1	619.3	617.0	615.0	617.0	619.3	621.1	626.5	632.2	638.9	649.2
45°	576.4	571.7	571.7	568.3	571.7	571.7	576.4	581.1	583.8	591.9	605.4
47.5°	530.2	526.6	527.0	523.5	527.0	526.6	530.2	531.7	536.0	544.0	551.4
50°	499.5	497.4	496.8	495.4	496.8	497.4	499.5	498.8	504.2	511.6	521.7
52.5°	468.7	467.7	470.3	467.3	470.3	467.7	468.7	470.2	473.9	478.7	488.3
55°	427.2	425.2	429.3	425.2	429.3	425.2	427.2	425.9	427.2	432.0	438.0
57.5°	379.6	377.7	381.3	379.3	381.3	377.7	379.6	379.9	383.9	384.6	390.0
60°	348.3	344.2	346.2	346.9	346.2	344.2	348.3	349.6	351.0	351.6	357.0
62.5°	311.0	308.6	310.1	307.0	310.1	308.6	311.0	314.0	317.0	320.3	323.6
65°	258.5	256.5	253.8	252.4	253.8	256.5	258.5	259.9	267.3	271.3	278.8
67.5°	217.2	212.3	212.2	213.3	212.2	212.3	217.2	216.9	222.3	225.6	230.6
70°	187.0	187.0	186.3	186.3	186.3	187.0	187.0	191.0	193.7	196.4	199.8
72.5°	165.9	165.4	164.1	163.6	164.1	165.4	165.9	167.3	168.9	171.6	174.9
75°	133.6	134.3	133.0	132.3	133.0	134.3	133.6	133.6	136.3	137.0	138.4
77.5°	98.7	95.8	97.3	95.8	97.3	95.8	98.7	101.4	102.3	105.3	105.4
80°	74.9	74.2	76.3	74.2	76.3	74.2	74.9	74.9	76.9	78.3	81.7
82.5°	59.3	58.6	59.5	58.0	59.5	58.6	59.3	58.7	59.7	61.6	61.1
85°	35.8	35.1	34.4	35.1	34.4	35.1	35.8	35.1	34.4	35.1	35.8
87.5°	17.5	17.0	17.2	17.2	17.2	17.0	17.5	17.0	17.1	16.8	16.6
90°	25.6	25.6	26.7	26.7	26.7	25.6	25.6	25.6	23.2	22.1	20.9
92.5°	80.4	77.6	76.0	74.1	76.0	77.6	80.4	95.3	112.5	149.4	205.9
95°	335.8	300.9	291.7	273.1	291.7	300.9	335.8	418.3	515.9	658.8	835.4
97.5°	773.6	708.6	674.9	660.0	674.9	708.6	773.6	845.4	981.2	1120.4	1244.2
100°	1051.6	967.9	924.9	906.3	924.9	967.9	1051.6	1131.7	1252.6	1372.3	1429.2
102.5°	1301.6	1242.1	1195.4	1181.5	1195.4	1242.1	1301.6	1387.4	1469.2	1526.6	1491.5
105°	1615.1	1576.8	1553.5	1539.6	1553.5	1576.8	1615.1	1652.3	1665.1	1614.0	1454.8
107.5°	1746.9	1746.7	1739.0	1729.7	1739.0	1746.7	1746.9	1728.1	1667.4	1536.1	1323.7
110°	1762.7	1784.8	1792.9	1792.9	1792.9	1784.8	1762.7	1710.4	1611.6	1447.8	1227.0



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1719.0	1756.9	1777.1	1785.5	1777.1	1756.9	1719.0	1642.5	1526.1	1360.4	1150.8
115°	1611.6	1667.4	1699.9	1715.0	1699.9	1667.4	1611.6	1521.0	1394.3	1235.2	1055.1
117.5°	1492.4	1550.1	1582.4	1591.6	1582.4	1550.1	1492.4	1401.8	1285.6	1148.5	993.2
120°	1415.3	1471.0	1502.4	1511.7	1502.4	1471.0	1415.3	1329.3	1227.0	1099.2	959.8
122.5°	1350.2	1401.3	1432.7	1441.1	1432.7	1401.3	1350.2	1273.5	1177.8	1063.9	934.7
125°	1266.5	1314.2	1339.7	1351.4	1339.7	1314.2	1266.5	1201.5	1117.8	1016.7	898.2
127.5°	1203.3	1245.4	1269.6	1274.7	1269.6	1245.4	1203.3	1144.3	1066.0	971.6	861.0
130°	1164.3	1202.6	1225.9	1232.8	1225.9	1202.6	1164.3	1106.2	1030.7	940.0	837.8
132.5°	1123.4	1161.7	1183.1	1191.0	1183.1	1161.7	1123.4	1065.3	992.5	910.3	814.5
135°	1056.2	1094.6	1115.5	1122.5	1115.5	1094.6	1056.2	1005.1	938.9	864.5	784.3
137.5°	987.4	1022.3	1041.6	1049.2	1041.6	1022.3	987.4	941.7	885.4	823.6	758.8
140°	944.7	974.9	992.3	998.1	992.3	974.9	944.7	901.7	852.9	799.4	744.8
142.5°	903.8	929.3	945.8	950.7	945.8	929.3	903.8	867.3	825.0	779.0	732.7
145°	848.2	868.0	880.8	885.4	880.8	868.0	848.2	820.3	789.0	752.9	716.9
147.5°	804.8	820.6	828.0	830.1	828.0	820.6	804.8	782.7	759.0	731.3	702.1
150°	779.7	793.6	798.3	799.4	798.3	793.6	779.7	762.2	741.3	719.3	693.7
152.5°	758.3	769.4	774.1	775.3	774.1	769.4	758.3	743.7	727.4	707.2	684.4
155°	729.7	737.8	741.3	742.5	741.3	737.8	729.7	718.1	705.3	689.0	670.4
157.5°	703.4	710.2	713.4	713.2	713.4	710.2	703.4	694.4	684.4	671.8	656.5
160°	686.7	692.5	694.9	693.7	694.9	692.5	686.7	678.6	670.4	658.8	647.2
162.5°	670.9	675.8	676.3	676.0	676.3	675.8	670.9	664.6	657.4	647.7	637.0
165°	648.4	650.7	650.7	650.7	650.7	650.7	648.4	643.7	637.9	630.9	622.8
167.5°	626.5	628.6	627.7	627.5	627.7	628.6	626.5	624.2	620.0	614.7	609.3
170°	613.5	614.7	614.7	613.5	614.7	614.7	613.5	611.2	608.9	605.4	601.9
172.5°	601.4	603.5	601.7	600.5	601.7	603.5	601.4	601.0	599.6	597.0	593.5
175°	586.8	588.0	585.6	584.5	585.6	588.0	586.8	586.8	586.8	584.5	584.5
177.5°	578.2	579.1	576.3	576.3	576.3	579.1	578.2	579.1	579.1	579.1	578.2
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1576.1	1582.1	1585.3	1592.9	1603.7	1609.1	1616.6	1622.0	1629.6	1638.8	1646.3
5°	1474.1	1490.3	1501.1	1517.9	1533.5	1549.0	1568.6	1582.7	1601.6	1623.2	1640.1
7.5°	1379.3	1399.6	1417.5	1439.8	1465.4	1485.4	1510.9	1537.0	1566.5	1597.2	1626.1
10°	1318.8	1339.1	1361.4	1389.0	1414.7	1441.7	1472.0	1502.4	1539.5	1574.0	1613.1
12.5°	1258.9	1281.3	1306.3	1337.2	1368.2	1402.8	1433.7	1467.9	1507.7	1552.4	1594.2
15°	1184.5	1206.1	1233.1	1259.4	1295.2	1333.0	1374.2	1419.4	1463.9	1513.9	1565.9
17.5°	1104.7	1128.5	1158.2	1188.7	1226.4	1270.6	1311.0	1360.5	1410.6	1468.8	1530.0
20°	1052.9	1077.2	1112.3	1146.1	1180.5	1223.7	1271.6	1322.2	1375.5	1437.0	1505.1
22.5°	1011.9	1029.2	1063.7	1098.0	1138.4	1182.6	1229.5	1282.3	1340.4	1404.0	1475.4
25°	951.0	971.2	996.2	1032.0	1073.8	1120.4	1167.6	1223.7	1287.1	1351.9	1428.2
27.5°	896.9	913.5	938.2	966.2	1008.0	1056.3	1106.5	1164.9	1230.0	1296.0	1376.2
30°	858.5	876.7	900.4	930.1	963.1	1015.8	1067.1	1124.5	1190.6	1258.8	1341.1
32.5°	825.0	843.8	864.2	892.3	928.0	974.8	1027.7	1084.0	1151.2	1221.5	1301.7
35°	778.2	791.0	809.9	837.6	872.7	910.5	964.5	1023.9	1089.4	1162.3	1242.6
37.5°	724.5	741.1	759.8	783.9	814.7	855.6	905.8	965.8	1026.6	1096.4	1169.7
40°	693.2	708.7	729.6	747.2	779.6	816.7	862.6	925.3	986.1	1051.6	1118.4
42.5°	661.3	676.3	694.0	715.8	745.0	781.0	823.7	882.1	947.2	1008.9	1064.9
45°	611.5	627.0	643.9	664.1	691.1	726.2	768.8	822.1	878.8	935.5	978.0
47.5°	563.8	578.4	594.4	615.1	640.0	673.9	711.9	759.0	814.1	862.3	892.7
50°	529.8	543.3	560.9	581.1	605.4	637.1	673.6	720.2	766.1	809.9	837.6
52.5°	496.4	511.5	529.0	546.6	569.8	601.5	635.3	675.3	719.1	754.9	777.7
55°	446.1	460.3	476.5	494.7	517.7	544.7	580.5	612.2	646.6	677.0	690.5
57.5°	397.7	410.1	425.3	444.2	464.9	490.0	518.4	548.9	573.2	594.6	609.9
60°	365.8	376.6	390.8	407.0	429.3	452.2	477.9	506.2	525.1	543.3	557.5
62.5°	333.4	343.7	357.3	371.9	391.5	412.8	437.4	460.3	478.7	491.0	507.3
65°	284.8	294.9	306.4	321.9	337.5	355.0	377.3	394.2	407.0	420.5	430.6
67.5°	239.6	248.0	258.9	271.1	284.2	301.0	318.3	332.3	341.1	349.2	361.4
70°	209.9	216.7	225.4	234.9	249.1	265.9	279.4	290.2	296.3	304.4	319.2
72.5°	179.7	187.5	195.7	205.2	216.7	230.8	242.7	253.5	257.4	263.9	273.4
75°	141.7	145.8	152.5	159.3	167.4	179.5	191.0	193.7	197.1	202.5	209.2
77.5°	107.2	110.8	113.5	118.0	124.5	134.2	140.3	144.3	145.1	147.1	153.8
80°	85.0	87.1	89.8	93.1	95.8	103.9	107.3	111.4	112.7	114.7	118.1
82.5°	62.4	64.4	66.0	68.8	73.2	76.4	79.8	83.8	84.1	85.6	86.3
85°	36.4	37.1	35.8	37.1	37.8	39.1	42.5	45.9	45.2	44.5	46.6
87.5°	16.9	16.7	15.7	17.1	15.5	15.8	15.4	15.4	16.0	16.7	17.5
90°	19.8	18.6	16.3	15.1	12.8	11.6	9.3	7.0	4.6	2.3	1.2
92.5°	303.3	374.6	380.7	265.2	158.7	95.3	61.4	41.4	27.0	17.2	14.2
95°	1007.4	1029.5	840.1	519.4	263.8	139.4	87.1	61.6	48.8	39.5	38.3
97.5°	1274.7	1099.4	750.2	414.6	227.3	145.0	107.4	84.4	71.6	65.1	63.7
100°	1339.7	1049.2	669.3	376.5	225.4	158.0	123.2	101.1	88.3	83.7	81.3
102.5°	1300.7	960.9	607.9	360.7	233.8	173.8	139.9	119.7	106.0	102.3	100.9
105°	1175.9	842.4	548.4	354.4	251.0	199.9	167.3	148.7	137.1	131.3	131.3
107.5°	1048.6	760.8	523.3	365.1	276.5	227.0	197.8	178.5	168.9	163.4	161.0
110°	976.0	722.7	515.9	375.3	295.1	247.5	217.3	199.9	189.4	184.8	182.4



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	922.1	700.4	515.9	388.3	312.8	267.0	237.7	220.3	209.8	206.1	203.8
115°	863.3	676.3	519.4	407.8	340.5	297.5	268.4	251.0	240.5	237.0	234.7
117.5°	828.2	664.4	527.1	430.2	368.8	328.1	300.0	280.3	269.8	266.1	262.6
120°	808.7	658.8	534.5	445.0	389.3	348.6	319.5	299.8	289.3	284.7	281.2
122.5°	792.0	654.2	541.0	461.8	408.8	368.1	339.1	317.4	307.0	303.3	300.7
125°	769.2	648.4	551.9	484.5	434.6	396.2	366.0	343.9	333.5	327.7	325.3
127.5°	748.3	645.6	564.2	505.5	459.4	422.5	392.3	368.8	355.6	348.1	344.6
130°	734.4	643.7	571.7	519.4	475.2	439.2	409.0	384.6	369.5	360.2	356.7
132.5°	723.2	643.7	580.0	531.5	490.1	454.1	423.9	398.6	381.6	370.4	366.0
135°	710.0	643.7	591.4	548.4	510.1	474.1	442.7	418.3	399.7	385.8	381.1
137.5°	698.1	645.1	601.9	561.0	524.3	491.5	459.2	435.3	416.7	403.7	400.2
140°	692.5	646.0	606.5	569.4	534.5	500.8	469.4	447.4	428.8	414.8	411.3
142.5°	687.9	647.0	609.3	574.0	541.0	509.2	479.7	458.5	439.9	426.9	424.3
145°	680.9	646.0	612.4	581.0	551.9	521.7	495.0	474.1	457.8	446.2	443.9
147.5°	673.7	643.0	613.5	585.2	558.9	532.4	508.9	490.8	475.7	465.7	464.3
150°	668.1	640.2	613.5	588.0	563.5	538.0	518.2	502.0	486.9	478.7	476.4
152.5°	661.6	636.5	612.6	589.8	568.2	544.5	526.6	511.3	498.0	490.8	489.4
155°	650.7	629.8	610.0	591.4	572.8	553.1	536.8	525.2	513.6	506.6	506.6
157.5°	640.5	622.8	607.0	592.6	576.8	559.8	547.5	537.3	527.3	521.7	522.0
160°	632.1	618.2	604.2	592.6	578.7	563.5	553.1	543.8	535.7	531.0	532.2
162.5°	624.7	612.6	601.4	591.7	580.5	567.3	558.7	551.2	544.0	539.4	540.5
165°	613.5	604.2	597.2	590.3	581.0	571.7	564.7	560.1	554.3	550.8	553.1
167.5°	602.6	596.1	590.7	587.5	581.0	573.3	568.9	565.6	562.4	560.3	561.5
170°	596.1	591.4	588.0	585.6	581.0	575.2	571.7	569.4	567.0	565.9	567.0
172.5°	589.6	585.9	584.2	583.8	580.0	575.2	573.5	572.1	569.8	568.7	570.8
175°	581.0	579.8	579.8	581.0	578.7	575.2	575.2	575.2	574.0	572.8	575.2
177.5°	577.3	576.3	576.3	578.2	577.3	575.4	575.4	576.3	575.4	575.4	577.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1652.3	1657.1	1664.1	1672.2	1678.7	1685.7	1689.5	1689.5	1692.8	1699.8	1709.0
5°	1657.0	1674.5	1691.4	1713.0	1729.9	1749.4	1764.3	1778.5	1791.3	1807.5	1824.4
7.5°	1655.6	1684.8	1715.2	1749.2	1786.7	1816.5	1847.2	1871.2	1895.0	1926.0	1950.4
10°	1650.2	1688.0	1729.2	1772.4	1819.6	1860.8	1897.9	1931.7	1964.1	1997.8	2028.2
12.5°	1640.5	1688.6	1738.9	1790.8	1850.4	1897.5	1945.5	1981.4	2019.2	2056.1	2093.5
15°	1625.9	1682.6	1743.4	1815.6	1888.5	1941.1	1988.4	2035.0	2070.0	2111.9	2147.7
17.5°	1595.8	1668.9	1745.3	1824.2	1894.3	1955.4	2005.0	2049.3	2086.7	2132.7	2181.3
20°	1578.0	1657.0	1736.6	1821.0	1887.8	1950.6	1998.5	2044.4	2091.0	2151.0	2210.4
22.5°	1553.2	1637.5	1722.0	1802.1	1872.7	1933.3	1982.8	2039.0	2100.1	2168.3	2240.1
25°	1513.9	1601.0	1684.7	1760.9	1829.8	1891.9	1959.4	2035.0	2109.2	2199.0	2302.2
27.5°	1464.1	1548.0	1622.7	1703.3	1771.7	1850.7	1934.9	2016.9	2123.9	2247.4	2376.3
30°	1426.8	1506.5	1577.3	1653.6	1731.2	1818.3	1912.8	2009.3	2136.9	2282.0	2435.2
32.5°	1383.6	1455.7	1526.0	1599.6	1689.1	1784.8	1885.2	2003.4	2155.8	2320.9	2479.5
35°	1308.7	1373.5	1441.7	1523.3	1618.5	1722.5	1850.7	1994.5	2178.7	2356.2	2498.6
37.5°	1230.1	1281.3	1349.7	1435.9	1539.5	1659.8	1805.3	1980.0	2169.3	2328.5	2389.2
40°	1169.7	1217.6	1289.8	1380.3	1482.8	1614.5	1777.8	1957.3	2147.7	2258.4	2253.6
42.5°	1109.7	1158.2	1227.7	1318.7	1425.6	1572.9	1741.1	1927.6	2088.3	2130.4	2042.5
45°	1017.8	1063.0	1131.2	1223.0	1337.7	1492.3	1669.1	1848.0	1950.6	1882.4	1708.3
47.5°	924.1	968.0	1031.3	1121.2	1246.5	1408.2	1575.4	1722.2	1736.6	1590.2	1381.3
50°	862.6	903.7	963.8	1059.7	1181.1	1339.1	1500.4	1615.8	1580.0	1401.2	1185.9
52.5°	802.6	842.2	898.5	988.9	1113.1	1267.8	1411.8	1502.4	1419.7	1229.5	1035.8
55°	714.1	751.9	808.6	891.6	1004.3	1146.1	1272.3	1305.3	1183.8	992.2	835.6
57.5°	630.0	657.7	713.7	787.1	895.8	1020.8	1111.2	1105.3	971.2	798.6	686.3
60°	574.4	599.3	652.7	720.2	823.4	935.5	998.9	971.9	836.3	693.8	585.8
62.5°	522.5	545.9	590.6	652.7	741.4	838.8	885.0	847.7	719.6	594.5	508.6
65°	444.1	461.0	496.8	554.1	623.6	691.1	732.3	677.6	564.3	469.8	405.0
67.5°	370.8	385.4	417.2	458.4	506.3	552.9	569.7	518.4	430.2	366.5	320.9
70°	323.3	336.8	358.4	396.9	428.6	461.7	469.8	423.9	350.3	301.7	273.4
72.5°	277.9	290.4	309.3	336.4	358.4	377.4	381.2	338.6	282.3	248.8	226.9
75°	211.9	222.7	234.9	245.0	259.2	262.6	261.2	228.1	197.8	175.5	163.3
77.5°	155.8	160.2	167.7	171.7	172.4	172.1	165.2	144.3	128.6	119.5	114.5
80°	120.1	123.5	125.5	126.9	127.6	120.8	113.4	100.6	95.2	89.8	83.7
82.5°	87.2	89.5	91.5	91.8	88.1	82.5	75.6	69.2	65.5	62.8	60.5
85°	47.2	47.9	47.2	43.9	39.1	37.1	35.8	34.4	33.7	33.1	33.1
87.5°	17.2	16.0	13.8	14.8	15.3	15.0	15.4	15.1	15.1	15.3	15.5
90°	2.3	4.6	7.0	9.3	11.6	12.8	15.1	16.3	18.6	19.8	20.9
92.5°	17.2	27.0	41.4	61.4	95.3	158.7	265.2	380.7	374.6	303.3	205.9
95°	39.5	48.8	61.6	87.1	139.4	263.8	519.4	840.1	1029.5	1007.4	835.4
97.5°	65.1	71.6	84.4	107.4	145.0	227.3	414.6	750.2	1099.4	1274.7	1244.2
100°	83.7	88.3	101.1	123.2	158.0	225.4	376.5	669.3	1049.2	1339.7	1429.2
102.5°	102.3	106.0	119.7	139.9	173.8	233.8	360.7	607.9	960.9	1300.7	1491.5
105°	131.3	137.1	148.7	167.3	199.9	251.0	354.4	548.4	842.4	1175.9	1454.8
107.5°	163.4	168.9	178.5	197.8	227.0	276.5	365.1	523.3	760.8	1048.6	1323.7
110°	184.8	189.4	199.9	217.3	247.5	295.1	375.3	515.9	722.7	976.0	1227.0



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	206.1	209.8	220.3	237.7	267.0	312.8	388.3	515.9	700.4	922.1	1150.8
115°	237.0	240.5	251.0	268.4	297.5	340.5	407.8	519.4	676.3	863.3	1055.1
117.5°	266.1	269.8	280.3	300.0	328.1	368.8	430.2	527.1	664.4	828.2	993.2
120°	284.7	289.3	299.8	319.5	348.6	389.3	445.0	534.5	658.8	808.7	959.8
122.5°	303.3	307.0	317.4	339.1	368.1	408.8	461.8	541.0	654.2	792.0	934.7
125°	327.7	333.5	343.9	366.0	396.2	434.6	484.5	551.9	648.4	769.2	898.2
127.5°	348.1	355.6	368.8	392.3	422.5	459.4	505.5	564.2	645.6	748.3	861.0
130°	360.2	369.5	384.6	409.0	439.2	475.2	519.4	571.7	643.7	734.4	837.8
132.5°	370.4	381.6	398.6	423.9	454.1	490.1	531.5	580.0	643.7	723.2	814.5
135°	385.8	399.7	418.3	442.7	474.1	510.1	548.4	591.4	643.7	710.0	784.3
137.5°	403.7	416.7	435.3	459.2	491.5	524.3	561.0	601.9	645.1	698.1	758.8
140°	414.8	428.8	447.4	469.4	500.8	534.5	569.4	606.5	646.0	692.5	744.8
142.5°	426.9	439.9	458.5	479.7	509.2	541.0	574.0	609.3	647.0	687.9	732.7
145°	446.2	457.8	474.1	495.0	521.7	551.9	581.0	612.4	646.0	680.9	716.9
147.5°	465.7	475.7	490.8	508.9	532.4	558.9	585.2	613.5	643.0	673.7	702.1
150°	478.7	486.9	502.0	518.2	538.0	563.5	588.0	613.5	640.2	668.1	693.7
152.5°	490.8	498.0	511.3	526.6	544.5	568.2	589.8	612.6	636.5	661.6	684.4
155°	506.6	513.6	525.2	536.8	553.1	572.8	591.4	610.0	629.8	650.7	670.4
157.5°	521.7	527.3	537.3	547.5	559.8	576.8	592.6	607.0	622.8	640.5	656.5
160°	531.0	535.7	543.8	553.1	563.5	578.7	592.6	604.2	618.2	632.1	647.2
162.5°	539.4	544.0	551.2	558.7	567.3	580.5	591.7	601.4	612.6	624.7	637.0
165°	550.8	554.3	560.1	564.7	571.7	581.0	590.3	597.2	604.2	613.5	622.8
167.5°	560.3	562.4	565.6	568.9	573.3	581.0	587.5	590.7	596.1	602.6	609.3
170°	565.9	567.0	569.4	571.7	575.2	581.0	585.6	588.0	591.4	596.1	601.9
172.5°	568.7	569.8	572.1	573.5	575.2	580.0	583.8	584.2	585.9	589.6	593.5
175°	572.8	574.0	575.2	575.2	575.2	578.7	581.0	579.8	579.8	581.0	584.5
177.5°	575.4	575.4	576.3	575.4	575.4	577.3	578.2	576.3	576.3	577.3	578.2
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1716.0	1716.0	1725.2	1724.6	1730.6	1728.4	1729.5
5°	1844.6	1856.1	1866.2	1873.0	1883.1	1885.8	1884.4
7.5°	1978.0	2003.5	2015.9	2032.9	2036.0	2044.9	2044.0
10°	2060.6	2085.6	2104.5	2119.3	2126.7	2136.2	2136.9
12.5°	2125.4	2146.6	2163.3	2177.1	2186.1	2189.1	2190.9
15°	2176.0	2199.6	2219.2	2238.8	2250.3	2259.0	2263.8
17.5°	2227.0	2263.5	2298.0	2324.6	2340.6	2354.1	2353.9
20°	2266.5	2308.3	2351.5	2381.9	2412.9	2426.4	2428.4
22.5°	2308.6	2372.6	2428.2	2475.3	2516.0	2530.1	2535.4
25°	2396.0	2479.7	2565.5	2631.6	2678.8	2706.5	2710.6
27.5°	2501.7	2615.0	2705.2	2766.2	2805.5	2826.0	2830.4
30°	2576.3	2680.9	2761.9	2807.8	2826.0	2828.7	2818.6
32.5°	2609.7	2687.9	2720.3	2717.6	2681.8	2658.1	2649.0
35°	2568.8	2552.6	2473.7	2379.2	2307.0	2261.1	2248.9
37.5°	2337.7	2198.0	2052.8	1910.0	1834.0	1795.3	1728.9
40°	2109.9	1910.8	1759.6	1639.4	1553.7	1484.9	1468.7
42.5°	1852.9	1647.3	1496.1	1393.2	1324.8	1277.5	1257.0
45°	1488.9	1312.1	1187.2	1108.3	1055.6	1021.2	1005.7
47.5°	1190.9	1054.0	963.0	904.6	864.5	834.5	826.1
50°	1027.3	917.9	841.0	791.7	761.3	738.4	728.9
52.5°	892.3	804.0	744.9	704.2	675.5	661.2	653.3
55°	736.4	660.1	617.6	585.2	569.0	557.5	552.1
57.5°	602.2	547.1	516.1	493.7	478.7	471.4	468.7
60°	527.1	483.9	455.6	438.0	427.9	418.5	415.8
62.5°	460.7	426.7	404.8	389.4	379.3	375.3	373.6
65°	371.2	348.9	332.7	323.3	315.2	313.8	313.2
67.5°	295.1	282.0	273.5	263.6	260.8	256.1	255.1
70°	252.4	243.7	233.5	230.2	226.8	222.1	222.7
72.5°	214.1	205.3	198.4	194.0	192.8	190.7	192.5
75°	156.6	153.9	151.2	147.8	146.5	146.5	145.8
77.5°	111.8	109.5	106.5	104.5	104.1	101.2	102.3
80°	81.0	77.6	76.3	76.9	74.9	74.2	74.2
82.5°	59.9	58.7	57.4	57.5	57.1	56.4	57.0
85°	33.1	32.4	32.4	31.7	31.7	31.0	31.0
87.5°	16.3	17.1	16.5	15.9	15.9	16.7	17.2
90°	22.1	23.2	25.6	25.6	25.6	26.7	26.7
92.5°	149.4	112.5	95.3	80.4	77.6	76.0	74.1
95°	658.8	515.9	418.3	335.8	300.9	291.7	273.1
97.5°	1120.4	981.2	845.4	773.6	708.6	674.9	660.0
100°	1372.3	1252.6	1131.7	1051.6	967.9	924.9	906.3
102.5°	1526.6	1469.2	1387.4	1301.6	1242.1	1195.4	1181.5
105°	1614.0	1665.1	1652.3	1615.1	1576.8	1553.5	1539.6
107.5°	1536.1	1667.4	1728.1	1746.9	1746.7	1739.0	1729.7
110°	1447.8	1611.6	1710.4	1762.7	1784.8	1792.9	1792.9



TEST NUMBER: P333606

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1360.4	1526.1	1642.5	1719.0	1756.9	1777.1	1785.5
115°	1235.2	1394.3	1521.0	1611.6	1667.4	1699.9	1715.0
117.5°	1148.5	1285.6	1401.8	1492.4	1550.1	1582.4	1591.6
120°	1099.2	1227.0	1329.3	1415.3	1471.0	1502.4	1511.7
122.5°	1063.9	1177.8	1273.5	1350.2	1401.3	1432.7	1441.1
125°	1016.7	1117.8	1201.5	1266.5	1314.2	1339.7	1351.4
127.5°	971.6	1066.0	1144.3	1203.3	1245.4	1269.6	1274.7
130°	940.0	1030.7	1106.2	1164.3	1202.6	1225.9	1232.8
132.5°	910.3	992.5	1065.3	1123.4	1161.7	1183.1	1191.0
135°	864.5	938.9	1005.1	1056.2	1094.6	1115.5	1122.5
137.5°	823.6	885.4	941.7	987.4	1022.3	1041.6	1049.2
140°	799.4	852.9	901.7	944.7	974.9	992.3	998.1
142.5°	779.0	825.0	867.3	903.8	929.3	945.8	950.7
145°	752.9	789.0	820.3	848.2	868.0	880.8	885.4
147.5°	731.3	759.0	782.7	804.8	820.6	828.0	830.1
150°	719.3	741.3	762.2	779.7	793.6	798.3	799.4
152.5°	707.2	727.4	743.7	758.3	769.4	774.1	775.3
155°	689.0	705.3	718.1	729.7	737.8	741.3	742.5
157.5°	671.8	684.4	694.4	703.4	710.2	713.4	713.2
160°	658.8	670.4	678.6	686.7	692.5	694.9	693.7
162.5°	647.7	657.4	664.6	670.9	675.8	676.3	676.0
165°	630.9	637.9	643.7	648.4	650.7	650.7	650.7
167.5°	614.7	620.0	624.2	626.5	628.6	627.7	627.5
170°	605.4	608.9	611.2	613.5	614.7	614.7	613.5
172.5°	597.0	599.6	601.0	601.4	603.5	601.7	600.5
175°	584.5	586.8	586.8	586.8	588.0	585.6	584.5
177.5°	579.1	579.1	579.1	578.2	579.1	576.3	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3

(END OF REPORT)