

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333590

Luminaire Tested: **S125RDIP-S1090D590U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333590
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D590U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6269.7 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333590

CATALOG NUMBER: S125RDIP-S1090D590U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333590

CATALOG NUMBER: S125RDIP-S1090D590U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	62	57
2	93	86	79	74	88	81	76	71	72	68	64	64	61	58	57	54	52	49
3	85	76	68	62	80	72	65	60	64	59	54	57	53	50	51	47	45	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11544	11544	11544
5°	11570	11439	11509
10°	11482	11332	11332
15°	11346	11102	11012
20°	11171	10781	10652
25°	10967	10467	10236
30°	10712	10097	9775
35°	10452	9717	9260
40°	10209	9321	8752
45°	9913	8878	8199
50°	9616	8396	7623
55°	9272	7935	7007
60°	8928	7375	6347
65°	8520	6725	5590
70°	8055	5914	4817
75°	7411	4986	4007
80°	6527	3916	3362
85°	5498	3201	3001



TEST NUMBER: P333590

CATALOG NUMBER: S125RDIP-S1090D590U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.1	2.7
10°-20°	469.7	7.5
20°-30°	681.1	10.9
30°-40°	776.2	12.4
40°-50°	756.6	12.1
50°-60°	636.9	10.2
60°-70°	446.5	7.1
70°-80°	229.5	3.7
80°-90°	59.6	0.9
90°-100°	49.1	0.8
100°-110°	145.0	2.3
110°-120°	245.6	3.9
120°-130°	323.2	5.2
130°-140°	362.1	5.8
140°-150°	354.9	5.7
150°-160°	298.1	4.8
160°-170°	198.2	3.2
170°-180°	69.4	1.1
0°-30°	1318.9	21.0
0°-40°	2095.1	33.4
0°-60°	3488.6	55.6
0°-90°	4224.1	67.4
90°-120°	439.7	7.0
90°-150°	1479.9	23.6
90°-180°	2046.0	32.6
0°-180°	6269.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1787	1787	1787	1787	1787	
5°	1785	1779	1764	1777	1775	169
15°	1697	1688	1660	1659	1647	478
25°	1539	1517	1469	1451	1436	708
35°	1326	1292	1232	1194	1174	830
45°	1085	1044	972	920	898	837
55°	824	778	705	646	622	736
65°	558	510	440	388	366	552
75°	297	256	200	171	161	314
85°	74	51	43	42	40	83
90°	1	5	9	12	14	5
95°	37	38	44	48	49	40
105°	130	133	136	140	142	139
115°	246	248	249	249	248	243
125°	359	362	363	362	361	321
135°	467	470	471	470	468	360
145°	565	568	569	569	568	353
155°	647	647	648	650	647	298
165°	703	702	703	705	702	198
175°	731	729	729	732	728	69
180°	733	733	733	733	733	



TEST NUMBER: P333590

CATALOG NUMBER: S125RDIP-S1090D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1790.6	1789.9	1789.2	1788.4	1787.7	1786.2	1783.8	1781.4	1779.0	1776.6	1779.0
5°	1784.7	1783.5	1782.3	1781.1	1779.9	1777.6	1774.3	1771.0	1767.7	1764.4	1767.4
7.5°	1767.1	1766.0	1764.8	1763.7	1762.5	1760.0	1756.0	1752.1	1748.1	1744.2	1746.3
10°	1750.9	1750.0	1749.1	1748.2	1747.3	1744.8	1740.6	1736.4	1732.2	1728.0	1728.9
12.5°	1732.5	1731.4	1730.3	1729.1	1728.0	1724.6	1719.0	1713.3	1707.7	1702.0	1702.7
15°	1696.9	1695.1	1693.3	1691.5	1689.7	1685.7	1679.4	1673.1	1666.8	1660.5	1660.2
17.5°	1656.7	1653.9	1651.2	1648.4	1645.6	1640.3	1632.4	1624.5	1616.5	1608.6	1607.1
20°	1625.4	1622.4	1619.4	1616.4	1613.4	1607.1	1597.5	1587.9	1578.3	1568.7	1567.2
22.5°	1590.8	1587.8	1584.8	1581.8	1578.8	1572.3	1562.2	1552.1	1542.0	1531.9	1529.0
25°	1539.0	1534.5	1530.0	1525.5	1521.0	1513.2	1502.1	1491.0	1479.9	1468.8	1464.9
27.5°	1479.6	1474.1	1468.6	1463.2	1457.7	1449.1	1437.2	1425.3	1413.4	1401.5	1396.1
30°	1436.4	1430.7	1425.0	1419.3	1413.6	1404.4	1391.8	1379.2	1366.6	1354.0	1347.1
32.5°	1394.2	1387.6	1380.9	1374.3	1367.6	1357.9	1345.0	1332.2	1319.3	1306.5	1298.9
35°	1325.7	1318.5	1311.3	1304.1	1296.9	1286.5	1273.0	1259.5	1246.0	1232.5	1223.8
37.5°	1258.4	1249.7	1240.9	1232.2	1223.4	1212.1	1198.1	1184.2	1170.3	1156.4	1145.9
40°	1210.9	1201.9	1192.9	1183.9	1174.9	1163.2	1148.8	1134.4	1120.0	1105.6	1094.2
42.5°	1161.2	1152.0	1142.8	1133.5	1124.3	1112.2	1097.3	1082.5	1067.6	1052.7	1041.8
45°	1085.4	1076.7	1068.0	1059.3	1050.6	1038.0	1021.5	1005.0	988.5	972.0	960.0
47.5°	1006.8	997.6	988.4	979.3	970.1	957.2	940.6	923.9	907.3	890.7	878.3
50°	957.1	947.2	937.3	927.4	917.5	904.0	886.9	869.8	852.7	835.6	823.0
52.5°	903.1	893.0	882.8	872.7	862.6	849.4	833.3	817.1	801.0	784.9	771.3
55°	823.5	813.9	804.3	794.7	785.1	771.9	755.1	738.3	721.5	704.7	691.2
57.5°	743.0	732.8	722.5	712.2	702.0	688.8	672.6	656.4	640.2	624.0	610.8
60°	691.2	680.7	670.2	659.7	649.2	635.8	619.6	603.4	587.2	571.0	557.8
62.5°	636.1	626.1	616.1	606.0	596.0	582.8	566.4	549.9	533.5	517.0	504.8
65°	557.5	547.3	537.1	526.9	516.7	503.7	487.8	471.9	456.0	440.1	428.1
67.5°	479.5	469.3	459.1	448.9	438.7	426.0	410.7	395.5	380.3	365.0	354.1
70°	426.6	416.4	406.2	396.0	385.8	373.2	358.2	343.2	328.2	313.2	303.9
72.5°	374.8	364.8	354.8	344.9	334.9	322.9	308.9	294.8	280.8	266.8	258.2
75°	297.0	288.0	279.0	270.0	261.0	250.2	237.6	225.0	212.4	199.8	193.2
77.5°	219.8	212.6	205.4	198.2	191.0	182.3	172.3	162.2	152.1	142.0	137.4
80°	175.5	168.3	161.1	153.9	146.7	138.9	130.5	122.1	113.7	105.3	102.6
82.5°	132.3	125.8	119.3	112.9	106.4	100.3	94.5	88.7	83.0	77.2	76.0
85°	74.2	68.8	63.4	58.0	52.6	49.2	47.7	46.2	44.7	43.2	42.9
87.5°	25.0	23.5	22.0	20.5	19.0	18.3	18.2	18.2	18.1	18.0	18.2
90°	0.6	1.6	2.6	3.6	4.6	5.6	6.5	7.4	8.2	9.1	9.8
92.5°	13.8	14.5	15.2	15.9	16.6	17.5	18.6	19.7	20.8	21.9	22.7
95°	37.1	37.3	37.6	37.8	38.1	38.9	40.1	41.4	42.7	43.9	44.8
97.5°	61.6	61.7	61.8	61.9	62.0	62.9	64.7	66.4	68.2	69.9	70.8
100°	79.9	79.9	79.9	79.9	79.9	80.7	82.3	84.0	85.6	87.3	88.4
102.5°	99.5	100.0	100.5	101.0	101.5	102.2	103.0	103.9	104.7	105.5	106.8
105°	130.1	130.7	131.3	132.0	132.6	133.3	134.1	134.8	135.6	136.3	137.1
107.5°	163.8	164.5	165.1	165.7	166.4	167.0	167.6	168.1	168.7	169.3	169.7
110°	187.1	187.7	188.4	189.0	189.7	190.2	190.5	190.9	191.3	191.7	192.1



TEST NUMBER: P333590

CATALOG NUMBER: S125RDIP-S1090D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.8	211.2	211.5	211.8	212.2	212.6	213.1	213.5	214.0	214.5	214.7
115°	245.9	246.4	246.9	247.4	247.9	248.3	248.5	248.8	249.0	249.3	249.2
117.5°	281.0	281.2	281.5	281.7	281.9	282.2	282.4	282.6	282.8	283.1	283.2
120°	302.9	303.6	304.2	304.8	305.5	305.8	306.0	306.1	306.2	306.3	306.3
122.5°	326.7	326.9	327.1	327.3	327.6	327.8	328.2	328.5	328.8	329.2	329.1
125°	358.8	359.6	360.3	361.1	361.9	362.3	362.4	362.6	362.7	362.8	362.6
127.5°	393.1	393.5	393.9	394.3	394.8	395.1	395.2	395.4	395.5	395.7	395.6
130°	413.6	414.2	414.9	415.5	416.1	416.6	416.8	417.1	417.3	417.6	417.5
132.5°	434.1	435.2	436.2	437.2	438.3	438.8	438.7	438.7	438.6	438.6	438.5
135°	466.6	467.4	468.2	468.9	469.7	470.1	470.3	470.4	470.5	470.6	470.6
137.5°	497.2	498.0	498.7	499.4	500.2	500.7	501.0	501.2	501.5	501.8	501.9
140°	516.8	517.5	518.1	518.7	519.4	519.9	520.3	520.7	521.0	521.4	521.7
142.5°	536.5	537.0	537.5	538.1	538.6	539.1	539.6	540.1	540.6	541.0	541.2
145°	565.3	565.8	566.4	566.9	567.4	567.8	568.2	568.6	569.0	569.3	569.3
147.5°	592.0	592.3	592.6	592.9	593.2	593.4	593.7	594.1	594.4	594.7	595.0
150°	609.8	609.7	609.6	609.5	609.3	609.5	610.0	610.5	611.0	611.5	611.5
152.5°	624.4	624.6	624.8	625.0	625.1	625.3	625.5	625.7	625.9	626.2	626.5
155°	646.9	646.9	646.9	646.9	646.9	647.0	647.1	647.2	647.4	647.5	648.0
157.5°	667.0	666.7	666.4	666.2	665.9	665.8	665.9	666.1	666.2	666.3	666.8
160°	678.9	678.5	678.1	677.7	677.3	677.2	677.3	677.5	677.6	677.7	678.2
162.5°	689.4	689.1	688.8	688.5	688.2	688.1	688.1	688.2	688.2	688.2	688.8
165°	703.4	703.1	702.9	702.6	702.4	702.3	702.4	702.6	702.7	702.8	703.3
167.5°	715.3	714.8	714.2	713.7	713.2	713.0	713.0	713.0	713.0	713.0	713.7
170°	721.6	721.1	720.6	720.1	719.6	719.4	719.4	719.4	719.4	719.4	720.1
172.5°	726.2	725.7	725.2	724.7	724.2	723.9	723.9	723.9	723.9	723.9	724.7
175°	731.3	730.8	730.3	729.8	729.3	729.1	729.1	729.1	729.1	729.1	729.8
177.5°	734.0	733.6	733.2	732.8	732.3	732.1	732.0	731.9	731.8	731.7	732.3
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333590

CATALOG NUMBER: S125RDIP-S1090D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1781.4	1783.8	1786.2	1787.2	1787.0	1786.8	1786.5	1786.3
5°	1770.4	1773.4	1776.4	1777.6	1777.0	1776.4	1775.8	1775.2
7.5°	1748.4	1750.5	1752.6	1753.3	1752.6	1752.0	1751.3	1750.6
10°	1729.8	1730.7	1731.6	1731.6	1730.7	1729.8	1728.9	1728.0
12.5°	1703.4	1704.0	1704.7	1704.3	1702.9	1701.6	1700.2	1698.8
15°	1659.9	1659.6	1659.3	1657.8	1655.1	1652.4	1649.7	1647.0
17.5°	1605.6	1604.1	1602.6	1600.8	1598.5	1596.3	1594.1	1591.9
20°	1565.7	1564.2	1562.7	1560.6	1557.9	1555.2	1552.5	1549.8
22.5°	1526.1	1523.1	1520.2	1517.6	1515.4	1513.2	1510.9	1508.7
25°	1461.0	1457.1	1453.2	1449.6	1446.3	1443.0	1439.7	1436.4
27.5°	1390.6	1385.2	1379.7	1375.4	1372.2	1369.0	1365.8	1362.7
30°	1340.2	1333.3	1326.4	1321.6	1318.9	1316.2	1313.5	1310.8
32.5°	1291.3	1283.6	1276.0	1270.5	1267.1	1263.7	1260.2	1256.8
35°	1215.1	1206.4	1197.7	1191.3	1187.1	1182.9	1178.7	1174.5
37.5°	1135.5	1125.1	1114.6	1107.4	1103.3	1099.2	1095.1	1091.0
40°	1082.8	1071.4	1060.0	1052.5	1048.9	1045.3	1041.7	1038.1
42.5°	1030.9	1019.9	1009.0	1000.9	995.6	990.4	985.1	979.8
45°	948.0	936.0	924.0	915.7	911.2	906.7	902.2	897.7
47.5°	866.0	853.6	841.3	832.6	827.6	822.6	817.7	812.7
50°	810.4	797.8	785.2	776.7	772.2	767.7	763.2	758.7
52.5°	757.8	744.2	730.6	721.6	717.1	712.6	708.1	703.6
55°	677.7	664.2	650.7	641.5	636.7	631.9	627.1	622.3
57.5°	597.6	584.4	571.2	562.4	558.2	553.9	549.6	545.4
60°	544.6	531.4	518.2	509.4	504.9	500.4	495.9	491.4
62.5°	492.6	480.3	468.1	459.7	455.2	450.7	446.2	441.7
65°	416.1	404.1	392.1	383.8	379.3	374.8	370.3	365.8
67.5°	343.1	332.1	321.1	313.8	310.2	306.6	303.0	299.4
70°	294.6	285.3	276.0	269.5	265.9	262.3	258.7	255.1
72.5°	249.6	241.0	232.4	226.9	224.5	222.1	219.7	217.3
75°	186.6	180.0	173.4	169.0	166.9	164.8	162.7	160.6
77.5°	132.8	128.2	123.5	120.4	118.9	117.3	115.8	114.2
80°	99.9	97.2	94.5	92.8	92.2	91.6	91.0	90.4
82.5°	74.7	73.4	72.2	71.4	71.0	70.6	70.3	69.9
85°	42.6	42.3	42.0	41.7	41.4	41.1	40.8	40.5
87.5°	18.3	18.4	18.5	18.5	18.3	18.2	18.0	17.9
90°	10.4	11.0	11.7	12.2	12.6	12.9	13.3	13.7
92.5°	23.6	24.4	25.3	25.8	26.1	26.4	26.6	26.9
95°	45.7	46.6	47.5	48.0	48.3	48.6	48.8	49.1
97.5°	71.6	72.5	73.3	73.8	73.9	74.1	74.2	74.4
100°	89.6	90.7	91.8	92.5	92.8	93.1	93.3	93.6
102.5°	108.0	109.3	110.5	111.3	111.7	112.0	112.4	112.7
105°	137.9	138.6	139.4	140.0	140.3	140.7	141.1	141.5
107.5°	170.1	170.5	170.8	171.0	171.0	171.0	170.9	170.9
110°	192.4	192.8	193.2	193.3	193.2	193.1	192.9	192.8



TEST NUMBER: P333590

CATALOG NUMBER: S125RDIP-S1090D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	214.9	215.0	215.2	215.2	215.0	214.7	214.5	214.3
115°	249.0	248.9	248.8	248.7	248.5	248.4	248.3	248.2
117.5°	283.3	283.4	283.5	283.3	282.8	282.3	281.8	281.2
120°	306.3	306.3	306.3	306.1	305.6	305.1	304.6	304.1
122.5°	329.0	328.9	328.8	328.5	328.1	327.7	327.3	326.9
125°	362.3	362.1	361.8	361.6	361.5	361.4	361.2	361.1
127.5°	395.4	395.3	395.2	395.0	394.7	394.5	394.2	394.0
130°	417.3	417.2	417.1	416.9	416.6	416.4	416.1	415.9
132.5°	438.3	438.2	438.1	437.8	437.5	437.1	436.8	436.4
135°	470.6	470.6	470.6	470.4	469.9	469.4	468.9	468.4
137.5°	502.1	502.2	502.4	502.2	501.5	500.9	500.3	499.6
140°	521.9	522.2	522.4	522.2	521.6	521.0	520.3	519.7
142.5°	541.3	541.5	541.6	541.4	540.8	540.1	539.5	538.9
145°	569.3	569.3	569.3	569.1	568.8	568.4	568.0	567.6
147.5°	595.3	595.6	595.9	595.6	594.7	593.9	593.0	592.2
150°	611.5	611.5	611.5	611.4	611.2	610.9	610.7	610.4
152.5°	626.8	627.1	627.4	627.3	626.8	626.4	625.9	625.5
155°	648.5	649.0	649.5	649.5	648.8	648.2	647.5	646.9
157.5°	667.3	667.8	668.3	668.2	667.3	666.5	665.7	664.8
160°	678.7	679.2	679.7	679.7	679.1	678.4	677.8	677.2
162.5°	689.4	690.0	690.7	690.6	689.9	689.1	688.4	687.6
165°	703.8	704.3	704.9	704.7	704.0	703.2	702.4	701.7
167.5°	714.5	715.3	716.0	716.0	715.2	714.4	713.6	712.9
170°	720.9	721.6	722.4	722.3	721.5	720.6	719.7	718.8
172.5°	725.5	726.2	727.0	727.0	726.2	725.4	724.6	723.8
175°	730.6	731.3	732.1	732.0	731.2	730.3	729.4	728.5
177.5°	732.9	733.5	734.1	734.1	733.4	732.7	731.9	731.2
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1

(END OF REPORT)