

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333594

Luminaire Tested: **S125RDIP-S1090D810U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333594
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D810U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7170.2 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59																												
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	58	57	56	51																												
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44																												
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37																												
4	77	66	59	53	72	62	56	50	55	50	45	48	44	40	42	38	36	32																												
5	71	59	51	45	66	56	49	43	49	44	39	43	39	35	38	34	31	28																												
6	65	53	45	40	61	50	43	38	45	39	34	39	35	31	34	31	28	25																												
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	31	28	25	22																												
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20																												
9	52	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20	18																												
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10619	10619	10619	10619
5°	12217	10633	9390	10633
10°	14014	10579	8286	10579
15°	15136	10470	7365	10470
20°	16690	10344	6801	10344
25°	19316	10177	6310	10177
30°	21020	10001	5990	10001
35°	17731	9797	5694	9797
40°	12382	9429	5440	9429
45°	9186	8933	5191	8933
50°	7324	8416	4977	8416
55°	6217	7775	4788	7775
60°	5371	7201	4481	7201
65°	4786	6580	3857	6580
70°	4205	6027	3518	6027
75°	3638	5220	3301	5220
80°	2760	4392	2760	4392
85°	2297	3453	2601	3453



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	2.2
10°-20°	462.1	6.4
20°-30°	732.6	10.2
30°-40°	883.5	12.3
40°-50°	789.0	11.0
50°-60°	605.0	8.4
60°-70°	393.2	5.5
70°-80°	191.2	2.7
80°-90°	47.8	0.7
90°-100°	281.1	3.9
100°-110°	604.3	8.4
110°-120°	567.1	7.9
120°-130°	459.6	6.4
130°-140°	368.8	5.1
140°-150°	278.3	3.9
150°-160°	195.9	2.7
160°-170°	115.5	1.6
170°-180°	37.6	0.5
0°-30°	1352.3	18.9
0°-40°	2235.8	31.2
0°-60°	3629.8	50.6
0°-90°	4261.9	59.4
90°-120°	1452.5	20.3
90°-150°	2559.3	35.7
90°-180°	2908.0	40.6
0°-180°	7170.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1884	1640	1448	1640	1884	188
15°	2264	1566	1102	1566	2264	649
25°	2711	1428	886	1428	2711	1245
35°	2249	1243	722	1243	2249	1358
45°	1006	978	568	978	1006	802
55°	552	690	425	690	552	501
65°	313	431	252	431	313	312
75°	146	209	132	209	146	155
85°	31	47	35	47	31	36
90°	18	1	18	1	18	14
95°	184	26	184	26	184	260
105°	1036	88	1036	88	1036	1030
115°	1154	158	1154	158	1154	1128
125°	909	219	909	219	909	823
135°	755	256	755	256	755	585
145°	596	299	596	299	596	379
155°	500	341	500	341	500	233
165°	438	372	438	372	438	125
175°	393	387	393	387	393	38
180°	388	388	388	388	388	



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1729.5	1728.4	1730.6	1724.6	1725.2	1716.0	1716.0	1709.0	1699.8	1692.8	1689.5
5°	1884.4	1885.8	1883.1	1873.0	1866.2	1856.1	1844.6	1824.4	1807.5	1791.3	1778.5
7.5°	2044.0	2044.9	2036.0	2032.9	2015.9	2003.5	1978.0	1950.4	1926.0	1895.0	1871.2
10°	2136.9	2136.2	2126.7	2119.3	2104.5	2085.6	2060.6	2028.2	1997.8	1964.1	1931.7
12.5°	2190.9	2189.1	2186.1	2177.1	2163.3	2146.6	2125.4	2093.5	2056.1	2019.2	1981.4
15°	2263.8	2259.0	2250.3	2238.8	2219.2	2199.6	2176.0	2147.7	2111.9	2070.0	2035.0
17.5°	2353.9	2354.1	2340.6	2324.6	2298.0	2263.5	2227.0	2181.3	2132.7	2086.7	2049.3
20°	2428.4	2426.4	2412.9	2381.9	2351.5	2308.3	2266.5	2210.4	2151.0	2091.0	2044.4
22.5°	2535.4	2530.1	2516.0	2475.3	2428.2	2372.6	2308.6	2240.1	2168.3	2100.1	2039.0
25°	2710.6	2706.5	2678.8	2631.6	2565.5	2479.7	2396.0	2302.2	2199.0	2109.2	2035.0
27.5°	2830.4	2826.0	2805.5	2766.2	2705.2	2615.0	2501.7	2376.3	2247.4	2123.9	2016.9
30°	2818.6	2828.7	2826.0	2807.8	2761.9	2680.9	2576.3	2435.2	2282.0	2136.9	2009.3
32.5°	2649.0	2658.1	2681.8	2717.6	2720.3	2687.9	2609.7	2479.5	2320.9	2155.8	2003.4
35°	2248.9	2261.1	2307.0	2379.2	2473.7	2552.6	2568.8	2498.6	2356.2	2178.7	1994.5
37.5°	1728.9	1795.3	1834.0	1910.0	2052.8	2198.0	2337.7	2389.2	2328.5	2169.3	1980.0
40°	1468.7	1484.9	1553.7	1639.4	1759.6	1910.8	2109.9	2253.6	2258.4	2147.7	1957.3
42.5°	1257.0	1277.5	1324.8	1393.2	1496.1	1647.3	1852.9	2042.5	2130.4	2088.3	1927.6
45°	1005.7	1021.2	1055.6	1108.3	1187.2	1312.1	1488.9	1708.3	1882.4	1950.6	1848.0
47.5°	826.1	834.5	864.5	904.6	963.0	1054.0	1190.9	1381.3	1590.2	1736.6	1722.2
50°	728.9	738.4	761.3	791.7	841.0	917.9	1027.3	1185.9	1401.2	1580.0	1615.8
52.5°	653.3	661.2	675.5	704.2	744.9	804.0	892.3	1035.8	1229.5	1419.7	1502.4
55°	552.1	557.5	569.0	585.2	617.6	660.1	736.4	835.6	992.2	1183.8	1305.3
57.5°	468.7	471.4	478.7	493.7	516.1	547.1	602.2	686.3	798.6	971.2	1105.3
60°	415.8	418.5	427.9	438.0	455.6	483.9	527.1	585.8	693.8	836.3	971.9
62.5°	373.6	375.3	379.3	389.4	404.8	426.7	460.7	508.6	594.5	719.6	847.7
65°	313.2	313.8	315.2	323.3	332.7	348.9	371.2	405.0	469.8	564.3	677.6
67.5°	255.1	256.1	260.8	263.6	273.5	282.0	295.1	320.9	366.5	430.2	518.4
70°	222.7	222.1	226.8	230.2	233.5	243.7	252.4	273.4	301.7	350.3	423.9
72.5°	192.5	190.7	192.8	194.0	198.4	205.3	214.1	226.9	248.8	282.3	338.6
75°	145.8	146.5	146.5	147.8	151.2	153.9	156.6	163.3	175.5	197.8	228.1
77.5°	102.3	101.2	104.1	104.5	106.5	109.5	111.8	114.5	119.5	128.6	144.3
80°	74.2	74.2	74.9	76.9	76.3	77.6	81.0	83.7	89.8	95.2	100.6
82.5°	57.0	56.4	57.1	57.5	57.4	58.7	59.9	60.5	62.8	65.5	69.2
85°	31.0	31.0	31.7	31.7	32.4	32.4	33.1	33.1	33.1	33.7	34.4
87.5°	15.5	14.9	14.2	14.2	14.8	15.5	14.9	14.2	14.0	13.8	14.1
90°	18.0	18.0	17.2	17.2	17.2	15.6	14.9	14.1	13.3	12.5	10.9
92.5°	49.9	51.1	52.2	54.1	64.1	75.7	100.6	138.6	204.1	252.1	256.1
95°	183.7	196.3	202.5	226.0	281.5	347.2	443.3	562.2	677.9	692.8	565.3
97.5°	444.1	454.1	476.8	520.6	568.9	660.2	753.9	837.3	857.7	739.8	504.8
100°	609.9	622.4	651.3	707.6	761.6	842.9	923.4	961.7	901.5	706.1	450.4
102.5°	795.0	804.4	835.8	875.9	933.6	988.6	1027.3	1003.6	875.3	646.6	409.1
105°	1036.0	1045.4	1061.0	1086.8	1111.9	1120.5	1086.1	978.9	791.3	566.9	369.1
107.5°	1163.9	1170.2	1175.3	1175.5	1162.8	1122.0	1033.7	890.7	705.6	512.0	352.2
110°	1206.5	1206.5	1201.0	1186.1	1150.9	1084.5	974.2	825.7	656.8	486.3	347.2



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1201.5	1195.8	1182.2	1156.7	1105.3	1026.9	915.4	774.4	620.5	471.3	347.2
115°	1154.1	1143.9	1122.0	1084.5	1023.5	938.3	831.2	710.0	580.9	455.1	349.5
117.5°	1071.0	1064.8	1043.0	1004.3	943.3	865.1	772.8	668.4	557.3	447.1	354.7
120°	1017.2	1011.0	989.9	952.3	894.5	825.7	739.7	645.8	544.2	443.3	359.7
122.5°	969.7	964.1	943.0	908.6	857.0	792.5	715.9	629.0	532.9	440.2	364.0
125°	909.3	901.5	884.3	852.3	808.5	752.2	684.2	604.4	517.6	436.3	371.4
127.5°	857.7	854.3	838.0	809.7	770.0	717.3	653.8	579.4	503.5	434.4	379.7
130°	829.6	824.9	809.3	783.5	744.4	693.5	632.6	563.7	494.2	433.2	384.7
132.5°	801.4	796.1	781.7	755.9	716.8	667.9	612.5	548.1	486.7	433.2	390.3
135°	755.3	750.6	736.5	710.7	676.3	631.8	581.7	527.8	477.7	433.2	398.0
137.5°	706.1	700.9	687.9	664.5	633.6	595.8	554.2	510.6	469.8	434.1	405.0
140°	671.6	667.7	656.0	635.7	606.7	573.9	537.9	501.2	466.0	434.7	408.1
142.5°	639.7	636.5	625.4	608.2	583.6	555.1	524.2	493.1	462.9	435.4	410.0
145°	595.8	592.7	584.1	570.8	552.0	530.9	506.7	482.4	458.2	434.7	412.1
147.5°	558.6	557.2	552.2	541.5	526.7	510.7	492.1	472.4	453.3	432.7	412.8
150°	537.9	537.2	534.0	524.7	512.9	498.8	484.0	466.8	449.6	430.8	412.8
152.5°	521.7	520.9	517.8	510.3	500.4	489.5	475.9	460.5	445.2	428.3	412.2
155°	499.6	498.8	496.5	491.0	483.2	474.6	463.7	451.2	437.9	423.8	410.5
157.5°	479.9	480.1	477.9	473.4	467.3	460.5	452.1	441.8	431.0	419.1	408.5
160°	466.8	467.6	466.0	462.1	456.6	451.2	443.3	435.5	425.4	416.0	406.6
162.5°	454.9	455.1	454.7	451.5	447.2	442.4	435.8	428.6	420.3	412.2	404.7
165°	437.9	437.9	437.9	436.3	433.2	429.3	424.6	419.1	412.8	406.6	401.9
167.5°	422.2	422.4	423.0	421.6	420.0	417.2	413.6	410.0	405.5	401.1	397.5
170°	412.8	413.6	413.6	412.8	411.3	409.7	407.4	405.0	401.1	398.0	395.6
172.5°	404.1	404.9	406.1	404.7	404.4	403.5	401.7	399.4	396.7	394.2	393.1
175°	393.3	394.1	395.6	394.9	394.9	394.9	393.3	393.3	390.9	390.2	390.2
177.5°	387.8	387.8	389.7	389.1	389.7	389.7	389.7	389.1	388.4	387.8	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1689.5	1685.7	1678.7	1672.2	1664.1	1657.1	1652.3	1646.3	1638.8	1629.6	1622.0
5°	1764.3	1749.4	1729.9	1713.0	1691.4	1674.5	1657.0	1640.1	1623.2	1601.6	1582.7
7.5°	1847.2	1816.5	1786.7	1749.2	1715.2	1684.8	1655.6	1626.1	1597.2	1566.5	1537.0
10°	1897.9	1860.8	1819.6	1772.4	1729.2	1688.0	1650.2	1613.1	1574.0	1539.5	1502.4
12.5°	1945.5	1897.5	1850.4	1790.8	1738.9	1688.6	1640.5	1594.2	1552.4	1507.7	1467.9
15°	1988.4	1941.1	1888.5	1815.6	1743.4	1682.6	1625.9	1565.9	1513.9	1463.9	1419.4
17.5°	2005.0	1955.4	1894.3	1824.2	1745.3	1668.9	1595.8	1530.0	1468.8	1410.6	1360.5
20°	1998.5	1950.6	1887.8	1821.0	1736.6	1657.0	1578.0	1505.1	1437.0	1375.5	1322.2
22.5°	1982.8	1933.3	1872.7	1802.1	1722.0	1637.5	1553.2	1475.4	1404.0	1340.4	1282.3
25°	1959.4	1891.9	1829.8	1760.9	1684.7	1601.0	1513.9	1428.2	1351.9	1287.1	1223.7
27.5°	1934.9	1850.7	1771.7	1703.3	1622.7	1548.0	1464.1	1376.2	1296.0	1230.0	1164.9
30°	1912.8	1818.3	1731.2	1653.6	1577.3	1506.5	1426.8	1341.1	1258.8	1190.6	1124.5
32.5°	1885.2	1784.8	1689.1	1599.6	1526.0	1455.7	1383.6	1301.7	1221.5	1151.2	1084.0
35°	1850.7	1722.5	1618.5	1523.3	1441.7	1373.5	1308.7	1242.6	1162.3	1089.4	1023.9
37.5°	1805.3	1659.8	1539.5	1435.9	1349.7	1281.3	1230.1	1169.7	1096.4	1026.6	965.8
40°	1777.8	1614.5	1482.8	1380.3	1289.8	1217.6	1169.7	1118.4	1051.6	986.1	925.3
42.5°	1741.1	1572.9	1425.6	1318.7	1227.7	1158.2	1109.7	1064.9	1008.9	947.2	882.1
45°	1669.1	1492.3	1337.7	1223.0	1131.2	1063.0	1017.8	978.0	935.5	878.8	822.1
47.5°	1575.4	1408.2	1246.5	1121.2	1031.3	968.0	924.1	892.7	862.3	814.1	759.0
50°	1500.4	1339.1	1181.1	1059.7	963.8	903.7	862.6	837.6	809.9	766.1	720.2
52.5°	1411.8	1267.8	1113.1	988.9	898.5	842.2	802.6	777.7	754.9	719.1	675.3
55°	1272.3	1146.1	1004.3	891.6	808.6	751.9	714.1	690.5	677.0	646.6	612.2
57.5°	1111.2	1020.8	895.8	787.1	713.7	657.7	630.0	609.9	594.6	573.2	548.9
60°	998.9	935.5	823.4	720.2	652.7	599.3	574.4	557.5	543.3	525.1	506.2
62.5°	885.0	838.8	741.4	652.7	590.6	545.9	522.5	507.3	491.0	478.7	460.3
65°	732.3	691.1	623.6	554.1	496.8	461.0	444.1	430.6	420.5	407.0	394.2
67.5°	569.7	552.9	506.3	458.4	417.2	385.4	370.8	361.4	349.2	341.1	332.3
70°	469.8	461.7	428.6	396.9	358.4	336.8	323.3	319.2	304.4	296.3	290.2
72.5°	381.2	377.4	358.4	336.4	309.3	290.4	277.9	273.4	263.9	257.4	253.5
75°	261.2	262.6	259.2	245.0	234.9	222.7	211.9	209.2	202.5	197.1	193.7
77.5°	165.2	172.1	172.4	171.7	167.7	160.2	155.8	153.8	147.1	145.1	144.3
80°	113.4	120.8	127.6	126.9	125.5	123.5	120.1	118.1	114.7	112.7	111.4
82.5°	75.6	82.5	88.1	91.8	91.5	89.5	87.2	86.3	85.6	84.1	83.8
85°	35.8	37.1	39.1	43.9	47.2	47.9	47.2	46.6	44.5	45.2	45.9
87.5°	14.5	14.1	14.5	14.2	13.4	15.7	17.1	17.4	16.5	15.7	15.0
90°	10.2	8.6	7.8	6.3	4.7	3.1	1.6	0.8	1.6	3.1	4.7
92.5°	178.4	106.8	64.1	41.3	27.8	18.1	11.6	9.5	11.6	18.1	27.8
95°	349.5	177.5	93.8	58.6	41.4	32.8	26.6	25.8	26.6	32.8	41.4
97.5°	279.0	152.9	97.6	72.2	56.8	48.2	43.8	42.8	43.8	48.2	56.8
100°	253.3	151.7	106.3	82.9	68.0	59.4	56.3	54.7	56.3	59.4	68.0
102.5°	242.7	157.3	117.0	94.1	80.5	71.3	68.8	67.9	68.8	71.3	80.5
105°	238.5	168.9	134.5	112.6	100.1	92.3	88.4	88.4	88.4	92.3	100.1
107.5°	245.7	186.1	152.8	133.1	120.1	113.7	109.9	108.4	109.9	113.7	120.1
110°	252.6	198.6	166.5	146.2	134.5	127.4	124.3	122.8	124.3	127.4	134.5



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.3	210.5	179.7	160.0	148.2	141.2	138.7	137.1	138.7	141.2	148.2
115°	274.4	229.1	200.2	180.6	168.9	161.9	159.5	157.9	159.5	161.9	168.9
117.5°	289.5	248.2	220.8	201.9	188.6	181.6	179.1	176.7	179.1	181.6	188.6
120°	299.5	261.9	234.6	215.0	201.7	194.7	191.6	189.2	191.6	194.7	201.7
122.5°	310.7	275.1	247.7	228.2	213.6	206.6	204.1	202.4	204.1	206.6	213.6
125°	326.0	292.4	266.6	246.3	231.4	224.4	220.5	218.9	220.5	224.4	231.4
127.5°	340.1	309.2	284.3	264.0	248.2	239.3	234.3	231.9	234.3	239.3	248.2
130°	349.5	319.8	295.6	275.2	258.8	248.6	242.4	240.0	242.4	248.6	258.8
132.5°	357.6	329.8	305.6	285.2	268.2	256.8	249.3	246.3	249.3	256.8	268.2
135°	369.1	343.3	319.0	297.9	281.5	269.0	259.6	256.5	259.6	269.0	281.5
137.5°	377.5	352.8	330.7	309.0	292.9	280.4	271.6	269.3	271.6	280.4	292.9
140°	383.1	359.7	337.0	315.9	301.0	288.5	279.1	276.8	279.1	288.5	301.0
142.5°	386.3	364.0	342.6	322.8	308.5	296.0	287.3	285.5	287.3	296.0	308.5
145°	390.9	371.4	351.1	333.1	319.0	308.1	300.2	298.7	300.2	308.1	319.0
147.5°	393.8	376.1	358.3	342.5	330.3	320.1	313.4	312.4	313.4	320.1	330.3
150°	395.6	379.2	362.0	348.7	337.8	327.6	322.1	320.6	322.1	327.6	337.8
152.5°	396.9	382.3	366.4	354.4	344.0	335.1	330.3	329.3	330.3	335.1	344.0
155°	398.0	385.5	372.2	361.2	353.4	345.6	340.9	340.9	340.9	345.6	353.4
157.5°	398.8	388.1	376.7	368.4	361.5	354.8	351.1	351.2	351.1	354.8	361.5
160°	398.8	389.4	379.2	372.2	365.9	360.5	357.3	358.1	357.3	360.5	365.9
162.5°	398.1	390.6	381.7	375.9	370.9	366.1	363.0	363.7	363.0	366.1	370.9
165°	397.2	390.9	384.7	380.0	376.9	373.0	370.6	372.2	370.6	373.0	376.9
167.5°	395.3	390.9	385.8	382.8	380.6	378.4	377.0	377.8	377.0	378.4	380.6
170°	394.1	390.9	387.0	384.7	383.1	381.6	380.8	381.6	380.8	381.6	383.1
172.5°	392.8	390.3	387.0	385.9	385.0	383.4	382.7	384.1	382.7	383.4	385.0
175°	390.9	389.4	387.0	387.0	387.0	386.3	385.5	387.0	385.5	386.3	387.0
177.5°	389.1	388.4	387.2	387.2	387.8	387.2	387.2	388.4	387.2	387.2	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1616.6	1609.1	1603.7	1592.9	1585.3	1582.1	1576.1	1574.5	1580.4	1576.1	1575.6
5°	1568.6	1549.0	1533.5	1517.9	1501.1	1490.3	1474.1	1471.4	1467.3	1461.2	1459.9
7.5°	1510.9	1485.4	1465.4	1439.8	1417.5	1399.6	1379.3	1369.7	1364.5	1356.6	1346.1
10°	1472.0	1441.7	1414.7	1389.0	1361.4	1339.1	1318.8	1303.3	1293.2	1283.7	1279.7
12.5°	1433.7	1402.8	1368.2	1337.2	1306.3	1281.3	1258.9	1248.8	1237.6	1226.5	1217.1
15°	1374.2	1333.0	1295.2	1259.4	1233.1	1206.1	1184.5	1169.7	1152.8	1148.1	1129.9
17.5°	1311.0	1270.6	1226.4	1188.7	1158.2	1128.5	1104.7	1087.9	1075.2	1057.8	1049.4
20°	1271.6	1223.7	1180.5	1146.1	1112.3	1077.2	1052.9	1038.7	1026.6	1012.4	1005.7
22.5°	1229.5	1182.6	1138.4	1098.0	1063.7	1029.2	1011.9	997.2	983.4	970.3	961.4
25°	1167.6	1120.4	1073.8	1032.0	996.2	971.2	951.0	934.1	926.7	913.9	904.4
27.5°	1106.5	1056.3	1008.0	966.2	938.2	913.5	896.9	883.5	870.1	858.9	850.7
30°	1067.1	1015.8	963.1	930.1	900.4	876.7	858.5	845.7	835.6	825.5	819.4
32.5°	1027.7	974.8	928.0	892.3	864.2	843.8	825.0	812.8	802.1	790.9	783.7
35°	964.5	910.5	872.7	837.6	809.9	791.0	778.2	760.7	751.9	743.8	736.4
37.5°	905.8	855.6	814.7	783.9	759.8	741.1	724.5	715.0	704.2	696.9	690.7
40°	862.6	816.7	779.6	747.2	729.6	708.7	693.2	681.0	672.9	663.5	656.7
42.5°	823.7	781.0	745.0	715.8	694.0	676.3	661.3	649.2	638.9	632.2	626.5
45°	768.8	726.2	691.1	664.1	643.9	627.0	611.5	605.4	591.9	583.8	581.1
47.5°	711.9	673.9	640.0	615.1	594.4	578.4	563.8	551.4	544.0	536.0	531.7
50°	673.6	637.1	605.4	581.1	560.9	543.3	529.8	521.7	511.6	504.2	498.8
52.5°	635.3	601.5	569.8	546.6	529.0	511.5	496.4	488.3	478.7	473.9	470.2
55°	580.5	544.7	517.7	494.7	476.5	460.3	446.1	438.0	432.0	427.2	425.9
57.5°	518.4	490.0	464.9	444.2	425.3	410.1	397.7	390.0	384.6	383.9	379.9
60°	477.9	452.2	429.3	407.0	390.8	376.6	365.8	357.0	351.6	351.0	349.6
62.5°	437.4	412.8	391.5	371.9	357.3	343.7	333.4	323.6	320.3	317.0	314.0
65°	377.3	355.0	337.5	321.9	306.4	294.9	284.8	278.8	271.3	267.3	259.9
67.5°	318.3	301.0	284.2	271.1	258.9	248.0	239.6	230.6	225.6	222.3	216.9
70°	279.4	265.9	249.1	234.9	225.4	216.7	209.9	199.8	196.4	193.7	191.0
72.5°	242.7	230.8	216.7	205.2	195.7	187.5	179.7	174.9	171.6	168.9	167.3
75°	191.0	179.5	167.4	159.3	152.5	145.8	141.7	138.4	137.0	136.3	133.6
77.5°	140.3	134.2	124.5	118.0	113.5	110.8	107.2	105.4	105.3	102.3	101.4
80°	107.3	103.9	95.8	93.1	89.8	87.1	85.0	81.7	78.3	76.9	74.9
82.5°	79.8	76.4	73.2	68.8	66.0	64.4	62.4	61.1	61.6	59.7	58.7
85°	42.5	39.1	37.8	37.1	35.8	37.1	36.4	35.8	35.1	34.4	35.1
87.5°	14.7	15.1	14.7	16.1	14.6	15.5	15.6	15.2	15.4	15.5	15.3
90°	6.3	7.8	8.6	10.2	10.9	12.5	13.3	14.1	14.9	15.6	17.2
92.5°	41.3	64.1	106.8	178.4	256.1	252.1	204.1	138.6	100.6	75.7	64.1
95°	58.6	93.8	177.5	349.5	565.3	692.8	677.9	562.2	443.3	347.2	281.5
97.5°	72.2	97.6	152.9	279.0	504.8	739.8	857.7	837.3	753.9	660.2	568.9
100°	82.9	106.3	151.7	253.3	450.4	706.1	901.5	961.7	923.4	842.9	761.6
102.5°	94.1	117.0	157.3	242.7	409.1	646.6	875.3	1003.6	1027.3	988.6	933.6
105°	112.6	134.5	168.9	238.5	369.1	566.9	791.3	978.9	1086.1	1120.5	1111.9
107.5°	133.1	152.8	186.1	245.7	352.2	512.0	705.6	890.7	1033.7	1122.0	1162.8
110°	146.2	166.5	198.6	252.6	347.2	486.3	656.8	825.7	974.2	1084.5	1150.9



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	160.0	179.7	210.5	261.3	347.2	471.3	620.5	774.4	915.4	1026.9	1105.3
115°	180.6	200.2	229.1	274.4	349.5	455.1	580.9	710.0	831.2	938.3	1023.5
117.5°	201.9	220.8	248.2	289.5	354.7	447.1	557.3	668.4	772.8	865.1	943.3
120°	215.0	234.6	261.9	299.5	359.7	443.3	544.2	645.8	739.7	825.7	894.5
122.5°	228.2	247.7	275.1	310.7	364.0	440.2	532.9	629.0	715.9	792.5	857.0
125°	246.3	266.6	292.4	326.0	371.4	436.3	517.6	604.4	684.2	752.2	808.5
127.5°	264.0	284.3	309.2	340.1	379.7	434.4	503.5	579.4	653.8	717.3	770.0
130°	275.2	295.6	319.8	349.5	384.7	433.2	494.2	563.7	632.6	693.5	744.4
132.5°	285.2	305.6	329.8	357.6	390.3	433.2	486.7	548.1	612.5	667.9	716.8
135°	297.9	319.0	343.3	369.1	398.0	433.2	477.7	527.8	581.7	631.8	676.3
137.5°	309.0	330.7	352.8	377.5	405.0	434.1	469.8	510.6	554.2	595.8	633.6
140°	315.9	337.0	359.7	383.1	408.1	434.7	466.0	501.2	537.9	573.9	606.7
142.5°	322.8	342.6	364.0	386.3	410.0	435.4	462.9	493.1	524.2	555.1	583.6
145°	333.1	351.1	371.4	390.9	412.1	434.7	458.2	482.4	506.7	530.9	552.0
147.5°	342.5	358.3	376.1	393.8	412.8	432.7	453.3	472.4	492.1	510.7	526.7
150°	348.7	362.0	379.2	395.6	412.8	430.8	449.6	466.8	484.0	498.8	512.9
152.5°	354.4	366.4	382.3	396.9	412.2	428.3	445.2	460.5	475.9	489.5	500.4
155°	361.2	372.2	385.5	398.0	410.5	423.8	437.9	451.2	463.7	474.6	483.2
157.5°	368.4	376.7	388.1	398.8	408.5	419.1	431.0	441.8	452.1	460.5	467.3
160°	372.2	379.2	389.4	398.8	406.6	416.0	425.4	435.5	443.3	451.2	456.6
162.5°	375.9	381.7	390.6	398.1	404.7	412.2	420.3	428.6	435.8	442.4	447.2
165°	380.0	384.7	390.9	397.2	401.9	406.6	412.8	419.1	424.6	429.3	433.2
167.5°	382.8	385.8	390.9	395.3	397.5	401.1	405.5	410.0	413.6	417.2	420.0
170°	384.7	387.0	390.9	394.1	395.6	398.0	401.1	405.0	407.4	409.7	411.3
172.5°	385.9	387.0	390.3	392.8	393.1	394.2	396.7	399.4	401.7	403.5	404.4
175°	387.0	387.0	389.4	390.9	390.2	390.2	390.9	393.3	393.3	394.9	394.9
177.5°	387.2	387.2	388.4	389.1	387.8	387.8	388.4	389.1	389.7	389.7	389.7
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1575.0	1569.1	1567.5	1569.6	1567.5	1569.1	1575.0	1575.6	1576.1	1580.4	1574.5
5°	1453.2	1446.4	1449.8	1448.4	1449.8	1446.4	1453.2	1459.9	1461.2	1467.3	1471.4
7.5°	1346.0	1337.6	1328.7	1331.5	1328.7	1337.6	1346.0	1346.1	1356.6	1364.5	1369.7
10°	1270.9	1264.2	1260.1	1263.5	1260.1	1264.2	1270.9	1279.7	1283.7	1293.2	1303.3
12.5°	1207.7	1203.7	1200.2	1198.7	1200.2	1203.7	1207.7	1217.1	1226.5	1237.6	1248.8
15°	1121.8	1113.7	1110.3	1101.5	1110.3	1113.7	1121.8	1129.9	1148.1	1152.8	1169.7
17.5°	1042.5	1039.8	1031.0	1027.3	1031.0	1039.8	1042.5	1049.4	1057.8	1075.2	1087.9
20°	995.5	992.8	984.1	989.5	984.1	992.8	995.5	1005.7	1012.4	1026.6	1038.7
22.5°	956.7	950.7	947.9	946.3	947.9	950.7	956.7	961.4	970.3	983.4	997.2
25°	901.7	892.9	889.6	885.5	889.6	892.9	901.7	904.4	913.9	926.7	934.1
27.5°	846.9	842.2	837.7	836.7	837.7	842.2	846.9	850.7	858.9	870.1	883.5
30°	811.3	806.6	803.2	803.2	803.2	806.6	811.3	819.4	825.5	835.6	845.7
32.5°	779.4	775.8	772.4	771.9	772.4	775.8	779.4	783.7	790.9	802.1	812.8
35°	733.0	727.6	726.2	722.2	726.2	727.6	733.0	736.4	743.8	751.9	760.7
37.5°	684.8	680.3	680.2	679.8	680.2	680.3	684.8	690.7	696.9	704.2	715.0
40°	654.0	650.6	650.0	645.2	650.0	650.6	654.0	656.7	663.5	672.9	681.0
42.5°	621.1	619.3	617.0	615.0	617.0	619.3	621.1	626.5	632.2	638.9	649.2
45°	576.4	571.7	571.7	568.3	571.7	571.7	576.4	581.1	583.8	591.9	605.4
47.5°	530.2	526.6	527.0	523.5	527.0	526.6	530.2	531.7	536.0	544.0	551.4
50°	499.5	497.4	496.8	495.4	496.8	497.4	499.5	498.8	504.2	511.6	521.7
52.5°	468.7	467.7	470.3	467.3	470.3	467.7	468.7	470.2	473.9	478.7	488.3
55°	427.2	425.2	429.3	425.2	429.3	425.2	427.2	425.9	427.2	432.0	438.0
57.5°	379.6	377.7	381.3	379.3	381.3	377.7	379.6	379.9	383.9	384.6	390.0
60°	348.3	344.2	346.2	346.9	346.2	344.2	348.3	349.6	351.0	351.6	357.0
62.5°	311.0	308.6	310.1	307.0	310.1	308.6	311.0	314.0	317.0	320.3	323.6
65°	258.5	256.5	253.8	252.4	253.8	256.5	258.5	259.9	267.3	271.3	278.8
67.5°	217.2	212.3	212.2	213.3	212.2	212.3	217.2	216.9	222.3	225.6	230.6
70°	187.0	187.0	186.3	186.3	186.3	187.0	187.0	191.0	193.7	196.4	199.8
72.5°	165.9	165.4	164.1	163.6	164.1	165.4	165.9	167.3	168.9	171.6	174.9
75°	133.6	134.3	133.0	132.3	133.0	134.3	133.6	133.6	136.3	137.0	138.4
77.5°	98.7	95.8	97.3	95.8	97.3	95.8	98.7	101.4	102.3	105.3	105.4
80°	74.9	74.2	76.3	74.2	76.3	74.2	74.9	74.9	76.9	78.3	81.7
82.5°	59.3	58.6	59.5	58.0	59.5	58.6	59.3	58.7	59.7	61.6	61.1
85°	35.8	35.1	34.4	35.1	34.4	35.1	35.8	35.1	34.4	35.1	35.8
87.5°	15.9	15.3	15.5	15.5	15.5	15.3	15.9	15.3	15.5	15.4	15.2
90°	17.2	17.2	18.0	18.0	18.0	17.2	17.2	17.2	15.6	14.9	14.1
92.5°	54.1	52.2	51.1	49.9	51.1	52.2	54.1	64.1	75.7	100.6	138.6
95°	226.0	202.5	196.3	183.7	196.3	202.5	226.0	281.5	347.2	443.3	562.2
97.5°	520.6	476.8	454.1	444.1	454.1	476.8	520.6	568.9	660.2	753.9	837.3
100°	707.6	651.3	622.4	609.9	622.4	651.3	707.6	761.6	842.9	923.4	961.7
102.5°	875.9	835.8	804.4	795.0	804.4	835.8	875.9	933.6	988.6	1027.3	1003.6
105°	1086.8	1061.0	1045.4	1036.0	1045.4	1061.0	1086.8	1111.9	1120.5	1086.1	978.9
107.5°	1175.5	1175.3	1170.2	1163.9	1170.2	1175.3	1175.5	1162.8	1122.0	1033.7	890.7
110°	1186.1	1201.0	1206.5	1206.5	1206.5	1201.0	1186.1	1150.9	1084.5	974.2	825.7



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1156.7	1182.2	1195.8	1201.5	1195.8	1182.2	1156.7	1105.3	1026.9	915.4	774.4
115°	1084.5	1122.0	1143.9	1154.1	1143.9	1122.0	1084.5	1023.5	938.3	831.2	710.0
117.5°	1004.3	1043.0	1064.8	1071.0	1064.8	1043.0	1004.3	943.3	865.1	772.8	668.4
120°	952.3	989.9	1011.0	1017.2	1011.0	989.9	952.3	894.5	825.7	739.7	645.8
122.5°	908.6	943.0	964.1	969.7	964.1	943.0	908.6	857.0	792.5	715.9	629.0
125°	852.3	884.3	901.5	909.3	901.5	884.3	852.3	808.5	752.2	684.2	604.4
127.5°	809.7	838.0	854.3	857.7	854.3	838.0	809.7	770.0	717.3	653.8	579.4
130°	783.5	809.3	824.9	829.6	824.9	809.3	783.5	744.4	693.5	632.6	563.7
132.5°	755.9	781.7	796.1	801.4	796.1	781.7	755.9	716.8	667.9	612.5	548.1
135°	710.7	736.5	750.6	755.3	750.6	736.5	710.7	676.3	631.8	581.7	527.8
137.5°	664.5	687.9	700.9	706.1	700.9	687.9	664.5	633.6	595.8	554.2	510.6
140°	635.7	656.0	667.7	671.6	667.7	656.0	635.7	606.7	573.9	537.9	501.2
142.5°	608.2	625.4	636.5	639.7	636.5	625.4	608.2	583.6	555.1	524.2	493.1
145°	570.8	584.1	592.7	595.8	592.7	584.1	570.8	552.0	530.9	506.7	482.4
147.5°	541.5	552.2	557.2	558.6	557.2	552.2	541.5	526.7	510.7	492.1	472.4
150°	524.7	534.0	537.2	537.9	537.2	534.0	524.7	512.9	498.8	484.0	466.8
152.5°	510.3	517.8	520.9	521.7	520.9	517.8	510.3	500.4	489.5	475.9	460.5
155°	491.0	496.5	498.8	499.6	498.8	496.5	491.0	483.2	474.6	463.7	451.2
157.5°	473.4	477.9	480.1	479.9	480.1	477.9	473.4	467.3	460.5	452.1	441.8
160°	462.1	466.0	467.6	466.8	467.6	466.0	462.1	456.6	451.2	443.3	435.5
162.5°	451.5	454.7	455.1	454.9	455.1	454.7	451.5	447.2	442.4	435.8	428.6
165°	436.3	437.9	437.9	437.9	437.9	437.9	436.3	433.2	429.3	424.6	419.1
167.5°	421.6	423.0	422.4	422.2	422.4	423.0	421.6	420.0	417.2	413.6	410.0
170°	412.8	413.6	413.6	412.8	413.6	413.6	412.8	411.3	409.7	407.4	405.0
172.5°	404.7	406.1	404.9	404.1	404.9	406.1	404.7	404.4	403.5	401.7	399.4
175°	394.9	395.6	394.1	393.3	394.1	395.6	394.9	394.9	394.9	393.3	393.3
177.5°	389.1	389.7	387.8	387.8	387.8	389.7	389.1	389.7	389.7	389.7	389.1
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1576.1	1582.1	1585.3	1592.9	1603.7	1609.1	1616.6	1622.0	1629.6	1638.8	1646.3
5°	1474.1	1490.3	1501.1	1517.9	1533.5	1549.0	1568.6	1582.7	1601.6	1623.2	1640.1
7.5°	1379.3	1399.6	1417.5	1439.8	1465.4	1485.4	1510.9	1537.0	1566.5	1597.2	1626.1
10°	1318.8	1339.1	1361.4	1389.0	1414.7	1441.7	1472.0	1502.4	1539.5	1574.0	1613.1
12.5°	1258.9	1281.3	1306.3	1337.2	1368.2	1402.8	1433.7	1467.9	1507.7	1552.4	1594.2
15°	1184.5	1206.1	1233.1	1259.4	1295.2	1333.0	1374.2	1419.4	1463.9	1513.9	1565.9
17.5°	1104.7	1128.5	1158.2	1188.7	1226.4	1270.6	1311.0	1360.5	1410.6	1468.8	1530.0
20°	1052.9	1077.2	1112.3	1146.1	1180.5	1223.7	1271.6	1322.2	1375.5	1437.0	1505.1
22.5°	1011.9	1029.2	1063.7	1098.0	1138.4	1182.6	1229.5	1282.3	1340.4	1404.0	1475.4
25°	951.0	971.2	996.2	1032.0	1073.8	1120.4	1167.6	1223.7	1287.1	1351.9	1428.2
27.5°	896.9	913.5	938.2	966.2	1008.0	1056.3	1106.5	1164.9	1230.0	1296.0	1376.2
30°	858.5	876.7	900.4	930.1	963.1	1015.8	1067.1	1124.5	1190.6	1258.8	1341.1
32.5°	825.0	843.8	864.2	892.3	928.0	974.8	1027.7	1084.0	1151.2	1221.5	1301.7
35°	778.2	791.0	809.9	837.6	872.7	910.5	964.5	1023.9	1089.4	1162.3	1242.6
37.5°	724.5	741.1	759.8	783.9	814.7	855.6	905.8	965.8	1026.6	1096.4	1169.7
40°	693.2	708.7	729.6	747.2	779.6	816.7	862.6	925.3	986.1	1051.6	1118.4
42.5°	661.3	676.3	694.0	715.8	745.0	781.0	823.7	882.1	947.2	1008.9	1064.9
45°	611.5	627.0	643.9	664.1	691.1	726.2	768.8	822.1	878.8	935.5	978.0
47.5°	563.8	578.4	594.4	615.1	640.0	673.9	711.9	759.0	814.1	862.3	892.7
50°	529.8	543.3	560.9	581.1	605.4	637.1	673.6	720.2	766.1	809.9	837.6
52.5°	496.4	511.5	529.0	546.6	569.8	601.5	635.3	675.3	719.1	754.9	777.7
55°	446.1	460.3	476.5	494.7	517.7	544.7	580.5	612.2	646.6	677.0	690.5
57.5°	397.7	410.1	425.3	444.2	464.9	490.0	518.4	548.9	573.2	594.6	609.9
60°	365.8	376.6	390.8	407.0	429.3	452.2	477.9	506.2	525.1	543.3	557.5
62.5°	333.4	343.7	357.3	371.9	391.5	412.8	437.4	460.3	478.7	491.0	507.3
65°	284.8	294.9	306.4	321.9	337.5	355.0	377.3	394.2	407.0	420.5	430.6
67.5°	239.6	248.0	258.9	271.1	284.2	301.0	318.3	332.3	341.1	349.2	361.4
70°	209.9	216.7	225.4	234.9	249.1	265.9	279.4	290.2	296.3	304.4	319.2
72.5°	179.7	187.5	195.7	205.2	216.7	230.8	242.7	253.5	257.4	263.9	273.4
75°	141.7	145.8	152.5	159.3	167.4	179.5	191.0	193.7	197.1	202.5	209.2
77.5°	107.2	110.8	113.5	118.0	124.5	134.2	140.3	144.3	145.1	147.1	153.8
80°	85.0	87.1	89.8	93.1	95.8	103.9	107.3	111.4	112.7	114.7	118.1
82.5°	62.4	64.4	66.0	68.8	73.2	76.4	79.8	83.8	84.1	85.6	86.3
85°	36.4	37.1	35.8	37.1	37.8	39.1	42.5	45.9	45.2	44.5	46.6
87.5°	15.6	15.5	14.6	16.1	14.7	15.1	14.7	15.0	15.7	16.5	17.4
90°	13.3	12.5	10.9	10.2	8.6	7.8	6.3	4.7	3.1	1.6	0.8
92.5°	204.1	252.1	256.1	178.4	106.8	64.1	41.3	27.8	18.1	11.6	9.5
95°	677.9	692.8	565.3	349.5	177.5	93.8	58.6	41.4	32.8	26.6	25.8
97.5°	857.7	739.8	504.8	279.0	152.9	97.6	72.2	56.8	48.2	43.8	42.8
100°	901.5	706.1	450.4	253.3	151.7	106.3	82.9	68.0	59.4	56.3	54.7
102.5°	875.3	646.6	409.1	242.7	157.3	117.0	94.1	80.5	71.3	68.8	67.9
105°	791.3	566.9	369.1	238.5	168.9	134.5	112.6	100.1	92.3	88.4	88.4
107.5°	705.6	512.0	352.2	245.7	186.1	152.8	133.1	120.1	113.7	109.9	108.4
110°	656.8	486.3	347.2	252.6	198.6	166.5	146.2	134.5	127.4	124.3	122.8



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	620.5	471.3	347.2	261.3	210.5	179.7	160.0	148.2	141.2	138.7	137.1
115°	580.9	455.1	349.5	274.4	229.1	200.2	180.6	168.9	161.9	159.5	157.9
117.5°	557.3	447.1	354.7	289.5	248.2	220.8	201.9	188.6	181.6	179.1	176.7
120°	544.2	443.3	359.7	299.5	261.9	234.6	215.0	201.7	194.7	191.6	189.2
122.5°	532.9	440.2	364.0	310.7	275.1	247.7	228.2	213.6	206.6	204.1	202.4
125°	517.6	436.3	371.4	326.0	292.4	266.6	246.3	231.4	224.4	220.5	218.9
127.5°	503.5	434.4	379.7	340.1	309.2	284.3	264.0	248.2	239.3	234.3	231.9
130°	494.2	433.2	384.7	349.5	319.8	295.6	275.2	258.8	248.6	242.4	240.0
132.5°	486.7	433.2	390.3	357.6	329.8	305.6	285.2	268.2	256.8	249.3	246.3
135°	477.7	433.2	398.0	369.1	343.3	319.0	297.9	281.5	269.0	259.6	256.5
137.5°	469.8	434.1	405.0	377.5	352.8	330.7	309.0	292.9	280.4	271.6	269.3
140°	466.0	434.7	408.1	383.1	359.7	337.0	315.9	301.0	288.5	279.1	276.8
142.5°	462.9	435.4	410.0	386.3	364.0	342.6	322.8	308.5	296.0	287.3	285.5
145°	458.2	434.7	412.1	390.9	371.4	351.1	333.1	319.0	308.1	300.2	298.7
147.5°	453.3	432.7	412.8	393.8	376.1	358.3	342.5	330.3	320.1	313.4	312.4
150°	449.6	430.8	412.8	395.6	379.2	362.0	348.7	337.8	327.6	322.1	320.6
152.5°	445.2	428.3	412.2	396.9	382.3	366.4	354.4	344.0	335.1	330.3	329.3
155°	437.9	423.8	410.5	398.0	385.5	372.2	361.2	353.4	345.6	340.9	340.9
157.5°	431.0	419.1	408.5	398.8	388.1	376.7	368.4	361.5	354.8	351.1	351.2
160°	425.4	416.0	406.6	398.8	389.4	379.2	372.2	365.9	360.5	357.3	358.1
162.5°	420.3	412.2	404.7	398.1	390.6	381.7	375.9	370.9	366.1	363.0	363.7
165°	412.8	406.6	401.9	397.2	390.9	384.7	380.0	376.9	373.0	370.6	372.2
167.5°	405.5	401.1	397.5	395.3	390.9	385.8	382.8	380.6	378.4	377.0	377.8
170°	401.1	398.0	395.6	394.1	390.9	387.0	384.7	383.1	381.6	380.8	381.6
172.5°	396.7	394.2	393.1	392.8	390.3	387.0	385.9	385.0	383.4	382.7	384.1
175°	390.9	390.2	390.2	390.9	389.4	387.0	387.0	387.0	386.3	385.5	387.0
177.5°	388.4	387.8	387.8	389.1	388.4	387.2	387.2	387.8	387.2	387.2	388.4
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1652.3	1657.1	1664.1	1672.2	1678.7	1685.7	1689.5	1689.5	1692.8	1699.8	1709.0
5°	1657.0	1674.5	1691.4	1713.0	1729.9	1749.4	1764.3	1778.5	1791.3	1807.5	1824.4
7.5°	1655.6	1684.8	1715.2	1749.2	1786.7	1816.5	1847.2	1871.2	1895.0	1926.0	1950.4
10°	1650.2	1688.0	1729.2	1772.4	1819.6	1860.8	1897.9	1931.7	1964.1	1997.8	2028.2
12.5°	1640.5	1688.6	1738.9	1790.8	1850.4	1897.5	1945.5	1981.4	2019.2	2056.1	2093.5
15°	1625.9	1682.6	1743.4	1815.6	1888.5	1941.1	1988.4	2035.0	2070.0	2111.9	2147.7
17.5°	1595.8	1668.9	1745.3	1824.2	1894.3	1955.4	2005.0	2049.3	2086.7	2132.7	2181.3
20°	1578.0	1657.0	1736.6	1821.0	1887.8	1950.6	1998.5	2044.4	2091.0	2151.0	2210.4
22.5°	1553.2	1637.5	1722.0	1802.1	1872.7	1933.3	1982.8	2039.0	2100.1	2168.3	2240.1
25°	1513.9	1601.0	1684.7	1760.9	1829.8	1891.9	1959.4	2035.0	2109.2	2199.0	2302.2
27.5°	1464.1	1548.0	1622.7	1703.3	1771.7	1850.7	1934.9	2016.9	2123.9	2247.4	2376.3
30°	1426.8	1506.5	1577.3	1653.6	1731.2	1818.3	1912.8	2009.3	2136.9	2282.0	2435.2
32.5°	1383.6	1455.7	1526.0	1599.6	1689.1	1784.8	1885.2	2003.4	2155.8	2320.9	2479.5
35°	1308.7	1373.5	1441.7	1523.3	1618.5	1722.5	1850.7	1994.5	2178.7	2356.2	2498.6
37.5°	1230.1	1281.3	1349.7	1435.9	1539.5	1659.8	1805.3	1980.0	2169.3	2328.5	2389.2
40°	1169.7	1217.6	1289.8	1380.3	1482.8	1614.5	1777.8	1957.3	2147.7	2258.4	2253.6
42.5°	1109.7	1158.2	1227.7	1318.7	1425.6	1572.9	1741.1	1927.6	2088.3	2130.4	2042.5
45°	1017.8	1063.0	1131.2	1223.0	1337.7	1492.3	1669.1	1848.0	1950.6	1882.4	1708.3
47.5°	924.1	968.0	1031.3	1121.2	1246.5	1408.2	1575.4	1722.2	1736.6	1590.2	1381.3
50°	862.6	903.7	963.8	1059.7	1181.1	1339.1	1500.4	1615.8	1580.0	1401.2	1185.9
52.5°	802.6	842.2	898.5	988.9	1113.1	1267.8	1411.8	1502.4	1419.7	1229.5	1035.8
55°	714.1	751.9	808.6	891.6	1004.3	1146.1	1272.3	1305.3	1183.8	992.2	835.6
57.5°	630.0	657.7	713.7	787.1	895.8	1020.8	1111.2	1105.3	971.2	798.6	686.3
60°	574.4	599.3	652.7	720.2	823.4	935.5	998.9	971.9	836.3	693.8	585.8
62.5°	522.5	545.9	590.6	652.7	741.4	838.8	885.0	847.7	719.6	594.5	508.6
65°	444.1	461.0	496.8	554.1	623.6	691.1	732.3	677.6	564.3	469.8	405.0
67.5°	370.8	385.4	417.2	458.4	506.3	552.9	569.7	518.4	430.2	366.5	320.9
70°	323.3	336.8	358.4	396.9	428.6	461.7	469.8	423.9	350.3	301.7	273.4
72.5°	277.9	290.4	309.3	336.4	358.4	377.4	381.2	338.6	282.3	248.8	226.9
75°	211.9	222.7	234.9	245.0	259.2	262.6	261.2	228.1	197.8	175.5	163.3
77.5°	155.8	160.2	167.7	171.7	172.4	172.1	165.2	144.3	128.6	119.5	114.5
80°	120.1	123.5	125.5	126.9	127.6	120.8	113.4	100.6	95.2	89.8	83.7
82.5°	87.2	89.5	91.5	91.8	88.1	82.5	75.6	69.2	65.5	62.8	60.5
85°	47.2	47.9	47.2	43.9	39.1	37.1	35.8	34.4	33.7	33.1	33.1
87.5°	17.1	15.7	13.4	14.2	14.5	14.1	14.5	14.1	13.8	14.0	14.2
90°	1.6	3.1	4.7	6.3	7.8	8.6	10.2	10.9	12.5	13.3	14.1
92.5°	11.6	18.1	27.8	41.3	64.1	106.8	178.4	256.1	252.1	204.1	138.6
95°	26.6	32.8	41.4	58.6	93.8	177.5	349.5	565.3	692.8	677.9	562.2
97.5°	43.8	48.2	56.8	72.2	97.6	152.9	279.0	504.8	739.8	857.7	837.3
100°	56.3	59.4	68.0	82.9	106.3	151.7	253.3	450.4	706.1	901.5	961.7
102.5°	68.8	71.3	80.5	94.1	117.0	157.3	242.7	409.1	646.6	875.3	1003.6
105°	88.4	92.3	100.1	112.6	134.5	168.9	238.5	369.1	566.9	791.3	978.9
107.5°	109.9	113.7	120.1	133.1	152.8	186.1	245.7	352.2	512.0	705.6	890.7
110°	124.3	127.4	134.5	146.2	166.5	198.6	252.6	347.2	486.3	656.8	825.7



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	138.7	141.2	148.2	160.0	179.7	210.5	261.3	347.2	471.3	620.5	774.4
115°	159.5	161.9	168.9	180.6	200.2	229.1	274.4	349.5	455.1	580.9	710.0
117.5°	179.1	181.6	188.6	201.9	220.8	248.2	289.5	354.7	447.1	557.3	668.4
120°	191.6	194.7	201.7	215.0	234.6	261.9	299.5	359.7	443.3	544.2	645.8
122.5°	204.1	206.6	213.6	228.2	247.7	275.1	310.7	364.0	440.2	532.9	629.0
125°	220.5	224.4	231.4	246.3	266.6	292.4	326.0	371.4	436.3	517.6	604.4
127.5°	234.3	239.3	248.2	264.0	284.3	309.2	340.1	379.7	434.4	503.5	579.4
130°	242.4	248.6	258.8	275.2	295.6	319.8	349.5	384.7	433.2	494.2	563.7
132.5°	249.3	256.8	268.2	285.2	305.6	329.8	357.6	390.3	433.2	486.7	548.1
135°	259.6	269.0	281.5	297.9	319.0	343.3	369.1	398.0	433.2	477.7	527.8
137.5°	271.6	280.4	292.9	309.0	330.7	352.8	377.5	405.0	434.1	469.8	510.6
140°	279.1	288.5	301.0	315.9	337.0	359.7	383.1	408.1	434.7	466.0	501.2
142.5°	287.3	296.0	308.5	322.8	342.6	364.0	386.3	410.0	435.4	462.9	493.1
145°	300.2	308.1	319.0	333.1	351.1	371.4	390.9	412.1	434.7	458.2	482.4
147.5°	313.4	320.1	330.3	342.5	358.3	376.1	393.8	412.8	432.7	453.3	472.4
150°	322.1	327.6	337.8	348.7	362.0	379.2	395.6	412.8	430.8	449.6	466.8
152.5°	330.3	335.1	344.0	354.4	366.4	382.3	396.9	412.2	428.3	445.2	460.5
155°	340.9	345.6	353.4	361.2	372.2	385.5	398.0	410.5	423.8	437.9	451.2
157.5°	351.1	354.8	361.5	368.4	376.7	388.1	398.8	408.5	419.1	431.0	441.8
160°	357.3	360.5	365.9	372.2	379.2	389.4	398.8	406.6	416.0	425.4	435.5
162.5°	363.0	366.1	370.9	375.9	381.7	390.6	398.1	404.7	412.2	420.3	428.6
165°	370.6	373.0	376.9	380.0	384.7	390.9	397.2	401.9	406.6	412.8	419.1
167.5°	377.0	378.4	380.6	382.8	385.8	390.9	395.3	397.5	401.1	405.5	410.0
170°	380.8	381.6	383.1	384.7	387.0	390.9	394.1	395.6	398.0	401.1	405.0
172.5°	382.7	383.4	385.0	385.9	387.0	390.3	392.8	393.1	394.2	396.7	399.4
175°	385.5	386.3	387.0	387.0	387.0	389.4	390.9	390.2	390.2	390.9	393.3
177.5°	387.2	387.2	387.8	387.2	387.2	388.4	389.1	387.8	387.8	388.4	389.1
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1716.0	1716.0	1725.2	1724.6	1730.6	1728.4	1729.5
5°	1844.6	1856.1	1866.2	1873.0	1883.1	1885.8	1884.4
7.5°	1978.0	2003.5	2015.9	2032.9	2036.0	2044.9	2044.0
10°	2060.6	2085.6	2104.5	2119.3	2126.7	2136.2	2136.9
12.5°	2125.4	2146.6	2163.3	2177.1	2186.1	2189.1	2190.9
15°	2176.0	2199.6	2219.2	2238.8	2250.3	2259.0	2263.8
17.5°	2227.0	2263.5	2298.0	2324.6	2340.6	2354.1	2353.9
20°	2266.5	2308.3	2351.5	2381.9	2412.9	2426.4	2428.4
22.5°	2308.6	2372.6	2428.2	2475.3	2516.0	2530.1	2535.4
25°	2396.0	2479.7	2565.5	2631.6	2678.8	2706.5	2710.6
27.5°	2501.7	2615.0	2705.2	2766.2	2805.5	2826.0	2830.4
30°	2576.3	2680.9	2761.9	2807.8	2826.0	2828.7	2818.6
32.5°	2609.7	2687.9	2720.3	2717.6	2681.8	2658.1	2649.0
35°	2568.8	2552.6	2473.7	2379.2	2307.0	2261.1	2248.9
37.5°	2337.7	2198.0	2052.8	1910.0	1834.0	1795.3	1728.9
40°	2109.9	1910.8	1759.6	1639.4	1553.7	1484.9	1468.7
42.5°	1852.9	1647.3	1496.1	1393.2	1324.8	1277.5	1257.0
45°	1488.9	1312.1	1187.2	1108.3	1055.6	1021.2	1005.7
47.5°	1190.9	1054.0	963.0	904.6	864.5	834.5	826.1
50°	1027.3	917.9	841.0	791.7	761.3	738.4	728.9
52.5°	892.3	804.0	744.9	704.2	675.5	661.2	653.3
55°	736.4	660.1	617.6	585.2	569.0	557.5	552.1
57.5°	602.2	547.1	516.1	493.7	478.7	471.4	468.7
60°	527.1	483.9	455.6	438.0	427.9	418.5	415.8
62.5°	460.7	426.7	404.8	389.4	379.3	375.3	373.6
65°	371.2	348.9	332.7	323.3	315.2	313.8	313.2
67.5°	295.1	282.0	273.5	263.6	260.8	256.1	255.1
70°	252.4	243.7	233.5	230.2	226.8	222.1	222.7
72.5°	214.1	205.3	198.4	194.0	192.8	190.7	192.5
75°	156.6	153.9	151.2	147.8	146.5	146.5	145.8
77.5°	111.8	109.5	106.5	104.5	104.1	101.2	102.3
80°	81.0	77.6	76.3	76.9	74.9	74.2	74.2
82.5°	59.9	58.7	57.4	57.5	57.1	56.4	57.0
85°	33.1	32.4	32.4	31.7	31.7	31.0	31.0
87.5°	14.9	15.5	14.8	14.2	14.2	14.9	15.5
90°	14.9	15.6	17.2	17.2	17.2	18.0	18.0
92.5°	100.6	75.7	64.1	54.1	52.2	51.1	49.9
95°	443.3	347.2	281.5	226.0	202.5	196.3	183.7
97.5°	753.9	660.2	568.9	520.6	476.8	454.1	444.1
100°	923.4	842.9	761.6	707.6	651.3	622.4	609.9
102.5°	1027.3	988.6	933.6	875.9	835.8	804.4	795.0
105°	1086.1	1120.5	1111.9	1086.8	1061.0	1045.4	1036.0
107.5°	1033.7	1122.0	1162.8	1175.5	1175.3	1170.2	1163.9
110°	974.2	1084.5	1150.9	1186.1	1201.0	1206.5	1206.5



TEST NUMBER: P333594

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	915.4	1026.9	1105.3	1156.7	1182.2	1195.8	1201.5
115°	831.2	938.3	1023.5	1084.5	1122.0	1143.9	1154.1
117.5°	772.8	865.1	943.3	1004.3	1043.0	1064.8	1071.0
120°	739.7	825.7	894.5	952.3	989.9	1011.0	1017.2
122.5°	715.9	792.5	857.0	908.6	943.0	964.1	969.7
125°	684.2	752.2	808.5	852.3	884.3	901.5	909.3
127.5°	653.8	717.3	770.0	809.7	838.0	854.3	857.7
130°	632.6	693.5	744.4	783.5	809.3	824.9	829.6
132.5°	612.5	667.9	716.8	755.9	781.7	796.1	801.4
135°	581.7	631.8	676.3	710.7	736.5	750.6	755.3
137.5°	554.2	595.8	633.6	664.5	687.9	700.9	706.1
140°	537.9	573.9	606.7	635.7	656.0	667.7	671.6
142.5°	524.2	555.1	583.6	608.2	625.4	636.5	639.7
145°	506.7	530.9	552.0	570.8	584.1	592.7	595.8
147.5°	492.1	510.7	526.7	541.5	552.2	557.2	558.6
150°	484.0	498.8	512.9	524.7	534.0	537.2	537.9
152.5°	475.9	489.5	500.4	510.3	517.8	520.9	521.7
155°	463.7	474.6	483.2	491.0	496.5	498.8	499.6
157.5°	452.1	460.5	467.3	473.4	477.9	480.1	479.9
160°	443.3	451.2	456.6	462.1	466.0	467.6	466.8
162.5°	435.8	442.4	447.2	451.5	454.7	455.1	454.9
165°	424.6	429.3	433.2	436.3	437.9	437.9	437.9
167.5°	413.6	417.2	420.0	421.6	423.0	422.4	422.2
170°	407.4	409.7	411.3	412.8	413.6	413.6	412.8
172.5°	401.7	403.5	404.4	404.7	406.1	404.9	404.1
175°	393.3	394.9	394.9	394.9	395.6	394.1	393.3
177.5°	389.7	389.7	389.7	389.1	389.7	387.8	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8

(END OF REPORT)