

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333595

Luminaire Tested: **S125RDIP-S1090D810U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333595  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D810U835-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7464.4 lumens  
Efficiency: N/A  
Efficacy: 137.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333595

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333595

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	95	91	88	92	89	85	82	77	74	72	66	64	62	55	54	53	48
2	91	83	77	72	84	78	73	68	68	63	60	58	55	52	49	47	45	41
3	83	74	66	60	77	69	62	57	60	55	51	51	48	45	44	41	39	35
4	76	65	57	51	71	61	54	49	53	48	43	46	42	38	39	36	33	30
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29	26
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	29	26	23
7	60	47	39	34	55	45	37	32	39	33	29	34	30	26	29	26	23	21
8	55	43	35	30	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11544	11544	11544
5°	11570	11439	11509
10°	11482	11332	11332
15°	11346	11102	11012
20°	11171	10781	10652
25°	10967	10467	10236
30°	10712	10097	9775
35°	10452	9717	9260
40°	10209	9321	8752
45°	9913	8878	8199
50°	9616	8396	7623
55°	9272	7935	7007
60°	8928	7375	6347
65°	8520	6725	5590
70°	8055	5914	4817
75°	7411	4986	4007
80°	6527	3916	3362
85°	5498	3201	3001



TEST NUMBER: P333595

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.1	2.3
10°-20°	469.7	6.3
20°-30°	681.1	9.1
30°-40°	776.2	10.4
40°-50°	756.6	10.1
50°-60°	636.9	8.5
60°-70°	446.5	6.0
70°-80°	229.5	3.1
80°-90°	60.2	0.8
90°-100°	38.3	0.5
100°-110°	236.3	3.2
110°-120°	428.5	5.7
120°-130°	550.0	7.4
130°-140°	591.5	7.9
140°-150°	555.2	7.4
150°-160°	449.1	6.0
160°-170°	290.5	3.9
170°-180°	100.2	1.3
0°-30°	1318.9	17.7
0°-40°	2095.1	28.1
0°-60°	3488.6	46.7
0°-90°	4224.7	56.6
90°-120°	703.1	9.4
90°-150°	2399.9	32.2
90°-180°	3240.0	43.4
0°-180°	7464.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1787	1787	1787	1787	1787	
5°	1785	1779	1764	1777	1775	169
15°	1697	1688	1660	1659	1647	478
25°	1539	1517	1469	1451	1436	708
35°	1326	1292	1232	1194	1174	830
45°	1085	1044	972	920	898	837
55°	824	778	705	646	622	736
65°	558	510	440	388	366	552
75°	297	256	200	171	161	314
85°	74	51	43	42	40	83
90°	1	7	12	16	19	5
95°	45	41	12	16	16	57
105°	230	233	233	233	232	244
115°	432	435	436	433	429	428
125°	614	619	619	616	614	548
135°	766	770	769	767	762	590
145°	888	889	889	890	885	555
155°	978	973	974	976	970	450
165°	1032	1027	1028	1032	1026	291
175°	1055	1051	1051	1057	1050	100
180°	1055	1055	1055	1055	1055	



TEST NUMBER: P333595

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1790.6	1789.9	1789.2	1788.4	1787.7	1786.2	1783.8	1781.4	1779.0	1776.6	1779.0
5°	1784.7	1783.5	1782.3	1781.1	1779.9	1777.6	1774.3	1771.0	1767.7	1764.4	1767.4
7.5°	1767.1	1766.0	1764.8	1763.7	1762.5	1760.0	1756.0	1752.1	1748.1	1744.2	1746.3
10°	1750.9	1750.0	1749.1	1748.2	1747.3	1744.8	1740.6	1736.4	1732.2	1728.0	1728.9
12.5°	1732.5	1731.4	1730.3	1729.1	1728.0	1724.6	1719.0	1713.3	1707.7	1702.0	1702.7
15°	1696.9	1695.1	1693.3	1691.5	1689.7	1685.7	1679.4	1673.1	1666.8	1660.5	1660.2
17.5°	1656.7	1653.9	1651.2	1648.4	1645.6	1640.3	1632.4	1624.5	1616.5	1608.6	1607.1
20°	1625.4	1622.4	1619.4	1616.4	1613.4	1607.1	1597.5	1587.9	1578.3	1568.7	1567.2
22.5°	1590.8	1587.8	1584.8	1581.8	1578.8	1572.3	1562.2	1552.1	1542.0	1531.9	1529.0
25°	1539.0	1534.5	1530.0	1525.5	1521.0	1513.2	1502.1	1491.0	1479.9	1468.8	1464.9
27.5°	1479.6	1474.1	1468.6	1463.2	1457.7	1449.1	1437.2	1425.3	1413.4	1401.5	1396.1
30°	1436.4	1430.7	1425.0	1419.3	1413.6	1404.4	1391.8	1379.2	1366.6	1354.0	1347.1
32.5°	1394.2	1387.6	1380.9	1374.3	1367.6	1357.9	1345.0	1332.2	1319.3	1306.5	1298.9
35°	1325.7	1318.5	1311.3	1304.1	1296.9	1286.5	1273.0	1259.5	1246.0	1232.5	1223.8
37.5°	1258.4	1249.7	1240.9	1232.2	1223.4	1212.1	1198.1	1184.2	1170.3	1156.4	1145.9
40°	1210.9	1201.9	1192.9	1183.9	1174.9	1163.2	1148.8	1134.4	1120.0	1105.6	1094.2
42.5°	1161.2	1152.0	1142.8	1133.5	1124.3	1112.2	1097.3	1082.5	1067.6	1052.7	1041.8
45°	1085.4	1076.7	1068.0	1059.3	1050.6	1038.0	1021.5	1005.0	988.5	972.0	960.0
47.5°	1006.8	997.6	988.4	979.3	970.1	957.2	940.6	923.9	907.3	890.7	878.3
50°	957.1	947.2	937.3	927.4	917.5	904.0	886.9	869.8	852.7	835.6	823.0
52.5°	903.1	893.0	882.8	872.7	862.6	849.4	833.3	817.1	801.0	784.9	771.3
55°	823.5	813.9	804.3	794.7	785.1	771.9	755.1	738.3	721.5	704.7	691.2
57.5°	743.0	732.8	722.5	712.2	702.0	688.8	672.6	656.4	640.2	624.0	610.8
60°	691.2	680.7	670.2	659.7	649.2	635.8	619.6	603.4	587.2	571.0	557.8
62.5°	636.1	626.1	616.1	606.0	596.0	582.8	566.4	549.9	533.5	517.0	504.8
65°	557.5	547.3	537.1	526.9	516.7	503.7	487.8	471.9	456.0	440.1	428.1
67.5°	479.5	469.3	459.1	448.9	438.7	426.0	410.7	395.5	380.3	365.0	354.1
70°	426.6	416.4	406.2	396.0	385.8	373.2	358.2	343.2	328.2	313.2	303.9
72.5°	374.8	364.8	354.8	344.9	334.9	322.9	308.9	294.8	280.8	266.8	258.2
75°	297.0	288.0	279.0	270.0	261.0	250.2	237.6	225.0	212.4	199.8	193.2
77.5°	219.8	212.6	205.4	198.2	191.0	182.3	172.3	162.2	152.1	142.0	137.4
80°	175.5	168.3	161.1	153.9	146.7	138.9	130.5	122.1	113.7	105.3	102.6
82.5°	132.3	125.8	119.3	112.9	106.4	100.3	94.5	88.7	83.0	77.2	76.0
85°	74.2	68.8	63.4	58.0	52.6	49.2	47.7	46.2	44.7	43.2	42.9
87.5°	25.0	23.6	22.2	20.8	19.4	18.7	18.7	18.7	18.7	18.7	18.9
90°	0.8	2.2	3.6	5.0	6.3	7.6	8.9	10.1	11.3	12.5	13.4
92.5°	12.0	11.1	10.1	9.1	8.2	8.2	9.3	10.4	11.4	12.5	13.4
95°	44.6	44.1	43.5	43.0	42.5	38.9	32.3	25.7	19.1	12.5	13.4
97.5°	93.1	94.0	94.9	95.9	96.8	90.8	77.7	64.6	51.5	38.5	33.6
100°	130.6	131.1	131.6	132.2	132.7	133.3	134.0	134.7	135.4	136.1	110.2
102.5°	168.8	169.4	170.1	170.7	171.4	171.9	172.4	172.8	173.2	173.6	168.7
105°	229.9	230.6	231.3	232.0	232.7	233.0	233.0	233.0	233.0	233.0	233.0
107.5°	293.4	293.4	293.4	293.4	293.4	293.6	293.9	294.3	294.6	295.0	295.0
110°	334.7	334.7	334.7	334.7	334.7	334.9	335.2	335.6	335.9	336.3	335.8



TEST NUMBER: P333595

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	373.5	373.9	374.3	374.8	375.2	375.5	375.7	375.9	376.1	376.3	375.7
115°	431.7	432.6	433.4	434.3	435.2	435.7	435.9	436.0	436.2	436.4	435.7
117.5°	491.9	491.9	491.8	491.8	491.8	492.1	492.7	493.4	494.1	494.7	493.8
120°	529.4	529.3	529.1	528.9	528.7	528.9	529.4	530.0	530.5	531.0	530.7
122.5°	562.6	563.3	563.9	564.6	565.2	565.7	565.9	566.2	566.4	566.7	566.3
125°	613.9	615.1	616.3	617.6	618.8	619.4	619.4	619.4	619.4	619.4	618.7
127.5°	662.9	663.7	664.6	665.5	666.3	666.7	666.6	666.5	666.4	666.3	665.9
130°	692.9	693.8	694.6	695.5	696.4	696.9	697.1	697.2	697.4	697.6	697.1
132.5°	722.9	723.9	724.9	725.9	727.0	727.3	726.9	726.5	726.1	725.7	725.6
135°	765.6	766.7	767.7	768.8	769.8	770.1	769.8	769.4	769.1	768.8	768.4
137.5°	804.9	805.8	806.7	807.6	808.5	808.8	808.5	808.2	807.9	807.5	807.6
140°	830.5	830.9	831.2	831.6	831.9	832.0	831.8	831.7	831.5	831.3	831.7
142.5°	853.7	853.9	854.1	854.3	854.5	854.7	855.0	855.2	855.5	855.7	855.8
145°	887.6	888.0	888.3	888.7	889.0	889.2	889.2	889.2	889.2	889.2	889.4
147.5°	917.3	917.3	917.2	917.1	917.1	917.1	917.3	917.5	917.8	918.0	918.2
150°	936.1	935.8	935.4	935.1	934.7	934.7	935.1	935.4	935.8	936.1	936.5
152.5°	954.3	953.5	952.7	952.0	951.2	951.0	951.3	951.7	952.0	952.4	952.7
155°	977.6	976.5	975.5	974.4	973.4	973.0	973.4	973.7	974.1	974.4	974.9
157.5°	995.5	994.9	994.3	993.7	993.0	992.7	992.8	992.8	992.8	992.9	993.4
160°	1008.1	1007.0	1006.0	1004.9	1003.9	1003.5	1003.6	1003.8	1004.0	1004.1	1004.8
162.5°	1018.1	1017.0	1016.0	1014.9	1013.9	1013.5	1013.6	1013.8	1014.0	1014.2	1015.1
165°	1031.5	1030.5	1029.4	1028.4	1027.3	1026.9	1027.1	1027.3	1027.4	1027.6	1028.7
167.5°	1041.5	1040.5	1039.4	1038.3	1037.2	1036.8	1036.9	1037.1	1037.3	1037.5	1038.7
170°	1047.2	1045.9	1044.7	1043.5	1042.3	1041.8	1041.9	1042.1	1042.3	1042.5	1043.9
172.5°	1050.9	1049.7	1048.5	1047.3	1046.0	1045.6	1045.9	1046.2	1046.5	1046.8	1048.1
175°	1055.0	1053.9	1052.9	1051.9	1050.8	1050.4	1050.5	1050.7	1050.9	1051.1	1052.5
177.5°	1056.9	1056.0	1055.2	1054.4	1053.5	1053.2	1053.3	1053.4	1053.6	1053.7	1054.7
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333595

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1781.4	1783.8	1786.2	1787.2	1787.0	1786.8	1786.5	1786.3
5°	1770.4	1773.4	1776.4	1777.6	1777.0	1776.4	1775.8	1775.2
7.5°	1748.4	1750.5	1752.6	1753.3	1752.6	1752.0	1751.3	1750.6
10°	1729.8	1730.7	1731.6	1731.6	1730.7	1729.8	1728.9	1728.0
12.5°	1703.4	1704.0	1704.7	1704.3	1702.9	1701.6	1700.2	1698.8
15°	1659.9	1659.6	1659.3	1657.8	1655.1	1652.4	1649.7	1647.0
17.5°	1605.6	1604.1	1602.6	1600.8	1598.5	1596.3	1594.1	1591.9
20°	1565.7	1564.2	1562.7	1560.6	1557.9	1555.2	1552.5	1549.8
22.5°	1526.1	1523.1	1520.2	1517.6	1515.4	1513.2	1510.9	1508.7
25°	1461.0	1457.1	1453.2	1449.6	1446.3	1443.0	1439.7	1436.4
27.5°	1390.6	1385.2	1379.7	1375.4	1372.2	1369.0	1365.8	1362.7
30°	1340.2	1333.3	1326.4	1321.6	1318.9	1316.2	1313.5	1310.8
32.5°	1291.3	1283.6	1276.0	1270.5	1267.1	1263.7	1260.2	1256.8
35°	1215.1	1206.4	1197.7	1191.3	1187.1	1182.9	1178.7	1174.5
37.5°	1135.5	1125.1	1114.6	1107.4	1103.3	1099.2	1095.1	1091.0
40°	1082.8	1071.4	1060.0	1052.5	1048.9	1045.3	1041.7	1038.1
42.5°	1030.9	1019.9	1009.0	1000.9	995.6	990.4	985.1	979.8
45°	948.0	936.0	924.0	915.7	911.2	906.7	902.2	897.7
47.5°	866.0	853.6	841.3	832.6	827.6	822.6	817.7	812.7
50°	810.4	797.8	785.2	776.7	772.2	767.7	763.2	758.7
52.5°	757.8	744.2	730.6	721.6	717.1	712.6	708.1	703.6
55°	677.7	664.2	650.7	641.5	636.7	631.9	627.1	622.3
57.5°	597.6	584.4	571.2	562.4	558.2	553.9	549.6	545.4
60°	544.6	531.4	518.2	509.4	504.9	500.4	495.9	491.4
62.5°	492.6	480.3	468.1	459.7	455.2	450.7	446.2	441.7
65°	416.1	404.1	392.1	383.8	379.3	374.8	370.3	365.8
67.5°	343.1	332.1	321.1	313.8	310.2	306.6	303.0	299.4
70°	294.6	285.3	276.0	269.5	265.9	262.3	258.7	255.1
72.5°	249.6	241.0	232.4	226.9	224.5	222.1	219.7	217.3
75°	186.6	180.0	173.4	169.0	166.9	164.8	162.7	160.6
77.5°	132.8	128.2	123.5	120.4	118.9	117.3	115.8	114.2
80°	99.9	97.2	94.5	92.8	92.2	91.6	91.0	90.4
82.5°	74.7	73.4	72.2	71.4	71.0	70.6	70.3	69.9
85°	42.6	42.3	42.0	41.7	41.4	41.1	40.8	40.5
87.5°	19.0	19.2	19.4	19.4	19.3	19.1	19.0	18.9
90°	14.3	15.1	16.0	16.7	17.2	17.7	18.2	18.8
92.5°	14.3	15.1	16.0	16.5	16.8	17.0	17.3	17.5
95°	14.3	15.1	16.0	16.4	16.4	16.4	16.4	16.4
97.5°	28.7	23.8	18.9	16.4	16.4	16.4	16.4	16.4
100°	84.3	58.4	32.5	19.2	18.5	17.8	17.1	16.4
102.5°	163.8	158.9	154.0	145.7	133.8	122.0	110.2	98.4
105°	233.0	233.0	233.0	233.0	232.8	232.6	232.4	232.3
107.5°	295.1	295.1	295.1	294.9	294.4	293.8	293.3	292.8
110°	335.2	334.7	334.2	334.0	334.2	334.4	334.5	334.7





TEST NUMBER: P333595

CATALOG NUMBER: S125RDIP-S1090D810U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	375.0	374.3	373.7	373.2	373.0	372.7	372.5	372.3
115°	435.0	434.3	433.6	432.7	431.7	430.6	429.6	428.6
117.5°	492.9	492.0	491.1	490.4	490.0	489.5	489.1	488.6
120°	530.3	530.0	529.6	529.0	528.1	527.3	526.4	525.5
122.5°	566.0	565.6	565.3	564.6	563.6	562.6	561.6	560.6
125°	618.0	617.3	616.6	616.0	615.5	614.9	614.4	613.9
127.5°	665.5	665.2	664.8	663.9	662.7	661.4	660.1	658.8
130°	696.5	696.0	695.5	694.8	693.9	693.1	692.2	691.3
132.5°	725.5	725.4	725.3	724.8	724.0	723.1	722.2	721.4
135°	768.1	767.7	767.4	766.7	765.6	764.6	763.5	762.5
137.5°	807.7	807.7	807.8	807.4	806.5	805.6	804.7	803.8
140°	832.0	832.4	832.7	832.4	831.3	830.3	829.2	828.2
142.5°	855.9	855.9	856.0	855.5	854.5	853.4	852.4	851.3
145°	889.5	889.7	889.9	889.4	888.4	887.4	886.3	885.3
147.5°	918.4	918.6	918.8	918.3	917.0	915.8	914.5	913.3
150°	936.8	937.2	937.5	937.0	935.6	934.2	932.8	931.4
152.5°	953.1	953.4	953.8	953.3	952.1	950.8	949.6	948.3
155°	975.5	976.0	976.5	976.1	974.7	973.3	971.9	970.5
157.5°	994.0	994.6	995.1	994.7	993.3	991.9	990.5	989.1
160°	1005.5	1006.2	1006.9	1006.6	1005.2	1003.8	1002.4	1001.0
162.5°	1016.1	1017.1	1018.0	1017.8	1016.2	1014.7	1013.2	1011.7
165°	1029.7	1030.7	1031.8	1031.6	1030.2	1028.8	1027.4	1026.0
167.5°	1040.0	1041.2	1042.5	1042.3	1040.7	1039.2	1037.6	1036.1
170°	1045.2	1046.6	1048.0	1047.9	1046.4	1044.8	1043.2	1041.7
172.5°	1049.3	1050.6	1051.9	1051.7	1050.1	1048.6	1047.0	1045.4
175°	1053.8	1055.2	1056.6	1056.5	1055.0	1053.4	1051.9	1050.3
177.5°	1055.7	1056.6	1057.6	1057.6	1056.4	1055.3	1054.2	1053.1
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0

(END OF REPORT)