

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333630

Luminaire Tested: **S125RDIP-S1270D1035U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333630
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8635.6 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	84	74	67	61	78	70	63	58	61	56	52	52	49	46	45	42	40	36
4	77	66	58	52	71	62	55	50	54	49	44	47	43	39	40	37	34	31
5	70	59	51	45	65	55	48	43	49	43	39	42	38	34	36	33	30	27
6	65	53	45	39	60	50	43	37	44	38	34	38	34	30	33	29	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	44	36	31	52	41	34	29	36	31	27	32	27	24	28	24	21	19
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12264	12264	12264	12264
5°	14110	12280	10845	12280
10°	16184	12218	9569	12218
15°	17481	12092	8506	12092
20°	19276	11947	7854	11947
25°	22308	11754	7288	11754
30°	24276	11551	6918	11551
35°	20478	11315	6576	11315
40°	14300	10890	6283	10890
45°	10609	10316	5994	10316
50°	8459	9720	5749	9720
55°	7179	8979	5530	8979
60°	6203	8317	5176	8317
65°	5527	7600	4455	7600
70°	4857	6962	4062	6962
75°	4202	6029	3813	6029
80°	3187	5073	3187	5073
85°	2660	3987	3001	3987



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.1	2.1
10°-20°	533.6	6.2
20°-30°	846.1	9.8
30°-40°	1020.3	11.8
40°-50°	911.2	10.6
50°-60°	698.8	8.1
60°-70°	454.1	5.3
70°-80°	220.8	2.6
80°-90°	55.5	0.6
90°-100°	358.9	4.2
100°-110°	771.5	8.9
110°-120°	724.1	8.4
120°-130°	586.8	6.8
130°-140°	470.9	5.5
140°-150°	355.4	4.1
150°-160°	250.1	2.9
160°-170°	147.4	1.7
170°-180°	48.0	0.6
0°-30°	1561.8	18.1
0°-40°	2582.2	29.9
0°-60°	4192.1	48.5
0°-90°	4922.5	57.0
90°-120°	1854.5	21.5
90°-150°	3267.6	37.8
90°-180°	3713.0	43.0
0°-180°	8635.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2176	1894	1673	1894	2176	217
15°	2614	1808	1272	1808	2614	749
25°	3130	1649	1023	1649	3130	1437
35°	2597	1435	834	1435	2597	1569
45°	1162	1130	656	1130	1162	927
55°	638	797	491	797	638	579
65°	362	497	292	497	362	360
75°	168	242	153	242	168	179
85°	36	54	40	54	36	42
90°	23	1	23	1	23	18
95°	235	33	235	33	235	332
105°	1323	113	1323	113	1323	1315
115°	1474	202	1474	202	1474	1440
125°	1161	280	1161	280	1161	1050
135°	964	327	964	327	964	747
145°	761	381	761	381	761	483
155°	638	435	638	435	638	297
165°	559	475	559	475	559	160
175°	502	494	502	494	502	49
180°	495	495	495	495	495	



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1997.4	1996.2	1998.7	1991.8	1992.4	1981.8	1981.8	1973.7	1963.1	1955.0	1951.3
5°	2176.4	2178.0	2174.8	2163.1	2155.4	2143.7	2130.4	2107.0	2087.5	2068.8	2054.0
7.5°	2360.7	2361.8	2351.5	2347.9	2328.2	2313.9	2284.4	2252.6	2224.4	2188.6	2161.1
10°	2467.9	2467.2	2456.2	2447.7	2430.5	2408.7	2379.9	2342.4	2307.4	2268.4	2231.0
12.5°	2530.3	2528.3	2524.8	2514.4	2498.5	2479.2	2454.7	2417.9	2374.7	2332.0	2288.3
15°	2614.5	2609.0	2598.9	2585.6	2563.0	2540.4	2513.1	2480.4	2439.1	2390.8	2350.2
17.5°	2718.6	2718.8	2703.2	2684.8	2654.1	2614.2	2572.1	2519.2	2463.1	2409.9	2366.8
20°	2804.7	2802.3	2786.8	2750.9	2715.8	2665.9	2617.6	2552.9	2484.3	2414.9	2361.1
22.5°	2928.2	2922.1	2905.9	2858.8	2804.4	2740.1	2666.2	2587.2	2504.3	2425.5	2354.9
25°	3130.5	3125.8	3093.9	3039.3	2962.9	2863.9	2767.3	2658.9	2539.7	2436.0	2350.2
27.5°	3269.0	3263.8	3240.1	3194.8	3124.3	3020.1	2889.3	2744.5	2595.6	2453.0	2329.3
30°	3255.2	3266.9	3263.8	3242.8	3189.8	3096.2	2975.4	2812.5	2635.5	2467.9	2320.6
32.5°	3059.4	3069.9	3097.3	3138.6	3141.7	3104.3	3014.1	2863.6	2680.4	2489.8	2313.7
35°	2597.3	2611.4	2664.4	2747.8	2856.9	2948.1	2966.8	2885.8	2721.3	2516.3	2303.5
37.5°	1996.8	2073.5	2118.1	2205.9	2370.8	2538.6	2699.9	2759.3	2689.3	2505.4	2286.8
40°	1696.2	1714.9	1794.4	1893.4	2032.2	2206.8	2436.8	2602.8	2608.2	2480.4	2260.6
42.5°	1451.8	1475.5	1530.0	1609.1	1727.9	1902.5	2139.9	2359.0	2460.5	2411.8	2226.3
45°	1161.5	1179.4	1219.2	1280.0	1371.2	1515.4	1719.6	1972.9	2174.1	2252.8	2134.3
47.5°	954.1	963.8	998.4	1044.7	1112.2	1217.3	1375.4	1595.3	1836.5	2005.7	1989.0
50°	841.9	852.8	879.3	914.4	971.3	1060.1	1186.4	1369.6	1618.3	1824.8	1866.2
52.5°	754.6	763.6	780.1	813.3	860.3	928.6	1030.5	1196.2	1420.0	1639.6	1735.2
55°	637.6	643.9	657.1	675.8	713.3	762.4	850.4	965.0	1145.9	1367.3	1507.6
57.5°	541.3	544.4	552.8	570.1	596.0	631.9	695.5	792.6	922.3	1121.7	1276.5
60°	480.2	483.3	494.2	505.9	526.2	558.9	608.8	676.6	801.3	965.8	1122.5
62.5°	431.5	433.4	438.1	449.8	467.6	492.8	532.1	587.4	686.6	831.1	979.1
65°	361.7	362.5	364.0	373.4	384.3	403.0	428.7	467.7	542.5	651.7	782.6
67.5°	294.7	295.7	301.2	304.5	315.9	325.7	340.8	370.6	423.3	496.9	598.7
70°	257.2	256.5	261.9	265.8	269.7	281.4	291.5	315.7	348.4	404.6	489.5
72.5°	222.3	220.3	222.6	224.0	229.2	237.1	247.3	262.1	287.3	326.0	391.0
75°	168.4	169.2	169.2	170.7	174.6	177.7	180.8	188.6	202.7	228.4	263.5
77.5°	118.2	116.9	120.2	120.7	123.0	126.4	129.1	132.2	138.0	148.6	166.7
80°	85.7	85.7	86.5	88.9	88.1	89.6	93.5	96.7	103.7	109.9	116.1
82.5°	65.8	65.2	65.9	66.4	66.3	67.8	69.2	69.8	72.5	75.6	80.0
85°	35.9	35.9	36.6	36.6	37.4	37.4	38.2	38.2	38.2	39.0	39.8
87.5°	18.3	17.7	16.9	16.9	17.5	18.3	17.5	16.7	16.5	16.3	16.5
90°	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0	17.0	16.0	14.0
92.5°	63.7	65.3	66.7	69.1	81.9	96.6	128.4	176.9	260.5	321.8	327.0
95°	234.6	250.6	258.6	288.5	359.4	443.2	566.0	717.8	865.5	884.5	721.8
97.5°	567.0	579.8	608.7	664.7	726.3	842.9	962.5	1069.0	1095.1	944.6	644.5
100°	778.7	794.6	831.6	903.4	972.3	1076.1	1179.0	1227.9	1151.0	901.4	575.0
102.5°	1015.0	1027.0	1067.2	1118.3	1191.9	1262.2	1311.5	1281.4	1117.5	825.6	522.3
105°	1322.7	1334.7	1354.7	1387.6	1419.5	1430.5	1386.6	1249.8	1010.3	723.7	471.2
107.5°	1486.0	1494.0	1500.6	1500.8	1484.6	1432.5	1319.7	1137.2	900.8	653.7	449.6
110°	1540.3	1540.3	1533.3	1514.4	1469.5	1384.6	1243.8	1054.2	838.5	620.9	443.2



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1533.9	1526.8	1509.4	1476.8	1411.2	1311.1	1168.8	988.7	792.2	601.8	443.2
115°	1473.5	1460.5	1432.5	1384.6	1306.7	1197.9	1061.2	906.4	741.7	581.0	446.2
117.5°	1367.4	1359.4	1331.7	1282.2	1204.3	1104.5	986.7	853.3	711.6	570.8	452.8
120°	1298.8	1290.8	1263.8	1215.9	1142.0	1054.2	944.4	824.6	694.8	566.0	459.2
122.5°	1238.1	1230.9	1203.9	1160.0	1094.1	1011.8	914.0	803.0	680.4	562.0	464.8
125°	1161.0	1151.0	1129.0	1088.1	1032.2	960.3	873.5	771.7	660.9	557.0	474.2
127.5°	1095.1	1090.7	1069.9	1033.8	983.1	915.8	834.8	739.7	642.9	554.6	484.8
130°	1059.2	1053.2	1033.2	1000.3	950.4	885.5	807.6	719.8	630.9	553.0	491.2
132.5°	1023.2	1016.4	998.1	965.1	915.2	852.7	782.0	699.8	621.3	553.0	498.3
135°	964.3	958.3	940.4	907.4	863.5	806.6	742.7	673.8	609.9	553.0	508.1
137.5°	901.4	894.9	878.3	848.3	809.0	760.7	707.6	651.9	599.8	554.2	517.1
140°	857.5	852.5	837.6	811.6	774.7	732.7	686.8	639.9	595.0	555.0	521.1
142.5°	816.8	812.6	798.4	776.5	745.1	708.8	669.2	629.5	591.0	555.8	523.5
145°	760.7	756.7	745.7	728.7	704.8	677.8	646.9	615.9	585.0	555.0	526.1
147.5°	713.2	711.4	705.0	691.4	672.4	652.1	628.3	603.2	578.8	552.4	527.1
150°	686.8	685.8	681.8	669.8	654.9	636.9	617.9	596.0	574.0	550.0	527.1
152.5°	666.0	665.0	661.1	651.5	638.9	624.9	607.5	588.0	568.4	546.9	526.3
155°	637.9	636.9	633.9	626.9	616.9	606.0	592.0	576.0	559.0	541.1	524.1
157.5°	612.7	612.9	610.1	604.4	596.6	588.0	577.2	564.0	550.2	535.1	521.5
160°	596.0	597.0	595.0	590.0	583.0	576.0	566.0	556.0	543.1	531.1	519.1
162.5°	580.8	581.0	580.6	576.4	571.0	564.8	556.4	547.3	536.7	526.3	516.7
165°	559.0	559.0	559.0	557.0	553.0	548.1	542.1	535.1	527.1	519.1	513.1
167.5°	539.1	539.3	540.1	538.3	536.3	532.7	528.1	523.5	517.7	512.1	507.5
170°	527.1	528.1	528.1	527.1	525.1	523.1	520.1	517.1	512.1	508.1	505.1
172.5°	515.9	516.9	518.5	516.7	516.3	515.1	512.9	509.9	506.5	503.3	501.9
175°	502.1	503.1	505.1	504.1	504.1	504.1	502.1	502.1	499.1	498.1	498.1
177.5°	495.1	495.1	497.5	496.7	497.5	497.5	497.5	496.7	495.9	495.1	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1951.3	1946.9	1938.8	1931.3	1922.0	1913.9	1908.2	1901.4	1892.7	1882.1	1873.3
5°	2037.6	2020.5	1997.9	1978.4	1953.5	1934.0	1913.7	1894.2	1874.7	1849.8	1828.0
7.5°	2133.4	2098.0	2063.5	2020.2	1980.9	1945.8	1912.1	1878.0	1844.6	1809.2	1775.1
10°	2192.0	2149.1	2101.6	2047.0	1997.1	1949.6	1905.9	1863.0	1817.8	1778.1	1735.2
12.5°	2246.9	2191.5	2137.1	2068.2	2008.3	1950.2	1894.7	1841.2	1792.9	1741.3	1695.3
15°	2296.4	2241.9	2181.1	2096.9	2013.5	1943.3	1877.8	1808.5	1748.4	1690.8	1639.3
17.5°	2315.6	2258.4	2187.8	2106.9	2015.7	1927.4	1843.1	1767.0	1696.4	1629.2	1571.3
20°	2308.1	2252.8	2180.3	2103.1	2005.7	1913.7	1822.5	1738.3	1659.6	1588.6	1527.1
22.5°	2290.1	2232.8	2162.8	2081.3	1988.8	1891.3	1793.8	1704.0	1621.5	1548.1	1480.9
25°	2262.9	2185.0	2113.3	2033.7	1945.7	1849.0	1748.4	1649.4	1561.4	1486.5	1413.3
27.5°	2234.7	2137.4	2046.2	1967.2	1874.1	1787.9	1690.9	1589.4	1496.8	1420.6	1345.4
30°	2209.1	2100.0	1999.4	1909.8	1821.7	1739.9	1647.9	1548.9	1453.8	1375.1	1298.7
32.5°	2177.3	2061.3	1950.8	1847.4	1762.5	1681.3	1598.0	1503.4	1410.8	1329.5	1251.9
35°	2137.4	1989.3	1869.3	1759.4	1665.0	1586.3	1511.5	1435.1	1342.3	1258.1	1182.5
37.5°	2085.0	1917.0	1778.1	1658.3	1558.9	1479.8	1420.7	1350.9	1266.2	1185.6	1115.5
40°	2053.2	1864.6	1712.6	1594.1	1489.6	1406.2	1350.9	1291.7	1214.5	1138.9	1068.7
42.5°	2010.8	1816.6	1646.5	1523.0	1417.9	1337.6	1281.7	1229.9	1165.2	1094.0	1018.8
45°	1927.7	1723.5	1545.0	1412.5	1306.5	1227.7	1175.5	1129.5	1080.4	1014.9	949.4
47.5°	1819.5	1626.4	1439.6	1294.9	1191.1	1118.0	1067.3	1031.0	995.9	940.2	876.6
50°	1732.9	1546.6	1364.1	1223.8	1113.1	1043.8	996.2	967.4	935.4	884.7	831.7
52.5°	1630.6	1464.2	1285.6	1142.1	1037.7	972.7	927.0	898.2	871.8	830.5	780.0
55°	1469.4	1323.6	1159.9	1029.7	933.9	868.4	824.7	797.4	781.9	746.8	707.0
57.5°	1283.4	1178.9	1034.6	909.1	824.3	759.6	727.6	704.4	686.8	662.0	633.9
60°	1153.7	1080.4	951.0	831.7	753.8	692.2	663.4	643.9	627.5	606.5	584.6
62.5°	1022.1	968.8	856.2	753.8	682.1	630.5	603.5	585.9	567.0	552.8	531.6
65°	845.8	798.2	720.3	640.0	573.7	532.4	512.9	497.3	485.6	470.0	455.2
67.5°	657.9	638.6	584.8	529.4	481.9	445.1	428.3	417.4	403.3	394.0	383.8
70°	542.5	533.2	495.0	458.4	413.9	389.0	373.4	368.7	351.6	342.2	335.2
72.5°	440.3	435.9	413.9	388.5	357.2	335.3	321.0	315.7	304.8	297.3	292.8
75°	301.7	303.2	299.3	283.0	271.3	257.2	244.8	241.6	233.9	227.6	223.7
77.5°	190.8	198.8	199.1	198.3	193.6	185.1	179.9	177.6	169.9	167.6	166.7
80°	131.0	139.5	147.3	146.5	145.0	142.7	138.8	136.4	132.5	130.2	128.6
82.5°	87.3	95.3	101.8	106.0	105.7	103.4	100.7	99.6	98.8	97.1	96.8
85°	41.3	42.9	45.2	50.7	54.6	55.3	54.6	53.8	51.4	52.2	53.0
87.5°	16.9	16.5	17.0	16.6	15.5	18.3	19.7	20.2	19.1	18.3	17.4
90°	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0	2.0	4.0	6.0
92.5°	227.8	136.4	81.9	52.7	35.5	23.2	14.8	12.2	14.8	23.2	35.5
95°	446.2	226.6	119.8	74.9	52.9	41.9	33.9	32.9	33.9	41.9	52.9
97.5°	356.2	195.3	124.6	92.2	72.5	61.5	55.9	54.7	55.9	61.5	72.5
100°	323.4	193.7	135.8	105.8	86.8	75.9	71.9	69.9	71.9	75.9	86.8
102.5°	309.9	200.9	149.3	120.2	102.8	91.0	87.8	86.7	87.8	91.0	102.8
105°	304.5	215.6	171.7	143.8	127.8	117.8	112.8	112.8	112.8	117.8	127.8
107.5°	313.7	237.6	195.1	169.9	153.3	145.1	140.4	138.4	140.4	145.1	153.3
110°	322.4	253.6	212.6	186.7	171.7	162.7	158.7	156.7	158.7	162.7	171.7



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	333.6	268.7	229.4	204.2	189.3	180.3	177.1	175.1	177.1	180.3	189.3
115°	350.4	292.5	255.6	230.6	215.6	206.6	203.6	201.7	203.6	206.6	215.6
117.5°	369.6	316.9	281.9	257.8	240.8	231.8	228.6	225.6	228.6	231.8	240.8
120°	382.3	334.4	299.5	274.5	257.6	248.6	244.6	241.6	244.6	248.6	257.6
122.5°	396.7	351.2	316.3	291.3	272.7	263.7	260.5	258.4	260.5	263.7	272.7
125°	416.3	373.4	340.4	314.5	295.5	286.5	281.5	279.5	281.5	286.5	295.5
127.5°	434.2	394.7	363.0	337.0	316.9	305.5	299.1	296.1	299.1	305.5	316.9
130°	446.2	408.3	377.3	351.4	330.4	317.5	309.5	306.5	309.5	317.5	330.4
132.5°	456.6	421.1	390.1	364.2	342.4	327.8	318.2	314.5	318.2	327.8	342.4
135°	471.2	438.2	407.3	380.3	359.4	343.4	331.4	327.4	331.4	343.4	359.4
137.5°	482.0	450.4	422.3	394.5	374.0	358.0	346.8	343.8	346.8	358.0	374.0
140°	489.2	459.2	430.3	403.3	384.3	368.4	356.4	353.4	356.4	368.4	384.3
142.5°	493.1	464.8	437.4	412.1	393.9	377.9	366.8	364.6	366.8	377.9	393.9
145°	499.1	474.2	448.2	425.3	407.3	393.3	383.3	381.3	383.3	393.3	407.3
147.5°	502.7	480.2	457.4	437.2	421.7	408.7	400.1	398.9	400.1	408.7	421.7
150°	505.1	484.2	462.2	445.2	431.3	418.3	411.3	409.3	411.3	418.3	431.3
152.5°	506.7	488.2	467.8	452.4	439.2	427.9	421.7	420.5	421.7	427.9	439.2
155°	508.1	492.1	475.2	461.2	451.2	441.2	435.2	435.2	435.2	441.2	451.2
157.5°	509.1	495.5	481.0	470.4	461.6	453.0	448.2	448.4	448.2	453.0	461.6
160°	509.1	497.1	484.2	475.2	467.2	460.2	456.2	457.2	456.2	460.2	467.2
162.5°	508.3	498.7	487.4	480.0	473.6	467.4	463.4	464.4	463.4	467.4	473.6
165°	507.1	499.1	491.2	485.2	481.2	476.2	473.2	475.2	473.2	476.2	481.2
167.5°	504.7	499.1	492.5	488.8	486.0	483.2	481.4	482.4	481.4	483.2	486.0
170°	503.1	499.1	494.1	491.2	489.2	487.2	486.2	487.2	486.2	487.2	489.2
172.5°	501.5	498.3	494.1	492.7	491.5	489.6	488.6	490.4	488.6	489.6	491.5
175°	499.1	497.1	494.1	494.1	494.1	493.1	492.1	494.1	492.1	493.1	494.1
177.5°	496.7	495.9	494.3	494.3	495.1	494.3	494.3	495.9	494.3	494.3	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1867.1	1858.4	1852.1	1839.6	1830.9	1827.2	1820.3	1818.4	1825.3	1820.3	1819.7
5°	1811.6	1789.0	1771.1	1753.1	1733.6	1721.2	1702.5	1699.3	1694.7	1687.6	1686.1
7.5°	1745.0	1715.6	1692.5	1662.9	1637.1	1616.4	1593.0	1581.9	1575.9	1566.8	1554.7
10°	1700.1	1665.0	1633.9	1604.2	1572.3	1546.6	1523.2	1505.2	1493.5	1482.6	1478.0
12.5°	1655.8	1620.1	1580.2	1544.4	1508.7	1479.8	1453.9	1442.3	1429.3	1416.5	1405.6
15°	1587.1	1539.5	1495.9	1454.6	1424.2	1393.0	1368.0	1350.9	1331.4	1326.0	1304.9
17.5°	1514.1	1467.5	1416.4	1372.9	1337.6	1303.3	1275.9	1256.4	1241.8	1221.7	1212.0
20°	1468.6	1413.3	1363.4	1323.6	1284.6	1244.1	1216.0	1199.7	1185.6	1169.3	1161.5
22.5°	1420.0	1365.9	1314.7	1268.1	1228.5	1188.6	1168.6	1151.7	1135.7	1120.6	1110.3
25°	1348.6	1294.0	1240.2	1191.9	1150.6	1121.7	1098.3	1078.8	1070.3	1055.5	1044.5
27.5°	1277.9	1219.9	1164.1	1115.9	1083.5	1055.0	1035.8	1020.4	1004.9	992.0	982.5
30°	1232.4	1173.2	1112.4	1074.2	1039.9	1012.6	991.5	976.7	965.0	953.3	946.3
32.5°	1186.9	1125.8	1071.8	1030.5	998.1	974.5	952.9	938.7	926.4	913.4	905.2
35°	1113.9	1051.6	1007.9	967.4	935.4	913.6	898.8	878.5	868.4	859.0	850.4
37.5°	1046.1	988.1	940.9	905.3	877.6	855.9	836.7	825.8	813.3	804.9	797.8
40°	996.2	943.2	900.3	862.9	842.7	818.5	800.6	786.5	777.2	766.3	758.5
42.5°	951.3	902.1	860.4	826.8	801.5	781.1	763.8	749.7	737.9	730.1	723.5
45°	887.9	838.8	798.2	767.0	743.7	724.2	706.2	699.2	683.6	674.3	671.2
47.5°	822.2	778.3	739.1	710.4	686.4	668.0	651.2	636.9	628.3	619.1	614.1
50°	778.0	735.9	699.2	671.2	647.8	627.5	611.9	602.6	590.9	582.3	576.1
52.5°	733.7	694.7	658.1	631.2	611.0	590.7	573.3	563.9	552.8	547.4	543.0
55°	670.4	629.1	597.9	571.4	550.3	531.6	515.3	505.9	498.9	493.4	491.9
57.5°	598.7	565.9	536.9	513.1	491.2	473.6	459.3	450.4	444.2	443.4	438.7
60°	551.9	522.3	495.8	470.0	451.3	435.0	422.5	412.4	406.1	405.3	403.8
62.5°	505.1	476.7	452.1	429.5	412.7	396.9	385.1	373.7	370.0	366.1	362.6
65°	435.7	410.0	389.8	371.8	353.9	340.6	329.0	321.9	313.4	308.7	300.1
67.5°	367.6	347.7	328.2	313.1	299.0	286.4	276.7	266.3	260.5	256.8	250.5
70°	322.7	307.1	287.6	271.3	260.4	250.2	242.4	230.7	226.8	223.7	220.6
72.5°	280.3	266.6	250.2	237.0	226.1	216.5	207.5	202.0	198.2	195.0	193.2
75°	220.6	207.4	193.3	184.0	176.2	168.4	163.7	159.8	158.2	157.5	154.3
77.5°	162.0	155.0	143.7	136.3	131.1	128.0	123.8	121.8	121.6	118.2	117.1
80°	123.9	120.0	110.7	107.6	103.7	100.6	98.2	94.3	90.4	88.9	86.5
82.5°	92.1	88.2	84.5	79.5	76.2	74.4	72.0	70.6	71.1	68.9	67.8
85°	49.1	45.2	43.7	42.9	41.3	42.9	42.1	41.3	40.5	39.8	40.5
87.5°	17.2	17.6	17.2	18.8	17.1	18.2	18.4	17.9	18.1	18.3	18.1
90°	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0	19.0	20.0	22.0
92.5°	52.7	81.9	136.4	227.8	327.0	321.8	260.5	176.9	128.4	96.6	81.9
95°	74.9	119.8	226.6	446.2	721.8	884.5	865.5	717.8	566.0	443.2	359.4
97.5°	92.2	124.6	195.3	356.2	644.5	944.6	1095.1	1069.0	962.5	842.9	726.3
100°	105.8	135.8	193.7	323.4	575.0	901.4	1151.0	1227.9	1179.0	1076.1	972.3
102.5°	120.2	149.3	200.9	309.9	522.3	825.6	1117.5	1281.4	1311.5	1262.2	1191.9
105°	143.8	171.7	215.6	304.5	471.2	723.7	1010.3	1249.8	1386.6	1430.5	1419.5
107.5°	169.9	195.1	237.6	313.7	449.6	653.7	900.8	1137.2	1319.7	1432.5	1484.6
110°	186.7	212.6	253.6	322.4	443.2	620.9	838.5	1054.2	1243.8	1384.6	1469.5



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.2	229.4	268.7	333.6	443.2	601.8	792.2	988.7	1168.8	1311.1	1411.2
115°	230.6	255.6	292.5	350.4	446.2	581.0	741.7	906.4	1061.2	1197.9	1306.7
117.5°	257.8	281.9	316.9	369.6	452.8	570.8	711.6	853.3	986.7	1104.5	1204.3
120°	274.5	299.5	334.4	382.3	459.2	566.0	694.8	824.6	944.4	1054.2	1142.0
122.5°	291.3	316.3	351.2	396.7	464.8	562.0	680.4	803.0	914.0	1011.8	1094.1
125°	314.5	340.4	373.4	416.3	474.2	557.0	660.9	771.7	873.5	960.3	1032.2
127.5°	337.0	363.0	394.7	434.2	484.8	554.6	642.9	739.7	834.8	915.8	983.1
130°	351.4	377.3	408.3	446.2	491.2	553.0	630.9	719.8	807.6	885.5	950.4
132.5°	364.2	390.1	421.1	456.6	498.3	553.0	621.3	699.8	782.0	852.7	915.2
135°	380.3	407.3	438.2	471.2	508.1	553.0	609.9	673.8	742.7	806.6	863.5
137.5°	394.5	422.3	450.4	482.0	517.1	554.2	599.8	651.9	707.6	760.7	809.0
140°	403.3	430.3	459.2	489.2	521.1	555.0	595.0	639.9	686.8	732.7	774.7
142.5°	412.1	437.4	464.8	493.1	523.5	555.8	591.0	629.5	669.2	708.8	745.1
145°	425.3	448.2	474.2	499.1	526.1	555.0	585.0	615.9	646.9	677.8	704.8
147.5°	437.2	457.4	480.2	502.7	527.1	552.4	578.8	603.2	628.3	652.1	672.4
150°	445.2	462.2	484.2	505.1	527.1	550.0	574.0	596.0	617.9	636.9	654.9
152.5°	452.4	467.8	488.2	506.7	526.3	546.9	568.4	588.0	607.5	624.9	638.9
155°	461.2	475.2	492.1	508.1	524.1	541.1	559.0	576.0	592.0	606.0	616.9
157.5°	470.4	481.0	495.5	509.1	521.5	535.1	550.2	564.0	577.2	588.0	596.6
160°	475.2	484.2	497.1	509.1	519.1	531.1	543.1	556.0	566.0	576.0	583.0
162.5°	480.0	487.4	498.7	508.3	516.7	526.3	536.7	547.3	556.4	564.8	571.0
165°	485.2	491.2	499.1	507.1	513.1	519.1	527.1	535.1	542.1	548.1	553.0
167.5°	488.8	492.5	499.1	504.7	507.5	512.1	517.7	523.5	528.1	532.7	536.3
170°	491.2	494.1	499.1	503.1	505.1	508.1	512.1	517.1	520.1	523.1	525.1
172.5°	492.7	494.1	498.3	501.5	501.9	503.3	506.5	509.9	512.9	515.1	516.3
175°	494.1	494.1	497.1	499.1	498.1	498.1	499.1	502.1	502.1	504.1	504.1
177.5°	494.3	494.3	495.9	496.7	495.1	495.1	495.9	496.7	497.5	497.5	497.5
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1819.1	1812.2	1810.3	1812.8	1810.3	1812.2	1819.1	1819.7	1820.3	1825.3	1818.4
5°	1678.3	1670.5	1674.4	1672.8	1674.4	1670.5	1678.3	1686.1	1687.6	1694.7	1699.3
7.5°	1554.5	1544.8	1534.5	1537.8	1534.5	1544.8	1554.5	1554.7	1566.8	1575.9	1581.9
10°	1467.8	1460.0	1455.3	1459.2	1455.3	1460.0	1467.8	1478.0	1482.6	1493.5	1505.2
12.5°	1394.9	1390.2	1386.1	1384.4	1386.1	1390.2	1394.9	1405.6	1416.5	1429.3	1442.3
15°	1295.5	1286.2	1282.3	1272.2	1282.3	1286.2	1295.5	1304.9	1326.0	1331.4	1350.9
17.5°	1204.0	1200.9	1190.8	1186.4	1190.8	1200.9	1204.0	1212.0	1221.7	1241.8	1256.4
20°	1149.8	1146.7	1136.5	1142.8	1136.5	1146.7	1149.8	1161.5	1169.3	1185.6	1199.7
22.5°	1104.9	1098.0	1094.7	1092.9	1094.7	1098.0	1104.9	1110.3	1120.6	1135.7	1151.7
25°	1041.4	1031.3	1027.4	1022.7	1027.4	1031.3	1041.4	1044.5	1055.5	1070.3	1078.8
27.5°	978.1	972.7	967.5	966.3	967.5	972.7	978.1	982.5	992.0	1004.9	1020.4
30°	937.0	931.5	927.6	927.6	927.6	931.5	937.0	946.3	953.3	965.0	976.7
32.5°	900.2	896.0	892.1	891.5	892.1	896.0	900.2	905.2	913.4	926.4	938.7
35°	846.6	840.3	838.8	834.1	838.8	840.3	846.6	850.4	859.0	868.4	878.5
37.5°	790.9	785.7	785.6	785.1	785.6	785.7	790.9	797.8	804.9	813.3	825.8
40°	755.3	751.4	750.7	745.2	750.7	751.4	755.3	758.5	766.3	777.2	786.5
42.5°	717.3	715.3	712.6	710.3	712.6	715.3	717.3	723.5	730.1	737.9	749.7
45°	665.7	660.2	660.2	656.3	660.2	660.2	665.7	671.2	674.3	683.6	699.2
47.5°	612.4	608.2	608.6	604.6	608.6	608.2	612.4	614.1	619.1	628.3	636.9
50°	576.8	574.5	573.7	572.2	573.7	574.5	576.8	576.1	582.3	590.9	602.6
52.5°	541.3	540.2	543.2	539.7	543.2	540.2	541.3	543.0	547.4	552.8	563.9
55°	493.4	491.1	495.8	491.1	495.8	491.1	493.4	491.9	493.4	498.9	505.9
57.5°	438.4	436.2	440.4	438.1	440.4	436.2	438.4	438.7	443.4	444.2	450.4
60°	402.2	397.6	399.9	400.7	399.9	397.6	402.2	403.8	405.3	406.1	412.4
62.5°	359.2	356.4	358.1	354.5	358.1	356.4	359.2	362.6	366.1	370.0	373.7
65°	298.6	296.2	293.1	291.5	293.1	296.2	298.6	300.1	308.7	313.4	321.9
67.5°	250.8	245.2	245.1	246.3	245.1	245.2	250.8	250.5	256.8	260.5	266.3
70°	215.9	215.9	215.1	215.1	215.1	215.9	215.9	220.6	223.7	226.8	230.7
72.5°	191.6	191.0	189.6	189.0	189.6	191.0	191.6	193.2	195.0	198.2	202.0
75°	154.3	155.1	153.6	152.8	153.6	155.1	154.3	154.3	157.5	158.2	159.8
77.5°	114.0	110.7	112.4	110.7	112.4	110.7	114.0	117.1	118.2	121.6	121.8
80°	86.5	85.7	88.1	85.7	88.1	85.7	86.5	86.5	88.9	90.4	94.3
82.5°	68.4	67.7	68.8	67.0	68.8	67.7	68.4	67.8	68.9	71.1	70.6
85°	41.3	40.5	39.8	40.5	39.8	40.5	41.3	40.5	39.8	40.5	41.3
87.5°	18.7	18.1	18.3	18.3	18.3	18.1	18.7	18.1	18.3	18.1	17.9
90°	22.0	22.0	23.0	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0
92.5°	69.1	66.7	65.3	63.7	65.3	66.7	69.1	81.9	96.6	128.4	176.9
95°	288.5	258.6	250.6	234.6	250.6	258.6	288.5	359.4	443.2	566.0	717.8
97.5°	664.7	608.7	579.8	567.0	579.8	608.7	664.7	726.3	842.9	962.5	1069.0
100°	903.4	831.6	794.6	778.7	794.6	831.6	903.4	972.3	1076.1	1179.0	1227.9
102.5°	1118.3	1067.2	1027.0	1015.0	1027.0	1067.2	1118.3	1191.9	1262.2	1311.5	1281.4
105°	1387.6	1354.7	1334.7	1322.7	1334.7	1354.7	1387.6	1419.5	1430.5	1386.6	1249.8
107.5°	1500.8	1500.6	1494.0	1486.0	1494.0	1500.6	1500.8	1484.6	1432.5	1319.7	1137.2
110°	1514.4	1533.3	1540.3	1540.3	1540.3	1533.3	1514.4	1469.5	1384.6	1243.8	1054.2



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1476.8	1509.4	1526.8	1533.9	1526.8	1509.4	1476.8	1411.2	1311.1	1168.8	988.7
115°	1384.6	1432.5	1460.5	1473.5	1460.5	1432.5	1384.6	1306.7	1197.9	1061.2	906.4
117.5°	1282.2	1331.7	1359.4	1367.4	1359.4	1331.7	1282.2	1204.3	1104.5	986.7	853.3
120°	1215.9	1263.8	1290.8	1298.8	1290.8	1263.8	1215.9	1142.0	1054.2	944.4	824.6
122.5°	1160.0	1203.9	1230.9	1238.1	1230.9	1203.9	1160.0	1094.1	1011.8	914.0	803.0
125°	1088.1	1129.0	1151.0	1161.0	1151.0	1129.0	1088.1	1032.2	960.3	873.5	771.7
127.5°	1033.8	1069.9	1090.7	1095.1	1090.7	1069.9	1033.8	983.1	915.8	834.8	739.7
130°	1000.3	1033.2	1053.2	1059.2	1053.2	1033.2	1000.3	950.4	885.5	807.6	719.8
132.5°	965.1	998.1	1016.4	1023.2	1016.4	998.1	965.1	915.2	852.7	782.0	699.8
135°	907.4	940.4	958.3	964.3	958.3	940.4	907.4	863.5	806.6	742.7	673.8
137.5°	848.3	878.3	894.9	901.4	894.9	878.3	848.3	809.0	760.7	707.6	651.9
140°	811.6	837.6	852.5	857.5	852.5	837.6	811.6	774.7	732.7	686.8	639.9
142.5°	776.5	798.4	812.6	816.8	812.6	798.4	776.5	745.1	708.8	669.2	629.5
145°	728.7	745.7	756.7	760.7	756.7	745.7	728.7	704.8	677.8	646.9	615.9
147.5°	691.4	705.0	711.4	713.2	711.4	705.0	691.4	672.4	652.1	628.3	603.2
150°	669.8	681.8	685.8	686.8	685.8	681.8	669.8	654.9	636.9	617.9	596.0
152.5°	651.5	661.1	665.0	666.0	665.0	661.1	651.5	638.9	624.9	607.5	588.0
155°	626.9	633.9	636.9	637.9	636.9	633.9	626.9	616.9	606.0	592.0	576.0
157.5°	604.4	610.1	612.9	612.7	612.9	610.1	604.4	596.6	588.0	577.2	564.0
160°	590.0	595.0	597.0	596.0	597.0	595.0	590.0	583.0	576.0	566.0	556.0
162.5°	576.4	580.6	581.0	580.8	581.0	580.6	576.4	571.0	564.8	556.4	547.3
165°	557.0	559.0	559.0	559.0	559.0	559.0	557.0	553.0	548.1	542.1	535.1
167.5°	538.3	540.1	539.3	539.1	539.3	540.1	538.3	536.3	532.7	528.1	523.5
170°	527.1	528.1	528.1	527.1	528.1	528.1	527.1	525.1	523.1	520.1	517.1
172.5°	516.7	518.5	516.9	515.9	516.9	518.5	516.7	516.3	515.1	512.9	509.9
175°	504.1	505.1	503.1	502.1	503.1	505.1	504.1	504.1	504.1	502.1	502.1
177.5°	496.7	497.5	495.1	495.1	495.1	497.5	496.7	497.5	497.5	497.5	496.7
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1820.3	1827.2	1830.9	1839.6	1852.1	1858.4	1867.1	1873.3	1882.1	1892.7	1901.4
5°	1702.5	1721.2	1733.6	1753.1	1771.1	1789.0	1811.6	1828.0	1849.8	1874.7	1894.2
7.5°	1593.0	1616.4	1637.1	1662.9	1692.5	1715.6	1745.0	1775.1	1809.2	1844.6	1878.0
10°	1523.2	1546.6	1572.3	1604.2	1633.9	1665.0	1700.1	1735.2	1778.1	1817.8	1863.0
12.5°	1453.9	1479.8	1508.7	1544.4	1580.2	1620.1	1655.8	1695.3	1741.3	1792.9	1841.2
15°	1368.0	1393.0	1424.2	1454.6	1495.9	1539.5	1587.1	1639.3	1690.8	1748.4	1808.5
17.5°	1275.9	1303.3	1337.6	1372.9	1416.4	1467.5	1514.1	1571.3	1629.2	1696.4	1767.0
20°	1216.0	1244.1	1284.6	1323.6	1363.4	1413.3	1468.6	1527.1	1588.6	1659.6	1738.3
22.5°	1168.6	1188.6	1228.5	1268.1	1314.7	1365.9	1420.0	1480.9	1548.1	1621.5	1704.0
25°	1098.3	1121.7	1150.6	1191.9	1240.2	1294.0	1348.6	1413.3	1486.5	1561.4	1649.4
27.5°	1035.8	1055.0	1083.5	1115.9	1164.1	1219.9	1277.9	1345.4	1420.6	1496.8	1589.4
30°	991.5	1012.6	1039.9	1074.2	1112.4	1173.2	1232.4	1298.7	1375.1	1453.8	1548.9
32.5°	952.9	974.5	998.1	1030.5	1071.8	1125.8	1186.9	1251.9	1329.5	1410.8	1503.4
35°	898.8	913.6	935.4	967.4	1007.9	1051.6	1113.9	1182.5	1258.1	1342.3	1435.1
37.5°	836.7	855.9	877.6	905.3	940.9	988.1	1046.1	1115.5	1185.6	1266.2	1350.9
40°	800.6	818.5	842.7	862.9	900.3	943.2	996.2	1068.7	1138.9	1214.5	1291.7
42.5°	763.8	781.1	801.5	826.8	860.4	902.1	951.3	1018.8	1094.0	1165.2	1229.9
45°	706.2	724.2	743.7	767.0	798.2	838.8	887.9	949.4	1014.9	1080.4	1129.5
47.5°	651.2	668.0	686.4	710.4	739.1	778.3	822.2	876.6	940.2	995.9	1031.0
50°	611.9	627.5	647.8	671.2	699.2	735.9	778.0	831.7	884.7	935.4	967.4
52.5°	573.3	590.7	611.0	631.2	658.1	694.7	733.7	780.0	830.5	871.8	898.2
55°	515.3	531.6	550.3	571.4	597.9	629.1	670.4	707.0	746.8	781.9	797.4
57.5°	459.3	473.6	491.2	513.1	536.9	565.9	598.7	633.9	662.0	686.8	704.4
60°	422.5	435.0	451.3	470.0	495.8	522.3	551.9	584.6	606.5	627.5	643.9
62.5°	385.1	396.9	412.7	429.5	452.1	476.7	505.1	531.6	552.8	567.0	585.9
65°	329.0	340.6	353.9	371.8	389.8	410.0	435.7	455.2	470.0	485.6	497.3
67.5°	276.7	286.4	299.0	313.1	328.2	347.7	367.6	383.8	394.0	403.3	417.4
70°	242.4	250.2	260.4	271.3	287.6	307.1	322.7	335.2	342.2	351.6	368.7
72.5°	207.5	216.5	226.1	237.0	250.2	266.6	280.3	292.8	297.3	304.8	315.7
75°	163.7	168.4	176.2	184.0	193.3	207.4	220.6	223.7	227.6	233.9	241.6
77.5°	123.8	128.0	131.1	136.3	143.7	155.0	162.0	166.7	167.6	169.9	177.6
80°	98.2	100.6	103.7	107.6	110.7	120.0	123.9	128.6	130.2	132.5	136.4
82.5°	72.0	74.4	76.2	79.5	84.5	88.2	92.1	96.8	97.1	98.8	99.6
85°	42.1	42.9	41.3	42.9	43.7	45.2	49.1	53.0	52.2	51.4	53.8
87.5°	18.4	18.2	17.1	18.8	17.2	17.6	17.2	17.4	18.3	19.1	20.2
90°	17.0	16.0	14.0	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0
92.5°	260.5	321.8	327.0	227.8	136.4	81.9	52.7	35.5	23.2	14.8	12.2
95°	865.5	884.5	721.8	446.2	226.6	119.8	74.9	52.9	41.9	33.9	32.9
97.5°	1095.1	944.6	644.5	356.2	195.3	124.6	92.2	72.5	61.5	55.9	54.7
100°	1151.0	901.4	575.0	323.4	193.7	135.8	105.8	86.8	75.9	71.9	69.9
102.5°	1117.5	825.6	522.3	309.9	200.9	149.3	120.2	102.8	91.0	87.8	86.7
105°	1010.3	723.7	471.2	304.5	215.6	171.7	143.8	127.8	117.8	112.8	112.8
107.5°	900.8	653.7	449.6	313.7	237.6	195.1	169.9	153.3	145.1	140.4	138.4
110°	838.5	620.9	443.2	322.4	253.6	212.6	186.7	171.7	162.7	158.7	156.7



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	792.2	601.8	443.2	333.6	268.7	229.4	204.2	189.3	180.3	177.1	175.1
115°	741.7	581.0	446.2	350.4	292.5	255.6	230.6	215.6	206.6	203.6	201.7
117.5°	711.6	570.8	452.8	369.6	316.9	281.9	257.8	240.8	231.8	228.6	225.6
120°	694.8	566.0	459.2	382.3	334.4	299.5	274.5	257.6	248.6	244.6	241.6
122.5°	680.4	562.0	464.8	396.7	351.2	316.3	291.3	272.7	263.7	260.5	258.4
125°	660.9	557.0	474.2	416.3	373.4	340.4	314.5	295.5	286.5	281.5	279.5
127.5°	642.9	554.6	484.8	434.2	394.7	363.0	337.0	316.9	305.5	299.1	296.1
130°	630.9	553.0	491.2	446.2	408.3	377.3	351.4	330.4	317.5	309.5	306.5
132.5°	621.3	553.0	498.3	456.6	421.1	390.1	364.2	342.4	327.8	318.2	314.5
135°	609.9	553.0	508.1	471.2	438.2	407.3	380.3	359.4	343.4	331.4	327.4
137.5°	599.8	554.2	517.1	482.0	450.4	422.3	394.5	374.0	358.0	346.8	343.8
140°	595.0	555.0	521.1	489.2	459.2	430.3	403.3	384.3	368.4	356.4	353.4
142.5°	591.0	555.8	523.5	493.1	464.8	437.4	412.1	393.9	377.9	366.8	364.6
145°	585.0	555.0	526.1	499.1	474.2	448.2	425.3	407.3	393.3	383.3	381.3
147.5°	578.8	552.4	527.1	502.7	480.2	457.4	437.2	421.7	408.7	400.1	398.9
150°	574.0	550.0	527.1	505.1	484.2	462.2	445.2	431.3	418.3	411.3	409.3
152.5°	568.4	546.9	526.3	506.7	488.2	467.8	452.4	439.2	427.9	421.7	420.5
155°	559.0	541.1	524.1	508.1	492.1	475.2	461.2	451.2	441.2	435.2	435.2
157.5°	550.2	535.1	521.5	509.1	495.5	481.0	470.4	461.6	453.0	448.2	448.4
160°	543.1	531.1	519.1	509.1	497.1	484.2	475.2	467.2	460.2	456.2	457.2
162.5°	536.7	526.3	516.7	508.3	498.7	487.4	480.0	473.6	467.4	463.4	464.4
165°	527.1	519.1	513.1	507.1	499.1	491.2	485.2	481.2	476.2	473.2	475.2
167.5°	517.7	512.1	507.5	504.7	499.1	492.5	488.8	486.0	483.2	481.4	482.4
170°	512.1	508.1	505.1	503.1	499.1	494.1	491.2	489.2	487.2	486.2	487.2
172.5°	506.5	503.3	501.9	501.5	498.3	494.1	492.7	491.5	489.6	488.6	490.4
175°	499.1	498.1	498.1	499.1	497.1	494.1	494.1	494.1	493.1	492.1	494.1
177.5°	495.9	495.1	495.1	496.7	495.9	494.3	494.3	495.1	494.3	494.3	495.9
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1908.2	1913.9	1922.0	1931.3	1938.8	1946.9	1951.3	1951.3	1955.0	1963.1	1973.7
5°	1913.7	1934.0	1953.5	1978.4	1997.9	2020.5	2037.6	2054.0	2068.8	2087.5	2107.0
7.5°	1912.1	1945.8	1980.9	2020.2	2063.5	2098.0	2133.4	2161.1	2188.6	2224.4	2252.6
10°	1905.9	1949.6	1997.1	2047.0	2101.6	2149.1	2192.0	2231.0	2268.4	2307.4	2342.4
12.5°	1894.7	1950.2	2008.3	2068.2	2137.1	2191.5	2246.9	2288.3	2332.0	2374.7	2417.9
15°	1877.8	1943.3	2013.5	2096.9	2181.1	2241.9	2296.4	2350.2	2390.8	2439.1	2480.4
17.5°	1843.1	1927.4	2015.7	2106.9	2187.8	2258.4	2315.6	2366.8	2409.9	2463.1	2519.2
20°	1822.5	1913.7	2005.7	2103.1	2180.3	2252.8	2308.1	2361.1	2414.9	2484.3	2552.9
22.5°	1793.8	1891.3	1988.8	2081.3	2162.8	2232.8	2290.1	2354.9	2425.5	2504.3	2587.2
25°	1748.4	1849.0	1945.7	2033.7	2113.3	2185.0	2262.9	2350.2	2436.0	2539.7	2658.9
27.5°	1690.9	1787.9	1874.1	1967.2	2046.2	2137.4	2234.7	2329.3	2453.0	2595.6	2744.5
30°	1647.9	1739.9	1821.7	1909.8	1999.4	2100.0	2209.1	2320.6	2467.9	2635.5	2812.5
32.5°	1598.0	1681.3	1762.5	1847.4	1950.8	2061.3	2177.3	2313.7	2489.8	2680.4	2863.6
35°	1511.5	1586.3	1665.0	1759.4	1869.3	1989.3	2137.4	2303.5	2516.3	2721.3	2885.8
37.5°	1420.7	1479.8	1558.9	1658.3	1778.1	1917.0	2085.0	2286.8	2505.4	2689.3	2759.3
40°	1350.9	1406.2	1489.6	1594.1	1712.6	1864.6	2053.2	2260.6	2480.4	2608.2	2602.8
42.5°	1281.7	1337.6	1417.9	1523.0	1646.5	1816.6	2010.8	2226.3	2411.8	2460.5	2359.0
45°	1175.5	1227.7	1306.5	1412.5	1545.0	1723.5	1927.7	2134.3	2252.8	2174.1	1972.9
47.5°	1067.3	1118.0	1191.1	1294.9	1439.6	1626.4	1819.5	1989.0	2005.7	1836.5	1595.3
50°	996.2	1043.8	1113.1	1223.8	1364.1	1546.6	1732.9	1866.2	1824.8	1618.3	1369.6
52.5°	927.0	972.7	1037.7	1142.1	1285.6	1464.2	1630.6	1735.2	1639.6	1420.0	1196.2
55°	824.7	868.4	933.9	1029.7	1159.9	1323.6	1469.4	1507.6	1367.3	1145.9	965.0
57.5°	727.6	759.6	824.3	909.1	1034.6	1178.9	1283.4	1276.5	1121.7	922.3	792.6
60°	663.4	692.2	753.8	831.7	951.0	1080.4	1153.7	1122.5	965.8	801.3	676.6
62.5°	603.5	630.5	682.1	753.8	856.2	968.8	1022.1	979.1	831.1	686.6	587.4
65°	512.9	532.4	573.7	640.0	720.3	798.2	845.8	782.6	651.7	542.5	467.7
67.5°	428.3	445.1	481.9	529.4	584.8	638.6	657.9	598.7	496.9	423.3	370.6
70°	373.4	389.0	413.9	458.4	495.0	533.2	542.5	489.5	404.6	348.4	315.7
72.5°	321.0	335.3	357.2	388.5	413.9	435.9	440.3	391.0	326.0	287.3	262.1
75°	244.8	257.2	271.3	283.0	299.3	303.2	301.7	263.5	228.4	202.7	188.6
77.5°	179.9	185.1	193.6	198.3	199.1	198.8	190.8	166.7	148.6	138.0	132.2
80°	138.8	142.7	145.0	146.5	147.3	139.5	131.0	116.1	109.9	103.7	96.7
82.5°	100.7	103.4	105.7	106.0	101.8	95.3	87.3	80.0	75.6	72.5	69.8
85°	54.6	55.3	54.6	50.7	45.2	42.9	41.3	39.8	39.0	38.2	38.2
87.5°	19.7	18.3	15.5	16.6	17.0	16.5	16.9	16.5	16.3	16.5	16.7
90°	2.0	4.0	6.0	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0
92.5°	14.8	23.2	35.5	52.7	81.9	136.4	227.8	327.0	321.8	260.5	176.9
95°	33.9	41.9	52.9	74.9	119.8	226.6	446.2	721.8	884.5	865.5	717.8
97.5°	55.9	61.5	72.5	92.2	124.6	195.3	356.2	644.5	944.6	1095.1	1069.0
100°	71.9	75.9	86.8	105.8	135.8	193.7	323.4	575.0	901.4	1151.0	1227.9
102.5°	87.8	91.0	102.8	120.2	149.3	200.9	309.9	522.3	825.6	1117.5	1281.4
105°	112.8	117.8	127.8	143.8	171.7	215.6	304.5	471.2	723.7	1010.3	1249.8
107.5°	140.4	145.1	153.3	169.9	195.1	237.6	313.7	449.6	653.7	900.8	1137.2
110°	158.7	162.7	171.7	186.7	212.6	253.6	322.4	443.2	620.9	838.5	1054.2



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	177.1	180.3	189.3	204.2	229.4	268.7	333.6	443.2	601.8	792.2	988.7
115°	203.6	206.6	215.6	230.6	255.6	292.5	350.4	446.2	581.0	741.7	906.4
117.5°	228.6	231.8	240.8	257.8	281.9	316.9	369.6	452.8	570.8	711.6	853.3
120°	244.6	248.6	257.6	274.5	299.5	334.4	382.3	459.2	566.0	694.8	824.6
122.5°	260.5	263.7	272.7	291.3	316.3	351.2	396.7	464.8	562.0	680.4	803.0
125°	281.5	286.5	295.5	314.5	340.4	373.4	416.3	474.2	557.0	660.9	771.7
127.5°	299.1	305.5	316.9	337.0	363.0	394.7	434.2	484.8	554.6	642.9	739.7
130°	309.5	317.5	330.4	351.4	377.3	408.3	446.2	491.2	553.0	630.9	719.8
132.5°	318.2	327.8	342.4	364.2	390.1	421.1	456.6	498.3	553.0	621.3	699.8
135°	331.4	343.4	359.4	380.3	407.3	438.2	471.2	508.1	553.0	609.9	673.8
137.5°	346.8	358.0	374.0	394.5	422.3	450.4	482.0	517.1	554.2	599.8	651.9
140°	356.4	368.4	384.3	403.3	430.3	459.2	489.2	521.1	555.0	595.0	639.9
142.5°	366.8	377.9	393.9	412.1	437.4	464.8	493.1	523.5	555.8	591.0	629.5
145°	383.3	393.3	407.3	425.3	448.2	474.2	499.1	526.1	555.0	585.0	615.9
147.5°	400.1	408.7	421.7	437.2	457.4	480.2	502.7	527.1	552.4	578.8	603.2
150°	411.3	418.3	431.3	445.2	462.2	484.2	505.1	527.1	550.0	574.0	596.0
152.5°	421.7	427.9	439.2	452.4	467.8	488.2	506.7	526.3	546.9	568.4	588.0
155°	435.2	441.2	451.2	461.2	475.2	492.1	508.1	524.1	541.1	559.0	576.0
157.5°	448.2	453.0	461.6	470.4	481.0	495.5	509.1	521.5	535.1	550.2	564.0
160°	456.2	460.2	467.2	475.2	484.2	497.1	509.1	519.1	531.1	543.1	556.0
162.5°	463.4	467.4	473.6	480.0	487.4	498.7	508.3	516.7	526.3	536.7	547.3
165°	473.2	476.2	481.2	485.2	491.2	499.1	507.1	513.1	519.1	527.1	535.1
167.5°	481.4	483.2	486.0	488.8	492.5	499.1	504.7	507.5	512.1	517.7	523.5
170°	486.2	487.2	489.2	491.2	494.1	499.1	503.1	505.1	508.1	512.1	517.1
172.5°	488.6	489.6	491.5	492.7	494.1	498.3	501.5	501.9	503.3	506.5	509.9
175°	492.1	493.1	494.1	494.1	494.1	497.1	499.1	498.1	498.1	499.1	502.1
177.5°	494.3	494.3	495.1	494.3	494.3	495.9	496.7	495.1	495.1	495.9	496.7
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1981.8	1981.8	1992.4	1991.8	1998.7	1996.2	1997.4
5°	2130.4	2143.7	2155.4	2163.1	2174.8	2178.0	2176.4
7.5°	2284.4	2313.9	2328.2	2347.9	2351.5	2361.8	2360.7
10°	2379.9	2408.7	2430.5	2447.7	2456.2	2467.2	2467.9
12.5°	2454.7	2479.2	2498.5	2514.4	2524.8	2528.3	2530.3
15°	2513.1	2540.4	2563.0	2585.6	2598.9	2609.0	2614.5
17.5°	2572.1	2614.2	2654.1	2684.8	2703.2	2718.8	2718.6
20°	2617.6	2665.9	2715.8	2750.9	2786.8	2802.3	2804.7
22.5°	2666.2	2740.1	2804.4	2858.8	2905.9	2922.1	2928.2
25°	2767.3	2863.9	2962.9	3039.3	3093.9	3125.8	3130.5
27.5°	2889.3	3020.1	3124.3	3194.8	3240.1	3263.8	3269.0
30°	2975.4	3096.2	3189.8	3242.8	3263.8	3266.9	3255.2
32.5°	3014.1	3104.3	3141.7	3138.6	3097.3	3069.9	3059.4
35°	2966.8	2948.1	2856.9	2747.8	2664.4	2611.4	2597.3
37.5°	2699.9	2538.6	2370.8	2205.9	2118.1	2073.5	1996.8
40°	2436.8	2206.8	2032.2	1893.4	1794.4	1714.9	1696.2
42.5°	2139.9	1902.5	1727.9	1609.1	1530.0	1475.5	1451.8
45°	1719.6	1515.4	1371.2	1280.0	1219.2	1179.4	1161.5
47.5°	1375.4	1217.3	1112.2	1044.7	998.4	963.8	954.1
50°	1186.4	1060.1	971.3	914.4	879.3	852.8	841.9
52.5°	1030.5	928.6	860.3	813.3	780.1	763.6	754.6
55°	850.4	762.4	713.3	675.8	657.1	643.9	637.6
57.5°	695.5	631.9	596.0	570.1	552.8	544.4	541.3
60°	608.8	558.9	526.2	505.9	494.2	483.3	480.2
62.5°	532.1	492.8	467.6	449.8	438.1	433.4	431.5
65°	428.7	403.0	384.3	373.4	364.0	362.5	361.7
67.5°	340.8	325.7	315.9	304.5	301.2	295.7	294.7
70°	291.5	281.4	269.7	265.8	261.9	256.5	257.2
72.5°	247.3	237.1	229.2	224.0	222.6	220.3	222.3
75°	180.8	177.7	174.6	170.7	169.2	169.2	168.4
77.5°	129.1	126.4	123.0	120.7	120.2	116.9	118.2
80°	93.5	89.6	88.1	88.9	86.5	85.7	85.7
82.5°	69.2	67.8	66.3	66.4	65.9	65.2	65.8
85°	38.2	37.4	37.4	36.6	36.6	35.9	35.9
87.5°	17.5	18.3	17.5	16.9	16.9	17.7	18.3
90°	19.0	20.0	22.0	22.0	22.0	23.0	23.0
92.5°	128.4	96.6	81.9	69.1	66.7	65.3	63.7
95°	566.0	443.2	359.4	288.5	258.6	250.6	234.6
97.5°	962.5	842.9	726.3	664.7	608.7	579.8	567.0
100°	1179.0	1076.1	972.3	903.4	831.6	794.6	778.7
102.5°	1311.5	1262.2	1191.9	1118.3	1067.2	1027.0	1015.0
105°	1386.6	1430.5	1419.5	1387.6	1354.7	1334.7	1322.7
107.5°	1319.7	1432.5	1484.6	1500.8	1500.6	1494.0	1486.0
110°	1243.8	1384.6	1469.5	1514.4	1533.3	1540.3	1540.3



TEST NUMBER: P333630

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1168.8	1311.1	1411.2	1476.8	1509.4	1526.8	1533.9
115°	1061.2	1197.9	1306.7	1384.6	1432.5	1460.5	1473.5
117.5°	986.7	1104.5	1204.3	1282.2	1331.7	1359.4	1367.4
120°	944.4	1054.2	1142.0	1215.9	1263.8	1290.8	1298.8
122.5°	914.0	1011.8	1094.1	1160.0	1203.9	1230.9	1238.1
125°	873.5	960.3	1032.2	1088.1	1129.0	1151.0	1161.0
127.5°	834.8	915.8	983.1	1033.8	1069.9	1090.7	1095.1
130°	807.6	885.5	950.4	1000.3	1033.2	1053.2	1059.2
132.5°	782.0	852.7	915.2	965.1	998.1	1016.4	1023.2
135°	742.7	806.6	863.5	907.4	940.4	958.3	964.3
137.5°	707.6	760.7	809.0	848.3	878.3	894.9	901.4
140°	686.8	732.7	774.7	811.6	837.6	852.5	857.5
142.5°	669.2	708.8	745.1	776.5	798.4	812.6	816.8
145°	646.9	677.8	704.8	728.7	745.7	756.7	760.7
147.5°	628.3	652.1	672.4	691.4	705.0	711.4	713.2
150°	617.9	636.9	654.9	669.8	681.8	685.8	686.8
152.5°	607.5	624.9	638.9	651.5	661.1	665.0	666.0
155°	592.0	606.0	616.9	626.9	633.9	636.9	637.9
157.5°	577.2	588.0	596.6	604.4	610.1	612.9	612.7
160°	566.0	576.0	583.0	590.0	595.0	597.0	596.0
162.5°	556.4	564.8	571.0	576.4	580.6	581.0	580.8
165°	542.1	548.1	553.0	557.0	559.0	559.0	559.0
167.5°	528.1	532.7	536.3	538.3	540.1	539.3	539.1
170°	520.1	523.1	525.1	527.1	528.1	528.1	527.1
172.5°	512.9	515.1	516.3	516.7	518.5	516.9	515.9
175°	502.1	504.1	504.1	504.1	505.1	503.1	502.1
177.5°	497.5	497.5	497.5	496.7	497.5	495.1	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1

(END OF REPORT)