

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333636

Luminaire Tested: **S125RDIP-S1270D1205U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333636
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9244.9 lumens
Efficiency: N/A
Efficacy: 128.9 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	56	54	51	47	45	43	39
3	83	74	66	61	76	69	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	64	55	47	42	47	42	37	41	36	33	34	31	29	25
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	47	40	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20	18
9	52	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12264	12264	12264	12264
5°	14110	12280	10845	12280
10°	16184	12218	9569	12218
15°	17481	12092	8506	12092
20°	19276	11947	7854	11947
25°	22308	11754	7288	11754
30°	24276	11551	6918	11551
35°	20478	11315	6576	11315
40°	14300	10890	6283	10890
45°	10609	10316	5994	10316
50°	8459	9720	5749	9720
55°	7179	8979	5530	8979
60°	6203	8317	5176	8317
65°	5527	7600	4455	7600
70°	4857	6962	4062	6962
75°	4202	6029	3813	6029
80°	3187	5073	3187	5073
85°	2660	3987	3001	3987



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.1	2.0
10°-20°	533.6	5.8
20°-30°	846.1	9.2
30°-40°	1020.3	11.0
40°-50°	911.2	9.9
50°-60°	698.8	7.6
60°-70°	454.1	4.9
70°-80°	220.8	2.4
80°-90°	55.9	0.6
90°-100°	417.8	4.5
100°-110°	898.0	9.7
110°-120°	842.8	9.1
120°-130°	683.0	7.4
130°-140°	548.1	5.9
140°-150°	413.6	4.5
150°-160°	291.2	3.1
160°-170°	171.6	1.9
170°-180°	55.8	0.6
0°-30°	1561.8	16.9
0°-40°	2582.2	27.9
0°-60°	4192.1	45.3
0°-90°	4922.9	53.3
90°-120°	2158.6	23.3
90°-150°	3803.4	41.1
90°-180°	4322.0	46.7
0°-180°	9244.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2176	1894	1673	1894	2176	217
15°	2614	1808	1272	1808	2614	749
25°	3130	1649	1023	1649	3130	1437
35°	2597	1435	834	1435	2597	1569
45°	1162	1130	656	1130	1162	927
55°	638	797	491	797	638	579
65°	362	497	292	497	362	360
75°	168	242	153	242	168	179
85°	36	54	40	54	36	42
90°	27	1	27	1	27	20
95°	273	38	273	38	273	387
105°	1540	131	1540	131	1540	1530
115°	1715	235	1715	235	1715	1676
125°	1351	325	1351	325	1351	1223
135°	1122	381	1122	381	1122	870
145°	885	444	885	444	885	563
155°	742	507	742	507	742	346
165°	651	553	651	553	651	186
175°	584	575	584	575	584	57
180°	576	576	576	576	576	



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1997.4	1996.2	1998.7	1991.8	1992.4	1981.8	1981.8	1973.7	1963.1	1955.0	1951.3
5°	2176.4	2178.0	2174.8	2163.1	2155.4	2143.7	2130.4	2107.0	2087.5	2068.8	2054.0
7.5°	2360.7	2361.8	2351.5	2347.9	2328.2	2313.9	2284.4	2252.6	2224.4	2188.6	2161.1
10°	2467.9	2467.2	2456.2	2447.7	2430.5	2408.7	2379.9	2342.4	2307.4	2268.4	2231.0
12.5°	2530.3	2528.3	2524.8	2514.4	2498.5	2479.2	2454.7	2417.9	2374.7	2332.0	2288.3
15°	2614.5	2609.0	2598.9	2585.6	2563.0	2540.4	2513.1	2480.4	2439.1	2390.8	2350.2
17.5°	2718.6	2718.8	2703.2	2684.8	2654.1	2614.2	2572.1	2519.2	2463.1	2409.9	2366.8
20°	2804.7	2802.3	2786.8	2750.9	2715.8	2665.9	2617.6	2552.9	2484.3	2414.9	2361.1
22.5°	2928.2	2922.1	2905.9	2858.8	2804.4	2740.1	2666.2	2587.2	2504.3	2425.5	2354.9
25°	3130.5	3125.8	3093.9	3039.3	2962.9	2863.9	2767.3	2658.9	2539.7	2436.0	2350.2
27.5°	3269.0	3263.8	3240.1	3194.8	3124.3	3020.1	2889.3	2744.5	2595.6	2453.0	2329.3
30°	3255.2	3266.9	3263.8	3242.8	3189.8	3096.2	2975.4	2812.5	2635.5	2467.9	2320.6
32.5°	3059.4	3069.9	3097.3	3138.6	3141.7	3104.3	3014.1	2863.6	2680.4	2489.8	2313.7
35°	2597.3	2611.4	2664.4	2747.8	2856.9	2948.1	2966.8	2885.8	2721.3	2516.3	2303.5
37.5°	1996.8	2073.5	2118.1	2205.9	2370.8	2538.6	2699.9	2759.3	2689.3	2505.4	2286.8
40°	1696.2	1714.9	1794.4	1893.4	2032.2	2206.8	2436.8	2602.8	2608.2	2480.4	2260.6
42.5°	1451.8	1475.5	1530.0	1609.1	1727.9	1902.5	2139.9	2359.0	2460.5	2411.8	2226.3
45°	1161.5	1179.4	1219.2	1280.0	1371.2	1515.4	1719.6	1972.9	2174.1	2252.8	2134.3
47.5°	954.1	963.8	998.4	1044.7	1112.2	1217.3	1375.4	1595.3	1836.5	2005.7	1989.0
50°	841.9	852.8	879.3	914.4	971.3	1060.1	1186.4	1369.6	1618.3	1824.8	1866.2
52.5°	754.6	763.6	780.1	813.3	860.3	928.6	1030.5	1196.2	1420.0	1639.6	1735.2
55°	637.6	643.9	657.1	675.8	713.3	762.4	850.4	965.0	1145.9	1367.3	1507.6
57.5°	541.3	544.4	552.8	570.1	596.0	631.9	695.5	792.6	922.3	1121.7	1276.5
60°	480.2	483.3	494.2	505.9	526.2	558.9	608.8	676.6	801.3	965.8	1122.5
62.5°	431.5	433.4	438.1	449.8	467.6	492.8	532.1	587.4	686.6	831.1	979.1
65°	361.7	362.5	364.0	373.4	384.3	403.0	428.7	467.7	542.5	651.7	782.6
67.5°	294.7	295.7	301.2	304.5	315.9	325.7	340.8	370.6	423.3	496.9	598.7
70°	257.2	256.5	261.9	265.8	269.7	281.4	291.5	315.7	348.4	404.6	489.5
72.5°	222.3	220.3	222.6	224.0	229.2	237.1	247.3	262.1	287.3	326.0	391.0
75°	168.4	169.2	169.2	170.7	174.6	177.7	180.8	188.6	202.7	228.4	263.5
77.5°	118.2	116.9	120.2	120.7	123.0	126.4	129.1	132.2	138.0	148.6	166.7
80°	85.7	85.7	86.5	88.9	88.1	89.6	93.5	96.7	103.7	109.9	116.1
82.5°	65.8	65.2	65.9	66.4	66.3	67.8	69.2	69.8	72.5	75.6	80.0
85°	35.9	35.9	36.6	36.6	37.4	37.4	38.2	38.2	38.2	39.0	39.8
87.5°	19.1	18.4	17.6	17.6	18.2	19.0	18.1	17.3	17.0	16.8	17.0
90°	26.7	26.7	25.6	25.6	25.6	23.2	22.1	20.9	19.8	18.6	16.3
92.5°	74.1	76.0	77.6	80.4	95.3	112.5	149.4	205.9	303.3	374.6	380.7
95°	273.1	291.7	300.9	335.8	418.3	515.9	658.8	835.4	1007.4	1029.5	840.1
97.5°	660.0	674.9	708.6	773.6	845.4	981.2	1120.4	1244.2	1274.7	1099.4	750.2
100°	906.3	924.9	967.9	1051.6	1131.7	1252.6	1372.3	1429.2	1339.7	1049.2	669.3
102.5°	1181.5	1195.4	1242.1	1301.6	1387.4	1469.2	1526.6	1491.5	1300.7	960.9	607.9
105°	1539.6	1553.5	1576.8	1615.1	1652.3	1665.1	1614.0	1454.8	1175.9	842.4	548.4
107.5°	1729.7	1739.0	1746.7	1746.9	1728.1	1667.4	1536.1	1323.7	1048.6	760.8	523.3
110°	1792.9	1792.9	1784.8	1762.7	1710.4	1611.6	1447.8	1227.0	976.0	722.7	515.9



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1785.5	1777.1	1756.9	1719.0	1642.5	1526.1	1360.4	1150.8	922.1	700.4	515.9
115°	1715.0	1699.9	1667.4	1611.6	1521.0	1394.3	1235.2	1055.1	863.3	676.3	519.4
117.5°	1591.6	1582.4	1550.1	1492.4	1401.8	1285.6	1148.5	993.2	828.2	664.4	527.1
120°	1511.7	1502.4	1471.0	1415.3	1329.3	1227.0	1099.2	959.8	808.7	658.8	534.5
122.5°	1441.1	1432.7	1401.3	1350.2	1273.5	1177.8	1063.9	934.7	792.0	654.2	541.0
125°	1351.4	1339.7	1314.2	1266.5	1201.5	1117.8	1016.7	898.2	769.2	648.4	551.9
127.5°	1274.7	1269.6	1245.4	1203.3	1144.3	1066.0	971.6	861.0	748.3	645.6	564.2
130°	1232.8	1225.9	1202.6	1164.3	1106.2	1030.7	940.0	837.8	734.4	643.7	571.7
132.5°	1191.0	1183.1	1161.7	1123.4	1065.3	992.5	910.3	814.5	723.2	643.7	580.0
135°	1122.5	1115.5	1094.6	1056.2	1005.1	938.9	864.5	784.3	710.0	643.7	591.4
137.5°	1049.2	1041.6	1022.3	987.4	941.7	885.4	823.6	758.8	698.1	645.1	601.9
140°	998.1	992.3	974.9	944.7	901.7	852.9	799.4	744.8	692.5	646.0	606.5
142.5°	950.7	945.8	929.3	903.8	867.3	825.0	779.0	732.7	687.9	647.0	609.3
145°	885.4	880.8	868.0	848.2	820.3	789.0	752.9	716.9	680.9	646.0	612.4
147.5°	830.1	828.0	820.6	804.8	782.7	759.0	731.3	702.1	673.7	643.0	613.5
150°	799.4	798.3	793.6	779.7	762.2	741.3	719.3	693.7	668.1	640.2	613.5
152.5°	775.3	774.1	769.4	758.3	743.7	727.4	707.2	684.4	661.6	636.5	612.6
155°	742.5	741.3	737.8	729.7	718.1	705.3	689.0	670.4	650.7	629.8	610.0
157.5°	713.2	713.4	710.2	703.4	694.4	684.4	671.8	656.5	640.5	622.8	607.0
160°	693.7	694.9	692.5	686.7	678.6	670.4	658.8	647.2	632.1	618.2	604.2
162.5°	676.0	676.3	675.8	670.9	664.6	657.4	647.7	637.0	624.7	612.6	601.4
165°	650.7	650.7	650.7	648.4	643.7	637.9	630.9	622.8	613.5	604.2	597.2
167.5°	627.5	627.7	628.6	626.5	624.2	620.0	614.7	609.3	602.6	596.1	590.7
170°	613.5	614.7	614.7	613.5	611.2	608.9	605.4	601.9	596.1	591.4	588.0
172.5°	600.5	601.7	603.5	601.4	601.0	599.6	597.0	593.5	589.6	585.9	584.2
175°	584.5	585.6	588.0	586.8	586.8	586.8	584.5	584.5	581.0	579.8	579.8
177.5°	576.3	576.3	579.1	578.2	579.1	579.1	579.1	578.2	577.3	576.3	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1951.3	1946.9	1938.8	1931.3	1922.0	1913.9	1908.2	1901.4	1892.7	1882.1	1873.3
5°	2037.6	2020.5	1997.9	1978.4	1953.5	1934.0	1913.7	1894.2	1874.7	1849.8	1828.0
7.5°	2133.4	2098.0	2063.5	2020.2	1980.9	1945.8	1912.1	1878.0	1844.6	1809.2	1775.1
10°	2192.0	2149.1	2101.6	2047.0	1997.1	1949.6	1905.9	1863.0	1817.8	1778.1	1735.2
12.5°	2246.9	2191.5	2137.1	2068.2	2008.3	1950.2	1894.7	1841.2	1792.9	1741.3	1695.3
15°	2296.4	2241.9	2181.1	2096.9	2013.5	1943.3	1877.8	1808.5	1748.4	1690.8	1639.3
17.5°	2315.6	2258.4	2187.8	2106.9	2015.7	1927.4	1843.1	1767.0	1696.4	1629.2	1571.3
20°	2308.1	2252.8	2180.3	2103.1	2005.7	1913.7	1822.5	1738.3	1659.6	1588.6	1527.1
22.5°	2290.1	2232.8	2162.8	2081.3	1988.8	1891.3	1793.8	1704.0	1621.5	1548.1	1480.9
25°	2262.9	2185.0	2113.3	2033.7	1945.7	1849.0	1748.4	1649.4	1561.4	1486.5	1413.3
27.5°	2234.7	2137.4	2046.2	1967.2	1874.1	1787.9	1690.9	1589.4	1496.8	1420.6	1345.4
30°	2209.1	2100.0	1999.4	1909.8	1821.7	1739.9	1647.9	1548.9	1453.8	1375.1	1298.7
32.5°	2177.3	2061.3	1950.8	1847.4	1762.5	1681.3	1598.0	1503.4	1410.8	1329.5	1251.9
35°	2137.4	1989.3	1869.3	1759.4	1665.0	1586.3	1511.5	1435.1	1342.3	1258.1	1182.5
37.5°	2085.0	1917.0	1778.1	1658.3	1558.9	1479.8	1420.7	1350.9	1266.2	1185.6	1115.5
40°	2053.2	1864.6	1712.6	1594.1	1489.6	1406.2	1350.9	1291.7	1214.5	1138.9	1068.7
42.5°	2010.8	1816.6	1646.5	1523.0	1417.9	1337.6	1281.7	1229.9	1165.2	1094.0	1018.8
45°	1927.7	1723.5	1545.0	1412.5	1306.5	1227.7	1175.5	1129.5	1080.4	1014.9	949.4
47.5°	1819.5	1626.4	1439.6	1294.9	1191.1	1118.0	1067.3	1031.0	995.9	940.2	876.6
50°	1732.9	1546.6	1364.1	1223.8	1113.1	1043.8	996.2	967.4	935.4	884.7	831.7
52.5°	1630.6	1464.2	1285.6	1142.1	1037.7	972.7	927.0	898.2	871.8	830.5	780.0
55°	1469.4	1323.6	1159.9	1029.7	933.9	868.4	824.7	797.4	781.9	746.8	707.0
57.5°	1283.4	1178.9	1034.6	909.1	824.3	759.6	727.6	704.4	686.8	662.0	633.9
60°	1153.7	1080.4	951.0	831.7	753.8	692.2	663.4	643.9	627.5	606.5	584.6
62.5°	1022.1	968.8	856.2	753.8	682.1	630.5	603.5	585.9	567.0	552.8	531.6
65°	845.8	798.2	720.3	640.0	573.7	532.4	512.9	497.3	485.6	470.0	455.2
67.5°	657.9	638.6	584.8	529.4	481.9	445.1	428.3	417.4	403.3	394.0	383.8
70°	542.5	533.2	495.0	458.4	413.9	389.0	373.4	368.7	351.6	342.2	335.2
72.5°	440.3	435.9	413.9	388.5	357.2	335.3	321.0	315.7	304.8	297.3	292.8
75°	301.7	303.2	299.3	283.0	271.3	257.2	244.8	241.6	233.9	227.6	223.7
77.5°	190.8	198.8	199.1	198.3	193.6	185.1	179.9	177.6	169.9	167.6	166.7
80°	131.0	139.5	147.3	146.5	145.0	142.7	138.8	136.4	132.5	130.2	128.6
82.5°	87.3	95.3	101.8	106.0	105.7	103.4	100.7	99.6	98.8	97.1	96.8
85°	41.3	42.9	45.2	50.7	54.6	55.3	54.6	53.8	51.4	52.2	53.0
87.5°	17.4	16.9	17.3	16.8	15.7	18.4	19.8	20.2	19.2	18.4	17.6
90°	15.1	12.8	11.6	9.3	7.0	4.6	2.3	1.2	2.3	4.6	7.0
92.5°	265.2	158.7	95.3	61.4	41.4	27.0	17.2	14.2	17.2	27.0	41.4
95°	519.4	263.8	139.4	87.1	61.6	48.8	39.5	38.3	39.5	48.8	61.6
97.5°	414.6	227.3	145.0	107.4	84.4	71.6	65.1	63.7	65.1	71.6	84.4
100°	376.5	225.4	158.0	123.2	101.1	88.3	83.7	81.3	83.7	88.3	101.1
102.5°	360.7	233.8	173.8	139.9	119.7	106.0	102.3	100.9	102.3	106.0	119.7
105°	354.4	251.0	199.9	167.3	148.7	137.1	131.3	131.3	131.3	137.1	148.7
107.5°	365.1	276.5	227.0	197.8	178.5	168.9	163.4	161.0	163.4	168.9	178.5
110°	375.3	295.1	247.5	217.3	199.9	189.4	184.8	182.4	184.8	189.4	199.9



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	388.3	312.8	267.0	237.7	220.3	209.8	206.1	203.8	206.1	209.8	220.3
115°	407.8	340.5	297.5	268.4	251.0	240.5	237.0	234.7	237.0	240.5	251.0
117.5°	430.2	368.8	328.1	300.0	280.3	269.8	266.1	262.6	266.1	269.8	280.3
120°	445.0	389.3	348.6	319.5	299.8	289.3	284.7	281.2	284.7	289.3	299.8
122.5°	461.8	408.8	368.1	339.1	317.4	307.0	303.3	300.7	303.3	307.0	317.4
125°	484.5	434.6	396.2	366.0	343.9	333.5	327.7	325.3	327.7	333.5	343.9
127.5°	505.5	459.4	422.5	392.3	368.8	355.6	348.1	344.6	348.1	355.6	368.8
130°	519.4	475.2	439.2	409.0	384.6	369.5	360.2	356.7	360.2	369.5	384.6
132.5°	531.5	490.1	454.1	423.9	398.6	381.6	370.4	366.0	370.4	381.6	398.6
135°	548.4	510.1	474.1	442.7	418.3	399.7	385.8	381.1	385.8	399.7	418.3
137.5°	561.0	524.3	491.5	459.2	435.3	416.7	403.7	400.2	403.7	416.7	435.3
140°	569.4	534.5	500.8	469.4	447.4	428.8	414.8	411.3	414.8	428.8	447.4
142.5°	574.0	541.0	509.2	479.7	458.5	439.9	426.9	424.3	426.9	439.9	458.5
145°	581.0	551.9	521.7	495.0	474.1	457.8	446.2	443.9	446.2	457.8	474.1
147.5°	585.2	558.9	532.4	508.9	490.8	475.7	465.7	464.3	465.7	475.7	490.8
150°	588.0	563.5	538.0	518.2	502.0	486.9	478.7	476.4	478.7	486.9	502.0
152.5°	589.8	568.2	544.5	526.6	511.3	498.0	490.8	489.4	490.8	498.0	511.3
155°	591.4	572.8	553.1	536.8	525.2	513.6	506.6	506.6	506.6	513.6	525.2
157.5°	592.6	576.8	559.8	547.5	537.3	527.3	521.7	522.0	521.7	527.3	537.3
160°	592.6	578.7	563.5	553.1	543.8	535.7	531.0	532.2	531.0	535.7	543.8
162.5°	591.7	580.5	567.3	558.7	551.2	544.0	539.4	540.5	539.4	544.0	551.2
165°	590.3	581.0	571.7	564.7	560.1	554.3	550.8	553.1	550.8	554.3	560.1
167.5°	587.5	581.0	573.3	568.9	565.6	562.4	560.3	561.5	560.3	562.4	565.6
170°	585.6	581.0	575.2	571.7	569.4	567.0	565.9	567.0	565.9	567.0	569.4
172.5°	583.8	580.0	575.2	573.5	572.1	569.8	568.7	570.8	568.7	569.8	572.1
175°	581.0	578.7	575.2	575.2	575.2	574.0	572.8	575.2	572.8	574.0	575.2
177.5°	578.2	577.3	575.4	575.4	576.3	575.4	575.4	577.3	575.4	575.4	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1867.1	1858.4	1852.1	1839.6	1830.9	1827.2	1820.3	1818.4	1825.3	1820.3	1819.7
5°	1811.6	1789.0	1771.1	1753.1	1733.6	1721.2	1702.5	1699.3	1694.7	1687.6	1686.1
7.5°	1745.0	1715.6	1692.5	1662.9	1637.1	1616.4	1593.0	1581.9	1575.9	1566.8	1554.7
10°	1700.1	1665.0	1633.9	1604.2	1572.3	1546.6	1523.2	1505.2	1493.5	1482.6	1478.0
12.5°	1655.8	1620.1	1580.2	1544.4	1508.7	1479.8	1453.9	1442.3	1429.3	1416.5	1405.6
15°	1587.1	1539.5	1495.9	1454.6	1424.2	1393.0	1368.0	1350.9	1331.4	1326.0	1304.9
17.5°	1514.1	1467.5	1416.4	1372.9	1337.6	1303.3	1275.9	1256.4	1241.8	1221.7	1212.0
20°	1468.6	1413.3	1363.4	1323.6	1284.6	1244.1	1216.0	1199.7	1185.6	1169.3	1161.5
22.5°	1420.0	1365.9	1314.7	1268.1	1228.5	1188.6	1168.6	1151.7	1135.7	1120.6	1110.3
25°	1348.6	1294.0	1240.2	1191.9	1150.6	1121.7	1098.3	1078.8	1070.3	1055.5	1044.5
27.5°	1277.9	1219.9	1164.1	1115.9	1083.5	1055.0	1035.8	1020.4	1004.9	992.0	982.5
30°	1232.4	1173.2	1112.4	1074.2	1039.9	1012.6	991.5	976.7	965.0	953.3	946.3
32.5°	1186.9	1125.8	1071.8	1030.5	998.1	974.5	952.9	938.7	926.4	913.4	905.2
35°	1113.9	1051.6	1007.9	967.4	935.4	913.6	898.8	878.5	868.4	859.0	850.4
37.5°	1046.1	988.1	940.9	905.3	877.6	855.9	836.7	825.8	813.3	804.9	797.8
40°	996.2	943.2	900.3	862.9	842.7	818.5	800.6	786.5	777.2	766.3	758.5
42.5°	951.3	902.1	860.4	826.8	801.5	781.1	763.8	749.7	737.9	730.1	723.5
45°	887.9	838.8	798.2	767.0	743.7	724.2	706.2	699.2	683.6	674.3	671.2
47.5°	822.2	778.3	739.1	710.4	686.4	668.0	651.2	636.9	628.3	619.1	614.1
50°	778.0	735.9	699.2	671.2	647.8	627.5	611.9	602.6	590.9	582.3	576.1
52.5°	733.7	694.7	658.1	631.2	611.0	590.7	573.3	563.9	552.8	547.4	543.0
55°	670.4	629.1	597.9	571.4	550.3	531.6	515.3	505.9	498.9	493.4	491.9
57.5°	598.7	565.9	536.9	513.1	491.2	473.6	459.3	450.4	444.2	443.4	438.7
60°	551.9	522.3	495.8	470.0	451.3	435.0	422.5	412.4	406.1	405.3	403.8
62.5°	505.1	476.7	452.1	429.5	412.7	396.9	385.1	373.7	370.0	366.1	362.6
65°	435.7	410.0	389.8	371.8	353.9	340.6	329.0	321.9	313.4	308.7	300.1
67.5°	367.6	347.7	328.2	313.1	299.0	286.4	276.7	266.3	260.5	256.8	250.5
70°	322.7	307.1	287.6	271.3	260.4	250.2	242.4	230.7	226.8	223.7	220.6
72.5°	280.3	266.6	250.2	237.0	226.1	216.5	207.5	202.0	198.2	195.0	193.2
75°	220.6	207.4	193.3	184.0	176.2	168.4	163.7	159.8	158.2	157.5	154.3
77.5°	162.0	155.0	143.7	136.3	131.1	128.0	123.8	121.8	121.6	118.2	117.1
80°	123.9	120.0	110.7	107.6	103.7	100.6	98.2	94.3	90.4	88.9	86.5
82.5°	92.1	88.2	84.5	79.5	76.2	74.4	72.0	70.6	71.1	68.9	67.8
85°	49.1	45.2	43.7	42.9	41.3	42.9	42.1	41.3	40.5	39.8	40.5
87.5°	17.4	17.9	17.5	19.2	17.6	18.7	18.9	18.5	18.8	19.0	18.8
90°	9.3	11.6	12.8	15.1	16.3	18.6	19.8	20.9	22.1	23.2	25.6
92.5°	61.4	95.3	158.7	265.2	380.7	374.6	303.3	205.9	149.4	112.5	95.3
95°	87.1	139.4	263.8	519.4	840.1	1029.5	1007.4	835.4	658.8	515.9	418.3
97.5°	107.4	145.0	227.3	414.6	750.2	1099.4	1274.7	1244.2	1120.4	981.2	845.4
100°	123.2	158.0	225.4	376.5	669.3	1049.2	1339.7	1429.2	1372.3	1252.6	1131.7
102.5°	139.9	173.8	233.8	360.7	607.9	960.9	1300.7	1491.5	1526.6	1469.2	1387.4
105°	167.3	199.9	251.0	354.4	548.4	842.4	1175.9	1454.8	1614.0	1665.1	1652.3
107.5°	197.8	227.0	276.5	365.1	523.3	760.8	1048.6	1323.7	1536.1	1667.4	1728.1
110°	217.3	247.5	295.1	375.3	515.9	722.7	976.0	1227.0	1447.8	1611.6	1710.4



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	237.7	267.0	312.8	388.3	515.9	700.4	922.1	1150.8	1360.4	1526.1	1642.5
115°	268.4	297.5	340.5	407.8	519.4	676.3	863.3	1055.1	1235.2	1394.3	1521.0
117.5°	300.0	328.1	368.8	430.2	527.1	664.4	828.2	993.2	1148.5	1285.6	1401.8
120°	319.5	348.6	389.3	445.0	534.5	658.8	808.7	959.8	1099.2	1227.0	1329.3
122.5°	339.1	368.1	408.8	461.8	541.0	654.2	792.0	934.7	1063.9	1177.8	1273.5
125°	366.0	396.2	434.6	484.5	551.9	648.4	769.2	898.2	1016.7	1117.8	1201.5
127.5°	392.3	422.5	459.4	505.5	564.2	645.6	748.3	861.0	971.6	1066.0	1144.3
130°	409.0	439.2	475.2	519.4	571.7	643.7	734.4	837.8	940.0	1030.7	1106.2
132.5°	423.9	454.1	490.1	531.5	580.0	643.7	723.2	814.5	910.3	992.5	1065.3
135°	442.7	474.1	510.1	548.4	591.4	643.7	710.0	784.3	864.5	938.9	1005.1
137.5°	459.2	491.5	524.3	561.0	601.9	645.1	698.1	758.8	823.6	885.4	941.7
140°	469.4	500.8	534.5	569.4	606.5	646.0	692.5	744.8	799.4	852.9	901.7
142.5°	479.7	509.2	541.0	574.0	609.3	647.0	687.9	732.7	779.0	825.0	867.3
145°	495.0	521.7	551.9	581.0	612.4	646.0	680.9	716.9	752.9	789.0	820.3
147.5°	508.9	532.4	558.9	585.2	613.5	643.0	673.7	702.1	731.3	759.0	782.7
150°	518.2	538.0	563.5	588.0	613.5	640.2	668.1	693.7	719.3	741.3	762.2
152.5°	526.6	544.5	568.2	589.8	612.6	636.5	661.6	684.4	707.2	727.4	743.7
155°	536.8	553.1	572.8	591.4	610.0	629.8	650.7	670.4	689.0	705.3	718.1
157.5°	547.5	559.8	576.8	592.6	607.0	622.8	640.5	656.5	671.8	684.4	694.4
160°	553.1	563.5	578.7	592.6	604.2	618.2	632.1	647.2	658.8	670.4	678.6
162.5°	558.7	567.3	580.5	591.7	601.4	612.6	624.7	637.0	647.7	657.4	664.6
165°	564.7	571.7	581.0	590.3	597.2	604.2	613.5	622.8	630.9	637.9	643.7
167.5°	568.9	573.3	581.0	587.5	590.7	596.1	602.6	609.3	614.7	620.0	624.2
170°	571.7	575.2	581.0	585.6	588.0	591.4	596.1	601.9	605.4	608.9	611.2
172.5°	573.5	575.2	580.0	583.8	584.2	585.9	589.6	593.5	597.0	599.6	601.0
175°	575.2	575.2	578.7	581.0	579.8	579.8	581.0	584.5	584.5	586.8	586.8
177.5°	575.4	575.4	577.3	578.2	576.3	576.3	577.3	578.2	579.1	579.1	579.1
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1819.1	1812.2	1810.3	1812.8	1810.3	1812.2	1819.1	1819.7	1820.3	1825.3	1818.4
5°	1678.3	1670.5	1674.4	1672.8	1674.4	1670.5	1678.3	1686.1	1687.6	1694.7	1699.3
7.5°	1554.5	1544.8	1534.5	1537.8	1534.5	1544.8	1554.5	1554.7	1566.8	1575.9	1581.9
10°	1467.8	1460.0	1455.3	1459.2	1455.3	1460.0	1467.8	1478.0	1482.6	1493.5	1505.2
12.5°	1394.9	1390.2	1386.1	1384.4	1386.1	1390.2	1394.9	1405.6	1416.5	1429.3	1442.3
15°	1295.5	1286.2	1282.3	1272.2	1282.3	1286.2	1295.5	1304.9	1326.0	1331.4	1350.9
17.5°	1204.0	1200.9	1190.8	1186.4	1190.8	1200.9	1204.0	1212.0	1221.7	1241.8	1256.4
20°	1149.8	1146.7	1136.5	1142.8	1136.5	1146.7	1149.8	1161.5	1169.3	1185.6	1199.7
22.5°	1104.9	1098.0	1094.7	1092.9	1094.7	1098.0	1104.9	1110.3	1120.6	1135.7	1151.7
25°	1041.4	1031.3	1027.4	1022.7	1027.4	1031.3	1041.4	1044.5	1055.5	1070.3	1078.8
27.5°	978.1	972.7	967.5	966.3	967.5	972.7	978.1	982.5	992.0	1004.9	1020.4
30°	937.0	931.5	927.6	927.6	927.6	931.5	937.0	946.3	953.3	965.0	976.7
32.5°	900.2	896.0	892.1	891.5	892.1	896.0	900.2	905.2	913.4	926.4	938.7
35°	846.6	840.3	838.8	834.1	838.8	840.3	846.6	850.4	859.0	868.4	878.5
37.5°	790.9	785.7	785.6	785.1	785.6	785.7	790.9	797.8	804.9	813.3	825.8
40°	755.3	751.4	750.7	745.2	750.7	751.4	755.3	758.5	766.3	777.2	786.5
42.5°	717.3	715.3	712.6	710.3	712.6	715.3	717.3	723.5	730.1	737.9	749.7
45°	665.7	660.2	660.2	656.3	660.2	660.2	665.7	671.2	674.3	683.6	699.2
47.5°	612.4	608.2	608.6	604.6	608.6	608.2	612.4	614.1	619.1	628.3	636.9
50°	576.8	574.5	573.7	572.2	573.7	574.5	576.8	576.1	582.3	590.9	602.6
52.5°	541.3	540.2	543.2	539.7	543.2	540.2	541.3	543.0	547.4	552.8	563.9
55°	493.4	491.1	495.8	491.1	495.8	491.1	493.4	491.9	493.4	498.9	505.9
57.5°	438.4	436.2	440.4	438.1	440.4	436.2	438.4	438.7	443.4	444.2	450.4
60°	402.2	397.6	399.9	400.7	399.9	397.6	402.2	403.8	405.3	406.1	412.4
62.5°	359.2	356.4	358.1	354.5	358.1	356.4	359.2	362.6	366.1	370.0	373.7
65°	298.6	296.2	293.1	291.5	293.1	296.2	298.6	300.1	308.7	313.4	321.9
67.5°	250.8	245.2	245.1	246.3	245.1	245.2	250.8	250.5	256.8	260.5	266.3
70°	215.9	215.9	215.1	215.1	215.1	215.9	215.9	220.6	223.7	226.8	230.7
72.5°	191.6	191.0	189.6	189.0	189.6	191.0	191.6	193.2	195.0	198.2	202.0
75°	154.3	155.1	153.6	152.8	153.6	155.1	154.3	154.3	157.5	158.2	159.8
77.5°	114.0	110.7	112.4	110.7	112.4	110.7	114.0	117.1	118.2	121.6	121.8
80°	86.5	85.7	88.1	85.7	88.1	85.7	86.5	86.5	88.9	90.4	94.3
82.5°	68.4	67.7	68.8	67.0	68.8	67.7	68.4	67.8	68.9	71.1	70.6
85°	41.3	40.5	39.8	40.5	39.8	40.5	41.3	40.5	39.8	40.5	41.3
87.5°	19.5	18.8	19.1	19.1	19.1	18.8	19.5	18.8	19.0	18.8	18.5
90°	25.6	25.6	26.7	26.7	26.7	25.6	25.6	25.6	23.2	22.1	20.9
92.5°	80.4	77.6	76.0	74.1	76.0	77.6	80.4	95.3	112.5	149.4	205.9
95°	335.8	300.9	291.7	273.1	291.7	300.9	335.8	418.3	515.9	658.8	835.4
97.5°	773.6	708.6	674.9	660.0	674.9	708.6	773.6	845.4	981.2	1120.4	1244.2
100°	1051.6	967.9	924.9	906.3	924.9	967.9	1051.6	1131.7	1252.6	1372.3	1429.2
102.5°	1301.6	1242.1	1195.4	1181.5	1195.4	1242.1	1301.6	1387.4	1469.2	1526.6	1491.5
105°	1615.1	1576.8	1553.5	1539.6	1553.5	1576.8	1615.1	1652.3	1665.1	1614.0	1454.8
107.5°	1746.9	1746.7	1739.0	1729.7	1739.0	1746.7	1746.9	1728.1	1667.4	1536.1	1323.7
110°	1762.7	1784.8	1792.9	1792.9	1792.9	1784.8	1762.7	1710.4	1611.6	1447.8	1227.0



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1719.0	1756.9	1777.1	1785.5	1777.1	1756.9	1719.0	1642.5	1526.1	1360.4	1150.8
115°	1611.6	1667.4	1699.9	1715.0	1699.9	1667.4	1611.6	1521.0	1394.3	1235.2	1055.1
117.5°	1492.4	1550.1	1582.4	1591.6	1582.4	1550.1	1492.4	1401.8	1285.6	1148.5	993.2
120°	1415.3	1471.0	1502.4	1511.7	1502.4	1471.0	1415.3	1329.3	1227.0	1099.2	959.8
122.5°	1350.2	1401.3	1432.7	1441.1	1432.7	1401.3	1350.2	1273.5	1177.8	1063.9	934.7
125°	1266.5	1314.2	1339.7	1351.4	1339.7	1314.2	1266.5	1201.5	1117.8	1016.7	898.2
127.5°	1203.3	1245.4	1269.6	1274.7	1269.6	1245.4	1203.3	1144.3	1066.0	971.6	861.0
130°	1164.3	1202.6	1225.9	1232.8	1225.9	1202.6	1164.3	1106.2	1030.7	940.0	837.8
132.5°	1123.4	1161.7	1183.1	1191.0	1183.1	1161.7	1123.4	1065.3	992.5	910.3	814.5
135°	1056.2	1094.6	1115.5	1122.5	1115.5	1094.6	1056.2	1005.1	938.9	864.5	784.3
137.5°	987.4	1022.3	1041.6	1049.2	1041.6	1022.3	987.4	941.7	885.4	823.6	758.8
140°	944.7	974.9	992.3	998.1	992.3	974.9	944.7	901.7	852.9	799.4	744.8
142.5°	903.8	929.3	945.8	950.7	945.8	929.3	903.8	867.3	825.0	779.0	732.7
145°	848.2	868.0	880.8	885.4	880.8	868.0	848.2	820.3	789.0	752.9	716.9
147.5°	804.8	820.6	828.0	830.1	828.0	820.6	804.8	782.7	759.0	731.3	702.1
150°	779.7	793.6	798.3	799.4	798.3	793.6	779.7	762.2	741.3	719.3	693.7
152.5°	758.3	769.4	774.1	775.3	774.1	769.4	758.3	743.7	727.4	707.2	684.4
155°	729.7	737.8	741.3	742.5	741.3	737.8	729.7	718.1	705.3	689.0	670.4
157.5°	703.4	710.2	713.4	713.2	713.4	710.2	703.4	694.4	684.4	671.8	656.5
160°	686.7	692.5	694.9	693.7	694.9	692.5	686.7	678.6	670.4	658.8	647.2
162.5°	670.9	675.8	676.3	676.0	676.3	675.8	670.9	664.6	657.4	647.7	637.0
165°	648.4	650.7	650.7	650.7	650.7	650.7	648.4	643.7	637.9	630.9	622.8
167.5°	626.5	628.6	627.7	627.5	627.7	628.6	626.5	624.2	620.0	614.7	609.3
170°	613.5	614.7	614.7	613.5	614.7	614.7	613.5	611.2	608.9	605.4	601.9
172.5°	601.4	603.5	601.7	600.5	601.7	603.5	601.4	601.0	599.6	597.0	593.5
175°	586.8	588.0	585.6	584.5	585.6	588.0	586.8	586.8	586.8	584.5	584.5
177.5°	578.2	579.1	576.3	576.3	576.3	579.1	578.2	579.1	579.1	579.1	578.2
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1820.3	1827.2	1830.9	1839.6	1852.1	1858.4	1867.1	1873.3	1882.1	1892.7	1901.4
5°	1702.5	1721.2	1733.6	1753.1	1771.1	1789.0	1811.6	1828.0	1849.8	1874.7	1894.2
7.5°	1593.0	1616.4	1637.1	1662.9	1692.5	1715.6	1745.0	1775.1	1809.2	1844.6	1878.0
10°	1523.2	1546.6	1572.3	1604.2	1633.9	1665.0	1700.1	1735.2	1778.1	1817.8	1863.0
12.5°	1453.9	1479.8	1508.7	1544.4	1580.2	1620.1	1655.8	1695.3	1741.3	1792.9	1841.2
15°	1368.0	1393.0	1424.2	1454.6	1495.9	1539.5	1587.1	1639.3	1690.8	1748.4	1808.5
17.5°	1275.9	1303.3	1337.6	1372.9	1416.4	1467.5	1514.1	1571.3	1629.2	1696.4	1767.0
20°	1216.0	1244.1	1284.6	1323.6	1363.4	1413.3	1468.6	1527.1	1588.6	1659.6	1738.3
22.5°	1168.6	1188.6	1228.5	1268.1	1314.7	1365.9	1420.0	1480.9	1548.1	1621.5	1704.0
25°	1098.3	1121.7	1150.6	1191.9	1240.2	1294.0	1348.6	1413.3	1486.5	1561.4	1649.4
27.5°	1035.8	1055.0	1083.5	1115.9	1164.1	1219.9	1277.9	1345.4	1420.6	1496.8	1589.4
30°	991.5	1012.6	1039.9	1074.2	1112.4	1173.2	1232.4	1298.7	1375.1	1453.8	1548.9
32.5°	952.9	974.5	998.1	1030.5	1071.8	1125.8	1186.9	1251.9	1329.5	1410.8	1503.4
35°	898.8	913.6	935.4	967.4	1007.9	1051.6	1113.9	1182.5	1258.1	1342.3	1435.1
37.5°	836.7	855.9	877.6	905.3	940.9	988.1	1046.1	1115.5	1185.6	1266.2	1350.9
40°	800.6	818.5	842.7	862.9	900.3	943.2	996.2	1068.7	1138.9	1214.5	1291.7
42.5°	763.8	781.1	801.5	826.8	860.4	902.1	951.3	1018.8	1094.0	1165.2	1229.9
45°	706.2	724.2	743.7	767.0	798.2	838.8	887.9	949.4	1014.9	1080.4	1129.5
47.5°	651.2	668.0	686.4	710.4	739.1	778.3	822.2	876.6	940.2	995.9	1031.0
50°	611.9	627.5	647.8	671.2	699.2	735.9	778.0	831.7	884.7	935.4	967.4
52.5°	573.3	590.7	611.0	631.2	658.1	694.7	733.7	780.0	830.5	871.8	898.2
55°	515.3	531.6	550.3	571.4	597.9	629.1	670.4	707.0	746.8	781.9	797.4
57.5°	459.3	473.6	491.2	513.1	536.9	565.9	598.7	633.9	662.0	686.8	704.4
60°	422.5	435.0	451.3	470.0	495.8	522.3	551.9	584.6	606.5	627.5	643.9
62.5°	385.1	396.9	412.7	429.5	452.1	476.7	505.1	531.6	552.8	567.0	585.9
65°	329.0	340.6	353.9	371.8	389.8	410.0	435.7	455.2	470.0	485.6	497.3
67.5°	276.7	286.4	299.0	313.1	328.2	347.7	367.6	383.8	394.0	403.3	417.4
70°	242.4	250.2	260.4	271.3	287.6	307.1	322.7	335.2	342.2	351.6	368.7
72.5°	207.5	216.5	226.1	237.0	250.2	266.6	280.3	292.8	297.3	304.8	315.7
75°	163.7	168.4	176.2	184.0	193.3	207.4	220.6	223.7	227.6	233.9	241.6
77.5°	123.8	128.0	131.1	136.3	143.7	155.0	162.0	166.7	167.6	169.9	177.6
80°	98.2	100.6	103.7	107.6	110.7	120.0	123.9	128.6	130.2	132.5	136.4
82.5°	72.0	74.4	76.2	79.5	84.5	88.2	92.1	96.8	97.1	98.8	99.6
85°	42.1	42.9	41.3	42.9	43.7	45.2	49.1	53.0	52.2	51.4	53.8
87.5°	18.9	18.7	17.6	19.2	17.5	17.9	17.4	17.6	18.4	19.2	20.2
90°	19.8	18.6	16.3	15.1	12.8	11.6	9.3	7.0	4.6	2.3	1.2
92.5°	303.3	374.6	380.7	265.2	158.7	95.3	61.4	41.4	27.0	17.2	14.2
95°	1007.4	1029.5	840.1	519.4	263.8	139.4	87.1	61.6	48.8	39.5	38.3
97.5°	1274.7	1099.4	750.2	414.6	227.3	145.0	107.4	84.4	71.6	65.1	63.7
100°	1339.7	1049.2	669.3	376.5	225.4	158.0	123.2	101.1	88.3	83.7	81.3
102.5°	1300.7	960.9	607.9	360.7	233.8	173.8	139.9	119.7	106.0	102.3	100.9
105°	1175.9	842.4	548.4	354.4	251.0	199.9	167.3	148.7	137.1	131.3	131.3
107.5°	1048.6	760.8	523.3	365.1	276.5	227.0	197.8	178.5	168.9	163.4	161.0
110°	976.0	722.7	515.9	375.3	295.1	247.5	217.3	199.9	189.4	184.8	182.4



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	922.1	700.4	515.9	388.3	312.8	267.0	237.7	220.3	209.8	206.1	203.8
115°	863.3	676.3	519.4	407.8	340.5	297.5	268.4	251.0	240.5	237.0	234.7
117.5°	828.2	664.4	527.1	430.2	368.8	328.1	300.0	280.3	269.8	266.1	262.6
120°	808.7	658.8	534.5	445.0	389.3	348.6	319.5	299.8	289.3	284.7	281.2
122.5°	792.0	654.2	541.0	461.8	408.8	368.1	339.1	317.4	307.0	303.3	300.7
125°	769.2	648.4	551.9	484.5	434.6	396.2	366.0	343.9	333.5	327.7	325.3
127.5°	748.3	645.6	564.2	505.5	459.4	422.5	392.3	368.8	355.6	348.1	344.6
130°	734.4	643.7	571.7	519.4	475.2	439.2	409.0	384.6	369.5	360.2	356.7
132.5°	723.2	643.7	580.0	531.5	490.1	454.1	423.9	398.6	381.6	370.4	366.0
135°	710.0	643.7	591.4	548.4	510.1	474.1	442.7	418.3	399.7	385.8	381.1
137.5°	698.1	645.1	601.9	561.0	524.3	491.5	459.2	435.3	416.7	403.7	400.2
140°	692.5	646.0	606.5	569.4	534.5	500.8	469.4	447.4	428.8	414.8	411.3
142.5°	687.9	647.0	609.3	574.0	541.0	509.2	479.7	458.5	439.9	426.9	424.3
145°	680.9	646.0	612.4	581.0	551.9	521.7	495.0	474.1	457.8	446.2	443.9
147.5°	673.7	643.0	613.5	585.2	558.9	532.4	508.9	490.8	475.7	465.7	464.3
150°	668.1	640.2	613.5	588.0	563.5	538.0	518.2	502.0	486.9	478.7	476.4
152.5°	661.6	636.5	612.6	589.8	568.2	544.5	526.6	511.3	498.0	490.8	489.4
155°	650.7	629.8	610.0	591.4	572.8	553.1	536.8	525.2	513.6	506.6	506.6
157.5°	640.5	622.8	607.0	592.6	576.8	559.8	547.5	537.3	527.3	521.7	522.0
160°	632.1	618.2	604.2	592.6	578.7	563.5	553.1	543.8	535.7	531.0	532.2
162.5°	624.7	612.6	601.4	591.7	580.5	567.3	558.7	551.2	544.0	539.4	540.5
165°	613.5	604.2	597.2	590.3	581.0	571.7	564.7	560.1	554.3	550.8	553.1
167.5°	602.6	596.1	590.7	587.5	581.0	573.3	568.9	565.6	562.4	560.3	561.5
170°	596.1	591.4	588.0	585.6	581.0	575.2	571.7	569.4	567.0	565.9	567.0
172.5°	589.6	585.9	584.2	583.8	580.0	575.2	573.5	572.1	569.8	568.7	570.8
175°	581.0	579.8	579.8	581.0	578.7	575.2	575.2	575.2	574.0	572.8	575.2
177.5°	577.3	576.3	576.3	578.2	577.3	575.4	575.4	576.3	575.4	575.4	577.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1908.2	1913.9	1922.0	1931.3	1938.8	1946.9	1951.3	1951.3	1955.0	1963.1	1973.7
5°	1913.7	1934.0	1953.5	1978.4	1997.9	2020.5	2037.6	2054.0	2068.8	2087.5	2107.0
7.5°	1912.1	1945.8	1980.9	2020.2	2063.5	2098.0	2133.4	2161.1	2188.6	2224.4	2252.6
10°	1905.9	1949.6	1997.1	2047.0	2101.6	2149.1	2192.0	2231.0	2268.4	2307.4	2342.4
12.5°	1894.7	1950.2	2008.3	2068.2	2137.1	2191.5	2246.9	2288.3	2332.0	2374.7	2417.9
15°	1877.8	1943.3	2013.5	2096.9	2181.1	2241.9	2296.4	2350.2	2390.8	2439.1	2480.4
17.5°	1843.1	1927.4	2015.7	2106.9	2187.8	2258.4	2315.6	2366.8	2409.9	2463.1	2519.2
20°	1822.5	1913.7	2005.7	2103.1	2180.3	2252.8	2308.1	2361.1	2414.9	2484.3	2552.9
22.5°	1793.8	1891.3	1988.8	2081.3	2162.8	2232.8	2290.1	2354.9	2425.5	2504.3	2587.2
25°	1748.4	1849.0	1945.7	2033.7	2113.3	2185.0	2262.9	2350.2	2436.0	2539.7	2658.9
27.5°	1690.9	1787.9	1874.1	1967.2	2046.2	2137.4	2234.7	2329.3	2453.0	2595.6	2744.5
30°	1647.9	1739.9	1821.7	1909.8	1999.4	2100.0	2209.1	2320.6	2467.9	2635.5	2812.5
32.5°	1598.0	1681.3	1762.5	1847.4	1950.8	2061.3	2177.3	2313.7	2489.8	2680.4	2863.6
35°	1511.5	1586.3	1665.0	1759.4	1869.3	1989.3	2137.4	2303.5	2516.3	2721.3	2885.8
37.5°	1420.7	1479.8	1558.9	1658.3	1778.1	1917.0	2085.0	2286.8	2505.4	2689.3	2759.3
40°	1350.9	1406.2	1489.6	1594.1	1712.6	1864.6	2053.2	2260.6	2480.4	2608.2	2602.8
42.5°	1281.7	1337.6	1417.9	1523.0	1646.5	1816.6	2010.8	2226.3	2411.8	2460.5	2359.0
45°	1175.5	1227.7	1306.5	1412.5	1545.0	1723.5	1927.7	2134.3	2252.8	2174.1	1972.9
47.5°	1067.3	1118.0	1191.1	1294.9	1439.6	1626.4	1819.5	1989.0	2005.7	1836.5	1595.3
50°	996.2	1043.8	1113.1	1223.8	1364.1	1546.6	1732.9	1866.2	1824.8	1618.3	1369.6
52.5°	927.0	972.7	1037.7	1142.1	1285.6	1464.2	1630.6	1735.2	1639.6	1420.0	1196.2
55°	824.7	868.4	933.9	1029.7	1159.9	1323.6	1469.4	1507.6	1367.3	1145.9	965.0
57.5°	727.6	759.6	824.3	909.1	1034.6	1178.9	1283.4	1276.5	1121.7	922.3	792.6
60°	663.4	692.2	753.8	831.7	951.0	1080.4	1153.7	1122.5	965.8	801.3	676.6
62.5°	603.5	630.5	682.1	753.8	856.2	968.8	1022.1	979.1	831.1	686.6	587.4
65°	512.9	532.4	573.7	640.0	720.3	798.2	845.8	782.6	651.7	542.5	467.7
67.5°	428.3	445.1	481.9	529.4	584.8	638.6	657.9	598.7	496.9	423.3	370.6
70°	373.4	389.0	413.9	458.4	495.0	533.2	542.5	489.5	404.6	348.4	315.7
72.5°	321.0	335.3	357.2	388.5	413.9	435.9	440.3	391.0	326.0	287.3	262.1
75°	244.8	257.2	271.3	283.0	299.3	303.2	301.7	263.5	228.4	202.7	188.6
77.5°	179.9	185.1	193.6	198.3	199.1	198.8	190.8	166.7	148.6	138.0	132.2
80°	138.8	142.7	145.0	146.5	147.3	139.5	131.0	116.1	109.9	103.7	96.7
82.5°	100.7	103.4	105.7	106.0	101.8	95.3	87.3	80.0	75.6	72.5	69.8
85°	54.6	55.3	54.6	50.7	45.2	42.9	41.3	39.8	39.0	38.2	38.2
87.5°	19.8	18.4	15.7	16.8	17.3	16.9	17.4	17.0	16.8	17.0	17.3
90°	2.3	4.6	7.0	9.3	11.6	12.8	15.1	16.3	18.6	19.8	20.9
92.5°	17.2	27.0	41.4	61.4	95.3	158.7	265.2	380.7	374.6	303.3	205.9
95°	39.5	48.8	61.6	87.1	139.4	263.8	519.4	840.1	1029.5	1007.4	835.4
97.5°	65.1	71.6	84.4	107.4	145.0	227.3	414.6	750.2	1099.4	1274.7	1244.2
100°	83.7	88.3	101.1	123.2	158.0	225.4	376.5	669.3	1049.2	1339.7	1429.2
102.5°	102.3	106.0	119.7	139.9	173.8	233.8	360.7	607.9	960.9	1300.7	1491.5
105°	131.3	137.1	148.7	167.3	199.9	251.0	354.4	548.4	842.4	1175.9	1454.8
107.5°	163.4	168.9	178.5	197.8	227.0	276.5	365.1	523.3	760.8	1048.6	1323.7
110°	184.8	189.4	199.9	217.3	247.5	295.1	375.3	515.9	722.7	976.0	1227.0



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	206.1	209.8	220.3	237.7	267.0	312.8	388.3	515.9	700.4	922.1	1150.8
115°	237.0	240.5	251.0	268.4	297.5	340.5	407.8	519.4	676.3	863.3	1055.1
117.5°	266.1	269.8	280.3	300.0	328.1	368.8	430.2	527.1	664.4	828.2	993.2
120°	284.7	289.3	299.8	319.5	348.6	389.3	445.0	534.5	658.8	808.7	959.8
122.5°	303.3	307.0	317.4	339.1	368.1	408.8	461.8	541.0	654.2	792.0	934.7
125°	327.7	333.5	343.9	366.0	396.2	434.6	484.5	551.9	648.4	769.2	898.2
127.5°	348.1	355.6	368.8	392.3	422.5	459.4	505.5	564.2	645.6	748.3	861.0
130°	360.2	369.5	384.6	409.0	439.2	475.2	519.4	571.7	643.7	734.4	837.8
132.5°	370.4	381.6	398.6	423.9	454.1	490.1	531.5	580.0	643.7	723.2	814.5
135°	385.8	399.7	418.3	442.7	474.1	510.1	548.4	591.4	643.7	710.0	784.3
137.5°	403.7	416.7	435.3	459.2	491.5	524.3	561.0	601.9	645.1	698.1	758.8
140°	414.8	428.8	447.4	469.4	500.8	534.5	569.4	606.5	646.0	692.5	744.8
142.5°	426.9	439.9	458.5	479.7	509.2	541.0	574.0	609.3	647.0	687.9	732.7
145°	446.2	457.8	474.1	495.0	521.7	551.9	581.0	612.4	646.0	680.9	716.9
147.5°	465.7	475.7	490.8	508.9	532.4	558.9	585.2	613.5	643.0	673.7	702.1
150°	478.7	486.9	502.0	518.2	538.0	563.5	588.0	613.5	640.2	668.1	693.7
152.5°	490.8	498.0	511.3	526.6	544.5	568.2	589.8	612.6	636.5	661.6	684.4
155°	506.6	513.6	525.2	536.8	553.1	572.8	591.4	610.0	629.8	650.7	670.4
157.5°	521.7	527.3	537.3	547.5	559.8	576.8	592.6	607.0	622.8	640.5	656.5
160°	531.0	535.7	543.8	553.1	563.5	578.7	592.6	604.2	618.2	632.1	647.2
162.5°	539.4	544.0	551.2	558.7	567.3	580.5	591.7	601.4	612.6	624.7	637.0
165°	550.8	554.3	560.1	564.7	571.7	581.0	590.3	597.2	604.2	613.5	622.8
167.5°	560.3	562.4	565.6	568.9	573.3	581.0	587.5	590.7	596.1	602.6	609.3
170°	565.9	567.0	569.4	571.7	575.2	581.0	585.6	588.0	591.4	596.1	601.9
172.5°	568.7	569.8	572.1	573.5	575.2	580.0	583.8	584.2	585.9	589.6	593.5
175°	572.8	574.0	575.2	575.2	575.2	578.7	581.0	579.8	579.8	581.0	584.5
177.5°	575.4	575.4	576.3	575.4	575.4	577.3	578.2	576.3	576.3	577.3	578.2
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1981.8	1981.8	1992.4	1991.8	1998.7	1996.2	1997.4
5°	2130.4	2143.7	2155.4	2163.1	2174.8	2178.0	2176.4
7.5°	2284.4	2313.9	2328.2	2347.9	2351.5	2361.8	2360.7
10°	2379.9	2408.7	2430.5	2447.7	2456.2	2467.2	2467.9
12.5°	2454.7	2479.2	2498.5	2514.4	2524.8	2528.3	2530.3
15°	2513.1	2540.4	2563.0	2585.6	2598.9	2609.0	2614.5
17.5°	2572.1	2614.2	2654.1	2684.8	2703.2	2718.8	2718.6
20°	2617.6	2665.9	2715.8	2750.9	2786.8	2802.3	2804.7
22.5°	2666.2	2740.1	2804.4	2858.8	2905.9	2922.1	2928.2
25°	2767.3	2863.9	2962.9	3039.3	3093.9	3125.8	3130.5
27.5°	2889.3	3020.1	3124.3	3194.8	3240.1	3263.8	3269.0
30°	2975.4	3096.2	3189.8	3242.8	3263.8	3266.9	3255.2
32.5°	3014.1	3104.3	3141.7	3138.6	3097.3	3069.9	3059.4
35°	2966.8	2948.1	2856.9	2747.8	2664.4	2611.4	2597.3
37.5°	2699.9	2538.6	2370.8	2205.9	2118.1	2073.5	1996.8
40°	2436.8	2206.8	2032.2	1893.4	1794.4	1714.9	1696.2
42.5°	2139.9	1902.5	1727.9	1609.1	1530.0	1475.5	1451.8
45°	1719.6	1515.4	1371.2	1280.0	1219.2	1179.4	1161.5
47.5°	1375.4	1217.3	1112.2	1044.7	998.4	963.8	954.1
50°	1186.4	1060.1	971.3	914.4	879.3	852.8	841.9
52.5°	1030.5	928.6	860.3	813.3	780.1	763.6	754.6
55°	850.4	762.4	713.3	675.8	657.1	643.9	637.6
57.5°	695.5	631.9	596.0	570.1	552.8	544.4	541.3
60°	608.8	558.9	526.2	505.9	494.2	483.3	480.2
62.5°	532.1	492.8	467.6	449.8	438.1	433.4	431.5
65°	428.7	403.0	384.3	373.4	364.0	362.5	361.7
67.5°	340.8	325.7	315.9	304.5	301.2	295.7	294.7
70°	291.5	281.4	269.7	265.8	261.9	256.5	257.2
72.5°	247.3	237.1	229.2	224.0	222.6	220.3	222.3
75°	180.8	177.7	174.6	170.7	169.2	169.2	168.4
77.5°	129.1	126.4	123.0	120.7	120.2	116.9	118.2
80°	93.5	89.6	88.1	88.9	86.5	85.7	85.7
82.5°	69.2	67.8	66.3	66.4	65.9	65.2	65.8
85°	38.2	37.4	37.4	36.6	36.6	35.9	35.9
87.5°	18.1	19.0	18.2	17.6	17.6	18.4	19.1
90°	22.1	23.2	25.6	25.6	25.6	26.7	26.7
92.5°	149.4	112.5	95.3	80.4	77.6	76.0	74.1
95°	658.8	515.9	418.3	335.8	300.9	291.7	273.1
97.5°	1120.4	981.2	845.4	773.6	708.6	674.9	660.0
100°	1372.3	1252.6	1131.7	1051.6	967.9	924.9	906.3
102.5°	1526.6	1469.2	1387.4	1301.6	1242.1	1195.4	1181.5
105°	1614.0	1665.1	1652.3	1615.1	1576.8	1553.5	1539.6
107.5°	1536.1	1667.4	1728.1	1746.9	1746.7	1739.0	1729.7
110°	1447.8	1611.6	1710.4	1762.7	1784.8	1792.9	1792.9



TEST NUMBER: P333636

CATALOG NUMBER: S125RDIP-S1270D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1360.4	1526.1	1642.5	1719.0	1756.9	1777.1	1785.5
115°	1235.2	1394.3	1521.0	1611.6	1667.4	1699.9	1715.0
117.5°	1148.5	1285.6	1401.8	1492.4	1550.1	1582.4	1591.6
120°	1099.2	1227.0	1329.3	1415.3	1471.0	1502.4	1511.7
122.5°	1063.9	1177.8	1273.5	1350.2	1401.3	1432.7	1441.1
125°	1016.7	1117.8	1201.5	1266.5	1314.2	1339.7	1351.4
127.5°	971.6	1066.0	1144.3	1203.3	1245.4	1269.6	1274.7
130°	940.0	1030.7	1106.2	1164.3	1202.6	1225.9	1232.8
132.5°	910.3	992.5	1065.3	1123.4	1161.7	1183.1	1191.0
135°	864.5	938.9	1005.1	1056.2	1094.6	1115.5	1122.5
137.5°	823.6	885.4	941.7	987.4	1022.3	1041.6	1049.2
140°	799.4	852.9	901.7	944.7	974.9	992.3	998.1
142.5°	779.0	825.0	867.3	903.8	929.3	945.8	950.7
145°	752.9	789.0	820.3	848.2	868.0	880.8	885.4
147.5°	731.3	759.0	782.7	804.8	820.6	828.0	830.1
150°	719.3	741.3	762.2	779.7	793.6	798.3	799.4
152.5°	707.2	727.4	743.7	758.3	769.4	774.1	775.3
155°	689.0	705.3	718.1	729.7	737.8	741.3	742.5
157.5°	671.8	684.4	694.4	703.4	710.2	713.4	713.2
160°	658.8	670.4	678.6	686.7	692.5	694.9	693.7
162.5°	647.7	657.4	664.6	670.9	675.8	676.3	676.0
165°	630.9	637.9	643.7	648.4	650.7	650.7	650.7
167.5°	614.7	620.0	624.2	626.5	628.6	627.7	627.5
170°	605.4	608.9	611.2	613.5	614.7	614.7	613.5
172.5°	597.0	599.6	601.0	601.4	603.5	601.7	600.5
175°	584.5	586.8	586.8	586.8	588.0	585.6	584.5
177.5°	579.1	579.1	579.1	578.2	579.1	576.3	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3

(END OF REPORT)