

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333617

Luminaire Tested: **S125RDIP-S1270D590U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333617  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D590U835-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6966.9 lumens  
Efficiency: N/A  
Efficacy: 126.4 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	75	75	75	75	75	75	75	75	75	75	75	75	71																
1	103	99	95	92	97	94	90	87	84	82	79	75	74	72	67	66	65	65	65	65	65	65	65	65	65	65	65	65	65	61																
2	94	87	81	76	89	83	77	73	74	70	67	67	64	61	60	58	55	55	55	55	55	55	55	55	55	55	55	55	55	52																
3	86	77	70	64	82	73	67	61	66	61	57	60	56	52	54	50	48	48	48	48	48	48	48	48	48	48	48	48	48	44																
4	79	68	61	55	75	65	58	53	59	53	49	53	49	45	48	45	41	41	41	41	41	41	41	41	41	41	41	41	41	39																
5	73	61	53	47	69	59	51	46	53	47	42	48	43	39	44	40	36	36	36	36	36	36	36	36	36	36	36	36	36	34																
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	40	35	32	32	32	32	32	32	32	32	32	32	32	32	32	30																
7	63	50	42	36	59	48	41	35	44	38	33	40	35	31	36	32	29	29	29	29	29	29	29	29	29	29	29	29	29	26																
8	58	46	38	32	55	44	36	31	40	34	30	37	31	28	33	29	26	26	26	26	26	26	26	26	26	26	26	26	26	24																
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	27	23	23	23	23	23	23	23	23	23	23	23	23	23	21																
10	51	38	31	26	48	37	30	26	34	28	24	31	26	23	29	24	21	21	21	21	21	21	21	21	21	21	21	21	21	19																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12264	12264	12264	12264
5°	14110	12280	10845	12280
10°	16184	12218	9569	12218
15°	17481	12092	8506	12092
20°	19276	11947	7854	11947
25°	22308	11754	7288	11754
30°	24276	11551	6918	11551
35°	20478	11315	6576	11315
40°	14300	10890	6283	10890
45°	10609	10316	5994	10316
50°	8459	9720	5749	9720
55°	7179	8979	5530	8979
60°	6203	8317	5176	8317
65°	5527	7600	4455	7600
70°	4857	6962	4062	6962
75°	4202	6029	3813	6029
80°	3187	5073	3187	5073
85°	2660	3987	3001	3987



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.1	2.6
10°-20°	533.6	7.7
20°-30°	846.1	12.1
30°-40°	1020.3	14.6
40°-50°	911.2	13.1
50°-60°	698.8	10.0
60°-70°	454.1	6.5
70°-80°	220.8	3.2
80°-90°	54.3	0.8
90°-100°	49.1	0.7
100°-110°	145.0	2.1
110°-120°	245.6	3.5
120°-130°	323.2	4.6
130°-140°	362.1	5.2
140°-150°	354.9	5.1
150°-160°	298.1	4.3
160°-170°	198.2	2.8
170°-180°	69.4	1.0
0°-30°	1561.8	22.4
0°-40°	2582.2	37.1
0°-60°	4192.1	60.2
0°-90°	4921.3	70.6
90°-120°	439.7	6.3
90°-150°	1479.9	21.2
90°-180°	2046.0	29.4
0°-180°	6966.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2176	1894	1673	1894	2176	217
15°	2614	1808	1272	1808	2614	749
25°	3130	1649	1023	1649	3130	1437
35°	2597	1435	834	1435	2597	1569
45°	1162	1130	656	1130	1162	927
55°	638	797	491	797	638	579
65°	362	497	292	497	362	360
75°	168	242	153	242	168	179
85°	36	54	40	54	36	42
90°	14	1	14	1	14	10
95°	49	37	49	37	49	50
105°	142	130	142	130	142	150
115°	248	246	248	246	248	245
125°	361	359	361	359	361	322
135°	468	467	468	467	468	361
145°	568	565	568	565	568	354
155°	647	647	647	647	647	298
165°	702	703	702	703	702	198
175°	728	731	728	731	728	69
180°	733	733	733	733	733	



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1997.4	1996.2	1998.7	1991.8	1992.4	1981.8	1981.8	1973.7	1963.1	1955.0	1951.3
5°	2176.4	2178.0	2174.8	2163.1	2155.4	2143.7	2130.4	2107.0	2087.5	2068.8	2054.0
7.5°	2360.7	2361.8	2351.5	2347.9	2328.2	2313.9	2284.4	2252.6	2224.4	2188.6	2161.1
10°	2467.9	2467.2	2456.2	2447.7	2430.5	2408.7	2379.9	2342.4	2307.4	2268.4	2231.0
12.5°	2530.3	2528.3	2524.8	2514.4	2498.5	2479.2	2454.7	2417.9	2374.7	2332.0	2288.3
15°	2614.5	2609.0	2598.9	2585.6	2563.0	2540.4	2513.1	2480.4	2439.1	2390.8	2350.2
17.5°	2718.6	2718.8	2703.2	2684.8	2654.1	2614.2	2572.1	2519.2	2463.1	2409.9	2366.8
20°	2804.7	2802.3	2786.8	2750.9	2715.8	2665.9	2617.6	2552.9	2484.3	2414.9	2361.1
22.5°	2928.2	2922.1	2905.9	2858.8	2804.4	2740.1	2666.2	2587.2	2504.3	2425.5	2354.9
25°	3130.5	3125.8	3093.9	3039.3	2962.9	2863.9	2767.3	2658.9	2539.7	2436.0	2350.2
27.5°	3269.0	3263.8	3240.1	3194.8	3124.3	3020.1	2889.3	2744.5	2595.6	2453.0	2329.3
30°	3255.2	3266.9	3263.8	3242.8	3189.8	3096.2	2975.4	2812.5	2635.5	2467.9	2320.6
32.5°	3059.4	3069.9	3097.3	3138.6	3141.7	3104.3	3014.1	2863.6	2680.4	2489.8	2313.7
35°	2597.3	2611.4	2664.4	2747.8	2856.9	2948.1	2966.8	2885.8	2721.3	2516.3	2303.5
37.5°	1996.8	2073.5	2118.1	2205.9	2370.8	2538.6	2699.9	2759.3	2689.3	2505.4	2286.8
40°	1696.2	1714.9	1794.4	1893.4	2032.2	2206.8	2436.8	2602.8	2608.2	2480.4	2260.6
42.5°	1451.8	1475.5	1530.0	1609.1	1727.9	1902.5	2139.9	2359.0	2460.5	2411.8	2226.3
45°	1161.5	1179.4	1219.2	1280.0	1371.2	1515.4	1719.6	1972.9	2174.1	2252.8	2134.3
47.5°	954.1	963.8	998.4	1044.7	1112.2	1217.3	1375.4	1595.3	1836.5	2005.7	1989.0
50°	841.9	852.8	879.3	914.4	971.3	1060.1	1186.4	1369.6	1618.3	1824.8	1866.2
52.5°	754.6	763.6	780.1	813.3	860.3	928.6	1030.5	1196.2	1420.0	1639.6	1735.2
55°	637.6	643.9	657.1	675.8	713.3	762.4	850.4	965.0	1145.9	1367.3	1507.6
57.5°	541.3	544.4	552.8	570.1	596.0	631.9	695.5	792.6	922.3	1121.7	1276.5
60°	480.2	483.3	494.2	505.9	526.2	558.9	608.8	676.6	801.3	965.8	1122.5
62.5°	431.5	433.4	438.1	449.8	467.6	492.8	532.1	587.4	686.6	831.1	979.1
65°	361.7	362.5	364.0	373.4	384.3	403.0	428.7	467.7	542.5	651.7	782.6
67.5°	294.7	295.7	301.2	304.5	315.9	325.7	340.8	370.6	423.3	496.9	598.7
70°	257.2	256.5	261.9	265.8	269.7	281.4	291.5	315.7	348.4	404.6	489.5
72.5°	222.3	220.3	222.6	224.0	229.2	237.1	247.3	262.1	287.3	326.0	391.0
75°	168.4	169.2	169.2	170.7	174.6	177.7	180.8	188.6	202.7	228.4	263.5
77.5°	118.2	116.9	120.2	120.7	123.0	126.4	129.1	132.2	138.0	148.6	166.7
80°	85.7	85.7	86.5	88.9	88.1	89.6	93.5	96.7	103.7	109.9	116.1
82.5°	65.8	65.2	65.9	66.4	66.3	67.8	69.2	69.8	72.5	75.6	80.0
85°	35.9	35.9	36.6	36.6	37.4	37.4	38.2	38.2	38.2	39.0	39.8
87.5°	16.5	15.8	15.1	15.0	15.5	16.7	15.9	15.2	15.0	14.9	15.4
90°	13.7	13.3	12.9	12.6	12.2	11.7	11.0	10.4	9.8	9.1	8.2
92.5°	26.9	26.6	26.4	26.1	25.8	25.3	24.4	23.6	22.7	21.9	20.8
95°	49.1	48.8	48.6	48.3	48.0	47.5	46.6	45.7	44.8	43.9	42.7
97.5°	74.4	74.2	74.1	73.9	73.8	73.3	72.5	71.6	70.8	69.9	68.2
100°	93.6	93.3	93.1	92.8	92.5	91.8	90.7	89.6	88.4	87.3	85.6
102.5°	112.7	112.4	112.0	111.7	111.3	110.5	109.3	108.0	106.8	105.5	104.7
105°	141.5	141.1	140.7	140.3	140.0	139.4	138.6	137.9	137.1	136.3	135.6
107.5°	170.9	170.9	171.0	171.0	171.0	170.8	170.5	170.1	169.7	169.3	168.7
110°	192.8	192.9	193.1	193.2	193.3	193.2	192.8	192.4	192.1	191.7	191.3



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	214.3	214.5	214.7	215.0	215.2	215.2	215.0	214.9	214.7	214.5	214.0
115°	248.2	248.3	248.4	248.5	248.7	248.8	248.9	249.0	249.2	249.3	249.0
117.5°	281.2	281.8	282.3	282.8	283.3	283.5	283.4	283.3	283.2	283.1	282.8
120°	304.1	304.6	305.1	305.6	306.1	306.3	306.3	306.3	306.3	306.3	306.2
122.5°	326.9	327.3	327.7	328.1	328.5	328.8	328.9	329.0	329.1	329.2	328.8
125°	361.1	361.2	361.4	361.5	361.6	361.8	362.1	362.3	362.6	362.8	362.7
127.5°	394.0	394.2	394.5	394.7	395.0	395.2	395.3	395.4	395.6	395.7	395.5
130°	415.9	416.1	416.4	416.6	416.9	417.1	417.2	417.3	417.5	417.6	417.3
132.5°	436.4	436.8	437.1	437.5	437.8	438.1	438.2	438.3	438.5	438.6	438.6
135°	468.4	468.9	469.4	469.9	470.4	470.6	470.6	470.6	470.6	470.6	470.5
137.5°	499.6	500.3	500.9	501.5	502.2	502.4	502.2	502.1	501.9	501.8	501.5
140°	519.7	520.3	521.0	521.6	522.2	522.4	522.2	521.9	521.7	521.4	521.0
142.5°	538.9	539.5	540.1	540.8	541.4	541.6	541.5	541.3	541.2	541.0	540.6
145°	567.6	568.0	568.4	568.8	569.1	569.3	569.3	569.3	569.3	569.3	569.0
147.5°	592.2	593.0	593.9	594.7	595.6	595.9	595.6	595.3	595.0	594.7	594.4
150°	610.4	610.7	610.9	611.2	611.4	611.5	611.5	611.5	611.5	611.5	611.0
152.5°	625.5	625.9	626.4	626.8	627.3	627.4	627.1	626.8	626.5	626.2	625.9
155°	646.9	647.5	648.2	648.8	649.5	649.5	649.0	648.5	648.0	647.5	647.4
157.5°	664.8	665.7	666.5	667.3	668.2	668.3	667.8	667.3	666.8	666.3	666.2
160°	677.2	677.8	678.4	679.1	679.7	679.7	679.2	678.7	678.2	677.7	677.6
162.5°	687.6	688.4	689.1	689.9	690.6	690.7	690.0	689.4	688.8	688.2	688.2
165°	701.7	702.4	703.2	704.0	704.7	704.9	704.3	703.8	703.3	702.8	702.7
167.5°	712.9	713.6	714.4	715.2	716.0	716.0	715.3	714.5	713.7	713.0	713.0
170°	718.8	719.7	720.6	721.5	722.3	722.4	721.6	720.9	720.1	719.4	719.4
172.5°	723.8	724.6	725.4	726.2	727.0	727.0	726.2	725.5	724.7	723.9	723.9
175°	728.5	729.4	730.3	731.2	732.0	732.1	731.3	730.6	729.8	729.1	729.1
177.5°	731.2	731.9	732.7	733.4	734.1	734.1	733.5	732.9	732.3	731.7	731.8
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1951.3	1946.9	1938.8	1931.3	1922.0	1913.9	1908.2	1901.4	1892.7	1882.1	1873.3
5°	2037.6	2020.5	1997.9	1978.4	1953.5	1934.0	1913.7	1894.2	1874.7	1849.8	1828.0
7.5°	2133.4	2098.0	2063.5	2020.2	1980.9	1945.8	1912.1	1878.0	1844.6	1809.2	1775.1
10°	2192.0	2149.1	2101.6	2047.0	1997.1	1949.6	1905.9	1863.0	1817.8	1778.1	1735.2
12.5°	2246.9	2191.5	2137.1	2068.2	2008.3	1950.2	1894.7	1841.2	1792.9	1741.3	1695.3
15°	2296.4	2241.9	2181.1	2096.9	2013.5	1943.3	1877.8	1808.5	1748.4	1690.8	1639.3
17.5°	2315.6	2258.4	2187.8	2106.9	2015.7	1927.4	1843.1	1767.0	1696.4	1629.2	1571.3
20°	2308.1	2252.8	2180.3	2103.1	2005.7	1913.7	1822.5	1738.3	1659.6	1588.6	1527.1
22.5°	2290.1	2232.8	2162.8	2081.3	1988.8	1891.3	1793.8	1704.0	1621.5	1548.1	1480.9
25°	2262.9	2185.0	2113.3	2033.7	1945.7	1849.0	1748.4	1649.4	1561.4	1486.5	1413.3
27.5°	2234.7	2137.4	2046.2	1967.2	1874.1	1787.9	1690.9	1589.4	1496.8	1420.6	1345.4
30°	2209.1	2100.0	1999.4	1909.8	1821.7	1739.9	1647.9	1548.9	1453.8	1375.1	1298.7
32.5°	2177.3	2061.3	1950.8	1847.4	1762.5	1681.3	1598.0	1503.4	1410.8	1329.5	1251.9
35°	2137.4	1989.3	1869.3	1759.4	1665.0	1586.3	1511.5	1435.1	1342.3	1258.1	1182.5
37.5°	2085.0	1917.0	1778.1	1658.3	1558.9	1479.8	1420.7	1350.9	1266.2	1185.6	1115.5
40°	2053.2	1864.6	1712.6	1594.1	1489.6	1406.2	1350.9	1291.7	1214.5	1138.9	1068.7
42.5°	2010.8	1816.6	1646.5	1523.0	1417.9	1337.6	1281.7	1229.9	1165.2	1094.0	1018.8
45°	1927.7	1723.5	1545.0	1412.5	1306.5	1227.7	1175.5	1129.5	1080.4	1014.9	949.4
47.5°	1819.5	1626.4	1439.6	1294.9	1191.1	1118.0	1067.3	1031.0	995.9	940.2	876.6
50°	1732.9	1546.6	1364.1	1223.8	1113.1	1043.8	996.2	967.4	935.4	884.7	831.7
52.5°	1630.6	1464.2	1285.6	1142.1	1037.7	972.7	927.0	898.2	871.8	830.5	780.0
55°	1469.4	1323.6	1159.9	1029.7	933.9	868.4	824.7	797.4	781.9	746.8	707.0
57.5°	1283.4	1178.9	1034.6	909.1	824.3	759.6	727.6	704.4	686.8	662.0	633.9
60°	1153.7	1080.4	951.0	831.7	753.8	692.2	663.4	643.9	627.5	606.5	584.6
62.5°	1022.1	968.8	856.2	753.8	682.1	630.5	603.5	585.9	567.0	552.8	531.6
65°	845.8	798.2	720.3	640.0	573.7	532.4	512.9	497.3	485.6	470.0	455.2
67.5°	657.9	638.6	584.8	529.4	481.9	445.1	428.3	417.4	403.3	394.0	383.8
70°	542.5	533.2	495.0	458.4	413.9	389.0	373.4	368.7	351.6	342.2	335.2
72.5°	440.3	435.9	413.9	388.5	357.2	335.3	321.0	315.7	304.8	297.3	292.8
75°	301.7	303.2	299.3	283.0	271.3	257.2	244.8	241.6	233.9	227.6	223.7
77.5°	190.8	198.8	199.1	198.3	193.6	185.1	179.9	177.6	169.9	167.6	166.7
80°	131.0	139.5	147.3	146.5	145.0	142.7	138.8	136.4	132.5	130.2	128.6
82.5°	87.3	95.3	101.8	106.0	105.7	103.4	100.7	99.6	98.8	97.1	96.8
85°	41.3	42.9	45.2	50.7	54.6	55.3	54.6	53.8	51.4	52.2	53.0
87.5°	15.8	15.6	16.1	15.9	15.1	18.0	19.6	20.1	19.0	18.0	16.9
90°	7.4	6.5	5.6	4.6	3.6	2.6	1.6	0.6	1.6	2.6	3.6
92.5°	19.7	18.6	17.5	16.6	15.9	15.2	14.5	13.8	14.5	15.2	15.9
95°	41.4	40.1	38.9	38.1	37.8	37.6	37.3	37.1	37.3	37.6	37.8
97.5°	66.4	64.7	62.9	62.0	61.9	61.8	61.7	61.6	61.7	61.8	61.9
100°	84.0	82.3	80.7	79.9	79.9	79.9	79.9	79.9	79.9	79.9	79.9
102.5°	103.9	103.0	102.2	101.5	101.0	100.5	100.0	99.5	100.0	100.5	101.0
105°	134.8	134.1	133.3	132.6	132.0	131.3	130.7	130.1	130.7	131.3	132.0
107.5°	168.1	167.6	167.0	166.4	165.7	165.1	164.5	163.8	164.5	165.1	165.7
110°	190.9	190.5	190.2	189.7	189.0	188.4	187.7	187.1	187.7	188.4	189.0





TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	213.5	213.1	212.6	212.2	211.8	211.5	211.2	210.8	211.2	211.5	211.8
115°	248.8	248.5	248.3	247.9	247.4	246.9	246.4	245.9	246.4	246.9	247.4
117.5°	282.6	282.4	282.2	281.9	281.7	281.5	281.2	281.0	281.2	281.5	281.7
120°	306.1	306.0	305.8	305.5	304.8	304.2	303.6	302.9	303.6	304.2	304.8
122.5°	328.5	328.2	327.8	327.6	327.3	327.1	326.9	326.7	326.9	327.1	327.3
125°	362.6	362.4	362.3	361.9	361.1	360.3	359.6	358.8	359.6	360.3	361.1
127.5°	395.4	395.2	395.1	394.8	394.3	393.9	393.5	393.1	393.5	393.9	394.3
130°	417.1	416.8	416.6	416.1	415.5	414.9	414.2	413.6	414.2	414.9	415.5
132.5°	438.7	438.7	438.8	438.3	437.2	436.2	435.2	434.1	435.2	436.2	437.2
135°	470.4	470.3	470.1	469.7	468.9	468.2	467.4	466.6	467.4	468.2	468.9
137.5°	501.2	501.0	500.7	500.2	499.4	498.7	498.0	497.2	498.0	498.7	499.4
140°	520.7	520.3	519.9	519.4	518.7	518.1	517.5	516.8	517.5	518.1	518.7
142.5°	540.1	539.6	539.1	538.6	538.1	537.5	537.0	536.5	537.0	537.5	538.1
145°	568.6	568.2	567.8	567.4	566.9	566.4	565.8	565.3	565.8	566.4	566.9
147.5°	594.1	593.7	593.4	593.2	592.9	592.6	592.3	592.0	592.3	592.6	592.9
150°	610.5	610.0	609.5	609.3	609.5	609.6	609.7	609.8	609.7	609.6	609.5
152.5°	625.7	625.5	625.3	625.1	625.0	624.8	624.6	624.4	624.6	624.8	625.0
155°	647.2	647.1	647.0	646.9	646.9	646.9	646.9	646.9	646.9	646.9	646.9
157.5°	666.1	665.9	665.8	665.9	666.2	666.4	666.7	667.0	666.7	666.4	666.2
160°	677.5	677.3	677.2	677.3	677.7	678.1	678.5	678.9	678.5	678.1	677.7
162.5°	688.2	688.1	688.1	688.2	688.5	688.8	689.1	689.4	689.1	688.8	688.5
165°	702.6	702.4	702.3	702.4	702.6	702.9	703.1	703.4	703.1	702.9	702.6
167.5°	713.0	713.0	713.0	713.2	713.7	714.2	714.8	715.3	714.8	714.2	713.7
170°	719.4	719.4	719.4	719.6	720.1	720.6	721.1	721.6	721.1	720.6	720.1
172.5°	723.9	723.9	723.9	724.2	724.7	725.2	725.7	726.2	725.7	725.2	724.7
175°	729.1	729.1	729.1	729.3	729.8	730.3	730.8	731.3	730.8	730.3	729.8
177.5°	731.9	732.0	732.1	732.3	732.8	733.2	733.6	734.0	733.6	733.2	732.8
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1867.1	1858.4	1852.1	1839.6	1830.9	1827.2	1820.3	1818.4	1825.3	1820.3	1819.7
5°	1811.6	1789.0	1771.1	1753.1	1733.6	1721.2	1702.5	1699.3	1694.7	1687.6	1686.1
7.5°	1745.0	1715.6	1692.5	1662.9	1637.1	1616.4	1593.0	1581.9	1575.9	1566.8	1554.7
10°	1700.1	1665.0	1633.9	1604.2	1572.3	1546.6	1523.2	1505.2	1493.5	1482.6	1478.0
12.5°	1655.8	1620.1	1580.2	1544.4	1508.7	1479.8	1453.9	1442.3	1429.3	1416.5	1405.6
15°	1587.1	1539.5	1495.9	1454.6	1424.2	1393.0	1368.0	1350.9	1331.4	1326.0	1304.9
17.5°	1514.1	1467.5	1416.4	1372.9	1337.6	1303.3	1275.9	1256.4	1241.8	1221.7	1212.0
20°	1468.6	1413.3	1363.4	1323.6	1284.6	1244.1	1216.0	1199.7	1185.6	1169.3	1161.5
22.5°	1420.0	1365.9	1314.7	1268.1	1228.5	1188.6	1168.6	1151.7	1135.7	1120.6	1110.3
25°	1348.6	1294.0	1240.2	1191.9	1150.6	1121.7	1098.3	1078.8	1070.3	1055.5	1044.5
27.5°	1277.9	1219.9	1164.1	1115.9	1083.5	1055.0	1035.8	1020.4	1004.9	992.0	982.5
30°	1232.4	1173.2	1112.4	1074.2	1039.9	1012.6	991.5	976.7	965.0	953.3	946.3
32.5°	1186.9	1125.8	1071.8	1030.5	998.1	974.5	952.9	938.7	926.4	913.4	905.2
35°	1113.9	1051.6	1007.9	967.4	935.4	913.6	898.8	878.5	868.4	859.0	850.4
37.5°	1046.1	988.1	940.9	905.3	877.6	855.9	836.7	825.8	813.3	804.9	797.8
40°	996.2	943.2	900.3	862.9	842.7	818.5	800.6	786.5	777.2	766.3	758.5
42.5°	951.3	902.1	860.4	826.8	801.5	781.1	763.8	749.7	737.9	730.1	723.5
45°	887.9	838.8	798.2	767.0	743.7	724.2	706.2	699.2	683.6	674.3	671.2
47.5°	822.2	778.3	739.1	710.4	686.4	668.0	651.2	636.9	628.3	619.1	614.1
50°	778.0	735.9	699.2	671.2	647.8	627.5	611.9	602.6	590.9	582.3	576.1
52.5°	733.7	694.7	658.1	631.2	611.0	590.7	573.3	563.9	552.8	547.4	543.0
55°	670.4	629.1	597.9	571.4	550.3	531.6	515.3	505.9	498.9	493.4	491.9
57.5°	598.7	565.9	536.9	513.1	491.2	473.6	459.3	450.4	444.2	443.4	438.7
60°	551.9	522.3	495.8	470.0	451.3	435.0	422.5	412.4	406.1	405.3	403.8
62.5°	505.1	476.7	452.1	429.5	412.7	396.9	385.1	373.7	370.0	366.1	362.6
65°	435.7	410.0	389.8	371.8	353.9	340.6	329.0	321.9	313.4	308.7	300.1
67.5°	367.6	347.7	328.2	313.1	299.0	286.4	276.7	266.3	260.5	256.8	250.5
70°	322.7	307.1	287.6	271.3	260.4	250.2	242.4	230.7	226.8	223.7	220.6
72.5°	280.3	266.6	250.2	237.0	226.1	216.5	207.5	202.0	198.2	195.0	193.2
75°	220.6	207.4	193.3	184.0	176.2	168.4	163.7	159.8	158.2	157.5	154.3
77.5°	162.0	155.0	143.7	136.3	131.1	128.0	123.8	121.8	121.6	118.2	117.1
80°	123.9	120.0	110.7	107.6	103.7	100.6	98.2	94.3	90.4	88.9	86.5
82.5°	92.1	88.2	84.5	79.5	76.2	74.4	72.0	70.6	71.1	68.9	67.8
85°	49.1	45.2	43.7	42.9	41.3	42.9	42.1	41.3	40.5	39.8	40.5
87.5°	16.5	16.7	16.3	17.7	16.0	16.8	16.9	16.4	16.5	16.7	16.2
90°	4.6	5.6	6.5	7.4	8.2	9.1	9.8	10.4	11.0	11.7	12.2
92.5°	16.6	17.5	18.6	19.7	20.8	21.9	22.7	23.6	24.4	25.3	25.8
95°	38.1	38.9	40.1	41.4	42.7	43.9	44.8	45.7	46.6	47.5	48.0
97.5°	62.0	62.9	64.7	66.4	68.2	69.9	70.8	71.6	72.5	73.3	73.8
100°	79.9	80.7	82.3	84.0	85.6	87.3	88.4	89.6	90.7	91.8	92.5
102.5°	101.5	102.2	103.0	103.9	104.7	105.5	106.8	108.0	109.3	110.5	111.3
105°	132.6	133.3	134.1	134.8	135.6	136.3	137.1	137.9	138.6	139.4	140.0
107.5°	166.4	167.0	167.6	168.1	168.7	169.3	169.7	170.1	170.5	170.8	171.0
110°	189.7	190.2	190.5	190.9	191.3	191.7	192.1	192.4	192.8	193.2	193.3



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	212.2	212.6	213.1	213.5	214.0	214.5	214.7	214.9	215.0	215.2	215.2
115°	247.9	248.3	248.5	248.8	249.0	249.3	249.2	249.0	248.9	248.8	248.7
117.5°	281.9	282.2	282.4	282.6	282.8	283.1	283.2	283.3	283.4	283.5	283.3
120°	305.5	305.8	306.0	306.1	306.2	306.3	306.3	306.3	306.3	306.3	306.1
122.5°	327.6	327.8	328.2	328.5	328.8	329.2	329.1	329.0	328.9	328.8	328.5
125°	361.9	362.3	362.4	362.6	362.7	362.8	362.6	362.3	362.1	361.8	361.6
127.5°	394.8	395.1	395.2	395.4	395.5	395.7	395.6	395.4	395.3	395.2	395.0
130°	416.1	416.6	416.8	417.1	417.3	417.6	417.5	417.3	417.2	417.1	416.9
132.5°	438.3	438.8	438.7	438.7	438.6	438.6	438.5	438.3	438.2	438.1	437.8
135°	469.7	470.1	470.3	470.4	470.5	470.6	470.6	470.6	470.6	470.6	470.4
137.5°	500.2	500.7	501.0	501.2	501.5	501.8	501.9	502.1	502.2	502.4	502.2
140°	519.4	519.9	520.3	520.7	521.0	521.4	521.7	521.9	522.2	522.4	522.2
142.5°	538.6	539.1	539.6	540.1	540.6	541.0	541.2	541.3	541.5	541.6	541.4
145°	567.4	567.8	568.2	568.6	569.0	569.3	569.3	569.3	569.3	569.3	569.1
147.5°	593.2	593.4	593.7	594.1	594.4	594.7	595.0	595.3	595.6	595.9	595.6
150°	609.3	609.5	610.0	610.5	611.0	611.5	611.5	611.5	611.5	611.5	611.4
152.5°	625.1	625.3	625.5	625.7	625.9	626.2	626.5	626.8	627.1	627.4	627.3
155°	646.9	647.0	647.1	647.2	647.4	647.5	648.0	648.5	649.0	649.5	649.5
157.5°	665.9	665.8	665.9	666.1	666.2	666.3	666.8	667.3	667.8	668.3	668.2
160°	677.3	677.2	677.3	677.5	677.6	677.7	678.2	678.7	679.2	679.7	679.7
162.5°	688.2	688.1	688.1	688.2	688.2	688.2	688.8	689.4	690.0	690.7	690.6
165°	702.4	702.3	702.4	702.6	702.7	702.8	703.3	703.8	704.3	704.9	704.7
167.5°	713.2	713.0	713.0	713.0	713.0	713.0	713.7	714.5	715.3	716.0	716.0
170°	719.6	719.4	719.4	719.4	719.4	719.4	720.1	720.9	721.6	722.4	722.3
172.5°	724.2	723.9	723.9	723.9	723.9	723.9	724.7	725.5	726.2	727.0	727.0
175°	729.3	729.1	729.1	729.1	729.1	729.1	729.8	730.6	731.3	732.1	732.0
177.5°	732.3	732.1	732.0	731.9	731.8	731.7	732.3	732.9	733.5	734.1	734.1
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1819.1	1812.2	1810.3	1812.8	1810.3	1812.2	1819.1	1819.7	1820.3	1825.3	1818.4
5°	1678.3	1670.5	1674.4	1672.8	1674.4	1670.5	1678.3	1686.1	1687.6	1694.7	1699.3
7.5°	1554.5	1544.8	1534.5	1537.8	1534.5	1544.8	1554.5	1554.7	1566.8	1575.9	1581.9
10°	1467.8	1460.0	1455.3	1459.2	1455.3	1460.0	1467.8	1478.0	1482.6	1493.5	1505.2
12.5°	1394.9	1390.2	1386.1	1384.4	1386.1	1390.2	1394.9	1405.6	1416.5	1429.3	1442.3
15°	1295.5	1286.2	1282.3	1272.2	1282.3	1286.2	1295.5	1304.9	1326.0	1331.4	1350.9
17.5°	1204.0	1200.9	1190.8	1186.4	1190.8	1200.9	1204.0	1212.0	1221.7	1241.8	1256.4
20°	1149.8	1146.7	1136.5	1142.8	1136.5	1146.7	1149.8	1161.5	1169.3	1185.6	1199.7
22.5°	1104.9	1098.0	1094.7	1092.9	1094.7	1098.0	1104.9	1110.3	1120.6	1135.7	1151.7
25°	1041.4	1031.3	1027.4	1022.7	1027.4	1031.3	1041.4	1044.5	1055.5	1070.3	1078.8
27.5°	978.1	972.7	967.5	966.3	967.5	972.7	978.1	982.5	992.0	1004.9	1020.4
30°	937.0	931.5	927.6	927.6	927.6	931.5	937.0	946.3	953.3	965.0	976.7
32.5°	900.2	896.0	892.1	891.5	892.1	896.0	900.2	905.2	913.4	926.4	938.7
35°	846.6	840.3	838.8	834.1	838.8	840.3	846.6	850.4	859.0	868.4	878.5
37.5°	790.9	785.7	785.6	785.1	785.6	785.7	790.9	797.8	804.9	813.3	825.8
40°	755.3	751.4	750.7	745.2	750.7	751.4	755.3	758.5	766.3	777.2	786.5
42.5°	717.3	715.3	712.6	710.3	712.6	715.3	717.3	723.5	730.1	737.9	749.7
45°	665.7	660.2	660.2	656.3	660.2	660.2	665.7	671.2	674.3	683.6	699.2
47.5°	612.4	608.2	608.6	604.6	608.6	608.2	612.4	614.1	619.1	628.3	636.9
50°	576.8	574.5	573.7	572.2	573.7	574.5	576.8	576.1	582.3	590.9	602.6
52.5°	541.3	540.2	543.2	539.7	543.2	540.2	541.3	543.0	547.4	552.8	563.9
55°	493.4	491.1	495.8	491.1	495.8	491.1	493.4	491.9	493.4	498.9	505.9
57.5°	438.4	436.2	440.4	438.1	440.4	436.2	438.4	438.7	443.4	444.2	450.4
60°	402.2	397.6	399.9	400.7	399.9	397.6	402.2	403.8	405.3	406.1	412.4
62.5°	359.2	356.4	358.1	354.5	358.1	356.4	359.2	362.6	366.1	370.0	373.7
65°	298.6	296.2	293.1	291.5	293.1	296.2	298.6	300.1	308.7	313.4	321.9
67.5°	250.8	245.2	245.1	246.3	245.1	245.2	250.8	250.5	256.8	260.5	266.3
70°	215.9	215.9	215.1	215.1	215.1	215.9	215.9	220.6	223.7	226.8	230.7
72.5°	191.6	191.0	189.6	189.0	189.6	191.0	191.6	193.2	195.0	198.2	202.0
75°	154.3	155.1	153.6	152.8	153.6	155.1	154.3	154.3	157.5	158.2	159.8
77.5°	114.0	110.7	112.4	110.7	112.4	110.7	114.0	117.1	118.2	121.6	121.8
80°	86.5	85.7	88.1	85.7	88.1	85.7	86.5	86.5	88.9	90.4	94.3
82.5°	68.4	67.7	68.8	67.0	68.8	67.7	68.4	67.8	68.9	71.1	70.6
85°	41.3	40.5	39.8	40.5	39.8	40.5	41.3	40.5	39.8	40.5	41.3
87.5°	16.9	16.3	16.4	16.5	16.4	16.3	16.9	16.2	16.7	16.5	16.4
90°	12.6	12.9	13.3	13.7	13.3	12.9	12.6	12.2	11.7	11.0	10.4
92.5°	26.1	26.4	26.6	26.9	26.6	26.4	26.1	25.8	25.3	24.4	23.6
95°	48.3	48.6	48.8	49.1	48.8	48.6	48.3	48.0	47.5	46.6	45.7
97.5°	73.9	74.1	74.2	74.4	74.2	74.1	73.9	73.8	73.3	72.5	71.6
100°	92.8	93.1	93.3	93.6	93.3	93.1	92.8	92.5	91.8	90.7	89.6
102.5°	111.7	112.0	112.4	112.7	112.4	112.0	111.7	111.3	110.5	109.3	108.0
105°	140.3	140.7	141.1	141.5	141.1	140.7	140.3	140.0	139.4	138.6	137.9
107.5°	171.0	171.0	170.9	170.9	170.9	171.0	171.0	171.0	170.8	170.5	170.1
110°	193.2	193.1	192.9	192.8	192.9	193.1	193.2	193.3	193.2	192.8	192.4



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	215.0	214.7	214.5	214.3	214.5	214.7	215.0	215.2	215.2	215.0	214.9
115°	248.5	248.4	248.3	248.2	248.3	248.4	248.5	248.7	248.8	248.9	249.0
117.5°	282.8	282.3	281.8	281.2	281.8	282.3	282.8	283.3	283.5	283.4	283.3
120°	305.6	305.1	304.6	304.1	304.6	305.1	305.6	306.1	306.3	306.3	306.3
122.5°	328.1	327.7	327.3	326.9	327.3	327.7	328.1	328.5	328.8	328.9	329.0
125°	361.5	361.4	361.2	361.1	361.2	361.4	361.5	361.6	361.8	362.1	362.3
127.5°	394.7	394.5	394.2	394.0	394.2	394.5	394.7	395.0	395.2	395.3	395.4
130°	416.6	416.4	416.1	415.9	416.1	416.4	416.6	416.9	417.1	417.2	417.3
132.5°	437.5	437.1	436.8	436.4	436.8	437.1	437.5	437.8	438.1	438.2	438.3
135°	469.9	469.4	468.9	468.4	468.9	469.4	469.9	470.4	470.6	470.6	470.6
137.5°	501.5	500.9	500.3	499.6	500.3	500.9	501.5	502.2	502.4	502.2	502.1
140°	521.6	521.0	520.3	519.7	520.3	521.0	521.6	522.2	522.4	522.2	521.9
142.5°	540.8	540.1	539.5	538.9	539.5	540.1	540.8	541.4	541.6	541.5	541.3
145°	568.8	568.4	568.0	567.6	568.0	568.4	568.8	569.1	569.3	569.3	569.3
147.5°	594.7	593.9	593.0	592.2	593.0	593.9	594.7	595.6	595.9	595.6	595.3
150°	611.2	610.9	610.7	610.4	610.7	610.9	611.2	611.4	611.5	611.5	611.5
152.5°	626.8	626.4	625.9	625.5	625.9	626.4	626.8	627.3	627.4	627.1	626.8
155°	648.8	648.2	647.5	646.9	647.5	648.2	648.8	649.5	649.5	649.0	648.5
157.5°	667.3	666.5	665.7	664.8	665.7	666.5	667.3	668.2	668.3	667.8	667.3
160°	679.1	678.4	677.8	677.2	677.8	678.4	679.1	679.7	679.7	679.2	678.7
162.5°	689.9	689.1	688.4	687.6	688.4	689.1	689.9	690.6	690.7	690.0	689.4
165°	704.0	703.2	702.4	701.7	702.4	703.2	704.0	704.7	704.9	704.3	703.8
167.5°	715.2	714.4	713.6	712.9	713.6	714.4	715.2	716.0	716.0	715.3	714.5
170°	721.5	720.6	719.7	718.8	719.7	720.6	721.5	722.3	722.4	721.6	720.9
172.5°	726.2	725.4	724.6	723.8	724.6	725.4	726.2	727.0	727.0	726.2	725.5
175°	731.2	730.3	729.4	728.5	729.4	730.3	731.2	732.0	732.1	731.3	730.6
177.5°	733.4	732.7	731.9	731.2	731.9	732.7	733.4	734.1	734.1	733.5	732.9
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1820.3	1827.2	1830.9	1839.6	1852.1	1858.4	1867.1	1873.3	1882.1	1892.7	1901.4
5°	1702.5	1721.2	1733.6	1753.1	1771.1	1789.0	1811.6	1828.0	1849.8	1874.7	1894.2
7.5°	1593.0	1616.4	1637.1	1662.9	1692.5	1715.6	1745.0	1775.1	1809.2	1844.6	1878.0
10°	1523.2	1546.6	1572.3	1604.2	1633.9	1665.0	1700.1	1735.2	1778.1	1817.8	1863.0
12.5°	1453.9	1479.8	1508.7	1544.4	1580.2	1620.1	1655.8	1695.3	1741.3	1792.9	1841.2
15°	1368.0	1393.0	1424.2	1454.6	1495.9	1539.5	1587.1	1639.3	1690.8	1748.4	1808.5
17.5°	1275.9	1303.3	1337.6	1372.9	1416.4	1467.5	1514.1	1571.3	1629.2	1696.4	1767.0
20°	1216.0	1244.1	1284.6	1323.6	1363.4	1413.3	1468.6	1527.1	1588.6	1659.6	1738.3
22.5°	1168.6	1188.6	1228.5	1268.1	1314.7	1365.9	1420.0	1480.9	1548.1	1621.5	1704.0
25°	1098.3	1121.7	1150.6	1191.9	1240.2	1294.0	1348.6	1413.3	1486.5	1561.4	1649.4
27.5°	1035.8	1055.0	1083.5	1115.9	1164.1	1219.9	1277.9	1345.4	1420.6	1496.8	1589.4
30°	991.5	1012.6	1039.9	1074.2	1112.4	1173.2	1232.4	1298.7	1375.1	1453.8	1548.9
32.5°	952.9	974.5	998.1	1030.5	1071.8	1125.8	1186.9	1251.9	1329.5	1410.8	1503.4
35°	898.8	913.6	935.4	967.4	1007.9	1051.6	1113.9	1182.5	1258.1	1342.3	1435.1
37.5°	836.7	855.9	877.6	905.3	940.9	988.1	1046.1	1115.5	1185.6	1266.2	1350.9
40°	800.6	818.5	842.7	862.9	900.3	943.2	996.2	1068.7	1138.9	1214.5	1291.7
42.5°	763.8	781.1	801.5	826.8	860.4	902.1	951.3	1018.8	1094.0	1165.2	1229.9
45°	706.2	724.2	743.7	767.0	798.2	838.8	887.9	949.4	1014.9	1080.4	1129.5
47.5°	651.2	668.0	686.4	710.4	739.1	778.3	822.2	876.6	940.2	995.9	1031.0
50°	611.9	627.5	647.8	671.2	699.2	735.9	778.0	831.7	884.7	935.4	967.4
52.5°	573.3	590.7	611.0	631.2	658.1	694.7	733.7	780.0	830.5	871.8	898.2
55°	515.3	531.6	550.3	571.4	597.9	629.1	670.4	707.0	746.8	781.9	797.4
57.5°	459.3	473.6	491.2	513.1	536.9	565.9	598.7	633.9	662.0	686.8	704.4
60°	422.5	435.0	451.3	470.0	495.8	522.3	551.9	584.6	606.5	627.5	643.9
62.5°	385.1	396.9	412.7	429.5	452.1	476.7	505.1	531.6	552.8	567.0	585.9
65°	329.0	340.6	353.9	371.8	389.8	410.0	435.7	455.2	470.0	485.6	497.3
67.5°	276.7	286.4	299.0	313.1	328.2	347.7	367.6	383.8	394.0	403.3	417.4
70°	242.4	250.2	260.4	271.3	287.6	307.1	322.7	335.2	342.2	351.6	368.7
72.5°	207.5	216.5	226.1	237.0	250.2	266.6	280.3	292.8	297.3	304.8	315.7
75°	163.7	168.4	176.2	184.0	193.3	207.4	220.6	223.7	227.6	233.9	241.6
77.5°	123.8	128.0	131.1	136.3	143.7	155.0	162.0	166.7	167.6	169.9	177.6
80°	98.2	100.6	103.7	107.6	110.7	120.0	123.9	128.6	130.2	132.5	136.4
82.5°	72.0	74.4	76.2	79.5	84.5	88.2	92.1	96.8	97.1	98.8	99.6
85°	42.1	42.9	41.3	42.9	43.7	45.2	49.1	53.0	52.2	51.4	53.8
87.5°	16.9	16.8	16.0	17.7	16.3	16.7	16.5	16.9	18.0	19.0	20.1
90°	9.8	9.1	8.2	7.4	6.5	5.6	4.6	3.6	2.6	1.6	0.6
92.5°	22.7	21.9	20.8	19.7	18.6	17.5	16.6	15.9	15.2	14.5	13.8
95°	44.8	43.9	42.7	41.4	40.1	38.9	38.1	37.8	37.6	37.3	37.1
97.5°	70.8	69.9	68.2	66.4	64.7	62.9	62.0	61.9	61.8	61.7	61.6
100°	88.4	87.3	85.6	84.0	82.3	80.7	79.9	79.9	79.9	79.9	79.9
102.5°	106.8	105.5	104.7	103.9	103.0	102.2	101.5	101.0	100.5	100.0	99.5
105°	137.1	136.3	135.6	134.8	134.1	133.3	132.6	132.0	131.3	130.7	130.1
107.5°	169.7	169.3	168.7	168.1	167.6	167.0	166.4	165.7	165.1	164.5	163.8
110°	192.1	191.7	191.3	190.9	190.5	190.2	189.7	189.0	188.4	187.7	187.1



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	214.7	214.5	214.0	213.5	213.1	212.6	212.2	211.8	211.5	211.2	210.8
115°	249.2	249.3	249.0	248.8	248.5	248.3	247.9	247.4	246.9	246.4	245.9
117.5°	283.2	283.1	282.8	282.6	282.4	282.2	281.9	281.7	281.5	281.2	281.0
120°	306.3	306.3	306.2	306.1	306.0	305.8	305.5	304.8	304.2	303.6	302.9
122.5°	329.1	329.2	328.8	328.5	328.2	327.8	327.6	327.3	327.1	326.9	326.7
125°	362.6	362.8	362.7	362.6	362.4	362.3	361.9	361.1	360.3	359.6	358.8
127.5°	395.6	395.7	395.5	395.4	395.2	395.1	394.8	394.3	393.9	393.5	393.1
130°	417.5	417.6	417.3	417.1	416.8	416.6	416.1	415.5	414.9	414.2	413.6
132.5°	438.5	438.6	438.6	438.7	438.7	438.8	438.3	437.2	436.2	435.2	434.1
135°	470.6	470.6	470.5	470.4	470.3	470.1	469.7	468.9	468.2	467.4	466.6
137.5°	501.9	501.8	501.5	501.2	501.0	500.7	500.2	499.4	498.7	498.0	497.2
140°	521.7	521.4	521.0	520.7	520.3	519.9	519.4	518.7	518.1	517.5	516.8
142.5°	541.2	541.0	540.6	540.1	539.6	539.1	538.6	538.1	537.5	537.0	536.5
145°	569.3	569.3	569.0	568.6	568.2	567.8	567.4	566.9	566.4	565.8	565.3
147.5°	595.0	594.7	594.4	594.1	593.7	593.4	593.2	592.9	592.6	592.3	592.0
150°	611.5	611.5	611.0	610.5	610.0	609.5	609.3	609.5	609.6	609.7	609.8
152.5°	626.5	626.2	625.9	625.7	625.5	625.3	625.1	625.0	624.8	624.6	624.4
155°	648.0	647.5	647.4	647.2	647.1	647.0	646.9	646.9	646.9	646.9	646.9
157.5°	666.8	666.3	666.2	666.1	665.9	665.8	665.9	666.2	666.4	666.7	667.0
160°	678.2	677.7	677.6	677.5	677.3	677.2	677.3	677.7	678.1	678.5	678.9
162.5°	688.8	688.2	688.2	688.2	688.1	688.1	688.2	688.5	688.8	689.1	689.4
165°	703.3	702.8	702.7	702.6	702.4	702.3	702.4	702.6	702.9	703.1	703.4
167.5°	713.7	713.0	713.0	713.0	713.0	713.0	713.2	713.7	714.2	714.8	715.3
170°	720.1	719.4	719.4	719.4	719.4	719.4	719.6	720.1	720.6	721.1	721.6
172.5°	724.7	723.9	723.9	723.9	723.9	723.9	724.2	724.7	725.2	725.7	726.2
175°	729.8	729.1	729.1	729.1	729.1	729.1	729.3	729.8	730.3	730.8	731.3
177.5°	732.3	731.7	731.8	731.9	732.0	732.1	732.3	732.8	733.2	733.6	734.0
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1908.2	1913.9	1922.0	1931.3	1938.8	1946.9	1951.3	1951.3	1955.0	1963.1	1973.7
5°	1913.7	1934.0	1953.5	1978.4	1997.9	2020.5	2037.6	2054.0	2068.8	2087.5	2107.0
7.5°	1912.1	1945.8	1980.9	2020.2	2063.5	2098.0	2133.4	2161.1	2188.6	2224.4	2252.6
10°	1905.9	1949.6	1997.1	2047.0	2101.6	2149.1	2192.0	2231.0	2268.4	2307.4	2342.4
12.5°	1894.7	1950.2	2008.3	2068.2	2137.1	2191.5	2246.9	2288.3	2332.0	2374.7	2417.9
15°	1877.8	1943.3	2013.5	2096.9	2181.1	2241.9	2296.4	2350.2	2390.8	2439.1	2480.4
17.5°	1843.1	1927.4	2015.7	2106.9	2187.8	2258.4	2315.6	2366.8	2409.9	2463.1	2519.2
20°	1822.5	1913.7	2005.7	2103.1	2180.3	2252.8	2308.1	2361.1	2414.9	2484.3	2552.9
22.5°	1793.8	1891.3	1988.8	2081.3	2162.8	2232.8	2290.1	2354.9	2425.5	2504.3	2587.2
25°	1748.4	1849.0	1945.7	2033.7	2113.3	2185.0	2262.9	2350.2	2436.0	2539.7	2658.9
27.5°	1690.9	1787.9	1874.1	1967.2	2046.2	2137.4	2234.7	2329.3	2453.0	2595.6	2744.5
30°	1647.9	1739.9	1821.7	1909.8	1999.4	2100.0	2209.1	2320.6	2467.9	2635.5	2812.5
32.5°	1598.0	1681.3	1762.5	1847.4	1950.8	2061.3	2177.3	2313.7	2489.8	2680.4	2863.6
35°	1511.5	1586.3	1665.0	1759.4	1869.3	1989.3	2137.4	2303.5	2516.3	2721.3	2885.8
37.5°	1420.7	1479.8	1558.9	1658.3	1778.1	1917.0	2085.0	2286.8	2505.4	2689.3	2759.3
40°	1350.9	1406.2	1489.6	1594.1	1712.6	1864.6	2053.2	2260.6	2480.4	2608.2	2602.8
42.5°	1281.7	1337.6	1417.9	1523.0	1646.5	1816.6	2010.8	2226.3	2411.8	2460.5	2359.0
45°	1175.5	1227.7	1306.5	1412.5	1545.0	1723.5	1927.7	2134.3	2252.8	2174.1	1972.9
47.5°	1067.3	1118.0	1191.1	1294.9	1439.6	1626.4	1819.5	1989.0	2005.7	1836.5	1595.3
50°	996.2	1043.8	1113.1	1223.8	1364.1	1546.6	1732.9	1866.2	1824.8	1618.3	1369.6
52.5°	927.0	972.7	1037.7	1142.1	1285.6	1464.2	1630.6	1735.2	1639.6	1420.0	1196.2
55°	824.7	868.4	933.9	1029.7	1159.9	1323.6	1469.4	1507.6	1367.3	1145.9	965.0
57.5°	727.6	759.6	824.3	909.1	1034.6	1178.9	1283.4	1276.5	1121.7	922.3	792.6
60°	663.4	692.2	753.8	831.7	951.0	1080.4	1153.7	1122.5	965.8	801.3	676.6
62.5°	603.5	630.5	682.1	753.8	856.2	968.8	1022.1	979.1	831.1	686.6	587.4
65°	512.9	532.4	573.7	640.0	720.3	798.2	845.8	782.6	651.7	542.5	467.7
67.5°	428.3	445.1	481.9	529.4	584.8	638.6	657.9	598.7	496.9	423.3	370.6
70°	373.4	389.0	413.9	458.4	495.0	533.2	542.5	489.5	404.6	348.4	315.7
72.5°	321.0	335.3	357.2	388.5	413.9	435.9	440.3	391.0	326.0	287.3	262.1
75°	244.8	257.2	271.3	283.0	299.3	303.2	301.7	263.5	228.4	202.7	188.6
77.5°	179.9	185.1	193.6	198.3	199.1	198.8	190.8	166.7	148.6	138.0	132.2
80°	138.8	142.7	145.0	146.5	147.3	139.5	131.0	116.1	109.9	103.7	96.7
82.5°	100.7	103.4	105.7	106.0	101.8	95.3	87.3	80.0	75.6	72.5	69.8
85°	54.6	55.3	54.6	50.7	45.2	42.9	41.3	39.8	39.0	38.2	38.2
87.5°	19.6	18.0	15.1	15.9	16.1	15.6	15.8	15.4	14.9	15.0	15.2
90°	1.6	2.6	3.6	4.6	5.6	6.5	7.4	8.2	9.1	9.8	10.4
92.5°	14.5	15.2	15.9	16.6	17.5	18.6	19.7	20.8	21.9	22.7	23.6
95°	37.3	37.6	37.8	38.1	38.9	40.1	41.4	42.7	43.9	44.8	45.7
97.5°	61.7	61.8	61.9	62.0	62.9	64.7	66.4	68.2	69.9	70.8	71.6
100°	79.9	79.9	79.9	79.9	80.7	82.3	84.0	85.6	87.3	88.4	89.6
102.5°	100.0	100.5	101.0	101.5	102.2	103.0	103.9	104.7	105.5	106.8	108.0
105°	130.7	131.3	132.0	132.6	133.3	134.1	134.8	135.6	136.3	137.1	137.9
107.5°	164.5	165.1	165.7	166.4	167.0	167.6	168.1	168.7	169.3	169.7	170.1
110°	187.7	188.4	189.0	189.7	190.2	190.5	190.9	191.3	191.7	192.1	192.4





TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	211.2	211.5	211.8	212.2	212.6	213.1	213.5	214.0	214.5	214.7	214.9
115°	246.4	246.9	247.4	247.9	248.3	248.5	248.8	249.0	249.3	249.2	249.0
117.5°	281.2	281.5	281.7	281.9	282.2	282.4	282.6	282.8	283.1	283.2	283.3
120°	303.6	304.2	304.8	305.5	305.8	306.0	306.1	306.2	306.3	306.3	306.3
122.5°	326.9	327.1	327.3	327.6	327.8	328.2	328.5	328.8	329.2	329.1	329.0
125°	359.6	360.3	361.1	361.9	362.3	362.4	362.6	362.7	362.8	362.6	362.3
127.5°	393.5	393.9	394.3	394.8	395.1	395.2	395.4	395.5	395.7	395.6	395.4
130°	414.2	414.9	415.5	416.1	416.6	416.8	417.1	417.3	417.6	417.5	417.3
132.5°	435.2	436.2	437.2	438.3	438.8	438.7	438.7	438.6	438.6	438.5	438.3
135°	467.4	468.2	468.9	469.7	470.1	470.3	470.4	470.5	470.6	470.6	470.6
137.5°	498.0	498.7	499.4	500.2	500.7	501.0	501.2	501.5	501.8	501.9	502.1
140°	517.5	518.1	518.7	519.4	519.9	520.3	520.7	521.0	521.4	521.7	521.9
142.5°	537.0	537.5	538.1	538.6	539.1	539.6	540.1	540.6	541.0	541.2	541.3
145°	565.8	566.4	566.9	567.4	567.8	568.2	568.6	569.0	569.3	569.3	569.3
147.5°	592.3	592.6	592.9	593.2	593.4	593.7	594.1	594.4	594.7	595.0	595.3
150°	609.7	609.6	609.5	609.3	609.5	610.0	610.5	611.0	611.5	611.5	611.5
152.5°	624.6	624.8	625.0	625.1	625.3	625.5	625.7	625.9	626.2	626.5	626.8
155°	646.9	646.9	646.9	646.9	647.0	647.1	647.2	647.4	647.5	648.0	648.5
157.5°	666.7	666.4	666.2	665.9	665.8	665.9	666.1	666.2	666.3	666.8	667.3
160°	678.5	678.1	677.7	677.3	677.2	677.3	677.5	677.6	677.7	678.2	678.7
162.5°	689.1	688.8	688.5	688.2	688.1	688.1	688.2	688.2	688.2	688.8	689.4
165°	703.1	702.9	702.6	702.4	702.3	702.4	702.6	702.7	702.8	703.3	703.8
167.5°	714.8	714.2	713.7	713.2	713.0	713.0	713.0	713.0	713.0	713.7	714.5
170°	721.1	720.6	720.1	719.6	719.4	719.4	719.4	719.4	719.4	720.1	720.9
172.5°	725.7	725.2	724.7	724.2	723.9	723.9	723.9	723.9	723.9	724.7	725.5
175°	730.8	730.3	729.8	729.3	729.1	729.1	729.1	729.1	729.1	729.8	730.6
177.5°	733.6	733.2	732.8	732.3	732.1	732.0	731.9	731.8	731.7	732.3	732.9
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1981.8	1981.8	1992.4	1991.8	1998.7	1996.2	1997.4
5°	2130.4	2143.7	2155.4	2163.1	2174.8	2178.0	2176.4
7.5°	2284.4	2313.9	2328.2	2347.9	2351.5	2361.8	2360.7
10°	2379.9	2408.7	2430.5	2447.7	2456.2	2467.2	2467.9
12.5°	2454.7	2479.2	2498.5	2514.4	2524.8	2528.3	2530.3
15°	2513.1	2540.4	2563.0	2585.6	2598.9	2609.0	2614.5
17.5°	2572.1	2614.2	2654.1	2684.8	2703.2	2718.8	2718.6
20°	2617.6	2665.9	2715.8	2750.9	2786.8	2802.3	2804.7
22.5°	2666.2	2740.1	2804.4	2858.8	2905.9	2922.1	2928.2
25°	2767.3	2863.9	2962.9	3039.3	3093.9	3125.8	3130.5
27.5°	2889.3	3020.1	3124.3	3194.8	3240.1	3263.8	3269.0
30°	2975.4	3096.2	3189.8	3242.8	3263.8	3266.9	3255.2
32.5°	3014.1	3104.3	3141.7	3138.6	3097.3	3069.9	3059.4
35°	2966.8	2948.1	2856.9	2747.8	2664.4	2611.4	2597.3
37.5°	2699.9	2538.6	2370.8	2205.9	2118.1	2073.5	1996.8
40°	2436.8	2206.8	2032.2	1893.4	1794.4	1714.9	1696.2
42.5°	2139.9	1902.5	1727.9	1609.1	1530.0	1475.5	1451.8
45°	1719.6	1515.4	1371.2	1280.0	1219.2	1179.4	1161.5
47.5°	1375.4	1217.3	1112.2	1044.7	998.4	963.8	954.1
50°	1186.4	1060.1	971.3	914.4	879.3	852.8	841.9
52.5°	1030.5	928.6	860.3	813.3	780.1	763.6	754.6
55°	850.4	762.4	713.3	675.8	657.1	643.9	637.6
57.5°	695.5	631.9	596.0	570.1	552.8	544.4	541.3
60°	608.8	558.9	526.2	505.9	494.2	483.3	480.2
62.5°	532.1	492.8	467.6	449.8	438.1	433.4	431.5
65°	428.7	403.0	384.3	373.4	364.0	362.5	361.7
67.5°	340.8	325.7	315.9	304.5	301.2	295.7	294.7
70°	291.5	281.4	269.7	265.8	261.9	256.5	257.2
72.5°	247.3	237.1	229.2	224.0	222.6	220.3	222.3
75°	180.8	177.7	174.6	170.7	169.2	169.2	168.4
77.5°	129.1	126.4	123.0	120.7	120.2	116.9	118.2
80°	93.5	89.6	88.1	88.9	86.5	85.7	85.7
82.5°	69.2	67.8	66.3	66.4	65.9	65.2	65.8
85°	38.2	37.4	37.4	36.6	36.6	35.9	35.9
87.5°	15.9	16.7	15.5	15.0	15.1	15.8	16.5
90°	11.0	11.7	12.2	12.6	12.9	13.3	13.7
92.5°	24.4	25.3	25.8	26.1	26.4	26.6	26.9
95°	46.6	47.5	48.0	48.3	48.6	48.8	49.1
97.5°	72.5	73.3	73.8	73.9	74.1	74.2	74.4
100°	90.7	91.8	92.5	92.8	93.1	93.3	93.6
102.5°	109.3	110.5	111.3	111.7	112.0	112.4	112.7
105°	138.6	139.4	140.0	140.3	140.7	141.1	141.5
107.5°	170.5	170.8	171.0	171.0	171.0	170.9	170.9
110°	192.8	193.2	193.3	193.2	193.1	192.9	192.8



TEST NUMBER: P333617

CATALOG NUMBER: S125RDIP-S1270D590U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	215.0	215.2	215.2	215.0	214.7	214.5	214.3
115°	248.9	248.8	248.7	248.5	248.4	248.3	248.2
117.5°	283.4	283.5	283.3	282.8	282.3	281.8	281.2
120°	306.3	306.3	306.1	305.6	305.1	304.6	304.1
122.5°	328.9	328.8	328.5	328.1	327.7	327.3	326.9
125°	362.1	361.8	361.6	361.5	361.4	361.2	361.1
127.5°	395.3	395.2	395.0	394.7	394.5	394.2	394.0
130°	417.2	417.1	416.9	416.6	416.4	416.1	415.9
132.5°	438.2	438.1	437.8	437.5	437.1	436.8	436.4
135°	470.6	470.6	470.4	469.9	469.4	468.9	468.4
137.5°	502.2	502.4	502.2	501.5	500.9	500.3	499.6
140°	522.2	522.4	522.2	521.6	521.0	520.3	519.7
142.5°	541.5	541.6	541.4	540.8	540.1	539.5	538.9
145°	569.3	569.3	569.1	568.8	568.4	568.0	567.6
147.5°	595.6	595.9	595.6	594.7	593.9	593.0	592.2
150°	611.5	611.5	611.4	611.2	610.9	610.7	610.4
152.5°	627.1	627.4	627.3	626.8	626.4	625.9	625.5
155°	649.0	649.5	649.5	648.8	648.2	647.5	646.9
157.5°	667.8	668.3	668.2	667.3	666.5	665.7	664.8
160°	679.2	679.7	679.7	679.1	678.4	677.8	677.2
162.5°	690.0	690.7	690.6	689.9	689.1	688.4	687.6
165°	704.3	704.9	704.7	704.0	703.2	702.4	701.7
167.5°	715.3	716.0	716.0	715.2	714.4	713.6	712.9
170°	721.6	722.4	722.3	721.5	720.6	719.7	718.8
172.5°	726.2	727.0	727.0	726.2	725.4	724.6	723.8
175°	731.3	732.1	732.0	731.2	730.3	729.4	728.5
177.5°	733.5	734.1	734.1	733.4	732.7	731.9	731.2
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1

(END OF REPORT)