

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333510

Luminaire Tested: **S125RDIP-S375D1035U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333510  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D1035U835-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5174.2 lumens  
Efficiency: N/A  
Efficacy: 138.7 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28																												
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31	24																												
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26	21																												
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18																												
4	71	61	53	48	63	55	48	43	43	39	35	33	30	27	23	21	20	15																												
5	65	54	46	41	58	49	42	37	39	34	30	29	26	24	21	19	17	13																												
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12																												
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	11																												
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9																												
9	48	36	29	24	43	33	26	22	26	21	18	20	17	15	14	12	11	9																												
10	44	33	26	21	40	30	24	20	24	19	16	19	15	13	13	11	10	8																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3635	3635	3635	3635
5°	4182	3640	3215	3640
10°	4798	3621	2837	3621
15°	5182	3584	2521	3584
20°	5714	3542	2328	3542
25°	6613	3484	2161	3484
30°	7196	3424	2051	3424
35°	6070	3354	1949	3354
40°	4239	3228	1862	3228
45°	3145	3058	1777	3058
50°	2508	2882	1704	2882
55°	2128	2662	1639	2662
60°	1838	2466	1535	2466
65°	1638	2253	1320	2253
70°	1441	2064	1205	2064
75°	1245	1787	1130	1787
80°	945	1503	945	1503
85°	785	1178	889	1178



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.0	1.0
10°-20°	158.2	3.1
20°-30°	250.8	4.8
30°-40°	302.5	5.8
40°-50°	270.1	5.2
50°-60°	207.1	4.0
60°-70°	134.6	2.6
70°-80°	65.4	1.3
80°-90°	18.4	0.4
90°-100°	358.9	6.9
100°-110°	771.5	14.9
110°-120°	724.1	14.0
120°-130°	586.8	11.3
130°-140°	470.9	9.1
140°-150°	355.4	6.9
150°-160°	250.1	4.8
160°-170°	147.4	2.8
170°-180°	48.0	0.9
0°-30°	463.0	8.9
0°-40°	765.4	14.8
0°-60°	1242.7	24.0
0°-90°	1461.1	28.2
90°-120°	1854.5	35.8
90°-150°	3267.6	63.2
90°-180°	3713.0	71.8
0°-180°	5174.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	645	562	496	562	645	64
15°	775	536	377	536	775	222
25°	928	489	303	489	928	426
35°	770	425	247	425	770	465
45°	344	335	195	335	344	275
55°	189	236	146	236	189	172
65°	107	147	86	147	107	107
75°	50	72	45	72	50	53
85°	11	16	12	16	11	13
90°	23	1	23	1	23	16
95°	235	33	235	33	235	332
105°	1323	113	1323	113	1323	1315
115°	1474	202	1474	202	1474	1440
125°	1161	280	1161	280	1161	1050
135°	964	327	964	327	964	747
145°	761	381	761	381	761	483
155°	638	435	638	435	638	297
165°	559	475	559	475	559	160
175°	502	494	502	494	502	49
180°	495	495	495	495	495	



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	592.1	591.7	592.5	590.4	590.6	587.5	587.5	585.1	581.9	579.5	578.4
5°	645.1	645.6	644.7	641.2	638.9	635.4	631.5	624.6	618.8	613.2	608.9
7.5°	699.8	700.1	697.0	696.0	690.1	685.9	677.2	667.7	659.4	648.7	640.6
10°	731.6	731.3	728.1	725.5	720.5	714.0	705.4	694.4	684.0	672.4	661.3
12.5°	750.0	749.4	748.4	745.3	740.6	734.9	727.6	716.7	703.9	691.3	678.3
15°	775.0	773.4	770.4	766.4	759.7	753.0	745.0	735.3	723.0	708.7	696.7
17.5°	805.9	805.9	801.3	795.8	786.7	774.9	762.4	746.8	730.1	714.4	701.6
20°	831.4	830.7	826.1	815.4	805.0	790.2	775.9	756.7	736.4	715.8	699.9
22.5°	868.0	866.2	861.4	847.4	831.3	812.2	790.3	766.9	742.3	719.0	698.0
25°	928.0	926.6	917.1	900.9	878.3	848.9	820.3	788.2	752.8	722.1	696.7
27.5°	969.0	967.5	960.4	947.0	926.1	895.2	856.5	813.5	769.4	727.1	690.5
30°	964.9	968.4	967.5	961.2	945.5	917.8	882.0	833.7	781.2	731.6	687.9
32.5°	906.9	910.0	918.1	930.4	931.3	920.2	893.4	848.8	794.5	738.0	685.8
35°	769.9	774.1	789.8	814.5	846.9	873.9	879.4	855.4	806.6	745.9	682.8
37.5°	591.9	614.6	627.9	653.9	702.8	752.5	800.3	817.9	797.2	742.6	677.9
40°	502.8	508.3	531.9	561.3	602.4	654.1	722.3	771.5	773.1	735.3	670.1
42.5°	430.3	437.4	453.5	477.0	512.2	563.9	634.3	699.3	729.3	714.9	659.9
45°	344.3	349.6	361.4	379.4	406.4	449.2	509.7	584.8	644.4	667.8	632.7
47.5°	282.8	285.7	295.9	309.7	329.7	360.8	407.7	472.9	544.4	594.5	589.6
50°	249.6	252.8	260.6	271.0	287.9	314.2	351.7	406.0	479.7	540.9	553.2
52.5°	223.7	226.4	231.3	241.1	255.0	275.2	305.5	354.6	420.9	486.0	514.4
55°	189.0	190.9	194.8	200.3	211.4	226.0	252.1	286.1	339.7	405.3	446.9
57.5°	160.5	161.4	163.9	169.0	176.7	187.3	206.2	234.9	273.4	332.5	378.4
60°	142.3	143.3	146.5	150.0	156.0	165.7	180.5	200.6	237.5	286.3	332.7
62.5°	127.9	128.5	129.9	133.3	138.6	146.1	157.7	174.1	203.5	246.4	290.2
65°	107.2	107.4	107.9	110.7	113.9	119.5	127.1	138.6	160.8	193.2	232.0
67.5°	87.3	87.7	89.3	90.3	93.6	96.5	101.0	109.8	125.5	147.3	177.5
70°	76.3	76.0	77.6	78.8	79.9	83.4	86.4	93.6	103.3	119.9	145.1
72.5°	65.9	65.3	66.0	66.4	67.9	70.3	73.3	77.7	85.2	96.6	115.9
75°	49.9	50.1	50.1	50.6	51.8	52.7	53.6	55.9	60.1	67.7	78.1
77.5°	35.0	34.7	35.6	35.8	36.5	37.5	38.3	39.2	40.9	44.0	49.4
80°	25.4	25.4	25.6	26.3	26.1	26.6	27.7	28.7	30.7	32.6	34.4
82.5°	19.5	19.3	19.5	19.7	19.6	20.1	20.5	20.7	21.5	22.4	23.7
85°	10.6	10.6	10.9	10.9	11.1	11.1	11.3	11.3	11.3	11.6	11.8
87.5°	8.7	8.5	8.1	8.1	8.3	8.2	7.9	7.5	7.3	7.1	6.9
90°	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0	17.0	16.0	14.0
92.5°	63.7	65.3	66.7	69.1	81.9	96.6	128.4	176.9	260.5	321.8	327.0
95°	234.6	250.6	258.6	288.5	359.4	443.2	566.0	717.8	865.5	884.5	721.8
97.5°	567.0	579.8	608.7	664.7	726.3	842.9	962.5	1069.0	1095.1	944.6	644.5
100°	778.7	794.6	831.6	903.4	972.3	1076.1	1179.0	1227.9	1151.0	901.4	575.0
102.5°	1015.0	1027.0	1067.2	1118.3	1191.9	1262.2	1311.5	1281.4	1117.5	825.6	522.3
105°	1322.7	1334.7	1354.7	1387.6	1419.5	1430.5	1386.6	1249.8	1010.3	723.7	471.2
107.5°	1486.0	1494.0	1500.6	1500.8	1484.6	1432.5	1319.7	1137.2	900.8	653.7	449.6
110°	1540.3	1540.3	1533.3	1514.4	1469.5	1384.6	1243.8	1054.2	838.5	620.9	443.2



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1533.9	1526.8	1509.4	1476.8	1411.2	1311.1	1168.8	988.7	792.2	601.8	443.2
115°	1473.5	1460.5	1432.5	1384.6	1306.7	1197.9	1061.2	906.4	741.7	581.0	446.2
117.5°	1367.4	1359.4	1331.7	1282.2	1204.3	1104.5	986.7	853.3	711.6	570.8	452.8
120°	1298.8	1290.8	1263.8	1215.9	1142.0	1054.2	944.4	824.6	694.8	566.0	459.2
122.5°	1238.1	1230.9	1203.9	1160.0	1094.1	1011.8	914.0	803.0	680.4	562.0	464.8
125°	1161.0	1151.0	1129.0	1088.1	1032.2	960.3	873.5	771.7	660.9	557.0	474.2
127.5°	1095.1	1090.7	1069.9	1033.8	983.1	915.8	834.8	739.7	642.9	554.6	484.8
130°	1059.2	1053.2	1033.2	1000.3	950.4	885.5	807.6	719.8	630.9	553.0	491.2
132.5°	1023.2	1016.4	998.1	965.1	915.2	852.7	782.0	699.8	621.3	553.0	498.3
135°	964.3	958.3	940.4	907.4	863.5	806.6	742.7	673.8	609.9	553.0	508.1
137.5°	901.4	894.9	878.3	848.3	809.0	760.7	707.6	651.9	599.8	554.2	517.1
140°	857.5	852.5	837.6	811.6	774.7	732.7	686.8	639.9	595.0	555.0	521.1
142.5°	816.8	812.6	798.4	776.5	745.1	708.8	669.2	629.5	591.0	555.8	523.5
145°	760.7	756.7	745.7	728.7	704.8	677.8	646.9	615.9	585.0	555.0	526.1
147.5°	713.2	711.4	705.0	691.4	672.4	652.1	628.3	603.2	578.8	552.4	527.1
150°	686.8	685.8	681.8	669.8	654.9	636.9	617.9	596.0	574.0	550.0	527.1
152.5°	666.0	665.0	661.1	651.5	638.9	624.9	607.5	588.0	568.4	546.9	526.3
155°	637.9	636.9	633.9	626.9	616.9	606.0	592.0	576.0	559.0	541.1	524.1
157.5°	612.7	612.9	610.1	604.4	596.6	588.0	577.2	564.0	550.2	535.1	521.5
160°	596.0	597.0	595.0	590.0	583.0	576.0	566.0	556.0	543.1	531.1	519.1
162.5°	580.8	581.0	580.6	576.4	571.0	564.8	556.4	547.3	536.7	526.3	516.7
165°	559.0	559.0	559.0	557.0	553.0	548.1	542.1	535.1	527.1	519.1	513.1
167.5°	539.1	539.3	540.1	538.3	536.3	532.7	528.1	523.5	517.7	512.1	507.5
170°	527.1	528.1	528.1	527.1	525.1	523.1	520.1	517.1	512.1	508.1	505.1
172.5°	515.9	516.9	518.5	516.7	516.3	515.1	512.9	509.9	506.5	503.3	501.9
175°	502.1	503.1	505.1	504.1	504.1	504.1	502.1	502.1	499.1	498.1	498.1
177.5°	495.1	495.1	497.5	496.7	497.5	497.5	497.5	496.7	495.9	495.1	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	578.4	577.1	574.7	572.5	569.7	567.3	565.6	563.6	561.0	557.9	555.3
5°	604.0	598.9	592.2	586.4	579.0	573.3	567.3	561.5	555.7	548.3	541.8
7.5°	632.4	621.9	611.7	598.8	587.2	576.8	566.8	556.7	546.8	536.3	526.2
10°	649.8	637.0	623.0	606.8	592.0	577.9	565.0	552.2	538.8	527.1	514.4
12.5°	666.0	649.6	633.5	613.1	595.3	578.1	561.6	545.8	531.5	516.2	502.5
15°	680.7	664.5	646.5	621.6	596.8	576.0	556.6	536.1	518.3	501.2	485.9
17.5°	686.4	669.4	648.5	624.5	597.5	571.3	546.3	523.8	502.8	482.9	465.8
20°	684.2	667.8	646.3	623.4	594.5	567.3	540.2	515.3	491.9	470.9	452.7
22.5°	678.8	661.9	641.1	616.9	589.5	560.6	531.7	505.1	480.7	458.9	439.0
25°	670.8	647.7	626.4	602.8	576.7	548.1	518.3	488.9	462.8	440.6	418.9
27.5°	662.4	633.6	606.5	583.1	555.5	530.0	501.2	471.1	443.7	421.1	398.8
30°	654.8	622.5	592.7	566.1	540.0	515.7	488.5	459.1	430.9	407.6	385.0
32.5°	645.4	611.0	578.3	547.6	522.4	498.4	473.7	445.6	418.2	394.1	371.1
35°	633.6	589.7	554.1	521.5	493.6	470.2	448.0	425.4	397.9	372.9	350.5
37.5°	618.1	568.2	527.1	491.6	462.1	438.7	421.1	400.4	375.3	351.5	330.7
40°	608.6	552.7	507.7	472.5	441.6	416.8	400.4	382.9	360.0	337.6	316.8
42.5°	596.1	538.5	488.1	451.5	420.3	396.5	379.9	364.6	345.4	324.3	302.0
45°	571.4	510.9	458.0	418.7	387.3	363.9	348.4	334.8	320.3	300.8	281.4
47.5°	539.4	482.1	426.7	383.8	353.1	331.4	316.4	305.6	295.2	278.7	259.9
50°	513.7	458.4	404.4	362.8	330.0	309.4	295.3	286.8	277.3	262.3	246.5
52.5°	483.3	434.0	381.1	338.6	307.6	288.3	274.8	266.2	258.4	246.2	231.2
55°	435.6	392.3	343.8	305.2	276.8	257.4	244.5	236.4	231.8	221.4	209.6
57.5°	380.4	349.5	306.7	269.5	244.3	225.2	215.7	208.8	203.6	196.2	187.9
60°	342.0	320.3	281.9	246.5	223.4	205.2	196.6	190.9	186.0	179.8	173.3
62.5°	303.0	287.2	253.8	223.4	202.2	186.9	178.9	173.7	168.1	163.9	157.6
65°	250.7	236.6	213.5	189.7	170.1	157.8	152.0	147.4	144.0	139.3	134.9
67.5°	195.0	189.3	173.3	156.9	142.8	131.9	126.9	123.7	119.6	116.8	113.8
70°	160.8	158.0	146.7	135.9	122.7	115.3	110.7	109.3	104.2	101.4	99.4
72.5°	130.5	129.2	122.7	115.2	105.9	99.4	95.2	93.6	90.3	88.1	86.8
75°	89.4	89.9	88.7	83.9	80.4	76.3	72.6	71.6	69.3	67.5	66.3
77.5°	56.6	58.9	59.0	58.8	57.4	54.9	53.3	52.6	50.4	49.7	49.4
80°	38.8	41.4	43.7	43.4	43.0	42.3	41.1	40.4	39.3	38.6	38.1
82.5°	25.9	28.2	30.2	31.4	31.3	30.6	29.9	29.5	29.3	28.8	28.7
85°	12.2	12.7	13.4	15.0	16.2	16.4	16.2	15.9	15.3	15.5	15.7
87.5°	6.8	6.4	6.4	6.0	5.4	6.0	6.1	6.1	5.9	6.0	6.0
90°	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0	2.0	4.0	6.0
92.5°	227.8	136.4	81.9	52.7	35.5	23.2	14.8	12.2	14.8	23.2	35.5
95°	446.2	226.6	119.8	74.9	52.9	41.9	33.9	32.9	33.9	41.9	52.9
97.5°	356.2	195.3	124.6	92.2	72.5	61.5	55.9	54.7	55.9	61.5	72.5
100°	323.4	193.7	135.8	105.8	86.8	75.9	71.9	69.9	71.9	75.9	86.8
102.5°	309.9	200.9	149.3	120.2	102.8	91.0	87.8	86.7	87.8	91.0	102.8
105°	304.5	215.6	171.7	143.8	127.8	117.8	112.8	112.8	112.8	117.8	127.8
107.5°	313.7	237.6	195.1	169.9	153.3	145.1	140.4	138.4	140.4	145.1	153.3
110°	322.4	253.6	212.6	186.7	171.7	162.7	158.7	156.7	158.7	162.7	171.7





TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	333.6	268.7	229.4	204.2	189.3	180.3	177.1	175.1	177.1	180.3	189.3
115°	350.4	292.5	255.6	230.6	215.6	206.6	203.6	201.7	203.6	206.6	215.6
117.5°	369.6	316.9	281.9	257.8	240.8	231.8	228.6	225.6	228.6	231.8	240.8
120°	382.3	334.4	299.5	274.5	257.6	248.6	244.6	241.6	244.6	248.6	257.6
122.5°	396.7	351.2	316.3	291.3	272.7	263.7	260.5	258.4	260.5	263.7	272.7
125°	416.3	373.4	340.4	314.5	295.5	286.5	281.5	279.5	281.5	286.5	295.5
127.5°	434.2	394.7	363.0	337.0	316.9	305.5	299.1	296.1	299.1	305.5	316.9
130°	446.2	408.3	377.3	351.4	330.4	317.5	309.5	306.5	309.5	317.5	330.4
132.5°	456.6	421.1	390.1	364.2	342.4	327.8	318.2	314.5	318.2	327.8	342.4
135°	471.2	438.2	407.3	380.3	359.4	343.4	331.4	327.4	331.4	343.4	359.4
137.5°	482.0	450.4	422.3	394.5	374.0	358.0	346.8	343.8	346.8	358.0	374.0
140°	489.2	459.2	430.3	403.3	384.3	368.4	356.4	353.4	356.4	368.4	384.3
142.5°	493.1	464.8	437.4	412.1	393.9	377.9	366.8	364.6	366.8	377.9	393.9
145°	499.1	474.2	448.2	425.3	407.3	393.3	383.3	381.3	383.3	393.3	407.3
147.5°	502.7	480.2	457.4	437.2	421.7	408.7	400.1	398.9	400.1	408.7	421.7
150°	505.1	484.2	462.2	445.2	431.3	418.3	411.3	409.3	411.3	418.3	431.3
152.5°	506.7	488.2	467.8	452.4	439.2	427.9	421.7	420.5	421.7	427.9	439.2
155°	508.1	492.1	475.2	461.2	451.2	441.2	435.2	435.2	435.2	441.2	451.2
157.5°	509.1	495.5	481.0	470.4	461.6	453.0	448.2	448.4	448.2	453.0	461.6
160°	509.1	497.1	484.2	475.2	467.2	460.2	456.2	457.2	456.2	460.2	467.2
162.5°	508.3	498.7	487.4	480.0	473.6	467.4	463.4	464.4	463.4	467.4	473.6
165°	507.1	499.1	491.2	485.2	481.2	476.2	473.2	475.2	473.2	476.2	481.2
167.5°	504.7	499.1	492.5	488.8	486.0	483.2	481.4	482.4	481.4	483.2	486.0
170°	503.1	499.1	494.1	491.2	489.2	487.2	486.2	487.2	486.2	487.2	489.2
172.5°	501.5	498.3	494.1	492.7	491.5	489.6	488.6	490.4	488.6	489.6	491.5
175°	499.1	497.1	494.1	494.1	494.1	493.1	492.1	494.1	492.1	493.1	494.1
177.5°	496.7	495.9	494.3	494.3	495.1	494.3	494.3	495.9	494.3	494.3	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	553.4	550.9	549.0	545.3	542.7	541.6	539.6	539.0	541.1	539.6	539.4
5°	537.0	530.3	525.0	519.7	513.9	510.2	504.6	503.7	502.3	500.3	499.8
7.5°	517.3	508.5	501.7	492.9	485.3	479.1	472.2	468.9	467.1	464.4	460.8
10°	504.0	493.6	484.3	475.5	466.1	458.4	451.5	446.2	442.7	439.5	438.1
12.5°	490.8	480.2	468.4	457.8	447.2	438.7	431.0	427.5	423.7	419.9	416.7
15°	470.4	456.4	443.4	431.2	422.2	412.9	405.5	400.4	394.7	393.0	386.8
17.5°	448.8	435.0	419.8	407.0	396.5	386.3	378.2	372.4	368.1	362.1	359.3
20°	435.3	418.9	404.1	392.3	380.8	368.8	360.5	355.6	351.5	346.6	344.3
22.5°	420.9	404.9	389.7	375.9	364.2	352.3	346.4	341.4	336.7	332.2	329.1
25°	399.7	383.6	367.6	353.3	341.1	332.5	325.6	319.8	317.3	312.9	309.6
27.5°	378.8	361.6	345.1	330.8	321.2	312.7	307.0	302.5	297.9	294.1	291.2
30°	365.3	347.8	329.7	318.4	308.2	300.2	293.9	289.5	286.1	282.6	280.5
32.5°	351.8	333.7	317.7	305.5	295.9	288.9	282.5	278.2	274.6	270.8	268.3
35°	330.2	311.7	298.8	286.8	277.3	270.8	266.4	260.4	257.4	254.6	252.1
37.5°	310.1	292.9	278.9	268.4	260.1	253.7	248.0	244.8	241.1	238.6	236.5
40°	295.3	279.6	266.9	255.8	249.8	242.6	237.3	233.1	230.4	227.1	224.8
42.5°	282.0	267.4	255.0	245.1	237.6	231.5	226.4	222.2	218.7	216.4	214.5
45°	263.2	248.6	236.6	227.4	220.4	214.7	209.3	207.3	202.6	199.9	198.9
47.5°	243.7	230.7	219.1	210.6	203.5	198.0	193.0	188.8	186.2	183.5	182.0
50°	230.6	218.1	207.3	198.9	192.0	186.0	181.4	178.6	175.1	172.6	170.8
52.5°	217.5	205.9	195.1	187.1	181.1	175.1	169.9	167.2	163.9	162.3	161.0
55°	198.7	186.5	177.2	169.4	163.1	157.6	152.7	150.0	147.9	146.3	145.8
57.5°	177.5	167.8	159.2	152.1	145.6	140.4	136.1	133.5	131.7	131.4	130.0
60°	163.6	154.8	147.0	139.3	133.8	128.9	125.2	122.2	120.4	120.2	119.7
62.5°	149.7	141.3	134.0	127.3	122.3	117.7	114.1	110.8	109.7	108.5	107.5
65°	129.2	121.5	115.5	110.2	104.9	101.0	97.5	95.4	92.9	91.5	89.0
67.5°	109.0	103.1	97.3	92.8	88.6	84.9	82.0	78.9	77.2	76.1	74.3
70°	95.7	91.0	85.3	80.4	77.2	74.2	71.9	68.4	67.2	66.3	65.4
72.5°	83.1	79.0	74.2	70.2	67.0	64.2	61.5	59.9	58.7	57.8	57.3
75°	65.4	61.5	57.3	54.5	52.2	49.9	48.5	47.4	46.9	46.7	45.8
77.5°	48.0	45.9	42.6	40.4	38.9	37.9	36.7	36.1	36.0	35.0	34.7
80°	36.7	35.6	32.8	31.9	30.7	29.8	29.1	28.0	26.8	26.3	25.6
82.5°	27.3	26.2	25.0	23.6	22.6	22.0	21.4	20.9	21.1	20.4	20.1
85°	14.6	13.4	12.9	12.7	12.2	12.7	12.5	12.2	12.0	11.8	12.0
87.5°	6.2	6.6	6.6	7.4	7.0	7.6	7.8	7.8	8.0	8.2	8.5
90°	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0	19.0	20.0	22.0
92.5°	52.7	81.9	136.4	227.8	327.0	321.8	260.5	176.9	128.4	96.6	81.9
95°	74.9	119.8	226.6	446.2	721.8	884.5	865.5	717.8	566.0	443.2	359.4
97.5°	92.2	124.6	195.3	356.2	644.5	944.6	1095.1	1069.0	962.5	842.9	726.3
100°	105.8	135.8	193.7	323.4	575.0	901.4	1151.0	1227.9	1179.0	1076.1	972.3
102.5°	120.2	149.3	200.9	309.9	522.3	825.6	1117.5	1281.4	1311.5	1262.2	1191.9
105°	143.8	171.7	215.6	304.5	471.2	723.7	1010.3	1249.8	1386.6	1430.5	1419.5
107.5°	169.9	195.1	237.6	313.7	449.6	653.7	900.8	1137.2	1319.7	1432.5	1484.6
110°	186.7	212.6	253.6	322.4	443.2	620.9	838.5	1054.2	1243.8	1384.6	1469.5



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.2	229.4	268.7	333.6	443.2	601.8	792.2	988.7	1168.8	1311.1	1411.2
115°	230.6	255.6	292.5	350.4	446.2	581.0	741.7	906.4	1061.2	1197.9	1306.7
117.5°	257.8	281.9	316.9	369.6	452.8	570.8	711.6	853.3	986.7	1104.5	1204.3
120°	274.5	299.5	334.4	382.3	459.2	566.0	694.8	824.6	944.4	1054.2	1142.0
122.5°	291.3	316.3	351.2	396.7	464.8	562.0	680.4	803.0	914.0	1011.8	1094.1
125°	314.5	340.4	373.4	416.3	474.2	557.0	660.9	771.7	873.5	960.3	1032.2
127.5°	337.0	363.0	394.7	434.2	484.8	554.6	642.9	739.7	834.8	915.8	983.1
130°	351.4	377.3	408.3	446.2	491.2	553.0	630.9	719.8	807.6	885.5	950.4
132.5°	364.2	390.1	421.1	456.6	498.3	553.0	621.3	699.8	782.0	852.7	915.2
135°	380.3	407.3	438.2	471.2	508.1	553.0	609.9	673.8	742.7	806.6	863.5
137.5°	394.5	422.3	450.4	482.0	517.1	554.2	599.8	651.9	707.6	760.7	809.0
140°	403.3	430.3	459.2	489.2	521.1	555.0	595.0	639.9	686.8	732.7	774.7
142.5°	412.1	437.4	464.8	493.1	523.5	555.8	591.0	629.5	669.2	708.8	745.1
145°	425.3	448.2	474.2	499.1	526.1	555.0	585.0	615.9	646.9	677.8	704.8
147.5°	437.2	457.4	480.2	502.7	527.1	552.4	578.8	603.2	628.3	652.1	672.4
150°	445.2	462.2	484.2	505.1	527.1	550.0	574.0	596.0	617.9	636.9	654.9
152.5°	452.4	467.8	488.2	506.7	526.3	546.9	568.4	588.0	607.5	624.9	638.9
155°	461.2	475.2	492.1	508.1	524.1	541.1	559.0	576.0	592.0	606.0	616.9
157.5°	470.4	481.0	495.5	509.1	521.5	535.1	550.2	564.0	577.2	588.0	596.6
160°	475.2	484.2	497.1	509.1	519.1	531.1	543.1	556.0	566.0	576.0	583.0
162.5°	480.0	487.4	498.7	508.3	516.7	526.3	536.7	547.3	556.4	564.8	571.0
165°	485.2	491.2	499.1	507.1	513.1	519.1	527.1	535.1	542.1	548.1	553.0
167.5°	488.8	492.5	499.1	504.7	507.5	512.1	517.7	523.5	528.1	532.7	536.3
170°	491.2	494.1	499.1	503.1	505.1	508.1	512.1	517.1	520.1	523.1	525.1
172.5°	492.7	494.1	498.3	501.5	501.9	503.3	506.5	509.9	512.9	515.1	516.3
175°	494.1	494.1	497.1	499.1	498.1	498.1	499.1	502.1	502.1	504.1	504.1
177.5°	494.3	494.3	495.9	496.7	495.1	495.1	495.9	496.7	497.5	497.5	497.5
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.2	537.2	536.6	537.4	536.6	537.2	539.2	539.4	539.6	541.1	539.0
5°	497.5	495.2	496.3	495.9	496.3	495.2	497.5	499.8	500.3	502.3	503.7
7.5°	460.8	457.9	454.9	455.8	454.9	457.9	460.8	460.8	464.4	467.1	468.9
10°	435.1	432.8	431.4	432.6	431.4	432.8	435.1	438.1	439.5	442.7	446.2
12.5°	413.5	412.1	410.9	410.4	410.9	412.1	413.5	416.7	419.9	423.7	427.5
15°	384.0	381.3	380.1	377.1	380.1	381.3	384.0	386.8	393.0	394.7	400.4
17.5°	356.9	356.0	353.0	351.7	353.0	356.0	356.9	359.3	362.1	368.1	372.4
20°	340.8	339.9	336.9	338.7	336.9	339.9	340.8	344.3	346.6	351.5	355.6
22.5°	327.5	325.5	324.5	324.0	324.5	325.5	327.5	329.1	332.2	336.7	341.4
25°	308.7	305.7	304.5	303.2	304.5	305.7	308.7	309.6	312.9	317.3	319.8
27.5°	289.9	288.3	286.8	286.4	286.8	288.3	289.9	291.2	294.1	297.9	302.5
30°	277.7	276.1	275.0	275.0	275.0	276.1	277.7	280.5	282.6	286.1	289.5
32.5°	266.8	265.6	264.4	264.2	264.4	265.6	266.8	268.3	270.8	274.6	278.2
35°	250.9	249.1	248.6	247.2	248.6	249.1	250.9	252.1	254.6	257.4	260.4
37.5°	234.4	232.9	232.9	232.7	232.9	232.9	234.4	236.5	238.6	241.1	244.8
40°	223.9	222.7	222.5	220.9	222.5	222.7	223.9	224.8	227.1	230.4	233.1
42.5°	212.6	212.0	211.2	210.5	211.2	212.0	212.6	214.5	216.4	218.7	222.2
45°	197.3	195.7	195.7	194.6	195.7	195.7	197.3	198.9	199.9	202.6	207.3
47.5°	181.5	180.3	180.4	179.2	180.4	180.3	181.5	182.0	183.5	186.2	188.8
50°	171.0	170.3	170.1	169.6	170.1	170.3	171.0	170.8	172.6	175.1	178.6
52.5°	160.5	160.1	161.0	160.0	161.0	160.1	160.5	161.0	162.3	163.9	167.2
55°	146.3	145.6	147.0	145.6	147.0	145.6	146.3	145.8	146.3	147.9	150.0
57.5°	130.0	129.3	130.6	129.9	130.6	129.3	130.0	130.0	131.4	131.7	133.5
60°	119.2	117.8	118.5	118.8	118.5	117.8	119.2	119.7	120.2	120.4	122.2
62.5°	106.5	105.6	106.2	105.1	106.2	105.6	106.5	107.5	108.5	109.7	110.8
65°	88.5	87.8	86.9	86.4	86.9	87.8	88.5	89.0	91.5	92.9	95.4
67.5°	74.4	72.7	72.6	73.0	72.6	72.7	74.4	74.3	76.1	77.2	78.9
70°	64.0	64.0	63.8	63.8	63.8	64.0	64.0	65.4	66.3	67.2	68.4
72.5°	56.8	56.6	56.2	56.0	56.2	56.6	56.8	57.3	57.8	58.7	59.9
75°	45.8	46.0	45.5	45.3	45.5	46.0	45.8	45.8	46.7	46.9	47.4
77.5°	33.8	32.8	33.3	32.8	33.3	32.8	33.8	34.7	35.0	36.0	36.1
80°	25.6	25.4	26.1	25.4	26.1	25.4	25.6	25.6	26.3	26.8	28.0
82.5°	20.3	20.1	20.4	19.9	20.4	20.1	20.3	20.1	20.4	21.1	20.9
85°	12.2	12.0	11.8	12.0	11.8	12.0	12.2	12.0	11.8	12.0	12.2
87.5°	8.6	8.5	8.7	8.7	8.7	8.5	8.6	8.5	8.2	8.0	7.8
90°	22.0	22.0	23.0	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0
92.5°	69.1	66.7	65.3	63.7	65.3	66.7	69.1	81.9	96.6	128.4	176.9
95°	288.5	258.6	250.6	234.6	250.6	258.6	288.5	359.4	443.2	566.0	717.8
97.5°	664.7	608.7	579.8	567.0	579.8	608.7	664.7	726.3	842.9	962.5	1069.0
100°	903.4	831.6	794.6	778.7	794.6	831.6	903.4	972.3	1076.1	1179.0	1227.9
102.5°	1118.3	1067.2	1027.0	1015.0	1027.0	1067.2	1118.3	1191.9	1262.2	1311.5	1281.4
105°	1387.6	1354.7	1334.7	1322.7	1334.7	1354.7	1387.6	1419.5	1430.5	1386.6	1249.8
107.5°	1500.8	1500.6	1494.0	1486.0	1494.0	1500.6	1500.8	1484.6	1432.5	1319.7	1137.2
110°	1514.4	1533.3	1540.3	1540.3	1540.3	1533.3	1514.4	1469.5	1384.6	1243.8	1054.2



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1476.8	1509.4	1526.8	1533.9	1526.8	1509.4	1476.8	1411.2	1311.1	1168.8	988.7
115°	1384.6	1432.5	1460.5	1473.5	1460.5	1432.5	1384.6	1306.7	1197.9	1061.2	906.4
117.5°	1282.2	1331.7	1359.4	1367.4	1359.4	1331.7	1282.2	1204.3	1104.5	986.7	853.3
120°	1215.9	1263.8	1290.8	1298.8	1290.8	1263.8	1215.9	1142.0	1054.2	944.4	824.6
122.5°	1160.0	1203.9	1230.9	1238.1	1230.9	1203.9	1160.0	1094.1	1011.8	914.0	803.0
125°	1088.1	1129.0	1151.0	1161.0	1151.0	1129.0	1088.1	1032.2	960.3	873.5	771.7
127.5°	1033.8	1069.9	1090.7	1095.1	1090.7	1069.9	1033.8	983.1	915.8	834.8	739.7
130°	1000.3	1033.2	1053.2	1059.2	1053.2	1033.2	1000.3	950.4	885.5	807.6	719.8
132.5°	965.1	998.1	1016.4	1023.2	1016.4	998.1	965.1	915.2	852.7	782.0	699.8
135°	907.4	940.4	958.3	964.3	958.3	940.4	907.4	863.5	806.6	742.7	673.8
137.5°	848.3	878.3	894.9	901.4	894.9	878.3	848.3	809.0	760.7	707.6	651.9
140°	811.6	837.6	852.5	857.5	852.5	837.6	811.6	774.7	732.7	686.8	639.9
142.5°	776.5	798.4	812.6	816.8	812.6	798.4	776.5	745.1	708.8	669.2	629.5
145°	728.7	745.7	756.7	760.7	756.7	745.7	728.7	704.8	677.8	646.9	615.9
147.5°	691.4	705.0	711.4	713.2	711.4	705.0	691.4	672.4	652.1	628.3	603.2
150°	669.8	681.8	685.8	686.8	685.8	681.8	669.8	654.9	636.9	617.9	596.0
152.5°	651.5	661.1	665.0	666.0	665.0	661.1	651.5	638.9	624.9	607.5	588.0
155°	626.9	633.9	636.9	637.9	636.9	633.9	626.9	616.9	606.0	592.0	576.0
157.5°	604.4	610.1	612.9	612.7	612.9	610.1	604.4	596.6	588.0	577.2	564.0
160°	590.0	595.0	597.0	596.0	597.0	595.0	590.0	583.0	576.0	566.0	556.0
162.5°	576.4	580.6	581.0	580.8	581.0	580.6	576.4	571.0	564.8	556.4	547.3
165°	557.0	559.0	559.0	559.0	559.0	559.0	557.0	553.0	548.1	542.1	535.1
167.5°	538.3	540.1	539.3	539.1	539.3	540.1	538.3	536.3	532.7	528.1	523.5
170°	527.1	528.1	528.1	527.1	528.1	528.1	527.1	525.1	523.1	520.1	517.1
172.5°	516.7	518.5	516.9	515.9	516.9	518.5	516.7	516.3	515.1	512.9	509.9
175°	504.1	505.1	503.1	502.1	503.1	505.1	504.1	504.1	504.1	502.1	502.1
177.5°	496.7	497.5	495.1	495.1	495.1	497.5	496.7	497.5	497.5	497.5	496.7
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.6	541.6	542.7	545.3	549.0	550.9	553.4	555.3	557.9	561.0	563.6
5°	504.6	510.2	513.9	519.7	525.0	530.3	537.0	541.8	548.3	555.7	561.5
7.5°	472.2	479.1	485.3	492.9	501.7	508.5	517.3	526.2	536.3	546.8	556.7
10°	451.5	458.4	466.1	475.5	484.3	493.6	504.0	514.4	527.1	538.8	552.2
12.5°	431.0	438.7	447.2	457.8	468.4	480.2	490.8	502.5	516.2	531.5	545.8
15°	405.5	412.9	422.2	431.2	443.4	456.4	470.4	485.9	501.2	518.3	536.1
17.5°	378.2	386.3	396.5	407.0	419.8	435.0	448.8	465.8	482.9	502.8	523.8
20°	360.5	368.8	380.8	392.3	404.1	418.9	435.3	452.7	470.9	491.9	515.3
22.5°	346.4	352.3	364.2	375.9	389.7	404.9	420.9	439.0	458.9	480.7	505.1
25°	325.6	332.5	341.1	353.3	367.6	383.6	399.7	418.9	440.6	462.8	488.9
27.5°	307.0	312.7	321.2	330.8	345.1	361.6	378.8	398.8	421.1	443.7	471.1
30°	293.9	300.2	308.2	318.4	329.7	347.8	365.3	385.0	407.6	430.9	459.1
32.5°	282.5	288.9	295.9	305.5	317.7	333.7	351.8	371.1	394.1	418.2	445.6
35°	266.4	270.8	277.3	286.8	298.8	311.7	330.2	350.5	372.9	397.9	425.4
37.5°	248.0	253.7	260.1	268.4	278.9	292.9	310.1	330.7	351.5	375.3	400.4
40°	237.3	242.6	249.8	255.8	266.9	279.6	295.3	316.8	337.6	360.0	382.9
42.5°	226.4	231.5	237.6	245.1	255.0	267.4	282.0	302.0	324.3	345.4	364.6
45°	209.3	214.7	220.4	227.4	236.6	248.6	263.2	281.4	300.8	320.3	334.8
47.5°	193.0	198.0	203.5	210.6	219.1	230.7	243.7	259.9	278.7	295.2	305.6
50°	181.4	186.0	192.0	198.9	207.3	218.1	230.6	246.5	262.3	277.3	286.8
52.5°	169.9	175.1	181.1	187.1	195.1	205.9	217.5	231.2	246.2	258.4	266.2
55°	152.7	157.6	163.1	169.4	177.2	186.5	198.7	209.6	221.4	231.8	236.4
57.5°	136.1	140.4	145.6	152.1	159.2	167.8	177.5	187.9	196.2	203.6	208.8
60°	125.2	128.9	133.8	139.3	147.0	154.8	163.6	173.3	179.8	186.0	190.9
62.5°	114.1	117.7	122.3	127.3	134.0	141.3	149.7	157.6	163.9	168.1	173.7
65°	97.5	101.0	104.9	110.2	115.5	121.5	129.2	134.9	139.3	144.0	147.4
67.5°	82.0	84.9	88.6	92.8	97.3	103.1	109.0	113.8	116.8	119.6	123.7
70°	71.9	74.2	77.2	80.4	85.3	91.0	95.7	99.4	101.4	104.2	109.3
72.5°	61.5	64.2	67.0	70.2	74.2	79.0	83.1	86.8	88.1	90.3	93.6
75°	48.5	49.9	52.2	54.5	57.3	61.5	65.4	66.3	67.5	69.3	71.6
77.5°	36.7	37.9	38.9	40.4	42.6	45.9	48.0	49.4	49.7	50.4	52.6
80°	29.1	29.8	30.7	31.9	32.8	35.6	36.7	38.1	38.6	39.3	40.4
82.5°	21.4	22.0	22.6	23.6	25.0	26.2	27.3	28.7	28.8	29.3	29.5
85°	12.5	12.7	12.2	12.7	12.9	13.4	14.6	15.7	15.5	15.3	15.9
87.5°	7.8	7.6	7.0	7.4	6.6	6.6	6.2	6.0	6.0	5.9	6.1
90°	17.0	16.0	14.0	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0
92.5°	260.5	321.8	327.0	227.8	136.4	81.9	52.7	35.5	23.2	14.8	12.2
95°	865.5	884.5	721.8	446.2	226.6	119.8	74.9	52.9	41.9	33.9	32.9
97.5°	1095.1	944.6	644.5	356.2	195.3	124.6	92.2	72.5	61.5	55.9	54.7
100°	1151.0	901.4	575.0	323.4	193.7	135.8	105.8	86.8	75.9	71.9	69.9
102.5°	1117.5	825.6	522.3	309.9	200.9	149.3	120.2	102.8	91.0	87.8	86.7
105°	1010.3	723.7	471.2	304.5	215.6	171.7	143.8	127.8	117.8	112.8	112.8
107.5°	900.8	653.7	449.6	313.7	237.6	195.1	169.9	153.3	145.1	140.4	138.4
110°	838.5	620.9	443.2	322.4	253.6	212.6	186.7	171.7	162.7	158.7	156.7



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	792.2	601.8	443.2	333.6	268.7	229.4	204.2	189.3	180.3	177.1	175.1
115°	741.7	581.0	446.2	350.4	292.5	255.6	230.6	215.6	206.6	203.6	201.7
117.5°	711.6	570.8	452.8	369.6	316.9	281.9	257.8	240.8	231.8	228.6	225.6
120°	694.8	566.0	459.2	382.3	334.4	299.5	274.5	257.6	248.6	244.6	241.6
122.5°	680.4	562.0	464.8	396.7	351.2	316.3	291.3	272.7	263.7	260.5	258.4
125°	660.9	557.0	474.2	416.3	373.4	340.4	314.5	295.5	286.5	281.5	279.5
127.5°	642.9	554.6	484.8	434.2	394.7	363.0	337.0	316.9	305.5	299.1	296.1
130°	630.9	553.0	491.2	446.2	408.3	377.3	351.4	330.4	317.5	309.5	306.5
132.5°	621.3	553.0	498.3	456.6	421.1	390.1	364.2	342.4	327.8	318.2	314.5
135°	609.9	553.0	508.1	471.2	438.2	407.3	380.3	359.4	343.4	331.4	327.4
137.5°	599.8	554.2	517.1	482.0	450.4	422.3	394.5	374.0	358.0	346.8	343.8
140°	595.0	555.0	521.1	489.2	459.2	430.3	403.3	384.3	368.4	356.4	353.4
142.5°	591.0	555.8	523.5	493.1	464.8	437.4	412.1	393.9	377.9	366.8	364.6
145°	585.0	555.0	526.1	499.1	474.2	448.2	425.3	407.3	393.3	383.3	381.3
147.5°	578.8	552.4	527.1	502.7	480.2	457.4	437.2	421.7	408.7	400.1	398.9
150°	574.0	550.0	527.1	505.1	484.2	462.2	445.2	431.3	418.3	411.3	409.3
152.5°	568.4	546.9	526.3	506.7	488.2	467.8	452.4	439.2	427.9	421.7	420.5
155°	559.0	541.1	524.1	508.1	492.1	475.2	461.2	451.2	441.2	435.2	435.2
157.5°	550.2	535.1	521.5	509.1	495.5	481.0	470.4	461.6	453.0	448.2	448.4
160°	543.1	531.1	519.1	509.1	497.1	484.2	475.2	467.2	460.2	456.2	457.2
162.5°	536.7	526.3	516.7	508.3	498.7	487.4	480.0	473.6	467.4	463.4	464.4
165°	527.1	519.1	513.1	507.1	499.1	491.2	485.2	481.2	476.2	473.2	475.2
167.5°	517.7	512.1	507.5	504.7	499.1	492.5	488.8	486.0	483.2	481.4	482.4
170°	512.1	508.1	505.1	503.1	499.1	494.1	491.2	489.2	487.2	486.2	487.2
172.5°	506.5	503.3	501.9	501.5	498.3	494.1	492.7	491.5	489.6	488.6	490.4
175°	499.1	498.1	498.1	499.1	497.1	494.1	494.1	494.1	493.1	492.1	494.1
177.5°	495.9	495.1	495.1	496.7	495.9	494.3	494.3	495.1	494.3	494.3	495.9
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	565.6	567.3	569.7	572.5	574.7	577.1	578.4	578.4	579.5	581.9	585.1
5°	567.3	573.3	579.0	586.4	592.2	598.9	604.0	608.9	613.2	618.8	624.6
7.5°	566.8	576.8	587.2	598.8	611.7	621.9	632.4	640.6	648.7	659.4	667.7
10°	565.0	577.9	592.0	606.8	623.0	637.0	649.8	661.3	672.4	684.0	694.4
12.5°	561.6	578.1	595.3	613.1	633.5	649.6	666.0	678.3	691.3	703.9	716.7
15°	556.6	576.0	596.8	621.6	646.5	664.5	680.7	696.7	708.7	723.0	735.3
17.5°	546.3	571.3	597.5	624.5	648.5	669.4	686.4	701.6	714.4	730.1	746.8
20°	540.2	567.3	594.5	623.4	646.3	667.8	684.2	699.9	715.8	736.4	756.7
22.5°	531.7	560.6	589.5	616.9	641.1	661.9	678.8	698.0	719.0	742.3	766.9
25°	518.3	548.1	576.7	602.8	626.4	647.7	670.8	696.7	722.1	752.8	788.2
27.5°	501.2	530.0	555.5	583.1	606.5	633.6	662.4	690.5	727.1	769.4	813.5
30°	488.5	515.7	540.0	566.1	592.7	622.5	654.8	687.9	731.6	781.2	833.7
32.5°	473.7	498.4	522.4	547.6	578.3	611.0	645.4	685.8	738.0	794.5	848.8
35°	448.0	470.2	493.6	521.5	554.1	589.7	633.6	682.8	745.9	806.6	855.4
37.5°	421.1	438.7	462.1	491.6	527.1	568.2	618.1	677.9	742.6	797.2	817.9
40°	400.4	416.8	441.6	472.5	507.7	552.7	608.6	670.1	735.3	773.1	771.5
42.5°	379.9	396.5	420.3	451.5	488.1	538.5	596.1	659.9	714.9	729.3	699.3
45°	348.4	363.9	387.3	418.7	458.0	510.9	571.4	632.7	667.8	644.4	584.8
47.5°	316.4	331.4	353.1	383.8	426.7	482.1	539.4	589.6	594.5	544.4	472.9
50°	295.3	309.4	330.0	362.8	404.4	458.4	513.7	553.2	540.9	479.7	406.0
52.5°	274.8	288.3	307.6	338.6	381.1	434.0	483.3	514.4	486.0	420.9	354.6
55°	244.5	257.4	276.8	305.2	343.8	392.3	435.6	446.9	405.3	339.7	286.1
57.5°	215.7	225.2	244.3	269.5	306.7	349.5	380.4	378.4	332.5	273.4	234.9
60°	196.6	205.2	223.4	246.5	281.9	320.3	342.0	332.7	286.3	237.5	200.6
62.5°	178.9	186.9	202.2	223.4	253.8	287.2	303.0	290.2	246.4	203.5	174.1
65°	152.0	157.8	170.1	189.7	213.5	236.6	250.7	232.0	193.2	160.8	138.6
67.5°	126.9	131.9	142.8	156.9	173.3	189.3	195.0	177.5	147.3	125.5	109.8
70°	110.7	115.3	122.7	135.9	146.7	158.0	160.8	145.1	119.9	103.3	93.6
72.5°	95.2	99.4	105.9	115.2	122.7	129.2	130.5	115.9	96.6	85.2	77.7
75°	72.6	76.3	80.4	83.9	88.7	89.9	89.4	78.1	67.7	60.1	55.9
77.5°	53.3	54.9	57.4	58.8	59.0	58.9	56.6	49.4	44.0	40.9	39.2
80°	41.1	42.3	43.0	43.4	43.7	41.4	38.8	34.4	32.6	30.7	28.7
82.5°	29.9	30.6	31.3	31.4	30.2	28.2	25.9	23.7	22.4	21.5	20.7
85°	16.2	16.4	16.2	15.0	13.4	12.7	12.2	11.8	11.6	11.3	11.3
87.5°	6.1	6.0	5.4	6.0	6.4	6.4	6.8	6.9	7.1	7.3	7.5
90°	2.0	4.0	6.0	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0
92.5°	14.8	23.2	35.5	52.7	81.9	136.4	227.8	327.0	321.8	260.5	176.9
95°	33.9	41.9	52.9	74.9	119.8	226.6	446.2	721.8	884.5	865.5	717.8
97.5°	55.9	61.5	72.5	92.2	124.6	195.3	356.2	644.5	944.6	1095.1	1069.0
100°	71.9	75.9	86.8	105.8	135.8	193.7	323.4	575.0	901.4	1151.0	1227.9
102.5°	87.8	91.0	102.8	120.2	149.3	200.9	309.9	522.3	825.6	1117.5	1281.4
105°	112.8	117.8	127.8	143.8	171.7	215.6	304.5	471.2	723.7	1010.3	1249.8
107.5°	140.4	145.1	153.3	169.9	195.1	237.6	313.7	449.6	653.7	900.8	1137.2
110°	158.7	162.7	171.7	186.7	212.6	253.6	322.4	443.2	620.9	838.5	1054.2





TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	177.1	180.3	189.3	204.2	229.4	268.7	333.6	443.2	601.8	792.2	988.7
115°	203.6	206.6	215.6	230.6	255.6	292.5	350.4	446.2	581.0	741.7	906.4
117.5°	228.6	231.8	240.8	257.8	281.9	316.9	369.6	452.8	570.8	711.6	853.3
120°	244.6	248.6	257.6	274.5	299.5	334.4	382.3	459.2	566.0	694.8	824.6
122.5°	260.5	263.7	272.7	291.3	316.3	351.2	396.7	464.8	562.0	680.4	803.0
125°	281.5	286.5	295.5	314.5	340.4	373.4	416.3	474.2	557.0	660.9	771.7
127.5°	299.1	305.5	316.9	337.0	363.0	394.7	434.2	484.8	554.6	642.9	739.7
130°	309.5	317.5	330.4	351.4	377.3	408.3	446.2	491.2	553.0	630.9	719.8
132.5°	318.2	327.8	342.4	364.2	390.1	421.1	456.6	498.3	553.0	621.3	699.8
135°	331.4	343.4	359.4	380.3	407.3	438.2	471.2	508.1	553.0	609.9	673.8
137.5°	346.8	358.0	374.0	394.5	422.3	450.4	482.0	517.1	554.2	599.8	651.9
140°	356.4	368.4	384.3	403.3	430.3	459.2	489.2	521.1	555.0	595.0	639.9
142.5°	366.8	377.9	393.9	412.1	437.4	464.8	493.1	523.5	555.8	591.0	629.5
145°	383.3	393.3	407.3	425.3	448.2	474.2	499.1	526.1	555.0	585.0	615.9
147.5°	400.1	408.7	421.7	437.2	457.4	480.2	502.7	527.1	552.4	578.8	603.2
150°	411.3	418.3	431.3	445.2	462.2	484.2	505.1	527.1	550.0	574.0	596.0
152.5°	421.7	427.9	439.2	452.4	467.8	488.2	506.7	526.3	546.9	568.4	588.0
155°	435.2	441.2	451.2	461.2	475.2	492.1	508.1	524.1	541.1	559.0	576.0
157.5°	448.2	453.0	461.6	470.4	481.0	495.5	509.1	521.5	535.1	550.2	564.0
160°	456.2	460.2	467.2	475.2	484.2	497.1	509.1	519.1	531.1	543.1	556.0
162.5°	463.4	467.4	473.6	480.0	487.4	498.7	508.3	516.7	526.3	536.7	547.3
165°	473.2	476.2	481.2	485.2	491.2	499.1	507.1	513.1	519.1	527.1	535.1
167.5°	481.4	483.2	486.0	488.8	492.5	499.1	504.7	507.5	512.1	517.7	523.5
170°	486.2	487.2	489.2	491.2	494.1	499.1	503.1	505.1	508.1	512.1	517.1
172.5°	488.6	489.6	491.5	492.7	494.1	498.3	501.5	501.9	503.3	506.5	509.9
175°	492.1	493.1	494.1	494.1	494.1	497.1	499.1	498.1	498.1	499.1	502.1
177.5°	494.3	494.3	495.1	494.3	494.3	495.9	496.7	495.1	495.1	495.9	496.7
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	587.5	587.5	590.6	590.4	592.5	591.7	592.1
5°	631.5	635.4	638.9	641.2	644.7	645.6	645.1
7.5°	677.2	685.9	690.1	696.0	697.0	700.1	699.8
10°	705.4	714.0	720.5	725.5	728.1	731.3	731.6
12.5°	727.6	734.9	740.6	745.3	748.4	749.4	750.0
15°	745.0	753.0	759.7	766.4	770.4	773.4	775.0
17.5°	762.4	774.9	786.7	795.8	801.3	805.9	805.9
20°	775.9	790.2	805.0	815.4	826.1	830.7	831.4
22.5°	790.3	812.2	831.3	847.4	861.4	866.2	868.0
25°	820.3	848.9	878.3	900.9	917.1	926.6	928.0
27.5°	856.5	895.2	926.1	947.0	960.4	967.5	969.0
30°	882.0	917.8	945.5	961.2	967.5	968.4	964.9
32.5°	893.4	920.2	931.3	930.4	918.1	910.0	906.9
35°	879.4	873.9	846.9	814.5	789.8	774.1	769.9
37.5°	800.3	752.5	702.8	653.9	627.9	614.6	591.9
40°	722.3	654.1	602.4	561.3	531.9	508.3	502.8
42.5°	634.3	563.9	512.2	477.0	453.5	437.4	430.3
45°	509.7	449.2	406.4	379.4	361.4	349.6	344.3
47.5°	407.7	360.8	329.7	309.7	295.9	285.7	282.8
50°	351.7	314.2	287.9	271.0	260.6	252.8	249.6
52.5°	305.5	275.2	255.0	241.1	231.3	226.4	223.7
55°	252.1	226.0	211.4	200.3	194.8	190.9	189.0
57.5°	206.2	187.3	176.7	169.0	163.9	161.4	160.5
60°	180.5	165.7	156.0	150.0	146.5	143.3	142.3
62.5°	157.7	146.1	138.6	133.3	129.9	128.5	127.9
65°	127.1	119.5	113.9	110.7	107.9	107.4	107.2
67.5°	101.0	96.5	93.6	90.3	89.3	87.7	87.3
70°	86.4	83.4	79.9	78.8	77.6	76.0	76.3
72.5°	73.3	70.3	67.9	66.4	66.0	65.3	65.9
75°	53.6	52.7	51.8	50.6	50.1	50.1	49.9
77.5°	38.3	37.5	36.5	35.8	35.6	34.7	35.0
80°	27.7	26.6	26.1	26.3	25.6	25.4	25.4
82.5°	20.5	20.1	19.6	19.7	19.5	19.3	19.5
85°	11.3	11.1	11.1	10.9	10.9	10.6	10.6
87.5°	7.9	8.2	8.3	8.1	8.1	8.5	8.7
90°	19.0	20.0	22.0	22.0	22.0	23.0	23.0
92.5°	128.4	96.6	81.9	69.1	66.7	65.3	63.7
95°	566.0	443.2	359.4	288.5	258.6	250.6	234.6
97.5°	962.5	842.9	726.3	664.7	608.7	579.8	567.0
100°	1179.0	1076.1	972.3	903.4	831.6	794.6	778.7
102.5°	1311.5	1262.2	1191.9	1118.3	1067.2	1027.0	1015.0
105°	1386.6	1430.5	1419.5	1387.6	1354.7	1334.7	1322.7
107.5°	1319.7	1432.5	1484.6	1500.8	1500.6	1494.0	1486.0
110°	1243.8	1384.6	1469.5	1514.4	1533.3	1540.3	1540.3



TEST NUMBER: P333510

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1168.8	1311.1	1411.2	1476.8	1509.4	1526.8	1533.9
115°	1061.2	1197.9	1306.7	1384.6	1432.5	1460.5	1473.5
117.5°	986.7	1104.5	1204.3	1282.2	1331.7	1359.4	1367.4
120°	944.4	1054.2	1142.0	1215.9	1263.8	1290.8	1298.8
122.5°	914.0	1011.8	1094.1	1160.0	1203.9	1230.9	1238.1
125°	873.5	960.3	1032.2	1088.1	1129.0	1151.0	1161.0
127.5°	834.8	915.8	983.1	1033.8	1069.9	1090.7	1095.1
130°	807.6	885.5	950.4	1000.3	1033.2	1053.2	1059.2
132.5°	782.0	852.7	915.2	965.1	998.1	1016.4	1023.2
135°	742.7	806.6	863.5	907.4	940.4	958.3	964.3
137.5°	707.6	760.7	809.0	848.3	878.3	894.9	901.4
140°	686.8	732.7	774.7	811.6	837.6	852.5	857.5
142.5°	669.2	708.8	745.1	776.5	798.4	812.6	816.8
145°	646.9	677.8	704.8	728.7	745.7	756.7	760.7
147.5°	628.3	652.1	672.4	691.4	705.0	711.4	713.2
150°	617.9	636.9	654.9	669.8	681.8	685.8	686.8
152.5°	607.5	624.9	638.9	651.5	661.1	665.0	666.0
155°	592.0	606.0	616.9	626.9	633.9	636.9	637.9
157.5°	577.2	588.0	596.6	604.4	610.1	612.9	612.7
160°	566.0	576.0	583.0	590.0	595.0	597.0	596.0
162.5°	556.4	564.8	571.0	576.4	580.6	581.0	580.8
165°	542.1	548.1	553.0	557.0	559.0	559.0	559.0
167.5°	528.1	532.7	536.3	538.3	540.1	539.3	539.1
170°	520.1	523.1	525.1	527.1	528.1	528.1	527.1
172.5°	512.9	515.1	516.3	516.7	518.5	516.9	515.9
175°	502.1	504.1	504.1	504.1	505.1	503.1	502.1
177.5°	497.5	497.5	497.5	496.7	497.5	495.1	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1

(END OF REPORT)