

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333516

Luminaire Tested: **S125RDIP-S375D1205U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333516
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D1205U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5783.5 lumens
Efficiency: N/A
Efficacy: 137.1 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25					25			
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22					22			
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	26	25	24	18					18			
3	77	68	61	56	68	61	55	50	48	44	40	35	33	30	24	22	21	16					16			
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	14					14			
5	65	54	46	40	57	48	41	37	38	33	30	28	25	23	19	17	16	12					12			
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14	11					11			
7	55	43	36	30	49	39	32	28	31	26	22	23	20	17	16	14	12	9					9			
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	13	11	8					8			
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8					8			
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7					7			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3635	3635	3635	3635
5°	4182	3640	3215	3640
10°	4798	3621	2837	3621
15°	5182	3584	2521	3584
20°	5714	3542	2328	3542
25°	6613	3484	2161	3484
30°	7196	3424	2051	3424
35°	6070	3354	1949	3354
40°	4239	3228	1862	3228
45°	3145	3058	1777	3058
50°	2508	2882	1704	2882
55°	2128	2662	1639	2662
60°	1838	2466	1535	2466
65°	1638	2253	1320	2253
70°	1441	2064	1205	2064
75°	1245	1787	1130	1787
80°	945	1503	945	1503
85°	785	1178	889	1178



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	0.9
10°-20°	158.2	2.7
20°-30°	250.8	4.3
30°-40°	302.5	5.2
40°-50°	270.1	4.7
50°-60°	207.1	3.6
60°-70°	134.6	2.3
70°-80°	65.4	1.1
80°-90°	18.8	0.3
90°-100°	417.8	7.2
100°-110°	898.0	15.5
110°-120°	842.8	14.6
120°-130°	683.0	11.8
130°-140°	548.1	9.5
140°-150°	413.6	7.2
150°-160°	291.2	5.0
160°-170°	171.6	3.0
170°-180°	55.8	1.0
0°-30°	463.0	8.0
0°-40°	765.4	13.2
0°-60°	1242.7	21.5
0°-90°	1461.5	25.3
90°-120°	2158.6	37.3
90°-150°	3803.4	65.8
90°-180°	4322.0	74.7
0°-180°	5783.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	645	562	496	562	645	64
15°	775	536	377	536	775	222
25°	928	489	303	489	928	426
35°	770	425	247	425	770	465
45°	344	335	195	335	344	275
55°	189	236	146	236	189	172
65°	107	147	86	147	107	107
75°	50	72	45	72	50	53
85°	11	16	12	16	11	13
90°	27	1	27	1	27	19
95°	273	38	273	38	273	387
105°	1540	131	1540	131	1540	1530
115°	1715	235	1715	235	1715	1676
125°	1351	325	1351	325	1351	1223
135°	1122	381	1122	381	1122	870
145°	885	444	885	444	885	563
155°	742	507	742	507	742	346
165°	651	553	651	553	651	186
175°	584	575	584	575	584	57
180°	576	576	576	576	576	



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	592.1	591.7	592.5	590.4	590.6	587.5	587.5	585.1	581.9	579.5	578.4
5°	645.1	645.6	644.7	641.2	638.9	635.4	631.5	624.6	618.8	613.2	608.9
7.5°	699.8	700.1	697.0	696.0	690.1	685.9	677.2	667.7	659.4	648.7	640.6
10°	731.6	731.3	728.1	725.5	720.5	714.0	705.4	694.4	684.0	672.4	661.3
12.5°	750.0	749.4	748.4	745.3	740.6	734.9	727.6	716.7	703.9	691.3	678.3
15°	775.0	773.4	770.4	766.4	759.7	753.0	745.0	735.3	723.0	708.7	696.7
17.5°	805.9	805.9	801.3	795.8	786.7	774.9	762.4	746.8	730.1	714.4	701.6
20°	831.4	830.7	826.1	815.4	805.0	790.2	775.9	756.7	736.4	715.8	699.9
22.5°	868.0	866.2	861.4	847.4	831.3	812.2	790.3	766.9	742.3	719.0	698.0
25°	928.0	926.6	917.1	900.9	878.3	848.9	820.3	788.2	752.8	722.1	696.7
27.5°	969.0	967.5	960.4	947.0	926.1	895.2	856.5	813.5	769.4	727.1	690.5
30°	964.9	968.4	967.5	961.2	945.5	917.8	882.0	833.7	781.2	731.6	687.9
32.5°	906.9	910.0	918.1	930.4	931.3	920.2	893.4	848.8	794.5	738.0	685.8
35°	769.9	774.1	789.8	814.5	846.9	873.9	879.4	855.4	806.6	745.9	682.8
37.5°	591.9	614.6	627.9	653.9	702.8	752.5	800.3	817.9	797.2	742.6	677.9
40°	502.8	508.3	531.9	561.3	602.4	654.1	722.3	771.5	773.1	735.3	670.1
42.5°	430.3	437.4	453.5	477.0	512.2	563.9	634.3	699.3	729.3	714.9	659.9
45°	344.3	349.6	361.4	379.4	406.4	449.2	509.7	584.8	644.4	667.8	632.7
47.5°	282.8	285.7	295.9	309.7	329.7	360.8	407.7	472.9	544.4	594.5	589.6
50°	249.6	252.8	260.6	271.0	287.9	314.2	351.7	406.0	479.7	540.9	553.2
52.5°	223.7	226.4	231.3	241.1	255.0	275.2	305.5	354.6	420.9	486.0	514.4
55°	189.0	190.9	194.8	200.3	211.4	226.0	252.1	286.1	339.7	405.3	446.9
57.5°	160.5	161.4	163.9	169.0	176.7	187.3	206.2	234.9	273.4	332.5	378.4
60°	142.3	143.3	146.5	150.0	156.0	165.7	180.5	200.6	237.5	286.3	332.7
62.5°	127.9	128.5	129.9	133.3	138.6	146.1	157.7	174.1	203.5	246.4	290.2
65°	107.2	107.4	107.9	110.7	113.9	119.5	127.1	138.6	160.8	193.2	232.0
67.5°	87.3	87.7	89.3	90.3	93.6	96.5	101.0	109.8	125.5	147.3	177.5
70°	76.3	76.0	77.6	78.8	79.9	83.4	86.4	93.6	103.3	119.9	145.1
72.5°	65.9	65.3	66.0	66.4	67.9	70.3	73.3	77.7	85.2	96.6	115.9
75°	49.9	50.1	50.1	50.6	51.8	52.7	53.6	55.9	60.1	67.7	78.1
77.5°	35.0	34.7	35.6	35.8	36.5	37.5	38.3	39.2	40.9	44.0	49.4
80°	25.4	25.4	25.6	26.3	26.1	26.6	27.7	28.7	30.7	32.6	34.4
82.5°	19.5	19.3	19.5	19.7	19.6	20.1	20.5	20.7	21.5	22.4	23.7
85°	10.6	10.6	10.9	10.9	11.1	11.1	11.3	11.3	11.3	11.6	11.8
87.5°	9.4	9.2	8.8	8.8	9.0	8.9	8.5	8.1	7.8	7.6	7.3
90°	26.7	26.7	25.6	25.6	25.6	23.2	22.1	20.9	19.8	18.6	16.3
92.5°	74.1	76.0	77.6	80.4	95.3	112.5	149.4	205.9	303.3	374.6	380.7
95°	273.1	291.7	300.9	335.8	418.3	515.9	658.8	835.4	1007.4	1029.5	840.1
97.5°	660.0	674.9	708.6	773.6	845.4	981.2	1120.4	1244.2	1274.7	1099.4	750.2
100°	906.3	924.9	967.9	1051.6	1131.7	1252.6	1372.3	1429.2	1339.7	1049.2	669.3
102.5°	1181.5	1195.4	1242.1	1301.6	1387.4	1469.2	1526.6	1491.5	1300.7	960.9	607.9
105°	1539.6	1553.5	1576.8	1615.1	1652.3	1665.1	1614.0	1454.8	1175.9	842.4	548.4
107.5°	1729.7	1739.0	1746.7	1746.9	1728.1	1667.4	1536.1	1323.7	1048.6	760.8	523.3
110°	1792.9	1792.9	1784.8	1762.7	1710.4	1611.6	1447.8	1227.0	976.0	722.7	515.9



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1785.5	1777.1	1756.9	1719.0	1642.5	1526.1	1360.4	1150.8	922.1	700.4	515.9
115°	1715.0	1699.9	1667.4	1611.6	1521.0	1394.3	1235.2	1055.1	863.3	676.3	519.4
117.5°	1591.6	1582.4	1550.1	1492.4	1401.8	1285.6	1148.5	993.2	828.2	664.4	527.1
120°	1511.7	1502.4	1471.0	1415.3	1329.3	1227.0	1099.2	959.8	808.7	658.8	534.5
122.5°	1441.1	1432.7	1401.3	1350.2	1273.5	1177.8	1063.9	934.7	792.0	654.2	541.0
125°	1351.4	1339.7	1314.2	1266.5	1201.5	1117.8	1016.7	898.2	769.2	648.4	551.9
127.5°	1274.7	1269.6	1245.4	1203.3	1144.3	1066.0	971.6	861.0	748.3	645.6	564.2
130°	1232.8	1225.9	1202.6	1164.3	1106.2	1030.7	940.0	837.8	734.4	643.7	571.7
132.5°	1191.0	1183.1	1161.7	1123.4	1065.3	992.5	910.3	814.5	723.2	643.7	580.0
135°	1122.5	1115.5	1094.6	1056.2	1005.1	938.9	864.5	784.3	710.0	643.7	591.4
137.5°	1049.2	1041.6	1022.3	987.4	941.7	885.4	823.6	758.8	698.1	645.1	601.9
140°	998.1	992.3	974.9	944.7	901.7	852.9	799.4	744.8	692.5	646.0	606.5
142.5°	950.7	945.8	929.3	903.8	867.3	825.0	779.0	732.7	687.9	647.0	609.3
145°	885.4	880.8	868.0	848.2	820.3	789.0	752.9	716.9	680.9	646.0	612.4
147.5°	830.1	828.0	820.6	804.8	782.7	759.0	731.3	702.1	673.7	643.0	613.5
150°	799.4	798.3	793.6	779.7	762.2	741.3	719.3	693.7	668.1	640.2	613.5
152.5°	775.3	774.1	769.4	758.3	743.7	727.4	707.2	684.4	661.6	636.5	612.6
155°	742.5	741.3	737.8	729.7	718.1	705.3	689.0	670.4	650.7	629.8	610.0
157.5°	713.2	713.4	710.2	703.4	694.4	684.4	671.8	656.5	640.5	622.8	607.0
160°	693.7	694.9	692.5	686.7	678.6	670.4	658.8	647.2	632.1	618.2	604.2
162.5°	676.0	676.3	675.8	670.9	664.6	657.4	647.7	637.0	624.7	612.6	601.4
165°	650.7	650.7	650.7	648.4	643.7	637.9	630.9	622.8	613.5	604.2	597.2
167.5°	627.5	627.7	628.6	626.5	624.2	620.0	614.7	609.3	602.6	596.1	590.7
170°	613.5	614.7	614.7	613.5	611.2	608.9	605.4	601.9	596.1	591.4	588.0
172.5°	600.5	601.7	603.5	601.4	601.0	599.6	597.0	593.5	589.6	585.9	584.2
175°	584.5	585.6	588.0	586.8	586.8	586.8	584.5	584.5	581.0	579.8	579.8
177.5°	576.3	576.3	579.1	578.2	579.1	579.1	579.1	578.2	577.3	576.3	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	578.4	577.1	574.7	572.5	569.7	567.3	565.6	563.6	561.0	557.9	555.3
5°	604.0	598.9	592.2	586.4	579.0	573.3	567.3	561.5	555.7	548.3	541.8
7.5°	632.4	621.9	611.7	598.8	587.2	576.8	566.8	556.7	546.8	536.3	526.2
10°	649.8	637.0	623.0	606.8	592.0	577.9	565.0	552.2	538.8	527.1	514.4
12.5°	666.0	649.6	633.5	613.1	595.3	578.1	561.6	545.8	531.5	516.2	502.5
15°	680.7	664.5	646.5	621.6	596.8	576.0	556.6	536.1	518.3	501.2	485.9
17.5°	686.4	669.4	648.5	624.5	597.5	571.3	546.3	523.8	502.8	482.9	465.8
20°	684.2	667.8	646.3	623.4	594.5	567.3	540.2	515.3	491.9	470.9	452.7
22.5°	678.8	661.9	641.1	616.9	589.5	560.6	531.7	505.1	480.7	458.9	439.0
25°	670.8	647.7	626.4	602.8	576.7	548.1	518.3	488.9	462.8	440.6	418.9
27.5°	662.4	633.6	606.5	583.1	555.5	530.0	501.2	471.1	443.7	421.1	398.8
30°	654.8	622.5	592.7	566.1	540.0	515.7	488.5	459.1	430.9	407.6	385.0
32.5°	645.4	611.0	578.3	547.6	522.4	498.4	473.7	445.6	418.2	394.1	371.1
35°	633.6	589.7	554.1	521.5	493.6	470.2	448.0	425.4	397.9	372.9	350.5
37.5°	618.1	568.2	527.1	491.6	462.1	438.7	421.1	400.4	375.3	351.5	330.7
40°	608.6	552.7	507.7	472.5	441.6	416.8	400.4	382.9	360.0	337.6	316.8
42.5°	596.1	538.5	488.1	451.5	420.3	396.5	379.9	364.6	345.4	324.3	302.0
45°	571.4	510.9	458.0	418.7	387.3	363.9	348.4	334.8	320.3	300.8	281.4
47.5°	539.4	482.1	426.7	383.8	353.1	331.4	316.4	305.6	295.2	278.7	259.9
50°	513.7	458.4	404.4	362.8	330.0	309.4	295.3	286.8	277.3	262.3	246.5
52.5°	483.3	434.0	381.1	338.6	307.6	288.3	274.8	266.2	258.4	246.2	231.2
55°	435.6	392.3	343.8	305.2	276.8	257.4	244.5	236.4	231.8	221.4	209.6
57.5°	380.4	349.5	306.7	269.5	244.3	225.2	215.7	208.8	203.6	196.2	187.9
60°	342.0	320.3	281.9	246.5	223.4	205.2	196.6	190.9	186.0	179.8	173.3
62.5°	303.0	287.2	253.8	223.4	202.2	186.9	178.9	173.7	168.1	163.9	157.6
65°	250.7	236.6	213.5	189.7	170.1	157.8	152.0	147.4	144.0	139.3	134.9
67.5°	195.0	189.3	173.3	156.9	142.8	131.9	126.9	123.7	119.6	116.8	113.8
70°	160.8	158.0	146.7	135.9	122.7	115.3	110.7	109.3	104.2	101.4	99.4
72.5°	130.5	129.2	122.7	115.2	105.9	99.4	95.2	93.6	90.3	88.1	86.8
75°	89.4	89.9	88.7	83.9	80.4	76.3	72.6	71.6	69.3	67.5	66.3
77.5°	56.6	58.9	59.0	58.8	57.4	54.9	53.3	52.6	50.4	49.7	49.4
80°	38.8	41.4	43.7	43.4	43.0	42.3	41.1	40.4	39.3	38.6	38.1
82.5°	25.9	28.2	30.2	31.4	31.3	30.6	29.9	29.5	29.3	28.8	28.7
85°	12.2	12.7	13.4	15.0	16.2	16.4	16.2	15.9	15.3	15.5	15.7
87.5°	7.3	6.8	6.8	6.3	5.6	6.1	6.2	6.1	6.0	6.1	6.2
90°	15.1	12.8	11.6	9.3	7.0	4.6	2.3	1.2	2.3	4.6	7.0
92.5°	265.2	158.7	95.3	61.4	41.4	27.0	17.2	14.2	17.2	27.0	41.4
95°	519.4	263.8	139.4	87.1	61.6	48.8	39.5	38.3	39.5	48.8	61.6
97.5°	414.6	227.3	145.0	107.4	84.4	71.6	65.1	63.7	65.1	71.6	84.4
100°	376.5	225.4	158.0	123.2	101.1	88.3	83.7	81.3	83.7	88.3	101.1
102.5°	360.7	233.8	173.8	139.9	119.7	106.0	102.3	100.9	102.3	106.0	119.7
105°	354.4	251.0	199.9	167.3	148.7	137.1	131.3	131.3	131.3	137.1	148.7
107.5°	365.1	276.5	227.0	197.8	178.5	168.9	163.4	161.0	163.4	168.9	178.5
110°	375.3	295.1	247.5	217.3	199.9	189.4	184.8	182.4	184.8	189.4	199.9



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	388.3	312.8	267.0	237.7	220.3	209.8	206.1	203.8	206.1	209.8	220.3
115°	407.8	340.5	297.5	268.4	251.0	240.5	237.0	234.7	237.0	240.5	251.0
117.5°	430.2	368.8	328.1	300.0	280.3	269.8	266.1	262.6	266.1	269.8	280.3
120°	445.0	389.3	348.6	319.5	299.8	289.3	284.7	281.2	284.7	289.3	299.8
122.5°	461.8	408.8	368.1	339.1	317.4	307.0	303.3	300.7	303.3	307.0	317.4
125°	484.5	434.6	396.2	366.0	343.9	333.5	327.7	325.3	327.7	333.5	343.9
127.5°	505.5	459.4	422.5	392.3	368.8	355.6	348.1	344.6	348.1	355.6	368.8
130°	519.4	475.2	439.2	409.0	384.6	369.5	360.2	356.7	360.2	369.5	384.6
132.5°	531.5	490.1	454.1	423.9	398.6	381.6	370.4	366.0	370.4	381.6	398.6
135°	548.4	510.1	474.1	442.7	418.3	399.7	385.8	381.1	385.8	399.7	418.3
137.5°	561.0	524.3	491.5	459.2	435.3	416.7	403.7	400.2	403.7	416.7	435.3
140°	569.4	534.5	500.8	469.4	447.4	428.8	414.8	411.3	414.8	428.8	447.4
142.5°	574.0	541.0	509.2	479.7	458.5	439.9	426.9	424.3	426.9	439.9	458.5
145°	581.0	551.9	521.7	495.0	474.1	457.8	446.2	443.9	446.2	457.8	474.1
147.5°	585.2	558.9	532.4	508.9	490.8	475.7	465.7	464.3	465.7	475.7	490.8
150°	588.0	563.5	538.0	518.2	502.0	486.9	478.7	476.4	478.7	486.9	502.0
152.5°	589.8	568.2	544.5	526.6	511.3	498.0	490.8	489.4	490.8	498.0	511.3
155°	591.4	572.8	553.1	536.8	525.2	513.6	506.6	506.6	506.6	513.6	525.2
157.5°	592.6	576.8	559.8	547.5	537.3	527.3	521.7	522.0	521.7	527.3	537.3
160°	592.6	578.7	563.5	553.1	543.8	535.7	531.0	532.2	531.0	535.7	543.8
162.5°	591.7	580.5	567.3	558.7	551.2	544.0	539.4	540.5	539.4	544.0	551.2
165°	590.3	581.0	571.7	564.7	560.1	554.3	550.8	553.1	550.8	554.3	560.1
167.5°	587.5	581.0	573.3	568.9	565.6	562.4	560.3	561.5	560.3	562.4	565.6
170°	585.6	581.0	575.2	571.7	569.4	567.0	565.9	567.0	565.9	567.0	569.4
172.5°	583.8	580.0	575.2	573.5	572.1	569.8	568.7	570.8	568.7	569.8	572.1
175°	581.0	578.7	575.2	575.2	575.2	574.0	572.8	575.2	572.8	574.0	575.2
177.5°	578.2	577.3	575.4	575.4	576.3	575.4	575.4	577.3	575.4	575.4	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	553.4	550.9	549.0	545.3	542.7	541.6	539.6	539.0	541.1	539.6	539.4
5°	537.0	530.3	525.0	519.7	513.9	510.2	504.6	503.7	502.3	500.3	499.8
7.5°	517.3	508.5	501.7	492.9	485.3	479.1	472.2	468.9	467.1	464.4	460.8
10°	504.0	493.6	484.3	475.5	466.1	458.4	451.5	446.2	442.7	439.5	438.1
12.5°	490.8	480.2	468.4	457.8	447.2	438.7	431.0	427.5	423.7	419.9	416.7
15°	470.4	456.4	443.4	431.2	422.2	412.9	405.5	400.4	394.7	393.0	386.8
17.5°	448.8	435.0	419.8	407.0	396.5	386.3	378.2	372.4	368.1	362.1	359.3
20°	435.3	418.9	404.1	392.3	380.8	368.8	360.5	355.6	351.5	346.6	344.3
22.5°	420.9	404.9	389.7	375.9	364.2	352.3	346.4	341.4	336.7	332.2	329.1
25°	399.7	383.6	367.6	353.3	341.1	332.5	325.6	319.8	317.3	312.9	309.6
27.5°	378.8	361.6	345.1	330.8	321.2	312.7	307.0	302.5	297.9	294.1	291.2
30°	365.3	347.8	329.7	318.4	308.2	300.2	293.9	289.5	286.1	282.6	280.5
32.5°	351.8	333.7	317.7	305.5	295.9	288.9	282.5	278.2	274.6	270.8	268.3
35°	330.2	311.7	298.8	286.8	277.3	270.8	266.4	260.4	257.4	254.6	252.1
37.5°	310.1	292.9	278.9	268.4	260.1	253.7	248.0	244.8	241.1	238.6	236.5
40°	295.3	279.6	266.9	255.8	249.8	242.6	237.3	233.1	230.4	227.1	224.8
42.5°	282.0	267.4	255.0	245.1	237.6	231.5	226.4	222.2	218.7	216.4	214.5
45°	263.2	248.6	236.6	227.4	220.4	214.7	209.3	207.3	202.6	199.9	198.9
47.5°	243.7	230.7	219.1	210.6	203.5	198.0	193.0	188.8	186.2	183.5	182.0
50°	230.6	218.1	207.3	198.9	192.0	186.0	181.4	178.6	175.1	172.6	170.8
52.5°	217.5	205.9	195.1	187.1	181.1	175.1	169.9	167.2	163.9	162.3	161.0
55°	198.7	186.5	177.2	169.4	163.1	157.6	152.7	150.0	147.9	146.3	145.8
57.5°	177.5	167.8	159.2	152.1	145.6	140.4	136.1	133.5	131.7	131.4	130.0
60°	163.6	154.8	147.0	139.3	133.8	128.9	125.2	122.2	120.4	120.2	119.7
62.5°	149.7	141.3	134.0	127.3	122.3	117.7	114.1	110.8	109.7	108.5	107.5
65°	129.2	121.5	115.5	110.2	104.9	101.0	97.5	95.4	92.9	91.5	89.0
67.5°	109.0	103.1	97.3	92.8	88.6	84.9	82.0	78.9	77.2	76.1	74.3
70°	95.7	91.0	85.3	80.4	77.2	74.2	71.9	68.4	67.2	66.3	65.4
72.5°	83.1	79.0	74.2	70.2	67.0	64.2	61.5	59.9	58.7	57.8	57.3
75°	65.4	61.5	57.3	54.5	52.2	49.9	48.5	47.4	46.9	46.7	45.8
77.5°	48.0	45.9	42.6	40.4	38.9	37.9	36.7	36.1	36.0	35.0	34.7
80°	36.7	35.6	32.8	31.9	30.7	29.8	29.1	28.0	26.8	26.3	25.6
82.5°	27.3	26.2	25.0	23.6	22.6	22.0	21.4	20.9	21.1	20.4	20.1
85°	14.6	13.4	12.9	12.7	12.2	12.7	12.5	12.2	12.0	11.8	12.0
87.5°	6.5	6.9	7.0	7.8	7.5	8.2	8.4	8.4	8.7	8.9	9.2
90°	9.3	11.6	12.8	15.1	16.3	18.6	19.8	20.9	22.1	23.2	25.6
92.5°	61.4	95.3	158.7	265.2	380.7	374.6	303.3	205.9	149.4	112.5	95.3
95°	87.1	139.4	263.8	519.4	840.1	1029.5	1007.4	835.4	658.8	515.9	418.3
97.5°	107.4	145.0	227.3	414.6	750.2	1099.4	1274.7	1244.2	1120.4	981.2	845.4
100°	123.2	158.0	225.4	376.5	669.3	1049.2	1339.7	1429.2	1372.3	1252.6	1131.7
102.5°	139.9	173.8	233.8	360.7	607.9	960.9	1300.7	1491.5	1526.6	1469.2	1387.4
105°	167.3	199.9	251.0	354.4	548.4	842.4	1175.9	1454.8	1614.0	1665.1	1652.3
107.5°	197.8	227.0	276.5	365.1	523.3	760.8	1048.6	1323.7	1536.1	1667.4	1728.1
110°	217.3	247.5	295.1	375.3	515.9	722.7	976.0	1227.0	1447.8	1611.6	1710.4



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	237.7	267.0	312.8	388.3	515.9	700.4	922.1	1150.8	1360.4	1526.1	1642.5
115°	268.4	297.5	340.5	407.8	519.4	676.3	863.3	1055.1	1235.2	1394.3	1521.0
117.5°	300.0	328.1	368.8	430.2	527.1	664.4	828.2	993.2	1148.5	1285.6	1401.8
120°	319.5	348.6	389.3	445.0	534.5	658.8	808.7	959.8	1099.2	1227.0	1329.3
122.5°	339.1	368.1	408.8	461.8	541.0	654.2	792.0	934.7	1063.9	1177.8	1273.5
125°	366.0	396.2	434.6	484.5	551.9	648.4	769.2	898.2	1016.7	1117.8	1201.5
127.5°	392.3	422.5	459.4	505.5	564.2	645.6	748.3	861.0	971.6	1066.0	1144.3
130°	409.0	439.2	475.2	519.4	571.7	643.7	734.4	837.8	940.0	1030.7	1106.2
132.5°	423.9	454.1	490.1	531.5	580.0	643.7	723.2	814.5	910.3	992.5	1065.3
135°	442.7	474.1	510.1	548.4	591.4	643.7	710.0	784.3	864.5	938.9	1005.1
137.5°	459.2	491.5	524.3	561.0	601.9	645.1	698.1	758.8	823.6	885.4	941.7
140°	469.4	500.8	534.5	569.4	606.5	646.0	692.5	744.8	799.4	852.9	901.7
142.5°	479.7	509.2	541.0	574.0	609.3	647.0	687.9	732.7	779.0	825.0	867.3
145°	495.0	521.7	551.9	581.0	612.4	646.0	680.9	716.9	752.9	789.0	820.3
147.5°	508.9	532.4	558.9	585.2	613.5	643.0	673.7	702.1	731.3	759.0	782.7
150°	518.2	538.0	563.5	588.0	613.5	640.2	668.1	693.7	719.3	741.3	762.2
152.5°	526.6	544.5	568.2	589.8	612.6	636.5	661.6	684.4	707.2	727.4	743.7
155°	536.8	553.1	572.8	591.4	610.0	629.8	650.7	670.4	689.0	705.3	718.1
157.5°	547.5	559.8	576.8	592.6	607.0	622.8	640.5	656.5	671.8	684.4	694.4
160°	553.1	563.5	578.7	592.6	604.2	618.2	632.1	647.2	658.8	670.4	678.6
162.5°	558.7	567.3	580.5	591.7	601.4	612.6	624.7	637.0	647.7	657.4	664.6
165°	564.7	571.7	581.0	590.3	597.2	604.2	613.5	622.8	630.9	637.9	643.7
167.5°	568.9	573.3	581.0	587.5	590.7	596.1	602.6	609.3	614.7	620.0	624.2
170°	571.7	575.2	581.0	585.6	588.0	591.4	596.1	601.9	605.4	608.9	611.2
172.5°	573.5	575.2	580.0	583.8	584.2	585.9	589.6	593.5	597.0	599.6	601.0
175°	575.2	575.2	578.7	581.0	579.8	579.8	581.0	584.5	584.5	586.8	586.8
177.5°	575.4	575.4	577.3	578.2	576.3	576.3	577.3	578.2	579.1	579.1	579.1
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.2	537.2	536.6	537.4	536.6	537.2	539.2	539.4	539.6	541.1	539.0
5°	497.5	495.2	496.3	495.9	496.3	495.2	497.5	499.8	500.3	502.3	503.7
7.5°	460.8	457.9	454.9	455.8	454.9	457.9	460.8	460.8	464.4	467.1	468.9
10°	435.1	432.8	431.4	432.6	431.4	432.8	435.1	438.1	439.5	442.7	446.2
12.5°	413.5	412.1	410.9	410.4	410.9	412.1	413.5	416.7	419.9	423.7	427.5
15°	384.0	381.3	380.1	377.1	380.1	381.3	384.0	386.8	393.0	394.7	400.4
17.5°	356.9	356.0	353.0	351.7	353.0	356.0	356.9	359.3	362.1	368.1	372.4
20°	340.8	339.9	336.9	338.7	336.9	339.9	340.8	344.3	346.6	351.5	355.6
22.5°	327.5	325.5	324.5	324.0	324.5	325.5	327.5	329.1	332.2	336.7	341.4
25°	308.7	305.7	304.5	303.2	304.5	305.7	308.7	309.6	312.9	317.3	319.8
27.5°	289.9	288.3	286.8	286.4	286.8	288.3	289.9	291.2	294.1	297.9	302.5
30°	277.7	276.1	275.0	275.0	275.0	276.1	277.7	280.5	282.6	286.1	289.5
32.5°	266.8	265.6	264.4	264.2	264.4	265.6	266.8	268.3	270.8	274.6	278.2
35°	250.9	249.1	248.6	247.2	248.6	249.1	250.9	252.1	254.6	257.4	260.4
37.5°	234.4	232.9	232.9	232.7	232.9	232.9	234.4	236.5	238.6	241.1	244.8
40°	223.9	222.7	222.5	220.9	222.5	222.7	223.9	224.8	227.1	230.4	233.1
42.5°	212.6	212.0	211.2	210.5	211.2	212.0	212.6	214.5	216.4	218.7	222.2
45°	197.3	195.7	195.7	194.6	195.7	195.7	197.3	198.9	199.9	202.6	207.3
47.5°	181.5	180.3	180.4	179.2	180.4	180.3	181.5	182.0	183.5	186.2	188.8
50°	171.0	170.3	170.1	169.6	170.1	170.3	171.0	170.8	172.6	175.1	178.6
52.5°	160.5	160.1	161.0	160.0	161.0	160.1	160.5	161.0	162.3	163.9	167.2
55°	146.3	145.6	147.0	145.6	147.0	145.6	146.3	145.8	146.3	147.9	150.0
57.5°	130.0	129.3	130.6	129.9	130.6	129.3	130.0	130.0	131.4	131.7	133.5
60°	119.2	117.8	118.5	118.8	118.5	117.8	119.2	119.7	120.2	120.4	122.2
62.5°	106.5	105.6	106.2	105.1	106.2	105.6	106.5	107.5	108.5	109.7	110.8
65°	88.5	87.8	86.9	86.4	86.9	87.8	88.5	89.0	91.5	92.9	95.4
67.5°	74.4	72.7	72.6	73.0	72.6	72.7	74.4	74.3	76.1	77.2	78.9
70°	64.0	64.0	63.8	63.8	63.8	64.0	64.0	65.4	66.3	67.2	68.4
72.5°	56.8	56.6	56.2	56.0	56.2	56.6	56.8	57.3	57.8	58.7	59.9
75°	45.8	46.0	45.5	45.3	45.5	46.0	45.8	45.8	46.7	46.9	47.4
77.5°	33.8	32.8	33.3	32.8	33.3	32.8	33.8	34.7	35.0	36.0	36.1
80°	25.6	25.4	26.1	25.4	26.1	25.4	25.6	25.6	26.3	26.8	28.0
82.5°	20.3	20.1	20.4	19.9	20.4	20.1	20.3	20.1	20.4	21.1	20.9
85°	12.2	12.0	11.8	12.0	11.8	12.0	12.2	12.0	11.8	12.0	12.2
87.5°	9.4	9.2	9.4	9.4	9.4	9.2	9.4	9.2	8.9	8.7	8.4
90°	25.6	25.6	26.7	26.7	26.7	25.6	25.6	25.6	23.2	22.1	20.9
92.5°	80.4	77.6	76.0	74.1	76.0	77.6	80.4	95.3	112.5	149.4	205.9
95°	335.8	300.9	291.7	273.1	291.7	300.9	335.8	418.3	515.9	658.8	835.4
97.5°	773.6	708.6	674.9	660.0	674.9	708.6	773.6	845.4	981.2	1120.4	1244.2
100°	1051.6	967.9	924.9	906.3	924.9	967.9	1051.6	1131.7	1252.6	1372.3	1429.2
102.5°	1301.6	1242.1	1195.4	1181.5	1195.4	1242.1	1301.6	1387.4	1469.2	1526.6	1491.5
105°	1615.1	1576.8	1553.5	1539.6	1553.5	1576.8	1615.1	1652.3	1665.1	1614.0	1454.8
107.5°	1746.9	1746.7	1739.0	1729.7	1739.0	1746.7	1746.9	1728.1	1667.4	1536.1	1323.7
110°	1762.7	1784.8	1792.9	1792.9	1792.9	1784.8	1762.7	1710.4	1611.6	1447.8	1227.0



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1719.0	1756.9	1777.1	1785.5	1777.1	1756.9	1719.0	1642.5	1526.1	1360.4	1150.8
115°	1611.6	1667.4	1699.9	1715.0	1699.9	1667.4	1611.6	1521.0	1394.3	1235.2	1055.1
117.5°	1492.4	1550.1	1582.4	1591.6	1582.4	1550.1	1492.4	1401.8	1285.6	1148.5	993.2
120°	1415.3	1471.0	1502.4	1511.7	1502.4	1471.0	1415.3	1329.3	1227.0	1099.2	959.8
122.5°	1350.2	1401.3	1432.7	1441.1	1432.7	1401.3	1350.2	1273.5	1177.8	1063.9	934.7
125°	1266.5	1314.2	1339.7	1351.4	1339.7	1314.2	1266.5	1201.5	1117.8	1016.7	898.2
127.5°	1203.3	1245.4	1269.6	1274.7	1269.6	1245.4	1203.3	1144.3	1066.0	971.6	861.0
130°	1164.3	1202.6	1225.9	1232.8	1225.9	1202.6	1164.3	1106.2	1030.7	940.0	837.8
132.5°	1123.4	1161.7	1183.1	1191.0	1183.1	1161.7	1123.4	1065.3	992.5	910.3	814.5
135°	1056.2	1094.6	1115.5	1122.5	1115.5	1094.6	1056.2	1005.1	938.9	864.5	784.3
137.5°	987.4	1022.3	1041.6	1049.2	1041.6	1022.3	987.4	941.7	885.4	823.6	758.8
140°	944.7	974.9	992.3	998.1	992.3	974.9	944.7	901.7	852.9	799.4	744.8
142.5°	903.8	929.3	945.8	950.7	945.8	929.3	903.8	867.3	825.0	779.0	732.7
145°	848.2	868.0	880.8	885.4	880.8	868.0	848.2	820.3	789.0	752.9	716.9
147.5°	804.8	820.6	828.0	830.1	828.0	820.6	804.8	782.7	759.0	731.3	702.1
150°	779.7	793.6	798.3	799.4	798.3	793.6	779.7	762.2	741.3	719.3	693.7
152.5°	758.3	769.4	774.1	775.3	774.1	769.4	758.3	743.7	727.4	707.2	684.4
155°	729.7	737.8	741.3	742.5	741.3	737.8	729.7	718.1	705.3	689.0	670.4
157.5°	703.4	710.2	713.4	713.2	713.4	710.2	703.4	694.4	684.4	671.8	656.5
160°	686.7	692.5	694.9	693.7	694.9	692.5	686.7	678.6	670.4	658.8	647.2
162.5°	670.9	675.8	676.3	676.0	676.3	675.8	670.9	664.6	657.4	647.7	637.0
165°	648.4	650.7	650.7	650.7	650.7	650.7	648.4	643.7	637.9	630.9	622.8
167.5°	626.5	628.6	627.7	627.5	627.7	628.6	626.5	624.2	620.0	614.7	609.3
170°	613.5	614.7	614.7	613.5	614.7	614.7	613.5	611.2	608.9	605.4	601.9
172.5°	601.4	603.5	601.7	600.5	601.7	603.5	601.4	601.0	599.6	597.0	593.5
175°	586.8	588.0	585.6	584.5	585.6	588.0	586.8	586.8	586.8	584.5	584.5
177.5°	578.2	579.1	576.3	576.3	576.3	579.1	578.2	579.1	579.1	579.1	578.2
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.6	541.6	542.7	545.3	549.0	550.9	553.4	555.3	557.9	561.0	563.6
5°	504.6	510.2	513.9	519.7	525.0	530.3	537.0	541.8	548.3	555.7	561.5
7.5°	472.2	479.1	485.3	492.9	501.7	508.5	517.3	526.2	536.3	546.8	556.7
10°	451.5	458.4	466.1	475.5	484.3	493.6	504.0	514.4	527.1	538.8	552.2
12.5°	431.0	438.7	447.2	457.8	468.4	480.2	490.8	502.5	516.2	531.5	545.8
15°	405.5	412.9	422.2	431.2	443.4	456.4	470.4	485.9	501.2	518.3	536.1
17.5°	378.2	386.3	396.5	407.0	419.8	435.0	448.8	465.8	482.9	502.8	523.8
20°	360.5	368.8	380.8	392.3	404.1	418.9	435.3	452.7	470.9	491.9	515.3
22.5°	346.4	352.3	364.2	375.9	389.7	404.9	420.9	439.0	458.9	480.7	505.1
25°	325.6	332.5	341.1	353.3	367.6	383.6	399.7	418.9	440.6	462.8	488.9
27.5°	307.0	312.7	321.2	330.8	345.1	361.6	378.8	398.8	421.1	443.7	471.1
30°	293.9	300.2	308.2	318.4	329.7	347.8	365.3	385.0	407.6	430.9	459.1
32.5°	282.5	288.9	295.9	305.5	317.7	333.7	351.8	371.1	394.1	418.2	445.6
35°	266.4	270.8	277.3	286.8	298.8	311.7	330.2	350.5	372.9	397.9	425.4
37.5°	248.0	253.7	260.1	268.4	278.9	292.9	310.1	330.7	351.5	375.3	400.4
40°	237.3	242.6	249.8	255.8	266.9	279.6	295.3	316.8	337.6	360.0	382.9
42.5°	226.4	231.5	237.6	245.1	255.0	267.4	282.0	302.0	324.3	345.4	364.6
45°	209.3	214.7	220.4	227.4	236.6	248.6	263.2	281.4	300.8	320.3	334.8
47.5°	193.0	198.0	203.5	210.6	219.1	230.7	243.7	259.9	278.7	295.2	305.6
50°	181.4	186.0	192.0	198.9	207.3	218.1	230.6	246.5	262.3	277.3	286.8
52.5°	169.9	175.1	181.1	187.1	195.1	205.9	217.5	231.2	246.2	258.4	266.2
55°	152.7	157.6	163.1	169.4	177.2	186.5	198.7	209.6	221.4	231.8	236.4
57.5°	136.1	140.4	145.6	152.1	159.2	167.8	177.5	187.9	196.2	203.6	208.8
60°	125.2	128.9	133.8	139.3	147.0	154.8	163.6	173.3	179.8	186.0	190.9
62.5°	114.1	117.7	122.3	127.3	134.0	141.3	149.7	157.6	163.9	168.1	173.7
65°	97.5	101.0	104.9	110.2	115.5	121.5	129.2	134.9	139.3	144.0	147.4
67.5°	82.0	84.9	88.6	92.8	97.3	103.1	109.0	113.8	116.8	119.6	123.7
70°	71.9	74.2	77.2	80.4	85.3	91.0	95.7	99.4	101.4	104.2	109.3
72.5°	61.5	64.2	67.0	70.2	74.2	79.0	83.1	86.8	88.1	90.3	93.6
75°	48.5	49.9	52.2	54.5	57.3	61.5	65.4	66.3	67.5	69.3	71.6
77.5°	36.7	37.9	38.9	40.4	42.6	45.9	48.0	49.4	49.7	50.4	52.6
80°	29.1	29.8	30.7	31.9	32.8	35.6	36.7	38.1	38.6	39.3	40.4
82.5°	21.4	22.0	22.6	23.6	25.0	26.2	27.3	28.7	28.8	29.3	29.5
85°	12.5	12.7	12.2	12.7	12.9	13.4	14.6	15.7	15.5	15.3	15.9
87.5°	8.4	8.2	7.5	7.8	7.0	6.9	6.5	6.2	6.1	6.0	6.1
90°	19.8	18.6	16.3	15.1	12.8	11.6	9.3	7.0	4.6	2.3	1.2
92.5°	303.3	374.6	380.7	265.2	158.7	95.3	61.4	41.4	27.0	17.2	14.2
95°	1007.4	1029.5	840.1	519.4	263.8	139.4	87.1	61.6	48.8	39.5	38.3
97.5°	1274.7	1099.4	750.2	414.6	227.3	145.0	107.4	84.4	71.6	65.1	63.7
100°	1339.7	1049.2	669.3	376.5	225.4	158.0	123.2	101.1	88.3	83.7	81.3
102.5°	1300.7	960.9	607.9	360.7	233.8	173.8	139.9	119.7	106.0	102.3	100.9
105°	1175.9	842.4	548.4	354.4	251.0	199.9	167.3	148.7	137.1	131.3	131.3
107.5°	1048.6	760.8	523.3	365.1	276.5	227.0	197.8	178.5	168.9	163.4	161.0
110°	976.0	722.7	515.9	375.3	295.1	247.5	217.3	199.9	189.4	184.8	182.4



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	922.1	700.4	515.9	388.3	312.8	267.0	237.7	220.3	209.8	206.1	203.8
115°	863.3	676.3	519.4	407.8	340.5	297.5	268.4	251.0	240.5	237.0	234.7
117.5°	828.2	664.4	527.1	430.2	368.8	328.1	300.0	280.3	269.8	266.1	262.6
120°	808.7	658.8	534.5	445.0	389.3	348.6	319.5	299.8	289.3	284.7	281.2
122.5°	792.0	654.2	541.0	461.8	408.8	368.1	339.1	317.4	307.0	303.3	300.7
125°	769.2	648.4	551.9	484.5	434.6	396.2	366.0	343.9	333.5	327.7	325.3
127.5°	748.3	645.6	564.2	505.5	459.4	422.5	392.3	368.8	355.6	348.1	344.6
130°	734.4	643.7	571.7	519.4	475.2	439.2	409.0	384.6	369.5	360.2	356.7
132.5°	723.2	643.7	580.0	531.5	490.1	454.1	423.9	398.6	381.6	370.4	366.0
135°	710.0	643.7	591.4	548.4	510.1	474.1	442.7	418.3	399.7	385.8	381.1
137.5°	698.1	645.1	601.9	561.0	524.3	491.5	459.2	435.3	416.7	403.7	400.2
140°	692.5	646.0	606.5	569.4	534.5	500.8	469.4	447.4	428.8	414.8	411.3
142.5°	687.9	647.0	609.3	574.0	541.0	509.2	479.7	458.5	439.9	426.9	424.3
145°	680.9	646.0	612.4	581.0	551.9	521.7	495.0	474.1	457.8	446.2	443.9
147.5°	673.7	643.0	613.5	585.2	558.9	532.4	508.9	490.8	475.7	465.7	464.3
150°	668.1	640.2	613.5	588.0	563.5	538.0	518.2	502.0	486.9	478.7	476.4
152.5°	661.6	636.5	612.6	589.8	568.2	544.5	526.6	511.3	498.0	490.8	489.4
155°	650.7	629.8	610.0	591.4	572.8	553.1	536.8	525.2	513.6	506.6	506.6
157.5°	640.5	622.8	607.0	592.6	576.8	559.8	547.5	537.3	527.3	521.7	522.0
160°	632.1	618.2	604.2	592.6	578.7	563.5	553.1	543.8	535.7	531.0	532.2
162.5°	624.7	612.6	601.4	591.7	580.5	567.3	558.7	551.2	544.0	539.4	540.5
165°	613.5	604.2	597.2	590.3	581.0	571.7	564.7	560.1	554.3	550.8	553.1
167.5°	602.6	596.1	590.7	587.5	581.0	573.3	568.9	565.6	562.4	560.3	561.5
170°	596.1	591.4	588.0	585.6	581.0	575.2	571.7	569.4	567.0	565.9	567.0
172.5°	589.6	585.9	584.2	583.8	580.0	575.2	573.5	572.1	569.8	568.7	570.8
175°	581.0	579.8	579.8	581.0	578.7	575.2	575.2	575.2	574.0	572.8	575.2
177.5°	577.3	576.3	576.3	578.2	577.3	575.4	575.4	576.3	575.4	575.4	577.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	565.6	567.3	569.7	572.5	574.7	577.1	578.4	578.4	579.5	581.9	585.1
5°	567.3	573.3	579.0	586.4	592.2	598.9	604.0	608.9	613.2	618.8	624.6
7.5°	566.8	576.8	587.2	598.8	611.7	621.9	632.4	640.6	648.7	659.4	667.7
10°	565.0	577.9	592.0	606.8	623.0	637.0	649.8	661.3	672.4	684.0	694.4
12.5°	561.6	578.1	595.3	613.1	633.5	649.6	666.0	678.3	691.3	703.9	716.7
15°	556.6	576.0	596.8	621.6	646.5	664.5	680.7	696.7	708.7	723.0	735.3
17.5°	546.3	571.3	597.5	624.5	648.5	669.4	686.4	701.6	714.4	730.1	746.8
20°	540.2	567.3	594.5	623.4	646.3	667.8	684.2	699.9	715.8	736.4	756.7
22.5°	531.7	560.6	589.5	616.9	641.1	661.9	678.8	698.0	719.0	742.3	766.9
25°	518.3	548.1	576.7	602.8	626.4	647.7	670.8	696.7	722.1	752.8	788.2
27.5°	501.2	530.0	555.5	583.1	606.5	633.6	662.4	690.5	727.1	769.4	813.5
30°	488.5	515.7	540.0	566.1	592.7	622.5	654.8	687.9	731.6	781.2	833.7
32.5°	473.7	498.4	522.4	547.6	578.3	611.0	645.4	685.8	738.0	794.5	848.8
35°	448.0	470.2	493.6	521.5	554.1	589.7	633.6	682.8	745.9	806.6	855.4
37.5°	421.1	438.7	462.1	491.6	527.1	568.2	618.1	677.9	742.6	797.2	817.9
40°	400.4	416.8	441.6	472.5	507.7	552.7	608.6	670.1	735.3	773.1	771.5
42.5°	379.9	396.5	420.3	451.5	488.1	538.5	596.1	659.9	714.9	729.3	699.3
45°	348.4	363.9	387.3	418.7	458.0	510.9	571.4	632.7	667.8	644.4	584.8
47.5°	316.4	331.4	353.1	383.8	426.7	482.1	539.4	589.6	594.5	544.4	472.9
50°	295.3	309.4	330.0	362.8	404.4	458.4	513.7	553.2	540.9	479.7	406.0
52.5°	274.8	288.3	307.6	338.6	381.1	434.0	483.3	514.4	486.0	420.9	354.6
55°	244.5	257.4	276.8	305.2	343.8	392.3	435.6	446.9	405.3	339.7	286.1
57.5°	215.7	225.2	244.3	269.5	306.7	349.5	380.4	378.4	332.5	273.4	234.9
60°	196.6	205.2	223.4	246.5	281.9	320.3	342.0	332.7	286.3	237.5	200.6
62.5°	178.9	186.9	202.2	223.4	253.8	287.2	303.0	290.2	246.4	203.5	174.1
65°	152.0	157.8	170.1	189.7	213.5	236.6	250.7	232.0	193.2	160.8	138.6
67.5°	126.9	131.9	142.8	156.9	173.3	189.3	195.0	177.5	147.3	125.5	109.8
70°	110.7	115.3	122.7	135.9	146.7	158.0	160.8	145.1	119.9	103.3	93.6
72.5°	95.2	99.4	105.9	115.2	122.7	129.2	130.5	115.9	96.6	85.2	77.7
75°	72.6	76.3	80.4	83.9	88.7	89.9	89.4	78.1	67.7	60.1	55.9
77.5°	53.3	54.9	57.4	58.8	59.0	58.9	56.6	49.4	44.0	40.9	39.2
80°	41.1	42.3	43.0	43.4	43.7	41.4	38.8	34.4	32.6	30.7	28.7
82.5°	29.9	30.6	31.3	31.4	30.2	28.2	25.9	23.7	22.4	21.5	20.7
85°	16.2	16.4	16.2	15.0	13.4	12.7	12.2	11.8	11.6	11.3	11.3
87.5°	6.2	6.1	5.6	6.3	6.8	6.8	7.3	7.3	7.6	7.8	8.1
90°	2.3	4.6	7.0	9.3	11.6	12.8	15.1	16.3	18.6	19.8	20.9
92.5°	17.2	27.0	41.4	61.4	95.3	158.7	265.2	380.7	374.6	303.3	205.9
95°	39.5	48.8	61.6	87.1	139.4	263.8	519.4	840.1	1029.5	1007.4	835.4
97.5°	65.1	71.6	84.4	107.4	145.0	227.3	414.6	750.2	1099.4	1274.7	1244.2
100°	83.7	88.3	101.1	123.2	158.0	225.4	376.5	669.3	1049.2	1339.7	1429.2
102.5°	102.3	106.0	119.7	139.9	173.8	233.8	360.7	607.9	960.9	1300.7	1491.5
105°	131.3	137.1	148.7	167.3	199.9	251.0	354.4	548.4	842.4	1175.9	1454.8
107.5°	163.4	168.9	178.5	197.8	227.0	276.5	365.1	523.3	760.8	1048.6	1323.7
110°	184.8	189.4	199.9	217.3	247.5	295.1	375.3	515.9	722.7	976.0	1227.0



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	206.1	209.8	220.3	237.7	267.0	312.8	388.3	515.9	700.4	922.1	1150.8
115°	237.0	240.5	251.0	268.4	297.5	340.5	407.8	519.4	676.3	863.3	1055.1
117.5°	266.1	269.8	280.3	300.0	328.1	368.8	430.2	527.1	664.4	828.2	993.2
120°	284.7	289.3	299.8	319.5	348.6	389.3	445.0	534.5	658.8	808.7	959.8
122.5°	303.3	307.0	317.4	339.1	368.1	408.8	461.8	541.0	654.2	792.0	934.7
125°	327.7	333.5	343.9	366.0	396.2	434.6	484.5	551.9	648.4	769.2	898.2
127.5°	348.1	355.6	368.8	392.3	422.5	459.4	505.5	564.2	645.6	748.3	861.0
130°	360.2	369.5	384.6	409.0	439.2	475.2	519.4	571.7	643.7	734.4	837.8
132.5°	370.4	381.6	398.6	423.9	454.1	490.1	531.5	580.0	643.7	723.2	814.5
135°	385.8	399.7	418.3	442.7	474.1	510.1	548.4	591.4	643.7	710.0	784.3
137.5°	403.7	416.7	435.3	459.2	491.5	524.3	561.0	601.9	645.1	698.1	758.8
140°	414.8	428.8	447.4	469.4	500.8	534.5	569.4	606.5	646.0	692.5	744.8
142.5°	426.9	439.9	458.5	479.7	509.2	541.0	574.0	609.3	647.0	687.9	732.7
145°	446.2	457.8	474.1	495.0	521.7	551.9	581.0	612.4	646.0	680.9	716.9
147.5°	465.7	475.7	490.8	508.9	532.4	558.9	585.2	613.5	643.0	673.7	702.1
150°	478.7	486.9	502.0	518.2	538.0	563.5	588.0	613.5	640.2	668.1	693.7
152.5°	490.8	498.0	511.3	526.6	544.5	568.2	589.8	612.6	636.5	661.6	684.4
155°	506.6	513.6	525.2	536.8	553.1	572.8	591.4	610.0	629.8	650.7	670.4
157.5°	521.7	527.3	537.3	547.5	559.8	576.8	592.6	607.0	622.8	640.5	656.5
160°	531.0	535.7	543.8	553.1	563.5	578.7	592.6	604.2	618.2	632.1	647.2
162.5°	539.4	544.0	551.2	558.7	567.3	580.5	591.7	601.4	612.6	624.7	637.0
165°	550.8	554.3	560.1	564.7	571.7	581.0	590.3	597.2	604.2	613.5	622.8
167.5°	560.3	562.4	565.6	568.9	573.3	581.0	587.5	590.7	596.1	602.6	609.3
170°	565.9	567.0	569.4	571.7	575.2	581.0	585.6	588.0	591.4	596.1	601.9
172.5°	568.7	569.8	572.1	573.5	575.2	580.0	583.8	584.2	585.9	589.6	593.5
175°	572.8	574.0	575.2	575.2	575.2	578.7	581.0	579.8	579.8	581.0	584.5
177.5°	575.4	575.4	576.3	575.4	575.4	577.3	578.2	576.3	576.3	577.3	578.2
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	587.5	587.5	590.6	590.4	592.5	591.7	592.1
5°	631.5	635.4	638.9	641.2	644.7	645.6	645.1
7.5°	677.2	685.9	690.1	696.0	697.0	700.1	699.8
10°	705.4	714.0	720.5	725.5	728.1	731.3	731.6
12.5°	727.6	734.9	740.6	745.3	748.4	749.4	750.0
15°	745.0	753.0	759.7	766.4	770.4	773.4	775.0
17.5°	762.4	774.9	786.7	795.8	801.3	805.9	805.9
20°	775.9	790.2	805.0	815.4	826.1	830.7	831.4
22.5°	790.3	812.2	831.3	847.4	861.4	866.2	868.0
25°	820.3	848.9	878.3	900.9	917.1	926.6	928.0
27.5°	856.5	895.2	926.1	947.0	960.4	967.5	969.0
30°	882.0	917.8	945.5	961.2	967.5	968.4	964.9
32.5°	893.4	920.2	931.3	930.4	918.1	910.0	906.9
35°	879.4	873.9	846.9	814.5	789.8	774.1	769.9
37.5°	800.3	752.5	702.8	653.9	627.9	614.6	591.9
40°	722.3	654.1	602.4	561.3	531.9	508.3	502.8
42.5°	634.3	563.9	512.2	477.0	453.5	437.4	430.3
45°	509.7	449.2	406.4	379.4	361.4	349.6	344.3
47.5°	407.7	360.8	329.7	309.7	295.9	285.7	282.8
50°	351.7	314.2	287.9	271.0	260.6	252.8	249.6
52.5°	305.5	275.2	255.0	241.1	231.3	226.4	223.7
55°	252.1	226.0	211.4	200.3	194.8	190.9	189.0
57.5°	206.2	187.3	176.7	169.0	163.9	161.4	160.5
60°	180.5	165.7	156.0	150.0	146.5	143.3	142.3
62.5°	157.7	146.1	138.6	133.3	129.9	128.5	127.9
65°	127.1	119.5	113.9	110.7	107.9	107.4	107.2
67.5°	101.0	96.5	93.6	90.3	89.3	87.7	87.3
70°	86.4	83.4	79.9	78.8	77.6	76.0	76.3
72.5°	73.3	70.3	67.9	66.4	66.0	65.3	65.9
75°	53.6	52.7	51.8	50.6	50.1	50.1	49.9
77.5°	38.3	37.5	36.5	35.8	35.6	34.7	35.0
80°	27.7	26.6	26.1	26.3	25.6	25.4	25.4
82.5°	20.5	20.1	19.6	19.7	19.5	19.3	19.5
85°	11.3	11.1	11.1	10.9	10.9	10.6	10.6
87.5°	8.5	8.9	9.0	8.8	8.8	9.2	9.4
90°	22.1	23.2	25.6	25.6	25.6	26.7	26.7
92.5°	149.4	112.5	95.3	80.4	77.6	76.0	74.1
95°	658.8	515.9	418.3	335.8	300.9	291.7	273.1
97.5°	1120.4	981.2	845.4	773.6	708.6	674.9	660.0
100°	1372.3	1252.6	1131.7	1051.6	967.9	924.9	906.3
102.5°	1526.6	1469.2	1387.4	1301.6	1242.1	1195.4	1181.5
105°	1614.0	1665.1	1652.3	1615.1	1576.8	1553.5	1539.6
107.5°	1536.1	1667.4	1728.1	1746.9	1746.7	1739.0	1729.7
110°	1447.8	1611.6	1710.4	1762.7	1784.8	1792.9	1792.9



TEST NUMBER: P333516

CATALOG NUMBER: S125RDIP-S375D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1360.4	1526.1	1642.5	1719.0	1756.9	1777.1	1785.5
115°	1235.2	1394.3	1521.0	1611.6	1667.4	1699.9	1715.0
117.5°	1148.5	1285.6	1401.8	1492.4	1550.1	1582.4	1591.6
120°	1099.2	1227.0	1329.3	1415.3	1471.0	1502.4	1511.7
122.5°	1063.9	1177.8	1273.5	1350.2	1401.3	1432.7	1441.1
125°	1016.7	1117.8	1201.5	1266.5	1314.2	1339.7	1351.4
127.5°	971.6	1066.0	1144.3	1203.3	1245.4	1269.6	1274.7
130°	940.0	1030.7	1106.2	1164.3	1202.6	1225.9	1232.8
132.5°	910.3	992.5	1065.3	1123.4	1161.7	1183.1	1191.0
135°	864.5	938.9	1005.1	1056.2	1094.6	1115.5	1122.5
137.5°	823.6	885.4	941.7	987.4	1022.3	1041.6	1049.2
140°	799.4	852.9	901.7	944.7	974.9	992.3	998.1
142.5°	779.0	825.0	867.3	903.8	929.3	945.8	950.7
145°	752.9	789.0	820.3	848.2	868.0	880.8	885.4
147.5°	731.3	759.0	782.7	804.8	820.6	828.0	830.1
150°	719.3	741.3	762.2	779.7	793.6	798.3	799.4
152.5°	707.2	727.4	743.7	758.3	769.4	774.1	775.3
155°	689.0	705.3	718.1	729.7	737.8	741.3	742.5
157.5°	671.8	684.4	694.4	703.4	710.2	713.4	713.2
160°	658.8	670.4	678.6	686.7	692.5	694.9	693.7
162.5°	647.7	657.4	664.6	670.9	675.8	676.3	676.0
165°	630.9	637.9	643.7	648.4	650.7	650.7	650.7
167.5°	614.7	620.0	624.2	626.5	628.6	627.7	627.5
170°	605.4	608.9	611.2	613.5	614.7	614.7	613.5
172.5°	597.0	599.6	601.0	601.4	603.5	601.7	600.5
175°	584.5	586.8	586.8	586.8	588.0	585.6	584.5
177.5°	579.1	579.1	579.1	578.2	579.1	576.3	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3

(END OF REPORT)