

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333496

Luminaire Tested: **S125RDIP-S375D590U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333496
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D590U835-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3823.4 lumens
Efficiency: N/A
Efficacy: 149.4 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38																												
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	40	40	39	33																												
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28																												
3	80	71	64	58	72	64	58	54	53	48	45	42	39	37	32	30	29	24																												
4	73	63	55	49	66	57	51	46	47	42	38	38	34	31	29	27	25	21																												
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18																												
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16																												
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17	14																												
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13																												
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	12																												
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	13	11																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3635	3635	3635	3635
5°	4182	3640	3215	3640
10°	4798	3621	2837	3621
15°	5182	3584	2521	3584
20°	5714	3542	2328	3542
25°	6613	3484	2161	3484
30°	7196	3424	2051	3424
35°	6070	3354	1949	3354
40°	4239	3228	1862	3228
45°	3145	3058	1777	3058
50°	2508	2882	1704	2882
55°	2128	2662	1639	2662
60°	1838	2466	1535	2466
65°	1638	2253	1320	2253
70°	1441	2064	1205	2064
75°	1245	1787	1130	1787
80°	945	1503	945	1503
85°	785	1178	889	1178



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	1.4
10°-20°	158.2	4.1
20°-30°	250.8	6.6
30°-40°	302.5	7.9
40°-50°	270.1	7.1
50°-60°	207.1	5.4
60°-70°	134.6	3.5
70°-80°	65.4	1.7
80°-90°	17.2	0.5
90°-100°	28.0	0.7
100°-110°	172.4	4.5
110°-120°	312.6	8.2
120°-130°	401.2	10.5
130°-140°	431.5	11.3
140°-150°	405.1	10.6
150°-160°	327.7	8.6
160°-170°	211.9	5.5
170°-180°	73.1	1.9
0°-30°	463.0	12.1
0°-40°	765.4	20.0
0°-60°	1242.7	32.5
0°-90°	1459.9	38.2
90°-120°	513.0	13.4
90°-150°	1750.8	45.8
90°-180°	2364.0	61.8
0°-180°	3823.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	645	562	496	562	645	64
15°	775	536	377	536	775	222
25°	928	489	303	489	928	426
35°	770	425	247	425	770	465
45°	344	335	195	335	344	275
55°	189	236	146	236	189	172
65°	107	147	86	147	107	107
75°	50	72	45	72	50	53
85°	11	16	12	16	11	13
90°	14	1	14	1	14	6
95°	12	32	12	32	12	10
105°	169	168	169	168	169	153
115°	313	315	313	315	313	310
125°	448	448	448	448	448	398
135°	556	559	556	559	556	429
145°	646	648	646	648	646	403
155°	708	713	708	713	708	326
165°	748	752	748	752	748	211
175°	766	770	766	770	766	73
180°	770	770	770	770	770	



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	592.1	591.7	592.5	590.4	590.6	587.5	587.5	585.1	581.9	579.5	578.4
5°	645.1	645.6	644.7	641.2	638.9	635.4	631.5	624.6	618.8	613.2	608.9
7.5°	699.8	700.1	697.0	696.0	690.1	685.9	677.2	667.7	659.4	648.7	640.6
10°	731.6	731.3	728.1	725.5	720.5	714.0	705.4	694.4	684.0	672.4	661.3
12.5°	750.0	749.4	748.4	745.3	740.6	734.9	727.6	716.7	703.9	691.3	678.3
15°	775.0	773.4	770.4	766.4	759.7	753.0	745.0	735.3	723.0	708.7	696.7
17.5°	805.9	805.9	801.3	795.8	786.7	774.9	762.4	746.8	730.1	714.4	701.6
20°	831.4	830.7	826.1	815.4	805.0	790.2	775.9	756.7	736.4	715.8	699.9
22.5°	868.0	866.2	861.4	847.4	831.3	812.2	790.3	766.9	742.3	719.0	698.0
25°	928.0	926.6	917.1	900.9	878.3	848.9	820.3	788.2	752.8	722.1	696.7
27.5°	969.0	967.5	960.4	947.0	926.1	895.2	856.5	813.5	769.4	727.1	690.5
30°	964.9	968.4	967.5	961.2	945.5	917.8	882.0	833.7	781.2	731.6	687.9
32.5°	906.9	910.0	918.1	930.4	931.3	920.2	893.4	848.8	794.5	738.0	685.8
35°	769.9	774.1	789.8	814.5	846.9	873.9	879.4	855.4	806.6	745.9	682.8
37.5°	591.9	614.6	627.9	653.9	702.8	752.5	800.3	817.9	797.2	742.6	677.9
40°	502.8	508.3	531.9	561.3	602.4	654.1	722.3	771.5	773.1	735.3	670.1
42.5°	430.3	437.4	453.5	477.0	512.2	563.9	634.3	699.3	729.3	714.9	659.9
45°	344.3	349.6	361.4	379.4	406.4	449.2	509.7	584.8	644.4	667.8	632.7
47.5°	282.8	285.7	295.9	309.7	329.7	360.8	407.7	472.9	544.4	594.5	589.6
50°	249.6	252.8	260.6	271.0	287.9	314.2	351.7	406.0	479.7	540.9	553.2
52.5°	223.7	226.4	231.3	241.1	255.0	275.2	305.5	354.6	420.9	486.0	514.4
55°	189.0	190.9	194.8	200.3	211.4	226.0	252.1	286.1	339.7	405.3	446.9
57.5°	160.5	161.4	163.9	169.0	176.7	187.3	206.2	234.9	273.4	332.5	378.4
60°	142.3	143.3	146.5	150.0	156.0	165.7	180.5	200.6	237.5	286.3	332.7
62.5°	127.9	128.5	129.9	133.3	138.6	146.1	157.7	174.1	203.5	246.4	290.2
65°	107.2	107.4	107.9	110.7	113.9	119.5	127.1	138.6	160.8	193.2	232.0
67.5°	87.3	87.7	89.3	90.3	93.6	96.5	101.0	109.8	125.5	147.3	177.5
70°	76.3	76.0	77.6	78.8	79.9	83.4	86.4	93.6	103.3	119.9	145.1
72.5°	65.9	65.3	66.0	66.4	67.9	70.3	73.3	77.7	85.2	96.6	115.9
75°	49.9	50.1	50.1	50.6	51.8	52.7	53.6	55.9	60.1	67.7	78.1
77.5°	35.0	34.7	35.6	35.8	36.5	37.5	38.3	39.2	40.9	44.0	49.4
80°	25.4	25.4	25.6	26.3	26.1	26.6	27.7	28.7	30.7	32.6	34.4
82.5°	19.5	19.3	19.5	19.7	19.6	20.1	20.5	20.7	21.5	22.4	23.7
85°	10.6	10.6	10.9	10.9	11.1	11.1	11.3	11.3	11.3	11.6	11.8
87.5°	6.8	6.5	6.3	6.2	6.3	6.6	6.3	6.0	5.8	5.7	5.7
90°	13.7	13.3	12.9	12.6	12.2	11.7	11.0	10.4	9.8	9.1	8.2
92.5°	12.8	12.6	12.4	12.2	12.1	11.7	11.0	10.4	9.8	9.1	8.3
95°	12.0	12.0	12.0	12.0	12.0	11.7	11.0	10.4	9.8	9.1	13.9
97.5°	12.0	12.0	12.0	12.0	12.0	13.8	17.3	20.9	24.5	28.1	37.6
100°	12.0	12.5	13.0	13.5	14.0	23.7	42.6	61.5	80.4	99.3	98.8
102.5°	71.8	80.4	89.0	97.6	106.3	112.4	115.9	119.5	123.1	126.7	126.4
105°	169.4	169.6	169.7	169.8	170.0	170.0	170.0	170.0	170.0	170.0	170.0
107.5°	213.6	214.0	214.4	214.8	215.1	215.3	215.3	215.3	215.2	215.2	215.0
110°	244.2	244.1	243.9	243.8	243.7	243.8	244.2	244.6	245.0	245.3	245.1



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.6	271.8	271.9	272.1	272.3	272.6	273.1	273.6	274.1	274.5	274.4
115°	312.7	313.4	314.2	314.9	315.7	316.3	316.8	317.3	317.9	318.4	318.2
117.5°	356.5	356.8	357.1	357.5	357.8	358.3	358.9	359.6	360.3	360.9	360.4
120°	383.4	384.0	384.7	385.3	385.9	386.4	386.6	386.9	387.1	387.4	387.0
122.5°	409.0	409.7	410.4	411.2	411.9	412.4	412.7	412.9	413.2	413.4	413.2
125°	447.9	448.3	448.6	449.0	449.4	449.8	450.3	450.9	451.4	451.9	451.9
127.5°	480.6	481.6	482.5	483.4	484.4	485.0	485.3	485.5	485.8	486.1	486.2
130°	504.4	505.0	505.6	506.3	506.9	507.4	507.8	508.2	508.5	508.9	508.8
132.5°	526.3	526.9	527.5	528.2	528.8	529.2	529.2	529.3	529.4	529.5	529.7
135°	556.3	557.0	557.8	558.6	559.3	559.8	560.1	560.3	560.6	560.8	561.1
137.5°	586.4	587.1	587.7	588.4	589.0	589.3	589.3	589.2	589.2	589.1	589.4
140°	604.2	605.0	605.7	606.5	607.2	607.5	607.2	607.0	606.7	606.5	606.6
142.5°	621.1	621.8	622.6	623.4	624.1	624.5	624.4	624.4	624.3	624.3	624.1
145°	645.8	646.6	647.4	648.1	648.9	649.2	649.1	649.0	648.8	648.7	648.7
147.5°	666.3	667.2	668.1	669.0	669.9	670.3	670.2	670.0	669.9	669.7	669.5
150°	679.5	680.5	681.5	682.6	683.6	683.9	683.7	683.4	683.2	682.9	682.7
152.5°	691.8	692.7	693.7	694.6	695.5	695.8	695.6	695.3	695.1	694.8	694.5
155°	708.0	709.1	710.1	711.1	712.1	712.4	712.0	711.7	711.3	710.9	710.6
157.5°	721.6	722.6	723.6	724.7	725.7	726.0	725.6	725.2	724.8	724.4	724.3
160°	730.3	731.3	732.3	733.3	734.3	734.6	734.1	733.6	733.1	732.6	732.4
162.5°	738.0	739.2	740.3	741.4	742.5	742.7	742.0	741.3	740.6	739.9	739.7
165°	748.5	749.6	750.6	751.6	752.6	752.7	752.0	751.2	750.4	749.7	749.6
167.5°	755.8	757.0	758.1	759.3	760.4	760.5	759.6	758.7	757.8	756.9	756.7
170°	760.0	761.1	762.2	763.4	764.5	764.6	763.6	762.6	761.5	760.5	760.4
172.5°	762.7	763.8	765.0	766.1	767.3	767.4	766.5	765.5	764.6	763.7	763.5
175°	766.2	767.4	768.5	769.7	770.8	770.9	769.8	768.8	767.8	766.8	766.7
177.5°	768.3	769.1	769.9	770.7	771.5	771.6	770.9	770.2	769.5	768.7	768.6
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	578.4	577.1	574.7	572.5	569.7	567.3	565.6	563.6	561.0	557.9	555.3
5°	604.0	598.9	592.2	586.4	579.0	573.3	567.3	561.5	555.7	548.3	541.8
7.5°	632.4	621.9	611.7	598.8	587.2	576.8	566.8	556.7	546.8	536.3	526.2
10°	649.8	637.0	623.0	606.8	592.0	577.9	565.0	552.2	538.8	527.1	514.4
12.5°	666.0	649.6	633.5	613.1	595.3	578.1	561.6	545.8	531.5	516.2	502.5
15°	680.7	664.5	646.5	621.6	596.8	576.0	556.6	536.1	518.3	501.2	485.9
17.5°	686.4	669.4	648.5	624.5	597.5	571.3	546.3	523.8	502.8	482.9	465.8
20°	684.2	667.8	646.3	623.4	594.5	567.3	540.2	515.3	491.9	470.9	452.7
22.5°	678.8	661.9	641.1	616.9	589.5	560.6	531.7	505.1	480.7	458.9	439.0
25°	670.8	647.7	626.4	602.8	576.7	548.1	518.3	488.9	462.8	440.6	418.9
27.5°	662.4	633.6	606.5	583.1	555.5	530.0	501.2	471.1	443.7	421.1	398.8
30°	654.8	622.5	592.7	566.1	540.0	515.7	488.5	459.1	430.9	407.6	385.0
32.5°	645.4	611.0	578.3	547.6	522.4	498.4	473.7	445.6	418.2	394.1	371.1
35°	633.6	589.7	554.1	521.5	493.6	470.2	448.0	425.4	397.9	372.9	350.5
37.5°	618.1	568.2	527.1	491.6	462.1	438.7	421.1	400.4	375.3	351.5	330.7
40°	608.6	552.7	507.7	472.5	441.6	416.8	400.4	382.9	360.0	337.6	316.8
42.5°	596.1	538.5	488.1	451.5	420.3	396.5	379.9	364.6	345.4	324.3	302.0
45°	571.4	510.9	458.0	418.7	387.3	363.9	348.4	334.8	320.3	300.8	281.4
47.5°	539.4	482.1	426.7	383.8	353.1	331.4	316.4	305.6	295.2	278.7	259.9
50°	513.7	458.4	404.4	362.8	330.0	309.4	295.3	286.8	277.3	262.3	246.5
52.5°	483.3	434.0	381.1	338.6	307.6	288.3	274.8	266.2	258.4	246.2	231.2
55°	435.6	392.3	343.8	305.2	276.8	257.4	244.5	236.4	231.8	221.4	209.6
57.5°	380.4	349.5	306.7	269.5	244.3	225.2	215.7	208.8	203.6	196.2	187.9
60°	342.0	320.3	281.9	246.5	223.4	205.2	196.6	190.9	186.0	179.8	173.3
62.5°	303.0	287.2	253.8	223.4	202.2	186.9	178.9	173.7	168.1	163.9	157.6
65°	250.7	236.6	213.5	189.7	170.1	157.8	152.0	147.4	144.0	139.3	134.9
67.5°	195.0	189.3	173.3	156.9	142.8	131.9	126.9	123.7	119.6	116.8	113.8
70°	160.8	158.0	146.7	135.9	122.7	115.3	110.7	109.3	104.2	101.4	99.4
72.5°	130.5	129.2	122.7	115.2	105.9	99.4	95.2	93.6	90.3	88.1	86.8
75°	89.4	89.9	88.7	83.9	80.4	76.3	72.6	71.6	69.3	67.5	66.3
77.5°	56.6	58.9	59.0	58.8	57.4	54.9	53.3	52.6	50.4	49.7	49.4
80°	38.8	41.4	43.7	43.4	43.0	42.3	41.1	40.4	39.3	38.6	38.1
82.5°	25.9	28.2	30.2	31.4	31.3	30.6	29.9	29.5	29.3	28.8	28.7
85°	12.2	12.7	13.4	15.0	16.2	16.4	16.2	15.9	15.3	15.5	15.7
87.5°	5.7	5.5	5.6	5.4	5.0	5.7	6.0	6.0	5.9	5.7	5.5
90°	7.4	6.5	5.6	4.6	3.6	2.6	1.6	0.6	1.6	2.6	3.6
92.5°	7.6	6.8	6.0	5.9	6.7	7.4	8.1	8.8	8.1	7.4	6.7
95°	18.8	23.6	28.4	31.0	31.4	31.8	32.1	32.5	32.1	31.8	31.4
97.5°	47.1	56.7	66.2	70.6	69.9	69.3	68.6	67.9	68.6	69.3	69.9
100°	98.3	97.8	97.2	96.8	96.4	96.0	95.7	95.3	95.7	96.0	96.4
102.5°	126.1	125.7	125.4	125.0	124.6	124.1	123.6	123.1	123.6	124.1	124.6
105°	170.0	170.0	170.0	169.8	169.3	168.8	168.2	167.7	168.2	168.8	169.3
107.5°	214.7	214.4	214.2	214.1	214.1	214.1	214.1	214.1	214.1	214.1	214.1
110°	244.8	244.6	244.3	244.2	244.2	244.2	244.2	244.2	244.2	244.2	244.2



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	274.2	274.1	273.9	273.7	273.4	273.1	272.8	272.5	272.8	273.1	273.4
115°	318.1	318.0	317.9	317.5	316.8	316.2	315.6	314.9	315.6	316.2	316.8
117.5°	360.0	359.5	359.0	358.8	358.8	358.8	358.8	358.9	358.8	358.8	358.8
120°	386.6	386.3	385.9	385.7	385.9	386.0	386.1	386.3	386.1	386.0	385.9
122.5°	413.1	412.9	412.7	412.4	411.9	411.4	410.9	410.4	410.9	411.4	411.9
125°	451.9	451.9	451.9	451.4	450.5	449.6	448.8	447.9	448.8	449.6	450.5
127.5°	486.3	486.3	486.4	486.1	485.5	484.9	484.2	483.6	484.2	484.9	485.5
130°	508.7	508.5	508.4	508.0	507.4	506.8	506.1	505.5	506.1	506.8	507.4
132.5°	530.0	530.3	530.6	530.3	529.6	528.9	528.1	527.4	528.1	528.9	529.6
135°	561.3	561.6	561.9	561.6	560.8	560.1	559.3	558.6	559.3	560.1	560.8
137.5°	589.6	589.8	590.1	589.8	589.2	588.5	587.9	587.2	587.9	588.5	589.2
140°	606.7	606.9	607.0	606.9	606.7	606.4	606.2	605.9	606.2	606.4	606.7
142.5°	623.9	623.8	623.6	623.4	623.3	623.1	623.0	622.8	623.0	623.1	623.3
145°	648.7	648.7	648.7	648.6	648.3	648.1	647.8	647.6	647.8	648.1	648.3
147.5°	669.4	669.2	669.1	669.0	669.1	669.1	669.2	669.2	669.2	669.1	669.1
150°	682.4	682.2	681.9	681.9	682.2	682.4	682.7	682.9	682.7	682.4	682.2
152.5°	694.3	694.0	693.8	693.9	694.5	695.1	695.6	696.2	695.6	695.1	694.5
155°	710.4	710.1	709.9	710.1	710.9	711.7	712.4	713.2	712.4	711.7	710.9
157.5°	724.3	724.3	724.3	724.5	724.9	725.4	725.8	726.3	725.8	725.4	724.9
160°	732.3	732.2	732.1	732.4	733.1	733.9	734.7	735.4	734.7	733.9	733.1
162.5°	739.6	739.5	739.4	739.7	740.4	741.2	742.0	742.7	742.0	741.2	740.4
165°	749.4	749.3	749.2	749.5	750.3	751.0	751.8	752.5	751.8	751.0	750.3
167.5°	756.6	756.5	756.4	756.7	757.5	758.3	759.1	759.8	759.1	758.3	757.5
170°	760.3	760.1	760.0	760.4	761.3	762.2	763.1	764.0	763.1	762.2	761.3
172.5°	763.3	763.0	762.8	763.1	764.0	764.9	765.8	766.7	765.8	764.9	764.0
175°	766.6	766.4	766.3	766.6	767.4	768.1	768.9	769.7	768.9	768.1	767.4
177.5°	768.5	768.4	768.3	768.6	769.2	769.8	770.4	771.0	770.4	769.8	769.2
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	553.4	550.9	549.0	545.3	542.7	541.6	539.6	539.0	541.1	539.6	539.4
5°	537.0	530.3	525.0	519.7	513.9	510.2	504.6	503.7	502.3	500.3	499.8
7.5°	517.3	508.5	501.7	492.9	485.3	479.1	472.2	468.9	467.1	464.4	460.8
10°	504.0	493.6	484.3	475.5	466.1	458.4	451.5	446.2	442.7	439.5	438.1
12.5°	490.8	480.2	468.4	457.8	447.2	438.7	431.0	427.5	423.7	419.9	416.7
15°	470.4	456.4	443.4	431.2	422.2	412.9	405.5	400.4	394.7	393.0	386.8
17.5°	448.8	435.0	419.8	407.0	396.5	386.3	378.2	372.4	368.1	362.1	359.3
20°	435.3	418.9	404.1	392.3	380.8	368.8	360.5	355.6	351.5	346.6	344.3
22.5°	420.9	404.9	389.7	375.9	364.2	352.3	346.4	341.4	336.7	332.2	329.1
25°	399.7	383.6	367.6	353.3	341.1	332.5	325.6	319.8	317.3	312.9	309.6
27.5°	378.8	361.6	345.1	330.8	321.2	312.7	307.0	302.5	297.9	294.1	291.2
30°	365.3	347.8	329.7	318.4	308.2	300.2	293.9	289.5	286.1	282.6	280.5
32.5°	351.8	333.7	317.7	305.5	295.9	288.9	282.5	278.2	274.6	270.8	268.3
35°	330.2	311.7	298.8	286.8	277.3	270.8	266.4	260.4	257.4	254.6	252.1
37.5°	310.1	292.9	278.9	268.4	260.1	253.7	248.0	244.8	241.1	238.6	236.5
40°	295.3	279.6	266.9	255.8	249.8	242.6	237.3	233.1	230.4	227.1	224.8
42.5°	282.0	267.4	255.0	245.1	237.6	231.5	226.4	222.2	218.7	216.4	214.5
45°	263.2	248.6	236.6	227.4	220.4	214.7	209.3	207.3	202.6	199.9	198.9
47.5°	243.7	230.7	219.1	210.6	203.5	198.0	193.0	188.8	186.2	183.5	182.0
50°	230.6	218.1	207.3	198.9	192.0	186.0	181.4	178.6	175.1	172.6	170.8
52.5°	217.5	205.9	195.1	187.1	181.1	175.1	169.9	167.2	163.9	162.3	161.0
55°	198.7	186.5	177.2	169.4	163.1	157.6	152.7	150.0	147.9	146.3	145.8
57.5°	177.5	167.8	159.2	152.1	145.6	140.4	136.1	133.5	131.7	131.4	130.0
60°	163.6	154.8	147.0	139.3	133.8	128.9	125.2	122.2	120.4	120.2	119.7
62.5°	149.7	141.3	134.0	127.3	122.3	117.7	114.1	110.8	109.7	108.5	107.5
65°	129.2	121.5	115.5	110.2	104.9	101.0	97.5	95.4	92.9	91.5	89.0
67.5°	109.0	103.1	97.3	92.8	88.6	84.9	82.0	78.9	77.2	76.1	74.3
70°	95.7	91.0	85.3	80.4	77.2	74.2	71.9	68.4	67.2	66.3	65.4
72.5°	83.1	79.0	74.2	70.2	67.0	64.2	61.5	59.9	58.7	57.8	57.3
75°	65.4	61.5	57.3	54.5	52.2	49.9	48.5	47.4	46.9	46.7	45.8
77.5°	48.0	45.9	42.6	40.4	38.9	37.9	36.7	36.1	36.0	35.0	34.7
80°	36.7	35.6	32.8	31.9	30.7	29.8	29.1	28.0	26.8	26.3	25.6
82.5°	27.3	26.2	25.0	23.6	22.6	22.0	21.4	20.9	21.1	20.4	20.1
85°	14.6	13.4	12.9	12.7	12.2	12.7	12.5	12.2	12.0	11.8	12.0
87.5°	5.5	5.7	5.7	6.3	5.9	6.3	6.4	6.3	6.5	6.6	6.5
90°	4.6	5.6	6.5	7.4	8.2	9.1	9.8	10.4	11.0	11.7	12.2
92.5°	5.9	6.0	6.8	7.6	8.3	9.1	9.8	10.4	11.0	11.7	12.1
95°	31.0	28.4	23.6	18.8	13.9	9.1	9.8	10.4	11.0	11.7	12.0
97.5°	70.6	66.2	56.7	47.1	37.6	28.1	24.5	20.9	17.3	13.8	12.0
100°	96.8	97.2	97.8	98.3	98.8	99.3	80.4	61.5	42.6	23.7	14.0
102.5°	125.0	125.4	125.7	126.1	126.4	126.7	123.1	119.5	115.9	112.4	106.3
105°	169.8	170.0	170.0	170.0	170.0	170.0	170.0	170.0	170.0	170.0	170.0
107.5°	214.1	214.2	214.4	214.7	215.0	215.2	215.2	215.3	215.3	215.3	215.1
110°	244.2	244.3	244.6	244.8	245.1	245.3	245.0	244.6	244.2	243.8	243.7



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	273.7	273.9	274.1	274.2	274.4	274.5	274.1	273.6	273.1	272.6	272.3
115°	317.5	317.9	318.0	318.1	318.2	318.4	317.9	317.3	316.8	316.3	315.7
117.5°	358.8	359.0	359.5	360.0	360.4	360.9	360.3	359.6	358.9	358.3	357.8
120°	385.7	385.9	386.3	386.6	387.0	387.4	387.1	386.9	386.6	386.4	385.9
122.5°	412.4	412.7	412.9	413.1	413.2	413.4	413.2	412.9	412.7	412.4	411.9
125°	451.4	451.9	451.9	451.9	451.9	451.9	451.4	450.9	450.3	449.8	449.4
127.5°	486.1	486.4	486.3	486.3	486.2	486.1	485.8	485.5	485.3	485.0	484.4
130°	508.0	508.4	508.5	508.7	508.8	508.9	508.5	508.2	507.8	507.4	506.9
132.5°	530.3	530.6	530.3	530.0	529.7	529.5	529.4	529.3	529.2	529.2	528.8
135°	561.6	561.9	561.6	561.3	561.1	560.8	560.6	560.3	560.1	559.8	559.3
137.5°	589.8	590.1	589.8	589.6	589.4	589.1	589.2	589.2	589.3	589.3	589.0
140°	606.9	607.0	606.9	606.7	606.6	606.5	606.7	607.0	607.2	607.5	607.2
142.5°	623.4	623.6	623.8	623.9	624.1	624.3	624.3	624.4	624.4	624.5	624.1
145°	648.6	648.7	648.7	648.7	648.7	648.7	648.8	649.0	649.1	649.2	648.9
147.5°	669.0	669.1	669.2	669.4	669.5	669.7	669.9	670.0	670.2	670.3	669.9
150°	681.9	681.9	682.2	682.4	682.7	682.9	683.2	683.4	683.7	683.9	683.6
152.5°	693.9	693.8	694.0	694.3	694.5	694.8	695.1	695.3	695.6	695.8	695.5
155°	710.1	709.9	710.1	710.4	710.6	710.9	711.3	711.7	712.0	712.4	712.1
157.5°	724.5	724.3	724.3	724.3	724.3	724.4	724.8	725.2	725.6	726.0	725.7
160°	732.4	732.1	732.2	732.3	732.4	732.6	733.1	733.6	734.1	734.6	734.3
162.5°	739.7	739.4	739.5	739.6	739.7	739.9	740.6	741.3	742.0	742.7	742.5
165°	749.5	749.2	749.3	749.4	749.6	749.7	750.4	751.2	752.0	752.7	752.6
167.5°	756.7	756.4	756.5	756.6	756.7	756.9	757.8	758.7	759.6	760.5	760.4
170°	760.4	760.0	760.1	760.3	760.4	760.5	761.5	762.6	763.6	764.6	764.5
172.5°	763.1	762.8	763.0	763.3	763.5	763.7	764.6	765.5	766.5	767.4	767.3
175°	766.6	766.3	766.4	766.6	766.7	766.8	767.8	768.8	769.8	770.9	770.8
177.5°	768.6	768.3	768.4	768.5	768.6	768.7	769.5	770.2	770.9	771.6	771.5
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.2	537.2	536.6	537.4	536.6	537.2	539.2	539.4	539.6	541.1	539.0
5°	497.5	495.2	496.3	495.9	496.3	495.2	497.5	499.8	500.3	502.3	503.7
7.5°	460.8	457.9	454.9	455.8	454.9	457.9	460.8	460.8	464.4	467.1	468.9
10°	435.1	432.8	431.4	432.6	431.4	432.8	435.1	438.1	439.5	442.7	446.2
12.5°	413.5	412.1	410.9	410.4	410.9	412.1	413.5	416.7	419.9	423.7	427.5
15°	384.0	381.3	380.1	377.1	380.1	381.3	384.0	386.8	393.0	394.7	400.4
17.5°	356.9	356.0	353.0	351.7	353.0	356.0	356.9	359.3	362.1	368.1	372.4
20°	340.8	339.9	336.9	338.7	336.9	339.9	340.8	344.3	346.6	351.5	355.6
22.5°	327.5	325.5	324.5	324.0	324.5	325.5	327.5	329.1	332.2	336.7	341.4
25°	308.7	305.7	304.5	303.2	304.5	305.7	308.7	309.6	312.9	317.3	319.8
27.5°	289.9	288.3	286.8	286.4	286.8	288.3	289.9	291.2	294.1	297.9	302.5
30°	277.7	276.1	275.0	275.0	275.0	276.1	277.7	280.5	282.6	286.1	289.5
32.5°	266.8	265.6	264.4	264.2	264.4	265.6	266.8	268.3	270.8	274.6	278.2
35°	250.9	249.1	248.6	247.2	248.6	249.1	250.9	252.1	254.6	257.4	260.4
37.5°	234.4	232.9	232.9	232.7	232.9	232.9	234.4	236.5	238.6	241.1	244.8
40°	223.9	222.7	222.5	220.9	222.5	222.7	223.9	224.8	227.1	230.4	233.1
42.5°	212.6	212.0	211.2	210.5	211.2	212.0	212.6	214.5	216.4	218.7	222.2
45°	197.3	195.7	195.7	194.6	195.7	195.7	197.3	198.9	199.9	202.6	207.3
47.5°	181.5	180.3	180.4	179.2	180.4	180.3	181.5	182.0	183.5	186.2	188.8
50°	171.0	170.3	170.1	169.6	170.1	170.3	171.0	170.8	172.6	175.1	178.6
52.5°	160.5	160.1	161.0	160.0	161.0	160.1	160.5	161.0	162.3	163.9	167.2
55°	146.3	145.6	147.0	145.6	147.0	145.6	146.3	145.8	146.3	147.9	150.0
57.5°	130.0	129.3	130.6	129.9	130.6	129.3	130.0	130.0	131.4	131.7	133.5
60°	119.2	117.8	118.5	118.8	118.5	117.8	119.2	119.7	120.2	120.4	122.2
62.5°	106.5	105.6	106.2	105.1	106.2	105.6	106.5	107.5	108.5	109.7	110.8
65°	88.5	87.8	86.9	86.4	86.9	87.8	88.5	89.0	91.5	92.9	95.4
67.5°	74.4	72.7	72.6	73.0	72.6	72.7	74.4	74.3	76.1	77.2	78.9
70°	64.0	64.0	63.8	63.8	63.8	64.0	64.0	65.4	66.3	67.2	68.4
72.5°	56.8	56.6	56.2	56.0	56.2	56.6	56.8	57.3	57.8	58.7	59.9
75°	45.8	46.0	45.5	45.3	45.5	46.0	45.8	45.8	46.7	46.9	47.4
77.5°	33.8	32.8	33.3	32.8	33.3	32.8	33.8	34.7	35.0	36.0	36.1
80°	25.6	25.4	26.1	25.4	26.1	25.4	25.6	25.6	26.3	26.8	28.0
82.5°	20.3	20.1	20.4	19.9	20.4	20.1	20.3	20.1	20.4	21.1	20.9
85°	12.2	12.0	11.8	12.0	11.8	12.0	12.2	12.0	11.8	12.0	12.2
87.5°	6.8	6.7	6.7	6.8	6.7	6.7	6.8	6.5	6.6	6.5	6.3
90°	12.6	12.9	13.3	13.7	13.3	12.9	12.6	12.2	11.7	11.0	10.4
92.5°	12.2	12.4	12.6	12.8	12.6	12.4	12.2	12.1	11.7	11.0	10.4
95°	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0	11.7	11.0	10.4
97.5°	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0	13.8	17.3	20.9
100°	13.5	13.0	12.5	12.0	12.5	13.0	13.5	14.0	23.7	42.6	61.5
102.5°	97.6	89.0	80.4	71.8	80.4	89.0	97.6	106.3	112.4	115.9	119.5
105°	169.8	169.7	169.6	169.4	169.6	169.7	169.8	170.0	170.0	170.0	170.0
107.5°	214.8	214.4	214.0	213.6	214.0	214.4	214.8	215.1	215.3	215.3	215.3
110°	243.8	243.9	244.1	244.2	244.1	243.9	243.8	243.7	243.8	244.2	244.6



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	272.1	271.9	271.8	271.6	271.8	271.9	272.1	272.3	272.6	273.1	273.6
115°	314.9	314.2	313.4	312.7	313.4	314.2	314.9	315.7	316.3	316.8	317.3
117.5°	357.5	357.1	356.8	356.5	356.8	357.1	357.5	357.8	358.3	358.9	359.6
120°	385.3	384.7	384.0	383.4	384.0	384.7	385.3	385.9	386.4	386.6	386.9
122.5°	411.2	410.4	409.7	409.0	409.7	410.4	411.2	411.9	412.4	412.7	412.9
125°	449.0	448.6	448.3	447.9	448.3	448.6	449.0	449.4	449.8	450.3	450.9
127.5°	483.4	482.5	481.6	480.6	481.6	482.5	483.4	484.4	485.0	485.3	485.5
130°	506.3	505.6	505.0	504.4	505.0	505.6	506.3	506.9	507.4	507.8	508.2
132.5°	528.2	527.5	526.9	526.3	526.9	527.5	528.2	528.8	529.2	529.2	529.3
135°	558.6	557.8	557.0	556.3	557.0	557.8	558.6	559.3	559.8	560.1	560.3
137.5°	588.4	587.7	587.1	586.4	587.1	587.7	588.4	589.0	589.3	589.3	589.2
140°	606.5	605.7	605.0	604.2	605.0	605.7	606.5	607.2	607.5	607.2	607.0
142.5°	623.4	622.6	621.8	621.1	621.8	622.6	623.4	624.1	624.5	624.4	624.4
145°	648.1	647.4	646.6	645.8	646.6	647.4	648.1	648.9	649.2	649.1	649.0
147.5°	669.0	668.1	667.2	666.3	667.2	668.1	669.0	669.9	670.3	670.2	670.0
150°	682.6	681.5	680.5	679.5	680.5	681.5	682.6	683.6	683.9	683.7	683.4
152.5°	694.6	693.7	692.7	691.8	692.7	693.7	694.6	695.5	695.8	695.6	695.3
155°	711.1	710.1	709.1	708.0	709.1	710.1	711.1	712.1	712.4	712.0	711.7
157.5°	724.7	723.6	722.6	721.6	722.6	723.6	724.7	725.7	726.0	725.6	725.2
160°	733.3	732.3	731.3	730.3	731.3	732.3	733.3	734.3	734.6	734.1	733.6
162.5°	741.4	740.3	739.2	738.0	739.2	740.3	741.4	742.5	742.7	742.0	741.3
165°	751.6	750.6	749.6	748.5	749.6	750.6	751.6	752.6	752.7	752.0	751.2
167.5°	759.3	758.1	757.0	755.8	757.0	758.1	759.3	760.4	760.5	759.6	758.7
170°	763.4	762.2	761.1	760.0	761.1	762.2	763.4	764.5	764.6	763.6	762.6
172.5°	766.1	765.0	763.8	762.7	763.8	765.0	766.1	767.3	767.4	766.5	765.5
175°	769.7	768.5	767.4	766.2	767.4	768.5	769.7	770.8	770.9	769.8	768.8
177.5°	770.7	769.9	769.1	768.3	769.1	769.9	770.7	771.5	771.6	770.9	770.2
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.6	541.6	542.7	545.3	549.0	550.9	553.4	555.3	557.9	561.0	563.6
5°	504.6	510.2	513.9	519.7	525.0	530.3	537.0	541.8	548.3	555.7	561.5
7.5°	472.2	479.1	485.3	492.9	501.7	508.5	517.3	526.2	536.3	546.8	556.7
10°	451.5	458.4	466.1	475.5	484.3	493.6	504.0	514.4	527.1	538.8	552.2
12.5°	431.0	438.7	447.2	457.8	468.4	480.2	490.8	502.5	516.2	531.5	545.8
15°	405.5	412.9	422.2	431.2	443.4	456.4	470.4	485.9	501.2	518.3	536.1
17.5°	378.2	386.3	396.5	407.0	419.8	435.0	448.8	465.8	482.9	502.8	523.8
20°	360.5	368.8	380.8	392.3	404.1	418.9	435.3	452.7	470.9	491.9	515.3
22.5°	346.4	352.3	364.2	375.9	389.7	404.9	420.9	439.0	458.9	480.7	505.1
25°	325.6	332.5	341.1	353.3	367.6	383.6	399.7	418.9	440.6	462.8	488.9
27.5°	307.0	312.7	321.2	330.8	345.1	361.6	378.8	398.8	421.1	443.7	471.1
30°	293.9	300.2	308.2	318.4	329.7	347.8	365.3	385.0	407.6	430.9	459.1
32.5°	282.5	288.9	295.9	305.5	317.7	333.7	351.8	371.1	394.1	418.2	445.6
35°	266.4	270.8	277.3	286.8	298.8	311.7	330.2	350.5	372.9	397.9	425.4
37.5°	248.0	253.7	260.1	268.4	278.9	292.9	310.1	330.7	351.5	375.3	400.4
40°	237.3	242.6	249.8	255.8	266.9	279.6	295.3	316.8	337.6	360.0	382.9
42.5°	226.4	231.5	237.6	245.1	255.0	267.4	282.0	302.0	324.3	345.4	364.6
45°	209.3	214.7	220.4	227.4	236.6	248.6	263.2	281.4	300.8	320.3	334.8
47.5°	193.0	198.0	203.5	210.6	219.1	230.7	243.7	259.9	278.7	295.2	305.6
50°	181.4	186.0	192.0	198.9	207.3	218.1	230.6	246.5	262.3	277.3	286.8
52.5°	169.9	175.1	181.1	187.1	195.1	205.9	217.5	231.2	246.2	258.4	266.2
55°	152.7	157.6	163.1	169.4	177.2	186.5	198.7	209.6	221.4	231.8	236.4
57.5°	136.1	140.4	145.6	152.1	159.2	167.8	177.5	187.9	196.2	203.6	208.8
60°	125.2	128.9	133.8	139.3	147.0	154.8	163.6	173.3	179.8	186.0	190.9
62.5°	114.1	117.7	122.3	127.3	134.0	141.3	149.7	157.6	163.9	168.1	173.7
65°	97.5	101.0	104.9	110.2	115.5	121.5	129.2	134.9	139.3	144.0	147.4
67.5°	82.0	84.9	88.6	92.8	97.3	103.1	109.0	113.8	116.8	119.6	123.7
70°	71.9	74.2	77.2	80.4	85.3	91.0	95.7	99.4	101.4	104.2	109.3
72.5°	61.5	64.2	67.0	70.2	74.2	79.0	83.1	86.8	88.1	90.3	93.6
75°	48.5	49.9	52.2	54.5	57.3	61.5	65.4	66.3	67.5	69.3	71.6
77.5°	36.7	37.9	38.9	40.4	42.6	45.9	48.0	49.4	49.7	50.4	52.6
80°	29.1	29.8	30.7	31.9	32.8	35.6	36.7	38.1	38.6	39.3	40.4
82.5°	21.4	22.0	22.6	23.6	25.0	26.2	27.3	28.7	28.8	29.3	29.5
85°	12.5	12.7	12.2	12.7	12.9	13.4	14.6	15.7	15.5	15.3	15.9
87.5°	6.4	6.3	5.9	6.3	5.7	5.7	5.5	5.5	5.7	5.9	6.0
90°	9.8	9.1	8.2	7.4	6.5	5.6	4.6	3.6	2.6	1.6	0.6
92.5°	9.8	9.1	8.3	7.6	6.8	6.0	5.9	6.7	7.4	8.1	8.8
95°	9.8	9.1	13.9	18.8	23.6	28.4	31.0	31.4	31.8	32.1	32.5
97.5°	24.5	28.1	37.6	47.1	56.7	66.2	70.6	69.9	69.3	68.6	67.9
100°	80.4	99.3	98.8	98.3	97.8	97.2	96.8	96.4	96.0	95.7	95.3
102.5°	123.1	126.7	126.4	126.1	125.7	125.4	125.0	124.6	124.1	123.6	123.1
105°	170.0	170.0	170.0	170.0	170.0	170.0	169.8	169.3	168.8	168.2	167.7
107.5°	215.2	215.2	215.0	214.7	214.4	214.2	214.1	214.1	214.1	214.1	214.1
110°	245.0	245.3	245.1	244.8	244.6	244.3	244.2	244.2	244.2	244.2	244.2



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	274.1	274.5	274.4	274.2	274.1	273.9	273.7	273.4	273.1	272.8	272.5
115°	317.9	318.4	318.2	318.1	318.0	317.9	317.5	316.8	316.2	315.6	314.9
117.5°	360.3	360.9	360.4	360.0	359.5	359.0	358.8	358.8	358.8	358.8	358.9
120°	387.1	387.4	387.0	386.6	386.3	385.9	385.7	385.9	386.0	386.1	386.3
122.5°	413.2	413.4	413.2	413.1	412.9	412.7	412.4	411.9	411.4	410.9	410.4
125°	451.4	451.9	451.9	451.9	451.9	451.9	451.4	450.5	449.6	448.8	447.9
127.5°	485.8	486.1	486.2	486.3	486.3	486.4	486.1	485.5	484.9	484.2	483.6
130°	508.5	508.9	508.8	508.7	508.5	508.4	508.0	507.4	506.8	506.1	505.5
132.5°	529.4	529.5	529.7	530.0	530.3	530.6	530.3	529.6	528.9	528.1	527.4
135°	560.6	560.8	561.1	561.3	561.6	561.9	561.6	560.8	560.1	559.3	558.6
137.5°	589.2	589.1	589.4	589.6	589.8	590.1	589.8	589.2	588.5	587.9	587.2
140°	606.7	606.5	606.6	606.7	606.9	607.0	606.9	606.7	606.4	606.2	605.9
142.5°	624.3	624.3	624.1	623.9	623.8	623.6	623.4	623.3	623.1	623.0	622.8
145°	648.8	648.7	648.7	648.7	648.7	648.7	648.6	648.3	648.1	647.8	647.6
147.5°	669.9	669.7	669.5	669.4	669.2	669.1	669.0	669.1	669.1	669.2	669.2
150°	683.2	682.9	682.7	682.4	682.2	681.9	681.9	682.2	682.4	682.7	682.9
152.5°	695.1	694.8	694.5	694.3	694.0	693.8	693.9	694.5	695.1	695.6	696.2
155°	711.3	710.9	710.6	710.4	710.1	709.9	710.1	710.9	711.7	712.4	713.2
157.5°	724.8	724.4	724.3	724.3	724.3	724.3	724.5	724.9	725.4	725.8	726.3
160°	733.1	732.6	732.4	732.3	732.2	732.1	732.4	733.1	733.9	734.7	735.4
162.5°	740.6	739.9	739.7	739.6	739.5	739.4	739.7	740.4	741.2	742.0	742.7
165°	750.4	749.7	749.6	749.4	749.3	749.2	749.5	750.3	751.0	751.8	752.5
167.5°	757.8	756.9	756.7	756.6	756.5	756.4	756.7	757.5	758.3	759.1	759.8
170°	761.5	760.5	760.4	760.3	760.1	760.0	760.4	761.3	762.2	763.1	764.0
172.5°	764.6	763.7	763.5	763.3	763.0	762.8	763.1	764.0	764.9	765.8	766.7
175°	767.8	766.8	766.7	766.6	766.4	766.3	766.6	767.4	768.1	768.9	769.7
177.5°	769.5	768.7	768.6	768.5	768.4	768.3	768.6	769.2	769.8	770.4	771.0
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	565.6	567.3	569.7	572.5	574.7	577.1	578.4	578.4	579.5	581.9	585.1
5°	567.3	573.3	579.0	586.4	592.2	598.9	604.0	608.9	613.2	618.8	624.6
7.5°	566.8	576.8	587.2	598.8	611.7	621.9	632.4	640.6	648.7	659.4	667.7
10°	565.0	577.9	592.0	606.8	623.0	637.0	649.8	661.3	672.4	684.0	694.4
12.5°	561.6	578.1	595.3	613.1	633.5	649.6	666.0	678.3	691.3	703.9	716.7
15°	556.6	576.0	596.8	621.6	646.5	664.5	680.7	696.7	708.7	723.0	735.3
17.5°	546.3	571.3	597.5	624.5	648.5	669.4	686.4	701.6	714.4	730.1	746.8
20°	540.2	567.3	594.5	623.4	646.3	667.8	684.2	699.9	715.8	736.4	756.7
22.5°	531.7	560.6	589.5	616.9	641.1	661.9	678.8	698.0	719.0	742.3	766.9
25°	518.3	548.1	576.7	602.8	626.4	647.7	670.8	696.7	722.1	752.8	788.2
27.5°	501.2	530.0	555.5	583.1	606.5	633.6	662.4	690.5	727.1	769.4	813.5
30°	488.5	515.7	540.0	566.1	592.7	622.5	654.8	687.9	731.6	781.2	833.7
32.5°	473.7	498.4	522.4	547.6	578.3	611.0	645.4	685.8	738.0	794.5	848.8
35°	448.0	470.2	493.6	521.5	554.1	589.7	633.6	682.8	745.9	806.6	855.4
37.5°	421.1	438.7	462.1	491.6	527.1	568.2	618.1	677.9	742.6	797.2	817.9
40°	400.4	416.8	441.6	472.5	507.7	552.7	608.6	670.1	735.3	773.1	771.5
42.5°	379.9	396.5	420.3	451.5	488.1	538.5	596.1	659.9	714.9	729.3	699.3
45°	348.4	363.9	387.3	418.7	458.0	510.9	571.4	632.7	667.8	644.4	584.8
47.5°	316.4	331.4	353.1	383.8	426.7	482.1	539.4	589.6	594.5	544.4	472.9
50°	295.3	309.4	330.0	362.8	404.4	458.4	513.7	553.2	540.9	479.7	406.0
52.5°	274.8	288.3	307.6	338.6	381.1	434.0	483.3	514.4	486.0	420.9	354.6
55°	244.5	257.4	276.8	305.2	343.8	392.3	435.6	446.9	405.3	339.7	286.1
57.5°	215.7	225.2	244.3	269.5	306.7	349.5	380.4	378.4	332.5	273.4	234.9
60°	196.6	205.2	223.4	246.5	281.9	320.3	342.0	332.7	286.3	237.5	200.6
62.5°	178.9	186.9	202.2	223.4	253.8	287.2	303.0	290.2	246.4	203.5	174.1
65°	152.0	157.8	170.1	189.7	213.5	236.6	250.7	232.0	193.2	160.8	138.6
67.5°	126.9	131.9	142.8	156.9	173.3	189.3	195.0	177.5	147.3	125.5	109.8
70°	110.7	115.3	122.7	135.9	146.7	158.0	160.8	145.1	119.9	103.3	93.6
72.5°	95.2	99.4	105.9	115.2	122.7	129.2	130.5	115.9	96.6	85.2	77.7
75°	72.6	76.3	80.4	83.9	88.7	89.9	89.4	78.1	67.7	60.1	55.9
77.5°	53.3	54.9	57.4	58.8	59.0	58.9	56.6	49.4	44.0	40.9	39.2
80°	41.1	42.3	43.0	43.4	43.7	41.4	38.8	34.4	32.6	30.7	28.7
82.5°	29.9	30.6	31.3	31.4	30.2	28.2	25.9	23.7	22.4	21.5	20.7
85°	16.2	16.4	16.2	15.0	13.4	12.7	12.2	11.8	11.6	11.3	11.3
87.5°	6.0	5.7	5.0	5.4	5.6	5.5	5.7	5.7	5.7	5.8	6.0
90°	1.6	2.6	3.6	4.6	5.6	6.5	7.4	8.2	9.1	9.8	10.4
92.5°	8.1	7.4	6.7	5.9	6.0	6.8	7.6	8.3	9.1	9.8	10.4
95°	32.1	31.8	31.4	31.0	28.4	23.6	18.8	13.9	9.1	9.8	10.4
97.5°	68.6	69.3	69.9	70.6	66.2	56.7	47.1	37.6	28.1	24.5	20.9
100°	95.7	96.0	96.4	96.8	97.2	97.8	98.3	98.8	99.3	80.4	61.5
102.5°	123.6	124.1	124.6	125.0	125.4	125.7	126.1	126.4	126.7	123.1	119.5
105°	168.2	168.8	169.3	169.8	170.0	170.0	170.0	170.0	170.0	170.0	170.0
107.5°	214.1	214.1	214.1	214.1	214.2	214.4	214.7	215.0	215.2	215.2	215.3
110°	244.2	244.2	244.2	244.2	244.3	244.6	244.8	245.1	245.3	245.0	244.6



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.8	273.1	273.4	273.7	273.9	274.1	274.2	274.4	274.5	274.1	273.6
115°	315.6	316.2	316.8	317.5	317.9	318.0	318.1	318.2	318.4	317.9	317.3
117.5°	358.8	358.8	358.8	358.8	359.0	359.5	360.0	360.4	360.9	360.3	359.6
120°	386.1	386.0	385.9	385.7	385.9	386.3	386.6	387.0	387.4	387.1	386.9
122.5°	410.9	411.4	411.9	412.4	412.7	412.9	413.1	413.2	413.4	413.2	412.9
125°	448.8	449.6	450.5	451.4	451.9	451.9	451.9	451.9	451.9	451.4	450.9
127.5°	484.2	484.9	485.5	486.1	486.4	486.3	486.3	486.2	486.1	485.8	485.5
130°	506.1	506.8	507.4	508.0	508.4	508.5	508.7	508.8	508.9	508.5	508.2
132.5°	528.1	528.9	529.6	530.3	530.6	530.3	530.0	529.7	529.5	529.4	529.3
135°	559.3	560.1	560.8	561.6	561.9	561.6	561.3	561.1	560.8	560.6	560.3
137.5°	587.9	588.5	589.2	589.8	590.1	589.8	589.6	589.4	589.1	589.2	589.2
140°	606.2	606.4	606.7	606.9	607.0	606.9	606.7	606.6	606.5	606.7	607.0
142.5°	623.0	623.1	623.3	623.4	623.6	623.8	623.9	624.1	624.3	624.3	624.4
145°	647.8	648.1	648.3	648.6	648.7	648.7	648.7	648.7	648.7	648.8	649.0
147.5°	669.2	669.1	669.1	669.0	669.1	669.2	669.4	669.5	669.7	669.9	670.0
150°	682.7	682.4	682.2	681.9	681.9	682.2	682.4	682.7	682.9	683.2	683.4
152.5°	695.6	695.1	694.5	693.9	693.8	694.0	694.3	694.5	694.8	695.1	695.3
155°	712.4	711.7	710.9	710.1	709.9	710.1	710.4	710.6	710.9	711.3	711.7
157.5°	725.8	725.4	724.9	724.5	724.3	724.3	724.3	724.3	724.4	724.8	725.2
160°	734.7	733.9	733.1	732.4	732.1	732.2	732.3	732.4	732.6	733.1	733.6
162.5°	742.0	741.2	740.4	739.7	739.4	739.5	739.6	739.7	739.9	740.6	741.3
165°	751.8	751.0	750.3	749.5	749.2	749.3	749.4	749.6	749.7	750.4	751.2
167.5°	759.1	758.3	757.5	756.7	756.4	756.5	756.6	756.7	756.9	757.8	758.7
170°	763.1	762.2	761.3	760.4	760.0	760.1	760.3	760.4	760.5	761.5	762.6
172.5°	765.8	764.9	764.0	763.1	762.8	763.0	763.3	763.5	763.7	764.6	765.5
175°	768.9	768.1	767.4	766.6	766.3	766.4	766.6	766.7	766.8	767.8	768.8
177.5°	770.4	769.8	769.2	768.6	768.3	768.4	768.5	768.6	768.7	769.5	770.2
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	587.5	587.5	590.6	590.4	592.5	591.7	592.1
5°	631.5	635.4	638.9	641.2	644.7	645.6	645.1
7.5°	677.2	685.9	690.1	696.0	697.0	700.1	699.8
10°	705.4	714.0	720.5	725.5	728.1	731.3	731.6
12.5°	727.6	734.9	740.6	745.3	748.4	749.4	750.0
15°	745.0	753.0	759.7	766.4	770.4	773.4	775.0
17.5°	762.4	774.9	786.7	795.8	801.3	805.9	805.9
20°	775.9	790.2	805.0	815.4	826.1	830.7	831.4
22.5°	790.3	812.2	831.3	847.4	861.4	866.2	868.0
25°	820.3	848.9	878.3	900.9	917.1	926.6	928.0
27.5°	856.5	895.2	926.1	947.0	960.4	967.5	969.0
30°	882.0	917.8	945.5	961.2	967.5	968.4	964.9
32.5°	893.4	920.2	931.3	930.4	918.1	910.0	906.9
35°	879.4	873.9	846.9	814.5	789.8	774.1	769.9
37.5°	800.3	752.5	702.8	653.9	627.9	614.6	591.9
40°	722.3	654.1	602.4	561.3	531.9	508.3	502.8
42.5°	634.3	563.9	512.2	477.0	453.5	437.4	430.3
45°	509.7	449.2	406.4	379.4	361.4	349.6	344.3
47.5°	407.7	360.8	329.7	309.7	295.9	285.7	282.8
50°	351.7	314.2	287.9	271.0	260.6	252.8	249.6
52.5°	305.5	275.2	255.0	241.1	231.3	226.4	223.7
55°	252.1	226.0	211.4	200.3	194.8	190.9	189.0
57.5°	206.2	187.3	176.7	169.0	163.9	161.4	160.5
60°	180.5	165.7	156.0	150.0	146.5	143.3	142.3
62.5°	157.7	146.1	138.6	133.3	129.9	128.5	127.9
65°	127.1	119.5	113.9	110.7	107.9	107.4	107.2
67.5°	101.0	96.5	93.6	90.3	89.3	87.7	87.3
70°	86.4	83.4	79.9	78.8	77.6	76.0	76.3
72.5°	73.3	70.3	67.9	66.4	66.0	65.3	65.9
75°	53.6	52.7	51.8	50.6	50.1	50.1	49.9
77.5°	38.3	37.5	36.5	35.8	35.6	34.7	35.0
80°	27.7	26.6	26.1	26.3	25.6	25.4	25.4
82.5°	20.5	20.1	19.6	19.7	19.5	19.3	19.5
85°	11.3	11.1	11.1	10.9	10.9	10.6	10.6
87.5°	6.3	6.6	6.3	6.2	6.3	6.5	6.8
90°	11.0	11.7	12.2	12.6	12.9	13.3	13.7
92.5°	11.0	11.7	12.1	12.2	12.4	12.6	12.8
95°	11.0	11.7	12.0	12.0	12.0	12.0	12.0
97.5°	17.3	13.8	12.0	12.0	12.0	12.0	12.0
100°	42.6	23.7	14.0	13.5	13.0	12.5	12.0
102.5°	115.9	112.4	106.3	97.6	89.0	80.4	71.8
105°	170.0	170.0	170.0	169.8	169.7	169.6	169.4
107.5°	215.3	215.3	215.1	214.8	214.4	214.0	213.6
110°	244.2	243.8	243.7	243.8	243.9	244.1	244.2



TEST NUMBER: P333496

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	273.1	272.6	272.3	272.1	271.9	271.8	271.6
115°	316.8	316.3	315.7	314.9	314.2	313.4	312.7
117.5°	358.9	358.3	357.8	357.5	357.1	356.8	356.5
120°	386.6	386.4	385.9	385.3	384.7	384.0	383.4
122.5°	412.7	412.4	411.9	411.2	410.4	409.7	409.0
125°	450.3	449.8	449.4	449.0	448.6	448.3	447.9
127.5°	485.3	485.0	484.4	483.4	482.5	481.6	480.6
130°	507.8	507.4	506.9	506.3	505.6	505.0	504.4
132.5°	529.2	529.2	528.8	528.2	527.5	526.9	526.3
135°	560.1	559.8	559.3	558.6	557.8	557.0	556.3
137.5°	589.3	589.3	589.0	588.4	587.7	587.1	586.4
140°	607.2	607.5	607.2	606.5	605.7	605.0	604.2
142.5°	624.4	624.5	624.1	623.4	622.6	621.8	621.1
145°	649.1	649.2	648.9	648.1	647.4	646.6	645.8
147.5°	670.2	670.3	669.9	669.0	668.1	667.2	666.3
150°	683.7	683.9	683.6	682.6	681.5	680.5	679.5
152.5°	695.6	695.8	695.5	694.6	693.7	692.7	691.8
155°	712.0	712.4	712.1	711.1	710.1	709.1	708.0
157.5°	725.6	726.0	725.7	724.7	723.6	722.6	721.6
160°	734.1	734.6	734.3	733.3	732.3	731.3	730.3
162.5°	742.0	742.7	742.5	741.4	740.3	739.2	738.0
165°	752.0	752.7	752.6	751.6	750.6	749.6	748.5
167.5°	759.6	760.5	760.4	759.3	758.1	757.0	755.8
170°	763.6	764.6	764.5	763.4	762.2	761.1	760.0
172.5°	766.5	767.4	767.3	766.1	765.0	763.8	762.7
175°	769.8	770.9	770.8	769.7	768.5	767.4	766.2
177.5°	770.9	771.6	771.5	770.7	769.9	769.1	768.3
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7

(END OF REPORT)