

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333497

Luminaire Tested: **S125RDIP-S375D590U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333497
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D590U835-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3505.5 lumens
Efficiency: N/A
Efficacy: 136.9 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42																				
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	42	36																				
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	39	37	36	31																				
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	31	26																				
4	74	63	56	50	67	58	51	46	48	43	40	39	36	33	31	29	27	23																				
5	68	56	48	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20																				
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18																				
7	58	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	16																				
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	21	18	16	14																				
9	50	38	30	26	45	35	28	24	30	24	21	24	21	18	20	17	15	13																				
10	46	35	28	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3635	3635	3635	3635
5°	4182	3640	3215	3640
10°	4798	3621	2837	3621
15°	5182	3584	2521	3584
20°	5714	3542	2328	3542
25°	6613	3484	2161	3484
30°	7196	3424	2051	3424
35°	6070	3354	1949	3354
40°	4239	3228	1862	3228
45°	3145	3058	1777	3058
50°	2508	2882	1704	2882
55°	2128	2662	1639	2662
60°	1838	2466	1535	2466
65°	1638	2253	1320	2253
70°	1441	2064	1205	2064
75°	1245	1787	1130	1787
80°	945	1503	945	1503
85°	785	1178	889	1178



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	1.5
10°-20°	158.2	4.5
20°-30°	250.8	7.2
30°-40°	302.5	8.6
40°-50°	270.1	7.7
50°-60°	207.1	5.9
60°-70°	134.6	3.8
70°-80°	65.4	1.9
80°-90°	17.2	0.5
90°-100°	49.1	1.4
100°-110°	145.0	4.1
110°-120°	245.6	7.0
120°-130°	323.2	9.2
130°-140°	362.1	10.3
140°-150°	354.9	10.1
150°-160°	298.1	8.5
160°-170°	198.2	5.7
170°-180°	69.4	2.0
0°-30°	463.0	13.2
0°-40°	765.4	21.8
0°-60°	1242.7	35.4
0°-90°	1459.9	41.6
90°-120°	439.7	12.5
90°-150°	1479.9	42.2
90°-180°	2046.0	58.4
0°-180°	3505.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	645	562	496	562	645	64
15°	775	536	377	536	775	222
25°	928	489	303	489	928	426
35°	770	425	247	425	770	465
45°	344	335	195	335	344	275
55°	189	236	146	236	189	172
65°	107	147	86	147	107	107
75°	50	72	45	72	50	53
85°	11	16	12	16	11	13
90°	14	1	14	1	14	8
95°	49	37	49	37	49	50
105°	142	130	142	130	142	150
115°	248	246	248	246	248	245
125°	361	359	361	359	361	322
135°	468	467	468	467	468	361
145°	568	565	568	565	568	354
155°	647	647	647	647	647	298
165°	702	703	702	703	702	198
175°	728	731	728	731	728	69
180°	733	733	733	733	733	



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	592.1	591.7	592.5	590.4	590.6	587.5	587.5	585.1	581.9	579.5	578.4
5°	645.1	645.6	644.7	641.2	638.9	635.4	631.5	624.6	618.8	613.2	608.9
7.5°	699.8	700.1	697.0	696.0	690.1	685.9	677.2	667.7	659.4	648.7	640.6
10°	731.6	731.3	728.1	725.5	720.5	714.0	705.4	694.4	684.0	672.4	661.3
12.5°	750.0	749.4	748.4	745.3	740.6	734.9	727.6	716.7	703.9	691.3	678.3
15°	775.0	773.4	770.4	766.4	759.7	753.0	745.0	735.3	723.0	708.7	696.7
17.5°	805.9	805.9	801.3	795.8	786.7	774.9	762.4	746.8	730.1	714.4	701.6
20°	831.4	830.7	826.1	815.4	805.0	790.2	775.9	756.7	736.4	715.8	699.9
22.5°	868.0	866.2	861.4	847.4	831.3	812.2	790.3	766.9	742.3	719.0	698.0
25°	928.0	926.6	917.1	900.9	878.3	848.9	820.3	788.2	752.8	722.1	696.7
27.5°	969.0	967.5	960.4	947.0	926.1	895.2	856.5	813.5	769.4	727.1	690.5
30°	964.9	968.4	967.5	961.2	945.5	917.8	882.0	833.7	781.2	731.6	687.9
32.5°	906.9	910.0	918.1	930.4	931.3	920.2	893.4	848.8	794.5	738.0	685.8
35°	769.9	774.1	789.8	814.5	846.9	873.9	879.4	855.4	806.6	745.9	682.8
37.5°	591.9	614.6	627.9	653.9	702.8	752.5	800.3	817.9	797.2	742.6	677.9
40°	502.8	508.3	531.9	561.3	602.4	654.1	722.3	771.5	773.1	735.3	670.1
42.5°	430.3	437.4	453.5	477.0	512.2	563.9	634.3	699.3	729.3	714.9	659.9
45°	344.3	349.6	361.4	379.4	406.4	449.2	509.7	584.8	644.4	667.8	632.7
47.5°	282.8	285.7	295.9	309.7	329.7	360.8	407.7	472.9	544.4	594.5	589.6
50°	249.6	252.8	260.6	271.0	287.9	314.2	351.7	406.0	479.7	540.9	553.2
52.5°	223.7	226.4	231.3	241.1	255.0	275.2	305.5	354.6	420.9	486.0	514.4
55°	189.0	190.9	194.8	200.3	211.4	226.0	252.1	286.1	339.7	405.3	446.9
57.5°	160.5	161.4	163.9	169.0	176.7	187.3	206.2	234.9	273.4	332.5	378.4
60°	142.3	143.3	146.5	150.0	156.0	165.7	180.5	200.6	237.5	286.3	332.7
62.5°	127.9	128.5	129.9	133.3	138.6	146.1	157.7	174.1	203.5	246.4	290.2
65°	107.2	107.4	107.9	110.7	113.9	119.5	127.1	138.6	160.8	193.2	232.0
67.5°	87.3	87.7	89.3	90.3	93.6	96.5	101.0	109.8	125.5	147.3	177.5
70°	76.3	76.0	77.6	78.8	79.9	83.4	86.4	93.6	103.3	119.9	145.1
72.5°	65.9	65.3	66.0	66.4	67.9	70.3	73.3	77.7	85.2	96.6	115.9
75°	49.9	50.1	50.1	50.6	51.8	52.7	53.6	55.9	60.1	67.7	78.1
77.5°	35.0	34.7	35.6	35.8	36.5	37.5	38.3	39.2	40.9	44.0	49.4
80°	25.4	25.4	25.6	26.3	26.1	26.6	27.7	28.7	30.7	32.6	34.4
82.5°	19.5	19.3	19.5	19.7	19.6	20.1	20.5	20.7	21.5	22.4	23.7
85°	10.6	10.6	10.9	10.9	11.1	11.1	11.3	11.3	11.3	11.6	11.8
87.5°	6.8	6.5	6.3	6.2	6.3	6.6	6.3	6.0	5.8	5.7	5.7
90°	13.7	13.3	12.9	12.6	12.2	11.7	11.0	10.4	9.8	9.1	8.2
92.5°	26.9	26.6	26.4	26.1	25.8	25.3	24.4	23.6	22.7	21.9	20.8
95°	49.1	48.8	48.6	48.3	48.0	47.5	46.6	45.7	44.8	43.9	42.7
97.5°	74.4	74.2	74.1	73.9	73.8	73.3	72.5	71.6	70.8	69.9	68.2
100°	93.6	93.3	93.1	92.8	92.5	91.8	90.7	89.6	88.4	87.3	85.6
102.5°	112.7	112.4	112.0	111.7	111.3	110.5	109.3	108.0	106.8	105.5	104.7
105°	141.5	141.1	140.7	140.3	140.0	139.4	138.6	137.9	137.1	136.3	135.6
107.5°	170.9	170.9	171.0	171.0	171.0	170.8	170.5	170.1	169.7	169.3	168.7
110°	192.8	192.9	193.1	193.2	193.3	193.2	192.8	192.4	192.1	191.7	191.3



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	214.3	214.5	214.7	215.0	215.2	215.2	215.0	214.9	214.7	214.5	214.0
115°	248.2	248.3	248.4	248.5	248.7	248.8	248.9	249.0	249.2	249.3	249.0
117.5°	281.2	281.8	282.3	282.8	283.3	283.5	283.4	283.3	283.2	283.1	282.8
120°	304.1	304.6	305.1	305.6	306.1	306.3	306.3	306.3	306.3	306.3	306.2
122.5°	326.9	327.3	327.7	328.1	328.5	328.8	328.9	329.0	329.1	329.2	328.8
125°	361.1	361.2	361.4	361.5	361.6	361.8	362.1	362.3	362.6	362.8	362.7
127.5°	394.0	394.2	394.5	394.7	395.0	395.2	395.3	395.4	395.6	395.7	395.5
130°	415.9	416.1	416.4	416.6	416.9	417.1	417.2	417.3	417.5	417.6	417.3
132.5°	436.4	436.8	437.1	437.5	437.8	438.1	438.2	438.3	438.5	438.6	438.6
135°	468.4	468.9	469.4	469.9	470.4	470.6	470.6	470.6	470.6	470.6	470.5
137.5°	499.6	500.3	500.9	501.5	502.2	502.4	502.2	502.1	501.9	501.8	501.5
140°	519.7	520.3	521.0	521.6	522.2	522.4	522.2	521.9	521.7	521.4	521.0
142.5°	538.9	539.5	540.1	540.8	541.4	541.6	541.5	541.3	541.2	541.0	540.6
145°	567.6	568.0	568.4	568.8	569.1	569.3	569.3	569.3	569.3	569.3	569.0
147.5°	592.2	593.0	593.9	594.7	595.6	595.9	595.6	595.3	595.0	594.7	594.4
150°	610.4	610.7	610.9	611.2	611.4	611.5	611.5	611.5	611.5	611.5	611.0
152.5°	625.5	625.9	626.4	626.8	627.3	627.4	627.1	626.8	626.5	626.2	625.9
155°	646.9	647.5	648.2	648.8	649.5	649.5	649.0	648.5	648.0	647.5	647.4
157.5°	664.8	665.7	666.5	667.3	668.2	668.3	667.8	667.3	666.8	666.3	666.2
160°	677.2	677.8	678.4	679.1	679.7	679.7	679.2	678.7	678.2	677.7	677.6
162.5°	687.6	688.4	689.1	689.9	690.6	690.7	690.0	689.4	688.8	688.2	688.2
165°	701.7	702.4	703.2	704.0	704.7	704.9	704.3	703.8	703.3	702.8	702.7
167.5°	712.9	713.6	714.4	715.2	716.0	716.0	715.3	714.5	713.7	713.0	713.0
170°	718.8	719.7	720.6	721.5	722.3	722.4	721.6	720.9	720.1	719.4	719.4
172.5°	723.8	724.6	725.4	726.2	727.0	727.0	726.2	725.5	724.7	723.9	723.9
175°	728.5	729.4	730.3	731.2	732.0	732.1	731.3	730.6	729.8	729.1	729.1
177.5°	731.2	731.9	732.7	733.4	734.1	734.1	733.5	732.9	732.3	731.7	731.8
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	578.4	577.1	574.7	572.5	569.7	567.3	565.6	563.6	561.0	557.9	555.3
5°	604.0	598.9	592.2	586.4	579.0	573.3	567.3	561.5	555.7	548.3	541.8
7.5°	632.4	621.9	611.7	598.8	587.2	576.8	566.8	556.7	546.8	536.3	526.2
10°	649.8	637.0	623.0	606.8	592.0	577.9	565.0	552.2	538.8	527.1	514.4
12.5°	666.0	649.6	633.5	613.1	595.3	578.1	561.6	545.8	531.5	516.2	502.5
15°	680.7	664.5	646.5	621.6	596.8	576.0	556.6	536.1	518.3	501.2	485.9
17.5°	686.4	669.4	648.5	624.5	597.5	571.3	546.3	523.8	502.8	482.9	465.8
20°	684.2	667.8	646.3	623.4	594.5	567.3	540.2	515.3	491.9	470.9	452.7
22.5°	678.8	661.9	641.1	616.9	589.5	560.6	531.7	505.1	480.7	458.9	439.0
25°	670.8	647.7	626.4	602.8	576.7	548.1	518.3	488.9	462.8	440.6	418.9
27.5°	662.4	633.6	606.5	583.1	555.5	530.0	501.2	471.1	443.7	421.1	398.8
30°	654.8	622.5	592.7	566.1	540.0	515.7	488.5	459.1	430.9	407.6	385.0
32.5°	645.4	611.0	578.3	547.6	522.4	498.4	473.7	445.6	418.2	394.1	371.1
35°	633.6	589.7	554.1	521.5	493.6	470.2	448.0	425.4	397.9	372.9	350.5
37.5°	618.1	568.2	527.1	491.6	462.1	438.7	421.1	400.4	375.3	351.5	330.7
40°	608.6	552.7	507.7	472.5	441.6	416.8	400.4	382.9	360.0	337.6	316.8
42.5°	596.1	538.5	488.1	451.5	420.3	396.5	379.9	364.6	345.4	324.3	302.0
45°	571.4	510.9	458.0	418.7	387.3	363.9	348.4	334.8	320.3	300.8	281.4
47.5°	539.4	482.1	426.7	383.8	353.1	331.4	316.4	305.6	295.2	278.7	259.9
50°	513.7	458.4	404.4	362.8	330.0	309.4	295.3	286.8	277.3	262.3	246.5
52.5°	483.3	434.0	381.1	338.6	307.6	288.3	274.8	266.2	258.4	246.2	231.2
55°	435.6	392.3	343.8	305.2	276.8	257.4	244.5	236.4	231.8	221.4	209.6
57.5°	380.4	349.5	306.7	269.5	244.3	225.2	215.7	208.8	203.6	196.2	187.9
60°	342.0	320.3	281.9	246.5	223.4	205.2	196.6	190.9	186.0	179.8	173.3
62.5°	303.0	287.2	253.8	223.4	202.2	186.9	178.9	173.7	168.1	163.9	157.6
65°	250.7	236.6	213.5	189.7	170.1	157.8	152.0	147.4	144.0	139.3	134.9
67.5°	195.0	189.3	173.3	156.9	142.8	131.9	126.9	123.7	119.6	116.8	113.8
70°	160.8	158.0	146.7	135.9	122.7	115.3	110.7	109.3	104.2	101.4	99.4
72.5°	130.5	129.2	122.7	115.2	105.9	99.4	95.2	93.6	90.3	88.1	86.8
75°	89.4	89.9	88.7	83.9	80.4	76.3	72.6	71.6	69.3	67.5	66.3
77.5°	56.6	58.9	59.0	58.8	57.4	54.9	53.3	52.6	50.4	49.7	49.4
80°	38.8	41.4	43.7	43.4	43.0	42.3	41.1	40.4	39.3	38.6	38.1
82.5°	25.9	28.2	30.2	31.4	31.3	30.6	29.9	29.5	29.3	28.8	28.7
85°	12.2	12.7	13.4	15.0	16.2	16.4	16.2	15.9	15.3	15.5	15.7
87.5°	5.7	5.5	5.6	5.4	5.0	5.7	6.0	6.0	5.9	5.7	5.5
90°	7.4	6.5	5.6	4.6	3.6	2.6	1.6	0.6	1.6	2.6	3.6
92.5°	19.7	18.6	17.5	16.6	15.9	15.2	14.5	13.8	14.5	15.2	15.9
95°	41.4	40.1	38.9	38.1	37.8	37.6	37.3	37.1	37.3	37.6	37.8
97.5°	66.4	64.7	62.9	62.0	61.9	61.8	61.7	61.6	61.7	61.8	61.9
100°	84.0	82.3	80.7	79.9	79.9	79.9	79.9	79.9	79.9	79.9	79.9
102.5°	103.9	103.0	102.2	101.5	101.0	100.5	100.0	99.5	100.0	100.5	101.0
105°	134.8	134.1	133.3	132.6	132.0	131.3	130.7	130.1	130.7	131.3	132.0
107.5°	168.1	167.6	167.0	166.4	165.7	165.1	164.5	163.8	164.5	165.1	165.7
110°	190.9	190.5	190.2	189.7	189.0	188.4	187.7	187.1	187.7	188.4	189.0



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	213.5	213.1	212.6	212.2	211.8	211.5	211.2	210.8	211.2	211.5	211.8
115°	248.8	248.5	248.3	247.9	247.4	246.9	246.4	245.9	246.4	246.9	247.4
117.5°	282.6	282.4	282.2	281.9	281.7	281.5	281.2	281.0	281.2	281.5	281.7
120°	306.1	306.0	305.8	305.5	304.8	304.2	303.6	302.9	303.6	304.2	304.8
122.5°	328.5	328.2	327.8	327.6	327.3	327.1	326.9	326.7	326.9	327.1	327.3
125°	362.6	362.4	362.3	361.9	361.1	360.3	359.6	358.8	359.6	360.3	361.1
127.5°	395.4	395.2	395.1	394.8	394.3	393.9	393.5	393.1	393.5	393.9	394.3
130°	417.1	416.8	416.6	416.1	415.5	414.9	414.2	413.6	414.2	414.9	415.5
132.5°	438.7	438.7	438.8	438.3	437.2	436.2	435.2	434.1	435.2	436.2	437.2
135°	470.4	470.3	470.1	469.7	468.9	468.2	467.4	466.6	467.4	468.2	468.9
137.5°	501.2	501.0	500.7	500.2	499.4	498.7	498.0	497.2	498.0	498.7	499.4
140°	520.7	520.3	519.9	519.4	518.7	518.1	517.5	516.8	517.5	518.1	518.7
142.5°	540.1	539.6	539.1	538.6	538.1	537.5	537.0	536.5	537.0	537.5	538.1
145°	568.6	568.2	567.8	567.4	566.9	566.4	565.8	565.3	565.8	566.4	566.9
147.5°	594.1	593.7	593.4	593.2	592.9	592.6	592.3	592.0	592.3	592.6	592.9
150°	610.5	610.0	609.5	609.3	609.5	609.6	609.7	609.8	609.7	609.6	609.5
152.5°	625.7	625.5	625.3	625.1	625.0	624.8	624.6	624.4	624.6	624.8	625.0
155°	647.2	647.1	647.0	646.9	646.9	646.9	646.9	646.9	646.9	646.9	646.9
157.5°	666.1	665.9	665.8	665.9	666.2	666.4	666.7	667.0	666.7	666.4	666.2
160°	677.5	677.3	677.2	677.3	677.7	678.1	678.5	678.9	678.5	678.1	677.7
162.5°	688.2	688.1	688.1	688.2	688.5	688.8	689.1	689.4	689.1	688.8	688.5
165°	702.6	702.4	702.3	702.4	702.6	702.9	703.1	703.4	703.1	702.9	702.6
167.5°	713.0	713.0	713.0	713.2	713.7	714.2	714.8	715.3	714.8	714.2	713.7
170°	719.4	719.4	719.4	719.6	720.1	720.6	721.1	721.6	721.1	720.6	720.1
172.5°	723.9	723.9	723.9	724.2	724.7	725.2	725.7	726.2	725.7	725.2	724.7
175°	729.1	729.1	729.1	729.3	729.8	730.3	730.8	731.3	730.8	730.3	729.8
177.5°	731.9	732.0	732.1	732.3	732.8	733.2	733.6	734.0	733.6	733.2	732.8
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	553.4	550.9	549.0	545.3	542.7	541.6	539.6	539.0	541.1	539.6	539.4
5°	537.0	530.3	525.0	519.7	513.9	510.2	504.6	503.7	502.3	500.3	499.8
7.5°	517.3	508.5	501.7	492.9	485.3	479.1	472.2	468.9	467.1	464.4	460.8
10°	504.0	493.6	484.3	475.5	466.1	458.4	451.5	446.2	442.7	439.5	438.1
12.5°	490.8	480.2	468.4	457.8	447.2	438.7	431.0	427.5	423.7	419.9	416.7
15°	470.4	456.4	443.4	431.2	422.2	412.9	405.5	400.4	394.7	393.0	386.8
17.5°	448.8	435.0	419.8	407.0	396.5	386.3	378.2	372.4	368.1	362.1	359.3
20°	435.3	418.9	404.1	392.3	380.8	368.8	360.5	355.6	351.5	346.6	344.3
22.5°	420.9	404.9	389.7	375.9	364.2	352.3	346.4	341.4	336.7	332.2	329.1
25°	399.7	383.6	367.6	353.3	341.1	332.5	325.6	319.8	317.3	312.9	309.6
27.5°	378.8	361.6	345.1	330.8	321.2	312.7	307.0	302.5	297.9	294.1	291.2
30°	365.3	347.8	329.7	318.4	308.2	300.2	293.9	289.5	286.1	282.6	280.5
32.5°	351.8	333.7	317.7	305.5	295.9	288.9	282.5	278.2	274.6	270.8	268.3
35°	330.2	311.7	298.8	286.8	277.3	270.8	266.4	260.4	257.4	254.6	252.1
37.5°	310.1	292.9	278.9	268.4	260.1	253.7	248.0	244.8	241.1	238.6	236.5
40°	295.3	279.6	266.9	255.8	249.8	242.6	237.3	233.1	230.4	227.1	224.8
42.5°	282.0	267.4	255.0	245.1	237.6	231.5	226.4	222.2	218.7	216.4	214.5
45°	263.2	248.6	236.6	227.4	220.4	214.7	209.3	207.3	202.6	199.9	198.9
47.5°	243.7	230.7	219.1	210.6	203.5	198.0	193.0	188.8	186.2	183.5	182.0
50°	230.6	218.1	207.3	198.9	192.0	186.0	181.4	178.6	175.1	172.6	170.8
52.5°	217.5	205.9	195.1	187.1	181.1	175.1	169.9	167.2	163.9	162.3	161.0
55°	198.7	186.5	177.2	169.4	163.1	157.6	152.7	150.0	147.9	146.3	145.8
57.5°	177.5	167.8	159.2	152.1	145.6	140.4	136.1	133.5	131.7	131.4	130.0
60°	163.6	154.8	147.0	139.3	133.8	128.9	125.2	122.2	120.4	120.2	119.7
62.5°	149.7	141.3	134.0	127.3	122.3	117.7	114.1	110.8	109.7	108.5	107.5
65°	129.2	121.5	115.5	110.2	104.9	101.0	97.5	95.4	92.9	91.5	89.0
67.5°	109.0	103.1	97.3	92.8	88.6	84.9	82.0	78.9	77.2	76.1	74.3
70°	95.7	91.0	85.3	80.4	77.2	74.2	71.9	68.4	67.2	66.3	65.4
72.5°	83.1	79.0	74.2	70.2	67.0	64.2	61.5	59.9	58.7	57.8	57.3
75°	65.4	61.5	57.3	54.5	52.2	49.9	48.5	47.4	46.9	46.7	45.8
77.5°	48.0	45.9	42.6	40.4	38.9	37.9	36.7	36.1	36.0	35.0	34.7
80°	36.7	35.6	32.8	31.9	30.7	29.8	29.1	28.0	26.8	26.3	25.6
82.5°	27.3	26.2	25.0	23.6	22.6	22.0	21.4	20.9	21.1	20.4	20.1
85°	14.6	13.4	12.9	12.7	12.2	12.7	12.5	12.2	12.0	11.8	12.0
87.5°	5.5	5.7	5.7	6.3	5.9	6.3	6.4	6.3	6.5	6.6	6.5
90°	4.6	5.6	6.5	7.4	8.2	9.1	9.8	10.4	11.0	11.7	12.2
92.5°	16.6	17.5	18.6	19.7	20.8	21.9	22.7	23.6	24.4	25.3	25.8
95°	38.1	38.9	40.1	41.4	42.7	43.9	44.8	45.7	46.6	47.5	48.0
97.5°	62.0	62.9	64.7	66.4	68.2	69.9	70.8	71.6	72.5	73.3	73.8
100°	79.9	80.7	82.3	84.0	85.6	87.3	88.4	89.6	90.7	91.8	92.5
102.5°	101.5	102.2	103.0	103.9	104.7	105.5	106.8	108.0	109.3	110.5	111.3
105°	132.6	133.3	134.1	134.8	135.6	136.3	137.1	137.9	138.6	139.4	140.0
107.5°	166.4	167.0	167.6	168.1	168.7	169.3	169.7	170.1	170.5	170.8	171.0
110°	189.7	190.2	190.5	190.9	191.3	191.7	192.1	192.4	192.8	193.2	193.3



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	212.2	212.6	213.1	213.5	214.0	214.5	214.7	214.9	215.0	215.2	215.2
115°	247.9	248.3	248.5	248.8	249.0	249.3	249.2	249.0	248.9	248.8	248.7
117.5°	281.9	282.2	282.4	282.6	282.8	283.1	283.2	283.3	283.4	283.5	283.3
120°	305.5	305.8	306.0	306.1	306.2	306.3	306.3	306.3	306.3	306.3	306.1
122.5°	327.6	327.8	328.2	328.5	328.8	329.2	329.1	329.0	328.9	328.8	328.5
125°	361.9	362.3	362.4	362.6	362.7	362.8	362.6	362.3	362.1	361.8	361.6
127.5°	394.8	395.1	395.2	395.4	395.5	395.7	395.6	395.4	395.3	395.2	395.0
130°	416.1	416.6	416.8	417.1	417.3	417.6	417.5	417.3	417.2	417.1	416.9
132.5°	438.3	438.8	438.7	438.7	438.6	438.6	438.5	438.3	438.2	438.1	437.8
135°	469.7	470.1	470.3	470.4	470.5	470.6	470.6	470.6	470.6	470.6	470.4
137.5°	500.2	500.7	501.0	501.2	501.5	501.8	501.9	502.1	502.2	502.4	502.2
140°	519.4	519.9	520.3	520.7	521.0	521.4	521.7	521.9	522.2	522.4	522.2
142.5°	538.6	539.1	539.6	540.1	540.6	541.0	541.2	541.3	541.5	541.6	541.4
145°	567.4	567.8	568.2	568.6	569.0	569.3	569.3	569.3	569.3	569.3	569.1
147.5°	593.2	593.4	593.7	594.1	594.4	594.7	595.0	595.3	595.6	595.9	595.6
150°	609.3	609.5	610.0	610.5	611.0	611.5	611.5	611.5	611.5	611.5	611.4
152.5°	625.1	625.3	625.5	625.7	625.9	626.2	626.5	626.8	627.1	627.4	627.3
155°	646.9	647.0	647.1	647.2	647.4	647.5	648.0	648.5	649.0	649.5	649.5
157.5°	665.9	665.8	665.9	666.1	666.2	666.3	666.8	667.3	667.8	668.3	668.2
160°	677.3	677.2	677.3	677.5	677.6	677.7	678.2	678.7	679.2	679.7	679.7
162.5°	688.2	688.1	688.1	688.2	688.2	688.2	688.8	689.4	690.0	690.7	690.6
165°	702.4	702.3	702.4	702.6	702.7	702.8	703.3	703.8	704.3	704.9	704.7
167.5°	713.2	713.0	713.0	713.0	713.0	713.0	713.7	714.5	715.3	716.0	716.0
170°	719.6	719.4	719.4	719.4	719.4	719.4	720.1	720.9	721.6	722.4	722.3
172.5°	724.2	723.9	723.9	723.9	723.9	723.9	724.7	725.5	726.2	727.0	727.0
175°	729.3	729.1	729.1	729.1	729.1	729.1	729.8	730.6	731.3	732.1	732.0
177.5°	732.3	732.1	732.0	731.9	731.8	731.7	732.3	732.9	733.5	734.1	734.1
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.2	537.2	536.6	537.4	536.6	537.2	539.2	539.4	539.6	541.1	539.0
5°	497.5	495.2	496.3	495.9	496.3	495.2	497.5	499.8	500.3	502.3	503.7
7.5°	460.8	457.9	454.9	455.8	454.9	457.9	460.8	460.8	464.4	467.1	468.9
10°	435.1	432.8	431.4	432.6	431.4	432.8	435.1	438.1	439.5	442.7	446.2
12.5°	413.5	412.1	410.9	410.4	410.9	412.1	413.5	416.7	419.9	423.7	427.5
15°	384.0	381.3	380.1	377.1	380.1	381.3	384.0	386.8	393.0	394.7	400.4
17.5°	356.9	356.0	353.0	351.7	353.0	356.0	356.9	359.3	362.1	368.1	372.4
20°	340.8	339.9	336.9	338.7	336.9	339.9	340.8	344.3	346.6	351.5	355.6
22.5°	327.5	325.5	324.5	324.0	324.5	325.5	327.5	329.1	332.2	336.7	341.4
25°	308.7	305.7	304.5	303.2	304.5	305.7	308.7	309.6	312.9	317.3	319.8
27.5°	289.9	288.3	286.8	286.4	286.8	288.3	289.9	291.2	294.1	297.9	302.5
30°	277.7	276.1	275.0	275.0	275.0	276.1	277.7	280.5	282.6	286.1	289.5
32.5°	266.8	265.6	264.4	264.2	264.4	265.6	266.8	268.3	270.8	274.6	278.2
35°	250.9	249.1	248.6	247.2	248.6	249.1	250.9	252.1	254.6	257.4	260.4
37.5°	234.4	232.9	232.9	232.7	232.9	232.9	234.4	236.5	238.6	241.1	244.8
40°	223.9	222.7	222.5	220.9	222.5	222.7	223.9	224.8	227.1	230.4	233.1
42.5°	212.6	212.0	211.2	210.5	211.2	212.0	212.6	214.5	216.4	218.7	222.2
45°	197.3	195.7	195.7	194.6	195.7	195.7	197.3	198.9	199.9	202.6	207.3
47.5°	181.5	180.3	180.4	179.2	180.4	180.3	181.5	182.0	183.5	186.2	188.8
50°	171.0	170.3	170.1	169.6	170.1	170.3	171.0	170.8	172.6	175.1	178.6
52.5°	160.5	160.1	161.0	160.0	161.0	160.1	160.5	161.0	162.3	163.9	167.2
55°	146.3	145.6	147.0	145.6	147.0	145.6	146.3	145.8	146.3	147.9	150.0
57.5°	130.0	129.3	130.6	129.9	130.6	129.3	130.0	130.0	131.4	131.7	133.5
60°	119.2	117.8	118.5	118.8	118.5	117.8	119.2	119.7	120.2	120.4	122.2
62.5°	106.5	105.6	106.2	105.1	106.2	105.6	106.5	107.5	108.5	109.7	110.8
65°	88.5	87.8	86.9	86.4	86.9	87.8	88.5	89.0	91.5	92.9	95.4
67.5°	74.4	72.7	72.6	73.0	72.6	72.7	74.4	74.3	76.1	77.2	78.9
70°	64.0	64.0	63.8	63.8	63.8	64.0	64.0	65.4	66.3	67.2	68.4
72.5°	56.8	56.6	56.2	56.0	56.2	56.6	56.8	57.3	57.8	58.7	59.9
75°	45.8	46.0	45.5	45.3	45.5	46.0	45.8	45.8	46.7	46.9	47.4
77.5°	33.8	32.8	33.3	32.8	33.3	32.8	33.8	34.7	35.0	36.0	36.1
80°	25.6	25.4	26.1	25.4	26.1	25.4	25.6	25.6	26.3	26.8	28.0
82.5°	20.3	20.1	20.4	19.9	20.4	20.1	20.3	20.1	20.4	21.1	20.9
85°	12.2	12.0	11.8	12.0	11.8	12.0	12.2	12.0	11.8	12.0	12.2
87.5°	6.8	6.7	6.7	6.8	6.7	6.7	6.8	6.5	6.6	6.5	6.3
90°	12.6	12.9	13.3	13.7	13.3	12.9	12.6	12.2	11.7	11.0	10.4
92.5°	26.1	26.4	26.6	26.9	26.6	26.4	26.1	25.8	25.3	24.4	23.6
95°	48.3	48.6	48.8	49.1	48.8	48.6	48.3	48.0	47.5	46.6	45.7
97.5°	73.9	74.1	74.2	74.4	74.2	74.1	73.9	73.8	73.3	72.5	71.6
100°	92.8	93.1	93.3	93.6	93.3	93.1	92.8	92.5	91.8	90.7	89.6
102.5°	111.7	112.0	112.4	112.7	112.4	112.0	111.7	111.3	110.5	109.3	108.0
105°	140.3	140.7	141.1	141.5	141.1	140.7	140.3	140.0	139.4	138.6	137.9
107.5°	171.0	171.0	170.9	170.9	170.9	171.0	171.0	171.0	170.8	170.5	170.1
110°	193.2	193.1	192.9	192.8	192.9	193.1	193.2	193.3	193.2	192.8	192.4



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	215.0	214.7	214.5	214.3	214.5	214.7	215.0	215.2	215.2	215.0	214.9
115°	248.5	248.4	248.3	248.2	248.3	248.4	248.5	248.7	248.8	248.9	249.0
117.5°	282.8	282.3	281.8	281.2	281.8	282.3	282.8	283.3	283.5	283.4	283.3
120°	305.6	305.1	304.6	304.1	304.6	305.1	305.6	306.1	306.3	306.3	306.3
122.5°	328.1	327.7	327.3	326.9	327.3	327.7	328.1	328.5	328.8	328.9	329.0
125°	361.5	361.4	361.2	361.1	361.2	361.4	361.5	361.6	361.8	362.1	362.3
127.5°	394.7	394.5	394.2	394.0	394.2	394.5	394.7	395.0	395.2	395.3	395.4
130°	416.6	416.4	416.1	415.9	416.1	416.4	416.6	416.9	417.1	417.2	417.3
132.5°	437.5	437.1	436.8	436.4	436.8	437.1	437.5	437.8	438.1	438.2	438.3
135°	469.9	469.4	468.9	468.4	468.9	469.4	469.9	470.4	470.6	470.6	470.6
137.5°	501.5	500.9	500.3	499.6	500.3	500.9	501.5	502.2	502.4	502.2	502.1
140°	521.6	521.0	520.3	519.7	520.3	521.0	521.6	522.2	522.4	522.2	521.9
142.5°	540.8	540.1	539.5	538.9	539.5	540.1	540.8	541.4	541.6	541.5	541.3
145°	568.8	568.4	568.0	567.6	568.0	568.4	568.8	569.1	569.3	569.3	569.3
147.5°	594.7	593.9	593.0	592.2	593.0	593.9	594.7	595.6	595.9	595.6	595.3
150°	611.2	610.9	610.7	610.4	610.7	610.9	611.2	611.4	611.5	611.5	611.5
152.5°	626.8	626.4	625.9	625.5	625.9	626.4	626.8	627.3	627.4	627.1	626.8
155°	648.8	648.2	647.5	646.9	647.5	648.2	648.8	649.5	649.5	649.0	648.5
157.5°	667.3	666.5	665.7	664.8	665.7	666.5	667.3	668.2	668.3	667.8	667.3
160°	679.1	678.4	677.8	677.2	677.8	678.4	679.1	679.7	679.7	679.2	678.7
162.5°	689.9	689.1	688.4	687.6	688.4	689.1	689.9	690.6	690.7	690.0	689.4
165°	704.0	703.2	702.4	701.7	702.4	703.2	704.0	704.7	704.9	704.3	703.8
167.5°	715.2	714.4	713.6	712.9	713.6	714.4	715.2	716.0	716.0	715.3	714.5
170°	721.5	720.6	719.7	718.8	719.7	720.6	721.5	722.3	722.4	721.6	720.9
172.5°	726.2	725.4	724.6	723.8	724.6	725.4	726.2	727.0	727.0	726.2	725.5
175°	731.2	730.3	729.4	728.5	729.4	730.3	731.2	732.0	732.1	731.3	730.6
177.5°	733.4	732.7	731.9	731.2	731.9	732.7	733.4	734.1	734.1	733.5	732.9
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.6	541.6	542.7	545.3	549.0	550.9	553.4	555.3	557.9	561.0	563.6
5°	504.6	510.2	513.9	519.7	525.0	530.3	537.0	541.8	548.3	555.7	561.5
7.5°	472.2	479.1	485.3	492.9	501.7	508.5	517.3	526.2	536.3	546.8	556.7
10°	451.5	458.4	466.1	475.5	484.3	493.6	504.0	514.4	527.1	538.8	552.2
12.5°	431.0	438.7	447.2	457.8	468.4	480.2	490.8	502.5	516.2	531.5	545.8
15°	405.5	412.9	422.2	431.2	443.4	456.4	470.4	485.9	501.2	518.3	536.1
17.5°	378.2	386.3	396.5	407.0	419.8	435.0	448.8	465.8	482.9	502.8	523.8
20°	360.5	368.8	380.8	392.3	404.1	418.9	435.3	452.7	470.9	491.9	515.3
22.5°	346.4	352.3	364.2	375.9	389.7	404.9	420.9	439.0	458.9	480.7	505.1
25°	325.6	332.5	341.1	353.3	367.6	383.6	399.7	418.9	440.6	462.8	488.9
27.5°	307.0	312.7	321.2	330.8	345.1	361.6	378.8	398.8	421.1	443.7	471.1
30°	293.9	300.2	308.2	318.4	329.7	347.8	365.3	385.0	407.6	430.9	459.1
32.5°	282.5	288.9	295.9	305.5	317.7	333.7	351.8	371.1	394.1	418.2	445.6
35°	266.4	270.8	277.3	286.8	298.8	311.7	330.2	350.5	372.9	397.9	425.4
37.5°	248.0	253.7	260.1	268.4	278.9	292.9	310.1	330.7	351.5	375.3	400.4
40°	237.3	242.6	249.8	255.8	266.9	279.6	295.3	316.8	337.6	360.0	382.9
42.5°	226.4	231.5	237.6	245.1	255.0	267.4	282.0	302.0	324.3	345.4	364.6
45°	209.3	214.7	220.4	227.4	236.6	248.6	263.2	281.4	300.8	320.3	334.8
47.5°	193.0	198.0	203.5	210.6	219.1	230.7	243.7	259.9	278.7	295.2	305.6
50°	181.4	186.0	192.0	198.9	207.3	218.1	230.6	246.5	262.3	277.3	286.8
52.5°	169.9	175.1	181.1	187.1	195.1	205.9	217.5	231.2	246.2	258.4	266.2
55°	152.7	157.6	163.1	169.4	177.2	186.5	198.7	209.6	221.4	231.8	236.4
57.5°	136.1	140.4	145.6	152.1	159.2	167.8	177.5	187.9	196.2	203.6	208.8
60°	125.2	128.9	133.8	139.3	147.0	154.8	163.6	173.3	179.8	186.0	190.9
62.5°	114.1	117.7	122.3	127.3	134.0	141.3	149.7	157.6	163.9	168.1	173.7
65°	97.5	101.0	104.9	110.2	115.5	121.5	129.2	134.9	139.3	144.0	147.4
67.5°	82.0	84.9	88.6	92.8	97.3	103.1	109.0	113.8	116.8	119.6	123.7
70°	71.9	74.2	77.2	80.4	85.3	91.0	95.7	99.4	101.4	104.2	109.3
72.5°	61.5	64.2	67.0	70.2	74.2	79.0	83.1	86.8	88.1	90.3	93.6
75°	48.5	49.9	52.2	54.5	57.3	61.5	65.4	66.3	67.5	69.3	71.6
77.5°	36.7	37.9	38.9	40.4	42.6	45.9	48.0	49.4	49.7	50.4	52.6
80°	29.1	29.8	30.7	31.9	32.8	35.6	36.7	38.1	38.6	39.3	40.4
82.5°	21.4	22.0	22.6	23.6	25.0	26.2	27.3	28.7	28.8	29.3	29.5
85°	12.5	12.7	12.2	12.7	12.9	13.4	14.6	15.7	15.5	15.3	15.9
87.5°	6.4	6.3	5.9	6.3	5.7	5.7	5.5	5.5	5.7	5.9	6.0
90°	9.8	9.1	8.2	7.4	6.5	5.6	4.6	3.6	2.6	1.6	0.6
92.5°	22.7	21.9	20.8	19.7	18.6	17.5	16.6	15.9	15.2	14.5	13.8
95°	44.8	43.9	42.7	41.4	40.1	38.9	38.1	37.8	37.6	37.3	37.1
97.5°	70.8	69.9	68.2	66.4	64.7	62.9	62.0	61.9	61.8	61.7	61.6
100°	88.4	87.3	85.6	84.0	82.3	80.7	79.9	79.9	79.9	79.9	79.9
102.5°	106.8	105.5	104.7	103.9	103.0	102.2	101.5	101.0	100.5	100.0	99.5
105°	137.1	136.3	135.6	134.8	134.1	133.3	132.6	132.0	131.3	130.7	130.1
107.5°	169.7	169.3	168.7	168.1	167.6	167.0	166.4	165.7	165.1	164.5	163.8
110°	192.1	191.7	191.3	190.9	190.5	190.2	189.7	189.0	188.4	187.7	187.1



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	214.7	214.5	214.0	213.5	213.1	212.6	212.2	211.8	211.5	211.2	210.8
115°	249.2	249.3	249.0	248.8	248.5	248.3	247.9	247.4	246.9	246.4	245.9
117.5°	283.2	283.1	282.8	282.6	282.4	282.2	281.9	281.7	281.5	281.2	281.0
120°	306.3	306.3	306.2	306.1	306.0	305.8	305.5	304.8	304.2	303.6	302.9
122.5°	329.1	329.2	328.8	328.5	328.2	327.8	327.6	327.3	327.1	326.9	326.7
125°	362.6	362.8	362.7	362.6	362.4	362.3	361.9	361.1	360.3	359.6	358.8
127.5°	395.6	395.7	395.5	395.4	395.2	395.1	394.8	394.3	393.9	393.5	393.1
130°	417.5	417.6	417.3	417.1	416.8	416.6	416.1	415.5	414.9	414.2	413.6
132.5°	438.5	438.6	438.6	438.7	438.7	438.8	438.3	437.2	436.2	435.2	434.1
135°	470.6	470.6	470.5	470.4	470.3	470.1	469.7	468.9	468.2	467.4	466.6
137.5°	501.9	501.8	501.5	501.2	501.0	500.7	500.2	499.4	498.7	498.0	497.2
140°	521.7	521.4	521.0	520.7	520.3	519.9	519.4	518.7	518.1	517.5	516.8
142.5°	541.2	541.0	540.6	540.1	539.6	539.1	538.6	538.1	537.5	537.0	536.5
145°	569.3	569.3	569.0	568.6	568.2	567.8	567.4	566.9	566.4	565.8	565.3
147.5°	595.0	594.7	594.4	594.1	593.7	593.4	593.2	592.9	592.6	592.3	592.0
150°	611.5	611.5	611.0	610.5	610.0	609.5	609.3	609.5	609.6	609.7	609.8
152.5°	626.5	626.2	625.9	625.7	625.5	625.3	625.1	625.0	624.8	624.6	624.4
155°	648.0	647.5	647.4	647.2	647.1	647.0	646.9	646.9	646.9	646.9	646.9
157.5°	666.8	666.3	666.2	666.1	665.9	665.8	665.9	666.2	666.4	666.7	667.0
160°	678.2	677.7	677.6	677.5	677.3	677.2	677.3	677.7	678.1	678.5	678.9
162.5°	688.8	688.2	688.2	688.2	688.1	688.1	688.2	688.5	688.8	689.1	689.4
165°	703.3	702.8	702.7	702.6	702.4	702.3	702.4	702.6	702.9	703.1	703.4
167.5°	713.7	713.0	713.0	713.0	713.0	713.0	713.2	713.7	714.2	714.8	715.3
170°	720.1	719.4	719.4	719.4	719.4	719.4	719.6	720.1	720.6	721.1	721.6
172.5°	724.7	723.9	723.9	723.9	723.9	723.9	724.2	724.7	725.2	725.7	726.2
175°	729.8	729.1	729.1	729.1	729.1	729.1	729.3	729.8	730.3	730.8	731.3
177.5°	732.3	731.7	731.8	731.9	732.0	732.1	732.3	732.8	733.2	733.6	734.0
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	565.6	567.3	569.7	572.5	574.7	577.1	578.4	578.4	579.5	581.9	585.1
5°	567.3	573.3	579.0	586.4	592.2	598.9	604.0	608.9	613.2	618.8	624.6
7.5°	566.8	576.8	587.2	598.8	611.7	621.9	632.4	640.6	648.7	659.4	667.7
10°	565.0	577.9	592.0	606.8	623.0	637.0	649.8	661.3	672.4	684.0	694.4
12.5°	561.6	578.1	595.3	613.1	633.5	649.6	666.0	678.3	691.3	703.9	716.7
15°	556.6	576.0	596.8	621.6	646.5	664.5	680.7	696.7	708.7	723.0	735.3
17.5°	546.3	571.3	597.5	624.5	648.5	669.4	686.4	701.6	714.4	730.1	746.8
20°	540.2	567.3	594.5	623.4	646.3	667.8	684.2	699.9	715.8	736.4	756.7
22.5°	531.7	560.6	589.5	616.9	641.1	661.9	678.8	698.0	719.0	742.3	766.9
25°	518.3	548.1	576.7	602.8	626.4	647.7	670.8	696.7	722.1	752.8	788.2
27.5°	501.2	530.0	555.5	583.1	606.5	633.6	662.4	690.5	727.1	769.4	813.5
30°	488.5	515.7	540.0	566.1	592.7	622.5	654.8	687.9	731.6	781.2	833.7
32.5°	473.7	498.4	522.4	547.6	578.3	611.0	645.4	685.8	738.0	794.5	848.8
35°	448.0	470.2	493.6	521.5	554.1	589.7	633.6	682.8	745.9	806.6	855.4
37.5°	421.1	438.7	462.1	491.6	527.1	568.2	618.1	677.9	742.6	797.2	817.9
40°	400.4	416.8	441.6	472.5	507.7	552.7	608.6	670.1	735.3	773.1	771.5
42.5°	379.9	396.5	420.3	451.5	488.1	538.5	596.1	659.9	714.9	729.3	699.3
45°	348.4	363.9	387.3	418.7	458.0	510.9	571.4	632.7	667.8	644.4	584.8
47.5°	316.4	331.4	353.1	383.8	426.7	482.1	539.4	589.6	594.5	544.4	472.9
50°	295.3	309.4	330.0	362.8	404.4	458.4	513.7	553.2	540.9	479.7	406.0
52.5°	274.8	288.3	307.6	338.6	381.1	434.0	483.3	514.4	486.0	420.9	354.6
55°	244.5	257.4	276.8	305.2	343.8	392.3	435.6	446.9	405.3	339.7	286.1
57.5°	215.7	225.2	244.3	269.5	306.7	349.5	380.4	378.4	332.5	273.4	234.9
60°	196.6	205.2	223.4	246.5	281.9	320.3	342.0	332.7	286.3	237.5	200.6
62.5°	178.9	186.9	202.2	223.4	253.8	287.2	303.0	290.2	246.4	203.5	174.1
65°	152.0	157.8	170.1	189.7	213.5	236.6	250.7	232.0	193.2	160.8	138.6
67.5°	126.9	131.9	142.8	156.9	173.3	189.3	195.0	177.5	147.3	125.5	109.8
70°	110.7	115.3	122.7	135.9	146.7	158.0	160.8	145.1	119.9	103.3	93.6
72.5°	95.2	99.4	105.9	115.2	122.7	129.2	130.5	115.9	96.6	85.2	77.7
75°	72.6	76.3	80.4	83.9	88.7	89.9	89.4	78.1	67.7	60.1	55.9
77.5°	53.3	54.9	57.4	58.8	59.0	58.9	56.6	49.4	44.0	40.9	39.2
80°	41.1	42.3	43.0	43.4	43.7	41.4	38.8	34.4	32.6	30.7	28.7
82.5°	29.9	30.6	31.3	31.4	30.2	28.2	25.9	23.7	22.4	21.5	20.7
85°	16.2	16.4	16.2	15.0	13.4	12.7	12.2	11.8	11.6	11.3	11.3
87.5°	6.0	5.7	5.0	5.4	5.6	5.5	5.7	5.7	5.7	5.8	6.0
90°	1.6	2.6	3.6	4.6	5.6	6.5	7.4	8.2	9.1	9.8	10.4
92.5°	14.5	15.2	15.9	16.6	17.5	18.6	19.7	20.8	21.9	22.7	23.6
95°	37.3	37.6	37.8	38.1	38.9	40.1	41.4	42.7	43.9	44.8	45.7
97.5°	61.7	61.8	61.9	62.0	62.9	64.7	66.4	68.2	69.9	70.8	71.6
100°	79.9	79.9	79.9	79.9	80.7	82.3	84.0	85.6	87.3	88.4	89.6
102.5°	100.0	100.5	101.0	101.5	102.2	103.0	103.9	104.7	105.5	106.8	108.0
105°	130.7	131.3	132.0	132.6	133.3	134.1	134.8	135.6	136.3	137.1	137.9
107.5°	164.5	165.1	165.7	166.4	167.0	167.6	168.1	168.7	169.3	169.7	170.1
110°	187.7	188.4	189.0	189.7	190.2	190.5	190.9	191.3	191.7	192.1	192.4



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	211.2	211.5	211.8	212.2	212.6	213.1	213.5	214.0	214.5	214.7	214.9
115°	246.4	246.9	247.4	247.9	248.3	248.5	248.8	249.0	249.3	249.2	249.0
117.5°	281.2	281.5	281.7	281.9	282.2	282.4	282.6	282.8	283.1	283.2	283.3
120°	303.6	304.2	304.8	305.5	305.8	306.0	306.1	306.2	306.3	306.3	306.3
122.5°	326.9	327.1	327.3	327.6	327.8	328.2	328.5	328.8	329.2	329.1	329.0
125°	359.6	360.3	361.1	361.9	362.3	362.4	362.6	362.7	362.8	362.6	362.3
127.5°	393.5	393.9	394.3	394.8	395.1	395.2	395.4	395.5	395.7	395.6	395.4
130°	414.2	414.9	415.5	416.1	416.6	416.8	417.1	417.3	417.6	417.5	417.3
132.5°	435.2	436.2	437.2	438.3	438.8	438.7	438.7	438.6	438.6	438.5	438.3
135°	467.4	468.2	468.9	469.7	470.1	470.3	470.4	470.5	470.6	470.6	470.6
137.5°	498.0	498.7	499.4	500.2	500.7	501.0	501.2	501.5	501.8	501.9	502.1
140°	517.5	518.1	518.7	519.4	519.9	520.3	520.7	521.0	521.4	521.7	521.9
142.5°	537.0	537.5	538.1	538.6	539.1	539.6	540.1	540.6	541.0	541.2	541.3
145°	565.8	566.4	566.9	567.4	567.8	568.2	568.6	569.0	569.3	569.3	569.3
147.5°	592.3	592.6	592.9	593.2	593.4	593.7	594.1	594.4	594.7	595.0	595.3
150°	609.7	609.6	609.5	609.3	609.5	610.0	610.5	611.0	611.5	611.5	611.5
152.5°	624.6	624.8	625.0	625.1	625.3	625.5	625.7	625.9	626.2	626.5	626.8
155°	646.9	646.9	646.9	646.9	647.0	647.1	647.2	647.4	647.5	648.0	648.5
157.5°	666.7	666.4	666.2	665.9	665.8	665.9	666.1	666.2	666.3	666.8	667.3
160°	678.5	678.1	677.7	677.3	677.2	677.3	677.5	677.6	677.7	678.2	678.7
162.5°	689.1	688.8	688.5	688.2	688.1	688.1	688.2	688.2	688.2	688.8	689.4
165°	703.1	702.9	702.6	702.4	702.3	702.4	702.6	702.7	702.8	703.3	703.8
167.5°	714.8	714.2	713.7	713.2	713.0	713.0	713.0	713.0	713.0	713.7	714.5
170°	721.1	720.6	720.1	719.6	719.4	719.4	719.4	719.4	719.4	720.1	720.9
172.5°	725.7	725.2	724.7	724.2	723.9	723.9	723.9	723.9	723.9	724.7	725.5
175°	730.8	730.3	729.8	729.3	729.1	729.1	729.1	729.1	729.1	729.8	730.6
177.5°	733.6	733.2	732.8	732.3	732.1	732.0	731.9	731.8	731.7	732.3	732.9
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	587.5	587.5	590.6	590.4	592.5	591.7	592.1
5°	631.5	635.4	638.9	641.2	644.7	645.6	645.1
7.5°	677.2	685.9	690.1	696.0	697.0	700.1	699.8
10°	705.4	714.0	720.5	725.5	728.1	731.3	731.6
12.5°	727.6	734.9	740.6	745.3	748.4	749.4	750.0
15°	745.0	753.0	759.7	766.4	770.4	773.4	775.0
17.5°	762.4	774.9	786.7	795.8	801.3	805.9	805.9
20°	775.9	790.2	805.0	815.4	826.1	830.7	831.4
22.5°	790.3	812.2	831.3	847.4	861.4	866.2	868.0
25°	820.3	848.9	878.3	900.9	917.1	926.6	928.0
27.5°	856.5	895.2	926.1	947.0	960.4	967.5	969.0
30°	882.0	917.8	945.5	961.2	967.5	968.4	964.9
32.5°	893.4	920.2	931.3	930.4	918.1	910.0	906.9
35°	879.4	873.9	846.9	814.5	789.8	774.1	769.9
37.5°	800.3	752.5	702.8	653.9	627.9	614.6	591.9
40°	722.3	654.1	602.4	561.3	531.9	508.3	502.8
42.5°	634.3	563.9	512.2	477.0	453.5	437.4	430.3
45°	509.7	449.2	406.4	379.4	361.4	349.6	344.3
47.5°	407.7	360.8	329.7	309.7	295.9	285.7	282.8
50°	351.7	314.2	287.9	271.0	260.6	252.8	249.6
52.5°	305.5	275.2	255.0	241.1	231.3	226.4	223.7
55°	252.1	226.0	211.4	200.3	194.8	190.9	189.0
57.5°	206.2	187.3	176.7	169.0	163.9	161.4	160.5
60°	180.5	165.7	156.0	150.0	146.5	143.3	142.3
62.5°	157.7	146.1	138.6	133.3	129.9	128.5	127.9
65°	127.1	119.5	113.9	110.7	107.9	107.4	107.2
67.5°	101.0	96.5	93.6	90.3	89.3	87.7	87.3
70°	86.4	83.4	79.9	78.8	77.6	76.0	76.3
72.5°	73.3	70.3	67.9	66.4	66.0	65.3	65.9
75°	53.6	52.7	51.8	50.6	50.1	50.1	49.9
77.5°	38.3	37.5	36.5	35.8	35.6	34.7	35.0
80°	27.7	26.6	26.1	26.3	25.6	25.4	25.4
82.5°	20.5	20.1	19.6	19.7	19.5	19.3	19.5
85°	11.3	11.1	11.1	10.9	10.9	10.6	10.6
87.5°	6.3	6.6	6.3	6.2	6.3	6.5	6.8
90°	11.0	11.7	12.2	12.6	12.9	13.3	13.7
92.5°	24.4	25.3	25.8	26.1	26.4	26.6	26.9
95°	46.6	47.5	48.0	48.3	48.6	48.8	49.1
97.5°	72.5	73.3	73.8	73.9	74.1	74.2	74.4
100°	90.7	91.8	92.5	92.8	93.1	93.3	93.6
102.5°	109.3	110.5	111.3	111.7	112.0	112.4	112.7
105°	138.6	139.4	140.0	140.3	140.7	141.1	141.5
107.5°	170.5	170.8	171.0	171.0	171.0	170.9	170.9
110°	192.8	193.2	193.3	193.2	193.1	192.9	192.8



TEST NUMBER: P333497

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	215.0	215.2	215.2	215.0	214.7	214.5	214.3
115°	248.9	248.8	248.7	248.5	248.4	248.3	248.2
117.5°	283.4	283.5	283.3	282.8	282.3	281.8	281.2
120°	306.3	306.3	306.1	305.6	305.1	304.6	304.1
122.5°	328.9	328.8	328.5	328.1	327.7	327.3	326.9
125°	362.1	361.8	361.6	361.5	361.4	361.2	361.1
127.5°	395.3	395.2	395.0	394.7	394.5	394.2	394.0
130°	417.2	417.1	416.9	416.6	416.4	416.1	415.9
132.5°	438.2	438.1	437.8	437.5	437.1	436.8	436.4
135°	470.6	470.6	470.4	469.9	469.4	468.9	468.4
137.5°	502.2	502.4	502.2	501.5	500.9	500.3	499.6
140°	522.2	522.4	522.2	521.6	521.0	520.3	519.7
142.5°	541.5	541.6	541.4	540.8	540.1	539.5	538.9
145°	569.3	569.3	569.1	568.8	568.4	568.0	567.6
147.5°	595.6	595.9	595.6	594.7	593.9	593.0	592.2
150°	611.5	611.5	611.4	611.2	610.9	610.7	610.4
152.5°	627.1	627.4	627.3	626.8	626.4	625.9	625.5
155°	649.0	649.5	649.5	648.8	648.2	647.5	646.9
157.5°	667.8	668.3	668.2	667.3	666.5	665.7	664.8
160°	679.2	679.7	679.7	679.1	678.4	677.8	677.2
162.5°	690.0	690.7	690.6	689.9	689.1	688.4	687.6
165°	704.3	704.9	704.7	704.0	703.2	702.4	701.7
167.5°	715.3	716.0	716.0	715.2	714.4	713.6	712.9
170°	721.6	722.4	722.3	721.5	720.6	719.7	718.8
172.5°	726.2	727.0	727.0	726.2	725.4	724.6	723.8
175°	731.3	732.1	732.0	731.2	730.3	729.4	728.5
177.5°	733.5	734.1	734.1	733.4	732.7	731.9	731.2
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1

(END OF REPORT)