

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333500

Luminaire Tested: **S125RDIP-S375D590U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333500  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D590U835-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3492.7 lumens  
Efficiency: N/A  
Efficacy: 136.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333500

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333500

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41																				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35																				
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35	30																				
3	80	71	64	58	73	65	59	54	54	49	45	43	40	38	34	32	30	25																				
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22																				
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	23	19																				
6	62	50	42	36	56	46	39	34	39	33	29	31	28	25	25	22	20	17																				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																				
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	13																				
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12																				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3952	3952	3952
5°	3961	3916	3940
10°	3931	3880	3880
15°	3884	3801	3770
20°	3824	3691	3647
25°	3755	3583	3504
30°	3667	3457	3347
35°	3578	3327	3170
40°	3495	3191	2996
45°	3394	3040	2807
50°	3293	2875	2609
55°	3174	2716	2399
60°	3056	2525	2173
65°	2917	2303	1913
70°	2757	2024	1648
75°	2538	1707	1372
80°	2235	1339	1153
85°	1882	1097	1030



TEST NUMBER: P333500

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.5	1.6
10°-20°	160.8	4.6
20°-30°	233.2	6.7
30°-40°	265.7	7.6
40°-50°	259.0	7.4
50°-60°	218.0	6.2
60°-70°	152.8	4.4
70°-80°	78.6	2.2
80°-90°	21.4	0.6
90°-100°	49.1	1.4
100°-110°	145.0	4.2
110°-120°	245.6	7.0
120°-130°	323.2	9.3
130°-140°	362.1	10.4
140°-150°	354.9	10.2
150°-160°	298.1	8.5
160°-170°	198.2	5.7
170°-180°	69.4	2.0
0°-30°	451.5	12.9
0°-40°	717.3	20.5
0°-60°	1194.3	34.2
0°-90°	1447.2	41.4
90°-120°	439.7	12.6
90°-150°	1479.9	42.4
90°-180°	2046.0	58.6
0°-180°	3492.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	612	612	612	612	612	
5°	611	609	604	608	608	58
15°	581	578	568	568	564	164
25°	527	519	503	497	492	242
35°	454	442	422	409	402	284
45°	372	358	333	315	307	287
55°	282	267	241	221	213	252
65°	191	175	151	133	125	189
75°	102	88	68	59	55	108
85°	25	17	15	14	14	29
90°	1	5	9	12	14	3
95°	37	38	44	48	49	40
105°	130	133	136	140	142	139
115°	246	248	249	249	248	243
125°	359	362	363	362	361	321
135°	467	470	471	470	468	360
145°	565	568	569	569	568	353
155°	647	647	648	650	647	298
165°	703	702	703	705	702	198
175°	731	729	729	732	728	69
180°	733	733	733	733	733	



TEST NUMBER: P333500

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9
2.5°	613.0	612.8	612.5	612.3	612.0	611.5	610.7	609.8	609.0	608.2	609.0
5°	611.0	610.6	610.2	609.7	609.3	608.6	607.4	606.3	605.2	604.0	605.1
7.5°	605.0	604.6	604.2	603.8	603.4	602.5	601.2	599.8	598.5	597.1	597.8
10°	599.4	599.1	598.8	598.5	598.2	597.3	595.9	594.4	593.0	591.6	591.9
12.5°	593.1	592.7	592.4	592.0	591.6	590.4	588.5	586.6	584.6	582.7	582.9
15°	580.9	580.3	579.7	579.1	578.5	577.1	574.9	572.8	570.6	568.5	568.4
17.5°	567.2	566.2	565.3	564.3	563.4	561.6	558.8	556.1	553.4	550.7	550.2
20°	556.4	555.4	554.4	553.4	552.3	550.2	546.9	543.6	540.3	537.0	536.5
22.5°	544.6	543.6	542.6	541.5	540.5	538.3	534.8	531.4	527.9	524.5	523.5
25°	526.9	525.3	523.8	522.2	520.7	518.0	514.2	510.4	506.6	502.8	501.5
27.5°	506.5	504.7	502.8	500.9	499.0	496.1	492.0	487.9	483.9	479.8	477.9
30°	491.7	489.8	487.8	485.9	483.9	480.8	476.5	472.2	467.9	463.5	461.2
32.5°	477.3	475.0	472.8	470.5	468.2	464.9	460.5	456.1	451.7	447.3	444.7
35°	453.8	451.4	448.9	446.4	444.0	440.4	435.8	431.2	426.6	422.0	419.0
37.5°	430.8	427.8	424.8	421.8	418.8	414.9	410.2	405.4	400.7	395.9	392.3
40°	414.6	411.5	408.4	405.3	402.2	398.2	393.3	388.4	383.4	378.5	374.6
42.5°	397.5	394.4	391.2	388.1	384.9	380.8	375.7	370.6	365.5	360.4	356.7
45°	371.6	368.6	365.6	362.6	359.7	355.3	349.7	344.1	338.4	332.8	328.6
47.5°	344.7	341.5	338.4	335.2	332.1	327.7	322.0	316.3	310.6	304.9	300.7
50°	327.7	324.3	320.9	317.5	314.1	309.5	303.6	297.8	291.9	286.1	281.8
52.5°	309.2	305.7	302.2	298.8	295.3	290.8	285.3	279.7	274.2	268.7	264.1
55°	281.9	278.6	275.3	272.1	268.8	264.3	258.5	252.7	247.0	241.2	236.6
57.5°	254.4	250.9	247.3	243.8	240.3	235.8	230.2	224.7	219.2	213.6	209.1
60°	236.6	233.0	229.4	225.8	222.2	217.7	212.1	206.6	201.0	195.5	191.0
62.5°	217.8	214.3	210.9	207.5	204.0	199.5	193.9	188.3	182.6	177.0	172.8
65°	190.9	187.4	183.9	180.4	176.9	172.4	167.0	161.6	156.1	150.7	146.6
67.5°	164.2	160.7	157.2	153.7	150.2	145.8	140.6	135.4	130.2	125.0	121.2
70°	146.0	142.6	139.1	135.6	132.1	127.8	122.6	117.5	112.4	107.2	104.0
72.5°	128.3	124.9	121.5	118.1	114.7	110.5	105.7	100.9	96.1	91.3	88.4
75°	101.7	98.6	95.5	92.4	89.4	85.7	81.3	77.0	72.7	68.4	66.1
77.5°	75.2	72.8	70.3	67.8	65.4	62.4	59.0	55.5	52.1	48.6	47.0
80°	60.1	57.6	55.2	52.7	50.2	47.6	44.7	41.8	38.9	36.0	35.1
82.5°	45.3	43.1	40.9	38.6	36.4	34.3	32.4	30.4	28.4	26.4	26.0
85°	25.4	23.6	21.7	19.9	18.0	16.8	16.3	15.8	15.3	14.8	14.7
87.5°	8.6	8.2	7.9	7.5	7.1	7.0	7.1	7.2	7.3	7.4	7.5
90°	0.6	1.6	2.6	3.6	4.6	5.6	6.5	7.4	8.2	9.1	9.8
92.5°	13.8	14.5	15.2	15.9	16.6	17.5	18.6	19.7	20.8	21.9	22.7
95°	37.1	37.3	37.6	37.8	38.1	38.9	40.1	41.4	42.7	43.9	44.8
97.5°	61.6	61.7	61.8	61.9	62.0	62.9	64.7	66.4	68.2	69.9	70.8
100°	79.9	79.9	79.9	79.9	79.9	80.7	82.3	84.0	85.6	87.3	88.4
102.5°	99.5	100.0	100.5	101.0	101.5	102.2	103.0	103.9	104.7	105.5	106.8
105°	130.1	130.7	131.3	132.0	132.6	133.3	134.1	134.8	135.6	136.3	137.1
107.5°	163.8	164.5	165.1	165.7	166.4	167.0	167.6	168.1	168.7	169.3	169.7
110°	187.1	187.7	188.4	189.0	189.7	190.2	190.5	190.9	191.3	191.7	192.1



TEST NUMBER: P333500

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.8	211.2	211.5	211.8	212.2	212.6	213.1	213.5	214.0	214.5	214.7
115°	245.9	246.4	246.9	247.4	247.9	248.3	248.5	248.8	249.0	249.3	249.2
117.5°	281.0	281.2	281.5	281.7	281.9	282.2	282.4	282.6	282.8	283.1	283.2
120°	302.9	303.6	304.2	304.8	305.5	305.8	306.0	306.1	306.2	306.3	306.3
122.5°	326.7	326.9	327.1	327.3	327.6	327.8	328.2	328.5	328.8	329.2	329.1
125°	358.8	359.6	360.3	361.1	361.9	362.3	362.4	362.6	362.7	362.8	362.6
127.5°	393.1	393.5	393.9	394.3	394.8	395.1	395.2	395.4	395.5	395.7	395.6
130°	413.6	414.2	414.9	415.5	416.1	416.6	416.8	417.1	417.3	417.6	417.5
132.5°	434.1	435.2	436.2	437.2	438.3	438.8	438.7	438.7	438.6	438.6	438.5
135°	466.6	467.4	468.2	468.9	469.7	470.1	470.3	470.4	470.5	470.6	470.6
137.5°	497.2	498.0	498.7	499.4	500.2	500.7	501.0	501.2	501.5	501.8	501.9
140°	516.8	517.5	518.1	518.7	519.4	519.9	520.3	520.7	521.0	521.4	521.7
142.5°	536.5	537.0	537.5	538.1	538.6	539.1	539.6	540.1	540.6	541.0	541.2
145°	565.3	565.8	566.4	566.9	567.4	567.8	568.2	568.6	569.0	569.3	569.3
147.5°	592.0	592.3	592.6	592.9	593.2	593.4	593.7	594.1	594.4	594.7	595.0
150°	609.8	609.7	609.6	609.5	609.3	609.5	610.0	610.5	611.0	611.5	611.5
152.5°	624.4	624.6	624.8	625.0	625.1	625.3	625.5	625.7	625.9	626.2	626.5
155°	646.9	646.9	646.9	646.9	646.9	647.0	647.1	647.2	647.4	647.5	648.0
157.5°	667.0	666.7	666.4	666.2	665.9	665.8	665.9	666.1	666.2	666.3	666.8
160°	678.9	678.5	678.1	677.7	677.3	677.2	677.3	677.5	677.6	677.7	678.2
162.5°	689.4	689.1	688.8	688.5	688.2	688.1	688.1	688.2	688.2	688.2	688.8
165°	703.4	703.1	702.9	702.6	702.4	702.3	702.4	702.6	702.7	702.8	703.3
167.5°	715.3	714.8	714.2	713.7	713.2	713.0	713.0	713.0	713.0	713.0	713.7
170°	721.6	721.1	720.6	720.1	719.6	719.4	719.4	719.4	719.4	719.4	720.1
172.5°	726.2	725.7	725.2	724.7	724.2	723.9	723.9	723.9	723.9	723.9	724.7
175°	731.3	730.8	730.3	729.8	729.3	729.1	729.1	729.1	729.1	729.1	729.8
177.5°	734.0	733.6	733.2	732.8	732.3	732.1	732.0	731.9	731.8	731.7	732.3
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333500

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9
2.5°	609.8	610.7	611.5	611.9	611.8	611.7	611.6	611.5
5°	606.1	607.1	608.1	608.6	608.4	608.1	607.9	607.7
7.5°	598.5	599.3	600.0	600.2	600.0	599.8	599.6	599.3
10°	592.2	592.5	592.8	592.8	592.5	592.2	591.9	591.6
12.5°	583.1	583.4	583.6	583.5	583.0	582.5	582.1	581.6
15°	568.2	568.1	568.0	567.5	566.6	565.7	564.8	563.8
17.5°	549.7	549.2	548.7	548.0	547.3	546.5	545.7	545.0
20°	536.0	535.5	535.0	534.3	533.3	532.4	531.5	530.6
22.5°	522.4	521.4	520.4	519.5	518.8	518.0	517.3	516.5
25°	500.2	498.8	497.5	496.3	495.1	494.0	492.9	491.7
27.5°	476.1	474.2	472.3	470.9	469.8	468.7	467.6	466.5
30°	458.8	456.5	454.1	452.5	451.5	450.6	449.7	448.8
32.5°	442.1	439.5	436.8	435.0	433.8	432.6	431.4	430.3
35°	416.0	413.0	410.0	407.8	406.4	405.0	403.5	402.1
37.5°	388.7	385.2	381.6	379.1	377.7	376.3	374.9	373.5
40°	370.7	366.8	362.9	360.3	359.1	357.9	356.6	355.4
42.5°	352.9	349.2	345.4	342.7	340.9	339.0	337.2	335.4
45°	324.5	320.4	316.3	313.5	312.0	310.4	308.9	307.3
47.5°	296.5	292.2	288.0	285.0	283.3	281.6	279.9	278.2
50°	277.4	273.1	268.8	265.9	264.4	262.8	261.3	259.7
52.5°	259.4	254.8	250.1	247.0	245.5	244.0	242.4	240.9
55°	232.0	227.4	222.8	219.6	218.0	216.3	214.7	213.1
57.5°	204.6	200.1	195.5	192.5	191.1	189.6	188.2	186.7
60°	186.5	181.9	177.4	174.4	172.8	171.3	169.8	168.2
62.5°	168.6	164.4	160.2	157.4	155.8	154.3	152.8	151.2
65°	142.4	138.3	134.2	131.4	129.9	128.3	126.8	125.2
67.5°	117.4	113.7	109.9	107.4	106.2	105.0	103.7	102.5
70°	100.9	97.7	94.5	92.3	91.0	89.8	88.6	87.3
72.5°	85.4	82.5	79.6	77.7	76.9	76.1	75.2	74.4
75°	63.9	61.6	59.4	57.9	57.2	56.4	55.7	55.0
77.5°	45.5	43.9	42.3	41.2	40.7	40.2	39.6	39.1
80°	34.2	33.3	32.4	31.8	31.6	31.4	31.2	31.0
82.5°	25.6	25.1	24.7	24.4	24.3	24.2	24.1	23.9
85°	14.6	14.5	14.4	14.3	14.2	14.1	14.0	13.9
87.5°	7.6	7.8	7.9	7.9	7.9	7.9	7.9	7.9
90°	10.4	11.0	11.7	12.2	12.6	12.9	13.3	13.7
92.5°	23.6	24.4	25.3	25.8	26.1	26.4	26.6	26.9
95°	45.7	46.6	47.5	48.0	48.3	48.6	48.8	49.1
97.5°	71.6	72.5	73.3	73.8	73.9	74.1	74.2	74.4
100°	89.6	90.7	91.8	92.5	92.8	93.1	93.3	93.6
102.5°	108.0	109.3	110.5	111.3	111.7	112.0	112.4	112.7
105°	137.9	138.6	139.4	140.0	140.3	140.7	141.1	141.5
107.5°	170.1	170.5	170.8	171.0	171.0	171.0	170.9	170.9
110°	192.4	192.8	193.2	193.3	193.2	193.1	192.9	192.8





TEST NUMBER: P333500

CATALOG NUMBER: S125RDIP-S375D590U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	214.9	215.0	215.2	215.2	215.0	214.7	214.5	214.3
115°	249.0	248.9	248.8	248.7	248.5	248.4	248.3	248.2
117.5°	283.3	283.4	283.5	283.3	282.8	282.3	281.8	281.2
120°	306.3	306.3	306.3	306.1	305.6	305.1	304.6	304.1
122.5°	329.0	328.9	328.8	328.5	328.1	327.7	327.3	326.9
125°	362.3	362.1	361.8	361.6	361.5	361.4	361.2	361.1
127.5°	395.4	395.3	395.2	395.0	394.7	394.5	394.2	394.0
130°	417.3	417.2	417.1	416.9	416.6	416.4	416.1	415.9
132.5°	438.3	438.2	438.1	437.8	437.5	437.1	436.8	436.4
135°	470.6	470.6	470.6	470.4	469.9	469.4	468.9	468.4
137.5°	502.1	502.2	502.4	502.2	501.5	500.9	500.3	499.6
140°	521.9	522.2	522.4	522.2	521.6	521.0	520.3	519.7
142.5°	541.3	541.5	541.6	541.4	540.8	540.1	539.5	538.9
145°	569.3	569.3	569.3	569.1	568.8	568.4	568.0	567.6
147.5°	595.3	595.6	595.9	595.6	594.7	593.9	593.0	592.2
150°	611.5	611.5	611.5	611.4	611.2	610.9	610.7	610.4
152.5°	626.8	627.1	627.4	627.3	626.8	626.4	625.9	625.5
155°	648.5	649.0	649.5	649.5	648.8	648.2	647.5	646.9
157.5°	667.3	667.8	668.3	668.2	667.3	666.5	665.7	664.8
160°	678.7	679.2	679.7	679.7	679.1	678.4	677.8	677.2
162.5°	689.4	690.0	690.7	690.6	689.9	689.1	688.4	687.6
165°	703.8	704.3	704.9	704.7	704.0	703.2	702.4	701.7
167.5°	714.5	715.3	716.0	716.0	715.2	714.4	713.6	712.9
170°	720.9	721.6	722.4	722.3	721.5	720.6	719.7	718.8
172.5°	725.5	726.2	727.0	727.0	726.2	725.4	724.6	723.8
175°	730.6	731.3	732.1	732.0	731.2	730.3	729.4	728.5
177.5°	732.9	733.5	734.1	734.1	733.4	732.7	731.9	731.2
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1

(END OF REPORT)