

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333522

Luminaire Tested: **S125RDIP-S610D365U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333522  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D365U835-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3713.0 lumens  
Efficiency: N/A  
Efficacy: 135.0 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65
1	102	97	94	90	95	92	88	86	81	79	76	71	70	68	62	61	60	56
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51	47
3	85	76	69	63	80	72	65	60	64	59	54	56	52	49	50	47	44	41
4	78	67	60	54	73	64	57	51	57	51	47	51	46	43	45	41	38	35
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	40	37	34	31
6	66	54	46	40	62	52	44	39	46	40	36	41	36	33	37	33	30	27
7	62	49	41	36	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	32	54	43	35	30	38	32	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	38	30	26	47	36	29	25	33	27	23	29	25	21	26	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5977	5977	5977	5977
5°	6876	5984	5285	5984
10°	7887	5954	4663	5954
15°	8519	5893	4145	5893
20°	9394	5822	3827	5822
25°	10871	5728	3552	5728
30°	11830	5629	3371	5629
35°	9979	5513	3205	5513
40°	6969	5306	3062	5306
45°	5170	5027	2922	5027
50°	4122	4736	2801	4736
55°	3498	4376	2694	4376
60°	3023	4053	2523	4053
65°	2694	3704	2172	3704
70°	2368	3393	1979	3393
75°	2049	2939	1859	2939
80°	1555	2473	1555	2473
85°	1297	1941	1467	1941



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.7	2.4
10°-20°	260.1	7.0
20°-30°	412.3	11.1
30°-40°	497.2	13.4
40°-50°	444.0	12.0
50°-60°	340.5	9.2
60°-70°	221.3	6.0
70°-80°	107.6	2.9
80°-90°	26.7	0.7
90°-100°	127.1	3.4
100°-110°	273.1	7.4
110°-120°	256.3	6.9
120°-130°	207.7	5.6
130°-140°	166.7	4.5
140°-150°	125.8	3.4
150°-160°	88.6	2.4
160°-170°	52.2	1.4
170°-180°	17.0	0.5
0°-30°	761.1	20.5
0°-40°	1258.3	33.9
0°-60°	2042.9	55.0
0°-90°	2398.5	64.6
90°-120°	656.5	17.7
90°-150°	1156.8	31.2
90°-180°	1315.0	35.4
0°-180°	3713.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	925	925	925	925	925	
5°	1061	923	815	923	1061	106
15°	1274	881	620	881	1274	365
25°	1526	804	498	804	1526	700
35°	1266	699	406	699	1266	765
45°	566	550	320	550	566	452
55°	311	389	239	389	311	282
65°	176	242	142	242	176	175
75°	82	118	74	118	82	87
85°	18	26	20	26	18	20
90°	8	0	8	0	8	6
95°	83	12	83	12	83	118
105°	468	40	468	40	468	465
115°	522	71	522	71	522	510
125°	411	99	411	99	411	372
135°	341	116	341	116	341	265
145°	269	135	269	135	269	171
155°	226	154	226	154	226	105
165°	198	168	198	168	198	57
175°	178	175	178	175	178	17
180°	175	175	175	175	175	



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	973.4	972.8	974.0	970.6	971.0	965.8	965.8	961.8	956.7	952.7	950.9
5°	1060.6	1061.4	1059.8	1054.1	1050.3	1044.6	1038.2	1026.8	1017.3	1008.2	1001.0
7.5°	1150.4	1150.9	1145.9	1144.2	1134.6	1127.6	1113.3	1097.8	1084.0	1066.5	1053.2
10°	1202.7	1202.3	1197.0	1192.8	1184.4	1173.8	1159.7	1141.5	1124.4	1105.4	1087.2
12.5°	1233.1	1232.1	1230.4	1225.3	1217.6	1208.1	1196.2	1178.3	1157.2	1136.4	1115.2
15°	1274.1	1271.4	1266.5	1260.0	1249.0	1238.0	1224.7	1208.8	1188.6	1165.1	1145.3
17.5°	1324.8	1324.9	1317.3	1308.4	1293.4	1273.9	1253.4	1227.7	1200.3	1174.4	1153.4
20°	1366.8	1365.6	1358.0	1340.6	1323.5	1299.2	1275.6	1244.1	1210.7	1176.8	1150.6
22.5°	1426.9	1424.0	1416.1	1393.1	1366.6	1335.3	1299.3	1260.8	1220.4	1182.0	1147.6
25°	1525.6	1523.3	1507.7	1481.1	1443.9	1395.6	1348.5	1295.7	1237.6	1187.1	1145.3
27.5°	1593.0	1590.5	1579.0	1556.9	1522.5	1471.8	1408.0	1337.5	1264.9	1195.4	1135.1
30°	1586.3	1592.0	1590.5	1580.3	1554.4	1508.8	1450.0	1370.6	1284.3	1202.7	1130.9
32.5°	1490.9	1496.0	1509.4	1529.5	1531.0	1512.8	1468.8	1395.5	1306.2	1213.3	1127.5
35°	1265.7	1272.6	1298.4	1339.0	1392.2	1436.7	1445.8	1406.3	1326.1	1226.2	1122.5
37.5°	973.1	1010.5	1032.2	1075.0	1155.3	1237.1	1315.7	1344.7	1310.6	1220.9	1114.4
40°	826.6	835.7	874.5	922.7	990.3	1075.4	1187.5	1268.4	1271.0	1208.8	1101.6
42.5°	707.5	719.0	745.6	784.1	842.0	927.1	1042.8	1149.6	1199.0	1175.3	1084.9
45°	566.0	574.7	594.1	623.7	668.2	738.5	838.0	961.5	1059.5	1097.8	1040.1
47.5°	465.0	469.7	486.5	509.1	542.0	593.2	670.2	777.4	895.0	977.4	969.3
50°	410.3	415.6	428.5	445.6	473.3	516.6	578.2	667.4	788.6	889.3	909.4
52.5°	367.7	372.1	380.2	396.4	419.2	452.5	502.2	583.0	692.0	799.0	845.6
55°	310.7	313.8	320.2	329.3	347.6	371.5	414.4	470.3	558.4	666.3	734.7
57.5°	263.8	265.3	269.4	277.8	290.4	307.9	338.9	386.3	449.5	546.6	622.1
60°	234.0	235.5	240.8	246.5	256.4	272.4	296.7	329.7	390.5	470.7	547.0
62.5°	210.3	211.2	213.5	219.2	227.8	240.2	259.3	286.3	334.6	405.0	477.1
65°	176.3	176.6	177.4	182.0	187.3	196.4	208.9	227.9	264.4	317.6	381.4
67.5°	143.6	144.1	146.8	148.4	153.9	158.7	166.1	180.6	206.3	242.1	291.7
70°	125.4	125.0	127.6	129.5	131.4	137.1	142.1	153.8	169.8	197.2	238.6
72.5°	108.3	107.4	108.5	109.2	111.7	115.6	120.5	127.7	140.0	158.9	190.5
75°	82.1	82.4	82.4	83.2	85.1	86.6	88.1	91.9	98.8	111.3	128.4
77.5°	57.6	57.0	58.6	58.8	59.9	61.6	62.9	64.4	67.2	72.4	81.2
80°	41.8	41.8	42.2	43.3	42.9	43.7	45.6	47.1	50.5	53.6	56.6
82.5°	32.1	31.8	32.1	32.4	32.3	33.0	33.7	34.0	35.3	36.8	39.0
85°	17.5	17.5	17.9	17.9	18.2	18.2	18.6	18.6	18.6	19.0	19.4
87.5°	8.3	8.0	7.6	7.6	7.9	8.4	8.0	7.7	7.6	7.5	7.7
90°	8.1	8.1	7.8	7.8	7.8	7.1	6.7	6.4	6.0	5.7	4.9
92.5°	22.5	23.1	23.6	24.5	29.0	34.2	45.4	62.6	92.2	113.9	115.8
95°	83.1	88.7	91.5	102.1	127.2	156.9	200.4	254.1	306.4	313.1	255.5
97.5°	200.7	205.3	215.5	235.3	257.1	298.4	340.8	378.4	387.7	334.4	228.2
100°	275.7	281.3	294.4	319.8	344.2	381.0	417.4	434.7	407.5	319.1	203.6
102.5°	359.4	363.6	377.8	395.9	422.0	446.9	464.3	453.6	395.6	292.3	184.9
105°	468.3	472.5	479.6	491.2	502.6	506.4	490.9	442.5	357.7	256.2	166.8
107.5°	526.1	528.9	531.3	531.3	525.6	507.1	467.2	402.6	318.9	231.4	159.2
110°	545.3	545.3	542.8	536.1	520.2	490.2	440.4	373.2	296.9	219.8	156.9



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	543.1	540.5	534.4	522.8	499.6	464.2	413.8	350.0	280.5	213.0	156.9
115°	521.6	517.0	507.1	490.2	462.6	424.1	375.7	320.9	262.6	205.7	158.0
117.5°	484.1	481.3	471.5	453.9	426.4	391.0	349.3	302.1	251.9	202.1	160.3
120°	459.8	457.0	447.4	430.5	404.3	373.2	334.3	291.9	246.0	200.4	162.6
122.5°	438.3	435.8	426.2	410.7	387.3	358.2	323.6	284.3	240.9	199.0	164.5
125°	411.0	407.5	399.7	385.2	365.4	340.0	309.2	273.2	234.0	197.2	167.9
127.5°	387.7	386.1	378.8	366.0	348.0	324.2	295.5	261.9	227.6	196.4	171.6
130°	375.0	372.9	365.8	354.1	336.5	313.5	285.9	254.8	223.4	195.8	173.9
132.5°	362.2	359.8	353.3	341.7	324.0	301.9	276.9	247.7	220.0	195.8	176.4
135°	341.4	339.3	332.9	321.3	305.7	285.6	262.9	238.6	215.9	195.8	179.9
137.5°	319.1	316.8	310.9	300.3	286.4	269.3	250.5	230.8	212.3	196.2	183.1
140°	303.6	301.8	296.5	287.3	274.2	259.4	243.1	226.5	210.6	196.5	184.5
142.5°	289.2	287.7	282.7	274.9	263.8	250.9	236.9	222.9	209.2	196.8	185.3
145°	269.3	267.9	264.0	258.0	249.5	240.0	229.0	218.1	207.1	196.5	186.2
147.5°	252.5	251.8	249.6	244.8	238.1	230.9	222.4	213.5	204.9	195.6	186.6
150°	243.1	242.8	241.4	237.1	231.8	225.5	218.8	211.0	203.2	194.7	186.6
152.5°	235.8	235.4	234.0	230.6	226.2	221.2	215.1	208.2	201.2	193.6	186.3
155°	225.8	225.5	224.4	221.9	218.4	214.5	209.6	203.9	197.9	191.6	185.5
157.5°	216.9	217.0	216.0	214.0	211.2	208.2	204.3	199.7	194.8	189.4	184.6
160°	211.0	211.3	210.6	208.9	206.4	203.9	200.4	196.9	192.3	188.0	183.8
162.5°	205.6	205.7	205.5	204.1	202.2	200.0	197.0	193.7	190.0	186.3	182.9
165°	197.9	197.9	197.9	197.2	195.8	194.0	191.9	189.4	186.6	183.8	181.7
167.5°	190.8	190.9	191.2	190.6	189.9	188.6	187.0	185.3	183.3	181.3	179.7
170°	186.6	187.0	187.0	186.6	185.9	185.2	184.1	183.1	181.3	179.9	178.8
172.5°	182.6	183.0	183.6	182.9	182.8	182.4	181.6	180.5	179.3	178.2	177.7
175°	177.8	178.1	178.8	178.5	178.5	178.5	177.8	177.8	176.7	176.4	176.4
177.5°	175.3	175.3	176.1	175.9	176.1	176.1	176.1	175.9	175.6	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	950.9	948.8	944.8	941.2	936.6	932.7	929.9	926.6	922.3	917.2	912.9
5°	993.0	984.6	973.6	964.1	952.0	942.5	932.6	923.1	913.6	901.4	890.8
7.5°	1039.6	1022.4	1005.6	984.5	965.3	948.2	931.8	915.2	898.9	881.7	865.0
10°	1068.2	1047.3	1024.1	997.5	973.2	950.1	928.8	907.9	885.9	866.5	845.6
12.5°	1094.9	1068.0	1041.5	1007.9	978.7	950.4	923.3	897.3	873.7	848.6	826.1
15°	1119.1	1092.5	1062.9	1021.9	981.2	947.0	915.1	881.3	852.1	823.9	798.9
17.5°	1128.4	1100.6	1066.1	1026.7	982.3	939.3	898.2	861.1	826.7	793.9	765.7
20°	1124.8	1097.8	1062.5	1024.9	977.4	932.6	888.1	847.1	808.7	774.2	744.2
22.5°	1116.0	1088.1	1054.0	1014.3	969.2	921.6	874.2	830.4	790.2	754.4	721.7
25°	1102.8	1064.8	1029.8	991.1	948.2	901.1	852.1	803.8	760.9	724.4	688.7
27.5°	1089.0	1041.6	997.2	958.6	913.3	871.3	824.0	774.6	729.4	692.3	655.7
30°	1076.6	1023.4	974.4	930.7	887.8	847.9	803.0	754.8	708.5	670.1	632.9
32.5°	1061.1	1004.5	950.7	900.3	858.9	819.3	778.7	732.6	687.5	647.9	610.1
35°	1041.6	969.4	910.9	857.4	811.4	773.0	736.6	699.3	654.1	613.1	576.3
37.5°	1016.1	934.2	866.5	808.1	759.7	721.1	692.4	658.3	617.1	577.8	543.6
40°	1000.6	908.7	834.6	776.8	725.9	685.3	658.3	629.4	591.8	555.0	520.8
42.5°	979.9	885.3	802.4	742.2	691.0	651.9	624.6	599.4	567.8	533.1	496.5
45°	939.4	839.9	752.9	688.3	636.7	598.3	572.8	550.4	526.5	494.6	462.7
47.5°	886.7	792.6	701.5	631.0	580.4	544.8	520.1	502.4	485.3	458.2	427.2
50°	844.5	753.7	664.8	596.4	542.5	508.6	485.5	471.4	455.8	431.2	405.3
52.5°	794.6	713.6	626.5	556.6	505.7	474.0	451.7	437.7	424.8	404.7	380.1
55°	716.1	645.0	565.2	501.8	455.1	423.2	401.9	388.6	381.0	363.9	344.5
57.5°	625.4	574.5	504.2	443.0	401.7	370.1	354.6	343.3	334.7	322.6	308.9
60°	562.2	526.5	463.4	405.3	367.3	337.3	323.3	313.8	305.8	295.5	284.9
62.5°	498.1	472.1	417.3	367.3	332.4	307.2	294.1	285.5	276.3	269.4	259.1
65°	412.2	389.0	351.0	311.9	279.6	259.5	250.0	242.4	236.7	229.1	221.8
67.5°	320.6	311.2	285.0	258.0	234.8	216.9	208.7	203.4	196.5	192.0	187.0
70°	264.4	259.8	241.2	223.4	201.7	189.6	182.0	179.7	171.3	166.8	163.3
72.5°	214.6	212.4	201.7	189.3	174.1	163.4	156.4	153.8	148.5	144.9	142.7
75°	147.0	147.8	145.9	137.9	132.2	125.4	119.3	117.8	114.0	110.9	109.0
77.5°	93.0	96.9	97.0	96.6	94.4	90.2	87.7	86.5	82.8	81.7	81.2
80°	63.8	68.0	71.8	71.4	70.7	69.5	67.6	66.5	64.6	63.4	62.7
82.5°	42.5	46.4	49.6	51.7	51.5	50.4	49.1	48.5	48.2	47.3	47.2
85°	20.1	20.9	22.0	24.7	26.6	27.0	26.6	26.2	25.1	25.5	25.8
87.5°	7.9	7.8	8.0	7.9	7.4	8.8	9.6	9.8	9.3	8.8	8.3
90°	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	80.6	48.3	29.0	18.7	12.6	8.2	5.2	4.3	5.2	8.2	12.6
95°	158.0	80.2	42.4	26.5	18.7	14.8	12.0	11.7	12.0	14.8	18.7
97.5°	126.1	69.1	44.1	32.7	25.7	21.8	19.8	19.4	19.8	21.8	25.7
100°	114.5	68.6	48.1	37.5	30.7	26.9	25.4	24.7	25.4	26.9	30.7
102.5°	109.7	71.1	52.9	42.6	36.4	32.2	31.1	30.7	31.1	32.2	36.4
105°	107.8	76.3	60.8	50.9	45.2	41.7	39.9	39.9	39.9	41.7	45.2
107.5°	111.0	84.1	69.1	60.2	54.3	51.4	49.7	49.0	49.7	51.4	54.3
110°	114.2	89.8	75.3	66.1	60.8	57.6	56.2	55.5	56.2	57.6	60.8





TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	118.1	95.1	81.2	72.3	67.0	63.8	62.7	62.0	62.7	63.8	67.0
115°	124.0	103.6	90.5	81.6	76.3	73.2	72.1	71.4	72.1	73.2	76.3
117.5°	130.8	112.2	99.8	91.3	85.2	82.1	80.9	79.9	80.9	82.1	85.2
120°	135.4	118.4	106.0	97.2	91.2	88.0	86.6	85.5	86.6	88.0	91.2
122.5°	140.4	124.3	112.0	103.1	96.6	93.4	92.2	91.5	92.2	93.4	96.6
125°	147.4	132.2	120.5	111.3	104.6	101.4	99.7	99.0	99.7	101.4	104.6
127.5°	153.7	139.7	128.5	119.3	112.2	108.1	105.9	104.8	105.9	108.1	112.2
130°	158.0	144.5	133.6	124.4	117.0	112.4	109.6	108.5	109.6	112.4	117.0
132.5°	161.7	149.1	138.1	128.9	121.2	116.1	112.7	111.3	112.7	116.1	121.2
135°	166.8	155.1	144.2	134.7	127.2	121.6	117.3	115.9	117.3	121.6	127.2
137.5°	170.6	159.5	149.5	139.7	132.4	126.7	122.8	121.7	122.8	126.7	132.4
140°	173.2	162.6	152.3	142.8	136.1	130.4	126.2	125.1	126.2	130.4	136.1
142.5°	174.6	164.5	154.9	145.9	139.5	133.8	129.8	129.1	129.8	133.8	139.5
145°	176.7	167.9	158.7	150.6	144.2	139.2	135.7	135.0	135.7	139.2	144.2
147.5°	178.0	170.0	161.9	154.8	149.3	144.7	141.6	141.2	141.6	144.7	149.3
150°	178.8	171.4	163.6	157.6	152.7	148.1	145.6	144.9	145.6	148.1	152.7
152.5°	179.4	172.8	165.6	160.2	155.5	151.5	149.3	148.9	149.3	151.5	155.5
155°	179.9	174.2	168.2	163.3	159.7	156.2	154.1	154.1	154.1	156.2	159.7
157.5°	180.2	175.4	170.3	166.5	163.4	160.4	158.7	158.8	158.7	160.4	163.4
160°	180.2	176.0	171.4	168.2	165.4	162.9	161.5	161.9	161.5	162.9	165.4
162.5°	180.0	176.6	172.5	169.9	167.7	165.5	164.1	164.4	164.1	165.5	167.7
165°	179.5	176.7	173.9	171.8	170.3	168.6	167.5	168.2	167.5	168.6	170.3
167.5°	178.7	176.7	174.4	173.0	172.0	171.1	170.4	170.8	170.4	171.1	172.0
170°	178.1	176.7	174.9	173.9	173.2	172.5	172.1	172.5	172.1	172.5	173.2
172.5°	177.6	176.4	174.9	174.4	174.0	173.3	173.0	173.6	173.0	173.3	174.0
175°	176.7	176.0	174.9	174.9	174.9	174.6	174.2	174.9	174.2	174.6	174.9
177.5°	175.9	175.6	175.0	175.0	175.3	175.0	175.0	175.6	175.0	175.0	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	909.9	905.6	902.6	896.5	892.2	890.4	887.1	886.2	889.5	887.1	886.8
5°	882.8	871.8	863.1	854.3	844.8	838.8	829.6	828.1	825.8	822.4	821.7
7.5°	850.4	836.0	824.8	810.3	797.8	787.7	776.3	770.9	767.9	763.5	757.6
10°	828.5	811.4	796.2	781.8	766.2	753.7	742.3	733.5	727.8	722.5	720.2
12.5°	806.9	789.5	770.1	752.6	735.2	721.1	708.5	702.8	696.5	690.3	685.0
15°	773.4	750.2	729.0	708.8	694.0	678.8	666.7	658.3	648.8	646.2	635.9
17.5°	737.9	715.1	690.2	669.0	651.9	635.1	621.8	612.3	605.1	595.3	590.6
20°	715.7	688.7	664.4	645.0	626.0	606.3	592.6	584.6	577.8	569.8	566.0
22.5°	692.0	665.6	640.7	618.0	598.7	579.2	569.5	561.2	553.5	546.1	541.1
25°	657.2	630.6	604.4	580.8	560.7	546.6	535.2	525.7	521.6	514.3	509.0
27.5°	622.8	594.5	567.3	543.8	528.0	514.1	504.8	497.3	489.7	483.4	478.8
30°	600.6	571.7	542.1	523.5	506.7	493.5	483.2	476.0	470.3	464.6	461.2
32.5°	578.4	548.6	522.3	502.2	486.4	474.9	464.4	457.4	451.4	445.1	441.1
35°	542.8	512.4	491.2	471.4	455.8	445.2	438.0	428.1	423.2	418.6	414.4
37.5°	509.8	481.5	458.5	441.2	427.7	417.1	407.8	402.4	396.4	392.3	388.8
40°	485.5	459.6	438.8	420.5	410.6	398.9	390.1	383.3	378.7	373.4	369.6
42.5°	463.6	439.6	419.3	402.9	390.6	380.6	372.2	365.4	359.6	355.8	352.6
45°	432.7	408.7	389.0	373.8	362.4	352.9	344.2	340.7	333.1	328.6	327.1
47.5°	400.7	379.3	360.2	346.2	334.5	325.5	317.3	310.4	306.2	301.7	299.3
50°	379.1	358.6	340.7	327.1	315.7	305.8	298.2	293.6	287.9	283.8	280.7
52.5°	357.5	338.5	320.7	307.6	297.7	287.9	279.4	274.8	269.4	266.7	264.6
55°	326.7	306.6	291.4	278.4	268.2	259.1	251.1	246.5	243.1	240.5	239.7
57.5°	291.7	275.8	261.7	250.0	239.4	230.8	223.8	219.5	216.5	216.1	213.8
60°	268.9	254.5	241.6	229.1	219.9	212.0	205.9	201.0	197.9	197.5	196.8
62.5°	246.2	232.3	220.3	209.3	201.1	193.4	187.7	182.1	180.3	178.4	176.7
65°	212.3	199.8	189.9	181.2	172.5	166.0	160.3	156.9	152.7	150.4	146.3
67.5°	179.1	169.4	159.9	152.6	145.7	139.6	134.9	129.8	127.0	125.1	122.1
70°	157.3	149.7	140.2	132.2	126.9	121.9	118.1	112.4	110.5	109.0	107.5
72.5°	136.6	129.9	121.9	115.5	110.2	105.5	101.1	98.5	96.6	95.0	94.1
75°	107.5	101.0	94.2	89.6	85.9	82.1	79.8	77.9	77.1	76.7	75.2
77.5°	78.9	75.5	70.0	66.4	63.9	62.4	60.3	59.3	59.3	57.6	57.1
80°	60.4	58.5	53.9	52.4	50.5	49.0	47.9	46.0	44.1	43.3	42.2
82.5°	44.9	43.0	41.2	38.7	37.2	36.2	35.1	34.4	34.6	33.6	33.0
85°	23.9	22.0	21.3	20.9	20.1	20.9	20.5	20.1	19.8	19.4	19.8
87.5°	8.2	8.3	8.1	8.8	8.0	8.4	8.5	8.3	8.3	8.4	8.2
90°	2.8	3.5	3.9	4.6	4.9	5.7	6.0	6.4	6.7	7.1	7.8
92.5°	18.7	29.0	48.3	80.6	115.8	113.9	92.2	62.6	45.4	34.2	29.0
95°	26.5	42.4	80.2	158.0	255.5	313.1	306.4	254.1	200.4	156.9	127.2
97.5°	32.7	44.1	69.1	126.1	228.2	334.4	387.7	378.4	340.8	298.4	257.1
100°	37.5	48.1	68.6	114.5	203.6	319.1	407.5	434.7	417.4	381.0	344.2
102.5°	42.6	52.9	71.1	109.7	184.9	292.3	395.6	453.6	464.3	446.9	422.0
105°	50.9	60.8	76.3	107.8	166.8	256.2	357.7	442.5	490.9	506.4	502.6
107.5°	60.2	69.1	84.1	111.0	159.2	231.4	318.9	402.6	467.2	507.1	525.6
110°	66.1	75.3	89.8	114.2	156.9	219.8	296.9	373.2	440.4	490.2	520.2



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	72.3	81.2	95.1	118.1	156.9	213.0	280.5	350.0	413.8	464.2	499.6
115°	81.6	90.5	103.6	124.0	158.0	205.7	262.6	320.9	375.7	424.1	462.6
117.5°	91.3	99.8	112.2	130.8	160.3	202.1	251.9	302.1	349.3	391.0	426.4
120°	97.2	106.0	118.4	135.4	162.6	200.4	246.0	291.9	334.3	373.2	404.3
122.5°	103.1	112.0	124.3	140.4	164.5	199.0	240.9	284.3	323.6	358.2	387.3
125°	111.3	120.5	132.2	147.4	167.9	197.2	234.0	273.2	309.2	340.0	365.4
127.5°	119.3	128.5	139.7	153.7	171.6	196.4	227.6	261.9	295.5	324.2	348.0
130°	124.4	133.6	144.5	158.0	173.9	195.8	223.4	254.8	285.9	313.5	336.5
132.5°	128.9	138.1	149.1	161.7	176.4	195.8	220.0	247.7	276.9	301.9	324.0
135°	134.7	144.2	155.1	166.8	179.9	195.8	215.9	238.6	262.9	285.6	305.7
137.5°	139.7	149.5	159.5	170.6	183.1	196.2	212.3	230.8	250.5	269.3	286.4
140°	142.8	152.3	162.6	173.2	184.5	196.5	210.6	226.5	243.1	259.4	274.2
142.5°	145.9	154.9	164.5	174.6	185.3	196.8	209.2	222.9	236.9	250.9	263.8
145°	150.6	158.7	167.9	176.7	186.2	196.5	207.1	218.1	229.0	240.0	249.5
147.5°	154.8	161.9	170.0	178.0	186.6	195.6	204.9	213.5	222.4	230.9	238.1
150°	157.6	163.6	171.4	178.8	186.6	194.7	203.2	211.0	218.8	225.5	231.8
152.5°	160.2	165.6	172.8	179.4	186.3	193.6	201.2	208.2	215.1	221.2	226.2
155°	163.3	168.2	174.2	179.9	185.5	191.6	197.9	203.9	209.6	214.5	218.4
157.5°	166.5	170.3	175.4	180.2	184.6	189.4	194.8	199.7	204.3	208.2	211.2
160°	168.2	171.4	176.0	180.2	183.8	188.0	192.3	196.9	200.4	203.9	206.4
162.5°	169.9	172.5	176.6	180.0	182.9	186.3	190.0	193.7	197.0	200.0	202.2
165°	171.8	173.9	176.7	179.5	181.7	183.8	186.6	189.4	191.9	194.0	195.8
167.5°	173.0	174.4	176.7	178.7	179.7	181.3	183.3	185.3	187.0	188.6	189.9
170°	173.9	174.9	176.7	178.1	178.8	179.9	181.3	183.1	184.1	185.2	185.9
172.5°	174.4	174.9	176.4	177.6	177.7	178.2	179.3	180.5	181.6	182.4	182.8
175°	174.9	174.9	176.0	176.7	176.4	176.4	176.7	177.8	177.8	178.5	178.5
177.5°	175.0	175.0	175.6	175.9	175.3	175.3	175.6	175.9	176.1	176.1	176.1
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	886.5	883.1	882.2	883.4	882.2	883.1	886.5	886.8	887.1	889.5	886.2
5°	817.9	814.1	816.0	815.2	816.0	814.1	817.9	821.7	822.4	825.8	828.1
7.5°	757.5	752.8	747.8	749.4	747.8	752.8	757.5	757.6	763.5	767.9	770.9
10°	715.3	711.5	709.2	711.1	709.2	711.5	715.3	720.2	722.5	727.8	733.5
12.5°	679.7	677.5	675.5	674.7	675.5	677.5	679.7	685.0	690.3	696.5	702.8
15°	631.3	626.8	624.9	620.0	624.9	626.8	631.3	635.9	646.2	648.8	658.3
17.5°	586.7	585.2	580.3	578.2	580.3	585.2	586.7	590.6	595.3	605.1	612.3
20°	560.3	558.8	553.9	556.9	553.9	558.8	560.3	566.0	569.8	577.8	584.6
22.5°	538.4	535.1	533.5	532.6	533.5	535.1	538.4	541.1	546.1	553.5	561.2
25°	507.5	502.6	500.7	498.4	500.7	502.6	507.5	509.0	514.3	521.6	525.7
27.5°	476.7	474.0	471.5	470.9	471.5	474.0	476.7	478.8	483.4	489.7	497.3
30°	456.6	453.9	452.0	452.0	452.0	453.9	456.6	461.2	464.6	470.3	476.0
32.5°	438.7	436.6	434.7	434.4	434.7	436.6	438.7	441.1	445.1	451.4	457.4
35°	412.5	409.5	408.7	406.5	408.7	409.5	412.5	414.4	418.6	423.2	428.1
37.5°	385.4	382.9	382.8	382.6	382.8	382.9	385.4	388.8	392.3	396.4	402.4
40°	368.1	366.2	365.8	363.2	365.8	366.2	368.1	369.6	373.4	378.7	383.3
42.5°	349.6	348.6	347.3	346.1	347.3	348.6	349.6	352.6	355.8	359.6	365.4
45°	324.4	321.8	321.8	319.9	321.8	321.8	324.4	327.1	328.6	333.1	340.7
47.5°	298.4	296.4	296.6	294.6	296.6	296.4	298.4	299.3	301.7	306.2	310.4
50°	281.1	280.0	279.6	278.8	279.6	280.0	281.1	280.7	283.8	287.9	293.6
52.5°	263.8	263.3	264.7	263.0	264.7	263.3	263.8	264.6	266.7	269.4	274.8
55°	240.5	239.3	241.6	239.3	241.6	239.3	240.5	239.7	240.5	243.1	246.5
57.5°	213.6	212.6	214.6	213.5	214.6	212.6	213.6	213.8	216.1	216.5	219.5
60°	196.0	193.7	194.9	195.3	194.9	193.7	196.0	196.8	197.5	197.9	201.0
62.5°	175.0	173.7	174.5	172.8	174.5	173.7	175.0	176.7	178.4	180.3	182.1
65°	145.5	144.4	142.8	142.1	142.8	144.4	145.5	146.3	150.4	152.7	156.9
67.5°	122.2	119.5	119.4	120.0	119.4	119.5	122.2	122.1	125.1	127.0	129.8
70°	105.2	105.2	104.8	104.8	104.8	105.2	105.2	107.5	109.0	110.5	112.4
72.5°	93.4	93.1	92.4	92.1	92.4	93.1	93.4	94.1	95.0	96.6	98.5
75°	75.2	75.6	74.8	74.5	74.8	75.6	75.2	75.2	76.7	77.1	77.9
77.5°	55.5	53.9	54.8	53.9	54.8	53.9	55.5	57.1	57.6	59.3	59.3
80°	42.2	41.8	42.9	41.8	42.9	41.8	42.2	42.2	43.3	44.1	46.0
82.5°	33.4	33.0	33.5	32.7	33.5	33.0	33.4	33.0	33.6	34.6	34.4
85°	20.1	19.8	19.4	19.8	19.4	19.8	20.1	19.8	19.4	19.8	20.1
87.5°	8.5	8.2	8.3	8.3	8.3	8.2	8.5	8.2	8.4	8.3	8.3
90°	7.8	7.8	8.1	8.1	8.1	7.8	7.8	7.8	7.1	6.7	6.4
92.5°	24.5	23.6	23.1	22.5	23.1	23.6	24.5	29.0	34.2	45.4	62.6
95°	102.1	91.5	88.7	83.1	88.7	91.5	102.1	127.2	156.9	200.4	254.1
97.5°	235.3	215.5	205.3	200.7	205.3	215.5	235.3	257.1	298.4	340.8	378.4
100°	319.8	294.4	281.3	275.7	281.3	294.4	319.8	344.2	381.0	417.4	434.7
102.5°	395.9	377.8	363.6	359.4	363.6	377.8	395.9	422.0	446.9	464.3	453.6
105°	491.2	479.6	472.5	468.3	472.5	479.6	491.2	502.6	506.4	490.9	442.5
107.5°	531.3	531.3	528.9	526.1	528.9	531.3	531.3	525.6	507.1	467.2	402.6
110°	536.1	542.8	545.3	545.3	545.3	542.8	536.1	520.2	490.2	440.4	373.2



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	522.8	534.4	540.5	543.1	540.5	534.4	522.8	499.6	464.2	413.8	350.0
115°	490.2	507.1	517.0	521.6	517.0	507.1	490.2	462.6	424.1	375.7	320.9
117.5°	453.9	471.5	481.3	484.1	481.3	471.5	453.9	426.4	391.0	349.3	302.1
120°	430.5	447.4	457.0	459.8	457.0	447.4	430.5	404.3	373.2	334.3	291.9
122.5°	410.7	426.2	435.8	438.3	435.8	426.2	410.7	387.3	358.2	323.6	284.3
125°	385.2	399.7	407.5	411.0	407.5	399.7	385.2	365.4	340.0	309.2	273.2
127.5°	366.0	378.8	386.1	387.7	386.1	378.8	366.0	348.0	324.2	295.5	261.9
130°	354.1	365.8	372.9	375.0	372.9	365.8	354.1	336.5	313.5	285.9	254.8
132.5°	341.7	353.3	359.8	362.2	359.8	353.3	341.7	324.0	301.9	276.9	247.7
135°	321.3	332.9	339.3	341.4	339.3	332.9	321.3	305.7	285.6	262.9	238.6
137.5°	300.3	310.9	316.8	319.1	316.8	310.9	300.3	286.4	269.3	250.5	230.8
140°	287.3	296.5	301.8	303.6	301.8	296.5	287.3	274.2	259.4	243.1	226.5
142.5°	274.9	282.7	287.7	289.2	287.7	282.7	274.9	263.8	250.9	236.9	222.9
145°	258.0	264.0	267.9	269.3	267.9	264.0	258.0	249.5	240.0	229.0	218.1
147.5°	244.8	249.6	251.8	252.5	251.8	249.6	244.8	238.1	230.9	222.4	213.5
150°	237.1	241.4	242.8	243.1	242.8	241.4	237.1	231.8	225.5	218.8	211.0
152.5°	230.6	234.0	235.4	235.8	235.4	234.0	230.6	226.2	221.2	215.1	208.2
155°	221.9	224.4	225.5	225.8	225.5	224.4	221.9	218.4	214.5	209.6	203.9
157.5°	214.0	216.0	217.0	216.9	217.0	216.0	214.0	211.2	208.2	204.3	199.7
160°	208.9	210.6	211.3	211.0	211.3	210.6	208.9	206.4	203.9	200.4	196.9
162.5°	204.1	205.5	205.7	205.6	205.7	205.5	204.1	202.2	200.0	197.0	193.7
165°	197.2	197.9	197.9	197.9	197.9	197.9	197.2	195.8	194.0	191.9	189.4
167.5°	190.6	191.2	190.9	190.8	190.9	191.2	190.6	189.9	188.6	187.0	185.3
170°	186.6	187.0	187.0	186.6	187.0	187.0	186.6	185.9	185.2	184.1	183.1
172.5°	182.9	183.6	183.0	182.6	183.0	183.6	182.9	182.8	182.4	181.6	180.5
175°	178.5	178.8	178.1	177.8	178.1	178.8	178.5	178.5	178.5	177.8	177.8
177.5°	175.9	176.1	175.3	175.3	175.3	176.1	175.9	176.1	176.1	176.1	175.9
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	887.1	890.4	892.2	896.5	902.6	905.6	909.9	912.9	917.2	922.3	926.6
5°	829.6	838.8	844.8	854.3	863.1	871.8	882.8	890.8	901.4	913.6	923.1
7.5°	776.3	787.7	797.8	810.3	824.8	836.0	850.4	865.0	881.7	898.9	915.2
10°	742.3	753.7	766.2	781.8	796.2	811.4	828.5	845.6	866.5	885.9	907.9
12.5°	708.5	721.1	735.2	752.6	770.1	789.5	806.9	826.1	848.6	873.7	897.3
15°	666.7	678.8	694.0	708.8	729.0	750.2	773.4	798.9	823.9	852.1	881.3
17.5°	621.8	635.1	651.9	669.0	690.2	715.1	737.9	765.7	793.9	826.7	861.1
20°	592.6	606.3	626.0	645.0	664.4	688.7	715.7	744.2	774.2	808.7	847.1
22.5°	569.5	579.2	598.7	618.0	640.7	665.6	692.0	721.7	754.4	790.2	830.4
25°	535.2	546.6	560.7	580.8	604.4	630.6	657.2	688.7	724.4	760.9	803.8
27.5°	504.8	514.1	528.0	543.8	567.3	594.5	622.8	655.7	692.3	729.4	774.6
30°	483.2	493.5	506.7	523.5	542.1	571.7	600.6	632.9	670.1	708.5	754.8
32.5°	464.4	474.9	486.4	502.2	522.3	548.6	578.4	610.1	647.9	687.5	732.6
35°	438.0	445.2	455.8	471.4	491.2	512.4	542.8	576.3	613.1	654.1	699.3
37.5°	407.8	417.1	427.7	441.2	458.5	481.5	509.8	543.6	577.8	617.1	658.3
40°	390.1	398.9	410.6	420.5	438.8	459.6	485.5	520.8	555.0	591.8	629.4
42.5°	372.2	380.6	390.6	402.9	419.3	439.6	463.6	496.5	533.1	567.8	599.4
45°	344.2	352.9	362.4	373.8	389.0	408.7	432.7	462.7	494.6	526.5	550.4
47.5°	317.3	325.5	334.5	346.2	360.2	379.3	400.7	427.2	458.2	485.3	502.4
50°	298.2	305.8	315.7	327.1	340.7	358.6	379.1	405.3	431.2	455.8	471.4
52.5°	279.4	287.9	297.7	307.6	320.7	338.5	357.5	380.1	404.7	424.8	437.7
55°	251.1	259.1	268.2	278.4	291.4	306.6	326.7	344.5	363.9	381.0	388.6
57.5°	223.8	230.8	239.4	250.0	261.7	275.8	291.7	308.9	322.6	334.7	343.3
60°	205.9	212.0	219.9	229.1	241.6	254.5	268.9	284.9	295.5	305.8	313.8
62.5°	187.7	193.4	201.1	209.3	220.3	232.3	246.2	259.1	269.4	276.3	285.5
65°	160.3	166.0	172.5	181.2	189.9	199.8	212.3	221.8	229.1	236.7	242.4
67.5°	134.9	139.6	145.7	152.6	159.9	169.4	179.1	187.0	192.0	196.5	203.4
70°	118.1	121.9	126.9	132.2	140.2	149.7	157.3	163.3	166.8	171.3	179.7
72.5°	101.1	105.5	110.2	115.5	121.9	129.9	136.6	142.7	144.9	148.5	153.8
75°	79.8	82.1	85.9	89.6	94.2	101.0	107.5	109.0	110.9	114.0	117.8
77.5°	60.3	62.4	63.9	66.4	70.0	75.5	78.9	81.2	81.7	82.8	86.5
80°	47.9	49.0	50.5	52.4	53.9	58.5	60.4	62.7	63.4	64.6	66.5
82.5°	35.1	36.2	37.2	38.7	41.2	43.0	44.9	47.2	47.3	48.2	48.5
85°	20.5	20.9	20.1	20.9	21.3	22.0	23.9	25.8	25.5	25.1	26.2
87.5°	8.5	8.4	8.0	8.8	8.1	8.3	8.2	8.3	8.8	9.3	9.8
90°	6.0	5.7	4.9	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4
92.5°	92.2	113.9	115.8	80.6	48.3	29.0	18.7	12.6	8.2	5.2	4.3
95°	306.4	313.1	255.5	158.0	80.2	42.4	26.5	18.7	14.8	12.0	11.7
97.5°	387.7	334.4	228.2	126.1	69.1	44.1	32.7	25.7	21.8	19.8	19.4
100°	407.5	319.1	203.6	114.5	68.6	48.1	37.5	30.7	26.9	25.4	24.7
102.5°	395.6	292.3	184.9	109.7	71.1	52.9	42.6	36.4	32.2	31.1	30.7
105°	357.7	256.2	166.8	107.8	76.3	60.8	50.9	45.2	41.7	39.9	39.9
107.5°	318.9	231.4	159.2	111.0	84.1	69.1	60.2	54.3	51.4	49.7	49.0
110°	296.9	219.8	156.9	114.2	89.8	75.3	66.1	60.8	57.6	56.2	55.5



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	280.5	213.0	156.9	118.1	95.1	81.2	72.3	67.0	63.8	62.7	62.0
115°	262.6	205.7	158.0	124.0	103.6	90.5	81.6	76.3	73.2	72.1	71.4
117.5°	251.9	202.1	160.3	130.8	112.2	99.8	91.3	85.2	82.1	80.9	79.9
120°	246.0	200.4	162.6	135.4	118.4	106.0	97.2	91.2	88.0	86.6	85.5
122.5°	240.9	199.0	164.5	140.4	124.3	112.0	103.1	96.6	93.4	92.2	91.5
125°	234.0	197.2	167.9	147.4	132.2	120.5	111.3	104.6	101.4	99.7	99.0
127.5°	227.6	196.4	171.6	153.7	139.7	128.5	119.3	112.2	108.1	105.9	104.8
130°	223.4	195.8	173.9	158.0	144.5	133.6	124.4	117.0	112.4	109.6	108.5
132.5°	220.0	195.8	176.4	161.7	149.1	138.1	128.9	121.2	116.1	112.7	111.3
135°	215.9	195.8	179.9	166.8	155.1	144.2	134.7	127.2	121.6	117.3	115.9
137.5°	212.3	196.2	183.1	170.6	159.5	149.5	139.7	132.4	126.7	122.8	121.7
140°	210.6	196.5	184.5	173.2	162.6	152.3	142.8	136.1	130.4	126.2	125.1
142.5°	209.2	196.8	185.3	174.6	164.5	154.9	145.9	139.5	133.8	129.8	129.1
145°	207.1	196.5	186.2	176.7	167.9	158.7	150.6	144.2	139.2	135.7	135.0
147.5°	204.9	195.6	186.6	178.0	170.0	161.9	154.8	149.3	144.7	141.6	141.2
150°	203.2	194.7	186.6	178.8	171.4	163.6	157.6	152.7	148.1	145.6	144.9
152.5°	201.2	193.6	186.3	179.4	172.8	165.6	160.2	155.5	151.5	149.3	148.9
155°	197.9	191.6	185.5	179.9	174.2	168.2	163.3	159.7	156.2	154.1	154.1
157.5°	194.8	189.4	184.6	180.2	175.4	170.3	166.5	163.4	160.4	158.7	158.8
160°	192.3	188.0	183.8	180.2	176.0	171.4	168.2	165.4	162.9	161.5	161.9
162.5°	190.0	186.3	182.9	180.0	176.6	172.5	169.9	167.7	165.5	164.1	164.4
165°	186.6	183.8	181.7	179.5	176.7	173.9	171.8	170.3	168.6	167.5	168.2
167.5°	183.3	181.3	179.7	178.7	176.7	174.4	173.0	172.0	171.1	170.4	170.8
170°	181.3	179.9	178.8	178.1	176.7	174.9	173.9	173.2	172.5	172.1	172.5
172.5°	179.3	178.2	177.7	177.6	176.4	174.9	174.4	174.0	173.3	173.0	173.6
175°	176.7	176.4	176.4	176.7	176.0	174.9	174.9	174.9	174.6	174.2	174.9
177.5°	175.6	175.3	175.3	175.9	175.6	175.0	175.0	175.3	175.0	175.0	175.6
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	929.9	932.7	936.6	941.2	944.8	948.8	950.9	950.9	952.7	956.7	961.8
5°	932.6	942.5	952.0	964.1	973.6	984.6	993.0	1001.0	1008.2	1017.3	1026.8
7.5°	931.8	948.2	965.3	984.5	1005.6	1022.4	1039.6	1053.2	1066.5	1084.0	1097.8
10°	928.8	950.1	973.2	997.5	1024.1	1047.3	1068.2	1087.2	1105.4	1124.4	1141.5
12.5°	923.3	950.4	978.7	1007.9	1041.5	1068.0	1094.9	1115.2	1136.4	1157.2	1178.3
15°	915.1	947.0	981.2	1021.9	1062.9	1092.5	1119.1	1145.3	1165.1	1188.6	1208.8
17.5°	898.2	939.3	982.3	1026.7	1066.1	1100.6	1128.4	1153.4	1174.4	1200.3	1227.7
20°	888.1	932.6	977.4	1024.9	1062.5	1097.8	1124.8	1150.6	1176.8	1210.7	1244.1
22.5°	874.2	921.6	969.2	1014.3	1054.0	1088.1	1116.0	1147.6	1182.0	1220.4	1260.8
25°	852.1	901.1	948.2	991.1	1029.8	1064.8	1102.8	1145.3	1187.1	1237.6	1295.7
27.5°	824.0	871.3	913.3	958.6	997.2	1041.6	1089.0	1135.1	1195.4	1264.9	1337.5
30°	803.0	847.9	887.8	930.7	974.4	1023.4	1076.6	1130.9	1202.7	1284.3	1370.6
32.5°	778.7	819.3	858.9	900.3	950.7	1004.5	1061.1	1127.5	1213.3	1306.2	1395.5
35°	736.6	773.0	811.4	857.4	910.9	969.4	1041.6	1122.5	1226.2	1326.1	1406.3
37.5°	692.4	721.1	759.7	808.1	866.5	934.2	1016.1	1114.4	1220.9	1310.6	1344.7
40°	658.3	685.3	725.9	776.8	834.6	908.7	1000.6	1101.6	1208.8	1271.0	1268.4
42.5°	624.6	651.9	691.0	742.2	802.4	885.3	979.9	1084.9	1175.3	1199.0	1149.6
45°	572.8	598.3	636.7	688.3	752.9	839.9	939.4	1040.1	1097.8	1059.5	961.5
47.5°	520.1	544.8	580.4	631.0	701.5	792.6	886.7	969.3	977.4	895.0	777.4
50°	485.5	508.6	542.5	596.4	664.8	753.7	844.5	909.4	889.3	788.6	667.4
52.5°	451.7	474.0	505.7	556.6	626.5	713.6	794.6	845.6	799.0	692.0	583.0
55°	401.9	423.2	455.1	501.8	565.2	645.0	716.1	734.7	666.3	558.4	470.3
57.5°	354.6	370.1	401.7	443.0	504.2	574.5	625.4	622.1	546.6	449.5	386.3
60°	323.3	337.3	367.3	405.3	463.4	526.5	562.2	547.0	470.7	390.5	329.7
62.5°	294.1	307.2	332.4	367.3	417.3	472.1	498.1	477.1	405.0	334.6	286.3
65°	250.0	259.5	279.6	311.9	351.0	389.0	412.2	381.4	317.6	264.4	227.9
67.5°	208.7	216.9	234.8	258.0	285.0	311.2	320.6	291.7	242.1	206.3	180.6
70°	182.0	189.6	201.7	223.4	241.2	259.8	264.4	238.6	197.2	169.8	153.8
72.5°	156.4	163.4	174.1	189.3	201.7	212.4	214.6	190.5	158.9	140.0	127.7
75°	119.3	125.4	132.2	137.9	145.9	147.8	147.0	128.4	111.3	98.8	91.9
77.5°	87.7	90.2	94.4	96.6	97.0	96.9	93.0	81.2	72.4	67.2	64.4
80°	67.6	69.5	70.7	71.4	71.8	68.0	63.8	56.6	53.6	50.5	47.1
82.5°	49.1	50.4	51.5	51.7	49.6	46.4	42.5	39.0	36.8	35.3	34.0
85°	26.6	27.0	26.6	24.7	22.0	20.9	20.1	19.4	19.0	18.6	18.6
87.5°	9.6	8.8	7.4	7.9	8.0	7.8	7.9	7.7	7.5	7.6	7.7
90°	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.7	6.0	6.4
92.5°	5.2	8.2	12.6	18.7	29.0	48.3	80.6	115.8	113.9	92.2	62.6
95°	12.0	14.8	18.7	26.5	42.4	80.2	158.0	255.5	313.1	306.4	254.1
97.5°	19.8	21.8	25.7	32.7	44.1	69.1	126.1	228.2	334.4	387.7	378.4
100°	25.4	26.9	30.7	37.5	48.1	68.6	114.5	203.6	319.1	407.5	434.7
102.5°	31.1	32.2	36.4	42.6	52.9	71.1	109.7	184.9	292.3	395.6	453.6
105°	39.9	41.7	45.2	50.9	60.8	76.3	107.8	166.8	256.2	357.7	442.5
107.5°	49.7	51.4	54.3	60.2	69.1	84.1	111.0	159.2	231.4	318.9	402.6
110°	56.2	57.6	60.8	66.1	75.3	89.8	114.2	156.9	219.8	296.9	373.2





TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	62.7	63.8	67.0	72.3	81.2	95.1	118.1	156.9	213.0	280.5	350.0
115°	72.1	73.2	76.3	81.6	90.5	103.6	124.0	158.0	205.7	262.6	320.9
117.5°	80.9	82.1	85.2	91.3	99.8	112.2	130.8	160.3	202.1	251.9	302.1
120°	86.6	88.0	91.2	97.2	106.0	118.4	135.4	162.6	200.4	246.0	291.9
122.5°	92.2	93.4	96.6	103.1	112.0	124.3	140.4	164.5	199.0	240.9	284.3
125°	99.7	101.4	104.6	111.3	120.5	132.2	147.4	167.9	197.2	234.0	273.2
127.5°	105.9	108.1	112.2	119.3	128.5	139.7	153.7	171.6	196.4	227.6	261.9
130°	109.6	112.4	117.0	124.4	133.6	144.5	158.0	173.9	195.8	223.4	254.8
132.5°	112.7	116.1	121.2	128.9	138.1	149.1	161.7	176.4	195.8	220.0	247.7
135°	117.3	121.6	127.2	134.7	144.2	155.1	166.8	179.9	195.8	215.9	238.6
137.5°	122.8	126.7	132.4	139.7	149.5	159.5	170.6	183.1	196.2	212.3	230.8
140°	126.2	130.4	136.1	142.8	152.3	162.6	173.2	184.5	196.5	210.6	226.5
142.5°	129.8	133.8	139.5	145.9	154.9	164.5	174.6	185.3	196.8	209.2	222.9
145°	135.7	139.2	144.2	150.6	158.7	167.9	176.7	186.2	196.5	207.1	218.1
147.5°	141.6	144.7	149.3	154.8	161.9	170.0	178.0	186.6	195.6	204.9	213.5
150°	145.6	148.1	152.7	157.6	163.6	171.4	178.8	186.6	194.7	203.2	211.0
152.5°	149.3	151.5	155.5	160.2	165.6	172.8	179.4	186.3	193.6	201.2	208.2
155°	154.1	156.2	159.7	163.3	168.2	174.2	179.9	185.5	191.6	197.9	203.9
157.5°	158.7	160.4	163.4	166.5	170.3	175.4	180.2	184.6	189.4	194.8	199.7
160°	161.5	162.9	165.4	168.2	171.4	176.0	180.2	183.8	188.0	192.3	196.9
162.5°	164.1	165.5	167.7	169.9	172.5	176.6	180.0	182.9	186.3	190.0	193.7
165°	167.5	168.6	170.3	171.8	173.9	176.7	179.5	181.7	183.8	186.6	189.4
167.5°	170.4	171.1	172.0	173.0	174.4	176.7	178.7	179.7	181.3	183.3	185.3
170°	172.1	172.5	173.2	173.9	174.9	176.7	178.1	178.8	179.9	181.3	183.1
172.5°	173.0	173.3	174.0	174.4	174.9	176.4	177.6	177.7	178.2	179.3	180.5
175°	174.2	174.6	174.9	174.9	174.9	176.0	176.7	176.4	176.4	176.7	177.8
177.5°	175.0	175.0	175.3	175.0	175.0	175.6	175.9	175.3	175.3	175.6	175.9
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	965.8	965.8	971.0	970.6	974.0	972.8	973.4
5°	1038.2	1044.6	1050.3	1054.1	1059.8	1061.4	1060.6
7.5°	1113.3	1127.6	1134.6	1144.2	1145.9	1150.9	1150.4
10°	1159.7	1173.8	1184.4	1192.8	1197.0	1202.3	1202.7
12.5°	1196.2	1208.1	1217.6	1225.3	1230.4	1232.1	1233.1
15°	1224.7	1238.0	1249.0	1260.0	1266.5	1271.4	1274.1
17.5°	1253.4	1273.9	1293.4	1308.4	1317.3	1324.9	1324.8
20°	1275.6	1299.2	1323.5	1340.6	1358.0	1365.6	1366.8
22.5°	1299.3	1335.3	1366.6	1393.1	1416.1	1424.0	1426.9
25°	1348.5	1395.6	1443.9	1481.1	1507.7	1523.3	1525.6
27.5°	1408.0	1471.8	1522.5	1556.9	1579.0	1590.5	1593.0
30°	1450.0	1508.8	1554.4	1580.3	1590.5	1592.0	1586.3
32.5°	1468.8	1512.8	1531.0	1529.5	1509.4	1496.0	1490.9
35°	1445.8	1436.7	1392.2	1339.0	1298.4	1272.6	1265.7
37.5°	1315.7	1237.1	1155.3	1075.0	1032.2	1010.5	973.1
40°	1187.5	1075.4	990.3	922.7	874.5	835.7	826.6
42.5°	1042.8	927.1	842.0	784.1	745.6	719.0	707.5
45°	838.0	738.5	668.2	623.7	594.1	574.7	566.0
47.5°	670.2	593.2	542.0	509.1	486.5	469.7	465.0
50°	578.2	516.6	473.3	445.6	428.5	415.6	410.3
52.5°	502.2	452.5	419.2	396.4	380.2	372.1	367.7
55°	414.4	371.5	347.6	329.3	320.2	313.8	310.7
57.5°	338.9	307.9	290.4	277.8	269.4	265.3	263.8
60°	296.7	272.4	256.4	246.5	240.8	235.5	234.0
62.5°	259.3	240.2	227.8	219.2	213.5	211.2	210.3
65°	208.9	196.4	187.3	182.0	177.4	176.6	176.3
67.5°	166.1	158.7	153.9	148.4	146.8	144.1	143.6
70°	142.1	137.1	131.4	129.5	127.6	125.0	125.4
72.5°	120.5	115.6	111.7	109.2	108.5	107.4	108.3
75°	88.1	86.6	85.1	83.2	82.4	82.4	82.1
77.5°	62.9	61.6	59.9	58.8	58.6	57.0	57.6
80°	45.6	43.7	42.9	43.3	42.2	41.8	41.8
82.5°	33.7	33.0	32.3	32.4	32.1	31.8	32.1
85°	18.6	18.2	18.2	17.9	17.9	17.5	17.5
87.5°	8.0	8.4	7.9	7.6	7.6	8.0	8.3
90°	6.7	7.1	7.8	7.8	7.8	8.1	8.1
92.5°	45.4	34.2	29.0	24.5	23.6	23.1	22.5
95°	200.4	156.9	127.2	102.1	91.5	88.7	83.1
97.5°	340.8	298.4	257.1	235.3	215.5	205.3	200.7
100°	417.4	381.0	344.2	319.8	294.4	281.3	275.7
102.5°	464.3	446.9	422.0	395.9	377.8	363.6	359.4
105°	490.9	506.4	502.6	491.2	479.6	472.5	468.3
107.5°	467.2	507.1	525.6	531.3	531.3	528.9	526.1
110°	440.4	490.2	520.2	536.1	542.8	545.3	545.3



TEST NUMBER: P333522

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	413.8	464.2	499.6	522.8	534.4	540.5	543.1
115°	375.7	424.1	462.6	490.2	507.1	517.0	521.6
117.5°	349.3	391.0	426.4	453.9	471.5	481.3	484.1
120°	334.3	373.2	404.3	430.5	447.4	457.0	459.8
122.5°	323.6	358.2	387.3	410.7	426.2	435.8	438.3
125°	309.2	340.0	365.4	385.2	399.7	407.5	411.0
127.5°	295.5	324.2	348.0	366.0	378.8	386.1	387.7
130°	285.9	313.5	336.5	354.1	365.8	372.9	375.0
132.5°	276.9	301.9	324.0	341.7	353.3	359.8	362.2
135°	262.9	285.6	305.7	321.3	332.9	339.3	341.4
137.5°	250.5	269.3	286.4	300.3	310.9	316.8	319.1
140°	243.1	259.4	274.2	287.3	296.5	301.8	303.6
142.5°	236.9	250.9	263.8	274.9	282.7	287.7	289.2
145°	229.0	240.0	249.5	258.0	264.0	267.9	269.3
147.5°	222.4	230.9	238.1	244.8	249.6	251.8	252.5
150°	218.8	225.5	231.8	237.1	241.4	242.8	243.1
152.5°	215.1	221.2	226.2	230.6	234.0	235.4	235.8
155°	209.6	214.5	218.4	221.9	224.4	225.5	225.8
157.5°	204.3	208.2	211.2	214.0	216.0	217.0	216.9
160°	200.4	203.9	206.4	208.9	210.6	211.3	211.0
162.5°	197.0	200.0	202.2	204.1	205.5	205.7	205.6
165°	191.9	194.0	195.8	197.2	197.9	197.9	197.9
167.5°	187.0	188.6	189.9	190.6	191.2	190.9	190.8
170°	184.1	185.2	185.9	186.6	187.0	187.0	186.6
172.5°	181.6	182.4	182.8	182.9	183.6	183.0	182.6
175°	177.8	178.5	178.5	178.5	178.8	178.1	177.8
177.5°	176.1	176.1	176.1	175.9	176.1	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3

(END OF REPORT)