

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333526

Luminaire Tested: **S125RDIP-S610D590U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333526
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D590U835-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4762.6 lumens
Efficiency: N/A
Efficacy: 145.2 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	43
2	90	83	77	72	83	77	71	67	65	61	58	55	52	50	45	43	41	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5977	5977	5977	5977
5°	6876	5984	5285	5984
10°	7887	5954	4663	5954
15°	8519	5893	4145	5893
20°	9394	5822	3827	5822
25°	10871	5728	3552	5728
30°	11830	5629	3371	5629
35°	9979	5513	3205	5513
40°	6969	5306	3062	5306
45°	5170	5027	2922	5027
50°	4122	4736	2801	4736
55°	3498	4376	2694	4376
60°	3023	4053	2523	4053
65°	2694	3704	2172	3704
70°	2368	3393	1979	3393
75°	2049	2939	1859	2939
80°	1555	2473	1555	2473
85°	1297	1941	1467	1941



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.7	1.9
10°-20°	260.1	5.5
20°-30°	412.3	8.7
30°-40°	497.2	10.4
40°-50°	444.0	9.3
50°-60°	340.5	7.1
60°-70°	221.3	4.6
70°-80°	107.6	2.3
80°-90°	27.3	0.6
90°-100°	28.0	0.6
100°-110°	172.4	3.6
110°-120°	312.6	6.6
120°-130°	401.2	8.4
130°-140°	431.5	9.1
140°-150°	405.1	8.5
150°-160°	327.7	6.9
160°-170°	211.9	4.4
170°-180°	73.1	1.5
0°-30°	761.1	16.0
0°-40°	1258.3	26.4
0°-60°	2042.9	42.9
0°-90°	2399.1	50.4
90°-120°	513.0	10.8
90°-150°	1750.8	36.8
90°-180°	2364.0	49.6
0°-180°	4762.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	925	925	925	925	925	
5°	1061	923	815	923	1061	106
15°	1274	881	620	881	1274	365
25°	1526	804	498	804	1526	700
35°	1266	699	406	699	1266	765
45°	566	550	320	550	566	452
55°	311	389	239	389	311	282
65°	176	242	142	242	176	175
75°	82	118	74	118	82	87
85°	18	26	20	26	18	20
90°	14	1	14	1	14	7
95°	12	32	12	32	12	10
105°	169	168	169	168	169	153
115°	313	315	313	315	313	310
125°	448	448	448	448	448	398
135°	556	559	556	559	556	429
145°	646	648	646	648	646	403
155°	708	713	708	713	708	326
165°	748	752	748	752	748	211
175°	766	770	766	770	766	73
180°	770	770	770	770	770	



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	973.4	972.8	974.0	970.6	971.0	965.8	965.8	961.8	956.7	952.7	950.9
5°	1060.6	1061.4	1059.8	1054.1	1050.3	1044.6	1038.2	1026.8	1017.3	1008.2	1001.0
7.5°	1150.4	1150.9	1145.9	1144.2	1134.6	1127.6	1113.3	1097.8	1084.0	1066.5	1053.2
10°	1202.7	1202.3	1197.0	1192.8	1184.4	1173.8	1159.7	1141.5	1124.4	1105.4	1087.2
12.5°	1233.1	1232.1	1230.4	1225.3	1217.6	1208.1	1196.2	1178.3	1157.2	1136.4	1115.2
15°	1274.1	1271.4	1266.5	1260.0	1249.0	1238.0	1224.7	1208.8	1188.6	1165.1	1145.3
17.5°	1324.8	1324.9	1317.3	1308.4	1293.4	1273.9	1253.4	1227.7	1200.3	1174.4	1153.4
20°	1366.8	1365.6	1358.0	1340.6	1323.5	1299.2	1275.6	1244.1	1210.7	1176.8	1150.6
22.5°	1426.9	1424.0	1416.1	1393.1	1366.6	1335.3	1299.3	1260.8	1220.4	1182.0	1147.6
25°	1525.6	1523.3	1507.7	1481.1	1443.9	1395.6	1348.5	1295.7	1237.6	1187.1	1145.3
27.5°	1593.0	1590.5	1579.0	1556.9	1522.5	1471.8	1408.0	1337.5	1264.9	1195.4	1135.1
30°	1586.3	1592.0	1590.5	1580.3	1554.4	1508.8	1450.0	1370.6	1284.3	1202.7	1130.9
32.5°	1490.9	1496.0	1509.4	1529.5	1531.0	1512.8	1468.8	1395.5	1306.2	1213.3	1127.5
35°	1265.7	1272.6	1298.4	1339.0	1392.2	1436.7	1445.8	1406.3	1326.1	1226.2	1122.5
37.5°	973.1	1010.5	1032.2	1075.0	1155.3	1237.1	1315.7	1344.7	1310.6	1220.9	1114.4
40°	826.6	835.7	874.5	922.7	990.3	1075.4	1187.5	1268.4	1271.0	1208.8	1101.6
42.5°	707.5	719.0	745.6	784.1	842.0	927.1	1042.8	1149.6	1199.0	1175.3	1084.9
45°	566.0	574.7	594.1	623.7	668.2	738.5	838.0	961.5	1059.5	1097.8	1040.1
47.5°	465.0	469.7	486.5	509.1	542.0	593.2	670.2	777.4	895.0	977.4	969.3
50°	410.3	415.6	428.5	445.6	473.3	516.6	578.2	667.4	788.6	889.3	909.4
52.5°	367.7	372.1	380.2	396.4	419.2	452.5	502.2	583.0	692.0	799.0	845.6
55°	310.7	313.8	320.2	329.3	347.6	371.5	414.4	470.3	558.4	666.3	734.7
57.5°	263.8	265.3	269.4	277.8	290.4	307.9	338.9	386.3	449.5	546.6	622.1
60°	234.0	235.5	240.8	246.5	256.4	272.4	296.7	329.7	390.5	470.7	547.0
62.5°	210.3	211.2	213.5	219.2	227.8	240.2	259.3	286.3	334.6	405.0	477.1
65°	176.3	176.6	177.4	182.0	187.3	196.4	208.9	227.9	264.4	317.6	381.4
67.5°	143.6	144.1	146.8	148.4	153.9	158.7	166.1	180.6	206.3	242.1	291.7
70°	125.4	125.0	127.6	129.5	131.4	137.1	142.1	153.8	169.8	197.2	238.6
72.5°	108.3	107.4	108.5	109.2	111.7	115.6	120.5	127.7	140.0	158.9	190.5
75°	82.1	82.4	82.4	83.2	85.1	86.6	88.1	91.9	98.8	111.3	128.4
77.5°	57.6	57.0	58.6	58.8	59.9	61.6	62.9	64.4	67.2	72.4	81.2
80°	41.8	41.8	42.2	43.3	42.9	43.7	45.6	47.1	50.5	53.6	56.6
82.5°	32.1	31.8	32.1	32.4	32.3	33.0	33.7	34.0	35.3	36.8	39.0
85°	17.5	17.5	17.9	17.9	18.2	18.2	18.6	18.6	18.6	19.0	19.4
87.5°	9.4	9.0	8.7	8.6	8.8	9.3	8.9	8.5	8.3	8.2	8.3
90°	13.7	13.3	12.9	12.6	12.2	11.7	11.0	10.4	9.8	9.1	8.2
92.5°	12.8	12.6	12.4	12.2	12.1	11.7	11.0	10.4	9.8	9.1	8.3
95°	12.0	12.0	12.0	12.0	12.0	11.7	11.0	10.4	9.8	9.1	13.9
97.5°	12.0	12.0	12.0	12.0	12.0	13.8	17.3	20.9	24.5	28.1	37.6
100°	12.0	12.5	13.0	13.5	14.0	23.7	42.6	61.5	80.4	99.3	98.8
102.5°	71.8	80.4	89.0	97.6	106.3	112.4	115.9	119.5	123.1	126.7	126.4
105°	169.4	169.6	169.7	169.8	170.0	170.0	170.0	170.0	170.0	170.0	170.0
107.5°	213.6	214.0	214.4	214.8	215.1	215.3	215.3	215.3	215.2	215.2	215.0
110°	244.2	244.1	243.9	243.8	243.7	243.8	244.2	244.6	245.0	245.3	245.1



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.6	271.8	271.9	272.1	272.3	272.6	273.1	273.6	274.1	274.5	274.4
115°	312.7	313.4	314.2	314.9	315.7	316.3	316.8	317.3	317.9	318.4	318.2
117.5°	356.5	356.8	357.1	357.5	357.8	358.3	358.9	359.6	360.3	360.9	360.4
120°	383.4	384.0	384.7	385.3	385.9	386.4	386.6	386.9	387.1	387.4	387.0
122.5°	409.0	409.7	410.4	411.2	411.9	412.4	412.7	412.9	413.2	413.4	413.2
125°	447.9	448.3	448.6	449.0	449.4	449.8	450.3	450.9	451.4	451.9	451.9
127.5°	480.6	481.6	482.5	483.4	484.4	485.0	485.3	485.5	485.8	486.1	486.2
130°	504.4	505.0	505.6	506.3	506.9	507.4	507.8	508.2	508.5	508.9	508.8
132.5°	526.3	526.9	527.5	528.2	528.8	529.2	529.2	529.3	529.4	529.5	529.7
135°	556.3	557.0	557.8	558.6	559.3	559.8	560.1	560.3	560.6	560.8	561.1
137.5°	586.4	587.1	587.7	588.4	589.0	589.3	589.3	589.2	589.2	589.1	589.4
140°	604.2	605.0	605.7	606.5	607.2	607.5	607.2	607.0	606.7	606.5	606.6
142.5°	621.1	621.8	622.6	623.4	624.1	624.5	624.4	624.4	624.3	624.3	624.1
145°	645.8	646.6	647.4	648.1	648.9	649.2	649.1	649.0	648.8	648.7	648.7
147.5°	666.3	667.2	668.1	669.0	669.9	670.3	670.2	670.0	669.9	669.7	669.5
150°	679.5	680.5	681.5	682.6	683.6	683.9	683.7	683.4	683.2	682.9	682.7
152.5°	691.8	692.7	693.7	694.6	695.5	695.8	695.6	695.3	695.1	694.8	694.5
155°	708.0	709.1	710.1	711.1	712.1	712.4	712.0	711.7	711.3	710.9	710.6
157.5°	721.6	722.6	723.6	724.7	725.7	726.0	725.6	725.2	724.8	724.4	724.3
160°	730.3	731.3	732.3	733.3	734.3	734.6	734.1	733.6	733.1	732.6	732.4
162.5°	738.0	739.2	740.3	741.4	742.5	742.7	742.0	741.3	740.6	739.9	739.7
165°	748.5	749.6	750.6	751.6	752.6	752.7	752.0	751.2	750.4	749.7	749.6
167.5°	755.8	757.0	758.1	759.3	760.4	760.5	759.6	758.7	757.8	756.9	756.7
170°	760.0	761.1	762.2	763.4	764.5	764.6	763.6	762.6	761.5	760.5	760.4
172.5°	762.7	763.8	765.0	766.1	767.3	767.4	766.5	765.5	764.6	763.7	763.5
175°	766.2	767.4	768.5	769.7	770.8	770.9	769.8	768.8	767.8	766.8	766.7
177.5°	768.3	769.1	769.9	770.7	771.5	771.6	770.9	770.2	769.5	768.7	768.6
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	950.9	948.8	944.8	941.2	936.6	932.7	929.9	926.6	922.3	917.2	912.9
5°	993.0	984.6	973.6	964.1	952.0	942.5	932.6	923.1	913.6	901.4	890.8
7.5°	1039.6	1022.4	1005.6	984.5	965.3	948.2	931.8	915.2	898.9	881.7	865.0
10°	1068.2	1047.3	1024.1	997.5	973.2	950.1	928.8	907.9	885.9	866.5	845.6
12.5°	1094.9	1068.0	1041.5	1007.9	978.7	950.4	923.3	897.3	873.7	848.6	826.1
15°	1119.1	1092.5	1062.9	1021.9	981.2	947.0	915.1	881.3	852.1	823.9	798.9
17.5°	1128.4	1100.6	1066.1	1026.7	982.3	939.3	898.2	861.1	826.7	793.9	765.7
20°	1124.8	1097.8	1062.5	1024.9	977.4	932.6	888.1	847.1	808.7	774.2	744.2
22.5°	1116.0	1088.1	1054.0	1014.3	969.2	921.6	874.2	830.4	790.2	754.4	721.7
25°	1102.8	1064.8	1029.8	991.1	948.2	901.1	852.1	803.8	760.9	724.4	688.7
27.5°	1089.0	1041.6	997.2	958.6	913.3	871.3	824.0	774.6	729.4	692.3	655.7
30°	1076.6	1023.4	974.4	930.7	887.8	847.9	803.0	754.8	708.5	670.1	632.9
32.5°	1061.1	1004.5	950.7	900.3	858.9	819.3	778.7	732.6	687.5	647.9	610.1
35°	1041.6	969.4	910.9	857.4	811.4	773.0	736.6	699.3	654.1	613.1	576.3
37.5°	1016.1	934.2	866.5	808.1	759.7	721.1	692.4	658.3	617.1	577.8	543.6
40°	1000.6	908.7	834.6	776.8	725.9	685.3	658.3	629.4	591.8	555.0	520.8
42.5°	979.9	885.3	802.4	742.2	691.0	651.9	624.6	599.4	567.8	533.1	496.5
45°	939.4	839.9	752.9	688.3	636.7	598.3	572.8	550.4	526.5	494.6	462.7
47.5°	886.7	792.6	701.5	631.0	580.4	544.8	520.1	502.4	485.3	458.2	427.2
50°	844.5	753.7	664.8	596.4	542.5	508.6	485.5	471.4	455.8	431.2	405.3
52.5°	794.6	713.6	626.5	556.6	505.7	474.0	451.7	437.7	424.8	404.7	380.1
55°	716.1	645.0	565.2	501.8	455.1	423.2	401.9	388.6	381.0	363.9	344.5
57.5°	625.4	574.5	504.2	443.0	401.7	370.1	354.6	343.3	334.7	322.6	308.9
60°	562.2	526.5	463.4	405.3	367.3	337.3	323.3	313.8	305.8	295.5	284.9
62.5°	498.1	472.1	417.3	367.3	332.4	307.2	294.1	285.5	276.3	269.4	259.1
65°	412.2	389.0	351.0	311.9	279.6	259.5	250.0	242.4	236.7	229.1	221.8
67.5°	320.6	311.2	285.0	258.0	234.8	216.9	208.7	203.4	196.5	192.0	187.0
70°	264.4	259.8	241.2	223.4	201.7	189.6	182.0	179.7	171.3	166.8	163.3
72.5°	214.6	212.4	201.7	189.3	174.1	163.4	156.4	153.8	148.5	144.9	142.7
75°	147.0	147.8	145.9	137.9	132.2	125.4	119.3	117.8	114.0	110.9	109.0
77.5°	93.0	96.9	97.0	96.6	94.4	90.2	87.7	86.5	82.8	81.7	81.2
80°	63.8	68.0	71.8	71.4	70.7	69.5	67.6	66.5	64.6	63.4	62.7
82.5°	42.5	46.4	49.6	51.7	51.5	50.4	49.1	48.5	48.2	47.3	47.2
85°	20.1	20.9	22.0	24.7	26.6	27.0	26.6	26.2	25.1	25.5	25.8
87.5°	8.5	8.3	8.4	8.2	7.7	9.0	9.7	9.8	9.4	9.0	8.6
90°	7.4	6.5	5.6	4.6	3.6	2.6	1.6	0.6	1.6	2.6	3.6
92.5°	7.6	6.8	6.0	5.9	6.7	7.4	8.1	8.8	8.1	7.4	6.7
95°	18.8	23.6	28.4	31.0	31.4	31.8	32.1	32.5	32.1	31.8	31.4
97.5°	47.1	56.7	66.2	70.6	69.9	69.3	68.6	67.9	68.6	69.3	69.9
100°	98.3	97.8	97.2	96.8	96.4	96.0	95.7	95.3	95.7	96.0	96.4
102.5°	126.1	125.7	125.4	125.0	124.6	124.1	123.6	123.1	123.6	124.1	124.6
105°	170.0	170.0	170.0	169.8	169.3	168.8	168.2	167.7	168.2	168.8	169.3
107.5°	214.7	214.4	214.2	214.1	214.1	214.1	214.1	214.1	214.1	214.1	214.1
110°	244.8	244.6	244.3	244.2	244.2	244.2	244.2	244.2	244.2	244.2	244.2



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	274.2	274.1	273.9	273.7	273.4	273.1	272.8	272.5	272.8	273.1	273.4
115°	318.1	318.0	317.9	317.5	316.8	316.2	315.6	314.9	315.6	316.2	316.8
117.5°	360.0	359.5	359.0	358.8	358.8	358.8	358.8	358.9	358.8	358.8	358.8
120°	386.6	386.3	385.9	385.7	385.9	386.0	386.1	386.3	386.1	386.0	385.9
122.5°	413.1	412.9	412.7	412.4	411.9	411.4	410.9	410.4	410.9	411.4	411.9
125°	451.9	451.9	451.9	451.4	450.5	449.6	448.8	447.9	448.8	449.6	450.5
127.5°	486.3	486.3	486.4	486.1	485.5	484.9	484.2	483.6	484.2	484.9	485.5
130°	508.7	508.5	508.4	508.0	507.4	506.8	506.1	505.5	506.1	506.8	507.4
132.5°	530.0	530.3	530.6	530.3	529.6	528.9	528.1	527.4	528.1	528.9	529.6
135°	561.3	561.6	561.9	561.6	560.8	560.1	559.3	558.6	559.3	560.1	560.8
137.5°	589.6	589.8	590.1	589.8	589.2	588.5	587.9	587.2	587.9	588.5	589.2
140°	606.7	606.9	607.0	606.9	606.7	606.4	606.2	605.9	606.2	606.4	606.7
142.5°	623.9	623.8	623.6	623.4	623.3	623.1	623.0	622.8	623.0	623.1	623.3
145°	648.7	648.7	648.7	648.6	648.3	648.1	647.8	647.6	647.8	648.1	648.3
147.5°	669.4	669.2	669.1	669.0	669.1	669.1	669.2	669.2	669.2	669.1	669.1
150°	682.4	682.2	681.9	681.9	682.2	682.4	682.7	682.9	682.7	682.4	682.2
152.5°	694.3	694.0	693.8	693.9	694.5	695.1	695.6	696.2	695.6	695.1	694.5
155°	710.4	710.1	709.9	710.1	710.9	711.7	712.4	713.2	712.4	711.7	710.9
157.5°	724.3	724.3	724.3	724.5	724.9	725.4	725.8	726.3	725.8	725.4	724.9
160°	732.3	732.2	732.1	732.4	733.1	733.9	734.7	735.4	734.7	733.9	733.1
162.5°	739.6	739.5	739.4	739.7	740.4	741.2	742.0	742.7	742.0	741.2	740.4
165°	749.4	749.3	749.2	749.5	750.3	751.0	751.8	752.5	751.8	751.0	750.3
167.5°	756.6	756.5	756.4	756.7	757.5	758.3	759.1	759.8	759.1	758.3	757.5
170°	760.3	760.1	760.0	760.4	761.3	762.2	763.1	764.0	763.1	762.2	761.3
172.5°	763.3	763.0	762.8	763.1	764.0	764.9	765.8	766.7	765.8	764.9	764.0
175°	766.6	766.4	766.3	766.6	767.4	768.1	768.9	769.7	768.9	768.1	767.4
177.5°	768.5	768.4	768.3	768.6	769.2	769.8	770.4	771.0	770.4	769.8	769.2
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	909.9	905.6	902.6	896.5	892.2	890.4	887.1	886.2	889.5	887.1	886.8
5°	882.8	871.8	863.1	854.3	844.8	838.8	829.6	828.1	825.8	822.4	821.7
7.5°	850.4	836.0	824.8	810.3	797.8	787.7	776.3	770.9	767.9	763.5	757.6
10°	828.5	811.4	796.2	781.8	766.2	753.7	742.3	733.5	727.8	722.5	720.2
12.5°	806.9	789.5	770.1	752.6	735.2	721.1	708.5	702.8	696.5	690.3	685.0
15°	773.4	750.2	729.0	708.8	694.0	678.8	666.7	658.3	648.8	646.2	635.9
17.5°	737.9	715.1	690.2	669.0	651.9	635.1	621.8	612.3	605.1	595.3	590.6
20°	715.7	688.7	664.4	645.0	626.0	606.3	592.6	584.6	577.8	569.8	566.0
22.5°	692.0	665.6	640.7	618.0	598.7	579.2	569.5	561.2	553.5	546.1	541.1
25°	657.2	630.6	604.4	580.8	560.7	546.6	535.2	525.7	521.6	514.3	509.0
27.5°	622.8	594.5	567.3	543.8	528.0	514.1	504.8	497.3	489.7	483.4	478.8
30°	600.6	571.7	542.1	523.5	506.7	493.5	483.2	476.0	470.3	464.6	461.2
32.5°	578.4	548.6	522.3	502.2	486.4	474.9	464.4	457.4	451.4	445.1	441.1
35°	542.8	512.4	491.2	471.4	455.8	445.2	438.0	428.1	423.2	418.6	414.4
37.5°	509.8	481.5	458.5	441.2	427.7	417.1	407.8	402.4	396.4	392.3	388.8
40°	485.5	459.6	438.8	420.5	410.6	398.9	390.1	383.3	378.7	373.4	369.6
42.5°	463.6	439.6	419.3	402.9	390.6	380.6	372.2	365.4	359.6	355.8	352.6
45°	432.7	408.7	389.0	373.8	362.4	352.9	344.2	340.7	333.1	328.6	327.1
47.5°	400.7	379.3	360.2	346.2	334.5	325.5	317.3	310.4	306.2	301.7	299.3
50°	379.1	358.6	340.7	327.1	315.7	305.8	298.2	293.6	287.9	283.8	280.7
52.5°	357.5	338.5	320.7	307.6	297.7	287.9	279.4	274.8	269.4	266.7	264.6
55°	326.7	306.6	291.4	278.4	268.2	259.1	251.1	246.5	243.1	240.5	239.7
57.5°	291.7	275.8	261.7	250.0	239.4	230.8	223.8	219.5	216.5	216.1	213.8
60°	268.9	254.5	241.6	229.1	219.9	212.0	205.9	201.0	197.9	197.5	196.8
62.5°	246.2	232.3	220.3	209.3	201.1	193.4	187.7	182.1	180.3	178.4	176.7
65°	212.3	199.8	189.9	181.2	172.5	166.0	160.3	156.9	152.7	150.4	146.3
67.5°	179.1	169.4	159.9	152.6	145.7	139.6	134.9	129.8	127.0	125.1	122.1
70°	157.3	149.7	140.2	132.2	126.9	121.9	118.1	112.4	110.5	109.0	107.5
72.5°	136.6	129.9	121.9	115.5	110.2	105.5	101.1	98.5	96.6	95.0	94.1
75°	107.5	101.0	94.2	89.6	85.9	82.1	79.8	77.9	77.1	76.7	75.2
77.5°	78.9	75.5	70.0	66.4	63.9	62.4	60.3	59.3	59.3	57.6	57.1
80°	60.4	58.5	53.9	52.4	50.5	49.0	47.9	46.0	44.1	43.3	42.2
82.5°	44.9	43.0	41.2	38.7	37.2	36.2	35.1	34.4	34.6	33.6	33.0
85°	23.9	22.0	21.3	20.9	20.1	20.9	20.5	20.1	19.8	19.4	19.8
87.5°	8.5	8.7	8.6	9.4	8.6	9.1	9.2	9.1	9.2	9.3	9.1
90°	4.6	5.6	6.5	7.4	8.2	9.1	9.8	10.4	11.0	11.7	12.2
92.5°	5.9	6.0	6.8	7.6	8.3	9.1	9.8	10.4	11.0	11.7	12.1
95°	31.0	28.4	23.6	18.8	13.9	9.1	9.8	10.4	11.0	11.7	12.0
97.5°	70.6	66.2	56.7	47.1	37.6	28.1	24.5	20.9	17.3	13.8	12.0
100°	96.8	97.2	97.8	98.3	98.8	99.3	80.4	61.5	42.6	23.7	14.0
102.5°	125.0	125.4	125.7	126.1	126.4	126.7	123.1	119.5	115.9	112.4	106.3
105°	169.8	170.0	170.0	170.0	170.0	170.0	170.0	170.0	170.0	170.0	170.0
107.5°	214.1	214.2	214.4	214.7	215.0	215.2	215.2	215.3	215.3	215.3	215.1
110°	244.2	244.3	244.6	244.8	245.1	245.3	245.0	244.6	244.2	243.8	243.7



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	273.7	273.9	274.1	274.2	274.4	274.5	274.1	273.6	273.1	272.6	272.3
115°	317.5	317.9	318.0	318.1	318.2	318.4	317.9	317.3	316.8	316.3	315.7
117.5°	358.8	359.0	359.5	360.0	360.4	360.9	360.3	359.6	358.9	358.3	357.8
120°	385.7	385.9	386.3	386.6	387.0	387.4	387.1	386.9	386.6	386.4	385.9
122.5°	412.4	412.7	412.9	413.1	413.2	413.4	413.2	412.9	412.7	412.4	411.9
125°	451.4	451.9	451.9	451.9	451.9	451.9	451.4	450.9	450.3	449.8	449.4
127.5°	486.1	486.4	486.3	486.3	486.2	486.1	485.8	485.5	485.3	485.0	484.4
130°	508.0	508.4	508.5	508.7	508.8	508.9	508.5	508.2	507.8	507.4	506.9
132.5°	530.3	530.6	530.3	530.0	529.7	529.5	529.4	529.3	529.2	529.2	528.8
135°	561.6	561.9	561.6	561.3	561.1	560.8	560.6	560.3	560.1	559.8	559.3
137.5°	589.8	590.1	589.8	589.6	589.4	589.1	589.2	589.2	589.3	589.3	589.0
140°	606.9	607.0	606.9	606.7	606.6	606.5	606.7	607.0	607.2	607.5	607.2
142.5°	623.4	623.6	623.8	623.9	624.1	624.3	624.3	624.4	624.4	624.5	624.1
145°	648.6	648.7	648.7	648.7	648.7	648.7	648.8	649.0	649.1	649.2	648.9
147.5°	669.0	669.1	669.2	669.4	669.5	669.7	669.9	670.0	670.2	670.3	669.9
150°	681.9	681.9	682.2	682.4	682.7	682.9	683.2	683.4	683.7	683.9	683.6
152.5°	693.9	693.8	694.0	694.3	694.5	694.8	695.1	695.3	695.6	695.8	695.5
155°	710.1	709.9	710.1	710.4	710.6	710.9	711.3	711.7	712.0	712.4	712.1
157.5°	724.5	724.3	724.3	724.3	724.3	724.4	724.8	725.2	725.6	726.0	725.7
160°	732.4	732.1	732.2	732.3	732.4	732.6	733.1	733.6	734.1	734.6	734.3
162.5°	739.7	739.4	739.5	739.6	739.7	739.9	740.6	741.3	742.0	742.7	742.5
165°	749.5	749.2	749.3	749.4	749.6	749.7	750.4	751.2	752.0	752.7	752.6
167.5°	756.7	756.4	756.5	756.6	756.7	756.9	757.8	758.7	759.6	760.5	760.4
170°	760.4	760.0	760.1	760.3	760.4	760.5	761.5	762.6	763.6	764.6	764.5
172.5°	763.1	762.8	763.0	763.3	763.5	763.7	764.6	765.5	766.5	767.4	767.3
175°	766.6	766.3	766.4	766.6	766.7	766.8	767.8	768.8	769.8	770.9	770.8
177.5°	768.6	768.3	768.4	768.5	768.6	768.7	769.5	770.2	770.9	771.6	771.5
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	886.5	883.1	882.2	883.4	882.2	883.1	886.5	886.8	887.1	889.5	886.2
5°	817.9	814.1	816.0	815.2	816.0	814.1	817.9	821.7	822.4	825.8	828.1
7.5°	757.5	752.8	747.8	749.4	747.8	752.8	757.5	757.6	763.5	767.9	770.9
10°	715.3	711.5	709.2	711.1	709.2	711.5	715.3	720.2	722.5	727.8	733.5
12.5°	679.7	677.5	675.5	674.7	675.5	677.5	679.7	685.0	690.3	696.5	702.8
15°	631.3	626.8	624.9	620.0	624.9	626.8	631.3	635.9	646.2	648.8	658.3
17.5°	586.7	585.2	580.3	578.2	580.3	585.2	586.7	590.6	595.3	605.1	612.3
20°	560.3	558.8	553.9	556.9	553.9	558.8	560.3	566.0	569.8	577.8	584.6
22.5°	538.4	535.1	533.5	532.6	533.5	535.1	538.4	541.1	546.1	553.5	561.2
25°	507.5	502.6	500.7	498.4	500.7	502.6	507.5	509.0	514.3	521.6	525.7
27.5°	476.7	474.0	471.5	470.9	471.5	474.0	476.7	478.8	483.4	489.7	497.3
30°	456.6	453.9	452.0	452.0	452.0	453.9	456.6	461.2	464.6	470.3	476.0
32.5°	438.7	436.6	434.7	434.4	434.7	436.6	438.7	441.1	445.1	451.4	457.4
35°	412.5	409.5	408.7	406.5	408.7	409.5	412.5	414.4	418.6	423.2	428.1
37.5°	385.4	382.9	382.8	382.6	382.8	382.9	385.4	388.8	392.3	396.4	402.4
40°	368.1	366.2	365.8	363.2	365.8	366.2	368.1	369.6	373.4	378.7	383.3
42.5°	349.6	348.6	347.3	346.1	347.3	348.6	349.6	352.6	355.8	359.6	365.4
45°	324.4	321.8	321.8	319.9	321.8	321.8	324.4	327.1	328.6	333.1	340.7
47.5°	298.4	296.4	296.6	294.6	296.6	296.4	298.4	299.3	301.7	306.2	310.4
50°	281.1	280.0	279.6	278.8	279.6	280.0	281.1	280.7	283.8	287.9	293.6
52.5°	263.8	263.3	264.7	263.0	264.7	263.3	263.8	264.6	266.7	269.4	274.8
55°	240.5	239.3	241.6	239.3	241.6	239.3	240.5	239.7	240.5	243.1	246.5
57.5°	213.6	212.6	214.6	213.5	214.6	212.6	213.6	213.8	216.1	216.5	219.5
60°	196.0	193.7	194.9	195.3	194.9	193.7	196.0	196.8	197.5	197.9	201.0
62.5°	175.0	173.7	174.5	172.8	174.5	173.7	175.0	176.7	178.4	180.3	182.1
65°	145.5	144.4	142.8	142.1	142.8	144.4	145.5	146.3	150.4	152.7	156.9
67.5°	122.2	119.5	119.4	120.0	119.4	119.5	122.2	122.1	125.1	127.0	129.8
70°	105.2	105.2	104.8	104.8	104.8	105.2	105.2	107.5	109.0	110.5	112.4
72.5°	93.4	93.1	92.4	92.1	92.4	93.1	93.4	94.1	95.0	96.6	98.5
75°	75.2	75.6	74.8	74.5	74.8	75.6	75.2	75.2	76.7	77.1	77.9
77.5°	55.5	53.9	54.8	53.9	54.8	53.9	55.5	57.1	57.6	59.3	59.3
80°	42.2	41.8	42.9	41.8	42.9	41.8	42.2	42.2	43.3	44.1	46.0
82.5°	33.4	33.0	33.5	32.7	33.5	33.0	33.4	33.0	33.6	34.6	34.4
85°	20.1	19.8	19.4	19.8	19.4	19.8	20.1	19.8	19.4	19.8	20.1
87.5°	9.5	9.3	9.3	9.4	9.3	9.3	9.5	9.1	9.3	9.2	9.1
90°	12.6	12.9	13.3	13.7	13.3	12.9	12.6	12.2	11.7	11.0	10.4
92.5°	12.2	12.4	12.6	12.8	12.6	12.4	12.2	12.1	11.7	11.0	10.4
95°	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0	11.7	11.0	10.4
97.5°	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0	13.8	17.3	20.9
100°	13.5	13.0	12.5	12.0	12.5	13.0	13.5	14.0	23.7	42.6	61.5
102.5°	97.6	89.0	80.4	71.8	80.4	89.0	97.6	106.3	112.4	115.9	119.5
105°	169.8	169.7	169.6	169.4	169.6	169.7	169.8	170.0	170.0	170.0	170.0
107.5°	214.8	214.4	214.0	213.6	214.0	214.4	214.8	215.1	215.3	215.3	215.3
110°	243.8	243.9	244.1	244.2	244.1	243.9	243.8	243.7	243.8	244.2	244.6



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	272.1	271.9	271.8	271.6	271.8	271.9	272.1	272.3	272.6	273.1	273.6
115°	314.9	314.2	313.4	312.7	313.4	314.2	314.9	315.7	316.3	316.8	317.3
117.5°	357.5	357.1	356.8	356.5	356.8	357.1	357.5	357.8	358.3	358.9	359.6
120°	385.3	384.7	384.0	383.4	384.0	384.7	385.3	385.9	386.4	386.6	386.9
122.5°	411.2	410.4	409.7	409.0	409.7	410.4	411.2	411.9	412.4	412.7	412.9
125°	449.0	448.6	448.3	447.9	448.3	448.6	449.0	449.4	449.8	450.3	450.9
127.5°	483.4	482.5	481.6	480.6	481.6	482.5	483.4	484.4	485.0	485.3	485.5
130°	506.3	505.6	505.0	504.4	505.0	505.6	506.3	506.9	507.4	507.8	508.2
132.5°	528.2	527.5	526.9	526.3	526.9	527.5	528.2	528.8	529.2	529.2	529.3
135°	558.6	557.8	557.0	556.3	557.0	557.8	558.6	559.3	559.8	560.1	560.3
137.5°	588.4	587.7	587.1	586.4	587.1	587.7	588.4	589.0	589.3	589.3	589.2
140°	606.5	605.7	605.0	604.2	605.0	605.7	606.5	607.2	607.5	607.2	607.0
142.5°	623.4	622.6	621.8	621.1	621.8	622.6	623.4	624.1	624.5	624.4	624.4
145°	648.1	647.4	646.6	645.8	646.6	647.4	648.1	648.9	649.2	649.1	649.0
147.5°	669.0	668.1	667.2	666.3	667.2	668.1	669.0	669.9	670.3	670.2	670.0
150°	682.6	681.5	680.5	679.5	680.5	681.5	682.6	683.6	683.9	683.7	683.4
152.5°	694.6	693.7	692.7	691.8	692.7	693.7	694.6	695.5	695.8	695.6	695.3
155°	711.1	710.1	709.1	708.0	709.1	710.1	711.1	712.1	712.4	712.0	711.7
157.5°	724.7	723.6	722.6	721.6	722.6	723.6	724.7	725.7	726.0	725.6	725.2
160°	733.3	732.3	731.3	730.3	731.3	732.3	733.3	734.3	734.6	734.1	733.6
162.5°	741.4	740.3	739.2	738.0	739.2	740.3	741.4	742.5	742.7	742.0	741.3
165°	751.6	750.6	749.6	748.5	749.6	750.6	751.6	752.6	752.7	752.0	751.2
167.5°	759.3	758.1	757.0	755.8	757.0	758.1	759.3	760.4	760.5	759.6	758.7
170°	763.4	762.2	761.1	760.0	761.1	762.2	763.4	764.5	764.6	763.6	762.6
172.5°	766.1	765.0	763.8	762.7	763.8	765.0	766.1	767.3	767.4	766.5	765.5
175°	769.7	768.5	767.4	766.2	767.4	768.5	769.7	770.8	770.9	769.8	768.8
177.5°	770.7	769.9	769.1	768.3	769.1	769.9	770.7	771.5	771.6	770.9	770.2
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	887.1	890.4	892.2	896.5	902.6	905.6	909.9	912.9	917.2	922.3	926.6
5°	829.6	838.8	844.8	854.3	863.1	871.8	882.8	890.8	901.4	913.6	923.1
7.5°	776.3	787.7	797.8	810.3	824.8	836.0	850.4	865.0	881.7	898.9	915.2
10°	742.3	753.7	766.2	781.8	796.2	811.4	828.5	845.6	866.5	885.9	907.9
12.5°	708.5	721.1	735.2	752.6	770.1	789.5	806.9	826.1	848.6	873.7	897.3
15°	666.7	678.8	694.0	708.8	729.0	750.2	773.4	798.9	823.9	852.1	881.3
17.5°	621.8	635.1	651.9	669.0	690.2	715.1	737.9	765.7	793.9	826.7	861.1
20°	592.6	606.3	626.0	645.0	664.4	688.7	715.7	744.2	774.2	808.7	847.1
22.5°	569.5	579.2	598.7	618.0	640.7	665.6	692.0	721.7	754.4	790.2	830.4
25°	535.2	546.6	560.7	580.8	604.4	630.6	657.2	688.7	724.4	760.9	803.8
27.5°	504.8	514.1	528.0	543.8	567.3	594.5	622.8	655.7	692.3	729.4	774.6
30°	483.2	493.5	506.7	523.5	542.1	571.7	600.6	632.9	670.1	708.5	754.8
32.5°	464.4	474.9	486.4	502.2	522.3	548.6	578.4	610.1	647.9	687.5	732.6
35°	438.0	445.2	455.8	471.4	491.2	512.4	542.8	576.3	613.1	654.1	699.3
37.5°	407.8	417.1	427.7	441.2	458.5	481.5	509.8	543.6	577.8	617.1	658.3
40°	390.1	398.9	410.6	420.5	438.8	459.6	485.5	520.8	555.0	591.8	629.4
42.5°	372.2	380.6	390.6	402.9	419.3	439.6	463.6	496.5	533.1	567.8	599.4
45°	344.2	352.9	362.4	373.8	389.0	408.7	432.7	462.7	494.6	526.5	550.4
47.5°	317.3	325.5	334.5	346.2	360.2	379.3	400.7	427.2	458.2	485.3	502.4
50°	298.2	305.8	315.7	327.1	340.7	358.6	379.1	405.3	431.2	455.8	471.4
52.5°	279.4	287.9	297.7	307.6	320.7	338.5	357.5	380.1	404.7	424.8	437.7
55°	251.1	259.1	268.2	278.4	291.4	306.6	326.7	344.5	363.9	381.0	388.6
57.5°	223.8	230.8	239.4	250.0	261.7	275.8	291.7	308.9	322.6	334.7	343.3
60°	205.9	212.0	219.9	229.1	241.6	254.5	268.9	284.9	295.5	305.8	313.8
62.5°	187.7	193.4	201.1	209.3	220.3	232.3	246.2	259.1	269.4	276.3	285.5
65°	160.3	166.0	172.5	181.2	189.9	199.8	212.3	221.8	229.1	236.7	242.4
67.5°	134.9	139.6	145.7	152.6	159.9	169.4	179.1	187.0	192.0	196.5	203.4
70°	118.1	121.9	126.9	132.2	140.2	149.7	157.3	163.3	166.8	171.3	179.7
72.5°	101.1	105.5	110.2	115.5	121.9	129.9	136.6	142.7	144.9	148.5	153.8
75°	79.8	82.1	85.9	89.6	94.2	101.0	107.5	109.0	110.9	114.0	117.8
77.5°	60.3	62.4	63.9	66.4	70.0	75.5	78.9	81.2	81.7	82.8	86.5
80°	47.9	49.0	50.5	52.4	53.9	58.5	60.4	62.7	63.4	64.6	66.5
82.5°	35.1	36.2	37.2	38.7	41.2	43.0	44.9	47.2	47.3	48.2	48.5
85°	20.5	20.9	20.1	20.9	21.3	22.0	23.9	25.8	25.5	25.1	26.2
87.5°	9.2	9.1	8.6	9.4	8.6	8.7	8.5	8.6	9.0	9.4	9.8
90°	9.8	9.1	8.2	7.4	6.5	5.6	4.6	3.6	2.6	1.6	0.6
92.5°	9.8	9.1	8.3	7.6	6.8	6.0	5.9	6.7	7.4	8.1	8.8
95°	9.8	9.1	13.9	18.8	23.6	28.4	31.0	31.4	31.8	32.1	32.5
97.5°	24.5	28.1	37.6	47.1	56.7	66.2	70.6	69.9	69.3	68.6	67.9
100°	80.4	99.3	98.8	98.3	97.8	97.2	96.8	96.4	96.0	95.7	95.3
102.5°	123.1	126.7	126.4	126.1	125.7	125.4	125.0	124.6	124.1	123.6	123.1
105°	170.0	170.0	170.0	170.0	170.0	170.0	169.8	169.3	168.8	168.2	167.7
107.5°	215.2	215.2	215.0	214.7	214.4	214.2	214.1	214.1	214.1	214.1	214.1
110°	245.0	245.3	245.1	244.8	244.6	244.3	244.2	244.2	244.2	244.2	244.2



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	274.1	274.5	274.4	274.2	274.1	273.9	273.7	273.4	273.1	272.8	272.5
115°	317.9	318.4	318.2	318.1	318.0	317.9	317.5	316.8	316.2	315.6	314.9
117.5°	360.3	360.9	360.4	360.0	359.5	359.0	358.8	358.8	358.8	358.8	358.9
120°	387.1	387.4	387.0	386.6	386.3	385.9	385.7	385.9	386.0	386.1	386.3
122.5°	413.2	413.4	413.2	413.1	412.9	412.7	412.4	411.9	411.4	410.9	410.4
125°	451.4	451.9	451.9	451.9	451.9	451.9	451.4	450.5	449.6	448.8	447.9
127.5°	485.8	486.1	486.2	486.3	486.3	486.4	486.1	485.5	484.9	484.2	483.6
130°	508.5	508.9	508.8	508.7	508.5	508.4	508.0	507.4	506.8	506.1	505.5
132.5°	529.4	529.5	529.7	530.0	530.3	530.6	530.3	529.6	528.9	528.1	527.4
135°	560.6	560.8	561.1	561.3	561.6	561.9	561.6	560.8	560.1	559.3	558.6
137.5°	589.2	589.1	589.4	589.6	589.8	590.1	589.8	589.2	588.5	587.9	587.2
140°	606.7	606.5	606.6	606.7	606.9	607.0	606.9	606.7	606.4	606.2	605.9
142.5°	624.3	624.3	624.1	623.9	623.8	623.6	623.4	623.3	623.1	623.0	622.8
145°	648.8	648.7	648.7	648.7	648.7	648.7	648.6	648.3	648.1	647.8	647.6
147.5°	669.9	669.7	669.5	669.4	669.2	669.1	669.0	669.1	669.1	669.2	669.2
150°	683.2	682.9	682.7	682.4	682.2	681.9	681.9	682.2	682.4	682.7	682.9
152.5°	695.1	694.8	694.5	694.3	694.0	693.8	693.9	694.5	695.1	695.6	696.2
155°	711.3	710.9	710.6	710.4	710.1	709.9	710.1	710.9	711.7	712.4	713.2
157.5°	724.8	724.4	724.3	724.3	724.3	724.3	724.5	724.9	725.4	725.8	726.3
160°	733.1	732.6	732.4	732.3	732.2	732.1	732.4	733.1	733.9	734.7	735.4
162.5°	740.6	739.9	739.7	739.6	739.5	739.4	739.7	740.4	741.2	742.0	742.7
165°	750.4	749.7	749.6	749.4	749.3	749.2	749.5	750.3	751.0	751.8	752.5
167.5°	757.8	756.9	756.7	756.6	756.5	756.4	756.7	757.5	758.3	759.1	759.8
170°	761.5	760.5	760.4	760.3	760.1	760.0	760.4	761.3	762.2	763.1	764.0
172.5°	764.6	763.7	763.5	763.3	763.0	762.8	763.1	764.0	764.9	765.8	766.7
175°	767.8	766.8	766.7	766.6	766.4	766.3	766.6	767.4	768.1	768.9	769.7
177.5°	769.5	768.7	768.6	768.5	768.4	768.3	768.6	769.2	769.8	770.4	771.0
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	929.9	932.7	936.6	941.2	944.8	948.8	950.9	950.9	952.7	956.7	961.8
5°	932.6	942.5	952.0	964.1	973.6	984.6	993.0	1001.0	1008.2	1017.3	1026.8
7.5°	931.8	948.2	965.3	984.5	1005.6	1022.4	1039.6	1053.2	1066.5	1084.0	1097.8
10°	928.8	950.1	973.2	997.5	1024.1	1047.3	1068.2	1087.2	1105.4	1124.4	1141.5
12.5°	923.3	950.4	978.7	1007.9	1041.5	1068.0	1094.9	1115.2	1136.4	1157.2	1178.3
15°	915.1	947.0	981.2	1021.9	1062.9	1092.5	1119.1	1145.3	1165.1	1188.6	1208.8
17.5°	898.2	939.3	982.3	1026.7	1066.1	1100.6	1128.4	1153.4	1174.4	1200.3	1227.7
20°	888.1	932.6	977.4	1024.9	1062.5	1097.8	1124.8	1150.6	1176.8	1210.7	1244.1
22.5°	874.2	921.6	969.2	1014.3	1054.0	1088.1	1116.0	1147.6	1182.0	1220.4	1260.8
25°	852.1	901.1	948.2	991.1	1029.8	1064.8	1102.8	1145.3	1187.1	1237.6	1295.7
27.5°	824.0	871.3	913.3	958.6	997.2	1041.6	1089.0	1135.1	1195.4	1264.9	1337.5
30°	803.0	847.9	887.8	930.7	974.4	1023.4	1076.6	1130.9	1202.7	1284.3	1370.6
32.5°	778.7	819.3	858.9	900.3	950.7	1004.5	1061.1	1127.5	1213.3	1306.2	1395.5
35°	736.6	773.0	811.4	857.4	910.9	969.4	1041.6	1122.5	1226.2	1326.1	1406.3
37.5°	692.4	721.1	759.7	808.1	866.5	934.2	1016.1	1114.4	1220.9	1310.6	1344.7
40°	658.3	685.3	725.9	776.8	834.6	908.7	1000.6	1101.6	1208.8	1271.0	1268.4
42.5°	624.6	651.9	691.0	742.2	802.4	885.3	979.9	1084.9	1175.3	1199.0	1149.6
45°	572.8	598.3	636.7	688.3	752.9	839.9	939.4	1040.1	1097.8	1059.5	961.5
47.5°	520.1	544.8	580.4	631.0	701.5	792.6	886.7	969.3	977.4	895.0	777.4
50°	485.5	508.6	542.5	596.4	664.8	753.7	844.5	909.4	889.3	788.6	667.4
52.5°	451.7	474.0	505.7	556.6	626.5	713.6	794.6	845.6	799.0	692.0	583.0
55°	401.9	423.2	455.1	501.8	565.2	645.0	716.1	734.7	666.3	558.4	470.3
57.5°	354.6	370.1	401.7	443.0	504.2	574.5	625.4	622.1	546.6	449.5	386.3
60°	323.3	337.3	367.3	405.3	463.4	526.5	562.2	547.0	470.7	390.5	329.7
62.5°	294.1	307.2	332.4	367.3	417.3	472.1	498.1	477.1	405.0	334.6	286.3
65°	250.0	259.5	279.6	311.9	351.0	389.0	412.2	381.4	317.6	264.4	227.9
67.5°	208.7	216.9	234.8	258.0	285.0	311.2	320.6	291.7	242.1	206.3	180.6
70°	182.0	189.6	201.7	223.4	241.2	259.8	264.4	238.6	197.2	169.8	153.8
72.5°	156.4	163.4	174.1	189.3	201.7	212.4	214.6	190.5	158.9	140.0	127.7
75°	119.3	125.4	132.2	137.9	145.9	147.8	147.0	128.4	111.3	98.8	91.9
77.5°	87.7	90.2	94.4	96.6	97.0	96.9	93.0	81.2	72.4	67.2	64.4
80°	67.6	69.5	70.7	71.4	71.8	68.0	63.8	56.6	53.6	50.5	47.1
82.5°	49.1	50.4	51.5	51.7	49.6	46.4	42.5	39.0	36.8	35.3	34.0
85°	26.6	27.0	26.6	24.7	22.0	20.9	20.1	19.4	19.0	18.6	18.6
87.5°	9.7	9.0	7.7	8.2	8.4	8.3	8.5	8.3	8.2	8.3	8.5
90°	1.6	2.6	3.6	4.6	5.6	6.5	7.4	8.2	9.1	9.8	10.4
92.5°	8.1	7.4	6.7	5.9	6.0	6.8	7.6	8.3	9.1	9.8	10.4
95°	32.1	31.8	31.4	31.0	28.4	23.6	18.8	13.9	9.1	9.8	10.4
97.5°	68.6	69.3	69.9	70.6	66.2	56.7	47.1	37.6	28.1	24.5	20.9
100°	95.7	96.0	96.4	96.8	97.2	97.8	98.3	98.8	99.3	80.4	61.5
102.5°	123.6	124.1	124.6	125.0	125.4	125.7	126.1	126.4	126.7	123.1	119.5
105°	168.2	168.8	169.3	169.8	170.0	170.0	170.0	170.0	170.0	170.0	170.0
107.5°	214.1	214.1	214.1	214.1	214.2	214.4	214.7	215.0	215.2	215.2	215.3
110°	244.2	244.2	244.2	244.2	244.3	244.6	244.8	245.1	245.3	245.0	244.6



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.8	273.1	273.4	273.7	273.9	274.1	274.2	274.4	274.5	274.1	273.6
115°	315.6	316.2	316.8	317.5	317.9	318.0	318.1	318.2	318.4	317.9	317.3
117.5°	358.8	358.8	358.8	358.8	359.0	359.5	360.0	360.4	360.9	360.3	359.6
120°	386.1	386.0	385.9	385.7	385.9	386.3	386.6	387.0	387.4	387.1	386.9
122.5°	410.9	411.4	411.9	412.4	412.7	412.9	413.1	413.2	413.4	413.2	412.9
125°	448.8	449.6	450.5	451.4	451.9	451.9	451.9	451.9	451.9	451.4	450.9
127.5°	484.2	484.9	485.5	486.1	486.4	486.3	486.3	486.2	486.1	485.8	485.5
130°	506.1	506.8	507.4	508.0	508.4	508.5	508.7	508.8	508.9	508.5	508.2
132.5°	528.1	528.9	529.6	530.3	530.6	530.3	530.0	529.7	529.5	529.4	529.3
135°	559.3	560.1	560.8	561.6	561.9	561.6	561.3	561.1	560.8	560.6	560.3
137.5°	587.9	588.5	589.2	589.8	590.1	589.8	589.6	589.4	589.1	589.2	589.2
140°	606.2	606.4	606.7	606.9	607.0	606.9	606.7	606.6	606.5	606.7	607.0
142.5°	623.0	623.1	623.3	623.4	623.6	623.8	623.9	624.1	624.3	624.3	624.4
145°	647.8	648.1	648.3	648.6	648.7	648.7	648.7	648.7	648.7	648.8	649.0
147.5°	669.2	669.1	669.1	669.0	669.1	669.2	669.4	669.5	669.7	669.9	670.0
150°	682.7	682.4	682.2	681.9	681.9	682.2	682.4	682.7	682.9	683.2	683.4
152.5°	695.6	695.1	694.5	693.9	693.8	694.0	694.3	694.5	694.8	695.1	695.3
155°	712.4	711.7	710.9	710.1	709.9	710.1	710.4	710.6	710.9	711.3	711.7
157.5°	725.8	725.4	724.9	724.5	724.3	724.3	724.3	724.3	724.4	724.8	725.2
160°	734.7	733.9	733.1	732.4	732.1	732.2	732.3	732.4	732.6	733.1	733.6
162.5°	742.0	741.2	740.4	739.7	739.4	739.5	739.6	739.7	739.9	740.6	741.3
165°	751.8	751.0	750.3	749.5	749.2	749.3	749.4	749.6	749.7	750.4	751.2
167.5°	759.1	758.3	757.5	756.7	756.4	756.5	756.6	756.7	756.9	757.8	758.7
170°	763.1	762.2	761.3	760.4	760.0	760.1	760.3	760.4	760.5	761.5	762.6
172.5°	765.8	764.9	764.0	763.1	762.8	763.0	763.3	763.5	763.7	764.6	765.5
175°	768.9	768.1	767.4	766.6	766.3	766.4	766.6	766.7	766.8	767.8	768.8
177.5°	770.4	769.8	769.2	768.6	768.3	768.4	768.5	768.6	768.7	769.5	770.2
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	965.8	965.8	971.0	970.6	974.0	972.8	973.4
5°	1038.2	1044.6	1050.3	1054.1	1059.8	1061.4	1060.6
7.5°	1113.3	1127.6	1134.6	1144.2	1145.9	1150.9	1150.4
10°	1159.7	1173.8	1184.4	1192.8	1197.0	1202.3	1202.7
12.5°	1196.2	1208.1	1217.6	1225.3	1230.4	1232.1	1233.1
15°	1224.7	1238.0	1249.0	1260.0	1266.5	1271.4	1274.1
17.5°	1253.4	1273.9	1293.4	1308.4	1317.3	1324.9	1324.8
20°	1275.6	1299.2	1323.5	1340.6	1358.0	1365.6	1366.8
22.5°	1299.3	1335.3	1366.6	1393.1	1416.1	1424.0	1426.9
25°	1348.5	1395.6	1443.9	1481.1	1507.7	1523.3	1525.6
27.5°	1408.0	1471.8	1522.5	1556.9	1579.0	1590.5	1593.0
30°	1450.0	1508.8	1554.4	1580.3	1590.5	1592.0	1586.3
32.5°	1468.8	1512.8	1531.0	1529.5	1509.4	1496.0	1490.9
35°	1445.8	1436.7	1392.2	1339.0	1298.4	1272.6	1265.7
37.5°	1315.7	1237.1	1155.3	1075.0	1032.2	1010.5	973.1
40°	1187.5	1075.4	990.3	922.7	874.5	835.7	826.6
42.5°	1042.8	927.1	842.0	784.1	745.6	719.0	707.5
45°	838.0	738.5	668.2	623.7	594.1	574.7	566.0
47.5°	670.2	593.2	542.0	509.1	486.5	469.7	465.0
50°	578.2	516.6	473.3	445.6	428.5	415.6	410.3
52.5°	502.2	452.5	419.2	396.4	380.2	372.1	367.7
55°	414.4	371.5	347.6	329.3	320.2	313.8	310.7
57.5°	338.9	307.9	290.4	277.8	269.4	265.3	263.8
60°	296.7	272.4	256.4	246.5	240.8	235.5	234.0
62.5°	259.3	240.2	227.8	219.2	213.5	211.2	210.3
65°	208.9	196.4	187.3	182.0	177.4	176.6	176.3
67.5°	166.1	158.7	153.9	148.4	146.8	144.1	143.6
70°	142.1	137.1	131.4	129.5	127.6	125.0	125.4
72.5°	120.5	115.6	111.7	109.2	108.5	107.4	108.3
75°	88.1	86.6	85.1	83.2	82.4	82.4	82.1
77.5°	62.9	61.6	59.9	58.8	58.6	57.0	57.6
80°	45.6	43.7	42.9	43.3	42.2	41.8	41.8
82.5°	33.7	33.0	32.3	32.4	32.1	31.8	32.1
85°	18.6	18.2	18.2	17.9	17.9	17.5	17.5
87.5°	8.9	9.3	8.8	8.6	8.7	9.0	9.4
90°	11.0	11.7	12.2	12.6	12.9	13.3	13.7
92.5°	11.0	11.7	12.1	12.2	12.4	12.6	12.8
95°	11.0	11.7	12.0	12.0	12.0	12.0	12.0
97.5°	17.3	13.8	12.0	12.0	12.0	12.0	12.0
100°	42.6	23.7	14.0	13.5	13.0	12.5	12.0
102.5°	115.9	112.4	106.3	97.6	89.0	80.4	71.8
105°	170.0	170.0	170.0	169.8	169.7	169.6	169.4
107.5°	215.3	215.3	215.1	214.8	214.4	214.0	213.6
110°	244.2	243.8	243.7	243.8	243.9	244.1	244.2



TEST NUMBER: P333526

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	273.1	272.6	272.3	272.1	271.9	271.8	271.6
115°	316.8	316.3	315.7	314.9	314.2	313.4	312.7
117.5°	358.9	358.3	357.8	357.5	357.1	356.8	356.5
120°	386.6	386.4	385.9	385.3	384.7	384.0	383.4
122.5°	412.7	412.4	411.9	411.2	410.4	409.7	409.0
125°	450.3	449.8	449.4	449.0	448.6	448.3	447.9
127.5°	485.3	485.0	484.4	483.4	482.5	481.6	480.6
130°	507.8	507.4	506.9	506.3	505.6	505.0	504.4
132.5°	529.2	529.2	528.8	528.2	527.5	526.9	526.3
135°	560.1	559.8	559.3	558.6	557.8	557.0	556.3
137.5°	589.3	589.3	589.0	588.4	587.7	587.1	586.4
140°	607.2	607.5	607.2	606.5	605.7	605.0	604.2
142.5°	624.4	624.5	624.1	623.4	622.6	621.8	621.1
145°	649.1	649.2	648.9	648.1	647.4	646.6	645.8
147.5°	670.2	670.3	669.9	669.0	668.1	667.2	666.3
150°	683.7	683.9	683.6	682.6	681.5	680.5	679.5
152.5°	695.6	695.8	695.5	694.6	693.7	692.7	691.8
155°	712.0	712.4	712.1	711.1	710.1	709.1	708.0
157.5°	725.6	726.0	725.7	724.7	723.6	722.6	721.6
160°	734.1	734.6	734.3	733.3	732.3	731.3	730.3
162.5°	742.0	742.7	742.5	741.4	740.3	739.2	738.0
165°	752.0	752.7	752.6	751.6	750.6	749.6	748.5
167.5°	759.6	760.5	760.4	759.3	758.1	757.0	755.8
170°	763.6	764.6	764.5	763.4	762.2	761.1	760.0
172.5°	766.5	767.4	767.3	766.1	765.0	763.8	762.7
175°	769.8	770.9	770.8	769.7	768.5	767.4	766.2
177.5°	770.9	771.6	771.5	770.7	769.9	769.1	768.3
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7

(END OF REPORT)