

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333528

Luminaire Tested: **S125RDIP-S610D590U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333528  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D590U835-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4520.8 lumens  
Efficiency: N/A  
Efficacy: 137.8 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	84	77	72	68	66	63	59	56	54	51	47	45	43	39
3	83	74	66	61	76	68	62	57	59	54	50	50	47	44	42	39	37	33
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	52	44	39	59	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	47	40	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5977	5977	5977	5977
5°	6876	5984	5285	5984
10°	7887	5954	4663	5954
15°	8519	5893	4145	5893
20°	9394	5822	3827	5822
25°	10871	5728	3552	5728
30°	11830	5629	3371	5629
35°	9979	5513	3205	5513
40°	6969	5306	3062	5306
45°	5170	5027	2922	5027
50°	4122	4736	2801	4736
55°	3498	4376	2694	4376
60°	3023	4053	2523	4053
65°	2694	3704	2172	3704
70°	2368	3393	1979	3393
75°	2049	2939	1859	2939
80°	1555	2473	1555	2473
85°	1297	1941	1467	1941



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.7	2.0
10°-20°	260.1	5.8
20°-30°	412.3	9.1
30°-40°	497.2	11.0
40°-50°	444.0	9.8
50°-60°	340.5	7.5
60°-70°	221.3	4.9
70°-80°	107.6	2.4
80°-90°	27.3	0.6
90°-100°	205.1	4.5
100°-110°	440.9	9.8
110°-120°	413.8	9.2
120°-130°	335.3	7.4
130°-140°	269.1	6.0
140°-150°	203.1	4.5
150°-160°	142.9	3.2
160°-170°	84.3	1.9
170°-180°	27.4	0.6
0°-30°	761.1	16.8
0°-40°	1258.3	27.8
0°-60°	2042.9	45.2
0°-90°	2399.0	53.1
90°-120°	1059.7	23.4
90°-150°	1867.2	41.3
90°-180°	2122.0	46.9
0°-180°	4520.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	925	925	925	925	925	
5°	1061	923	815	923	1061	106
15°	1274	881	620	881	1274	365
25°	1526	804	498	804	1526	700
35°	1266	699	406	699	1266	765
45°	566	550	320	550	566	452
55°	311	389	239	389	311	282
65°	176	242	142	242	176	175
75°	82	118	74	118	82	87
85°	18	26	20	26	18	20
90°	13	1	13	1	13	10
95°	134	19	134	19	134	190
105°	756	64	756	64	756	751
115°	842	115	842	115	842	823
125°	663	160	663	160	663	600
135°	551	187	551	187	551	427
145°	435	218	435	218	435	276
155°	364	249	364	249	364	170
165°	319	272	319	272	319	91
175°	287	282	287	282	287	28
180°	283	283	283	283	283	



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	973.4	972.8	974.0	970.6	971.0	965.8	965.8	961.8	956.7	952.7	950.9
5°	1060.6	1061.4	1059.8	1054.1	1050.3	1044.6	1038.2	1026.8	1017.3	1008.2	1001.0
7.5°	1150.4	1150.9	1145.9	1144.2	1134.6	1127.6	1113.3	1097.8	1084.0	1066.5	1053.2
10°	1202.7	1202.3	1197.0	1192.8	1184.4	1173.8	1159.7	1141.5	1124.4	1105.4	1087.2
12.5°	1233.1	1232.1	1230.4	1225.3	1217.6	1208.1	1196.2	1178.3	1157.2	1136.4	1115.2
15°	1274.1	1271.4	1266.5	1260.0	1249.0	1238.0	1224.7	1208.8	1188.6	1165.1	1145.3
17.5°	1324.8	1324.9	1317.3	1308.4	1293.4	1273.9	1253.4	1227.7	1200.3	1174.4	1153.4
20°	1366.8	1365.6	1358.0	1340.6	1323.5	1299.2	1275.6	1244.1	1210.7	1176.8	1150.6
22.5°	1426.9	1424.0	1416.1	1393.1	1366.6	1335.3	1299.3	1260.8	1220.4	1182.0	1147.6
25°	1525.6	1523.3	1507.7	1481.1	1443.9	1395.6	1348.5	1295.7	1237.6	1187.1	1145.3
27.5°	1593.0	1590.5	1579.0	1556.9	1522.5	1471.8	1408.0	1337.5	1264.9	1195.4	1135.1
30°	1586.3	1592.0	1590.5	1580.3	1554.4	1508.8	1450.0	1370.6	1284.3	1202.7	1130.9
32.5°	1490.9	1496.0	1509.4	1529.5	1531.0	1512.8	1468.8	1395.5	1306.2	1213.3	1127.5
35°	1265.7	1272.6	1298.4	1339.0	1392.2	1436.7	1445.8	1406.3	1326.1	1226.2	1122.5
37.5°	973.1	1010.5	1032.2	1075.0	1155.3	1237.1	1315.7	1344.7	1310.6	1220.9	1114.4
40°	826.6	835.7	874.5	922.7	990.3	1075.4	1187.5	1268.4	1271.0	1208.8	1101.6
42.5°	707.5	719.0	745.6	784.1	842.0	927.1	1042.8	1149.6	1199.0	1175.3	1084.9
45°	566.0	574.7	594.1	623.7	668.2	738.5	838.0	961.5	1059.5	1097.8	1040.1
47.5°	465.0	469.7	486.5	509.1	542.0	593.2	670.2	777.4	895.0	977.4	969.3
50°	410.3	415.6	428.5	445.6	473.3	516.6	578.2	667.4	788.6	889.3	909.4
52.5°	367.7	372.1	380.2	396.4	419.2	452.5	502.2	583.0	692.0	799.0	845.6
55°	310.7	313.8	320.2	329.3	347.6	371.5	414.4	470.3	558.4	666.3	734.7
57.5°	263.8	265.3	269.4	277.8	290.4	307.9	338.9	386.3	449.5	546.6	622.1
60°	234.0	235.5	240.8	246.5	256.4	272.4	296.7	329.7	390.5	470.7	547.0
62.5°	210.3	211.2	213.5	219.2	227.8	240.2	259.3	286.3	334.6	405.0	477.1
65°	176.3	176.6	177.4	182.0	187.3	196.4	208.9	227.9	264.4	317.6	381.4
67.5°	143.6	144.1	146.8	148.4	153.9	158.7	166.1	180.6	206.3	242.1	291.7
70°	125.4	125.0	127.6	129.5	131.4	137.1	142.1	153.8	169.8	197.2	238.6
72.5°	108.3	107.4	108.5	109.2	111.7	115.6	120.5	127.7	140.0	158.9	190.5
75°	82.1	82.4	82.4	83.2	85.1	86.6	88.1	91.9	98.8	111.3	128.4
77.5°	57.6	57.0	58.6	58.8	59.9	61.6	62.9	64.4	67.2	72.4	81.2
80°	41.8	41.8	42.2	43.3	42.9	43.7	45.6	47.1	50.5	53.6	56.6
82.5°	32.1	31.8	32.1	32.4	32.3	33.0	33.7	34.0	35.3	36.8	39.0
85°	17.5	17.5	17.9	17.9	18.2	18.2	18.6	18.6	18.6	19.0	19.4
87.5°	9.3	9.0	8.6	8.6	8.9	9.3	8.9	8.4	8.3	8.2	8.3
90°	13.1	13.1	12.5	12.5	12.5	11.4	10.8	10.3	9.7	9.1	8.0
92.5°	36.4	37.3	38.1	39.5	46.8	55.2	73.4	101.1	148.9	183.9	186.9
95°	134.1	143.2	147.7	164.9	205.4	253.3	323.4	410.1	494.6	505.4	412.4
97.5°	324.0	331.3	347.8	379.8	415.0	481.7	550.0	610.8	625.8	539.7	368.3
100°	444.9	454.1	475.2	516.2	555.6	614.9	673.7	701.6	657.7	515.1	328.6
102.5°	580.0	586.9	609.8	639.0	681.1	721.2	749.4	732.2	638.5	471.7	298.4
105°	755.8	762.7	774.1	792.9	811.1	817.4	792.3	714.2	577.3	413.6	269.2
107.5°	849.1	853.7	857.5	857.6	848.3	818.6	754.1	649.8	514.8	373.5	256.9
110°	880.2	880.2	876.2	865.3	839.7	791.2	710.8	602.4	479.2	354.8	253.3



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	876.5	872.4	862.5	843.9	806.4	749.2	667.9	565.0	452.7	343.9	253.3
115°	842.0	834.5	818.6	791.2	746.7	684.5	606.4	517.9	423.8	332.0	255.0
117.5°	781.4	776.8	761.0	732.7	688.2	631.1	563.8	487.6	406.6	326.2	258.7
120°	742.1	737.6	722.2	694.8	652.6	602.4	539.6	471.2	397.0	323.4	262.4
122.5°	707.4	703.3	687.9	662.8	625.2	578.2	522.3	458.9	388.8	321.2	265.6
125°	663.4	657.7	645.2	621.8	589.8	548.8	499.1	440.9	377.6	318.3	271.0
127.5°	625.8	623.2	611.4	590.7	561.8	523.3	477.0	422.7	367.4	316.9	277.0
130°	605.2	601.8	590.4	571.6	543.0	506.0	461.5	411.3	360.5	316.0	280.7
132.5°	584.7	580.8	570.3	551.5	523.0	487.3	446.9	399.9	355.0	316.0	284.8
135°	551.0	547.6	537.3	518.5	493.4	460.9	424.4	385.0	348.5	316.0	290.3
137.5°	515.1	511.3	501.9	484.7	462.3	434.7	404.3	372.5	342.7	316.7	295.5
140°	490.0	487.1	478.6	463.8	442.7	418.7	392.5	365.6	340.0	317.2	297.8
142.5°	466.7	464.3	456.2	443.7	425.8	405.0	382.4	359.7	337.7	317.6	299.1
145°	434.7	432.4	426.1	416.4	402.7	387.3	369.6	352.0	334.3	317.2	300.6
147.5°	407.5	406.5	402.8	395.1	384.2	372.6	359.0	344.7	330.7	315.7	301.2
150°	392.5	391.9	389.6	382.8	374.2	363.9	353.1	340.5	328.0	314.3	301.2
152.5°	380.6	380.0	377.7	372.3	365.1	357.1	347.2	336.0	324.8	312.5	300.7
155°	364.5	363.9	362.2	358.2	352.5	346.2	338.3	329.1	319.4	309.2	299.5
157.5°	350.1	350.2	348.6	345.3	340.9	336.0	329.8	322.3	314.4	305.7	298.0
160°	340.5	341.1	340.0	337.1	333.1	329.1	323.4	317.7	310.3	303.5	296.6
162.5°	331.9	332.0	331.8	329.4	326.3	322.7	318.0	312.7	306.7	300.7	295.3
165°	319.4	319.4	319.4	318.3	316.0	313.2	309.7	305.7	301.2	296.6	293.2
167.5°	308.0	308.1	308.6	307.6	306.4	304.4	301.8	299.1	295.8	292.6	290.0
170°	301.2	301.8	301.8	301.2	300.0	298.9	297.2	295.5	292.6	290.3	288.6
172.5°	294.8	295.4	296.3	295.3	295.0	294.3	293.1	291.4	289.4	287.6	286.8
175°	286.9	287.5	288.6	288.1	288.1	288.1	286.9	286.9	285.2	284.6	284.6
177.5°	282.9	282.9	284.3	283.8	284.3	284.3	284.3	283.8	283.4	282.9	282.9
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	950.9	948.8	944.8	941.2	936.6	932.7	929.9	926.6	922.3	917.2	912.9
5°	993.0	984.6	973.6	964.1	952.0	942.5	932.6	923.1	913.6	901.4	890.8
7.5°	1039.6	1022.4	1005.6	984.5	965.3	948.2	931.8	915.2	898.9	881.7	865.0
10°	1068.2	1047.3	1024.1	997.5	973.2	950.1	928.8	907.9	885.9	866.5	845.6
12.5°	1094.9	1068.0	1041.5	1007.9	978.7	950.4	923.3	897.3	873.7	848.6	826.1
15°	1119.1	1092.5	1062.9	1021.9	981.2	947.0	915.1	881.3	852.1	823.9	798.9
17.5°	1128.4	1100.6	1066.1	1026.7	982.3	939.3	898.2	861.1	826.7	793.9	765.7
20°	1124.8	1097.8	1062.5	1024.9	977.4	932.6	888.1	847.1	808.7	774.2	744.2
22.5°	1116.0	1088.1	1054.0	1014.3	969.2	921.6	874.2	830.4	790.2	754.4	721.7
25°	1102.8	1064.8	1029.8	991.1	948.2	901.1	852.1	803.8	760.9	724.4	688.7
27.5°	1089.0	1041.6	997.2	958.6	913.3	871.3	824.0	774.6	729.4	692.3	655.7
30°	1076.6	1023.4	974.4	930.7	887.8	847.9	803.0	754.8	708.5	670.1	632.9
32.5°	1061.1	1004.5	950.7	900.3	858.9	819.3	778.7	732.6	687.5	647.9	610.1
35°	1041.6	969.4	910.9	857.4	811.4	773.0	736.6	699.3	654.1	613.1	576.3
37.5°	1016.1	934.2	866.5	808.1	759.7	721.1	692.4	658.3	617.1	577.8	543.6
40°	1000.6	908.7	834.6	776.8	725.9	685.3	658.3	629.4	591.8	555.0	520.8
42.5°	979.9	885.3	802.4	742.2	691.0	651.9	624.6	599.4	567.8	533.1	496.5
45°	939.4	839.9	752.9	688.3	636.7	598.3	572.8	550.4	526.5	494.6	462.7
47.5°	886.7	792.6	701.5	631.0	580.4	544.8	520.1	502.4	485.3	458.2	427.2
50°	844.5	753.7	664.8	596.4	542.5	508.6	485.5	471.4	455.8	431.2	405.3
52.5°	794.6	713.6	626.5	556.6	505.7	474.0	451.7	437.7	424.8	404.7	380.1
55°	716.1	645.0	565.2	501.8	455.1	423.2	401.9	388.6	381.0	363.9	344.5
57.5°	625.4	574.5	504.2	443.0	401.7	370.1	354.6	343.3	334.7	322.6	308.9
60°	562.2	526.5	463.4	405.3	367.3	337.3	323.3	313.8	305.8	295.5	284.9
62.5°	498.1	472.1	417.3	367.3	332.4	307.2	294.1	285.5	276.3	269.4	259.1
65°	412.2	389.0	351.0	311.9	279.6	259.5	250.0	242.4	236.7	229.1	221.8
67.5°	320.6	311.2	285.0	258.0	234.8	216.9	208.7	203.4	196.5	192.0	187.0
70°	264.4	259.8	241.2	223.4	201.7	189.6	182.0	179.7	171.3	166.8	163.3
72.5°	214.6	212.4	201.7	189.3	174.1	163.4	156.4	153.8	148.5	144.9	142.7
75°	147.0	147.8	145.9	137.9	132.2	125.4	119.3	117.8	114.0	110.9	109.0
77.5°	93.0	96.9	97.0	96.6	94.4	90.2	87.7	86.5	82.8	81.7	81.2
80°	63.8	68.0	71.8	71.4	70.7	69.5	67.6	66.5	64.6	63.4	62.7
82.5°	42.5	46.4	49.6	51.7	51.5	50.4	49.1	48.5	48.2	47.3	47.2
85°	20.1	20.9	22.0	24.7	26.6	27.0	26.6	26.2	25.1	25.5	25.8
87.5°	8.5	8.2	8.4	8.2	7.7	9.0	9.6	9.8	9.3	9.0	8.6
90°	7.4	6.3	5.7	4.6	3.4	2.3	1.1	0.6	1.1	2.3	3.4
92.5°	130.2	77.9	46.8	30.1	20.3	13.2	8.4	7.0	8.4	13.2	20.3
95°	255.0	129.5	68.5	42.8	30.2	24.0	19.4	18.8	19.4	24.0	30.2
97.5°	203.5	111.6	71.2	52.7	41.4	35.1	31.9	31.3	31.9	35.1	41.4
100°	184.8	110.7	77.6	60.5	49.6	43.4	41.1	39.9	41.1	43.4	49.6
102.5°	177.1	114.8	85.3	68.7	58.8	52.0	50.2	49.5	50.2	52.0	58.8
105°	174.0	123.2	98.1	82.1	73.0	67.3	64.5	64.5	64.5	67.3	73.0
107.5°	179.2	135.8	111.5	97.1	87.6	82.9	80.2	79.1	80.2	82.9	87.6
110°	184.2	144.9	121.5	106.7	98.1	93.0	90.7	89.6	90.7	93.0	98.1





TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	190.6	153.6	131.1	116.7	108.2	103.0	101.2	100.1	101.2	103.0	108.2
115°	200.2	167.1	146.0	131.8	123.2	118.1	116.4	115.2	116.4	118.1	123.2
117.5°	211.2	181.1	161.1	147.3	137.6	132.5	130.6	128.9	130.6	132.5	137.6
120°	218.5	191.1	171.1	156.9	147.2	142.0	139.8	138.0	139.8	142.0	147.2
122.5°	226.7	200.7	180.7	166.5	155.8	150.7	148.9	147.6	148.9	150.7	155.8
125°	237.9	213.3	194.5	179.7	168.8	163.7	160.9	159.7	160.9	163.7	168.8
127.5°	248.1	225.5	207.4	192.6	181.1	174.6	170.9	169.2	170.9	174.6	181.1
130°	255.0	233.3	215.6	200.8	188.8	181.4	176.8	175.1	176.8	181.4	188.8
132.5°	260.9	240.6	222.9	208.1	195.7	187.3	181.9	179.7	181.9	187.3	195.7
135°	269.2	250.4	232.7	217.3	205.4	196.2	189.4	187.1	189.4	196.2	205.4
137.5°	275.4	257.4	241.3	225.4	213.7	204.6	198.2	196.5	198.2	204.6	213.7
140°	279.5	262.4	245.9	230.5	219.6	210.5	203.6	201.9	203.6	210.5	219.6
142.5°	281.8	265.6	250.0	235.5	225.1	216.0	209.6	208.3	209.6	216.0	225.1
145°	285.2	271.0	256.1	243.0	232.7	224.7	219.0	217.9	219.0	224.7	232.7
147.5°	287.3	274.4	261.4	249.8	240.9	233.5	228.6	227.9	228.6	233.5	240.9
150°	288.6	276.7	264.1	254.4	246.4	239.0	235.0	233.9	235.0	239.0	246.4
152.5°	289.5	278.9	267.3	258.5	251.0	244.5	240.9	240.3	240.9	244.5	251.0
155°	290.3	281.2	271.5	263.5	257.8	252.1	248.7	248.7	248.7	252.1	257.8
157.5°	290.9	283.2	274.8	268.8	263.8	258.9	256.1	256.2	256.1	258.9	263.8
160°	290.9	284.1	276.7	271.5	267.0	263.0	260.7	261.3	260.7	263.0	267.0
162.5°	290.5	285.0	278.5	274.3	270.6	267.1	264.8	265.4	264.8	267.1	270.6
165°	289.8	285.2	280.7	277.2	274.9	272.1	270.4	271.5	270.4	272.1	274.9
167.5°	288.4	285.2	281.4	279.3	277.7	276.1	275.1	275.6	275.1	276.1	277.7
170°	287.5	285.2	282.4	280.7	279.5	278.4	277.8	278.4	277.8	278.4	279.5
172.5°	286.6	284.8	282.4	281.6	280.9	279.7	279.2	280.2	279.2	279.7	280.9
175°	285.2	284.1	282.4	282.4	282.4	281.8	281.2	282.4	281.2	281.8	282.4
177.5°	283.8	283.4	282.5	282.5	282.9	282.5	282.5	283.4	282.5	282.5	282.9
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	909.9	905.6	902.6	896.5	892.2	890.4	887.1	886.2	889.5	887.1	886.8
5°	882.8	871.8	863.1	854.3	844.8	838.8	829.6	828.1	825.8	822.4	821.7
7.5°	850.4	836.0	824.8	810.3	797.8	787.7	776.3	770.9	767.9	763.5	757.6
10°	828.5	811.4	796.2	781.8	766.2	753.7	742.3	733.5	727.8	722.5	720.2
12.5°	806.9	789.5	770.1	752.6	735.2	721.1	708.5	702.8	696.5	690.3	685.0
15°	773.4	750.2	729.0	708.8	694.0	678.8	666.7	658.3	648.8	646.2	635.9
17.5°	737.9	715.1	690.2	669.0	651.9	635.1	621.8	612.3	605.1	595.3	590.6
20°	715.7	688.7	664.4	645.0	626.0	606.3	592.6	584.6	577.8	569.8	566.0
22.5°	692.0	665.6	640.7	618.0	598.7	579.2	569.5	561.2	553.5	546.1	541.1
25°	657.2	630.6	604.4	580.8	560.7	546.6	535.2	525.7	521.6	514.3	509.0
27.5°	622.8	594.5	567.3	543.8	528.0	514.1	504.8	497.3	489.7	483.4	478.8
30°	600.6	571.7	542.1	523.5	506.7	493.5	483.2	476.0	470.3	464.6	461.2
32.5°	578.4	548.6	522.3	502.2	486.4	474.9	464.4	457.4	451.4	445.1	441.1
35°	542.8	512.4	491.2	471.4	455.8	445.2	438.0	428.1	423.2	418.6	414.4
37.5°	509.8	481.5	458.5	441.2	427.7	417.1	407.8	402.4	396.4	392.3	388.8
40°	485.5	459.6	438.8	420.5	410.6	398.9	390.1	383.3	378.7	373.4	369.6
42.5°	463.6	439.6	419.3	402.9	390.6	380.6	372.2	365.4	359.6	355.8	352.6
45°	432.7	408.7	389.0	373.8	362.4	352.9	344.2	340.7	333.1	328.6	327.1
47.5°	400.7	379.3	360.2	346.2	334.5	325.5	317.3	310.4	306.2	301.7	299.3
50°	379.1	358.6	340.7	327.1	315.7	305.8	298.2	293.6	287.9	283.8	280.7
52.5°	357.5	338.5	320.7	307.6	297.7	287.9	279.4	274.8	269.4	266.7	264.6
55°	326.7	306.6	291.4	278.4	268.2	259.1	251.1	246.5	243.1	240.5	239.7
57.5°	291.7	275.8	261.7	250.0	239.4	230.8	223.8	219.5	216.5	216.1	213.8
60°	268.9	254.5	241.6	229.1	219.9	212.0	205.9	201.0	197.9	197.5	196.8
62.5°	246.2	232.3	220.3	209.3	201.1	193.4	187.7	182.1	180.3	178.4	176.7
65°	212.3	199.8	189.9	181.2	172.5	166.0	160.3	156.9	152.7	150.4	146.3
67.5°	179.1	169.4	159.9	152.6	145.7	139.6	134.9	129.8	127.0	125.1	122.1
70°	157.3	149.7	140.2	132.2	126.9	121.9	118.1	112.4	110.5	109.0	107.5
72.5°	136.6	129.9	121.9	115.5	110.2	105.5	101.1	98.5	96.6	95.0	94.1
75°	107.5	101.0	94.2	89.6	85.9	82.1	79.8	77.9	77.1	76.7	75.2
77.5°	78.9	75.5	70.0	66.4	63.9	62.4	60.3	59.3	59.3	57.6	57.1
80°	60.4	58.5	53.9	52.4	50.5	49.0	47.9	46.0	44.1	43.3	42.2
82.5°	44.9	43.0	41.2	38.7	37.2	36.2	35.1	34.4	34.6	33.6	33.0
85°	23.9	22.0	21.3	20.9	20.1	20.9	20.5	20.1	19.8	19.4	19.8
87.5°	8.5	8.7	8.5	9.4	8.6	9.1	9.2	9.0	9.2	9.3	9.2
90°	4.6	5.7	6.3	7.4	8.0	9.1	9.7	10.3	10.8	11.4	12.5
92.5°	30.1	46.8	77.9	130.2	186.9	183.9	148.9	101.1	73.4	55.2	46.8
95°	42.8	68.5	129.5	255.0	412.4	505.4	494.6	410.1	323.4	253.3	205.4
97.5°	52.7	71.2	111.6	203.5	368.3	539.7	625.8	610.8	550.0	481.7	415.0
100°	60.5	77.6	110.7	184.8	328.6	515.1	657.7	701.6	673.7	614.9	555.6
102.5°	68.7	85.3	114.8	177.1	298.4	471.7	638.5	732.2	749.4	721.2	681.1
105°	82.1	98.1	123.2	174.0	269.2	413.6	577.3	714.2	792.3	817.4	811.1
107.5°	97.1	111.5	135.8	179.2	256.9	373.5	514.8	649.8	754.1	818.6	848.3
110°	106.7	121.5	144.9	184.2	253.3	354.8	479.2	602.4	710.8	791.2	839.7



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	116.7	131.1	153.6	190.6	253.3	343.9	452.7	565.0	667.9	749.2	806.4
115°	131.8	146.0	167.1	200.2	255.0	332.0	423.8	517.9	606.4	684.5	746.7
117.5°	147.3	161.1	181.1	211.2	258.7	326.2	406.6	487.6	563.8	631.1	688.2
120°	156.9	171.1	191.1	218.5	262.4	323.4	397.0	471.2	539.6	602.4	652.6
122.5°	166.5	180.7	200.7	226.7	265.6	321.2	388.8	458.9	522.3	578.2	625.2
125°	179.7	194.5	213.3	237.9	271.0	318.3	377.6	440.9	499.1	548.8	589.8
127.5°	192.6	207.4	225.5	248.1	277.0	316.9	367.4	422.7	477.0	523.3	561.8
130°	200.8	215.6	233.3	255.0	280.7	316.0	360.5	411.3	461.5	506.0	543.0
132.5°	208.1	222.9	240.6	260.9	284.8	316.0	355.0	399.9	446.9	487.3	523.0
135°	217.3	232.7	250.4	269.2	290.3	316.0	348.5	385.0	424.4	460.9	493.4
137.5°	225.4	241.3	257.4	275.4	295.5	316.7	342.7	372.5	404.3	434.7	462.3
140°	230.5	245.9	262.4	279.5	297.8	317.2	340.0	365.6	392.5	418.7	442.7
142.5°	235.5	250.0	265.6	281.8	299.1	317.6	337.7	359.7	382.4	405.0	425.8
145°	243.0	256.1	271.0	285.2	300.6	317.2	334.3	352.0	369.6	387.3	402.7
147.5°	249.8	261.4	274.4	287.3	301.2	315.7	330.7	344.7	359.0	372.6	384.2
150°	254.4	264.1	276.7	288.6	301.2	314.3	328.0	340.5	353.1	363.9	374.2
152.5°	258.5	267.3	278.9	289.5	300.7	312.5	324.8	336.0	347.2	357.1	365.1
155°	263.5	271.5	281.2	290.3	299.5	309.2	319.4	329.1	338.3	346.2	352.5
157.5°	268.8	274.8	283.2	290.9	298.0	305.7	314.4	322.3	329.8	336.0	340.9
160°	271.5	276.7	284.1	290.9	296.6	303.5	310.3	317.7	323.4	329.1	333.1
162.5°	274.3	278.5	285.0	290.5	295.3	300.7	306.7	312.7	318.0	322.7	326.3
165°	277.2	280.7	285.2	289.8	293.2	296.6	301.2	305.7	309.7	313.2	316.0
167.5°	279.3	281.4	285.2	288.4	290.0	292.6	295.8	299.1	301.8	304.4	306.4
170°	280.7	282.4	285.2	287.5	288.6	290.3	292.6	295.5	297.2	298.9	300.0
172.5°	281.6	282.4	284.8	286.6	286.8	287.6	289.4	291.4	293.1	294.3	295.0
175°	282.4	282.4	284.1	285.2	284.6	284.6	285.2	286.9	286.9	288.1	288.1
177.5°	282.5	282.5	283.4	283.8	282.9	282.9	283.4	283.8	284.3	284.3	284.3
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	886.5	883.1	882.2	883.4	882.2	883.1	886.5	886.8	887.1	889.5	886.2
5°	817.9	814.1	816.0	815.2	816.0	814.1	817.9	821.7	822.4	825.8	828.1
7.5°	757.5	752.8	747.8	749.4	747.8	752.8	757.5	757.6	763.5	767.9	770.9
10°	715.3	711.5	709.2	711.1	709.2	711.5	715.3	720.2	722.5	727.8	733.5
12.5°	679.7	677.5	675.5	674.7	675.5	677.5	679.7	685.0	690.3	696.5	702.8
15°	631.3	626.8	624.9	620.0	624.9	626.8	631.3	635.9	646.2	648.8	658.3
17.5°	586.7	585.2	580.3	578.2	580.3	585.2	586.7	590.6	595.3	605.1	612.3
20°	560.3	558.8	553.9	556.9	553.9	558.8	560.3	566.0	569.8	577.8	584.6
22.5°	538.4	535.1	533.5	532.6	533.5	535.1	538.4	541.1	546.1	553.5	561.2
25°	507.5	502.6	500.7	498.4	500.7	502.6	507.5	509.0	514.3	521.6	525.7
27.5°	476.7	474.0	471.5	470.9	471.5	474.0	476.7	478.8	483.4	489.7	497.3
30°	456.6	453.9	452.0	452.0	452.0	453.9	456.6	461.2	464.6	470.3	476.0
32.5°	438.7	436.6	434.7	434.4	434.7	436.6	438.7	441.1	445.1	451.4	457.4
35°	412.5	409.5	408.7	406.5	408.7	409.5	412.5	414.4	418.6	423.2	428.1
37.5°	385.4	382.9	382.8	382.6	382.8	382.9	385.4	388.8	392.3	396.4	402.4
40°	368.1	366.2	365.8	363.2	365.8	366.2	368.1	369.6	373.4	378.7	383.3
42.5°	349.6	348.6	347.3	346.1	347.3	348.6	349.6	352.6	355.8	359.6	365.4
45°	324.4	321.8	321.8	319.9	321.8	321.8	324.4	327.1	328.6	333.1	340.7
47.5°	298.4	296.4	296.6	294.6	296.6	296.4	298.4	299.3	301.7	306.2	310.4
50°	281.1	280.0	279.6	278.8	279.6	280.0	281.1	280.7	283.8	287.9	293.6
52.5°	263.8	263.3	264.7	263.0	264.7	263.3	263.8	264.6	266.7	269.4	274.8
55°	240.5	239.3	241.6	239.3	241.6	239.3	240.5	239.7	240.5	243.1	246.5
57.5°	213.6	212.6	214.6	213.5	214.6	212.6	213.6	213.8	216.1	216.5	219.5
60°	196.0	193.7	194.9	195.3	194.9	193.7	196.0	196.8	197.5	197.9	201.0
62.5°	175.0	173.7	174.5	172.8	174.5	173.7	175.0	176.7	178.4	180.3	182.1
65°	145.5	144.4	142.8	142.1	142.8	144.4	145.5	146.3	150.4	152.7	156.9
67.5°	122.2	119.5	119.4	120.0	119.4	119.5	122.2	122.1	125.1	127.0	129.8
70°	105.2	105.2	104.8	104.8	104.8	105.2	105.2	107.5	109.0	110.5	112.4
72.5°	93.4	93.1	92.4	92.1	92.4	93.1	93.4	94.1	95.0	96.6	98.5
75°	75.2	75.6	74.8	74.5	74.8	75.6	75.2	75.2	76.7	77.1	77.9
77.5°	55.5	53.9	54.8	53.9	54.8	53.9	55.5	57.1	57.6	59.3	59.3
80°	42.2	41.8	42.9	41.8	42.9	41.8	42.2	42.2	43.3	44.1	46.0
82.5°	33.4	33.0	33.5	32.7	33.5	33.0	33.4	33.0	33.6	34.6	34.4
85°	20.1	19.8	19.4	19.8	19.4	19.8	20.1	19.8	19.4	19.8	20.1
87.5°	9.5	9.2	9.3	9.3	9.3	9.2	9.5	9.2	9.3	9.2	9.0
90°	12.5	12.5	13.1	13.1	13.1	12.5	12.5	12.5	11.4	10.8	10.3
92.5°	39.5	38.1	37.3	36.4	37.3	38.1	39.5	46.8	55.2	73.4	101.1
95°	164.9	147.7	143.2	134.1	143.2	147.7	164.9	205.4	253.3	323.4	410.1
97.5°	379.8	347.8	331.3	324.0	331.3	347.8	379.8	415.0	481.7	550.0	610.8
100°	516.2	475.2	454.1	444.9	454.1	475.2	516.2	555.6	614.9	673.7	701.6
102.5°	639.0	609.8	586.9	580.0	586.9	609.8	639.0	681.1	721.2	749.4	732.2
105°	792.9	774.1	762.7	755.8	762.7	774.1	792.9	811.1	817.4	792.3	714.2
107.5°	857.6	857.5	853.7	849.1	853.7	857.5	857.6	848.3	818.6	754.1	649.8
110°	865.3	876.2	880.2	880.2	880.2	876.2	865.3	839.7	791.2	710.8	602.4



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	843.9	862.5	872.4	876.5	872.4	862.5	843.9	806.4	749.2	667.9	565.0
115°	791.2	818.6	834.5	842.0	834.5	818.6	791.2	746.7	684.5	606.4	517.9
117.5°	732.7	761.0	776.8	781.4	776.8	761.0	732.7	688.2	631.1	563.8	487.6
120°	694.8	722.2	737.6	742.1	737.6	722.2	694.8	652.6	602.4	539.6	471.2
122.5°	662.8	687.9	703.3	707.4	703.3	687.9	662.8	625.2	578.2	522.3	458.9
125°	621.8	645.2	657.7	663.4	657.7	645.2	621.8	589.8	548.8	499.1	440.9
127.5°	590.7	611.4	623.2	625.8	623.2	611.4	590.7	561.8	523.3	477.0	422.7
130°	571.6	590.4	601.8	605.2	601.8	590.4	571.6	543.0	506.0	461.5	411.3
132.5°	551.5	570.3	580.8	584.7	580.8	570.3	551.5	523.0	487.3	446.9	399.9
135°	518.5	537.3	547.6	551.0	547.6	537.3	518.5	493.4	460.9	424.4	385.0
137.5°	484.7	501.9	511.3	515.1	511.3	501.9	484.7	462.3	434.7	404.3	372.5
140°	463.8	478.6	487.1	490.0	487.1	478.6	463.8	442.7	418.7	392.5	365.6
142.5°	443.7	456.2	464.3	466.7	464.3	456.2	443.7	425.8	405.0	382.4	359.7
145°	416.4	426.1	432.4	434.7	432.4	426.1	416.4	402.7	387.3	369.6	352.0
147.5°	395.1	402.8	406.5	407.5	406.5	402.8	395.1	384.2	372.6	359.0	344.7
150°	382.8	389.6	391.9	392.5	391.9	389.6	382.8	374.2	363.9	353.1	340.5
152.5°	372.3	377.7	380.0	380.6	380.0	377.7	372.3	365.1	357.1	347.2	336.0
155°	358.2	362.2	363.9	364.5	363.9	362.2	358.2	352.5	346.2	338.3	329.1
157.5°	345.3	348.6	350.2	350.1	350.2	348.6	345.3	340.9	336.0	329.8	322.3
160°	337.1	340.0	341.1	340.5	341.1	340.0	337.1	333.1	329.1	323.4	317.7
162.5°	329.4	331.8	332.0	331.9	332.0	331.8	329.4	326.3	322.7	318.0	312.7
165°	318.3	319.4	319.4	319.4	319.4	319.4	318.3	316.0	313.2	309.7	305.7
167.5°	307.6	308.6	308.1	308.0	308.1	308.6	307.6	306.4	304.4	301.8	299.1
170°	301.2	301.8	301.8	301.2	301.8	301.8	301.2	300.0	298.9	297.2	295.5
172.5°	295.3	296.3	295.4	294.8	295.4	296.3	295.3	295.0	294.3	293.1	291.4
175°	288.1	288.6	287.5	286.9	287.5	288.6	288.1	288.1	288.1	286.9	286.9
177.5°	283.8	284.3	282.9	282.9	282.9	284.3	283.8	284.3	284.3	284.3	283.8
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	887.1	890.4	892.2	896.5	902.6	905.6	909.9	912.9	917.2	922.3	926.6
5°	829.6	838.8	844.8	854.3	863.1	871.8	882.8	890.8	901.4	913.6	923.1
7.5°	776.3	787.7	797.8	810.3	824.8	836.0	850.4	865.0	881.7	898.9	915.2
10°	742.3	753.7	766.2	781.8	796.2	811.4	828.5	845.6	866.5	885.9	907.9
12.5°	708.5	721.1	735.2	752.6	770.1	789.5	806.9	826.1	848.6	873.7	897.3
15°	666.7	678.8	694.0	708.8	729.0	750.2	773.4	798.9	823.9	852.1	881.3
17.5°	621.8	635.1	651.9	669.0	690.2	715.1	737.9	765.7	793.9	826.7	861.1
20°	592.6	606.3	626.0	645.0	664.4	688.7	715.7	744.2	774.2	808.7	847.1
22.5°	569.5	579.2	598.7	618.0	640.7	665.6	692.0	721.7	754.4	790.2	830.4
25°	535.2	546.6	560.7	580.8	604.4	630.6	657.2	688.7	724.4	760.9	803.8
27.5°	504.8	514.1	528.0	543.8	567.3	594.5	622.8	655.7	692.3	729.4	774.6
30°	483.2	493.5	506.7	523.5	542.1	571.7	600.6	632.9	670.1	708.5	754.8
32.5°	464.4	474.9	486.4	502.2	522.3	548.6	578.4	610.1	647.9	687.5	732.6
35°	438.0	445.2	455.8	471.4	491.2	512.4	542.8	576.3	613.1	654.1	699.3
37.5°	407.8	417.1	427.7	441.2	458.5	481.5	509.8	543.6	577.8	617.1	658.3
40°	390.1	398.9	410.6	420.5	438.8	459.6	485.5	520.8	555.0	591.8	629.4
42.5°	372.2	380.6	390.6	402.9	419.3	439.6	463.6	496.5	533.1	567.8	599.4
45°	344.2	352.9	362.4	373.8	389.0	408.7	432.7	462.7	494.6	526.5	550.4
47.5°	317.3	325.5	334.5	346.2	360.2	379.3	400.7	427.2	458.2	485.3	502.4
50°	298.2	305.8	315.7	327.1	340.7	358.6	379.1	405.3	431.2	455.8	471.4
52.5°	279.4	287.9	297.7	307.6	320.7	338.5	357.5	380.1	404.7	424.8	437.7
55°	251.1	259.1	268.2	278.4	291.4	306.6	326.7	344.5	363.9	381.0	388.6
57.5°	223.8	230.8	239.4	250.0	261.7	275.8	291.7	308.9	322.6	334.7	343.3
60°	205.9	212.0	219.9	229.1	241.6	254.5	268.9	284.9	295.5	305.8	313.8
62.5°	187.7	193.4	201.1	209.3	220.3	232.3	246.2	259.1	269.4	276.3	285.5
65°	160.3	166.0	172.5	181.2	189.9	199.8	212.3	221.8	229.1	236.7	242.4
67.5°	134.9	139.6	145.7	152.6	159.9	169.4	179.1	187.0	192.0	196.5	203.4
70°	118.1	121.9	126.9	132.2	140.2	149.7	157.3	163.3	166.8	171.3	179.7
72.5°	101.1	105.5	110.2	115.5	121.9	129.9	136.6	142.7	144.9	148.5	153.8
75°	79.8	82.1	85.9	89.6	94.2	101.0	107.5	109.0	110.9	114.0	117.8
77.5°	60.3	62.4	63.9	66.4	70.0	75.5	78.9	81.2	81.7	82.8	86.5
80°	47.9	49.0	50.5	52.4	53.9	58.5	60.4	62.7	63.4	64.6	66.5
82.5°	35.1	36.2	37.2	38.7	41.2	43.0	44.9	47.2	47.3	48.2	48.5
85°	20.5	20.9	20.1	20.9	21.3	22.0	23.9	25.8	25.5	25.1	26.2
87.5°	9.2	9.1	8.6	9.4	8.5	8.7	8.5	8.6	9.0	9.3	9.8
90°	9.7	9.1	8.0	7.4	6.3	5.7	4.6	3.4	2.3	1.1	0.6
92.5°	148.9	183.9	186.9	130.2	77.9	46.8	30.1	20.3	13.2	8.4	7.0
95°	494.6	505.4	412.4	255.0	129.5	68.5	42.8	30.2	24.0	19.4	18.8
97.5°	625.8	539.7	368.3	203.5	111.6	71.2	52.7	41.4	35.1	31.9	31.3
100°	657.7	515.1	328.6	184.8	110.7	77.6	60.5	49.6	43.4	41.1	39.9
102.5°	638.5	471.7	298.4	177.1	114.8	85.3	68.7	58.8	52.0	50.2	49.5
105°	577.3	413.6	269.2	174.0	123.2	98.1	82.1	73.0	67.3	64.5	64.5
107.5°	514.8	373.5	256.9	179.2	135.8	111.5	97.1	87.6	82.9	80.2	79.1
110°	479.2	354.8	253.3	184.2	144.9	121.5	106.7	98.1	93.0	90.7	89.6



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	452.7	343.9	253.3	190.6	153.6	131.1	116.7	108.2	103.0	101.2	100.1
115°	423.8	332.0	255.0	200.2	167.1	146.0	131.8	123.2	118.1	116.4	115.2
117.5°	406.6	326.2	258.7	211.2	181.1	161.1	147.3	137.6	132.5	130.6	128.9
120°	397.0	323.4	262.4	218.5	191.1	171.1	156.9	147.2	142.0	139.8	138.0
122.5°	388.8	321.2	265.6	226.7	200.7	180.7	166.5	155.8	150.7	148.9	147.6
125°	377.6	318.3	271.0	237.9	213.3	194.5	179.7	168.8	163.7	160.9	159.7
127.5°	367.4	316.9	277.0	248.1	225.5	207.4	192.6	181.1	174.6	170.9	169.2
130°	360.5	316.0	280.7	255.0	233.3	215.6	200.8	188.8	181.4	176.8	175.1
132.5°	355.0	316.0	284.8	260.9	240.6	222.9	208.1	195.7	187.3	181.9	179.7
135°	348.5	316.0	290.3	269.2	250.4	232.7	217.3	205.4	196.2	189.4	187.1
137.5°	342.7	316.7	295.5	275.4	257.4	241.3	225.4	213.7	204.6	198.2	196.5
140°	340.0	317.2	297.8	279.5	262.4	245.9	230.5	219.6	210.5	203.6	201.9
142.5°	337.7	317.6	299.1	281.8	265.6	250.0	235.5	225.1	216.0	209.6	208.3
145°	334.3	317.2	300.6	285.2	271.0	256.1	243.0	232.7	224.7	219.0	217.9
147.5°	330.7	315.7	301.2	287.3	274.4	261.4	249.8	240.9	233.5	228.6	227.9
150°	328.0	314.3	301.2	288.6	276.7	264.1	254.4	246.4	239.0	235.0	233.9
152.5°	324.8	312.5	300.7	289.5	278.9	267.3	258.5	251.0	244.5	240.9	240.3
155°	319.4	309.2	299.5	290.3	281.2	271.5	263.5	257.8	252.1	248.7	248.7
157.5°	314.4	305.7	298.0	290.9	283.2	274.8	268.8	263.8	258.9	256.1	256.2
160°	310.3	303.5	296.6	290.9	284.1	276.7	271.5	267.0	263.0	260.7	261.3
162.5°	306.7	300.7	295.3	290.5	285.0	278.5	274.3	270.6	267.1	264.8	265.4
165°	301.2	296.6	293.2	289.8	285.2	280.7	277.2	274.9	272.1	270.4	271.5
167.5°	295.8	292.6	290.0	288.4	285.2	281.4	279.3	277.7	276.1	275.1	275.6
170°	292.6	290.3	288.6	287.5	285.2	282.4	280.7	279.5	278.4	277.8	278.4
172.5°	289.4	287.6	286.8	286.6	284.8	282.4	281.6	280.9	279.7	279.2	280.2
175°	285.2	284.6	284.6	285.2	284.1	282.4	282.4	282.4	281.8	281.2	282.4
177.5°	283.4	282.9	282.9	283.8	283.4	282.5	282.5	282.9	282.5	282.5	283.4
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	929.9	932.7	936.6	941.2	944.8	948.8	950.9	950.9	952.7	956.7	961.8
5°	932.6	942.5	952.0	964.1	973.6	984.6	993.0	1001.0	1008.2	1017.3	1026.8
7.5°	931.8	948.2	965.3	984.5	1005.6	1022.4	1039.6	1053.2	1066.5	1084.0	1097.8
10°	928.8	950.1	973.2	997.5	1024.1	1047.3	1068.2	1087.2	1105.4	1124.4	1141.5
12.5°	923.3	950.4	978.7	1007.9	1041.5	1068.0	1094.9	1115.2	1136.4	1157.2	1178.3
15°	915.1	947.0	981.2	1021.9	1062.9	1092.5	1119.1	1145.3	1165.1	1188.6	1208.8
17.5°	898.2	939.3	982.3	1026.7	1066.1	1100.6	1128.4	1153.4	1174.4	1200.3	1227.7
20°	888.1	932.6	977.4	1024.9	1062.5	1097.8	1124.8	1150.6	1176.8	1210.7	1244.1
22.5°	874.2	921.6	969.2	1014.3	1054.0	1088.1	1116.0	1147.6	1182.0	1220.4	1260.8
25°	852.1	901.1	948.2	991.1	1029.8	1064.8	1102.8	1145.3	1187.1	1237.6	1295.7
27.5°	824.0	871.3	913.3	958.6	997.2	1041.6	1089.0	1135.1	1195.4	1264.9	1337.5
30°	803.0	847.9	887.8	930.7	974.4	1023.4	1076.6	1130.9	1202.7	1284.3	1370.6
32.5°	778.7	819.3	858.9	900.3	950.7	1004.5	1061.1	1127.5	1213.3	1306.2	1395.5
35°	736.6	773.0	811.4	857.4	910.9	969.4	1041.6	1122.5	1226.2	1326.1	1406.3
37.5°	692.4	721.1	759.7	808.1	866.5	934.2	1016.1	1114.4	1220.9	1310.6	1344.7
40°	658.3	685.3	725.9	776.8	834.6	908.7	1000.6	1101.6	1208.8	1271.0	1268.4
42.5°	624.6	651.9	691.0	742.2	802.4	885.3	979.9	1084.9	1175.3	1199.0	1149.6
45°	572.8	598.3	636.7	688.3	752.9	839.9	939.4	1040.1	1097.8	1059.5	961.5
47.5°	520.1	544.8	580.4	631.0	701.5	792.6	886.7	969.3	977.4	895.0	777.4
50°	485.5	508.6	542.5	596.4	664.8	753.7	844.5	909.4	889.3	788.6	667.4
52.5°	451.7	474.0	505.7	556.6	626.5	713.6	794.6	845.6	799.0	692.0	583.0
55°	401.9	423.2	455.1	501.8	565.2	645.0	716.1	734.7	666.3	558.4	470.3
57.5°	354.6	370.1	401.7	443.0	504.2	574.5	625.4	622.1	546.6	449.5	386.3
60°	323.3	337.3	367.3	405.3	463.4	526.5	562.2	547.0	470.7	390.5	329.7
62.5°	294.1	307.2	332.4	367.3	417.3	472.1	498.1	477.1	405.0	334.6	286.3
65°	250.0	259.5	279.6	311.9	351.0	389.0	412.2	381.4	317.6	264.4	227.9
67.5°	208.7	216.9	234.8	258.0	285.0	311.2	320.6	291.7	242.1	206.3	180.6
70°	182.0	189.6	201.7	223.4	241.2	259.8	264.4	238.6	197.2	169.8	153.8
72.5°	156.4	163.4	174.1	189.3	201.7	212.4	214.6	190.5	158.9	140.0	127.7
75°	119.3	125.4	132.2	137.9	145.9	147.8	147.0	128.4	111.3	98.8	91.9
77.5°	87.7	90.2	94.4	96.6	97.0	96.9	93.0	81.2	72.4	67.2	64.4
80°	67.6	69.5	70.7	71.4	71.8	68.0	63.8	56.6	53.6	50.5	47.1
82.5°	49.1	50.4	51.5	51.7	49.6	46.4	42.5	39.0	36.8	35.3	34.0
85°	26.6	27.0	26.6	24.7	22.0	20.9	20.1	19.4	19.0	18.6	18.6
87.5°	9.6	9.0	7.7	8.2	8.4	8.2	8.5	8.3	8.2	8.3	8.4
90°	1.1	2.3	3.4	4.6	5.7	6.3	7.4	8.0	9.1	9.7	10.3
92.5°	8.4	13.2	20.3	30.1	46.8	77.9	130.2	186.9	183.9	148.9	101.1
95°	19.4	24.0	30.2	42.8	68.5	129.5	255.0	412.4	505.4	494.6	410.1
97.5°	31.9	35.1	41.4	52.7	71.2	111.6	203.5	368.3	539.7	625.8	610.8
100°	41.1	43.4	49.6	60.5	77.6	110.7	184.8	328.6	515.1	657.7	701.6
102.5°	50.2	52.0	58.8	68.7	85.3	114.8	177.1	298.4	471.7	638.5	732.2
105°	64.5	67.3	73.0	82.1	98.1	123.2	174.0	269.2	413.6	577.3	714.2
107.5°	80.2	82.9	87.6	97.1	111.5	135.8	179.2	256.9	373.5	514.8	649.8
110°	90.7	93.0	98.1	106.7	121.5	144.9	184.2	253.3	354.8	479.2	602.4





TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	101.2	103.0	108.2	116.7	131.1	153.6	190.6	253.3	343.9	452.7	565.0
115°	116.4	118.1	123.2	131.8	146.0	167.1	200.2	255.0	332.0	423.8	517.9
117.5°	130.6	132.5	137.6	147.3	161.1	181.1	211.2	258.7	326.2	406.6	487.6
120°	139.8	142.0	147.2	156.9	171.1	191.1	218.5	262.4	323.4	397.0	471.2
122.5°	148.9	150.7	155.8	166.5	180.7	200.7	226.7	265.6	321.2	388.8	458.9
125°	160.9	163.7	168.8	179.7	194.5	213.3	237.9	271.0	318.3	377.6	440.9
127.5°	170.9	174.6	181.1	192.6	207.4	225.5	248.1	277.0	316.9	367.4	422.7
130°	176.8	181.4	188.8	200.8	215.6	233.3	255.0	280.7	316.0	360.5	411.3
132.5°	181.9	187.3	195.7	208.1	222.9	240.6	260.9	284.8	316.0	355.0	399.9
135°	189.4	196.2	205.4	217.3	232.7	250.4	269.2	290.3	316.0	348.5	385.0
137.5°	198.2	204.6	213.7	225.4	241.3	257.4	275.4	295.5	316.7	342.7	372.5
140°	203.6	210.5	219.6	230.5	245.9	262.4	279.5	297.8	317.2	340.0	365.6
142.5°	209.6	216.0	225.1	235.5	250.0	265.6	281.8	299.1	317.6	337.7	359.7
145°	219.0	224.7	232.7	243.0	256.1	271.0	285.2	300.6	317.2	334.3	352.0
147.5°	228.6	233.5	240.9	249.8	261.4	274.4	287.3	301.2	315.7	330.7	344.7
150°	235.0	239.0	246.4	254.4	264.1	276.7	288.6	301.2	314.3	328.0	340.5
152.5°	240.9	244.5	251.0	258.5	267.3	278.9	289.5	300.7	312.5	324.8	336.0
155°	248.7	252.1	257.8	263.5	271.5	281.2	290.3	299.5	309.2	319.4	329.1
157.5°	256.1	258.9	263.8	268.8	274.8	283.2	290.9	298.0	305.7	314.4	322.3
160°	260.7	263.0	267.0	271.5	276.7	284.1	290.9	296.6	303.5	310.3	317.7
162.5°	264.8	267.1	270.6	274.3	278.5	285.0	290.5	295.3	300.7	306.7	312.7
165°	270.4	272.1	274.9	277.2	280.7	285.2	289.8	293.2	296.6	301.2	305.7
167.5°	275.1	276.1	277.7	279.3	281.4	285.2	288.4	290.0	292.6	295.8	299.1
170°	277.8	278.4	279.5	280.7	282.4	285.2	287.5	288.6	290.3	292.6	295.5
172.5°	279.2	279.7	280.9	281.6	282.4	284.8	286.6	286.8	287.6	289.4	291.4
175°	281.2	281.8	282.4	282.4	282.4	284.1	285.2	284.6	284.6	285.2	286.9
177.5°	282.5	282.5	282.9	282.5	282.5	283.4	283.8	282.9	282.9	283.4	283.8
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	965.8	965.8	971.0	970.6	974.0	972.8	973.4
5°	1038.2	1044.6	1050.3	1054.1	1059.8	1061.4	1060.6
7.5°	1113.3	1127.6	1134.6	1144.2	1145.9	1150.9	1150.4
10°	1159.7	1173.8	1184.4	1192.8	1197.0	1202.3	1202.7
12.5°	1196.2	1208.1	1217.6	1225.3	1230.4	1232.1	1233.1
15°	1224.7	1238.0	1249.0	1260.0	1266.5	1271.4	1274.1
17.5°	1253.4	1273.9	1293.4	1308.4	1317.3	1324.9	1324.8
20°	1275.6	1299.2	1323.5	1340.6	1358.0	1365.6	1366.8
22.5°	1299.3	1335.3	1366.6	1393.1	1416.1	1424.0	1426.9
25°	1348.5	1395.6	1443.9	1481.1	1507.7	1523.3	1525.6
27.5°	1408.0	1471.8	1522.5	1556.9	1579.0	1590.5	1593.0
30°	1450.0	1508.8	1554.4	1580.3	1590.5	1592.0	1586.3
32.5°	1468.8	1512.8	1531.0	1529.5	1509.4	1496.0	1490.9
35°	1445.8	1436.7	1392.2	1339.0	1298.4	1272.6	1265.7
37.5°	1315.7	1237.1	1155.3	1075.0	1032.2	1010.5	973.1
40°	1187.5	1075.4	990.3	922.7	874.5	835.7	826.6
42.5°	1042.8	927.1	842.0	784.1	745.6	719.0	707.5
45°	838.0	738.5	668.2	623.7	594.1	574.7	566.0
47.5°	670.2	593.2	542.0	509.1	486.5	469.7	465.0
50°	578.2	516.6	473.3	445.6	428.5	415.6	410.3
52.5°	502.2	452.5	419.2	396.4	380.2	372.1	367.7
55°	414.4	371.5	347.6	329.3	320.2	313.8	310.7
57.5°	338.9	307.9	290.4	277.8	269.4	265.3	263.8
60°	296.7	272.4	256.4	246.5	240.8	235.5	234.0
62.5°	259.3	240.2	227.8	219.2	213.5	211.2	210.3
65°	208.9	196.4	187.3	182.0	177.4	176.6	176.3
67.5°	166.1	158.7	153.9	148.4	146.8	144.1	143.6
70°	142.1	137.1	131.4	129.5	127.6	125.0	125.4
72.5°	120.5	115.6	111.7	109.2	108.5	107.4	108.3
75°	88.1	86.6	85.1	83.2	82.4	82.4	82.1
77.5°	62.9	61.6	59.9	58.8	58.6	57.0	57.6
80°	45.6	43.7	42.9	43.3	42.2	41.8	41.8
82.5°	33.7	33.0	32.3	32.4	32.1	31.8	32.1
85°	18.6	18.2	18.2	17.9	17.9	17.5	17.5
87.5°	8.9	9.3	8.9	8.6	8.6	9.0	9.3
90°	10.8	11.4	12.5	12.5	12.5	13.1	13.1
92.5°	73.4	55.2	46.8	39.5	38.1	37.3	36.4
95°	323.4	253.3	205.4	164.9	147.7	143.2	134.1
97.5°	550.0	481.7	415.0	379.8	347.8	331.3	324.0
100°	673.7	614.9	555.6	516.2	475.2	454.1	444.9
102.5°	749.4	721.2	681.1	639.0	609.8	586.9	580.0
105°	792.3	817.4	811.1	792.9	774.1	762.7	755.8
107.5°	754.1	818.6	848.3	857.6	857.5	853.7	849.1
110°	710.8	791.2	839.7	865.3	876.2	880.2	880.2



TEST NUMBER: P333528

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	667.9	749.2	806.4	843.9	862.5	872.4	876.5
115°	606.4	684.5	746.7	791.2	818.6	834.5	842.0
117.5°	563.8	631.1	688.2	732.7	761.0	776.8	781.4
120°	539.6	602.4	652.6	694.8	722.2	737.6	742.1
122.5°	522.3	578.2	625.2	662.8	687.9	703.3	707.4
125°	499.1	548.8	589.8	621.8	645.2	657.7	663.4
127.5°	477.0	523.3	561.8	590.7	611.4	623.2	625.8
130°	461.5	506.0	543.0	571.6	590.4	601.8	605.2
132.5°	446.9	487.3	523.0	551.5	570.3	580.8	584.7
135°	424.4	460.9	493.4	518.5	537.3	547.6	551.0
137.5°	404.3	434.7	462.3	484.7	501.9	511.3	515.1
140°	392.5	418.7	442.7	463.8	478.6	487.1	490.0
142.5°	382.4	405.0	425.8	443.7	456.2	464.3	466.7
145°	369.6	387.3	402.7	416.4	426.1	432.4	434.7
147.5°	359.0	372.6	384.2	395.1	402.8	406.5	407.5
150°	353.1	363.9	374.2	382.8	389.6	391.9	392.5
152.5°	347.2	357.1	365.1	372.3	377.7	380.0	380.6
155°	338.3	346.2	352.5	358.2	362.2	363.9	364.5
157.5°	329.8	336.0	340.9	345.3	348.6	350.2	350.1
160°	323.4	329.1	333.1	337.1	340.0	341.1	340.5
162.5°	318.0	322.7	326.3	329.4	331.8	332.0	331.9
165°	309.7	313.2	316.0	318.3	319.4	319.4	319.4
167.5°	301.8	304.4	306.4	307.6	308.6	308.1	308.0
170°	297.2	298.9	300.0	301.2	301.8	301.8	301.2
172.5°	293.1	294.3	295.0	295.3	296.3	295.4	294.8
175°	286.9	288.1	288.1	288.1	288.6	287.5	286.9
177.5°	284.3	284.3	284.3	283.8	284.3	282.9	282.9
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9

(END OF REPORT)