

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333529

Luminaire Tested: **S125RDIP-S610D590U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333529
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D590U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4741.6 lumens
Efficiency: N/A
Efficacy: 144.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333529

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333529

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50																				
1	98	94	90	87	90	87	83	81	73	71	69	61	60	58	50	49	48	43																				
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36																				
3	82	72	65	59	75	67	61	56	57	52	49	48	44	42	39	37	35	31																				
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	33	30	27																				
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	23																				
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	20																				
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	27	23	21	18																				
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16																				
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15																				
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6497	6497	6497
5°	6512	6438	6477
10°	6462	6378	6378
15°	6386	6248	6197
20°	6287	6068	5994
25°	6173	5890	5761
30°	6029	5683	5502
35°	5882	5469	5211
40°	5746	5246	4926
45°	5580	4996	4615
50°	5413	4725	4290
55°	5219	4466	3944
60°	5025	4151	3573
65°	4795	3785	3147
70°	4534	3329	2712
75°	4172	2805	2256
80°	3675	2205	1893
85°	3097	1801	1690



TEST NUMBER: P333529

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	2.0
10°-20°	264.3	5.6
20°-30°	383.3	8.1
30°-40°	436.9	9.2
40°-50°	425.9	9.0
50°-60°	358.5	7.6
60°-70°	251.3	5.3
70°-80°	129.2	2.7
80°-90°	34.2	0.7
90°-100°	28.0	0.6
100°-110°	172.4	3.6
110°-120°	312.6	6.6
120°-130°	401.2	8.5
130°-140°	431.5	9.1
140°-150°	405.1	8.5
150°-160°	327.7	6.9
160°-170°	211.9	4.5
170°-180°	73.1	1.5
0°-30°	742.3	15.7
0°-40°	1179.2	24.9
0°-60°	1963.5	41.4
0°-90°	2378.1	50.2
90°-120°	513.0	10.8
90°-150°	1750.8	36.9
90°-180°	2364.0	49.9
0°-180°	4741.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1004	1001	993	1000	999	95
15°	955	950	934	933	927	269
25°	866	854	827	817	808	398
35°	746	727	694	672	661	467
45°	611	588	547	518	505	471
55°	464	438	397	364	350	414
65°	314	287	248	218	206	311
75°	167	144	112	96	90	177
85°	42	29	24	24	23	47
90°	1	5	9	12	14	3
95°	32	30	9	12	12	41
105°	168	170	170	170	169	178
115°	315	318	318	316	313	312
125°	448	452	452	450	448	400
135°	559	562	561	560	556	430
145°	648	649	649	649	646	405
155°	713	710	711	712	708	328
165°	752	749	750	753	748	212
175°	770	766	767	771	766	73
180°	770	770	770	770	770	



TEST NUMBER: P333529

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1007.8	1007.4	1007.0	1006.6	1006.2	1005.3	1003.9	1002.6	1001.2	999.9	1001.2
5°	1004.4	1003.8	1003.1	1002.4	1001.7	1000.5	998.6	996.8	994.9	993.0	994.7
7.5°	994.6	993.9	993.3	992.6	992.0	990.6	988.3	986.1	983.9	981.6	982.8
10°	985.4	984.9	984.4	983.9	983.4	982.0	979.6	977.3	974.9	972.5	973.0
12.5°	975.1	974.5	973.8	973.2	972.5	970.6	967.5	964.3	961.1	957.9	958.3
15°	955.1	954.0	953.0	952.0	951.0	948.7	945.2	941.6	938.1	934.5	934.4
17.5°	932.4	930.9	929.3	927.8	926.2	923.2	918.7	914.3	909.8	905.4	904.5
20°	914.8	913.1	911.4	909.7	908.0	904.5	899.1	893.7	888.3	882.9	882.0
22.5°	895.3	893.6	892.0	890.3	888.6	884.9	879.2	873.6	867.9	862.2	860.6
25°	866.2	863.6	861.1	858.6	856.0	851.6	845.4	839.1	832.9	826.6	824.5
27.5°	832.7	829.7	826.6	823.5	820.4	815.6	808.9	802.2	795.5	788.8	785.7
30°	808.4	805.2	802.0	798.8	795.6	790.4	783.3	776.3	769.2	762.1	758.2
32.5°	784.7	781.0	777.2	773.5	769.7	764.2	757.0	749.8	742.5	735.3	731.0
35°	746.1	742.1	738.0	734.0	729.9	724.1	716.5	708.9	701.3	693.7	688.8
37.5°	708.3	703.3	698.4	693.5	688.6	682.2	674.3	666.5	658.7	650.8	645.0
40°	681.5	676.5	671.4	666.3	661.3	654.7	646.6	638.5	630.4	622.3	615.9
42.5°	653.6	648.4	643.2	638.0	632.8	626.0	617.6	609.2	600.9	592.5	586.3
45°	610.9	606.0	601.1	596.2	591.3	584.2	574.9	565.6	556.3	547.0	540.3
47.5°	566.7	561.5	556.3	551.2	546.0	538.7	529.4	520.0	510.7	501.3	494.4
50°	538.7	533.1	527.5	522.0	516.4	508.8	499.2	489.6	479.9	470.3	463.2
52.5°	508.3	502.6	496.9	491.2	485.5	478.1	469.0	459.9	450.8	441.7	434.1
55°	463.5	458.1	452.7	447.3	441.9	434.4	425.0	415.5	406.1	396.6	389.0
57.5°	418.2	412.4	406.6	400.9	395.1	387.6	378.5	369.4	360.3	351.2	343.7
60°	389.0	383.1	377.2	371.3	365.4	357.9	348.7	339.6	330.5	321.4	314.0
62.5°	358.0	352.4	346.7	341.1	335.5	328.0	318.8	309.5	300.3	291.0	284.1
65°	313.8	308.1	302.3	296.6	290.8	283.5	274.5	265.6	256.6	247.7	240.9
67.5°	269.9	264.1	258.4	252.7	246.9	239.8	231.2	222.6	214.0	205.4	199.3
70°	240.1	234.4	228.6	222.9	217.1	210.0	201.6	193.2	184.7	176.3	171.0
72.5°	210.9	205.3	199.7	194.1	188.5	181.7	173.8	165.9	158.0	150.1	145.3
75°	167.2	162.1	157.0	152.0	146.9	140.8	133.7	126.6	119.5	112.4	108.7
77.5°	123.7	119.6	115.6	111.5	107.5	102.6	96.9	91.3	85.6	79.9	77.3
80°	98.8	94.7	90.7	86.6	82.6	78.2	73.4	68.7	64.0	59.3	57.7
82.5°	74.5	70.8	67.2	63.5	59.9	56.4	53.2	49.9	46.7	43.5	42.8
85°	41.8	38.7	35.7	32.7	29.6	27.7	26.8	26.0	25.2	24.3	24.1
87.5°	14.1	13.4	12.6	11.9	11.1	10.8	10.8	10.9	10.9	10.9	11.1
90°	0.6	1.6	2.6	3.6	4.6	5.6	6.5	7.4	8.2	9.1	9.8
92.5°	8.8	8.1	7.4	6.7	5.9	6.0	6.8	7.6	8.3	9.1	9.8
95°	32.5	32.1	31.8	31.4	31.0	28.4	23.6	18.8	13.9	9.1	9.8
97.5°	67.9	68.6	69.3	69.9	70.6	66.2	56.7	47.1	37.6	28.1	24.5
100°	95.3	95.7	96.0	96.4	96.8	97.2	97.8	98.3	98.8	99.3	80.4
102.5°	123.1	123.6	124.1	124.6	125.0	125.4	125.7	126.1	126.4	126.7	123.1
105°	167.7	168.2	168.8	169.3	169.8	170.0	170.0	170.0	170.0	170.0	170.0
107.5°	214.1	214.1	214.1	214.1	214.1	214.2	214.4	214.7	215.0	215.2	215.2
110°	244.2	244.2	244.2	244.2	244.2	244.3	244.6	244.8	245.1	245.3	245.0



TEST NUMBER: P333529

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	272.5	272.8	273.1	273.4	273.7	273.9	274.1	274.2	274.4	274.5	274.1
115°	314.9	315.6	316.2	316.8	317.5	317.9	318.0	318.1	318.2	318.4	317.9
117.5°	358.9	358.8	358.8	358.8	358.8	359.0	359.5	360.0	360.4	360.9	360.3
120°	386.3	386.1	386.0	385.9	385.7	385.9	386.3	386.6	387.0	387.4	387.1
122.5°	410.4	410.9	411.4	411.9	412.4	412.7	412.9	413.1	413.2	413.4	413.2
125°	447.9	448.8	449.6	450.5	451.4	451.9	451.9	451.9	451.9	451.9	451.4
127.5°	483.6	484.2	484.9	485.5	486.1	486.4	486.3	486.3	486.2	486.1	485.8
130°	505.5	506.1	506.8	507.4	508.0	508.4	508.5	508.7	508.8	508.9	508.5
132.5°	527.4	528.1	528.9	529.6	530.3	530.6	530.3	530.0	529.7	529.5	529.4
135°	558.6	559.3	560.1	560.8	561.6	561.9	561.6	561.3	561.1	560.8	560.6
137.5°	587.2	587.9	588.5	589.2	589.8	590.1	589.8	589.6	589.4	589.1	589.2
140°	605.9	606.2	606.4	606.7	606.9	607.0	606.9	606.7	606.6	606.5	606.7
142.5°	622.8	623.0	623.1	623.3	623.4	623.6	623.8	623.9	624.1	624.3	624.3
145°	647.6	647.8	648.1	648.3	648.6	648.7	648.7	648.7	648.7	648.7	648.8
147.5°	669.2	669.2	669.1	669.1	669.0	669.1	669.2	669.4	669.5	669.7	669.9
150°	682.9	682.7	682.4	682.2	681.9	681.9	682.2	682.4	682.7	682.9	683.2
152.5°	696.2	695.6	695.1	694.5	693.9	693.8	694.0	694.3	694.5	694.8	695.1
155°	713.2	712.4	711.7	710.9	710.1	709.9	710.1	710.4	710.6	710.9	711.3
157.5°	726.3	725.8	725.4	724.9	724.5	724.3	724.3	724.3	724.3	724.4	724.8
160°	735.4	734.7	733.9	733.1	732.4	732.1	732.2	732.3	732.4	732.6	733.1
162.5°	742.7	742.0	741.2	740.4	739.7	739.4	739.5	739.6	739.7	739.9	740.6
165°	752.5	751.8	751.0	750.3	749.5	749.2	749.3	749.4	749.6	749.7	750.4
167.5°	759.8	759.1	758.3	757.5	756.7	756.4	756.5	756.6	756.7	756.9	757.8
170°	764.0	763.1	762.2	761.3	760.4	760.0	760.1	760.3	760.4	760.5	761.5
172.5°	766.7	765.8	764.9	764.0	763.1	762.8	763.0	763.3	763.5	763.7	764.6
175°	769.7	768.9	768.1	767.4	766.6	766.3	766.4	766.6	766.7	766.8	767.8
177.5°	771.0	770.4	769.8	769.2	768.6	768.3	768.4	768.5	768.6	768.7	769.5
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333529

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1002.6	1003.9	1005.3	1005.9	1005.8	1005.6	1005.5	1005.4
5°	996.4	998.1	999.8	1000.5	1000.1	999.8	999.5	999.1
7.5°	984.0	985.2	986.4	986.8	986.4	986.0	985.7	985.3
10°	973.5	974.0	974.6	974.6	974.0	973.5	973.0	972.5
12.5°	958.7	959.1	959.4	959.2	958.4	957.7	956.9	956.1
15°	934.2	934.0	933.9	933.0	931.5	930.0	928.5	926.9
17.5°	903.7	902.8	902.0	900.9	899.7	898.4	897.2	895.9
20°	881.2	880.3	879.5	878.3	876.8	875.3	873.8	872.2
22.5°	858.9	857.2	855.6	854.1	852.9	851.6	850.4	849.1
25°	822.3	820.1	817.9	815.8	814.0	812.1	810.3	808.4
27.5°	782.7	779.6	776.5	774.1	772.3	770.5	768.7	766.9
30°	754.3	750.4	746.5	743.8	742.3	740.8	739.3	737.8
32.5°	726.7	722.5	718.2	715.1	713.1	711.2	709.3	707.4
35°	683.9	679.0	674.1	670.5	668.1	665.7	663.4	661.0
37.5°	639.1	633.2	627.3	623.2	620.9	618.7	616.4	614.1
40°	609.4	603.0	596.6	592.4	590.4	588.3	586.3	584.3
42.5°	580.2	574.0	567.9	563.3	560.4	557.4	554.4	551.5
45°	533.5	526.8	520.0	515.4	512.9	510.3	507.8	505.3
47.5°	487.4	480.4	473.5	468.6	465.8	463.0	460.2	457.4
50°	456.1	449.0	441.9	437.1	434.6	432.1	429.5	427.0
52.5°	426.5	418.8	411.2	406.1	403.6	401.1	398.5	396.0
55°	381.4	373.8	366.2	361.1	358.4	355.7	353.0	350.3
57.5°	336.3	328.9	321.5	316.5	314.1	311.7	309.4	307.0
60°	306.5	299.1	291.7	286.7	284.2	281.6	279.1	276.6
62.5°	277.2	270.3	263.4	258.7	256.2	253.7	251.1	248.6
65°	234.2	227.4	220.7	216.0	213.5	211.0	208.4	205.9
67.5°	193.1	186.9	180.7	176.6	174.6	172.6	170.5	168.5
70°	165.8	160.6	155.3	151.7	149.7	147.7	145.6	143.6
72.5°	140.5	135.6	130.8	127.7	126.4	125.0	123.7	122.3
75°	105.0	101.3	97.6	95.1	94.0	92.8	91.6	90.4
77.5°	74.7	72.1	69.5	67.8	66.9	66.0	65.2	64.3
80°	56.2	54.7	53.2	52.3	51.9	51.6	51.2	50.9
82.5°	42.0	41.3	40.6	40.2	40.0	39.8	39.6	39.4
85°	24.0	23.8	23.6	23.5	23.3	23.1	23.0	22.8
87.5°	11.2	11.3	11.5	11.5	11.4	11.4	11.3	11.2
90°	10.4	11.0	11.7	12.2	12.6	12.9	13.3	13.7
92.5°	10.4	11.0	11.7	12.1	12.2	12.4	12.6	12.8
95°	10.4	11.0	11.7	12.0	12.0	12.0	12.0	12.0
97.5°	20.9	17.3	13.8	12.0	12.0	12.0	12.0	12.0
100°	61.5	42.6	23.7	14.0	13.5	13.0	12.5	12.0
102.5°	119.5	115.9	112.4	106.3	97.6	89.0	80.4	71.8
105°	170.0	170.0	170.0	170.0	169.8	169.7	169.6	169.4
107.5°	215.3	215.3	215.3	215.1	214.8	214.4	214.0	213.6
110°	244.6	244.2	243.8	243.7	243.8	243.9	244.1	244.2



TEST NUMBER: P333529

CATALOG NUMBER: S125RDIP-S610D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	273.6	273.1	272.6	272.3	272.1	271.9	271.8	271.6
115°	317.3	316.8	316.3	315.7	314.9	314.2	313.4	312.7
117.5°	359.6	358.9	358.3	357.8	357.5	357.1	356.8	356.5
120°	386.9	386.6	386.4	385.9	385.3	384.7	384.0	383.4
122.5°	412.9	412.7	412.4	411.9	411.2	410.4	409.7	409.0
125°	450.9	450.3	449.8	449.4	449.0	448.6	448.3	447.9
127.5°	485.5	485.3	485.0	484.4	483.4	482.5	481.6	480.6
130°	508.2	507.8	507.4	506.9	506.3	505.6	505.0	504.4
132.5°	529.3	529.2	529.2	528.8	528.2	527.5	526.9	526.3
135°	560.3	560.1	559.8	559.3	558.6	557.8	557.0	556.3
137.5°	589.2	589.3	589.3	589.0	588.4	587.7	587.1	586.4
140°	607.0	607.2	607.5	607.2	606.5	605.7	605.0	604.2
142.5°	624.4	624.4	624.5	624.1	623.4	622.6	621.8	621.1
145°	649.0	649.1	649.2	648.9	648.1	647.4	646.6	645.8
147.5°	670.0	670.2	670.3	669.9	669.0	668.1	667.2	666.3
150°	683.4	683.7	683.9	683.6	682.6	681.5	680.5	679.5
152.5°	695.3	695.6	695.8	695.5	694.6	693.7	692.7	691.8
155°	711.7	712.0	712.4	712.1	711.1	710.1	709.1	708.0
157.5°	725.2	725.6	726.0	725.7	724.7	723.6	722.6	721.6
160°	733.6	734.1	734.6	734.3	733.3	732.3	731.3	730.3
162.5°	741.3	742.0	742.7	742.5	741.4	740.3	739.2	738.0
165°	751.2	752.0	752.7	752.6	751.6	750.6	749.6	748.5
167.5°	758.7	759.6	760.5	760.4	759.3	758.1	757.0	755.8
170°	762.6	763.6	764.6	764.5	763.4	762.2	761.1	760.0
172.5°	765.5	766.5	767.4	767.3	766.1	765.0	763.8	762.7
175°	768.8	769.8	770.9	770.8	769.7	768.5	767.4	766.2
177.5°	770.2	770.9	771.6	771.5	770.7	769.9	769.1	768.3
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7

(END OF REPORT)