

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333535

Luminaire Tested: **S125RDIP-S610D810U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333535
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D810U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5618.4 lumens
Efficiency: N/A
Efficacy: 146.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333535

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333535

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42																				
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36																				
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	39	37	35	30																				
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26																				
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	28	26	22																				
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	20																				
6	62	50	42	37	57	46	39	34	39	33	29	32	28	25	25	22	20	17																				
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																				
8	53	41	34	28	49	38	31	27	32	27	23	26	23	20	21	18	16	14																				
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12																				
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6497	6497	6497
5°	6512	6438	6477
10°	6462	6378	6378
15°	6386	6248	6197
20°	6287	6068	5994
25°	6173	5890	5761
30°	6029	5683	5502
35°	5882	5469	5211
40°	5746	5246	4926
45°	5580	4996	4615
50°	5413	4725	4290
55°	5219	4466	3944
60°	5025	4151	3573
65°	4795	3785	3147
70°	4534	3329	2712
75°	4172	2805	2256
80°	3675	2205	1893
85°	3097	1801	1690



TEST NUMBER: P333535

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	1.7
10°-20°	264.3	4.7
20°-30°	383.3	6.8
30°-40°	436.9	7.8
40°-50°	425.9	7.6
50°-60°	358.5	6.4
60°-70°	251.3	4.5
70°-80°	129.2	2.3
80°-90°	34.8	0.6
90°-100°	38.3	0.7
100°-110°	236.3	4.2
110°-120°	428.5	7.6
120°-130°	550.0	9.8
130°-140°	591.5	10.5
140°-150°	555.2	9.9
150°-160°	449.1	8.0
160°-170°	290.5	5.2
170°-180°	100.2	1.8
0°-30°	742.3	13.2
0°-40°	1179.2	21.0
0°-60°	1963.5	34.9
0°-90°	2378.7	42.3
90°-120°	703.1	12.5
90°-150°	2399.9	42.7
90°-180°	3240.0	57.7
0°-180°	5618.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1004	1001	993	1000	999	95
15°	955	950	934	933	927	269
25°	866	854	827	817	808	398
35°	746	727	694	672	661	467
45°	611	588	547	518	505	471
55°	464	438	397	364	350	414
65°	314	287	248	218	206	311
75°	167	144	112	96	90	177
85°	42	29	24	24	23	47
90°	1	7	12	16	19	4
95°	45	41	12	16	16	57
105°	230	233	233	233	232	244
115°	432	435	436	433	429	428
125°	614	619	619	616	614	548
135°	766	770	769	767	762	590
145°	888	889	889	890	885	555
155°	978	973	974	976	970	450
165°	1032	1027	1028	1032	1026	291
175°	1055	1051	1051	1057	1050	100
180°	1055	1055	1055	1055	1055	



TEST NUMBER: P333535

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1007.8	1007.4	1007.0	1006.6	1006.2	1005.3	1003.9	1002.6	1001.2	999.9	1001.2
5°	1004.4	1003.8	1003.1	1002.4	1001.7	1000.5	998.6	996.8	994.9	993.0	994.7
7.5°	994.6	993.9	993.3	992.6	992.0	990.6	988.3	986.1	983.9	981.6	982.8
10°	985.4	984.9	984.4	983.9	983.4	982.0	979.6	977.3	974.9	972.5	973.0
12.5°	975.1	974.5	973.8	973.2	972.5	970.6	967.5	964.3	961.1	957.9	958.3
15°	955.1	954.0	953.0	952.0	951.0	948.7	945.2	941.6	938.1	934.5	934.4
17.5°	932.4	930.9	929.3	927.8	926.2	923.2	918.7	914.3	909.8	905.4	904.5
20°	914.8	913.1	911.4	909.7	908.0	904.5	899.1	893.7	888.3	882.9	882.0
22.5°	895.3	893.6	892.0	890.3	888.6	884.9	879.2	873.6	867.9	862.2	860.6
25°	866.2	863.6	861.1	858.6	856.0	851.6	845.4	839.1	832.9	826.6	824.5
27.5°	832.7	829.7	826.6	823.5	820.4	815.6	808.9	802.2	795.5	788.8	785.7
30°	808.4	805.2	802.0	798.8	795.6	790.4	783.3	776.3	769.2	762.1	758.2
32.5°	784.7	781.0	777.2	773.5	769.7	764.2	757.0	749.8	742.5	735.3	731.0
35°	746.1	742.1	738.0	734.0	729.9	724.1	716.5	708.9	701.3	693.7	688.8
37.5°	708.3	703.3	698.4	693.5	688.6	682.2	674.3	666.5	658.7	650.8	645.0
40°	681.5	676.5	671.4	666.3	661.3	654.7	646.6	638.5	630.4	622.3	615.9
42.5°	653.6	648.4	643.2	638.0	632.8	626.0	617.6	609.2	600.9	592.5	586.3
45°	610.9	606.0	601.1	596.2	591.3	584.2	574.9	565.6	556.3	547.0	540.3
47.5°	566.7	561.5	556.3	551.2	546.0	538.7	529.4	520.0	510.7	501.3	494.4
50°	538.7	533.1	527.5	522.0	516.4	508.8	499.2	489.6	479.9	470.3	463.2
52.5°	508.3	502.6	496.9	491.2	485.5	478.1	469.0	459.9	450.8	441.7	434.1
55°	463.5	458.1	452.7	447.3	441.9	434.4	425.0	415.5	406.1	396.6	389.0
57.5°	418.2	412.4	406.6	400.9	395.1	387.6	378.5	369.4	360.3	351.2	343.7
60°	389.0	383.1	377.2	371.3	365.4	357.9	348.7	339.6	330.5	321.4	314.0
62.5°	358.0	352.4	346.7	341.1	335.5	328.0	318.8	309.5	300.3	291.0	284.1
65°	313.8	308.1	302.3	296.6	290.8	283.5	274.5	265.6	256.6	247.7	240.9
67.5°	269.9	264.1	258.4	252.7	246.9	239.8	231.2	222.6	214.0	205.4	199.3
70°	240.1	234.4	228.6	222.9	217.1	210.0	201.6	193.2	184.7	176.3	171.0
72.5°	210.9	205.3	199.7	194.1	188.5	181.7	173.8	165.9	158.0	150.1	145.3
75°	167.2	162.1	157.0	152.0	146.9	140.8	133.7	126.6	119.5	112.4	108.7
77.5°	123.7	119.6	115.6	111.5	107.5	102.6	96.9	91.3	85.6	79.9	77.3
80°	98.8	94.7	90.7	86.6	82.6	78.2	73.4	68.7	64.0	59.3	57.7
82.5°	74.5	70.8	67.2	63.5	59.9	56.4	53.2	49.9	46.7	43.5	42.8
85°	41.8	38.7	35.7	32.7	29.6	27.7	26.8	26.0	25.2	24.3	24.1
87.5°	14.1	13.5	12.8	12.1	11.5	11.2	11.3	11.4	11.5	11.6	11.8
90°	0.8	2.2	3.6	5.0	6.3	7.6	8.9	10.1	11.3	12.5	13.4
92.5°	12.0	11.1	10.1	9.1	8.2	8.2	9.3	10.4	11.4	12.5	13.4
95°	44.6	44.1	43.5	43.0	42.5	38.9	32.3	25.7	19.1	12.5	13.4
97.5°	93.1	94.0	94.9	95.9	96.8	90.8	77.7	64.6	51.5	38.5	33.6
100°	130.6	131.1	131.6	132.2	132.7	133.3	134.0	134.7	135.4	136.1	110.2
102.5°	168.8	169.4	170.1	170.7	171.4	171.9	172.4	172.8	173.2	173.6	168.7
105°	229.9	230.6	231.3	232.0	232.7	233.0	233.0	233.0	233.0	233.0	233.0
107.5°	293.4	293.4	293.4	293.4	293.4	293.6	293.9	294.3	294.6	295.0	295.0
110°	334.7	334.7	334.7	334.7	334.7	334.9	335.2	335.6	335.9	336.3	335.8



TEST NUMBER: P333535

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	373.5	373.9	374.3	374.8	375.2	375.5	375.7	375.9	376.1	376.3	375.7
115°	431.7	432.6	433.4	434.3	435.2	435.7	435.9	436.0	436.2	436.4	435.7
117.5°	491.9	491.9	491.8	491.8	491.8	492.1	492.7	493.4	494.1	494.7	493.8
120°	529.4	529.3	529.1	528.9	528.7	528.9	529.4	530.0	530.5	531.0	530.7
122.5°	562.6	563.3	563.9	564.6	565.2	565.7	565.9	566.2	566.4	566.7	566.3
125°	613.9	615.1	616.3	617.6	618.8	619.4	619.4	619.4	619.4	619.4	618.7
127.5°	662.9	663.7	664.6	665.5	666.3	666.7	666.6	666.5	666.4	666.3	665.9
130°	692.9	693.8	694.6	695.5	696.4	696.9	697.1	697.2	697.4	697.6	697.1
132.5°	722.9	723.9	724.9	725.9	727.0	727.3	726.9	726.5	726.1	725.7	725.6
135°	765.6	766.7	767.7	768.8	769.8	770.1	769.8	769.4	769.1	768.8	768.4
137.5°	804.9	805.8	806.7	807.6	808.5	808.8	808.5	808.2	807.9	807.5	807.6
140°	830.5	830.9	831.2	831.6	831.9	832.0	831.8	831.7	831.5	831.3	831.7
142.5°	853.7	853.9	854.1	854.3	854.5	854.7	855.0	855.2	855.5	855.7	855.8
145°	887.6	888.0	888.3	888.7	889.0	889.2	889.2	889.2	889.2	889.2	889.4
147.5°	917.3	917.3	917.2	917.1	917.1	917.1	917.3	917.5	917.8	918.0	918.2
150°	936.1	935.8	935.4	935.1	934.7	934.7	935.1	935.4	935.8	936.1	936.5
152.5°	954.3	953.5	952.7	952.0	951.2	951.0	951.3	951.7	952.0	952.4	952.7
155°	977.6	976.5	975.5	974.4	973.4	973.0	973.4	973.7	974.1	974.4	974.9
157.5°	995.5	994.9	994.3	993.7	993.0	992.7	992.8	992.8	992.8	992.9	993.4
160°	1008.1	1007.0	1006.0	1004.9	1003.9	1003.5	1003.6	1003.8	1004.0	1004.1	1004.8
162.5°	1018.1	1017.0	1016.0	1014.9	1013.9	1013.5	1013.6	1013.8	1014.0	1014.2	1015.1
165°	1031.5	1030.5	1029.4	1028.4	1027.3	1026.9	1027.1	1027.3	1027.4	1027.6	1028.7
167.5°	1041.5	1040.5	1039.4	1038.3	1037.2	1036.8	1036.9	1037.1	1037.3	1037.5	1038.7
170°	1047.2	1045.9	1044.7	1043.5	1042.3	1041.8	1041.9	1042.1	1042.3	1042.5	1043.9
172.5°	1050.9	1049.7	1048.5	1047.3	1046.0	1045.6	1045.9	1046.2	1046.5	1046.8	1048.1
175°	1055.0	1053.9	1052.9	1051.9	1050.8	1050.4	1050.5	1050.7	1050.9	1051.1	1052.5
177.5°	1056.9	1056.0	1055.2	1054.4	1053.5	1053.2	1053.3	1053.4	1053.6	1053.7	1054.7
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333535

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1002.6	1003.9	1005.3	1005.9	1005.8	1005.6	1005.5	1005.4
5°	996.4	998.1	999.8	1000.5	1000.1	999.8	999.5	999.1
7.5°	984.0	985.2	986.4	986.8	986.4	986.0	985.7	985.3
10°	973.5	974.0	974.6	974.6	974.0	973.5	973.0	972.5
12.5°	958.7	959.1	959.4	959.2	958.4	957.7	956.9	956.1
15°	934.2	934.0	933.9	933.0	931.5	930.0	928.5	926.9
17.5°	903.7	902.8	902.0	900.9	899.7	898.4	897.2	895.9
20°	881.2	880.3	879.5	878.3	876.8	875.3	873.8	872.2
22.5°	858.9	857.2	855.6	854.1	852.9	851.6	850.4	849.1
25°	822.3	820.1	817.9	815.8	814.0	812.1	810.3	808.4
27.5°	782.7	779.6	776.5	774.1	772.3	770.5	768.7	766.9
30°	754.3	750.4	746.5	743.8	742.3	740.8	739.3	737.8
32.5°	726.7	722.5	718.2	715.1	713.1	711.2	709.3	707.4
35°	683.9	679.0	674.1	670.5	668.1	665.7	663.4	661.0
37.5°	639.1	633.2	627.3	623.2	620.9	618.7	616.4	614.1
40°	609.4	603.0	596.6	592.4	590.4	588.3	586.3	584.3
42.5°	580.2	574.0	567.9	563.3	560.4	557.4	554.4	551.5
45°	533.5	526.8	520.0	515.4	512.9	510.3	507.8	505.3
47.5°	487.4	480.4	473.5	468.6	465.8	463.0	460.2	457.4
50°	456.1	449.0	441.9	437.1	434.6	432.1	429.5	427.0
52.5°	426.5	418.8	411.2	406.1	403.6	401.1	398.5	396.0
55°	381.4	373.8	366.2	361.1	358.4	355.7	353.0	350.3
57.5°	336.3	328.9	321.5	316.5	314.1	311.7	309.4	307.0
60°	306.5	299.1	291.7	286.7	284.2	281.6	279.1	276.6
62.5°	277.2	270.3	263.4	258.7	256.2	253.7	251.1	248.6
65°	234.2	227.4	220.7	216.0	213.5	211.0	208.4	205.9
67.5°	193.1	186.9	180.7	176.6	174.6	172.6	170.5	168.5
70°	165.8	160.6	155.3	151.7	149.7	147.7	145.6	143.6
72.5°	140.5	135.6	130.8	127.7	126.4	125.0	123.7	122.3
75°	105.0	101.3	97.6	95.1	94.0	92.8	91.6	90.4
77.5°	74.7	72.1	69.5	67.8	66.9	66.0	65.2	64.3
80°	56.2	54.7	53.2	52.3	51.9	51.6	51.2	50.9
82.5°	42.0	41.3	40.6	40.2	40.0	39.8	39.6	39.4
85°	24.0	23.8	23.6	23.5	23.3	23.1	23.0	22.8
87.5°	12.0	12.1	12.3	12.4	12.4	12.3	12.3	12.3
90°	14.3	15.1	16.0	16.7	17.2	17.7	18.2	18.8
92.5°	14.3	15.1	16.0	16.5	16.8	17.0	17.3	17.5
95°	14.3	15.1	16.0	16.4	16.4	16.4	16.4	16.4
97.5°	28.7	23.8	18.9	16.4	16.4	16.4	16.4	16.4
100°	84.3	58.4	32.5	19.2	18.5	17.8	17.1	16.4
102.5°	163.8	158.9	154.0	145.7	133.8	122.0	110.2	98.4
105°	233.0	233.0	233.0	233.0	232.8	232.6	232.4	232.3
107.5°	295.1	295.1	295.1	294.9	294.4	293.8	293.3	292.8
110°	335.2	334.7	334.2	334.0	334.2	334.4	334.5	334.7



TEST NUMBER: P333535

CATALOG NUMBER: S125RDIP-S610D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	375.0	374.3	373.7	373.2	373.0	372.7	372.5	372.3
115°	435.0	434.3	433.6	432.7	431.7	430.6	429.6	428.6
117.5°	492.9	492.0	491.1	490.4	490.0	489.5	489.1	488.6
120°	530.3	530.0	529.6	529.0	528.1	527.3	526.4	525.5
122.5°	566.0	565.6	565.3	564.6	563.6	562.6	561.6	560.6
125°	618.0	617.3	616.6	616.0	615.5	614.9	614.4	613.9
127.5°	665.5	665.2	664.8	663.9	662.7	661.4	660.1	658.8
130°	696.5	696.0	695.5	694.8	693.9	693.1	692.2	691.3
132.5°	725.5	725.4	725.3	724.8	724.0	723.1	722.2	721.4
135°	768.1	767.7	767.4	766.7	765.6	764.6	763.5	762.5
137.5°	807.7	807.7	807.8	807.4	806.5	805.6	804.7	803.8
140°	832.0	832.4	832.7	832.4	831.3	830.3	829.2	828.2
142.5°	855.9	855.9	856.0	855.5	854.5	853.4	852.4	851.3
145°	889.5	889.7	889.9	889.4	888.4	887.4	886.3	885.3
147.5°	918.4	918.6	918.8	918.3	917.0	915.8	914.5	913.3
150°	936.8	937.2	937.5	937.0	935.6	934.2	932.8	931.4
152.5°	953.1	953.4	953.8	953.3	952.1	950.8	949.6	948.3
155°	975.5	976.0	976.5	976.1	974.7	973.3	971.9	970.5
157.5°	994.0	994.6	995.1	994.7	993.3	991.9	990.5	989.1
160°	1005.5	1006.2	1006.9	1006.6	1005.2	1003.8	1002.4	1001.0
162.5°	1016.1	1017.1	1018.0	1017.8	1016.2	1014.7	1013.2	1011.7
165°	1029.7	1030.7	1031.8	1031.6	1030.2	1028.8	1027.4	1026.0
167.5°	1040.0	1041.2	1042.5	1042.3	1040.7	1039.2	1037.6	1036.1
170°	1045.2	1046.6	1048.0	1047.9	1046.4	1044.8	1043.2	1041.7
172.5°	1049.3	1050.6	1051.9	1051.7	1050.1	1048.6	1047.0	1045.4
175°	1053.8	1055.2	1056.6	1056.5	1055.0	1053.4	1051.9	1050.3
177.5°	1055.7	1056.6	1057.6	1057.6	1056.4	1055.3	1054.2	1053.1
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0

(END OF REPORT)