

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333279-935

Luminaire Tested: **S125DIP-S1090D1035U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333279-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D1035U935-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7062.9 lumens  
Efficiency: N/A  
Efficacy: 116.7 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	39	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	29	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8843	8843	8843	8843
5°	10240	8873	7769	8873
10°	11913	8826	6807	8826
15°	13188	8762	6279	8762
20°	14762	8659	5856	8659
25°	17293	8543	5648	8543
30°	18678	8429	5469	8429
35°	15358	8215	5351	8215
40°	10916	7917	5223	7917
45°	8386	7516	5149	7516
50°	7159	7018	5138	7018
55°	6373	6531	5183	6531
60°	5749	5997	5315	5997
65°	5310	5462	5453	5462
70°	4828	4906	5531	4906
75°	4262	4319	5480	4319
80°	3585	3522	5013	3522
85°	2838	2542	4046	2542



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.8	1.9
10°-20°	392.4	5.6
20°-30°	637.2	9.0
30°-40°	777.3	11.0
40°-50°	707.1	10.0
50°-60°	563.2	8.0
60°-70°	392.3	5.6
70°-80°	209.2	3.0
80°-90°	55.2	0.8
90°-100°	309.0	4.4
100°-110°	664.3	9.4
110°-120°	623.4	8.8
120°-130°	505.2	7.2
130°-140°	405.5	5.7
140°-150°	306.0	4.3
150°-160°	215.4	3.0
160°-170°	126.9	1.8
170°-180°	41.3	0.6
0°-30°	1161.5	16.4
0°-40°	1938.8	27.5
0°-60°	3209.2	45.4
0°-90°	3865.9	54.7
90°-120°	1596.7	22.6
90°-150°	2813.4	39.8
90°-180°	3197.0	45.3
0°-180°	7062.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1369	1369	1369	1369	1369	
5°	1580	1369	1198	1369	1580	159
15°	1972	1310	939	1310	1972	565
25°	2427	1199	793	1199	2427	1108
35°	1948	1042	679	1042	1948	1192
45°	918	823	564	823	918	735
55°	566	580	460	580	566	510
65°	348	357	357	357	348	345
75°	171	173	220	173	171	184
85°	38	34	55	34	38	45
90°	20	1	20	1	20	15
95°	202	28	202	28	202	286
105°	1139	97	1139	97	1139	1132
115°	1269	174	1269	174	1269	1240
125°	1000	241	1000	241	1000	904
135°	830	282	830	282	830	643
145°	655	328	655	328	655	416
155°	549	375	549	375	549	256
165°	481	409	481	409	481	138
175°	432	425	432	425	432	42
180°	426	426	426	426	426	



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1448.2	1446.3	1444.5	1440.7	1443.6	1435.6	1431.9	1425.4	1417.5	1414.7	1411.4
5°	1579.5	1582.4	1585.4	1573.1	1574.3	1566.2	1547.6	1532.4	1520.3	1504.5	1493.5
7.5°	1737.6	1730.7	1730.2	1722.3	1708.7	1697.7	1678.2	1653.3	1629.3	1601.8	1579.2
10°	1816.6	1817.2	1812.0	1802.7	1788.1	1777.7	1752.1	1727.7	1698.1	1663.2	1638.2
12.5°	1876.1	1878.5	1872.0	1859.4	1852.3	1828.9	1808.9	1779.8	1744.6	1716.7	1678.7
15°	1972.4	1966.0	1961.4	1945.6	1933.5	1909.0	1877.1	1846.8	1808.4	1773.1	1737.6
17.5°	2065.1	2070.2	2061.5	2047.2	2009.3	1980.8	1937.9	1896.6	1848.8	1801.3	1758.9
20°	2147.9	2152.5	2139.2	2114.2	2068.8	2040.4	1984.0	1930.5	1875.3	1814.3	1767.8
22.5°	2251.1	2247.4	2229.3	2191.3	2152.1	2099.4	2038.4	1973.3	1904.1	1835.2	1773.4
25°	2426.8	2402.4	2391.3	2344.3	2292.6	2215.3	2131.6	2036.3	1950.3	1859.1	1780.0
27.5°	2524.2	2516.5	2504.2	2471.4	2417.1	2334.4	2235.8	2119.6	1998.3	1883.1	1779.7
30°	2504.6	2505.9	2507.0	2496.6	2461.7	2399.5	2301.3	2176.3	2032.2	1902.6	1782.9
32.5°	2331.8	2352.9	2373.1	2397.0	2406.8	2394.9	2333.4	2220.5	2072.2	1924.9	1781.1
35°	1947.9	1954.4	2020.0	2085.1	2173.4	2242.0	2287.9	2237.9	2113.0	1943.9	1778.8
37.5°	1518.9	1550.2	1595.7	1669.2	1796.7	1910.9	2057.7	2125.2	2084.9	1950.1	1774.8
40°	1294.8	1323.8	1353.5	1428.4	1535.9	1674.2	1841.0	1983.4	2016.5	1930.5	1760.8
42.5°	1121.8	1144.9	1177.8	1234.1	1324.0	1446.5	1605.8	1791.8	1906.3	1873.8	1731.6
45°	918.2	932.7	958.3	1003.1	1068.2	1164.0	1304.7	1508.0	1685.3	1744.0	1662.1
47.5°	785.9	785.8	805.7	836.6	883.6	965.0	1069.0	1228.4	1417.7	1557.8	1551.3
50°	712.5	709.6	725.2	752.0	789.2	843.3	942.6	1069.9	1251.7	1410.4	1454.6
52.5°	649.3	649.6	659.3	679.0	710.2	756.3	830.5	945.3	1100.7	1263.5	1346.7
55°	566.0	563.7	574.7	588.1	610.8	641.0	694.5	782.2	908.3	1068.7	1176.8
57.5°	489.7	496.2	500.6	509.9	528.7	549.0	594.0	658.4	758.5	896.1	1010.4
60°	445.1	451.5	455.0	464.3	479.4	496.9	531.8	584.0	668.3	786.9	900.2
62.5°	405.2	410.2	411.3	419.7	432.0	449.0	476.4	520.4	586.9	690.6	801.6
65°	347.5	347.5	349.8	358.5	364.4	379.4	400.4	432.4	485.9	566.6	661.3
67.5°	292.0	294.7	294.2	298.0	303.3	315.1	330.1	356.5	396.1	455.0	530.8
70°	255.7	258.0	257.4	260.4	266.1	273.7	285.9	310.9	339.4	389.9	455.0
72.5°	223.2	224.1	222.6	226.4	229.9	236.5	250.1	263.5	290.1	332.8	386.2
75°	170.8	172.0	173.1	175.5	179.0	182.4	189.4	202.9	220.2	252.2	286.5
77.5°	128.1	125.9	128.6	128.3	130.3	132.9	139.1	146.2	160.5	180.7	207.2
80°	96.4	97.0	97.0	97.6	100.6	102.3	107.5	112.7	123.8	138.9	157.5
82.5°	70.4	72.0	71.0	72.1	74.5	75.8	78.7	83.0	89.4	101.3	114.7
85°	38.3	35.5	36.6	37.8	37.8	38.3	40.6	42.4	45.9	50.5	55.8
87.5°	15.2	16.0	16.4	16.4	16.8	16.4	18.2	18.0	19.2	20.4	22.0
90°	19.8	19.8	18.9	18.9	18.9	17.2	16.4	15.5	14.6	13.8	12.1
92.5°	54.8	56.2	57.4	59.5	70.5	83.2	110.6	152.3	224.3	277.1	281.5
95°	202.0	215.8	222.7	248.4	309.4	381.6	487.3	618.0	745.2	761.6	621.5
97.5°	488.2	499.2	524.1	572.3	625.3	725.7	828.7	920.4	942.9	813.3	554.9
100°	670.5	684.2	716.0	777.8	837.2	926.5	1015.1	1057.2	991.0	776.1	495.1
102.5°	873.9	884.2	918.9	962.9	1026.2	1086.8	1129.2	1103.3	962.2	710.8	449.7
105°	1138.8	1149.2	1166.4	1194.7	1222.2	1231.7	1193.9	1076.1	869.9	623.1	405.7
107.5°	1279.4	1286.3	1292.0	1292.2	1278.2	1233.4	1136.3	979.1	775.6	562.8	387.1
110°	1326.2	1326.2	1320.2	1303.9	1265.2	1192.1	1070.9	907.7	721.9	534.6	381.6



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1320.7	1314.6	1299.6	1271.5	1215.0	1128.9	1006.3	851.3	682.1	518.1	381.6
115°	1268.7	1257.5	1233.4	1192.1	1125.1	1031.4	913.7	780.4	638.6	500.2	384.2
117.5°	1177.3	1170.4	1146.6	1104.0	1036.9	951.0	849.5	734.7	612.7	491.5	389.9
120°	1118.3	1111.4	1088.1	1046.9	983.3	907.7	813.1	710.0	598.2	487.3	395.4
122.5°	1066.0	1059.8	1036.6	998.8	942.0	871.2	787.0	691.4	585.8	483.9	400.2
125°	999.6	991.0	972.1	936.9	888.7	826.8	752.1	664.4	569.0	479.6	408.3
127.5°	942.9	939.1	921.2	890.1	846.4	788.5	718.8	636.9	553.5	477.5	417.4
130°	912.0	906.8	889.6	861.3	818.3	762.4	695.3	619.7	543.2	476.1	422.9
132.5°	881.0	875.1	859.4	831.0	788.0	734.2	673.3	602.5	534.9	476.1	429.0
135°	830.3	825.1	809.7	781.3	743.5	694.5	639.5	580.1	525.1	476.1	437.5
137.5°	776.1	770.5	756.2	730.4	696.5	655.0	609.2	561.3	516.4	477.2	445.2
140°	738.3	734.0	721.2	698.8	667.0	630.9	591.3	551.0	512.3	477.9	448.7
142.5°	703.3	699.6	687.4	668.6	641.5	610.3	576.2	542.0	508.9	478.5	450.7
145°	655.0	651.5	642.0	627.4	606.8	583.6	557.0	530.3	503.7	477.9	453.0
147.5°	614.1	612.5	607.0	595.3	578.9	561.5	541.0	519.4	498.3	475.6	453.8
150°	591.3	590.5	587.0	576.7	563.9	548.4	532.0	513.2	494.2	473.6	453.8
152.5°	573.4	572.6	569.2	560.9	550.1	538.0	523.1	506.3	489.4	470.9	453.1
155°	549.2	548.4	545.8	539.8	531.2	521.8	509.7	495.9	481.3	465.9	451.3
157.5°	527.5	527.7	525.3	520.4	513.7	506.3	497.0	485.6	473.7	460.7	449.0
160°	513.2	514.0	512.3	508.0	502.0	495.9	487.3	478.7	467.6	457.3	446.9
162.5°	500.1	500.2	499.9	496.3	491.6	486.3	479.1	471.2	462.1	453.1	444.9
165°	481.3	481.3	481.3	479.6	476.1	471.9	466.7	460.7	453.8	446.9	441.8
167.5°	464.2	464.3	465.0	463.5	461.8	458.7	454.7	450.7	445.7	440.9	437.0
170°	453.8	454.7	454.7	453.8	452.1	450.4	447.8	445.2	440.9	437.5	434.9
172.5°	444.2	445.1	446.4	444.9	444.5	443.5	441.6	439.0	436.1	433.3	432.1
175°	432.3	433.2	434.9	434.0	434.0	434.0	432.3	432.3	429.7	428.9	428.9
177.5°	426.3	426.3	428.3	427.7	428.3	428.3	428.3	427.7	427.0	426.3	426.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1408.7	1405.4	1401.7	1395.2	1387.2	1383.1	1376.6	1372.4	1364.0	1357.0	1349.6
5°	1480.1	1465.1	1451.1	1433.0	1413.3	1400.5	1385.4	1368.6	1351.2	1333.1	1313.4
7.5°	1554.2	1527.4	1498.4	1467.1	1436.6	1408.4	1381.6	1355.2	1330.6	1300.8	1275.6
10°	1604.0	1570.2	1534.2	1491.8	1450.5	1414.5	1377.9	1345.9	1313.4	1278.5	1247.7
12.5°	1653.6	1608.8	1557.9	1511.3	1461.6	1418.2	1375.1	1334.3	1293.4	1254.8	1218.8
15°	1688.8	1649.2	1602.1	1535.9	1480.1	1420.3	1363.3	1310.4	1261.0	1218.1	1172.8
17.5°	1711.9	1661.0	1610.4	1546.9	1473.8	1406.8	1342.3	1281.8	1226.1	1171.6	1127.8
20°	1716.1	1663.8	1610.9	1548.7	1473.8	1397.1	1332.6	1259.9	1200.1	1143.7	1090.2
22.5°	1714.7	1655.4	1597.8	1533.9	1460.8	1390.1	1312.1	1238.0	1173.1	1117.7	1061.9
25°	1701.6	1638.2	1566.2	1501.7	1429.6	1354.6	1275.6	1198.9	1132.6	1069.3	1014.1
27.5°	1690.7	1608.4	1526.9	1451.6	1382.1	1313.4	1237.7	1159.2	1085.6	1021.5	969.5
30°	1677.1	1587.1	1495.2	1416.8	1345.3	1278.5	1207.0	1130.3	1053.6	990.8	935.0
32.5°	1665.1	1560.1	1463.2	1377.8	1302.1	1237.1	1171.2	1098.2	1022.9	959.2	903.4
35°	1641.7	1520.3	1409.3	1312.8	1232.0	1165.2	1110.0	1042.0	972.8	911.2	857.7
37.5°	1612.1	1467.9	1348.8	1247.7	1159.2	1088.7	1037.3	985.2	918.8	859.4	811.1
40°	1588.8	1430.7	1304.7	1201.2	1109.4	1036.1	988.5	939.1	883.9	828.7	777.6
42.5°	1559.5	1397.3	1260.0	1148.7	1057.7	986.4	936.4	894.5	845.8	794.3	746.8
45°	1505.7	1336.6	1187.8	1068.2	976.3	905.9	854.3	822.9	786.3	737.4	697.3
47.5°	1426.6	1263.7	1109.8	986.3	891.6	826.4	777.9	747.8	722.0	685.7	649.4
50°	1356.3	1209.4	1053.6	931.0	836.3	770.6	725.8	698.5	676.4	648.5	617.8
52.5°	1277.8	1141.0	998.2	877.0	783.3	718.5	674.7	650.7	632.2	612.3	581.9
55°	1153.0	1036.7	904.2	789.2	702.6	639.2	600.9	580.0	564.9	549.7	531.2
57.5°	1015.5	924.5	807.2	702.0	622.2	564.6	528.8	508.5	496.7	489.0	478.0
60°	918.8	840.9	739.8	643.9	566.0	514.9	480.0	464.3	454.4	448.1	439.9
62.5°	829.1	765.1	671.4	583.9	515.8	467.4	436.4	421.1	411.6	408.5	401.8
65°	696.8	647.4	570.1	497.5	439.4	398.0	372.0	357.4	351.5	348.1	348.7
67.5°	566.5	536.4	474.3	412.3	366.0	331.4	310.5	299.3	296.4	291.7	291.6
70°	487.0	464.3	412.0	358.0	316.7	290.0	271.4	259.8	256.8	254.5	254.0
72.5°	416.8	396.9	351.5	308.2	271.1	247.7	232.3	225.3	220.6	219.2	219.1
75°	313.2	302.2	266.1	231.9	206.3	190.0	179.6	173.1	169.7	169.1	169.7
77.5°	222.7	213.0	190.1	165.8	149.7	137.4	128.5	126.3	122.3	122.5	121.9
80°	167.4	161.0	146.5	127.3	113.9	103.4	98.8	94.7	93.6	91.8	93.6
82.5°	121.3	114.5	104.6	92.4	81.4	75.1	70.4	69.1	68.4	67.7	68.0
85°	59.8	60.4	54.6	45.3	40.6	37.2	34.3	34.3	33.7	33.1	33.7
87.5°	22.7	21.4	19.4	17.7	15.0	13.3	12.4	12.7	11.5	11.4	12.2
90°	11.2	9.5	8.6	6.9	5.2	3.4	1.7	0.9	1.7	3.4	5.2
92.5°	196.1	117.4	70.5	45.4	30.6	20.0	12.7	10.5	12.7	20.0	30.6
95°	384.2	195.1	103.1	64.5	45.5	36.1	29.2	28.3	29.2	36.1	45.5
97.5°	306.7	168.2	107.3	79.4	62.4	53.0	48.1	47.1	48.1	53.0	62.4
100°	278.4	166.8	116.9	91.1	74.7	65.3	61.9	60.2	61.9	65.3	74.7
102.5°	266.8	173.0	128.5	103.5	88.5	78.4	75.6	74.6	75.6	78.4	88.5
105°	262.2	185.6	147.8	123.8	110.0	101.4	97.1	97.1	97.1	101.4	110.0
107.5°	270.1	204.6	168.0	146.3	132.0	124.9	120.9	119.2	120.9	124.9	132.0
110°	277.6	218.3	183.0	160.7	147.8	140.1	136.6	134.9	136.6	140.1	147.8





TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	287.2	231.4	197.5	175.8	163.0	155.2	152.5	150.8	152.5	155.2	163.0
115°	301.7	251.8	220.1	198.5	185.6	177.9	175.3	173.7	175.3	177.9	185.6
117.5°	318.2	272.9	242.7	222.0	207.3	199.6	196.8	194.2	196.8	199.6	207.3
120°	329.2	287.9	257.9	236.3	221.8	214.0	210.6	208.0	210.6	214.0	221.8
122.5°	341.6	302.4	272.3	250.8	234.8	227.0	224.3	222.5	224.3	227.0	234.8
125°	358.4	321.5	293.1	270.8	254.4	246.7	242.4	240.6	242.4	246.7	254.4
127.5°	373.8	339.8	312.5	290.2	272.9	263.0	257.5	254.9	257.5	263.0	272.9
130°	384.2	351.5	324.9	302.6	284.5	273.4	266.5	263.9	266.5	273.4	284.5
132.5°	393.1	362.6	335.9	313.6	294.8	282.2	274.0	270.8	274.0	282.2	294.8
135°	405.7	377.3	350.7	327.4	309.4	295.7	285.3	281.9	285.3	295.7	309.4
137.5°	415.0	387.8	363.6	339.7	322.0	308.2	298.6	296.0	298.6	308.2	322.0
140°	421.2	395.4	370.5	347.2	330.9	317.2	306.9	304.3	306.9	317.2	330.9
142.5°	424.6	400.2	376.6	354.8	339.1	325.4	315.8	313.9	315.8	325.4	339.1
145°	429.7	408.3	385.9	366.2	350.7	338.6	330.0	328.3	330.0	338.6	350.7
147.5°	432.8	413.5	393.8	376.4	363.1	351.9	344.5	343.5	344.5	351.9	363.1
150°	434.9	416.9	398.0	383.3	371.3	360.2	354.1	352.4	354.1	360.2	371.3
152.5°	436.3	420.3	402.8	389.5	378.2	368.4	363.1	362.1	363.1	368.4	378.2
155°	437.5	423.7	409.1	397.1	388.5	379.9	374.7	374.7	374.7	379.9	388.5
157.5°	438.3	426.6	414.1	405.0	397.4	390.0	385.9	386.1	385.9	390.0	397.4
160°	438.3	428.0	416.9	409.1	402.3	396.2	392.8	393.6	392.8	396.2	402.3
162.5°	437.6	429.4	419.7	413.3	407.8	402.4	399.0	399.8	399.0	402.4	407.8
165°	436.6	429.7	422.9	417.8	414.3	410.0	407.4	409.1	407.4	410.0	414.3
167.5°	434.5	429.7	424.0	420.9	418.4	416.0	414.5	415.3	414.5	416.0	418.4
170°	433.2	429.7	425.4	422.9	421.2	419.5	418.6	419.5	418.6	419.5	421.2
172.5°	431.8	429.0	425.4	424.2	423.2	421.5	420.7	422.2	420.7	421.5	423.2
175°	429.7	428.0	425.4	425.4	425.4	424.6	423.7	425.4	423.7	424.6	425.4
177.5°	427.7	427.0	425.6	425.6	426.3	425.6	425.6	427.0	425.6	425.6	426.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1345.4	1340.3	1336.1	1326.8	1321.7	1314.7	1309.2	1315.2	1308.7	1311.5	1307.3
5°	1303.5	1287.2	1275.6	1258.7	1244.2	1230.8	1221.0	1219.2	1214.5	1212.2	1205.2
7.5°	1253.0	1232.7	1212.7	1190.6	1172.0	1153.1	1141.0	1131.0	1124.4	1115.7	1109.7
10°	1223.3	1195.9	1172.8	1146.0	1122.7	1102.4	1086.2	1078.0	1070.5	1059.4	1055.3
12.5°	1186.5	1158.3	1130.0	1101.4	1079.0	1056.4	1042.4	1030.1	1024.8	1012.4	1011.2
15°	1142.5	1100.1	1072.2	1043.1	1012.4	993.8	982.1	968.7	962.9	954.2	947.8
17.5°	1089.9	1052.1	1017.2	987.1	960.7	945.0	930.7	921.4	911.5	905.8	895.3
20°	1051.9	1015.8	980.9	949.0	928.7	910.6	899.0	890.3	879.9	876.9	866.5
22.5°	1019.8	980.0	946.6	919.7	897.5	877.2	864.6	858.7	851.4	842.5	840.4
25°	967.6	926.3	897.9	871.2	851.4	832.8	824.1	816.5	809.5	803.1	800.8
27.5°	922.5	885.6	851.8	827.7	810.5	793.5	785.8	776.6	771.5	766.4	760.1
30°	890.9	853.1	823.5	800.2	781.6	766.5	758.4	752.0	747.3	742.7	739.2
32.5°	858.3	823.4	794.6	771.9	753.3	741.8	734.7	730.1	725.0	719.5	715.1
35°	815.4	777.0	749.1	729.4	714.8	706.1	697.9	693.9	688.0	688.0	683.4
37.5°	766.9	733.7	709.1	691.1	678.0	670.3	661.4	658.7	655.0	652.5	650.8
40°	738.0	707.2	684.0	666.0	652.0	645.7	638.7	634.0	631.7	628.8	627.6
42.5°	708.3	678.9	656.6	640.0	627.8	622.4	615.9	612.6	608.0	604.2	603.5
45°	663.1	634.6	614.2	600.9	590.4	584.0	580.0	573.0	570.7	566.0	565.4
47.5°	620.2	592.9	572.9	562.0	552.8	547.5	541.1	534.2	531.5	529.2	528.9
50°	588.1	563.1	544.5	534.1	525.4	517.8	511.4	506.8	505.0	505.0	506.2
52.5°	555.6	534.3	518.5	505.7	497.5	489.4	483.5	480.7	478.0	480.9	482.9
55°	507.9	486.4	474.8	462.6	454.4	445.1	442.2	441.1	439.4	444.0	446.3
57.5°	457.4	442.4	428.8	416.6	409.3	404.0	400.0	399.3	402.6	404.8	412.3
60°	425.4	407.9	395.7	386.4	377.7	374.3	373.1	372.0	374.3	380.6	390.5
62.5°	390.0	375.9	362.7	355.8	349.4	343.5	343.4	344.1	348.7	356.0	365.8
65°	338.2	326.0	317.3	309.2	303.9	300.4	301.6	303.9	309.2	319.0	330.1
67.5°	285.6	277.2	269.4	262.8	257.8	257.8	259.0	262.4	268.6	280.0	290.1
70°	251.7	242.4	235.9	233.1	228.9	226.6	230.1	235.9	241.2	251.7	260.4
72.5°	217.7	209.8	204.8	202.9	201.0	199.2	200.4	206.6	213.7	224.2	234.3
75°	167.4	164.5	161.0	158.7	156.9	158.1	159.2	165.1	170.8	181.9	193.6
77.5°	122.2	119.2	117.0	116.5	115.5	116.1	119.3	123.6	129.3	137.4	146.2
80°	92.4	91.3	90.1	89.5	89.5	90.1	94.7	97.6	102.9	110.4	117.4
82.5°	67.3	66.6	66.4	66.2	66.7	66.8	69.7	73.4	77.7	83.4	89.5
85°	35.5	34.3	36.0	36.6	35.5	37.2	38.3	40.6	42.4	45.3	48.2
87.5°	13.0	14.3	13.9	14.8	15.0	16.3	15.9	18.0	19.1	20.1	20.1
90°	6.9	8.6	9.5	11.2	12.1	13.8	14.6	15.5	16.4	17.2	18.9
92.5°	45.4	70.5	117.4	196.1	281.5	277.1	224.3	152.3	110.6	83.2	70.5
95°	64.5	103.1	195.1	384.2	621.5	761.6	745.2	618.0	487.3	381.6	309.4
97.5°	79.4	107.3	168.2	306.7	554.9	813.3	942.9	920.4	828.7	725.7	625.3
100°	91.1	116.9	166.8	278.4	495.1	776.1	991.0	1057.2	1015.1	926.5	837.2
102.5°	103.5	128.5	173.0	266.8	449.7	710.8	962.2	1103.3	1129.2	1086.8	1026.2
105°	123.8	147.8	185.6	262.2	405.7	623.1	869.9	1076.1	1193.9	1231.7	1222.2
107.5°	146.3	168.0	204.6	270.1	387.1	562.8	775.6	979.1	1136.3	1233.4	1278.2
110°	160.7	183.0	218.3	277.6	381.6	534.6	721.9	907.7	1070.9	1192.1	1265.2



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	175.8	197.5	231.4	287.2	381.6	518.1	682.1	851.3	1006.3	1128.9	1215.0
115°	198.5	220.1	251.8	301.7	384.2	500.2	638.6	780.4	913.7	1031.4	1125.1
117.5°	222.0	242.7	272.9	318.2	389.9	491.5	612.7	734.7	849.5	951.0	1036.9
120°	236.3	257.9	287.9	329.2	395.4	487.3	598.2	710.0	813.1	907.7	983.3
122.5°	250.8	272.3	302.4	341.6	400.2	483.9	585.8	691.4	787.0	871.2	942.0
125°	270.8	293.1	321.5	358.4	408.3	479.6	569.0	664.4	752.1	826.8	888.7
127.5°	290.2	312.5	339.8	373.8	417.4	477.5	553.5	636.9	718.8	788.5	846.4
130°	302.6	324.9	351.5	384.2	422.9	476.1	543.2	619.7	695.3	762.4	818.3
132.5°	313.6	335.9	362.6	393.1	429.0	476.1	534.9	602.5	673.3	734.2	788.0
135°	327.4	350.7	377.3	405.7	437.5	476.1	525.1	580.1	639.5	694.5	743.5
137.5°	339.7	363.6	387.8	415.0	445.2	477.2	516.4	561.3	609.2	655.0	696.5
140°	347.2	370.5	395.4	421.2	448.7	477.9	512.3	551.0	591.3	630.9	667.0
142.5°	354.8	376.6	400.2	424.6	450.7	478.5	508.9	542.0	576.2	610.3	641.5
145°	366.2	385.9	408.3	429.7	453.0	477.9	503.7	530.3	557.0	583.6	606.8
147.5°	376.4	393.8	413.5	432.8	453.8	475.6	498.3	519.4	541.0	561.5	578.9
150°	383.3	398.0	416.9	434.9	453.8	473.6	494.2	513.2	532.0	548.4	563.9
152.5°	389.5	402.8	420.3	436.3	453.1	470.9	489.4	506.3	523.1	538.0	550.1
155°	397.1	409.1	423.7	437.5	451.3	465.9	481.3	495.9	509.7	521.8	531.2
157.5°	405.0	414.1	426.6	438.3	449.0	460.7	473.7	485.6	497.0	506.3	513.7
160°	409.1	416.9	428.0	438.3	446.9	457.3	467.6	478.7	487.3	495.9	502.0
162.5°	413.3	419.7	429.4	437.6	444.9	453.1	462.1	471.2	479.1	486.3	491.6
165°	417.8	422.9	429.7	436.6	441.8	446.9	453.8	460.7	466.7	471.9	476.1
167.5°	420.9	424.0	429.7	434.5	437.0	440.9	445.7	450.7	454.7	458.7	461.8
170°	422.9	425.4	429.7	433.2	434.9	437.5	440.9	445.2	447.8	450.4	452.1
172.5°	424.2	425.4	429.0	431.8	432.1	433.3	436.1	439.0	441.6	443.5	444.5
175°	425.4	425.4	428.0	429.7	428.9	428.9	429.7	432.3	432.3	434.0	434.0
177.5°	425.6	425.6	427.0	427.7	426.3	426.3	427.0	427.7	428.3	428.3	428.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1304.5	1307.8	1305.0	1308.7	1305.0	1307.8	1304.5	1307.3	1311.5	1308.7	1315.2
5°	1202.4	1197.1	1200.6	1198.3	1200.6	1197.1	1202.4	1205.2	1212.2	1214.5	1219.2
7.5°	1108.0	1103.0	1097.3	1094.6	1097.3	1103.0	1108.0	1109.7	1115.7	1124.4	1131.0
10°	1049.0	1042.6	1042.0	1037.9	1042.0	1042.6	1049.0	1055.3	1059.4	1070.5	1078.0
12.5°	1005.7	999.8	993.2	991.4	993.2	999.8	1005.7	1011.2	1012.4	1024.8	1030.1
15°	944.3	939.7	935.6	939.1	935.6	939.7	944.3	947.8	954.2	962.9	968.7
17.5°	893.3	889.5	888.8	884.5	888.8	889.5	893.3	895.3	905.8	911.5	921.4
20°	861.3	858.3	859.5	852.0	859.5	858.3	861.3	866.5	876.9	879.9	890.3
22.5°	835.7	830.0	829.3	827.8	829.3	830.0	835.7	840.4	842.5	851.4	858.7
25°	795.6	792.6	789.8	792.6	789.8	792.6	795.6	800.8	803.1	809.5	816.5
27.5°	760.6	757.1	756.3	756.6	756.3	757.1	760.6	760.1	766.4	771.5	776.6
30°	739.2	733.4	734.0	733.4	734.0	733.4	739.2	739.2	742.7	747.3	752.0
32.5°	715.9	712.0	711.2	710.2	711.2	712.0	715.9	715.1	719.5	725.0	730.1
35°	681.7	681.7	678.7	678.7	678.7	681.7	681.7	683.4	688.0	688.0	693.9
37.5°	649.5	648.8	647.1	647.4	647.1	648.8	649.5	650.8	652.5	655.0	658.7
40°	625.3	624.7	622.9	619.5	622.9	624.7	625.3	627.6	628.8	631.7	634.0
42.5°	602.0	600.1	599.3	598.1	599.3	600.1	602.0	603.5	604.2	608.0	612.6
45°	565.4	565.4	564.3	563.7	564.3	565.4	565.4	565.4	566.0	570.7	573.0
47.5°	529.9	530.9	533.1	532.8	533.1	530.9	529.9	528.9	529.2	531.5	534.2
50°	508.5	509.1	510.8	511.4	510.8	509.1	508.5	506.2	505.0	505.0	506.8
52.5°	484.7	488.2	490.3	490.0	490.3	488.2	484.7	482.9	480.9	478.0	480.7
55°	451.5	455.6	459.7	460.3	459.7	455.6	451.5	446.3	444.0	439.4	441.1
57.5°	418.6	424.3	428.6	430.1	428.6	424.3	418.6	412.3	404.8	402.6	399.3
60°	396.3	403.9	409.1	411.5	409.1	403.9	396.3	390.5	380.6	374.3	372.0
62.5°	375.0	383.4	388.7	389.1	388.7	383.4	375.0	365.8	356.0	348.7	344.1
65°	339.9	348.7	353.4	356.8	353.4	348.7	339.9	330.1	319.0	309.2	303.9
67.5°	302.3	311.0	316.2	318.9	316.2	311.0	302.3	290.1	280.0	268.6	262.4
70°	274.9	283.6	290.6	292.9	290.6	283.6	274.9	260.4	251.7	241.2	235.9
72.5°	247.9	255.7	261.3	264.1	261.3	255.7	247.9	234.3	224.2	213.7	206.6
75°	201.0	211.5	216.8	219.6	216.8	211.5	201.0	193.6	181.9	170.8	165.1
77.5°	155.1	164.5	167.7	169.2	167.7	164.5	155.1	146.2	137.4	129.3	123.6
80°	124.3	130.2	134.2	134.8	134.2	130.2	124.3	117.4	110.4	102.9	97.6
82.5°	95.6	100.4	101.7	103.2	101.7	100.4	95.6	89.5	83.4	77.7	73.4
85°	52.3	54.6	55.2	54.6	55.2	54.6	52.3	48.2	45.3	42.4	40.6
87.5°	21.0	20.5	20.7	21.6	20.7	20.5	21.0	20.1	20.1	19.1	18.0
90°	18.9	18.9	19.8	19.8	19.8	18.9	18.9	18.9	17.2	16.4	15.5
92.5°	59.5	57.4	56.2	54.8	56.2	57.4	59.5	70.5	83.2	110.6	152.3
95°	248.4	222.7	215.8	202.0	215.8	222.7	248.4	309.4	381.6	487.3	618.0
97.5°	572.3	524.1	499.2	488.2	499.2	524.1	572.3	625.3	725.7	828.7	920.4
100°	777.8	716.0	684.2	670.5	684.2	716.0	777.8	837.2	926.5	1015.1	1057.2
102.5°	962.9	918.9	884.2	873.9	884.2	918.9	962.9	1026.2	1086.8	1129.2	1103.3
105°	1194.7	1166.4	1149.2	1138.8	1149.2	1166.4	1194.7	1222.2	1231.7	1193.9	1076.1
107.5°	1292.2	1292.0	1286.3	1279.4	1286.3	1292.0	1292.2	1278.2	1233.4	1136.3	979.1
110°	1303.9	1320.2	1326.2	1326.2	1326.2	1320.2	1303.9	1265.2	1192.1	1070.9	907.7



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1271.5	1299.6	1314.6	1320.7	1314.6	1299.6	1271.5	1215.0	1128.9	1006.3	851.3
115°	1192.1	1233.4	1257.5	1268.7	1257.5	1233.4	1192.1	1125.1	1031.4	913.7	780.4
117.5°	1104.0	1146.6	1170.4	1177.3	1170.4	1146.6	1104.0	1036.9	951.0	849.5	734.7
120°	1046.9	1088.1	1111.4	1118.3	1111.4	1088.1	1046.9	983.3	907.7	813.1	710.0
122.5°	998.8	1036.6	1059.8	1066.0	1059.8	1036.6	998.8	942.0	871.2	787.0	691.4
125°	936.9	972.1	991.0	999.6	991.0	972.1	936.9	888.7	826.8	752.1	664.4
127.5°	890.1	921.2	939.1	942.9	939.1	921.2	890.1	846.4	788.5	718.8	636.9
130°	861.3	889.6	906.8	912.0	906.8	889.6	861.3	818.3	762.4	695.3	619.7
132.5°	831.0	859.4	875.1	881.0	875.1	859.4	831.0	788.0	734.2	673.3	602.5
135°	781.3	809.7	825.1	830.3	825.1	809.7	781.3	743.5	694.5	639.5	580.1
137.5°	730.4	756.2	770.5	776.1	770.5	756.2	730.4	696.5	655.0	609.2	561.3
140°	698.8	721.2	734.0	738.3	734.0	721.2	698.8	667.0	630.9	591.3	551.0
142.5°	668.6	687.4	699.6	703.3	699.6	687.4	668.6	641.5	610.3	576.2	542.0
145°	627.4	642.0	651.5	655.0	651.5	642.0	627.4	606.8	583.6	557.0	530.3
147.5°	595.3	607.0	612.5	614.1	612.5	607.0	595.3	578.9	561.5	541.0	519.4
150°	576.7	587.0	590.5	591.3	590.5	587.0	576.7	563.9	548.4	532.0	513.2
152.5°	560.9	569.2	572.6	573.4	572.6	569.2	560.9	550.1	538.0	523.1	506.3
155°	539.8	545.8	548.4	549.2	548.4	545.8	539.8	531.2	521.8	509.7	495.9
157.5°	520.4	525.3	527.7	527.5	527.7	525.3	520.4	513.7	506.3	497.0	485.6
160°	508.0	512.3	514.0	513.2	514.0	512.3	508.0	502.0	495.9	487.3	478.7
162.5°	496.3	499.9	500.2	500.1	500.2	499.9	496.3	491.6	486.3	479.1	471.2
165°	479.6	481.3	481.3	481.3	481.3	481.3	479.6	476.1	471.9	466.7	460.7
167.5°	463.5	465.0	464.3	464.2	464.3	465.0	463.5	461.8	458.7	454.7	450.7
170°	453.8	454.7	454.7	453.8	454.7	454.7	453.8	452.1	450.4	447.8	445.2
172.5°	444.9	446.4	445.1	444.2	445.1	446.4	444.9	444.5	443.5	441.6	439.0
175°	434.0	434.9	433.2	432.3	433.2	434.9	434.0	434.0	434.0	432.3	432.3
177.5°	427.7	428.3	426.3	426.3	426.3	428.3	427.7	428.3	428.3	428.3	427.7
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1309.2	1314.7	1321.7	1326.8	1336.1	1340.3	1345.4	1349.6	1357.0	1364.0	1372.4
5°	1221.0	1230.8	1244.2	1258.7	1275.6	1287.2	1303.5	1313.4	1333.1	1351.2	1368.6
7.5°	1141.0	1153.1	1172.0	1190.6	1212.7	1232.7	1253.0	1275.6	1300.8	1330.6	1355.2
10°	1086.2	1102.4	1122.7	1146.0	1172.8	1195.9	1223.3	1247.7	1278.5	1313.4	1345.9
12.5°	1042.4	1056.4	1079.0	1101.4	1130.0	1158.3	1186.5	1218.8	1254.8	1293.4	1334.3
15°	982.1	993.8	1012.4	1043.1	1072.2	1100.1	1142.5	1172.8	1218.1	1261.0	1310.4
17.5°	930.7	945.0	960.7	987.1	1017.2	1052.1	1089.9	1127.8	1171.6	1226.1	1281.8
20°	899.0	910.6	928.7	949.0	980.9	1015.8	1051.9	1090.2	1143.7	1200.1	1259.9
22.5°	864.6	877.2	897.5	919.7	946.6	980.0	1019.8	1061.9	1117.7	1173.1	1238.0
25°	824.1	832.8	851.4	871.2	897.9	926.3	967.6	1014.1	1069.3	1132.6	1198.9
27.5°	785.8	793.5	810.5	827.7	851.8	885.6	922.5	969.5	1021.5	1085.6	1159.2
30°	758.4	766.5	781.6	800.2	823.5	853.1	890.9	935.0	990.8	1053.6	1130.3
32.5°	734.7	741.8	753.3	771.9	794.6	823.4	858.3	903.4	959.2	1022.9	1098.2
35°	697.9	706.1	714.8	729.4	749.1	777.0	815.4	857.7	911.2	972.8	1042.0
37.5°	661.4	670.3	678.0	691.1	709.1	733.7	766.9	811.1	859.4	918.8	985.2
40°	638.7	645.7	652.0	666.0	684.0	707.2	738.0	777.6	828.7	883.9	939.1
42.5°	615.9	622.4	627.8	640.0	656.6	678.9	708.3	746.8	794.3	845.8	894.5
45°	580.0	584.0	590.4	600.9	614.2	634.6	663.1	697.3	737.4	786.3	822.9
47.5°	541.1	547.5	552.8	562.0	572.9	592.9	620.2	649.4	685.7	722.0	747.8
50°	511.4	517.8	525.4	534.1	544.5	563.1	588.1	617.8	648.5	676.4	698.5
52.5°	483.5	489.4	497.5	505.7	518.5	534.3	555.6	581.9	612.3	632.2	650.7
55°	442.2	445.1	454.4	462.6	474.8	486.4	507.9	531.2	549.7	564.9	580.0
57.5°	400.0	404.0	409.3	416.6	428.8	442.4	457.4	478.0	489.0	496.7	508.5
60°	373.1	374.3	377.7	386.4	395.7	407.9	425.4	439.9	448.1	454.4	464.3
62.5°	343.4	343.5	349.4	355.8	362.7	375.9	390.0	401.8	408.5	411.6	421.1
65°	301.6	300.4	303.9	309.2	317.3	326.0	338.2	348.7	348.1	351.5	357.4
67.5°	259.0	257.8	257.8	262.8	269.4	277.2	285.6	291.6	291.7	296.4	299.3
70°	230.1	226.6	228.9	233.1	235.9	242.4	251.7	254.0	254.5	256.8	259.8
72.5°	200.4	199.2	201.0	202.9	204.8	209.8	217.7	219.1	219.2	220.6	225.3
75°	159.2	158.1	156.9	158.7	161.0	164.5	167.4	169.7	169.1	169.7	173.1
77.5°	119.3	116.1	115.5	116.5	117.0	119.2	122.2	121.9	122.5	122.3	126.3
80°	94.7	90.1	89.5	89.5	90.1	91.3	92.4	93.6	91.8	93.6	94.7
82.5°	69.7	66.8	66.7	66.2	66.4	66.6	67.3	68.0	67.7	68.4	69.1
85°	38.3	37.2	35.5	36.6	36.0	34.3	35.5	33.7	33.1	33.7	34.3
87.5°	15.9	16.3	15.0	14.8	13.9	14.3	13.0	12.2	11.4	11.5	12.7
90°	14.6	13.8	12.1	11.2	9.5	8.6	6.9	5.2	3.4	1.7	0.9
92.5°	224.3	277.1	281.5	196.1	117.4	70.5	45.4	30.6	20.0	12.7	10.5
95°	745.2	761.6	621.5	384.2	195.1	103.1	64.5	45.5	36.1	29.2	28.3
97.5°	942.9	813.3	554.9	306.7	168.2	107.3	79.4	62.4	53.0	48.1	47.1
100°	991.0	776.1	495.1	278.4	166.8	116.9	91.1	74.7	65.3	61.9	60.2
102.5°	962.2	710.8	449.7	266.8	173.0	128.5	103.5	88.5	78.4	75.6	74.6
105°	869.9	623.1	405.7	262.2	185.6	147.8	123.8	110.0	101.4	97.1	97.1
107.5°	775.6	562.8	387.1	270.1	204.6	168.0	146.3	132.0	124.9	120.9	119.2
110°	721.9	534.6	381.6	277.6	218.3	183.0	160.7	147.8	140.1	136.6	134.9



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	682.1	518.1	381.6	287.2	231.4	197.5	175.8	163.0	155.2	152.5	150.8
115°	638.6	500.2	384.2	301.7	251.8	220.1	198.5	185.6	177.9	175.3	173.7
117.5°	612.7	491.5	389.9	318.2	272.9	242.7	222.0	207.3	199.6	196.8	194.2
120°	598.2	487.3	395.4	329.2	287.9	257.9	236.3	221.8	214.0	210.6	208.0
122.5°	585.8	483.9	400.2	341.6	302.4	272.3	250.8	234.8	227.0	224.3	222.5
125°	569.0	479.6	408.3	358.4	321.5	293.1	270.8	254.4	246.7	242.4	240.6
127.5°	553.5	477.5	417.4	373.8	339.8	312.5	290.2	272.9	263.0	257.5	254.9
130°	543.2	476.1	422.9	384.2	351.5	324.9	302.6	284.5	273.4	266.5	263.9
132.5°	534.9	476.1	429.0	393.1	362.6	335.9	313.6	294.8	282.2	274.0	270.8
135°	525.1	476.1	437.5	405.7	377.3	350.7	327.4	309.4	295.7	285.3	281.9
137.5°	516.4	477.2	445.2	415.0	387.8	363.6	339.7	322.0	308.2	298.6	296.0
140°	512.3	477.9	448.7	421.2	395.4	370.5	347.2	330.9	317.2	306.9	304.3
142.5°	508.9	478.5	450.7	424.6	400.2	376.6	354.8	339.1	325.4	315.8	313.9
145°	503.7	477.9	453.0	429.7	408.3	385.9	366.2	350.7	338.6	330.0	328.3
147.5°	498.3	475.6	453.8	432.8	413.5	393.8	376.4	363.1	351.9	344.5	343.5
150°	494.2	473.6	453.8	434.9	416.9	398.0	383.3	371.3	360.2	354.1	352.4
152.5°	489.4	470.9	453.1	436.3	420.3	402.8	389.5	378.2	368.4	363.1	362.1
155°	481.3	465.9	451.3	437.5	423.7	409.1	397.1	388.5	379.9	374.7	374.7
157.5°	473.7	460.7	449.0	438.3	426.6	414.1	405.0	397.4	390.0	385.9	386.1
160°	467.6	457.3	446.9	438.3	428.0	416.9	409.1	402.3	396.2	392.8	393.6
162.5°	462.1	453.1	444.9	437.6	429.4	419.7	413.3	407.8	402.4	399.0	399.8
165°	453.8	446.9	441.8	436.6	429.7	422.9	417.8	414.3	410.0	407.4	409.1
167.5°	445.7	440.9	437.0	434.5	429.7	424.0	420.9	418.4	416.0	414.5	415.3
170°	440.9	437.5	434.9	433.2	429.7	425.4	422.9	421.2	419.5	418.6	419.5
172.5°	436.1	433.3	432.1	431.8	429.0	425.4	424.2	423.2	421.5	420.7	422.2
175°	429.7	428.9	428.9	429.7	428.0	425.4	425.4	425.4	424.6	423.7	425.4
177.5°	427.0	426.3	426.3	427.7	427.0	425.6	425.6	426.3	425.6	425.6	427.0
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1376.6	1383.1	1387.2	1395.2	1401.7	1405.4	1408.7	1411.4	1414.7	1417.5	1425.4
5°	1385.4	1400.5	1413.3	1433.0	1451.1	1465.1	1480.1	1493.5	1504.5	1520.3	1532.4
7.5°	1381.6	1408.4	1436.6	1467.1	1498.4	1527.4	1554.2	1579.2	1601.8	1629.3	1653.3
10°	1377.9	1414.5	1450.5	1491.8	1534.2	1570.2	1604.0	1638.2	1663.2	1698.1	1727.7
12.5°	1375.1	1418.2	1461.6	1511.3	1557.9	1608.8	1653.6	1678.7	1716.7	1744.6	1779.8
15°	1363.3	1420.3	1480.1	1535.9	1602.1	1649.2	1688.8	1737.6	1773.1	1808.4	1846.8
17.5°	1342.3	1406.8	1473.8	1546.9	1610.4	1661.0	1711.9	1758.9	1801.3	1848.8	1896.6
20°	1332.6	1397.1	1473.8	1548.7	1610.9	1663.8	1716.1	1767.8	1814.3	1875.3	1930.5
22.5°	1312.1	1390.1	1460.8	1533.9	1597.8	1655.4	1714.7	1773.4	1835.2	1904.1	1973.3
25°	1275.6	1354.6	1429.6	1501.7	1566.2	1638.2	1701.6	1780.0	1859.1	1950.3	2036.3
27.5°	1237.7	1313.4	1382.1	1451.6	1526.9	1608.4	1690.7	1779.7	1883.1	1998.3	2119.6
30°	1207.0	1278.5	1345.3	1416.8	1495.2	1587.1	1677.1	1782.9	1902.6	2032.2	2176.3
32.5°	1171.2	1237.1	1302.1	1377.8	1463.2	1560.1	1665.1	1781.1	1924.9	2072.2	2220.5
35°	1110.0	1165.2	1232.0	1312.8	1409.3	1520.3	1641.7	1778.8	1943.9	2113.0	2237.9
37.5°	1037.3	1088.7	1159.2	1247.7	1348.8	1467.9	1612.1	1774.8	1950.1	2084.9	2125.2
40°	988.5	1036.1	1109.4	1201.2	1304.7	1430.7	1588.8	1760.8	1930.5	2016.5	1983.4
42.5°	936.4	986.4	1057.7	1148.7	1260.0	1397.3	1559.5	1731.6	1873.8	1906.3	1791.8
45°	854.3	905.9	976.3	1068.2	1187.8	1336.6	1505.7	1662.1	1744.0	1685.3	1508.0
47.5°	777.9	826.4	891.6	986.3	1109.8	1263.7	1426.6	1551.3	1557.8	1417.7	1228.4
50°	725.8	770.6	836.3	931.0	1053.6	1209.4	1356.3	1454.6	1410.4	1251.7	1069.9
52.5°	674.7	718.5	783.3	877.0	998.2	1141.0	1277.8	1346.7	1263.5	1100.7	945.3
55°	600.9	639.2	702.6	789.2	904.2	1036.7	1153.0	1176.8	1068.7	908.3	782.2
57.5°	528.8	564.6	622.2	702.0	807.2	924.5	1015.5	1010.4	896.1	758.5	658.4
60°	480.0	514.9	566.0	643.9	739.8	840.9	918.8	900.2	786.9	668.3	584.0
62.5°	436.4	467.4	515.8	583.9	671.4	765.1	829.1	801.6	690.6	586.9	520.4
65°	372.0	398.0	439.4	497.5	570.1	647.4	696.8	661.3	566.6	485.9	432.4
67.5°	310.5	331.4	366.0	412.3	474.3	536.4	566.5	530.8	455.0	396.1	356.5
70°	271.4	290.0	316.7	358.0	412.0	464.3	487.0	455.0	389.9	339.4	310.9
72.5°	232.3	247.7	271.1	308.2	351.5	396.9	416.8	386.2	332.8	290.1	263.5
75°	179.6	190.0	206.3	231.9	266.1	302.2	313.2	286.5	252.2	220.2	202.9
77.5°	128.5	137.4	149.7	165.8	190.1	213.0	222.7	207.2	180.7	160.5	146.2
80°	98.8	103.4	113.9	127.3	146.5	161.0	167.4	157.5	138.9	123.8	112.7
82.5°	70.4	75.1	81.4	92.4	104.6	114.5	121.3	114.7	101.3	89.4	83.0
85°	34.3	37.2	40.6	45.3	54.6	60.4	59.8	55.8	50.5	45.9	42.4
87.5°	12.4	13.3	15.0	17.7	19.4	21.4	22.7	22.0	20.4	19.2	18.0
90°	1.7	3.4	5.2	6.9	8.6	9.5	11.2	12.1	13.8	14.6	15.5
92.5°	12.7	20.0	30.6	45.4	70.5	117.4	196.1	281.5	277.1	224.3	152.3
95°	29.2	36.1	45.5	64.5	103.1	195.1	384.2	621.5	761.6	745.2	618.0
97.5°	48.1	53.0	62.4	79.4	107.3	168.2	306.7	554.9	813.3	942.9	920.4
100°	61.9	65.3	74.7	91.1	116.9	166.8	278.4	495.1	776.1	991.0	1057.2
102.5°	75.6	78.4	88.5	103.5	128.5	173.0	266.8	449.7	710.8	962.2	1103.3
105°	97.1	101.4	110.0	123.8	147.8	185.6	262.2	405.7	623.1	869.9	1076.1
107.5°	120.9	124.9	132.0	146.3	168.0	204.6	270.1	387.1	562.8	775.6	979.1
110°	136.6	140.1	147.8	160.7	183.0	218.3	277.6	381.6	534.6	721.9	907.7





TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	152.5	155.2	163.0	175.8	197.5	231.4	287.2	381.6	518.1	682.1	851.3
115°	175.3	177.9	185.6	198.5	220.1	251.8	301.7	384.2	500.2	638.6	780.4
117.5°	196.8	199.6	207.3	222.0	242.7	272.9	318.2	389.9	491.5	612.7	734.7
120°	210.6	214.0	221.8	236.3	257.9	287.9	329.2	395.4	487.3	598.2	710.0
122.5°	224.3	227.0	234.8	250.8	272.3	302.4	341.6	400.2	483.9	585.8	691.4
125°	242.4	246.7	254.4	270.8	293.1	321.5	358.4	408.3	479.6	569.0	664.4
127.5°	257.5	263.0	272.9	290.2	312.5	339.8	373.8	417.4	477.5	553.5	636.9
130°	266.5	273.4	284.5	302.6	324.9	351.5	384.2	422.9	476.1	543.2	619.7
132.5°	274.0	282.2	294.8	313.6	335.9	362.6	393.1	429.0	476.1	534.9	602.5
135°	285.3	295.7	309.4	327.4	350.7	377.3	405.7	437.5	476.1	525.1	580.1
137.5°	298.6	308.2	322.0	339.7	363.6	387.8	415.0	445.2	477.2	516.4	561.3
140°	306.9	317.2	330.9	347.2	370.5	395.4	421.2	448.7	477.9	512.3	551.0
142.5°	315.8	325.4	339.1	354.8	376.6	400.2	424.6	450.7	478.5	508.9	542.0
145°	330.0	338.6	350.7	366.2	385.9	408.3	429.7	453.0	477.9	503.7	530.3
147.5°	344.5	351.9	363.1	376.4	393.8	413.5	432.8	453.8	475.6	498.3	519.4
150°	354.1	360.2	371.3	383.3	398.0	416.9	434.9	453.8	473.6	494.2	513.2
152.5°	363.1	368.4	378.2	389.5	402.8	420.3	436.3	453.1	470.9	489.4	506.3
155°	374.7	379.9	388.5	397.1	409.1	423.7	437.5	451.3	465.9	481.3	495.9
157.5°	385.9	390.0	397.4	405.0	414.1	426.6	438.3	449.0	460.7	473.7	485.6
160°	392.8	396.2	402.3	409.1	416.9	428.0	438.3	446.9	457.3	467.6	478.7
162.5°	399.0	402.4	407.8	413.3	419.7	429.4	437.6	444.9	453.1	462.1	471.2
165°	407.4	410.0	414.3	417.8	422.9	429.7	436.6	441.8	446.9	453.8	460.7
167.5°	414.5	416.0	418.4	420.9	424.0	429.7	434.5	437.0	440.9	445.7	450.7
170°	418.6	419.5	421.2	422.9	425.4	429.7	433.2	434.9	437.5	440.9	445.2
172.5°	420.7	421.5	423.2	424.2	425.4	429.0	431.8	432.1	433.3	436.1	439.0
175°	423.7	424.6	425.4	425.4	425.4	428.0	429.7	428.9	428.9	429.7	432.3
177.5°	425.6	425.6	426.3	425.6	425.6	427.0	427.7	426.3	426.3	427.0	427.7
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1431.9	1435.6	1443.6	1440.7	1444.5	1446.3	1448.2
5°	1547.6	1566.2	1574.3	1573.1	1585.4	1582.4	1579.5
7.5°	1678.2	1697.7	1708.7	1722.3	1730.2	1730.7	1737.6
10°	1752.1	1777.7	1788.1	1802.7	1812.0	1817.2	1816.6
12.5°	1808.9	1828.9	1852.3	1859.4	1872.0	1878.5	1876.1
15°	1877.1	1909.0	1933.5	1945.6	1961.4	1966.0	1972.4
17.5°	1937.9	1980.8	2009.3	2047.2	2061.5	2070.2	2065.1
20°	1984.0	2040.4	2068.8	2114.2	2139.2	2152.5	2147.9
22.5°	2038.4	2099.4	2152.1	2191.3	2229.3	2247.4	2251.1
25°	2131.6	2215.3	2292.6	2344.3	2391.3	2402.4	2426.8
27.5°	2235.8	2334.4	2417.1	2471.4	2504.2	2516.5	2524.2
30°	2301.3	2399.5	2461.7	2496.6	2507.0	2505.9	2504.6
32.5°	2333.4	2394.9	2406.8	2397.0	2373.1	2352.9	2331.8
35°	2287.9	2242.0	2173.4	2085.1	2020.0	1954.4	1947.9
37.5°	2057.7	1910.9	1796.7	1669.2	1595.7	1550.2	1518.9
40°	1841.0	1674.2	1535.9	1428.4	1353.5	1323.8	1294.8
42.5°	1605.8	1446.5	1324.0	1234.1	1177.8	1144.9	1121.8
45°	1304.7	1164.0	1068.2	1003.1	958.3	932.7	918.2
47.5°	1069.0	965.0	883.6	836.6	805.7	785.8	785.9
50°	942.6	843.3	789.2	752.0	725.2	709.6	712.5
52.5°	830.5	756.3	710.2	679.0	659.3	649.6	649.3
55°	694.5	641.0	610.8	588.1	574.7	563.7	566.0
57.5°	594.0	549.0	528.7	509.9	500.6	496.2	489.7
60°	531.8	496.9	479.4	464.3	455.0	451.5	445.1
62.5°	476.4	449.0	432.0	419.7	411.3	410.2	405.2
65°	400.4	379.4	364.4	358.5	349.8	347.5	347.5
67.5°	330.1	315.1	303.3	298.0	294.2	294.7	292.0
70°	285.9	273.7	266.1	260.4	257.4	258.0	255.7
72.5°	250.1	236.5	229.9	226.4	222.6	224.1	223.2
75°	189.4	182.4	179.0	175.5	173.1	172.0	170.8
77.5°	139.1	132.9	130.3	128.3	128.6	125.9	128.1
80°	107.5	102.3	100.6	97.6	97.0	97.0	96.4
82.5°	78.7	75.8	74.5	72.1	71.0	72.0	70.4
85°	40.6	38.3	37.8	37.8	36.6	35.5	38.3
87.5°	18.2	16.4	16.8	16.4	16.4	16.0	15.2
90°	16.4	17.2	18.9	18.9	18.9	19.8	19.8
92.5°	110.6	83.2	70.5	59.5	57.4	56.2	54.8
95°	487.3	381.6	309.4	248.4	222.7	215.8	202.0
97.5°	828.7	725.7	625.3	572.3	524.1	499.2	488.2
100°	1015.1	926.5	837.2	777.8	716.0	684.2	670.5
102.5°	1129.2	1086.8	1026.2	962.9	918.9	884.2	873.9
105°	1193.9	1231.7	1222.2	1194.7	1166.4	1149.2	1138.8
107.5°	1136.3	1233.4	1278.2	1292.2	1292.0	1286.3	1279.4
110°	1070.9	1192.1	1265.2	1303.9	1320.2	1326.2	1326.2



TEST NUMBER: P333279-935

CATALOG NUMBER: S125DIP-S1090D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1006.3	1128.9	1215.0	1271.5	1299.6	1314.6	1320.7
115°	913.7	1031.4	1125.1	1192.1	1233.4	1257.5	1268.7
117.5°	849.5	951.0	1036.9	1104.0	1146.6	1170.4	1177.3
120°	813.1	907.7	983.3	1046.9	1088.1	1111.4	1118.3
122.5°	787.0	871.2	942.0	998.8	1036.6	1059.8	1066.0
125°	752.1	826.8	888.7	936.9	972.1	991.0	999.6
127.5°	718.8	788.5	846.4	890.1	921.2	939.1	942.9
130°	695.3	762.4	818.3	861.3	889.6	906.8	912.0
132.5°	673.3	734.2	788.0	831.0	859.4	875.1	881.0
135°	639.5	694.5	743.5	781.3	809.7	825.1	830.3
137.5°	609.2	655.0	696.5	730.4	756.2	770.5	776.1
140°	591.3	630.9	667.0	698.8	721.2	734.0	738.3
142.5°	576.2	610.3	641.5	668.6	687.4	699.6	703.3
145°	557.0	583.6	606.8	627.4	642.0	651.5	655.0
147.5°	541.0	561.5	578.9	595.3	607.0	612.5	614.1
150°	532.0	548.4	563.9	576.7	587.0	590.5	591.3
152.5°	523.1	538.0	550.1	560.9	569.2	572.6	573.4
155°	509.7	521.8	531.2	539.8	545.8	548.4	549.2
157.5°	497.0	506.3	513.7	520.4	525.3	527.7	527.5
160°	487.3	495.9	502.0	508.0	512.3	514.0	513.2
162.5°	479.1	486.3	491.6	496.3	499.9	500.2	500.1
165°	466.7	471.9	476.1	479.6	481.3	481.3	481.3
167.5°	454.7	458.7	461.8	463.5	465.0	464.3	464.2
170°	447.8	450.4	452.1	453.8	454.7	454.7	453.8
172.5°	441.6	443.5	444.5	444.9	446.4	445.1	444.2
175°	432.3	434.0	434.0	434.0	434.9	433.2	432.3
177.5°	428.3	428.3	428.3	427.7	428.3	426.3	426.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3

(END OF REPORT)