

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333324-935

Luminaire Tested: **S125DIP-S1270D1035U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333324-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1270D1035U935-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7661.5 lumens  
Efficiency: N/A  
Efficacy: 114.7 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58				
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	56	54	50				
2	91	84	78	73	85	78	73	69	68	64	61	59	56	53	50	48	46	42				
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	45	42	40	36				
4	76	66	58	52	71	61	54	49	54	48	44	47	42	39	40	37	34	31				
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	33	30	27				
6	65	53	44	39	60	49	42	37	44	38	33	38	33	30	33	29	26	24				
7	60	47	39	34	56	45	37	32	39	34	29	35	30	26	30	26	23	21				
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19				
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	22	19	17				
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	24	20	17	15				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10213	10213	10213	10213
5°	11826	10247	8972	10247
10°	13759	10194	7861	10194
15°	15230	10120	7252	10120
20°	17049	10001	6763	10001
25°	19973	9867	6524	9867
30°	21572	9735	6317	9735
35°	17738	9488	6180	9488
40°	12607	9144	6032	9144
45°	9685	8680	5946	8680
50°	8268	8106	5934	8106
55°	7362	7543	5986	7543
60°	6640	6926	6138	6926
65°	6134	6308	6298	6308
70°	5576	5665	6388	5665
75°	4923	4991	6331	4991
80°	4143	4069	5791	4069
85°	3283	2934	4676	2934



TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.2	2.0
10°-20°	453.2	5.9
20°-30°	736.0	9.6
30°-40°	897.7	11.7
40°-50°	816.7	10.7
50°-60°	650.5	8.5
60°-70°	453.1	5.9
70°-80°	241.6	3.2
80°-90°	63.4	0.8
90°-100°	309.0	4.0
100°-110°	664.3	8.7
110°-120°	623.4	8.1
120°-130°	505.2	6.6
130°-140°	405.5	5.3
140°-150°	306.0	4.0
150°-160°	215.4	2.8
160°-170°	126.9	1.7
170°-180°	41.3	0.5
0°-30°	1341.4	17.5
0°-40°	2239.2	29.2
0°-60°	3706.4	48.4
0°-90°	4464.4	58.3
90°-120°	1596.7	20.8
90°-150°	2813.4	36.7
90°-180°	3197.0	41.7
0°-180°	7661.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1581	1581	1581	1581	1581	
5°	1824	1581	1384	1581	1824	184
15°	2278	1514	1085	1514	2278	652
25°	2803	1385	916	1385	2803	1280
35°	2250	1203	784	1203	2250	1377
45°	1060	950	651	950	1060	849
55°	654	670	532	670	654	589
65°	401	413	412	413	401	398
75°	197	200	254	200	197	212
85°	44	40	63	40	44	52
90°	20	1	20	1	20	15
95°	202	28	202	28	202	286
105°	1139	97	1139	97	1139	1132
115°	1269	174	1269	174	1269	1240
125°	1000	241	1000	241	1000	904
135°	830	282	830	282	830	643
145°	655	328	655	328	655	416
155°	549	375	549	375	549	256
165°	481	409	481	409	481	138
175°	432	425	432	425	432	42
180°	426	426	426	426	426	



TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1672.6	1670.4	1668.3	1664.0	1667.2	1658.0	1653.7	1646.2	1637.1	1633.9	1630.1
5°	1824.2	1827.6	1830.9	1816.9	1818.2	1808.8	1787.3	1769.9	1755.8	1737.7	1724.9
7.5°	2006.8	1998.9	1998.2	1989.1	1973.4	1960.8	1938.2	1909.4	1881.7	1850.0	1823.9
10°	2098.1	2098.8	2092.7	2082.0	2065.2	2053.1	2023.6	1995.4	1961.2	1920.9	1892.0
12.5°	2166.8	2169.6	2162.0	2147.5	2139.2	2112.2	2089.0	2055.6	2014.8	1982.6	1938.7
15°	2277.9	2270.5	2265.2	2247.0	2233.0	2204.8	2167.9	2133.0	2088.7	2047.7	2006.8
17.5°	2385.1	2391.0	2380.9	2364.4	2320.7	2287.8	2238.3	2190.4	2135.3	2080.3	2031.5
20°	2480.6	2486.1	2470.6	2441.7	2389.4	2356.5	2291.4	2229.6	2165.8	2095.4	2041.7
22.5°	2599.9	2595.6	2574.7	2530.8	2485.4	2424.7	2354.2	2279.0	2199.2	2119.5	2048.1
25°	2802.8	2774.6	2761.8	2707.5	2647.7	2558.5	2461.9	2351.7	2252.5	2147.1	2055.8
27.5°	2915.3	2906.4	2892.2	2854.4	2791.5	2696.0	2582.1	2448.0	2307.9	2174.9	2055.4
30°	2892.7	2894.1	2895.5	2883.3	2843.1	2771.2	2657.8	2513.5	2347.1	2197.4	2059.2
32.5°	2693.0	2717.4	2740.8	2768.5	2779.7	2765.9	2694.8	2564.6	2393.2	2223.2	2057.0
35°	2249.8	2257.1	2333.0	2408.1	2510.2	2589.4	2642.4	2584.6	2440.3	2245.1	2054.4
37.5°	1754.2	1790.4	1842.9	1927.9	2075.1	2206.9	2376.4	2454.5	2407.9	2252.2	2049.8
40°	1495.4	1529.0	1563.1	1649.8	1773.9	1933.6	2126.2	2290.7	2328.9	2229.6	2033.7
42.5°	1295.6	1322.2	1360.2	1425.3	1529.0	1670.5	1854.6	2069.5	2201.7	2164.1	1999.8
45°	1060.4	1077.2	1106.7	1158.5	1233.6	1344.4	1506.8	1741.7	1946.4	2014.1	1919.5
47.5°	907.7	907.6	930.5	966.2	1020.5	1114.6	1234.7	1418.8	1637.4	1799.1	1791.7
50°	822.9	819.5	837.6	868.5	911.5	973.9	1088.6	1235.6	1445.7	1628.9	1679.9
52.5°	749.8	750.2	761.4	784.2	820.2	873.5	959.2	1091.7	1271.2	1459.2	1555.4
55°	653.8	651.0	663.7	679.2	705.4	740.3	802.0	903.4	1049.0	1234.2	1359.1
57.5°	565.7	573.1	578.2	588.9	610.6	634.0	686.0	760.4	876.0	1034.9	1166.9
60°	514.1	521.5	525.6	536.2	553.7	573.9	614.2	674.5	771.9	908.8	1039.7
62.5°	468.0	473.7	475.0	484.7	498.9	518.6	550.3	601.0	677.9	797.6	925.8
65°	401.4	401.4	404.1	414.1	420.9	438.2	462.4	499.4	561.1	654.4	763.8
67.5°	337.2	340.4	339.8	344.1	350.3	363.9	381.3	411.7	457.4	525.6	613.0
70°	295.3	298.0	297.3	300.7	307.4	316.2	330.2	359.0	391.9	450.4	525.6
72.5°	257.7	258.8	257.1	261.5	265.5	273.2	288.9	304.3	335.0	384.4	446.1
75°	197.3	198.6	200.0	202.7	206.7	210.8	218.8	234.3	254.3	291.3	330.9
77.5°	147.9	145.3	148.6	148.2	150.5	153.6	160.7	168.8	185.4	208.7	239.4
80°	111.4	112.1	112.1	112.8	116.1	118.1	124.2	130.2	142.9	160.4	181.9
82.5°	81.4	83.1	82.1	83.3	86.0	87.5	90.8	95.8	103.2	116.9	132.5
85°	44.3	41.0	42.3	43.7	43.7	44.3	47.0	49.0	53.0	58.4	64.4
87.5°	16.9	17.9	18.3	18.3	18.9	18.5	20.4	20.2	21.7	23.2	25.0
90°	19.8	19.8	18.9	18.9	18.9	17.2	16.4	15.5	14.6	13.8	12.1
92.5°	54.8	56.2	57.4	59.5	70.5	83.2	110.6	152.3	224.3	277.1	281.5
95°	202.0	215.8	222.7	248.4	309.4	381.6	487.3	618.0	745.2	761.6	621.5
97.5°	488.2	499.2	524.1	572.3	625.3	725.7	828.7	920.4	942.9	813.3	554.9
100°	670.5	684.2	716.0	777.8	837.2	926.5	1015.1	1057.2	991.0	776.1	495.1
102.5°	873.9	884.2	918.9	962.9	1026.2	1086.8	1129.2	1103.3	962.2	710.8	449.7
105°	1138.8	1149.2	1166.4	1194.7	1222.2	1231.7	1193.9	1076.1	869.9	623.1	405.7
107.5°	1279.4	1286.3	1292.0	1292.2	1278.2	1233.4	1136.3	979.1	775.6	562.8	387.1
110°	1326.2	1326.2	1320.2	1303.9	1265.2	1192.1	1070.9	907.7	721.9	534.6	381.6



TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1320.7	1314.6	1299.6	1271.5	1215.0	1128.9	1006.3	851.3	682.1	518.1	381.6
115°	1268.7	1257.5	1233.4	1192.1	1125.1	1031.4	913.7	780.4	638.6	500.2	384.2
117.5°	1177.3	1170.4	1146.6	1104.0	1036.9	951.0	849.5	734.7	612.7	491.5	389.9
120°	1118.3	1111.4	1088.1	1046.9	983.3	907.7	813.1	710.0	598.2	487.3	395.4
122.5°	1066.0	1059.8	1036.6	998.8	942.0	871.2	787.0	691.4	585.8	483.9	400.2
125°	999.6	991.0	972.1	936.9	888.7	826.8	752.1	664.4	569.0	479.6	408.3
127.5°	942.9	939.1	921.2	890.1	846.4	788.5	718.8	636.9	553.5	477.5	417.4
130°	912.0	906.8	889.6	861.3	818.3	762.4	695.3	619.7	543.2	476.1	422.9
132.5°	881.0	875.1	859.4	831.0	788.0	734.2	673.3	602.5	534.9	476.1	429.0
135°	830.3	825.1	809.7	781.3	743.5	694.5	639.5	580.1	525.1	476.1	437.5
137.5°	776.1	770.5	756.2	730.4	696.5	655.0	609.2	561.3	516.4	477.2	445.2
140°	738.3	734.0	721.2	698.8	667.0	630.9	591.3	551.0	512.3	477.9	448.7
142.5°	703.3	699.6	687.4	668.6	641.5	610.3	576.2	542.0	508.9	478.5	450.7
145°	655.0	651.5	642.0	627.4	606.8	583.6	557.0	530.3	503.7	477.9	453.0
147.5°	614.1	612.5	607.0	595.3	578.9	561.5	541.0	519.4	498.3	475.6	453.8
150°	591.3	590.5	587.0	576.7	563.9	548.4	532.0	513.2	494.2	473.6	453.8
152.5°	573.4	572.6	569.2	560.9	550.1	538.0	523.1	506.3	489.4	470.9	453.1
155°	549.2	548.4	545.8	539.8	531.2	521.8	509.7	495.9	481.3	465.9	451.3
157.5°	527.5	527.7	525.3	520.4	513.7	506.3	497.0	485.6	473.7	460.7	449.0
160°	513.2	514.0	512.3	508.0	502.0	495.9	487.3	478.7	467.6	457.3	446.9
162.5°	500.1	500.2	499.9	496.3	491.6	486.3	479.1	471.2	462.1	453.1	444.9
165°	481.3	481.3	481.3	479.6	476.1	471.9	466.7	460.7	453.8	446.9	441.8
167.5°	464.2	464.3	465.0	463.5	461.8	458.7	454.7	450.7	445.7	440.9	437.0
170°	453.8	454.7	454.7	453.8	452.1	450.4	447.8	445.2	440.9	437.5	434.9
172.5°	444.2	445.1	446.4	444.9	444.5	443.5	441.6	439.0	436.1	433.3	432.1
175°	432.3	433.2	434.9	434.0	434.0	434.0	432.3	432.3	429.7	428.9	428.9
177.5°	426.3	426.3	428.3	427.7	428.3	428.3	428.3	427.7	427.0	426.3	426.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1626.9	1623.2	1618.9	1611.4	1602.2	1597.4	1589.8	1585.0	1575.4	1567.3	1558.8
5°	1709.4	1692.0	1675.9	1655.1	1632.3	1617.5	1600.1	1580.6	1560.5	1539.6	1516.8
7.5°	1795.0	1764.1	1730.5	1694.4	1659.1	1626.6	1595.6	1565.1	1536.7	1502.4	1473.3
10°	1852.4	1813.5	1771.9	1722.9	1675.2	1633.7	1591.3	1554.4	1516.8	1476.5	1441.0
12.5°	1909.9	1858.0	1799.2	1745.4	1688.2	1637.9	1588.1	1541.0	1493.7	1449.1	1407.7
15°	1950.4	1904.8	1850.4	1773.9	1709.4	1640.4	1574.6	1513.5	1456.5	1406.8	1354.4
17.5°	1977.1	1918.3	1859.9	1786.5	1702.1	1624.8	1550.2	1480.3	1416.0	1353.1	1302.6
20°	1981.9	1921.6	1860.4	1788.6	1702.1	1613.5	1539.0	1455.1	1386.0	1320.9	1259.1
22.5°	1980.4	1911.9	1845.5	1771.5	1687.0	1605.4	1515.4	1429.9	1354.8	1290.8	1226.3
25°	1965.1	1892.0	1808.8	1734.3	1651.1	1564.5	1473.3	1384.7	1308.1	1234.9	1171.2
27.5°	1952.6	1857.7	1763.4	1676.5	1596.2	1516.8	1429.4	1338.7	1253.9	1179.7	1119.6
30°	1937.0	1833.0	1726.9	1636.3	1553.8	1476.5	1394.0	1305.4	1216.9	1144.4	1080.0
32.5°	1923.0	1801.8	1689.9	1591.2	1503.8	1428.7	1352.6	1268.3	1181.4	1107.8	1043.4
35°	1896.1	1755.8	1627.5	1516.1	1422.9	1345.7	1281.9	1203.4	1123.5	1052.4	990.7
37.5°	1861.8	1695.4	1557.8	1441.0	1338.7	1257.4	1198.0	1137.7	1061.1	992.6	936.7
40°	1835.0	1652.4	1506.8	1387.3	1281.3	1196.7	1141.7	1084.6	1020.9	957.1	898.0
42.5°	1801.1	1613.8	1455.3	1326.6	1221.7	1139.3	1081.5	1033.0	976.8	917.4	862.5
45°	1739.0	1543.7	1371.8	1233.6	1127.6	1046.4	986.6	950.4	908.1	851.7	805.4
47.5°	1647.6	1459.5	1281.8	1139.1	1029.7	954.4	898.5	863.7	833.9	791.9	749.9
50°	1566.5	1396.7	1216.9	1075.2	965.8	889.9	838.3	806.8	781.3	749.0	713.4
52.5°	1475.8	1317.8	1153.0	1013.0	904.6	829.8	779.2	751.5	730.2	707.1	672.1
55°	1331.6	1197.4	1044.3	911.5	811.4	738.3	694.0	669.9	652.4	634.9	613.5
57.5°	1172.8	1067.8	932.3	810.8	718.7	652.1	610.8	587.3	573.7	564.7	552.1
60°	1061.1	971.2	854.4	743.6	653.8	594.7	554.4	536.2	524.9	517.5	508.1
62.5°	957.5	883.6	775.5	674.4	595.7	539.8	503.9	486.3	475.4	471.8	464.1
65°	804.7	747.7	658.4	574.5	507.4	459.8	429.6	412.8	406.0	402.0	402.7
67.5°	654.3	619.5	547.8	476.2	422.7	382.7	358.5	345.7	342.3	336.9	336.8
70°	562.4	536.2	475.9	413.5	365.8	334.9	313.4	300.0	296.6	293.9	293.3
72.5°	481.4	458.4	406.0	356.0	313.1	286.0	268.4	260.3	254.8	253.1	253.0
75°	361.8	349.0	307.4	267.8	238.2	219.5	207.4	200.0	196.0	195.3	196.0
77.5°	257.2	246.1	219.6	191.6	172.9	158.7	148.4	145.9	141.4	141.5	140.8
80°	193.3	185.9	169.1	147.0	131.6	119.5	114.1	109.4	108.1	106.1	108.1
82.5°	140.2	132.2	120.8	106.7	93.9	86.7	81.4	79.9	79.0	78.1	78.5
85°	69.1	69.8	63.1	52.3	47.0	43.0	39.6	39.6	38.9	38.2	38.9
87.5°	25.8	24.5	22.1	20.1	17.1	15.2	14.3	14.6	13.3	13.0	13.9
90°	11.2	9.5	8.6	6.9	5.2	3.4	1.7	0.9	1.7	3.4	5.2
92.5°	196.1	117.4	70.5	45.4	30.6	20.0	12.7	10.5	12.7	20.0	30.6
95°	384.2	195.1	103.1	64.5	45.5	36.1	29.2	28.3	29.2	36.1	45.5
97.5°	306.7	168.2	107.3	79.4	62.4	53.0	48.1	47.1	48.1	53.0	62.4
100°	278.4	166.8	116.9	91.1	74.7	65.3	61.9	60.2	61.9	65.3	74.7
102.5°	266.8	173.0	128.5	103.5	88.5	78.4	75.6	74.6	75.6	78.4	88.5
105°	262.2	185.6	147.8	123.8	110.0	101.4	97.1	97.1	97.1	101.4	110.0
107.5°	270.1	204.6	168.0	146.3	132.0	124.9	120.9	119.2	120.9	124.9	132.0
110°	277.6	218.3	183.0	160.7	147.8	140.1	136.6	134.9	136.6	140.1	147.8





TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	287.2	231.4	197.5	175.8	163.0	155.2	152.5	150.8	152.5	155.2	163.0
115°	301.7	251.8	220.1	198.5	185.6	177.9	175.3	173.7	175.3	177.9	185.6
117.5°	318.2	272.9	242.7	222.0	207.3	199.6	196.8	194.2	196.8	199.6	207.3
120°	329.2	287.9	257.9	236.3	221.8	214.0	210.6	208.0	210.6	214.0	221.8
122.5°	341.6	302.4	272.3	250.8	234.8	227.0	224.3	222.5	224.3	227.0	234.8
125°	358.4	321.5	293.1	270.8	254.4	246.7	242.4	240.6	242.4	246.7	254.4
127.5°	373.8	339.8	312.5	290.2	272.9	263.0	257.5	254.9	257.5	263.0	272.9
130°	384.2	351.5	324.9	302.6	284.5	273.4	266.5	263.9	266.5	273.4	284.5
132.5°	393.1	362.6	335.9	313.6	294.8	282.2	274.0	270.8	274.0	282.2	294.8
135°	405.7	377.3	350.7	327.4	309.4	295.7	285.3	281.9	285.3	295.7	309.4
137.5°	415.0	387.8	363.6	339.7	322.0	308.2	298.6	296.0	298.6	308.2	322.0
140°	421.2	395.4	370.5	347.2	330.9	317.2	306.9	304.3	306.9	317.2	330.9
142.5°	424.6	400.2	376.6	354.8	339.1	325.4	315.8	313.9	315.8	325.4	339.1
145°	429.7	408.3	385.9	366.2	350.7	338.6	330.0	328.3	330.0	338.6	350.7
147.5°	432.8	413.5	393.8	376.4	363.1	351.9	344.5	343.5	344.5	351.9	363.1
150°	434.9	416.9	398.0	383.3	371.3	360.2	354.1	352.4	354.1	360.2	371.3
152.5°	436.3	420.3	402.8	389.5	378.2	368.4	363.1	362.1	363.1	368.4	378.2
155°	437.5	423.7	409.1	397.1	388.5	379.9	374.7	374.7	374.7	379.9	388.5
157.5°	438.3	426.6	414.1	405.0	397.4	390.0	385.9	386.1	385.9	390.0	397.4
160°	438.3	428.0	416.9	409.1	402.3	396.2	392.8	393.6	392.8	396.2	402.3
162.5°	437.6	429.4	419.7	413.3	407.8	402.4	399.0	399.8	399.0	402.4	407.8
165°	436.6	429.7	422.9	417.8	414.3	410.0	407.4	409.1	407.4	410.0	414.3
167.5°	434.5	429.7	424.0	420.9	418.4	416.0	414.5	415.3	414.5	416.0	418.4
170°	433.2	429.7	425.4	422.9	421.2	419.5	418.6	419.5	418.6	419.5	421.2
172.5°	431.8	429.0	425.4	424.2	423.2	421.5	420.7	422.2	420.7	421.5	423.2
175°	429.7	428.0	425.4	425.4	425.4	424.6	423.7	425.4	423.7	424.6	425.4
177.5°	427.7	427.0	425.6	425.6	426.3	425.6	425.6	427.0	425.6	425.6	426.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1553.8	1548.0	1543.2	1532.4	1526.5	1518.5	1512.0	1519.0	1511.5	1514.7	1509.8
5°	1505.5	1486.6	1473.3	1453.7	1437.0	1421.5	1410.1	1408.1	1402.7	1400.1	1392.0
7.5°	1447.2	1423.7	1400.6	1375.1	1353.6	1331.7	1317.8	1306.2	1298.6	1288.5	1281.7
10°	1412.8	1381.3	1354.4	1323.5	1296.7	1273.2	1254.4	1245.0	1236.3	1223.6	1218.8
12.5°	1370.4	1337.7	1305.0	1272.0	1246.2	1220.0	1203.9	1189.7	1183.7	1169.3	1167.9
15°	1319.5	1270.5	1238.3	1204.7	1169.2	1147.7	1134.3	1118.9	1112.2	1102.1	1094.7
17.5°	1258.9	1215.0	1174.8	1140.1	1109.6	1091.5	1074.8	1064.2	1052.7	1046.1	1034.0
20°	1214.8	1173.2	1132.9	1096.1	1072.5	1051.7	1038.3	1028.2	1016.2	1012.8	1000.7
22.5°	1177.8	1131.9	1093.2	1062.2	1036.6	1013.1	998.6	991.7	983.4	973.1	970.6
25°	1117.5	1069.9	1037.0	1006.1	983.3	961.8	951.7	943.0	935.0	927.6	924.9
27.5°	1065.4	1022.9	983.8	955.9	936.0	916.4	907.6	897.0	891.0	885.1	877.9
30°	1028.9	985.2	951.1	924.2	902.8	885.3	875.9	868.5	863.2	857.7	853.8
32.5°	991.4	950.9	917.7	891.5	870.0	856.8	848.5	843.3	837.3	830.9	825.8
35°	941.7	897.3	865.1	842.3	825.5	815.5	806.1	801.3	794.7	794.7	789.3
37.5°	885.7	847.4	819.0	798.1	783.1	774.1	764.0	760.7	756.4	753.5	751.7
40°	852.4	816.8	790.0	769.1	753.0	745.6	737.6	732.3	729.5	726.2	724.9
42.5°	818.0	784.0	758.3	739.1	725.1	718.8	711.3	707.6	702.1	697.8	697.0
45°	765.8	732.9	709.5	694.0	681.9	674.5	669.9	661.8	659.1	653.8	653.1
47.5°	716.3	684.8	661.7	649.0	638.4	632.4	625.0	616.9	613.9	611.1	610.9
50°	679.2	650.4	628.9	616.8	606.7	598.1	590.6	585.2	583.2	583.2	584.6
52.5°	641.6	617.1	598.8	584.0	574.5	565.2	558.4	555.2	552.1	555.3	557.8
55°	586.6	561.8	548.4	534.3	524.9	514.1	510.7	509.5	507.4	512.8	515.5
57.5°	528.3	510.9	495.2	481.2	472.8	466.6	462.0	461.2	465.0	467.5	476.2
60°	491.3	471.1	457.1	446.3	436.3	432.2	430.9	429.6	432.2	439.6	451.0
62.5°	450.5	434.1	419.0	410.9	403.5	396.8	396.5	397.4	402.7	411.1	422.6
65°	390.6	376.5	366.4	357.1	351.0	347.0	348.4	351.0	357.1	368.5	381.3
67.5°	329.8	320.1	311.2	303.5	297.7	297.7	299.1	303.1	310.2	323.4	335.0
70°	290.6	279.9	272.5	269.1	264.4	261.7	265.8	272.5	278.5	290.6	300.7
72.5°	251.4	242.3	236.5	234.3	232.2	230.1	231.4	238.7	246.8	258.9	270.6
75°	193.3	189.9	185.9	183.2	181.2	182.5	183.9	190.6	197.3	210.1	223.5
77.5°	141.1	137.6	135.2	134.5	133.5	134.1	137.8	142.8	149.4	158.7	168.8
80°	106.7	105.4	104.0	103.3	103.3	104.0	109.4	112.8	118.8	127.5	135.6
82.5°	77.7	76.9	76.6	76.5	77.1	77.1	80.4	84.8	89.8	96.3	103.3
85°	41.0	39.6	41.6	42.3	41.0	43.0	44.3	47.0	49.0	52.3	55.7
87.5°	14.8	16.2	15.8	16.7	16.9	18.3	18.0	20.2	21.5	22.7	22.6
90°	6.9	8.6	9.5	11.2	12.1	13.8	14.6	15.5	16.4	17.2	18.9
92.5°	45.4	70.5	117.4	196.1	281.5	277.1	224.3	152.3	110.6	83.2	70.5
95°	64.5	103.1	195.1	384.2	621.5	761.6	745.2	618.0	487.3	381.6	309.4
97.5°	79.4	107.3	168.2	306.7	554.9	813.3	942.9	920.4	828.7	725.7	625.3
100°	91.1	116.9	166.8	278.4	495.1	776.1	991.0	1057.2	1015.1	926.5	837.2
102.5°	103.5	128.5	173.0	266.8	449.7	710.8	962.2	1103.3	1129.2	1086.8	1026.2
105°	123.8	147.8	185.6	262.2	405.7	623.1	869.9	1076.1	1193.9	1231.7	1222.2
107.5°	146.3	168.0	204.6	270.1	387.1	562.8	775.6	979.1	1136.3	1233.4	1278.2
110°	160.7	183.0	218.3	277.6	381.6	534.6	721.9	907.7	1070.9	1192.1	1265.2



TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	175.8	197.5	231.4	287.2	381.6	518.1	682.1	851.3	1006.3	1128.9	1215.0
115°	198.5	220.1	251.8	301.7	384.2	500.2	638.6	780.4	913.7	1031.4	1125.1
117.5°	222.0	242.7	272.9	318.2	389.9	491.5	612.7	734.7	849.5	951.0	1036.9
120°	236.3	257.9	287.9	329.2	395.4	487.3	598.2	710.0	813.1	907.7	983.3
122.5°	250.8	272.3	302.4	341.6	400.2	483.9	585.8	691.4	787.0	871.2	942.0
125°	270.8	293.1	321.5	358.4	408.3	479.6	569.0	664.4	752.1	826.8	888.7
127.5°	290.2	312.5	339.8	373.8	417.4	477.5	553.5	636.9	718.8	788.5	846.4
130°	302.6	324.9	351.5	384.2	422.9	476.1	543.2	619.7	695.3	762.4	818.3
132.5°	313.6	335.9	362.6	393.1	429.0	476.1	534.9	602.5	673.3	734.2	788.0
135°	327.4	350.7	377.3	405.7	437.5	476.1	525.1	580.1	639.5	694.5	743.5
137.5°	339.7	363.6	387.8	415.0	445.2	477.2	516.4	561.3	609.2	655.0	696.5
140°	347.2	370.5	395.4	421.2	448.7	477.9	512.3	551.0	591.3	630.9	667.0
142.5°	354.8	376.6	400.2	424.6	450.7	478.5	508.9	542.0	576.2	610.3	641.5
145°	366.2	385.9	408.3	429.7	453.0	477.9	503.7	530.3	557.0	583.6	606.8
147.5°	376.4	393.8	413.5	432.8	453.8	475.6	498.3	519.4	541.0	561.5	578.9
150°	383.3	398.0	416.9	434.9	453.8	473.6	494.2	513.2	532.0	548.4	563.9
152.5°	389.5	402.8	420.3	436.3	453.1	470.9	489.4	506.3	523.1	538.0	550.1
155°	397.1	409.1	423.7	437.5	451.3	465.9	481.3	495.9	509.7	521.8	531.2
157.5°	405.0	414.1	426.6	438.3	449.0	460.7	473.7	485.6	497.0	506.3	513.7
160°	409.1	416.9	428.0	438.3	446.9	457.3	467.6	478.7	487.3	495.9	502.0
162.5°	413.3	419.7	429.4	437.6	444.9	453.1	462.1	471.2	479.1	486.3	491.6
165°	417.8	422.9	429.7	436.6	441.8	446.9	453.8	460.7	466.7	471.9	476.1
167.5°	420.9	424.0	429.7	434.5	437.0	440.9	445.7	450.7	454.7	458.7	461.8
170°	422.9	425.4	429.7	433.2	434.9	437.5	440.9	445.2	447.8	450.4	452.1
172.5°	424.2	425.4	429.0	431.8	432.1	433.3	436.1	439.0	441.6	443.5	444.5
175°	425.4	425.4	428.0	429.7	428.9	428.9	429.7	432.3	432.3	434.0	434.0
177.5°	425.6	425.6	427.0	427.7	426.3	426.3	427.0	427.7	428.3	428.3	428.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1506.7	1510.4	1507.2	1511.5	1507.2	1510.4	1506.7	1509.8	1514.7	1511.5	1519.0
5°	1388.6	1382.6	1386.6	1384.0	1386.6	1382.6	1388.6	1392.0	1400.1	1402.7	1408.1
7.5°	1279.6	1273.8	1267.3	1264.2	1267.3	1273.8	1279.6	1281.7	1288.5	1298.6	1306.2
10°	1211.4	1204.1	1203.4	1198.7	1203.4	1204.1	1211.4	1218.8	1223.6	1236.3	1245.0
12.5°	1161.5	1154.7	1147.0	1145.0	1147.0	1154.7	1161.5	1167.9	1169.3	1183.7	1189.7
15°	1090.6	1085.3	1080.6	1084.6	1080.6	1085.3	1090.6	1094.7	1102.1	1112.2	1118.9
17.5°	1031.7	1027.3	1026.5	1021.5	1026.5	1027.3	1031.7	1034.0	1046.1	1052.7	1064.2
20°	994.7	991.4	992.6	984.0	992.6	991.4	994.7	1000.7	1012.8	1016.2	1028.2
22.5°	965.2	958.6	957.8	956.1	957.8	958.6	965.2	970.6	973.1	983.4	991.7
25°	918.9	915.5	912.1	915.5	912.1	915.5	918.9	924.9	927.6	935.0	943.0
27.5°	878.4	874.4	873.5	873.8	873.5	874.4	878.4	877.9	885.1	891.0	897.0
30°	853.8	847.1	847.7	847.1	847.7	847.1	853.8	853.8	857.7	863.2	868.5
32.5°	826.9	822.3	821.4	820.2	821.4	822.3	826.9	825.8	830.9	837.3	843.3
35°	787.3	787.3	783.9	783.9	783.9	787.3	787.3	789.3	794.7	794.7	801.3
37.5°	750.1	749.4	747.4	747.7	747.4	749.4	750.1	751.7	753.5	756.4	760.7
40°	722.2	721.5	719.5	715.5	719.5	721.5	722.2	724.9	726.2	729.5	732.3
42.5°	695.3	693.0	692.1	690.8	692.1	693.0	695.3	697.0	697.8	702.1	707.6
45°	653.1	653.1	651.7	651.0	651.7	653.1	653.1	653.1	653.8	659.1	661.8
47.5°	612.0	613.2	615.7	615.4	615.7	613.2	612.0	610.9	611.1	613.9	616.9
50°	587.3	588.0	590.0	590.6	590.0	588.0	587.3	584.6	583.2	583.2	585.2
52.5°	559.9	563.8	566.4	565.9	566.4	563.8	559.9	557.8	555.3	552.1	555.2
55°	521.5	526.2	530.9	531.6	530.9	526.2	521.5	515.5	512.8	507.4	509.5
57.5°	483.5	490.1	495.1	496.6	495.1	490.1	483.5	476.2	467.5	465.0	461.2
60°	457.7	466.5	472.5	475.2	472.5	466.5	457.7	451.0	439.6	432.2	429.6
62.5°	433.0	442.8	448.8	449.4	448.8	442.8	433.0	422.6	411.1	402.7	397.4
65°	392.6	402.7	408.0	412.1	408.0	402.7	392.6	381.3	368.5	357.1	351.0
67.5°	349.1	359.2	365.2	368.3	365.2	359.2	349.1	335.0	323.4	310.2	303.1
70°	317.5	327.5	335.6	338.3	335.6	327.5	317.5	300.7	290.6	278.5	272.5
72.5°	286.3	295.3	301.8	305.0	301.8	295.3	286.3	270.6	258.9	246.8	238.7
75°	232.2	244.3	250.4	253.7	250.4	244.3	232.2	223.5	210.1	197.3	190.6
77.5°	179.1	190.1	193.7	195.4	193.7	190.1	179.1	168.8	158.7	149.4	142.8
80°	143.6	150.3	155.1	155.7	155.1	150.3	143.6	135.6	127.5	118.8	112.8
82.5°	110.4	116.0	117.4	119.2	117.4	116.0	110.4	103.3	96.3	89.8	84.8
85°	60.4	63.1	63.8	63.1	63.8	63.1	60.4	55.7	52.3	49.0	47.0
87.5°	23.7	23.1	23.2	24.4	23.2	23.1	23.7	22.6	22.7	21.5	20.2
90°	18.9	18.9	19.8	19.8	19.8	18.9	18.9	18.9	17.2	16.4	15.5
92.5°	59.5	57.4	56.2	54.8	56.2	57.4	59.5	70.5	83.2	110.6	152.3
95°	248.4	222.7	215.8	202.0	215.8	222.7	248.4	309.4	381.6	487.3	618.0
97.5°	572.3	524.1	499.2	488.2	499.2	524.1	572.3	625.3	725.7	828.7	920.4
100°	777.8	716.0	684.2	670.5	684.2	716.0	777.8	837.2	926.5	1015.1	1057.2
102.5°	962.9	918.9	884.2	873.9	884.2	918.9	962.9	1026.2	1086.8	1129.2	1103.3
105°	1194.7	1166.4	1149.2	1138.8	1149.2	1166.4	1194.7	1222.2	1231.7	1193.9	1076.1
107.5°	1292.2	1292.0	1286.3	1279.4	1286.3	1292.0	1292.2	1278.2	1233.4	1136.3	979.1
110°	1303.9	1320.2	1326.2	1326.2	1326.2	1320.2	1303.9	1265.2	1192.1	1070.9	907.7



TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1271.5	1299.6	1314.6	1320.7	1314.6	1299.6	1271.5	1215.0	1128.9	1006.3	851.3
115°	1192.1	1233.4	1257.5	1268.7	1257.5	1233.4	1192.1	1125.1	1031.4	913.7	780.4
117.5°	1104.0	1146.6	1170.4	1177.3	1170.4	1146.6	1104.0	1036.9	951.0	849.5	734.7
120°	1046.9	1088.1	1111.4	1118.3	1111.4	1088.1	1046.9	983.3	907.7	813.1	710.0
122.5°	998.8	1036.6	1059.8	1066.0	1059.8	1036.6	998.8	942.0	871.2	787.0	691.4
125°	936.9	972.1	991.0	999.6	991.0	972.1	936.9	888.7	826.8	752.1	664.4
127.5°	890.1	921.2	939.1	942.9	939.1	921.2	890.1	846.4	788.5	718.8	636.9
130°	861.3	889.6	906.8	912.0	906.8	889.6	861.3	818.3	762.4	695.3	619.7
132.5°	831.0	859.4	875.1	881.0	875.1	859.4	831.0	788.0	734.2	673.3	602.5
135°	781.3	809.7	825.1	830.3	825.1	809.7	781.3	743.5	694.5	639.5	580.1
137.5°	730.4	756.2	770.5	776.1	770.5	756.2	730.4	696.5	655.0	609.2	561.3
140°	698.8	721.2	734.0	738.3	734.0	721.2	698.8	667.0	630.9	591.3	551.0
142.5°	668.6	687.4	699.6	703.3	699.6	687.4	668.6	641.5	610.3	576.2	542.0
145°	627.4	642.0	651.5	655.0	651.5	642.0	627.4	606.8	583.6	557.0	530.3
147.5°	595.3	607.0	612.5	614.1	612.5	607.0	595.3	578.9	561.5	541.0	519.4
150°	576.7	587.0	590.5	591.3	590.5	587.0	576.7	563.9	548.4	532.0	513.2
152.5°	560.9	569.2	572.6	573.4	572.6	569.2	560.9	550.1	538.0	523.1	506.3
155°	539.8	545.8	548.4	549.2	548.4	545.8	539.8	531.2	521.8	509.7	495.9
157.5°	520.4	525.3	527.7	527.5	527.7	525.3	520.4	513.7	506.3	497.0	485.6
160°	508.0	512.3	514.0	513.2	514.0	512.3	508.0	502.0	495.9	487.3	478.7
162.5°	496.3	499.9	500.2	500.1	500.2	499.9	496.3	491.6	486.3	479.1	471.2
165°	479.6	481.3	481.3	481.3	481.3	481.3	479.6	476.1	471.9	466.7	460.7
167.5°	463.5	465.0	464.3	464.2	464.3	465.0	463.5	461.8	458.7	454.7	450.7
170°	453.8	454.7	454.7	453.8	454.7	454.7	453.8	452.1	450.4	447.8	445.2
172.5°	444.9	446.4	445.1	444.2	445.1	446.4	444.9	444.5	443.5	441.6	439.0
175°	434.0	434.9	433.2	432.3	433.2	434.9	434.0	434.0	434.0	432.3	432.3
177.5°	427.7	428.3	426.3	426.3	426.3	428.3	427.7	428.3	428.3	428.3	427.7
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1512.0	1518.5	1526.5	1532.4	1543.2	1548.0	1553.8	1558.8	1567.3	1575.4	1585.0
5°	1410.1	1421.5	1437.0	1453.7	1473.3	1486.6	1505.5	1516.8	1539.6	1560.5	1580.6
7.5°	1317.8	1331.7	1353.6	1375.1	1400.6	1423.7	1447.2	1473.3	1502.4	1536.7	1565.1
10°	1254.4	1273.2	1296.7	1323.5	1354.4	1381.3	1412.8	1441.0	1476.5	1516.8	1554.4
12.5°	1203.9	1220.0	1246.2	1272.0	1305.0	1337.7	1370.4	1407.7	1449.1	1493.7	1541.0
15°	1134.3	1147.7	1169.2	1204.7	1238.3	1270.5	1319.5	1354.4	1406.8	1456.5	1513.5
17.5°	1074.8	1091.5	1109.6	1140.1	1174.8	1215.0	1258.9	1302.6	1353.1	1416.0	1480.3
20°	1038.3	1051.7	1072.5	1096.1	1132.9	1173.2	1214.8	1259.1	1320.9	1386.0	1455.1
22.5°	998.6	1013.1	1036.6	1062.2	1093.2	1131.9	1177.8	1226.3	1290.8	1354.8	1429.9
25°	951.7	961.8	983.3	1006.1	1037.0	1069.9	1117.5	1171.2	1234.9	1308.1	1384.7
27.5°	907.6	916.4	936.0	955.9	983.8	1022.9	1065.4	1119.6	1179.7	1253.9	1338.7
30°	875.9	885.3	902.8	924.2	951.1	985.2	1028.9	1080.0	1144.4	1216.9	1305.4
32.5°	848.5	856.8	870.0	891.5	917.7	950.9	991.4	1043.4	1107.8	1181.4	1268.3
35°	806.1	815.5	825.5	842.3	865.1	897.3	941.7	990.7	1052.4	1123.5	1203.4
37.5°	764.0	774.1	783.1	798.1	819.0	847.4	885.7	936.7	992.6	1061.1	1137.7
40°	737.6	745.6	753.0	769.1	790.0	816.8	852.4	898.0	957.1	1020.9	1084.6
42.5°	711.3	718.8	725.1	739.1	758.3	784.0	818.0	862.5	917.4	976.8	1033.0
45°	669.9	674.5	681.9	694.0	709.5	732.9	765.8	805.4	851.7	908.1	950.4
47.5°	625.0	632.4	638.4	649.0	661.7	684.8	716.3	749.9	791.9	833.9	863.7
50°	590.6	598.1	606.7	616.8	628.9	650.4	679.2	713.4	749.0	781.3	806.8
52.5°	558.4	565.2	574.5	584.0	598.8	617.1	641.6	672.1	707.1	730.2	751.5
55°	510.7	514.1	524.9	534.3	548.4	561.8	586.6	613.5	634.9	652.4	669.9
57.5°	462.0	466.6	472.8	481.2	495.2	510.9	528.3	552.1	564.7	573.7	587.3
60°	430.9	432.2	436.3	446.3	457.1	471.1	491.3	508.1	517.5	524.9	536.2
62.5°	396.5	396.8	403.5	410.9	419.0	434.1	450.5	464.1	471.8	475.4	486.3
65°	348.4	347.0	351.0	357.1	366.4	376.5	390.6	402.7	402.0	406.0	412.8
67.5°	299.1	297.7	297.7	303.5	311.2	320.1	329.8	336.8	336.9	342.3	345.7
70°	265.8	261.7	264.4	269.1	272.5	279.9	290.6	293.3	293.9	296.6	300.0
72.5°	231.4	230.1	232.2	234.3	236.5	242.3	251.4	253.0	253.1	254.8	260.3
75°	183.9	182.5	181.2	183.2	185.9	189.9	193.3	196.0	195.3	196.0	200.0
77.5°	137.8	134.1	133.5	134.5	135.2	137.6	141.1	140.8	141.5	141.4	145.9
80°	109.4	104.0	103.3	103.3	104.0	105.4	106.7	108.1	106.1	108.1	109.4
82.5°	80.4	77.1	77.1	76.5	76.6	76.9	77.7	78.5	78.1	79.0	79.9
85°	44.3	43.0	41.0	42.3	41.6	39.6	41.0	38.9	38.2	38.9	39.6
87.5°	18.0	18.3	16.9	16.7	15.8	16.2	14.8	13.9	13.0	13.3	14.6
90°	14.6	13.8	12.1	11.2	9.5	8.6	6.9	5.2	3.4	1.7	0.9
92.5°	224.3	277.1	281.5	196.1	117.4	70.5	45.4	30.6	20.0	12.7	10.5
95°	745.2	761.6	621.5	384.2	195.1	103.1	64.5	45.5	36.1	29.2	28.3
97.5°	942.9	813.3	554.9	306.7	168.2	107.3	79.4	62.4	53.0	48.1	47.1
100°	991.0	776.1	495.1	278.4	166.8	116.9	91.1	74.7	65.3	61.9	60.2
102.5°	962.2	710.8	449.7	266.8	173.0	128.5	103.5	88.5	78.4	75.6	74.6
105°	869.9	623.1	405.7	262.2	185.6	147.8	123.8	110.0	101.4	97.1	97.1
107.5°	775.6	562.8	387.1	270.1	204.6	168.0	146.3	132.0	124.9	120.9	119.2
110°	721.9	534.6	381.6	277.6	218.3	183.0	160.7	147.8	140.1	136.6	134.9



TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	682.1	518.1	381.6	287.2	231.4	197.5	175.8	163.0	155.2	152.5	150.8
115°	638.6	500.2	384.2	301.7	251.8	220.1	198.5	185.6	177.9	175.3	173.7
117.5°	612.7	491.5	389.9	318.2	272.9	242.7	222.0	207.3	199.6	196.8	194.2
120°	598.2	487.3	395.4	329.2	287.9	257.9	236.3	221.8	214.0	210.6	208.0
122.5°	585.8	483.9	400.2	341.6	302.4	272.3	250.8	234.8	227.0	224.3	222.5
125°	569.0	479.6	408.3	358.4	321.5	293.1	270.8	254.4	246.7	242.4	240.6
127.5°	553.5	477.5	417.4	373.8	339.8	312.5	290.2	272.9	263.0	257.5	254.9
130°	543.2	476.1	422.9	384.2	351.5	324.9	302.6	284.5	273.4	266.5	263.9
132.5°	534.9	476.1	429.0	393.1	362.6	335.9	313.6	294.8	282.2	274.0	270.8
135°	525.1	476.1	437.5	405.7	377.3	350.7	327.4	309.4	295.7	285.3	281.9
137.5°	516.4	477.2	445.2	415.0	387.8	363.6	339.7	322.0	308.2	298.6	296.0
140°	512.3	477.9	448.7	421.2	395.4	370.5	347.2	330.9	317.2	306.9	304.3
142.5°	508.9	478.5	450.7	424.6	400.2	376.6	354.8	339.1	325.4	315.8	313.9
145°	503.7	477.9	453.0	429.7	408.3	385.9	366.2	350.7	338.6	330.0	328.3
147.5°	498.3	475.6	453.8	432.8	413.5	393.8	376.4	363.1	351.9	344.5	343.5
150°	494.2	473.6	453.8	434.9	416.9	398.0	383.3	371.3	360.2	354.1	352.4
152.5°	489.4	470.9	453.1	436.3	420.3	402.8	389.5	378.2	368.4	363.1	362.1
155°	481.3	465.9	451.3	437.5	423.7	409.1	397.1	388.5	379.9	374.7	374.7
157.5°	473.7	460.7	449.0	438.3	426.6	414.1	405.0	397.4	390.0	385.9	386.1
160°	467.6	457.3	446.9	438.3	428.0	416.9	409.1	402.3	396.2	392.8	393.6
162.5°	462.1	453.1	444.9	437.6	429.4	419.7	413.3	407.8	402.4	399.0	399.8
165°	453.8	446.9	441.8	436.6	429.7	422.9	417.8	414.3	410.0	407.4	409.1
167.5°	445.7	440.9	437.0	434.5	429.7	424.0	420.9	418.4	416.0	414.5	415.3
170°	440.9	437.5	434.9	433.2	429.7	425.4	422.9	421.2	419.5	418.6	419.5
172.5°	436.1	433.3	432.1	431.8	429.0	425.4	424.2	423.2	421.5	420.7	422.2
175°	429.7	428.9	428.9	429.7	428.0	425.4	425.4	425.4	424.6	423.7	425.4
177.5°	427.0	426.3	426.3	427.7	427.0	425.6	425.6	426.3	425.6	425.6	427.0
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3





TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1589.8	1597.4	1602.2	1611.4	1618.9	1623.2	1626.9	1630.1	1633.9	1637.1	1646.2
5°	1600.1	1617.5	1632.3	1655.1	1675.9	1692.0	1709.4	1724.9	1737.7	1755.8	1769.9
7.5°	1595.6	1626.6	1659.1	1694.4	1730.5	1764.1	1795.0	1823.9	1850.0	1881.7	1909.4
10°	1591.3	1633.7	1675.2	1722.9	1771.9	1813.5	1852.4	1892.0	1920.9	1961.2	1995.4
12.5°	1588.1	1637.9	1688.2	1745.4	1799.2	1858.0	1909.9	1938.7	1982.6	2014.8	2055.6
15°	1574.6	1640.4	1709.4	1773.9	1850.4	1904.8	1950.4	2006.8	2047.7	2088.7	2133.0
17.5°	1550.2	1624.8	1702.1	1786.5	1859.9	1918.3	1977.1	2031.5	2080.3	2135.3	2190.4
20°	1539.0	1613.5	1702.1	1788.6	1860.4	1921.6	1981.9	2041.7	2095.4	2165.8	2229.6
22.5°	1515.4	1605.4	1687.0	1771.5	1845.5	1911.9	1980.4	2048.1	2119.5	2199.2	2279.0
25°	1473.3	1564.5	1651.1	1734.3	1808.8	1892.0	1965.1	2055.8	2147.1	2252.5	2351.7
27.5°	1429.4	1516.8	1596.2	1676.5	1763.4	1857.7	1952.6	2055.4	2174.9	2307.9	2448.0
30°	1394.0	1476.5	1553.8	1636.3	1726.9	1833.0	1937.0	2059.2	2197.4	2347.1	2513.5
32.5°	1352.6	1428.7	1503.8	1591.2	1689.9	1801.8	1923.0	2057.0	2223.2	2393.2	2564.6
35°	1281.9	1345.7	1422.9	1516.1	1627.5	1755.8	1896.1	2054.4	2245.1	2440.3	2584.6
37.5°	1198.0	1257.4	1338.7	1441.0	1557.8	1695.4	1861.8	2049.8	2252.2	2407.9	2454.5
40°	1141.7	1196.7	1281.3	1387.3	1506.8	1652.4	1835.0	2033.7	2229.6	2328.9	2290.7
42.5°	1081.5	1139.3	1221.7	1326.6	1455.3	1613.8	1801.1	1999.8	2164.1	2201.7	2069.5
45°	986.6	1046.4	1127.6	1233.6	1371.8	1543.7	1739.0	1919.5	2014.1	1946.4	1741.7
47.5°	898.5	954.4	1029.7	1139.1	1281.8	1459.5	1647.6	1791.7	1799.1	1637.4	1418.8
50°	838.3	889.9	965.8	1075.2	1216.9	1396.7	1566.5	1679.9	1628.9	1445.7	1235.6
52.5°	779.2	829.8	904.6	1013.0	1153.0	1317.8	1475.8	1555.4	1459.2	1271.2	1091.7
55°	694.0	738.3	811.4	911.5	1044.3	1197.4	1331.6	1359.1	1234.2	1049.0	903.4
57.5°	610.8	652.1	718.7	810.8	932.3	1067.8	1172.8	1166.9	1034.9	876.0	760.4
60°	554.4	594.7	653.8	743.6	854.4	971.2	1061.1	1039.7	908.8	771.9	674.5
62.5°	503.9	539.8	595.7	674.4	775.5	883.6	957.5	925.8	797.6	677.9	601.0
65°	429.6	459.8	507.4	574.5	658.4	747.7	804.7	763.8	654.4	561.1	499.4
67.5°	358.5	382.7	422.7	476.2	547.8	619.5	654.3	613.0	525.6	457.4	411.7
70°	313.4	334.9	365.8	413.5	475.9	536.2	562.4	525.6	450.4	391.9	359.0
72.5°	268.4	286.0	313.1	356.0	406.0	458.4	481.4	446.1	384.4	335.0	304.3
75°	207.4	219.5	238.2	267.8	307.4	349.0	361.8	330.9	291.3	254.3	234.3
77.5°	148.4	158.7	172.9	191.6	219.6	246.1	257.2	239.4	208.7	185.4	168.8
80°	114.1	119.5	131.6	147.0	169.1	185.9	193.3	181.9	160.4	142.9	130.2
82.5°	81.4	86.7	93.9	106.7	120.8	132.2	140.2	132.5	116.9	103.2	95.8
85°	39.6	43.0	47.0	52.3	63.1	69.8	69.1	64.4	58.4	53.0	49.0
87.5°	14.3	15.2	17.1	20.1	22.1	24.5	25.8	25.0	23.2	21.7	20.2
90°	1.7	3.4	5.2	6.9	8.6	9.5	11.2	12.1	13.8	14.6	15.5
92.5°	12.7	20.0	30.6	45.4	70.5	117.4	196.1	281.5	277.1	224.3	152.3
95°	29.2	36.1	45.5	64.5	103.1	195.1	384.2	621.5	761.6	745.2	618.0
97.5°	48.1	53.0	62.4	79.4	107.3	168.2	306.7	554.9	813.3	942.9	920.4
100°	61.9	65.3	74.7	91.1	116.9	166.8	278.4	495.1	776.1	991.0	1057.2
102.5°	75.6	78.4	88.5	103.5	128.5	173.0	266.8	449.7	710.8	962.2	1103.3
105°	97.1	101.4	110.0	123.8	147.8	185.6	262.2	405.7	623.1	869.9	1076.1
107.5°	120.9	124.9	132.0	146.3	168.0	204.6	270.1	387.1	562.8	775.6	979.1
110°	136.6	140.1	147.8	160.7	183.0	218.3	277.6	381.6	534.6	721.9	907.7





TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	152.5	155.2	163.0	175.8	197.5	231.4	287.2	381.6	518.1	682.1	851.3
115°	175.3	177.9	185.6	198.5	220.1	251.8	301.7	384.2	500.2	638.6	780.4
117.5°	196.8	199.6	207.3	222.0	242.7	272.9	318.2	389.9	491.5	612.7	734.7
120°	210.6	214.0	221.8	236.3	257.9	287.9	329.2	395.4	487.3	598.2	710.0
122.5°	224.3	227.0	234.8	250.8	272.3	302.4	341.6	400.2	483.9	585.8	691.4
125°	242.4	246.7	254.4	270.8	293.1	321.5	358.4	408.3	479.6	569.0	664.4
127.5°	257.5	263.0	272.9	290.2	312.5	339.8	373.8	417.4	477.5	553.5	636.9
130°	266.5	273.4	284.5	302.6	324.9	351.5	384.2	422.9	476.1	543.2	619.7
132.5°	274.0	282.2	294.8	313.6	335.9	362.6	393.1	429.0	476.1	534.9	602.5
135°	285.3	295.7	309.4	327.4	350.7	377.3	405.7	437.5	476.1	525.1	580.1
137.5°	298.6	308.2	322.0	339.7	363.6	387.8	415.0	445.2	477.2	516.4	561.3
140°	306.9	317.2	330.9	347.2	370.5	395.4	421.2	448.7	477.9	512.3	551.0
142.5°	315.8	325.4	339.1	354.8	376.6	400.2	424.6	450.7	478.5	508.9	542.0
145°	330.0	338.6	350.7	366.2	385.9	408.3	429.7	453.0	477.9	503.7	530.3
147.5°	344.5	351.9	363.1	376.4	393.8	413.5	432.8	453.8	475.6	498.3	519.4
150°	354.1	360.2	371.3	383.3	398.0	416.9	434.9	453.8	473.6	494.2	513.2
152.5°	363.1	368.4	378.2	389.5	402.8	420.3	436.3	453.1	470.9	489.4	506.3
155°	374.7	379.9	388.5	397.1	409.1	423.7	437.5	451.3	465.9	481.3	495.9
157.5°	385.9	390.0	397.4	405.0	414.1	426.6	438.3	449.0	460.7	473.7	485.6
160°	392.8	396.2	402.3	409.1	416.9	428.0	438.3	446.9	457.3	467.6	478.7
162.5°	399.0	402.4	407.8	413.3	419.7	429.4	437.6	444.9	453.1	462.1	471.2
165°	407.4	410.0	414.3	417.8	422.9	429.7	436.6	441.8	446.9	453.8	460.7
167.5°	414.5	416.0	418.4	420.9	424.0	429.7	434.5	437.0	440.9	445.7	450.7
170°	418.6	419.5	421.2	422.9	425.4	429.7	433.2	434.9	437.5	440.9	445.2
172.5°	420.7	421.5	423.2	424.2	425.4	429.0	431.8	432.1	433.3	436.1	439.0
175°	423.7	424.6	425.4	425.4	425.4	428.0	429.7	428.9	428.9	429.7	432.3
177.5°	425.6	425.6	426.3	425.6	425.6	427.0	427.7	426.3	426.3	427.0	427.7
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1653.7	1658.0	1667.2	1664.0	1668.3	1670.4	1672.6
5°	1787.3	1808.8	1818.2	1816.9	1830.9	1827.6	1824.2
7.5°	1938.2	1960.8	1973.4	1989.1	1998.2	1998.9	2006.8
10°	2023.6	2053.1	2065.2	2082.0	2092.7	2098.8	2098.1
12.5°	2089.0	2112.2	2139.2	2147.5	2162.0	2169.6	2166.8
15°	2167.9	2204.8	2233.0	2247.0	2265.2	2270.5	2277.9
17.5°	2238.3	2287.8	2320.7	2364.4	2380.9	2391.0	2385.1
20°	2291.4	2356.5	2389.4	2441.7	2470.6	2486.1	2480.6
22.5°	2354.2	2424.7	2485.4	2530.8	2574.7	2595.6	2599.9
25°	2461.9	2558.5	2647.7	2707.5	2761.8	2774.6	2802.8
27.5°	2582.1	2696.0	2791.5	2854.4	2892.2	2906.4	2915.3
30°	2657.8	2771.2	2843.1	2883.3	2895.5	2894.1	2892.7
32.5°	2694.8	2765.9	2779.7	2768.5	2740.8	2717.4	2693.0
35°	2642.4	2589.4	2510.2	2408.1	2333.0	2257.1	2249.8
37.5°	2376.4	2206.9	2075.1	1927.9	1842.9	1790.4	1754.2
40°	2126.2	1933.6	1773.9	1649.8	1563.1	1529.0	1495.4
42.5°	1854.6	1670.5	1529.0	1425.3	1360.2	1322.2	1295.6
45°	1506.8	1344.4	1233.6	1158.5	1106.7	1077.2	1060.4
47.5°	1234.7	1114.6	1020.5	966.2	930.5	907.6	907.7
50°	1088.6	973.9	911.5	868.5	837.6	819.5	822.9
52.5°	959.2	873.5	820.2	784.2	761.4	750.2	749.8
55°	802.0	740.3	705.4	679.2	663.7	651.0	653.8
57.5°	686.0	634.0	610.6	588.9	578.2	573.1	565.7
60°	614.2	573.9	553.7	536.2	525.6	521.5	514.1
62.5°	550.3	518.6	498.9	484.7	475.0	473.7	468.0
65°	462.4	438.2	420.9	414.1	404.1	401.4	401.4
67.5°	381.3	363.9	350.3	344.1	339.8	340.4	337.2
70°	330.2	316.2	307.4	300.7	297.3	298.0	295.3
72.5°	288.9	273.2	265.5	261.5	257.1	258.8	257.7
75°	218.8	210.8	206.7	202.7	200.0	198.6	197.3
77.5°	160.7	153.6	150.5	148.2	148.6	145.3	147.9
80°	124.2	118.1	116.1	112.8	112.1	112.1	111.4
82.5°	90.8	87.5	86.0	83.3	82.1	83.1	81.4
85°	47.0	44.3	43.7	43.7	42.3	41.0	44.3
87.5°	20.4	18.5	18.9	18.3	18.3	17.9	16.9
90°	16.4	17.2	18.9	18.9	18.9	19.8	19.8
92.5°	110.6	83.2	70.5	59.5	57.4	56.2	54.8
95°	487.3	381.6	309.4	248.4	222.7	215.8	202.0
97.5°	828.7	725.7	625.3	572.3	524.1	499.2	488.2
100°	1015.1	926.5	837.2	777.8	716.0	684.2	670.5
102.5°	1129.2	1086.8	1026.2	962.9	918.9	884.2	873.9
105°	1193.9	1231.7	1222.2	1194.7	1166.4	1149.2	1138.8
107.5°	1136.3	1233.4	1278.2	1292.2	1292.0	1286.3	1279.4
110°	1070.9	1192.1	1265.2	1303.9	1320.2	1326.2	1326.2



TEST NUMBER: P333324-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1006.3	1128.9	1215.0	1271.5	1299.6	1314.6	1320.7
115°	913.7	1031.4	1125.1	1192.1	1233.4	1257.5	1268.7
117.5°	849.5	951.0	1036.9	1104.0	1146.6	1170.4	1177.3
120°	813.1	907.7	983.3	1046.9	1088.1	1111.4	1118.3
122.5°	787.0	871.2	942.0	998.8	1036.6	1059.8	1066.0
125°	752.1	826.8	888.7	936.9	972.1	991.0	999.6
127.5°	718.8	788.5	846.4	890.1	921.2	939.1	942.9
130°	695.3	762.4	818.3	861.3	889.6	906.8	912.0
132.5°	673.3	734.2	788.0	831.0	859.4	875.1	881.0
135°	639.5	694.5	743.5	781.3	809.7	825.1	830.3
137.5°	609.2	655.0	696.5	730.4	756.2	770.5	776.1
140°	591.3	630.9	667.0	698.8	721.2	734.0	738.3
142.5°	576.2	610.3	641.5	668.6	687.4	699.6	703.3
145°	557.0	583.6	606.8	627.4	642.0	651.5	655.0
147.5°	541.0	561.5	578.9	595.3	607.0	612.5	614.1
150°	532.0	548.4	563.9	576.7	587.0	590.5	591.3
152.5°	523.1	538.0	550.1	560.9	569.2	572.6	573.4
155°	509.7	521.8	531.2	539.8	545.8	548.4	549.2
157.5°	497.0	506.3	513.7	520.4	525.3	527.7	527.5
160°	487.3	495.9	502.0	508.0	512.3	514.0	513.2
162.5°	479.1	486.3	491.6	496.3	499.9	500.2	500.1
165°	466.7	471.9	476.1	479.6	481.3	481.3	481.3
167.5°	454.7	458.7	461.8	463.5	465.0	464.3	464.2
170°	447.8	450.4	452.1	453.8	454.7	454.7	453.8
172.5°	441.6	443.5	444.5	444.9	446.4	445.1	444.2
175°	432.3	434.0	434.0	434.0	434.9	433.2	432.3
177.5°	428.3	428.3	428.3	427.7	428.3	426.3	426.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3

(END OF REPORT)