

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333306-935

Luminaire Tested: **S125DIP-S1270D590U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333306-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D590U935-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6290.3 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	75	75	75	75	75	75	75	75	75	75	75	71																
	1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	64	64	64	64	64	64	64	64	64	64	64	60																
	2	94	86	80	75	89	82	77	72	74	70	66	66	63	60	59	57	55	55	55	55	55	55	55	55	55	55	55	55	51																
	3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	50	47	47	47	47	47	47	47	47	47	47	47	47	44																
	4	79	68	60	53	74	64	57	52	58	52	48	53	48	44	47	44	41	41	41	41	41	41	41	41	41	41	41	41	38																
	5	72	61	52	46	68	58	50	44	52	46	41	47	42	38	43	39	35	35	35	35	35	35	35	35	35	35	35	35	33																
	6	67	54	46	40	63	52	44	39	47	41	36	43	38	34	39	35	31	31	31	31	31	31	31	31	31	31	31	31	29																
	7	62	49	41	35	58	47	40	34	43	37	32	39	34	30	36	31	28	28	28	28	28	28	28	28	28	28	28	28	26																
	8	58	45	37	31	54	43	36	31	39	33	29	36	31	27	33	28	25	25	25	25	25	25	25	25	25	25	25	25	23																
	9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	23	23	23	23	23	23	23	23	23	23	23	23	21																
	10	50	38	30	25	48	36	29	25	33	27	23	31	25	22	28	24	21	21	21	21	21	21	21	21	21	21	21	21	19																

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10213	10213	10213	10213
5°	11826	10247	8972	10247
10°	13759	10194	7861	10194
15°	15230	10120	7252	10120
20°	17049	10001	6763	10001
25°	19973	9867	6524	9867
30°	21572	9735	6317	9735
35°	17738	9488	6180	9488
40°	12607	9144	6032	9144
45°	9685	8680	5946	8680
50°	8268	8106	5934	8106
55°	7362	7543	5986	7543
60°	6640	6926	6138	6926
65°	6134	6308	6298	6308
70°	5576	5665	6388	5665
75°	4923	4991	6331	4991
80°	4143	4069	5791	4069
85°	3283	2934	4676	2934



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.2	2.4
10°-20°	453.2	7.2
20°-30°	736.0	11.7
30°-40°	897.7	14.3
40°-50°	816.7	13.0
50°-60°	650.5	10.3
60°-70°	453.1	7.2
70°-80°	241.6	3.8
80°-90°	62.3	1.0
90°-100°	176.6	2.8
100°-110°	379.6	6.0
110°-120°	356.2	5.7
120°-130°	288.7	4.6
130°-140°	231.7	3.7
140°-150°	174.8	2.8
150°-160°	123.1	2.0
160°-170°	72.5	1.2
170°-180°	23.6	0.4
0°-30°	1341.4	21.3
0°-40°	2239.2	35.6
0°-60°	3706.4	58.9
0°-90°	4463.4	71.0
90°-120°	912.4	14.5
90°-150°	1607.6	25.6
90°-180°	1827.0	29.0
0°-180°	6290.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1581	1581	1581	1581	1581	
5°	1824	1581	1384	1581	1824	184
15°	2278	1514	1085	1514	2278	652
25°	2803	1385	916	1385	2803	1280
35°	2250	1203	784	1203	2250	1377
45°	1060	950	651	950	1060	849
55°	654	670	532	670	654	589
65°	401	413	412	413	401	398
75°	197	200	254	200	197	212
85°	44	40	63	40	44	51
90°	11	0	11	0	11	9
95°	116	16	116	16	116	164
105°	651	56	651	56	651	647
115°	725	99	725	99	725	708
125°	571	138	571	138	571	517
135°	474	161	474	161	474	368
145°	374	188	374	188	374	238
155°	314	214	314	214	314	146
165°	275	234	275	234	275	79
175°	247	243	247	243	247	24
180°	244	244	244	244	244	



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1672.6	1670.4	1668.3	1664.0	1667.2	1658.0	1653.7	1646.2	1637.1	1633.9	1630.1
5°	1824.2	1827.6	1830.9	1816.9	1818.2	1808.8	1787.3	1769.9	1755.8	1737.7	1724.9
7.5°	2006.8	1998.9	1998.2	1989.1	1973.4	1960.8	1938.2	1909.4	1881.7	1850.0	1823.9
10°	2098.1	2098.8	2092.7	2082.0	2065.2	2053.1	2023.6	1995.4	1961.2	1920.9	1892.0
12.5°	2166.8	2169.6	2162.0	2147.5	2139.2	2112.2	2089.0	2055.6	2014.8	1982.6	1938.7
15°	2277.9	2270.5	2265.2	2247.0	2233.0	2204.8	2167.9	2133.0	2088.7	2047.7	2006.8
17.5°	2385.1	2391.0	2380.9	2364.4	2320.7	2287.8	2238.3	2190.4	2135.3	2080.3	2031.5
20°	2480.6	2486.1	2470.6	2441.7	2389.4	2356.5	2291.4	2229.6	2165.8	2095.4	2041.7
22.5°	2599.9	2595.6	2574.7	2530.8	2485.4	2424.7	2354.2	2279.0	2199.2	2119.5	2048.1
25°	2802.8	2774.6	2761.8	2707.5	2647.7	2558.5	2461.9	2351.7	2252.5	2147.1	2055.8
27.5°	2915.3	2906.4	2892.2	2854.4	2791.5	2696.0	2582.1	2448.0	2307.9	2174.9	2055.4
30°	2892.7	2894.1	2895.5	2883.3	2843.1	2771.2	2657.8	2513.5	2347.1	2197.4	2059.2
32.5°	2693.0	2717.4	2740.8	2768.5	2779.7	2765.9	2694.8	2564.6	2393.2	2223.2	2057.0
35°	2249.8	2257.1	2333.0	2408.1	2510.2	2589.4	2642.4	2584.6	2440.3	2245.1	2054.4
37.5°	1754.2	1790.4	1842.9	1927.9	2075.1	2206.9	2376.4	2454.5	2407.9	2252.2	2049.8
40°	1495.4	1529.0	1563.1	1649.8	1773.9	1933.6	2126.2	2290.7	2328.9	2229.6	2033.7
42.5°	1295.6	1322.2	1360.2	1425.3	1529.0	1670.5	1854.6	2069.5	2201.7	2164.1	1999.8
45°	1060.4	1077.2	1106.7	1158.5	1233.6	1344.4	1506.8	1741.7	1946.4	2014.1	1919.5
47.5°	907.7	907.6	930.5	966.2	1020.5	1114.6	1234.7	1418.8	1637.4	1799.1	1791.7
50°	822.9	819.5	837.6	868.5	911.5	973.9	1088.6	1235.6	1445.7	1628.9	1679.9
52.5°	749.8	750.2	761.4	784.2	820.2	873.5	959.2	1091.7	1271.2	1459.2	1555.4
55°	653.8	651.0	663.7	679.2	705.4	740.3	802.0	903.4	1049.0	1234.2	1359.1
57.5°	565.7	573.1	578.2	588.9	610.6	634.0	686.0	760.4	876.0	1034.9	1166.9
60°	514.1	521.5	525.6	536.2	553.7	573.9	614.2	674.5	771.9	908.8	1039.7
62.5°	468.0	473.7	475.0	484.7	498.9	518.6	550.3	601.0	677.9	797.6	925.8
65°	401.4	401.4	404.1	414.1	420.9	438.2	462.4	499.4	561.1	654.4	763.8
67.5°	337.2	340.4	339.8	344.1	350.3	363.9	381.3	411.7	457.4	525.6	613.0
70°	295.3	298.0	297.3	300.7	307.4	316.2	330.2	359.0	391.9	450.4	525.6
72.5°	257.7	258.8	257.1	261.5	265.5	273.2	288.9	304.3	335.0	384.4	446.1
75°	197.3	198.6	200.0	202.7	206.7	210.8	218.8	234.3	254.3	291.3	330.9
77.5°	147.9	145.3	148.6	148.2	150.5	153.6	160.7	168.8	185.4	208.7	239.4
80°	111.4	112.1	112.1	112.8	116.1	118.1	124.2	130.2	142.9	160.4	181.9
82.5°	81.4	83.1	82.1	83.3	86.0	87.5	90.8	95.8	103.2	116.9	132.5
85°	44.3	41.0	42.3	43.7	43.7	44.3	47.0	49.0	53.0	58.4	64.4
87.5°	15.2	16.2	16.6	16.6	17.2	17.0	19.0	18.9	20.5	22.0	23.9
90°	11.3	11.3	10.8	10.8	10.8	9.8	9.3	8.9	8.4	7.8	6.9
92.5°	31.3	32.1	32.8	34.0	40.3	47.5	63.2	87.0	128.2	158.3	160.9
95°	115.5	123.3	127.2	142.0	176.8	218.1	278.4	353.1	425.9	435.1	355.1
97.5°	279.0	285.2	299.5	327.0	357.3	414.7	473.6	525.9	538.8	464.7	317.1
100°	383.1	391.0	409.1	444.4	478.4	529.4	580.1	604.1	566.3	443.5	282.9
102.5°	499.4	505.3	525.0	550.2	586.4	621.0	645.2	630.4	549.7	406.1	256.9
105°	650.7	656.7	666.5	682.7	698.4	703.8	682.2	614.9	497.1	356.1	231.8
107.5°	731.1	735.0	738.3	738.4	730.4	704.8	649.3	559.5	443.2	321.6	221.2
110°	757.9	757.9	754.4	745.0	723.0	681.2	612.0	518.7	412.6	305.5	218.1



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	754.7	751.1	742.6	726.6	694.3	645.1	575.1	486.5	389.8	296.1	218.1
115°	725.0	718.5	704.8	681.2	642.9	589.4	522.1	445.9	364.9	285.9	219.6
117.5°	672.8	668.8	655.2	630.9	592.5	543.4	485.4	419.8	350.1	280.9	222.7
120°	638.9	635.1	621.8	598.2	561.9	518.7	464.6	405.7	341.8	278.4	225.9
122.5°	609.1	605.5	592.3	570.7	538.3	497.8	449.7	395.1	334.8	276.6	228.7
125°	571.2	566.3	555.5	535.4	507.8	472.5	429.7	379.6	325.1	274.1	233.3
127.5°	538.8	536.6	526.4	508.6	483.7	450.6	410.7	363.9	316.3	272.9	238.5
130°	521.1	518.1	508.3	492.1	467.5	435.7	397.4	354.1	310.4	272.1	241.7
132.5°	503.4	500.1	491.0	474.8	450.3	419.6	384.8	344.3	305.7	272.1	245.2
135°	474.4	471.5	462.6	446.4	424.8	396.8	365.4	331.5	300.1	272.1	249.9
137.5°	443.5	440.2	432.1	417.3	398.0	374.3	348.1	320.7	295.1	272.7	254.4
140°	421.9	419.4	412.1	399.3	381.2	360.5	337.9	314.8	292.7	273.1	256.4
142.5°	401.8	399.8	392.8	382.0	366.6	348.7	329.2	309.7	290.8	273.5	257.5
145°	374.3	372.3	366.9	358.5	346.7	333.5	318.2	303.1	287.8	273.1	258.8
147.5°	350.9	350.0	346.8	340.2	330.8	320.8	309.1	296.8	284.7	271.8	259.3
150°	337.9	337.4	335.4	329.6	322.2	313.3	304.0	293.2	282.4	270.6	259.3
152.5°	327.7	327.2	325.2	320.6	314.4	307.5	298.9	289.3	279.7	269.1	258.9
155°	313.8	313.3	311.9	308.4	303.5	298.1	291.3	283.4	275.0	266.2	257.9
157.5°	301.4	301.5	300.1	297.3	293.5	289.3	284.0	277.5	270.7	263.2	256.6
160°	293.2	293.7	292.7	290.2	286.8	283.4	278.4	273.5	267.2	261.3	255.4
162.5°	285.8	285.9	285.7	283.6	280.9	277.8	273.8	269.2	264.1	258.9	254.3
165°	275.0	275.0	275.0	274.1	272.1	269.7	266.7	263.2	259.3	255.4	252.4
167.5°	265.2	265.3	265.7	264.8	263.8	262.1	259.8	257.5	254.7	251.9	249.7
170°	259.3	259.8	259.8	259.3	258.3	257.4	255.9	254.4	251.9	249.9	248.5
172.5°	253.8	254.3	255.1	254.3	254.0	253.4	252.4	250.9	249.2	247.6	246.9
175°	247.0	247.5	248.5	248.1	248.1	248.1	247.0	247.0	245.6	245.0	245.0
177.5°	243.6	243.6	244.8	244.4	244.8	244.8	244.8	244.4	244.0	243.6	243.6
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1626.9	1623.2	1618.9	1611.4	1602.2	1597.4	1589.8	1585.0	1575.4	1567.3	1558.8
5°	1709.4	1692.0	1675.9	1655.1	1632.3	1617.5	1600.1	1580.6	1560.5	1539.6	1516.8
7.5°	1795.0	1764.1	1730.5	1694.4	1659.1	1626.6	1595.6	1565.1	1536.7	1502.4	1473.3
10°	1852.4	1813.5	1771.9	1722.9	1675.2	1633.7	1591.3	1554.4	1516.8	1476.5	1441.0
12.5°	1909.9	1858.0	1799.2	1745.4	1688.2	1637.9	1588.1	1541.0	1493.7	1449.1	1407.7
15°	1950.4	1904.8	1850.4	1773.9	1709.4	1640.4	1574.6	1513.5	1456.5	1406.8	1354.4
17.5°	1977.1	1918.3	1859.9	1786.5	1702.1	1624.8	1550.2	1480.3	1416.0	1353.1	1302.6
20°	1981.9	1921.6	1860.4	1788.6	1702.1	1613.5	1539.0	1455.1	1386.0	1320.9	1259.1
22.5°	1980.4	1911.9	1845.5	1771.5	1687.0	1605.4	1515.4	1429.9	1354.8	1290.8	1226.3
25°	1965.1	1892.0	1808.8	1734.3	1651.1	1564.5	1473.3	1384.7	1308.1	1234.9	1171.2
27.5°	1952.6	1857.7	1763.4	1676.5	1596.2	1516.8	1429.4	1338.7	1253.9	1179.7	1119.6
30°	1937.0	1833.0	1726.9	1636.3	1553.8	1476.5	1394.0	1305.4	1216.9	1144.4	1080.0
32.5°	1923.0	1801.8	1689.9	1591.2	1503.8	1428.7	1352.6	1268.3	1181.4	1107.8	1043.4
35°	1896.1	1755.8	1627.5	1516.1	1422.9	1345.7	1281.9	1203.4	1123.5	1052.4	990.7
37.5°	1861.8	1695.4	1557.8	1441.0	1338.7	1257.4	1198.0	1137.7	1061.1	992.6	936.7
40°	1835.0	1652.4	1506.8	1387.3	1281.3	1196.7	1141.7	1084.6	1020.9	957.1	898.0
42.5°	1801.1	1613.8	1455.3	1326.6	1221.7	1139.3	1081.5	1033.0	976.8	917.4	862.5
45°	1739.0	1543.7	1371.8	1233.6	1127.6	1046.4	986.6	950.4	908.1	851.7	805.4
47.5°	1647.6	1459.5	1281.8	1139.1	1029.7	954.4	898.5	863.7	833.9	791.9	749.9
50°	1566.5	1396.7	1216.9	1075.2	965.8	889.9	838.3	806.8	781.3	749.0	713.4
52.5°	1475.8	1317.8	1153.0	1013.0	904.6	829.8	779.2	751.5	730.2	707.1	672.1
55°	1331.6	1197.4	1044.3	911.5	811.4	738.3	694.0	669.9	652.4	634.9	613.5
57.5°	1172.8	1067.8	932.3	810.8	718.7	652.1	610.8	587.3	573.7	564.7	552.1
60°	1061.1	971.2	854.4	743.6	653.8	594.7	554.4	536.2	524.9	517.5	508.1
62.5°	957.5	883.6	775.5	674.4	595.7	539.8	503.9	486.3	475.4	471.8	464.1
65°	804.7	747.7	658.4	574.5	507.4	459.8	429.6	412.8	406.0	402.0	402.7
67.5°	654.3	619.5	547.8	476.2	422.7	382.7	358.5	345.7	342.3	336.9	336.8
70°	562.4	536.2	475.9	413.5	365.8	334.9	313.4	300.0	296.6	293.9	293.3
72.5°	481.4	458.4	406.0	356.0	313.1	286.0	268.4	260.3	254.8	253.1	253.0
75°	361.8	349.0	307.4	267.8	238.2	219.5	207.4	200.0	196.0	195.3	196.0
77.5°	257.2	246.1	219.6	191.6	172.9	158.7	148.4	145.9	141.4	141.5	140.8
80°	193.3	185.9	169.1	147.0	131.6	119.5	114.1	109.4	108.1	106.1	108.1
82.5°	140.2	132.2	120.8	106.7	93.9	86.7	81.4	79.9	79.0	78.1	78.5
85°	69.1	69.8	63.1	52.3	47.0	43.0	39.6	39.6	38.9	38.2	38.9
87.5°	24.9	23.6	21.4	19.5	16.7	14.9	14.1	14.6	13.1	12.7	13.5
90°	6.4	5.4	4.9	4.0	2.9	2.0	0.9	0.5	0.9	2.0	2.9
92.5°	112.1	67.1	40.3	25.9	17.5	11.4	7.2	6.0	7.2	11.4	17.5
95°	219.6	111.5	59.0	36.9	26.0	20.7	16.7	16.2	16.7	20.7	26.0
97.5°	175.2	96.1	61.3	45.4	35.6	30.2	27.5	26.9	27.5	30.2	35.6
100°	159.1	95.3	66.8	52.1	42.7	37.4	35.4	34.4	35.4	37.4	42.7
102.5°	152.5	98.8	73.4	59.2	50.6	44.8	43.2	42.6	43.2	44.8	50.6
105°	149.8	106.1	84.5	70.7	62.9	57.9	55.5	55.5	55.5	57.9	62.9
107.5°	154.3	116.9	96.0	83.6	75.4	71.4	69.1	68.1	69.1	71.4	75.4
110°	158.6	124.8	104.6	91.9	84.5	80.1	78.1	77.1	78.1	80.1	84.5



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	164.1	132.2	112.9	100.5	93.2	88.7	87.1	86.2	87.1	88.7	93.2
115°	172.4	143.9	125.7	113.5	106.1	101.7	100.2	99.2	100.2	101.7	106.1
117.5°	181.8	155.9	138.7	126.8	118.5	114.1	112.4	111.0	112.4	114.1	118.5
120°	188.1	164.5	147.3	135.1	126.7	122.3	120.4	118.8	120.4	122.3	126.7
122.5°	195.2	172.8	155.6	143.4	134.1	129.8	128.2	127.1	128.2	129.8	134.1
125°	204.8	183.7	167.5	154.7	145.3	140.9	138.5	137.5	138.5	140.9	145.3
127.5°	213.6	194.2	178.6	165.8	155.9	150.3	147.1	145.7	147.1	150.3	155.9
130°	219.6	200.9	185.6	172.9	162.6	156.2	152.2	150.8	152.2	156.2	162.6
132.5°	224.6	207.2	191.9	179.2	168.5	161.3	156.6	154.7	156.6	161.3	168.5
135°	231.8	215.6	200.4	187.1	176.8	168.9	163.1	161.1	163.1	168.9	176.8
137.5°	237.1	221.6	207.8	194.1	184.0	176.2	170.7	169.2	170.7	176.2	184.0
140°	240.6	225.9	211.7	198.5	189.1	181.2	175.3	173.8	175.3	181.2	189.1
142.5°	242.6	228.7	215.2	202.8	193.8	186.0	180.5	179.3	180.5	186.0	193.8
145°	245.6	233.3	220.5	209.2	200.4	193.5	188.6	187.6	188.6	193.5	200.4
147.5°	247.4	236.3	225.1	215.1	207.4	201.0	196.8	196.2	196.8	201.0	207.4
150°	248.5	238.2	227.4	219.0	212.2	205.8	202.3	201.4	202.3	205.8	212.2
152.5°	249.3	240.1	230.1	222.6	216.1	210.5	207.4	206.9	207.4	210.5	216.1
155°	249.9	242.1	233.8	226.9	222.0	217.1	214.1	214.1	214.1	217.1	222.0
157.5°	250.5	243.8	236.6	231.4	227.1	222.9	220.5	220.6	220.5	222.9	227.1
160°	250.5	244.6	238.2	233.8	229.9	226.4	224.5	225.0	224.5	226.4	229.9
162.5°	250.1	245.4	239.8	236.2	233.0	230.0	228.0	228.5	228.0	230.0	233.0
165°	249.5	245.6	241.7	238.7	236.7	234.3	232.8	233.8	232.8	234.3	236.7
167.5°	248.3	245.6	242.3	240.5	239.1	237.7	236.9	237.3	236.9	237.7	239.1
170°	247.5	245.6	243.1	241.7	240.6	239.7	239.2	239.7	239.2	239.7	240.6
172.5°	246.8	245.2	243.1	242.5	241.9	240.8	240.4	241.3	240.4	240.8	241.9
175°	245.6	244.6	243.1	243.1	243.1	242.6	242.1	243.1	242.1	242.6	243.1
177.5°	244.4	244.0	243.2	243.2	243.6	243.2	243.2	244.0	243.2	243.2	243.6
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1553.8	1548.0	1543.2	1532.4	1526.5	1518.5	1512.0	1519.0	1511.5	1514.7	1509.8
5°	1505.5	1486.6	1473.3	1453.7	1437.0	1421.5	1410.1	1408.1	1402.7	1400.1	1392.0
7.5°	1447.2	1423.7	1400.6	1375.1	1353.6	1331.7	1317.8	1306.2	1298.6	1288.5	1281.7
10°	1412.8	1381.3	1354.4	1323.5	1296.7	1273.2	1254.4	1245.0	1236.3	1223.6	1218.8
12.5°	1370.4	1337.7	1305.0	1272.0	1246.2	1220.0	1203.9	1189.7	1183.7	1169.3	1167.9
15°	1319.5	1270.5	1238.3	1204.7	1169.2	1147.7	1134.3	1118.9	1112.2	1102.1	1094.7
17.5°	1258.9	1215.0	1174.8	1140.1	1109.6	1091.5	1074.8	1064.2	1052.7	1046.1	1034.0
20°	1214.8	1173.2	1132.9	1096.1	1072.5	1051.7	1038.3	1028.2	1016.2	1012.8	1000.7
22.5°	1177.8	1131.9	1093.2	1062.2	1036.6	1013.1	998.6	991.7	983.4	973.1	970.6
25°	1117.5	1069.9	1037.0	1006.1	983.3	961.8	951.7	943.0	935.0	927.6	924.9
27.5°	1065.4	1022.9	983.8	955.9	936.0	916.4	907.6	897.0	891.0	885.1	877.9
30°	1028.9	985.2	951.1	924.2	902.8	885.3	875.9	868.5	863.2	857.7	853.8
32.5°	991.4	950.9	917.7	891.5	870.0	856.8	848.5	843.3	837.3	830.9	825.8
35°	941.7	897.3	865.1	842.3	825.5	815.5	806.1	801.3	794.7	794.7	789.3
37.5°	885.7	847.4	819.0	798.1	783.1	774.1	764.0	760.7	756.4	753.5	751.7
40°	852.4	816.8	790.0	769.1	753.0	745.6	737.6	732.3	729.5	726.2	724.9
42.5°	818.0	784.0	758.3	739.1	725.1	718.8	711.3	707.6	702.1	697.8	697.0
45°	765.8	732.9	709.5	694.0	681.9	674.5	669.9	661.8	659.1	653.8	653.1
47.5°	716.3	684.8	661.7	649.0	638.4	632.4	625.0	616.9	613.9	611.1	610.9
50°	679.2	650.4	628.9	616.8	606.7	598.1	590.6	585.2	583.2	583.2	584.6
52.5°	641.6	617.1	598.8	584.0	574.5	565.2	558.4	555.2	552.1	555.3	557.8
55°	586.6	561.8	548.4	534.3	524.9	514.1	510.7	509.5	507.4	512.8	515.5
57.5°	528.3	510.9	495.2	481.2	472.8	466.6	462.0	461.2	465.0	467.5	476.2
60°	491.3	471.1	457.1	446.3	436.3	432.2	430.9	429.6	432.2	439.6	451.0
62.5°	450.5	434.1	419.0	410.9	403.5	396.8	396.5	397.4	402.7	411.1	422.6
65°	390.6	376.5	366.4	357.1	351.0	347.0	348.4	351.0	357.1	368.5	381.3
67.5°	329.8	320.1	311.2	303.5	297.7	297.7	299.1	303.1	310.2	323.4	335.0
70°	290.6	279.9	272.5	269.1	264.4	261.7	265.8	272.5	278.5	290.6	300.7
72.5°	251.4	242.3	236.5	234.3	232.2	230.1	231.4	238.7	246.8	258.9	270.6
75°	193.3	189.9	185.9	183.2	181.2	182.5	183.9	190.6	197.3	210.1	223.5
77.5°	141.1	137.6	135.2	134.5	133.5	134.1	137.8	142.8	149.4	158.7	168.8
80°	106.7	105.4	104.0	103.3	103.3	104.0	109.4	112.8	118.8	127.5	135.6
82.5°	77.7	76.9	76.6	76.5	77.1	77.1	80.4	84.8	89.8	96.3	103.3
85°	41.0	39.6	41.6	42.3	41.0	43.0	44.3	47.0	49.0	52.3	55.7
87.5°	14.2	15.5	15.1	15.8	15.8	17.1	16.7	18.9	20.1	21.3	20.9
90°	4.0	4.9	5.4	6.4	6.9	7.8	8.4	8.9	9.3	9.8	10.8
92.5°	25.9	40.3	67.1	112.1	160.9	158.3	128.2	87.0	63.2	47.5	40.3
95°	36.9	59.0	111.5	219.6	355.1	435.1	425.9	353.1	278.4	218.1	176.8
97.5°	45.4	61.3	96.1	175.2	317.1	464.7	538.8	525.9	473.6	414.7	357.3
100°	52.1	66.8	95.3	159.1	282.9	443.5	566.3	604.1	580.1	529.4	478.4
102.5°	59.2	73.4	98.8	152.5	256.9	406.1	549.7	630.4	645.2	621.0	586.4
105°	70.7	84.5	106.1	149.8	231.8	356.1	497.1	614.9	682.2	703.8	698.4
107.5°	83.6	96.0	116.9	154.3	221.2	321.6	443.2	559.5	649.3	704.8	730.4
110°	91.9	104.6	124.8	158.6	218.1	305.5	412.6	518.7	612.0	681.2	723.0



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	100.5	112.9	132.2	164.1	218.1	296.1	389.8	486.5	575.1	645.1	694.3
115°	113.5	125.7	143.9	172.4	219.6	285.9	364.9	445.9	522.1	589.4	642.9
117.5°	126.8	138.7	155.9	181.8	222.7	280.9	350.1	419.8	485.4	543.4	592.5
120°	135.1	147.3	164.5	188.1	225.9	278.4	341.8	405.7	464.6	518.7	561.9
122.5°	143.4	155.6	172.8	195.2	228.7	276.6	334.8	395.1	449.7	497.8	538.3
125°	154.7	167.5	183.7	204.8	233.3	274.1	325.1	379.6	429.7	472.5	507.8
127.5°	165.8	178.6	194.2	213.6	238.5	272.9	316.3	363.9	410.7	450.6	483.7
130°	172.9	185.6	200.9	219.6	241.7	272.1	310.4	354.1	397.4	435.7	467.5
132.5°	179.2	191.9	207.2	224.6	245.2	272.1	305.7	344.3	384.8	419.6	450.3
135°	187.1	200.4	215.6	231.8	249.9	272.1	300.1	331.5	365.4	396.8	424.8
137.5°	194.1	207.8	221.6	237.1	254.4	272.7	295.1	320.7	348.1	374.3	398.0
140°	198.5	211.7	225.9	240.6	256.4	273.1	292.7	314.8	337.9	360.5	381.2
142.5°	202.8	215.2	228.7	242.6	257.5	273.5	290.8	309.7	329.2	348.7	366.6
145°	209.2	220.5	233.3	245.6	258.8	273.1	287.8	303.1	318.2	333.5	346.7
147.5°	215.1	225.1	236.3	247.4	259.3	271.8	284.7	296.8	309.1	320.8	330.8
150°	219.0	227.4	238.2	248.5	259.3	270.6	282.4	293.2	304.0	313.3	322.2
152.5°	222.6	230.1	240.1	249.3	258.9	269.1	279.7	289.3	298.9	307.5	314.4
155°	226.9	233.8	242.1	249.9	257.9	266.2	275.0	283.4	291.3	298.1	303.5
157.5°	231.4	236.6	243.8	250.5	256.6	263.2	270.7	277.5	284.0	289.3	293.5
160°	233.8	238.2	244.6	250.5	255.4	261.3	267.2	273.5	278.4	283.4	286.8
162.5°	236.2	239.8	245.4	250.1	254.3	258.9	264.1	269.2	273.8	277.8	280.9
165°	238.7	241.7	245.6	249.5	252.4	255.4	259.3	263.2	266.7	269.7	272.1
167.5°	240.5	242.3	245.6	248.3	249.7	251.9	254.7	257.5	259.8	262.1	263.8
170°	241.7	243.1	245.6	247.5	248.5	249.9	251.9	254.4	255.9	257.4	258.3
172.5°	242.5	243.1	245.2	246.8	246.9	247.6	249.2	250.9	252.4	253.4	254.0
175°	243.1	243.1	244.6	245.6	245.0	245.0	245.6	247.0	247.0	248.1	248.1
177.5°	243.2	243.2	244.0	244.4	243.6	243.6	244.0	244.4	244.8	244.8	244.8
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1506.7	1510.4	1507.2	1511.5	1507.2	1510.4	1506.7	1509.8	1514.7	1511.5	1519.0
5°	1388.6	1382.6	1386.6	1384.0	1386.6	1382.6	1388.6	1392.0	1400.1	1402.7	1408.1
7.5°	1279.6	1273.8	1267.3	1264.2	1267.3	1273.8	1279.6	1281.7	1288.5	1298.6	1306.2
10°	1211.4	1204.1	1203.4	1198.7	1203.4	1204.1	1211.4	1218.8	1223.6	1236.3	1245.0
12.5°	1161.5	1154.7	1147.0	1145.0	1147.0	1154.7	1161.5	1167.9	1169.3	1183.7	1189.7
15°	1090.6	1085.3	1080.6	1084.6	1080.6	1085.3	1090.6	1094.7	1102.1	1112.2	1118.9
17.5°	1031.7	1027.3	1026.5	1021.5	1026.5	1027.3	1031.7	1034.0	1046.1	1052.7	1064.2
20°	994.7	991.4	992.6	984.0	992.6	991.4	994.7	1000.7	1012.8	1016.2	1028.2
22.5°	965.2	958.6	957.8	956.1	957.8	958.6	965.2	970.6	973.1	983.4	991.7
25°	918.9	915.5	912.1	915.5	912.1	915.5	918.9	924.9	927.6	935.0	943.0
27.5°	878.4	874.4	873.5	873.8	873.5	874.4	878.4	877.9	885.1	891.0	897.0
30°	853.8	847.1	847.7	847.1	847.7	847.1	853.8	853.8	857.7	863.2	868.5
32.5°	826.9	822.3	821.4	820.2	821.4	822.3	826.9	825.8	830.9	837.3	843.3
35°	787.3	787.3	783.9	783.9	783.9	787.3	787.3	789.3	794.7	794.7	801.3
37.5°	750.1	749.4	747.4	747.7	747.4	749.4	750.1	751.7	753.5	756.4	760.7
40°	722.2	721.5	719.5	715.5	719.5	721.5	722.2	724.9	726.2	729.5	732.3
42.5°	695.3	693.0	692.1	690.8	692.1	693.0	695.3	697.0	697.8	702.1	707.6
45°	653.1	653.1	651.7	651.0	651.7	653.1	653.1	653.1	653.8	659.1	661.8
47.5°	612.0	613.2	615.7	615.4	615.7	613.2	612.0	610.9	611.1	613.9	616.9
50°	587.3	588.0	590.0	590.6	590.0	588.0	587.3	584.6	583.2	583.2	585.2
52.5°	559.9	563.8	566.4	565.9	566.4	563.8	559.9	557.8	555.3	552.1	555.2
55°	521.5	526.2	530.9	531.6	530.9	526.2	521.5	515.5	512.8	507.4	509.5
57.5°	483.5	490.1	495.1	496.6	495.1	490.1	483.5	476.2	467.5	465.0	461.2
60°	457.7	466.5	472.5	475.2	472.5	466.5	457.7	451.0	439.6	432.2	429.6
62.5°	433.0	442.8	448.8	449.4	448.8	442.8	433.0	422.6	411.1	402.7	397.4
65°	392.6	402.7	408.0	412.1	408.0	402.7	392.6	381.3	368.5	357.1	351.0
67.5°	349.1	359.2	365.2	368.3	365.2	359.2	349.1	335.0	323.4	310.2	303.1
70°	317.5	327.5	335.6	338.3	335.6	327.5	317.5	300.7	290.6	278.5	272.5
72.5°	286.3	295.3	301.8	305.0	301.8	295.3	286.3	270.6	258.9	246.8	238.7
75°	232.2	244.3	250.4	253.7	250.4	244.3	232.2	223.5	210.1	197.3	190.6
77.5°	179.1	190.1	193.7	195.4	193.7	190.1	179.1	168.8	158.7	149.4	142.8
80°	143.6	150.3	155.1	155.7	155.1	150.3	143.6	135.6	127.5	118.8	112.8
82.5°	110.4	116.0	117.4	119.2	117.4	116.0	110.4	103.3	96.3	89.8	84.8
85°	60.4	63.1	63.8	63.1	63.8	63.1	60.4	55.7	52.3	49.0	47.0
87.5°	22.0	21.5	21.6	22.6	21.6	21.5	22.0	20.9	21.3	20.1	18.9
90°	10.8	10.8	11.3	11.3	11.3	10.8	10.8	10.8	9.8	9.3	8.9
92.5°	34.0	32.8	32.1	31.3	32.1	32.8	34.0	40.3	47.5	63.2	87.0
95°	142.0	127.2	123.3	115.5	123.3	127.2	142.0	176.8	218.1	278.4	353.1
97.5°	327.0	299.5	285.2	279.0	285.2	299.5	327.0	357.3	414.7	473.6	525.9
100°	444.4	409.1	391.0	383.1	391.0	409.1	444.4	478.4	529.4	580.1	604.1
102.5°	550.2	525.0	505.3	499.4	505.3	525.0	550.2	586.4	621.0	645.2	630.4
105°	682.7	666.5	656.7	650.7	656.7	666.5	682.7	698.4	703.8	682.2	614.9
107.5°	738.4	738.3	735.0	731.1	735.0	738.3	738.4	730.4	704.8	649.3	559.5
110°	745.0	754.4	757.9	757.9	757.9	754.4	745.0	723.0	681.2	612.0	518.7



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	726.6	742.6	751.1	754.7	751.1	742.6	726.6	694.3	645.1	575.1	486.5
115°	681.2	704.8	718.5	725.0	718.5	704.8	681.2	642.9	589.4	522.1	445.9
117.5°	630.9	655.2	668.8	672.8	668.8	655.2	630.9	592.5	543.4	485.4	419.8
120°	598.2	621.8	635.1	638.9	635.1	621.8	598.2	561.9	518.7	464.6	405.7
122.5°	570.7	592.3	605.5	609.1	605.5	592.3	570.7	538.3	497.8	449.7	395.1
125°	535.4	555.5	566.3	571.2	566.3	555.5	535.4	507.8	472.5	429.7	379.6
127.5°	508.6	526.4	536.6	538.8	536.6	526.4	508.6	483.7	450.6	410.7	363.9
130°	492.1	508.3	518.1	521.1	518.1	508.3	492.1	467.5	435.7	397.4	354.1
132.5°	474.8	491.0	500.1	503.4	500.1	491.0	474.8	450.3	419.6	384.8	344.3
135°	446.4	462.6	471.5	474.4	471.5	462.6	446.4	424.8	396.8	365.4	331.5
137.5°	417.3	432.1	440.2	443.5	440.2	432.1	417.3	398.0	374.3	348.1	320.7
140°	399.3	412.1	419.4	421.9	419.4	412.1	399.3	381.2	360.5	337.9	314.8
142.5°	382.0	392.8	399.8	401.8	399.8	392.8	382.0	366.6	348.7	329.2	309.7
145°	358.5	366.9	372.3	374.3	372.3	366.9	358.5	346.7	333.5	318.2	303.1
147.5°	340.2	346.8	350.0	350.9	350.0	346.8	340.2	330.8	320.8	309.1	296.8
150°	329.6	335.4	337.4	337.9	337.4	335.4	329.6	322.2	313.3	304.0	293.2
152.5°	320.6	325.2	327.2	327.7	327.2	325.2	320.6	314.4	307.5	298.9	289.3
155°	308.4	311.9	313.3	313.8	313.3	311.9	308.4	303.5	298.1	291.3	283.4
157.5°	297.3	300.1	301.5	301.4	301.5	300.1	297.3	293.5	289.3	284.0	277.5
160°	290.2	292.7	293.7	293.2	293.7	292.7	290.2	286.8	283.4	278.4	273.5
162.5°	283.6	285.7	285.9	285.8	285.9	285.7	283.6	280.9	277.8	273.8	269.2
165°	274.1	275.0	275.0	275.0	275.0	275.0	274.1	272.1	269.7	266.7	263.2
167.5°	264.8	265.7	265.3	265.2	265.3	265.7	264.8	263.8	262.1	259.8	257.5
170°	259.3	259.8	259.8	259.3	259.8	259.8	259.3	258.3	257.4	255.9	254.4
172.5°	254.3	255.1	254.3	253.8	254.3	255.1	254.3	254.0	253.4	252.4	250.9
175°	248.1	248.5	247.5	247.0	247.5	248.5	248.1	248.1	248.1	247.0	247.0
177.5°	244.4	244.8	243.6	243.6	243.6	244.8	244.4	244.8	244.8	244.8	244.4
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1512.0	1518.5	1526.5	1532.4	1543.2	1548.0	1553.8	1558.8	1567.3	1575.4	1585.0
5°	1410.1	1421.5	1437.0	1453.7	1473.3	1486.6	1505.5	1516.8	1539.6	1560.5	1580.6
7.5°	1317.8	1331.7	1353.6	1375.1	1400.6	1423.7	1447.2	1473.3	1502.4	1536.7	1565.1
10°	1254.4	1273.2	1296.7	1323.5	1354.4	1381.3	1412.8	1441.0	1476.5	1516.8	1554.4
12.5°	1203.9	1220.0	1246.2	1272.0	1305.0	1337.7	1370.4	1407.7	1449.1	1493.7	1541.0
15°	1134.3	1147.7	1169.2	1204.7	1238.3	1270.5	1319.5	1354.4	1406.8	1456.5	1513.5
17.5°	1074.8	1091.5	1109.6	1140.1	1174.8	1215.0	1258.9	1302.6	1353.1	1416.0	1480.3
20°	1038.3	1051.7	1072.5	1096.1	1132.9	1173.2	1214.8	1259.1	1320.9	1386.0	1455.1
22.5°	998.6	1013.1	1036.6	1062.2	1093.2	1131.9	1177.8	1226.3	1290.8	1354.8	1429.9
25°	951.7	961.8	983.3	1006.1	1037.0	1069.9	1117.5	1171.2	1234.9	1308.1	1384.7
27.5°	907.6	916.4	936.0	955.9	983.8	1022.9	1065.4	1119.6	1179.7	1253.9	1338.7
30°	875.9	885.3	902.8	924.2	951.1	985.2	1028.9	1080.0	1144.4	1216.9	1305.4
32.5°	848.5	856.8	870.0	891.5	917.7	950.9	991.4	1043.4	1107.8	1181.4	1268.3
35°	806.1	815.5	825.5	842.3	865.1	897.3	941.7	990.7	1052.4	1123.5	1203.4
37.5°	764.0	774.1	783.1	798.1	819.0	847.4	885.7	936.7	992.6	1061.1	1137.7
40°	737.6	745.6	753.0	769.1	790.0	816.8	852.4	898.0	957.1	1020.9	1084.6
42.5°	711.3	718.8	725.1	739.1	758.3	784.0	818.0	862.5	917.4	976.8	1033.0
45°	669.9	674.5	681.9	694.0	709.5	732.9	765.8	805.4	851.7	908.1	950.4
47.5°	625.0	632.4	638.4	649.0	661.7	684.8	716.3	749.9	791.9	833.9	863.7
50°	590.6	598.1	606.7	616.8	628.9	650.4	679.2	713.4	749.0	781.3	806.8
52.5°	558.4	565.2	574.5	584.0	598.8	617.1	641.6	672.1	707.1	730.2	751.5
55°	510.7	514.1	524.9	534.3	548.4	561.8	586.6	613.5	634.9	652.4	669.9
57.5°	462.0	466.6	472.8	481.2	495.2	510.9	528.3	552.1	564.7	573.7	587.3
60°	430.9	432.2	436.3	446.3	457.1	471.1	491.3	508.1	517.5	524.9	536.2
62.5°	396.5	396.8	403.5	410.9	419.0	434.1	450.5	464.1	471.8	475.4	486.3
65°	348.4	347.0	351.0	357.1	366.4	376.5	390.6	402.7	402.0	406.0	412.8
67.5°	299.1	297.7	297.7	303.5	311.2	320.1	329.8	336.8	336.9	342.3	345.7
70°	265.8	261.7	264.4	269.1	272.5	279.9	290.6	293.3	293.9	296.6	300.0
72.5°	231.4	230.1	232.2	234.3	236.5	242.3	251.4	253.0	253.1	254.8	260.3
75°	183.9	182.5	181.2	183.2	185.9	189.9	193.3	196.0	195.3	196.0	200.0
77.5°	137.8	134.1	133.5	134.5	135.2	137.6	141.1	140.8	141.5	141.4	145.9
80°	109.4	104.0	103.3	103.3	104.0	105.4	106.7	108.1	106.1	108.1	109.4
82.5°	80.4	77.1	77.1	76.5	76.6	76.9	77.7	78.5	78.1	79.0	79.9
85°	44.3	43.0	41.0	42.3	41.6	39.6	41.0	38.9	38.2	38.9	39.6
87.5°	16.7	17.1	15.8	15.8	15.1	15.5	14.2	13.5	12.7	13.1	14.6
90°	8.4	7.8	6.9	6.4	5.4	4.9	4.0	2.9	2.0	0.9	0.5
92.5°	128.2	158.3	160.9	112.1	67.1	40.3	25.9	17.5	11.4	7.2	6.0
95°	425.9	435.1	355.1	219.6	111.5	59.0	36.9	26.0	20.7	16.7	16.2
97.5°	538.8	464.7	317.1	175.2	96.1	61.3	45.4	35.6	30.2	27.5	26.9
100°	566.3	443.5	282.9	159.1	95.3	66.8	52.1	42.7	37.4	35.4	34.4
102.5°	549.7	406.1	256.9	152.5	98.8	73.4	59.2	50.6	44.8	43.2	42.6
105°	497.1	356.1	231.8	149.8	106.1	84.5	70.7	62.9	57.9	55.5	55.5
107.5°	443.2	321.6	221.2	154.3	116.9	96.0	83.6	75.4	71.4	69.1	68.1
110°	412.6	305.5	218.1	158.6	124.8	104.6	91.9	84.5	80.1	78.1	77.1



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	389.8	296.1	218.1	164.1	132.2	112.9	100.5	93.2	88.7	87.1	86.2
115°	364.9	285.9	219.6	172.4	143.9	125.7	113.5	106.1	101.7	100.2	99.2
117.5°	350.1	280.9	222.7	181.8	155.9	138.7	126.8	118.5	114.1	112.4	111.0
120°	341.8	278.4	225.9	188.1	164.5	147.3	135.1	126.7	122.3	120.4	118.8
122.5°	334.8	276.6	228.7	195.2	172.8	155.6	143.4	134.1	129.8	128.2	127.1
125°	325.1	274.1	233.3	204.8	183.7	167.5	154.7	145.3	140.9	138.5	137.5
127.5°	316.3	272.9	238.5	213.6	194.2	178.6	165.8	155.9	150.3	147.1	145.7
130°	310.4	272.1	241.7	219.6	200.9	185.6	172.9	162.6	156.2	152.2	150.8
132.5°	305.7	272.1	245.2	224.6	207.2	191.9	179.2	168.5	161.3	156.6	154.7
135°	300.1	272.1	249.9	231.8	215.6	200.4	187.1	176.8	168.9	163.1	161.1
137.5°	295.1	272.7	254.4	237.1	221.6	207.8	194.1	184.0	176.2	170.7	169.2
140°	292.7	273.1	256.4	240.6	225.9	211.7	198.5	189.1	181.2	175.3	173.8
142.5°	290.8	273.5	257.5	242.6	228.7	215.2	202.8	193.8	186.0	180.5	179.3
145°	287.8	273.1	258.8	245.6	233.3	220.5	209.2	200.4	193.5	188.6	187.6
147.5°	284.7	271.8	259.3	247.4	236.3	225.1	215.1	207.4	201.0	196.8	196.2
150°	282.4	270.6	259.3	248.5	238.2	227.4	219.0	212.2	205.8	202.3	201.4
152.5°	279.7	269.1	258.9	249.3	240.1	230.1	222.6	216.1	210.5	207.4	206.9
155°	275.0	266.2	257.9	249.9	242.1	233.8	226.9	222.0	217.1	214.1	214.1
157.5°	270.7	263.2	256.6	250.5	243.8	236.6	231.4	227.1	222.9	220.5	220.6
160°	267.2	261.3	255.4	250.5	244.6	238.2	233.8	229.9	226.4	224.5	225.0
162.5°	264.1	258.9	254.3	250.1	245.4	239.8	236.2	233.0	230.0	228.0	228.5
165°	259.3	255.4	252.4	249.5	245.6	241.7	238.7	236.7	234.3	232.8	233.8
167.5°	254.7	251.9	249.7	248.3	245.6	242.3	240.5	239.1	237.7	236.9	237.3
170°	251.9	249.9	248.5	247.5	245.6	243.1	241.7	240.6	239.7	239.2	239.7
172.5°	249.2	247.6	246.9	246.8	245.2	243.1	242.5	241.9	240.8	240.4	241.3
175°	245.6	245.0	245.0	245.6	244.6	243.1	243.1	243.1	242.6	242.1	243.1
177.5°	244.0	243.6	243.6	244.4	244.0	243.2	243.2	243.6	243.2	243.2	244.0
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1589.8	1597.4	1602.2	1611.4	1618.9	1623.2	1626.9	1630.1	1633.9	1637.1	1646.2
5°	1600.1	1617.5	1632.3	1655.1	1675.9	1692.0	1709.4	1724.9	1737.7	1755.8	1769.9
7.5°	1595.6	1626.6	1659.1	1694.4	1730.5	1764.1	1795.0	1823.9	1850.0	1881.7	1909.4
10°	1591.3	1633.7	1675.2	1722.9	1771.9	1813.5	1852.4	1892.0	1920.9	1961.2	1995.4
12.5°	1588.1	1637.9	1688.2	1745.4	1799.2	1858.0	1909.9	1938.7	1982.6	2014.8	2055.6
15°	1574.6	1640.4	1709.4	1773.9	1850.4	1904.8	1950.4	2006.8	2047.7	2088.7	2133.0
17.5°	1550.2	1624.8	1702.1	1786.5	1859.9	1918.3	1977.1	2031.5	2080.3	2135.3	2190.4
20°	1539.0	1613.5	1702.1	1788.6	1860.4	1921.6	1981.9	2041.7	2095.4	2165.8	2229.6
22.5°	1515.4	1605.4	1687.0	1771.5	1845.5	1911.9	1980.4	2048.1	2119.5	2199.2	2279.0
25°	1473.3	1564.5	1651.1	1734.3	1808.8	1892.0	1965.1	2055.8	2147.1	2252.5	2351.7
27.5°	1429.4	1516.8	1596.2	1676.5	1763.4	1857.7	1952.6	2055.4	2174.9	2307.9	2448.0
30°	1394.0	1476.5	1553.8	1636.3	1726.9	1833.0	1937.0	2059.2	2197.4	2347.1	2513.5
32.5°	1352.6	1428.7	1503.8	1591.2	1689.9	1801.8	1923.0	2057.0	2223.2	2393.2	2564.6
35°	1281.9	1345.7	1422.9	1516.1	1627.5	1755.8	1896.1	2054.4	2245.1	2440.3	2584.6
37.5°	1198.0	1257.4	1338.7	1441.0	1557.8	1695.4	1861.8	2049.8	2252.2	2407.9	2454.5
40°	1141.7	1196.7	1281.3	1387.3	1506.8	1652.4	1835.0	2033.7	2229.6	2328.9	2290.7
42.5°	1081.5	1139.3	1221.7	1326.6	1455.3	1613.8	1801.1	1999.8	2164.1	2201.7	2069.5
45°	986.6	1046.4	1127.6	1233.6	1371.8	1543.7	1739.0	1919.5	2014.1	1946.4	1741.7
47.5°	898.5	954.4	1029.7	1139.1	1281.8	1459.5	1647.6	1791.7	1799.1	1637.4	1418.8
50°	838.3	889.9	965.8	1075.2	1216.9	1396.7	1566.5	1679.9	1628.9	1445.7	1235.6
52.5°	779.2	829.8	904.6	1013.0	1153.0	1317.8	1475.8	1555.4	1459.2	1271.2	1091.7
55°	694.0	738.3	811.4	911.5	1044.3	1197.4	1331.6	1359.1	1234.2	1049.0	903.4
57.5°	610.8	652.1	718.7	810.8	932.3	1067.8	1172.8	1166.9	1034.9	876.0	760.4
60°	554.4	594.7	653.8	743.6	854.4	971.2	1061.1	1039.7	908.8	771.9	674.5
62.5°	503.9	539.8	595.7	674.4	775.5	883.6	957.5	925.8	797.6	677.9	601.0
65°	429.6	459.8	507.4	574.5	658.4	747.7	804.7	763.8	654.4	561.1	499.4
67.5°	358.5	382.7	422.7	476.2	547.8	619.5	654.3	613.0	525.6	457.4	411.7
70°	313.4	334.9	365.8	413.5	475.9	536.2	562.4	525.6	450.4	391.9	359.0
72.5°	268.4	286.0	313.1	356.0	406.0	458.4	481.4	446.1	384.4	335.0	304.3
75°	207.4	219.5	238.2	267.8	307.4	349.0	361.8	330.9	291.3	254.3	234.3
77.5°	148.4	158.7	172.9	191.6	219.6	246.1	257.2	239.4	208.7	185.4	168.8
80°	114.1	119.5	131.6	147.0	169.1	185.9	193.3	181.9	160.4	142.9	130.2
82.5°	81.4	86.7	93.9	106.7	120.8	132.2	140.2	132.5	116.9	103.2	95.8
85°	39.6	43.0	47.0	52.3	63.1	69.8	69.1	64.4	58.4	53.0	49.0
87.5°	14.1	14.9	16.7	19.5	21.4	23.6	24.9	23.9	22.0	20.5	18.9
90°	0.9	2.0	2.9	4.0	4.9	5.4	6.4	6.9	7.8	8.4	8.9
92.5°	7.2	11.4	17.5	25.9	40.3	67.1	112.1	160.9	158.3	128.2	87.0
95°	16.7	20.7	26.0	36.9	59.0	111.5	219.6	355.1	435.1	425.9	353.1
97.5°	27.5	30.2	35.6	45.4	61.3	96.1	175.2	317.1	464.7	538.8	525.9
100°	35.4	37.4	42.7	52.1	66.8	95.3	159.1	282.9	443.5	566.3	604.1
102.5°	43.2	44.8	50.6	59.2	73.4	98.8	152.5	256.9	406.1	549.7	630.4
105°	55.5	57.9	62.9	70.7	84.5	106.1	149.8	231.8	356.1	497.1	614.9
107.5°	69.1	71.4	75.4	83.6	96.0	116.9	154.3	221.2	321.6	443.2	559.5
110°	78.1	80.1	84.5	91.9	104.6	124.8	158.6	218.1	305.5	412.6	518.7



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	87.1	88.7	93.2	100.5	112.9	132.2	164.1	218.1	296.1	389.8	486.5
115°	100.2	101.7	106.1	113.5	125.7	143.9	172.4	219.6	285.9	364.9	445.9
117.5°	112.4	114.1	118.5	126.8	138.7	155.9	181.8	222.7	280.9	350.1	419.8
120°	120.4	122.3	126.7	135.1	147.3	164.5	188.1	225.9	278.4	341.8	405.7
122.5°	128.2	129.8	134.1	143.4	155.6	172.8	195.2	228.7	276.6	334.8	395.1
125°	138.5	140.9	145.3	154.7	167.5	183.7	204.8	233.3	274.1	325.1	379.6
127.5°	147.1	150.3	155.9	165.8	178.6	194.2	213.6	238.5	272.9	316.3	363.9
130°	152.2	156.2	162.6	172.9	185.6	200.9	219.6	241.7	272.1	310.4	354.1
132.5°	156.6	161.3	168.5	179.2	191.9	207.2	224.6	245.2	272.1	305.7	344.3
135°	163.1	168.9	176.8	187.1	200.4	215.6	231.8	249.9	272.1	300.1	331.5
137.5°	170.7	176.2	184.0	194.1	207.8	221.6	237.1	254.4	272.7	295.1	320.7
140°	175.3	181.2	189.1	198.5	211.7	225.9	240.6	256.4	273.1	292.7	314.8
142.5°	180.5	186.0	193.8	202.8	215.2	228.7	242.6	257.5	273.5	290.8	309.7
145°	188.6	193.5	200.4	209.2	220.5	233.3	245.6	258.8	273.1	287.8	303.1
147.5°	196.8	201.0	207.4	215.1	225.1	236.3	247.4	259.3	271.8	284.7	296.8
150°	202.3	205.8	212.2	219.0	227.4	238.2	248.5	259.3	270.6	282.4	293.2
152.5°	207.4	210.5	216.1	222.6	230.1	240.1	249.3	258.9	269.1	279.7	289.3
155°	214.1	217.1	222.0	226.9	233.8	242.1	249.9	257.9	266.2	275.0	283.4
157.5°	220.5	222.9	227.1	231.4	236.6	243.8	250.5	256.6	263.2	270.7	277.5
160°	224.5	226.4	229.9	233.8	238.2	244.6	250.5	255.4	261.3	267.2	273.5
162.5°	228.0	230.0	233.0	236.2	239.8	245.4	250.1	254.3	258.9	264.1	269.2
165°	232.8	234.3	236.7	238.7	241.7	245.6	249.5	252.4	255.4	259.3	263.2
167.5°	236.9	237.7	239.1	240.5	242.3	245.6	248.3	249.7	251.9	254.7	257.5
170°	239.2	239.7	240.6	241.7	243.1	245.6	247.5	248.5	249.9	251.9	254.4
172.5°	240.4	240.8	241.9	242.5	243.1	245.2	246.8	246.9	247.6	249.2	250.9
175°	242.1	242.6	243.1	243.1	243.1	244.6	245.6	245.0	245.0	245.6	247.0
177.5°	243.2	243.2	243.6	243.2	243.2	244.0	244.4	243.6	243.6	244.0	244.4
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1653.7	1658.0	1667.2	1664.0	1668.3	1670.4	1672.6
5°	1787.3	1808.8	1818.2	1816.9	1830.9	1827.6	1824.2
7.5°	1938.2	1960.8	1973.4	1989.1	1998.2	1998.9	2006.8
10°	2023.6	2053.1	2065.2	2082.0	2092.7	2098.8	2098.1
12.5°	2089.0	2112.2	2139.2	2147.5	2162.0	2169.6	2166.8
15°	2167.9	2204.8	2233.0	2247.0	2265.2	2270.5	2277.9
17.5°	2238.3	2287.8	2320.7	2364.4	2380.9	2391.0	2385.1
20°	2291.4	2356.5	2389.4	2441.7	2470.6	2486.1	2480.6
22.5°	2354.2	2424.7	2485.4	2530.8	2574.7	2595.6	2599.9
25°	2461.9	2558.5	2647.7	2707.5	2761.8	2774.6	2802.8
27.5°	2582.1	2696.0	2791.5	2854.4	2892.2	2906.4	2915.3
30°	2657.8	2771.2	2843.1	2883.3	2895.5	2894.1	2892.7
32.5°	2694.8	2765.9	2779.7	2768.5	2740.8	2717.4	2693.0
35°	2642.4	2589.4	2510.2	2408.1	2333.0	2257.1	2249.8
37.5°	2376.4	2206.9	2075.1	1927.9	1842.9	1790.4	1754.2
40°	2126.2	1933.6	1773.9	1649.8	1563.1	1529.0	1495.4
42.5°	1854.6	1670.5	1529.0	1425.3	1360.2	1322.2	1295.6
45°	1506.8	1344.4	1233.6	1158.5	1106.7	1077.2	1060.4
47.5°	1234.7	1114.6	1020.5	966.2	930.5	907.6	907.7
50°	1088.6	973.9	911.5	868.5	837.6	819.5	822.9
52.5°	959.2	873.5	820.2	784.2	761.4	750.2	749.8
55°	802.0	740.3	705.4	679.2	663.7	651.0	653.8
57.5°	686.0	634.0	610.6	588.9	578.2	573.1	565.7
60°	614.2	573.9	553.7	536.2	525.6	521.5	514.1
62.5°	550.3	518.6	498.9	484.7	475.0	473.7	468.0
65°	462.4	438.2	420.9	414.1	404.1	401.4	401.4
67.5°	381.3	363.9	350.3	344.1	339.8	340.4	337.2
70°	330.2	316.2	307.4	300.7	297.3	298.0	295.3
72.5°	288.9	273.2	265.5	261.5	257.1	258.8	257.7
75°	218.8	210.8	206.7	202.7	200.0	198.6	197.3
77.5°	160.7	153.6	150.5	148.2	148.6	145.3	147.9
80°	124.2	118.1	116.1	112.8	112.1	112.1	111.4
82.5°	90.8	87.5	86.0	83.3	82.1	83.1	81.4
85°	47.0	44.3	43.7	43.7	42.3	41.0	44.3
87.5°	19.0	17.0	17.2	16.6	16.6	16.2	15.2
90°	9.3	9.8	10.8	10.8	10.8	11.3	11.3
92.5°	63.2	47.5	40.3	34.0	32.8	32.1	31.3
95°	278.4	218.1	176.8	142.0	127.2	123.3	115.5
97.5°	473.6	414.7	357.3	327.0	299.5	285.2	279.0
100°	580.1	529.4	478.4	444.4	409.1	391.0	383.1
102.5°	645.2	621.0	586.4	550.2	525.0	505.3	499.4
105°	682.2	703.8	698.4	682.7	666.5	656.7	650.7
107.5°	649.3	704.8	730.4	738.4	738.3	735.0	731.1
110°	612.0	681.2	723.0	745.0	754.4	757.9	757.9



TEST NUMBER: P333306-935

CATALOG NUMBER: S125DIP-S1270D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	575.1	645.1	694.3	726.6	742.6	751.1	754.7
115°	522.1	589.4	642.9	681.2	704.8	718.5	725.0
117.5°	485.4	543.4	592.5	630.9	655.2	668.8	672.8
120°	464.6	518.7	561.9	598.2	621.8	635.1	638.9
122.5°	449.7	497.8	538.3	570.7	592.3	605.5	609.1
125°	429.7	472.5	507.8	535.4	555.5	566.3	571.2
127.5°	410.7	450.6	483.7	508.6	526.4	536.6	538.8
130°	397.4	435.7	467.5	492.1	508.3	518.1	521.1
132.5°	384.8	419.6	450.3	474.8	491.0	500.1	503.4
135°	365.4	396.8	424.8	446.4	462.6	471.5	474.4
137.5°	348.1	374.3	398.0	417.3	432.1	440.2	443.5
140°	337.9	360.5	381.2	399.3	412.1	419.4	421.9
142.5°	329.2	348.7	366.6	382.0	392.8	399.8	401.8
145°	318.2	333.5	346.7	358.5	366.9	372.3	374.3
147.5°	309.1	320.8	330.8	340.2	346.8	350.0	350.9
150°	304.0	313.3	322.2	329.6	335.4	337.4	337.9
152.5°	298.9	307.5	314.4	320.6	325.2	327.2	327.7
155°	291.3	298.1	303.5	308.4	311.9	313.3	313.8
157.5°	284.0	289.3	293.5	297.3	300.1	301.5	301.4
160°	278.4	283.4	286.8	290.2	292.7	293.7	293.2
162.5°	273.8	277.8	280.9	283.6	285.7	285.9	285.8
165°	266.7	269.7	272.1	274.1	275.0	275.0	275.0
167.5°	259.8	262.1	263.8	264.8	265.7	265.3	265.2
170°	255.9	257.4	258.3	259.3	259.8	259.8	259.3
172.5°	252.4	253.4	254.0	254.3	255.1	254.3	253.8
175°	247.0	248.1	248.1	248.1	248.5	247.5	247.0
177.5°	244.8	244.8	244.8	244.4	244.8	243.6	243.6
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6

(END OF REPORT)