

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333144-935

Luminaire Tested: **S125DIP-S375D1035U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333144-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D1035U935-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4522.0 lumens  
Efficiency: N/A  
Efficacy: 121.2 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	40	58	49	42	37	39	34	30	29	26	24	21	19	17	13
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	43	36	30	49	39	33	28	31	27	23	24	21	18	17	15	13	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	15	12	11	8
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3027	3027	3027	3027
5°	3505	3038	2660	3038
10°	4078	3022	2330	3022
15°	4515	3000	2150	3000
20°	5054	2965	2004	2965
25°	5920	2925	1934	2925
30°	6395	2885	1873	2885
35°	5257	2812	1832	2812
40°	3737	2710	1788	2710
45°	2872	2573	1763	2573
50°	2451	2402	1758	2402
55°	2182	2235	1775	2235
60°	1969	2052	1820	2052
65°	1819	1869	1867	1869
70°	1654	1679	1894	1679
75°	1460	1480	1876	1480
80°	1231	1209	1715	1209
85°	978	867	1386	867



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.1	1.0
10°-20°	134.4	3.0
20°-30°	218.2	4.8
30°-40°	266.1	5.9
40°-50°	242.1	5.4
50°-60°	192.8	4.3
60°-70°	134.3	3.0
70°-80°	71.6	1.6
80°-90°	20.4	0.5
90°-100°	309.0	6.8
100°-110°	664.3	14.7
110°-120°	623.4	13.8
120°-130°	505.2	11.2
130°-140°	405.5	9.0
140°-150°	306.0	6.8
150°-160°	215.4	4.8
160°-170°	126.9	2.8
170°-180°	41.3	0.9
0°-30°	397.6	8.8
0°-40°	663.7	14.7
0°-60°	1098.7	24.3
0°-90°	1325.0	29.3
90°-120°	1596.7	35.3
90°-150°	2813.4	62.2
90°-180°	3197.0	70.7
0°-180°	4522.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	469	469	469	469	469	
5°	541	469	410	469	541	54
15°	675	449	322	449	675	193
25°	831	410	271	410	831	379
35°	667	357	232	357	667	408
45°	314	282	193	282	314	252
55°	194	198	158	198	194	174
65°	119	122	122	122	119	118
75°	58	59	75	59	58	63
85°	13	12	19	12	13	16
90°	20	1	20	1	20	14
95°	202	28	202	28	202	286
105°	1139	97	1139	97	1139	1132
115°	1269	174	1269	174	1269	1240
125°	1000	241	1000	241	1000	904
135°	830	282	830	282	830	643
145°	655	328	655	328	655	416
155°	549	375	549	375	549	256
165°	481	409	481	409	481	138
175°	432	425	432	425	432	42
180°	426	426	426	426	426	



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	495.8	495.2	494.5	493.3	494.2	491.5	490.3	488.0	485.3	484.3	483.2
5°	540.7	541.7	542.8	538.6	539.0	536.1	529.8	524.6	520.5	515.1	511.3
7.5°	594.9	592.5	592.3	589.6	585.0	581.2	574.5	566.0	557.8	548.4	540.6
10°	621.9	622.2	620.4	617.2	612.2	608.6	599.9	591.5	581.3	569.4	560.9
12.5°	642.3	643.2	640.8	636.5	634.1	626.1	619.2	609.3	597.3	587.7	574.7
15°	675.2	673.0	671.5	666.1	661.9	653.6	642.7	632.2	619.1	607.0	594.9
17.5°	707.0	708.8	705.8	700.9	687.9	678.1	663.5	649.3	632.9	616.6	602.2
20°	735.3	736.9	732.4	723.8	708.3	698.5	679.2	660.9	642.0	621.1	605.2
22.5°	770.7	769.4	763.2	750.2	736.8	718.8	697.8	675.5	651.9	628.3	607.1
25°	830.8	822.4	818.6	802.5	784.9	758.4	729.8	697.2	667.7	636.5	609.4
27.5°	864.2	861.5	857.3	846.1	827.5	799.2	765.4	725.7	684.2	644.7	609.2
30°	857.5	857.9	858.2	854.7	842.7	821.5	787.8	745.1	695.7	651.3	610.4
32.5°	798.2	805.5	812.4	820.6	824.0	819.8	798.8	760.2	709.4	659.0	609.8
35°	666.8	669.1	691.6	713.9	744.1	767.6	783.3	766.1	723.4	665.5	609.0
37.5°	520.0	530.7	546.3	571.4	615.1	654.2	704.5	727.5	713.8	667.6	607.6
40°	443.2	453.2	463.4	489.0	525.8	573.2	630.3	679.0	690.3	660.9	602.8
42.5°	384.1	391.9	403.2	422.5	453.2	495.2	549.7	613.5	652.6	641.5	592.8
45°	314.4	319.3	328.0	343.4	365.7	398.5	446.6	516.3	577.0	597.0	569.0
47.5°	269.1	269.1	275.9	286.4	302.5	330.4	366.0	420.5	485.3	533.3	531.1
50°	243.9	242.9	248.3	257.4	270.2	288.7	322.7	366.3	428.5	482.8	498.0
52.5°	222.2	222.4	225.7	232.5	243.1	258.9	284.3	323.6	376.8	432.6	461.1
55°	193.8	193.0	196.7	201.3	209.1	219.5	237.7	267.8	311.0	365.8	402.9
57.5°	167.6	169.9	171.3	174.5	181.0	188.0	203.4	225.4	259.7	306.8	345.9
60°	152.4	154.5	155.8	158.9	164.1	170.1	182.0	199.9	228.8	269.4	308.2
62.5°	138.7	140.4	140.9	143.7	147.9	153.7	163.1	178.1	201.0	236.4	274.4
65°	119.0	119.0	119.8	122.8	124.8	129.9	137.1	148.0	166.3	194.0	226.4
67.5°	100.0	100.9	100.7	102.0	103.8	107.9	113.0	122.0	135.6	155.8	181.8
70°	87.6	88.3	88.2	89.1	91.1	93.7	97.9	106.4	116.1	133.5	155.8
72.5°	76.4	76.7	76.2	77.5	78.7	80.9	85.7	90.2	99.3	113.9	132.2
75°	58.5	58.9	59.3	60.1	61.3	62.5	64.8	69.4	75.4	86.4	98.1
77.5°	43.8	43.0	44.1	43.9	44.6	45.5	47.6	50.0	54.9	61.9	70.9
80°	33.1	33.2	33.2	33.4	34.4	35.0	36.8	38.6	42.4	47.5	53.9
82.5°	24.1	24.6	24.3	24.7	25.5	25.9	26.9	28.4	30.6	34.7	39.3
85°	13.2	12.1	12.6	12.9	12.9	13.2	13.9	14.6	15.8	17.3	19.1
87.5°	7.7	8.1	8.1	8.1	8.3	7.9	8.4	8.2	8.5	8.8	9.1
90°	19.8	19.8	18.9	18.9	18.9	17.2	16.4	15.5	14.6	13.8	12.1
92.5°	54.8	56.2	57.4	59.5	70.5	83.2	110.6	152.3	224.3	277.1	281.5
95°	202.0	215.8	222.7	248.4	309.4	381.6	487.3	618.0	745.2	761.6	621.5
97.5°	488.2	499.2	524.1	572.3	625.3	725.7	828.7	920.4	942.9	813.3	554.9
100°	670.5	684.2	716.0	777.8	837.2	926.5	1015.1	1057.2	991.0	776.1	495.1
102.5°	873.9	884.2	918.9	962.9	1026.2	1086.8	1129.2	1103.3	962.2	710.8	449.7
105°	1138.8	1149.2	1166.4	1194.7	1222.2	1231.7	1193.9	1076.1	869.9	623.1	405.7
107.5°	1279.4	1286.3	1292.0	1292.2	1278.2	1233.4	1136.3	979.1	775.6	562.8	387.1
110°	1326.2	1326.2	1320.2	1303.9	1265.2	1192.1	1070.9	907.7	721.9	534.6	381.6



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1320.7	1314.6	1299.6	1271.5	1215.0	1128.9	1006.3	851.3	682.1	518.1	381.6
115°	1268.7	1257.5	1233.4	1192.1	1125.1	1031.4	913.7	780.4	638.6	500.2	384.2
117.5°	1177.3	1170.4	1146.6	1104.0	1036.9	951.0	849.5	734.7	612.7	491.5	389.9
120°	1118.3	1111.4	1088.1	1046.9	983.3	907.7	813.1	710.0	598.2	487.3	395.4
122.5°	1066.0	1059.8	1036.6	998.8	942.0	871.2	787.0	691.4	585.8	483.9	400.2
125°	999.6	991.0	972.1	936.9	888.7	826.8	752.1	664.4	569.0	479.6	408.3
127.5°	942.9	939.1	921.2	890.1	846.4	788.5	718.8	636.9	553.5	477.5	417.4
130°	912.0	906.8	889.6	861.3	818.3	762.4	695.3	619.7	543.2	476.1	422.9
132.5°	881.0	875.1	859.4	831.0	788.0	734.2	673.3	602.5	534.9	476.1	429.0
135°	830.3	825.1	809.7	781.3	743.5	694.5	639.5	580.1	525.1	476.1	437.5
137.5°	776.1	770.5	756.2	730.4	696.5	655.0	609.2	561.3	516.4	477.2	445.2
140°	738.3	734.0	721.2	698.8	667.0	630.9	591.3	551.0	512.3	477.9	448.7
142.5°	703.3	699.6	687.4	668.6	641.5	610.3	576.2	542.0	508.9	478.5	450.7
145°	655.0	651.5	642.0	627.4	606.8	583.6	557.0	530.3	503.7	477.9	453.0
147.5°	614.1	612.5	607.0	595.3	578.9	561.5	541.0	519.4	498.3	475.6	453.8
150°	591.3	590.5	587.0	576.7	563.9	548.4	532.0	513.2	494.2	473.6	453.8
152.5°	573.4	572.6	569.2	560.9	550.1	538.0	523.1	506.3	489.4	470.9	453.1
155°	549.2	548.4	545.8	539.8	531.2	521.8	509.7	495.9	481.3	465.9	451.3
157.5°	527.5	527.7	525.3	520.4	513.7	506.3	497.0	485.6	473.7	460.7	449.0
160°	513.2	514.0	512.3	508.0	502.0	495.9	487.3	478.7	467.6	457.3	446.9
162.5°	500.1	500.2	499.9	496.3	491.6	486.3	479.1	471.2	462.1	453.1	444.9
165°	481.3	481.3	481.3	479.6	476.1	471.9	466.7	460.7	453.8	446.9	441.8
167.5°	464.2	464.3	465.0	463.5	461.8	458.7	454.7	450.7	445.7	440.9	437.0
170°	453.8	454.7	454.7	453.8	452.1	450.4	447.8	445.2	440.9	437.5	434.9
172.5°	444.2	445.1	446.4	444.9	444.5	443.5	441.6	439.0	436.1	433.3	432.1
175°	432.3	433.2	434.9	434.0	434.0	434.0	432.3	432.3	429.7	428.9	428.9
177.5°	426.3	426.3	428.3	427.7	428.3	428.3	428.3	427.7	427.0	426.3	426.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	482.2	481.1	479.8	477.6	474.9	473.5	471.3	469.8	467.0	464.6	462.0
5°	506.7	501.5	496.8	490.6	483.9	479.5	474.3	468.6	462.5	456.4	449.6
7.5°	532.1	522.9	513.0	502.3	491.8	482.2	472.9	464.0	455.6	445.3	436.7
10°	549.1	537.5	525.2	510.7	496.5	484.2	471.7	460.8	449.6	437.7	427.1
12.5°	566.1	550.8	533.3	517.4	500.4	485.5	470.8	456.8	442.8	429.6	417.2
15°	578.2	564.6	548.5	525.8	506.7	486.2	466.7	448.7	431.7	417.0	401.5
17.5°	586.1	568.6	551.3	529.6	504.5	481.6	459.5	438.8	419.7	401.1	386.2
20°	587.5	569.6	551.5	530.2	504.5	478.3	456.2	431.4	410.9	391.5	373.2
22.5°	587.0	566.7	547.0	525.1	500.1	475.9	449.2	423.9	401.6	382.6	363.5
25°	582.6	560.9	536.1	514.1	489.4	463.7	436.7	410.4	387.8	366.1	347.2
27.5°	578.8	550.7	522.7	497.0	473.1	449.6	423.7	396.8	371.7	349.7	331.9
30°	574.2	543.3	511.9	485.0	460.5	437.7	413.2	386.9	360.7	339.2	320.1
32.5°	570.1	534.1	500.9	471.7	445.7	423.5	401.0	376.0	350.2	328.4	309.3
35°	562.1	520.5	482.4	449.4	421.8	398.9	380.0	356.7	333.0	311.9	293.7
37.5°	551.9	502.6	461.8	427.1	396.8	372.7	355.2	337.3	314.5	294.2	277.7
40°	543.9	489.8	446.6	411.2	379.8	354.7	338.4	321.5	302.6	283.7	266.2
42.5°	533.9	478.4	431.4	393.2	362.1	337.7	320.6	306.3	289.6	271.9	255.7
45°	515.5	457.6	406.7	365.7	334.2	310.1	292.5	281.7	269.1	252.4	238.8
47.5°	488.4	432.7	380.0	337.7	305.2	282.9	266.3	256.0	247.2	234.8	222.3
50°	464.3	414.1	360.7	318.7	286.3	263.8	248.5	239.1	231.6	222.1	211.5
52.5°	437.5	390.6	341.7	300.2	268.1	246.0	231.0	222.7	216.5	209.7	199.2
55°	394.7	354.9	309.5	270.2	240.6	218.9	205.7	198.5	193.4	188.2	181.8
57.5°	347.7	316.5	276.4	240.3	213.0	193.3	181.1	174.1	170.0	167.4	163.7
60°	314.5	287.9	253.3	220.4	193.8	176.2	164.4	158.9	155.6	153.4	150.6
62.5°	283.8	261.9	229.9	199.9	176.6	160.1	149.4	144.1	140.9	139.8	137.6
65°	238.6	221.6	195.2	170.3	150.4	136.3	127.3	122.3	120.4	119.2	119.3
67.5°	193.9	183.7	162.4	141.2	125.3	113.5	106.2	102.5	101.4	99.9	99.9
70°	166.7	158.9	141.0	122.5	108.4	99.3	92.9	88.9	87.9	87.1	87.0
72.5°	142.7	135.9	120.4	105.6	92.8	84.8	79.6	77.1	75.5	75.1	75.0
75°	107.2	103.5	91.1	79.4	70.6	65.1	61.5	59.3	58.1	57.9	58.1
77.5°	76.2	72.9	65.1	56.7	51.2	47.0	44.0	43.2	41.9	41.9	41.8
80°	57.3	55.1	50.1	43.6	39.0	35.4	33.8	32.5	32.0	31.4	32.0
82.5°	41.5	39.2	35.8	31.6	27.8	25.7	24.1	23.7	23.4	23.2	23.2
85°	20.5	20.7	18.7	15.5	13.9	12.7	11.7	11.7	11.5	11.4	11.5
87.5°	9.2	8.6	7.7	7.0	5.8	5.0	4.5	4.5	4.1	4.4	4.8
90°	11.2	9.5	8.6	6.9	5.2	3.4	1.7	0.9	1.7	3.4	5.2
92.5°	196.1	117.4	70.5	45.4	30.6	20.0	12.7	10.5	12.7	20.0	30.6
95°	384.2	195.1	103.1	64.5	45.5	36.1	29.2	28.3	29.2	36.1	45.5
97.5°	306.7	168.2	107.3	79.4	62.4	53.0	48.1	47.1	48.1	53.0	62.4
100°	278.4	166.8	116.9	91.1	74.7	65.3	61.9	60.2	61.9	65.3	74.7
102.5°	266.8	173.0	128.5	103.5	88.5	78.4	75.6	74.6	75.6	78.4	88.5
105°	262.2	185.6	147.8	123.8	110.0	101.4	97.1	97.1	97.1	101.4	110.0
107.5°	270.1	204.6	168.0	146.3	132.0	124.9	120.9	119.2	120.9	124.9	132.0
110°	277.6	218.3	183.0	160.7	147.8	140.1	136.6	134.9	136.6	140.1	147.8





TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	287.2	231.4	197.5	175.8	163.0	155.2	152.5	150.8	152.5	155.2	163.0
115°	301.7	251.8	220.1	198.5	185.6	177.9	175.3	173.7	175.3	177.9	185.6
117.5°	318.2	272.9	242.7	222.0	207.3	199.6	196.8	194.2	196.8	199.6	207.3
120°	329.2	287.9	257.9	236.3	221.8	214.0	210.6	208.0	210.6	214.0	221.8
122.5°	341.6	302.4	272.3	250.8	234.8	227.0	224.3	222.5	224.3	227.0	234.8
125°	358.4	321.5	293.1	270.8	254.4	246.7	242.4	240.6	242.4	246.7	254.4
127.5°	373.8	339.8	312.5	290.2	272.9	263.0	257.5	254.9	257.5	263.0	272.9
130°	384.2	351.5	324.9	302.6	284.5	273.4	266.5	263.9	266.5	273.4	284.5
132.5°	393.1	362.6	335.9	313.6	294.8	282.2	274.0	270.8	274.0	282.2	294.8
135°	405.7	377.3	350.7	327.4	309.4	295.7	285.3	281.9	285.3	295.7	309.4
137.5°	415.0	387.8	363.6	339.7	322.0	308.2	298.6	296.0	298.6	308.2	322.0
140°	421.2	395.4	370.5	347.2	330.9	317.2	306.9	304.3	306.9	317.2	330.9
142.5°	424.6	400.2	376.6	354.8	339.1	325.4	315.8	313.9	315.8	325.4	339.1
145°	429.7	408.3	385.9	366.2	350.7	338.6	330.0	328.3	330.0	338.6	350.7
147.5°	432.8	413.5	393.8	376.4	363.1	351.9	344.5	343.5	344.5	351.9	363.1
150°	434.9	416.9	398.0	383.3	371.3	360.2	354.1	352.4	354.1	360.2	371.3
152.5°	436.3	420.3	402.8	389.5	378.2	368.4	363.1	362.1	363.1	368.4	378.2
155°	437.5	423.7	409.1	397.1	388.5	379.9	374.7	374.7	374.7	379.9	388.5
157.5°	438.3	426.6	414.1	405.0	397.4	390.0	385.9	386.1	385.9	390.0	397.4
160°	438.3	428.0	416.9	409.1	402.3	396.2	392.8	393.6	392.8	396.2	402.3
162.5°	437.6	429.4	419.7	413.3	407.8	402.4	399.0	399.8	399.0	402.4	407.8
165°	436.6	429.7	422.9	417.8	414.3	410.0	407.4	409.1	407.4	410.0	414.3
167.5°	434.5	429.7	424.0	420.9	418.4	416.0	414.5	415.3	414.5	416.0	418.4
170°	433.2	429.7	425.4	422.9	421.2	419.5	418.6	419.5	418.6	419.5	421.2
172.5°	431.8	429.0	425.4	424.2	423.2	421.5	420.7	422.2	420.7	421.5	423.2
175°	429.7	428.0	425.4	425.4	425.4	424.6	423.7	425.4	423.7	424.6	425.4
177.5°	427.7	427.0	425.6	425.6	426.3	425.6	425.6	427.0	425.6	425.6	426.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	460.6	458.8	457.4	454.3	452.5	450.1	448.2	450.3	448.1	449.0	447.5
5°	446.3	440.7	436.7	430.9	425.9	421.4	418.0	417.4	415.8	415.0	412.6
7.5°	429.0	422.0	415.2	407.6	401.2	394.8	390.6	387.2	385.0	381.9	379.9
10°	418.8	409.4	401.5	392.4	384.4	377.4	371.9	369.0	366.4	362.7	361.3
12.5°	406.2	396.6	386.8	377.0	369.4	361.6	356.9	352.7	350.9	346.6	346.2
15°	391.2	376.6	367.0	357.1	346.6	340.2	336.2	331.7	329.7	326.7	324.5
17.5°	373.2	360.2	348.3	337.9	328.9	323.6	318.6	315.5	312.0	310.0	306.5
20°	360.1	347.8	335.8	324.9	317.9	311.8	307.8	304.8	301.2	300.2	296.6
22.5°	349.1	335.5	324.1	314.9	307.3	300.3	296.0	293.9	291.5	288.4	287.7
25°	331.2	317.1	307.4	298.3	291.4	285.1	282.1	279.6	277.2	274.9	274.1
27.5°	315.8	303.2	291.6	283.4	277.4	271.6	269.1	265.9	264.2	262.3	260.2
30°	305.0	292.1	281.9	274.0	267.6	262.4	259.6	257.4	255.9	254.3	253.0
32.5°	293.9	281.9	272.1	264.2	257.9	254.0	251.5	249.9	248.2	246.3	244.8
35°	279.1	266.0	256.4	249.7	244.7	241.7	238.9	237.5	235.6	235.6	233.9
37.5°	262.5	251.2	242.7	236.6	232.1	229.5	226.4	225.5	224.2	223.3	222.8
40°	252.7	242.1	234.2	228.0	223.3	221.0	218.6	217.1	216.3	215.2	214.9
42.5°	242.5	232.4	224.8	219.1	214.9	213.1	210.9	209.7	208.1	206.8	206.6
45°	227.0	217.2	210.3	205.7	202.2	199.9	198.5	196.1	195.4	193.8	193.6
47.5°	212.3	202.9	196.1	192.3	189.2	187.4	185.3	182.9	181.9	181.2	181.1
50°	201.3	192.8	186.4	182.9	179.9	177.3	175.0	173.5	172.9	172.9	173.3
52.5°	190.2	182.9	177.5	173.1	170.3	167.6	165.5	164.5	163.7	164.6	165.3
55°	173.9	166.5	162.6	158.3	155.6	152.4	151.4	151.0	150.4	152.0	152.8
57.5°	156.6	151.4	146.8	142.7	140.2	138.3	137.0	136.7	137.8	138.6	141.2
60°	145.6	139.7	135.5	132.3	129.3	128.1	127.7	127.3	128.1	130.3	133.7
62.5°	133.5	128.7	124.2	121.8	119.6	117.6	117.5	117.8	119.3	121.9	125.3
65°	115.8	111.6	108.7	105.8	104.0	102.9	103.2	104.0	105.8	109.3	113.0
67.5°	97.7	94.9	92.2	90.0	88.3	88.3	88.7	89.9	92.0	95.8	99.3
70°	86.2	83.0	80.8	79.8	78.4	77.6	78.8	80.8	82.6	86.2	89.1
72.5°	74.6	71.8	70.1	69.4	68.8	68.2	68.6	70.8	73.2	76.7	80.2
75°	57.3	56.3	55.1	54.3	53.7	54.2	54.5	56.5	58.5	62.3	66.2
77.5°	41.8	40.8	40.0	39.9	39.5	39.8	40.9	42.4	44.3	47.0	50.0
80°	31.6	31.3	30.8	30.7	30.7	30.8	32.5	33.4	35.2	37.8	40.2
82.5°	23.1	22.8	22.7	22.6	22.8	22.9	23.8	25.1	26.6	28.6	30.7
85°	12.1	11.7	12.3	12.6	12.1	12.7	13.2	13.9	14.6	15.5	16.5
87.5°	5.3	6.0	6.0	6.5	6.7	7.4	7.4	8.2	8.7	9.1	9.4
90°	6.9	8.6	9.5	11.2	12.1	13.8	14.6	15.5	16.4	17.2	18.9
92.5°	45.4	70.5	117.4	196.1	281.5	277.1	224.3	152.3	110.6	83.2	70.5
95°	64.5	103.1	195.1	384.2	621.5	761.6	745.2	618.0	487.3	381.6	309.4
97.5°	79.4	107.3	168.2	306.7	554.9	813.3	942.9	920.4	828.7	725.7	625.3
100°	91.1	116.9	166.8	278.4	495.1	776.1	991.0	1057.2	1015.1	926.5	837.2
102.5°	103.5	128.5	173.0	266.8	449.7	710.8	962.2	1103.3	1129.2	1086.8	1026.2
105°	123.8	147.8	185.6	262.2	405.7	623.1	869.9	1076.1	1193.9	1231.7	1222.2
107.5°	146.3	168.0	204.6	270.1	387.1	562.8	775.6	979.1	1136.3	1233.4	1278.2
110°	160.7	183.0	218.3	277.6	381.6	534.6	721.9	907.7	1070.9	1192.1	1265.2



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	175.8	197.5	231.4	287.2	381.6	518.1	682.1	851.3	1006.3	1128.9	1215.0
115°	198.5	220.1	251.8	301.7	384.2	500.2	638.6	780.4	913.7	1031.4	1125.1
117.5°	222.0	242.7	272.9	318.2	389.9	491.5	612.7	734.7	849.5	951.0	1036.9
120°	236.3	257.9	287.9	329.2	395.4	487.3	598.2	710.0	813.1	907.7	983.3
122.5°	250.8	272.3	302.4	341.6	400.2	483.9	585.8	691.4	787.0	871.2	942.0
125°	270.8	293.1	321.5	358.4	408.3	479.6	569.0	664.4	752.1	826.8	888.7
127.5°	290.2	312.5	339.8	373.8	417.4	477.5	553.5	636.9	718.8	788.5	846.4
130°	302.6	324.9	351.5	384.2	422.9	476.1	543.2	619.7	695.3	762.4	818.3
132.5°	313.6	335.9	362.6	393.1	429.0	476.1	534.9	602.5	673.3	734.2	788.0
135°	327.4	350.7	377.3	405.7	437.5	476.1	525.1	580.1	639.5	694.5	743.5
137.5°	339.7	363.6	387.8	415.0	445.2	477.2	516.4	561.3	609.2	655.0	696.5
140°	347.2	370.5	395.4	421.2	448.7	477.9	512.3	551.0	591.3	630.9	667.0
142.5°	354.8	376.6	400.2	424.6	450.7	478.5	508.9	542.0	576.2	610.3	641.5
145°	366.2	385.9	408.3	429.7	453.0	477.9	503.7	530.3	557.0	583.6	606.8
147.5°	376.4	393.8	413.5	432.8	453.8	475.6	498.3	519.4	541.0	561.5	578.9
150°	383.3	398.0	416.9	434.9	453.8	473.6	494.2	513.2	532.0	548.4	563.9
152.5°	389.5	402.8	420.3	436.3	453.1	470.9	489.4	506.3	523.1	538.0	550.1
155°	397.1	409.1	423.7	437.5	451.3	465.9	481.3	495.9	509.7	521.8	531.2
157.5°	405.0	414.1	426.6	438.3	449.0	460.7	473.7	485.6	497.0	506.3	513.7
160°	409.1	416.9	428.0	438.3	446.9	457.3	467.6	478.7	487.3	495.9	502.0
162.5°	413.3	419.7	429.4	437.6	444.9	453.1	462.1	471.2	479.1	486.3	491.6
165°	417.8	422.9	429.7	436.6	441.8	446.9	453.8	460.7	466.7	471.9	476.1
167.5°	420.9	424.0	429.7	434.5	437.0	440.9	445.7	450.7	454.7	458.7	461.8
170°	422.9	425.4	429.7	433.2	434.9	437.5	440.9	445.2	447.8	450.4	452.1
172.5°	424.2	425.4	429.0	431.8	432.1	433.3	436.1	439.0	441.6	443.5	444.5
175°	425.4	425.4	428.0	429.7	428.9	428.9	429.7	432.3	432.3	434.0	434.0
177.5°	425.6	425.6	427.0	427.7	426.3	426.3	427.0	427.7	428.3	428.3	428.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	446.6	447.7	446.8	448.1	446.8	447.7	446.6	447.5	449.0	448.1	450.3
5°	411.6	409.8	411.0	410.3	411.0	409.8	411.6	412.6	415.0	415.8	417.4
7.5°	379.4	377.6	375.7	374.7	375.7	377.6	379.4	379.9	381.9	385.0	387.2
10°	359.1	356.9	356.7	355.3	356.7	356.9	359.1	361.3	362.7	366.4	369.0
12.5°	344.3	342.2	340.0	339.4	340.0	342.2	344.3	346.2	346.6	350.9	352.7
15°	323.3	321.7	320.3	321.5	320.3	321.7	323.3	324.5	326.7	329.7	331.7
17.5°	305.8	304.5	304.3	302.8	304.3	304.5	305.8	306.5	310.0	312.0	315.5
20°	294.8	293.9	294.3	291.6	294.3	293.9	294.8	296.6	300.2	301.2	304.8
22.5°	286.1	284.1	283.9	283.4	283.9	284.1	286.1	287.7	288.4	291.5	293.9
25°	272.3	271.4	270.4	271.4	270.4	271.4	272.3	274.1	274.9	277.2	279.6
27.5°	260.4	259.2	258.9	259.1	258.9	259.2	260.4	260.2	262.3	264.2	265.9
30°	253.0	251.1	251.2	251.1	251.2	251.1	253.0	253.0	254.3	255.9	257.4
32.5°	245.1	243.7	243.5	243.1	243.5	243.7	245.1	244.8	246.3	248.2	249.9
35°	233.3	233.3	232.4	232.4	232.4	233.3	233.3	233.9	235.6	235.6	237.5
37.5°	222.3	222.1	221.5	221.6	221.5	222.1	222.3	222.8	223.3	224.2	225.5
40°	214.0	213.9	213.3	212.1	213.3	213.9	214.0	214.9	215.2	216.3	217.1
42.5°	206.1	205.4	205.2	204.7	205.2	205.4	206.1	206.6	206.8	208.1	209.7
45°	193.6	193.6	193.2	193.0	193.2	193.6	193.6	193.6	193.8	195.4	196.1
47.5°	181.4	181.8	182.5	182.4	182.5	181.8	181.4	181.1	181.2	181.9	182.9
50°	174.1	174.3	174.9	175.0	174.9	174.3	174.1	173.3	172.9	172.9	173.5
52.5°	166.0	167.1	167.9	167.7	167.9	167.1	166.0	165.3	164.6	163.7	164.5
55°	154.5	156.0	157.4	157.6	157.4	156.0	154.5	152.8	152.0	150.4	151.0
57.5°	143.4	145.3	146.7	147.2	146.7	145.3	143.4	141.2	138.6	137.8	136.7
60°	135.7	138.3	140.1	140.9	140.1	138.3	135.7	133.7	130.3	128.1	127.3
62.5°	128.4	131.3	133.0	133.2	133.0	131.3	128.4	125.3	121.9	119.3	117.8
65°	116.4	119.3	121.0	122.2	121.0	119.3	116.4	113.0	109.3	105.8	104.0
67.5°	103.5	106.5	108.2	109.2	108.2	106.5	103.5	99.3	95.8	92.0	89.9
70°	94.1	97.1	99.4	100.3	99.4	97.1	94.1	89.1	86.2	82.6	80.8
72.5°	84.9	87.6	89.5	90.4	89.5	87.6	84.9	80.2	76.7	73.2	70.8
75°	68.8	72.4	74.2	75.2	74.2	72.4	68.8	66.2	62.3	58.5	56.5
77.5°	53.0	56.3	57.4	57.9	57.4	56.3	53.0	50.0	47.0	44.3	42.4
80°	42.5	44.6	46.0	46.1	46.0	44.6	42.5	40.2	37.8	35.2	33.4
82.5°	32.7	34.4	34.8	35.3	34.8	34.4	32.7	30.7	28.6	26.6	25.1
85°	17.9	18.7	18.9	18.7	18.9	18.7	17.9	16.5	15.5	14.6	13.9
87.5°	9.6	9.5	9.6	10.0	9.6	9.5	9.6	9.4	9.1	8.7	8.2
90°	18.9	18.9	19.8	19.8	19.8	18.9	18.9	18.9	17.2	16.4	15.5
92.5°	59.5	57.4	56.2	54.8	56.2	57.4	59.5	70.5	83.2	110.6	152.3
95°	248.4	222.7	215.8	202.0	215.8	222.7	248.4	309.4	381.6	487.3	618.0
97.5°	572.3	524.1	499.2	488.2	499.2	524.1	572.3	625.3	725.7	828.7	920.4
100°	777.8	716.0	684.2	670.5	684.2	716.0	777.8	837.2	926.5	1015.1	1057.2
102.5°	962.9	918.9	884.2	873.9	884.2	918.9	962.9	1026.2	1086.8	1129.2	1103.3
105°	1194.7	1166.4	1149.2	1138.8	1149.2	1166.4	1194.7	1222.2	1231.7	1193.9	1076.1
107.5°	1292.2	1292.0	1286.3	1279.4	1286.3	1292.0	1292.2	1278.2	1233.4	1136.3	979.1
110°	1303.9	1320.2	1326.2	1326.2	1326.2	1320.2	1303.9	1265.2	1192.1	1070.9	907.7



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1271.5	1299.6	1314.6	1320.7	1314.6	1299.6	1271.5	1215.0	1128.9	1006.3	851.3
115°	1192.1	1233.4	1257.5	1268.7	1257.5	1233.4	1192.1	1125.1	1031.4	913.7	780.4
117.5°	1104.0	1146.6	1170.4	1177.3	1170.4	1146.6	1104.0	1036.9	951.0	849.5	734.7
120°	1046.9	1088.1	1111.4	1118.3	1111.4	1088.1	1046.9	983.3	907.7	813.1	710.0
122.5°	998.8	1036.6	1059.8	1066.0	1059.8	1036.6	998.8	942.0	871.2	787.0	691.4
125°	936.9	972.1	991.0	999.6	991.0	972.1	936.9	888.7	826.8	752.1	664.4
127.5°	890.1	921.2	939.1	942.9	939.1	921.2	890.1	846.4	788.5	718.8	636.9
130°	861.3	889.6	906.8	912.0	906.8	889.6	861.3	818.3	762.4	695.3	619.7
132.5°	831.0	859.4	875.1	881.0	875.1	859.4	831.0	788.0	734.2	673.3	602.5
135°	781.3	809.7	825.1	830.3	825.1	809.7	781.3	743.5	694.5	639.5	580.1
137.5°	730.4	756.2	770.5	776.1	770.5	756.2	730.4	696.5	655.0	609.2	561.3
140°	698.8	721.2	734.0	738.3	734.0	721.2	698.8	667.0	630.9	591.3	551.0
142.5°	668.6	687.4	699.6	703.3	699.6	687.4	668.6	641.5	610.3	576.2	542.0
145°	627.4	642.0	651.5	655.0	651.5	642.0	627.4	606.8	583.6	557.0	530.3
147.5°	595.3	607.0	612.5	614.1	612.5	607.0	595.3	578.9	561.5	541.0	519.4
150°	576.7	587.0	590.5	591.3	590.5	587.0	576.7	563.9	548.4	532.0	513.2
152.5°	560.9	569.2	572.6	573.4	572.6	569.2	560.9	550.1	538.0	523.1	506.3
155°	539.8	545.8	548.4	549.2	548.4	545.8	539.8	531.2	521.8	509.7	495.9
157.5°	520.4	525.3	527.7	527.5	527.7	525.3	520.4	513.7	506.3	497.0	485.6
160°	508.0	512.3	514.0	513.2	514.0	512.3	508.0	502.0	495.9	487.3	478.7
162.5°	496.3	499.9	500.2	500.1	500.2	499.9	496.3	491.6	486.3	479.1	471.2
165°	479.6	481.3	481.3	481.3	481.3	481.3	479.6	476.1	471.9	466.7	460.7
167.5°	463.5	465.0	464.3	464.2	464.3	465.0	463.5	461.8	458.7	454.7	450.7
170°	453.8	454.7	454.7	453.8	454.7	454.7	453.8	452.1	450.4	447.8	445.2
172.5°	444.9	446.4	445.1	444.2	445.1	446.4	444.9	444.5	443.5	441.6	439.0
175°	434.0	434.9	433.2	432.3	433.2	434.9	434.0	434.0	434.0	432.3	432.3
177.5°	427.7	428.3	426.3	426.3	426.3	428.3	427.7	428.3	428.3	428.3	427.7
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	448.2	450.1	452.5	454.3	457.4	458.8	460.6	462.0	464.6	467.0	469.8
5°	418.0	421.4	425.9	430.9	436.7	440.7	446.3	449.6	456.4	462.5	468.6
7.5°	390.6	394.8	401.2	407.6	415.2	422.0	429.0	436.7	445.3	455.6	464.0
10°	371.9	377.4	384.4	392.4	401.5	409.4	418.8	427.1	437.7	449.6	460.8
12.5°	356.9	361.6	369.4	377.0	386.8	396.6	406.2	417.2	429.6	442.8	456.8
15°	336.2	340.2	346.6	357.1	367.0	376.6	391.2	401.5	417.0	431.7	448.7
17.5°	318.6	323.6	328.9	337.9	348.3	360.2	373.2	386.2	401.1	419.7	438.8
20°	307.8	311.8	317.9	324.9	335.8	347.8	360.1	373.2	391.5	410.9	431.4
22.5°	296.0	300.3	307.3	314.9	324.1	335.5	349.1	363.5	382.6	401.6	423.9
25°	282.1	285.1	291.4	298.3	307.4	317.1	331.2	347.2	366.1	387.8	410.4
27.5°	269.1	271.6	277.4	283.4	291.6	303.2	315.8	331.9	349.7	371.7	396.8
30°	259.6	262.4	267.6	274.0	281.9	292.1	305.0	320.1	339.2	360.7	386.9
32.5°	251.5	254.0	257.9	264.2	272.1	281.9	293.9	309.3	328.4	350.2	376.0
35°	238.9	241.7	244.7	249.7	256.4	266.0	279.1	293.7	311.9	333.0	356.7
37.5°	226.4	229.5	232.1	236.6	242.7	251.2	262.5	277.7	294.2	314.5	337.3
40°	218.6	221.0	223.3	228.0	234.2	242.1	252.7	266.2	283.7	302.6	321.5
42.5°	210.9	213.1	214.9	219.1	224.8	232.4	242.5	255.7	271.9	289.6	306.3
45°	198.5	199.9	202.2	205.7	210.3	217.2	227.0	238.8	252.4	269.1	281.7
47.5°	185.3	187.4	189.2	192.3	196.1	202.9	212.3	222.3	234.8	247.2	256.0
50°	175.0	177.3	179.9	182.9	186.4	192.8	201.3	211.5	222.1	231.6	239.1
52.5°	165.5	167.6	170.3	173.1	177.5	182.9	190.2	199.2	209.7	216.5	222.7
55°	151.4	152.4	155.6	158.3	162.6	166.5	173.9	181.8	188.2	193.4	198.5
57.5°	137.0	138.3	140.2	142.7	146.8	151.4	156.6	163.7	167.4	170.0	174.1
60°	127.7	128.1	129.3	132.3	135.5	139.7	145.6	150.6	153.4	155.6	158.9
62.5°	117.5	117.6	119.6	121.8	124.2	128.7	133.5	137.6	139.8	140.9	144.1
65°	103.2	102.9	104.0	105.8	108.7	111.6	115.8	119.3	119.2	120.4	122.3
67.5°	88.7	88.3	88.3	90.0	92.2	94.9	97.7	99.9	99.9	101.4	102.5
70°	78.8	77.6	78.4	79.8	80.8	83.0	86.2	87.0	87.1	87.9	88.9
72.5°	68.6	68.2	68.8	69.4	70.1	71.8	74.6	75.0	75.1	75.5	77.1
75°	54.5	54.2	53.7	54.3	55.1	56.3	57.3	58.1	57.9	58.1	59.3
77.5°	40.9	39.8	39.5	39.9	40.0	40.8	41.8	41.8	41.9	41.9	43.2
80°	32.5	30.8	30.7	30.7	30.8	31.3	31.6	32.0	31.4	32.0	32.5
82.5°	23.8	22.9	22.8	22.6	22.7	22.8	23.1	23.2	23.2	23.4	23.7
85°	13.2	12.7	12.1	12.6	12.3	11.7	12.1	11.5	11.4	11.5	11.7
87.5°	7.4	7.4	6.7	6.5	6.0	6.0	5.3	4.8	4.4	4.1	4.5
90°	14.6	13.8	12.1	11.2	9.5	8.6	6.9	5.2	3.4	1.7	0.9
92.5°	224.3	277.1	281.5	196.1	117.4	70.5	45.4	30.6	20.0	12.7	10.5
95°	745.2	761.6	621.5	384.2	195.1	103.1	64.5	45.5	36.1	29.2	28.3
97.5°	942.9	813.3	554.9	306.7	168.2	107.3	79.4	62.4	53.0	48.1	47.1
100°	991.0	776.1	495.1	278.4	166.8	116.9	91.1	74.7	65.3	61.9	60.2
102.5°	962.2	710.8	449.7	266.8	173.0	128.5	103.5	88.5	78.4	75.6	74.6
105°	869.9	623.1	405.7	262.2	185.6	147.8	123.8	110.0	101.4	97.1	97.1
107.5°	775.6	562.8	387.1	270.1	204.6	168.0	146.3	132.0	124.9	120.9	119.2
110°	721.9	534.6	381.6	277.6	218.3	183.0	160.7	147.8	140.1	136.6	134.9



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	682.1	518.1	381.6	287.2	231.4	197.5	175.8	163.0	155.2	152.5	150.8
115°	638.6	500.2	384.2	301.7	251.8	220.1	198.5	185.6	177.9	175.3	173.7
117.5°	612.7	491.5	389.9	318.2	272.9	242.7	222.0	207.3	199.6	196.8	194.2
120°	598.2	487.3	395.4	329.2	287.9	257.9	236.3	221.8	214.0	210.6	208.0
122.5°	585.8	483.9	400.2	341.6	302.4	272.3	250.8	234.8	227.0	224.3	222.5
125°	569.0	479.6	408.3	358.4	321.5	293.1	270.8	254.4	246.7	242.4	240.6
127.5°	553.5	477.5	417.4	373.8	339.8	312.5	290.2	272.9	263.0	257.5	254.9
130°	543.2	476.1	422.9	384.2	351.5	324.9	302.6	284.5	273.4	266.5	263.9
132.5°	534.9	476.1	429.0	393.1	362.6	335.9	313.6	294.8	282.2	274.0	270.8
135°	525.1	476.1	437.5	405.7	377.3	350.7	327.4	309.4	295.7	285.3	281.9
137.5°	516.4	477.2	445.2	415.0	387.8	363.6	339.7	322.0	308.2	298.6	296.0
140°	512.3	477.9	448.7	421.2	395.4	370.5	347.2	330.9	317.2	306.9	304.3
142.5°	508.9	478.5	450.7	424.6	400.2	376.6	354.8	339.1	325.4	315.8	313.9
145°	503.7	477.9	453.0	429.7	408.3	385.9	366.2	350.7	338.6	330.0	328.3
147.5°	498.3	475.6	453.8	432.8	413.5	393.8	376.4	363.1	351.9	344.5	343.5
150°	494.2	473.6	453.8	434.9	416.9	398.0	383.3	371.3	360.2	354.1	352.4
152.5°	489.4	470.9	453.1	436.3	420.3	402.8	389.5	378.2	368.4	363.1	362.1
155°	481.3	465.9	451.3	437.5	423.7	409.1	397.1	388.5	379.9	374.7	374.7
157.5°	473.7	460.7	449.0	438.3	426.6	414.1	405.0	397.4	390.0	385.9	386.1
160°	467.6	457.3	446.9	438.3	428.0	416.9	409.1	402.3	396.2	392.8	393.6
162.5°	462.1	453.1	444.9	437.6	429.4	419.7	413.3	407.8	402.4	399.0	399.8
165°	453.8	446.9	441.8	436.6	429.7	422.9	417.8	414.3	410.0	407.4	409.1
167.5°	445.7	440.9	437.0	434.5	429.7	424.0	420.9	418.4	416.0	414.5	415.3
170°	440.9	437.5	434.9	433.2	429.7	425.4	422.9	421.2	419.5	418.6	419.5
172.5°	436.1	433.3	432.1	431.8	429.0	425.4	424.2	423.2	421.5	420.7	422.2
175°	429.7	428.9	428.9	429.7	428.0	425.4	425.4	425.4	424.6	423.7	425.4
177.5°	427.0	426.3	426.3	427.7	427.0	425.6	425.6	426.3	425.6	425.6	427.0
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	471.3	473.5	474.9	477.6	479.8	481.1	482.2	483.2	484.3	485.3	488.0
5°	474.3	479.5	483.9	490.6	496.8	501.5	506.7	511.3	515.1	520.5	524.6
7.5°	472.9	482.2	491.8	502.3	513.0	522.9	532.1	540.6	548.4	557.8	566.0
10°	471.7	484.2	496.5	510.7	525.2	537.5	549.1	560.9	569.4	581.3	591.5
12.5°	470.8	485.5	500.4	517.4	533.3	550.8	566.1	574.7	587.7	597.3	609.3
15°	466.7	486.2	506.7	525.8	548.5	564.6	578.2	594.9	607.0	619.1	632.2
17.5°	459.5	481.6	504.5	529.6	551.3	568.6	586.1	602.2	616.6	632.9	649.3
20°	456.2	478.3	504.5	530.2	551.5	569.6	587.5	605.2	621.1	642.0	660.9
22.5°	449.2	475.9	500.1	525.1	547.0	566.7	587.0	607.1	628.3	651.9	675.5
25°	436.7	463.7	489.4	514.1	536.1	560.9	582.6	609.4	636.5	667.7	697.2
27.5°	423.7	449.6	473.1	497.0	522.7	550.7	578.8	609.2	644.7	684.2	725.7
30°	413.2	437.7	460.5	485.0	511.9	543.3	574.2	610.4	651.3	695.7	745.1
32.5°	401.0	423.5	445.7	471.7	500.9	534.1	570.1	609.8	659.0	709.4	760.2
35°	380.0	398.9	421.8	449.4	482.4	520.5	562.1	609.0	665.5	723.4	766.1
37.5°	355.2	372.7	396.8	427.1	461.8	502.6	551.9	607.6	667.6	713.8	727.5
40°	338.4	354.7	379.8	411.2	446.6	489.8	543.9	602.8	660.9	690.3	679.0
42.5°	320.6	337.7	362.1	393.2	431.4	478.4	533.9	592.8	641.5	652.6	613.5
45°	292.5	310.1	334.2	365.7	406.7	457.6	515.5	569.0	597.0	577.0	516.3
47.5°	266.3	282.9	305.2	337.7	380.0	432.7	488.4	531.1	533.3	485.3	420.5
50°	248.5	263.8	286.3	318.7	360.7	414.1	464.3	498.0	482.8	428.5	366.3
52.5°	231.0	246.0	268.1	300.2	341.7	390.6	437.5	461.1	432.6	376.8	323.6
55°	205.7	218.9	240.6	270.2	309.5	354.9	394.7	402.9	365.8	311.0	267.8
57.5°	181.1	193.3	213.0	240.3	276.4	316.5	347.7	345.9	306.8	259.7	225.4
60°	164.4	176.2	193.8	220.4	253.3	287.9	314.5	308.2	269.4	228.8	199.9
62.5°	149.4	160.1	176.6	199.9	229.9	261.9	283.8	274.4	236.4	201.0	178.1
65°	127.3	136.3	150.4	170.3	195.2	221.6	238.6	226.4	194.0	166.3	148.0
67.5°	106.2	113.5	125.3	141.2	162.4	183.7	193.9	181.8	155.8	135.6	122.0
70°	92.9	99.3	108.4	122.5	141.0	158.9	166.7	155.8	133.5	116.1	106.4
72.5°	79.6	84.8	92.8	105.6	120.4	135.9	142.7	132.2	113.9	99.3	90.2
75°	61.5	65.1	70.6	79.4	91.1	103.5	107.2	98.1	86.4	75.4	69.4
77.5°	44.0	47.0	51.2	56.7	65.1	72.9	76.2	70.9	61.9	54.9	50.0
80°	33.8	35.4	39.0	43.6	50.1	55.1	57.3	53.9	47.5	42.4	38.6
82.5°	24.1	25.7	27.8	31.6	35.8	39.2	41.5	39.3	34.7	30.6	28.4
85°	11.7	12.7	13.9	15.5	18.7	20.7	20.5	19.1	17.3	15.8	14.6
87.5°	4.5	5.0	5.8	7.0	7.7	8.6	9.2	9.1	8.8	8.5	8.2
90°	1.7	3.4	5.2	6.9	8.6	9.5	11.2	12.1	13.8	14.6	15.5
92.5°	12.7	20.0	30.6	45.4	70.5	117.4	196.1	281.5	277.1	224.3	152.3
95°	29.2	36.1	45.5	64.5	103.1	195.1	384.2	621.5	761.6	745.2	618.0
97.5°	48.1	53.0	62.4	79.4	107.3	168.2	306.7	554.9	813.3	942.9	920.4
100°	61.9	65.3	74.7	91.1	116.9	166.8	278.4	495.1	776.1	991.0	1057.2
102.5°	75.6	78.4	88.5	103.5	128.5	173.0	266.8	449.7	710.8	962.2	1103.3
105°	97.1	101.4	110.0	123.8	147.8	185.6	262.2	405.7	623.1	869.9	1076.1
107.5°	120.9	124.9	132.0	146.3	168.0	204.6	270.1	387.1	562.8	775.6	979.1
110°	136.6	140.1	147.8	160.7	183.0	218.3	277.6	381.6	534.6	721.9	907.7





TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	152.5	155.2	163.0	175.8	197.5	231.4	287.2	381.6	518.1	682.1	851.3
115°	175.3	177.9	185.6	198.5	220.1	251.8	301.7	384.2	500.2	638.6	780.4
117.5°	196.8	199.6	207.3	222.0	242.7	272.9	318.2	389.9	491.5	612.7	734.7
120°	210.6	214.0	221.8	236.3	257.9	287.9	329.2	395.4	487.3	598.2	710.0
122.5°	224.3	227.0	234.8	250.8	272.3	302.4	341.6	400.2	483.9	585.8	691.4
125°	242.4	246.7	254.4	270.8	293.1	321.5	358.4	408.3	479.6	569.0	664.4
127.5°	257.5	263.0	272.9	290.2	312.5	339.8	373.8	417.4	477.5	553.5	636.9
130°	266.5	273.4	284.5	302.6	324.9	351.5	384.2	422.9	476.1	543.2	619.7
132.5°	274.0	282.2	294.8	313.6	335.9	362.6	393.1	429.0	476.1	534.9	602.5
135°	285.3	295.7	309.4	327.4	350.7	377.3	405.7	437.5	476.1	525.1	580.1
137.5°	298.6	308.2	322.0	339.7	363.6	387.8	415.0	445.2	477.2	516.4	561.3
140°	306.9	317.2	330.9	347.2	370.5	395.4	421.2	448.7	477.9	512.3	551.0
142.5°	315.8	325.4	339.1	354.8	376.6	400.2	424.6	450.7	478.5	508.9	542.0
145°	330.0	338.6	350.7	366.2	385.9	408.3	429.7	453.0	477.9	503.7	530.3
147.5°	344.5	351.9	363.1	376.4	393.8	413.5	432.8	453.8	475.6	498.3	519.4
150°	354.1	360.2	371.3	383.3	398.0	416.9	434.9	453.8	473.6	494.2	513.2
152.5°	363.1	368.4	378.2	389.5	402.8	420.3	436.3	453.1	470.9	489.4	506.3
155°	374.7	379.9	388.5	397.1	409.1	423.7	437.5	451.3	465.9	481.3	495.9
157.5°	385.9	390.0	397.4	405.0	414.1	426.6	438.3	449.0	460.7	473.7	485.6
160°	392.8	396.2	402.3	409.1	416.9	428.0	438.3	446.9	457.3	467.6	478.7
162.5°	399.0	402.4	407.8	413.3	419.7	429.4	437.6	444.9	453.1	462.1	471.2
165°	407.4	410.0	414.3	417.8	422.9	429.7	436.6	441.8	446.9	453.8	460.7
167.5°	414.5	416.0	418.4	420.9	424.0	429.7	434.5	437.0	440.9	445.7	450.7
170°	418.6	419.5	421.2	422.9	425.4	429.7	433.2	434.9	437.5	440.9	445.2
172.5°	420.7	421.5	423.2	424.2	425.4	429.0	431.8	432.1	433.3	436.1	439.0
175°	423.7	424.6	425.4	425.4	425.4	428.0	429.7	428.9	428.9	429.7	432.3
177.5°	425.6	425.6	426.3	425.6	425.6	427.0	427.7	426.3	426.3	427.0	427.7
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	490.3	491.5	494.2	493.3	494.5	495.2	495.8
5°	529.8	536.1	539.0	538.6	542.8	541.7	540.7
7.5°	574.5	581.2	585.0	589.6	592.3	592.5	594.9
10°	599.9	608.6	612.2	617.2	620.4	622.2	621.9
12.5°	619.2	626.1	634.1	636.5	640.8	643.2	642.3
15°	642.7	653.6	661.9	666.1	671.5	673.0	675.2
17.5°	663.5	678.1	687.9	700.9	705.8	708.8	707.0
20°	679.2	698.5	708.3	723.8	732.4	736.9	735.3
22.5°	697.8	718.8	736.8	750.2	763.2	769.4	770.7
25°	729.8	758.4	784.9	802.5	818.6	822.4	830.8
27.5°	765.4	799.2	827.5	846.1	857.3	861.5	864.2
30°	787.8	821.5	842.7	854.7	858.2	857.9	857.5
32.5°	798.8	819.8	824.0	820.6	812.4	805.5	798.2
35°	783.3	767.6	744.1	713.9	691.6	669.1	666.8
37.5°	704.5	654.2	615.1	571.4	546.3	530.7	520.0
40°	630.3	573.2	525.8	489.0	463.4	453.2	443.2
42.5°	549.7	495.2	453.2	422.5	403.2	391.9	384.1
45°	446.6	398.5	365.7	343.4	328.0	319.3	314.4
47.5°	366.0	330.4	302.5	286.4	275.9	269.1	269.1
50°	322.7	288.7	270.2	257.4	248.3	242.9	243.9
52.5°	284.3	258.9	243.1	232.5	225.7	222.4	222.2
55°	237.7	219.5	209.1	201.3	196.7	193.0	193.8
57.5°	203.4	188.0	181.0	174.5	171.3	169.9	167.6
60°	182.0	170.1	164.1	158.9	155.8	154.5	152.4
62.5°	163.1	153.7	147.9	143.7	140.9	140.4	138.7
65°	137.1	129.9	124.8	122.8	119.8	119.0	119.0
67.5°	113.0	107.9	103.8	102.0	100.7	100.9	100.0
70°	97.9	93.7	91.1	89.1	88.2	88.3	87.6
72.5°	85.7	80.9	78.7	77.5	76.2	76.7	76.4
75°	64.8	62.5	61.3	60.1	59.3	58.9	58.5
77.5°	47.6	45.5	44.6	43.9	44.1	43.0	43.8
80°	36.8	35.0	34.4	33.4	33.2	33.2	33.1
82.5°	26.9	25.9	25.5	24.7	24.3	24.6	24.1
85°	13.9	13.2	12.9	12.9	12.6	12.1	13.2
87.5°	8.4	7.9	8.3	8.1	8.1	8.1	7.7
90°	16.4	17.2	18.9	18.9	18.9	19.8	19.8
92.5°	110.6	83.2	70.5	59.5	57.4	56.2	54.8
95°	487.3	381.6	309.4	248.4	222.7	215.8	202.0
97.5°	828.7	725.7	625.3	572.3	524.1	499.2	488.2
100°	1015.1	926.5	837.2	777.8	716.0	684.2	670.5
102.5°	1129.2	1086.8	1026.2	962.9	918.9	884.2	873.9
105°	1193.9	1231.7	1222.2	1194.7	1166.4	1149.2	1138.8
107.5°	1136.3	1233.4	1278.2	1292.2	1292.0	1286.3	1279.4
110°	1070.9	1192.1	1265.2	1303.9	1320.2	1326.2	1326.2



TEST NUMBER: P333144-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1006.3	1128.9	1215.0	1271.5	1299.6	1314.6	1320.7
115°	913.7	1031.4	1125.1	1192.1	1233.4	1257.5	1268.7
117.5°	849.5	951.0	1036.9	1104.0	1146.6	1170.4	1177.3
120°	813.1	907.7	983.3	1046.9	1088.1	1111.4	1118.3
122.5°	787.0	871.2	942.0	998.8	1036.6	1059.8	1066.0
125°	752.1	826.8	888.7	936.9	972.1	991.0	999.6
127.5°	718.8	788.5	846.4	890.1	921.2	939.1	942.9
130°	695.3	762.4	818.3	861.3	889.6	906.8	912.0
132.5°	673.3	734.2	788.0	831.0	859.4	875.1	881.0
135°	639.5	694.5	743.5	781.3	809.7	825.1	830.3
137.5°	609.2	655.0	696.5	730.4	756.2	770.5	776.1
140°	591.3	630.9	667.0	698.8	721.2	734.0	738.3
142.5°	576.2	610.3	641.5	668.6	687.4	699.6	703.3
145°	557.0	583.6	606.8	627.4	642.0	651.5	655.0
147.5°	541.0	561.5	578.9	595.3	607.0	612.5	614.1
150°	532.0	548.4	563.9	576.7	587.0	590.5	591.3
152.5°	523.1	538.0	550.1	560.9	569.2	572.6	573.4
155°	509.7	521.8	531.2	539.8	545.8	548.4	549.2
157.5°	497.0	506.3	513.7	520.4	525.3	527.7	527.5
160°	487.3	495.9	502.0	508.0	512.3	514.0	513.2
162.5°	479.1	486.3	491.6	496.3	499.9	500.2	500.1
165°	466.7	471.9	476.1	479.6	481.3	481.3	481.3
167.5°	454.7	458.7	461.8	463.5	465.0	464.3	464.2
170°	447.8	450.4	452.1	453.8	454.7	454.7	453.8
172.5°	441.6	443.5	444.5	444.9	446.4	445.1	444.2
175°	432.3	434.0	434.0	434.0	434.9	433.2	432.3
177.5°	428.3	428.3	428.3	427.7	428.3	426.3	426.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3

(END OF REPORT)