

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333153-935

Luminaire Tested: **S125DIP-S375D1205U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333153-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D1205U935-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5046.6 lumens  
Efficiency: N/A  
Efficacy: 119.6 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	93	88	85	81	82	79	76	73	61	59	58	45	44	43	30	30	29	22
2	84	77	71	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	44	40	35	33	30	24	22	21	16
4	70	60	53	47	63	54	47	43	42	38	34	31	28	26	21	20	18	14
5	64	53	46	40	57	48	41	36	38	33	29	28	25	23	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3027	3027	3027	3027
5°	3505	3038	2660	3038
10°	4078	3022	2330	3022
15°	4515	3000	2150	3000
20°	5054	2965	2004	2965
25°	5920	2925	1934	2925
30°	6395	2885	1873	2885
35°	5257	2812	1832	2812
40°	3737	2710	1788	2710
45°	2872	2573	1763	2573
50°	2451	2402	1758	2402
55°	2182	2235	1775	2235
60°	1969	2052	1820	2052
65°	1819	1869	1867	1869
70°	1654	1679	1894	1679
75°	1460	1480	1876	1480
80°	1231	1209	1715	1209
85°	978	867	1386	867



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.1	0.9
10°-20°	134.4	2.7
20°-30°	218.2	4.3
30°-40°	266.1	5.3
40°-50°	242.1	4.8
50°-60°	192.8	3.8
60°-70°	134.3	2.7
70°-80°	71.6	1.4
80°-90°	20.8	0.4
90°-100°	359.7	7.1
100°-110°	773.2	15.3
110°-120°	725.6	14.4
120°-130°	588.1	11.7
130°-140°	471.9	9.4
140°-150°	356.1	7.1
150°-160°	250.7	5.0
160°-170°	147.8	2.9
170°-180°	48.1	1.0
0°-30°	397.6	7.9
0°-40°	663.7	13.2
0°-60°	1098.7	21.8
0°-90°	1325.4	26.3
90°-120°	1858.5	36.8
90°-150°	3274.7	64.9
90°-180°	3721.0	73.7
0°-180°	5046.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	469	469	469	469	469	
5°	541	469	410	469	541	54
15°	675	449	322	449	675	193
25°	831	410	271	410	831	379
35°	667	357	232	357	667	408
45°	314	282	193	282	314	252
55°	194	198	158	198	194	174
65°	119	122	122	122	119	118
75°	58	59	75	59	58	63
85°	13	12	19	12	13	16
90°	23	1	23	1	23	16
95°	235	33	235	33	235	333
105°	1326	113	1326	113	1326	1318
115°	1477	202	1477	202	1477	1443
125°	1164	280	1164	280	1164	1053
135°	966	328	966	328	966	749
145°	762	382	762	382	762	484
155°	639	436	639	436	639	298
165°	560	476	560	476	560	160
175°	503	495	503	495	503	49
180°	496	496	496	496	496	



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	495.8	495.2	494.5	493.3	494.2	491.5	490.3	488.0	485.3	484.3	483.2
5°	540.7	541.7	542.8	538.6	539.0	536.1	529.8	524.6	520.5	515.1	511.3
7.5°	594.9	592.5	592.3	589.6	585.0	581.2	574.5	566.0	557.8	548.4	540.6
10°	621.9	622.2	620.4	617.2	612.2	608.6	599.9	591.5	581.3	569.4	560.9
12.5°	642.3	643.2	640.8	636.5	634.1	626.1	619.2	609.3	597.3	587.7	574.7
15°	675.2	673.0	671.5	666.1	661.9	653.6	642.7	632.2	619.1	607.0	594.9
17.5°	707.0	708.8	705.8	700.9	687.9	678.1	663.5	649.3	632.9	616.6	602.2
20°	735.3	736.9	732.4	723.8	708.3	698.5	679.2	660.9	642.0	621.1	605.2
22.5°	770.7	769.4	763.2	750.2	736.8	718.8	697.8	675.5	651.9	628.3	607.1
25°	830.8	822.4	818.6	802.5	784.9	758.4	729.8	697.2	667.7	636.5	609.4
27.5°	864.2	861.5	857.3	846.1	827.5	799.2	765.4	725.7	684.2	644.7	609.2
30°	857.5	857.9	858.2	854.7	842.7	821.5	787.8	745.1	695.7	651.3	610.4
32.5°	798.2	805.5	812.4	820.6	824.0	819.8	798.8	760.2	709.4	659.0	609.8
35°	666.8	669.1	691.6	713.9	744.1	767.6	783.3	766.1	723.4	665.5	609.0
37.5°	520.0	530.7	546.3	571.4	615.1	654.2	704.5	727.5	713.8	667.6	607.6
40°	443.2	453.2	463.4	489.0	525.8	573.2	630.3	679.0	690.3	660.9	602.8
42.5°	384.1	391.9	403.2	422.5	453.2	495.2	549.7	613.5	652.6	641.5	592.8
45°	314.4	319.3	328.0	343.4	365.7	398.5	446.6	516.3	577.0	597.0	569.0
47.5°	269.1	269.1	275.9	286.4	302.5	330.4	366.0	420.5	485.3	533.3	531.1
50°	243.9	242.9	248.3	257.4	270.2	288.7	322.7	366.3	428.5	482.8	498.0
52.5°	222.2	222.4	225.7	232.5	243.1	258.9	284.3	323.6	376.8	432.6	461.1
55°	193.8	193.0	196.7	201.3	209.1	219.5	237.7	267.8	311.0	365.8	402.9
57.5°	167.6	169.9	171.3	174.5	181.0	188.0	203.4	225.4	259.7	306.8	345.9
60°	152.4	154.5	155.8	158.9	164.1	170.1	182.0	199.9	228.8	269.4	308.2
62.5°	138.7	140.4	140.9	143.7	147.9	153.7	163.1	178.1	201.0	236.4	274.4
65°	119.0	119.0	119.8	122.8	124.8	129.9	137.1	148.0	166.3	194.0	226.4
67.5°	100.0	100.9	100.7	102.0	103.8	107.9	113.0	122.0	135.6	155.8	181.8
70°	87.6	88.3	88.2	89.1	91.1	93.7	97.9	106.4	116.1	133.5	155.8
72.5°	76.4	76.7	76.2	77.5	78.7	80.9	85.7	90.2	99.3	113.9	132.2
75°	58.5	58.9	59.3	60.1	61.3	62.5	64.8	69.4	75.4	86.4	98.1
77.5°	43.8	43.0	44.1	43.9	44.6	45.5	47.6	50.0	54.9	61.9	70.9
80°	33.1	33.2	33.2	33.4	34.4	35.0	36.8	38.6	42.4	47.5	53.9
82.5°	24.1	24.6	24.3	24.7	25.5	25.9	26.9	28.4	30.6	34.7	39.3
85°	13.2	12.1	12.6	12.9	12.9	13.2	13.9	14.6	15.8	17.3	19.1
87.5°	8.4	8.8	8.7	8.7	8.9	8.4	8.9	8.7	9.0	9.2	9.5
90°	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0	17.0	16.0	14.0
92.5°	63.8	65.4	66.8	69.2	82.1	96.9	128.6	177.3	261.1	322.5	327.8
95°	235.1	251.2	259.1	289.1	360.2	444.2	567.2	719.3	867.4	886.4	723.3
97.5°	568.3	581.1	610.1	666.1	727.9	844.8	964.7	1071.3	1097.5	946.6	645.9
100°	780.3	796.3	833.4	905.4	974.4	1078.5	1181.6	1230.5	1153.5	903.4	576.3
102.5°	1017.3	1029.2	1069.4	1120.7	1194.6	1265.0	1314.4	1284.2	1119.9	827.3	523.4
105°	1325.6	1337.6	1357.6	1390.6	1422.6	1433.7	1389.7	1252.6	1012.4	725.3	472.2
107.5°	1489.3	1497.3	1503.9	1504.1	1487.9	1435.6	1322.6	1139.7	902.8	655.0	450.6
110°	1543.7	1543.7	1536.7	1517.7	1472.7	1387.6	1246.6	1056.4	840.3	622.2	444.2



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1537.3	1530.1	1512.7	1480.1	1414.2	1314.0	1171.3	990.8	793.9	603.0	444.2
115°	1476.6	1463.6	1435.6	1387.6	1309.6	1200.5	1063.5	908.4	743.3	582.3	447.2
117.5°	1370.4	1362.4	1334.6	1285.0	1206.9	1106.9	988.9	855.1	713.1	572.0	453.8
120°	1301.6	1293.6	1266.5	1218.6	1144.5	1056.4	946.4	826.4	696.3	567.2	460.2
122.5°	1240.8	1233.6	1206.5	1162.5	1096.5	1014.1	916.0	804.8	681.9	563.3	465.8
125°	1163.6	1153.5	1131.5	1090.5	1034.5	962.4	875.4	773.4	662.3	558.3	475.2
127.5°	1097.5	1093.1	1072.3	1036.0	985.2	917.8	836.5	741.3	644.3	555.9	485.8
130°	1061.4	1055.5	1035.4	1002.5	952.4	887.4	809.3	721.3	632.3	554.2	492.2
132.5°	1025.5	1018.6	1000.2	967.2	917.2	854.5	783.8	701.3	622.7	554.2	499.4
135°	966.5	960.4	942.5	909.4	865.4	808.4	744.3	675.3	611.3	554.2	509.2
137.5°	903.4	896.8	880.2	850.2	810.8	762.3	709.1	653.3	601.1	555.4	518.2
140°	859.4	854.4	839.4	813.4	776.4	734.3	688.3	641.3	596.2	556.2	522.2
142.5°	818.6	814.3	800.1	778.2	746.7	710.3	670.7	630.9	592.3	557.1	524.6
145°	762.3	758.4	747.3	730.3	706.3	679.3	648.2	617.3	586.3	556.2	527.3
147.5°	714.7	712.9	706.5	692.9	673.9	653.5	629.6	604.5	580.1	553.6	528.2
150°	688.3	687.3	683.3	671.3	656.3	638.3	619.3	597.3	575.2	551.2	528.2
152.5°	667.5	666.5	662.5	652.9	640.3	626.3	608.9	589.3	569.6	548.0	527.4
155°	639.3	638.3	635.2	628.3	618.3	607.3	593.2	577.2	560.3	542.3	525.2
157.5°	614.1	614.2	611.5	605.6	597.9	589.3	578.4	565.2	551.5	536.2	522.6
160°	597.3	598.3	596.2	591.2	584.3	577.2	567.2	557.2	544.2	532.3	520.2
162.5°	582.0	582.3	581.9	577.6	572.2	566.0	557.7	548.5	537.9	527.4	517.8
165°	560.3	560.3	560.3	558.3	554.2	549.2	543.2	536.2	528.2	520.2	514.2
167.5°	540.3	540.4	541.2	539.4	537.4	533.8	529.3	524.6	518.8	513.2	508.6
170°	528.2	529.3	529.3	528.2	526.2	524.3	521.2	518.2	513.2	509.2	506.3
172.5°	517.0	518.1	519.6	517.8	517.5	516.3	514.0	511.0	507.6	504.5	503.0
175°	503.3	504.2	506.3	505.2	505.2	505.2	503.3	503.3	500.2	499.2	499.2
177.5°	496.2	496.2	498.6	497.8	498.6	498.6	498.6	497.8	497.1	496.2	496.2
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	482.2	481.1	479.8	477.6	474.9	473.5	471.3	469.8	467.0	464.6	462.0
5°	506.7	501.5	496.8	490.6	483.9	479.5	474.3	468.6	462.5	456.4	449.6
7.5°	532.1	522.9	513.0	502.3	491.8	482.2	472.9	464.0	455.6	445.3	436.7
10°	549.1	537.5	525.2	510.7	496.5	484.2	471.7	460.8	449.6	437.7	427.1
12.5°	566.1	550.8	533.3	517.4	500.4	485.5	470.8	456.8	442.8	429.6	417.2
15°	578.2	564.6	548.5	525.8	506.7	486.2	466.7	448.7	431.7	417.0	401.5
17.5°	586.1	568.6	551.3	529.6	504.5	481.6	459.5	438.8	419.7	401.1	386.2
20°	587.5	569.6	551.5	530.2	504.5	478.3	456.2	431.4	410.9	391.5	373.2
22.5°	587.0	566.7	547.0	525.1	500.1	475.9	449.2	423.9	401.6	382.6	363.5
25°	582.6	560.9	536.1	514.1	489.4	463.7	436.7	410.4	387.8	366.1	347.2
27.5°	578.8	550.7	522.7	497.0	473.1	449.6	423.7	396.8	371.7	349.7	331.9
30°	574.2	543.3	511.9	485.0	460.5	437.7	413.2	386.9	360.7	339.2	320.1
32.5°	570.1	534.1	500.9	471.7	445.7	423.5	401.0	376.0	350.2	328.4	309.3
35°	562.1	520.5	482.4	449.4	421.8	398.9	380.0	356.7	333.0	311.9	293.7
37.5°	551.9	502.6	461.8	427.1	396.8	372.7	355.2	337.3	314.5	294.2	277.7
40°	543.9	489.8	446.6	411.2	379.8	354.7	338.4	321.5	302.6	283.7	266.2
42.5°	533.9	478.4	431.4	393.2	362.1	337.7	320.6	306.3	289.6	271.9	255.7
45°	515.5	457.6	406.7	365.7	334.2	310.1	292.5	281.7	269.1	252.4	238.8
47.5°	488.4	432.7	380.0	337.7	305.2	282.9	266.3	256.0	247.2	234.8	222.3
50°	464.3	414.1	360.7	318.7	286.3	263.8	248.5	239.1	231.6	222.1	211.5
52.5°	437.5	390.6	341.7	300.2	268.1	246.0	231.0	222.7	216.5	209.7	199.2
55°	394.7	354.9	309.5	270.2	240.6	218.9	205.7	198.5	193.4	188.2	181.8
57.5°	347.7	316.5	276.4	240.3	213.0	193.3	181.1	174.1	170.0	167.4	163.7
60°	314.5	287.9	253.3	220.4	193.8	176.2	164.4	158.9	155.6	153.4	150.6
62.5°	283.8	261.9	229.9	199.9	176.6	160.1	149.4	144.1	140.9	139.8	137.6
65°	238.6	221.6	195.2	170.3	150.4	136.3	127.3	122.3	120.4	119.2	119.3
67.5°	193.9	183.7	162.4	141.2	125.3	113.5	106.2	102.5	101.4	99.9	99.9
70°	166.7	158.9	141.0	122.5	108.4	99.3	92.9	88.9	87.9	87.1	87.0
72.5°	142.7	135.9	120.4	105.6	92.8	84.8	79.6	77.1	75.5	75.1	75.0
75°	107.2	103.5	91.1	79.4	70.6	65.1	61.5	59.3	58.1	57.9	58.1
77.5°	76.2	72.9	65.1	56.7	51.2	47.0	44.0	43.2	41.9	41.9	41.8
80°	57.3	55.1	50.1	43.6	39.0	35.4	33.8	32.5	32.0	31.4	32.0
82.5°	41.5	39.2	35.8	31.6	27.8	25.7	24.1	23.7	23.4	23.2	23.2
85°	20.5	20.7	18.7	15.5	13.9	12.7	11.7	11.7	11.5	11.4	11.5
87.5°	9.6	8.9	8.0	7.1	5.9	5.1	4.6	4.5	4.2	4.5	5.0
90°	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0	2.0	4.0	6.0
92.5°	228.3	136.6	82.1	52.9	35.6	23.2	14.8	12.2	14.8	23.2	35.6
95°	447.2	227.1	120.0	75.0	53.0	42.0	34.0	33.0	34.0	42.0	53.0
97.5°	357.0	195.7	124.8	92.5	72.7	61.6	56.1	54.8	56.1	61.6	72.7
100°	324.2	194.1	136.0	106.1	87.0	76.0	72.1	70.0	72.1	76.0	87.0
102.5°	310.6	201.3	149.6	120.5	103.1	91.3	88.1	86.9	88.1	91.3	103.1
105°	305.1	216.1	172.1	144.0	128.0	118.0	113.0	113.0	113.0	118.0	128.0
107.5°	314.4	238.1	195.4	170.3	153.7	145.4	140.7	138.6	140.7	145.4	153.7
110°	323.1	254.1	213.1	187.1	172.1	163.1	159.1	157.0	159.1	163.1	172.1





TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.3	269.3	229.9	204.7	189.7	180.6	177.5	175.5	177.5	180.6	189.7
115°	351.1	293.2	256.1	231.1	216.1	207.1	204.1	202.1	204.1	207.1	216.1
117.5°	370.4	317.5	282.5	258.3	241.3	232.3	229.1	226.1	229.1	232.3	241.3
120°	383.1	335.2	300.1	275.1	258.1	249.1	245.1	242.1	245.1	249.1	258.1
122.5°	397.6	352.0	316.9	292.0	273.3	264.3	261.1	258.9	261.1	264.3	273.3
125°	417.2	374.2	341.1	315.1	296.1	287.1	282.1	280.1	282.1	287.1	296.1
127.5°	435.2	395.5	363.8	337.8	317.5	306.2	299.7	296.7	299.7	306.2	317.5
130°	447.2	409.1	378.2	352.1	331.1	318.1	310.1	307.1	310.1	318.1	331.1
132.5°	457.6	422.0	391.0	365.0	343.2	328.6	318.9	315.1	318.9	328.6	343.2
135°	472.2	439.2	408.2	381.2	360.2	344.1	332.2	328.1	332.2	344.1	360.2
137.5°	483.0	451.4	423.2	395.4	374.8	358.8	347.6	344.6	347.6	358.8	374.8
140°	490.3	460.2	431.2	404.2	385.2	369.2	357.1	354.1	357.1	369.2	385.2
142.5°	494.2	465.8	438.4	413.0	394.8	378.8	367.6	365.3	367.6	378.8	394.8
145°	500.2	475.2	449.2	426.2	408.2	394.2	384.2	382.2	384.2	394.2	408.2
147.5°	503.9	481.2	458.4	438.2	422.6	409.6	401.0	399.8	401.0	409.6	422.6
150°	506.3	485.2	463.2	446.2	432.2	419.2	412.2	410.2	412.2	419.2	432.2
152.5°	507.8	489.2	468.8	453.4	440.2	428.8	422.6	421.4	422.6	428.8	440.2
155°	509.2	493.2	476.2	462.2	452.2	442.2	436.2	436.2	436.2	442.2	452.2
157.5°	510.2	496.6	482.0	471.4	462.6	454.0	449.2	449.4	449.2	454.0	462.6
160°	510.2	498.3	485.2	476.2	468.2	461.2	457.2	458.2	457.2	461.2	468.2
162.5°	509.5	499.8	488.4	481.0	474.6	468.4	464.4	465.4	464.4	468.4	474.6
165°	508.2	500.2	492.2	486.2	482.2	477.3	474.2	476.2	474.2	477.3	482.2
167.5°	505.8	500.2	493.6	489.8	487.0	484.2	482.4	483.5	482.4	484.2	487.0
170°	504.2	500.2	495.2	492.2	490.3	488.2	487.2	488.2	487.2	488.2	490.3
172.5°	502.7	499.4	495.2	493.8	492.6	490.6	489.7	491.5	489.7	490.6	492.6
175°	500.2	498.3	495.2	495.2	495.2	494.2	493.2	495.2	493.2	494.2	495.2
177.5°	497.8	497.1	495.4	495.4	496.2	495.4	495.4	497.1	495.4	495.4	496.2
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	460.6	458.8	457.4	454.3	452.5	450.1	448.2	450.3	448.1	449.0	447.5
5°	446.3	440.7	436.7	430.9	425.9	421.4	418.0	417.4	415.8	415.0	412.6
7.5°	429.0	422.0	415.2	407.6	401.2	394.8	390.6	387.2	385.0	381.9	379.9
10°	418.8	409.4	401.5	392.4	384.4	377.4	371.9	369.0	366.4	362.7	361.3
12.5°	406.2	396.6	386.8	377.0	369.4	361.6	356.9	352.7	350.9	346.6	346.2
15°	391.2	376.6	367.0	357.1	346.6	340.2	336.2	331.7	329.7	326.7	324.5
17.5°	373.2	360.2	348.3	337.9	328.9	323.6	318.6	315.5	312.0	310.0	306.5
20°	360.1	347.8	335.8	324.9	317.9	311.8	307.8	304.8	301.2	300.2	296.6
22.5°	349.1	335.5	324.1	314.9	307.3	300.3	296.0	293.9	291.5	288.4	287.7
25°	331.2	317.1	307.4	298.3	291.4	285.1	282.1	279.6	277.2	274.9	274.1
27.5°	315.8	303.2	291.6	283.4	277.4	271.6	269.1	265.9	264.2	262.3	260.2
30°	305.0	292.1	281.9	274.0	267.6	262.4	259.6	257.4	255.9	254.3	253.0
32.5°	293.9	281.9	272.1	264.2	257.9	254.0	251.5	249.9	248.2	246.3	244.8
35°	279.1	266.0	256.4	249.7	244.7	241.7	238.9	237.5	235.6	235.6	233.9
37.5°	262.5	251.2	242.7	236.6	232.1	229.5	226.4	225.5	224.2	223.3	222.8
40°	252.7	242.1	234.2	228.0	223.3	221.0	218.6	217.1	216.3	215.2	214.9
42.5°	242.5	232.4	224.8	219.1	214.9	213.1	210.9	209.7	208.1	206.8	206.6
45°	227.0	217.2	210.3	205.7	202.2	199.9	198.5	196.1	195.4	193.8	193.6
47.5°	212.3	202.9	196.1	192.3	189.2	187.4	185.3	182.9	181.9	181.2	181.1
50°	201.3	192.8	186.4	182.9	179.9	177.3	175.0	173.5	172.9	172.9	173.3
52.5°	190.2	182.9	177.5	173.1	170.3	167.6	165.5	164.5	163.7	164.6	165.3
55°	173.9	166.5	162.6	158.3	155.6	152.4	151.4	151.0	150.4	152.0	152.8
57.5°	156.6	151.4	146.8	142.7	140.2	138.3	137.0	136.7	137.8	138.6	141.2
60°	145.6	139.7	135.5	132.3	129.3	128.1	127.7	127.3	128.1	130.3	133.7
62.5°	133.5	128.7	124.2	121.8	119.6	117.6	117.5	117.8	119.3	121.9	125.3
65°	115.8	111.6	108.7	105.8	104.0	102.9	103.2	104.0	105.8	109.3	113.0
67.5°	97.7	94.9	92.2	90.0	88.3	88.3	88.7	89.9	92.0	95.8	99.3
70°	86.2	83.0	80.8	79.8	78.4	77.6	78.8	80.8	82.6	86.2	89.1
72.5°	74.6	71.8	70.1	69.4	68.8	68.2	68.6	70.8	73.2	76.7	80.2
75°	57.3	56.3	55.1	54.3	53.7	54.2	54.5	56.5	58.5	62.3	66.2
77.5°	41.8	40.8	40.0	39.9	39.5	39.8	40.9	42.4	44.3	47.0	50.0
80°	31.6	31.3	30.8	30.7	30.7	30.8	32.5	33.4	35.2	37.8	40.2
82.5°	23.1	22.8	22.7	22.6	22.8	22.9	23.8	25.1	26.6	28.6	30.7
85°	12.1	11.7	12.3	12.6	12.1	12.7	13.2	13.9	14.6	15.5	16.5
87.5°	5.6	6.3	6.4	6.9	7.1	7.8	7.8	8.7	9.2	9.7	10.0
90°	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0	19.0	20.0	22.0
92.5°	52.9	82.1	136.6	228.3	327.8	322.5	261.1	177.3	128.6	96.9	82.1
95°	75.0	120.0	227.1	447.2	723.3	886.4	867.4	719.3	567.2	444.2	360.2
97.5°	92.5	124.8	195.7	357.0	645.9	946.6	1097.5	1071.3	964.7	844.8	727.9
100°	106.1	136.0	194.1	324.2	576.3	903.4	1153.5	1230.5	1181.6	1078.5	974.4
102.5°	120.5	149.6	201.3	310.6	523.4	827.3	1119.9	1284.2	1314.4	1265.0	1194.6
105°	144.0	172.1	216.1	305.1	472.2	725.3	1012.4	1252.6	1389.7	1433.7	1422.6
107.5°	170.3	195.4	238.1	314.4	450.6	655.0	902.8	1139.7	1322.6	1435.6	1487.9
110°	187.1	213.1	254.1	323.1	444.2	622.2	840.3	1056.4	1246.6	1387.6	1472.7



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.7	229.9	269.3	334.3	444.2	603.0	793.9	990.8	1171.3	1314.0	1414.2
115°	231.1	256.1	293.2	351.1	447.2	582.3	743.3	908.4	1063.5	1200.5	1309.6
117.5°	258.3	282.5	317.5	370.4	453.8	572.0	713.1	855.1	988.9	1106.9	1206.9
120°	275.1	300.1	335.2	383.1	460.2	567.2	696.3	826.4	946.4	1056.4	1144.5
122.5°	292.0	316.9	352.0	397.6	465.8	563.3	681.9	804.8	916.0	1014.1	1096.5
125°	315.1	341.1	374.2	417.2	475.2	558.3	662.3	773.4	875.4	962.4	1034.5
127.5°	337.8	363.8	395.5	435.2	485.8	555.9	644.3	741.3	836.5	917.8	985.2
130°	352.1	378.2	409.1	447.2	492.2	554.2	632.3	721.3	809.3	887.4	952.4
132.5°	365.0	391.0	422.0	457.6	499.4	554.2	622.7	701.3	783.8	854.5	917.2
135°	381.2	408.2	439.2	472.2	509.2	554.2	611.3	675.3	744.3	808.4	865.4
137.5°	395.4	423.2	451.4	483.0	518.2	555.4	601.1	653.3	709.1	762.3	810.8
140°	404.2	431.2	460.2	490.3	522.2	556.2	596.2	641.3	688.3	734.3	776.4
142.5°	413.0	438.4	465.8	494.2	524.6	557.1	592.3	630.9	670.7	710.3	746.7
145°	426.2	449.2	475.2	500.2	527.3	556.2	586.3	617.3	648.2	679.3	706.3
147.5°	438.2	458.4	481.2	503.9	528.2	553.6	580.1	604.5	629.6	653.5	673.9
150°	446.2	463.2	485.2	506.3	528.2	551.2	575.2	597.3	619.3	638.3	656.3
152.5°	453.4	468.8	489.2	507.8	527.4	548.0	569.6	589.3	608.9	626.3	640.3
155°	462.2	476.2	493.2	509.2	525.2	542.3	560.3	577.2	593.2	607.3	618.3
157.5°	471.4	482.0	496.6	510.2	522.6	536.2	551.5	565.2	578.4	589.3	597.9
160°	476.2	485.2	498.3	510.2	520.2	532.3	544.2	557.2	567.2	577.2	584.3
162.5°	481.0	488.4	499.8	509.5	517.8	527.4	537.9	548.5	557.7	566.0	572.2
165°	486.2	492.2	500.2	508.2	514.2	520.2	528.2	536.2	543.2	549.2	554.2
167.5°	489.8	493.6	500.2	505.8	508.6	513.2	518.8	524.6	529.3	533.8	537.4
170°	492.2	495.2	500.2	504.2	506.3	509.2	513.2	518.2	521.2	524.3	526.2
172.5°	493.8	495.2	499.4	502.7	503.0	504.5	507.6	511.0	514.0	516.3	517.5
175°	495.2	495.2	498.3	500.2	499.2	499.2	500.2	503.3	503.3	505.2	505.2
177.5°	495.4	495.4	497.1	497.8	496.2	496.2	497.1	497.8	498.6	498.6	498.6
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	446.6	447.7	446.8	448.1	446.8	447.7	446.6	447.5	449.0	448.1	450.3
5°	411.6	409.8	411.0	410.3	411.0	409.8	411.6	412.6	415.0	415.8	417.4
7.5°	379.4	377.6	375.7	374.7	375.7	377.6	379.4	379.9	381.9	385.0	387.2
10°	359.1	356.9	356.7	355.3	356.7	356.9	359.1	361.3	362.7	366.4	369.0
12.5°	344.3	342.2	340.0	339.4	340.0	342.2	344.3	346.2	346.6	350.9	352.7
15°	323.3	321.7	320.3	321.5	320.3	321.7	323.3	324.5	326.7	329.7	331.7
17.5°	305.8	304.5	304.3	302.8	304.3	304.5	305.8	306.5	310.0	312.0	315.5
20°	294.8	293.9	294.3	291.6	294.3	293.9	294.8	296.6	300.2	301.2	304.8
22.5°	286.1	284.1	283.9	283.4	283.9	284.1	286.1	287.7	288.4	291.5	293.9
25°	272.3	271.4	270.4	271.4	270.4	271.4	272.3	274.1	274.9	277.2	279.6
27.5°	260.4	259.2	258.9	259.1	258.9	259.2	260.4	260.2	262.3	264.2	265.9
30°	253.0	251.1	251.2	251.1	251.2	251.1	253.0	253.0	254.3	255.9	257.4
32.5°	245.1	243.7	243.5	243.1	243.5	243.7	245.1	244.8	246.3	248.2	249.9
35°	233.3	233.3	232.4	232.4	232.4	233.3	233.3	233.9	235.6	235.6	237.5
37.5°	222.3	222.1	221.5	221.6	221.5	222.1	222.3	222.8	223.3	224.2	225.5
40°	214.0	213.9	213.3	212.1	213.3	213.9	214.0	214.9	215.2	216.3	217.1
42.5°	206.1	205.4	205.2	204.7	205.2	205.4	206.1	206.6	206.8	208.1	209.7
45°	193.6	193.6	193.2	193.0	193.2	193.6	193.6	193.6	193.8	195.4	196.1
47.5°	181.4	181.8	182.5	182.4	182.5	181.8	181.4	181.1	181.2	181.9	182.9
50°	174.1	174.3	174.9	175.0	174.9	174.3	174.1	173.3	172.9	172.9	173.5
52.5°	166.0	167.1	167.9	167.7	167.9	167.1	166.0	165.3	164.6	163.7	164.5
55°	154.5	156.0	157.4	157.6	157.4	156.0	154.5	152.8	152.0	150.4	151.0
57.5°	143.4	145.3	146.7	147.2	146.7	145.3	143.4	141.2	138.6	137.8	136.7
60°	135.7	138.3	140.1	140.9	140.1	138.3	135.7	133.7	130.3	128.1	127.3
62.5°	128.4	131.3	133.0	133.2	133.0	131.3	128.4	125.3	121.9	119.3	117.8
65°	116.4	119.3	121.0	122.2	121.0	119.3	116.4	113.0	109.3	105.8	104.0
67.5°	103.5	106.5	108.2	109.2	108.2	106.5	103.5	99.3	95.8	92.0	89.9
70°	94.1	97.1	99.4	100.3	99.4	97.1	94.1	89.1	86.2	82.6	80.8
72.5°	84.9	87.6	89.5	90.4	89.5	87.6	84.9	80.2	76.7	73.2	70.8
75°	68.8	72.4	74.2	75.2	74.2	72.4	68.8	66.2	62.3	58.5	56.5
77.5°	53.0	56.3	57.4	57.9	57.4	56.3	53.0	50.0	47.0	44.3	42.4
80°	42.5	44.6	46.0	46.1	46.0	44.6	42.5	40.2	37.8	35.2	33.4
82.5°	32.7	34.4	34.8	35.3	34.8	34.4	32.7	30.7	28.6	26.6	25.1
85°	17.9	18.7	18.9	18.7	18.9	18.7	17.9	16.5	15.5	14.6	13.9
87.5°	10.3	10.2	10.3	10.7	10.3	10.2	10.3	10.0	9.7	9.2	8.7
90°	22.0	22.0	23.0	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0
92.5°	69.2	66.8	65.4	63.8	65.4	66.8	69.2	82.1	96.9	128.6	177.3
95°	289.1	259.1	251.2	235.1	251.2	259.1	289.1	360.2	444.2	567.2	719.3
97.5°	666.1	610.1	581.1	568.3	581.1	610.1	666.1	727.9	844.8	964.7	1071.3
100°	905.4	833.4	796.3	780.3	796.3	833.4	905.4	974.4	1078.5	1181.6	1230.5
102.5°	1120.7	1069.4	1029.2	1017.3	1029.2	1069.4	1120.7	1194.6	1265.0	1314.4	1284.2
105°	1390.6	1357.6	1337.6	1325.6	1337.6	1357.6	1390.6	1422.6	1433.7	1389.7	1252.6
107.5°	1504.1	1503.9	1497.3	1489.3	1497.3	1503.9	1504.1	1487.9	1435.6	1322.6	1139.7
110°	1517.7	1536.7	1543.7	1543.7	1543.7	1536.7	1517.7	1472.7	1387.6	1246.6	1056.4



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1480.1	1512.7	1530.1	1537.3	1530.1	1512.7	1480.1	1414.2	1314.0	1171.3	990.8
115°	1387.6	1435.6	1463.6	1476.6	1463.6	1435.6	1387.6	1309.6	1200.5	1063.5	908.4
117.5°	1285.0	1334.6	1362.4	1370.4	1362.4	1334.6	1285.0	1206.9	1106.9	988.9	855.1
120°	1218.6	1266.5	1293.6	1301.6	1293.6	1266.5	1218.6	1144.5	1056.4	946.4	826.4
122.5°	1162.5	1206.5	1233.6	1240.8	1233.6	1206.5	1162.5	1096.5	1014.1	916.0	804.8
125°	1090.5	1131.5	1153.5	1163.6	1153.5	1131.5	1090.5	1034.5	962.4	875.4	773.4
127.5°	1036.0	1072.3	1093.1	1097.5	1093.1	1072.3	1036.0	985.2	917.8	836.5	741.3
130°	1002.5	1035.4	1055.5	1061.4	1055.5	1035.4	1002.5	952.4	887.4	809.3	721.3
132.5°	967.2	1000.2	1018.6	1025.5	1018.6	1000.2	967.2	917.2	854.5	783.8	701.3
135°	909.4	942.5	960.4	966.5	960.4	942.5	909.4	865.4	808.4	744.3	675.3
137.5°	850.2	880.2	896.8	903.4	896.8	880.2	850.2	810.8	762.3	709.1	653.3
140°	813.4	839.4	854.4	859.4	854.4	839.4	813.4	776.4	734.3	688.3	641.3
142.5°	778.2	800.1	814.3	818.6	814.3	800.1	778.2	746.7	710.3	670.7	630.9
145°	730.3	747.3	758.4	762.3	758.4	747.3	730.3	706.3	679.3	648.2	617.3
147.5°	692.9	706.5	712.9	714.7	712.9	706.5	692.9	673.9	653.5	629.6	604.5
150°	671.3	683.3	687.3	688.3	687.3	683.3	671.3	656.3	638.3	619.3	597.3
152.5°	652.9	662.5	666.5	667.5	666.5	662.5	652.9	640.3	626.3	608.9	589.3
155°	628.3	635.2	638.3	639.3	638.3	635.2	628.3	618.3	607.3	593.2	577.2
157.5°	605.6	611.5	614.2	614.1	614.2	611.5	605.6	597.9	589.3	578.4	565.2
160°	591.2	596.2	598.3	597.3	598.3	596.2	591.2	584.3	577.2	567.2	557.2
162.5°	577.6	581.9	582.3	582.0	582.3	581.9	577.6	572.2	566.0	557.7	548.5
165°	558.3	560.3	560.3	560.3	560.3	560.3	558.3	554.2	549.2	543.2	536.2
167.5°	539.4	541.2	540.4	540.3	540.4	541.2	539.4	537.4	533.8	529.3	524.6
170°	528.2	529.3	529.3	528.2	529.3	529.3	528.2	526.2	524.3	521.2	518.2
172.5°	517.8	519.6	518.1	517.0	518.1	519.6	517.8	517.5	516.3	514.0	511.0
175°	505.2	506.3	504.2	503.3	504.2	506.3	505.2	505.2	505.2	503.3	503.3
177.5°	497.8	498.6	496.2	496.2	496.2	498.6	497.8	498.6	498.6	498.6	497.8
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	448.2	450.1	452.5	454.3	457.4	458.8	460.6	462.0	464.6	467.0	469.8
5°	418.0	421.4	425.9	430.9	436.7	440.7	446.3	449.6	456.4	462.5	468.6
7.5°	390.6	394.8	401.2	407.6	415.2	422.0	429.0	436.7	445.3	455.6	464.0
10°	371.9	377.4	384.4	392.4	401.5	409.4	418.8	427.1	437.7	449.6	460.8
12.5°	356.9	361.6	369.4	377.0	386.8	396.6	406.2	417.2	429.6	442.8	456.8
15°	336.2	340.2	346.6	357.1	367.0	376.6	391.2	401.5	417.0	431.7	448.7
17.5°	318.6	323.6	328.9	337.9	348.3	360.2	373.2	386.2	401.1	419.7	438.8
20°	307.8	311.8	317.9	324.9	335.8	347.8	360.1	373.2	391.5	410.9	431.4
22.5°	296.0	300.3	307.3	314.9	324.1	335.5	349.1	363.5	382.6	401.6	423.9
25°	282.1	285.1	291.4	298.3	307.4	317.1	331.2	347.2	366.1	387.8	410.4
27.5°	269.1	271.6	277.4	283.4	291.6	303.2	315.8	331.9	349.7	371.7	396.8
30°	259.6	262.4	267.6	274.0	281.9	292.1	305.0	320.1	339.2	360.7	386.9
32.5°	251.5	254.0	257.9	264.2	272.1	281.9	293.9	309.3	328.4	350.2	376.0
35°	238.9	241.7	244.7	249.7	256.4	266.0	279.1	293.7	311.9	333.0	356.7
37.5°	226.4	229.5	232.1	236.6	242.7	251.2	262.5	277.7	294.2	314.5	337.3
40°	218.6	221.0	223.3	228.0	234.2	242.1	252.7	266.2	283.7	302.6	321.5
42.5°	210.9	213.1	214.9	219.1	224.8	232.4	242.5	255.7	271.9	289.6	306.3
45°	198.5	199.9	202.2	205.7	210.3	217.2	227.0	238.8	252.4	269.1	281.7
47.5°	185.3	187.4	189.2	192.3	196.1	202.9	212.3	222.3	234.8	247.2	256.0
50°	175.0	177.3	179.9	182.9	186.4	192.8	201.3	211.5	222.1	231.6	239.1
52.5°	165.5	167.6	170.3	173.1	177.5	182.9	190.2	199.2	209.7	216.5	222.7
55°	151.4	152.4	155.6	158.3	162.6	166.5	173.9	181.8	188.2	193.4	198.5
57.5°	137.0	138.3	140.2	142.7	146.8	151.4	156.6	163.7	167.4	170.0	174.1
60°	127.7	128.1	129.3	132.3	135.5	139.7	145.6	150.6	153.4	155.6	158.9
62.5°	117.5	117.6	119.6	121.8	124.2	128.7	133.5	137.6	139.8	140.9	144.1
65°	103.2	102.9	104.0	105.8	108.7	111.6	115.8	119.3	119.2	120.4	122.3
67.5°	88.7	88.3	88.3	90.0	92.2	94.9	97.7	99.9	99.9	101.4	102.5
70°	78.8	77.6	78.4	79.8	80.8	83.0	86.2	87.0	87.1	87.9	88.9
72.5°	68.6	68.2	68.8	69.4	70.1	71.8	74.6	75.0	75.1	75.5	77.1
75°	54.5	54.2	53.7	54.3	55.1	56.3	57.3	58.1	57.9	58.1	59.3
77.5°	40.9	39.8	39.5	39.9	40.0	40.8	41.8	41.8	41.9	41.9	43.2
80°	32.5	30.8	30.7	30.7	30.8	31.3	31.6	32.0	31.4	32.0	32.5
82.5°	23.8	22.9	22.8	22.6	22.7	22.8	23.1	23.2	23.2	23.4	23.7
85°	13.2	12.7	12.1	12.6	12.3	11.7	12.1	11.5	11.4	11.5	11.7
87.5°	7.8	7.8	7.1	6.9	6.4	6.3	5.6	5.0	4.5	4.2	4.5
90°	17.0	16.0	14.0	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0
92.5°	261.1	322.5	327.8	228.3	136.6	82.1	52.9	35.6	23.2	14.8	12.2
95°	867.4	886.4	723.3	447.2	227.1	120.0	75.0	53.0	42.0	34.0	33.0
97.5°	1097.5	946.6	645.9	357.0	195.7	124.8	92.5	72.7	61.6	56.1	54.8
100°	1153.5	903.4	576.3	324.2	194.1	136.0	106.1	87.0	76.0	72.1	70.0
102.5°	1119.9	827.3	523.4	310.6	201.3	149.6	120.5	103.1	91.3	88.1	86.9
105°	1012.4	725.3	472.2	305.1	216.1	172.1	144.0	128.0	118.0	113.0	113.0
107.5°	902.8	655.0	450.6	314.4	238.1	195.4	170.3	153.7	145.4	140.7	138.6
110°	840.3	622.2	444.2	323.1	254.1	213.1	187.1	172.1	163.1	159.1	157.0



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	793.9	603.0	444.2	334.3	269.3	229.9	204.7	189.7	180.6	177.5	175.5
115°	743.3	582.3	447.2	351.1	293.2	256.1	231.1	216.1	207.1	204.1	202.1
117.5°	713.1	572.0	453.8	370.4	317.5	282.5	258.3	241.3	232.3	229.1	226.1
120°	696.3	567.2	460.2	383.1	335.2	300.1	275.1	258.1	249.1	245.1	242.1
122.5°	681.9	563.3	465.8	397.6	352.0	316.9	292.0	273.3	264.3	261.1	258.9
125°	662.3	558.3	475.2	417.2	374.2	341.1	315.1	296.1	287.1	282.1	280.1
127.5°	644.3	555.9	485.8	435.2	395.5	363.8	337.8	317.5	306.2	299.7	296.7
130°	632.3	554.2	492.2	447.2	409.1	378.2	352.1	331.1	318.1	310.1	307.1
132.5°	622.7	554.2	499.4	457.6	422.0	391.0	365.0	343.2	328.6	318.9	315.1
135°	611.3	554.2	509.2	472.2	439.2	408.2	381.2	360.2	344.1	332.2	328.1
137.5°	601.1	555.4	518.2	483.0	451.4	423.2	395.4	374.8	358.8	347.6	344.6
140°	596.2	556.2	522.2	490.3	460.2	431.2	404.2	385.2	369.2	357.1	354.1
142.5°	592.3	557.1	524.6	494.2	465.8	438.4	413.0	394.8	378.8	367.6	365.3
145°	586.3	556.2	527.3	500.2	475.2	449.2	426.2	408.2	394.2	384.2	382.2
147.5°	580.1	553.6	528.2	503.9	481.2	458.4	438.2	422.6	409.6	401.0	399.8
150°	575.2	551.2	528.2	506.3	485.2	463.2	446.2	432.2	419.2	412.2	410.2
152.5°	569.6	548.0	527.4	507.8	489.2	468.8	453.4	440.2	428.8	422.6	421.4
155°	560.3	542.3	525.2	509.2	493.2	476.2	462.2	452.2	442.2	436.2	436.2
157.5°	551.5	536.2	522.6	510.2	496.6	482.0	471.4	462.6	454.0	449.2	449.4
160°	544.2	532.3	520.2	510.2	498.3	485.2	476.2	468.2	461.2	457.2	458.2
162.5°	537.9	527.4	517.8	509.5	499.8	488.4	481.0	474.6	468.4	464.4	465.4
165°	528.2	520.2	514.2	508.2	500.2	492.2	486.2	482.2	477.3	474.2	476.2
167.5°	518.8	513.2	508.6	505.8	500.2	493.6	489.8	487.0	484.2	482.4	483.5
170°	513.2	509.2	506.3	504.2	500.2	495.2	492.2	490.3	488.2	487.2	488.2
172.5°	507.6	504.5	503.0	502.7	499.4	495.2	493.8	492.6	490.6	489.7	491.5
175°	500.2	499.2	499.2	500.2	498.3	495.2	495.2	495.2	494.2	493.2	495.2
177.5°	497.1	496.2	496.2	497.8	497.1	495.4	495.4	496.2	495.4	495.4	497.1
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	471.3	473.5	474.9	477.6	479.8	481.1	482.2	483.2	484.3	485.3	488.0
5°	474.3	479.5	483.9	490.6	496.8	501.5	506.7	511.3	515.1	520.5	524.6
7.5°	472.9	482.2	491.8	502.3	513.0	522.9	532.1	540.6	548.4	557.8	566.0
10°	471.7	484.2	496.5	510.7	525.2	537.5	549.1	560.9	569.4	581.3	591.5
12.5°	470.8	485.5	500.4	517.4	533.3	550.8	566.1	574.7	587.7	597.3	609.3
15°	466.7	486.2	506.7	525.8	548.5	564.6	578.2	594.9	607.0	619.1	632.2
17.5°	459.5	481.6	504.5	529.6	551.3	568.6	586.1	602.2	616.6	632.9	649.3
20°	456.2	478.3	504.5	530.2	551.5	569.6	587.5	605.2	621.1	642.0	660.9
22.5°	449.2	475.9	500.1	525.1	547.0	566.7	587.0	607.1	628.3	651.9	675.5
25°	436.7	463.7	489.4	514.1	536.1	560.9	582.6	609.4	636.5	667.7	697.2
27.5°	423.7	449.6	473.1	497.0	522.7	550.7	578.8	609.2	644.7	684.2	725.7
30°	413.2	437.7	460.5	485.0	511.9	543.3	574.2	610.4	651.3	695.7	745.1
32.5°	401.0	423.5	445.7	471.7	500.9	534.1	570.1	609.8	659.0	709.4	760.2
35°	380.0	398.9	421.8	449.4	482.4	520.5	562.1	609.0	665.5	723.4	766.1
37.5°	355.2	372.7	396.8	427.1	461.8	502.6	551.9	607.6	667.6	713.8	727.5
40°	338.4	354.7	379.8	411.2	446.6	489.8	543.9	602.8	660.9	690.3	679.0
42.5°	320.6	337.7	362.1	393.2	431.4	478.4	533.9	592.8	641.5	652.6	613.5
45°	292.5	310.1	334.2	365.7	406.7	457.6	515.5	569.0	597.0	577.0	516.3
47.5°	266.3	282.9	305.2	337.7	380.0	432.7	488.4	531.1	533.3	485.3	420.5
50°	248.5	263.8	286.3	318.7	360.7	414.1	464.3	498.0	482.8	428.5	366.3
52.5°	231.0	246.0	268.1	300.2	341.7	390.6	437.5	461.1	432.6	376.8	323.6
55°	205.7	218.9	240.6	270.2	309.5	354.9	394.7	402.9	365.8	311.0	267.8
57.5°	181.1	193.3	213.0	240.3	276.4	316.5	347.7	345.9	306.8	259.7	225.4
60°	164.4	176.2	193.8	220.4	253.3	287.9	314.5	308.2	269.4	228.8	199.9
62.5°	149.4	160.1	176.6	199.9	229.9	261.9	283.8	274.4	236.4	201.0	178.1
65°	127.3	136.3	150.4	170.3	195.2	221.6	238.6	226.4	194.0	166.3	148.0
67.5°	106.2	113.5	125.3	141.2	162.4	183.7	193.9	181.8	155.8	135.6	122.0
70°	92.9	99.3	108.4	122.5	141.0	158.9	166.7	155.8	133.5	116.1	106.4
72.5°	79.6	84.8	92.8	105.6	120.4	135.9	142.7	132.2	113.9	99.3	90.2
75°	61.5	65.1	70.6	79.4	91.1	103.5	107.2	98.1	86.4	75.4	69.4
77.5°	44.0	47.0	51.2	56.7	65.1	72.9	76.2	70.9	61.9	54.9	50.0
80°	33.8	35.4	39.0	43.6	50.1	55.1	57.3	53.9	47.5	42.4	38.6
82.5°	24.1	25.7	27.8	31.6	35.8	39.2	41.5	39.3	34.7	30.6	28.4
85°	11.7	12.7	13.9	15.5	18.7	20.7	20.5	19.1	17.3	15.8	14.6
87.5°	4.6	5.1	5.9	7.1	8.0	8.9	9.6	9.5	9.2	9.0	8.7
90°	2.0	4.0	6.0	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0
92.5°	14.8	23.2	35.6	52.9	82.1	136.6	228.3	327.8	322.5	261.1	177.3
95°	34.0	42.0	53.0	75.0	120.0	227.1	447.2	723.3	886.4	867.4	719.3
97.5°	56.1	61.6	72.7	92.5	124.8	195.7	357.0	645.9	946.6	1097.5	1071.3
100°	72.1	76.0	87.0	106.1	136.0	194.1	324.2	576.3	903.4	1153.5	1230.5
102.5°	88.1	91.3	103.1	120.5	149.6	201.3	310.6	523.4	827.3	1119.9	1284.2
105°	113.0	118.0	128.0	144.0	172.1	216.1	305.1	472.2	725.3	1012.4	1252.6
107.5°	140.7	145.4	153.7	170.3	195.4	238.1	314.4	450.6	655.0	902.8	1139.7
110°	159.1	163.1	172.1	187.1	213.1	254.1	323.1	444.2	622.2	840.3	1056.4





TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	177.5	180.6	189.7	204.7	229.9	269.3	334.3	444.2	603.0	793.9	990.8
115°	204.1	207.1	216.1	231.1	256.1	293.2	351.1	447.2	582.3	743.3	908.4
117.5°	229.1	232.3	241.3	258.3	282.5	317.5	370.4	453.8	572.0	713.1	855.1
120°	245.1	249.1	258.1	275.1	300.1	335.2	383.1	460.2	567.2	696.3	826.4
122.5°	261.1	264.3	273.3	292.0	316.9	352.0	397.6	465.8	563.3	681.9	804.8
125°	282.1	287.1	296.1	315.1	341.1	374.2	417.2	475.2	558.3	662.3	773.4
127.5°	299.7	306.2	317.5	337.8	363.8	395.5	435.2	485.8	555.9	644.3	741.3
130°	310.1	318.1	331.1	352.1	378.2	409.1	447.2	492.2	554.2	632.3	721.3
132.5°	318.9	328.6	343.2	365.0	391.0	422.0	457.6	499.4	554.2	622.7	701.3
135°	332.2	344.1	360.2	381.2	408.2	439.2	472.2	509.2	554.2	611.3	675.3
137.5°	347.6	358.8	374.8	395.4	423.2	451.4	483.0	518.2	555.4	601.1	653.3
140°	357.1	369.2	385.2	404.2	431.2	460.2	490.3	522.2	556.2	596.2	641.3
142.5°	367.6	378.8	394.8	413.0	438.4	465.8	494.2	524.6	557.1	592.3	630.9
145°	384.2	394.2	408.2	426.2	449.2	475.2	500.2	527.3	556.2	586.3	617.3
147.5°	401.0	409.6	422.6	438.2	458.4	481.2	503.9	528.2	553.6	580.1	604.5
150°	412.2	419.2	432.2	446.2	463.2	485.2	506.3	528.2	551.2	575.2	597.3
152.5°	422.6	428.8	440.2	453.4	468.8	489.2	507.8	527.4	548.0	569.6	589.3
155°	436.2	442.2	452.2	462.2	476.2	493.2	509.2	525.2	542.3	560.3	577.2
157.5°	449.2	454.0	462.6	471.4	482.0	496.6	510.2	522.6	536.2	551.5	565.2
160°	457.2	461.2	468.2	476.2	485.2	498.3	510.2	520.2	532.3	544.2	557.2
162.5°	464.4	468.4	474.6	481.0	488.4	499.8	509.5	517.8	527.4	537.9	548.5
165°	474.2	477.3	482.2	486.2	492.2	500.2	508.2	514.2	520.2	528.2	536.2
167.5°	482.4	484.2	487.0	489.8	493.6	500.2	505.8	508.6	513.2	518.8	524.6
170°	487.2	488.2	490.3	492.2	495.2	500.2	504.2	506.3	509.2	513.2	518.2
172.5°	489.7	490.6	492.6	493.8	495.2	499.4	502.7	503.0	504.5	507.6	511.0
175°	493.2	494.2	495.2	495.2	495.2	498.3	500.2	499.2	499.2	500.2	503.3
177.5°	495.4	495.4	496.2	495.4	495.4	497.1	497.8	496.2	496.2	497.1	497.8
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	490.3	491.5	494.2	493.3	494.5	495.2	495.8
5°	529.8	536.1	539.0	538.6	542.8	541.7	540.7
7.5°	574.5	581.2	585.0	589.6	592.3	592.5	594.9
10°	599.9	608.6	612.2	617.2	620.4	622.2	621.9
12.5°	619.2	626.1	634.1	636.5	640.8	643.2	642.3
15°	642.7	653.6	661.9	666.1	671.5	673.0	675.2
17.5°	663.5	678.1	687.9	700.9	705.8	708.8	707.0
20°	679.2	698.5	708.3	723.8	732.4	736.9	735.3
22.5°	697.8	718.8	736.8	750.2	763.2	769.4	770.7
25°	729.8	758.4	784.9	802.5	818.6	822.4	830.8
27.5°	765.4	799.2	827.5	846.1	857.3	861.5	864.2
30°	787.8	821.5	842.7	854.7	858.2	857.9	857.5
32.5°	798.8	819.8	824.0	820.6	812.4	805.5	798.2
35°	783.3	767.6	744.1	713.9	691.6	669.1	666.8
37.5°	704.5	654.2	615.1	571.4	546.3	530.7	520.0
40°	630.3	573.2	525.8	489.0	463.4	453.2	443.2
42.5°	549.7	495.2	453.2	422.5	403.2	391.9	384.1
45°	446.6	398.5	365.7	343.4	328.0	319.3	314.4
47.5°	366.0	330.4	302.5	286.4	275.9	269.1	269.1
50°	322.7	288.7	270.2	257.4	248.3	242.9	243.9
52.5°	284.3	258.9	243.1	232.5	225.7	222.4	222.2
55°	237.7	219.5	209.1	201.3	196.7	193.0	193.8
57.5°	203.4	188.0	181.0	174.5	171.3	169.9	167.6
60°	182.0	170.1	164.1	158.9	155.8	154.5	152.4
62.5°	163.1	153.7	147.9	143.7	140.9	140.4	138.7
65°	137.1	129.9	124.8	122.8	119.8	119.0	119.0
67.5°	113.0	107.9	103.8	102.0	100.7	100.9	100.0
70°	97.9	93.7	91.1	89.1	88.2	88.3	87.6
72.5°	85.7	80.9	78.7	77.5	76.2	76.7	76.4
75°	64.8	62.5	61.3	60.1	59.3	58.9	58.5
77.5°	47.6	45.5	44.6	43.9	44.1	43.0	43.8
80°	36.8	35.0	34.4	33.4	33.2	33.2	33.1
82.5°	26.9	25.9	25.5	24.7	24.3	24.6	24.1
85°	13.9	13.2	12.9	12.9	12.6	12.1	13.2
87.5°	8.9	8.4	8.9	8.7	8.7	8.8	8.4
90°	19.0	20.0	22.0	22.0	22.0	23.0	23.0
92.5°	128.6	96.9	82.1	69.2	66.8	65.4	63.8
95°	567.2	444.2	360.2	289.1	259.1	251.2	235.1
97.5°	964.7	844.8	727.9	666.1	610.1	581.1	568.3
100°	1181.6	1078.5	974.4	905.4	833.4	796.3	780.3
102.5°	1314.4	1265.0	1194.6	1120.7	1069.4	1029.2	1017.3
105°	1389.7	1433.7	1422.6	1390.6	1357.6	1337.6	1325.6
107.5°	1322.6	1435.6	1487.9	1504.1	1503.9	1497.3	1489.3
110°	1246.6	1387.6	1472.7	1517.7	1536.7	1543.7	1543.7



TEST NUMBER: P333153-935

CATALOG NUMBER: S125DIP-S375D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1171.3	1314.0	1414.2	1480.1	1512.7	1530.1	1537.3
115°	1063.5	1200.5	1309.6	1387.6	1435.6	1463.6	1476.6
117.5°	988.9	1106.9	1206.9	1285.0	1334.6	1362.4	1370.4
120°	946.4	1056.4	1144.5	1218.6	1266.5	1293.6	1301.6
122.5°	916.0	1014.1	1096.5	1162.5	1206.5	1233.6	1240.8
125°	875.4	962.4	1034.5	1090.5	1131.5	1153.5	1163.6
127.5°	836.5	917.8	985.2	1036.0	1072.3	1093.1	1097.5
130°	809.3	887.4	952.4	1002.5	1035.4	1055.5	1061.4
132.5°	783.8	854.5	917.2	967.2	1000.2	1018.6	1025.5
135°	744.3	808.4	865.4	909.4	942.5	960.4	966.5
137.5°	709.1	762.3	810.8	850.2	880.2	896.8	903.4
140°	688.3	734.3	776.4	813.4	839.4	854.4	859.4
142.5°	670.7	710.3	746.7	778.2	800.1	814.3	818.6
145°	648.2	679.3	706.3	730.3	747.3	758.4	762.3
147.5°	629.6	653.5	673.9	692.9	706.5	712.9	714.7
150°	619.3	638.3	656.3	671.3	683.3	687.3	688.3
152.5°	608.9	626.3	640.3	652.9	662.5	666.5	667.5
155°	593.2	607.3	618.3	628.3	635.2	638.3	639.3
157.5°	578.4	589.3	597.9	605.6	611.5	614.2	614.1
160°	567.2	577.2	584.3	591.2	596.2	598.3	597.3
162.5°	557.7	566.0	572.2	577.6	581.9	582.3	582.0
165°	543.2	549.2	554.2	558.3	560.3	560.3	560.3
167.5°	529.3	533.8	537.4	539.4	541.2	540.4	540.3
170°	521.2	524.3	526.2	528.2	529.3	529.3	528.2
172.5°	514.0	516.3	517.5	517.8	519.6	518.1	517.0
175°	503.3	505.2	505.2	505.2	506.3	504.2	503.3
177.5°	498.6	498.6	498.6	497.8	498.6	496.2	496.2
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2

(END OF REPORT)