

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333180-935

Luminaire Tested: **S125DIP-S610D810U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333180-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D810U935-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4680.4 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	46				
1	97	93	89	86	89	86	82	79	72	69	67	59	57	56	47	46	45	40				
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38	33				
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29				
4	74	64	56	50	68	59	52	47	50	44	40	41	37	34	33	31	28	25				
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19				
7	58	46	38	32	53	43	36	31	36	31	27	30	26	23	25	22	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15				
9	50	38	30	25	46	35	29	24	30	25	21	25	21	18	21	18	16	13				
10	47	35	28	23	43	32	26	22	28	23	19	24	19	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4977	4977	4977	4977
5°	5763	4994	4372	4994
10°	6705	4968	3831	4968
15°	7422	4931	3534	4931
20°	8308	4874	3296	4874
25°	9733	4809	3180	4809
30°	10513	4744	3078	4744
35°	8643	4623	3012	4623
40°	6144	4457	2939	4457
45°	4720	4230	2898	4230
50°	4029	3950	2892	3950
55°	3587	3675	2917	3675
60°	3237	3375	2992	3375
65°	2989	3073	3069	3073
70°	2717	2761	3114	2761
75°	2400	2433	3084	2433
80°	2020	1982	2823	1982
85°	1601	1430	2275	1430



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.2	1.6
10°-20°	220.9	4.7
20°-30°	358.6	7.7
30°-40°	437.5	9.3
40°-50°	398.0	8.5
50°-60°	317.0	6.8
60°-70°	220.8	4.7
70°-80°	117.7	2.5
80°-90°	31.6	0.7
90°-100°	242.0	5.2
100°-110°	520.3	11.1
110°-120°	488.3	10.4
120°-130°	395.7	8.5
130°-140°	317.6	6.8
140°-150°	239.7	5.1
150°-160°	168.7	3.6
160°-170°	99.4	2.1
170°-180°	32.3	0.7
0°-30°	653.7	14.0
0°-40°	1091.2	23.3
0°-60°	1806.2	38.6
0°-90°	2176.3	46.5
90°-120°	1250.6	26.7
90°-150°	2203.6	47.1
90°-180°	2504.0	53.5
0°-180°	4680.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	771	771	771	771	771	
5°	889	770	674	770	889	90
15°	1110	738	529	738	1110	318
25°	1366	675	446	675	1366	624
35°	1096	586	382	586	1096	671
45°	517	463	317	463	517	414
55°	319	326	259	326	319	287
65°	196	201	201	201	196	194
75°	96	98	124	98	96	104
85°	22	19	31	19	22	25
90°	16	1	16	1	16	11
95°	158	22	158	22	158	224
105°	892	76	892	76	892	887
115°	994	136	994	136	994	971
125°	783	188	783	188	783	708
135°	650	221	650	221	650	504
145°	513	257	513	257	513	326
155°	430	294	430	294	430	201
165°	377	320	377	320	377	108
175°	339	333	339	333	339	33
180°	334	334	334	334	334	



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	815.1	814.0	813.0	810.9	812.4	808.0	805.9	802.3	797.8	796.3	794.4
5°	889.0	890.6	892.3	885.4	886.1	881.5	871.0	862.5	855.7	846.8	840.6
7.5°	977.9	974.0	973.8	969.3	961.7	955.5	944.5	930.5	917.0	901.6	888.8
10°	1022.4	1022.8	1019.9	1014.6	1006.4	1000.5	986.1	972.4	955.7	936.1	922.0
12.5°	1055.9	1057.3	1053.6	1046.5	1042.5	1029.3	1018.0	1001.7	981.9	966.2	944.8
15°	1110.1	1106.5	1103.9	1095.0	1088.1	1074.4	1056.4	1039.4	1017.9	997.9	977.9
17.5°	1162.3	1165.2	1160.3	1152.2	1130.9	1114.8	1090.7	1067.5	1040.5	1013.8	990.0
20°	1208.8	1211.5	1203.9	1189.9	1164.4	1148.3	1116.6	1086.5	1055.5	1021.1	995.0
22.5°	1267.0	1264.9	1254.7	1233.3	1211.3	1181.6	1147.3	1110.6	1071.7	1032.9	998.1
25°	1365.9	1352.1	1345.9	1319.4	1290.3	1246.8	1199.7	1146.1	1097.7	1046.3	1001.9
27.5°	1420.6	1416.3	1409.5	1390.9	1360.4	1313.9	1258.4	1193.0	1124.6	1059.9	1001.6
30°	1409.7	1410.3	1411.0	1405.1	1385.5	1350.5	1295.2	1224.9	1143.8	1070.8	1003.5
32.5°	1312.3	1324.2	1335.7	1349.1	1354.6	1347.9	1313.3	1249.7	1166.3	1083.4	1002.4
35°	1096.3	1099.9	1137.0	1173.5	1223.2	1261.9	1287.7	1259.6	1189.2	1094.1	1001.2
37.5°	854.8	872.5	898.1	939.5	1011.2	1075.5	1158.1	1196.1	1173.4	1097.5	998.8
40°	728.8	745.1	761.7	803.9	864.4	942.3	1036.1	1116.3	1135.0	1086.5	991.0
42.5°	631.4	644.4	662.9	694.6	745.1	814.1	903.8	1008.5	1072.9	1054.6	974.6
45°	516.8	525.0	539.3	564.6	601.2	655.1	734.3	848.8	948.5	981.5	935.4
47.5°	442.3	442.3	453.5	470.9	497.3	543.1	601.7	691.4	797.9	876.8	873.1
50°	401.0	399.3	408.2	423.3	444.2	474.6	530.5	602.2	704.6	793.8	818.6
52.5°	365.4	365.6	371.0	382.1	399.7	425.7	467.4	532.0	619.5	711.1	757.9
55°	318.6	317.3	323.5	331.0	343.8	360.8	390.9	440.2	511.2	601.5	662.3
57.5°	275.7	279.2	281.7	287.0	297.6	308.9	334.3	370.6	426.9	504.4	568.7
60°	250.6	254.2	256.1	261.3	269.8	279.7	299.3	328.7	376.2	442.9	506.6
62.5°	228.0	230.8	231.5	236.2	243.1	252.7	268.1	292.8	330.4	388.7	451.2
65°	195.6	195.6	196.9	201.8	205.1	213.6	225.3	243.3	273.5	318.9	372.2
67.5°	164.3	165.9	165.6	167.7	170.7	177.4	185.8	200.6	222.9	256.1	298.8
70°	143.9	145.3	144.9	146.5	149.8	154.0	160.9	175.0	191.0	219.5	256.1
72.5°	125.6	126.1	125.3	127.4	129.4	133.1	140.8	148.3	163.2	187.3	217.4
75°	96.2	96.8	97.5	98.8	100.7	102.7	106.6	114.2	124.0	142.0	161.3
77.5°	72.1	70.9	72.4	72.2	73.4	74.8	78.3	82.3	90.3	101.7	116.7
80°	54.3	54.6	54.6	54.9	56.6	57.6	60.5	63.5	69.7	78.2	88.6
82.5°	39.6	40.5	40.0	40.6	41.9	42.6	44.3	46.7	50.3	57.0	64.6
85°	21.6	20.0	20.6	21.3	21.3	21.6	22.9	23.8	25.8	28.4	31.4
87.5°	9.4	9.9	10.0	10.0	10.2	10.0	10.9	10.8	11.5	12.1	12.9
90°	15.5	15.5	14.8	14.8	14.8	13.4	12.8	12.1	11.5	10.8	9.4
92.5°	43.0	44.0	44.9	46.6	55.2	65.2	86.6	119.3	175.7	217.1	220.5
95°	158.2	169.0	174.4	194.6	242.4	298.9	381.7	484.1	583.7	596.5	486.7
97.5°	382.4	391.0	410.5	448.2	489.8	568.4	649.1	720.9	738.5	637.0	434.6
100°	525.1	535.9	560.8	609.2	655.7	725.7	795.0	828.0	776.2	608.0	387.8
102.5°	684.5	692.6	719.6	754.1	803.8	851.2	884.5	864.1	753.6	556.7	352.2
105°	892.0	900.1	913.5	935.7	957.3	964.8	935.1	842.8	681.3	488.1	317.8
107.5°	1002.1	1007.5	1011.9	1012.1	1001.2	966.0	890.0	766.9	607.5	440.8	303.2
110°	1038.8	1038.8	1034.1	1021.2	990.9	933.8	838.8	710.9	565.5	418.7	298.9



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1034.5	1029.6	1017.9	995.9	951.7	884.2	788.2	666.8	534.3	405.8	298.9
115°	993.7	984.9	966.0	933.8	881.2	807.9	715.7	611.3	500.2	391.8	300.9
117.5°	922.1	916.8	898.0	864.7	812.2	744.9	665.4	575.5	479.8	385.0	305.4
120°	875.8	870.5	852.3	819.9	770.2	710.9	636.9	556.0	468.6	381.7	309.7
122.5°	834.9	830.1	811.9	782.3	737.9	682.3	616.4	541.6	458.8	379.0	313.4
125°	782.9	776.2	761.4	733.8	696.1	647.6	589.1	520.4	445.7	375.7	319.8
127.5°	738.5	735.6	721.5	697.2	663.0	617.6	562.9	498.9	433.5	374.0	326.9
130°	714.3	710.2	696.8	674.6	640.9	597.1	544.7	485.3	425.5	373.0	331.2
132.5°	690.0	685.4	673.0	650.8	617.2	575.1	527.4	471.9	419.0	373.0	336.0
135°	650.3	646.3	634.1	611.9	582.3	544.0	500.8	454.4	411.3	373.0	342.7
137.5°	608.0	603.5	592.3	572.1	545.5	513.0	477.2	439.6	404.5	373.8	348.7
140°	578.2	574.9	564.8	547.3	522.4	494.1	463.1	431.5	401.2	374.3	351.4
142.5°	550.8	548.0	538.5	523.7	502.5	477.9	451.3	424.6	398.6	374.9	353.0
145°	513.0	510.3	502.9	491.5	475.3	457.1	436.3	415.3	394.5	374.3	354.8
147.5°	481.0	479.7	475.4	466.2	453.5	439.7	423.7	406.7	390.3	372.6	355.4
150°	463.1	462.5	459.8	451.8	441.6	429.5	416.7	401.9	387.1	370.9	355.4
152.5°	449.2	448.5	445.8	439.4	430.8	421.5	409.7	396.5	383.3	368.8	354.9
155°	430.2	429.5	427.5	422.8	416.0	408.6	399.2	388.5	377.0	364.9	353.4
157.5°	413.2	413.4	411.5	407.6	402.3	396.5	389.3	380.4	371.1	360.8	351.7
160°	401.9	402.6	401.2	397.9	393.1	388.5	381.7	375.0	366.3	358.2	350.1
162.5°	391.7	391.8	391.5	388.7	385.0	380.9	375.2	369.0	361.9	354.9	348.4
165°	377.0	377.0	377.0	375.7	373.0	369.6	365.6	360.8	355.4	350.1	346.0
167.5°	363.5	363.7	364.2	363.0	361.6	359.2	356.1	353.0	349.1	345.3	342.2
170°	355.4	356.1	356.1	355.4	354.1	352.8	350.8	348.7	345.3	342.7	340.6
172.5°	347.9	348.6	349.7	348.4	348.2	347.4	345.9	343.9	341.6	339.4	338.5
175°	338.6	339.3	340.6	340.0	340.0	340.0	338.6	338.6	336.6	336.0	336.0
177.5°	333.9	333.9	335.5	335.0	335.5	335.5	335.5	335.0	334.4	333.9	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	792.8	791.0	788.9	785.2	780.8	778.4	774.8	772.4	767.7	763.8	759.6
5°	833.0	824.6	816.7	806.6	795.5	788.2	779.7	770.3	760.4	750.3	739.2
7.5°	874.7	859.7	843.3	825.7	808.6	792.7	777.6	762.8	748.9	732.1	717.9
10°	902.8	883.7	863.5	839.6	816.4	796.1	775.5	757.5	739.2	719.5	702.2
12.5°	930.7	905.4	876.8	850.6	822.7	798.2	774.0	751.0	728.0	706.2	686.0
15°	950.5	928.2	901.7	864.4	833.0	799.4	767.3	737.5	709.7	685.5	660.0
17.5°	963.5	934.9	906.4	870.6	829.5	791.8	755.4	721.4	690.1	659.4	634.8
20°	965.9	936.4	906.6	871.7	829.5	786.3	750.0	709.1	675.4	643.7	613.5
22.5°	965.1	931.7	899.3	863.2	822.2	782.4	738.5	696.8	660.2	629.0	597.6
25°	957.7	922.0	881.5	845.2	804.6	762.4	717.9	674.8	637.5	601.8	570.8
27.5°	951.5	905.3	859.4	817.0	777.8	739.2	696.6	652.4	611.1	574.9	545.6
30°	943.9	893.2	841.5	797.4	757.2	719.5	679.3	636.2	593.0	557.7	526.2
32.5°	937.1	878.0	823.5	775.4	732.9	696.3	659.2	618.1	575.8	539.8	508.5
35°	924.0	855.7	793.2	738.8	693.4	655.8	624.7	586.4	547.5	512.8	482.8
37.5°	907.3	826.2	759.1	702.2	652.4	612.8	583.8	554.5	517.1	483.7	456.5
40°	894.2	805.3	734.3	676.1	624.4	583.2	556.4	528.6	497.5	466.4	437.6
42.5°	877.7	786.4	709.1	646.5	595.4	555.2	527.0	503.4	476.0	447.0	420.3
45°	847.5	752.3	668.6	601.2	549.5	509.9	480.8	463.1	442.6	415.1	392.5
47.5°	802.9	711.3	624.7	555.1	501.8	465.1	437.8	420.9	406.4	386.0	365.5
50°	763.4	680.6	593.0	524.0	470.6	433.7	408.5	393.1	380.7	365.0	347.7
52.5°	719.2	642.1	561.9	493.6	440.8	404.4	379.7	366.2	355.9	344.6	327.5
55°	648.9	583.5	508.9	444.2	395.5	359.8	338.2	326.4	317.9	309.4	298.9
57.5°	571.5	520.4	454.3	395.1	350.3	317.8	297.6	286.2	279.6	275.2	269.1
60°	517.1	473.3	416.4	362.4	318.6	289.8	270.2	261.3	255.8	252.2	247.6
62.5°	466.6	430.6	377.9	328.6	290.3	263.1	245.6	237.0	231.7	230.0	226.1
65°	392.2	364.4	320.9	280.0	247.3	224.0	209.3	201.1	197.9	195.9	196.2
67.5°	318.8	301.9	267.0	232.1	206.0	186.5	174.7	168.4	166.8	164.2	164.1
70°	274.1	261.3	231.9	201.5	178.2	163.2	152.7	146.2	144.6	143.3	142.9
72.5°	234.5	223.4	197.9	173.5	152.7	139.4	130.8	126.8	124.2	123.4	123.3
75°	176.3	170.0	149.8	130.5	116.1	106.9	101.1	97.5	95.5	95.1	95.5
77.5°	125.4	119.9	107.0	93.3	84.3	77.3	72.3	71.1	68.9	69.0	68.6
80°	94.2	90.6	82.4	71.6	64.1	58.2	55.6	53.3	52.7	51.7	52.7
82.5°	68.3	64.4	58.9	52.0	45.8	42.3	39.6	38.9	38.5	38.1	38.2
85°	33.7	34.0	30.7	25.5	22.9	20.9	19.3	19.3	18.9	18.7	18.9
87.5°	13.3	12.5	11.3	10.2	8.7	7.6	7.1	7.2	6.5	6.5	7.1
90°	8.8	7.4	6.7	5.4	4.0	2.7	1.4	0.7	1.4	2.7	4.0
92.5°	153.6	92.0	55.2	35.6	23.9	15.6	10.0	8.2	10.0	15.6	23.9
95°	300.9	152.8	80.8	50.5	35.6	28.2	22.9	22.2	22.9	28.2	35.6
97.5°	240.2	131.6	84.0	62.2	48.9	41.5	37.7	36.9	37.7	41.5	48.9
100°	218.1	130.6	91.5	71.4	58.5	51.1	48.5	47.1	48.5	51.1	58.5
102.5°	209.0	135.4	100.7	81.0	69.3	61.4	59.2	58.5	59.2	61.4	69.3
105°	205.3	145.4	115.8	96.9	86.2	79.5	76.1	76.1	76.1	79.5	86.2
107.5°	211.5	160.2	131.6	114.6	103.4	97.9	94.6	93.3	94.6	97.9	103.4
110°	217.5	171.0	143.4	125.9	115.8	109.7	107.0	105.7	107.0	109.7	115.8



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	225.0	181.2	154.7	137.8	127.6	121.6	119.4	118.0	119.4	121.6	127.6
115°	236.3	197.3	172.4	155.5	145.4	139.4	137.3	136.0	137.3	139.4	145.4
117.5°	249.3	213.7	190.1	173.8	162.4	156.4	154.2	152.1	154.2	156.4	162.4
120°	257.9	225.5	202.0	185.1	173.7	167.6	165.0	162.9	165.0	167.6	173.7
122.5°	267.5	236.9	213.3	196.5	183.9	177.9	175.7	174.3	175.7	177.9	183.9
125°	280.7	251.8	229.5	212.1	199.2	193.2	189.9	188.5	189.9	193.2	199.2
127.5°	292.8	266.2	244.8	227.3	213.7	206.0	201.7	199.7	201.7	206.0	213.7
130°	300.9	275.3	254.5	236.9	222.8	214.0	208.7	206.6	208.7	214.0	222.8
132.5°	307.9	284.0	263.1	245.6	230.9	221.1	214.6	212.1	214.6	221.1	230.9
135°	317.8	295.6	274.7	256.5	242.4	231.6	223.5	220.8	223.5	231.6	242.4
137.5°	325.0	303.8	284.7	266.0	252.2	241.4	233.8	231.9	233.8	241.4	252.2
140°	329.8	309.7	290.2	272.0	259.2	248.4	240.3	238.3	240.3	248.4	259.2
142.5°	332.6	313.4	295.0	277.9	265.6	254.9	247.4	245.8	247.4	254.9	265.6
145°	336.6	319.8	302.3	286.8	274.7	265.3	258.5	257.2	258.5	265.3	274.7
147.5°	339.1	323.8	308.5	294.9	284.4	275.6	269.8	269.0	269.8	275.6	284.4
150°	340.6	326.5	311.7	300.2	290.8	282.1	277.3	276.0	277.3	282.1	290.8
152.5°	341.7	329.2	315.5	305.1	296.2	288.5	284.4	283.5	284.4	288.5	296.2
155°	342.7	331.9	320.5	311.0	304.3	297.6	293.5	293.5	293.5	297.6	304.3
157.5°	343.4	334.2	324.3	317.2	311.3	305.5	302.3	302.4	302.3	305.5	311.3
160°	343.4	335.3	326.5	320.5	315.0	310.4	307.6	308.3	307.6	310.4	315.0
162.5°	342.8	336.3	328.6	323.6	319.3	315.2	312.5	313.1	312.5	315.2	319.3
165°	342.0	336.6	331.2	327.2	324.5	321.2	319.1	320.5	319.1	321.2	324.5
167.5°	340.4	336.6	332.2	329.6	327.7	325.8	324.6	325.3	324.6	325.8	327.7
170°	339.3	336.6	333.2	331.2	329.8	328.6	327.9	328.6	327.9	328.6	329.8
172.5°	338.2	336.0	333.2	332.3	331.5	330.1	329.5	330.7	329.5	330.1	331.5
175°	336.6	335.3	333.2	333.2	333.2	332.6	331.9	333.2	331.9	332.6	333.2
177.5°	335.0	334.4	333.4	333.4	333.9	333.4	333.4	334.4	333.4	333.4	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	757.2	754.3	752.0	746.7	743.9	739.9	736.8	740.2	736.6	738.1	735.8
5°	733.7	724.4	717.9	708.4	700.3	692.8	687.2	686.2	683.5	682.3	678.4
7.5°	705.2	693.8	682.5	670.1	659.6	649.0	642.1	636.5	632.8	627.9	624.6
10°	688.5	673.1	660.0	645.0	631.9	620.4	611.3	606.7	602.4	596.2	594.0
12.5°	667.8	651.9	635.9	619.8	607.3	594.5	586.7	579.8	576.9	569.8	569.1
15°	643.0	619.1	603.5	587.1	569.7	559.3	552.8	545.3	542.0	537.1	533.5
17.5°	613.5	592.1	572.5	555.6	540.7	531.9	523.7	518.6	513.0	509.8	503.9
20°	592.0	571.7	552.1	534.1	522.6	512.6	506.0	501.1	495.2	493.5	487.7
22.5°	573.9	551.6	532.7	517.6	505.1	493.7	486.6	483.3	479.2	474.2	473.0
25°	544.6	521.3	505.3	490.3	479.1	468.7	463.8	459.5	455.6	452.0	450.7
27.5°	519.2	498.4	479.4	465.8	456.2	446.6	442.3	437.1	434.2	431.4	427.8
30°	501.4	480.2	463.5	450.4	439.9	431.4	426.8	423.3	420.6	418.0	416.0
32.5°	483.1	463.4	447.2	434.5	424.0	417.6	413.5	411.0	408.0	404.9	402.4
35°	458.9	437.3	421.6	410.4	402.3	397.4	392.8	390.5	387.3	387.3	384.6
37.5°	431.6	412.9	399.1	388.9	381.6	377.2	372.3	370.7	368.6	367.2	366.4
40°	415.3	398.0	385.0	374.8	367.0	363.3	359.5	356.8	355.5	353.9	353.3
42.5°	398.6	382.1	369.5	360.2	353.4	350.3	346.6	344.8	342.2	340.0	339.7
45°	373.2	357.1	345.7	338.2	332.3	328.7	326.4	322.5	321.2	318.6	318.2
47.5°	349.0	333.6	322.4	316.2	311.1	308.2	304.5	300.7	299.1	297.8	297.7
50°	331.0	316.9	306.4	300.6	295.7	291.4	287.8	285.2	284.2	284.2	284.9
52.5°	312.7	300.7	291.8	284.6	280.0	275.4	272.2	270.5	269.1	270.6	271.8
55°	285.9	273.8	267.3	260.4	255.8	250.6	248.9	248.2	247.3	249.9	251.2
57.5°	257.4	249.0	241.3	234.5	230.4	227.4	225.2	224.8	226.6	227.8	232.1
60°	239.4	229.6	222.7	217.5	212.6	210.6	210.0	209.3	210.6	214.2	219.8
62.5°	219.6	211.5	204.1	200.3	196.7	193.4	193.2	193.6	196.2	200.4	206.0
65°	190.4	183.5	178.6	174.0	171.1	169.1	169.8	171.1	174.0	179.6	185.8
67.5°	160.7	156.0	151.6	147.9	145.1	145.1	145.8	147.7	151.2	157.6	163.2
70°	141.6	136.4	132.8	131.1	128.9	127.6	129.5	132.8	135.7	141.6	146.5
72.5°	122.5	118.0	115.3	114.2	113.1	112.1	112.8	116.3	120.3	126.2	131.9
75°	94.2	92.6	90.6	89.3	88.3	88.9	89.6	92.9	96.2	102.4	108.9
77.5°	68.8	67.1	65.9	65.5	65.0	65.3	67.2	69.6	72.8	77.3	82.3
80°	52.0	51.3	50.7	50.4	50.4	50.7	53.3	54.9	57.9	62.2	66.0
82.5°	37.9	37.5	37.4	37.3	37.5	37.6	39.2	41.3	43.7	47.0	50.4
85°	20.0	19.3	20.3	20.6	20.0	20.9	21.6	22.9	23.8	25.5	27.1
87.5°	7.6	8.4	8.3	8.8	9.0	9.7	9.6	10.8	11.5	12.1	12.1
90°	5.4	6.7	7.4	8.8	9.4	10.8	11.5	12.1	12.8	13.4	14.8
92.5°	35.6	55.2	92.0	153.6	220.5	217.1	175.7	119.3	86.6	65.2	55.2
95°	50.5	80.8	152.8	300.9	486.7	596.5	583.7	484.1	381.7	298.9	242.4
97.5°	62.2	84.0	131.6	240.2	434.6	637.0	738.5	720.9	649.1	568.4	489.8
100°	71.4	91.5	130.6	218.1	387.8	608.0	776.2	828.0	795.0	725.7	655.7
102.5°	81.0	100.7	135.4	209.0	352.2	556.7	753.6	864.1	884.5	851.2	803.8
105°	96.9	115.8	145.4	205.3	317.8	488.1	681.3	842.8	935.1	964.8	957.3
107.5°	114.6	131.6	160.2	211.5	303.2	440.8	607.5	766.9	890.0	966.0	1001.2
110°	125.9	143.4	171.0	217.5	298.9	418.7	565.5	710.9	838.8	933.8	990.9



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	137.8	154.7	181.2	225.0	298.9	405.8	534.3	666.8	788.2	884.2	951.7
115°	155.5	172.4	197.3	236.3	300.9	391.8	500.2	611.3	715.7	807.9	881.2
117.5°	173.8	190.1	213.7	249.3	305.4	385.0	479.8	575.5	665.4	744.9	812.2
120°	185.1	202.0	225.5	257.9	309.7	381.7	468.6	556.0	636.9	710.9	770.2
122.5°	196.5	213.3	236.9	267.5	313.4	379.0	458.8	541.6	616.4	682.3	737.9
125°	212.1	229.5	251.8	280.7	319.8	375.7	445.7	520.4	589.1	647.6	696.1
127.5°	227.3	244.8	266.2	292.8	326.9	374.0	433.5	498.9	562.9	617.6	663.0
130°	236.9	254.5	275.3	300.9	331.2	373.0	425.5	485.3	544.7	597.1	640.9
132.5°	245.6	263.1	284.0	307.9	336.0	373.0	419.0	471.9	527.4	575.1	617.2
135°	256.5	274.7	295.6	317.8	342.7	373.0	411.3	454.4	500.8	544.0	582.3
137.5°	266.0	284.7	303.8	325.0	348.7	373.8	404.5	439.6	477.2	513.0	545.5
140°	272.0	290.2	309.7	329.8	351.4	374.3	401.2	431.5	463.1	494.1	522.4
142.5°	277.9	295.0	313.4	332.6	353.0	374.9	398.6	424.6	451.3	477.9	502.5
145°	286.8	302.3	319.8	336.6	354.8	374.3	394.5	415.3	436.3	457.1	475.3
147.5°	294.9	308.5	323.8	339.1	355.4	372.6	390.3	406.7	423.7	439.7	453.5
150°	300.2	311.7	326.5	340.6	355.4	370.9	387.1	401.9	416.7	429.5	441.6
152.5°	305.1	315.5	329.2	341.7	354.9	368.8	383.3	396.5	409.7	421.5	430.8
155°	311.0	320.5	331.9	342.7	353.4	364.9	377.0	388.5	399.2	408.6	416.0
157.5°	317.2	324.3	334.2	343.4	351.7	360.8	371.1	380.4	389.3	396.5	402.3
160°	320.5	326.5	335.3	343.4	350.1	358.2	366.3	375.0	381.7	388.5	393.1
162.5°	323.6	328.6	336.3	342.8	348.4	354.9	361.9	369.0	375.2	380.9	385.0
165°	327.2	331.2	336.6	342.0	346.0	350.1	355.4	360.8	365.6	369.6	373.0
167.5°	329.6	332.2	336.6	340.4	342.2	345.3	349.1	353.0	356.1	359.2	361.6
170°	331.2	333.2	336.6	339.3	340.6	342.7	345.3	348.7	350.8	352.8	354.1
172.5°	332.3	333.2	336.0	338.2	338.5	339.4	341.6	343.9	345.9	347.4	348.2
175°	333.2	333.2	335.3	336.6	336.0	336.0	336.6	338.6	338.6	340.0	340.0
177.5°	333.4	333.4	334.4	335.0	333.9	333.9	334.4	335.0	335.5	335.5	335.5
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	734.2	736.1	734.5	736.6	734.5	736.1	734.2	735.8	738.1	736.6	740.2
5°	676.7	673.7	675.7	674.4	675.7	673.7	676.7	678.4	682.3	683.5	686.2
7.5°	623.6	620.8	617.6	616.0	617.6	620.8	623.6	624.6	627.9	632.8	636.5
10°	590.4	586.8	586.4	584.2	586.4	586.8	590.4	594.0	596.2	602.4	606.7
12.5°	566.0	562.7	559.0	558.0	559.0	562.7	566.0	569.1	569.8	576.9	579.8
15°	531.5	528.9	526.6	528.6	526.6	528.9	531.5	533.5	537.1	542.0	545.3
17.5°	502.7	500.6	500.2	497.8	500.2	500.6	502.7	503.9	509.8	513.0	518.6
20°	484.7	483.1	483.7	479.5	483.7	483.1	484.7	487.7	493.5	495.2	501.1
22.5°	470.4	467.1	466.7	465.9	466.7	467.1	470.4	473.0	474.2	479.2	483.3
25°	447.8	446.2	444.5	446.2	444.5	446.2	447.8	450.7	452.0	455.6	459.5
27.5°	428.1	426.1	425.7	425.9	425.7	426.1	428.1	427.8	431.4	434.2	437.1
30°	416.0	412.8	413.1	412.8	413.1	412.8	416.0	416.0	418.0	420.6	423.3
32.5°	402.9	400.7	400.3	399.7	400.3	400.7	402.9	402.4	404.9	408.0	411.0
35°	383.7	383.7	382.0	382.0	382.0	383.7	383.7	384.6	387.3	387.3	390.5
37.5°	365.5	365.2	364.2	364.4	364.2	365.2	365.5	366.4	367.2	368.6	370.7
40°	351.9	351.6	350.6	348.6	350.6	351.6	351.9	353.3	353.9	355.5	356.8
42.5°	338.9	337.8	337.3	336.7	337.3	337.8	338.9	339.7	340.0	342.2	344.8
45°	318.2	318.2	317.6	317.3	317.6	318.2	318.2	318.2	318.6	321.2	322.5
47.5°	298.3	298.9	300.1	299.9	300.1	298.9	298.3	297.7	297.8	299.1	300.7
50°	286.2	286.5	287.5	287.8	287.5	286.5	286.2	284.9	284.2	284.2	285.2
52.5°	272.9	274.7	276.0	275.8	276.0	274.7	272.9	271.8	270.6	269.1	270.5
55°	254.2	256.4	258.7	259.1	258.7	256.4	254.2	251.2	249.9	247.3	248.2
57.5°	235.7	238.8	241.3	242.0	241.3	238.8	235.7	232.1	227.8	226.6	224.8
60°	223.1	227.3	230.2	231.6	230.2	227.3	223.1	219.8	214.2	210.6	209.3
62.5°	211.0	215.8	218.8	219.0	218.8	215.8	211.0	206.0	200.4	196.2	193.6
65°	191.3	196.2	198.9	200.8	198.9	196.2	191.3	185.8	179.6	174.0	171.1
67.5°	170.1	175.0	178.0	179.5	178.0	175.0	170.1	163.2	157.6	151.2	147.7
70°	154.7	159.6	163.5	164.9	163.5	159.6	154.7	146.5	141.6	135.7	132.8
72.5°	139.6	143.9	147.1	148.6	147.1	143.9	139.6	131.9	126.2	120.3	116.3
75°	113.1	119.1	122.0	123.6	122.0	119.1	113.1	108.9	102.4	96.2	92.9
77.5°	87.3	92.6	94.4	95.2	94.4	92.6	87.3	82.3	77.3	72.8	69.6
80°	70.0	73.3	75.6	75.9	75.6	73.3	70.0	66.0	62.2	57.9	54.9
82.5°	53.8	56.5	57.3	58.1	57.3	56.5	53.8	50.4	47.0	43.7	41.3
85°	29.4	30.7	31.1	30.7	31.1	30.7	29.4	27.1	25.5	23.8	22.9
87.5°	12.7	12.4	12.5	13.0	12.5	12.4	12.7	12.1	12.1	11.5	10.8
90°	14.8	14.8	15.5	15.5	15.5	14.8	14.8	14.8	13.4	12.8	12.1
92.5°	46.6	44.9	44.0	43.0	44.0	44.9	46.6	55.2	65.2	86.6	119.3
95°	194.6	174.4	169.0	158.2	169.0	174.4	194.6	242.4	298.9	381.7	484.1
97.5°	448.2	410.5	391.0	382.4	391.0	410.5	448.2	489.8	568.4	649.1	720.9
100°	609.2	560.8	535.9	525.1	535.9	560.8	609.2	655.7	725.7	795.0	828.0
102.5°	754.1	719.6	692.6	684.5	692.6	719.6	754.1	803.8	851.2	884.5	864.1
105°	935.7	913.5	900.1	892.0	900.1	913.5	935.7	957.3	964.8	935.1	842.8
107.5°	1012.1	1011.9	1007.5	1002.1	1007.5	1011.9	1012.1	1001.2	966.0	890.0	766.9
110°	1021.2	1034.1	1038.8	1038.8	1038.8	1034.1	1021.2	990.9	933.8	838.8	710.9



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	995.9	1017.9	1029.6	1034.5	1029.6	1017.9	995.9	951.7	884.2	788.2	666.8
115°	933.8	966.0	984.9	993.7	984.9	966.0	933.8	881.2	807.9	715.7	611.3
117.5°	864.7	898.0	916.8	922.1	916.8	898.0	864.7	812.2	744.9	665.4	575.5
120°	819.9	852.3	870.5	875.8	870.5	852.3	819.9	770.2	710.9	636.9	556.0
122.5°	782.3	811.9	830.1	834.9	830.1	811.9	782.3	737.9	682.3	616.4	541.6
125°	733.8	761.4	776.2	782.9	776.2	761.4	733.8	696.1	647.6	589.1	520.4
127.5°	697.2	721.5	735.6	738.5	735.6	721.5	697.2	663.0	617.6	562.9	498.9
130°	674.6	696.8	710.2	714.3	710.2	696.8	674.6	640.9	597.1	544.7	485.3
132.5°	650.8	673.0	685.4	690.0	685.4	673.0	650.8	617.2	575.1	527.4	471.9
135°	611.9	634.1	646.3	650.3	646.3	634.1	611.9	582.3	544.0	500.8	454.4
137.5°	572.1	592.3	603.5	608.0	603.5	592.3	572.1	545.5	513.0	477.2	439.6
140°	547.3	564.8	574.9	578.2	574.9	564.8	547.3	522.4	494.1	463.1	431.5
142.5°	523.7	538.5	548.0	550.8	548.0	538.5	523.7	502.5	477.9	451.3	424.6
145°	491.5	502.9	510.3	513.0	510.3	502.9	491.5	475.3	457.1	436.3	415.3
147.5°	466.2	475.4	479.7	481.0	479.7	475.4	466.2	453.5	439.7	423.7	406.7
150°	451.8	459.8	462.5	463.1	462.5	459.8	451.8	441.6	429.5	416.7	401.9
152.5°	439.4	445.8	448.5	449.2	448.5	445.8	439.4	430.8	421.5	409.7	396.5
155°	422.8	427.5	429.5	430.2	429.5	427.5	422.8	416.0	408.6	399.2	388.5
157.5°	407.6	411.5	413.4	413.2	413.4	411.5	407.6	402.3	396.5	389.3	380.4
160°	397.9	401.2	402.6	401.9	402.6	401.2	397.9	393.1	388.5	381.7	375.0
162.5°	388.7	391.5	391.8	391.7	391.8	391.5	388.7	385.0	380.9	375.2	369.0
165°	375.7	377.0	377.0	377.0	377.0	377.0	375.7	373.0	369.6	365.6	360.8
167.5°	363.0	364.2	363.7	363.5	363.7	364.2	363.0	361.6	359.2	356.1	353.0
170°	355.4	356.1	356.1	355.4	356.1	356.1	355.4	354.1	352.8	350.8	348.7
172.5°	348.4	349.7	348.6	347.9	348.6	349.7	348.4	348.2	347.4	345.9	343.9
175°	340.0	340.6	339.3	338.6	339.3	340.6	340.0	340.0	340.0	338.6	338.6
177.5°	335.0	335.5	333.9	333.9	333.9	335.5	335.0	335.5	335.5	335.5	335.0
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	736.8	739.9	743.9	746.7	752.0	754.3	757.2	759.6	763.8	767.7	772.4
5°	687.2	692.8	700.3	708.4	717.9	724.4	733.7	739.2	750.3	760.4	770.3
7.5°	642.1	649.0	659.6	670.1	682.5	693.8	705.2	717.9	732.1	748.9	762.8
10°	611.3	620.4	631.9	645.0	660.0	673.1	688.5	702.2	719.5	739.2	757.5
12.5°	586.7	594.5	607.3	619.8	635.9	651.9	667.8	686.0	706.2	728.0	751.0
15°	552.8	559.3	569.7	587.1	603.5	619.1	643.0	660.0	685.5	709.7	737.5
17.5°	523.7	531.9	540.7	555.6	572.5	592.1	613.5	634.8	659.4	690.1	721.4
20°	506.0	512.6	522.6	534.1	552.1	571.7	592.0	613.5	643.7	675.4	709.1
22.5°	486.6	493.7	505.1	517.6	532.7	551.6	573.9	597.6	629.0	660.2	696.8
25°	463.8	468.7	479.1	490.3	505.3	521.3	544.6	570.8	601.8	637.5	674.8
27.5°	442.3	446.6	456.2	465.8	479.4	498.4	519.2	545.6	574.9	611.1	652.4
30°	426.8	431.4	439.9	450.4	463.5	480.2	501.4	526.2	557.7	593.0	636.2
32.5°	413.5	417.6	424.0	434.5	447.2	463.4	483.1	508.5	539.8	575.8	618.1
35°	392.8	397.4	402.3	410.4	421.6	437.3	458.9	482.8	512.8	547.5	586.4
37.5°	372.3	377.2	381.6	388.9	399.1	412.9	431.6	456.5	483.7	517.1	554.5
40°	359.5	363.3	367.0	374.8	385.0	398.0	415.3	437.6	466.4	497.5	528.6
42.5°	346.6	350.3	353.4	360.2	369.5	382.1	398.6	420.3	447.0	476.0	503.4
45°	326.4	328.7	332.3	338.2	345.7	357.1	373.2	392.5	415.1	442.6	463.1
47.5°	304.5	308.2	311.1	316.2	322.4	333.6	349.0	365.5	386.0	406.4	420.9
50°	287.8	291.4	295.7	300.6	306.4	316.9	331.0	347.7	365.0	380.7	393.1
52.5°	272.2	275.4	280.0	284.6	291.8	300.7	312.7	327.5	344.6	355.9	366.2
55°	248.9	250.6	255.8	260.4	267.3	273.8	285.9	298.9	309.4	317.9	326.4
57.5°	225.2	227.4	230.4	234.5	241.3	249.0	257.4	269.1	275.2	279.6	286.2
60°	210.0	210.6	212.6	217.5	222.7	229.6	239.4	247.6	252.2	255.8	261.3
62.5°	193.2	193.4	196.7	200.3	204.1	211.5	219.6	226.1	230.0	231.7	237.0
65°	169.8	169.1	171.1	174.0	178.6	183.5	190.4	196.2	195.9	197.9	201.1
67.5°	145.8	145.1	145.1	147.9	151.6	156.0	160.7	164.1	164.2	166.8	168.4
70°	129.5	127.6	128.9	131.1	132.8	136.4	141.6	142.9	143.3	144.6	146.2
72.5°	112.8	112.1	113.1	114.2	115.3	118.0	122.5	123.3	123.4	124.2	126.8
75°	89.6	88.9	88.3	89.3	90.6	92.6	94.2	95.5	95.1	95.5	97.5
77.5°	67.2	65.3	65.0	65.5	65.9	67.1	68.8	68.6	69.0	68.9	71.1
80°	53.3	50.7	50.4	50.4	50.7	51.3	52.0	52.7	51.7	52.7	53.3
82.5°	39.2	37.6	37.5	37.3	37.4	37.5	37.9	38.2	38.1	38.5	38.9
85°	21.6	20.9	20.0	20.6	20.3	19.3	20.0	18.9	18.7	18.9	19.3
87.5°	9.6	9.7	9.0	8.8	8.3	8.4	7.6	7.1	6.5	6.5	7.2
90°	11.5	10.8	9.4	8.8	7.4	6.7	5.4	4.0	2.7	1.4	0.7
92.5°	175.7	217.1	220.5	153.6	92.0	55.2	35.6	23.9	15.6	10.0	8.2
95°	583.7	596.5	486.7	300.9	152.8	80.8	50.5	35.6	28.2	22.9	22.2
97.5°	738.5	637.0	434.6	240.2	131.6	84.0	62.2	48.9	41.5	37.7	36.9
100°	776.2	608.0	387.8	218.1	130.6	91.5	71.4	58.5	51.1	48.5	47.1
102.5°	753.6	556.7	352.2	209.0	135.4	100.7	81.0	69.3	61.4	59.2	58.5
105°	681.3	488.1	317.8	205.3	145.4	115.8	96.9	86.2	79.5	76.1	76.1
107.5°	607.5	440.8	303.2	211.5	160.2	131.6	114.6	103.4	97.9	94.6	93.3
110°	565.5	418.7	298.9	217.5	171.0	143.4	125.9	115.8	109.7	107.0	105.7



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	534.3	405.8	298.9	225.0	181.2	154.7	137.8	127.6	121.6	119.4	118.0
115°	500.2	391.8	300.9	236.3	197.3	172.4	155.5	145.4	139.4	137.3	136.0
117.5°	479.8	385.0	305.4	249.3	213.7	190.1	173.8	162.4	156.4	154.2	152.1
120°	468.6	381.7	309.7	257.9	225.5	202.0	185.1	173.7	167.6	165.0	162.9
122.5°	458.8	379.0	313.4	267.5	236.9	213.3	196.5	183.9	177.9	175.7	174.3
125°	445.7	375.7	319.8	280.7	251.8	229.5	212.1	199.2	193.2	189.9	188.5
127.5°	433.5	374.0	326.9	292.8	266.2	244.8	227.3	213.7	206.0	201.7	199.7
130°	425.5	373.0	331.2	300.9	275.3	254.5	236.9	222.8	214.0	208.7	206.6
132.5°	419.0	373.0	336.0	307.9	284.0	263.1	245.6	230.9	221.1	214.6	212.1
135°	411.3	373.0	342.7	317.8	295.6	274.7	256.5	242.4	231.6	223.5	220.8
137.5°	404.5	373.8	348.7	325.0	303.8	284.7	266.0	252.2	241.4	233.8	231.9
140°	401.2	374.3	351.4	329.8	309.7	290.2	272.0	259.2	248.4	240.3	238.3
142.5°	398.6	374.9	353.0	332.6	313.4	295.0	277.9	265.6	254.9	247.4	245.8
145°	394.5	374.3	354.8	336.6	319.8	302.3	286.8	274.7	265.3	258.5	257.2
147.5°	390.3	372.6	355.4	339.1	323.8	308.5	294.9	284.4	275.6	269.8	269.0
150°	387.1	370.9	355.4	340.6	326.5	311.7	300.2	290.8	282.1	277.3	276.0
152.5°	383.3	368.8	354.9	341.7	329.2	315.5	305.1	296.2	288.5	284.4	283.5
155°	377.0	364.9	353.4	342.7	331.9	320.5	311.0	304.3	297.6	293.5	293.5
157.5°	371.1	360.8	351.7	343.4	334.2	324.3	317.2	311.3	305.5	302.3	302.4
160°	366.3	358.2	350.1	343.4	335.3	326.5	320.5	315.0	310.4	307.6	308.3
162.5°	361.9	354.9	348.4	342.8	336.3	328.6	323.6	319.3	315.2	312.5	313.1
165°	355.4	350.1	346.0	342.0	336.6	331.2	327.2	324.5	321.2	319.1	320.5
167.5°	349.1	345.3	342.2	340.4	336.6	332.2	329.6	327.7	325.8	324.6	325.3
170°	345.3	342.7	340.6	339.3	336.6	333.2	331.2	329.8	328.6	327.9	328.6
172.5°	341.6	339.4	338.5	338.2	336.0	333.2	332.3	331.5	330.1	329.5	330.7
175°	336.6	336.0	336.0	336.6	335.3	333.2	333.2	333.2	332.6	331.9	333.2
177.5°	334.4	333.9	333.9	335.0	334.4	333.4	333.4	333.9	333.4	333.4	334.4
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	774.8	778.4	780.8	785.2	788.9	791.0	792.8	794.4	796.3	797.8	802.3
5°	779.7	788.2	795.5	806.6	816.7	824.6	833.0	840.6	846.8	855.7	862.5
7.5°	777.6	792.7	808.6	825.7	843.3	859.7	874.7	888.8	901.6	917.0	930.5
10°	775.5	796.1	816.4	839.6	863.5	883.7	902.8	922.0	936.1	955.7	972.4
12.5°	774.0	798.2	822.7	850.6	876.8	905.4	930.7	944.8	966.2	981.9	1001.7
15°	767.3	799.4	833.0	864.4	901.7	928.2	950.5	977.9	997.9	1017.9	1039.4
17.5°	755.4	791.8	829.5	870.6	906.4	934.9	963.5	990.0	1013.8	1040.5	1067.5
20°	750.0	786.3	829.5	871.7	906.6	936.4	965.9	995.0	1021.1	1055.5	1086.5
22.5°	738.5	782.4	822.2	863.2	899.3	931.7	965.1	998.1	1032.9	1071.7	1110.6
25°	717.9	762.4	804.6	845.2	881.5	922.0	957.7	1001.9	1046.3	1097.7	1146.1
27.5°	696.6	739.2	777.8	817.0	859.4	905.3	951.5	1001.6	1059.9	1124.6	1193.0
30°	679.3	719.5	757.2	797.4	841.5	893.2	943.9	1003.5	1070.8	1143.8	1224.9
32.5°	659.2	696.3	732.9	775.4	823.5	878.0	937.1	1002.4	1083.4	1166.3	1249.7
35°	624.7	655.8	693.4	738.8	793.2	855.7	924.0	1001.2	1094.1	1189.2	1259.6
37.5°	583.8	612.8	652.4	702.2	759.1	826.2	907.3	998.8	1097.5	1173.4	1196.1
40°	556.4	583.2	624.4	676.1	734.3	805.3	894.2	991.0	1086.5	1135.0	1116.3
42.5°	527.0	555.2	595.4	646.5	709.1	786.4	877.7	974.6	1054.6	1072.9	1008.5
45°	480.8	509.9	549.5	601.2	668.6	752.3	847.5	935.4	981.5	948.5	848.8
47.5°	437.8	465.1	501.8	555.1	624.7	711.3	802.9	873.1	876.8	797.9	691.4
50°	408.5	433.7	470.6	524.0	593.0	680.6	763.4	818.6	793.8	704.6	602.2
52.5°	379.7	404.4	440.8	493.6	561.9	642.1	719.2	757.9	711.1	619.5	532.0
55°	338.2	359.8	395.5	444.2	508.9	583.5	648.9	662.3	601.5	511.2	440.2
57.5°	297.6	317.8	350.3	395.1	454.3	520.4	571.5	568.7	504.4	426.9	370.6
60°	270.2	289.8	318.6	362.4	416.4	473.3	517.1	506.6	442.9	376.2	328.7
62.5°	245.6	263.1	290.3	328.6	377.9	430.6	466.6	451.2	388.7	330.4	292.8
65°	209.3	224.0	247.3	280.0	320.9	364.4	392.2	372.2	318.9	273.5	243.3
67.5°	174.7	186.5	206.0	232.1	267.0	301.9	318.8	298.8	256.1	222.9	200.6
70°	152.7	163.2	178.2	201.5	231.9	261.3	274.1	256.1	219.5	191.0	175.0
72.5°	130.8	139.4	152.7	173.5	197.9	223.4	234.5	217.4	187.3	163.2	148.3
75°	101.1	106.9	116.1	130.5	149.8	170.0	176.3	161.3	142.0	124.0	114.2
77.5°	72.3	77.3	84.3	93.3	107.0	119.9	125.4	116.7	101.7	90.3	82.3
80°	55.6	58.2	64.1	71.6	82.4	90.6	94.2	88.6	78.2	69.7	63.5
82.5°	39.6	42.3	45.8	52.0	58.9	64.4	68.3	64.6	57.0	50.3	46.7
85°	19.3	20.9	22.9	25.5	30.7	34.0	33.7	31.4	28.4	25.8	23.8
87.5°	7.1	7.6	8.7	10.2	11.3	12.5	13.3	12.9	12.1	11.5	10.8
90°	1.4	2.7	4.0	5.4	6.7	7.4	8.8	9.4	10.8	11.5	12.1
92.5°	10.0	15.6	23.9	35.6	55.2	92.0	153.6	220.5	217.1	175.7	119.3
95°	22.9	28.2	35.6	50.5	80.8	152.8	300.9	486.7	596.5	583.7	484.1
97.5°	37.7	41.5	48.9	62.2	84.0	131.6	240.2	434.6	637.0	738.5	720.9
100°	48.5	51.1	58.5	71.4	91.5	130.6	218.1	387.8	608.0	776.2	828.0
102.5°	59.2	61.4	69.3	81.0	100.7	135.4	209.0	352.2	556.7	753.6	864.1
105°	76.1	79.5	86.2	96.9	115.8	145.4	205.3	317.8	488.1	681.3	842.8
107.5°	94.6	97.9	103.4	114.6	131.6	160.2	211.5	303.2	440.8	607.5	766.9
110°	107.0	109.7	115.8	125.9	143.4	171.0	217.5	298.9	418.7	565.5	710.9



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	119.4	121.6	127.6	137.8	154.7	181.2	225.0	298.9	405.8	534.3	666.8
115°	137.3	139.4	145.4	155.5	172.4	197.3	236.3	300.9	391.8	500.2	611.3
117.5°	154.2	156.4	162.4	173.8	190.1	213.7	249.3	305.4	385.0	479.8	575.5
120°	165.0	167.6	173.7	185.1	202.0	225.5	257.9	309.7	381.7	468.6	556.0
122.5°	175.7	177.9	183.9	196.5	213.3	236.9	267.5	313.4	379.0	458.8	541.6
125°	189.9	193.2	199.2	212.1	229.5	251.8	280.7	319.8	375.7	445.7	520.4
127.5°	201.7	206.0	213.7	227.3	244.8	266.2	292.8	326.9	374.0	433.5	498.9
130°	208.7	214.0	222.8	236.9	254.5	275.3	300.9	331.2	373.0	425.5	485.3
132.5°	214.6	221.1	230.9	245.6	263.1	284.0	307.9	336.0	373.0	419.0	471.9
135°	223.5	231.6	242.4	256.5	274.7	295.6	317.8	342.7	373.0	411.3	454.4
137.5°	233.8	241.4	252.2	266.0	284.7	303.8	325.0	348.7	373.8	404.5	439.6
140°	240.3	248.4	259.2	272.0	290.2	309.7	329.8	351.4	374.3	401.2	431.5
142.5°	247.4	254.9	265.6	277.9	295.0	313.4	332.6	353.0	374.9	398.6	424.6
145°	258.5	265.3	274.7	286.8	302.3	319.8	336.6	354.8	374.3	394.5	415.3
147.5°	269.8	275.6	284.4	294.9	308.5	323.8	339.1	355.4	372.6	390.3	406.7
150°	277.3	282.1	290.8	300.2	311.7	326.5	340.6	355.4	370.9	387.1	401.9
152.5°	284.4	288.5	296.2	305.1	315.5	329.2	341.7	354.9	368.8	383.3	396.5
155°	293.5	297.6	304.3	311.0	320.5	331.9	342.7	353.4	364.9	377.0	388.5
157.5°	302.3	305.5	311.3	317.2	324.3	334.2	343.4	351.7	360.8	371.1	380.4
160°	307.6	310.4	315.0	320.5	326.5	335.3	343.4	350.1	358.2	366.3	375.0
162.5°	312.5	315.2	319.3	323.6	328.6	336.3	342.8	348.4	354.9	361.9	369.0
165°	319.1	321.2	324.5	327.2	331.2	336.6	342.0	346.0	350.1	355.4	360.8
167.5°	324.6	325.8	327.7	329.6	332.2	336.6	340.4	342.2	345.3	349.1	353.0
170°	327.9	328.6	329.8	331.2	333.2	336.6	339.3	340.6	342.7	345.3	348.7
172.5°	329.5	330.1	331.5	332.3	333.2	336.0	338.2	338.5	339.4	341.6	343.9
175°	331.9	332.6	333.2	333.2	333.2	335.3	336.6	336.0	336.0	336.6	338.6
177.5°	333.4	333.4	333.9	333.4	333.4	334.4	335.0	333.9	333.9	334.4	335.0
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	805.9	808.0	812.4	810.9	813.0	814.0	815.1
5°	871.0	881.5	886.1	885.4	892.3	890.6	889.0
7.5°	944.5	955.5	961.7	969.3	973.8	974.0	977.9
10°	986.1	1000.5	1006.4	1014.6	1019.9	1022.8	1022.4
12.5°	1018.0	1029.3	1042.5	1046.5	1053.6	1057.3	1055.9
15°	1056.4	1074.4	1088.1	1095.0	1103.9	1106.5	1110.1
17.5°	1090.7	1114.8	1130.9	1152.2	1160.3	1165.2	1162.3
20°	1116.6	1148.3	1164.4	1189.9	1203.9	1211.5	1208.8
22.5°	1147.3	1181.6	1211.3	1233.3	1254.7	1264.9	1267.0
25°	1199.7	1246.8	1290.3	1319.4	1345.9	1352.1	1365.9
27.5°	1258.4	1313.9	1360.4	1390.9	1409.5	1416.3	1420.6
30°	1295.2	1350.5	1385.5	1405.1	1411.0	1410.3	1409.7
32.5°	1313.3	1347.9	1354.6	1349.1	1335.7	1324.2	1312.3
35°	1287.7	1261.9	1223.2	1173.5	1137.0	1099.9	1096.3
37.5°	1158.1	1075.5	1011.2	939.5	898.1	872.5	854.8
40°	1036.1	942.3	864.4	803.9	761.7	745.1	728.8
42.5°	903.8	814.1	745.1	694.6	662.9	644.4	631.4
45°	734.3	655.1	601.2	564.6	539.3	525.0	516.8
47.5°	601.7	543.1	497.3	470.9	453.5	442.3	442.3
50°	530.5	474.6	444.2	423.3	408.2	399.3	401.0
52.5°	467.4	425.7	399.7	382.1	371.0	365.6	365.4
55°	390.9	360.8	343.8	331.0	323.5	317.3	318.6
57.5°	334.3	308.9	297.6	287.0	281.7	279.2	275.7
60°	299.3	279.7	269.8	261.3	256.1	254.2	250.6
62.5°	268.1	252.7	243.1	236.2	231.5	230.8	228.0
65°	225.3	213.6	205.1	201.8	196.9	195.6	195.6
67.5°	185.8	177.4	170.7	167.7	165.6	165.9	164.3
70°	160.9	154.0	149.8	146.5	144.9	145.3	143.9
72.5°	140.8	133.1	129.4	127.4	125.3	126.1	125.6
75°	106.6	102.7	100.7	98.8	97.5	96.8	96.2
77.5°	78.3	74.8	73.4	72.2	72.4	70.9	72.1
80°	60.5	57.6	56.6	54.9	54.6	54.6	54.3
82.5°	44.3	42.6	41.9	40.6	40.0	40.5	39.6
85°	22.9	21.6	21.3	21.3	20.6	20.0	21.6
87.5°	10.9	10.0	10.2	10.0	10.0	9.9	9.4
90°	12.8	13.4	14.8	14.8	14.8	15.5	15.5
92.5°	86.6	65.2	55.2	46.6	44.9	44.0	43.0
95°	381.7	298.9	242.4	194.6	174.4	169.0	158.2
97.5°	649.1	568.4	489.8	448.2	410.5	391.0	382.4
100°	795.0	725.7	655.7	609.2	560.8	535.9	525.1
102.5°	884.5	851.2	803.8	754.1	719.6	692.6	684.5
105°	935.1	964.8	957.3	935.7	913.5	900.1	892.0
107.5°	890.0	966.0	1001.2	1012.1	1011.9	1007.5	1002.1
110°	838.8	933.8	990.9	1021.2	1034.1	1038.8	1038.8



TEST NUMBER: P333180-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	788.2	884.2	951.7	995.9	1017.9	1029.6	1034.5
115°	715.7	807.9	881.2	933.8	966.0	984.9	993.7
117.5°	665.4	744.9	812.2	864.7	898.0	916.8	922.1
120°	636.9	710.9	770.2	819.9	852.3	870.5	875.8
122.5°	616.4	682.3	737.9	782.3	811.9	830.1	834.9
125°	589.1	647.6	696.1	733.8	761.4	776.2	782.9
127.5°	562.9	617.6	663.0	697.2	721.5	735.6	738.5
130°	544.7	597.1	640.9	674.6	696.8	710.2	714.3
132.5°	527.4	575.1	617.2	650.8	673.0	685.4	690.0
135°	500.8	544.0	582.3	611.9	634.1	646.3	650.3
137.5°	477.2	513.0	545.5	572.1	592.3	603.5	608.0
140°	463.1	494.1	522.4	547.3	564.8	574.9	578.2
142.5°	451.3	477.9	502.5	523.7	538.5	548.0	550.8
145°	436.3	457.1	475.3	491.5	502.9	510.3	513.0
147.5°	423.7	439.7	453.5	466.2	475.4	479.7	481.0
150°	416.7	429.5	441.6	451.8	459.8	462.5	463.1
152.5°	409.7	421.5	430.8	439.4	445.8	448.5	449.2
155°	399.2	408.6	416.0	422.8	427.5	429.5	430.2
157.5°	389.3	396.5	402.3	407.6	411.5	413.4	413.2
160°	381.7	388.5	393.1	397.9	401.2	402.6	401.9
162.5°	375.2	380.9	385.0	388.7	391.5	391.8	391.7
165°	365.6	369.6	373.0	375.7	377.0	377.0	377.0
167.5°	356.1	359.2	361.6	363.0	364.2	363.7	363.5
170°	350.8	352.8	354.1	355.4	356.1	356.1	355.4
172.5°	345.9	347.4	348.2	348.4	349.7	348.6	347.9
175°	338.6	340.0	340.0	340.0	340.6	339.3	338.6
177.5°	335.5	335.5	335.5	335.0	335.5	333.9	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9

(END OF REPORT)