

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333607-935

Luminaire Tested: **S125RDIP-S1090D1205U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333607-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1205U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7783.6 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333607-935

CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333607-935

CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	86	89	86	82	79	72	69	67	59	57	56	47	46	45	40
2	89	81	75	70	81	75	70	66	63	59	56	52	49	47	42	40	38	34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29
4	74	64	56	50	68	59	52	47	50	45	40	41	37	34	33	31	28	25
5	68	57	49	43	62	52	45	40	45	39	35	37	33	30	30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	30	25	21	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9939	9939	9939
5°	9962	9848	9909
10°	9886	9757	9757
15°	9768	9559	9482
20°	9619	9283	9171
25°	9443	9012	8813
30°	9223	8694	8416
35°	8999	8367	7972
40°	8790	8025	7535
45°	8535	7644	7059
50°	8280	7229	6563
55°	7983	6831	6033
60°	7687	6350	5465
65°	7335	5790	4814
70°	6936	5093	4147
75°	6381	4292	3451
80°	5620	3373	2894
85°	4735	2757	2586



TEST NUMBER: P333607-935

CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.7	1.9
10°-20°	404.4	5.2
20°-30°	586.4	7.5
30°-40°	668.3	8.6
40°-50°	651.5	8.4
50°-60°	548.4	7.0
60°-70°	384.4	4.9
70°-80°	197.6	2.5
80°-90°	52.7	0.7
90°-100°	49.1	0.6
100°-110°	302.3	3.9
110°-120°	548.3	7.0
120°-130°	703.7	9.0
130°-140°	756.9	9.7
140°-150°	710.4	9.1
150°-160°	574.7	7.4
160°-170°	371.7	4.8
170°-180°	128.2	1.6
0°-30°	1135.5	14.6
0°-40°	1803.9	23.2
0°-60°	3003.7	38.6
0°-90°	3638.4	46.7
90°-120°	899.7	11.6
90°-150°	3070.7	39.5
90°-180°	4145.0	53.3
0°-180°	7783.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1537	1532	1519	1530	1528	146
15°	1461	1453	1430	1428	1418	412
25°	1325	1306	1265	1250	1237	609
35°	1141	1112	1061	1028	1011	714
45°	934	899	837	792	773	721
55°	709	670	607	556	536	634
65°	480	439	379	334	315	475
75°	256	220	172	147	138	271
85°	64	44	37	36	35	72
90°	1	9	16	21	24	5
95°	57	52	16	21	21	73
105°	294	298	298	298	297	312
115°	552	557	558	554	548	547
125°	786	792	792	789	786	701
135°	980	985	984	981	976	755
145°	1136	1138	1138	1138	1133	710
155°	1251	1245	1247	1249	1242	576
165°	1320	1314	1315	1320	1313	373
175°	1350	1344	1345	1352	1344	128
180°	1350	1350	1350	1350	1350	



TEST NUMBER: P333607-935

CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0
2.5°	1541.7	1541.1	1540.5	1539.8	1539.2	1537.9	1535.9	1533.8	1531.7	1529.7	1531.7
5°	1536.6	1535.6	1534.6	1533.5	1532.5	1530.5	1527.7	1524.8	1522.0	1519.1	1521.7
7.5°	1521.5	1520.5	1519.5	1518.5	1517.5	1515.4	1511.9	1508.6	1505.1	1501.8	1503.6
10°	1507.5	1506.8	1506.0	1505.2	1504.4	1502.3	1498.7	1495.0	1491.4	1487.8	1488.6
12.5°	1491.7	1490.7	1489.8	1488.8	1487.8	1484.9	1480.1	1475.2	1470.3	1465.4	1466.0
15°	1461.0	1459.5	1457.9	1456.4	1454.8	1451.4	1446.0	1440.5	1435.1	1429.7	1429.4
17.5°	1426.4	1424.0	1421.7	1419.3	1416.9	1412.3	1405.5	1398.7	1391.8	1385.0	1383.7
20°	1399.5	1396.9	1394.3	1391.7	1389.1	1383.7	1375.4	1367.2	1358.9	1350.7	1349.4
22.5°	1369.7	1367.1	1364.5	1361.9	1359.3	1353.8	1345.1	1336.4	1327.7	1319.0	1316.5
25°	1325.1	1321.2	1317.3	1313.5	1309.6	1302.9	1293.3	1283.8	1274.2	1264.6	1261.3
27.5°	1273.9	1269.2	1264.5	1259.8	1255.1	1247.7	1237.4	1227.2	1216.9	1206.7	1202.0
30°	1236.7	1231.8	1226.9	1222.0	1217.1	1209.2	1198.3	1187.5	1176.6	1165.8	1159.9
32.5°	1200.4	1194.7	1189.0	1183.3	1177.5	1169.2	1158.0	1147.0	1135.9	1124.9	1118.4
35°	1141.4	1135.2	1129.0	1122.8	1116.6	1107.7	1096.1	1084.4	1072.8	1061.2	1053.7
37.5°	1083.5	1076.0	1068.4	1060.9	1053.3	1043.6	1031.6	1019.6	1007.6	995.7	986.6
40°	1042.6	1034.8	1027.1	1019.3	1011.6	1001.5	989.1	976.7	964.3	951.9	942.1
42.5°	999.8	991.9	984.0	975.9	968.0	957.6	944.8	932.0	919.2	906.4	897.0
45°	934.5	927.0	919.5	912.1	904.6	893.7	879.5	865.3	851.1	836.9	826.6
47.5°	866.9	858.9	851.0	843.2	835.3	824.1	809.9	795.5	781.2	766.9	756.2
50°	824.1	815.5	807.0	798.5	790.0	778.3	763.6	748.9	734.2	719.5	708.6
52.5°	777.6	768.9	760.1	751.4	742.7	731.3	717.5	703.5	689.7	675.8	664.1
55°	709.0	700.8	692.5	684.2	676.0	664.6	650.1	635.7	621.2	606.7	595.1
57.5°	639.7	630.9	622.1	613.2	604.4	593.1	579.1	565.2	551.2	537.3	525.9
60°	595.1	586.1	577.0	568.0	559.0	547.4	533.5	519.5	505.6	491.6	480.3
62.5°	547.7	539.1	530.5	521.8	513.2	501.8	487.7	473.5	459.3	445.1	434.6
65°	480.0	471.2	462.4	453.7	444.9	433.7	420.0	406.3	392.6	378.9	368.6
67.5°	412.8	404.1	395.3	386.5	377.7	366.8	353.6	340.5	327.4	314.3	304.9
70°	367.3	358.5	349.7	341.0	332.2	321.3	308.4	295.5	282.6	269.7	261.7
72.5°	322.7	314.1	305.5	297.0	288.3	278.0	266.0	253.8	241.8	229.7	222.3
75°	255.7	248.0	240.2	232.5	224.7	215.4	204.6	193.7	182.9	172.0	166.3
77.5°	189.2	183.0	176.8	170.7	164.5	157.0	148.4	139.7	131.0	122.3	118.3
80°	151.1	144.9	138.7	132.5	126.3	119.6	112.4	105.1	97.9	90.7	88.3
82.5°	113.9	108.3	102.7	97.2	91.6	86.4	81.4	76.4	71.5	66.5	65.4
85°	63.9	59.2	54.6	49.9	45.3	42.4	41.1	39.8	38.5	37.2	36.9
87.5°	21.6	20.5	19.4	18.3	17.2	16.7	16.9	17.0	17.0	17.1	17.4
90°	1.0	2.8	4.6	6.4	8.1	9.8	11.4	12.9	14.5	16.0	17.1
92.5°	15.4	14.2	12.9	11.7	10.4	10.5	11.9	13.3	14.6	16.0	17.1
95°	57.0	56.4	55.7	55.0	54.3	49.9	41.3	32.9	24.5	16.0	17.1
97.5°	119.1	120.3	121.5	122.7	123.9	116.1	99.4	82.7	66.0	49.2	43.0
100°	167.1	167.8	168.4	169.1	169.8	170.6	171.4	172.4	173.2	174.1	140.9
102.5°	215.9	216.8	217.7	218.4	219.3	220.0	220.5	221.1	221.6	222.1	215.9
105°	294.2	295.1	295.9	296.9	297.7	298.2	298.2	298.2	298.2	298.2	298.2
107.5°	375.5	375.5	375.5	375.5	375.5	375.7	376.1	376.5	377.0	377.5	377.5
110°	428.3	428.3	428.3	428.3	428.3	428.5	429.0	429.4	429.8	430.2	429.6



TEST NUMBER: P333607-935

CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	477.9	478.5	479.0	479.5	480.0	480.4	480.7	481.0	481.2	481.5	480.7
115°	552.3	553.5	554.6	555.7	556.8	557.5	557.7	557.9	558.1	558.4	557.5
117.5°	629.4	629.4	629.3	629.3	629.2	629.6	630.5	631.3	632.1	633.0	631.9
120°	677.4	677.2	677.0	676.7	676.6	676.7	677.4	678.1	678.7	679.4	679.0
122.5°	719.9	720.7	721.5	722.4	723.2	723.8	724.1	724.4	724.8	725.0	724.6
125°	785.5	787.0	788.6	790.1	791.7	792.5	792.5	792.5	792.5	792.5	791.6
127.5°	848.2	849.3	850.3	851.4	852.6	853.1	852.9	852.8	852.6	852.6	852.0
130°	886.6	887.7	888.8	889.9	891.0	891.7	891.9	892.2	892.3	892.6	891.9
132.5°	925.0	926.3	927.6	928.8	930.1	930.6	930.1	929.5	929.1	928.6	928.5
135°	979.6	980.9	982.3	983.6	985.0	985.4	985.0	984.6	984.0	983.6	983.2
137.5°	1029.8	1031.0	1032.2	1033.3	1034.5	1034.8	1034.5	1034.1	1033.6	1033.3	1033.4
140°	1062.6	1063.2	1063.6	1064.0	1064.5	1064.5	1064.4	1064.1	1063.9	1063.7	1064.1
142.5°	1092.3	1092.5	1092.9	1093.1	1093.4	1093.6	1094.0	1094.2	1094.6	1094.9	1095.0
145°	1135.7	1136.2	1136.6	1137.0	1137.5	1137.7	1137.7	1137.7	1137.7	1137.7	1138.0
147.5°	1173.7	1173.6	1173.5	1173.5	1173.4	1173.5	1173.7	1174.0	1174.3	1174.6	1174.8
150°	1197.7	1197.3	1196.9	1196.4	1196.0	1196.0	1196.4	1196.9	1197.3	1197.7	1198.2
152.5°	1221.0	1220.0	1219.0	1218.1	1217.0	1216.8	1217.3	1217.7	1218.1	1218.6	1219.0
155°	1250.8	1249.5	1248.1	1246.8	1245.4	1245.0	1245.4	1245.9	1246.4	1246.8	1247.5
157.5°	1273.8	1273.0	1272.2	1271.4	1270.6	1270.2	1270.3	1270.3	1270.4	1270.4	1271.1
160°	1289.9	1288.5	1287.2	1285.8	1284.5	1283.9	1284.2	1284.4	1284.6	1284.8	1285.7
162.5°	1302.6	1301.3	1299.9	1298.6	1297.3	1296.8	1296.9	1297.2	1297.4	1297.6	1298.9
165°	1319.8	1318.5	1317.2	1315.9	1314.5	1314.0	1314.1	1314.4	1314.6	1314.8	1316.2
167.5°	1332.7	1331.3	1329.9	1328.5	1327.1	1326.5	1326.8	1327.0	1327.2	1327.5	1329.0
170°	1339.9	1338.3	1336.7	1335.2	1333.6	1333.0	1333.2	1333.4	1333.6	1333.9	1335.7
172.5°	1344.6	1343.1	1341.5	1340.0	1338.4	1337.8	1338.3	1338.7	1339.0	1339.5	1341.1
175°	1349.9	1348.5	1347.2	1345.8	1344.5	1343.9	1344.2	1344.5	1344.6	1344.9	1346.6
177.5°	1352.3	1351.2	1350.1	1349.1	1348.0	1347.6	1347.7	1347.9	1348.1	1348.2	1349.5
180°	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9



TEST NUMBER: P333607-935

CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0
2.5°	1533.8	1535.9	1537.9	1538.8	1538.6	1538.4	1538.2	1538.0
5°	1524.3	1526.9	1529.5	1530.5	1530.0	1529.5	1529.0	1528.4
7.5°	1505.4	1507.2	1509.0	1509.6	1509.0	1508.5	1507.9	1507.3
10°	1489.4	1490.1	1490.9	1490.9	1490.1	1489.4	1488.6	1487.8
12.5°	1466.6	1467.1	1467.7	1467.4	1466.2	1465.1	1463.9	1462.7
15°	1429.2	1428.9	1428.7	1427.4	1425.0	1422.7	1420.4	1418.1
17.5°	1382.4	1381.1	1379.8	1378.3	1376.3	1374.4	1372.5	1370.6
20°	1348.1	1346.8	1345.5	1343.7	1341.4	1339.0	1336.7	1334.4
22.5°	1314.0	1311.4	1308.9	1306.7	1304.8	1302.9	1300.9	1299.0
25°	1257.9	1254.6	1251.2	1248.1	1245.3	1242.4	1239.6	1236.7
27.5°	1197.3	1192.7	1187.9	1184.2	1181.5	1178.7	1176.0	1173.3
30°	1153.9	1148.0	1142.0	1137.9	1135.6	1133.2	1130.9	1128.6
32.5°	1111.8	1105.2	1098.6	1093.9	1091.0	1088.0	1085.0	1082.1
35°	1046.2	1038.7	1031.2	1025.7	1022.1	1018.5	1014.9	1011.2
37.5°	977.7	968.7	959.7	953.5	949.9	946.4	942.9	939.4
40°	932.3	922.5	912.7	906.2	903.1	900.0	896.9	893.8
42.5°	887.6	878.1	868.7	861.8	857.2	852.7	848.2	843.6
45°	816.2	805.9	795.6	788.4	784.5	780.7	776.8	772.9
47.5°	745.6	734.9	724.4	716.9	712.6	708.3	704.0	699.7
50°	697.8	686.9	676.1	668.7	664.9	661.0	657.1	653.2
52.5°	652.5	640.8	629.0	621.3	617.4	613.5	609.7	605.8
55°	583.5	571.9	560.3	552.3	548.2	544.1	539.9	535.8
57.5°	514.5	503.2	491.8	484.2	480.6	476.9	473.2	469.6
60°	468.9	457.5	446.2	438.6	434.7	430.8	427.0	423.1
62.5°	424.1	413.5	403.0	395.8	391.9	388.1	384.2	380.3
65°	358.3	347.9	337.6	330.5	326.6	322.7	318.8	315.0
67.5°	295.4	285.9	276.5	270.2	267.1	264.0	260.9	257.8
70°	253.7	245.6	237.6	232.0	228.9	225.8	222.7	219.6
72.5°	214.9	207.5	200.1	195.4	193.3	191.2	189.2	187.1
75°	160.7	155.0	149.3	145.5	143.7	141.9	140.1	138.3
77.5°	114.3	110.4	106.3	103.7	102.4	101.0	99.7	98.3
80°	86.0	83.7	81.4	79.9	79.4	78.9	78.4	77.8
82.5°	64.3	63.2	62.2	61.5	61.1	60.8	60.5	60.2
85°	36.7	36.4	36.2	35.9	35.6	35.4	35.1	34.9
87.5°	17.6	17.8	18.1	18.1	18.1	18.0	17.9	17.8
90°	18.3	19.4	20.5	21.4	22.0	22.6	23.3	24.0
92.5°	18.3	19.4	20.5	21.2	21.4	21.8	22.1	22.4
95°	18.3	19.4	20.5	21.0	21.0	21.0	21.0	21.0
97.5°	36.7	30.4	24.1	21.0	21.0	21.0	21.0	21.0
100°	107.9	74.7	41.6	24.5	23.7	22.8	21.9	21.0
102.5°	209.6	203.4	197.1	186.4	171.3	156.1	141.0	125.9
105°	298.2	298.2	298.2	298.1	297.8	297.6	297.4	297.2
107.5°	377.5	377.5	377.6	377.3	376.6	376.0	375.3	374.6
110°	429.0	428.3	427.6	427.4	427.6	427.8	428.1	428.3



TEST NUMBER: P333607-935

CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	479.8	479.0	478.1	477.5	477.3	476.9	476.6	476.3
115°	556.6	555.7	554.8	553.7	552.3	551.0	549.7	548.4
117.5°	630.7	629.6	628.4	627.5	626.9	626.4	625.8	625.2
120°	678.6	678.1	677.7	676.9	675.8	674.7	673.6	672.4
122.5°	724.2	723.8	723.3	722.4	721.1	719.8	718.6	717.3
125°	790.7	789.8	788.9	788.2	787.5	786.9	786.2	785.5
127.5°	851.5	851.1	850.6	849.5	847.9	846.2	844.6	842.9
130°	891.2	890.5	889.9	889.0	887.9	886.8	885.7	884.6
132.5°	928.3	928.2	928.1	927.5	926.3	925.2	924.1	923.0
135°	982.7	982.3	981.9	980.9	979.6	978.3	977.0	975.6
137.5°	1033.5	1033.5	1033.6	1033.1	1031.9	1030.8	1029.6	1028.5
140°	1064.5	1065.0	1065.5	1065.0	1063.7	1062.4	1061.0	1059.7
142.5°	1095.1	1095.2	1095.3	1094.7	1093.3	1092.0	1090.6	1089.3
145°	1138.2	1138.4	1138.6	1138.1	1136.7	1135.4	1134.0	1132.7
147.5°	1175.1	1175.4	1175.6	1174.9	1173.4	1171.7	1170.2	1168.5
150°	1198.7	1199.1	1199.5	1198.9	1197.1	1195.3	1193.5	1191.8
152.5°	1219.4	1220.0	1220.4	1219.8	1218.1	1216.6	1215.0	1213.4
155°	1248.1	1248.8	1249.5	1248.9	1247.2	1245.4	1243.5	1241.8
157.5°	1271.9	1272.6	1273.2	1272.7	1270.9	1269.2	1267.4	1265.6
160°	1286.6	1287.5	1288.4	1288.0	1286.2	1284.4	1282.6	1280.8
162.5°	1300.1	1301.4	1302.6	1302.3	1300.3	1298.3	1296.4	1294.4
165°	1317.5	1318.9	1320.2	1319.9	1318.2	1316.4	1314.6	1312.9
167.5°	1330.7	1332.2	1333.9	1333.7	1331.6	1329.6	1327.7	1325.7
170°	1337.4	1339.2	1341.0	1340.8	1338.9	1336.9	1334.9	1332.8
172.5°	1342.6	1344.3	1345.8	1345.7	1343.7	1341.7	1339.6	1337.6
175°	1348.4	1350.2	1351.9	1351.9	1349.9	1347.9	1345.8	1343.8
177.5°	1350.7	1352.0	1353.2	1353.1	1351.8	1350.3	1348.8	1347.5
180°	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9

(END OF REPORT)