

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333609-935

Luminaire Tested: **S125RDIP-S1090D1205U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333609-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1205U935-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7359.6 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333609-935
CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333609-935

CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		56	56	56	49
1	98	94	90	86	90	86	83	80	73	71	69		61	59	58		49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57		54	51	48		44	42	40	36
3	82	72	65	59	75	67	61	56	57	52	48		48	44	41		39	37	34	30
4	75	64	56	50	69	59	53	47	51	45	41		43	39	35		35	32	30	26
5	69	57	49	43	63	53	46	41	45	40	36		38	34	31		32	29	26	23
6	63	51	43	38	58	48	41	35	41	35	31		35	30	27		29	26	23	20
7	59	46	38	33	54	43	36	31	37	32	28		32	27	24		26	23	21	18
8	54	42	34	29	50	39	32	28	34	28	25		29	25	21		24	21	18	16
9	51	38	31	26	47	36	29	25	31	26	22		27	22	19		22	19	17	15
10	47	35	28	23	44	33	27	22	29	23	20		25	20	18		21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9939	9939	9939
5°	9962	9848	9909
10°	9886	9757	9757
15°	9768	9559	9482
20°	9619	9283	9171
25°	9443	9012	8813
30°	9223	8694	8416
35°	8999	8367	7972
40°	8790	8025	7535
45°	8535	7644	7059
50°	8280	7229	6563
55°	7983	6831	6033
60°	7687	6350	5465
65°	7335	5790	4814
70°	6936	5093	4147
75°	6381	4292	3451
80°	5620	3373	2894
85°	4735	2757	2586



TEST NUMBER: P333609-935

CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.7	2.0
10°-20°	404.4	5.5
20°-30°	586.4	8.0
30°-40°	668.3	9.1
40°-50°	651.5	8.9
50°-60°	548.4	7.5
60°-70°	384.4	5.2
70°-80°	197.6	2.7
80°-90°	52.7	0.7
90°-100°	359.7	4.9
100°-110°	773.2	10.5
110°-120°	725.6	9.9
120°-130°	588.1	8.0
130°-140°	471.9	6.4
140°-150°	356.1	4.8
150°-160°	250.7	3.4
160°-170°	147.8	2.0
170°-180°	48.1	0.7
0°-30°	1135.5	15.4
0°-40°	1803.9	24.5
0°-60°	3003.7	40.8
0°-90°	3638.4	49.4
90°-120°	1858.5	25.3
90°-150°	3274.7	44.5
90°-180°	3721.0	50.6
0°-180°	7359.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1537	1532	1519	1530	1528	146
15°	1461	1453	1430	1428	1418	412
25°	1325	1306	1265	1250	1237	609
35°	1141	1112	1061	1028	1011	714
45°	934	899	837	792	773	721
55°	709	670	607	556	536	634
65°	480	439	379	334	315	475
75°	256	220	172	147	138	271
85°	64	44	37	36	35	72
90°	1	9	16	21	23	5
95°	33	98	886	402	235	35
105°	113	158	725	1428	1326	119
115°	202	244	582	1255	1477	199
125°	280	328	558	998	1164	248
135°	328	395	554	837	966	255
145°	382	438	556	693	762	239
155°	436	469	542	613	639	201
165°	476	489	520	552	560	134
175°	495	495	499	505	503	47
180°	496	496	496	496	496	



TEST NUMBER: P333609-935

CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0
2.5°	1541.7	1541.1	1540.5	1539.8	1539.2	1537.9	1535.9	1533.8	1531.7	1529.7	1531.7
5°	1536.6	1535.6	1534.6	1533.5	1532.5	1530.5	1527.7	1524.8	1522.0	1519.1	1521.7
7.5°	1521.5	1520.5	1519.5	1518.5	1517.5	1515.4	1511.9	1508.6	1505.1	1501.8	1503.6
10°	1507.5	1506.8	1506.0	1505.2	1504.4	1502.3	1498.7	1495.0	1491.4	1487.8	1488.6
12.5°	1491.7	1490.7	1489.8	1488.8	1487.8	1484.9	1480.1	1475.2	1470.3	1465.4	1466.0
15°	1461.0	1459.5	1457.9	1456.4	1454.8	1451.4	1446.0	1440.5	1435.1	1429.7	1429.4
17.5°	1426.4	1424.0	1421.7	1419.3	1416.9	1412.3	1405.5	1398.7	1391.8	1385.0	1383.7
20°	1399.5	1396.9	1394.3	1391.7	1389.1	1383.7	1375.4	1367.2	1358.9	1350.7	1349.4
22.5°	1369.7	1367.1	1364.5	1361.9	1359.3	1353.8	1345.1	1336.4	1327.7	1319.0	1316.5
25°	1325.1	1321.2	1317.3	1313.5	1309.6	1302.9	1293.3	1283.8	1274.2	1264.6	1261.3
27.5°	1273.9	1269.2	1264.5	1259.8	1255.1	1247.7	1237.4	1227.2	1216.9	1206.7	1202.0
30°	1236.7	1231.8	1226.9	1222.0	1217.1	1209.2	1198.3	1187.5	1176.6	1165.8	1159.9
32.5°	1200.4	1194.7	1189.0	1183.3	1177.5	1169.2	1158.0	1147.0	1135.9	1124.9	1118.4
35°	1141.4	1135.2	1129.0	1122.8	1116.6	1107.7	1096.1	1084.4	1072.8	1061.2	1053.7
37.5°	1083.5	1076.0	1068.4	1060.9	1053.3	1043.6	1031.6	1019.6	1007.6	995.7	986.6
40°	1042.6	1034.8	1027.1	1019.3	1011.6	1001.5	989.1	976.7	964.3	951.9	942.1
42.5°	999.8	991.9	984.0	975.9	968.0	957.6	944.8	932.0	919.2	906.4	897.0
45°	934.5	927.0	919.5	912.1	904.6	893.7	879.5	865.3	851.1	836.9	826.6
47.5°	866.9	858.9	851.0	843.2	835.3	824.1	809.9	795.5	781.2	766.9	756.2
50°	824.1	815.5	807.0	798.5	790.0	778.3	763.6	748.9	734.2	719.5	708.6
52.5°	777.6	768.9	760.1	751.4	742.7	731.3	717.5	703.5	689.7	675.8	664.1
55°	709.0	700.8	692.5	684.2	676.0	664.6	650.1	635.7	621.2	606.7	595.1
57.5°	639.7	630.9	622.1	613.2	604.4	593.1	579.1	565.2	551.2	537.3	525.9
60°	595.1	586.1	577.0	568.0	559.0	547.4	533.5	519.5	505.6	491.6	480.3
62.5°	547.7	539.1	530.5	521.8	513.2	501.8	487.7	473.5	459.3	445.1	434.6
65°	480.0	471.2	462.4	453.7	444.9	433.7	420.0	406.3	392.6	378.9	368.6
67.5°	412.8	404.1	395.3	386.5	377.7	366.8	353.6	340.5	327.4	314.3	304.9
70°	367.3	358.5	349.7	341.0	332.2	321.3	308.4	295.5	282.6	269.7	261.7
72.5°	322.7	314.1	305.5	297.0	288.3	278.0	266.0	253.8	241.8	229.7	222.3
75°	255.7	248.0	240.2	232.5	224.7	215.4	204.6	193.7	182.9	172.0	166.3
77.5°	189.2	183.0	176.8	170.7	164.5	157.0	148.4	139.7	131.0	122.3	118.3
80°	151.1	144.9	138.7	132.5	126.3	119.6	112.4	105.1	97.9	90.7	88.3
82.5°	113.9	108.3	102.7	97.2	91.6	86.4	81.4	76.4	71.5	66.5	65.4
85°	63.9	59.2	54.6	49.9	45.3	42.4	41.1	39.8	38.5	37.2	36.9
87.5°	21.6	20.3	19.3	18.3	17.2	16.8	16.8	17.0	17.0	17.1	17.4
90°	1.0	2.0	4.0	6.0	8.0	10.0	11.0	13.0	14.0	16.0	17.0
92.5°	12.2	14.8	23.2	35.6	52.9	82.1	136.6	228.3	327.8	322.5	261.1
95°	33.0	34.0	42.0	53.0	75.0	120.0	227.1	447.2	723.3	886.4	867.4
97.5°	54.8	56.1	61.6	72.7	92.5	124.8	195.7	357.0	645.9	946.6	1097.5
100°	70.0	72.1	76.0	87.0	106.1	136.0	194.1	324.2	576.3	903.4	1153.5
102.5°	86.9	88.1	91.3	103.1	120.5	149.6	201.3	310.6	523.4	827.3	1119.9
105°	113.0	113.0	118.0	128.0	144.0	172.1	216.1	305.1	472.2	725.3	1012.4
107.5°	138.6	140.7	145.4	153.7	170.3	195.4	238.1	314.4	450.6	655.0	902.8
110°	157.0	159.1	163.1	172.1	187.1	213.1	254.1	323.1	444.2	622.2	840.3



TEST NUMBER: P333609-935

CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	175.5	177.5	180.6	189.7	204.7	229.9	269.3	334.3	444.2	603.0	793.9
115°	202.1	204.1	207.1	216.1	231.1	256.1	293.2	351.1	447.2	582.3	743.3
117.5°	226.1	229.1	232.3	241.3	258.3	282.5	317.5	370.4	453.8	572.0	713.1
120°	242.1	245.1	249.1	258.1	275.1	300.1	335.2	383.1	460.2	567.2	696.3
122.5°	258.9	261.1	264.3	273.3	292.0	316.9	352.0	397.6	465.8	563.3	681.9
125°	280.1	282.1	287.1	296.1	315.1	341.1	374.2	417.2	475.2	558.3	662.3
127.5°	296.7	299.7	306.2	317.5	337.8	363.8	395.5	435.2	485.8	555.9	644.3
130°	307.1	310.1	318.1	331.1	352.1	378.2	409.1	447.2	492.2	554.2	632.3
132.5°	315.1	318.9	328.6	343.2	365.0	391.0	422.0	457.6	499.4	554.2	622.7
135°	328.1	332.2	344.1	360.2	381.2	408.2	439.2	472.2	509.2	554.2	611.3
137.5°	344.6	347.6	358.8	374.8	395.4	423.2	451.4	483.0	518.2	555.4	601.1
140°	354.1	357.1	369.2	385.2	404.2	431.2	460.2	490.3	522.2	556.2	596.2
142.5°	365.3	367.6	378.8	394.8	413.0	438.4	465.8	494.2	524.6	557.1	592.3
145°	382.2	384.2	394.2	408.2	426.2	449.2	475.2	500.2	527.3	556.2	586.3
147.5°	399.8	401.0	409.6	422.6	438.2	458.4	481.2	503.9	528.2	553.6	580.1
150°	410.2	412.2	419.2	432.2	446.2	463.2	485.2	506.3	528.2	551.2	575.2
152.5°	421.4	422.6	428.8	440.2	453.4	468.8	489.2	507.8	527.4	548.0	569.6
155°	436.2	436.2	442.2	452.2	462.2	476.2	493.2	509.2	525.2	542.3	560.3
157.5°	449.4	449.2	454.0	462.6	471.4	482.0	496.6	510.2	522.6	536.2	551.5
160°	458.2	457.2	461.2	468.2	476.2	485.2	498.3	510.2	520.2	532.3	544.2
162.5°	465.4	464.4	468.4	474.6	481.0	488.4	499.8	509.5	517.8	527.4	537.9
165°	476.2	474.2	477.3	482.2	486.2	492.2	500.2	508.2	514.2	520.2	528.2
167.5°	483.5	482.4	484.2	487.0	489.8	493.6	500.2	505.8	508.6	513.2	518.8
170°	488.2	487.2	488.2	490.3	492.2	495.2	500.2	504.2	506.3	509.2	513.2
172.5°	491.5	489.7	490.6	492.6	493.8	495.2	499.4	502.7	503.0	504.5	507.6
175°	495.2	493.2	494.2	495.2	495.2	495.2	498.3	500.2	499.2	499.2	500.2
177.5°	497.1	495.4	495.4	496.2	495.4	495.4	497.1	497.8	496.2	496.2	497.1
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333609-935

CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0
2.5°	1533.8	1535.9	1537.9	1538.8	1538.6	1538.4	1538.2	1538.0
5°	1524.3	1526.9	1529.5	1530.5	1530.0	1529.5	1529.0	1528.4
7.5°	1505.4	1507.2	1509.0	1509.6	1509.0	1508.5	1507.9	1507.3
10°	1489.4	1490.1	1490.9	1490.9	1490.1	1489.4	1488.6	1487.8
12.5°	1466.6	1467.1	1467.7	1467.4	1466.2	1465.1	1463.9	1462.7
15°	1429.2	1428.9	1428.7	1427.4	1425.0	1422.7	1420.4	1418.1
17.5°	1382.4	1381.1	1379.8	1378.3	1376.3	1374.4	1372.5	1370.6
20°	1348.1	1346.8	1345.5	1343.7	1341.4	1339.0	1336.7	1334.4
22.5°	1314.0	1311.4	1308.9	1306.7	1304.8	1302.9	1300.9	1299.0
25°	1257.9	1254.6	1251.2	1248.1	1245.3	1242.4	1239.6	1236.7
27.5°	1197.3	1192.7	1187.9	1184.2	1181.5	1178.7	1176.0	1173.3
30°	1153.9	1148.0	1142.0	1137.9	1135.6	1133.2	1130.9	1128.6
32.5°	1111.8	1105.2	1098.6	1093.9	1091.0	1088.0	1085.0	1082.1
35°	1046.2	1038.7	1031.2	1025.7	1022.1	1018.5	1014.9	1011.2
37.5°	977.7	968.7	959.7	953.5	949.9	946.4	942.9	939.4
40°	932.3	922.5	912.7	906.2	903.1	900.0	896.9	893.8
42.5°	887.6	878.1	868.7	861.8	857.2	852.7	848.2	843.6
45°	816.2	805.9	795.6	788.4	784.5	780.7	776.8	772.9
47.5°	745.6	734.9	724.4	716.9	712.6	708.3	704.0	699.7
50°	697.8	686.9	676.1	668.7	664.9	661.0	657.1	653.2
52.5°	652.5	640.8	629.0	621.3	617.4	613.5	609.7	605.8
55°	583.5	571.9	560.3	552.3	548.2	544.1	539.9	535.8
57.5°	514.5	503.2	491.8	484.2	480.6	476.9	473.2	469.6
60°	468.9	457.5	446.2	438.6	434.7	430.8	427.0	423.1
62.5°	424.1	413.5	403.0	395.8	391.9	388.1	384.2	380.3
65°	358.3	347.9	337.6	330.5	326.6	322.7	318.8	315.0
67.5°	295.4	285.9	276.5	270.2	267.1	264.0	260.9	257.8
70°	253.7	245.6	237.6	232.0	228.9	225.8	222.7	219.6
72.5°	214.9	207.5	200.1	195.4	193.3	191.2	189.2	187.1
75°	160.7	155.0	149.3	145.5	143.7	141.9	140.1	138.3
77.5°	114.3	110.4	106.3	103.7	102.4	101.0	99.7	98.3
80°	86.0	83.7	81.4	79.9	79.4	78.9	78.4	77.8
82.5°	64.3	63.2	62.2	61.5	61.1	60.8	60.5	60.2
85°	36.7	36.4	36.2	35.9	35.6	35.4	35.1	34.9
87.5°	17.6	17.7	17.9	18.3	18.1	17.8	17.8	17.7
90°	18.0	19.0	20.0	22.0	22.0	22.0	23.0	23.0
92.5°	177.3	128.6	96.9	82.1	69.2	66.8	65.4	63.8
95°	719.3	567.2	444.2	360.2	289.1	259.1	251.2	235.1
97.5°	1071.3	964.7	844.8	727.9	666.1	610.1	581.1	568.3
100°	1230.5	1181.6	1078.5	974.4	905.4	833.4	796.3	780.3
102.5°	1284.2	1314.4	1265.0	1194.6	1120.7	1069.4	1029.2	1017.3
105°	1252.6	1389.7	1433.7	1422.6	1390.6	1357.6	1337.6	1325.6
107.5°	1139.7	1322.6	1435.6	1487.9	1504.1	1503.9	1497.3	1489.3
110°	1056.4	1246.6	1387.6	1472.7	1517.7	1536.7	1543.7	1543.7



TEST NUMBER: P333609-935

CATALOG NUMBER: S125RDIP-S1090D1205U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	990.8	1171.3	1314.0	1414.2	1480.1	1512.7	1530.1	1537.3
115°	908.4	1063.5	1200.5	1309.6	1387.6	1435.6	1463.6	1476.6
117.5°	855.1	988.9	1106.9	1206.9	1285.0	1334.6	1362.4	1370.4
120°	826.4	946.4	1056.4	1144.5	1218.6	1266.5	1293.6	1301.6
122.5°	804.8	916.0	1014.1	1096.5	1162.5	1206.5	1233.6	1240.8
125°	773.4	875.4	962.4	1034.5	1090.5	1131.5	1153.5	1163.6
127.5°	741.3	836.5	917.8	985.2	1036.0	1072.3	1093.1	1097.5
130°	721.3	809.3	887.4	952.4	1002.5	1035.4	1055.5	1061.4
132.5°	701.3	783.8	854.5	917.2	967.2	1000.2	1018.6	1025.5
135°	675.3	744.3	808.4	865.4	909.4	942.5	960.4	966.5
137.5°	653.3	709.1	762.3	810.8	850.2	880.2	896.8	903.4
140°	641.3	688.3	734.3	776.4	813.4	839.4	854.4	859.4
142.5°	630.9	670.7	710.3	746.7	778.2	800.1	814.3	818.6
145°	617.3	648.2	679.3	706.3	730.3	747.3	758.4	762.3
147.5°	604.5	629.6	653.5	673.9	692.9	706.5	712.9	714.7
150°	597.3	619.3	638.3	656.3	671.3	683.3	687.3	688.3
152.5°	589.3	608.9	626.3	640.3	652.9	662.5	666.5	667.5
155°	577.2	593.2	607.3	618.3	628.3	635.2	638.3	639.3
157.5°	565.2	578.4	589.3	597.9	605.6	611.5	614.2	614.1
160°	557.2	567.2	577.2	584.3	591.2	596.2	598.3	597.3
162.5°	548.5	557.7	566.0	572.2	577.6	581.9	582.3	582.0
165°	536.2	543.2	549.2	554.2	558.3	560.3	560.3	560.3
167.5°	524.6	529.3	533.8	537.4	539.4	541.2	540.4	540.3
170°	518.2	521.2	524.3	526.2	528.2	529.3	529.3	528.2
172.5°	511.0	514.0	516.3	517.5	517.8	519.6	518.1	517.0
175°	503.3	503.3	505.2	505.2	505.2	506.3	504.2	503.3
177.5°	497.8	498.6	498.6	498.6	497.8	498.6	496.2	496.2
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2

(END OF REPORT)