

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333588-935

Luminaire Tested: **S125RDIP-S1090D590U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333588-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D590U935-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5495.9 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	62	57
2	93	86	80	75	88	81	76	72	73	69	65	65	61	59	57	55	53	49
3	86	76	69	63	80	72	66	60	65	59	55	58	54	50	51	48	45	42
4	79	68	60	54	74	64	57	52	58	52	48	52	47	43	46	42	39	36
5	72	61	53	47	68	58	50	45	52	46	41	47	42	38	42	38	35	32
6	67	55	46	41	63	52	45	39	47	41	36	42	37	33	38	34	31	28
7	62	50	41	36	58	47	40	35	43	37	32	38	33	30	35	30	27	25
8	58	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22
9	54	41	34	29	51	39	32	28	36	30	26	33	28	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9143	9143	9143	9143
5°	10519	9155	8085	9155
10°	12066	9108	7134	9108
15°	13032	9014	6341	9014
20°	14370	8906	5856	8906
25°	16631	8763	5433	8763
30°	18098	8611	5158	8611
35°	15266	8435	4902	8435
40°	10662	8118	4683	8118
45°	7909	7691	4469	7691
50°	6306	7246	4285	7246
55°	5353	6694	4122	6694
60°	4624	6200	3858	6200
65°	4121	5665	3321	5665
70°	3620	5189	3029	5189
75°	3132	4494	2842	4494
80°	2377	3782	2377	3782
85°	1979	2971	2238	2971



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.8	2.5
10°-20°	397.8	7.2
20°-30°	630.8	11.5
30°-40°	760.7	13.8
40°-50°	679.3	12.4
50°-60°	520.9	9.5
60°-70°	338.5	6.2
70°-80°	164.6	3.0
80°-90°	40.6	0.7
90°-100°	176.6	3.2
100°-110°	379.6	6.9
110°-120°	356.2	6.5
120°-130°	288.7	5.3
130°-140°	231.7	4.2
140°-150°	174.8	3.2
150°-160°	123.1	2.2
160°-170°	72.5	1.3
170°-180°	23.6	0.4
0°-30°	1164.4	21.2
0°-40°	1925.0	35.0
0°-60°	3125.2	56.9
0°-90°	3669.0	66.8
90°-120°	912.4	16.6
90°-150°	1607.6	29.3
90°-180°	1827.0	33.2
0°-180°	5495.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1416	1416	1416	1416	1416	
5°	1622	1412	1247	1412	1622	162
15°	1949	1348	948	1348	1949	559
25°	2334	1230	762	1230	2334	1072
35°	1936	1070	622	1070	1936	1170
45°	866	842	489	842	866	691
55°	475	594	366	594	475	431
65°	270	371	217	371	270	268
75°	126	180	114	180	126	134
85°	27	40	30	40	27	31
90°	11	0	11	0	11	9
95°	116	16	116	16	116	164
105°	651	56	651	56	651	647
115°	725	99	725	99	725	708
125°	571	138	571	138	571	517
135°	474	161	474	161	474	368
145°	374	188	374	188	374	238
155°	314	214	314	214	314	146
165°	275	234	275	234	275	79
175°	247	243	247	243	247	24
180°	244	244	244	244	244	



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1489.1	1488.2	1490.0	1484.9	1485.4	1477.5	1477.5	1471.4	1463.5	1457.5	1454.7
5°	1622.5	1623.7	1621.3	1612.7	1606.8	1598.1	1588.2	1570.8	1556.3	1542.3	1531.3
7.5°	1759.9	1760.7	1753.0	1750.3	1735.7	1725.0	1703.1	1679.3	1658.3	1631.6	1611.1
10°	1839.9	1839.3	1831.1	1824.7	1812.0	1795.7	1774.2	1746.3	1720.1	1691.1	1663.2
12.5°	1886.4	1884.8	1882.2	1874.5	1862.6	1848.2	1830.0	1802.5	1770.3	1738.5	1706.0
15°	1949.1	1945.0	1937.5	1927.6	1910.7	1893.9	1873.5	1849.2	1818.3	1782.3	1752.1
17.5°	2026.7	2026.9	2015.3	2001.5	1978.6	1948.9	1917.4	1878.1	1836.3	1796.6	1764.4
20°	2090.9	2089.1	2077.5	2050.8	2024.6	1987.4	1951.5	1903.2	1852.0	1800.4	1760.2
22.5°	2183.0	2178.4	2166.3	2131.2	2090.7	2042.8	1987.7	1928.7	1866.9	1808.2	1755.6
25°	2333.8	2330.3	2306.4	2265.8	2208.9	2135.0	2063.0	1982.2	1893.3	1816.0	1752.1
27.5°	2437.0	2433.2	2415.5	2381.7	2329.2	2251.5	2154.0	2046.0	1935.0	1828.7	1736.6
30°	2426.8	2435.5	2433.2	2417.5	2378.0	2308.3	2218.2	2096.7	1964.8	1839.9	1730.0
32.5°	2280.8	2288.6	2309.0	2339.9	2342.2	2314.3	2247.0	2134.8	1998.3	1856.1	1724.9
35°	1936.3	1946.8	1986.3	2048.5	2129.9	2197.8	2211.7	2151.3	2028.7	1875.9	1717.3
37.5°	1488.6	1545.8	1579.1	1644.5	1767.5	1892.5	2012.8	2057.1	2004.8	1867.8	1704.8
40°	1264.6	1278.5	1337.7	1411.5	1515.0	1645.2	1816.6	1940.3	1944.5	1849.2	1685.2
42.5°	1082.3	1099.9	1140.7	1199.5	1288.1	1418.3	1595.3	1758.6	1834.3	1798.0	1659.7
45°	865.9	879.3	908.9	954.2	1022.2	1129.7	1281.9	1470.8	1620.7	1679.5	1591.1
47.5°	711.3	718.5	744.3	778.9	829.1	907.5	1025.4	1189.3	1369.2	1495.2	1482.8
50°	627.6	635.8	655.5	681.7	724.1	790.3	884.5	1021.1	1206.4	1360.4	1391.2
52.5°	562.5	569.3	581.6	606.3	641.4	692.2	768.3	891.8	1058.6	1222.4	1293.6
55°	475.4	480.0	489.9	503.9	531.8	568.3	634.0	719.5	854.3	1019.3	1123.9
57.5°	403.6	405.9	412.2	425.1	444.4	471.1	518.5	590.9	687.6	836.2	951.7
60°	358.0	360.3	368.4	377.1	392.3	416.6	453.8	504.4	597.4	720.1	836.8
62.5°	321.7	323.1	326.6	335.3	348.5	367.4	396.7	437.9	511.9	619.6	729.9
65°	269.7	270.2	271.4	278.4	286.5	300.4	319.6	348.7	404.5	485.9	583.4
67.5°	219.6	220.5	224.5	227.0	235.5	242.8	254.1	276.3	315.6	370.4	446.3
70°	191.7	191.2	195.3	198.2	201.0	209.8	217.3	235.4	259.8	301.6	365.0
72.5°	165.7	164.2	166.0	167.0	170.8	176.8	184.3	195.4	214.2	243.1	291.5
75°	125.5	126.1	126.1	127.3	130.2	132.5	134.8	140.6	151.1	170.3	196.4
77.5°	88.1	87.1	89.6	90.0	91.7	94.3	96.3	98.6	102.9	110.7	124.2
80°	63.9	63.9	64.5	66.2	65.7	66.8	69.7	72.1	77.3	82.0	86.6
82.5°	49.1	48.6	49.2	49.5	49.4	50.5	51.6	52.1	54.1	56.4	59.6
85°	26.7	26.7	27.3	27.3	27.9	27.9	28.5	28.5	28.5	29.0	29.6
87.5°	12.5	12.1	11.5	11.5	11.9	12.7	12.1	11.5	11.5	11.4	11.6
90°	11.3	11.3	10.8	10.8	10.8	9.8	9.3	8.9	8.4	7.8	6.9
92.5°	31.3	32.1	32.8	34.0	40.3	47.5	63.2	87.0	128.2	158.3	160.9
95°	115.5	123.3	127.2	142.0	176.8	218.1	278.4	353.1	425.9	435.1	355.1
97.5°	279.0	285.2	299.5	327.0	357.3	414.7	473.6	525.9	538.8	464.7	317.1
100°	383.1	391.0	409.1	444.4	478.4	529.4	580.1	604.1	566.3	443.5	282.9
102.5°	499.4	505.3	525.0	550.2	586.4	621.0	645.2	630.4	549.7	406.1	256.9
105°	650.7	656.7	666.5	682.7	698.4	703.8	682.2	614.9	497.1	356.1	231.8
107.5°	731.1	735.0	738.3	738.4	730.4	704.8	649.3	559.5	443.2	321.6	221.2
110°	757.9	757.9	754.4	745.0	723.0	681.2	612.0	518.7	412.6	305.5	218.1



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	754.7	751.1	742.6	726.6	694.3	645.1	575.1	486.5	389.8	296.1	218.1
115°	725.0	718.5	704.8	681.2	642.9	589.4	522.1	445.9	364.9	285.9	219.6
117.5°	672.8	668.8	655.2	630.9	592.5	543.4	485.4	419.8	350.1	280.9	222.7
120°	638.9	635.1	621.8	598.2	561.9	518.7	464.6	405.7	341.8	278.4	225.9
122.5°	609.1	605.5	592.3	570.7	538.3	497.8	449.7	395.1	334.8	276.6	228.7
125°	571.2	566.3	555.5	535.4	507.8	472.5	429.7	379.6	325.1	274.1	233.3
127.5°	538.8	536.6	526.4	508.6	483.7	450.6	410.7	363.9	316.3	272.9	238.5
130°	521.1	518.1	508.3	492.1	467.5	435.7	397.4	354.1	310.4	272.1	241.7
132.5°	503.4	500.1	491.0	474.8	450.3	419.6	384.8	344.3	305.7	272.1	245.2
135°	474.4	471.5	462.6	446.4	424.8	396.8	365.4	331.5	300.1	272.1	249.9
137.5°	443.5	440.2	432.1	417.3	398.0	374.3	348.1	320.7	295.1	272.7	254.4
140°	421.9	419.4	412.1	399.3	381.2	360.5	337.9	314.8	292.7	273.1	256.4
142.5°	401.8	399.8	392.8	382.0	366.6	348.7	329.2	309.7	290.8	273.5	257.5
145°	374.3	372.3	366.9	358.5	346.7	333.5	318.2	303.1	287.8	273.1	258.8
147.5°	350.9	350.0	346.8	340.2	330.8	320.8	309.1	296.8	284.7	271.8	259.3
150°	337.9	337.4	335.4	329.6	322.2	313.3	304.0	293.2	282.4	270.6	259.3
152.5°	327.7	327.2	325.2	320.6	314.4	307.5	298.9	289.3	279.7	269.1	258.9
155°	313.8	313.3	311.9	308.4	303.5	298.1	291.3	283.4	275.0	266.2	257.9
157.5°	301.4	301.5	300.1	297.3	293.5	289.3	284.0	277.5	270.7	263.2	256.6
160°	293.2	293.7	292.7	290.2	286.8	283.4	278.4	273.5	267.2	261.3	255.4
162.5°	285.8	285.9	285.7	283.6	280.9	277.8	273.8	269.2	264.1	258.9	254.3
165°	275.0	275.0	275.0	274.1	272.1	269.7	266.7	263.2	259.3	255.4	252.4
167.5°	265.2	265.3	265.7	264.8	263.8	262.1	259.8	257.5	254.7	251.9	249.7
170°	259.3	259.8	259.8	259.3	258.3	257.4	255.9	254.4	251.9	249.9	248.5
172.5°	253.8	254.3	255.1	254.3	254.0	253.4	252.4	250.9	249.2	247.6	246.9
175°	247.0	247.5	248.5	248.1	248.1	248.1	247.0	247.0	245.6	245.0	245.0
177.5°	243.6	243.6	244.8	244.4	244.8	244.8	244.8	244.4	244.0	243.6	243.6
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1454.7	1451.4	1445.4	1439.8	1432.8	1426.8	1422.6	1417.5	1411.0	1403.1	1396.5
5°	1519.1	1506.2	1489.4	1474.9	1456.3	1441.7	1426.7	1412.1	1397.6	1379.0	1362.7
7.5°	1590.4	1564.0	1538.3	1506.1	1476.8	1450.6	1425.5	1400.1	1375.2	1348.8	1323.4
10°	1634.1	1602.1	1566.7	1526.0	1488.8	1453.4	1420.8	1388.9	1355.2	1325.5	1293.6
12.5°	1675.1	1633.7	1593.2	1541.9	1497.2	1453.9	1412.5	1372.6	1336.6	1298.1	1263.9
15°	1712.0	1671.3	1626.0	1563.2	1501.1	1448.7	1399.9	1348.2	1303.5	1260.4	1222.1
17.5°	1726.3	1683.6	1631.0	1570.6	1502.7	1436.9	1374.0	1317.3	1264.6	1214.5	1171.4
20°	1720.7	1679.5	1625.4	1567.9	1495.2	1426.7	1358.7	1295.9	1237.3	1184.3	1138.4
22.5°	1707.2	1664.6	1612.4	1551.6	1482.6	1409.9	1337.3	1270.3	1208.8	1154.1	1104.1
25°	1687.0	1628.9	1575.5	1516.1	1450.5	1378.5	1303.5	1229.7	1164.0	1108.2	1053.6
27.5°	1665.9	1593.5	1525.4	1466.5	1397.1	1332.8	1260.6	1184.9	1115.9	1059.0	1003.0
30°	1646.9	1565.6	1490.6	1423.7	1358.1	1297.1	1228.5	1154.7	1083.8	1025.1	968.2
32.5°	1623.2	1536.7	1454.3	1377.3	1313.9	1253.4	1191.3	1120.8	1051.7	991.2	933.3
35°	1593.5	1483.1	1393.5	1311.6	1241.3	1182.6	1126.8	1069.9	1000.7	938.0	881.6
37.5°	1554.4	1429.1	1325.5	1236.3	1162.1	1103.2	1059.1	1007.1	944.0	883.9	831.6
40°	1530.7	1390.1	1276.7	1188.4	1110.5	1048.4	1007.1	962.9	905.4	849.0	796.7
42.5°	1499.1	1354.3	1227.4	1135.4	1057.0	997.2	955.5	916.9	868.7	815.5	759.5
45°	1437.1	1284.9	1151.8	1053.0	974.0	915.2	876.3	842.1	805.5	756.6	707.8
47.5°	1356.4	1212.5	1073.2	965.4	887.9	833.4	795.7	768.6	742.4	700.9	653.5
50°	1291.8	1153.0	1016.9	912.4	829.8	778.1	742.7	721.2	697.3	659.6	620.1
52.5°	1215.6	1091.6	958.4	851.4	773.6	725.1	691.0	669.6	650.0	619.1	581.4
55°	1095.5	986.8	864.7	767.7	696.2	647.4	614.8	594.5	582.9	556.7	527.1
57.5°	956.7	878.9	771.3	677.7	614.5	566.3	542.4	525.1	512.0	493.5	472.6
60°	860.1	805.5	708.9	620.1	562.0	516.0	494.6	480.0	467.8	452.1	435.8
62.5°	762.0	722.2	638.3	562.0	508.5	470.0	449.9	436.8	422.8	412.2	396.3
65°	630.5	595.0	536.9	477.1	427.7	396.9	382.4	370.7	362.1	350.4	339.4
67.5°	490.5	476.0	435.9	394.7	359.2	331.8	319.3	311.2	300.7	293.7	286.1
70°	404.5	397.5	369.0	341.7	308.6	290.0	278.4	274.8	262.1	255.1	249.9
72.5°	328.2	324.9	308.6	289.6	266.3	250.0	239.3	235.4	227.2	221.6	218.3
75°	224.9	226.1	223.2	210.9	202.2	191.7	182.4	180.1	174.4	169.7	166.8
77.5°	142.2	148.2	148.4	147.8	144.4	137.9	134.1	132.4	126.7	124.9	124.2
80°	97.6	104.0	109.9	109.3	108.1	106.3	103.4	101.7	98.8	97.0	95.9
82.5°	65.1	71.0	75.9	79.0	78.8	77.1	75.1	74.3	73.7	72.4	72.2
85°	30.8	31.9	33.7	37.8	40.6	41.2	40.6	40.1	38.3	38.9	39.5
87.5°	12.0	11.8	12.1	12.0	11.3	13.4	14.6	15.0	14.1	13.4	12.7
90°	6.4	5.4	4.9	4.0	2.9	2.0	0.9	0.5	0.9	2.0	2.9
92.5°	112.1	67.1	40.3	25.9	17.5	11.4	7.2	6.0	7.2	11.4	17.5
95°	219.6	111.5	59.0	36.9	26.0	20.7	16.7	16.2	16.7	20.7	26.0
97.5°	175.2	96.1	61.3	45.4	35.6	30.2	27.5	26.9	27.5	30.2	35.6
100°	159.1	95.3	66.8	52.1	42.7	37.4	35.4	34.4	35.4	37.4	42.7
102.5°	152.5	98.8	73.4	59.2	50.6	44.8	43.2	42.6	43.2	44.8	50.6
105°	149.8	106.1	84.5	70.7	62.9	57.9	55.5	55.5	55.5	57.9	62.9
107.5°	154.3	116.9	96.0	83.6	75.4	71.4	69.1	68.1	69.1	71.4	75.4
110°	158.6	124.8	104.6	91.9	84.5	80.1	78.1	77.1	78.1	80.1	84.5



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	164.1	132.2	112.9	100.5	93.2	88.7	87.1	86.2	87.1	88.7	93.2
115°	172.4	143.9	125.7	113.5	106.1	101.7	100.2	99.2	100.2	101.7	106.1
117.5°	181.8	155.9	138.7	126.8	118.5	114.1	112.4	111.0	112.4	114.1	118.5
120°	188.1	164.5	147.3	135.1	126.7	122.3	120.4	118.8	120.4	122.3	126.7
122.5°	195.2	172.8	155.6	143.4	134.1	129.8	128.2	127.1	128.2	129.8	134.1
125°	204.8	183.7	167.5	154.7	145.3	140.9	138.5	137.5	138.5	140.9	145.3
127.5°	213.6	194.2	178.6	165.8	155.9	150.3	147.1	145.7	147.1	150.3	155.9
130°	219.6	200.9	185.6	172.9	162.6	156.2	152.2	150.8	152.2	156.2	162.6
132.5°	224.6	207.2	191.9	179.2	168.5	161.3	156.6	154.7	156.6	161.3	168.5
135°	231.8	215.6	200.4	187.1	176.8	168.9	163.1	161.1	163.1	168.9	176.8
137.5°	237.1	221.6	207.8	194.1	184.0	176.2	170.7	169.2	170.7	176.2	184.0
140°	240.6	225.9	211.7	198.5	189.1	181.2	175.3	173.8	175.3	181.2	189.1
142.5°	242.6	228.7	215.2	202.8	193.8	186.0	180.5	179.3	180.5	186.0	193.8
145°	245.6	233.3	220.5	209.2	200.4	193.5	188.6	187.6	188.6	193.5	200.4
147.5°	247.4	236.3	225.1	215.1	207.4	201.0	196.8	196.2	196.8	201.0	207.4
150°	248.5	238.2	227.4	219.0	212.2	205.8	202.3	201.4	202.3	205.8	212.2
152.5°	249.3	240.1	230.1	222.6	216.1	210.5	207.4	206.9	207.4	210.5	216.1
155°	249.9	242.1	233.8	226.9	222.0	217.1	214.1	214.1	214.1	217.1	222.0
157.5°	250.5	243.8	236.6	231.4	227.1	222.9	220.5	220.6	220.5	222.9	227.1
160°	250.5	244.6	238.2	233.8	229.9	226.4	224.5	225.0	224.5	226.4	229.9
162.5°	250.1	245.4	239.8	236.2	233.0	230.0	228.0	228.5	228.0	230.0	233.0
165°	249.5	245.6	241.7	238.7	236.7	234.3	232.8	233.8	232.8	234.3	236.7
167.5°	248.3	245.6	242.3	240.5	239.1	237.7	236.9	237.3	236.9	237.7	239.1
170°	247.5	245.6	243.1	241.7	240.6	239.7	239.2	239.7	239.2	239.7	240.6
172.5°	246.8	245.2	243.1	242.5	241.9	240.8	240.4	241.3	240.4	240.8	241.9
175°	245.6	244.6	243.1	243.1	243.1	242.6	242.1	243.1	242.1	242.6	243.1
177.5°	244.4	244.0	243.2	243.2	243.6	243.2	243.2	244.0	243.2	243.2	243.6
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1391.9	1385.4	1380.8	1371.5	1364.9	1362.2	1357.0	1355.6	1360.7	1357.0	1356.6
5°	1350.6	1333.7	1320.3	1306.9	1292.4	1283.1	1269.2	1266.9	1263.3	1258.1	1257.0
7.5°	1300.9	1278.9	1261.7	1239.7	1220.5	1205.1	1187.6	1179.3	1174.8	1168.0	1159.0
10°	1267.4	1241.3	1218.1	1195.9	1172.2	1153.0	1135.5	1122.1	1113.4	1105.3	1101.8
12.5°	1234.4	1207.8	1178.0	1151.3	1124.7	1103.2	1083.9	1075.2	1065.6	1056.0	1047.9
15°	1183.2	1147.7	1115.2	1084.3	1061.7	1038.5	1019.9	1007.1	992.6	988.5	972.8
17.5°	1128.8	1094.0	1055.9	1023.5	997.2	971.6	951.1	936.7	925.7	910.8	903.5
20°	1094.8	1053.6	1016.4	986.8	957.7	927.5	906.5	894.3	883.9	871.7	865.9
22.5°	1058.6	1018.2	980.2	945.4	915.8	886.1	871.2	858.6	846.7	835.4	827.8
25°	1005.3	964.7	924.5	888.6	857.7	836.2	818.8	804.3	797.9	786.9	778.7
27.5°	952.7	909.5	867.9	831.9	807.8	786.5	772.2	760.7	749.2	739.5	732.5
30°	918.8	874.6	829.2	800.8	775.2	754.8	739.2	728.1	719.5	710.8	705.5
32.5°	884.8	839.3	799.0	768.3	744.1	726.5	710.3	699.8	690.6	681.0	674.8
35°	830.4	783.9	751.4	721.2	697.3	681.1	670.0	655.0	647.4	640.4	634.0
37.5°	779.9	736.7	701.5	674.9	654.2	638.1	623.8	615.6	606.3	600.0	594.7
40°	742.7	703.2	671.2	643.3	628.2	610.2	596.8	586.3	579.4	571.3	565.4
42.5°	709.2	672.4	641.4	616.3	597.5	582.3	569.4	559.0	550.1	544.3	539.4
45°	661.9	625.3	595.0	571.8	554.4	539.8	526.5	521.2	509.6	502.7	500.3
47.5°	612.9	580.2	551.0	529.6	511.8	498.0	485.4	474.8	468.4	461.5	457.8
50°	580.0	548.5	521.2	500.3	482.9	467.8	456.2	449.2	440.5	434.1	429.5
52.5°	547.0	517.9	490.6	470.6	455.5	440.4	427.4	420.4	412.2	408.0	404.8
55°	499.8	469.0	445.7	425.9	410.3	396.3	384.1	377.1	372.0	367.8	366.7
57.5°	446.3	421.9	400.3	382.5	366.2	353.1	342.4	335.8	331.1	330.5	327.1
60°	411.5	389.3	369.6	350.4	336.5	324.3	315.0	307.4	302.7	302.2	301.0
62.5°	376.6	355.4	337.1	320.2	307.6	295.9	287.1	278.6	275.8	272.9	270.4
65°	324.9	305.7	290.6	277.2	263.8	253.9	245.2	240.0	233.6	230.1	223.8
67.5°	274.1	259.2	244.7	233.4	222.9	213.5	206.3	198.5	194.2	191.4	186.8
70°	240.6	228.9	214.5	202.2	194.1	186.6	180.7	172.0	169.1	166.8	164.5
72.5°	209.0	198.7	186.6	176.7	168.5	161.4	154.7	150.6	147.7	145.4	144.0
75°	164.5	154.5	144.1	137.2	131.3	125.5	122.0	119.2	118.0	117.4	115.0
77.5°	120.8	115.5	107.2	101.6	97.7	95.4	92.3	90.7	90.7	88.1	87.3
80°	92.4	89.5	82.5	80.2	77.3	75.0	73.2	70.3	67.4	66.2	64.5
82.5°	68.7	65.8	63.0	59.2	56.8	55.4	53.7	52.6	53.0	51.4	50.5
85°	36.6	33.7	32.5	31.9	30.8	31.9	31.3	30.8	30.2	29.6	30.2
87.5°	12.4	12.6	12.2	13.3	12.1	12.7	12.8	12.5	12.6	12.7	12.4
90°	4.0	4.9	5.4	6.4	6.9	7.8	8.4	8.9	9.3	9.8	10.8
92.5°	25.9	40.3	67.1	112.1	160.9	158.3	128.2	87.0	63.2	47.5	40.3
95°	36.9	59.0	111.5	219.6	355.1	435.1	425.9	353.1	278.4	218.1	176.8
97.5°	45.4	61.3	96.1	175.2	317.1	464.7	538.8	525.9	473.6	414.7	357.3
100°	52.1	66.8	95.3	159.1	282.9	443.5	566.3	604.1	580.1	529.4	478.4
102.5°	59.2	73.4	98.8	152.5	256.9	406.1	549.7	630.4	645.2	621.0	586.4
105°	70.7	84.5	106.1	149.8	231.8	356.1	497.1	614.9	682.2	703.8	698.4
107.5°	83.6	96.0	116.9	154.3	221.2	321.6	443.2	559.5	649.3	704.8	730.4
110°	91.9	104.6	124.8	158.6	218.1	305.5	412.6	518.7	612.0	681.2	723.0



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	100.5	112.9	132.2	164.1	218.1	296.1	389.8	486.5	575.1	645.1	694.3
115°	113.5	125.7	143.9	172.4	219.6	285.9	364.9	445.9	522.1	589.4	642.9
117.5°	126.8	138.7	155.9	181.8	222.7	280.9	350.1	419.8	485.4	543.4	592.5
120°	135.1	147.3	164.5	188.1	225.9	278.4	341.8	405.7	464.6	518.7	561.9
122.5°	143.4	155.6	172.8	195.2	228.7	276.6	334.8	395.1	449.7	497.8	538.3
125°	154.7	167.5	183.7	204.8	233.3	274.1	325.1	379.6	429.7	472.5	507.8
127.5°	165.8	178.6	194.2	213.6	238.5	272.9	316.3	363.9	410.7	450.6	483.7
130°	172.9	185.6	200.9	219.6	241.7	272.1	310.4	354.1	397.4	435.7	467.5
132.5°	179.2	191.9	207.2	224.6	245.2	272.1	305.7	344.3	384.8	419.6	450.3
135°	187.1	200.4	215.6	231.8	249.9	272.1	300.1	331.5	365.4	396.8	424.8
137.5°	194.1	207.8	221.6	237.1	254.4	272.7	295.1	320.7	348.1	374.3	398.0
140°	198.5	211.7	225.9	240.6	256.4	273.1	292.7	314.8	337.9	360.5	381.2
142.5°	202.8	215.2	228.7	242.6	257.5	273.5	290.8	309.7	329.2	348.7	366.6
145°	209.2	220.5	233.3	245.6	258.8	273.1	287.8	303.1	318.2	333.5	346.7
147.5°	215.1	225.1	236.3	247.4	259.3	271.8	284.7	296.8	309.1	320.8	330.8
150°	219.0	227.4	238.2	248.5	259.3	270.6	282.4	293.2	304.0	313.3	322.2
152.5°	222.6	230.1	240.1	249.3	258.9	269.1	279.7	289.3	298.9	307.5	314.4
155°	226.9	233.8	242.1	249.9	257.9	266.2	275.0	283.4	291.3	298.1	303.5
157.5°	231.4	236.6	243.8	250.5	256.6	263.2	270.7	277.5	284.0	289.3	293.5
160°	233.8	238.2	244.6	250.5	255.4	261.3	267.2	273.5	278.4	283.4	286.8
162.5°	236.2	239.8	245.4	250.1	254.3	258.9	264.1	269.2	273.8	277.8	280.9
165°	238.7	241.7	245.6	249.5	252.4	255.4	259.3	263.2	266.7	269.7	272.1
167.5°	240.5	242.3	245.6	248.3	249.7	251.9	254.7	257.5	259.8	262.1	263.8
170°	241.7	243.1	245.6	247.5	248.5	249.9	251.9	254.4	255.9	257.4	258.3
172.5°	242.5	243.1	245.2	246.8	246.9	247.6	249.2	250.9	252.4	253.4	254.0
175°	243.1	243.1	244.6	245.6	245.0	245.0	245.6	247.0	247.0	248.1	248.1
177.5°	243.2	243.2	244.0	244.4	243.6	243.6	244.0	244.4	244.8	244.8	244.8
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1356.1	1351.0	1349.6	1351.4	1349.6	1351.0	1356.1	1356.6	1357.0	1360.7	1355.6
5°	1251.2	1245.4	1248.3	1247.1	1248.3	1245.4	1251.2	1257.0	1258.1	1263.3	1266.9
7.5°	1158.9	1151.7	1144.0	1146.4	1144.0	1151.7	1158.9	1159.0	1168.0	1174.8	1179.3
10°	1094.2	1088.5	1084.9	1087.9	1084.9	1088.5	1094.2	1101.8	1105.3	1113.4	1122.1
12.5°	1039.8	1036.4	1033.4	1032.1	1033.4	1036.4	1039.8	1047.9	1056.0	1065.6	1075.2
15°	965.9	958.9	956.0	948.4	956.0	958.9	965.9	972.8	988.5	992.6	1007.1
17.5°	897.6	895.3	887.7	884.5	887.7	895.3	897.6	903.5	910.8	925.7	936.7
20°	857.1	854.8	847.3	852.0	847.3	854.8	857.1	865.9	871.7	883.9	894.3
22.5°	823.7	818.6	816.1	814.8	816.1	818.6	823.7	827.8	835.4	846.7	858.6
25°	776.4	768.8	765.9	762.4	765.9	768.8	776.4	778.7	786.9	797.9	804.3
27.5°	729.2	725.1	721.3	720.4	721.3	725.1	729.2	732.5	739.5	749.2	760.7
30°	698.5	694.5	691.6	691.6	691.6	694.5	698.5	705.5	710.8	719.5	728.1
32.5°	671.1	668.0	665.0	664.6	665.0	668.0	671.1	674.8	681.0	690.6	699.8
35°	631.1	626.5	625.3	621.8	625.3	626.5	631.1	634.0	640.4	647.4	655.0
37.5°	589.6	585.7	585.7	585.3	585.7	585.7	589.6	594.7	600.0	606.3	615.6
40°	563.1	560.2	559.6	555.5	559.6	560.2	563.1	565.4	571.3	579.4	586.3
42.5°	534.8	533.2	531.2	529.5	531.2	533.2	534.8	539.4	544.3	550.1	559.0
45°	496.3	492.2	492.2	489.3	492.2	492.2	496.3	500.3	502.7	509.6	521.2
47.5°	456.5	453.4	453.7	450.7	453.7	453.4	456.5	457.8	461.5	468.4	474.8
50°	430.1	428.3	427.7	426.5	427.7	428.3	430.1	429.5	434.1	440.5	449.2
52.5°	403.6	402.7	404.9	402.3	404.9	402.7	403.6	404.8	408.0	412.2	420.4
55°	367.8	366.1	369.6	366.1	369.6	366.1	367.8	366.7	367.8	372.0	377.1
57.5°	326.8	325.2	328.3	326.6	328.3	325.2	326.8	327.1	330.5	331.1	335.8
60°	299.9	296.4	298.1	298.7	298.1	296.4	299.9	301.0	302.2	302.7	307.4
62.5°	267.8	265.7	267.0	264.3	267.0	265.7	267.8	270.4	272.9	275.8	278.6
65°	222.6	220.8	218.5	217.3	218.5	220.8	222.6	223.8	230.1	233.6	240.0
67.5°	187.0	182.8	182.7	183.7	182.7	182.8	187.0	186.8	191.4	194.2	198.5
70°	161.0	161.0	160.4	160.4	160.4	161.0	161.0	164.5	166.8	169.1	172.0
72.5°	142.8	142.4	141.3	140.9	141.3	142.4	142.8	144.0	145.4	147.7	150.6
75°	115.0	115.6	114.5	113.9	114.5	115.6	115.0	115.0	117.4	118.0	119.2
77.5°	85.0	82.5	83.8	82.5	83.8	82.5	85.0	87.3	88.1	90.7	90.7
80°	64.5	63.9	65.7	63.9	65.7	63.9	64.5	64.5	66.2	67.4	70.3
82.5°	51.1	50.5	51.2	49.9	51.2	50.5	51.1	50.5	51.4	53.0	52.6
85°	30.8	30.2	29.6	30.2	29.6	30.2	30.8	30.2	29.6	30.2	30.8
87.5°	12.8	12.4	12.5	12.5	12.5	12.4	12.8	12.4	12.7	12.6	12.5
90°	10.8	10.8	11.3	11.3	11.3	10.8	10.8	10.8	9.8	9.3	8.9
92.5°	34.0	32.8	32.1	31.3	32.1	32.8	34.0	40.3	47.5	63.2	87.0
95°	142.0	127.2	123.3	115.5	123.3	127.2	142.0	176.8	218.1	278.4	353.1
97.5°	327.0	299.5	285.2	279.0	285.2	299.5	327.0	357.3	414.7	473.6	525.9
100°	444.4	409.1	391.0	383.1	391.0	409.1	444.4	478.4	529.4	580.1	604.1
102.5°	550.2	525.0	505.3	499.4	505.3	525.0	550.2	586.4	621.0	645.2	630.4
105°	682.7	666.5	656.7	650.7	656.7	666.5	682.7	698.4	703.8	682.2	614.9
107.5°	738.4	738.3	735.0	731.1	735.0	738.3	738.4	730.4	704.8	649.3	559.5
110°	745.0	754.4	757.9	757.9	757.9	754.4	745.0	723.0	681.2	612.0	518.7



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	726.6	742.6	751.1	754.7	751.1	742.6	726.6	694.3	645.1	575.1	486.5
115°	681.2	704.8	718.5	725.0	718.5	704.8	681.2	642.9	589.4	522.1	445.9
117.5°	630.9	655.2	668.8	672.8	668.8	655.2	630.9	592.5	543.4	485.4	419.8
120°	598.2	621.8	635.1	638.9	635.1	621.8	598.2	561.9	518.7	464.6	405.7
122.5°	570.7	592.3	605.5	609.1	605.5	592.3	570.7	538.3	497.8	449.7	395.1
125°	535.4	555.5	566.3	571.2	566.3	555.5	535.4	507.8	472.5	429.7	379.6
127.5°	508.6	526.4	536.6	538.8	536.6	526.4	508.6	483.7	450.6	410.7	363.9
130°	492.1	508.3	518.1	521.1	518.1	508.3	492.1	467.5	435.7	397.4	354.1
132.5°	474.8	491.0	500.1	503.4	500.1	491.0	474.8	450.3	419.6	384.8	344.3
135°	446.4	462.6	471.5	474.4	471.5	462.6	446.4	424.8	396.8	365.4	331.5
137.5°	417.3	432.1	440.2	443.5	440.2	432.1	417.3	398.0	374.3	348.1	320.7
140°	399.3	412.1	419.4	421.9	419.4	412.1	399.3	381.2	360.5	337.9	314.8
142.5°	382.0	392.8	399.8	401.8	399.8	392.8	382.0	366.6	348.7	329.2	309.7
145°	358.5	366.9	372.3	374.3	372.3	366.9	358.5	346.7	333.5	318.2	303.1
147.5°	340.2	346.8	350.0	350.9	350.0	346.8	340.2	330.8	320.8	309.1	296.8
150°	329.6	335.4	337.4	337.9	337.4	335.4	329.6	322.2	313.3	304.0	293.2
152.5°	320.6	325.2	327.2	327.7	327.2	325.2	320.6	314.4	307.5	298.9	289.3
155°	308.4	311.9	313.3	313.8	313.3	311.9	308.4	303.5	298.1	291.3	283.4
157.5°	297.3	300.1	301.5	301.4	301.5	300.1	297.3	293.5	289.3	284.0	277.5
160°	290.2	292.7	293.7	293.2	293.7	292.7	290.2	286.8	283.4	278.4	273.5
162.5°	283.6	285.7	285.9	285.8	285.9	285.7	283.6	280.9	277.8	273.8	269.2
165°	274.1	275.0	275.0	275.0	275.0	275.0	274.1	272.1	269.7	266.7	263.2
167.5°	264.8	265.7	265.3	265.2	265.3	265.7	264.8	263.8	262.1	259.8	257.5
170°	259.3	259.8	259.8	259.3	259.8	259.8	259.3	258.3	257.4	255.9	254.4
172.5°	254.3	255.1	254.3	253.8	254.3	255.1	254.3	254.0	253.4	252.4	250.9
175°	248.1	248.5	247.5	247.0	247.5	248.5	248.1	248.1	248.1	247.0	247.0
177.5°	244.4	244.8	243.6	243.6	243.6	244.8	244.4	244.8	244.8	244.8	244.4
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1357.0	1362.2	1364.9	1371.5	1380.8	1385.4	1391.9	1396.5	1403.1	1411.0	1417.5
5°	1269.2	1283.1	1292.4	1306.9	1320.3	1333.7	1350.6	1362.7	1379.0	1397.6	1412.1
7.5°	1187.6	1205.1	1220.5	1239.7	1261.7	1278.9	1300.9	1323.4	1348.8	1375.2	1400.1
10°	1135.5	1153.0	1172.2	1195.9	1218.1	1241.3	1267.4	1293.6	1325.5	1355.2	1388.9
12.5°	1083.9	1103.2	1124.7	1151.3	1178.0	1207.8	1234.4	1263.9	1298.1	1336.6	1372.6
15°	1019.9	1038.5	1061.7	1084.3	1115.2	1147.7	1183.2	1222.1	1260.4	1303.5	1348.2
17.5°	951.1	971.6	997.2	1023.5	1055.9	1094.0	1128.8	1171.4	1214.5	1264.6	1317.3
20°	906.5	927.5	957.7	986.8	1016.4	1053.6	1094.8	1138.4	1184.3	1237.3	1295.9
22.5°	871.2	886.1	915.8	945.4	980.2	1018.2	1058.6	1104.1	1154.1	1208.8	1270.3
25°	818.8	836.2	857.7	888.6	924.5	964.7	1005.3	1053.6	1108.2	1164.0	1229.7
27.5°	772.2	786.5	807.8	831.9	867.9	909.5	952.7	1003.0	1059.0	1115.9	1184.9
30°	739.2	754.8	775.2	800.8	829.2	874.6	918.8	968.2	1025.1	1083.8	1154.7
32.5°	710.3	726.5	744.1	768.3	799.0	839.3	884.8	933.3	991.2	1051.7	1120.8
35°	670.0	681.1	697.3	721.2	751.4	783.9	830.4	881.6	938.0	1000.7	1069.9
37.5°	623.8	638.1	654.2	674.9	701.5	736.7	779.9	831.6	883.9	944.0	1007.1
40°	596.8	610.2	628.2	643.3	671.2	703.2	742.7	796.7	849.0	905.4	962.9
42.5°	569.4	582.3	597.5	616.3	641.4	672.4	709.2	759.5	815.5	868.7	916.9
45°	526.5	539.8	554.4	571.8	595.0	625.3	661.9	707.8	756.6	805.5	842.1
47.5°	485.4	498.0	511.8	529.6	551.0	580.2	612.9	653.5	700.9	742.4	768.6
50°	456.2	467.8	482.9	500.3	521.2	548.5	580.0	620.1	659.6	697.3	721.2
52.5°	427.4	440.4	455.5	470.6	490.6	517.9	547.0	581.4	619.1	650.0	669.6
55°	384.1	396.3	410.3	425.9	445.7	469.0	499.8	527.1	556.7	582.9	594.5
57.5°	342.4	353.1	366.2	382.5	400.3	421.9	446.3	472.6	493.5	512.0	525.1
60°	315.0	324.3	336.5	350.4	369.6	389.3	411.5	435.8	452.1	467.8	480.0
62.5°	287.1	295.9	307.6	320.2	337.1	355.4	376.6	396.3	412.2	422.8	436.8
65°	245.2	253.9	263.8	277.2	290.6	305.7	324.9	339.4	350.4	362.1	370.7
67.5°	206.3	213.5	222.9	233.4	244.7	259.2	274.1	286.1	293.7	300.7	311.2
70°	180.7	186.6	194.1	202.2	214.5	228.9	240.6	249.9	255.1	262.1	274.8
72.5°	154.7	161.4	168.5	176.7	186.6	198.7	209.0	218.3	221.6	227.2	235.4
75°	122.0	125.5	131.3	137.2	144.1	154.5	164.5	166.8	169.7	174.4	180.1
77.5°	92.3	95.4	97.7	101.6	107.2	115.5	120.8	124.2	124.9	126.7	132.4
80°	73.2	75.0	77.3	80.2	82.5	89.5	92.4	95.9	97.0	98.8	101.7
82.5°	53.7	55.4	56.8	59.2	63.0	65.8	68.7	72.2	72.4	73.7	74.3
85°	31.3	31.9	30.8	31.9	32.5	33.7	36.6	39.5	38.9	38.3	40.1
87.5°	12.8	12.7	12.1	13.3	12.2	12.6	12.4	12.7	13.4	14.1	15.0
90°	8.4	7.8	6.9	6.4	5.4	4.9	4.0	2.9	2.0	0.9	0.5
92.5°	128.2	158.3	160.9	112.1	67.1	40.3	25.9	17.5	11.4	7.2	6.0
95°	425.9	435.1	355.1	219.6	111.5	59.0	36.9	26.0	20.7	16.7	16.2
97.5°	538.8	464.7	317.1	175.2	96.1	61.3	45.4	35.6	30.2	27.5	26.9
100°	566.3	443.5	282.9	159.1	95.3	66.8	52.1	42.7	37.4	35.4	34.4
102.5°	549.7	406.1	256.9	152.5	98.8	73.4	59.2	50.6	44.8	43.2	42.6
105°	497.1	356.1	231.8	149.8	106.1	84.5	70.7	62.9	57.9	55.5	55.5
107.5°	443.2	321.6	221.2	154.3	116.9	96.0	83.6	75.4	71.4	69.1	68.1
110°	412.6	305.5	218.1	158.6	124.8	104.6	91.9	84.5	80.1	78.1	77.1



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	389.8	296.1	218.1	164.1	132.2	112.9	100.5	93.2	88.7	87.1	86.2
115°	364.9	285.9	219.6	172.4	143.9	125.7	113.5	106.1	101.7	100.2	99.2
117.5°	350.1	280.9	222.7	181.8	155.9	138.7	126.8	118.5	114.1	112.4	111.0
120°	341.8	278.4	225.9	188.1	164.5	147.3	135.1	126.7	122.3	120.4	118.8
122.5°	334.8	276.6	228.7	195.2	172.8	155.6	143.4	134.1	129.8	128.2	127.1
125°	325.1	274.1	233.3	204.8	183.7	167.5	154.7	145.3	140.9	138.5	137.5
127.5°	316.3	272.9	238.5	213.6	194.2	178.6	165.8	155.9	150.3	147.1	145.7
130°	310.4	272.1	241.7	219.6	200.9	185.6	172.9	162.6	156.2	152.2	150.8
132.5°	305.7	272.1	245.2	224.6	207.2	191.9	179.2	168.5	161.3	156.6	154.7
135°	300.1	272.1	249.9	231.8	215.6	200.4	187.1	176.8	168.9	163.1	161.1
137.5°	295.1	272.7	254.4	237.1	221.6	207.8	194.1	184.0	176.2	170.7	169.2
140°	292.7	273.1	256.4	240.6	225.9	211.7	198.5	189.1	181.2	175.3	173.8
142.5°	290.8	273.5	257.5	242.6	228.7	215.2	202.8	193.8	186.0	180.5	179.3
145°	287.8	273.1	258.8	245.6	233.3	220.5	209.2	200.4	193.5	188.6	187.6
147.5°	284.7	271.8	259.3	247.4	236.3	225.1	215.1	207.4	201.0	196.8	196.2
150°	282.4	270.6	259.3	248.5	238.2	227.4	219.0	212.2	205.8	202.3	201.4
152.5°	279.7	269.1	258.9	249.3	240.1	230.1	222.6	216.1	210.5	207.4	206.9
155°	275.0	266.2	257.9	249.9	242.1	233.8	226.9	222.0	217.1	214.1	214.1
157.5°	270.7	263.2	256.6	250.5	243.8	236.6	231.4	227.1	222.9	220.5	220.6
160°	267.2	261.3	255.4	250.5	244.6	238.2	233.8	229.9	226.4	224.5	225.0
162.5°	264.1	258.9	254.3	250.1	245.4	239.8	236.2	233.0	230.0	228.0	228.5
165°	259.3	255.4	252.4	249.5	245.6	241.7	238.7	236.7	234.3	232.8	233.8
167.5°	254.7	251.9	249.7	248.3	245.6	242.3	240.5	239.1	237.7	236.9	237.3
170°	251.9	249.9	248.5	247.5	245.6	243.1	241.7	240.6	239.7	239.2	239.7
172.5°	249.2	247.6	246.9	246.8	245.2	243.1	242.5	241.9	240.8	240.4	241.3
175°	245.6	245.0	245.0	245.6	244.6	243.1	243.1	243.1	242.6	242.1	243.1
177.5°	244.0	243.6	243.6	244.4	244.0	243.2	243.2	243.6	243.2	243.2	244.0
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1422.6	1426.8	1432.8	1439.8	1445.4	1451.4	1454.7	1454.7	1457.5	1463.5	1471.4
5°	1426.7	1441.7	1456.3	1474.9	1489.4	1506.2	1519.1	1531.3	1542.3	1556.3	1570.8
7.5°	1425.5	1450.6	1476.8	1506.1	1538.3	1564.0	1590.4	1611.1	1631.6	1658.3	1679.3
10°	1420.8	1453.4	1488.8	1526.0	1566.7	1602.1	1634.1	1663.2	1691.1	1720.1	1746.3
12.5°	1412.5	1453.9	1497.2	1541.9	1593.2	1633.7	1675.1	1706.0	1738.5	1770.3	1802.5
15°	1399.9	1448.7	1501.1	1563.2	1626.0	1671.3	1712.0	1752.1	1782.3	1818.3	1849.2
17.5°	1374.0	1436.9	1502.7	1570.6	1631.0	1683.6	1726.3	1764.4	1796.6	1836.3	1878.1
20°	1358.7	1426.7	1495.2	1567.9	1625.4	1679.5	1720.7	1760.2	1800.4	1852.0	1903.2
22.5°	1337.3	1409.9	1482.6	1551.6	1612.4	1664.6	1707.2	1755.6	1808.2	1866.9	1928.7
25°	1303.5	1378.5	1450.5	1516.1	1575.5	1628.9	1687.0	1752.1	1816.0	1893.3	1982.2
27.5°	1260.6	1332.8	1397.1	1466.5	1525.4	1593.5	1665.9	1736.6	1828.7	1935.0	2046.0
30°	1228.5	1297.1	1358.1	1423.7	1490.6	1565.6	1646.9	1730.0	1839.9	1964.8	2096.7
32.5°	1191.3	1253.4	1313.9	1377.3	1454.3	1536.7	1623.2	1724.9	1856.1	1998.3	2134.8
35°	1126.8	1182.6	1241.3	1311.6	1393.5	1483.1	1593.5	1717.3	1875.9	2028.7	2151.3
37.5°	1059.1	1103.2	1162.1	1236.3	1325.5	1429.1	1554.4	1704.8	1867.8	2004.8	2057.1
40°	1007.1	1048.4	1110.5	1188.4	1276.7	1390.1	1530.7	1685.2	1849.2	1944.5	1940.3
42.5°	955.5	997.2	1057.0	1135.4	1227.4	1354.3	1499.1	1659.7	1798.0	1834.3	1758.6
45°	876.3	915.2	974.0	1053.0	1151.8	1284.9	1437.1	1591.1	1679.5	1620.7	1470.8
47.5°	795.7	833.4	887.9	965.4	1073.2	1212.5	1356.4	1482.8	1495.2	1369.2	1189.3
50°	742.7	778.1	829.8	912.4	1016.9	1153.0	1291.8	1391.2	1360.4	1206.4	1021.1
52.5°	691.0	725.1	773.6	851.4	958.4	1091.6	1215.6	1293.6	1222.4	1058.6	891.8
55°	614.8	647.4	696.2	767.7	864.7	986.8	1095.5	1123.9	1019.3	854.3	719.5
57.5°	542.4	566.3	614.5	677.7	771.3	878.9	956.7	951.7	836.2	687.6	590.9
60°	494.6	516.0	562.0	620.1	708.9	805.5	860.1	836.8	720.1	597.4	504.4
62.5°	449.9	470.0	508.5	562.0	638.3	722.2	762.0	729.9	619.6	511.9	437.9
65°	382.4	396.9	427.7	477.1	536.9	595.0	630.5	583.4	485.9	404.5	348.7
67.5°	319.3	331.8	359.2	394.7	435.9	476.0	490.5	446.3	370.4	315.6	276.3
70°	278.4	290.0	308.6	341.7	369.0	397.5	404.5	365.0	301.6	259.8	235.4
72.5°	239.3	250.0	266.3	289.6	308.6	324.9	328.2	291.5	243.1	214.2	195.4
75°	182.4	191.7	202.2	210.9	223.2	226.1	224.9	196.4	170.3	151.1	140.6
77.5°	134.1	137.9	144.4	147.8	148.4	148.2	142.2	124.2	110.7	102.9	98.6
80°	103.4	106.3	108.1	109.3	109.9	104.0	97.6	86.6	82.0	77.3	72.1
82.5°	75.1	77.1	78.8	79.0	75.9	71.0	65.1	59.6	56.4	54.1	52.1
85°	40.6	41.2	40.6	37.8	33.7	31.9	30.8	29.6	29.0	28.5	28.5
87.5°	14.6	13.4	11.3	12.0	12.1	11.8	12.0	11.6	11.4	11.5	11.5
90°	0.9	2.0	2.9	4.0	4.9	5.4	6.4	6.9	7.8	8.4	8.9
92.5°	7.2	11.4	17.5	25.9	40.3	67.1	112.1	160.9	158.3	128.2	87.0
95°	16.7	20.7	26.0	36.9	59.0	111.5	219.6	355.1	435.1	425.9	353.1
97.5°	27.5	30.2	35.6	45.4	61.3	96.1	175.2	317.1	464.7	538.8	525.9
100°	35.4	37.4	42.7	52.1	66.8	95.3	159.1	282.9	443.5	566.3	604.1
102.5°	43.2	44.8	50.6	59.2	73.4	98.8	152.5	256.9	406.1	549.7	630.4
105°	55.5	57.9	62.9	70.7	84.5	106.1	149.8	231.8	356.1	497.1	614.9
107.5°	69.1	71.4	75.4	83.6	96.0	116.9	154.3	221.2	321.6	443.2	559.5
110°	78.1	80.1	84.5	91.9	104.6	124.8	158.6	218.1	305.5	412.6	518.7



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	87.1	88.7	93.2	100.5	112.9	132.2	164.1	218.1	296.1	389.8	486.5
115°	100.2	101.7	106.1	113.5	125.7	143.9	172.4	219.6	285.9	364.9	445.9
117.5°	112.4	114.1	118.5	126.8	138.7	155.9	181.8	222.7	280.9	350.1	419.8
120°	120.4	122.3	126.7	135.1	147.3	164.5	188.1	225.9	278.4	341.8	405.7
122.5°	128.2	129.8	134.1	143.4	155.6	172.8	195.2	228.7	276.6	334.8	395.1
125°	138.5	140.9	145.3	154.7	167.5	183.7	204.8	233.3	274.1	325.1	379.6
127.5°	147.1	150.3	155.9	165.8	178.6	194.2	213.6	238.5	272.9	316.3	363.9
130°	152.2	156.2	162.6	172.9	185.6	200.9	219.6	241.7	272.1	310.4	354.1
132.5°	156.6	161.3	168.5	179.2	191.9	207.2	224.6	245.2	272.1	305.7	344.3
135°	163.1	168.9	176.8	187.1	200.4	215.6	231.8	249.9	272.1	300.1	331.5
137.5°	170.7	176.2	184.0	194.1	207.8	221.6	237.1	254.4	272.7	295.1	320.7
140°	175.3	181.2	189.1	198.5	211.7	225.9	240.6	256.4	273.1	292.7	314.8
142.5°	180.5	186.0	193.8	202.8	215.2	228.7	242.6	257.5	273.5	290.8	309.7
145°	188.6	193.5	200.4	209.2	220.5	233.3	245.6	258.8	273.1	287.8	303.1
147.5°	196.8	201.0	207.4	215.1	225.1	236.3	247.4	259.3	271.8	284.7	296.8
150°	202.3	205.8	212.2	219.0	227.4	238.2	248.5	259.3	270.6	282.4	293.2
152.5°	207.4	210.5	216.1	222.6	230.1	240.1	249.3	258.9	269.1	279.7	289.3
155°	214.1	217.1	222.0	226.9	233.8	242.1	249.9	257.9	266.2	275.0	283.4
157.5°	220.5	222.9	227.1	231.4	236.6	243.8	250.5	256.6	263.2	270.7	277.5
160°	224.5	226.4	229.9	233.8	238.2	244.6	250.5	255.4	261.3	267.2	273.5
162.5°	228.0	230.0	233.0	236.2	239.8	245.4	250.1	254.3	258.9	264.1	269.2
165°	232.8	234.3	236.7	238.7	241.7	245.6	249.5	252.4	255.4	259.3	263.2
167.5°	236.9	237.7	239.1	240.5	242.3	245.6	248.3	249.7	251.9	254.7	257.5
170°	239.2	239.7	240.6	241.7	243.1	245.6	247.5	248.5	249.9	251.9	254.4
172.5°	240.4	240.8	241.9	242.5	243.1	245.2	246.8	246.9	247.6	249.2	250.9
175°	242.1	242.6	243.1	243.1	243.1	244.6	245.6	245.0	245.0	245.6	247.0
177.5°	243.2	243.2	243.6	243.2	243.2	244.0	244.4	243.6	243.6	244.0	244.4
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1477.5	1477.5	1485.4	1484.9	1490.0	1488.2	1489.1
5°	1588.2	1598.1	1606.8	1612.7	1621.3	1623.7	1622.5
7.5°	1703.1	1725.0	1735.7	1750.3	1753.0	1760.7	1759.9
10°	1774.2	1795.7	1812.0	1824.7	1831.1	1839.3	1839.9
12.5°	1830.0	1848.2	1862.6	1874.5	1882.2	1884.8	1886.4
15°	1873.5	1893.9	1910.7	1927.6	1937.5	1945.0	1949.1
17.5°	1917.4	1948.9	1978.6	2001.5	2015.3	2026.9	2026.7
20°	1951.5	1987.4	2024.6	2050.8	2077.5	2089.1	2090.9
22.5°	1987.7	2042.8	2090.7	2131.2	2166.3	2178.4	2183.0
25°	2063.0	2135.0	2208.9	2265.8	2306.4	2330.3	2333.8
27.5°	2154.0	2251.5	2329.2	2381.7	2415.5	2433.2	2437.0
30°	2218.2	2308.3	2378.0	2417.5	2433.2	2435.5	2426.8
32.5°	2247.0	2314.3	2342.2	2339.9	2309.0	2288.6	2280.8
35°	2211.7	2197.8	2129.9	2048.5	1986.3	1946.8	1936.3
37.5°	2012.8	1892.5	1767.5	1644.5	1579.1	1545.8	1488.6
40°	1816.6	1645.2	1515.0	1411.5	1337.7	1278.5	1264.6
42.5°	1595.3	1418.3	1288.1	1199.5	1140.7	1099.9	1082.3
45°	1281.9	1129.7	1022.2	954.2	908.9	879.3	865.9
47.5°	1025.4	907.5	829.1	778.9	744.3	718.5	711.3
50°	884.5	790.3	724.1	681.7	655.5	635.8	627.6
52.5°	768.3	692.2	641.4	606.3	581.6	569.3	562.5
55°	634.0	568.3	531.8	503.9	489.9	480.0	475.4
57.5°	518.5	471.1	444.4	425.1	412.2	405.9	403.6
60°	453.8	416.6	392.3	377.1	368.4	360.3	358.0
62.5°	396.7	367.4	348.5	335.3	326.6	323.1	321.7
65°	319.6	300.4	286.5	278.4	271.4	270.2	269.7
67.5°	254.1	242.8	235.5	227.0	224.5	220.5	219.6
70°	217.3	209.8	201.0	198.2	195.3	191.2	191.7
72.5°	184.3	176.8	170.8	167.0	166.0	164.2	165.7
75°	134.8	132.5	130.2	127.3	126.1	126.1	125.5
77.5°	96.3	94.3	91.7	90.0	89.6	87.1	88.1
80°	69.7	66.8	65.7	66.2	64.5	63.9	63.9
82.5°	51.6	50.5	49.4	49.5	49.2	48.6	49.1
85°	28.5	27.9	27.9	27.3	27.3	26.7	26.7
87.5°	12.1	12.7	11.9	11.5	11.5	12.1	12.5
90°	9.3	9.8	10.8	10.8	10.8	11.3	11.3
92.5°	63.2	47.5	40.3	34.0	32.8	32.1	31.3
95°	278.4	218.1	176.8	142.0	127.2	123.3	115.5
97.5°	473.6	414.7	357.3	327.0	299.5	285.2	279.0
100°	580.1	529.4	478.4	444.4	409.1	391.0	383.1
102.5°	645.2	621.0	586.4	550.2	525.0	505.3	499.4
105°	682.2	703.8	698.4	682.7	666.5	656.7	650.7
107.5°	649.3	704.8	730.4	738.4	738.3	735.0	731.1
110°	612.0	681.2	723.0	745.0	754.4	757.9	757.9



TEST NUMBER: P333588-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	575.1	645.1	694.3	726.6	742.6	751.1	754.7
115°	522.1	589.4	642.9	681.2	704.8	718.5	725.0
117.5°	485.4	543.4	592.5	630.9	655.2	668.8	672.8
120°	464.6	518.7	561.9	598.2	621.8	635.1	638.9
122.5°	449.7	497.8	538.3	570.7	592.3	605.5	609.1
125°	429.7	472.5	507.8	535.4	555.5	566.3	571.2
127.5°	410.7	450.6	483.7	508.6	526.4	536.6	538.8
130°	397.4	435.7	467.5	492.1	508.3	518.1	521.1
132.5°	384.8	419.6	450.3	474.8	491.0	500.1	503.4
135°	365.4	396.8	424.8	446.4	462.6	471.5	474.4
137.5°	348.1	374.3	398.0	417.3	432.1	440.2	443.5
140°	337.9	360.5	381.2	399.3	412.1	419.4	421.9
142.5°	329.2	348.7	366.6	382.0	392.8	399.8	401.8
145°	318.2	333.5	346.7	358.5	366.9	372.3	374.3
147.5°	309.1	320.8	330.8	340.2	346.8	350.0	350.9
150°	304.0	313.3	322.2	329.6	335.4	337.4	337.9
152.5°	298.9	307.5	314.4	320.6	325.2	327.2	327.7
155°	291.3	298.1	303.5	308.4	311.9	313.3	313.8
157.5°	284.0	289.3	293.5	297.3	300.1	301.5	301.4
160°	278.4	283.4	286.8	290.2	292.7	293.7	293.2
162.5°	273.8	277.8	280.9	283.6	285.7	285.9	285.8
165°	266.7	269.7	272.1	274.1	275.0	275.0	275.0
167.5°	259.8	262.1	263.8	264.8	265.7	265.3	265.2
170°	255.9	257.4	258.3	259.3	259.8	259.8	259.3
172.5°	252.4	253.4	254.0	254.3	255.1	254.3	253.8
175°	247.0	248.1	248.1	248.1	248.5	247.5	247.0
177.5°	244.8	244.8	244.8	244.4	244.8	243.6	243.6
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6

(END OF REPORT)