

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333590-935

Luminaire Tested: **S125RDIP-S1090D590U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333590-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D590U935-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5398.2 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333590-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333590-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	62	57
2	93	86	79	74	88	81	76	71	72	68	64	64	61	58	57	54	52	49
3	85	76	68	62	80	72	65	60	64	59	54	57	53	50	51	47	45	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9939	9939	9939
5°	9962	9848	9909
10°	9886	9757	9757
15°	9768	9559	9482
20°	9619	9283	9171
25°	9443	9012	8813
30°	9223	8694	8416
35°	8999	8367	7972
40°	8790	8025	7535
45°	8535	7644	7059
50°	8280	7229	6563
55°	7983	6831	6033
60°	7687	6350	5465
65°	7335	5790	4814
70°	6936	5093	4147
75°	6381	4292	3451
80°	5620	3373	2894
85°	4735	2757	2586



TEST NUMBER: P333590-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.7	2.7
10°-20°	404.4	7.5
20°-30°	586.4	10.9
30°-40°	668.3	12.4
40°-50°	651.5	12.1
50°-60°	548.4	10.2
60°-70°	384.4	7.1
70°-80°	197.6	3.7
80°-90°	51.3	1.0
90°-100°	42.3	0.8
100°-110°	124.8	2.3
110°-120°	211.4	3.9
120°-130°	278.3	5.2
130°-140°	311.8	5.8
140°-150°	305.6	5.7
150°-160°	256.7	4.8
160°-170°	170.6	3.2
170°-180°	59.7	1.1
0°-30°	1135.5	21.0
0°-40°	1803.9	33.4
0°-60°	3003.7	55.6
0°-90°	3637.0	67.4
90°-120°	378.5	7.0
90°-150°	1274.2	23.6
90°-180°	1761.0	32.6
0°-180°	5398.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1537	1532	1519	1530	1528	146
15°	1461	1453	1430	1428	1418	412
25°	1325	1306	1265	1250	1237	609
35°	1141	1112	1061	1028	1011	714
45°	934	899	837	792	773	721
55°	709	670	607	556	536	634
65°	480	439	379	334	315	475
75°	256	220	172	147	138	271
85°	64	44	37	36	35	72
90°	0	4	8	10	12	5
95°	32	33	38	41	42	34
105°	112	114	117	120	122	120
115°	212	214	215	214	214	209
125°	309	312	312	311	311	277
135°	402	405	405	405	403	310
145°	487	489	490	490	489	304
155°	557	557	558	559	557	256
165°	606	605	605	607	604	171
175°	630	628	628	630	627	60
180°	631	631	631	631	631	



TEST NUMBER: P333590-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0
2.5°	1541.7	1541.1	1540.5	1539.8	1539.2	1537.9	1535.9	1533.8	1531.7	1529.7	1531.7
5°	1536.6	1535.6	1534.6	1533.5	1532.5	1530.5	1527.7	1524.8	1522.0	1519.1	1521.7
7.5°	1521.5	1520.5	1519.5	1518.5	1517.5	1515.4	1511.9	1508.6	1505.1	1501.8	1503.6
10°	1507.5	1506.8	1506.0	1505.2	1504.4	1502.3	1498.7	1495.0	1491.4	1487.8	1488.6
12.5°	1491.7	1490.7	1489.8	1488.8	1487.8	1484.9	1480.1	1475.2	1470.3	1465.4	1466.0
15°	1461.0	1459.5	1457.9	1456.4	1454.8	1451.4	1446.0	1440.5	1435.1	1429.7	1429.4
17.5°	1426.4	1424.0	1421.7	1419.3	1416.9	1412.3	1405.5	1398.7	1391.8	1385.0	1383.7
20°	1399.5	1396.9	1394.3	1391.7	1389.1	1383.7	1375.4	1367.2	1358.9	1350.7	1349.4
22.5°	1369.7	1367.1	1364.5	1361.9	1359.3	1353.8	1345.1	1336.4	1327.7	1319.0	1316.5
25°	1325.1	1321.2	1317.3	1313.5	1309.6	1302.9	1293.3	1283.8	1274.2	1264.6	1261.3
27.5°	1273.9	1269.2	1264.5	1259.8	1255.1	1247.7	1237.4	1227.2	1216.9	1206.7	1202.0
30°	1236.7	1231.8	1226.9	1222.0	1217.1	1209.2	1198.3	1187.5	1176.6	1165.8	1159.9
32.5°	1200.4	1194.7	1189.0	1183.3	1177.5	1169.2	1158.0	1147.0	1135.9	1124.9	1118.4
35°	1141.4	1135.2	1129.0	1122.8	1116.6	1107.7	1096.1	1084.4	1072.8	1061.2	1053.7
37.5°	1083.5	1076.0	1068.4	1060.9	1053.3	1043.6	1031.6	1019.6	1007.6	995.7	986.6
40°	1042.6	1034.8	1027.1	1019.3	1011.6	1001.5	989.1	976.7	964.3	951.9	942.1
42.5°	999.8	991.9	984.0	975.9	968.0	957.6	944.8	932.0	919.2	906.4	897.0
45°	934.5	927.0	919.5	912.1	904.6	893.7	879.5	865.3	851.1	836.9	826.6
47.5°	866.9	858.9	851.0	843.2	835.3	824.1	809.9	795.5	781.2	766.9	756.2
50°	824.1	815.5	807.0	798.5	790.0	778.3	763.6	748.9	734.2	719.5	708.6
52.5°	777.6	768.9	760.1	751.4	742.7	731.3	717.5	703.5	689.7	675.8	664.1
55°	709.0	700.8	692.5	684.2	676.0	664.6	650.1	635.7	621.2	606.7	595.1
57.5°	639.7	630.9	622.1	613.2	604.4	593.1	579.1	565.2	551.2	537.3	525.9
60°	595.1	586.1	577.0	568.0	559.0	547.4	533.5	519.5	505.6	491.6	480.3
62.5°	547.7	539.1	530.5	521.8	513.2	501.8	487.7	473.5	459.3	445.1	434.6
65°	480.0	471.2	462.4	453.7	444.9	433.7	420.0	406.3	392.6	378.9	368.6
67.5°	412.8	404.1	395.3	386.5	377.7	366.8	353.6	340.5	327.4	314.3	304.9
70°	367.3	358.5	349.7	341.0	332.2	321.3	308.4	295.5	282.6	269.7	261.7
72.5°	322.7	314.1	305.5	297.0	288.3	278.0	266.0	253.8	241.8	229.7	222.3
75°	255.7	248.0	240.2	232.5	224.7	215.4	204.6	193.7	182.9	172.0	166.3
77.5°	189.2	183.0	176.8	170.7	164.5	157.0	148.4	139.7	131.0	122.3	118.3
80°	151.1	144.9	138.7	132.5	126.3	119.6	112.4	105.1	97.9	90.7	88.3
82.5°	113.9	108.3	102.7	97.2	91.6	86.4	81.4	76.4	71.5	66.5	65.4
85°	63.9	59.2	54.6	49.9	45.3	42.4	41.1	39.8	38.5	37.2	36.9
87.5°	21.5	20.2	18.9	17.7	16.4	15.8	15.7	15.7	15.6	15.5	15.7
90°	0.5	1.4	2.2	3.1	4.0	4.8	5.6	6.4	7.1	7.8	8.4
92.5°	11.9	12.5	13.1	13.7	14.3	15.1	16.0	17.0	17.9	18.9	19.5
95°	31.9	32.1	32.4	32.5	32.8	33.5	34.5	35.6	36.8	37.8	38.6
97.5°	53.0	53.1	53.2	53.3	53.4	54.2	55.7	57.2	58.7	60.2	61.0
100°	68.8	68.8	68.8	68.8	68.8	69.5	70.9	72.3	73.7	75.2	76.1
102.5°	85.7	86.1	86.5	87.0	87.4	88.0	88.7	89.5	90.1	90.8	92.0
105°	112.0	112.5	113.0	113.7	114.2	114.8	115.5	116.1	116.8	117.4	118.0
107.5°	141.0	141.6	142.2	142.7	143.3	143.8	144.3	144.7	145.3	145.8	146.1
110°	161.1	161.6	162.2	162.7	163.3	163.8	164.0	164.4	164.7	165.1	165.4



TEST NUMBER: P333590-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	181.5	181.8	182.1	182.4	182.7	183.0	183.5	183.8	184.3	184.7	184.9
115°	211.7	212.2	212.6	213.0	213.4	213.8	214.0	214.2	214.4	214.6	214.6
117.5°	241.9	242.1	242.4	242.5	242.7	243.0	243.1	243.3	243.5	243.7	243.8
120°	260.8	261.4	261.9	262.4	263.0	263.3	263.5	263.6	263.6	263.7	263.7
122.5°	281.3	281.5	281.6	281.8	282.1	282.2	282.6	282.8	283.1	283.4	283.4
125°	308.9	309.6	310.2	310.9	311.6	311.9	312.0	312.2	312.3	312.4	312.2
127.5°	338.5	338.8	339.1	339.5	339.9	340.2	340.3	340.4	340.5	340.7	340.6
130°	356.1	356.6	357.2	357.7	358.3	358.7	358.9	359.1	359.3	359.6	359.5
132.5°	373.8	374.7	375.6	376.4	377.4	377.8	377.7	377.7	377.6	377.6	377.5
135°	401.7	402.4	403.1	403.7	404.4	404.8	404.9	405.0	405.1	405.2	405.2
137.5°	428.1	428.8	429.4	430.0	430.7	431.1	431.4	431.5	431.8	432.0	432.1
140°	445.0	445.6	446.1	446.6	447.2	447.6	448.0	448.3	448.6	448.9	449.2
142.5°	461.9	462.4	462.8	463.3	463.7	464.2	464.6	465.0	465.5	465.8	466.0
145°	486.7	487.2	487.7	488.1	488.5	488.9	489.2	489.6	489.9	490.2	490.2
147.5°	509.7	510.0	510.2	510.5	510.7	510.9	511.2	511.5	511.8	512.0	512.3
150°	525.0	525.0	524.9	524.8	524.6	524.8	525.2	525.6	526.1	526.5	526.5
152.5°	537.6	537.8	538.0	538.1	538.2	538.4	538.6	538.7	538.9	539.2	539.4
155°	557.0	557.0	557.0	557.0	557.0	557.1	557.2	557.2	557.4	557.5	557.9
157.5°	574.3	574.0	573.8	573.6	573.3	573.3	573.3	573.5	573.6	573.7	574.1
160°	584.5	584.2	583.8	583.5	583.2	583.1	583.2	583.3	583.4	583.5	583.9
162.5°	593.6	593.3	593.1	592.8	592.5	592.5	592.5	592.5	592.5	592.5	593.1
165°	605.6	605.4	605.2	604.9	604.8	604.7	604.8	604.9	605.0	605.1	605.5
167.5°	615.9	615.4	614.9	614.5	614.1	613.9	613.9	613.9	613.9	613.9	614.5
170°	621.3	620.9	620.4	620.0	619.6	619.4	619.4	619.4	619.4	619.4	620.0
172.5°	625.3	624.8	624.4	624.0	623.5	623.3	623.3	623.3	623.3	623.3	624.0
175°	629.6	629.2	628.8	628.4	627.9	627.8	627.8	627.8	627.8	627.8	628.4
177.5°	632.0	631.6	631.3	630.9	630.5	630.3	630.3	630.2	630.1	630.0	630.5
180°	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2



TEST NUMBER: P333590-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0
2.5°	1533.8	1535.9	1537.9	1538.8	1538.6	1538.4	1538.2	1538.0
5°	1524.3	1526.9	1529.5	1530.5	1530.0	1529.5	1529.0	1528.4
7.5°	1505.4	1507.2	1509.0	1509.6	1509.0	1508.5	1507.9	1507.3
10°	1489.4	1490.1	1490.9	1490.9	1490.1	1489.4	1488.6	1487.8
12.5°	1466.6	1467.1	1467.7	1467.4	1466.2	1465.1	1463.9	1462.7
15°	1429.2	1428.9	1428.7	1427.4	1425.0	1422.7	1420.4	1418.1
17.5°	1382.4	1381.1	1379.8	1378.3	1376.3	1374.4	1372.5	1370.6
20°	1348.1	1346.8	1345.5	1343.7	1341.4	1339.0	1336.7	1334.4
22.5°	1314.0	1311.4	1308.9	1306.7	1304.8	1302.9	1300.9	1299.0
25°	1257.9	1254.6	1251.2	1248.1	1245.3	1242.4	1239.6	1236.7
27.5°	1197.3	1192.7	1187.9	1184.2	1181.5	1178.7	1176.0	1173.3
30°	1153.9	1148.0	1142.0	1137.9	1135.6	1133.2	1130.9	1128.6
32.5°	1111.8	1105.2	1098.6	1093.9	1091.0	1088.0	1085.0	1082.1
35°	1046.2	1038.7	1031.2	1025.7	1022.1	1018.5	1014.9	1011.2
37.5°	977.7	968.7	959.7	953.5	949.9	946.4	942.9	939.4
40°	932.3	922.5	912.7	906.2	903.1	900.0	896.9	893.8
42.5°	887.6	878.1	868.7	861.8	857.2	852.7	848.2	843.6
45°	816.2	805.9	795.6	788.4	784.5	780.7	776.8	772.9
47.5°	745.6	734.9	724.4	716.9	712.6	708.3	704.0	699.7
50°	697.8	686.9	676.1	668.7	664.9	661.0	657.1	653.2
52.5°	652.5	640.8	629.0	621.3	617.4	613.5	609.7	605.8
55°	583.5	571.9	560.3	552.3	548.2	544.1	539.9	535.8
57.5°	514.5	503.2	491.8	484.2	480.6	476.9	473.2	469.6
60°	468.9	457.5	446.2	438.6	434.7	430.8	427.0	423.1
62.5°	424.1	413.5	403.0	395.8	391.9	388.1	384.2	380.3
65°	358.3	347.9	337.6	330.5	326.6	322.7	318.8	315.0
67.5°	295.4	285.9	276.5	270.2	267.1	264.0	260.9	257.8
70°	253.7	245.6	237.6	232.0	228.9	225.8	222.7	219.6
72.5°	214.9	207.5	200.1	195.4	193.3	191.2	189.2	187.1
75°	160.7	155.0	149.3	145.5	143.7	141.9	140.1	138.3
77.5°	114.3	110.4	106.3	103.7	102.4	101.0	99.7	98.3
80°	86.0	83.7	81.4	79.9	79.4	78.9	78.4	77.8
82.5°	64.3	63.2	62.2	61.5	61.1	60.8	60.5	60.2
85°	36.7	36.4	36.2	35.9	35.6	35.4	35.1	34.9
87.5°	15.8	15.8	15.9	15.9	15.8	15.7	15.5	15.4
90°	9.0	9.5	10.1	10.5	10.8	11.1	11.5	11.8
92.5°	20.3	21.0	21.8	22.2	22.5	22.7	22.9	23.2
95°	39.3	40.1	40.9	41.3	41.6	41.8	42.0	42.3
97.5°	61.6	62.4	63.1	63.5	63.6	63.8	63.9	64.1
100°	77.1	78.1	79.0	79.6	79.9	80.2	80.3	80.6
102.5°	93.0	94.1	95.1	95.8	96.2	96.4	96.8	97.0
105°	118.7	119.3	120.0	120.5	120.8	121.1	121.5	121.8
107.5°	146.5	146.8	147.1	147.2	147.2	147.2	147.1	147.1
110°	165.7	166.0	166.3	166.4	166.3	166.3	166.1	166.0



TEST NUMBER: P333590-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	185.0	185.1	185.3	185.3	185.1	184.9	184.7	184.5
115°	214.4	214.3	214.2	214.1	214.0	213.9	213.8	213.7
117.5°	243.9	244.0	244.1	243.9	243.5	243.1	242.6	242.1
120°	263.7	263.7	263.7	263.6	263.1	262.7	262.3	261.8
122.5°	283.3	283.2	283.1	282.8	282.5	282.1	281.8	281.5
125°	311.9	311.8	311.5	311.3	311.3	311.2	311.0	310.9
127.5°	340.4	340.4	340.3	340.1	339.8	339.7	339.4	339.2
130°	359.3	359.2	359.1	359.0	358.7	358.5	358.3	358.1
132.5°	377.4	377.3	377.2	376.9	376.7	376.3	376.1	375.7
135°	405.2	405.2	405.2	405.0	404.6	404.2	403.7	403.3
137.5°	432.3	432.4	432.6	432.4	431.8	431.3	430.8	430.2
140°	449.4	449.6	449.8	449.6	449.1	448.6	448.0	447.5
142.5°	466.1	466.2	466.3	466.1	465.6	465.0	464.5	464.0
145°	490.2	490.2	490.2	490.0	489.7	489.4	489.0	488.7
147.5°	512.6	512.8	513.1	512.8	512.0	511.3	510.6	509.9
150°	526.5	526.5	526.5	526.4	526.2	526.0	525.8	525.6
152.5°	539.7	539.9	540.2	540.1	539.7	539.3	538.9	538.6
155°	558.4	558.8	559.2	559.2	558.6	558.1	557.5	557.0
157.5°	574.5	575.0	575.4	575.3	574.5	573.9	573.2	572.4
160°	584.4	584.8	585.2	585.2	584.7	584.1	583.6	583.1
162.5°	593.6	594.1	594.7	594.6	594.0	593.3	592.7	592.0
165°	606.0	606.4	606.9	606.7	606.1	605.5	604.8	604.2
167.5°	615.2	615.9	616.5	616.5	615.8	615.1	614.4	613.8
170°	620.7	621.3	622.0	621.9	621.2	620.4	619.7	618.9
172.5°	624.7	625.3	625.9	625.9	625.3	624.6	623.9	623.2
175°	629.0	629.6	630.3	630.3	629.6	628.8	628.0	627.2
177.5°	631.0	631.5	632.1	632.1	631.5	630.9	630.2	629.6
180°	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2

(END OF REPORT)