

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333630-935

Luminaire Tested: **S125RDIP-S1270D1035U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333630-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7435.3 lumens  
Efficiency: N/A  
Efficacy: 111.3 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	84	74	67	61	78	70	63	58	61	56	52	52	49	46	45	42	40	36
4	77	66	58	52	71	62	55	50	54	49	44	47	43	39	40	37	34	31
5	70	59	51	45	65	55	48	43	49	43	39	42	38	34	36	33	30	27
6	65	53	45	39	60	50	43	37	44	38	34	38	34	30	33	29	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	44	36	31	52	41	34	29	36	31	27	32	27	24	28	24	21	19
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10559	10559	10559	10559
5°	12149	10573	9337	10573
10°	13935	10519	8239	10519
15°	15051	10411	7324	10411
20°	16597	10287	6763	10287
25°	19207	10120	6274	10120
30°	20901	9945	5956	9945
35°	17631	9742	5662	9742
40°	12312	9377	5409	9377
45°	9134	8882	5161	8882
50°	7283	8368	4950	8368
55°	6182	7731	4761	7731
60°	5341	7161	4456	7161
65°	4759	6544	3836	6544
70°	4181	5995	3497	5995
75°	3618	5190	3284	5190
80°	2745	4366	2745	4366
85°	2290	3431	2586	3431



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.8	2.1
10°-20°	459.5	6.2
20°-30°	728.5	9.8
30°-40°	878.5	11.8
40°-50°	784.5	10.6
50°-60°	601.6	8.1
60°-70°	391.0	5.3
70°-80°	190.1	2.6
80°-90°	47.8	0.6
90°-100°	309.0	4.2
100°-110°	664.3	8.9
110°-120°	623.4	8.4
120°-130°	505.2	6.8
130°-140°	405.5	5.5
140°-150°	306.0	4.1
150°-160°	215.4	2.9
160°-170°	126.9	1.7
170°-180°	41.3	0.6
0°-30°	1344.7	18.1
0°-40°	2223.3	29.9
0°-60°	3609.4	48.5
0°-90°	4238.3	57.0
90°-120°	1596.7	21.5
90°-150°	2813.4	37.8
90°-180°	3197.0	43.0
0°-180°	7435.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1635	1635	1635	1635	1635	
5°	1874	1631	1440	1631	1874	187
15°	2251	1557	1095	1557	2251	645
25°	2695	1420	880	1420	2695	1238
35°	2236	1236	718	1236	2236	1351
45°	1000	972	565	972	1000	798
55°	549	687	423	687	549	498
65°	311	428	251	428	311	310
75°	145	208	132	208	145	154
85°	31	46	35	46	31	36
90°	20	1	20	1	20	15
95°	202	28	202	28	202	286
105°	1139	97	1139	97	1139	1132
115°	1269	174	1269	174	1269	1240
125°	1000	241	1000	241	1000	904
135°	830	282	830	282	830	643
145°	655	328	655	328	655	416
155°	549	375	549	375	549	256
165°	481	409	481	409	481	138
175°	432	425	432	425	432	42
180°	426	426	426	426	426	



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1719.8	1718.7	1720.9	1714.9	1715.5	1706.3	1706.3	1699.4	1690.2	1683.3	1680.1
5°	1873.9	1875.3	1872.5	1862.4	1855.8	1845.7	1834.3	1814.1	1797.3	1781.2	1768.5
7.5°	2032.6	2033.5	2024.6	2021.5	2004.6	1992.3	1966.9	1939.5	1915.2	1884.4	1860.7
10°	2124.9	2124.3	2114.8	2107.5	2092.7	2073.9	2049.1	2016.8	1986.7	1953.1	1920.9
12.5°	2178.6	2176.9	2173.9	2164.9	2151.2	2134.6	2113.5	2081.8	2044.6	2007.9	1970.2
15°	2251.1	2246.3	2237.7	2226.2	2206.7	2187.3	2163.8	2135.6	2100.1	2058.5	2023.5
17.5°	2340.7	2340.9	2327.5	2311.6	2285.2	2250.8	2214.6	2169.0	2120.7	2074.9	2037.8
20°	2414.8	2412.8	2399.4	2368.5	2338.3	2295.3	2253.8	2198.0	2139.0	2079.2	2032.9
22.5°	2521.2	2515.9	2502.0	2461.4	2414.6	2359.2	2295.6	2227.6	2156.2	2088.4	2027.6
25°	2695.4	2691.3	2663.8	2616.8	2551.1	2465.8	2382.6	2289.3	2186.7	2097.4	2023.5
27.5°	2814.6	2810.1	2789.7	2750.7	2690.0	2600.3	2487.7	2363.0	2234.8	2112.0	2005.5
30°	2802.7	2812.8	2810.1	2792.1	2746.4	2665.8	2561.8	2421.6	2269.2	2124.9	1998.0
32.5°	2634.1	2643.2	2666.8	2702.3	2705.0	2672.8	2595.1	2465.6	2307.8	2143.7	1992.1
35°	2236.3	2248.4	2294.0	2365.9	2459.8	2538.3	2554.4	2484.7	2343.0	2166.5	1983.3
37.5°	1719.2	1785.3	1823.7	1899.3	2041.3	2185.7	2324.6	2375.8	2315.5	2157.1	1968.9
40°	1460.4	1476.5	1545.0	1630.2	1749.7	1900.1	2098.1	2241.0	2245.7	2135.6	1946.4
42.5°	1250.0	1270.4	1317.3	1385.4	1487.7	1638.1	1842.5	2031.1	2118.5	2076.6	1916.8
45°	1000.1	1015.5	1049.7	1102.1	1180.6	1304.8	1480.6	1698.7	1871.9	1939.7	1837.6
47.5°	821.5	829.8	859.6	899.5	957.6	1048.1	1184.2	1373.6	1581.2	1726.9	1712.5
50°	724.9	734.3	757.1	787.3	836.3	912.7	1021.5	1179.2	1393.4	1571.2	1606.8
52.5°	649.7	657.5	671.7	700.3	740.7	799.5	887.3	1029.9	1222.6	1411.7	1494.0
55°	549.0	554.4	565.8	581.9	614.2	656.4	732.2	830.9	986.6	1177.2	1298.0
57.5°	466.1	468.7	476.0	490.9	513.2	544.1	598.8	682.4	794.1	965.8	1099.1
60°	413.5	416.1	425.5	435.6	453.1	481.2	524.2	582.6	689.9	831.6	966.5
62.5°	371.5	373.2	377.2	387.3	402.6	424.3	458.1	505.8	591.2	715.6	843.0
65°	311.4	312.1	313.4	321.5	330.9	347.0	369.1	402.7	467.1	561.1	673.8
67.5°	253.7	254.6	259.3	262.2	272.0	280.4	293.4	319.1	364.5	427.8	515.5
70°	221.4	220.8	225.5	228.9	232.2	242.3	251.0	271.8	300.0	348.4	421.5
72.5°	191.4	189.7	191.7	192.9	197.3	204.1	212.9	225.7	247.4	280.7	336.7
75°	145.0	145.7	145.7	147.0	150.3	153.0	155.7	162.4	174.5	196.7	226.9
77.5°	101.8	100.7	103.5	103.9	105.9	108.8	111.2	113.8	118.8	127.9	143.5
80°	73.8	73.8	74.5	76.5	75.9	77.1	80.5	83.3	89.3	94.6	100.0
82.5°	56.7	56.1	56.7	57.2	57.1	58.4	59.6	60.1	62.4	65.1	68.9
85°	30.9	30.9	31.5	31.5	32.2	32.2	32.9	32.9	32.9	33.6	34.3
87.5°	15.8	15.2	14.6	14.6	15.1	15.8	15.1	14.4	14.2	14.0	14.2
90°	19.8	19.8	18.9	18.9	18.9	17.2	16.4	15.5	14.6	13.8	12.1
92.5°	54.8	56.2	57.4	59.5	70.5	83.2	110.6	152.3	224.3	277.1	281.5
95°	202.0	215.8	222.7	248.4	309.4	381.6	487.3	618.0	745.2	761.6	621.5
97.5°	488.2	499.2	524.1	572.3	625.3	725.7	828.7	920.4	942.9	813.3	554.9
100°	670.5	684.2	716.0	777.8	837.2	926.5	1015.1	1057.2	991.0	776.1	495.1
102.5°	873.9	884.2	918.9	962.9	1026.2	1086.8	1129.2	1103.3	962.2	710.8	449.7
105°	1138.8	1149.2	1166.4	1194.7	1222.2	1231.7	1193.9	1076.1	869.9	623.1	405.7
107.5°	1279.4	1286.3	1292.0	1292.2	1278.2	1233.4	1136.3	979.1	775.6	562.8	387.1
110°	1326.2	1326.2	1320.2	1303.9	1265.2	1192.1	1070.9	907.7	721.9	534.6	381.6



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1320.7	1314.6	1299.6	1271.5	1215.0	1128.9	1006.3	851.3	682.1	518.1	381.6
115°	1268.7	1257.5	1233.4	1192.1	1125.1	1031.4	913.7	780.4	638.6	500.2	384.2
117.5°	1177.3	1170.4	1146.6	1104.0	1036.9	951.0	849.5	734.7	612.7	491.5	389.9
120°	1118.3	1111.4	1088.1	1046.9	983.3	907.7	813.1	710.0	598.2	487.3	395.4
122.5°	1066.0	1059.8	1036.6	998.8	942.0	871.2	787.0	691.4	585.8	483.9	400.2
125°	999.6	991.0	972.1	936.9	888.7	826.8	752.1	664.4	569.0	479.6	408.3
127.5°	942.9	939.1	921.2	890.1	846.4	788.5	718.8	636.9	553.5	477.5	417.4
130°	912.0	906.8	889.6	861.3	818.3	762.4	695.3	619.7	543.2	476.1	422.9
132.5°	881.0	875.1	859.4	831.0	788.0	734.2	673.3	602.5	534.9	476.1	429.0
135°	830.3	825.1	809.7	781.3	743.5	694.5	639.5	580.1	525.1	476.1	437.5
137.5°	776.1	770.5	756.2	730.4	696.5	655.0	609.2	561.3	516.4	477.2	445.2
140°	738.3	734.0	721.2	698.8	667.0	630.9	591.3	551.0	512.3	477.9	448.7
142.5°	703.3	699.6	687.4	668.6	641.5	610.3	576.2	542.0	508.9	478.5	450.7
145°	655.0	651.5	642.0	627.4	606.8	583.6	557.0	530.3	503.7	477.9	453.0
147.5°	614.1	612.5	607.0	595.3	578.9	561.5	541.0	519.4	498.3	475.6	453.8
150°	591.3	590.5	587.0	576.7	563.9	548.4	532.0	513.2	494.2	473.6	453.8
152.5°	573.4	572.6	569.2	560.9	550.1	538.0	523.1	506.3	489.4	470.9	453.1
155°	549.2	548.4	545.8	539.8	531.2	521.8	509.7	495.9	481.3	465.9	451.3
157.5°	527.5	527.7	525.3	520.4	513.7	506.3	497.0	485.6	473.7	460.7	449.0
160°	513.2	514.0	512.3	508.0	502.0	495.9	487.3	478.7	467.6	457.3	446.9
162.5°	500.1	500.2	499.9	496.3	491.6	486.3	479.1	471.2	462.1	453.1	444.9
165°	481.3	481.3	481.3	479.6	476.1	471.9	466.7	460.7	453.8	446.9	441.8
167.5°	464.2	464.3	465.0	463.5	461.8	458.7	454.7	450.7	445.7	440.9	437.0
170°	453.8	454.7	454.7	453.8	452.1	450.4	447.8	445.2	440.9	437.5	434.9
172.5°	444.2	445.1	446.4	444.9	444.5	443.5	441.6	439.0	436.1	433.3	432.1
175°	432.3	433.2	434.9	434.0	434.0	434.0	432.3	432.3	429.7	428.9	428.9
177.5°	426.3	426.3	428.3	427.7	428.3	428.3	428.3	427.7	427.0	426.3	426.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1680.1	1676.3	1669.3	1662.8	1654.8	1647.9	1643.0	1637.1	1629.6	1620.5	1612.9
5°	1754.4	1739.7	1720.2	1703.4	1682.0	1665.2	1647.7	1630.9	1614.1	1592.7	1573.9
7.5°	1836.9	1806.4	1776.7	1739.4	1705.6	1675.3	1646.3	1617.0	1588.2	1557.7	1528.4
10°	1887.3	1850.4	1809.5	1762.5	1719.5	1678.6	1641.0	1604.0	1565.1	1530.9	1494.0
12.5°	1934.6	1886.9	1840.0	1780.7	1729.1	1679.1	1631.3	1585.3	1543.7	1499.3	1459.7
15°	1977.2	1930.3	1877.9	1805.4	1733.6	1673.2	1616.8	1557.1	1505.4	1455.8	1411.4
17.5°	1993.7	1944.5	1883.7	1814.0	1735.5	1659.5	1586.9	1521.4	1460.6	1402.7	1352.9
20°	1987.3	1939.7	1877.2	1810.8	1726.9	1647.7	1569.2	1496.7	1428.9	1367.8	1314.8
22.5°	1971.8	1922.4	1862.2	1792.0	1712.4	1628.4	1544.5	1467.1	1396.1	1332.9	1275.1
25°	1948.4	1881.3	1819.6	1751.0	1675.2	1592.0	1505.4	1420.1	1344.4	1279.9	1216.9
27.5°	1924.1	1840.3	1761.8	1693.8	1613.6	1539.4	1455.9	1368.5	1288.7	1223.1	1158.4
30°	1902.0	1808.1	1721.5	1644.3	1568.5	1498.1	1418.8	1333.6	1251.7	1184.0	1118.2
32.5°	1874.7	1774.8	1679.6	1590.6	1517.5	1447.6	1375.9	1294.4	1214.7	1144.7	1077.9
35°	1840.3	1712.8	1609.5	1514.8	1433.6	1365.8	1301.4	1235.6	1155.7	1083.2	1018.1
37.5°	1795.2	1650.5	1530.9	1427.8	1342.2	1274.1	1223.2	1163.1	1090.2	1020.8	960.4
40°	1767.8	1605.4	1474.5	1372.5	1282.5	1210.7	1163.1	1112.2	1045.7	980.6	920.2
42.5°	1731.3	1564.1	1417.6	1311.3	1220.8	1151.7	1103.5	1058.9	1003.2	941.9	877.2
45°	1659.7	1483.9	1330.2	1216.2	1124.9	1057.0	1012.1	972.5	930.2	873.8	817.4
47.5°	1566.6	1400.3	1239.5	1114.9	1025.5	962.6	918.9	887.7	857.5	809.5	754.8
50°	1492.0	1331.6	1174.5	1053.7	958.4	898.7	857.7	832.9	805.4	761.7	716.1
52.5°	1403.9	1260.7	1106.9	983.3	893.5	837.5	798.1	773.4	750.6	715.1	671.6
55°	1265.2	1139.6	998.7	886.6	804.1	747.7	710.1	686.6	673.2	643.0	608.7
57.5°	1105.0	1015.0	890.8	782.7	709.7	654.0	626.5	606.5	591.3	570.0	545.8
60°	993.3	930.2	818.8	716.1	649.0	596.0	571.2	554.4	540.3	522.2	503.3
62.5°	880.0	834.1	737.2	649.0	587.3	542.9	519.6	504.5	488.2	476.0	457.7
65°	728.2	687.3	620.2	551.0	494.0	458.4	441.6	428.2	418.1	404.7	391.9
67.5°	566.5	549.8	503.5	455.8	414.9	383.2	368.8	359.4	347.2	339.2	330.5
70°	467.1	459.1	426.2	394.7	356.4	334.9	321.5	317.5	302.7	294.6	288.6
72.5°	379.1	375.3	356.4	334.5	307.5	288.7	276.4	271.8	262.4	256.0	252.1
75°	259.8	261.1	257.7	243.7	233.6	221.4	210.8	208.0	201.4	196.0	192.6
77.5°	164.3	171.2	171.4	170.7	166.7	159.4	154.9	152.9	146.3	144.3	143.5
80°	112.8	120.1	126.8	126.1	124.8	122.9	119.5	117.4	114.1	112.1	110.7
82.5°	75.2	82.1	87.6	91.3	91.0	89.0	86.7	85.8	85.1	83.6	83.3
85°	35.6	36.9	38.9	43.7	47.0	47.6	47.0	46.3	44.3	44.9	45.6
87.5°	14.6	14.2	14.6	14.3	13.3	15.8	17.0	17.4	16.4	15.8	15.0
90°	11.2	9.5	8.6	6.9	5.2	3.4	1.7	0.9	1.7	3.4	5.2
92.5°	196.1	117.4	70.5	45.4	30.6	20.0	12.7	10.5	12.7	20.0	30.6
95°	384.2	195.1	103.1	64.5	45.5	36.1	29.2	28.3	29.2	36.1	45.5
97.5°	306.7	168.2	107.3	79.4	62.4	53.0	48.1	47.1	48.1	53.0	62.4
100°	278.4	166.8	116.9	91.1	74.7	65.3	61.9	60.2	61.9	65.3	74.7
102.5°	266.8	173.0	128.5	103.5	88.5	78.4	75.6	74.6	75.6	78.4	88.5
105°	262.2	185.6	147.8	123.8	110.0	101.4	97.1	97.1	97.1	101.4	110.0
107.5°	270.1	204.6	168.0	146.3	132.0	124.9	120.9	119.2	120.9	124.9	132.0
110°	277.6	218.3	183.0	160.7	147.8	140.1	136.6	134.9	136.6	140.1	147.8





TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	287.2	231.4	197.5	175.8	163.0	155.2	152.5	150.8	152.5	155.2	163.0
115°	301.7	251.8	220.1	198.5	185.6	177.9	175.3	173.7	175.3	177.9	185.6
117.5°	318.2	272.9	242.7	222.0	207.3	199.6	196.8	194.2	196.8	199.6	207.3
120°	329.2	287.9	257.9	236.3	221.8	214.0	210.6	208.0	210.6	214.0	221.8
122.5°	341.6	302.4	272.3	250.8	234.8	227.0	224.3	222.5	224.3	227.0	234.8
125°	358.4	321.5	293.1	270.8	254.4	246.7	242.4	240.6	242.4	246.7	254.4
127.5°	373.8	339.8	312.5	290.2	272.9	263.0	257.5	254.9	257.5	263.0	272.9
130°	384.2	351.5	324.9	302.6	284.5	273.4	266.5	263.9	266.5	273.4	284.5
132.5°	393.1	362.6	335.9	313.6	294.8	282.2	274.0	270.8	274.0	282.2	294.8
135°	405.7	377.3	350.7	327.4	309.4	295.7	285.3	281.9	285.3	295.7	309.4
137.5°	415.0	387.8	363.6	339.7	322.0	308.2	298.6	296.0	298.6	308.2	322.0
140°	421.2	395.4	370.5	347.2	330.9	317.2	306.9	304.3	306.9	317.2	330.9
142.5°	424.6	400.2	376.6	354.8	339.1	325.4	315.8	313.9	315.8	325.4	339.1
145°	429.7	408.3	385.9	366.2	350.7	338.6	330.0	328.3	330.0	338.6	350.7
147.5°	432.8	413.5	393.8	376.4	363.1	351.9	344.5	343.5	344.5	351.9	363.1
150°	434.9	416.9	398.0	383.3	371.3	360.2	354.1	352.4	354.1	360.2	371.3
152.5°	436.3	420.3	402.8	389.5	378.2	368.4	363.1	362.1	363.1	368.4	378.2
155°	437.5	423.7	409.1	397.1	388.5	379.9	374.7	374.7	374.7	379.9	388.5
157.5°	438.3	426.6	414.1	405.0	397.4	390.0	385.9	386.1	385.9	390.0	397.4
160°	438.3	428.0	416.9	409.1	402.3	396.2	392.8	393.6	392.8	396.2	402.3
162.5°	437.6	429.4	419.7	413.3	407.8	402.4	399.0	399.8	399.0	402.4	407.8
165°	436.6	429.7	422.9	417.8	414.3	410.0	407.4	409.1	407.4	410.0	414.3
167.5°	434.5	429.7	424.0	420.9	418.4	416.0	414.5	415.3	414.5	416.0	418.4
170°	433.2	429.7	425.4	422.9	421.2	419.5	418.6	419.5	418.6	419.5	421.2
172.5°	431.8	429.0	425.4	424.2	423.2	421.5	420.7	422.2	420.7	421.5	423.2
175°	429.7	428.0	425.4	425.4	425.4	424.6	423.7	425.4	423.7	424.6	425.4
177.5°	427.7	427.0	425.6	425.6	426.3	425.6	425.6	427.0	425.6	425.6	426.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1607.6	1600.1	1594.7	1583.9	1576.4	1573.2	1567.3	1565.6	1571.6	1567.3	1566.8
5°	1559.8	1540.3	1524.9	1509.4	1492.6	1482.0	1465.9	1463.1	1459.1	1453.0	1451.7
7.5°	1502.4	1477.1	1457.2	1431.8	1409.5	1391.7	1371.6	1362.0	1356.8	1349.0	1338.6
10°	1463.8	1433.6	1406.8	1381.2	1353.8	1331.6	1311.5	1296.0	1285.9	1276.5	1272.6
12.5°	1425.6	1394.9	1360.6	1329.7	1299.0	1274.1	1251.8	1241.8	1230.6	1219.6	1210.2
15°	1366.5	1325.5	1288.0	1252.4	1226.2	1199.4	1177.8	1163.1	1146.3	1141.7	1123.5
17.5°	1303.6	1263.5	1219.5	1182.1	1151.7	1122.1	1098.5	1081.8	1069.2	1051.9	1043.5
20°	1264.5	1216.9	1173.9	1139.6	1106.0	1071.2	1047.0	1032.9	1020.8	1006.8	1000.1
22.5°	1222.6	1176.0	1132.0	1091.8	1057.7	1023.4	1006.2	991.6	977.8	964.8	956.0
25°	1161.1	1114.1	1067.8	1026.2	990.7	965.8	945.6	928.8	921.5	908.8	899.3
27.5°	1100.3	1050.3	1002.3	960.8	932.9	908.4	891.8	878.6	865.2	854.1	845.9
30°	1061.1	1010.1	957.8	924.9	895.4	871.8	853.7	840.9	830.9	820.8	814.8
32.5°	1021.9	969.3	922.8	887.3	859.4	839.0	820.4	808.2	797.6	786.4	779.4
35°	959.1	905.4	867.8	832.9	805.4	786.6	773.9	756.4	747.7	739.6	732.2
37.5°	900.7	850.8	810.1	779.5	755.6	736.9	720.4	711.0	700.3	693.0	686.9
40°	857.7	812.1	775.2	743.0	725.6	704.7	689.3	677.2	669.2	659.8	653.1
42.5°	819.1	776.7	740.8	711.9	690.1	672.5	657.6	645.5	635.3	628.6	622.9
45°	764.5	722.2	687.3	660.4	640.3	623.5	608.0	602.0	588.6	580.6	577.9
47.5°	707.9	670.1	636.4	611.7	591.0	575.1	560.7	548.4	541.0	533.0	528.7
50°	669.9	633.6	602.0	577.9	557.8	540.3	526.8	518.8	508.8	501.4	496.0
52.5°	631.7	598.1	566.6	543.5	526.1	508.6	493.6	485.5	476.0	471.3	467.5
55°	577.2	541.7	514.8	492.0	473.8	457.7	443.7	435.6	429.6	424.8	423.5
57.5°	515.5	487.2	462.3	441.8	422.9	407.8	395.5	387.8	382.5	381.8	377.7
60°	475.2	449.7	426.9	404.7	388.6	374.5	363.8	355.1	349.7	349.0	347.7
62.5°	434.9	410.4	389.3	369.8	355.3	341.7	331.6	321.8	318.6	315.2	312.2
65°	375.1	353.0	335.6	320.1	304.7	293.3	283.3	277.2	269.8	265.8	258.4
67.5°	316.5	299.4	282.6	269.6	257.4	246.6	238.2	229.3	224.3	221.1	215.7
70°	277.8	264.4	247.6	233.6	224.2	215.4	208.7	198.6	195.3	192.6	189.9
72.5°	241.3	229.5	215.4	204.1	194.7	186.4	178.7	173.9	170.7	167.9	166.3
75°	189.9	178.6	166.4	158.4	151.7	145.0	140.9	137.6	136.2	135.6	132.9
77.5°	139.5	133.5	123.7	117.4	112.9	110.2	106.6	104.9	104.7	101.8	100.8
80°	106.7	103.3	95.3	92.6	89.3	86.6	84.6	81.2	77.8	76.5	74.5
82.5°	79.3	75.9	72.8	68.4	65.6	64.1	62.0	60.8	61.2	59.3	58.4
85°	42.3	38.9	37.6	36.9	35.6	36.9	36.2	35.6	34.9	34.3	34.9
87.5°	14.8	15.2	14.8	16.2	14.7	15.7	15.8	15.4	15.6	15.8	15.6
90°	6.9	8.6	9.5	11.2	12.1	13.8	14.6	15.5	16.4	17.2	18.9
92.5°	45.4	70.5	117.4	196.1	281.5	277.1	224.3	152.3	110.6	83.2	70.5
95°	64.5	103.1	195.1	384.2	621.5	761.6	745.2	618.0	487.3	381.6	309.4
97.5°	79.4	107.3	168.2	306.7	554.9	813.3	942.9	920.4	828.7	725.7	625.3
100°	91.1	116.9	166.8	278.4	495.1	776.1	991.0	1057.2	1015.1	926.5	837.2
102.5°	103.5	128.5	173.0	266.8	449.7	710.8	962.2	1103.3	1129.2	1086.8	1026.2
105°	123.8	147.8	185.6	262.2	405.7	623.1	869.9	1076.1	1193.9	1231.7	1222.2
107.5°	146.3	168.0	204.6	270.1	387.1	562.8	775.6	979.1	1136.3	1233.4	1278.2
110°	160.7	183.0	218.3	277.6	381.6	534.6	721.9	907.7	1070.9	1192.1	1265.2



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	175.8	197.5	231.4	287.2	381.6	518.1	682.1	851.3	1006.3	1128.9	1215.0
115°	198.5	220.1	251.8	301.7	384.2	500.2	638.6	780.4	913.7	1031.4	1125.1
117.5°	222.0	242.7	272.9	318.2	389.9	491.5	612.7	734.7	849.5	951.0	1036.9
120°	236.3	257.9	287.9	329.2	395.4	487.3	598.2	710.0	813.1	907.7	983.3
122.5°	250.8	272.3	302.4	341.6	400.2	483.9	585.8	691.4	787.0	871.2	942.0
125°	270.8	293.1	321.5	358.4	408.3	479.6	569.0	664.4	752.1	826.8	888.7
127.5°	290.2	312.5	339.8	373.8	417.4	477.5	553.5	636.9	718.8	788.5	846.4
130°	302.6	324.9	351.5	384.2	422.9	476.1	543.2	619.7	695.3	762.4	818.3
132.5°	313.6	335.9	362.6	393.1	429.0	476.1	534.9	602.5	673.3	734.2	788.0
135°	327.4	350.7	377.3	405.7	437.5	476.1	525.1	580.1	639.5	694.5	743.5
137.5°	339.7	363.6	387.8	415.0	445.2	477.2	516.4	561.3	609.2	655.0	696.5
140°	347.2	370.5	395.4	421.2	448.7	477.9	512.3	551.0	591.3	630.9	667.0
142.5°	354.8	376.6	400.2	424.6	450.7	478.5	508.9	542.0	576.2	610.3	641.5
145°	366.2	385.9	408.3	429.7	453.0	477.9	503.7	530.3	557.0	583.6	606.8
147.5°	376.4	393.8	413.5	432.8	453.8	475.6	498.3	519.4	541.0	561.5	578.9
150°	383.3	398.0	416.9	434.9	453.8	473.6	494.2	513.2	532.0	548.4	563.9
152.5°	389.5	402.8	420.3	436.3	453.1	470.9	489.4	506.3	523.1	538.0	550.1
155°	397.1	409.1	423.7	437.5	451.3	465.9	481.3	495.9	509.7	521.8	531.2
157.5°	405.0	414.1	426.6	438.3	449.0	460.7	473.7	485.6	497.0	506.3	513.7
160°	409.1	416.9	428.0	438.3	446.9	457.3	467.6	478.7	487.3	495.9	502.0
162.5°	413.3	419.7	429.4	437.6	444.9	453.1	462.1	471.2	479.1	486.3	491.6
165°	417.8	422.9	429.7	436.6	441.8	446.9	453.8	460.7	466.7	471.9	476.1
167.5°	420.9	424.0	429.7	434.5	437.0	440.9	445.7	450.7	454.7	458.7	461.8
170°	422.9	425.4	429.7	433.2	434.9	437.5	440.9	445.2	447.8	450.4	452.1
172.5°	424.2	425.4	429.0	431.8	432.1	433.3	436.1	439.0	441.6	443.5	444.5
175°	425.4	425.4	428.0	429.7	428.9	428.9	429.7	432.3	432.3	434.0	434.0
177.5°	425.6	425.6	427.0	427.7	426.3	426.3	427.0	427.7	428.3	428.3	428.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1566.2	1560.3	1558.7	1560.8	1558.7	1560.3	1566.2	1566.8	1567.3	1571.6	1565.6
5°	1445.0	1438.3	1441.7	1440.3	1441.7	1438.3	1445.0	1451.7	1453.0	1459.1	1463.1
7.5°	1338.4	1330.1	1321.2	1324.0	1321.2	1330.1	1338.4	1338.6	1349.0	1356.8	1362.0
10°	1263.8	1257.1	1253.0	1256.4	1253.0	1257.1	1263.8	1272.6	1276.5	1285.9	1296.0
12.5°	1201.0	1197.0	1193.4	1192.0	1193.4	1197.0	1201.0	1210.2	1219.6	1230.6	1241.8
15°	1115.4	1107.4	1104.1	1095.4	1104.1	1107.4	1115.4	1123.5	1141.7	1146.3	1163.1
17.5°	1036.6	1034.0	1025.3	1021.5	1025.3	1034.0	1036.6	1043.5	1051.9	1069.2	1081.8
20°	990.0	987.3	978.5	984.0	978.5	987.3	990.0	1000.1	1006.8	1020.8	1032.9
22.5°	951.3	945.4	942.5	941.0	942.5	945.4	951.3	956.0	964.8	977.8	991.6
25°	896.6	887.9	884.6	880.5	884.6	887.9	896.6	899.3	908.8	921.5	928.8
27.5°	842.1	837.5	833.0	832.0	833.0	837.5	842.1	845.9	854.1	865.2	878.6
30°	806.8	802.0	798.7	798.7	798.7	802.0	806.8	814.8	820.8	830.9	840.9
32.5°	775.1	771.5	768.1	767.6	768.1	771.5	775.1	779.4	786.4	797.6	808.2
35°	728.9	723.5	722.2	718.2	722.2	723.5	728.9	732.2	739.6	747.7	756.4
37.5°	681.0	676.5	676.4	676.0	676.4	676.5	681.0	686.9	693.0	700.3	711.0
40°	650.3	647.0	646.4	641.6	646.4	647.0	650.3	653.1	659.8	669.2	677.2
42.5°	617.6	615.9	613.5	611.6	613.5	615.9	617.6	622.9	628.6	635.3	645.5
45°	573.2	568.4	568.4	565.1	568.4	568.4	573.2	577.9	580.6	588.6	602.0
47.5°	527.3	523.7	524.0	520.6	524.0	523.7	527.3	528.7	533.0	541.0	548.4
50°	496.6	494.6	494.0	492.7	494.0	494.6	496.6	496.0	501.4	508.8	518.8
52.5°	466.1	465.1	467.7	464.7	467.7	465.1	466.1	467.5	471.3	476.0	485.5
55°	424.8	422.8	426.9	422.8	426.9	422.8	424.8	423.5	424.8	429.6	435.6
57.5°	377.5	375.6	379.2	377.2	379.2	375.6	377.5	377.7	381.8	382.5	387.8
60°	346.3	342.3	344.3	345.0	344.3	342.3	346.3	347.7	349.0	349.7	355.1
62.5°	309.3	306.9	308.3	305.2	308.3	306.9	309.3	312.2	315.2	318.6	321.8
65°	257.1	255.0	252.4	251.0	252.4	255.0	257.1	258.4	265.8	269.8	277.2
67.5°	215.9	211.1	211.0	212.1	211.0	211.1	215.9	215.7	221.1	224.3	229.3
70°	185.9	185.9	185.2	185.2	185.2	185.9	185.9	189.9	192.6	195.3	198.6
72.5°	165.0	164.5	163.2	162.7	163.2	164.5	165.0	166.3	167.9	170.7	173.9
75°	132.9	133.5	132.2	131.6	132.2	133.5	132.9	132.9	135.6	136.2	137.6
77.5°	98.2	95.3	96.8	95.3	96.8	95.3	98.2	100.8	101.8	104.7	104.9
80°	74.5	73.8	75.9	73.8	75.9	73.8	74.5	74.5	76.5	77.8	81.2
82.5°	58.9	58.3	59.2	57.7	59.2	58.3	58.9	58.4	59.3	61.2	60.8
85°	35.6	34.9	34.3	34.9	34.3	34.9	35.6	34.9	34.3	34.9	35.6
87.5°	16.1	15.6	15.8	15.8	15.8	15.6	16.1	15.6	15.8	15.6	15.4
90°	18.9	18.9	19.8	19.8	19.8	18.9	18.9	18.9	17.2	16.4	15.5
92.5°	59.5	57.4	56.2	54.8	56.2	57.4	59.5	70.5	83.2	110.6	152.3
95°	248.4	222.7	215.8	202.0	215.8	222.7	248.4	309.4	381.6	487.3	618.0
97.5°	572.3	524.1	499.2	488.2	499.2	524.1	572.3	625.3	725.7	828.7	920.4
100°	777.8	716.0	684.2	670.5	684.2	716.0	777.8	837.2	926.5	1015.1	1057.2
102.5°	962.9	918.9	884.2	873.9	884.2	918.9	962.9	1026.2	1086.8	1129.2	1103.3
105°	1194.7	1166.4	1149.2	1138.8	1149.2	1166.4	1194.7	1222.2	1231.7	1193.9	1076.1
107.5°	1292.2	1292.0	1286.3	1279.4	1286.3	1292.0	1292.2	1278.2	1233.4	1136.3	979.1
110°	1303.9	1320.2	1326.2	1326.2	1326.2	1320.2	1303.9	1265.2	1192.1	1070.9	907.7



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1271.5	1299.6	1314.6	1320.7	1314.6	1299.6	1271.5	1215.0	1128.9	1006.3	851.3
115°	1192.1	1233.4	1257.5	1268.7	1257.5	1233.4	1192.1	1125.1	1031.4	913.7	780.4
117.5°	1104.0	1146.6	1170.4	1177.3	1170.4	1146.6	1104.0	1036.9	951.0	849.5	734.7
120°	1046.9	1088.1	1111.4	1118.3	1111.4	1088.1	1046.9	983.3	907.7	813.1	710.0
122.5°	998.8	1036.6	1059.8	1066.0	1059.8	1036.6	998.8	942.0	871.2	787.0	691.4
125°	936.9	972.1	991.0	999.6	991.0	972.1	936.9	888.7	826.8	752.1	664.4
127.5°	890.1	921.2	939.1	942.9	939.1	921.2	890.1	846.4	788.5	718.8	636.9
130°	861.3	889.6	906.8	912.0	906.8	889.6	861.3	818.3	762.4	695.3	619.7
132.5°	831.0	859.4	875.1	881.0	875.1	859.4	831.0	788.0	734.2	673.3	602.5
135°	781.3	809.7	825.1	830.3	825.1	809.7	781.3	743.5	694.5	639.5	580.1
137.5°	730.4	756.2	770.5	776.1	770.5	756.2	730.4	696.5	655.0	609.2	561.3
140°	698.8	721.2	734.0	738.3	734.0	721.2	698.8	667.0	630.9	591.3	551.0
142.5°	668.6	687.4	699.6	703.3	699.6	687.4	668.6	641.5	610.3	576.2	542.0
145°	627.4	642.0	651.5	655.0	651.5	642.0	627.4	606.8	583.6	557.0	530.3
147.5°	595.3	607.0	612.5	614.1	612.5	607.0	595.3	578.9	561.5	541.0	519.4
150°	576.7	587.0	590.5	591.3	590.5	587.0	576.7	563.9	548.4	532.0	513.2
152.5°	560.9	569.2	572.6	573.4	572.6	569.2	560.9	550.1	538.0	523.1	506.3
155°	539.8	545.8	548.4	549.2	548.4	545.8	539.8	531.2	521.8	509.7	495.9
157.5°	520.4	525.3	527.7	527.5	527.7	525.3	520.4	513.7	506.3	497.0	485.6
160°	508.0	512.3	514.0	513.2	514.0	512.3	508.0	502.0	495.9	487.3	478.7
162.5°	496.3	499.9	500.2	500.1	500.2	499.9	496.3	491.6	486.3	479.1	471.2
165°	479.6	481.3	481.3	481.3	481.3	481.3	479.6	476.1	471.9	466.7	460.7
167.5°	463.5	465.0	464.3	464.2	464.3	465.0	463.5	461.8	458.7	454.7	450.7
170°	453.8	454.7	454.7	453.8	454.7	454.7	453.8	452.1	450.4	447.8	445.2
172.5°	444.9	446.4	445.1	444.2	445.1	446.4	444.9	444.5	443.5	441.6	439.0
175°	434.0	434.9	433.2	432.3	433.2	434.9	434.0	434.0	434.0	432.3	432.3
177.5°	427.7	428.3	426.3	426.3	426.3	428.3	427.7	428.3	428.3	428.3	427.7
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1567.3	1573.2	1576.4	1583.9	1594.7	1600.1	1607.6	1612.9	1620.5	1629.6	1637.1
5°	1465.9	1482.0	1492.6	1509.4	1524.9	1540.3	1559.8	1573.9	1592.7	1614.1	1630.9
7.5°	1371.6	1391.7	1409.5	1431.8	1457.2	1477.1	1502.4	1528.4	1557.7	1588.2	1617.0
10°	1311.5	1331.6	1353.8	1381.2	1406.8	1433.6	1463.8	1494.0	1530.9	1565.1	1604.0
12.5°	1251.8	1274.1	1299.0	1329.7	1360.6	1394.9	1425.6	1459.7	1499.3	1543.7	1585.3
15°	1177.8	1199.4	1226.2	1252.4	1288.0	1325.5	1366.5	1411.4	1455.8	1505.4	1557.1
17.5°	1098.5	1122.1	1151.7	1182.1	1219.5	1263.5	1303.6	1352.9	1402.7	1460.6	1521.4
20°	1047.0	1071.2	1106.0	1139.6	1173.9	1216.9	1264.5	1314.8	1367.8	1428.9	1496.7
22.5°	1006.2	1023.4	1057.7	1091.8	1132.0	1176.0	1222.6	1275.1	1332.9	1396.1	1467.1
25°	945.6	965.8	990.7	1026.2	1067.8	1114.1	1161.1	1216.9	1279.9	1344.4	1420.1
27.5°	891.8	908.4	932.9	960.8	1002.3	1050.3	1100.3	1158.4	1223.1	1288.7	1368.5
30°	853.7	871.8	895.4	924.9	957.8	1010.1	1061.1	1118.2	1184.0	1251.7	1333.6
32.5°	820.4	839.0	859.4	887.3	922.8	969.3	1021.9	1077.9	1144.7	1214.7	1294.4
35°	773.9	786.6	805.4	832.9	867.8	905.4	959.1	1018.1	1083.2	1155.7	1235.6
37.5°	720.4	736.9	755.6	779.5	810.1	850.8	900.7	960.4	1020.8	1090.2	1163.1
40°	689.3	704.7	725.6	743.0	775.2	812.1	857.7	920.2	980.6	1045.7	1112.2
42.5°	657.6	672.5	690.1	711.9	740.8	776.7	819.1	877.2	941.9	1003.2	1058.9
45°	608.0	623.5	640.3	660.4	687.3	722.2	764.5	817.4	873.8	930.2	972.5
47.5°	560.7	575.1	591.0	611.7	636.4	670.1	707.9	754.8	809.5	857.5	887.7
50°	526.8	540.3	557.8	577.9	602.0	633.6	669.9	716.1	761.7	805.4	832.9
52.5°	493.6	508.6	526.1	543.5	566.6	598.1	631.7	671.6	715.1	750.6	773.4
55°	443.7	457.7	473.8	492.0	514.8	541.7	577.2	608.7	643.0	673.2	686.6
57.5°	395.5	407.8	422.9	441.8	462.3	487.2	515.5	545.8	570.0	591.3	606.5
60°	363.8	374.5	388.6	404.7	426.9	449.7	475.2	503.3	522.2	540.3	554.4
62.5°	331.6	341.7	355.3	369.8	389.3	410.4	434.9	457.7	476.0	488.2	504.5
65°	283.3	293.3	304.7	320.1	335.6	353.0	375.1	391.9	404.7	418.1	428.2
67.5°	238.2	246.6	257.4	269.6	282.6	299.4	316.5	330.5	339.2	347.2	359.4
70°	208.7	215.4	224.2	233.6	247.6	264.4	277.8	288.6	294.6	302.7	317.5
72.5°	178.7	186.4	194.7	204.1	215.4	229.5	241.3	252.1	256.0	262.4	271.8
75°	140.9	145.0	151.7	158.4	166.4	178.6	189.9	192.6	196.0	201.4	208.0
77.5°	106.6	110.2	112.9	117.4	123.7	133.5	139.5	143.5	144.3	146.3	152.9
80°	84.6	86.6	89.3	92.6	95.3	103.3	106.7	110.7	112.1	114.1	117.4
82.5°	62.0	64.1	65.6	68.4	72.8	75.9	79.3	83.3	83.6	85.1	85.8
85°	36.2	36.9	35.6	36.9	37.6	38.9	42.3	45.6	44.9	44.3	46.3
87.5°	15.8	15.7	14.7	16.2	14.8	15.2	14.8	15.0	15.8	16.4	17.4
90°	14.6	13.8	12.1	11.2	9.5	8.6	6.9	5.2	3.4	1.7	0.9
92.5°	224.3	277.1	281.5	196.1	117.4	70.5	45.4	30.6	20.0	12.7	10.5
95°	745.2	761.6	621.5	384.2	195.1	103.1	64.5	45.5	36.1	29.2	28.3
97.5°	942.9	813.3	554.9	306.7	168.2	107.3	79.4	62.4	53.0	48.1	47.1
100°	991.0	776.1	495.1	278.4	166.8	116.9	91.1	74.7	65.3	61.9	60.2
102.5°	962.2	710.8	449.7	266.8	173.0	128.5	103.5	88.5	78.4	75.6	74.6
105°	869.9	623.1	405.7	262.2	185.6	147.8	123.8	110.0	101.4	97.1	97.1
107.5°	775.6	562.8	387.1	270.1	204.6	168.0	146.3	132.0	124.9	120.9	119.2
110°	721.9	534.6	381.6	277.6	218.3	183.0	160.7	147.8	140.1	136.6	134.9



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	682.1	518.1	381.6	287.2	231.4	197.5	175.8	163.0	155.2	152.5	150.8
115°	638.6	500.2	384.2	301.7	251.8	220.1	198.5	185.6	177.9	175.3	173.7
117.5°	612.7	491.5	389.9	318.2	272.9	242.7	222.0	207.3	199.6	196.8	194.2
120°	598.2	487.3	395.4	329.2	287.9	257.9	236.3	221.8	214.0	210.6	208.0
122.5°	585.8	483.9	400.2	341.6	302.4	272.3	250.8	234.8	227.0	224.3	222.5
125°	569.0	479.6	408.3	358.4	321.5	293.1	270.8	254.4	246.7	242.4	240.6
127.5°	553.5	477.5	417.4	373.8	339.8	312.5	290.2	272.9	263.0	257.5	254.9
130°	543.2	476.1	422.9	384.2	351.5	324.9	302.6	284.5	273.4	266.5	263.9
132.5°	534.9	476.1	429.0	393.1	362.6	335.9	313.6	294.8	282.2	274.0	270.8
135°	525.1	476.1	437.5	405.7	377.3	350.7	327.4	309.4	295.7	285.3	281.9
137.5°	516.4	477.2	445.2	415.0	387.8	363.6	339.7	322.0	308.2	298.6	296.0
140°	512.3	477.9	448.7	421.2	395.4	370.5	347.2	330.9	317.2	306.9	304.3
142.5°	508.9	478.5	450.7	424.6	400.2	376.6	354.8	339.1	325.4	315.8	313.9
145°	503.7	477.9	453.0	429.7	408.3	385.9	366.2	350.7	338.6	330.0	328.3
147.5°	498.3	475.6	453.8	432.8	413.5	393.8	376.4	363.1	351.9	344.5	343.5
150°	494.2	473.6	453.8	434.9	416.9	398.0	383.3	371.3	360.2	354.1	352.4
152.5°	489.4	470.9	453.1	436.3	420.3	402.8	389.5	378.2	368.4	363.1	362.1
155°	481.3	465.9	451.3	437.5	423.7	409.1	397.1	388.5	379.9	374.7	374.7
157.5°	473.7	460.7	449.0	438.3	426.6	414.1	405.0	397.4	390.0	385.9	386.1
160°	467.6	457.3	446.9	438.3	428.0	416.9	409.1	402.3	396.2	392.8	393.6
162.5°	462.1	453.1	444.9	437.6	429.4	419.7	413.3	407.8	402.4	399.0	399.8
165°	453.8	446.9	441.8	436.6	429.7	422.9	417.8	414.3	410.0	407.4	409.1
167.5°	445.7	440.9	437.0	434.5	429.7	424.0	420.9	418.4	416.0	414.5	415.3
170°	440.9	437.5	434.9	433.2	429.7	425.4	422.9	421.2	419.5	418.6	419.5
172.5°	436.1	433.3	432.1	431.8	429.0	425.4	424.2	423.2	421.5	420.7	422.2
175°	429.7	428.9	428.9	429.7	428.0	425.4	425.4	425.4	424.6	423.7	425.4
177.5°	427.0	426.3	426.3	427.7	427.0	425.6	425.6	426.3	425.6	425.6	427.0
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1643.0	1647.9	1654.8	1662.8	1669.3	1676.3	1680.1	1680.1	1683.3	1690.2	1699.4
5°	1647.7	1665.2	1682.0	1703.4	1720.2	1739.7	1754.4	1768.5	1781.2	1797.3	1814.1
7.5°	1646.3	1675.3	1705.6	1739.4	1776.7	1806.4	1836.9	1860.7	1884.4	1915.2	1939.5
10°	1641.0	1678.6	1719.5	1762.5	1809.5	1850.4	1887.3	1920.9	1953.1	1986.7	2016.8
12.5°	1631.3	1679.1	1729.1	1780.7	1840.0	1886.9	1934.6	1970.2	2007.9	2044.6	2081.8
15°	1616.8	1673.2	1733.6	1805.4	1877.9	1930.3	1977.2	2023.5	2058.5	2100.1	2135.6
17.5°	1586.9	1659.5	1735.5	1814.0	1883.7	1944.5	1993.7	2037.8	2074.9	2120.7	2169.0
20°	1569.2	1647.7	1726.9	1810.8	1877.2	1939.7	1987.3	2032.9	2079.2	2139.0	2198.0
22.5°	1544.5	1628.4	1712.4	1792.0	1862.2	1922.4	1971.8	2027.6	2088.4	2156.2	2227.6
25°	1505.4	1592.0	1675.2	1751.0	1819.6	1881.3	1948.4	2023.5	2097.4	2186.7	2289.3
27.5°	1455.9	1539.4	1613.6	1693.8	1761.8	1840.3	1924.1	2005.5	2112.0	2234.8	2363.0
30°	1418.8	1498.1	1568.5	1644.3	1721.5	1808.1	1902.0	1998.0	2124.9	2269.2	2421.6
32.5°	1375.9	1447.6	1517.5	1590.6	1679.6	1774.8	1874.7	1992.1	2143.7	2307.8	2465.6
35°	1301.4	1365.8	1433.6	1514.8	1609.5	1712.8	1840.3	1983.3	2166.5	2343.0	2484.7
37.5°	1223.2	1274.1	1342.2	1427.8	1530.9	1650.5	1795.2	1968.9	2157.1	2315.5	2375.8
40°	1163.1	1210.7	1282.5	1372.5	1474.5	1605.4	1767.8	1946.4	2135.6	2245.7	2241.0
42.5°	1103.5	1151.7	1220.8	1311.3	1417.6	1564.1	1731.3	1916.8	2076.6	2118.5	2031.1
45°	1012.1	1057.0	1124.9	1216.2	1330.2	1483.9	1659.7	1837.6	1939.7	1871.9	1698.7
47.5°	918.9	962.6	1025.5	1114.9	1239.5	1400.3	1566.6	1712.5	1726.9	1581.2	1373.6
50°	857.7	898.7	958.4	1053.7	1174.5	1331.6	1492.0	1606.8	1571.2	1393.4	1179.2
52.5°	798.1	837.5	893.5	983.3	1106.9	1260.7	1403.9	1494.0	1411.7	1222.6	1029.9
55°	710.1	747.7	804.1	886.6	998.7	1139.6	1265.2	1298.0	1177.2	986.6	830.9
57.5°	626.5	654.0	709.7	782.7	890.8	1015.0	1105.0	1099.1	965.8	794.1	682.4
60°	571.2	596.0	649.0	716.1	818.8	930.2	993.3	966.5	831.6	689.9	582.6
62.5°	519.6	542.9	587.3	649.0	737.2	834.1	880.0	843.0	715.6	591.2	505.8
65°	441.6	458.4	494.0	551.0	620.2	687.3	728.2	673.8	561.1	467.1	402.7
67.5°	368.8	383.2	414.9	455.8	503.5	549.8	566.5	515.5	427.8	364.5	319.1
70°	321.5	334.9	356.4	394.7	426.2	459.1	467.1	421.5	348.4	300.0	271.8
72.5°	276.4	288.7	307.5	334.5	356.4	375.3	379.1	336.7	280.7	247.4	225.7
75°	210.8	221.4	233.6	243.7	257.7	261.1	259.8	226.9	196.7	174.5	162.4
77.5°	154.9	159.4	166.7	170.7	171.4	171.2	164.3	143.5	127.9	118.8	113.8
80°	119.5	122.9	124.8	126.1	126.8	120.1	112.8	100.0	94.6	89.3	83.3
82.5°	86.7	89.0	91.0	91.3	87.6	82.1	75.2	68.9	65.1	62.4	60.1
85°	47.0	47.6	47.0	43.7	38.9	36.9	35.6	34.3	33.6	32.9	32.9
87.5°	17.0	15.8	13.3	14.3	14.6	14.2	14.6	14.2	14.0	14.2	14.4
90°	1.7	3.4	5.2	6.9	8.6	9.5	11.2	12.1	13.8	14.6	15.5
92.5°	12.7	20.0	30.6	45.4	70.5	117.4	196.1	281.5	277.1	224.3	152.3
95°	29.2	36.1	45.5	64.5	103.1	195.1	384.2	621.5	761.6	745.2	618.0
97.5°	48.1	53.0	62.4	79.4	107.3	168.2	306.7	554.9	813.3	942.9	920.4
100°	61.9	65.3	74.7	91.1	116.9	166.8	278.4	495.1	776.1	991.0	1057.2
102.5°	75.6	78.4	88.5	103.5	128.5	173.0	266.8	449.7	710.8	962.2	1103.3
105°	97.1	101.4	110.0	123.8	147.8	185.6	262.2	405.7	623.1	869.9	1076.1
107.5°	120.9	124.9	132.0	146.3	168.0	204.6	270.1	387.1	562.8	775.6	979.1
110°	136.6	140.1	147.8	160.7	183.0	218.3	277.6	381.6	534.6	721.9	907.7





TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	152.5	155.2	163.0	175.8	197.5	231.4	287.2	381.6	518.1	682.1	851.3
115°	175.3	177.9	185.6	198.5	220.1	251.8	301.7	384.2	500.2	638.6	780.4
117.5°	196.8	199.6	207.3	222.0	242.7	272.9	318.2	389.9	491.5	612.7	734.7
120°	210.6	214.0	221.8	236.3	257.9	287.9	329.2	395.4	487.3	598.2	710.0
122.5°	224.3	227.0	234.8	250.8	272.3	302.4	341.6	400.2	483.9	585.8	691.4
125°	242.4	246.7	254.4	270.8	293.1	321.5	358.4	408.3	479.6	569.0	664.4
127.5°	257.5	263.0	272.9	290.2	312.5	339.8	373.8	417.4	477.5	553.5	636.9
130°	266.5	273.4	284.5	302.6	324.9	351.5	384.2	422.9	476.1	543.2	619.7
132.5°	274.0	282.2	294.8	313.6	335.9	362.6	393.1	429.0	476.1	534.9	602.5
135°	285.3	295.7	309.4	327.4	350.7	377.3	405.7	437.5	476.1	525.1	580.1
137.5°	298.6	308.2	322.0	339.7	363.6	387.8	415.0	445.2	477.2	516.4	561.3
140°	306.9	317.2	330.9	347.2	370.5	395.4	421.2	448.7	477.9	512.3	551.0
142.5°	315.8	325.4	339.1	354.8	376.6	400.2	424.6	450.7	478.5	508.9	542.0
145°	330.0	338.6	350.7	366.2	385.9	408.3	429.7	453.0	477.9	503.7	530.3
147.5°	344.5	351.9	363.1	376.4	393.8	413.5	432.8	453.8	475.6	498.3	519.4
150°	354.1	360.2	371.3	383.3	398.0	416.9	434.9	453.8	473.6	494.2	513.2
152.5°	363.1	368.4	378.2	389.5	402.8	420.3	436.3	453.1	470.9	489.4	506.3
155°	374.7	379.9	388.5	397.1	409.1	423.7	437.5	451.3	465.9	481.3	495.9
157.5°	385.9	390.0	397.4	405.0	414.1	426.6	438.3	449.0	460.7	473.7	485.6
160°	392.8	396.2	402.3	409.1	416.9	428.0	438.3	446.9	457.3	467.6	478.7
162.5°	399.0	402.4	407.8	413.3	419.7	429.4	437.6	444.9	453.1	462.1	471.2
165°	407.4	410.0	414.3	417.8	422.9	429.7	436.6	441.8	446.9	453.8	460.7
167.5°	414.5	416.0	418.4	420.9	424.0	429.7	434.5	437.0	440.9	445.7	450.7
170°	418.6	419.5	421.2	422.9	425.4	429.7	433.2	434.9	437.5	440.9	445.2
172.5°	420.7	421.5	423.2	424.2	425.4	429.0	431.8	432.1	433.3	436.1	439.0
175°	423.7	424.6	425.4	425.4	425.4	428.0	429.7	428.9	428.9	429.7	432.3
177.5°	425.6	425.6	426.3	425.6	425.6	427.0	427.7	426.3	426.3	427.0	427.7
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3	426.3



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1706.3	1706.3	1715.5	1714.9	1720.9	1718.7	1719.8
5°	1834.3	1845.7	1855.8	1862.4	1872.5	1875.3	1873.9
7.5°	1966.9	1992.3	2004.6	2021.5	2024.6	2033.5	2032.6
10°	2049.1	2073.9	2092.7	2107.5	2114.8	2124.3	2124.9
12.5°	2113.5	2134.6	2151.2	2164.9	2173.9	2176.9	2178.6
15°	2163.8	2187.3	2206.7	2226.2	2237.7	2246.3	2251.1
17.5°	2214.6	2250.8	2285.2	2311.6	2327.5	2340.9	2340.7
20°	2253.8	2295.3	2338.3	2368.5	2399.4	2412.8	2414.8
22.5°	2295.6	2359.2	2414.6	2461.4	2502.0	2515.9	2521.2
25°	2382.6	2465.8	2551.1	2616.8	2663.8	2691.3	2695.4
27.5°	2487.7	2600.3	2690.0	2750.7	2789.7	2810.1	2814.6
30°	2561.8	2665.8	2746.4	2792.1	2810.1	2812.8	2802.7
32.5°	2595.1	2672.8	2705.0	2702.3	2666.8	2643.2	2634.1
35°	2554.4	2538.3	2459.8	2365.9	2294.0	2248.4	2236.3
37.5°	2324.6	2185.7	2041.3	1899.3	1823.7	1785.3	1719.2
40°	2098.1	1900.1	1749.7	1630.2	1545.0	1476.5	1460.4
42.5°	1842.5	1638.1	1487.7	1385.4	1317.3	1270.4	1250.0
45°	1480.6	1304.8	1180.6	1102.1	1049.7	1015.5	1000.1
47.5°	1184.2	1048.1	957.6	899.5	859.6	829.8	821.5
50°	1021.5	912.7	836.3	787.3	757.1	734.3	724.9
52.5°	887.3	799.5	740.7	700.3	671.7	657.5	649.7
55°	732.2	656.4	614.2	581.9	565.8	554.4	549.0
57.5°	598.8	544.1	513.2	490.9	476.0	468.7	466.1
60°	524.2	481.2	453.1	435.6	425.5	416.1	413.5
62.5°	458.1	424.3	402.6	387.3	377.2	373.2	371.5
65°	369.1	347.0	330.9	321.5	313.4	312.1	311.4
67.5°	293.4	280.4	272.0	262.2	259.3	254.6	253.7
70°	251.0	242.3	232.2	228.9	225.5	220.8	221.4
72.5°	212.9	204.1	197.3	192.9	191.7	189.7	191.4
75°	155.7	153.0	150.3	147.0	145.7	145.7	145.0
77.5°	111.2	108.8	105.9	103.9	103.5	100.7	101.8
80°	80.5	77.1	75.9	76.5	74.5	73.8	73.8
82.5°	59.6	58.4	57.1	57.2	56.7	56.1	56.7
85°	32.9	32.2	32.2	31.5	31.5	30.9	30.9
87.5°	15.1	15.8	15.1	14.6	14.6	15.2	15.8
90°	16.4	17.2	18.9	18.9	18.9	19.8	19.8
92.5°	110.6	83.2	70.5	59.5	57.4	56.2	54.8
95°	487.3	381.6	309.4	248.4	222.7	215.8	202.0
97.5°	828.7	725.7	625.3	572.3	524.1	499.2	488.2
100°	1015.1	926.5	837.2	777.8	716.0	684.2	670.5
102.5°	1129.2	1086.8	1026.2	962.9	918.9	884.2	873.9
105°	1193.9	1231.7	1222.2	1194.7	1166.4	1149.2	1138.8
107.5°	1136.3	1233.4	1278.2	1292.2	1292.0	1286.3	1279.4
110°	1070.9	1192.1	1265.2	1303.9	1320.2	1326.2	1326.2



TEST NUMBER: P333630-935

CATALOG NUMBER: S125RDIP-S1270D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1006.3	1128.9	1215.0	1271.5	1299.6	1314.6	1320.7
115°	913.7	1031.4	1125.1	1192.1	1233.4	1257.5	1268.7
117.5°	849.5	951.0	1036.9	1104.0	1146.6	1170.4	1177.3
120°	813.1	907.7	983.3	1046.9	1088.1	1111.4	1118.3
122.5°	787.0	871.2	942.0	998.8	1036.6	1059.8	1066.0
125°	752.1	826.8	888.7	936.9	972.1	991.0	999.6
127.5°	718.8	788.5	846.4	890.1	921.2	939.1	942.9
130°	695.3	762.4	818.3	861.3	889.6	906.8	912.0
132.5°	673.3	734.2	788.0	831.0	859.4	875.1	881.0
135°	639.5	694.5	743.5	781.3	809.7	825.1	830.3
137.5°	609.2	655.0	696.5	730.4	756.2	770.5	776.1
140°	591.3	630.9	667.0	698.8	721.2	734.0	738.3
142.5°	576.2	610.3	641.5	668.6	687.4	699.6	703.3
145°	557.0	583.6	606.8	627.4	642.0	651.5	655.0
147.5°	541.0	561.5	578.9	595.3	607.0	612.5	614.1
150°	532.0	548.4	563.9	576.7	587.0	590.5	591.3
152.5°	523.1	538.0	550.1	560.9	569.2	572.6	573.4
155°	509.7	521.8	531.2	539.8	545.8	548.4	549.2
157.5°	497.0	506.3	513.7	520.4	525.3	527.7	527.5
160°	487.3	495.9	502.0	508.0	512.3	514.0	513.2
162.5°	479.1	486.3	491.6	496.3	499.9	500.2	500.1
165°	466.7	471.9	476.1	479.6	481.3	481.3	481.3
167.5°	454.7	458.7	461.8	463.5	465.0	464.3	464.2
170°	447.8	450.4	452.1	453.8	454.7	454.7	453.8
172.5°	441.6	443.5	444.5	444.9	446.4	445.1	444.2
175°	432.3	434.0	434.0	434.0	434.9	433.2	432.3
177.5°	428.3	428.3	428.3	427.7	428.3	426.3	426.3
180°	426.3	426.3	426.3	426.3	426.3	426.3	426.3

(END OF REPORT)