

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333619-935

Luminaire Tested: **S125RDIP-S1270D590U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333619-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D590U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6235.2 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333619-935

CATALOG NUMBER: S125RDIP-S1270D590U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333619-935

CATALOG NUMBER: S125RDIP-S1270D590U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	62	57				
2	93	86	79	74	88	81	76	71	72	68	64	64	61	58	57	54	52	49				
3	85	76	68	62	80	72	65	60	64	59	54	57	53	50	51	47	45	41				
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	36				
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31				
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	27				
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	24				
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22				
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20				
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11479	11479	11479
5°	11505	11374	11444
10°	11418	11269	11269
15°	11282	11040	10950
20°	11109	10721	10592
25°	10905	10408	10178
30°	10651	10041	9721
35°	10394	9663	9208
40°	10151	9269	8703
45°	9858	8828	8153
50°	9562	8349	7580
55°	9221	7891	6969
60°	8878	7334	6311
65°	8472	6687	5559
70°	8010	5880	4791
75°	7369	4956	3985
80°	6490	3894	3347
85°	5476	3186	2986



TEST NUMBER: P333619-935

CATALOG NUMBER: S125RDIP-S1270D590U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.1	2.7
10°-20°	467.1	7.5
20°-30°	677.3	10.9
30°-40°	771.9	12.4
40°-50°	752.4	12.1
50°-60°	633.3	10.2
60°-70°	444.0	7.1
70°-80°	228.2	3.7
80°-90°	59.0	0.9
90°-100°	24.1	0.4
100°-110°	148.4	2.4
110°-120°	269.2	4.3
120°-130°	345.5	5.5
130°-140°	371.6	6.0
140°-150°	348.8	5.6
150°-160°	282.1	4.5
160°-170°	182.5	2.9
170°-180°	62.9	1.0
0°-30°	1311.5	21.0
0°-40°	2083.3	33.4
0°-60°	3469.1	55.6
0°-90°	4200.2	67.4
90°-120°	441.7	7.1
90°-150°	1507.5	24.2
90°-180°	2035.0	32.6
0°-180°	6235.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1775	1769	1754	1767	1765	168
15°	1687	1678	1651	1649	1638	475
25°	1530	1509	1460	1443	1428	704
35°	1318	1284	1226	1188	1168	825
45°	1079	1038	967	915	893	832
55°	819	774	701	642	619	732
65°	554	507	438	386	364	549
75°	295	254	199	170	160	313
85°	74	51	43	42	40	83
90°	0	4	8	10	12	5
95°	28	26	8	10	10	36
105°	144	146	146	146	146	153
115°	271	274	274	272	269	269
125°	386	389	389	387	386	344
135°	481	484	483	482	479	371
145°	558	558	558	559	556	349
155°	614	611	612	613	610	283
165°	648	645	646	648	644	183
175°	663	660	660	664	660	63
180°	663	663	663	663	663	



TEST NUMBER: P333619-935

CATALOG NUMBER: S125RDIP-S1270D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4
2.5°	1780.5	1779.9	1779.1	1778.4	1777.7	1776.2	1773.7	1771.3	1769.0	1766.6	1769.0
5°	1774.7	1773.5	1772.3	1771.1	1769.9	1767.6	1764.4	1761.1	1757.8	1754.5	1757.5
7.5°	1757.2	1756.1	1755.0	1753.8	1752.7	1750.2	1746.2	1742.2	1738.4	1734.4	1736.5
10°	1741.1	1740.2	1739.3	1738.4	1737.5	1735.0	1730.8	1726.6	1722.4	1718.3	1719.2
12.5°	1722.9	1721.7	1720.5	1719.4	1718.3	1714.9	1709.3	1703.7	1698.1	1692.5	1693.2
15°	1687.4	1685.6	1683.9	1682.0	1680.2	1676.2	1669.9	1663.7	1657.4	1651.1	1650.9
17.5°	1647.4	1644.7	1641.9	1639.2	1636.4	1631.1	1623.2	1615.3	1607.5	1599.6	1598.1
20°	1616.3	1613.3	1610.2	1607.3	1604.3	1598.0	1588.5	1579.0	1569.4	1559.9	1558.4
22.5°	1581.9	1578.9	1575.9	1573.0	1569.9	1563.5	1553.4	1543.4	1533.4	1523.4	1520.4
25°	1530.3	1525.9	1521.4	1516.9	1512.4	1504.7	1493.7	1482.6	1471.5	1460.5	1456.6
27.5°	1471.3	1465.9	1460.4	1455.0	1449.6	1441.0	1429.1	1417.3	1405.5	1393.7	1388.3
30°	1428.3	1422.6	1416.9	1411.4	1405.7	1396.5	1384.0	1371.5	1358.9	1346.4	1339.5
32.5°	1386.5	1379.8	1373.2	1366.6	1359.9	1350.2	1337.5	1324.7	1311.9	1299.2	1291.6
35°	1318.3	1311.0	1303.9	1296.8	1289.6	1279.3	1265.8	1252.5	1239.1	1225.6	1216.9
37.5°	1251.4	1242.7	1234.0	1225.3	1216.5	1205.2	1191.5	1177.6	1163.7	1149.9	1139.5
40°	1204.1	1195.2	1186.2	1177.2	1168.4	1156.7	1142.4	1128.1	1113.7	1099.4	1088.1
42.5°	1154.8	1145.6	1136.3	1127.1	1118.0	1106.0	1091.2	1076.4	1061.6	1046.8	1036.0
45°	1079.3	1070.7	1062.0	1053.3	1044.7	1032.2	1015.7	999.4	982.9	966.6	954.6
47.5°	1001.2	992.0	982.9	973.8	964.7	951.8	935.3	918.8	902.2	885.7	873.4
50°	951.7	941.9	932.0	922.2	912.4	899.0	881.9	865.0	847.9	831.0	818.4
52.5°	898.0	887.9	877.9	867.8	857.7	844.6	828.6	812.6	796.5	780.5	767.0
55°	818.9	809.3	799.8	790.2	780.7	767.6	750.9	734.2	717.5	700.8	687.3
57.5°	738.8	728.7	718.4	708.3	698.0	684.9	668.8	652.6	636.5	620.4	607.3
60°	687.3	676.8	666.4	656.0	645.6	632.2	616.1	600.0	583.9	567.8	554.7
62.5°	632.6	622.6	612.6	602.6	592.7	579.5	563.2	546.8	530.5	514.1	502.0
65°	554.4	544.2	534.2	524.0	513.8	500.8	485.1	469.2	453.4	437.6	425.7
67.5°	476.8	466.7	456.5	446.4	436.3	423.6	408.5	393.3	378.2	363.0	352.1
70°	424.2	414.1	403.9	393.7	383.7	371.1	356.2	341.3	326.3	311.4	302.2
72.5°	372.6	362.7	352.8	342.9	333.0	321.1	307.1	293.2	279.2	265.3	256.8
75°	295.3	286.4	277.4	268.5	259.5	248.8	236.3	223.8	211.2	198.6	192.1
77.5°	218.5	211.4	204.2	197.1	189.9	181.3	171.3	161.3	151.3	141.2	136.6
80°	174.5	167.4	160.2	153.0	145.9	138.1	129.8	121.4	113.0	104.7	102.0
82.5°	131.6	125.1	118.6	112.2	105.8	99.7	93.9	88.3	82.5	76.8	75.5
85°	73.9	68.4	63.1	57.7	52.3	48.9	47.4	46.0	44.4	43.0	42.6
87.5°	24.8	23.3	21.8	20.3	18.9	18.0	17.9	17.8	17.7	17.7	17.8
90°	0.5	1.4	2.2	3.1	4.0	4.8	5.6	6.4	7.1	7.8	8.4
92.5°	7.6	7.0	6.4	5.8	5.1	5.2	5.9	6.5	7.1	7.8	8.4
95°	28.0	27.6	27.4	27.0	26.7	24.5	20.3	16.2	12.0	7.8	8.4
97.5°	58.5	59.1	59.7	60.2	60.8	57.0	48.8	40.6	32.4	24.2	21.1
100°	82.1	82.4	82.7	83.0	83.3	83.7	84.2	84.6	85.1	85.5	69.2
102.5°	106.0	106.4	106.9	107.3	107.6	108.0	108.2	108.6	108.8	109.1	106.0
105°	144.4	144.8	145.3	145.8	146.2	146.4	146.4	146.4	146.4	146.4	146.4
107.5°	184.3	184.3	184.3	184.3	184.3	184.4	184.6	184.9	185.1	185.3	185.3
110°	210.3	210.3	210.3	210.3	210.3	210.3	210.6	210.8	211.0	211.2	210.9



TEST NUMBER: P333619-935

CATALOG NUMBER: S125RDIP-S1270D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	234.6	234.9	235.1	235.4	235.7	235.8	236.0	236.1	236.3	236.3	236.0
115°	271.1	271.7	272.2	272.8	273.4	273.7	273.8	273.9	274.0	274.1	273.7
117.5°	309.0	308.9	308.9	308.9	308.9	309.1	309.5	310.0	310.3	310.7	310.2
120°	332.6	332.4	332.3	332.3	332.1	332.3	332.6	332.9	333.2	333.6	333.3
122.5°	353.4	353.8	354.2	354.6	355.1	355.3	355.5	355.7	355.8	355.9	355.8
125°	385.6	386.4	387.1	387.9	388.7	389.1	389.1	389.1	389.1	389.1	388.7
127.5°	416.4	416.9	417.5	418.0	418.5	418.8	418.7	418.7	418.6	418.5	418.3
130°	435.2	435.8	436.4	436.9	437.4	437.7	437.8	438.0	438.1	438.2	437.8
132.5°	454.1	454.7	455.4	456.0	456.6	456.8	456.6	456.3	456.1	455.9	455.8
135°	481.0	481.6	482.2	482.8	483.5	483.8	483.5	483.3	483.1	482.8	482.7
137.5°	505.6	506.2	506.7	507.3	507.8	508.1	507.8	507.6	507.5	507.2	507.3
140°	521.7	521.9	522.1	522.4	522.5	522.6	522.5	522.4	522.3	522.2	522.4
142.5°	536.2	536.4	536.5	536.7	536.7	536.9	537.1	537.2	537.4	537.5	537.5
145°	557.6	557.8	558.0	558.2	558.4	558.5	558.5	558.5	558.5	558.5	558.6
147.5°	576.2	576.2	576.1	576.1	576.0	576.1	576.2	576.4	576.4	576.6	576.8
150°	588.0	587.8	587.5	587.4	587.1	587.1	587.4	587.5	587.8	588.0	588.2
152.5°	599.4	598.9	598.5	598.0	597.4	597.4	597.5	597.8	598.0	598.2	598.5
155°	614.1	613.4	612.8	612.1	611.4	611.2	611.4	611.7	611.8	612.1	612.4
157.5°	625.3	624.9	624.6	624.1	623.8	623.6	623.6	623.6	623.6	623.7	624.1
160°	633.2	632.6	631.9	631.2	630.6	630.3	630.4	630.5	630.6	630.8	631.2
162.5°	639.5	638.9	638.2	637.5	636.9	636.6	636.7	636.8	636.9	637.1	637.7
165°	647.9	647.3	646.6	646.0	645.3	645.1	645.1	645.2	645.4	645.5	646.1
167.5°	654.2	653.6	652.9	652.2	651.5	651.3	651.3	651.4	651.5	651.7	652.5
170°	657.8	657.0	656.3	655.5	654.7	654.4	654.4	654.6	654.7	654.8	655.7
172.5°	660.1	659.4	658.6	657.8	657.0	656.8	656.9	657.2	657.4	657.5	658.3
175°	662.7	662.0	661.3	660.7	660.0	659.8	659.9	660.0	660.1	660.2	661.1
177.5°	663.8	663.3	662.8	662.3	661.8	661.5	661.6	661.7	661.8	661.9	662.5
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7



TEST NUMBER: P333619-935

CATALOG NUMBER: S125RDIP-S1270D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4
2.5°	1771.3	1773.7	1776.2	1777.2	1777.0	1776.8	1776.5	1776.2
5°	1760.5	1763.5	1766.4	1767.6	1767.0	1766.4	1765.8	1765.2
7.5°	1738.5	1740.7	1742.8	1743.4	1742.8	1742.1	1741.5	1740.9
10°	1720.0	1721.0	1721.8	1721.8	1721.0	1720.0	1719.2	1718.3
12.5°	1693.8	1694.4	1695.1	1694.8	1693.4	1692.0	1690.7	1689.3
15°	1650.5	1650.3	1649.9	1648.5	1645.8	1643.1	1640.4	1637.7
17.5°	1596.6	1595.1	1593.6	1591.8	1589.6	1587.3	1585.2	1582.9
20°	1556.9	1555.4	1553.9	1551.8	1549.1	1546.4	1543.8	1541.1
22.5°	1517.5	1514.6	1511.7	1509.1	1506.9	1504.7	1502.4	1500.3
25°	1452.8	1448.9	1445.0	1441.4	1438.1	1434.9	1431.6	1428.3
27.5°	1382.9	1377.4	1372.0	1367.7	1364.5	1361.3	1358.1	1355.0
30°	1332.7	1325.9	1319.0	1314.2	1311.6	1308.8	1306.1	1303.5
32.5°	1284.0	1276.4	1268.9	1263.3	1260.0	1256.5	1253.2	1249.7
35°	1208.3	1199.6	1191.0	1184.6	1180.4	1176.2	1172.1	1167.9
37.5°	1129.1	1118.8	1108.4	1101.1	1097.1	1093.0	1089.0	1084.9
40°	1076.8	1065.4	1054.1	1046.6	1043.0	1039.5	1035.9	1032.3
42.5°	1025.1	1014.3	1003.4	995.3	990.1	984.8	979.6	974.3
45°	942.6	930.7	918.8	910.6	906.1	901.6	897.2	892.7
47.5°	861.2	848.9	836.5	827.9	822.9	818.0	813.0	808.1
50°	805.9	793.3	780.8	772.3	767.8	763.4	758.9	754.4
52.5°	753.5	740.0	726.5	717.6	713.1	708.6	704.1	699.6
55°	673.9	660.5	647.0	637.9	633.2	628.4	623.6	618.9
57.5°	594.2	581.1	567.9	559.3	555.0	550.8	546.6	542.3
60°	541.6	528.5	515.3	506.5	502.0	497.6	493.1	488.6
62.5°	489.8	477.6	465.5	457.1	452.6	448.2	443.7	439.2
65°	413.8	401.8	389.9	381.7	377.2	372.7	368.2	363.8
67.5°	341.1	330.2	319.3	312.0	308.5	304.9	301.4	297.7
70°	292.9	283.7	274.5	268.0	264.4	260.9	257.3	253.7
72.5°	248.2	239.7	231.1	225.7	223.3	220.9	218.5	216.1
75°	185.5	179.0	172.5	168.1	166.0	163.9	161.9	159.7
77.5°	132.0	127.4	122.9	119.8	118.2	116.7	115.1	113.6
80°	99.4	96.7	93.9	92.3	91.7	91.1	90.6	90.0
82.5°	74.3	73.0	71.8	70.9	70.6	70.3	69.9	69.6
85°	42.4	42.1	41.8	41.5	41.2	40.9	40.6	40.3
87.5°	17.9	18.0	18.1	18.1	17.9	17.7	17.6	17.4
90°	9.0	9.5	10.1	10.5	10.8	11.1	11.5	11.8
92.5°	9.0	9.5	10.1	10.4	10.5	10.7	10.8	11.0
95°	9.0	9.5	10.1	10.3	10.3	10.3	10.3	10.3
97.5°	18.0	14.9	11.9	10.3	10.3	10.3	10.3	10.3
100°	53.0	36.7	20.4	12.1	11.6	11.2	10.8	10.3
102.5°	102.9	99.8	96.8	91.5	84.0	76.6	69.2	61.8
105°	146.4	146.4	146.4	146.4	146.2	146.1	146.0	145.9
107.5°	185.4	185.4	185.4	185.2	184.9	184.6	184.3	183.9
110°	210.6	210.3	209.9	209.8	209.9	210.0	210.2	210.3



TEST NUMBER: P333619-935

CATALOG NUMBER: S125RDIP-S1270D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.6	235.1	234.7	234.5	234.3	234.1	234.0	233.8
115°	273.2	272.8	272.3	271.8	271.1	270.5	269.8	269.2
117.5°	309.6	309.0	308.5	308.1	307.8	307.5	307.2	306.9
120°	333.1	332.9	332.7	332.3	331.7	331.2	330.6	330.1
122.5°	355.5	355.3	355.1	354.6	354.0	353.4	352.8	352.1
125°	388.2	387.7	387.3	386.9	386.6	386.2	386.0	385.6
127.5°	418.0	417.8	417.6	417.1	416.2	415.4	414.7	413.8
130°	437.6	437.2	436.9	436.4	435.9	435.3	434.8	434.3
132.5°	455.7	455.6	455.6	455.3	454.8	454.2	453.7	453.1
135°	482.4	482.2	482.0	481.6	481.0	480.3	479.6	479.0
137.5°	507.3	507.4	507.4	507.1	506.6	506.0	505.5	504.9
140°	522.6	522.8	523.1	522.8	522.2	521.5	520.9	520.2
142.5°	537.6	537.6	537.7	537.4	536.7	536.1	535.4	534.8
145°	558.8	558.9	559.0	558.7	558.0	557.4	556.7	556.0
147.5°	576.9	577.0	577.1	576.8	576.0	575.2	574.5	573.7
150°	588.4	588.7	588.8	588.6	587.7	586.8	585.9	585.0
152.5°	598.7	598.9	599.1	598.8	598.1	597.3	596.4	595.6
155°	612.8	613.0	613.4	613.1	612.3	611.4	610.5	609.6
157.5°	624.4	624.7	625.1	624.8	624.0	623.0	622.2	621.3
160°	631.6	632.1	632.5	632.2	631.4	630.5	629.6	628.8
162.5°	638.3	638.9	639.5	639.3	638.3	637.4	636.5	635.4
165°	646.8	647.5	648.1	648.0	647.1	646.3	645.4	644.5
167.5°	653.2	654.0	654.8	654.7	653.8	652.7	651.8	650.7
170°	656.6	657.5	658.3	658.2	657.3	656.3	655.3	654.4
172.5°	659.1	660.0	660.7	660.6	659.6	658.7	657.6	656.7
175°	661.9	662.8	663.7	663.7	662.7	661.7	660.7	659.7
177.5°	663.1	663.7	664.3	664.3	663.6	662.9	662.2	661.5
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7

(END OF REPORT)