

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333624-935

Luminaire Tested: **S125RDIP-S1270D810U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333624-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D810U935-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6741.8 lumens  
Efficiency: N/A  
Efficacy: 111.1 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63																												
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	58	54																												
2	93	85	79	74	87	80	75	71	71	67	63	62	59	57	54	52	50	46																												
3	85	75	68	62	79	71	65	60	63	58	54	55	52	48	48	46	43	40																												
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	44	40	37	34																												
5	72	60	52	46	67	57	49	44	51	45	40	45	40	36	39	36	33	30																												
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	26																												
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24																												
8	57	45	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21																												
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19																												
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10559	10559	10559	10559
5°	12149	10573	9337	10573
10°	13935	10519	8239	10519
15°	15051	10411	7324	10411
20°	16597	10287	6763	10287
25°	19207	10120	6274	10120
30°	20901	9945	5956	9945
35°	17631	9742	5662	9742
40°	12312	9377	5409	9377
45°	9134	8882	5161	8882
50°	7283	8368	4950	8368
55°	6182	7731	4761	7731
60°	5341	7161	4456	7161
65°	4759	6544	3836	6544
70°	4181	5995	3497	5995
75°	3618	5190	3284	5190
80°	2745	4366	2745	4366
85°	2290	3431	2586	3431



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.8	2.3
10°-20°	459.5	6.8
20°-30°	728.5	10.8
30°-40°	878.5	13.0
40°-50°	784.5	11.6
50°-60°	601.6	8.9
60°-70°	391.0	5.8
70°-80°	190.1	2.8
80°-90°	47.2	0.7
90°-100°	242.0	3.6
100°-110°	520.3	7.7
110°-120°	488.3	7.2
120°-130°	395.7	5.9
130°-140°	317.6	4.7
140°-150°	239.7	3.6
150°-160°	168.7	2.5
160°-170°	99.4	1.5
170°-180°	32.3	0.5
0°-30°	1344.7	19.9
0°-40°	2223.3	33.0
0°-60°	3609.4	53.5
0°-90°	4237.8	62.9
90°-120°	1250.6	18.6
90°-150°	2203.6	32.7
90°-180°	2504.0	37.1
0°-180°	6741.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1635	1635	1635	1635	1635	
5°	1874	1631	1440	1631	1874	187
15°	2251	1557	1095	1557	2251	645
25°	2695	1420	880	1420	2695	1238
35°	2236	1236	718	1236	2236	1351
45°	1000	972	565	972	1000	798
55°	549	687	423	687	549	498
65°	311	428	251	428	311	310
75°	145	208	132	208	145	154
85°	31	46	35	46	31	36
90°	16	1	16	1	16	12
95°	158	22	158	22	158	224
105°	892	76	892	76	892	887
115°	994	136	994	136	994	971
125°	783	188	783	188	783	708
135°	650	221	650	221	650	504
145°	513	257	513	257	513	326
155°	430	294	430	294	430	201
165°	377	320	377	320	377	108
175°	339	333	339	333	339	33
180°	334	334	334	334	334	



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1719.8	1718.7	1720.9	1714.9	1715.5	1706.3	1706.3	1699.4	1690.2	1683.3	1680.1
5°	1873.9	1875.3	1872.5	1862.4	1855.8	1845.7	1834.3	1814.1	1797.3	1781.2	1768.5
7.5°	2032.6	2033.5	2024.6	2021.5	2004.6	1992.3	1966.9	1939.5	1915.2	1884.4	1860.7
10°	2124.9	2124.3	2114.8	2107.5	2092.7	2073.9	2049.1	2016.8	1986.7	1953.1	1920.9
12.5°	2178.6	2176.9	2173.9	2164.9	2151.2	2134.6	2113.5	2081.8	2044.6	2007.9	1970.2
15°	2251.1	2246.3	2237.7	2226.2	2206.7	2187.3	2163.8	2135.6	2100.1	2058.5	2023.5
17.5°	2340.7	2340.9	2327.5	2311.6	2285.2	2250.8	2214.6	2169.0	2120.7	2074.9	2037.8
20°	2414.8	2412.8	2399.4	2368.5	2338.3	2295.3	2253.8	2198.0	2139.0	2079.2	2032.9
22.5°	2521.2	2515.9	2502.0	2461.4	2414.6	2359.2	2295.6	2227.6	2156.2	2088.4	2027.6
25°	2695.4	2691.3	2663.8	2616.8	2551.1	2465.8	2382.6	2289.3	2186.7	2097.4	2023.5
27.5°	2814.6	2810.1	2789.7	2750.7	2690.0	2600.3	2487.7	2363.0	2234.8	2112.0	2005.5
30°	2802.7	2812.8	2810.1	2792.1	2746.4	2665.8	2561.8	2421.6	2269.2	2124.9	1998.0
32.5°	2634.1	2643.2	2666.8	2702.3	2705.0	2672.8	2595.1	2465.6	2307.8	2143.7	1992.1
35°	2236.3	2248.4	2294.0	2365.9	2459.8	2538.3	2554.4	2484.7	2343.0	2166.5	1983.3
37.5°	1719.2	1785.3	1823.7	1899.3	2041.3	2185.7	2324.6	2375.8	2315.5	2157.1	1968.9
40°	1460.4	1476.5	1545.0	1630.2	1749.7	1900.1	2098.1	2241.0	2245.7	2135.6	1946.4
42.5°	1250.0	1270.4	1317.3	1385.4	1487.7	1638.1	1842.5	2031.1	2118.5	2076.6	1916.8
45°	1000.1	1015.5	1049.7	1102.1	1180.6	1304.8	1480.6	1698.7	1871.9	1939.7	1837.6
47.5°	821.5	829.8	859.6	899.5	957.6	1048.1	1184.2	1373.6	1581.2	1726.9	1712.5
50°	724.9	734.3	757.1	787.3	836.3	912.7	1021.5	1179.2	1393.4	1571.2	1606.8
52.5°	649.7	657.5	671.7	700.3	740.7	799.5	887.3	1029.9	1222.6	1411.7	1494.0
55°	549.0	554.4	565.8	581.9	614.2	656.4	732.2	830.9	986.6	1177.2	1298.0
57.5°	466.1	468.7	476.0	490.9	513.2	544.1	598.8	682.4	794.1	965.8	1099.1
60°	413.5	416.1	425.5	435.6	453.1	481.2	524.2	582.6	689.9	831.6	966.5
62.5°	371.5	373.2	377.2	387.3	402.6	424.3	458.1	505.8	591.2	715.6	843.0
65°	311.4	312.1	313.4	321.5	330.9	347.0	369.1	402.7	467.1	561.1	673.8
67.5°	253.7	254.6	259.3	262.2	272.0	280.4	293.4	319.1	364.5	427.8	515.5
70°	221.4	220.8	225.5	228.9	232.2	242.3	251.0	271.8	300.0	348.4	421.5
72.5°	191.4	189.7	191.7	192.9	197.3	204.1	212.9	225.7	247.4	280.7	336.7
75°	145.0	145.7	145.7	147.0	150.3	153.0	155.7	162.4	174.5	196.7	226.9
77.5°	101.8	100.7	103.5	103.9	105.9	108.8	111.2	113.8	118.8	127.9	143.5
80°	73.8	73.8	74.5	76.5	75.9	77.1	80.5	83.3	89.3	94.6	100.0
82.5°	56.7	56.1	56.7	57.2	57.1	58.4	59.6	60.1	62.4	65.1	68.9
85°	30.9	30.9	31.5	31.5	32.2	32.2	32.9	32.9	32.9	33.6	34.3
87.5°	14.9	14.4	13.7	13.7	14.2	15.1	14.4	13.7	13.6	13.4	13.7
90°	15.5	15.5	14.8	14.8	14.8	13.4	12.8	12.1	11.5	10.8	9.4
92.5°	43.0	44.0	44.9	46.6	55.2	65.2	86.6	119.3	175.7	217.1	220.5
95°	158.2	169.0	174.4	194.6	242.4	298.9	381.7	484.1	583.7	596.5	486.7
97.5°	382.4	391.0	410.5	448.2	489.8	568.4	649.1	720.9	738.5	637.0	434.6
100°	525.1	535.9	560.8	609.2	655.7	725.7	795.0	828.0	776.2	608.0	387.8
102.5°	684.5	692.6	719.6	754.1	803.8	851.2	884.5	864.1	753.6	556.7	352.2
105°	892.0	900.1	913.5	935.7	957.3	964.8	935.1	842.8	681.3	488.1	317.8
107.5°	1002.1	1007.5	1011.9	1012.1	1001.2	966.0	890.0	766.9	607.5	440.8	303.2
110°	1038.8	1038.8	1034.1	1021.2	990.9	933.8	838.8	710.9	565.5	418.7	298.9



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1034.5	1029.6	1017.9	995.9	951.7	884.2	788.2	666.8	534.3	405.8	298.9
115°	993.7	984.9	966.0	933.8	881.2	807.9	715.7	611.3	500.2	391.8	300.9
117.5°	922.1	916.8	898.0	864.7	812.2	744.9	665.4	575.5	479.8	385.0	305.4
120°	875.8	870.5	852.3	819.9	770.2	710.9	636.9	556.0	468.6	381.7	309.7
122.5°	834.9	830.1	811.9	782.3	737.9	682.3	616.4	541.6	458.8	379.0	313.4
125°	782.9	776.2	761.4	733.8	696.1	647.6	589.1	520.4	445.7	375.7	319.8
127.5°	738.5	735.6	721.5	697.2	663.0	617.6	562.9	498.9	433.5	374.0	326.9
130°	714.3	710.2	696.8	674.6	640.9	597.1	544.7	485.3	425.5	373.0	331.2
132.5°	690.0	685.4	673.0	650.8	617.2	575.1	527.4	471.9	419.0	373.0	336.0
135°	650.3	646.3	634.1	611.9	582.3	544.0	500.8	454.4	411.3	373.0	342.7
137.5°	608.0	603.5	592.3	572.1	545.5	513.0	477.2	439.6	404.5	373.8	348.7
140°	578.2	574.9	564.8	547.3	522.4	494.1	463.1	431.5	401.2	374.3	351.4
142.5°	550.8	548.0	538.5	523.7	502.5	477.9	451.3	424.6	398.6	374.9	353.0
145°	513.0	510.3	502.9	491.5	475.3	457.1	436.3	415.3	394.5	374.3	354.8
147.5°	481.0	479.7	475.4	466.2	453.5	439.7	423.7	406.7	390.3	372.6	355.4
150°	463.1	462.5	459.8	451.8	441.6	429.5	416.7	401.9	387.1	370.9	355.4
152.5°	449.2	448.5	445.8	439.4	430.8	421.5	409.7	396.5	383.3	368.8	354.9
155°	430.2	429.5	427.5	422.8	416.0	408.6	399.2	388.5	377.0	364.9	353.4
157.5°	413.2	413.4	411.5	407.6	402.3	396.5	389.3	380.4	371.1	360.8	351.7
160°	401.9	402.6	401.2	397.9	393.1	388.5	381.7	375.0	366.3	358.2	350.1
162.5°	391.7	391.8	391.5	388.7	385.0	380.9	375.2	369.0	361.9	354.9	348.4
165°	377.0	377.0	377.0	375.7	373.0	369.6	365.6	360.8	355.4	350.1	346.0
167.5°	363.5	363.7	364.2	363.0	361.6	359.2	356.1	353.0	349.1	345.3	342.2
170°	355.4	356.1	356.1	355.4	354.1	352.8	350.8	348.7	345.3	342.7	340.6
172.5°	347.9	348.6	349.7	348.4	348.2	347.4	345.9	343.9	341.6	339.4	338.5
175°	338.6	339.3	340.6	340.0	340.0	340.0	338.6	338.6	336.6	336.0	336.0
177.5°	333.9	333.9	335.5	335.0	335.5	335.5	335.5	335.0	334.4	333.9	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1680.1	1676.3	1669.3	1662.8	1654.8	1647.9	1643.0	1637.1	1629.6	1620.5	1612.9
5°	1754.4	1739.7	1720.2	1703.4	1682.0	1665.2	1647.7	1630.9	1614.1	1592.7	1573.9
7.5°	1836.9	1806.4	1776.7	1739.4	1705.6	1675.3	1646.3	1617.0	1588.2	1557.7	1528.4
10°	1887.3	1850.4	1809.5	1762.5	1719.5	1678.6	1641.0	1604.0	1565.1	1530.9	1494.0
12.5°	1934.6	1886.9	1840.0	1780.7	1729.1	1679.1	1631.3	1585.3	1543.7	1499.3	1459.7
15°	1977.2	1930.3	1877.9	1805.4	1733.6	1673.2	1616.8	1557.1	1505.4	1455.8	1411.4
17.5°	1993.7	1944.5	1883.7	1814.0	1735.5	1659.5	1586.9	1521.4	1460.6	1402.7	1352.9
20°	1987.3	1939.7	1877.2	1810.8	1726.9	1647.7	1569.2	1496.7	1428.9	1367.8	1314.8
22.5°	1971.8	1922.4	1862.2	1792.0	1712.4	1628.4	1544.5	1467.1	1396.1	1332.9	1275.1
25°	1948.4	1881.3	1819.6	1751.0	1675.2	1592.0	1505.4	1420.1	1344.4	1279.9	1216.9
27.5°	1924.1	1840.3	1761.8	1693.8	1613.6	1539.4	1455.9	1368.5	1288.7	1223.1	1158.4
30°	1902.0	1808.1	1721.5	1644.3	1568.5	1498.1	1418.8	1333.6	1251.7	1184.0	1118.2
32.5°	1874.7	1774.8	1679.6	1590.6	1517.5	1447.6	1375.9	1294.4	1214.7	1144.7	1077.9
35°	1840.3	1712.8	1609.5	1514.8	1433.6	1365.8	1301.4	1235.6	1155.7	1083.2	1018.1
37.5°	1795.2	1650.5	1530.9	1427.8	1342.2	1274.1	1223.2	1163.1	1090.2	1020.8	960.4
40°	1767.8	1605.4	1474.5	1372.5	1282.5	1210.7	1163.1	1112.2	1045.7	980.6	920.2
42.5°	1731.3	1564.1	1417.6	1311.3	1220.8	1151.7	1103.5	1058.9	1003.2	941.9	877.2
45°	1659.7	1483.9	1330.2	1216.2	1124.9	1057.0	1012.1	972.5	930.2	873.8	817.4
47.5°	1566.6	1400.3	1239.5	1114.9	1025.5	962.6	918.9	887.7	857.5	809.5	754.8
50°	1492.0	1331.6	1174.5	1053.7	958.4	898.7	857.7	832.9	805.4	761.7	716.1
52.5°	1403.9	1260.7	1106.9	983.3	893.5	837.5	798.1	773.4	750.6	715.1	671.6
55°	1265.2	1139.6	998.7	886.6	804.1	747.7	710.1	686.6	673.2	643.0	608.7
57.5°	1105.0	1015.0	890.8	782.7	709.7	654.0	626.5	606.5	591.3	570.0	545.8
60°	993.3	930.2	818.8	716.1	649.0	596.0	571.2	554.4	540.3	522.2	503.3
62.5°	880.0	834.1	737.2	649.0	587.3	542.9	519.6	504.5	488.2	476.0	457.7
65°	728.2	687.3	620.2	551.0	494.0	458.4	441.6	428.2	418.1	404.7	391.9
67.5°	566.5	549.8	503.5	455.8	414.9	383.2	368.8	359.4	347.2	339.2	330.5
70°	467.1	459.1	426.2	394.7	356.4	334.9	321.5	317.5	302.7	294.6	288.6
72.5°	379.1	375.3	356.4	334.5	307.5	288.7	276.4	271.8	262.4	256.0	252.1
75°	259.8	261.1	257.7	243.7	233.6	221.4	210.8	208.0	201.4	196.0	192.6
77.5°	164.3	171.2	171.4	170.7	166.7	159.4	154.9	152.9	146.3	144.3	143.5
80°	112.8	120.1	126.8	126.1	124.8	122.9	119.5	117.4	114.1	112.1	110.7
82.5°	75.2	82.1	87.6	91.3	91.0	89.0	86.7	85.8	85.1	83.6	83.3
85°	35.6	36.9	38.9	43.7	47.0	47.6	47.0	46.3	44.3	44.9	45.6
87.5°	14.1	13.9	14.2	13.9	13.2	15.6	16.9	17.3	16.4	15.6	14.8
90°	8.8	7.4	6.7	5.4	4.0	2.7	1.4	0.7	1.4	2.7	4.0
92.5°	153.6	92.0	55.2	35.6	23.9	15.6	10.0	8.2	10.0	15.6	23.9
95°	300.9	152.8	80.8	50.5	35.6	28.2	22.9	22.2	22.9	28.2	35.6
97.5°	240.2	131.6	84.0	62.2	48.9	41.5	37.7	36.9	37.7	41.5	48.9
100°	218.1	130.6	91.5	71.4	58.5	51.1	48.5	47.1	48.5	51.1	58.5
102.5°	209.0	135.4	100.7	81.0	69.3	61.4	59.2	58.5	59.2	61.4	69.3
105°	205.3	145.4	115.8	96.9	86.2	79.5	76.1	76.1	76.1	79.5	86.2
107.5°	211.5	160.2	131.6	114.6	103.4	97.9	94.6	93.3	94.6	97.9	103.4
110°	217.5	171.0	143.4	125.9	115.8	109.7	107.0	105.7	107.0	109.7	115.8





TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	225.0	181.2	154.7	137.8	127.6	121.6	119.4	118.0	119.4	121.6	127.6
115°	236.3	197.3	172.4	155.5	145.4	139.4	137.3	136.0	137.3	139.4	145.4
117.5°	249.3	213.7	190.1	173.8	162.4	156.4	154.2	152.1	154.2	156.4	162.4
120°	257.9	225.5	202.0	185.1	173.7	167.6	165.0	162.9	165.0	167.6	173.7
122.5°	267.5	236.9	213.3	196.5	183.9	177.9	175.7	174.3	175.7	177.9	183.9
125°	280.7	251.8	229.5	212.1	199.2	193.2	189.9	188.5	189.9	193.2	199.2
127.5°	292.8	266.2	244.8	227.3	213.7	206.0	201.7	199.7	201.7	206.0	213.7
130°	300.9	275.3	254.5	236.9	222.8	214.0	208.7	206.6	208.7	214.0	222.8
132.5°	307.9	284.0	263.1	245.6	230.9	221.1	214.6	212.1	214.6	221.1	230.9
135°	317.8	295.6	274.7	256.5	242.4	231.6	223.5	220.8	223.5	231.6	242.4
137.5°	325.0	303.8	284.7	266.0	252.2	241.4	233.8	231.9	233.8	241.4	252.2
140°	329.8	309.7	290.2	272.0	259.2	248.4	240.3	238.3	240.3	248.4	259.2
142.5°	332.6	313.4	295.0	277.9	265.6	254.9	247.4	245.8	247.4	254.9	265.6
145°	336.6	319.8	302.3	286.8	274.7	265.3	258.5	257.2	258.5	265.3	274.7
147.5°	339.1	323.8	308.5	294.9	284.4	275.6	269.8	269.0	269.8	275.6	284.4
150°	340.6	326.5	311.7	300.2	290.8	282.1	277.3	276.0	277.3	282.1	290.8
152.5°	341.7	329.2	315.5	305.1	296.2	288.5	284.4	283.5	284.4	288.5	296.2
155°	342.7	331.9	320.5	311.0	304.3	297.6	293.5	293.5	293.5	297.6	304.3
157.5°	343.4	334.2	324.3	317.2	311.3	305.5	302.3	302.4	302.3	305.5	311.3
160°	343.4	335.3	326.5	320.5	315.0	310.4	307.6	308.3	307.6	310.4	315.0
162.5°	342.8	336.3	328.6	323.6	319.3	315.2	312.5	313.1	312.5	315.2	319.3
165°	342.0	336.6	331.2	327.2	324.5	321.2	319.1	320.5	319.1	321.2	324.5
167.5°	340.4	336.6	332.2	329.6	327.7	325.8	324.6	325.3	324.6	325.8	327.7
170°	339.3	336.6	333.2	331.2	329.8	328.6	327.9	328.6	327.9	328.6	329.8
172.5°	338.2	336.0	333.2	332.3	331.5	330.1	329.5	330.7	329.5	330.1	331.5
175°	336.6	335.3	333.2	333.2	333.2	332.6	331.9	333.2	331.9	332.6	333.2
177.5°	335.0	334.4	333.4	333.4	333.9	333.4	333.4	334.4	333.4	333.4	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1607.6	1600.1	1594.7	1583.9	1576.4	1573.2	1567.3	1565.6	1571.6	1567.3	1566.8
5°	1559.8	1540.3	1524.9	1509.4	1492.6	1482.0	1465.9	1463.1	1459.1	1453.0	1451.7
7.5°	1502.4	1477.1	1457.2	1431.8	1409.5	1391.7	1371.6	1362.0	1356.8	1349.0	1338.6
10°	1463.8	1433.6	1406.8	1381.2	1353.8	1331.6	1311.5	1296.0	1285.9	1276.5	1272.6
12.5°	1425.6	1394.9	1360.6	1329.7	1299.0	1274.1	1251.8	1241.8	1230.6	1219.6	1210.2
15°	1366.5	1325.5	1288.0	1252.4	1226.2	1199.4	1177.8	1163.1	1146.3	1141.7	1123.5
17.5°	1303.6	1263.5	1219.5	1182.1	1151.7	1122.1	1098.5	1081.8	1069.2	1051.9	1043.5
20°	1264.5	1216.9	1173.9	1139.6	1106.0	1071.2	1047.0	1032.9	1020.8	1006.8	1000.1
22.5°	1222.6	1176.0	1132.0	1091.8	1057.7	1023.4	1006.2	991.6	977.8	964.8	956.0
25°	1161.1	1114.1	1067.8	1026.2	990.7	965.8	945.6	928.8	921.5	908.8	899.3
27.5°	1100.3	1050.3	1002.3	960.8	932.9	908.4	891.8	878.6	865.2	854.1	845.9
30°	1061.1	1010.1	957.8	924.9	895.4	871.8	853.7	840.9	830.9	820.8	814.8
32.5°	1021.9	969.3	922.8	887.3	859.4	839.0	820.4	808.2	797.6	786.4	779.4
35°	959.1	905.4	867.8	832.9	805.4	786.6	773.9	756.4	747.7	739.6	732.2
37.5°	900.7	850.8	810.1	779.5	755.6	736.9	720.4	711.0	700.3	693.0	686.9
40°	857.7	812.1	775.2	743.0	725.6	704.7	689.3	677.2	669.2	659.8	653.1
42.5°	819.1	776.7	740.8	711.9	690.1	672.5	657.6	645.5	635.3	628.6	622.9
45°	764.5	722.2	687.3	660.4	640.3	623.5	608.0	602.0	588.6	580.6	577.9
47.5°	707.9	670.1	636.4	611.7	591.0	575.1	560.7	548.4	541.0	533.0	528.7
50°	669.9	633.6	602.0	577.9	557.8	540.3	526.8	518.8	508.8	501.4	496.0
52.5°	631.7	598.1	566.6	543.5	526.1	508.6	493.6	485.5	476.0	471.3	467.5
55°	577.2	541.7	514.8	492.0	473.8	457.7	443.7	435.6	429.6	424.8	423.5
57.5°	515.5	487.2	462.3	441.8	422.9	407.8	395.5	387.8	382.5	381.8	377.7
60°	475.2	449.7	426.9	404.7	388.6	374.5	363.8	355.1	349.7	349.0	347.7
62.5°	434.9	410.4	389.3	369.8	355.3	341.7	331.6	321.8	318.6	315.2	312.2
65°	375.1	353.0	335.6	320.1	304.7	293.3	283.3	277.2	269.8	265.8	258.4
67.5°	316.5	299.4	282.6	269.6	257.4	246.6	238.2	229.3	224.3	221.1	215.7
70°	277.8	264.4	247.6	233.6	224.2	215.4	208.7	198.6	195.3	192.6	189.9
72.5°	241.3	229.5	215.4	204.1	194.7	186.4	178.7	173.9	170.7	167.9	166.3
75°	189.9	178.6	166.4	158.4	151.7	145.0	140.9	137.6	136.2	135.6	132.9
77.5°	139.5	133.5	123.7	117.4	112.9	110.2	106.6	104.9	104.7	101.8	100.8
80°	106.7	103.3	95.3	92.6	89.3	86.6	84.6	81.2	77.8	76.5	74.5
82.5°	79.3	75.9	72.8	68.4	65.6	64.1	62.0	60.8	61.2	59.3	58.4
85°	42.3	38.9	37.6	36.9	35.6	36.9	36.2	35.6	34.9	34.3	34.9
87.5°	14.5	14.8	14.4	15.7	14.2	15.1	15.2	14.8	14.9	15.1	14.8
90°	5.4	6.7	7.4	8.8	9.4	10.8	11.5	12.1	12.8	13.4	14.8
92.5°	35.6	55.2	92.0	153.6	220.5	217.1	175.7	119.3	86.6	65.2	55.2
95°	50.5	80.8	152.8	300.9	486.7	596.5	583.7	484.1	381.7	298.9	242.4
97.5°	62.2	84.0	131.6	240.2	434.6	637.0	738.5	720.9	649.1	568.4	489.8
100°	71.4	91.5	130.6	218.1	387.8	608.0	776.2	828.0	795.0	725.7	655.7
102.5°	81.0	100.7	135.4	209.0	352.2	556.7	753.6	864.1	884.5	851.2	803.8
105°	96.9	115.8	145.4	205.3	317.8	488.1	681.3	842.8	935.1	964.8	957.3
107.5°	114.6	131.6	160.2	211.5	303.2	440.8	607.5	766.9	890.0	966.0	1001.2
110°	125.9	143.4	171.0	217.5	298.9	418.7	565.5	710.9	838.8	933.8	990.9



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	137.8	154.7	181.2	225.0	298.9	405.8	534.3	666.8	788.2	884.2	951.7
115°	155.5	172.4	197.3	236.3	300.9	391.8	500.2	611.3	715.7	807.9	881.2
117.5°	173.8	190.1	213.7	249.3	305.4	385.0	479.8	575.5	665.4	744.9	812.2
120°	185.1	202.0	225.5	257.9	309.7	381.7	468.6	556.0	636.9	710.9	770.2
122.5°	196.5	213.3	236.9	267.5	313.4	379.0	458.8	541.6	616.4	682.3	737.9
125°	212.1	229.5	251.8	280.7	319.8	375.7	445.7	520.4	589.1	647.6	696.1
127.5°	227.3	244.8	266.2	292.8	326.9	374.0	433.5	498.9	562.9	617.6	663.0
130°	236.9	254.5	275.3	300.9	331.2	373.0	425.5	485.3	544.7	597.1	640.9
132.5°	245.6	263.1	284.0	307.9	336.0	373.0	419.0	471.9	527.4	575.1	617.2
135°	256.5	274.7	295.6	317.8	342.7	373.0	411.3	454.4	500.8	544.0	582.3
137.5°	266.0	284.7	303.8	325.0	348.7	373.8	404.5	439.6	477.2	513.0	545.5
140°	272.0	290.2	309.7	329.8	351.4	374.3	401.2	431.5	463.1	494.1	522.4
142.5°	277.9	295.0	313.4	332.6	353.0	374.9	398.6	424.6	451.3	477.9	502.5
145°	286.8	302.3	319.8	336.6	354.8	374.3	394.5	415.3	436.3	457.1	475.3
147.5°	294.9	308.5	323.8	339.1	355.4	372.6	390.3	406.7	423.7	439.7	453.5
150°	300.2	311.7	326.5	340.6	355.4	370.9	387.1	401.9	416.7	429.5	441.6
152.5°	305.1	315.5	329.2	341.7	354.9	368.8	383.3	396.5	409.7	421.5	430.8
155°	311.0	320.5	331.9	342.7	353.4	364.9	377.0	388.5	399.2	408.6	416.0
157.5°	317.2	324.3	334.2	343.4	351.7	360.8	371.1	380.4	389.3	396.5	402.3
160°	320.5	326.5	335.3	343.4	350.1	358.2	366.3	375.0	381.7	388.5	393.1
162.5°	323.6	328.6	336.3	342.8	348.4	354.9	361.9	369.0	375.2	380.9	385.0
165°	327.2	331.2	336.6	342.0	346.0	350.1	355.4	360.8	365.6	369.6	373.0
167.5°	329.6	332.2	336.6	340.4	342.2	345.3	349.1	353.0	356.1	359.2	361.6
170°	331.2	333.2	336.6	339.3	340.6	342.7	345.3	348.7	350.8	352.8	354.1
172.5°	332.3	333.2	336.0	338.2	338.5	339.4	341.6	343.9	345.9	347.4	348.2
175°	333.2	333.2	335.3	336.6	336.0	336.0	336.6	338.6	338.6	340.0	340.0
177.5°	333.4	333.4	334.4	335.0	333.9	333.9	334.4	335.0	335.5	335.5	335.5
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1566.2	1560.3	1558.7	1560.8	1558.7	1560.3	1566.2	1566.8	1567.3	1571.6	1565.6
5°	1445.0	1438.3	1441.7	1440.3	1441.7	1438.3	1445.0	1451.7	1453.0	1459.1	1463.1
7.5°	1338.4	1330.1	1321.2	1324.0	1321.2	1330.1	1338.4	1338.6	1349.0	1356.8	1362.0
10°	1263.8	1257.1	1253.0	1256.4	1253.0	1257.1	1263.8	1272.6	1276.5	1285.9	1296.0
12.5°	1201.0	1197.0	1193.4	1192.0	1193.4	1197.0	1201.0	1210.2	1219.6	1230.6	1241.8
15°	1115.4	1107.4	1104.1	1095.4	1104.1	1107.4	1115.4	1123.5	1141.7	1146.3	1163.1
17.5°	1036.6	1034.0	1025.3	1021.5	1025.3	1034.0	1036.6	1043.5	1051.9	1069.2	1081.8
20°	990.0	987.3	978.5	984.0	978.5	987.3	990.0	1000.1	1006.8	1020.8	1032.9
22.5°	951.3	945.4	942.5	941.0	942.5	945.4	951.3	956.0	964.8	977.8	991.6
25°	896.6	887.9	884.6	880.5	884.6	887.9	896.6	899.3	908.8	921.5	928.8
27.5°	842.1	837.5	833.0	832.0	833.0	837.5	842.1	845.9	854.1	865.2	878.6
30°	806.8	802.0	798.7	798.7	798.7	802.0	806.8	814.8	820.8	830.9	840.9
32.5°	775.1	771.5	768.1	767.6	768.1	771.5	775.1	779.4	786.4	797.6	808.2
35°	728.9	723.5	722.2	718.2	722.2	723.5	728.9	732.2	739.6	747.7	756.4
37.5°	681.0	676.5	676.4	676.0	676.4	676.5	681.0	686.9	693.0	700.3	711.0
40°	650.3	647.0	646.4	641.6	646.4	647.0	650.3	653.1	659.8	669.2	677.2
42.5°	617.6	615.9	613.5	611.6	613.5	615.9	617.6	622.9	628.6	635.3	645.5
45°	573.2	568.4	568.4	565.1	568.4	568.4	573.2	577.9	580.6	588.6	602.0
47.5°	527.3	523.7	524.0	520.6	524.0	523.7	527.3	528.7	533.0	541.0	548.4
50°	496.6	494.6	494.0	492.7	494.0	494.6	496.6	496.0	501.4	508.8	518.8
52.5°	466.1	465.1	467.7	464.7	467.7	465.1	466.1	467.5	471.3	476.0	485.5
55°	424.8	422.8	426.9	422.8	426.9	422.8	424.8	423.5	424.8	429.6	435.6
57.5°	377.5	375.6	379.2	377.2	379.2	375.6	377.5	377.7	381.8	382.5	387.8
60°	346.3	342.3	344.3	345.0	344.3	342.3	346.3	347.7	349.0	349.7	355.1
62.5°	309.3	306.9	308.3	305.2	308.3	306.9	309.3	312.2	315.2	318.6	321.8
65°	257.1	255.0	252.4	251.0	252.4	255.0	257.1	258.4	265.8	269.8	277.2
67.5°	215.9	211.1	211.0	212.1	211.0	211.1	215.9	215.7	221.1	224.3	229.3
70°	185.9	185.9	185.2	185.2	185.2	185.9	185.9	189.9	192.6	195.3	198.6
72.5°	165.0	164.5	163.2	162.7	163.2	164.5	165.0	166.3	167.9	170.7	173.9
75°	132.9	133.5	132.2	131.6	132.2	133.5	132.9	132.9	135.6	136.2	137.6
77.5°	98.2	95.3	96.8	95.3	96.8	95.3	98.2	100.8	101.8	104.7	104.9
80°	74.5	73.8	75.9	73.8	75.9	73.8	74.5	74.5	76.5	77.8	81.2
82.5°	58.9	58.3	59.2	57.7	59.2	58.3	58.9	58.4	59.3	61.2	60.8
85°	35.6	34.9	34.3	34.9	34.3	34.9	35.6	34.9	34.3	34.9	35.6
87.5°	15.3	14.8	14.9	14.9	14.9	14.8	15.3	14.8	15.1	14.9	14.8
90°	14.8	14.8	15.5	15.5	15.5	14.8	14.8	14.8	13.4	12.8	12.1
92.5°	46.6	44.9	44.0	43.0	44.0	44.9	46.6	55.2	65.2	86.6	119.3
95°	194.6	174.4	169.0	158.2	169.0	174.4	194.6	242.4	298.9	381.7	484.1
97.5°	448.2	410.5	391.0	382.4	391.0	410.5	448.2	489.8	568.4	649.1	720.9
100°	609.2	560.8	535.9	525.1	535.9	560.8	609.2	655.7	725.7	795.0	828.0
102.5°	754.1	719.6	692.6	684.5	692.6	719.6	754.1	803.8	851.2	884.5	864.1
105°	935.7	913.5	900.1	892.0	900.1	913.5	935.7	957.3	964.8	935.1	842.8
107.5°	1012.1	1011.9	1007.5	1002.1	1007.5	1011.9	1012.1	1001.2	966.0	890.0	766.9
110°	1021.2	1034.1	1038.8	1038.8	1038.8	1034.1	1021.2	990.9	933.8	838.8	710.9



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	995.9	1017.9	1029.6	1034.5	1029.6	1017.9	995.9	951.7	884.2	788.2	666.8
115°	933.8	966.0	984.9	993.7	984.9	966.0	933.8	881.2	807.9	715.7	611.3
117.5°	864.7	898.0	916.8	922.1	916.8	898.0	864.7	812.2	744.9	665.4	575.5
120°	819.9	852.3	870.5	875.8	870.5	852.3	819.9	770.2	710.9	636.9	556.0
122.5°	782.3	811.9	830.1	834.9	830.1	811.9	782.3	737.9	682.3	616.4	541.6
125°	733.8	761.4	776.2	782.9	776.2	761.4	733.8	696.1	647.6	589.1	520.4
127.5°	697.2	721.5	735.6	738.5	735.6	721.5	697.2	663.0	617.6	562.9	498.9
130°	674.6	696.8	710.2	714.3	710.2	696.8	674.6	640.9	597.1	544.7	485.3
132.5°	650.8	673.0	685.4	690.0	685.4	673.0	650.8	617.2	575.1	527.4	471.9
135°	611.9	634.1	646.3	650.3	646.3	634.1	611.9	582.3	544.0	500.8	454.4
137.5°	572.1	592.3	603.5	608.0	603.5	592.3	572.1	545.5	513.0	477.2	439.6
140°	547.3	564.8	574.9	578.2	574.9	564.8	547.3	522.4	494.1	463.1	431.5
142.5°	523.7	538.5	548.0	550.8	548.0	538.5	523.7	502.5	477.9	451.3	424.6
145°	491.5	502.9	510.3	513.0	510.3	502.9	491.5	475.3	457.1	436.3	415.3
147.5°	466.2	475.4	479.7	481.0	479.7	475.4	466.2	453.5	439.7	423.7	406.7
150°	451.8	459.8	462.5	463.1	462.5	459.8	451.8	441.6	429.5	416.7	401.9
152.5°	439.4	445.8	448.5	449.2	448.5	445.8	439.4	430.8	421.5	409.7	396.5
155°	422.8	427.5	429.5	430.2	429.5	427.5	422.8	416.0	408.6	399.2	388.5
157.5°	407.6	411.5	413.4	413.2	413.4	411.5	407.6	402.3	396.5	389.3	380.4
160°	397.9	401.2	402.6	401.9	402.6	401.2	397.9	393.1	388.5	381.7	375.0
162.5°	388.7	391.5	391.8	391.7	391.8	391.5	388.7	385.0	380.9	375.2	369.0
165°	375.7	377.0	377.0	377.0	377.0	377.0	375.7	373.0	369.6	365.6	360.8
167.5°	363.0	364.2	363.7	363.5	363.7	364.2	363.0	361.6	359.2	356.1	353.0
170°	355.4	356.1	356.1	355.4	356.1	356.1	355.4	354.1	352.8	350.8	348.7
172.5°	348.4	349.7	348.6	347.9	348.6	349.7	348.4	348.2	347.4	345.9	343.9
175°	340.0	340.6	339.3	338.6	339.3	340.6	340.0	340.0	340.0	338.6	338.6
177.5°	335.0	335.5	333.9	333.9	333.9	335.5	335.0	335.5	335.5	335.5	335.0
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1567.3	1573.2	1576.4	1583.9	1594.7	1600.1	1607.6	1612.9	1620.5	1629.6	1637.1
5°	1465.9	1482.0	1492.6	1509.4	1524.9	1540.3	1559.8	1573.9	1592.7	1614.1	1630.9
7.5°	1371.6	1391.7	1409.5	1431.8	1457.2	1477.1	1502.4	1528.4	1557.7	1588.2	1617.0
10°	1311.5	1331.6	1353.8	1381.2	1406.8	1433.6	1463.8	1494.0	1530.9	1565.1	1604.0
12.5°	1251.8	1274.1	1299.0	1329.7	1360.6	1394.9	1425.6	1459.7	1499.3	1543.7	1585.3
15°	1177.8	1199.4	1226.2	1252.4	1288.0	1325.5	1366.5	1411.4	1455.8	1505.4	1557.1
17.5°	1098.5	1122.1	1151.7	1182.1	1219.5	1263.5	1303.6	1352.9	1402.7	1460.6	1521.4
20°	1047.0	1071.2	1106.0	1139.6	1173.9	1216.9	1264.5	1314.8	1367.8	1428.9	1496.7
22.5°	1006.2	1023.4	1057.7	1091.8	1132.0	1176.0	1222.6	1275.1	1332.9	1396.1	1467.1
25°	945.6	965.8	990.7	1026.2	1067.8	1114.1	1161.1	1216.9	1279.9	1344.4	1420.1
27.5°	891.8	908.4	932.9	960.8	1002.3	1050.3	1100.3	1158.4	1223.1	1288.7	1368.5
30°	853.7	871.8	895.4	924.9	957.8	1010.1	1061.1	1118.2	1184.0	1251.7	1333.6
32.5°	820.4	839.0	859.4	887.3	922.8	969.3	1021.9	1077.9	1144.7	1214.7	1294.4
35°	773.9	786.6	805.4	832.9	867.8	905.4	959.1	1018.1	1083.2	1155.7	1235.6
37.5°	720.4	736.9	755.6	779.5	810.1	850.8	900.7	960.4	1020.8	1090.2	1163.1
40°	689.3	704.7	725.6	743.0	775.2	812.1	857.7	920.2	980.6	1045.7	1112.2
42.5°	657.6	672.5	690.1	711.9	740.8	776.7	819.1	877.2	941.9	1003.2	1058.9
45°	608.0	623.5	640.3	660.4	687.3	722.2	764.5	817.4	873.8	930.2	972.5
47.5°	560.7	575.1	591.0	611.7	636.4	670.1	707.9	754.8	809.5	857.5	887.7
50°	526.8	540.3	557.8	577.9	602.0	633.6	669.9	716.1	761.7	805.4	832.9
52.5°	493.6	508.6	526.1	543.5	566.6	598.1	631.7	671.6	715.1	750.6	773.4
55°	443.7	457.7	473.8	492.0	514.8	541.7	577.2	608.7	643.0	673.2	686.6
57.5°	395.5	407.8	422.9	441.8	462.3	487.2	515.5	545.8	570.0	591.3	606.5
60°	363.8	374.5	388.6	404.7	426.9	449.7	475.2	503.3	522.2	540.3	554.4
62.5°	331.6	341.7	355.3	369.8	389.3	410.4	434.9	457.7	476.0	488.2	504.5
65°	283.3	293.3	304.7	320.1	335.6	353.0	375.1	391.9	404.7	418.1	428.2
67.5°	238.2	246.6	257.4	269.6	282.6	299.4	316.5	330.5	339.2	347.2	359.4
70°	208.7	215.4	224.2	233.6	247.6	264.4	277.8	288.6	294.6	302.7	317.5
72.5°	178.7	186.4	194.7	204.1	215.4	229.5	241.3	252.1	256.0	262.4	271.8
75°	140.9	145.0	151.7	158.4	166.4	178.6	189.9	192.6	196.0	201.4	208.0
77.5°	106.6	110.2	112.9	117.4	123.7	133.5	139.5	143.5	144.3	146.3	152.9
80°	84.6	86.6	89.3	92.6	95.3	103.3	106.7	110.7	112.1	114.1	117.4
82.5°	62.0	64.1	65.6	68.4	72.8	75.9	79.3	83.3	83.6	85.1	85.8
85°	36.2	36.9	35.6	36.9	37.6	38.9	42.3	45.6	44.9	44.3	46.3
87.5°	15.2	15.1	14.2	15.7	14.4	14.8	14.5	14.8	15.6	16.4	17.3
90°	11.5	10.8	9.4	8.8	7.4	6.7	5.4	4.0	2.7	1.4	0.7
92.5°	175.7	217.1	220.5	153.6	92.0	55.2	35.6	23.9	15.6	10.0	8.2
95°	583.7	596.5	486.7	300.9	152.8	80.8	50.5	35.6	28.2	22.9	22.2
97.5°	738.5	637.0	434.6	240.2	131.6	84.0	62.2	48.9	41.5	37.7	36.9
100°	776.2	608.0	387.8	218.1	130.6	91.5	71.4	58.5	51.1	48.5	47.1
102.5°	753.6	556.7	352.2	209.0	135.4	100.7	81.0	69.3	61.4	59.2	58.5
105°	681.3	488.1	317.8	205.3	145.4	115.8	96.9	86.2	79.5	76.1	76.1
107.5°	607.5	440.8	303.2	211.5	160.2	131.6	114.6	103.4	97.9	94.6	93.3
110°	565.5	418.7	298.9	217.5	171.0	143.4	125.9	115.8	109.7	107.0	105.7



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	534.3	405.8	298.9	225.0	181.2	154.7	137.8	127.6	121.6	119.4	118.0
115°	500.2	391.8	300.9	236.3	197.3	172.4	155.5	145.4	139.4	137.3	136.0
117.5°	479.8	385.0	305.4	249.3	213.7	190.1	173.8	162.4	156.4	154.2	152.1
120°	468.6	381.7	309.7	257.9	225.5	202.0	185.1	173.7	167.6	165.0	162.9
122.5°	458.8	379.0	313.4	267.5	236.9	213.3	196.5	183.9	177.9	175.7	174.3
125°	445.7	375.7	319.8	280.7	251.8	229.5	212.1	199.2	193.2	189.9	188.5
127.5°	433.5	374.0	326.9	292.8	266.2	244.8	227.3	213.7	206.0	201.7	199.7
130°	425.5	373.0	331.2	300.9	275.3	254.5	236.9	222.8	214.0	208.7	206.6
132.5°	419.0	373.0	336.0	307.9	284.0	263.1	245.6	230.9	221.1	214.6	212.1
135°	411.3	373.0	342.7	317.8	295.6	274.7	256.5	242.4	231.6	223.5	220.8
137.5°	404.5	373.8	348.7	325.0	303.8	284.7	266.0	252.2	241.4	233.8	231.9
140°	401.2	374.3	351.4	329.8	309.7	290.2	272.0	259.2	248.4	240.3	238.3
142.5°	398.6	374.9	353.0	332.6	313.4	295.0	277.9	265.6	254.9	247.4	245.8
145°	394.5	374.3	354.8	336.6	319.8	302.3	286.8	274.7	265.3	258.5	257.2
147.5°	390.3	372.6	355.4	339.1	323.8	308.5	294.9	284.4	275.6	269.8	269.0
150°	387.1	370.9	355.4	340.6	326.5	311.7	300.2	290.8	282.1	277.3	276.0
152.5°	383.3	368.8	354.9	341.7	329.2	315.5	305.1	296.2	288.5	284.4	283.5
155°	377.0	364.9	353.4	342.7	331.9	320.5	311.0	304.3	297.6	293.5	293.5
157.5°	371.1	360.8	351.7	343.4	334.2	324.3	317.2	311.3	305.5	302.3	302.4
160°	366.3	358.2	350.1	343.4	335.3	326.5	320.5	315.0	310.4	307.6	308.3
162.5°	361.9	354.9	348.4	342.8	336.3	328.6	323.6	319.3	315.2	312.5	313.1
165°	355.4	350.1	346.0	342.0	336.6	331.2	327.2	324.5	321.2	319.1	320.5
167.5°	349.1	345.3	342.2	340.4	336.6	332.2	329.6	327.7	325.8	324.6	325.3
170°	345.3	342.7	340.6	339.3	336.6	333.2	331.2	329.8	328.6	327.9	328.6
172.5°	341.6	339.4	338.5	338.2	336.0	333.2	332.3	331.5	330.1	329.5	330.7
175°	336.6	336.0	336.0	336.6	335.3	333.2	333.2	333.2	332.6	331.9	333.2
177.5°	334.4	333.9	333.9	335.0	334.4	333.4	333.4	333.9	333.4	333.4	334.4
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1643.0	1647.9	1654.8	1662.8	1669.3	1676.3	1680.1	1680.1	1683.3	1690.2	1699.4
5°	1647.7	1665.2	1682.0	1703.4	1720.2	1739.7	1754.4	1768.5	1781.2	1797.3	1814.1
7.5°	1646.3	1675.3	1705.6	1739.4	1776.7	1806.4	1836.9	1860.7	1884.4	1915.2	1939.5
10°	1641.0	1678.6	1719.5	1762.5	1809.5	1850.4	1887.3	1920.9	1953.1	1986.7	2016.8
12.5°	1631.3	1679.1	1729.1	1780.7	1840.0	1886.9	1934.6	1970.2	2007.9	2044.6	2081.8
15°	1616.8	1673.2	1733.6	1805.4	1877.9	1930.3	1977.2	2023.5	2058.5	2100.1	2135.6
17.5°	1586.9	1659.5	1735.5	1814.0	1883.7	1944.5	1993.7	2037.8	2074.9	2120.7	2169.0
20°	1569.2	1647.7	1726.9	1810.8	1877.2	1939.7	1987.3	2032.9	2079.2	2139.0	2198.0
22.5°	1544.5	1628.4	1712.4	1792.0	1862.2	1922.4	1971.8	2027.6	2088.4	2156.2	2227.6
25°	1505.4	1592.0	1675.2	1751.0	1819.6	1881.3	1948.4	2023.5	2097.4	2186.7	2289.3
27.5°	1455.9	1539.4	1613.6	1693.8	1761.8	1840.3	1924.1	2005.5	2112.0	2234.8	2363.0
30°	1418.8	1498.1	1568.5	1644.3	1721.5	1808.1	1902.0	1998.0	2124.9	2269.2	2421.6
32.5°	1375.9	1447.6	1517.5	1590.6	1679.6	1774.8	1874.7	1992.1	2143.7	2307.8	2465.6
35°	1301.4	1365.8	1433.6	1514.8	1609.5	1712.8	1840.3	1983.3	2166.5	2343.0	2484.7
37.5°	1223.2	1274.1	1342.2	1427.8	1530.9	1650.5	1795.2	1968.9	2157.1	2315.5	2375.8
40°	1163.1	1210.7	1282.5	1372.5	1474.5	1605.4	1767.8	1946.4	2135.6	2245.7	2241.0
42.5°	1103.5	1151.7	1220.8	1311.3	1417.6	1564.1	1731.3	1916.8	2076.6	2118.5	2031.1
45°	1012.1	1057.0	1124.9	1216.2	1330.2	1483.9	1659.7	1837.6	1939.7	1871.9	1698.7
47.5°	918.9	962.6	1025.5	1114.9	1239.5	1400.3	1566.6	1712.5	1726.9	1581.2	1373.6
50°	857.7	898.7	958.4	1053.7	1174.5	1331.6	1492.0	1606.8	1571.2	1393.4	1179.2
52.5°	798.1	837.5	893.5	983.3	1106.9	1260.7	1403.9	1494.0	1411.7	1222.6	1029.9
55°	710.1	747.7	804.1	886.6	998.7	1139.6	1265.2	1298.0	1177.2	986.6	830.9
57.5°	626.5	654.0	709.7	782.7	890.8	1015.0	1105.0	1099.1	965.8	794.1	682.4
60°	571.2	596.0	649.0	716.1	818.8	930.2	993.3	966.5	831.6	689.9	582.6
62.5°	519.6	542.9	587.3	649.0	737.2	834.1	880.0	843.0	715.6	591.2	505.8
65°	441.6	458.4	494.0	551.0	620.2	687.3	728.2	673.8	561.1	467.1	402.7
67.5°	368.8	383.2	414.9	455.8	503.5	549.8	566.5	515.5	427.8	364.5	319.1
70°	321.5	334.9	356.4	394.7	426.2	459.1	467.1	421.5	348.4	300.0	271.8
72.5°	276.4	288.7	307.5	334.5	356.4	375.3	379.1	336.7	280.7	247.4	225.7
75°	210.8	221.4	233.6	243.7	257.7	261.1	259.8	226.9	196.7	174.5	162.4
77.5°	154.9	159.4	166.7	170.7	171.4	171.2	164.3	143.5	127.9	118.8	113.8
80°	119.5	122.9	124.8	126.1	126.8	120.1	112.8	100.0	94.6	89.3	83.3
82.5°	86.7	89.0	91.0	91.3	87.6	82.1	75.2	68.9	65.1	62.4	60.1
85°	47.0	47.6	47.0	43.7	38.9	36.9	35.6	34.3	33.6	32.9	32.9
87.5°	16.9	15.6	13.2	13.9	14.2	13.9	14.1	13.7	13.4	13.6	13.7
90°	1.4	2.7	4.0	5.4	6.7	7.4	8.8	9.4	10.8	11.5	12.1
92.5°	10.0	15.6	23.9	35.6	55.2	92.0	153.6	220.5	217.1	175.7	119.3
95°	22.9	28.2	35.6	50.5	80.8	152.8	300.9	486.7	596.5	583.7	484.1
97.5°	37.7	41.5	48.9	62.2	84.0	131.6	240.2	434.6	637.0	738.5	720.9
100°	48.5	51.1	58.5	71.4	91.5	130.6	218.1	387.8	608.0	776.2	828.0
102.5°	59.2	61.4	69.3	81.0	100.7	135.4	209.0	352.2	556.7	753.6	864.1
105°	76.1	79.5	86.2	96.9	115.8	145.4	205.3	317.8	488.1	681.3	842.8
107.5°	94.6	97.9	103.4	114.6	131.6	160.2	211.5	303.2	440.8	607.5	766.9
110°	107.0	109.7	115.8	125.9	143.4	171.0	217.5	298.9	418.7	565.5	710.9





TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	119.4	121.6	127.6	137.8	154.7	181.2	225.0	298.9	405.8	534.3	666.8
115°	137.3	139.4	145.4	155.5	172.4	197.3	236.3	300.9	391.8	500.2	611.3
117.5°	154.2	156.4	162.4	173.8	190.1	213.7	249.3	305.4	385.0	479.8	575.5
120°	165.0	167.6	173.7	185.1	202.0	225.5	257.9	309.7	381.7	468.6	556.0
122.5°	175.7	177.9	183.9	196.5	213.3	236.9	267.5	313.4	379.0	458.8	541.6
125°	189.9	193.2	199.2	212.1	229.5	251.8	280.7	319.8	375.7	445.7	520.4
127.5°	201.7	206.0	213.7	227.3	244.8	266.2	292.8	326.9	374.0	433.5	498.9
130°	208.7	214.0	222.8	236.9	254.5	275.3	300.9	331.2	373.0	425.5	485.3
132.5°	214.6	221.1	230.9	245.6	263.1	284.0	307.9	336.0	373.0	419.0	471.9
135°	223.5	231.6	242.4	256.5	274.7	295.6	317.8	342.7	373.0	411.3	454.4
137.5°	233.8	241.4	252.2	266.0	284.7	303.8	325.0	348.7	373.8	404.5	439.6
140°	240.3	248.4	259.2	272.0	290.2	309.7	329.8	351.4	374.3	401.2	431.5
142.5°	247.4	254.9	265.6	277.9	295.0	313.4	332.6	353.0	374.9	398.6	424.6
145°	258.5	265.3	274.7	286.8	302.3	319.8	336.6	354.8	374.3	394.5	415.3
147.5°	269.8	275.6	284.4	294.9	308.5	323.8	339.1	355.4	372.6	390.3	406.7
150°	277.3	282.1	290.8	300.2	311.7	326.5	340.6	355.4	370.9	387.1	401.9
152.5°	284.4	288.5	296.2	305.1	315.5	329.2	341.7	354.9	368.8	383.3	396.5
155°	293.5	297.6	304.3	311.0	320.5	331.9	342.7	353.4	364.9	377.0	388.5
157.5°	302.3	305.5	311.3	317.2	324.3	334.2	343.4	351.7	360.8	371.1	380.4
160°	307.6	310.4	315.0	320.5	326.5	335.3	343.4	350.1	358.2	366.3	375.0
162.5°	312.5	315.2	319.3	323.6	328.6	336.3	342.8	348.4	354.9	361.9	369.0
165°	319.1	321.2	324.5	327.2	331.2	336.6	342.0	346.0	350.1	355.4	360.8
167.5°	324.6	325.8	327.7	329.6	332.2	336.6	340.4	342.2	345.3	349.1	353.0
170°	327.9	328.6	329.8	331.2	333.2	336.6	339.3	340.6	342.7	345.3	348.7
172.5°	329.5	330.1	331.5	332.3	333.2	336.0	338.2	338.5	339.4	341.6	343.9
175°	331.9	332.6	333.2	333.2	333.2	335.3	336.6	336.0	336.0	336.6	338.6
177.5°	333.4	333.4	333.9	333.4	333.4	334.4	335.0	333.9	333.9	334.4	335.0
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1706.3	1706.3	1715.5	1714.9	1720.9	1718.7	1719.8
5°	1834.3	1845.7	1855.8	1862.4	1872.5	1875.3	1873.9
7.5°	1966.9	1992.3	2004.6	2021.5	2024.6	2033.5	2032.6
10°	2049.1	2073.9	2092.7	2107.5	2114.8	2124.3	2124.9
12.5°	2113.5	2134.6	2151.2	2164.9	2173.9	2176.9	2178.6
15°	2163.8	2187.3	2206.7	2226.2	2237.7	2246.3	2251.1
17.5°	2214.6	2250.8	2285.2	2311.6	2327.5	2340.9	2340.7
20°	2253.8	2295.3	2338.3	2368.5	2399.4	2412.8	2414.8
22.5°	2295.6	2359.2	2414.6	2461.4	2502.0	2515.9	2521.2
25°	2382.6	2465.8	2551.1	2616.8	2663.8	2691.3	2695.4
27.5°	2487.7	2600.3	2690.0	2750.7	2789.7	2810.1	2814.6
30°	2561.8	2665.8	2746.4	2792.1	2810.1	2812.8	2802.7
32.5°	2595.1	2672.8	2705.0	2702.3	2666.8	2643.2	2634.1
35°	2554.4	2538.3	2459.8	2365.9	2294.0	2248.4	2236.3
37.5°	2324.6	2185.7	2041.3	1899.3	1823.7	1785.3	1719.2
40°	2098.1	1900.1	1749.7	1630.2	1545.0	1476.5	1460.4
42.5°	1842.5	1638.1	1487.7	1385.4	1317.3	1270.4	1250.0
45°	1480.6	1304.8	1180.6	1102.1	1049.7	1015.5	1000.1
47.5°	1184.2	1048.1	957.6	899.5	859.6	829.8	821.5
50°	1021.5	912.7	836.3	787.3	757.1	734.3	724.9
52.5°	887.3	799.5	740.7	700.3	671.7	657.5	649.7
55°	732.2	656.4	614.2	581.9	565.8	554.4	549.0
57.5°	598.8	544.1	513.2	490.9	476.0	468.7	466.1
60°	524.2	481.2	453.1	435.6	425.5	416.1	413.5
62.5°	458.1	424.3	402.6	387.3	377.2	373.2	371.5
65°	369.1	347.0	330.9	321.5	313.4	312.1	311.4
67.5°	293.4	280.4	272.0	262.2	259.3	254.6	253.7
70°	251.0	242.3	232.2	228.9	225.5	220.8	221.4
72.5°	212.9	204.1	197.3	192.9	191.7	189.7	191.4
75°	155.7	153.0	150.3	147.0	145.7	145.7	145.0
77.5°	111.2	108.8	105.9	103.9	103.5	100.7	101.8
80°	80.5	77.1	75.9	76.5	74.5	73.8	73.8
82.5°	59.6	58.4	57.1	57.2	56.7	56.1	56.7
85°	32.9	32.2	32.2	31.5	31.5	30.9	30.9
87.5°	14.4	15.1	14.2	13.7	13.7	14.4	14.9
90°	12.8	13.4	14.8	14.8	14.8	15.5	15.5
92.5°	86.6	65.2	55.2	46.6	44.9	44.0	43.0
95°	381.7	298.9	242.4	194.6	174.4	169.0	158.2
97.5°	649.1	568.4	489.8	448.2	410.5	391.0	382.4
100°	795.0	725.7	655.7	609.2	560.8	535.9	525.1
102.5°	884.5	851.2	803.8	754.1	719.6	692.6	684.5
105°	935.1	964.8	957.3	935.7	913.5	900.1	892.0
107.5°	890.0	966.0	1001.2	1012.1	1011.9	1007.5	1002.1
110°	838.8	933.8	990.9	1021.2	1034.1	1038.8	1038.8



TEST NUMBER: P333624-935

CATALOG NUMBER: S125RDIP-S1270D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	788.2	884.2	951.7	995.9	1017.9	1029.6	1034.5
115°	715.7	807.9	881.2	933.8	966.0	984.9	993.7
117.5°	665.4	744.9	812.2	864.7	898.0	916.8	922.1
120°	636.9	710.9	770.2	819.9	852.3	870.5	875.8
122.5°	616.4	682.3	737.9	782.3	811.9	830.1	834.9
125°	589.1	647.6	696.1	733.8	761.4	776.2	782.9
127.5°	562.9	617.6	663.0	697.2	721.5	735.6	738.5
130°	544.7	597.1	640.9	674.6	696.8	710.2	714.3
132.5°	527.4	575.1	617.2	650.8	673.0	685.4	690.0
135°	500.8	544.0	582.3	611.9	634.1	646.3	650.3
137.5°	477.2	513.0	545.5	572.1	592.3	603.5	608.0
140°	463.1	494.1	522.4	547.3	564.8	574.9	578.2
142.5°	451.3	477.9	502.5	523.7	538.5	548.0	550.8
145°	436.3	457.1	475.3	491.5	502.9	510.3	513.0
147.5°	423.7	439.7	453.5	466.2	475.4	479.7	481.0
150°	416.7	429.5	441.6	451.8	459.8	462.5	463.1
152.5°	409.7	421.5	430.8	439.4	445.8	448.5	449.2
155°	399.2	408.6	416.0	422.8	427.5	429.5	430.2
157.5°	389.3	396.5	402.3	407.6	411.5	413.4	413.2
160°	381.7	388.5	393.1	397.9	401.2	402.6	401.9
162.5°	375.2	380.9	385.0	388.7	391.5	391.8	391.7
165°	365.6	369.6	373.0	375.7	377.0	377.0	377.0
167.5°	356.1	359.2	361.6	363.0	364.2	363.7	363.5
170°	350.8	352.8	354.1	355.4	356.1	356.1	355.4
172.5°	345.9	347.4	348.2	348.4	349.7	348.6	347.9
175°	338.6	340.0	340.0	340.0	340.6	339.3	338.6
177.5°	335.5	335.5	335.5	335.0	335.5	333.9	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9

(END OF REPORT)