

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333516-935

Luminaire Tested: **S125RDIP-S375D1205U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333516-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D1205U935-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4979.6 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	26	25	24	18
3	77	68	61	56	68	61	55	50	48	44	40	35	33	30	24	22	21	16
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	14
5	65	54	46	40	57	48	41	37	38	33	30	28	25	23	19	17	16	12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14	11
7	55	43	36	30	49	39	32	28	31	26	22	23	20	17	16	14	12	9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	13	11	8
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3130	3130	3130	3130
5°	3601	3135	2768	3135
10°	4131	3118	2443	3118
15°	4462	3086	2171	3086
20°	4920	3049	2004	3049
25°	5694	2999	1861	2999
30°	6196	2948	1766	2948
35°	5226	2888	1678	2888
40°	3650	2780	1604	2780
45°	2707	2633	1531	2633
50°	2159	2481	1467	2481
55°	1832	2291	1412	2291
60°	1582	2124	1321	2124
65°	1411	1939	1137	1939
70°	1241	1777	1037	1777
75°	1073	1537	973	1537
80°	815	1294	815	1294
85°	674	1015	763	1015



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	0.9
10°-20°	136.2	2.7
20°-30°	215.9	4.3
30°-40°	260.4	5.2
40°-50°	232.6	4.7
50°-60°	178.3	3.6
60°-70°	115.9	2.3
70°-80°	56.3	1.1
80°-90°	16.2	0.3
90°-100°	359.7	7.2
100°-110°	773.2	15.5
110°-120°	725.6	14.6
120°-130°	588.1	11.8
130°-140°	471.9	9.5
140°-150°	356.1	7.2
150°-160°	250.7	5.0
160°-170°	147.8	3.0
170°-180°	48.1	1.0
0°-30°	398.6	8.0
0°-40°	659.0	13.2
0°-60°	1069.9	21.5
0°-90°	1258.4	25.3
90°-120°	1858.5	37.3
90°-150°	3274.7	65.8
90°-180°	3721.0	74.7
0°-180°	4979.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	555	484	427	484	555	55
15°	667	462	325	462	667	191
25°	799	421	261	421	799	367
35°	663	366	213	366	663	400
45°	296	288	168	288	296	237
55°	163	204	125	204	163	148
65°	92	127	74	127	92	92
75°	43	62	39	62	43	46
85°	9	14	10	14	9	11
90°	23	1	23	1	23	16
95°	235	33	235	33	235	333
105°	1326	113	1326	113	1326	1318
115°	1477	202	1477	202	1477	1443
125°	1164	280	1164	280	1164	1053
135°	966	328	966	328	966	749
145°	762	382	762	382	762	484
155°	639	436	639	436	639	298
165°	560	476	560	476	560	160
175°	503	495	503	495	503	49
180°	496	496	496	496	496	



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	509.8	509.5	510.1	508.3	508.5	505.8	505.8	503.8	501.0	498.9	498.0
5°	555.4	555.9	555.1	552.1	550.1	547.1	543.7	537.8	532.8	528.0	524.3
7.5°	602.5	602.8	600.1	599.3	594.2	590.6	583.1	574.9	567.7	558.5	551.6
10°	629.9	629.6	626.9	624.7	620.4	614.8	607.3	597.9	588.9	578.9	569.4
12.5°	645.8	645.2	644.4	641.7	637.7	632.7	626.5	617.1	606.1	595.2	584.0
15°	667.3	665.9	663.3	659.9	654.1	648.3	641.4	633.1	622.5	610.2	599.9
17.5°	693.9	693.9	689.9	685.2	677.3	667.2	656.4	643.0	628.6	615.1	604.1
20°	715.8	715.2	711.3	702.1	693.1	680.4	668.0	651.5	634.0	616.3	602.6
22.5°	747.3	745.8	741.7	729.6	715.7	699.3	680.4	660.3	639.1	619.1	601.0
25°	799.0	797.8	789.6	775.7	756.2	730.9	706.3	678.6	648.2	621.7	599.9
27.5°	834.3	833.0	826.9	815.4	797.4	770.8	737.4	700.4	662.5	626.0	594.5
30°	830.8	833.8	833.0	827.6	814.1	790.2	759.4	717.8	672.6	629.9	592.3
32.5°	780.8	783.5	790.5	801.1	801.8	792.3	769.2	730.8	684.1	635.4	590.5
35°	662.9	666.5	680.0	701.3	729.2	752.4	757.2	736.5	694.5	642.2	587.9
37.5°	509.6	529.2	540.6	563.0	605.1	647.9	689.1	704.2	686.4	639.4	583.7
40°	432.9	437.6	458.0	483.3	518.7	563.2	621.9	664.3	665.6	633.1	577.0
42.5°	370.5	376.6	390.5	410.7	441.0	485.5	546.1	602.1	627.9	615.5	568.2
45°	296.4	301.0	311.2	326.7	349.9	386.8	438.9	503.5	554.8	575.0	544.8
47.5°	243.5	246.0	254.8	266.7	283.9	310.6	351.0	407.2	468.7	511.9	507.6
50°	214.9	217.7	224.4	233.3	247.9	270.5	302.8	349.6	413.0	465.7	476.3
52.5°	192.6	194.9	199.1	207.6	219.6	236.9	263.0	305.3	362.4	418.4	442.9
55°	162.7	164.4	167.7	172.5	182.0	194.6	217.1	246.3	292.5	349.0	384.8
57.5°	138.2	139.0	141.1	145.5	152.1	161.3	177.5	202.2	235.4	286.3	325.8
60°	122.5	123.4	126.1	129.2	134.3	142.7	155.4	172.7	204.5	246.5	286.5
62.5°	110.1	110.6	111.8	114.8	119.3	125.8	135.8	149.9	175.2	212.2	249.9
65°	92.3	92.5	92.9	95.3	98.1	102.9	109.4	119.3	138.4	166.3	199.8
67.5°	75.2	75.5	76.9	77.7	80.6	83.1	87.0	94.5	108.1	126.8	152.8
70°	65.7	65.4	66.8	67.8	68.8	71.8	74.4	80.6	88.9	103.2	124.9
72.5°	56.7	56.2	56.8	57.2	58.5	60.5	63.1	66.9	73.4	83.2	99.8
75°	43.0	43.1	43.1	43.6	44.6	45.4	46.1	48.1	51.7	58.3	67.2
77.5°	30.1	29.9	30.7	30.8	31.4	32.3	33.0	33.8	35.2	37.9	42.5
80°	21.9	21.9	22.0	22.6	22.5	22.9	23.8	24.7	26.4	28.1	29.6
82.5°	16.8	16.6	16.8	17.0	16.9	17.3	17.7	17.8	18.5	19.3	20.4
85°	9.1	9.1	9.4	9.4	9.6	9.6	9.7	9.7	9.7	10.0	10.2
87.5°	8.1	7.9	7.6	7.6	7.7	7.7	7.3	7.0	6.7	6.5	6.3
90°	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0	17.0	16.0	14.0
92.5°	63.8	65.4	66.8	69.2	82.1	96.9	128.6	177.3	261.1	322.5	327.8
95°	235.1	251.2	259.1	289.1	360.2	444.2	567.2	719.3	867.4	886.4	723.3
97.5°	568.3	581.1	610.1	666.1	727.9	844.8	964.7	1071.3	1097.5	946.6	645.9
100°	780.3	796.3	833.4	905.4	974.4	1078.5	1181.6	1230.5	1153.5	903.4	576.3
102.5°	1017.3	1029.2	1069.4	1120.7	1194.6	1265.0	1314.4	1284.2	1119.9	827.3	523.4
105°	1325.6	1337.6	1357.6	1390.6	1422.6	1433.7	1389.7	1252.6	1012.4	725.3	472.2
107.5°	1489.3	1497.3	1503.9	1504.1	1487.9	1435.6	1322.6	1139.7	902.8	655.0	450.6
110°	1543.7	1543.7	1536.7	1517.7	1472.7	1387.6	1246.6	1056.4	840.3	622.2	444.2



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1537.3	1530.1	1512.7	1480.1	1414.2	1314.0	1171.3	990.8	793.9	603.0	444.2
115°	1476.6	1463.6	1435.6	1387.6	1309.6	1200.5	1063.5	908.4	743.3	582.3	447.2
117.5°	1370.4	1362.4	1334.6	1285.0	1206.9	1106.9	988.9	855.1	713.1	572.0	453.8
120°	1301.6	1293.6	1266.5	1218.6	1144.5	1056.4	946.4	826.4	696.3	567.2	460.2
122.5°	1240.8	1233.6	1206.5	1162.5	1096.5	1014.1	916.0	804.8	681.9	563.3	465.8
125°	1163.6	1153.5	1131.5	1090.5	1034.5	962.4	875.4	773.4	662.3	558.3	475.2
127.5°	1097.5	1093.1	1072.3	1036.0	985.2	917.8	836.5	741.3	644.3	555.9	485.8
130°	1061.4	1055.5	1035.4	1002.5	952.4	887.4	809.3	721.3	632.3	554.2	492.2
132.5°	1025.5	1018.6	1000.2	967.2	917.2	854.5	783.8	701.3	622.7	554.2	499.4
135°	966.5	960.4	942.5	909.4	865.4	808.4	744.3	675.3	611.3	554.2	509.2
137.5°	903.4	896.8	880.2	850.2	810.8	762.3	709.1	653.3	601.1	555.4	518.2
140°	859.4	854.4	839.4	813.4	776.4	734.3	688.3	641.3	596.2	556.2	522.2
142.5°	818.6	814.3	800.1	778.2	746.7	710.3	670.7	630.9	592.3	557.1	524.6
145°	762.3	758.4	747.3	730.3	706.3	679.3	648.2	617.3	586.3	556.2	527.3
147.5°	714.7	712.9	706.5	692.9	673.9	653.5	629.6	604.5	580.1	553.6	528.2
150°	688.3	687.3	683.3	671.3	656.3	638.3	619.3	597.3	575.2	551.2	528.2
152.5°	667.5	666.5	662.5	652.9	640.3	626.3	608.9	589.3	569.6	548.0	527.4
155°	639.3	638.3	635.2	628.3	618.3	607.3	593.2	577.2	560.3	542.3	525.2
157.5°	614.1	614.2	611.5	605.6	597.9	589.3	578.4	565.2	551.5	536.2	522.6
160°	597.3	598.3	596.2	591.2	584.3	577.2	567.2	557.2	544.2	532.3	520.2
162.5°	582.0	582.3	581.9	577.6	572.2	566.0	557.7	548.5	537.9	527.4	517.8
165°	560.3	560.3	560.3	558.3	554.2	549.2	543.2	536.2	528.2	520.2	514.2
167.5°	540.3	540.4	541.2	539.4	537.4	533.8	529.3	524.6	518.8	513.2	508.6
170°	528.2	529.3	529.3	528.2	526.2	524.3	521.2	518.2	513.2	509.2	506.3
172.5°	517.0	518.1	519.6	517.8	517.5	516.3	514.0	511.0	507.6	504.5	503.0
175°	503.3	504.2	506.3	505.2	505.2	505.2	503.3	503.3	500.2	499.2	499.2
177.5°	496.2	496.2	498.6	497.8	498.6	498.6	498.6	497.8	497.1	496.2	496.2
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	498.0	496.9	494.8	492.9	490.5	488.4	487.0	485.3	483.0	480.4	478.1
5°	520.0	515.7	509.9	504.9	498.5	493.6	488.4	483.5	478.5	472.1	466.5
7.5°	544.5	535.5	526.7	515.6	505.6	496.6	488.0	479.3	470.8	461.8	453.1
10°	559.5	548.5	536.4	522.5	509.7	497.6	486.5	475.4	463.9	453.8	442.9
12.5°	573.4	559.3	545.4	527.9	512.6	497.7	483.5	469.9	457.6	444.4	432.7
15°	586.1	572.1	556.6	535.2	513.8	495.9	479.2	461.6	446.3	431.5	418.4
17.5°	591.0	576.4	558.4	537.7	514.4	491.9	470.4	451.0	432.9	415.8	401.1
20°	589.1	575.0	556.5	536.7	511.9	488.4	465.1	443.7	423.5	405.4	389.8
22.5°	584.4	569.9	552.0	531.2	507.6	482.7	457.8	434.9	413.9	395.1	378.0
25°	577.6	557.7	539.3	519.0	496.5	471.9	446.3	420.9	398.5	379.4	360.7
27.5°	570.3	545.5	522.2	502.0	478.3	456.3	431.5	405.6	382.0	362.6	343.4
30°	563.8	536.0	510.3	487.4	464.9	444.0	420.6	395.3	371.0	350.9	331.5
32.5°	555.7	526.1	497.9	471.5	449.8	429.1	407.9	383.7	360.1	339.3	319.5
35°	545.5	507.7	477.1	449.0	425.0	404.8	385.7	366.3	342.6	321.1	301.8
37.5°	532.2	489.2	453.8	423.3	397.9	377.7	362.6	344.7	323.1	302.6	284.7
40°	524.0	475.9	437.1	406.8	380.2	358.9	344.7	329.7	310.0	290.7	272.8
42.5°	513.2	463.6	420.3	388.7	361.9	341.4	327.1	313.9	297.4	279.2	260.0
45°	492.0	439.9	394.3	360.5	333.5	313.3	300.0	288.3	275.8	259.0	242.3
47.5°	464.4	415.1	367.4	330.5	304.0	285.3	272.4	263.1	254.2	240.0	223.8
50°	442.3	394.7	348.2	312.4	284.1	266.4	254.3	246.9	238.8	225.8	212.2
52.5°	416.1	373.7	328.1	291.5	264.8	248.2	236.6	229.2	222.5	212.0	199.1
55°	375.1	337.8	296.0	262.8	238.3	221.6	210.5	203.5	199.6	190.6	180.5
57.5°	327.5	300.9	264.1	232.0	210.3	193.9	185.7	179.8	175.3	168.9	161.8
60°	294.5	275.8	242.7	212.2	192.3	176.7	169.3	164.4	160.1	154.8	149.2
62.5°	260.9	247.3	218.5	192.3	174.1	160.9	154.0	149.6	144.7	141.1	135.7
65°	215.9	203.7	183.8	163.3	146.5	135.9	130.9	126.9	124.0	119.9	116.1
67.5°	167.9	163.0	149.2	135.1	123.0	113.6	109.3	106.5	103.0	100.6	98.0
70°	138.4	136.0	126.3	117.0	105.6	99.3	95.3	94.1	89.7	87.3	85.6
72.5°	112.4	111.2	105.6	99.2	91.2	85.6	82.0	80.6	77.7	75.9	74.7
75°	77.0	77.4	76.4	72.2	69.2	65.7	62.5	61.6	59.7	58.1	57.1
77.5°	48.7	50.7	50.8	50.6	49.4	47.3	45.9	45.3	43.4	42.8	42.5
80°	33.4	35.6	37.6	37.4	37.0	36.4	35.4	34.8	33.8	33.2	32.8
82.5°	22.3	24.3	26.0	27.0	26.9	26.3	25.7	25.4	25.2	24.8	24.7
85°	10.5	10.9	11.5	12.9	13.9	14.1	13.9	13.7	13.2	13.3	13.5
87.5°	6.3	5.9	5.9	5.4	4.8	5.3	5.3	5.3	5.2	5.3	5.3
90°	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0	2.0	4.0	6.0
92.5°	228.3	136.6	82.1	52.9	35.6	23.2	14.8	12.2	14.8	23.2	35.6
95°	447.2	227.1	120.0	75.0	53.0	42.0	34.0	33.0	34.0	42.0	53.0
97.5°	357.0	195.7	124.8	92.5	72.7	61.6	56.1	54.8	56.1	61.6	72.7
100°	324.2	194.1	136.0	106.1	87.0	76.0	72.1	70.0	72.1	76.0	87.0
102.5°	310.6	201.3	149.6	120.5	103.1	91.3	88.1	86.9	88.1	91.3	103.1
105°	305.1	216.1	172.1	144.0	128.0	118.0	113.0	113.0	113.0	118.0	128.0
107.5°	314.4	238.1	195.4	170.3	153.7	145.4	140.7	138.6	140.7	145.4	153.7
110°	323.1	254.1	213.1	187.1	172.1	163.1	159.1	157.0	159.1	163.1	172.1



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.3	269.3	229.9	204.7	189.7	180.6	177.5	175.5	177.5	180.6	189.7
115°	351.1	293.2	256.1	231.1	216.1	207.1	204.1	202.1	204.1	207.1	216.1
117.5°	370.4	317.5	282.5	258.3	241.3	232.3	229.1	226.1	229.1	232.3	241.3
120°	383.1	335.2	300.1	275.1	258.1	249.1	245.1	242.1	245.1	249.1	258.1
122.5°	397.6	352.0	316.9	292.0	273.3	264.3	261.1	258.9	261.1	264.3	273.3
125°	417.2	374.2	341.1	315.1	296.1	287.1	282.1	280.1	282.1	287.1	296.1
127.5°	435.2	395.5	363.8	337.8	317.5	306.2	299.7	296.7	299.7	306.2	317.5
130°	447.2	409.1	378.2	352.1	331.1	318.1	310.1	307.1	310.1	318.1	331.1
132.5°	457.6	422.0	391.0	365.0	343.2	328.6	318.9	315.1	318.9	328.6	343.2
135°	472.2	439.2	408.2	381.2	360.2	344.1	332.2	328.1	332.2	344.1	360.2
137.5°	483.0	451.4	423.2	395.4	374.8	358.8	347.6	344.6	347.6	358.8	374.8
140°	490.3	460.2	431.2	404.2	385.2	369.2	357.1	354.1	357.1	369.2	385.2
142.5°	494.2	465.8	438.4	413.0	394.8	378.8	367.6	365.3	367.6	378.8	394.8
145°	500.2	475.2	449.2	426.2	408.2	394.2	384.2	382.2	384.2	394.2	408.2
147.5°	503.9	481.2	458.4	438.2	422.6	409.6	401.0	399.8	401.0	409.6	422.6
150°	506.3	485.2	463.2	446.2	432.2	419.2	412.2	410.2	412.2	419.2	432.2
152.5°	507.8	489.2	468.8	453.4	440.2	428.8	422.6	421.4	422.6	428.8	440.2
155°	509.2	493.2	476.2	462.2	452.2	442.2	436.2	436.2	436.2	442.2	452.2
157.5°	510.2	496.6	482.0	471.4	462.6	454.0	449.2	449.4	449.2	454.0	462.6
160°	510.2	498.3	485.2	476.2	468.2	461.2	457.2	458.2	457.2	461.2	468.2
162.5°	509.5	499.8	488.4	481.0	474.6	468.4	464.4	465.4	464.4	468.4	474.6
165°	508.2	500.2	492.2	486.2	482.2	477.3	474.2	476.2	474.2	477.3	482.2
167.5°	505.8	500.2	493.6	489.8	487.0	484.2	482.4	483.5	482.4	484.2	487.0
170°	504.2	500.2	495.2	492.2	490.3	488.2	487.2	488.2	487.2	488.2	490.3
172.5°	502.7	499.4	495.2	493.8	492.6	490.6	489.7	491.5	489.7	490.6	492.6
175°	500.2	498.3	495.2	495.2	495.2	494.2	493.2	495.2	493.2	494.2	495.2
177.5°	497.8	497.1	495.4	495.4	496.2	495.4	495.4	497.1	495.4	495.4	496.2
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	476.5	474.3	472.7	469.5	467.3	466.3	464.6	464.1	465.9	464.6	464.4
5°	462.4	456.6	452.0	447.5	442.5	439.3	434.5	433.7	432.5	430.8	430.3
7.5°	445.4	437.8	432.0	424.4	417.8	412.5	406.6	403.7	402.2	399.8	396.7
10°	433.9	425.0	417.0	409.4	401.3	394.7	388.7	384.2	381.2	378.4	377.2
12.5°	422.6	413.5	403.3	394.2	385.0	377.7	371.1	368.1	364.8	361.5	358.8
15°	405.0	393.0	381.8	371.3	363.5	355.5	349.1	344.7	339.8	338.4	333.0
17.5°	386.4	374.5	361.4	350.4	341.4	332.6	325.6	320.6	316.9	311.8	309.4
20°	374.8	360.7	347.9	337.8	327.9	317.5	310.4	306.2	302.6	298.4	296.4
22.5°	362.4	348.6	335.5	323.6	313.6	303.3	298.3	293.9	289.9	286.0	283.4
25°	344.1	330.3	316.5	304.2	293.7	286.3	280.3	275.3	273.2	269.4	266.6
27.5°	326.1	311.3	297.1	284.8	276.6	269.2	264.3	260.5	256.5	253.2	250.7
30°	314.5	299.5	283.9	274.1	265.4	258.5	253.0	249.3	246.3	243.3	241.5
32.5°	302.9	287.3	273.5	263.0	254.8	248.7	243.2	239.5	236.4	233.2	231.0
35°	284.3	268.4	257.3	246.9	238.8	233.2	229.4	224.2	221.6	219.2	217.1
37.5°	267.0	252.2	240.1	231.1	223.9	218.4	213.5	210.8	207.6	205.4	203.6
40°	254.3	240.7	229.8	220.2	215.1	208.9	204.3	200.7	198.4	195.5	193.6
42.5°	242.8	230.2	219.6	211.0	204.6	199.3	194.9	191.3	188.3	186.3	184.7
45°	226.6	214.0	203.7	195.8	189.8	184.9	180.2	178.5	174.4	172.1	171.3
47.5°	209.8	198.6	188.6	181.3	175.2	170.5	166.2	162.6	160.3	158.0	156.7
50°	198.5	187.8	178.5	171.3	165.3	160.1	156.2	153.8	150.8	148.6	147.1
52.5°	187.3	177.3	168.0	161.1	155.9	150.8	146.3	144.0	141.1	139.7	138.6
55°	171.1	160.6	152.6	145.9	140.4	135.7	131.5	129.2	127.3	126.0	125.5
57.5°	152.8	144.5	137.1	131.0	125.4	120.9	117.2	114.9	113.4	113.1	111.9
60°	140.9	133.3	126.6	119.9	115.2	111.0	107.8	105.2	103.7	103.5	103.1
62.5°	128.9	121.7	115.4	109.6	105.3	101.3	98.2	95.4	94.5	93.4	92.6
65°	111.2	104.6	99.4	94.9	90.3	87.0	83.9	82.1	80.0	78.8	76.6
67.5°	93.8	88.8	83.8	79.9	76.3	73.1	70.6	67.9	66.5	65.5	64.0
70°	82.4	78.4	73.4	69.2	66.5	63.9	61.9	58.9	57.9	57.1	56.3
72.5°	71.5	68.0	63.9	60.4	57.7	55.3	53.0	51.6	50.5	49.8	49.3
75°	56.3	53.0	49.3	46.9	44.9	43.0	41.8	40.8	40.4	40.2	39.4
77.5°	41.3	39.5	36.7	34.8	33.5	32.6	31.6	31.1	31.0	30.1	29.9
80°	31.6	30.7	28.2	27.5	26.4	25.7	25.1	24.1	23.1	22.6	22.0
82.5°	23.5	22.6	21.5	20.3	19.5	18.9	18.4	18.0	18.2	17.6	17.3
85°	12.6	11.5	11.1	10.9	10.5	10.9	10.8	10.5	10.3	10.2	10.3
87.5°	5.6	5.9	6.0	6.7	6.5	7.1	7.2	7.2	7.5	7.7	7.9
90°	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0	19.0	20.0	22.0
92.5°	52.9	82.1	136.6	228.3	327.8	322.5	261.1	177.3	128.6	96.9	82.1
95°	75.0	120.0	227.1	447.2	723.3	886.4	867.4	719.3	567.2	444.2	360.2
97.5°	92.5	124.8	195.7	357.0	645.9	946.6	1097.5	1071.3	964.7	844.8	727.9
100°	106.1	136.0	194.1	324.2	576.3	903.4	1153.5	1230.5	1181.6	1078.5	974.4
102.5°	120.5	149.6	201.3	310.6	523.4	827.3	1119.9	1284.2	1314.4	1265.0	1194.6
105°	144.0	172.1	216.1	305.1	472.2	725.3	1012.4	1252.6	1389.7	1433.7	1422.6
107.5°	170.3	195.4	238.1	314.4	450.6	655.0	902.8	1139.7	1322.6	1435.6	1487.9
110°	187.1	213.1	254.1	323.1	444.2	622.2	840.3	1056.4	1246.6	1387.6	1472.7



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.7	229.9	269.3	334.3	444.2	603.0	793.9	990.8	1171.3	1314.0	1414.2
115°	231.1	256.1	293.2	351.1	447.2	582.3	743.3	908.4	1063.5	1200.5	1309.6
117.5°	258.3	282.5	317.5	370.4	453.8	572.0	713.1	855.1	988.9	1106.9	1206.9
120°	275.1	300.1	335.2	383.1	460.2	567.2	696.3	826.4	946.4	1056.4	1144.5
122.5°	292.0	316.9	352.0	397.6	465.8	563.3	681.9	804.8	916.0	1014.1	1096.5
125°	315.1	341.1	374.2	417.2	475.2	558.3	662.3	773.4	875.4	962.4	1034.5
127.5°	337.8	363.8	395.5	435.2	485.8	555.9	644.3	741.3	836.5	917.8	985.2
130°	352.1	378.2	409.1	447.2	492.2	554.2	632.3	721.3	809.3	887.4	952.4
132.5°	365.0	391.0	422.0	457.6	499.4	554.2	622.7	701.3	783.8	854.5	917.2
135°	381.2	408.2	439.2	472.2	509.2	554.2	611.3	675.3	744.3	808.4	865.4
137.5°	395.4	423.2	451.4	483.0	518.2	555.4	601.1	653.3	709.1	762.3	810.8
140°	404.2	431.2	460.2	490.3	522.2	556.2	596.2	641.3	688.3	734.3	776.4
142.5°	413.0	438.4	465.8	494.2	524.6	557.1	592.3	630.9	670.7	710.3	746.7
145°	426.2	449.2	475.2	500.2	527.3	556.2	586.3	617.3	648.2	679.3	706.3
147.5°	438.2	458.4	481.2	503.9	528.2	553.6	580.1	604.5	629.6	653.5	673.9
150°	446.2	463.2	485.2	506.3	528.2	551.2	575.2	597.3	619.3	638.3	656.3
152.5°	453.4	468.8	489.2	507.8	527.4	548.0	569.6	589.3	608.9	626.3	640.3
155°	462.2	476.2	493.2	509.2	525.2	542.3	560.3	577.2	593.2	607.3	618.3
157.5°	471.4	482.0	496.6	510.2	522.6	536.2	551.5	565.2	578.4	589.3	597.9
160°	476.2	485.2	498.3	510.2	520.2	532.3	544.2	557.2	567.2	577.2	584.3
162.5°	481.0	488.4	499.8	509.5	517.8	527.4	537.9	548.5	557.7	566.0	572.2
165°	486.2	492.2	500.2	508.2	514.2	520.2	528.2	536.2	543.2	549.2	554.2
167.5°	489.8	493.6	500.2	505.8	508.6	513.2	518.8	524.6	529.3	533.8	537.4
170°	492.2	495.2	500.2	504.2	506.3	509.2	513.2	518.2	521.2	524.3	526.2
172.5°	493.8	495.2	499.4	502.7	503.0	504.5	507.6	511.0	514.0	516.3	517.5
175°	495.2	495.2	498.3	500.2	499.2	499.2	500.2	503.3	503.3	505.2	505.2
177.5°	495.4	495.4	497.1	497.8	496.2	496.2	497.1	497.8	498.6	498.6	498.6
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	464.3	462.5	462.0	462.7	462.0	462.5	464.3	464.4	464.6	465.9	464.1
5°	428.3	426.4	427.3	427.0	427.3	426.4	428.3	430.3	430.8	432.5	433.7
7.5°	396.7	394.3	391.7	392.4	391.7	394.3	396.7	396.7	399.8	402.2	403.7
10°	374.6	372.6	371.4	372.5	371.4	372.6	374.6	377.2	378.4	381.2	384.2
12.5°	356.0	354.8	353.8	353.4	353.8	354.8	356.0	358.8	361.5	364.8	368.1
15°	330.6	328.3	327.3	324.7	327.3	328.3	330.6	333.0	338.4	339.8	344.7
17.5°	307.3	306.5	303.9	302.8	303.9	306.5	307.3	309.4	311.8	316.9	320.6
20°	293.4	292.7	290.1	291.6	290.1	292.7	293.4	296.4	298.4	302.6	306.2
22.5°	282.0	280.3	279.4	279.0	279.4	280.3	282.0	283.4	286.0	289.9	293.9
25°	265.8	263.2	262.2	261.1	262.2	263.2	265.8	266.6	269.4	273.2	275.3
27.5°	249.6	248.2	246.9	246.6	246.9	248.2	249.6	250.7	253.2	256.5	260.5
30°	239.1	237.7	236.8	236.8	236.8	237.7	239.1	241.5	243.3	246.3	249.3
32.5°	229.7	228.7	227.6	227.5	227.6	228.7	229.7	231.0	233.2	236.4	239.5
35°	216.0	214.5	214.0	212.8	214.0	214.5	216.0	217.1	219.2	221.6	224.2
37.5°	201.8	200.5	200.5	200.4	200.5	200.5	201.8	203.6	205.4	207.6	210.8
40°	192.8	191.7	191.6	190.2	191.6	191.7	192.8	193.6	195.5	198.4	200.7
42.5°	183.0	182.5	181.8	181.2	181.8	182.5	183.0	184.7	186.3	188.3	191.3
45°	169.9	168.5	168.5	167.6	168.5	168.5	169.9	171.3	172.1	174.4	178.5
47.5°	156.3	155.2	155.3	154.3	155.3	155.2	156.3	156.7	158.0	160.3	162.6
50°	147.2	146.6	146.5	146.0	146.5	146.6	147.2	147.1	148.6	150.8	153.8
52.5°	138.2	137.8	138.6	137.8	138.6	137.8	138.2	138.6	139.7	141.1	144.0
55°	126.0	125.4	126.6	125.4	126.6	125.4	126.0	125.5	126.0	127.3	129.2
57.5°	111.9	111.3	112.4	111.8	112.4	111.3	111.9	111.9	113.1	113.4	114.9
60°	102.6	101.4	102.0	102.3	102.0	101.4	102.6	103.1	103.5	103.7	105.2
62.5°	91.7	90.9	91.4	90.5	91.4	90.9	91.7	92.6	93.4	94.5	95.4
65°	76.2	75.6	74.8	74.4	74.8	75.6	76.2	76.6	78.8	80.0	82.1
67.5°	64.1	62.6	62.5	62.9	62.5	62.6	64.1	64.0	65.5	66.5	67.9
70°	55.1	55.1	54.9	54.9	54.9	55.1	55.1	56.3	57.1	57.9	58.9
72.5°	48.9	48.7	48.4	48.2	48.4	48.7	48.9	49.3	49.8	50.5	51.6
75°	39.4	39.6	39.2	39.0	39.2	39.6	39.4	39.4	40.2	40.4	40.8
77.5°	29.1	28.2	28.7	28.2	28.7	28.2	29.1	29.9	30.1	31.0	31.1
80°	22.0	21.9	22.5	21.9	22.5	21.9	22.0	22.0	22.6	23.1	24.1
82.5°	17.5	17.3	17.6	17.1	17.6	17.3	17.5	17.3	17.6	18.2	18.0
85°	10.5	10.3	10.2	10.3	10.2	10.3	10.5	10.3	10.2	10.3	10.5
87.5°	8.1	7.9	8.1	8.1	8.1	7.9	8.1	7.9	7.7	7.5	7.2
90°	22.0	22.0	23.0	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0
92.5°	69.2	66.8	65.4	63.8	65.4	66.8	69.2	82.1	96.9	128.6	177.3
95°	289.1	259.1	251.2	235.1	251.2	259.1	289.1	360.2	444.2	567.2	719.3
97.5°	666.1	610.1	581.1	568.3	581.1	610.1	666.1	727.9	844.8	964.7	1071.3
100°	905.4	833.4	796.3	780.3	796.3	833.4	905.4	974.4	1078.5	1181.6	1230.5
102.5°	1120.7	1069.4	1029.2	1017.3	1029.2	1069.4	1120.7	1194.6	1265.0	1314.4	1284.2
105°	1390.6	1357.6	1337.6	1325.6	1337.6	1357.6	1390.6	1422.6	1433.7	1389.7	1252.6
107.5°	1504.1	1503.9	1497.3	1489.3	1497.3	1503.9	1504.1	1487.9	1435.6	1322.6	1139.7
110°	1517.7	1536.7	1543.7	1543.7	1543.7	1536.7	1517.7	1472.7	1387.6	1246.6	1056.4



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1480.1	1512.7	1530.1	1537.3	1530.1	1512.7	1480.1	1414.2	1314.0	1171.3	990.8
115°	1387.6	1435.6	1463.6	1476.6	1463.6	1435.6	1387.6	1309.6	1200.5	1063.5	908.4
117.5°	1285.0	1334.6	1362.4	1370.4	1362.4	1334.6	1285.0	1206.9	1106.9	988.9	855.1
120°	1218.6	1266.5	1293.6	1301.6	1293.6	1266.5	1218.6	1144.5	1056.4	946.4	826.4
122.5°	1162.5	1206.5	1233.6	1240.8	1233.6	1206.5	1162.5	1096.5	1014.1	916.0	804.8
125°	1090.5	1131.5	1153.5	1163.6	1153.5	1131.5	1090.5	1034.5	962.4	875.4	773.4
127.5°	1036.0	1072.3	1093.1	1097.5	1093.1	1072.3	1036.0	985.2	917.8	836.5	741.3
130°	1002.5	1035.4	1055.5	1061.4	1055.5	1035.4	1002.5	952.4	887.4	809.3	721.3
132.5°	967.2	1000.2	1018.6	1025.5	1018.6	1000.2	967.2	917.2	854.5	783.8	701.3
135°	909.4	942.5	960.4	966.5	960.4	942.5	909.4	865.4	808.4	744.3	675.3
137.5°	850.2	880.2	896.8	903.4	896.8	880.2	850.2	810.8	762.3	709.1	653.3
140°	813.4	839.4	854.4	859.4	854.4	839.4	813.4	776.4	734.3	688.3	641.3
142.5°	778.2	800.1	814.3	818.6	814.3	800.1	778.2	746.7	710.3	670.7	630.9
145°	730.3	747.3	758.4	762.3	758.4	747.3	730.3	706.3	679.3	648.2	617.3
147.5°	692.9	706.5	712.9	714.7	712.9	706.5	692.9	673.9	653.5	629.6	604.5
150°	671.3	683.3	687.3	688.3	687.3	683.3	671.3	656.3	638.3	619.3	597.3
152.5°	652.9	662.5	666.5	667.5	666.5	662.5	652.9	640.3	626.3	608.9	589.3
155°	628.3	635.2	638.3	639.3	638.3	635.2	628.3	618.3	607.3	593.2	577.2
157.5°	605.6	611.5	614.2	614.1	614.2	611.5	605.6	597.9	589.3	578.4	565.2
160°	591.2	596.2	598.3	597.3	598.3	596.2	591.2	584.3	577.2	567.2	557.2
162.5°	577.6	581.9	582.3	582.0	582.3	581.9	577.6	572.2	566.0	557.7	548.5
165°	558.3	560.3	560.3	560.3	560.3	560.3	558.3	554.2	549.2	543.2	536.2
167.5°	539.4	541.2	540.4	540.3	540.4	541.2	539.4	537.4	533.8	529.3	524.6
170°	528.2	529.3	529.3	528.2	529.3	529.3	528.2	526.2	524.3	521.2	518.2
172.5°	517.8	519.6	518.1	517.0	518.1	519.6	517.8	517.5	516.3	514.0	511.0
175°	505.2	506.3	504.2	503.3	504.2	506.3	505.2	505.2	505.2	503.3	503.3
177.5°	497.8	498.6	496.2	496.2	496.2	498.6	497.8	498.6	498.6	498.6	497.8
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	464.6	466.3	467.3	469.5	472.7	474.3	476.5	478.1	480.4	483.0	485.3
5°	434.5	439.3	442.5	447.5	452.0	456.6	462.4	466.5	472.1	478.5	483.5
7.5°	406.6	412.5	417.8	424.4	432.0	437.8	445.4	453.1	461.8	470.8	479.3
10°	388.7	394.7	401.3	409.4	417.0	425.0	433.9	442.9	453.8	463.9	475.4
12.5°	371.1	377.7	385.0	394.2	403.3	413.5	422.6	432.7	444.4	457.6	469.9
15°	349.1	355.5	363.5	371.3	381.8	393.0	405.0	418.4	431.5	446.3	461.6
17.5°	325.6	332.6	341.4	350.4	361.4	374.5	386.4	401.1	415.8	432.9	451.0
20°	310.4	317.5	327.9	337.8	347.9	360.7	374.8	389.8	405.4	423.5	443.7
22.5°	298.3	303.3	313.6	323.6	335.5	348.6	362.4	378.0	395.1	413.9	434.9
25°	280.3	286.3	293.7	304.2	316.5	330.3	344.1	360.7	379.4	398.5	420.9
27.5°	264.3	269.2	276.6	284.8	297.1	311.3	326.1	343.4	362.6	382.0	405.6
30°	253.0	258.5	265.4	274.1	283.9	299.5	314.5	331.5	350.9	371.0	395.3
32.5°	243.2	248.7	254.8	263.0	273.5	287.3	302.9	319.5	339.3	360.1	383.7
35°	229.4	233.2	238.8	246.9	257.3	268.4	284.3	301.8	321.1	342.6	366.3
37.5°	213.5	218.4	223.9	231.1	240.1	252.2	267.0	284.7	302.6	323.1	344.7
40°	204.3	208.9	215.1	220.2	229.8	240.7	254.3	272.8	290.7	310.0	329.7
42.5°	194.9	199.3	204.6	211.0	219.6	230.2	242.8	260.0	279.2	297.4	313.9
45°	180.2	184.9	189.8	195.8	203.7	214.0	226.6	242.3	259.0	275.8	288.3
47.5°	166.2	170.5	175.2	181.3	188.6	198.6	209.8	223.8	240.0	254.2	263.1
50°	156.2	160.1	165.3	171.3	178.5	187.8	198.5	212.2	225.8	238.8	246.9
52.5°	146.3	150.8	155.9	161.1	168.0	177.3	187.3	199.1	212.0	222.5	229.2
55°	131.5	135.7	140.4	145.9	152.6	160.6	171.1	180.5	190.6	199.6	203.5
57.5°	117.2	120.9	125.4	131.0	137.1	144.5	152.8	161.8	168.9	175.3	179.8
60°	107.8	111.0	115.2	119.9	126.6	133.3	140.9	149.2	154.8	160.1	164.4
62.5°	98.2	101.3	105.3	109.6	115.4	121.7	128.9	135.7	141.1	144.7	149.6
65°	83.9	87.0	90.3	94.9	99.4	104.6	111.2	116.1	119.9	124.0	126.9
67.5°	70.6	73.1	76.3	79.9	83.8	88.8	93.8	98.0	100.6	103.0	106.5
70°	61.9	63.9	66.5	69.2	73.4	78.4	82.4	85.6	87.3	89.7	94.1
72.5°	53.0	55.3	57.7	60.4	63.9	68.0	71.5	74.7	75.9	77.7	80.6
75°	41.8	43.0	44.9	46.9	49.3	53.0	56.3	57.1	58.1	59.7	61.6
77.5°	31.6	32.6	33.5	34.8	36.7	39.5	41.3	42.5	42.8	43.4	45.3
80°	25.1	25.7	26.4	27.5	28.2	30.7	31.6	32.8	33.2	33.8	34.8
82.5°	18.4	18.9	19.5	20.3	21.5	22.6	23.5	24.7	24.8	25.2	25.4
85°	10.8	10.9	10.5	10.9	11.1	11.5	12.6	13.5	13.3	13.2	13.7
87.5°	7.2	7.1	6.5	6.7	6.0	5.9	5.6	5.3	5.3	5.2	5.3
90°	17.0	16.0	14.0	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0
92.5°	261.1	322.5	327.8	228.3	136.6	82.1	52.9	35.6	23.2	14.8	12.2
95°	867.4	886.4	723.3	447.2	227.1	120.0	75.0	53.0	42.0	34.0	33.0
97.5°	1097.5	946.6	645.9	357.0	195.7	124.8	92.5	72.7	61.6	56.1	54.8
100°	1153.5	903.4	576.3	324.2	194.1	136.0	106.1	87.0	76.0	72.1	70.0
102.5°	1119.9	827.3	523.4	310.6	201.3	149.6	120.5	103.1	91.3	88.1	86.9
105°	1012.4	725.3	472.2	305.1	216.1	172.1	144.0	128.0	118.0	113.0	113.0
107.5°	902.8	655.0	450.6	314.4	238.1	195.4	170.3	153.7	145.4	140.7	138.6
110°	840.3	622.2	444.2	323.1	254.1	213.1	187.1	172.1	163.1	159.1	157.0



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	793.9	603.0	444.2	334.3	269.3	229.9	204.7	189.7	180.6	177.5	175.5
115°	743.3	582.3	447.2	351.1	293.2	256.1	231.1	216.1	207.1	204.1	202.1
117.5°	713.1	572.0	453.8	370.4	317.5	282.5	258.3	241.3	232.3	229.1	226.1
120°	696.3	567.2	460.2	383.1	335.2	300.1	275.1	258.1	249.1	245.1	242.1
122.5°	681.9	563.3	465.8	397.6	352.0	316.9	292.0	273.3	264.3	261.1	258.9
125°	662.3	558.3	475.2	417.2	374.2	341.1	315.1	296.1	287.1	282.1	280.1
127.5°	644.3	555.9	485.8	435.2	395.5	363.8	337.8	317.5	306.2	299.7	296.7
130°	632.3	554.2	492.2	447.2	409.1	378.2	352.1	331.1	318.1	310.1	307.1
132.5°	622.7	554.2	499.4	457.6	422.0	391.0	365.0	343.2	328.6	318.9	315.1
135°	611.3	554.2	509.2	472.2	439.2	408.2	381.2	360.2	344.1	332.2	328.1
137.5°	601.1	555.4	518.2	483.0	451.4	423.2	395.4	374.8	358.8	347.6	344.6
140°	596.2	556.2	522.2	490.3	460.2	431.2	404.2	385.2	369.2	357.1	354.1
142.5°	592.3	557.1	524.6	494.2	465.8	438.4	413.0	394.8	378.8	367.6	365.3
145°	586.3	556.2	527.3	500.2	475.2	449.2	426.2	408.2	394.2	384.2	382.2
147.5°	580.1	553.6	528.2	503.9	481.2	458.4	438.2	422.6	409.6	401.0	399.8
150°	575.2	551.2	528.2	506.3	485.2	463.2	446.2	432.2	419.2	412.2	410.2
152.5°	569.6	548.0	527.4	507.8	489.2	468.8	453.4	440.2	428.8	422.6	421.4
155°	560.3	542.3	525.2	509.2	493.2	476.2	462.2	452.2	442.2	436.2	436.2
157.5°	551.5	536.2	522.6	510.2	496.6	482.0	471.4	462.6	454.0	449.2	449.4
160°	544.2	532.3	520.2	510.2	498.3	485.2	476.2	468.2	461.2	457.2	458.2
162.5°	537.9	527.4	517.8	509.5	499.8	488.4	481.0	474.6	468.4	464.4	465.4
165°	528.2	520.2	514.2	508.2	500.2	492.2	486.2	482.2	477.3	474.2	476.2
167.5°	518.8	513.2	508.6	505.8	500.2	493.6	489.8	487.0	484.2	482.4	483.5
170°	513.2	509.2	506.3	504.2	500.2	495.2	492.2	490.3	488.2	487.2	488.2
172.5°	507.6	504.5	503.0	502.7	499.4	495.2	493.8	492.6	490.6	489.7	491.5
175°	500.2	499.2	499.2	500.2	498.3	495.2	495.2	495.2	494.2	493.2	495.2
177.5°	497.1	496.2	496.2	497.8	497.1	495.4	495.4	496.2	495.4	495.4	497.1
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	487.0	488.4	490.5	492.9	494.8	496.9	498.0	498.0	498.9	501.0	503.8
5°	488.4	493.6	498.5	504.9	509.9	515.7	520.0	524.3	528.0	532.8	537.8
7.5°	488.0	496.6	505.6	515.6	526.7	535.5	544.5	551.6	558.5	567.7	574.9
10°	486.5	497.6	509.7	522.5	536.4	548.5	559.5	569.4	578.9	588.9	597.9
12.5°	483.5	497.7	512.6	527.9	545.4	559.3	573.4	584.0	595.2	606.1	617.1
15°	479.2	495.9	513.8	535.2	556.6	572.1	586.1	599.9	610.2	622.5	633.1
17.5°	470.4	491.9	514.4	537.7	558.4	576.4	591.0	604.1	615.1	628.6	643.0
20°	465.1	488.4	511.9	536.7	556.5	575.0	589.1	602.6	616.3	634.0	651.5
22.5°	457.8	482.7	507.6	531.2	552.0	569.9	584.4	601.0	619.1	639.1	660.3
25°	446.3	471.9	496.5	519.0	539.3	557.7	577.6	599.9	621.7	648.2	678.6
27.5°	431.5	456.3	478.3	502.0	522.2	545.5	570.3	594.5	626.0	662.5	700.4
30°	420.6	444.0	464.9	487.4	510.3	536.0	563.8	592.3	629.9	672.6	717.8
32.5°	407.9	429.1	449.8	471.5	497.9	526.1	555.7	590.5	635.4	684.1	730.8
35°	385.7	404.8	425.0	449.0	477.1	507.7	545.5	587.9	642.2	694.5	736.5
37.5°	362.6	377.7	397.9	423.3	453.8	489.2	532.2	583.7	639.4	686.4	704.2
40°	344.7	358.9	380.2	406.8	437.1	475.9	524.0	577.0	633.1	665.6	664.3
42.5°	327.1	341.4	361.9	388.7	420.3	463.6	513.2	568.2	615.5	627.9	602.1
45°	300.0	313.3	333.5	360.5	394.3	439.9	492.0	544.8	575.0	554.8	503.5
47.5°	272.4	285.3	304.0	330.5	367.4	415.1	464.4	507.6	511.9	468.7	407.2
50°	254.3	266.4	284.1	312.4	348.2	394.7	442.3	476.3	465.7	413.0	349.6
52.5°	236.6	248.2	264.8	291.5	328.1	373.7	416.1	442.9	418.4	362.4	305.3
55°	210.5	221.6	238.3	262.8	296.0	337.8	375.1	384.8	349.0	292.5	246.3
57.5°	185.7	193.9	210.3	232.0	264.1	300.9	327.5	325.8	286.3	235.4	202.2
60°	169.3	176.7	192.3	212.2	242.7	275.8	294.5	286.5	246.5	204.5	172.7
62.5°	154.0	160.9	174.1	192.3	218.5	247.3	260.9	249.9	212.2	175.2	149.9
65°	130.9	135.9	146.5	163.3	183.8	203.7	215.9	199.8	166.3	138.4	119.3
67.5°	109.3	113.6	123.0	135.1	149.2	163.0	167.9	152.8	126.8	108.1	94.5
70°	95.3	99.3	105.6	117.0	126.3	136.0	138.4	124.9	103.2	88.9	80.6
72.5°	82.0	85.6	91.2	99.2	105.6	111.2	112.4	99.8	83.2	73.4	66.9
75°	62.5	65.7	69.2	72.2	76.4	77.4	77.0	67.2	58.3	51.7	48.1
77.5°	45.9	47.3	49.4	50.6	50.8	50.7	48.7	42.5	37.9	35.2	33.8
80°	35.4	36.4	37.0	37.4	37.6	35.6	33.4	29.6	28.1	26.4	24.7
82.5°	25.7	26.3	26.9	27.0	26.0	24.3	22.3	20.4	19.3	18.5	17.8
85°	13.9	14.1	13.9	12.9	11.5	10.9	10.5	10.2	10.0	9.7	9.7
87.5°	5.3	5.3	4.8	5.4	5.9	5.9	6.3	6.3	6.5	6.7	7.0
90°	2.0	4.0	6.0	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0
92.5°	14.8	23.2	35.6	52.9	82.1	136.6	228.3	327.8	322.5	261.1	177.3
95°	34.0	42.0	53.0	75.0	120.0	227.1	447.2	723.3	886.4	867.4	719.3
97.5°	56.1	61.6	72.7	92.5	124.8	195.7	357.0	645.9	946.6	1097.5	1071.3
100°	72.1	76.0	87.0	106.1	136.0	194.1	324.2	576.3	903.4	1153.5	1230.5
102.5°	88.1	91.3	103.1	120.5	149.6	201.3	310.6	523.4	827.3	1119.9	1284.2
105°	113.0	118.0	128.0	144.0	172.1	216.1	305.1	472.2	725.3	1012.4	1252.6
107.5°	140.7	145.4	153.7	170.3	195.4	238.1	314.4	450.6	655.0	902.8	1139.7
110°	159.1	163.1	172.1	187.1	213.1	254.1	323.1	444.2	622.2	840.3	1056.4



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	177.5	180.6	189.7	204.7	229.9	269.3	334.3	444.2	603.0	793.9	990.8
115°	204.1	207.1	216.1	231.1	256.1	293.2	351.1	447.2	582.3	743.3	908.4
117.5°	229.1	232.3	241.3	258.3	282.5	317.5	370.4	453.8	572.0	713.1	855.1
120°	245.1	249.1	258.1	275.1	300.1	335.2	383.1	460.2	567.2	696.3	826.4
122.5°	261.1	264.3	273.3	292.0	316.9	352.0	397.6	465.8	563.3	681.9	804.8
125°	282.1	287.1	296.1	315.1	341.1	374.2	417.2	475.2	558.3	662.3	773.4
127.5°	299.7	306.2	317.5	337.8	363.8	395.5	435.2	485.8	555.9	644.3	741.3
130°	310.1	318.1	331.1	352.1	378.2	409.1	447.2	492.2	554.2	632.3	721.3
132.5°	318.9	328.6	343.2	365.0	391.0	422.0	457.6	499.4	554.2	622.7	701.3
135°	332.2	344.1	360.2	381.2	408.2	439.2	472.2	509.2	554.2	611.3	675.3
137.5°	347.6	358.8	374.8	395.4	423.2	451.4	483.0	518.2	555.4	601.1	653.3
140°	357.1	369.2	385.2	404.2	431.2	460.2	490.3	522.2	556.2	596.2	641.3
142.5°	367.6	378.8	394.8	413.0	438.4	465.8	494.2	524.6	557.1	592.3	630.9
145°	384.2	394.2	408.2	426.2	449.2	475.2	500.2	527.3	556.2	586.3	617.3
147.5°	401.0	409.6	422.6	438.2	458.4	481.2	503.9	528.2	553.6	580.1	604.5
150°	412.2	419.2	432.2	446.2	463.2	485.2	506.3	528.2	551.2	575.2	597.3
152.5°	422.6	428.8	440.2	453.4	468.8	489.2	507.8	527.4	548.0	569.6	589.3
155°	436.2	442.2	452.2	462.2	476.2	493.2	509.2	525.2	542.3	560.3	577.2
157.5°	449.2	454.0	462.6	471.4	482.0	496.6	510.2	522.6	536.2	551.5	565.2
160°	457.2	461.2	468.2	476.2	485.2	498.3	510.2	520.2	532.3	544.2	557.2
162.5°	464.4	468.4	474.6	481.0	488.4	499.8	509.5	517.8	527.4	537.9	548.5
165°	474.2	477.3	482.2	486.2	492.2	500.2	508.2	514.2	520.2	528.2	536.2
167.5°	482.4	484.2	487.0	489.8	493.6	500.2	505.8	508.6	513.2	518.8	524.6
170°	487.2	488.2	490.3	492.2	495.2	500.2	504.2	506.3	509.2	513.2	518.2
172.5°	489.7	490.6	492.6	493.8	495.2	499.4	502.7	503.0	504.5	507.6	511.0
175°	493.2	494.2	495.2	495.2	495.2	498.3	500.2	499.2	499.2	500.2	503.3
177.5°	495.4	495.4	496.2	495.4	495.4	497.1	497.8	496.2	496.2	497.1	497.8
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	505.8	505.8	508.5	508.3	510.1	509.5	509.8
5°	543.7	547.1	550.1	552.1	555.1	555.9	555.4
7.5°	583.1	590.6	594.2	599.3	600.1	602.8	602.5
10°	607.3	614.8	620.4	624.7	626.9	629.6	629.9
12.5°	626.5	632.7	637.7	641.7	644.4	645.2	645.8
15°	641.4	648.3	654.1	659.9	663.3	665.9	667.3
17.5°	656.4	667.2	677.3	685.2	689.9	693.9	693.9
20°	668.0	680.4	693.1	702.1	711.3	715.2	715.8
22.5°	680.4	699.3	715.7	729.6	741.7	745.8	747.3
25°	706.3	730.9	756.2	775.7	789.6	797.8	799.0
27.5°	737.4	770.8	797.4	815.4	826.9	833.0	834.3
30°	759.4	790.2	814.1	827.6	833.0	833.8	830.8
32.5°	769.2	792.3	801.8	801.1	790.5	783.5	780.8
35°	757.2	752.4	729.2	701.3	680.0	666.5	662.9
37.5°	689.1	647.9	605.1	563.0	540.6	529.2	509.6
40°	621.9	563.2	518.7	483.3	458.0	437.6	432.9
42.5°	546.1	485.5	441.0	410.7	390.5	376.6	370.5
45°	438.9	386.8	349.9	326.7	311.2	301.0	296.4
47.5°	351.0	310.6	283.9	266.7	254.8	246.0	243.5
50°	302.8	270.5	247.9	233.3	224.4	217.7	214.9
52.5°	263.0	236.9	219.6	207.6	199.1	194.9	192.6
55°	217.1	194.6	182.0	172.5	167.7	164.4	162.7
57.5°	177.5	161.3	152.1	145.5	141.1	139.0	138.2
60°	155.4	142.7	134.3	129.2	126.1	123.4	122.5
62.5°	135.8	125.8	119.3	114.8	111.8	110.6	110.1
65°	109.4	102.9	98.1	95.3	92.9	92.5	92.3
67.5°	87.0	83.1	80.6	77.7	76.9	75.5	75.2
70°	74.4	71.8	68.8	67.8	66.8	65.4	65.7
72.5°	63.1	60.5	58.5	57.2	56.8	56.2	56.7
75°	46.1	45.4	44.6	43.6	43.1	43.1	43.0
77.5°	33.0	32.3	31.4	30.8	30.7	29.9	30.1
80°	23.8	22.9	22.5	22.6	22.0	21.9	21.9
82.5°	17.7	17.3	16.9	17.0	16.8	16.6	16.8
85°	9.7	9.6	9.6	9.4	9.4	9.1	9.1
87.5°	7.3	7.7	7.7	7.6	7.6	7.9	8.1
90°	19.0	20.0	22.0	22.0	22.0	23.0	23.0
92.5°	128.6	96.9	82.1	69.2	66.8	65.4	63.8
95°	567.2	444.2	360.2	289.1	259.1	251.2	235.1
97.5°	964.7	844.8	727.9	666.1	610.1	581.1	568.3
100°	1181.6	1078.5	974.4	905.4	833.4	796.3	780.3
102.5°	1314.4	1265.0	1194.6	1120.7	1069.4	1029.2	1017.3
105°	1389.7	1433.7	1422.6	1390.6	1357.6	1337.6	1325.6
107.5°	1322.6	1435.6	1487.9	1504.1	1503.9	1497.3	1489.3
110°	1246.6	1387.6	1472.7	1517.7	1536.7	1543.7	1543.7



TEST NUMBER: P333516-935

CATALOG NUMBER: S125RDIP-S375D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1171.3	1314.0	1414.2	1480.1	1512.7	1530.1	1537.3
115°	1063.5	1200.5	1309.6	1387.6	1435.6	1463.6	1476.6
117.5°	988.9	1106.9	1206.9	1285.0	1334.6	1362.4	1370.4
120°	946.4	1056.4	1144.5	1218.6	1266.5	1293.6	1301.6
122.5°	916.0	1014.1	1096.5	1162.5	1206.5	1233.6	1240.8
125°	875.4	962.4	1034.5	1090.5	1131.5	1153.5	1163.6
127.5°	836.5	917.8	985.2	1036.0	1072.3	1093.1	1097.5
130°	809.3	887.4	952.4	1002.5	1035.4	1055.5	1061.4
132.5°	783.8	854.5	917.2	967.2	1000.2	1018.6	1025.5
135°	744.3	808.4	865.4	909.4	942.5	960.4	966.5
137.5°	709.1	762.3	810.8	850.2	880.2	896.8	903.4
140°	688.3	734.3	776.4	813.4	839.4	854.4	859.4
142.5°	670.7	710.3	746.7	778.2	800.1	814.3	818.6
145°	648.2	679.3	706.3	730.3	747.3	758.4	762.3
147.5°	629.6	653.5	673.9	692.9	706.5	712.9	714.7
150°	619.3	638.3	656.3	671.3	683.3	687.3	688.3
152.5°	608.9	626.3	640.3	652.9	662.5	666.5	667.5
155°	593.2	607.3	618.3	628.3	635.2	638.3	639.3
157.5°	578.4	589.3	597.9	605.6	611.5	614.2	614.1
160°	567.2	577.2	584.3	591.2	596.2	598.3	597.3
162.5°	557.7	566.0	572.2	577.6	581.9	582.3	582.0
165°	543.2	549.2	554.2	558.3	560.3	560.3	560.3
167.5°	529.3	533.8	537.4	539.4	541.2	540.4	540.3
170°	521.2	524.3	526.2	528.2	529.3	529.3	528.2
172.5°	514.0	516.3	517.5	517.8	519.6	518.1	517.0
175°	503.3	505.2	505.2	505.2	506.3	504.2	503.3
177.5°	498.6	498.6	498.6	497.8	498.6	496.2	496.2
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2

(END OF REPORT)