

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333496-935

Luminaire Tested: **S125RDIP-S375D590U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333496-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D590U935-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3292.0 lumens
Efficiency: N/A
Efficacy: 128.6 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	40	40	39	33				
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28				
3	80	71	64	58	72	64	58	54	53	48	45	42	39	37	32	30	29	24				
4	73	63	55	49	66	57	51	46	47	42	38	38	34	31	29	27	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18				
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16				
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17	14				
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13				
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	12				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3130	3130	3130	3130
5°	3601	3135	2768	3135
10°	4131	3118	2443	3118
15°	4462	3086	2171	3086
20°	4920	3049	2004	3049
25°	5694	2999	1861	2999
30°	6196	2948	1766	2948
35°	5226	2888	1678	2888
40°	3650	2780	1604	2780
45°	2707	2633	1531	2633
50°	2159	2481	1467	2481
55°	1832	2291	1412	2291
60°	1582	2124	1321	2124
65°	1411	1939	1137	1939
70°	1241	1777	1037	1777
75°	1073	1537	973	1537
80°	815	1294	815	1294
85°	674	1015	763	1015



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	1.4
10°-20°	136.2	4.1
20°-30°	215.9	6.6
30°-40°	260.4	7.9
40°-50°	232.6	7.1
50°-60°	178.3	5.4
60°-70°	115.9	3.5
70°-80°	56.3	1.7
80°-90°	14.8	0.5
90°-100°	24.1	0.7
100°-110°	148.4	4.5
110°-120°	269.2	8.2
120°-130°	345.5	10.5
130°-140°	371.6	11.3
140°-150°	348.8	10.6
150°-160°	282.1	8.6
160°-170°	182.5	5.5
170°-180°	62.9	1.9
0°-30°	398.6	12.1
0°-40°	659.0	20.0
0°-60°	1069.9	32.5
0°-90°	1257.0	38.2
90°-120°	441.7	13.4
90°-150°	1507.5	45.8
90°-180°	2035.0	61.8
0°-180°	3292.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	555	484	427	484	555	55
15°	667	462	325	462	667	191
25°	799	421	261	421	799	367
35°	663	366	213	366	663	400
45°	296	288	168	288	296	237
55°	163	204	125	204	163	148
65°	92	127	74	127	92	92
75°	43	62	39	62	43	46
85°	9	14	10	14	9	11
90°	12	0	12	0	12	6
95°	10	28	10	28	10	9
105°	146	144	146	144	146	132
115°	269	271	269	271	269	267
125°	386	386	386	386	386	343
135°	479	481	479	481	479	370
145°	556	558	556	558	556	347
155°	610	614	610	614	610	281
165°	644	648	644	648	644	182
175°	660	663	660	663	660	63
180°	663	663	663	663	663	



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	509.8	509.5	510.1	508.3	508.5	505.8	505.8	503.8	501.0	498.9	498.0
5°	555.4	555.9	555.1	552.1	550.1	547.1	543.7	537.8	532.8	528.0	524.3
7.5°	602.5	602.8	600.1	599.3	594.2	590.6	583.1	574.9	567.7	558.5	551.6
10°	629.9	629.6	626.9	624.7	620.4	614.8	607.3	597.9	588.9	578.9	569.4
12.5°	645.8	645.2	644.4	641.7	637.7	632.7	626.5	617.1	606.1	595.2	584.0
15°	667.3	665.9	663.3	659.9	654.1	648.3	641.4	633.1	622.5	610.2	599.9
17.5°	693.9	693.9	689.9	685.2	677.3	667.2	656.4	643.0	628.6	615.1	604.1
20°	715.8	715.2	711.3	702.1	693.1	680.4	668.0	651.5	634.0	616.3	602.6
22.5°	747.3	745.8	741.7	729.6	715.7	699.3	680.4	660.3	639.1	619.1	601.0
25°	799.0	797.8	789.6	775.7	756.2	730.9	706.3	678.6	648.2	621.7	599.9
27.5°	834.3	833.0	826.9	815.4	797.4	770.8	737.4	700.4	662.5	626.0	594.5
30°	830.8	833.8	833.0	827.6	814.1	790.2	759.4	717.8	672.6	629.9	592.3
32.5°	780.8	783.5	790.5	801.1	801.8	792.3	769.2	730.8	684.1	635.4	590.5
35°	662.9	666.5	680.0	701.3	729.2	752.4	757.2	736.5	694.5	642.2	587.9
37.5°	509.6	529.2	540.6	563.0	605.1	647.9	689.1	704.2	686.4	639.4	583.7
40°	432.9	437.6	458.0	483.3	518.7	563.2	621.9	664.3	665.6	633.1	577.0
42.5°	370.5	376.6	390.5	410.7	441.0	485.5	546.1	602.1	627.9	615.5	568.2
45°	296.4	301.0	311.2	326.7	349.9	386.8	438.9	503.5	554.8	575.0	544.8
47.5°	243.5	246.0	254.8	266.7	283.9	310.6	351.0	407.2	468.7	511.9	507.6
50°	214.9	217.7	224.4	233.3	247.9	270.5	302.8	349.6	413.0	465.7	476.3
52.5°	192.6	194.9	199.1	207.6	219.6	236.9	263.0	305.3	362.4	418.4	442.9
55°	162.7	164.4	167.7	172.5	182.0	194.6	217.1	246.3	292.5	349.0	384.8
57.5°	138.2	139.0	141.1	145.5	152.1	161.3	177.5	202.2	235.4	286.3	325.8
60°	122.5	123.4	126.1	129.2	134.3	142.7	155.4	172.7	204.5	246.5	286.5
62.5°	110.1	110.6	111.8	114.8	119.3	125.8	135.8	149.9	175.2	212.2	249.9
65°	92.3	92.5	92.9	95.3	98.1	102.9	109.4	119.3	138.4	166.3	199.8
67.5°	75.2	75.5	76.9	77.7	80.6	83.1	87.0	94.5	108.1	126.8	152.8
70°	65.7	65.4	66.8	67.8	68.8	71.8	74.4	80.6	88.9	103.2	124.9
72.5°	56.7	56.2	56.8	57.2	58.5	60.5	63.1	66.9	73.4	83.2	99.8
75°	43.0	43.1	43.1	43.6	44.6	45.4	46.1	48.1	51.7	58.3	67.2
77.5°	30.1	29.9	30.7	30.8	31.4	32.3	33.0	33.8	35.2	37.9	42.5
80°	21.9	21.9	22.0	22.6	22.5	22.9	23.8	24.7	26.4	28.1	29.6
82.5°	16.8	16.6	16.8	17.0	16.9	17.3	17.7	17.8	18.5	19.3	20.4
85°	9.1	9.1	9.4	9.4	9.6	9.6	9.7	9.7	9.7	10.0	10.2
87.5°	5.9	5.6	5.4	5.3	5.4	5.7	5.4	5.2	5.0	4.9	4.9
90°	11.8	11.5	11.1	10.8	10.5	10.1	9.5	9.0	8.4	7.8	7.1
92.5°	11.0	10.8	10.7	10.5	10.4	10.1	9.5	9.0	8.4	7.8	7.1
95°	10.3	10.3	10.3	10.3	10.3	10.1	9.5	9.0	8.4	7.8	12.0
97.5°	10.3	10.3	10.3	10.3	10.3	11.9	14.9	18.0	21.1	24.2	32.4
100°	10.3	10.8	11.2	11.6	12.1	20.4	36.7	53.0	69.2	85.5	85.1
102.5°	61.8	69.2	76.6	84.0	91.5	96.8	99.8	102.9	106.0	109.1	108.8
105°	145.9	146.0	146.1	146.2	146.4	146.4	146.4	146.4	146.4	146.4	146.4
107.5°	183.9	184.3	184.6	184.9	185.2	185.4	185.4	185.4	185.3	185.3	185.1
110°	210.3	210.2	210.0	209.9	209.8	209.9	210.3	210.6	210.9	211.2	211.0



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	233.8	234.0	234.1	234.3	234.5	234.7	235.1	235.6	236.0	236.3	236.3
115°	269.2	269.8	270.5	271.1	271.8	272.3	272.8	273.2	273.7	274.1	274.0
117.5°	306.9	307.2	307.5	307.8	308.1	308.5	309.0	309.6	310.2	310.7	310.3
120°	330.1	330.6	331.2	331.7	332.3	332.7	332.9	333.1	333.3	333.6	333.2
122.5°	352.1	352.8	353.4	354.0	354.6	355.1	355.3	355.5	355.8	355.9	355.8
125°	385.6	386.0	386.2	386.6	386.9	387.3	387.7	388.2	388.7	389.1	389.1
127.5°	413.8	414.7	415.4	416.2	417.1	417.6	417.8	418.0	418.3	418.5	418.6
130°	434.3	434.8	435.3	435.9	436.4	436.9	437.2	437.6	437.8	438.2	438.1
132.5°	453.1	453.7	454.2	454.8	455.3	455.6	455.6	455.7	455.8	455.9	456.1
135°	479.0	479.6	480.3	481.0	481.6	482.0	482.2	482.4	482.7	482.8	483.1
137.5°	504.9	505.5	506.0	506.6	507.1	507.4	507.4	507.3	507.3	507.2	507.5
140°	520.2	520.9	521.5	522.2	522.8	523.1	522.8	522.6	522.4	522.2	522.3
142.5°	534.8	535.4	536.1	536.7	537.4	537.7	537.6	537.6	537.5	537.5	537.4
145°	556.0	556.7	557.4	558.0	558.7	559.0	558.9	558.8	558.6	558.5	558.5
147.5°	573.7	574.5	575.2	576.0	576.8	577.1	577.0	576.9	576.8	576.6	576.4
150°	585.0	585.9	586.8	587.7	588.6	588.8	588.7	588.4	588.2	588.0	587.8
152.5°	595.6	596.4	597.3	598.1	598.8	599.1	598.9	598.7	598.5	598.2	598.0
155°	609.6	610.5	611.4	612.3	613.1	613.4	613.0	612.8	612.4	612.1	611.8
157.5°	621.3	622.2	623.0	624.0	624.8	625.1	624.7	624.4	624.1	623.7	623.6
160°	628.8	629.6	630.5	631.4	632.2	632.5	632.1	631.6	631.2	630.8	630.6
162.5°	635.4	636.5	637.4	638.3	639.3	639.5	638.9	638.3	637.7	637.1	636.9
165°	644.5	645.4	646.3	647.1	648.0	648.1	647.5	646.8	646.1	645.5	645.4
167.5°	650.7	651.8	652.7	653.8	654.7	654.8	654.0	653.2	652.5	651.7	651.5
170°	654.4	655.3	656.3	657.3	658.2	658.3	657.5	656.6	655.7	654.8	654.7
172.5°	656.7	657.6	658.7	659.6	660.6	660.7	660.0	659.1	658.3	657.5	657.4
175°	659.7	660.7	661.7	662.7	663.7	663.7	662.8	661.9	661.1	660.2	660.1
177.5°	661.5	662.2	662.9	663.6	664.3	664.3	663.7	663.1	662.5	661.9	661.8
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	498.0	496.9	494.8	492.9	490.5	488.4	487.0	485.3	483.0	480.4	478.1
5°	520.0	515.7	509.9	504.9	498.5	493.6	488.4	483.5	478.5	472.1	466.5
7.5°	544.5	535.5	526.7	515.6	505.6	496.6	488.0	479.3	470.8	461.8	453.1
10°	559.5	548.5	536.4	522.5	509.7	497.6	486.5	475.4	463.9	453.8	442.9
12.5°	573.4	559.3	545.4	527.9	512.6	497.7	483.5	469.9	457.6	444.4	432.7
15°	586.1	572.1	556.6	535.2	513.8	495.9	479.2	461.6	446.3	431.5	418.4
17.5°	591.0	576.4	558.4	537.7	514.4	491.9	470.4	451.0	432.9	415.8	401.1
20°	589.1	575.0	556.5	536.7	511.9	488.4	465.1	443.7	423.5	405.4	389.8
22.5°	584.4	569.9	552.0	531.2	507.6	482.7	457.8	434.9	413.9	395.1	378.0
25°	577.6	557.7	539.3	519.0	496.5	471.9	446.3	420.9	398.5	379.4	360.7
27.5°	570.3	545.5	522.2	502.0	478.3	456.3	431.5	405.6	382.0	362.6	343.4
30°	563.8	536.0	510.3	487.4	464.9	444.0	420.6	395.3	371.0	350.9	331.5
32.5°	555.7	526.1	497.9	471.5	449.8	429.1	407.9	383.7	360.1	339.3	319.5
35°	545.5	507.7	477.1	449.0	425.0	404.8	385.7	366.3	342.6	321.1	301.8
37.5°	532.2	489.2	453.8	423.3	397.9	377.7	362.6	344.7	323.1	302.6	284.7
40°	524.0	475.9	437.1	406.8	380.2	358.9	344.7	329.7	310.0	290.7	272.8
42.5°	513.2	463.6	420.3	388.7	361.9	341.4	327.1	313.9	297.4	279.2	260.0
45°	492.0	439.9	394.3	360.5	333.5	313.3	300.0	288.3	275.8	259.0	242.3
47.5°	464.4	415.1	367.4	330.5	304.0	285.3	272.4	263.1	254.2	240.0	223.8
50°	442.3	394.7	348.2	312.4	284.1	266.4	254.3	246.9	238.8	225.8	212.2
52.5°	416.1	373.7	328.1	291.5	264.8	248.2	236.6	229.2	222.5	212.0	199.1
55°	375.1	337.8	296.0	262.8	238.3	221.6	210.5	203.5	199.6	190.6	180.5
57.5°	327.5	300.9	264.1	232.0	210.3	193.9	185.7	179.8	175.3	168.9	161.8
60°	294.5	275.8	242.7	212.2	192.3	176.7	169.3	164.4	160.1	154.8	149.2
62.5°	260.9	247.3	218.5	192.3	174.1	160.9	154.0	149.6	144.7	141.1	135.7
65°	215.9	203.7	183.8	163.3	146.5	135.9	130.9	126.9	124.0	119.9	116.1
67.5°	167.9	163.0	149.2	135.1	123.0	113.6	109.3	106.5	103.0	100.6	98.0
70°	138.4	136.0	126.3	117.0	105.6	99.3	95.3	94.1	89.7	87.3	85.6
72.5°	112.4	111.2	105.6	99.2	91.2	85.6	82.0	80.6	77.7	75.9	74.7
75°	77.0	77.4	76.4	72.2	69.2	65.7	62.5	61.6	59.7	58.1	57.1
77.5°	48.7	50.7	50.8	50.6	49.4	47.3	45.9	45.3	43.4	42.8	42.5
80°	33.4	35.6	37.6	37.4	37.0	36.4	35.4	34.8	33.8	33.2	32.8
82.5°	22.3	24.3	26.0	27.0	26.9	26.3	25.7	25.4	25.2	24.8	24.7
85°	10.5	10.9	11.5	12.9	13.9	14.1	13.9	13.7	13.2	13.3	13.5
87.5°	4.9	4.7	4.8	4.6	4.3	4.9	5.2	5.2	5.1	4.9	4.7
90°	6.4	5.6	4.8	4.0	3.1	2.2	1.4	0.5	1.4	2.2	3.1
92.5°	6.5	5.9	5.2	5.1	5.8	6.4	7.0	7.6	7.0	6.4	5.8
95°	16.2	20.3	24.5	26.7	27.0	27.4	27.6	28.0	27.6	27.4	27.0
97.5°	40.6	48.8	57.0	60.8	60.2	59.7	59.1	58.5	59.1	59.7	60.2
100°	84.6	84.2	83.7	83.3	83.0	82.7	82.4	82.1	82.4	82.7	83.0
102.5°	108.6	108.2	108.0	107.6	107.3	106.9	106.4	106.0	106.4	106.9	107.3
105°	146.4	146.4	146.4	146.2	145.8	145.3	144.8	144.4	144.8	145.3	145.8
107.5°	184.9	184.6	184.4	184.3	184.3	184.3	184.3	184.3	184.3	184.3	184.3
110°	210.8	210.6	210.3	210.3	210.3	210.3	210.3	210.3	210.3	210.3	210.3



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	236.1	236.0	235.8	235.7	235.4	235.1	234.9	234.6	234.9	235.1	235.4
115°	273.9	273.8	273.7	273.4	272.8	272.2	271.7	271.1	271.7	272.2	272.8
117.5°	310.0	309.5	309.1	308.9	308.9	308.9	308.9	309.0	308.9	308.9	308.9
120°	332.9	332.6	332.3	332.1	332.3	332.3	332.4	332.6	332.4	332.3	332.3
122.5°	355.7	355.5	355.3	355.1	354.6	354.2	353.8	353.4	353.8	354.2	354.6
125°	389.1	389.1	389.1	388.7	387.9	387.1	386.4	385.6	386.4	387.1	387.9
127.5°	418.7	418.7	418.8	418.5	418.0	417.5	416.9	416.4	416.9	417.5	418.0
130°	438.0	437.8	437.7	437.4	436.9	436.4	435.8	435.2	435.8	436.4	436.9
132.5°	456.3	456.6	456.8	456.6	456.0	455.4	454.7	454.1	454.7	455.4	456.0
135°	483.3	483.5	483.8	483.5	482.8	482.2	481.6	481.0	481.6	482.2	482.8
137.5°	507.6	507.8	508.1	507.8	507.3	506.7	506.2	505.6	506.2	506.7	507.3
140°	522.4	522.5	522.6	522.5	522.4	522.1	521.9	521.7	521.9	522.1	522.4
142.5°	537.2	537.1	536.9	536.7	536.7	536.5	536.4	536.2	536.4	536.5	536.7
145°	558.5	558.5	558.5	558.4	558.2	558.0	557.8	557.6	557.8	558.0	558.2
147.5°	576.4	576.2	576.1	576.0	576.1	576.1	576.2	576.2	576.2	576.1	576.1
150°	587.5	587.4	587.1	587.1	587.4	587.5	587.8	588.0	587.8	587.5	587.4
152.5°	597.8	597.5	597.4	597.4	598.0	598.5	598.9	599.4	598.9	598.5	598.0
155°	611.7	611.4	611.2	611.4	612.1	612.8	613.4	614.1	613.4	612.8	612.1
157.5°	623.6	623.6	623.6	623.8	624.1	624.6	624.9	625.3	624.9	624.6	624.1
160°	630.5	630.4	630.3	630.6	631.2	631.9	632.6	633.2	632.6	631.9	631.2
162.5°	636.8	636.7	636.6	636.9	637.5	638.2	638.9	639.5	638.9	638.2	637.5
165°	645.2	645.1	645.1	645.3	646.0	646.6	647.3	647.9	647.3	646.6	646.0
167.5°	651.4	651.3	651.3	651.5	652.2	652.9	653.6	654.2	653.6	652.9	652.2
170°	654.6	654.4	654.4	654.7	655.5	656.3	657.0	657.8	657.0	656.3	655.5
172.5°	657.2	656.9	656.8	657.0	657.8	658.6	659.4	660.1	659.4	658.6	657.8
175°	660.0	659.9	659.8	660.0	660.7	661.3	662.0	662.7	662.0	661.3	660.7
177.5°	661.7	661.6	661.5	661.8	662.3	662.8	663.3	663.8	663.3	662.8	662.3
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	476.5	474.3	472.7	469.5	467.3	466.3	464.6	464.1	465.9	464.6	464.4
5°	462.4	456.6	452.0	447.5	442.5	439.3	434.5	433.7	432.5	430.8	430.3
7.5°	445.4	437.8	432.0	424.4	417.8	412.5	406.6	403.7	402.2	399.8	396.7
10°	433.9	425.0	417.0	409.4	401.3	394.7	388.7	384.2	381.2	378.4	377.2
12.5°	422.6	413.5	403.3	394.2	385.0	377.7	371.1	368.1	364.8	361.5	358.8
15°	405.0	393.0	381.8	371.3	363.5	355.5	349.1	344.7	339.8	338.4	333.0
17.5°	386.4	374.5	361.4	350.4	341.4	332.6	325.6	320.6	316.9	311.8	309.4
20°	374.8	360.7	347.9	337.8	327.9	317.5	310.4	306.2	302.6	298.4	296.4
22.5°	362.4	348.6	335.5	323.6	313.6	303.3	298.3	293.9	289.9	286.0	283.4
25°	344.1	330.3	316.5	304.2	293.7	286.3	280.3	275.3	273.2	269.4	266.6
27.5°	326.1	311.3	297.1	284.8	276.6	269.2	264.3	260.5	256.5	253.2	250.7
30°	314.5	299.5	283.9	274.1	265.4	258.5	253.0	249.3	246.3	243.3	241.5
32.5°	302.9	287.3	273.5	263.0	254.8	248.7	243.2	239.5	236.4	233.2	231.0
35°	284.3	268.4	257.3	246.9	238.8	233.2	229.4	224.2	221.6	219.2	217.1
37.5°	267.0	252.2	240.1	231.1	223.9	218.4	213.5	210.8	207.6	205.4	203.6
40°	254.3	240.7	229.8	220.2	215.1	208.9	204.3	200.7	198.4	195.5	193.6
42.5°	242.8	230.2	219.6	211.0	204.6	199.3	194.9	191.3	188.3	186.3	184.7
45°	226.6	214.0	203.7	195.8	189.8	184.9	180.2	178.5	174.4	172.1	171.3
47.5°	209.8	198.6	188.6	181.3	175.2	170.5	166.2	162.6	160.3	158.0	156.7
50°	198.5	187.8	178.5	171.3	165.3	160.1	156.2	153.8	150.8	148.6	147.1
52.5°	187.3	177.3	168.0	161.1	155.9	150.8	146.3	144.0	141.1	139.7	138.6
55°	171.1	160.6	152.6	145.9	140.4	135.7	131.5	129.2	127.3	126.0	125.5
57.5°	152.8	144.5	137.1	131.0	125.4	120.9	117.2	114.9	113.4	113.1	111.9
60°	140.9	133.3	126.6	119.9	115.2	111.0	107.8	105.2	103.7	103.5	103.1
62.5°	128.9	121.7	115.4	109.6	105.3	101.3	98.2	95.4	94.5	93.4	92.6
65°	111.2	104.6	99.4	94.9	90.3	87.0	83.9	82.1	80.0	78.8	76.6
67.5°	93.8	88.8	83.8	79.9	76.3	73.1	70.6	67.9	66.5	65.5	64.0
70°	82.4	78.4	73.4	69.2	66.5	63.9	61.9	58.9	57.9	57.1	56.3
72.5°	71.5	68.0	63.9	60.4	57.7	55.3	53.0	51.6	50.5	49.8	49.3
75°	56.3	53.0	49.3	46.9	44.9	43.0	41.8	40.8	40.4	40.2	39.4
77.5°	41.3	39.5	36.7	34.8	33.5	32.6	31.6	31.1	31.0	30.1	29.9
80°	31.6	30.7	28.2	27.5	26.4	25.7	25.1	24.1	23.1	22.6	22.0
82.5°	23.5	22.6	21.5	20.3	19.5	18.9	18.4	18.0	18.2	17.6	17.3
85°	12.6	11.5	11.1	10.9	10.5	10.9	10.8	10.5	10.3	10.2	10.3
87.5°	4.7	4.9	4.9	5.4	5.1	5.4	5.5	5.4	5.6	5.7	5.6
90°	4.0	4.8	5.6	6.4	7.1	7.8	8.4	9.0	9.5	10.1	10.5
92.5°	5.1	5.2	5.9	6.5	7.1	7.8	8.4	9.0	9.5	10.1	10.4
95°	26.7	24.5	20.3	16.2	12.0	7.8	8.4	9.0	9.5	10.1	10.3
97.5°	60.8	57.0	48.8	40.6	32.4	24.2	21.1	18.0	14.9	11.9	10.3
100°	83.3	83.7	84.2	84.6	85.1	85.5	69.2	53.0	36.7	20.4	12.1
102.5°	107.6	108.0	108.2	108.6	108.8	109.1	106.0	102.9	99.8	96.8	91.5
105°	146.2	146.4	146.4	146.4	146.4	146.4	146.4	146.4	146.4	146.4	146.4
107.5°	184.3	184.4	184.6	184.9	185.1	185.3	185.3	185.4	185.4	185.4	185.2
110°	210.3	210.3	210.6	210.8	211.0	211.2	210.9	210.6	210.3	209.9	209.8



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	235.7	235.8	236.0	236.1	236.3	236.3	236.0	235.6	235.1	234.7	234.5
115°	273.4	273.7	273.8	273.9	274.0	274.1	273.7	273.2	272.8	272.3	271.8
117.5°	308.9	309.1	309.5	310.0	310.3	310.7	310.2	309.6	309.0	308.5	308.1
120°	332.1	332.3	332.6	332.9	333.2	333.6	333.3	333.1	332.9	332.7	332.3
122.5°	355.1	355.3	355.5	355.7	355.8	355.9	355.8	355.5	355.3	355.1	354.6
125°	388.7	389.1	389.1	389.1	389.1	389.1	388.7	388.2	387.7	387.3	386.9
127.5°	418.5	418.8	418.7	418.7	418.6	418.5	418.3	418.0	417.8	417.6	417.1
130°	437.4	437.7	437.8	438.0	438.1	438.2	437.8	437.6	437.2	436.9	436.4
132.5°	456.6	456.8	456.6	456.3	456.1	455.9	455.8	455.7	455.6	455.6	455.3
135°	483.5	483.8	483.5	483.3	483.1	482.8	482.7	482.4	482.2	482.0	481.6
137.5°	507.8	508.1	507.8	507.6	507.5	507.2	507.3	507.3	507.4	507.4	507.1
140°	522.5	522.6	522.5	522.4	522.3	522.2	522.4	522.6	522.8	523.1	522.8
142.5°	536.7	536.9	537.1	537.2	537.4	537.5	537.5	537.6	537.6	537.7	537.4
145°	558.4	558.5	558.5	558.5	558.5	558.5	558.6	558.8	558.9	559.0	558.7
147.5°	576.0	576.1	576.2	576.4	576.4	576.6	576.8	576.9	577.0	577.1	576.8
150°	587.1	587.1	587.4	587.5	587.8	588.0	588.2	588.4	588.7	588.8	588.6
152.5°	597.4	597.4	597.5	597.8	598.0	598.2	598.5	598.7	598.9	599.1	598.8
155°	611.4	611.2	611.4	611.7	611.8	612.1	612.4	612.8	613.0	613.4	613.1
157.5°	623.8	623.6	623.6	623.6	623.6	623.7	624.1	624.4	624.7	625.1	624.8
160°	630.6	630.3	630.4	630.5	630.6	630.8	631.2	631.6	632.1	632.5	632.2
162.5°	636.9	636.6	636.7	636.8	636.9	637.1	637.7	638.3	638.9	639.5	639.3
165°	645.3	645.1	645.1	645.2	645.4	645.5	646.1	646.8	647.5	648.1	648.0
167.5°	651.5	651.3	651.3	651.4	651.5	651.7	652.5	653.2	654.0	654.8	654.7
170°	654.7	654.4	654.4	654.6	654.7	654.8	655.7	656.6	657.5	658.3	658.2
172.5°	657.0	656.8	656.9	657.2	657.4	657.5	658.3	659.1	660.0	660.7	660.6
175°	660.0	659.8	659.9	660.0	660.1	660.2	661.1	661.9	662.8	663.7	663.7
177.5°	661.8	661.5	661.6	661.7	661.8	661.9	662.5	663.1	663.7	664.3	664.3
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	464.3	462.5	462.0	462.7	462.0	462.5	464.3	464.4	464.6	465.9	464.1
5°	428.3	426.4	427.3	427.0	427.3	426.4	428.3	430.3	430.8	432.5	433.7
7.5°	396.7	394.3	391.7	392.4	391.7	394.3	396.7	396.7	399.8	402.2	403.7
10°	374.6	372.6	371.4	372.5	371.4	372.6	374.6	377.2	378.4	381.2	384.2
12.5°	356.0	354.8	353.8	353.4	353.8	354.8	356.0	358.8	361.5	364.8	368.1
15°	330.6	328.3	327.3	324.7	327.3	328.3	330.6	333.0	338.4	339.8	344.7
17.5°	307.3	306.5	303.9	302.8	303.9	306.5	307.3	309.4	311.8	316.9	320.6
20°	293.4	292.7	290.1	291.6	290.1	292.7	293.4	296.4	298.4	302.6	306.2
22.5°	282.0	280.3	279.4	279.0	279.4	280.3	282.0	283.4	286.0	289.9	293.9
25°	265.8	263.2	262.2	261.1	262.2	263.2	265.8	266.6	269.4	273.2	275.3
27.5°	249.6	248.2	246.9	246.6	246.9	248.2	249.6	250.7	253.2	256.5	260.5
30°	239.1	237.7	236.8	236.8	236.8	237.7	239.1	241.5	243.3	246.3	249.3
32.5°	229.7	228.7	227.6	227.5	227.6	228.7	229.7	231.0	233.2	236.4	239.5
35°	216.0	214.5	214.0	212.8	214.0	214.5	216.0	217.1	219.2	221.6	224.2
37.5°	201.8	200.5	200.5	200.4	200.5	200.5	201.8	203.6	205.4	207.6	210.8
40°	192.8	191.7	191.6	190.2	191.6	191.7	192.8	193.6	195.5	198.4	200.7
42.5°	183.0	182.5	181.8	181.2	181.8	182.5	183.0	184.7	186.3	188.3	191.3
45°	169.9	168.5	168.5	167.6	168.5	168.5	169.9	171.3	172.1	174.4	178.5
47.5°	156.3	155.2	155.3	154.3	155.3	155.2	156.3	156.7	158.0	160.3	162.6
50°	147.2	146.6	146.5	146.0	146.5	146.6	147.2	147.1	148.6	150.8	153.8
52.5°	138.2	137.8	138.6	137.8	138.6	137.8	138.2	138.6	139.7	141.1	144.0
55°	126.0	125.4	126.6	125.4	126.6	125.4	126.0	125.5	126.0	127.3	129.2
57.5°	111.9	111.3	112.4	111.8	112.4	111.3	111.9	111.9	113.1	113.4	114.9
60°	102.6	101.4	102.0	102.3	102.0	101.4	102.6	103.1	103.5	103.7	105.2
62.5°	91.7	90.9	91.4	90.5	91.4	90.9	91.7	92.6	93.4	94.5	95.4
65°	76.2	75.6	74.8	74.4	74.8	75.6	76.2	76.6	78.8	80.0	82.1
67.5°	64.1	62.6	62.5	62.9	62.5	62.6	64.1	64.0	65.5	66.5	67.9
70°	55.1	55.1	54.9	54.9	54.9	55.1	55.1	56.3	57.1	57.9	58.9
72.5°	48.9	48.7	48.4	48.2	48.4	48.7	48.9	49.3	49.8	50.5	51.6
75°	39.4	39.6	39.2	39.0	39.2	39.6	39.4	39.4	40.2	40.4	40.8
77.5°	29.1	28.2	28.7	28.2	28.7	28.2	29.1	29.9	30.1	31.0	31.1
80°	22.0	21.9	22.5	21.9	22.5	21.9	22.0	22.0	22.6	23.1	24.1
82.5°	17.5	17.3	17.6	17.1	17.6	17.3	17.5	17.3	17.6	18.2	18.0
85°	10.5	10.3	10.2	10.3	10.2	10.3	10.5	10.3	10.2	10.3	10.5
87.5°	5.9	5.8	5.8	5.9	5.8	5.8	5.9	5.6	5.7	5.6	5.4
90°	10.8	11.1	11.5	11.8	11.5	11.1	10.8	10.5	10.1	9.5	9.0
92.5°	10.5	10.7	10.8	11.0	10.8	10.7	10.5	10.4	10.1	9.5	9.0
95°	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.1	9.5	9.0
97.5°	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	11.9	14.9	18.0
100°	11.6	11.2	10.8	10.3	10.8	11.2	11.6	12.1	20.4	36.7	53.0
102.5°	84.0	76.6	69.2	61.8	69.2	76.6	84.0	91.5	96.8	99.8	102.9
105°	146.2	146.1	146.0	145.9	146.0	146.1	146.2	146.4	146.4	146.4	146.4
107.5°	184.9	184.6	184.3	183.9	184.3	184.6	184.9	185.2	185.4	185.4	185.4
110°	209.9	210.0	210.2	210.3	210.2	210.0	209.9	209.8	209.9	210.3	210.6



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	234.3	234.1	234.0	233.8	234.0	234.1	234.3	234.5	234.7	235.1	235.6
115°	271.1	270.5	269.8	269.2	269.8	270.5	271.1	271.8	272.3	272.8	273.2
117.5°	307.8	307.5	307.2	306.9	307.2	307.5	307.8	308.1	308.5	309.0	309.6
120°	331.7	331.2	330.6	330.1	330.6	331.2	331.7	332.3	332.7	332.9	333.1
122.5°	354.0	353.4	352.8	352.1	352.8	353.4	354.0	354.6	355.1	355.3	355.5
125°	386.6	386.2	386.0	385.6	386.0	386.2	386.6	386.9	387.3	387.7	388.2
127.5°	416.2	415.4	414.7	413.8	414.7	415.4	416.2	417.1	417.6	417.8	418.0
130°	435.9	435.3	434.8	434.3	434.8	435.3	435.9	436.4	436.9	437.2	437.6
132.5°	454.8	454.2	453.7	453.1	453.7	454.2	454.8	455.3	455.6	455.6	455.7
135°	481.0	480.3	479.6	479.0	479.6	480.3	481.0	481.6	482.0	482.2	482.4
137.5°	506.6	506.0	505.5	504.9	505.5	506.0	506.6	507.1	507.4	507.4	507.3
140°	522.2	521.5	520.9	520.2	520.9	521.5	522.2	522.8	523.1	522.8	522.6
142.5°	536.7	536.1	535.4	534.8	535.4	536.1	536.7	537.4	537.7	537.6	537.6
145°	558.0	557.4	556.7	556.0	556.7	557.4	558.0	558.7	559.0	558.9	558.8
147.5°	576.0	575.2	574.5	573.7	574.5	575.2	576.0	576.8	577.1	577.0	576.9
150°	587.7	586.8	585.9	585.0	585.9	586.8	587.7	588.6	588.8	588.7	588.4
152.5°	598.1	597.3	596.4	595.6	596.4	597.3	598.1	598.8	599.1	598.9	598.7
155°	612.3	611.4	610.5	609.6	610.5	611.4	612.3	613.1	613.4	613.0	612.8
157.5°	624.0	623.0	622.2	621.3	622.2	623.0	624.0	624.8	625.1	624.7	624.4
160°	631.4	630.5	629.6	628.8	629.6	630.5	631.4	632.2	632.5	632.1	631.6
162.5°	638.3	637.4	636.5	635.4	636.5	637.4	638.3	639.3	639.5	638.9	638.3
165°	647.1	646.3	645.4	644.5	645.4	646.3	647.1	648.0	648.1	647.5	646.8
167.5°	653.8	652.7	651.8	650.7	651.8	652.7	653.8	654.7	654.8	654.0	653.2
170°	657.3	656.3	655.3	654.4	655.3	656.3	657.3	658.2	658.3	657.5	656.6
172.5°	659.6	658.7	657.6	656.7	657.6	658.7	659.6	660.6	660.7	660.0	659.1
175°	662.7	661.7	660.7	659.7	660.7	661.7	662.7	663.7	663.7	662.8	661.9
177.5°	663.6	662.9	662.2	661.5	662.2	662.9	663.6	664.3	664.3	663.7	663.1
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	464.6	466.3	467.3	469.5	472.7	474.3	476.5	478.1	480.4	483.0	485.3
5°	434.5	439.3	442.5	447.5	452.0	456.6	462.4	466.5	472.1	478.5	483.5
7.5°	406.6	412.5	417.8	424.4	432.0	437.8	445.4	453.1	461.8	470.8	479.3
10°	388.7	394.7	401.3	409.4	417.0	425.0	433.9	442.9	453.8	463.9	475.4
12.5°	371.1	377.7	385.0	394.2	403.3	413.5	422.6	432.7	444.4	457.6	469.9
15°	349.1	355.5	363.5	371.3	381.8	393.0	405.0	418.4	431.5	446.3	461.6
17.5°	325.6	332.6	341.4	350.4	361.4	374.5	386.4	401.1	415.8	432.9	451.0
20°	310.4	317.5	327.9	337.8	347.9	360.7	374.8	389.8	405.4	423.5	443.7
22.5°	298.3	303.3	313.6	323.6	335.5	348.6	362.4	378.0	395.1	413.9	434.9
25°	280.3	286.3	293.7	304.2	316.5	330.3	344.1	360.7	379.4	398.5	420.9
27.5°	264.3	269.2	276.6	284.8	297.1	311.3	326.1	343.4	362.6	382.0	405.6
30°	253.0	258.5	265.4	274.1	283.9	299.5	314.5	331.5	350.9	371.0	395.3
32.5°	243.2	248.7	254.8	263.0	273.5	287.3	302.9	319.5	339.3	360.1	383.7
35°	229.4	233.2	238.8	246.9	257.3	268.4	284.3	301.8	321.1	342.6	366.3
37.5°	213.5	218.4	223.9	231.1	240.1	252.2	267.0	284.7	302.6	323.1	344.7
40°	204.3	208.9	215.1	220.2	229.8	240.7	254.3	272.8	290.7	310.0	329.7
42.5°	194.9	199.3	204.6	211.0	219.6	230.2	242.8	260.0	279.2	297.4	313.9
45°	180.2	184.9	189.8	195.8	203.7	214.0	226.6	242.3	259.0	275.8	288.3
47.5°	166.2	170.5	175.2	181.3	188.6	198.6	209.8	223.8	240.0	254.2	263.1
50°	156.2	160.1	165.3	171.3	178.5	187.8	198.5	212.2	225.8	238.8	246.9
52.5°	146.3	150.8	155.9	161.1	168.0	177.3	187.3	199.1	212.0	222.5	229.2
55°	131.5	135.7	140.4	145.9	152.6	160.6	171.1	180.5	190.6	199.6	203.5
57.5°	117.2	120.9	125.4	131.0	137.1	144.5	152.8	161.8	168.9	175.3	179.8
60°	107.8	111.0	115.2	119.9	126.6	133.3	140.9	149.2	154.8	160.1	164.4
62.5°	98.2	101.3	105.3	109.6	115.4	121.7	128.9	135.7	141.1	144.7	149.6
65°	83.9	87.0	90.3	94.9	99.4	104.6	111.2	116.1	119.9	124.0	126.9
67.5°	70.6	73.1	76.3	79.9	83.8	88.8	93.8	98.0	100.6	103.0	106.5
70°	61.9	63.9	66.5	69.2	73.4	78.4	82.4	85.6	87.3	89.7	94.1
72.5°	53.0	55.3	57.7	60.4	63.9	68.0	71.5	74.7	75.9	77.7	80.6
75°	41.8	43.0	44.9	46.9	49.3	53.0	56.3	57.1	58.1	59.7	61.6
77.5°	31.6	32.6	33.5	34.8	36.7	39.5	41.3	42.5	42.8	43.4	45.3
80°	25.1	25.7	26.4	27.5	28.2	30.7	31.6	32.8	33.2	33.8	34.8
82.5°	18.4	18.9	19.5	20.3	21.5	22.6	23.5	24.7	24.8	25.2	25.4
85°	10.8	10.9	10.5	10.9	11.1	11.5	12.6	13.5	13.3	13.2	13.7
87.5°	5.5	5.4	5.1	5.4	4.9	4.9	4.7	4.7	4.9	5.1	5.2
90°	8.4	7.8	7.1	6.4	5.6	4.8	4.0	3.1	2.2	1.4	0.5
92.5°	8.4	7.8	7.1	6.5	5.9	5.2	5.1	5.8	6.4	7.0	7.6
95°	8.4	7.8	12.0	16.2	20.3	24.5	26.7	27.0	27.4	27.6	28.0
97.5°	21.1	24.2	32.4	40.6	48.8	57.0	60.8	60.2	59.7	59.1	58.5
100°	69.2	85.5	85.1	84.6	84.2	83.7	83.3	83.0	82.7	82.4	82.1
102.5°	106.0	109.1	108.8	108.6	108.2	108.0	107.6	107.3	106.9	106.4	106.0
105°	146.4	146.4	146.4	146.4	146.4	146.4	146.2	145.8	145.3	144.8	144.4
107.5°	185.3	185.3	185.1	184.9	184.6	184.4	184.3	184.3	184.3	184.3	184.3
110°	210.9	211.2	211.0	210.8	210.6	210.3	210.3	210.3	210.3	210.3	210.3



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	236.0	236.3	236.3	236.1	236.0	235.8	235.7	235.4	235.1	234.9	234.6
115°	273.7	274.1	274.0	273.9	273.8	273.7	273.4	272.8	272.2	271.7	271.1
117.5°	310.2	310.7	310.3	310.0	309.5	309.1	308.9	308.9	308.9	308.9	309.0
120°	333.3	333.6	333.2	332.9	332.6	332.3	332.1	332.3	332.3	332.4	332.6
122.5°	355.8	355.9	355.8	355.7	355.5	355.3	355.1	354.6	354.2	353.8	353.4
125°	388.7	389.1	389.1	389.1	389.1	389.1	388.7	387.9	387.1	386.4	385.6
127.5°	418.3	418.5	418.6	418.7	418.7	418.8	418.5	418.0	417.5	416.9	416.4
130°	437.8	438.2	438.1	438.0	437.8	437.7	437.4	436.9	436.4	435.8	435.2
132.5°	455.8	455.9	456.1	456.3	456.6	456.8	456.6	456.0	455.4	454.7	454.1
135°	482.7	482.8	483.1	483.3	483.5	483.8	483.5	482.8	482.2	481.6	481.0
137.5°	507.3	507.2	507.5	507.6	507.8	508.1	507.8	507.3	506.7	506.2	505.6
140°	522.4	522.2	522.3	522.4	522.5	522.6	522.5	522.4	522.1	521.9	521.7
142.5°	537.5	537.5	537.4	537.2	537.1	536.9	536.7	536.7	536.5	536.4	536.2
145°	558.6	558.5	558.5	558.5	558.5	558.5	558.4	558.2	558.0	557.8	557.6
147.5°	576.8	576.6	576.4	576.4	576.2	576.1	576.0	576.1	576.1	576.2	576.2
150°	588.2	588.0	587.8	587.5	587.4	587.1	587.1	587.4	587.5	587.8	588.0
152.5°	598.5	598.2	598.0	597.8	597.5	597.4	597.4	598.0	598.5	598.9	599.4
155°	612.4	612.1	611.8	611.7	611.4	611.2	611.4	612.1	612.8	613.4	614.1
157.5°	624.1	623.7	623.6	623.6	623.6	623.6	623.8	624.1	624.6	624.9	625.3
160°	631.2	630.8	630.6	630.5	630.4	630.3	630.6	631.2	631.9	632.6	633.2
162.5°	637.7	637.1	636.9	636.8	636.7	636.6	636.9	637.5	638.2	638.9	639.5
165°	646.1	645.5	645.4	645.2	645.1	645.1	645.3	646.0	646.6	647.3	647.9
167.5°	652.5	651.7	651.5	651.4	651.3	651.3	651.5	652.2	652.9	653.6	654.2
170°	655.7	654.8	654.7	654.6	654.4	654.4	654.7	655.5	656.3	657.0	657.8
172.5°	658.3	657.5	657.4	657.2	656.9	656.8	657.0	657.8	658.6	659.4	660.1
175°	661.1	660.2	660.1	660.0	659.9	659.8	660.0	660.7	661.3	662.0	662.7
177.5°	662.5	661.9	661.8	661.7	661.6	661.5	661.8	662.3	662.8	663.3	663.8
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	487.0	488.4	490.5	492.9	494.8	496.9	498.0	498.0	498.9	501.0	503.8
5°	488.4	493.6	498.5	504.9	509.9	515.7	520.0	524.3	528.0	532.8	537.8
7.5°	488.0	496.6	505.6	515.6	526.7	535.5	544.5	551.6	558.5	567.7	574.9
10°	486.5	497.6	509.7	522.5	536.4	548.5	559.5	569.4	578.9	588.9	597.9
12.5°	483.5	497.7	512.6	527.9	545.4	559.3	573.4	584.0	595.2	606.1	617.1
15°	479.2	495.9	513.8	535.2	556.6	572.1	586.1	599.9	610.2	622.5	633.1
17.5°	470.4	491.9	514.4	537.7	558.4	576.4	591.0	604.1	615.1	628.6	643.0
20°	465.1	488.4	511.9	536.7	556.5	575.0	589.1	602.6	616.3	634.0	651.5
22.5°	457.8	482.7	507.6	531.2	552.0	569.9	584.4	601.0	619.1	639.1	660.3
25°	446.3	471.9	496.5	519.0	539.3	557.7	577.6	599.9	621.7	648.2	678.6
27.5°	431.5	456.3	478.3	502.0	522.2	545.5	570.3	594.5	626.0	662.5	700.4
30°	420.6	444.0	464.9	487.4	510.3	536.0	563.8	592.3	629.9	672.6	717.8
32.5°	407.9	429.1	449.8	471.5	497.9	526.1	555.7	590.5	635.4	684.1	730.8
35°	385.7	404.8	425.0	449.0	477.1	507.7	545.5	587.9	642.2	694.5	736.5
37.5°	362.6	377.7	397.9	423.3	453.8	489.2	532.2	583.7	639.4	686.4	704.2
40°	344.7	358.9	380.2	406.8	437.1	475.9	524.0	577.0	633.1	665.6	664.3
42.5°	327.1	341.4	361.9	388.7	420.3	463.6	513.2	568.2	615.5	627.9	602.1
45°	300.0	313.3	333.5	360.5	394.3	439.9	492.0	544.8	575.0	554.8	503.5
47.5°	272.4	285.3	304.0	330.5	367.4	415.1	464.4	507.6	511.9	468.7	407.2
50°	254.3	266.4	284.1	312.4	348.2	394.7	442.3	476.3	465.7	413.0	349.6
52.5°	236.6	248.2	264.8	291.5	328.1	373.7	416.1	442.9	418.4	362.4	305.3
55°	210.5	221.6	238.3	262.8	296.0	337.8	375.1	384.8	349.0	292.5	246.3
57.5°	185.7	193.9	210.3	232.0	264.1	300.9	327.5	325.8	286.3	235.4	202.2
60°	169.3	176.7	192.3	212.2	242.7	275.8	294.5	286.5	246.5	204.5	172.7
62.5°	154.0	160.9	174.1	192.3	218.5	247.3	260.9	249.9	212.2	175.2	149.9
65°	130.9	135.9	146.5	163.3	183.8	203.7	215.9	199.8	166.3	138.4	119.3
67.5°	109.3	113.6	123.0	135.1	149.2	163.0	167.9	152.8	126.8	108.1	94.5
70°	95.3	99.3	105.6	117.0	126.3	136.0	138.4	124.9	103.2	88.9	80.6
72.5°	82.0	85.6	91.2	99.2	105.6	111.2	112.4	99.8	83.2	73.4	66.9
75°	62.5	65.7	69.2	72.2	76.4	77.4	77.0	67.2	58.3	51.7	48.1
77.5°	45.9	47.3	49.4	50.6	50.8	50.7	48.7	42.5	37.9	35.2	33.8
80°	35.4	36.4	37.0	37.4	37.6	35.6	33.4	29.6	28.1	26.4	24.7
82.5°	25.7	26.3	26.9	27.0	26.0	24.3	22.3	20.4	19.3	18.5	17.8
85°	13.9	14.1	13.9	12.9	11.5	10.9	10.5	10.2	10.0	9.7	9.7
87.5°	5.2	4.9	4.3	4.6	4.8	4.7	4.9	4.9	4.9	5.0	5.2
90°	1.4	2.2	3.1	4.0	4.8	5.6	6.4	7.1	7.8	8.4	9.0
92.5°	7.0	6.4	5.8	5.1	5.2	5.9	6.5	7.1	7.8	8.4	9.0
95°	27.6	27.4	27.0	26.7	24.5	20.3	16.2	12.0	7.8	8.4	9.0
97.5°	59.1	59.7	60.2	60.8	57.0	48.8	40.6	32.4	24.2	21.1	18.0
100°	82.4	82.7	83.0	83.3	83.7	84.2	84.6	85.1	85.5	69.2	53.0
102.5°	106.4	106.9	107.3	107.6	108.0	108.2	108.6	108.8	109.1	106.0	102.9
105°	144.8	145.3	145.8	146.2	146.4	146.4	146.4	146.4	146.4	146.4	146.4
107.5°	184.3	184.3	184.3	184.3	184.4	184.6	184.9	185.1	185.3	185.3	185.4
110°	210.3	210.3	210.3	210.3	210.3	210.6	210.8	211.0	211.2	210.9	210.6



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	234.9	235.1	235.4	235.7	235.8	236.0	236.1	236.3	236.3	236.0	235.6
115°	271.7	272.2	272.8	273.4	273.7	273.8	273.9	274.0	274.1	273.7	273.2
117.5°	308.9	308.9	308.9	308.9	309.1	309.5	310.0	310.3	310.7	310.2	309.6
120°	332.4	332.3	332.3	332.1	332.3	332.6	332.9	333.2	333.6	333.3	333.1
122.5°	353.8	354.2	354.6	355.1	355.3	355.5	355.7	355.8	355.9	355.8	355.5
125°	386.4	387.1	387.9	388.7	389.1	389.1	389.1	389.1	389.1	388.7	388.2
127.5°	416.9	417.5	418.0	418.5	418.8	418.7	418.7	418.6	418.5	418.3	418.0
130°	435.8	436.4	436.9	437.4	437.7	437.8	438.0	438.1	438.2	437.8	437.6
132.5°	454.7	455.4	456.0	456.6	456.8	456.6	456.3	456.1	455.9	455.8	455.7
135°	481.6	482.2	482.8	483.5	483.8	483.5	483.3	483.1	482.8	482.7	482.4
137.5°	506.2	506.7	507.3	507.8	508.1	507.8	507.6	507.5	507.2	507.3	507.3
140°	521.9	522.1	522.4	522.5	522.6	522.5	522.4	522.3	522.2	522.4	522.6
142.5°	536.4	536.5	536.7	536.7	536.9	537.1	537.2	537.4	537.5	537.5	537.6
145°	557.8	558.0	558.2	558.4	558.5	558.5	558.5	558.5	558.5	558.6	558.8
147.5°	576.2	576.1	576.1	576.0	576.1	576.2	576.4	576.4	576.6	576.8	576.9
150°	587.8	587.5	587.4	587.1	587.1	587.4	587.5	587.8	588.0	588.2	588.4
152.5°	598.9	598.5	598.0	597.4	597.4	597.5	597.8	598.0	598.2	598.5	598.7
155°	613.4	612.8	612.1	611.4	611.2	611.4	611.7	611.8	612.1	612.4	612.8
157.5°	624.9	624.6	624.1	623.8	623.6	623.6	623.6	623.6	623.7	624.1	624.4
160°	632.6	631.9	631.2	630.6	630.3	630.4	630.5	630.6	630.8	631.2	631.6
162.5°	638.9	638.2	637.5	636.9	636.6	636.7	636.8	636.9	637.1	637.7	638.3
165°	647.3	646.6	646.0	645.3	645.1	645.1	645.2	645.4	645.5	646.1	646.8
167.5°	653.6	652.9	652.2	651.5	651.3	651.3	651.4	651.5	651.7	652.5	653.2
170°	657.0	656.3	655.5	654.7	654.4	654.4	654.6	654.7	654.8	655.7	656.6
172.5°	659.4	658.6	657.8	657.0	656.8	656.9	657.2	657.4	657.5	658.3	659.1
175°	662.0	661.3	660.7	660.0	659.8	659.9	660.0	660.1	660.2	661.1	661.9
177.5°	663.3	662.8	662.3	661.8	661.5	661.6	661.7	661.8	661.9	662.5	663.1
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	505.8	505.8	508.5	508.3	510.1	509.5	509.8
5°	543.7	547.1	550.1	552.1	555.1	555.9	555.4
7.5°	583.1	590.6	594.2	599.3	600.1	602.8	602.5
10°	607.3	614.8	620.4	624.7	626.9	629.6	629.9
12.5°	626.5	632.7	637.7	641.7	644.4	645.2	645.8
15°	641.4	648.3	654.1	659.9	663.3	665.9	667.3
17.5°	656.4	667.2	677.3	685.2	689.9	693.9	693.9
20°	668.0	680.4	693.1	702.1	711.3	715.2	715.8
22.5°	680.4	699.3	715.7	729.6	741.7	745.8	747.3
25°	706.3	730.9	756.2	775.7	789.6	797.8	799.0
27.5°	737.4	770.8	797.4	815.4	826.9	833.0	834.3
30°	759.4	790.2	814.1	827.6	833.0	833.8	830.8
32.5°	769.2	792.3	801.8	801.1	790.5	783.5	780.8
35°	757.2	752.4	729.2	701.3	680.0	666.5	662.9
37.5°	689.1	647.9	605.1	563.0	540.6	529.2	509.6
40°	621.9	563.2	518.7	483.3	458.0	437.6	432.9
42.5°	546.1	485.5	441.0	410.7	390.5	376.6	370.5
45°	438.9	386.8	349.9	326.7	311.2	301.0	296.4
47.5°	351.0	310.6	283.9	266.7	254.8	246.0	243.5
50°	302.8	270.5	247.9	233.3	224.4	217.7	214.9
52.5°	263.0	236.9	219.6	207.6	199.1	194.9	192.6
55°	217.1	194.6	182.0	172.5	167.7	164.4	162.7
57.5°	177.5	161.3	152.1	145.5	141.1	139.0	138.2
60°	155.4	142.7	134.3	129.2	126.1	123.4	122.5
62.5°	135.8	125.8	119.3	114.8	111.8	110.6	110.1
65°	109.4	102.9	98.1	95.3	92.9	92.5	92.3
67.5°	87.0	83.1	80.6	77.7	76.9	75.5	75.2
70°	74.4	71.8	68.8	67.8	66.8	65.4	65.7
72.5°	63.1	60.5	58.5	57.2	56.8	56.2	56.7
75°	46.1	45.4	44.6	43.6	43.1	43.1	43.0
77.5°	33.0	32.3	31.4	30.8	30.7	29.9	30.1
80°	23.8	22.9	22.5	22.6	22.0	21.9	21.9
82.5°	17.7	17.3	16.9	17.0	16.8	16.6	16.8
85°	9.7	9.6	9.6	9.4	9.4	9.1	9.1
87.5°	5.4	5.7	5.4	5.3	5.4	5.6	5.9
90°	9.5	10.1	10.5	10.8	11.1	11.5	11.8
92.5°	9.5	10.1	10.4	10.5	10.7	10.8	11.0
95°	9.5	10.1	10.3	10.3	10.3	10.3	10.3
97.5°	14.9	11.9	10.3	10.3	10.3	10.3	10.3
100°	36.7	20.4	12.1	11.6	11.2	10.8	10.3
102.5°	99.8	96.8	91.5	84.0	76.6	69.2	61.8
105°	146.4	146.4	146.4	146.2	146.1	146.0	145.9
107.5°	185.4	185.4	185.2	184.9	184.6	184.3	183.9
110°	210.3	209.9	209.8	209.9	210.0	210.2	210.3



TEST NUMBER: P333496-935

CATALOG NUMBER: S125RDIP-S375D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	235.1	234.7	234.5	234.3	234.1	234.0	233.8
115°	272.8	272.3	271.8	271.1	270.5	269.8	269.2
117.5°	309.0	308.5	308.1	307.8	307.5	307.2	306.9
120°	332.9	332.7	332.3	331.7	331.2	330.6	330.1
122.5°	355.3	355.1	354.6	354.0	353.4	352.8	352.1
125°	387.7	387.3	386.9	386.6	386.2	386.0	385.6
127.5°	417.8	417.6	417.1	416.2	415.4	414.7	413.8
130°	437.2	436.9	436.4	435.9	435.3	434.8	434.3
132.5°	455.6	455.6	455.3	454.8	454.2	453.7	453.1
135°	482.2	482.0	481.6	481.0	480.3	479.6	479.0
137.5°	507.4	507.4	507.1	506.6	506.0	505.5	504.9
140°	522.8	523.1	522.8	522.2	521.5	520.9	520.2
142.5°	537.6	537.7	537.4	536.7	536.1	535.4	534.8
145°	558.9	559.0	558.7	558.0	557.4	556.7	556.0
147.5°	577.0	577.1	576.8	576.0	575.2	574.5	573.7
150°	588.7	588.8	588.6	587.7	586.8	585.9	585.0
152.5°	598.9	599.1	598.8	598.1	597.3	596.4	595.6
155°	613.0	613.4	613.1	612.3	611.4	610.5	609.6
157.5°	624.7	625.1	624.8	624.0	623.0	622.2	621.3
160°	632.1	632.5	632.2	631.4	630.5	629.6	628.8
162.5°	638.9	639.5	639.3	638.3	637.4	636.5	635.4
165°	647.5	648.1	648.0	647.1	646.3	645.4	644.5
167.5°	654.0	654.8	654.7	653.8	652.7	651.8	650.7
170°	657.5	658.3	658.2	657.3	656.3	655.3	654.4
172.5°	660.0	660.7	660.6	659.6	658.7	657.6	656.7
175°	662.8	663.7	663.7	662.7	661.7	660.7	659.7
177.5°	663.7	664.3	664.3	663.6	662.9	662.2	661.5
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7

(END OF REPORT)