

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333546-935

Luminaire Tested: **S125RDIP-S610D1205U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333546-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D1205U935-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5788.2 lumens  
Efficiency: N/A  
Efficacy: 117.2 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333546-935  
CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	38	38	37	31
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	31	26
3	79	70	63	58	71	64	58	53	52	48	44	41	38	35	30	29	27	22
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19
5	66	55	48	42	60	50	44	39	41	36	32	33	29	26	25	22	21	17
6	61	50	42	36	55	45	38	34	37	32	28	30	26	23	22	20	18	15
7	57	45	37	32	51	41	34	29	34	29	25	27	23	20	21	18	16	13
8	52	41	33	28	47	37	31	26	31	26	22	25	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5146	5146	5146	5146
5°	5920	5153	4550	5153
10°	6791	5126	4015	5126
15°	7335	5073	3569	5073
20°	8088	5013	3296	5013
25°	9360	4932	3058	4932
30°	10185	4847	2902	4847
35°	8592	4747	2759	4747
40°	6000	4569	2636	4569
45°	4451	4328	2515	4328
50°	3550	4078	2411	4078
55°	3012	3768	2320	3768
60°	2603	3490	2173	3490
65°	2320	3189	1869	3189
70°	2039	2921	1703	2921
75°	1764	2530	1599	2530
80°	1339	2131	1339	2131
85°	1119	1675	1260	1675



TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.4	1.3
10°-20°	223.9	3.9
20°-30°	355.0	6.1
30°-40°	428.1	7.4
40°-50°	382.3	6.6
50°-60°	293.2	5.1
60°-70°	190.5	3.3
70°-80°	92.6	1.6
80°-90°	24.9	0.4
90°-100°	359.7	6.2
100°-110°	773.2	13.4
110°-120°	725.6	12.5
120°-130°	588.1	10.2
130°-140°	471.9	8.2
140°-150°	356.1	6.2
150°-160°	250.7	4.3
160°-170°	147.8	2.6
170°-180°	48.1	0.8
0°-30°	655.3	11.3
0°-40°	1083.4	18.7
0°-60°	1758.9	30.4
0°-90°	2067.0	35.7
90°-120°	1858.5	32.1
90°-150°	3274.7	56.6
90°-180°	3721.0	64.3
0°-180°	5788.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	797	797	797	797	797	
5°	913	795	702	795	913	91
15°	1097	759	534	759	1097	314
25°	1314	692	429	692	1314	603
35°	1090	602	350	602	1090	658
45°	487	474	275	474	487	389
55°	268	335	206	335	268	243
65°	152	209	122	209	152	151
75°	71	101	64	101	71	75
85°	15	23	17	23	15	18
90°	23	1	23	1	23	16
95°	235	33	235	33	235	333
105°	1326	113	1326	113	1326	1318
115°	1477	202	1477	202	1477	1443
125°	1164	280	1164	280	1164	1053
135°	966	328	966	328	966	749
145°	762	382	762	382	762	484
155°	639	436	639	436	639	298
165°	560	476	560	476	560	160
175°	503	495	503	495	503	49
180°	496	496	496	496	496	



TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	838.1	837.6	838.6	835.7	836.0	831.6	831.6	828.1	823.7	820.3	818.7
5°	913.2	913.9	912.5	907.6	904.3	899.4	893.9	884.1	875.9	868.1	861.9
7.5°	990.5	990.9	986.6	985.2	976.9	970.9	958.6	945.2	933.3	918.3	906.8
10°	1035.5	1035.2	1030.6	1027.0	1019.8	1010.6	998.5	982.8	968.1	951.7	936.1
12.5°	1061.7	1060.8	1059.4	1055.0	1048.4	1040.2	1029.9	1014.5	996.3	978.4	960.2
15°	1097.0	1094.7	1090.5	1084.9	1075.4	1065.9	1054.5	1040.8	1023.4	1003.2	986.1
17.5°	1140.7	1140.7	1134.2	1126.5	1113.6	1096.8	1079.2	1057.0	1033.5	1011.2	993.1
20°	1176.8	1175.8	1169.2	1154.3	1139.5	1118.6	1098.3	1071.2	1042.4	1013.2	990.7
22.5°	1228.6	1226.1	1219.3	1199.5	1176.6	1149.7	1118.7	1085.5	1050.8	1017.7	988.1
25°	1313.5	1311.6	1298.1	1275.2	1243.2	1201.6	1161.1	1115.6	1065.6	1022.1	986.1
27.5°	1371.6	1369.4	1359.5	1340.5	1310.9	1267.2	1212.3	1151.6	1089.1	1029.2	977.3
30°	1365.8	1370.7	1369.4	1360.6	1338.3	1299.1	1248.4	1180.1	1105.8	1035.5	973.7
32.5°	1283.7	1288.1	1299.6	1316.9	1318.2	1302.5	1264.6	1201.5	1124.6	1044.7	970.8
35°	1089.8	1095.7	1117.9	1152.9	1198.7	1237.0	1244.8	1210.8	1141.8	1055.8	966.5
37.5°	837.8	870.0	888.7	925.6	994.7	1065.1	1132.8	1157.8	1128.4	1051.2	959.5
40°	711.7	719.5	752.9	794.4	852.6	925.9	1022.4	1092.1	1094.3	1040.8	948.5
42.5°	609.2	619.1	642.0	675.1	725.0	798.2	897.9	989.8	1032.3	1011.9	934.1
45°	487.3	494.8	511.5	537.0	575.3	635.8	721.5	827.9	912.2	945.2	895.5
47.5°	400.4	404.4	418.9	438.3	466.7	510.7	577.0	669.3	770.6	841.5	834.6
50°	353.3	357.8	368.9	383.7	407.5	444.8	497.8	574.6	679.0	765.7	783.0
52.5°	316.6	320.4	327.4	341.3	360.9	389.6	432.4	502.0	595.8	687.9	728.1
55°	267.5	270.2	275.7	283.5	299.3	319.9	356.8	404.9	480.8	573.7	632.6
57.5°	227.1	228.4	232.0	239.2	250.0	265.1	291.8	332.6	387.0	470.6	535.6
60°	201.5	202.8	207.3	212.2	220.8	234.5	255.5	283.9	336.2	405.3	471.0
62.5°	181.1	181.8	183.8	188.7	196.1	206.8	223.3	246.5	288.1	348.7	410.8
65°	151.8	152.1	152.7	156.7	161.3	169.1	179.9	196.2	227.6	273.5	328.4
67.5°	123.6	124.1	126.4	127.8	132.5	136.6	143.0	155.5	177.6	208.4	251.2
70°	108.0	107.6	109.9	111.5	113.1	118.0	122.3	132.4	146.2	169.8	205.4
72.5°	93.2	92.5	93.4	94.0	96.2	99.5	103.8	109.9	120.5	136.8	164.0
75°	70.7	70.9	70.9	71.6	73.3	74.6	75.9	79.1	85.1	95.8	110.6
77.5°	49.6	49.1	50.5	50.6	51.6	53.0	54.2	55.4	57.9	62.3	69.9
80°	36.0	36.0	36.3	37.3	36.9	37.6	39.3	40.6	43.5	46.1	48.7
82.5°	27.6	27.4	27.6	27.9	27.8	28.4	29.0	29.3	30.4	31.7	33.6
85°	15.1	15.1	15.4	15.4	15.7	15.7	16.0	16.0	16.0	16.4	16.7
87.5°	10.3	10.1	9.6	9.6	9.9	10.0	9.6	9.1	8.9	8.7	8.5
90°	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0	17.0	16.0	14.0
92.5°	63.8	65.4	66.8	69.2	82.1	96.9	128.6	177.3	261.1	322.5	327.8
95°	235.1	251.2	259.1	289.1	360.2	444.2	567.2	719.3	867.4	886.4	723.3
97.5°	568.3	581.1	610.1	666.1	727.9	844.8	964.7	1071.3	1097.5	946.6	645.9
100°	780.3	796.3	833.4	905.4	974.4	1078.5	1181.6	1230.5	1153.5	903.4	576.3
102.5°	1017.3	1029.2	1069.4	1120.7	1194.6	1265.0	1314.4	1284.2	1119.9	827.3	523.4
105°	1325.6	1337.6	1357.6	1390.6	1422.6	1433.7	1389.7	1252.6	1012.4	725.3	472.2
107.5°	1489.3	1497.3	1503.9	1504.1	1487.9	1435.6	1322.6	1139.7	902.8	655.0	450.6
110°	1543.7	1543.7	1536.7	1517.7	1472.7	1387.6	1246.6	1056.4	840.3	622.2	444.2



TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1537.3	1530.1	1512.7	1480.1	1414.2	1314.0	1171.3	990.8	793.9	603.0	444.2
115°	1476.6	1463.6	1435.6	1387.6	1309.6	1200.5	1063.5	908.4	743.3	582.3	447.2
117.5°	1370.4	1362.4	1334.6	1285.0	1206.9	1106.9	988.9	855.1	713.1	572.0	453.8
120°	1301.6	1293.6	1266.5	1218.6	1144.5	1056.4	946.4	826.4	696.3	567.2	460.2
122.5°	1240.8	1233.6	1206.5	1162.5	1096.5	1014.1	916.0	804.8	681.9	563.3	465.8
125°	1163.6	1153.5	1131.5	1090.5	1034.5	962.4	875.4	773.4	662.3	558.3	475.2
127.5°	1097.5	1093.1	1072.3	1036.0	985.2	917.8	836.5	741.3	644.3	555.9	485.8
130°	1061.4	1055.5	1035.4	1002.5	952.4	887.4	809.3	721.3	632.3	554.2	492.2
132.5°	1025.5	1018.6	1000.2	967.2	917.2	854.5	783.8	701.3	622.7	554.2	499.4
135°	966.5	960.4	942.5	909.4	865.4	808.4	744.3	675.3	611.3	554.2	509.2
137.5°	903.4	896.8	880.2	850.2	810.8	762.3	709.1	653.3	601.1	555.4	518.2
140°	859.4	854.4	839.4	813.4	776.4	734.3	688.3	641.3	596.2	556.2	522.2
142.5°	818.6	814.3	800.1	778.2	746.7	710.3	670.7	630.9	592.3	557.1	524.6
145°	762.3	758.4	747.3	730.3	706.3	679.3	648.2	617.3	586.3	556.2	527.3
147.5°	714.7	712.9	706.5	692.9	673.9	653.5	629.6	604.5	580.1	553.6	528.2
150°	688.3	687.3	683.3	671.3	656.3	638.3	619.3	597.3	575.2	551.2	528.2
152.5°	667.5	666.5	662.5	652.9	640.3	626.3	608.9	589.3	569.6	548.0	527.4
155°	639.3	638.3	635.2	628.3	618.3	607.3	593.2	577.2	560.3	542.3	525.2
157.5°	614.1	614.2	611.5	605.6	597.9	589.3	578.4	565.2	551.5	536.2	522.6
160°	597.3	598.3	596.2	591.2	584.3	577.2	567.2	557.2	544.2	532.3	520.2
162.5°	582.0	582.3	581.9	577.6	572.2	566.0	557.7	548.5	537.9	527.4	517.8
165°	560.3	560.3	560.3	558.3	554.2	549.2	543.2	536.2	528.2	520.2	514.2
167.5°	540.3	540.4	541.2	539.4	537.4	533.8	529.3	524.6	518.8	513.2	508.6
170°	528.2	529.3	529.3	528.2	526.2	524.3	521.2	518.2	513.2	509.2	506.3
172.5°	517.0	518.1	519.6	517.8	517.5	516.3	514.0	511.0	507.6	504.5	503.0
175°	503.3	504.2	506.3	505.2	505.2	505.2	503.3	503.3	500.2	499.2	499.2
177.5°	496.2	496.2	498.6	497.8	498.6	498.6	498.6	497.8	497.1	496.2	496.2
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	818.7	816.9	813.5	810.4	806.4	803.1	800.6	797.8	794.1	789.7	786.0
5°	855.0	847.7	838.3	830.1	819.7	811.5	803.0	794.8	786.6	776.1	767.0
7.5°	895.1	880.3	865.8	847.7	831.1	816.4	802.3	788.0	774.0	759.1	744.8
10°	919.7	901.7	881.8	858.8	837.9	818.0	799.7	781.7	762.8	746.1	728.1
12.5°	942.7	919.5	896.7	867.8	842.7	818.3	795.0	772.6	752.3	730.6	711.3
15°	963.5	940.6	915.2	879.9	844.8	815.4	787.9	758.8	733.7	709.4	687.9
17.5°	971.6	947.6	917.9	884.0	845.8	808.7	773.4	741.4	711.8	683.5	659.3
20°	968.5	945.2	914.8	882.4	841.5	803.0	764.7	729.4	696.3	666.6	640.8
22.5°	960.9	936.9	907.5	873.3	834.5	793.5	752.7	715.0	680.4	649.5	621.4
25°	949.5	916.8	886.7	853.3	816.4	775.8	733.7	692.1	655.1	623.7	593.0
27.5°	937.6	896.8	858.6	825.4	786.4	750.2	709.5	666.9	628.0	596.1	564.6
30°	927.0	881.1	839.0	801.3	764.4	730.0	691.4	649.9	610.0	577.0	544.9
32.5°	913.6	864.9	818.6	775.2	739.5	705.4	670.5	630.8	591.9	557.8	525.3
35°	896.8	834.7	784.3	738.2	698.6	665.6	634.2	602.1	563.2	527.9	496.2
37.5°	874.9	804.3	746.1	695.8	654.1	620.9	596.2	566.8	531.3	497.5	468.0
40°	861.5	782.4	718.6	668.8	625.0	590.0	566.8	541.9	509.5	477.9	448.4
42.5°	843.7	762.2	690.9	639.0	595.0	561.3	537.8	516.1	488.9	459.0	427.5
45°	808.8	723.2	648.2	592.6	548.2	515.1	493.2	473.9	453.3	425.9	398.4
47.5°	763.4	682.4	604.0	543.3	499.7	469.1	447.8	432.6	417.8	394.5	367.8
50°	727.1	648.9	572.4	513.5	467.1	437.9	418.0	405.9	392.4	371.3	349.0
52.5°	684.2	614.4	539.4	479.2	435.4	408.1	388.9	376.9	365.8	348.4	327.3
55°	616.6	555.3	486.6	432.0	391.8	364.4	346.0	334.6	328.0	313.3	296.6
57.5°	538.5	494.6	434.1	381.4	345.9	318.7	305.3	295.6	288.2	277.8	266.0
60°	484.1	453.3	399.0	349.0	316.2	290.4	278.4	270.2	263.3	254.4	245.3
62.5°	428.9	406.5	359.3	316.2	286.2	264.5	253.2	245.8	237.9	232.0	223.1
65°	354.9	334.9	302.2	268.5	240.7	223.4	215.2	208.7	203.8	197.3	191.0
67.5°	276.0	267.9	245.4	222.1	202.2	186.8	179.7	175.1	169.2	165.3	161.0
70°	227.6	223.7	207.7	192.3	173.7	163.2	156.7	154.7	147.5	143.6	140.6
72.5°	184.8	182.9	173.7	163.0	149.9	140.7	134.7	132.4	127.9	124.8	122.9
75°	126.6	127.3	125.6	118.7	113.8	108.0	102.7	101.4	98.2	95.5	93.8
77.5°	80.1	83.4	83.5	83.2	81.3	77.7	75.5	74.5	71.3	70.3	69.9
80°	54.9	58.5	61.8	61.5	60.9	59.8	58.2	57.3	55.6	54.6	54.0
82.5°	36.6	40.0	42.7	44.5	44.3	43.4	42.3	41.8	41.5	40.7	40.6
85°	17.3	18.0	18.9	21.3	22.9	23.2	22.9	22.6	21.6	22.0	22.2
87.5°	8.6	8.2	8.3	7.9	7.2	8.1	8.5	8.6	8.3	8.1	8.0
90°	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0	2.0	4.0	6.0
92.5°	228.3	136.6	82.1	52.9	35.6	23.2	14.8	12.2	14.8	23.2	35.6
95°	447.2	227.1	120.0	75.0	53.0	42.0	34.0	33.0	34.0	42.0	53.0
97.5°	357.0	195.7	124.8	92.5	72.7	61.6	56.1	54.8	56.1	61.6	72.7
100°	324.2	194.1	136.0	106.1	87.0	76.0	72.1	70.0	72.1	76.0	87.0
102.5°	310.6	201.3	149.6	120.5	103.1	91.3	88.1	86.9	88.1	91.3	103.1
105°	305.1	216.1	172.1	144.0	128.0	118.0	113.0	113.0	113.0	118.0	128.0
107.5°	314.4	238.1	195.4	170.3	153.7	145.4	140.7	138.6	140.7	145.4	153.7
110°	323.1	254.1	213.1	187.1	172.1	163.1	159.1	157.0	159.1	163.1	172.1





TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.3	269.3	229.9	204.7	189.7	180.6	177.5	175.5	177.5	180.6	189.7
115°	351.1	293.2	256.1	231.1	216.1	207.1	204.1	202.1	204.1	207.1	216.1
117.5°	370.4	317.5	282.5	258.3	241.3	232.3	229.1	226.1	229.1	232.3	241.3
120°	383.1	335.2	300.1	275.1	258.1	249.1	245.1	242.1	245.1	249.1	258.1
122.5°	397.6	352.0	316.9	292.0	273.3	264.3	261.1	258.9	261.1	264.3	273.3
125°	417.2	374.2	341.1	315.1	296.1	287.1	282.1	280.1	282.1	287.1	296.1
127.5°	435.2	395.5	363.8	337.8	317.5	306.2	299.7	296.7	299.7	306.2	317.5
130°	447.2	409.1	378.2	352.1	331.1	318.1	310.1	307.1	310.1	318.1	331.1
132.5°	457.6	422.0	391.0	365.0	343.2	328.6	318.9	315.1	318.9	328.6	343.2
135°	472.2	439.2	408.2	381.2	360.2	344.1	332.2	328.1	332.2	344.1	360.2
137.5°	483.0	451.4	423.2	395.4	374.8	358.8	347.6	344.6	347.6	358.8	374.8
140°	490.3	460.2	431.2	404.2	385.2	369.2	357.1	354.1	357.1	369.2	385.2
142.5°	494.2	465.8	438.4	413.0	394.8	378.8	367.6	365.3	367.6	378.8	394.8
145°	500.2	475.2	449.2	426.2	408.2	394.2	384.2	382.2	384.2	394.2	408.2
147.5°	503.9	481.2	458.4	438.2	422.6	409.6	401.0	399.8	401.0	409.6	422.6
150°	506.3	485.2	463.2	446.2	432.2	419.2	412.2	410.2	412.2	419.2	432.2
152.5°	507.8	489.2	468.8	453.4	440.2	428.8	422.6	421.4	422.6	428.8	440.2
155°	509.2	493.2	476.2	462.2	452.2	442.2	436.2	436.2	436.2	442.2	452.2
157.5°	510.2	496.6	482.0	471.4	462.6	454.0	449.2	449.4	449.2	454.0	462.6
160°	510.2	498.3	485.2	476.2	468.2	461.2	457.2	458.2	457.2	461.2	468.2
162.5°	509.5	499.8	488.4	481.0	474.6	468.4	464.4	465.4	464.4	468.4	474.6
165°	508.2	500.2	492.2	486.2	482.2	477.3	474.2	476.2	474.2	477.3	482.2
167.5°	505.8	500.2	493.6	489.8	487.0	484.2	482.4	483.5	482.4	484.2	487.0
170°	504.2	500.2	495.2	492.2	490.3	488.2	487.2	488.2	487.2	488.2	490.3
172.5°	502.7	499.4	495.2	493.8	492.6	490.6	489.7	491.5	489.7	490.6	492.6
175°	500.2	498.3	495.2	495.2	495.2	494.2	493.2	495.2	493.2	494.2	495.2
177.5°	497.8	497.1	495.4	495.4	496.2	495.4	495.4	497.1	495.4	495.4	496.2
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	783.4	779.7	777.1	771.9	768.2	766.6	763.8	763.0	765.9	763.8	763.5
5°	760.1	750.6	743.1	735.6	727.4	722.2	714.3	713.0	711.0	708.1	707.5
7.5°	732.2	719.8	710.2	697.7	686.9	678.2	668.4	663.7	661.2	657.4	652.3
10°	713.3	698.6	685.5	673.1	659.7	648.9	639.1	631.5	626.6	622.1	620.1
12.5°	694.7	679.8	663.1	648.0	633.0	620.9	610.0	605.1	599.7	594.3	589.8
15°	665.9	645.9	627.7	610.3	597.5	584.4	574.0	566.8	558.6	556.4	547.5
17.5°	635.3	615.7	594.3	576.0	561.3	546.8	535.4	527.2	521.0	512.6	508.5
20°	616.2	593.0	572.0	555.3	539.0	522.0	510.2	503.3	497.5	490.6	487.3
22.5°	595.8	573.1	551.6	532.1	515.5	498.7	490.3	483.2	476.6	470.2	465.9
25°	565.8	542.9	520.4	500.1	482.8	470.6	460.8	452.6	449.1	442.8	438.2
27.5°	536.2	511.9	488.4	468.2	454.6	442.6	434.6	428.2	421.6	416.2	412.2
30°	517.1	492.2	466.7	450.7	436.3	424.9	416.0	409.8	404.9	400.0	397.1
32.5°	498.0	472.3	449.7	432.4	418.8	408.9	399.8	393.8	388.7	383.2	379.8
35°	467.4	441.2	422.9	405.9	392.4	383.3	377.1	368.6	364.4	360.4	356.8
37.5°	438.9	414.6	394.8	379.9	368.2	359.1	351.1	346.5	341.3	337.8	334.8
40°	418.0	395.7	377.8	362.1	353.5	343.5	335.9	330.0	326.1	321.5	318.2
42.5°	399.2	378.5	361.0	346.9	336.3	327.7	320.5	314.6	309.6	306.3	303.6
45°	372.6	351.9	334.9	321.8	312.0	303.8	296.4	293.3	286.8	282.9	281.6
47.5°	345.0	326.6	310.1	298.1	288.0	280.3	273.2	267.3	263.6	259.8	257.7
50°	326.4	308.8	293.3	281.6	271.8	263.3	256.8	252.8	247.9	244.4	241.7
52.5°	307.8	291.4	276.1	264.8	256.3	247.9	240.6	236.6	232.0	229.6	227.8
55°	281.3	264.0	250.9	239.7	230.9	223.1	216.2	212.2	209.3	207.1	206.4
57.5°	251.2	237.5	225.3	215.2	206.1	198.7	192.7	189.0	186.4	186.1	184.1
60°	231.5	219.1	208.0	197.3	189.3	182.5	177.3	173.1	170.4	170.0	169.4
62.5°	212.0	200.0	189.7	180.2	173.1	166.5	161.6	156.8	155.2	153.6	152.1
65°	182.8	172.0	163.5	156.0	148.5	142.9	138.0	135.1	131.5	129.5	126.0
67.5°	154.2	145.9	137.7	131.4	125.4	120.2	116.1	111.8	109.3	107.7	105.1
70°	135.4	128.9	120.7	113.8	109.3	105.0	101.7	96.8	95.1	93.8	92.6
72.5°	117.6	111.8	105.0	99.4	94.9	90.8	87.0	84.8	83.2	81.8	81.0
75°	92.6	87.0	81.1	77.1	74.0	70.7	68.7	67.1	66.4	66.0	64.7
77.5°	67.9	65.0	60.3	57.2	55.0	53.7	51.9	51.1	51.1	49.6	49.2
80°	52.0	50.4	46.4	45.1	43.5	42.2	41.2	39.6	38.0	37.3	36.3
82.5°	38.7	37.0	35.5	33.3	32.0	31.2	30.2	29.6	29.8	28.9	28.4
85°	20.6	18.9	18.3	18.0	17.3	18.0	17.7	17.3	17.0	16.7	17.0
87.5°	8.2	8.5	8.4	9.4	8.8	9.5	9.6	9.6	9.8	10.0	10.2
90°	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0	19.0	20.0	22.0
92.5°	52.9	82.1	136.6	228.3	327.8	322.5	261.1	177.3	128.6	96.9	82.1
95°	75.0	120.0	227.1	447.2	723.3	886.4	867.4	719.3	567.2	444.2	360.2
97.5°	92.5	124.8	195.7	357.0	645.9	946.6	1097.5	1071.3	964.7	844.8	727.9
100°	106.1	136.0	194.1	324.2	576.3	903.4	1153.5	1230.5	1181.6	1078.5	974.4
102.5°	120.5	149.6	201.3	310.6	523.4	827.3	1119.9	1284.2	1314.4	1265.0	1194.6
105°	144.0	172.1	216.1	305.1	472.2	725.3	1012.4	1252.6	1389.7	1433.7	1422.6
107.5°	170.3	195.4	238.1	314.4	450.6	655.0	902.8	1139.7	1322.6	1435.6	1487.9
110°	187.1	213.1	254.1	323.1	444.2	622.2	840.3	1056.4	1246.6	1387.6	1472.7



TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.7	229.9	269.3	334.3	444.2	603.0	793.9	990.8	1171.3	1314.0	1414.2
115°	231.1	256.1	293.2	351.1	447.2	582.3	743.3	908.4	1063.5	1200.5	1309.6
117.5°	258.3	282.5	317.5	370.4	453.8	572.0	713.1	855.1	988.9	1106.9	1206.9
120°	275.1	300.1	335.2	383.1	460.2	567.2	696.3	826.4	946.4	1056.4	1144.5
122.5°	292.0	316.9	352.0	397.6	465.8	563.3	681.9	804.8	916.0	1014.1	1096.5
125°	315.1	341.1	374.2	417.2	475.2	558.3	662.3	773.4	875.4	962.4	1034.5
127.5°	337.8	363.8	395.5	435.2	485.8	555.9	644.3	741.3	836.5	917.8	985.2
130°	352.1	378.2	409.1	447.2	492.2	554.2	632.3	721.3	809.3	887.4	952.4
132.5°	365.0	391.0	422.0	457.6	499.4	554.2	622.7	701.3	783.8	854.5	917.2
135°	381.2	408.2	439.2	472.2	509.2	554.2	611.3	675.3	744.3	808.4	865.4
137.5°	395.4	423.2	451.4	483.0	518.2	555.4	601.1	653.3	709.1	762.3	810.8
140°	404.2	431.2	460.2	490.3	522.2	556.2	596.2	641.3	688.3	734.3	776.4
142.5°	413.0	438.4	465.8	494.2	524.6	557.1	592.3	630.9	670.7	710.3	746.7
145°	426.2	449.2	475.2	500.2	527.3	556.2	586.3	617.3	648.2	679.3	706.3
147.5°	438.2	458.4	481.2	503.9	528.2	553.6	580.1	604.5	629.6	653.5	673.9
150°	446.2	463.2	485.2	506.3	528.2	551.2	575.2	597.3	619.3	638.3	656.3
152.5°	453.4	468.8	489.2	507.8	527.4	548.0	569.6	589.3	608.9	626.3	640.3
155°	462.2	476.2	493.2	509.2	525.2	542.3	560.3	577.2	593.2	607.3	618.3
157.5°	471.4	482.0	496.6	510.2	522.6	536.2	551.5	565.2	578.4	589.3	597.9
160°	476.2	485.2	498.3	510.2	520.2	532.3	544.2	557.2	567.2	577.2	584.3
162.5°	481.0	488.4	499.8	509.5	517.8	527.4	537.9	548.5	557.7	566.0	572.2
165°	486.2	492.2	500.2	508.2	514.2	520.2	528.2	536.2	543.2	549.2	554.2
167.5°	489.8	493.6	500.2	505.8	508.6	513.2	518.8	524.6	529.3	533.8	537.4
170°	492.2	495.2	500.2	504.2	506.3	509.2	513.2	518.2	521.2	524.3	526.2
172.5°	493.8	495.2	499.4	502.7	503.0	504.5	507.6	511.0	514.0	516.3	517.5
175°	495.2	495.2	498.3	500.2	499.2	499.2	500.2	503.3	503.3	505.2	505.2
177.5°	495.4	495.4	497.1	497.8	496.2	496.2	497.1	497.8	498.6	498.6	498.6
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	763.3	760.3	759.6	760.6	759.6	760.3	763.3	763.5	763.8	765.9	763.0
5°	704.2	700.9	702.6	701.9	702.6	700.9	704.2	707.5	708.1	711.0	713.0
7.5°	652.2	648.2	643.9	645.2	643.9	648.2	652.2	652.3	657.4	661.2	663.7
10°	615.9	612.6	610.6	612.3	610.6	612.6	615.9	620.1	622.1	626.6	631.5
12.5°	585.2	583.3	581.6	580.9	581.6	583.3	585.2	589.8	594.3	599.7	605.1
15°	543.5	539.7	538.0	533.8	538.0	539.7	543.5	547.5	556.4	558.6	566.8
17.5°	505.1	503.9	499.6	497.8	499.6	503.9	505.1	508.5	512.6	521.0	527.2
20°	482.4	481.1	476.9	479.5	476.9	481.1	482.4	487.3	490.6	497.5	503.3
22.5°	463.6	460.7	459.3	458.6	459.3	460.7	463.6	465.9	470.2	476.6	483.2
25°	437.0	432.7	431.1	429.1	431.1	432.7	437.0	438.2	442.8	449.1	452.6
27.5°	410.4	408.1	406.0	405.4	406.0	408.1	410.4	412.2	416.2	421.6	428.2
30°	393.1	390.8	389.2	389.2	389.2	390.8	393.1	397.1	400.0	404.9	409.8
32.5°	377.7	375.9	374.3	374.0	374.3	375.9	377.7	379.8	383.2	388.7	393.8
35°	355.2	352.6	351.9	350.0	351.9	352.6	355.2	356.8	360.4	364.4	368.6
37.5°	331.8	329.7	329.6	329.4	329.6	329.7	331.8	334.8	337.8	341.3	346.5
40°	316.9	315.3	315.0	312.7	315.0	315.3	316.9	318.2	321.5	326.1	330.0
42.5°	301.0	300.1	299.0	298.0	299.0	300.1	301.0	303.6	306.3	309.6	314.6
45°	279.3	277.1	277.1	275.4	277.1	277.1	279.3	281.6	282.9	286.8	293.3
47.5°	256.9	255.2	255.4	253.7	255.4	255.2	256.9	257.7	259.8	263.6	267.3
50°	242.0	241.1	240.7	240.0	240.7	241.1	242.0	241.7	244.4	247.9	252.8
52.5°	227.1	226.7	227.9	226.4	227.9	226.7	227.1	227.8	229.6	232.0	236.6
55°	207.1	206.0	208.0	206.0	208.0	206.0	207.1	206.4	207.1	209.3	212.2
57.5°	183.9	183.0	184.8	183.8	184.8	183.0	183.9	184.1	186.1	186.4	189.0
60°	168.8	166.8	167.8	168.2	167.8	166.8	168.8	169.4	170.0	170.4	173.1
62.5°	150.7	149.6	150.2	148.8	150.2	149.6	150.7	152.1	153.6	155.2	156.8
65°	125.3	124.3	123.0	122.3	123.0	124.3	125.3	126.0	129.5	131.5	135.1
67.5°	105.2	102.9	102.8	103.3	102.8	102.9	105.2	105.1	107.7	109.3	111.8
70°	90.6	90.6	90.2	90.2	90.2	90.6	90.6	92.6	93.8	95.1	96.8
72.5°	80.4	80.2	79.6	79.3	79.6	80.2	80.4	81.0	81.8	83.2	84.8
75°	64.7	65.1	64.4	64.1	64.4	65.1	64.7	64.7	66.0	66.4	67.1
77.5°	47.8	46.4	47.2	46.4	47.2	46.4	47.8	49.2	49.6	51.1	51.1
80°	36.3	36.0	36.9	36.0	36.9	36.0	36.3	36.3	37.3	38.0	39.6
82.5°	28.8	28.4	28.8	28.2	28.8	28.4	28.8	28.4	28.9	29.8	29.6
85°	17.3	17.0	16.7	17.0	16.7	17.0	17.3	17.0	16.7	17.0	17.3
87.5°	10.4	10.2	10.3	10.3	10.3	10.2	10.4	10.2	10.0	9.8	9.6
90°	22.0	22.0	23.0	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0
92.5°	69.2	66.8	65.4	63.8	65.4	66.8	69.2	82.1	96.9	128.6	177.3
95°	289.1	259.1	251.2	235.1	251.2	259.1	289.1	360.2	444.2	567.2	719.3
97.5°	666.1	610.1	581.1	568.3	581.1	610.1	666.1	727.9	844.8	964.7	1071.3
100°	905.4	833.4	796.3	780.3	796.3	833.4	905.4	974.4	1078.5	1181.6	1230.5
102.5°	1120.7	1069.4	1029.2	1017.3	1029.2	1069.4	1120.7	1194.6	1265.0	1314.4	1284.2
105°	1390.6	1357.6	1337.6	1325.6	1337.6	1357.6	1390.6	1422.6	1433.7	1389.7	1252.6
107.5°	1504.1	1503.9	1497.3	1489.3	1497.3	1503.9	1504.1	1487.9	1435.6	1322.6	1139.7
110°	1517.7	1536.7	1543.7	1543.7	1543.7	1536.7	1517.7	1472.7	1387.6	1246.6	1056.4



TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1480.1	1512.7	1530.1	1537.3	1530.1	1512.7	1480.1	1414.2	1314.0	1171.3	990.8
115°	1387.6	1435.6	1463.6	1476.6	1463.6	1435.6	1387.6	1309.6	1200.5	1063.5	908.4
117.5°	1285.0	1334.6	1362.4	1370.4	1362.4	1334.6	1285.0	1206.9	1106.9	988.9	855.1
120°	1218.6	1266.5	1293.6	1301.6	1293.6	1266.5	1218.6	1144.5	1056.4	946.4	826.4
122.5°	1162.5	1206.5	1233.6	1240.8	1233.6	1206.5	1162.5	1096.5	1014.1	916.0	804.8
125°	1090.5	1131.5	1153.5	1163.6	1153.5	1131.5	1090.5	1034.5	962.4	875.4	773.4
127.5°	1036.0	1072.3	1093.1	1097.5	1093.1	1072.3	1036.0	985.2	917.8	836.5	741.3
130°	1002.5	1035.4	1055.5	1061.4	1055.5	1035.4	1002.5	952.4	887.4	809.3	721.3
132.5°	967.2	1000.2	1018.6	1025.5	1018.6	1000.2	967.2	917.2	854.5	783.8	701.3
135°	909.4	942.5	960.4	966.5	960.4	942.5	909.4	865.4	808.4	744.3	675.3
137.5°	850.2	880.2	896.8	903.4	896.8	880.2	850.2	810.8	762.3	709.1	653.3
140°	813.4	839.4	854.4	859.4	854.4	839.4	813.4	776.4	734.3	688.3	641.3
142.5°	778.2	800.1	814.3	818.6	814.3	800.1	778.2	746.7	710.3	670.7	630.9
145°	730.3	747.3	758.4	762.3	758.4	747.3	730.3	706.3	679.3	648.2	617.3
147.5°	692.9	706.5	712.9	714.7	712.9	706.5	692.9	673.9	653.5	629.6	604.5
150°	671.3	683.3	687.3	688.3	687.3	683.3	671.3	656.3	638.3	619.3	597.3
152.5°	652.9	662.5	666.5	667.5	666.5	662.5	652.9	640.3	626.3	608.9	589.3
155°	628.3	635.2	638.3	639.3	638.3	635.2	628.3	618.3	607.3	593.2	577.2
157.5°	605.6	611.5	614.2	614.1	614.2	611.5	605.6	597.9	589.3	578.4	565.2
160°	591.2	596.2	598.3	597.3	598.3	596.2	591.2	584.3	577.2	567.2	557.2
162.5°	577.6	581.9	582.3	582.0	582.3	581.9	577.6	572.2	566.0	557.7	548.5
165°	558.3	560.3	560.3	560.3	560.3	560.3	558.3	554.2	549.2	543.2	536.2
167.5°	539.4	541.2	540.4	540.3	540.4	541.2	539.4	537.4	533.8	529.3	524.6
170°	528.2	529.3	529.3	528.2	529.3	529.3	528.2	526.2	524.3	521.2	518.2
172.5°	517.8	519.6	518.1	517.0	518.1	519.6	517.8	517.5	516.3	514.0	511.0
175°	505.2	506.3	504.2	503.3	504.2	506.3	505.2	505.2	505.2	503.3	503.3
177.5°	497.8	498.6	496.2	496.2	496.2	498.6	497.8	498.6	498.6	498.6	497.8
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	763.8	766.6	768.2	771.9	777.1	779.7	783.4	786.0	789.7	794.1	797.8
5°	714.3	722.2	727.4	735.6	743.1	750.6	760.1	767.0	776.1	786.6	794.8
7.5°	668.4	678.2	686.9	697.7	710.2	719.8	732.2	744.8	759.1	774.0	788.0
10°	639.1	648.9	659.7	673.1	685.5	698.6	713.3	728.1	746.1	762.8	781.7
12.5°	610.0	620.9	633.0	648.0	663.1	679.8	694.7	711.3	730.6	752.3	772.6
15°	574.0	584.4	597.5	610.3	627.7	645.9	665.9	687.9	709.4	733.7	758.8
17.5°	535.4	546.8	561.3	576.0	594.3	615.7	635.3	659.3	683.5	711.8	741.4
20°	510.2	522.0	539.0	555.3	572.0	593.0	616.2	640.8	666.6	696.3	729.4
22.5°	490.3	498.7	515.5	532.1	551.6	573.1	595.8	621.4	649.5	680.4	715.0
25°	460.8	470.6	482.8	500.1	520.4	542.9	565.8	593.0	623.7	655.1	692.1
27.5°	434.6	442.6	454.6	468.2	488.4	511.9	536.2	564.6	596.1	628.0	666.9
30°	416.0	424.9	436.3	450.7	466.7	492.2	517.1	544.9	577.0	610.0	649.9
32.5°	399.8	408.9	418.8	432.4	449.7	472.3	498.0	525.3	557.8	591.9	630.8
35°	377.1	383.3	392.4	405.9	422.9	441.2	467.4	496.2	527.9	563.2	602.1
37.5°	351.1	359.1	368.2	379.9	394.8	414.6	438.9	468.0	497.5	531.3	566.8
40°	335.9	343.5	353.5	362.1	377.8	395.7	418.0	448.4	477.9	509.5	541.9
42.5°	320.5	327.7	336.3	346.9	361.0	378.5	399.2	427.5	459.0	488.9	516.1
45°	296.4	303.8	312.0	321.8	334.9	351.9	372.6	398.4	425.9	453.3	473.9
47.5°	273.2	280.3	288.0	298.1	310.1	326.6	345.0	367.8	394.5	417.8	432.6
50°	256.8	263.3	271.8	281.6	293.3	308.8	326.4	349.0	371.3	392.4	405.9
52.5°	240.6	247.9	256.3	264.8	276.1	291.4	307.8	327.3	348.4	365.8	376.9
55°	216.2	223.1	230.9	239.7	250.9	264.0	281.3	296.6	313.3	328.0	334.6
57.5°	192.7	198.7	206.1	215.2	225.3	237.5	251.2	266.0	277.8	288.2	295.6
60°	177.3	182.5	189.3	197.3	208.0	219.1	231.5	245.3	254.4	263.3	270.2
62.5°	161.6	166.5	173.1	180.2	189.7	200.0	212.0	223.1	232.0	237.9	245.8
65°	138.0	142.9	148.5	156.0	163.5	172.0	182.8	191.0	197.3	203.8	208.7
67.5°	116.1	120.2	125.4	131.4	137.7	145.9	154.2	161.0	165.3	169.2	175.1
70°	101.7	105.0	109.3	113.8	120.7	128.9	135.4	140.6	143.6	147.5	154.7
72.5°	87.0	90.8	94.9	99.4	105.0	111.8	117.6	122.9	124.8	127.9	132.4
75°	68.7	70.7	74.0	77.1	81.1	87.0	92.6	93.8	95.5	98.2	101.4
77.5°	51.9	53.7	55.0	57.2	60.3	65.0	67.9	69.9	70.3	71.3	74.5
80°	41.2	42.2	43.5	45.1	46.4	50.4	52.0	54.0	54.6	55.6	57.3
82.5°	30.2	31.2	32.0	33.3	35.5	37.0	38.7	40.6	40.7	41.5	41.8
85°	17.7	18.0	17.3	18.0	18.3	18.9	20.6	22.2	22.0	21.6	22.6
87.5°	9.6	9.5	8.8	9.4	8.4	8.5	8.2	8.0	8.1	8.3	8.6
90°	17.0	16.0	14.0	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0
92.5°	261.1	322.5	327.8	228.3	136.6	82.1	52.9	35.6	23.2	14.8	12.2
95°	867.4	886.4	723.3	447.2	227.1	120.0	75.0	53.0	42.0	34.0	33.0
97.5°	1097.5	946.6	645.9	357.0	195.7	124.8	92.5	72.7	61.6	56.1	54.8
100°	1153.5	903.4	576.3	324.2	194.1	136.0	106.1	87.0	76.0	72.1	70.0
102.5°	1119.9	827.3	523.4	310.6	201.3	149.6	120.5	103.1	91.3	88.1	86.9
105°	1012.4	725.3	472.2	305.1	216.1	172.1	144.0	128.0	118.0	113.0	113.0
107.5°	902.8	655.0	450.6	314.4	238.1	195.4	170.3	153.7	145.4	140.7	138.6
110°	840.3	622.2	444.2	323.1	254.1	213.1	187.1	172.1	163.1	159.1	157.0



TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	793.9	603.0	444.2	334.3	269.3	229.9	204.7	189.7	180.6	177.5	175.5
115°	743.3	582.3	447.2	351.1	293.2	256.1	231.1	216.1	207.1	204.1	202.1
117.5°	713.1	572.0	453.8	370.4	317.5	282.5	258.3	241.3	232.3	229.1	226.1
120°	696.3	567.2	460.2	383.1	335.2	300.1	275.1	258.1	249.1	245.1	242.1
122.5°	681.9	563.3	465.8	397.6	352.0	316.9	292.0	273.3	264.3	261.1	258.9
125°	662.3	558.3	475.2	417.2	374.2	341.1	315.1	296.1	287.1	282.1	280.1
127.5°	644.3	555.9	485.8	435.2	395.5	363.8	337.8	317.5	306.2	299.7	296.7
130°	632.3	554.2	492.2	447.2	409.1	378.2	352.1	331.1	318.1	310.1	307.1
132.5°	622.7	554.2	499.4	457.6	422.0	391.0	365.0	343.2	328.6	318.9	315.1
135°	611.3	554.2	509.2	472.2	439.2	408.2	381.2	360.2	344.1	332.2	328.1
137.5°	601.1	555.4	518.2	483.0	451.4	423.2	395.4	374.8	358.8	347.6	344.6
140°	596.2	556.2	522.2	490.3	460.2	431.2	404.2	385.2	369.2	357.1	354.1
142.5°	592.3	557.1	524.6	494.2	465.8	438.4	413.0	394.8	378.8	367.6	365.3
145°	586.3	556.2	527.3	500.2	475.2	449.2	426.2	408.2	394.2	384.2	382.2
147.5°	580.1	553.6	528.2	503.9	481.2	458.4	438.2	422.6	409.6	401.0	399.8
150°	575.2	551.2	528.2	506.3	485.2	463.2	446.2	432.2	419.2	412.2	410.2
152.5°	569.6	548.0	527.4	507.8	489.2	468.8	453.4	440.2	428.8	422.6	421.4
155°	560.3	542.3	525.2	509.2	493.2	476.2	462.2	452.2	442.2	436.2	436.2
157.5°	551.5	536.2	522.6	510.2	496.6	482.0	471.4	462.6	454.0	449.2	449.4
160°	544.2	532.3	520.2	510.2	498.3	485.2	476.2	468.2	461.2	457.2	458.2
162.5°	537.9	527.4	517.8	509.5	499.8	488.4	481.0	474.6	468.4	464.4	465.4
165°	528.2	520.2	514.2	508.2	500.2	492.2	486.2	482.2	477.3	474.2	476.2
167.5°	518.8	513.2	508.6	505.8	500.2	493.6	489.8	487.0	484.2	482.4	483.5
170°	513.2	509.2	506.3	504.2	500.2	495.2	492.2	490.3	488.2	487.2	488.2
172.5°	507.6	504.5	503.0	502.7	499.4	495.2	493.8	492.6	490.6	489.7	491.5
175°	500.2	499.2	499.2	500.2	498.3	495.2	495.2	495.2	494.2	493.2	495.2
177.5°	497.1	496.2	496.2	497.8	497.1	495.4	495.4	496.2	495.4	495.4	497.1
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	800.6	803.1	806.4	810.4	813.5	816.9	818.7	818.7	820.3	823.7	828.1
5°	803.0	811.5	819.7	830.1	838.3	847.7	855.0	861.9	868.1	875.9	884.1
7.5°	802.3	816.4	831.1	847.7	865.8	880.3	895.1	906.8	918.3	933.3	945.2
10°	799.7	818.0	837.9	858.8	881.8	901.7	919.7	936.1	951.7	968.1	982.8
12.5°	795.0	818.3	842.7	867.8	896.7	919.5	942.7	960.2	978.4	996.3	1014.5
15°	787.9	815.4	844.8	879.9	915.2	940.6	963.5	986.1	1003.2	1023.4	1040.8
17.5°	773.4	808.7	845.8	884.0	917.9	947.6	971.6	993.1	1011.2	1033.5	1057.0
20°	764.7	803.0	841.5	882.4	914.8	945.2	968.5	990.7	1013.2	1042.4	1071.2
22.5°	752.7	793.5	834.5	873.3	907.5	936.9	960.9	988.1	1017.7	1050.8	1085.5
25°	733.7	775.8	816.4	853.3	886.7	916.8	949.5	986.1	1022.1	1065.6	1115.6
27.5°	709.5	750.2	786.4	825.4	858.6	896.8	937.6	977.3	1029.2	1089.1	1151.6
30°	691.4	730.0	764.4	801.3	839.0	881.1	927.0	973.7	1035.5	1105.8	1180.1
32.5°	670.5	705.4	739.5	775.2	818.6	864.9	913.6	970.8	1044.7	1124.6	1201.5
35°	634.2	665.6	698.6	738.2	784.3	834.7	896.8	966.5	1055.8	1141.8	1210.8
37.5°	596.2	620.9	654.1	695.8	746.1	804.3	874.9	959.5	1051.2	1128.4	1157.8
40°	566.8	590.0	625.0	668.8	718.6	782.4	861.5	948.5	1040.8	1094.3	1092.1
42.5°	537.8	561.3	595.0	639.0	690.9	762.2	843.7	934.1	1011.9	1032.3	989.8
45°	493.2	515.1	548.2	592.6	648.2	723.2	808.8	895.5	945.2	912.2	827.9
47.5°	447.8	469.1	499.7	543.3	604.0	682.4	763.4	834.6	841.5	770.6	669.3
50°	418.0	437.9	467.1	513.5	572.4	648.9	727.1	783.0	765.7	679.0	574.6
52.5°	388.9	408.1	435.4	479.2	539.4	614.4	684.2	728.1	687.9	595.8	502.0
55°	346.0	364.4	391.8	432.0	486.6	555.3	616.6	632.6	573.7	480.8	404.9
57.5°	305.3	318.7	345.9	381.4	434.1	494.6	538.5	535.6	470.6	387.0	332.6
60°	278.4	290.4	316.2	349.0	399.0	453.3	484.1	471.0	405.3	336.2	283.9
62.5°	253.2	264.5	286.2	316.2	359.3	406.5	428.9	410.8	348.7	288.1	246.5
65°	215.2	223.4	240.7	268.5	302.2	334.9	354.9	328.4	273.5	227.6	196.2
67.5°	179.7	186.8	202.2	222.1	245.4	267.9	276.0	251.2	208.4	177.6	155.5
70°	156.7	163.2	173.7	192.3	207.7	223.7	227.6	205.4	169.8	146.2	132.4
72.5°	134.7	140.7	149.9	163.0	173.7	182.9	184.8	164.0	136.8	120.5	109.9
75°	102.7	108.0	113.8	118.7	125.6	127.3	126.6	110.6	95.8	85.1	79.1
77.5°	75.5	77.7	81.3	83.2	83.5	83.4	80.1	69.9	62.3	57.9	55.4
80°	58.2	59.8	60.9	61.5	61.8	58.5	54.9	48.7	46.1	43.5	40.6
82.5°	42.3	43.4	44.3	44.5	42.7	40.0	36.6	33.6	31.7	30.4	29.3
85°	22.9	23.2	22.9	21.3	18.9	18.0	17.3	16.7	16.4	16.0	16.0
87.5°	8.5	8.1	7.2	7.9	8.3	8.2	8.6	8.5	8.7	8.9	9.1
90°	2.0	4.0	6.0	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0
92.5°	14.8	23.2	35.6	52.9	82.1	136.6	228.3	327.8	322.5	261.1	177.3
95°	34.0	42.0	53.0	75.0	120.0	227.1	447.2	723.3	886.4	867.4	719.3
97.5°	56.1	61.6	72.7	92.5	124.8	195.7	357.0	645.9	946.6	1097.5	1071.3
100°	72.1	76.0	87.0	106.1	136.0	194.1	324.2	576.3	903.4	1153.5	1230.5
102.5°	88.1	91.3	103.1	120.5	149.6	201.3	310.6	523.4	827.3	1119.9	1284.2
105°	113.0	118.0	128.0	144.0	172.1	216.1	305.1	472.2	725.3	1012.4	1252.6
107.5°	140.7	145.4	153.7	170.3	195.4	238.1	314.4	450.6	655.0	902.8	1139.7
110°	159.1	163.1	172.1	187.1	213.1	254.1	323.1	444.2	622.2	840.3	1056.4





TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	177.5	180.6	189.7	204.7	229.9	269.3	334.3	444.2	603.0	793.9	990.8
115°	204.1	207.1	216.1	231.1	256.1	293.2	351.1	447.2	582.3	743.3	908.4
117.5°	229.1	232.3	241.3	258.3	282.5	317.5	370.4	453.8	572.0	713.1	855.1
120°	245.1	249.1	258.1	275.1	300.1	335.2	383.1	460.2	567.2	696.3	826.4
122.5°	261.1	264.3	273.3	292.0	316.9	352.0	397.6	465.8	563.3	681.9	804.8
125°	282.1	287.1	296.1	315.1	341.1	374.2	417.2	475.2	558.3	662.3	773.4
127.5°	299.7	306.2	317.5	337.8	363.8	395.5	435.2	485.8	555.9	644.3	741.3
130°	310.1	318.1	331.1	352.1	378.2	409.1	447.2	492.2	554.2	632.3	721.3
132.5°	318.9	328.6	343.2	365.0	391.0	422.0	457.6	499.4	554.2	622.7	701.3
135°	332.2	344.1	360.2	381.2	408.2	439.2	472.2	509.2	554.2	611.3	675.3
137.5°	347.6	358.8	374.8	395.4	423.2	451.4	483.0	518.2	555.4	601.1	653.3
140°	357.1	369.2	385.2	404.2	431.2	460.2	490.3	522.2	556.2	596.2	641.3
142.5°	367.6	378.8	394.8	413.0	438.4	465.8	494.2	524.6	557.1	592.3	630.9
145°	384.2	394.2	408.2	426.2	449.2	475.2	500.2	527.3	556.2	586.3	617.3
147.5°	401.0	409.6	422.6	438.2	458.4	481.2	503.9	528.2	553.6	580.1	604.5
150°	412.2	419.2	432.2	446.2	463.2	485.2	506.3	528.2	551.2	575.2	597.3
152.5°	422.6	428.8	440.2	453.4	468.8	489.2	507.8	527.4	548.0	569.6	589.3
155°	436.2	442.2	452.2	462.2	476.2	493.2	509.2	525.2	542.3	560.3	577.2
157.5°	449.2	454.0	462.6	471.4	482.0	496.6	510.2	522.6	536.2	551.5	565.2
160°	457.2	461.2	468.2	476.2	485.2	498.3	510.2	520.2	532.3	544.2	557.2
162.5°	464.4	468.4	474.6	481.0	488.4	499.8	509.5	517.8	527.4	537.9	548.5
165°	474.2	477.3	482.2	486.2	492.2	500.2	508.2	514.2	520.2	528.2	536.2
167.5°	482.4	484.2	487.0	489.8	493.6	500.2	505.8	508.6	513.2	518.8	524.6
170°	487.2	488.2	490.3	492.2	495.2	500.2	504.2	506.3	509.2	513.2	518.2
172.5°	489.7	490.6	492.6	493.8	495.2	499.4	502.7	503.0	504.5	507.6	511.0
175°	493.2	494.2	495.2	495.2	495.2	498.3	500.2	499.2	499.2	500.2	503.3
177.5°	495.4	495.4	496.2	495.4	495.4	497.1	497.8	496.2	496.2	497.1	497.8
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2	496.2



TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	831.6	831.6	836.0	835.7	838.6	837.6	838.1
5°	893.9	899.4	904.3	907.6	912.5	913.9	913.2
7.5°	958.6	970.9	976.9	985.2	986.6	990.9	990.5
10°	998.5	1010.6	1019.8	1027.0	1030.6	1035.2	1035.5
12.5°	1029.9	1040.2	1048.4	1055.0	1059.4	1060.8	1061.7
15°	1054.5	1065.9	1075.4	1084.9	1090.5	1094.7	1097.0
17.5°	1079.2	1096.8	1113.6	1126.5	1134.2	1140.7	1140.7
20°	1098.3	1118.6	1139.5	1154.3	1169.2	1175.8	1176.8
22.5°	1118.7	1149.7	1176.6	1199.5	1219.3	1226.1	1228.6
25°	1161.1	1201.6	1243.2	1275.2	1298.1	1311.6	1313.5
27.5°	1212.3	1267.2	1310.9	1340.5	1359.5	1369.4	1371.6
30°	1248.4	1299.1	1338.3	1360.6	1369.4	1370.7	1365.8
32.5°	1264.6	1302.5	1318.2	1316.9	1299.6	1288.1	1283.7
35°	1244.8	1237.0	1198.7	1152.9	1117.9	1095.7	1089.8
37.5°	1132.8	1065.1	994.7	925.6	888.7	870.0	837.8
40°	1022.4	925.9	852.6	794.4	752.9	719.5	711.7
42.5°	897.9	798.2	725.0	675.1	642.0	619.1	609.2
45°	721.5	635.8	575.3	537.0	511.5	494.8	487.3
47.5°	577.0	510.7	466.7	438.3	418.9	404.4	400.4
50°	497.8	444.8	407.5	383.7	368.9	357.8	353.3
52.5°	432.4	389.6	360.9	341.3	327.4	320.4	316.6
55°	356.8	319.9	299.3	283.5	275.7	270.2	267.5
57.5°	291.8	265.1	250.0	239.2	232.0	228.4	227.1
60°	255.5	234.5	220.8	212.2	207.3	202.8	201.5
62.5°	223.3	206.8	196.1	188.7	183.8	181.8	181.1
65°	179.9	169.1	161.3	156.7	152.7	152.1	151.8
67.5°	143.0	136.6	132.5	127.8	126.4	124.1	123.6
70°	122.3	118.0	113.1	111.5	109.9	107.6	108.0
72.5°	103.8	99.5	96.2	94.0	93.4	92.5	93.2
75°	75.9	74.6	73.3	71.6	70.9	70.9	70.7
77.5°	54.2	53.0	51.6	50.6	50.5	49.1	49.6
80°	39.3	37.6	36.9	37.3	36.3	36.0	36.0
82.5°	29.0	28.4	27.8	27.9	27.6	27.4	27.6
85°	16.0	15.7	15.7	15.4	15.4	15.1	15.1
87.5°	9.6	10.0	9.9	9.6	9.6	10.1	10.3
90°	19.0	20.0	22.0	22.0	22.0	23.0	23.0
92.5°	128.6	96.9	82.1	69.2	66.8	65.4	63.8
95°	567.2	444.2	360.2	289.1	259.1	251.2	235.1
97.5°	964.7	844.8	727.9	666.1	610.1	581.1	568.3
100°	1181.6	1078.5	974.4	905.4	833.4	796.3	780.3
102.5°	1314.4	1265.0	1194.6	1120.7	1069.4	1029.2	1017.3
105°	1389.7	1433.7	1422.6	1390.6	1357.6	1337.6	1325.6
107.5°	1322.6	1435.6	1487.9	1504.1	1503.9	1497.3	1489.3
110°	1246.6	1387.6	1472.7	1517.7	1536.7	1543.7	1543.7



TEST NUMBER: P333546-935

CATALOG NUMBER: S125RDIP-S610D1205U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1171.3	1314.0	1414.2	1480.1	1512.7	1530.1	1537.3
115°	1063.5	1200.5	1309.6	1387.6	1435.6	1463.6	1476.6
117.5°	988.9	1106.9	1206.9	1285.0	1334.6	1362.4	1370.4
120°	946.4	1056.4	1144.5	1218.6	1266.5	1293.6	1301.6
122.5°	916.0	1014.1	1096.5	1162.5	1206.5	1233.6	1240.8
125°	875.4	962.4	1034.5	1090.5	1131.5	1153.5	1163.6
127.5°	836.5	917.8	985.2	1036.0	1072.3	1093.1	1097.5
130°	809.3	887.4	952.4	1002.5	1035.4	1055.5	1061.4
132.5°	783.8	854.5	917.2	967.2	1000.2	1018.6	1025.5
135°	744.3	808.4	865.4	909.4	942.5	960.4	966.5
137.5°	709.1	762.3	810.8	850.2	880.2	896.8	903.4
140°	688.3	734.3	776.4	813.4	839.4	854.4	859.4
142.5°	670.7	710.3	746.7	778.2	800.1	814.3	818.6
145°	648.2	679.3	706.3	730.3	747.3	758.4	762.3
147.5°	629.6	653.5	673.9	692.9	706.5	712.9	714.7
150°	619.3	638.3	656.3	671.3	683.3	687.3	688.3
152.5°	608.9	626.3	640.3	652.9	662.5	666.5	667.5
155°	593.2	607.3	618.3	628.3	635.2	638.3	639.3
157.5°	578.4	589.3	597.9	605.6	611.5	614.2	614.1
160°	567.2	577.2	584.3	591.2	596.2	598.3	597.3
162.5°	557.7	566.0	572.2	577.6	581.9	582.3	582.0
165°	543.2	549.2	554.2	558.3	560.3	560.3	560.3
167.5°	529.3	533.8	537.4	539.4	541.2	540.4	540.3
170°	521.2	524.3	526.2	528.2	529.3	529.3	528.2
172.5°	514.0	516.3	517.5	517.8	519.6	518.1	517.0
175°	503.3	505.2	505.2	505.2	506.3	504.2	503.3
177.5°	498.6	498.6	498.6	497.8	498.6	496.2	496.2
180°	496.2	496.2	496.2	496.2	496.2	496.2	496.2

(END OF REPORT)