

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333522-935

Luminaire Tested: **S125RDIP-S610D365U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333522-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D365U935-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3196.9 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65
1	102	97	94	90	95	92	88	86	81	79	76	71	70	68	62	61	60	56
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51	47
3	85	76	69	63	80	72	65	60	64	59	54	56	52	49	50	47	44	41
4	78	67	60	54	73	64	57	51	57	51	47	51	46	43	45	41	38	35
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	40	37	34	31
6	66	54	46	40	62	52	44	39	46	40	36	41	36	33	37	33	30	27
7	62	49	41	36	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	32	54	43	35	30	38	32	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	38	30	26	47	36	29	25	33	27	23	29	25	21	26	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5146	5146	5146	5146
5°	5920	5153	4550	5153
10°	6791	5126	4015	5126
15°	7335	5073	3569	5073
20°	8088	5013	3296	5013
25°	9360	4932	3058	4932
30°	10185	4847	2902	4847
35°	8592	4747	2759	4747
40°	6000	4569	2636	4569
45°	4451	4328	2515	4328
50°	3550	4078	2411	4078
55°	3012	3768	2320	3768
60°	2603	3490	2173	3490
65°	2320	3189	1869	3189
70°	2039	2921	1703	2921
75°	1764	2530	1599	2530
80°	1339	2131	1339	2131
85°	1119	1675	1260	1675



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	2.4
10°-20°	223.9	7.0
20°-30°	355.0	11.1
30°-40°	428.1	13.4
40°-50°	382.3	12.0
50°-60°	293.2	9.2
60°-70°	190.5	6.0
70°-80°	92.6	2.9
80°-90°	23.0	0.7
90°-100°	109.4	3.4
100°-110°	235.2	7.4
110°-120°	220.7	6.9
120°-130°	178.9	5.6
130°-140°	143.5	4.5
140°-150°	108.3	3.4
150°-160°	76.2	2.4
160°-170°	44.9	1.4
170°-180°	14.6	0.5
0°-30°	655.3	20.5
0°-40°	1083.4	33.9
0°-60°	1758.9	55.0
0°-90°	2065.1	64.6
90°-120°	565.3	17.7
90°-150°	996.0	31.2
90°-180°	1132.0	35.4
0°-180°	3196.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	797	797	797	797	797	
5°	913	795	702	795	913	91
15°	1097	759	534	759	1097	314
25°	1314	692	429	692	1314	603
35°	1090	602	350	602	1090	658
45°	487	474	275	474	487	389
55°	268	335	206	335	268	243
65°	152	209	122	209	152	151
75°	71	101	64	101	71	75
85°	15	23	17	23	15	17
90°	7	0	7	0	7	6
95°	72	10	72	10	72	101
105°	403	34	403	34	403	401
115°	449	62	449	62	449	439
125°	354	85	354	85	354	320
135°	294	100	294	100	294	228
145°	232	116	232	116	232	147
155°	194	133	194	133	194	91
165°	170	145	170	145	170	49
175°	153	151	153	151	153	15
180°	151	151	151	151	151	



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	838.1	837.6	838.6	835.7	836.0	831.6	831.6	828.1	823.7	820.3	818.7
5°	913.2	913.9	912.5	907.6	904.3	899.4	893.9	884.1	875.9	868.1	861.9
7.5°	990.5	990.9	986.6	985.2	976.9	970.9	958.6	945.2	933.3	918.3	906.8
10°	1035.5	1035.2	1030.6	1027.0	1019.8	1010.6	998.5	982.8	968.1	951.7	936.1
12.5°	1061.7	1060.8	1059.4	1055.0	1048.4	1040.2	1029.9	1014.5	996.3	978.4	960.2
15°	1097.0	1094.7	1090.5	1084.9	1075.4	1065.9	1054.5	1040.8	1023.4	1003.2	986.1
17.5°	1140.7	1140.7	1134.2	1126.5	1113.6	1096.8	1079.2	1057.0	1033.5	1011.2	993.1
20°	1176.8	1175.8	1169.2	1154.3	1139.5	1118.6	1098.3	1071.2	1042.4	1013.2	990.7
22.5°	1228.6	1226.1	1219.3	1199.5	1176.6	1149.7	1118.7	1085.5	1050.8	1017.7	988.1
25°	1313.5	1311.6	1298.1	1275.2	1243.2	1201.6	1161.1	1115.6	1065.6	1022.1	986.1
27.5°	1371.6	1369.4	1359.5	1340.5	1310.9	1267.2	1212.3	1151.6	1089.1	1029.2	977.3
30°	1365.8	1370.7	1369.4	1360.6	1338.3	1299.1	1248.4	1180.1	1105.8	1035.5	973.7
32.5°	1283.7	1288.1	1299.6	1316.9	1318.2	1302.5	1264.6	1201.5	1124.6	1044.7	970.8
35°	1089.8	1095.7	1117.9	1152.9	1198.7	1237.0	1244.8	1210.8	1141.8	1055.8	966.5
37.5°	837.8	870.0	888.7	925.6	994.7	1065.1	1132.8	1157.8	1128.4	1051.2	959.5
40°	711.7	719.5	752.9	794.4	852.6	925.9	1022.4	1092.1	1094.3	1040.8	948.5
42.5°	609.2	619.1	642.0	675.1	725.0	798.2	897.9	989.8	1032.3	1011.9	934.1
45°	487.3	494.8	511.5	537.0	575.3	635.8	721.5	827.9	912.2	945.2	895.5
47.5°	400.4	404.4	418.9	438.3	466.7	510.7	577.0	669.3	770.6	841.5	834.6
50°	353.3	357.8	368.9	383.7	407.5	444.8	497.8	574.6	679.0	765.7	783.0
52.5°	316.6	320.4	327.4	341.3	360.9	389.6	432.4	502.0	595.8	687.9	728.1
55°	267.5	270.2	275.7	283.5	299.3	319.9	356.8	404.9	480.8	573.7	632.6
57.5°	227.1	228.4	232.0	239.2	250.0	265.1	291.8	332.6	387.0	470.6	535.6
60°	201.5	202.8	207.3	212.2	220.8	234.5	255.5	283.9	336.2	405.3	471.0
62.5°	181.1	181.8	183.8	188.7	196.1	206.8	223.3	246.5	288.1	348.7	410.8
65°	151.8	152.1	152.7	156.7	161.3	169.1	179.9	196.2	227.6	273.5	328.4
67.5°	123.6	124.1	126.4	127.8	132.5	136.6	143.0	155.5	177.6	208.4	251.2
70°	108.0	107.6	109.9	111.5	113.1	118.0	122.3	132.4	146.2	169.8	205.4
72.5°	93.2	92.5	93.4	94.0	96.2	99.5	103.8	109.9	120.5	136.8	164.0
75°	70.7	70.9	70.9	71.6	73.3	74.6	75.9	79.1	85.1	95.8	110.6
77.5°	49.6	49.1	50.5	50.6	51.6	53.0	54.2	55.4	57.9	62.3	69.9
80°	36.0	36.0	36.3	37.3	36.9	37.6	39.3	40.6	43.5	46.1	48.7
82.5°	27.6	27.4	27.6	27.9	27.8	28.4	29.0	29.3	30.4	31.7	33.6
85°	15.1	15.1	15.4	15.4	15.7	15.7	16.0	16.0	16.0	16.4	16.7
87.5°	7.1	6.9	6.5	6.5	6.8	7.2	6.9	6.6	6.5	6.5	6.6
90°	7.0	7.0	6.7	6.7	6.7	6.1	5.8	5.5	5.2	4.9	4.2
92.5°	19.4	19.9	20.3	21.1	25.0	29.4	39.1	53.9	79.4	98.1	99.7
95°	71.5	76.4	78.8	87.9	109.5	135.1	172.5	218.8	263.8	269.6	220.0
97.5°	172.8	176.8	185.5	202.6	221.4	256.9	293.4	325.8	333.8	287.9	196.5
100°	237.4	242.2	253.5	275.3	296.4	328.0	359.4	374.3	350.9	274.7	175.3
102.5°	309.4	313.1	325.3	340.9	363.3	384.8	399.8	390.5	340.6	251.7	159.2
105°	403.2	406.8	412.9	422.9	432.7	436.0	422.7	381.0	308.0	220.6	143.6
107.5°	453.0	455.4	457.4	457.4	452.5	436.6	402.3	346.6	274.6	199.2	137.1
110°	469.5	469.5	467.4	461.6	447.9	422.1	379.2	321.3	255.6	189.2	135.1



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	467.6	465.4	460.1	450.1	430.2	399.7	356.3	301.4	241.5	183.4	135.1
115°	449.1	445.1	436.6	422.1	398.3	365.2	323.5	276.3	226.1	177.1	136.0
117.5°	416.8	414.4	406.0	390.8	367.1	336.7	300.7	260.1	216.9	174.0	138.0
120°	395.9	393.5	385.2	370.7	348.1	321.3	287.8	251.3	211.8	172.5	140.0
122.5°	377.4	375.2	367.0	353.6	333.5	308.4	278.6	244.8	207.4	171.3	141.6
125°	353.9	350.9	344.1	331.7	314.6	292.7	266.2	235.2	201.5	169.8	144.6
127.5°	333.8	332.4	326.1	315.1	299.6	279.1	254.4	225.5	196.0	169.1	147.7
130°	322.9	321.1	315.0	304.9	289.7	269.9	246.2	219.4	192.3	168.6	149.7
132.5°	311.9	309.8	304.2	294.2	279.0	259.9	238.4	213.3	189.4	168.6	151.9
135°	293.9	292.1	286.6	276.6	263.2	245.9	226.4	205.4	185.9	168.6	154.9
137.5°	274.7	272.8	267.7	258.6	246.6	231.9	215.7	198.7	182.8	168.9	157.6
140°	261.4	259.8	255.3	247.4	236.1	223.3	209.3	195.0	181.3	169.2	158.9
142.5°	249.0	247.7	243.4	236.7	227.1	216.0	204.0	191.9	180.1	169.4	159.5
145°	231.9	230.7	227.3	222.1	214.8	206.6	197.2	187.8	178.3	169.2	160.3
147.5°	217.4	216.8	214.9	210.8	205.0	198.8	191.5	183.8	176.4	168.4	160.7
150°	209.3	209.1	207.8	204.1	199.6	194.2	188.4	181.7	175.0	167.6	160.7
152.5°	203.0	202.7	201.5	198.5	194.8	190.5	185.2	179.3	173.2	166.7	160.4
155°	194.4	194.2	193.2	191.1	188.0	184.7	180.5	175.6	170.4	165.0	159.7
157.5°	186.8	186.8	186.0	184.3	181.8	179.3	175.9	171.9	167.7	163.1	158.9
160°	181.7	181.9	181.3	179.9	177.7	175.6	172.5	169.5	165.6	161.9	158.3
162.5°	177.0	177.1	176.9	175.7	174.1	172.2	169.6	166.8	163.6	160.4	157.5
165°	170.4	170.4	170.4	169.8	168.6	167.0	165.2	163.1	160.7	158.3	156.4
167.5°	164.3	164.4	164.6	164.1	163.5	162.4	161.0	159.5	157.8	156.1	154.7
170°	160.7	161.0	161.0	160.7	160.1	159.5	158.5	157.6	156.1	154.9	153.9
172.5°	157.2	157.6	158.1	157.5	157.4	157.0	156.4	155.4	154.4	153.4	153.0
175°	153.1	153.3	153.9	153.7	153.7	153.7	153.1	153.1	152.1	151.9	151.9
177.5°	150.9	150.9	151.6	151.4	151.6	151.6	151.6	151.4	151.2	150.9	150.9
180°	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	818.7	816.9	813.5	810.4	806.4	803.1	800.6	797.8	794.1	789.7	786.0
5°	855.0	847.7	838.3	830.1	819.7	811.5	803.0	794.8	786.6	776.1	767.0
7.5°	895.1	880.3	865.8	847.7	831.1	816.4	802.3	788.0	774.0	759.1	744.8
10°	919.7	901.7	881.8	858.8	837.9	818.0	799.7	781.7	762.8	746.1	728.1
12.5°	942.7	919.5	896.7	867.8	842.7	818.3	795.0	772.6	752.3	730.6	711.3
15°	963.5	940.6	915.2	879.9	844.8	815.4	787.9	758.8	733.7	709.4	687.9
17.5°	971.6	947.6	917.9	884.0	845.8	808.7	773.4	741.4	711.8	683.5	659.3
20°	968.5	945.2	914.8	882.4	841.5	803.0	764.7	729.4	696.3	666.6	640.8
22.5°	960.9	936.9	907.5	873.3	834.5	793.5	752.7	715.0	680.4	649.5	621.4
25°	949.5	916.8	886.7	853.3	816.4	775.8	733.7	692.1	655.1	623.7	593.0
27.5°	937.6	896.8	858.6	825.4	786.4	750.2	709.5	666.9	628.0	596.1	564.6
30°	927.0	881.1	839.0	801.3	764.4	730.0	691.4	649.9	610.0	577.0	544.9
32.5°	913.6	864.9	818.6	775.2	739.5	705.4	670.5	630.8	591.9	557.8	525.3
35°	896.8	834.7	784.3	738.2	698.6	665.6	634.2	602.1	563.2	527.9	496.2
37.5°	874.9	804.3	746.1	695.8	654.1	620.9	596.2	566.8	531.3	497.5	468.0
40°	861.5	782.4	718.6	668.8	625.0	590.0	566.8	541.9	509.5	477.9	448.4
42.5°	843.7	762.2	690.9	639.0	595.0	561.3	537.8	516.1	488.9	459.0	427.5
45°	808.8	723.2	648.2	592.6	548.2	515.1	493.2	473.9	453.3	425.9	398.4
47.5°	763.4	682.4	604.0	543.3	499.7	469.1	447.8	432.6	417.8	394.5	367.8
50°	727.1	648.9	572.4	513.5	467.1	437.9	418.0	405.9	392.4	371.3	349.0
52.5°	684.2	614.4	539.4	479.2	435.4	408.1	388.9	376.9	365.8	348.4	327.3
55°	616.6	555.3	486.6	432.0	391.8	364.4	346.0	334.6	328.0	313.3	296.6
57.5°	538.5	494.6	434.1	381.4	345.9	318.7	305.3	295.6	288.2	277.8	266.0
60°	484.1	453.3	399.0	349.0	316.2	290.4	278.4	270.2	263.3	254.4	245.3
62.5°	428.9	406.5	359.3	316.2	286.2	264.5	253.2	245.8	237.9	232.0	223.1
65°	354.9	334.9	302.2	268.5	240.7	223.4	215.2	208.7	203.8	197.3	191.0
67.5°	276.0	267.9	245.4	222.1	202.2	186.8	179.7	175.1	169.2	165.3	161.0
70°	227.6	223.7	207.7	192.3	173.7	163.2	156.7	154.7	147.5	143.6	140.6
72.5°	184.8	182.9	173.7	163.0	149.9	140.7	134.7	132.4	127.9	124.8	122.9
75°	126.6	127.3	125.6	118.7	113.8	108.0	102.7	101.4	98.2	95.5	93.8
77.5°	80.1	83.4	83.5	83.2	81.3	77.7	75.5	74.5	71.3	70.3	69.9
80°	54.9	58.5	61.8	61.5	60.9	59.8	58.2	57.3	55.6	54.6	54.0
82.5°	36.6	40.0	42.7	44.5	44.3	43.4	42.3	41.8	41.5	40.7	40.6
85°	17.3	18.0	18.9	21.3	22.9	23.2	22.9	22.6	21.6	22.0	22.2
87.5°	6.8	6.7	6.9	6.8	6.4	7.6	8.3	8.4	8.0	7.6	7.1
90°	4.0	3.4	3.0	2.4	1.8	1.2	0.6	0.3	0.6	1.2	1.8
92.5°	69.4	41.6	25.0	16.1	10.8	7.1	4.5	3.7	4.5	7.1	10.8
95°	136.0	69.1	36.5	22.8	16.1	12.7	10.3	10.1	10.3	12.7	16.1
97.5°	108.6	59.5	38.0	28.2	22.1	18.8	17.0	16.7	17.0	18.8	22.1
100°	98.6	59.1	41.4	32.3	26.4	23.2	21.9	21.3	21.9	23.2	26.4
102.5°	94.5	61.2	45.5	36.7	31.3	27.7	26.8	26.4	26.8	27.7	31.3
105°	92.8	65.7	52.3	43.8	38.9	35.9	34.4	34.4	34.4	35.9	38.9
107.5°	95.6	72.4	59.5	51.8	46.8	44.3	42.8	42.2	42.8	44.3	46.8
110°	98.3	77.3	64.8	56.9	52.3	49.6	48.4	47.8	48.4	49.6	52.3



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	101.7	81.9	69.9	62.3	57.7	54.9	54.0	53.4	54.0	54.9	57.7
115°	106.8	89.2	77.9	70.3	65.7	63.0	62.1	61.5	62.1	63.0	65.7
117.5°	112.6	96.6	85.9	78.6	73.4	70.7	69.7	68.8	69.7	70.7	73.4
120°	116.6	101.9	91.3	83.7	78.5	75.8	74.6	73.6	74.6	75.8	78.5
122.5°	120.9	107.0	96.4	88.8	83.2	80.4	79.4	78.8	79.4	80.4	83.2
125°	126.9	113.8	103.8	95.8	90.1	87.3	85.8	85.2	85.8	87.3	90.1
127.5°	132.3	120.3	110.6	102.7	96.6	93.1	91.2	90.2	91.2	93.1	96.6
130°	136.0	124.4	115.0	107.1	100.7	96.8	94.4	93.4	94.4	96.8	100.7
132.5°	139.2	128.4	118.9	111.0	104.4	100.0	97.0	95.8	97.0	100.0	104.4
135°	143.6	133.5	124.2	116.0	109.5	104.7	101.0	99.8	101.0	104.7	109.5
137.5°	146.9	137.3	128.7	120.3	114.0	109.1	105.7	104.8	105.7	109.1	114.0
140°	149.1	140.0	131.1	123.0	117.2	112.3	108.7	107.7	108.7	112.3	117.2
142.5°	150.3	141.6	133.4	125.6	120.1	115.2	111.8	111.2	111.8	115.2	120.1
145°	152.1	144.6	136.6	129.7	124.2	119.9	116.8	116.2	116.8	119.9	124.2
147.5°	153.3	146.4	139.4	133.3	128.5	124.6	121.9	121.6	121.9	124.6	128.5
150°	153.9	147.6	140.9	135.7	131.5	127.5	125.4	124.8	125.4	127.5	131.5
152.5°	154.5	148.8	142.6	137.9	133.9	130.4	128.5	128.2	128.5	130.4	133.9
155°	154.9	150.0	144.8	140.6	137.5	134.5	132.7	132.7	132.7	134.5	137.5
157.5°	155.2	151.0	146.6	143.4	140.7	138.1	136.6	136.7	136.6	138.1	140.7
160°	155.2	151.5	147.6	144.8	142.4	140.3	139.1	139.4	139.1	140.3	142.4
162.5°	155.0	152.1	148.5	146.3	144.4	142.5	141.3	141.5	141.3	142.5	144.4
165°	154.5	152.1	149.7	147.9	146.6	145.2	144.2	144.8	144.2	145.2	146.6
167.5°	153.9	152.1	150.2	149.0	148.1	147.3	146.7	147.1	146.7	147.3	148.1
170°	153.3	152.1	150.6	149.7	149.1	148.5	148.2	148.5	148.2	148.5	149.1
172.5°	152.9	151.9	150.6	150.2	149.8	149.2	149.0	149.5	149.0	149.2	149.8
175°	152.1	151.5	150.6	150.6	150.6	150.3	150.0	150.6	150.0	150.3	150.6
177.5°	151.4	151.2	150.7	150.7	150.9	150.7	150.7	151.2	150.7	150.7	150.9
180°	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	783.4	779.7	777.1	771.9	768.2	766.6	763.8	763.0	765.9	763.8	763.5
5°	760.1	750.6	743.1	735.6	727.4	722.2	714.3	713.0	711.0	708.1	707.5
7.5°	732.2	719.8	710.2	697.7	686.9	678.2	668.4	663.7	661.2	657.4	652.3
10°	713.3	698.6	685.5	673.1	659.7	648.9	639.1	631.5	626.6	622.1	620.1
12.5°	694.7	679.8	663.1	648.0	633.0	620.9	610.0	605.1	599.7	594.3	589.8
15°	665.9	645.9	627.7	610.3	597.5	584.4	574.0	566.8	558.6	556.4	547.5
17.5°	635.3	615.7	594.3	576.0	561.3	546.8	535.4	527.2	521.0	512.6	508.5
20°	616.2	593.0	572.0	555.3	539.0	522.0	510.2	503.3	497.5	490.6	487.3
22.5°	595.8	573.1	551.6	532.1	515.5	498.7	490.3	483.2	476.6	470.2	465.9
25°	565.8	542.9	520.4	500.1	482.8	470.6	460.8	452.6	449.1	442.8	438.2
27.5°	536.2	511.9	488.4	468.2	454.6	442.6	434.6	428.2	421.6	416.2	412.2
30°	517.1	492.2	466.7	450.7	436.3	424.9	416.0	409.8	404.9	400.0	397.1
32.5°	498.0	472.3	449.7	432.4	418.8	408.9	399.8	393.8	388.7	383.2	379.8
35°	467.4	441.2	422.9	405.9	392.4	383.3	377.1	368.6	364.4	360.4	356.8
37.5°	438.9	414.6	394.8	379.9	368.2	359.1	351.1	346.5	341.3	337.8	334.8
40°	418.0	395.7	377.8	362.1	353.5	343.5	335.9	330.0	326.1	321.5	318.2
42.5°	399.2	378.5	361.0	346.9	336.3	327.7	320.5	314.6	309.6	306.3	303.6
45°	372.6	351.9	334.9	321.8	312.0	303.8	296.4	293.3	286.8	282.9	281.6
47.5°	345.0	326.6	310.1	298.1	288.0	280.3	273.2	267.3	263.6	259.8	257.7
50°	326.4	308.8	293.3	281.6	271.8	263.3	256.8	252.8	247.9	244.4	241.7
52.5°	307.8	291.4	276.1	264.8	256.3	247.9	240.6	236.6	232.0	229.6	227.8
55°	281.3	264.0	250.9	239.7	230.9	223.1	216.2	212.2	209.3	207.1	206.4
57.5°	251.2	237.5	225.3	215.2	206.1	198.7	192.7	189.0	186.4	186.1	184.1
60°	231.5	219.1	208.0	197.3	189.3	182.5	177.3	173.1	170.4	170.0	169.4
62.5°	212.0	200.0	189.7	180.2	173.1	166.5	161.6	156.8	155.2	153.6	152.1
65°	182.8	172.0	163.5	156.0	148.5	142.9	138.0	135.1	131.5	129.5	126.0
67.5°	154.2	145.9	137.7	131.4	125.4	120.2	116.1	111.8	109.3	107.7	105.1
70°	135.4	128.9	120.7	113.8	109.3	105.0	101.7	96.8	95.1	93.8	92.6
72.5°	117.6	111.8	105.0	99.4	94.9	90.8	87.0	84.8	83.2	81.8	81.0
75°	92.6	87.0	81.1	77.1	74.0	70.7	68.7	67.1	66.4	66.0	64.7
77.5°	67.9	65.0	60.3	57.2	55.0	53.7	51.9	51.1	51.1	49.6	49.2
80°	52.0	50.4	46.4	45.1	43.5	42.2	41.2	39.6	38.0	37.3	36.3
82.5°	38.7	37.0	35.5	33.3	32.0	31.2	30.2	29.6	29.8	28.9	28.4
85°	20.6	18.9	18.3	18.0	17.3	18.0	17.7	17.3	17.0	16.7	17.0
87.5°	7.1	7.1	7.0	7.6	6.9	7.2	7.3	7.1	7.1	7.2	7.1
90°	2.4	3.0	3.4	4.0	4.2	4.9	5.2	5.5	5.8	6.1	6.7
92.5°	16.1	25.0	41.6	69.4	99.7	98.1	79.4	53.9	39.1	29.4	25.0
95°	22.8	36.5	69.1	136.0	220.0	269.6	263.8	218.8	172.5	135.1	109.5
97.5°	28.2	38.0	59.5	108.6	196.5	287.9	333.8	325.8	293.4	256.9	221.4
100°	32.3	41.4	59.1	98.6	175.3	274.7	350.9	374.3	359.4	328.0	296.4
102.5°	36.7	45.5	61.2	94.5	159.2	251.7	340.6	390.5	399.8	384.8	363.3
105°	43.8	52.3	65.7	92.8	143.6	220.6	308.0	381.0	422.7	436.0	432.7
107.5°	51.8	59.5	72.4	95.6	137.1	199.2	274.6	346.6	402.3	436.6	452.5
110°	56.9	64.8	77.3	98.3	135.1	189.2	255.6	321.3	379.2	422.1	447.9



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	62.3	69.9	81.9	101.7	135.1	183.4	241.5	301.4	356.3	399.7	430.2
115°	70.3	77.9	89.2	106.8	136.0	177.1	226.1	276.3	323.5	365.2	398.3
117.5°	78.6	85.9	96.6	112.6	138.0	174.0	216.9	260.1	300.7	336.7	367.1
120°	83.7	91.3	101.9	116.6	140.0	172.5	211.8	251.3	287.8	321.3	348.1
122.5°	88.8	96.4	107.0	120.9	141.6	171.3	207.4	244.8	278.6	308.4	333.5
125°	95.8	103.8	113.8	126.9	144.6	169.8	201.5	235.2	266.2	292.7	314.6
127.5°	102.7	110.6	120.3	132.3	147.7	169.1	196.0	225.5	254.4	279.1	299.6
130°	107.1	115.0	124.4	136.0	149.7	168.6	192.3	219.4	246.2	269.9	289.7
132.5°	111.0	118.9	128.4	139.2	151.9	168.6	189.4	213.3	238.4	259.9	279.0
135°	116.0	124.2	133.5	143.6	154.9	168.6	185.9	205.4	226.4	245.9	263.2
137.5°	120.3	128.7	137.3	146.9	157.6	168.9	182.8	198.7	215.7	231.9	246.6
140°	123.0	131.1	140.0	149.1	158.9	169.2	181.3	195.0	209.3	223.3	236.1
142.5°	125.6	133.4	141.6	150.3	159.5	169.4	180.1	191.9	204.0	216.0	227.1
145°	129.7	136.6	144.6	152.1	160.3	169.2	178.3	187.8	197.2	206.6	214.8
147.5°	133.3	139.4	146.4	153.3	160.7	168.4	176.4	183.8	191.5	198.8	205.0
150°	135.7	140.9	147.6	153.9	160.7	167.6	175.0	181.7	188.4	194.2	199.6
152.5°	137.9	142.6	148.8	154.5	160.4	166.7	173.2	179.3	185.2	190.5	194.8
155°	140.6	144.8	150.0	154.9	159.7	165.0	170.4	175.6	180.5	184.7	188.0
157.5°	143.4	146.6	151.0	155.2	158.9	163.1	167.7	171.9	175.9	179.3	181.8
160°	144.8	147.6	151.5	155.2	158.3	161.9	165.6	169.5	172.5	175.6	177.7
162.5°	146.3	148.5	152.1	155.0	157.5	160.4	163.6	166.8	169.6	172.2	174.1
165°	147.9	149.7	152.1	154.5	156.4	158.3	160.7	163.1	165.2	167.0	168.6
167.5°	149.0	150.2	152.1	153.9	154.7	156.1	157.8	159.5	161.0	162.4	163.5
170°	149.7	150.6	152.1	153.3	153.9	154.9	156.1	157.6	158.5	159.5	160.1
172.5°	150.2	150.6	151.9	152.9	153.0	153.4	154.4	155.4	156.4	157.0	157.4
175°	150.6	150.6	151.5	152.1	151.9	151.9	152.1	153.1	153.1	153.7	153.7
177.5°	150.7	150.7	151.2	151.4	150.9	150.9	151.2	151.4	151.6	151.6	151.6
180°	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	763.3	760.3	759.6	760.6	759.6	760.3	763.3	763.5	763.8	765.9	763.0
5°	704.2	700.9	702.6	701.9	702.6	700.9	704.2	707.5	708.1	711.0	713.0
7.5°	652.2	648.2	643.9	645.2	643.9	648.2	652.2	652.3	657.4	661.2	663.7
10°	615.9	612.6	610.6	612.3	610.6	612.6	615.9	620.1	622.1	626.6	631.5
12.5°	585.2	583.3	581.6	580.9	581.6	583.3	585.2	589.8	594.3	599.7	605.1
15°	543.5	539.7	538.0	533.8	538.0	539.7	543.5	547.5	556.4	558.6	566.8
17.5°	505.1	503.9	499.6	497.8	499.6	503.9	505.1	508.5	512.6	521.0	527.2
20°	482.4	481.1	476.9	479.5	476.9	481.1	482.4	487.3	490.6	497.5	503.3
22.5°	463.6	460.7	459.3	458.6	459.3	460.7	463.6	465.9	470.2	476.6	483.2
25°	437.0	432.7	431.1	429.1	431.1	432.7	437.0	438.2	442.8	449.1	452.6
27.5°	410.4	408.1	406.0	405.4	406.0	408.1	410.4	412.2	416.2	421.6	428.2
30°	393.1	390.8	389.2	389.2	389.2	390.8	393.1	397.1	400.0	404.9	409.8
32.5°	377.7	375.9	374.3	374.0	374.3	375.9	377.7	379.8	383.2	388.7	393.8
35°	355.2	352.6	351.9	350.0	351.9	352.6	355.2	356.8	360.4	364.4	368.6
37.5°	331.8	329.7	329.6	329.4	329.6	329.7	331.8	334.8	337.8	341.3	346.5
40°	316.9	315.3	315.0	312.7	315.0	315.3	316.9	318.2	321.5	326.1	330.0
42.5°	301.0	300.1	299.0	298.0	299.0	300.1	301.0	303.6	306.3	309.6	314.6
45°	279.3	277.1	277.1	275.4	277.1	277.1	279.3	281.6	282.9	286.8	293.3
47.5°	256.9	255.2	255.4	253.7	255.4	255.2	256.9	257.7	259.8	263.6	267.3
50°	242.0	241.1	240.7	240.0	240.7	241.1	242.0	241.7	244.4	247.9	252.8
52.5°	227.1	226.7	227.9	226.4	227.9	226.7	227.1	227.8	229.6	232.0	236.6
55°	207.1	206.0	208.0	206.0	208.0	206.0	207.1	206.4	207.1	209.3	212.2
57.5°	183.9	183.0	184.8	183.8	184.8	183.0	183.9	184.1	186.1	186.4	189.0
60°	168.8	166.8	167.8	168.2	167.8	166.8	168.8	169.4	170.0	170.4	173.1
62.5°	150.7	149.6	150.2	148.8	150.2	149.6	150.7	152.1	153.6	155.2	156.8
65°	125.3	124.3	123.0	122.3	123.0	124.3	125.3	126.0	129.5	131.5	135.1
67.5°	105.2	102.9	102.8	103.3	102.8	102.9	105.2	105.1	107.7	109.3	111.8
70°	90.6	90.6	90.2	90.2	90.2	90.6	90.6	92.6	93.8	95.1	96.8
72.5°	80.4	80.2	79.6	79.3	79.6	80.2	80.4	81.0	81.8	83.2	84.8
75°	64.7	65.1	64.4	64.1	64.4	65.1	64.7	64.7	66.0	66.4	67.1
77.5°	47.8	46.4	47.2	46.4	47.2	46.4	47.8	49.2	49.6	51.1	51.1
80°	36.3	36.0	36.9	36.0	36.9	36.0	36.3	36.3	37.3	38.0	39.6
82.5°	28.8	28.4	28.8	28.2	28.8	28.4	28.8	28.4	28.9	29.8	29.6
85°	17.3	17.0	16.7	17.0	16.7	17.0	17.3	17.0	16.7	17.0	17.3
87.5°	7.3	7.1	7.1	7.1	7.1	7.1	7.3	7.1	7.2	7.1	7.1
90°	6.7	6.7	7.0	7.0	7.0	6.7	6.7	6.7	6.1	5.8	5.5
92.5°	21.1	20.3	19.9	19.4	19.9	20.3	21.1	25.0	29.4	39.1	53.9
95°	87.9	78.8	76.4	71.5	76.4	78.8	87.9	109.5	135.1	172.5	218.8
97.5°	202.6	185.5	176.8	172.8	176.8	185.5	202.6	221.4	256.9	293.4	325.8
100°	275.3	253.5	242.2	237.4	242.2	253.5	275.3	296.4	328.0	359.4	374.3
102.5°	340.9	325.3	313.1	309.4	313.1	325.3	340.9	363.3	384.8	399.8	390.5
105°	422.9	412.9	406.8	403.2	406.8	412.9	422.9	432.7	436.0	422.7	381.0
107.5°	457.4	457.4	455.4	453.0	455.4	457.4	457.4	452.5	436.6	402.3	346.6
110°	461.6	467.4	469.5	469.5	469.5	467.4	461.6	447.9	422.1	379.2	321.3



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	450.1	460.1	465.4	467.6	465.4	460.1	450.1	430.2	399.7	356.3	301.4
115°	422.1	436.6	445.1	449.1	445.1	436.6	422.1	398.3	365.2	323.5	276.3
117.5°	390.8	406.0	414.4	416.8	414.4	406.0	390.8	367.1	336.7	300.7	260.1
120°	370.7	385.2	393.5	395.9	393.5	385.2	370.7	348.1	321.3	287.8	251.3
122.5°	353.6	367.0	375.2	377.4	375.2	367.0	353.6	333.5	308.4	278.6	244.8
125°	331.7	344.1	350.9	353.9	350.9	344.1	331.7	314.6	292.7	266.2	235.2
127.5°	315.1	326.1	332.4	333.8	332.4	326.1	315.1	299.6	279.1	254.4	225.5
130°	304.9	315.0	321.1	322.9	321.1	315.0	304.9	289.7	269.9	246.2	219.4
132.5°	294.2	304.2	309.8	311.9	309.8	304.2	294.2	279.0	259.9	238.4	213.3
135°	276.6	286.6	292.1	293.9	292.1	286.6	276.6	263.2	245.9	226.4	205.4
137.5°	258.6	267.7	272.8	274.7	272.8	267.7	258.6	246.6	231.9	215.7	198.7
140°	247.4	255.3	259.8	261.4	259.8	255.3	247.4	236.1	223.3	209.3	195.0
142.5°	236.7	243.4	247.7	249.0	247.7	243.4	236.7	227.1	216.0	204.0	191.9
145°	222.1	227.3	230.7	231.9	230.7	227.3	222.1	214.8	206.6	197.2	187.8
147.5°	210.8	214.9	216.8	217.4	216.8	214.9	210.8	205.0	198.8	191.5	183.8
150°	204.1	207.8	209.1	209.3	209.1	207.8	204.1	199.6	194.2	188.4	181.7
152.5°	198.5	201.5	202.7	203.0	202.7	201.5	198.5	194.8	190.5	185.2	179.3
155°	191.1	193.2	194.2	194.4	194.2	193.2	191.1	188.0	184.7	180.5	175.6
157.5°	184.3	186.0	186.8	186.8	186.8	186.0	184.3	181.8	179.3	175.9	171.9
160°	179.9	181.3	181.9	181.7	181.9	181.3	179.9	177.7	175.6	172.5	169.5
162.5°	175.7	176.9	177.1	177.0	177.1	176.9	175.7	174.1	172.2	169.6	166.8
165°	169.8	170.4	170.4	170.4	170.4	170.4	169.8	168.6	167.0	165.2	163.1
167.5°	164.1	164.6	164.4	164.3	164.4	164.6	164.1	163.5	162.4	161.0	159.5
170°	160.7	161.0	161.0	160.7	161.0	161.0	160.7	160.1	159.5	158.5	157.6
172.5°	157.5	158.1	157.6	157.2	157.6	158.1	157.5	157.4	157.0	156.4	155.4
175°	153.7	153.9	153.3	153.1	153.3	153.9	153.7	153.7	153.7	153.1	153.1
177.5°	151.4	151.6	150.9	150.9	150.9	151.6	151.4	151.6	151.6	151.6	151.4
180°	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	763.8	766.6	768.2	771.9	777.1	779.7	783.4	786.0	789.7	794.1	797.8
5°	714.3	722.2	727.4	735.6	743.1	750.6	760.1	767.0	776.1	786.6	794.8
7.5°	668.4	678.2	686.9	697.7	710.2	719.8	732.2	744.8	759.1	774.0	788.0
10°	639.1	648.9	659.7	673.1	685.5	698.6	713.3	728.1	746.1	762.8	781.7
12.5°	610.0	620.9	633.0	648.0	663.1	679.8	694.7	711.3	730.6	752.3	772.6
15°	574.0	584.4	597.5	610.3	627.7	645.9	665.9	687.9	709.4	733.7	758.8
17.5°	535.4	546.8	561.3	576.0	594.3	615.7	635.3	659.3	683.5	711.8	741.4
20°	510.2	522.0	539.0	555.3	572.0	593.0	616.2	640.8	666.6	696.3	729.4
22.5°	490.3	498.7	515.5	532.1	551.6	573.1	595.8	621.4	649.5	680.4	715.0
25°	460.8	470.6	482.8	500.1	520.4	542.9	565.8	593.0	623.7	655.1	692.1
27.5°	434.6	442.6	454.6	468.2	488.4	511.9	536.2	564.6	596.1	628.0	666.9
30°	416.0	424.9	436.3	450.7	466.7	492.2	517.1	544.9	577.0	610.0	649.9
32.5°	399.8	408.9	418.8	432.4	449.7	472.3	498.0	525.3	557.8	591.9	630.8
35°	377.1	383.3	392.4	405.9	422.9	441.2	467.4	496.2	527.9	563.2	602.1
37.5°	351.1	359.1	368.2	379.9	394.8	414.6	438.9	468.0	497.5	531.3	566.8
40°	335.9	343.5	353.5	362.1	377.8	395.7	418.0	448.4	477.9	509.5	541.9
42.5°	320.5	327.7	336.3	346.9	361.0	378.5	399.2	427.5	459.0	488.9	516.1
45°	296.4	303.8	312.0	321.8	334.9	351.9	372.6	398.4	425.9	453.3	473.9
47.5°	273.2	280.3	288.0	298.1	310.1	326.6	345.0	367.8	394.5	417.8	432.6
50°	256.8	263.3	271.8	281.6	293.3	308.8	326.4	349.0	371.3	392.4	405.9
52.5°	240.6	247.9	256.3	264.8	276.1	291.4	307.8	327.3	348.4	365.8	376.9
55°	216.2	223.1	230.9	239.7	250.9	264.0	281.3	296.6	313.3	328.0	334.6
57.5°	192.7	198.7	206.1	215.2	225.3	237.5	251.2	266.0	277.8	288.2	295.6
60°	177.3	182.5	189.3	197.3	208.0	219.1	231.5	245.3	254.4	263.3	270.2
62.5°	161.6	166.5	173.1	180.2	189.7	200.0	212.0	223.1	232.0	237.9	245.8
65°	138.0	142.9	148.5	156.0	163.5	172.0	182.8	191.0	197.3	203.8	208.7
67.5°	116.1	120.2	125.4	131.4	137.7	145.9	154.2	161.0	165.3	169.2	175.1
70°	101.7	105.0	109.3	113.8	120.7	128.9	135.4	140.6	143.6	147.5	154.7
72.5°	87.0	90.8	94.9	99.4	105.0	111.8	117.6	122.9	124.8	127.9	132.4
75°	68.7	70.7	74.0	77.1	81.1	87.0	92.6	93.8	95.5	98.2	101.4
77.5°	51.9	53.7	55.0	57.2	60.3	65.0	67.9	69.9	70.3	71.3	74.5
80°	41.2	42.2	43.5	45.1	46.4	50.4	52.0	54.0	54.6	55.6	57.3
82.5°	30.2	31.2	32.0	33.3	35.5	37.0	38.7	40.6	40.7	41.5	41.8
85°	17.7	18.0	17.3	18.0	18.3	18.9	20.6	22.2	22.0	21.6	22.6
87.5°	7.3	7.2	6.9	7.6	7.0	7.1	7.1	7.1	7.6	8.0	8.4
90°	5.2	4.9	4.2	4.0	3.4	3.0	2.4	1.8	1.2	0.6	0.3
92.5°	79.4	98.1	99.7	69.4	41.6	25.0	16.1	10.8	7.1	4.5	3.7
95°	263.8	269.6	220.0	136.0	69.1	36.5	22.8	16.1	12.7	10.3	10.1
97.5°	333.8	287.9	196.5	108.6	59.5	38.0	28.2	22.1	18.8	17.0	16.7
100°	350.9	274.7	175.3	98.6	59.1	41.4	32.3	26.4	23.2	21.9	21.3
102.5°	340.6	251.7	159.2	94.5	61.2	45.5	36.7	31.3	27.7	26.8	26.4
105°	308.0	220.6	143.6	92.8	65.7	52.3	43.8	38.9	35.9	34.4	34.4
107.5°	274.6	199.2	137.1	95.6	72.4	59.5	51.8	46.8	44.3	42.8	42.2
110°	255.6	189.2	135.1	98.3	77.3	64.8	56.9	52.3	49.6	48.4	47.8



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	241.5	183.4	135.1	101.7	81.9	69.9	62.3	57.7	54.9	54.0	53.4
115°	226.1	177.1	136.0	106.8	89.2	77.9	70.3	65.7	63.0	62.1	61.5
117.5°	216.9	174.0	138.0	112.6	96.6	85.9	78.6	73.4	70.7	69.7	68.8
120°	211.8	172.5	140.0	116.6	101.9	91.3	83.7	78.5	75.8	74.6	73.6
122.5°	207.4	171.3	141.6	120.9	107.0	96.4	88.8	83.2	80.4	79.4	78.8
125°	201.5	169.8	144.6	126.9	113.8	103.8	95.8	90.1	87.3	85.8	85.2
127.5°	196.0	169.1	147.7	132.3	120.3	110.6	102.7	96.6	93.1	91.2	90.2
130°	192.3	168.6	149.7	136.0	124.4	115.0	107.1	100.7	96.8	94.4	93.4
132.5°	189.4	168.6	151.9	139.2	128.4	118.9	111.0	104.4	100.0	97.0	95.8
135°	185.9	168.6	154.9	143.6	133.5	124.2	116.0	109.5	104.7	101.0	99.8
137.5°	182.8	168.9	157.6	146.9	137.3	128.7	120.3	114.0	109.1	105.7	104.8
140°	181.3	169.2	158.9	149.1	140.0	131.1	123.0	117.2	112.3	108.7	107.7
142.5°	180.1	169.4	159.5	150.3	141.6	133.4	125.6	120.1	115.2	111.8	111.2
145°	178.3	169.2	160.3	152.1	144.6	136.6	129.7	124.2	119.9	116.8	116.2
147.5°	176.4	168.4	160.7	153.3	146.4	139.4	133.3	128.5	124.6	121.9	121.6
150°	175.0	167.6	160.7	153.9	147.6	140.9	135.7	131.5	127.5	125.4	124.8
152.5°	173.2	166.7	160.4	154.5	148.8	142.6	137.9	133.9	130.4	128.5	128.2
155°	170.4	165.0	159.7	154.9	150.0	144.8	140.6	137.5	134.5	132.7	132.7
157.5°	167.7	163.1	158.9	155.2	151.0	146.6	143.4	140.7	138.1	136.6	136.7
160°	165.6	161.9	158.3	155.2	151.5	147.6	144.8	142.4	140.3	139.1	139.4
162.5°	163.6	160.4	157.5	155.0	152.1	148.5	146.3	144.4	142.5	141.3	141.5
165°	160.7	158.3	156.4	154.5	152.1	149.7	147.9	146.6	145.2	144.2	144.8
167.5°	157.8	156.1	154.7	153.9	152.1	150.2	149.0	148.1	147.3	146.7	147.1
170°	156.1	154.9	153.9	153.3	152.1	150.6	149.7	149.1	148.5	148.2	148.5
172.5°	154.4	153.4	153.0	152.9	151.9	150.6	150.2	149.8	149.2	149.0	149.5
175°	152.1	151.9	151.9	152.1	151.5	150.6	150.6	150.6	150.3	150.0	150.6
177.5°	151.2	150.9	150.9	151.4	151.2	150.7	150.7	150.9	150.7	150.7	151.2
180°	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	800.6	803.1	806.4	810.4	813.5	816.9	818.7	818.7	820.3	823.7	828.1
5°	803.0	811.5	819.7	830.1	838.3	847.7	855.0	861.9	868.1	875.9	884.1
7.5°	802.3	816.4	831.1	847.7	865.8	880.3	895.1	906.8	918.3	933.3	945.2
10°	799.7	818.0	837.9	858.8	881.8	901.7	919.7	936.1	951.7	968.1	982.8
12.5°	795.0	818.3	842.7	867.8	896.7	919.5	942.7	960.2	978.4	996.3	1014.5
15°	787.9	815.4	844.8	879.9	915.2	940.6	963.5	986.1	1003.2	1023.4	1040.8
17.5°	773.4	808.7	845.8	884.0	917.9	947.6	971.6	993.1	1011.2	1033.5	1057.0
20°	764.7	803.0	841.5	882.4	914.8	945.2	968.5	990.7	1013.2	1042.4	1071.2
22.5°	752.7	793.5	834.5	873.3	907.5	936.9	960.9	988.1	1017.7	1050.8	1085.5
25°	733.7	775.8	816.4	853.3	886.7	916.8	949.5	986.1	1022.1	1065.6	1115.6
27.5°	709.5	750.2	786.4	825.4	858.6	896.8	937.6	977.3	1029.2	1089.1	1151.6
30°	691.4	730.0	764.4	801.3	839.0	881.1	927.0	973.7	1035.5	1105.8	1180.1
32.5°	670.5	705.4	739.5	775.2	818.6	864.9	913.6	970.8	1044.7	1124.6	1201.5
35°	634.2	665.6	698.6	738.2	784.3	834.7	896.8	966.5	1055.8	1141.8	1210.8
37.5°	596.2	620.9	654.1	695.8	746.1	804.3	874.9	959.5	1051.2	1128.4	1157.8
40°	566.8	590.0	625.0	668.8	718.6	782.4	861.5	948.5	1040.8	1094.3	1092.1
42.5°	537.8	561.3	595.0	639.0	690.9	762.2	843.7	934.1	1011.9	1032.3	989.8
45°	493.2	515.1	548.2	592.6	648.2	723.2	808.8	895.5	945.2	912.2	827.9
47.5°	447.8	469.1	499.7	543.3	604.0	682.4	763.4	834.6	841.5	770.6	669.3
50°	418.0	437.9	467.1	513.5	572.4	648.9	727.1	783.0	765.7	679.0	574.6
52.5°	388.9	408.1	435.4	479.2	539.4	614.4	684.2	728.1	687.9	595.8	502.0
55°	346.0	364.4	391.8	432.0	486.6	555.3	616.6	632.6	573.7	480.8	404.9
57.5°	305.3	318.7	345.9	381.4	434.1	494.6	538.5	535.6	470.6	387.0	332.6
60°	278.4	290.4	316.2	349.0	399.0	453.3	484.1	471.0	405.3	336.2	283.9
62.5°	253.2	264.5	286.2	316.2	359.3	406.5	428.9	410.8	348.7	288.1	246.5
65°	215.2	223.4	240.7	268.5	302.2	334.9	354.9	328.4	273.5	227.6	196.2
67.5°	179.7	186.8	202.2	222.1	245.4	267.9	276.0	251.2	208.4	177.6	155.5
70°	156.7	163.2	173.7	192.3	207.7	223.7	227.6	205.4	169.8	146.2	132.4
72.5°	134.7	140.7	149.9	163.0	173.7	182.9	184.8	164.0	136.8	120.5	109.9
75°	102.7	108.0	113.8	118.7	125.6	127.3	126.6	110.6	95.8	85.1	79.1
77.5°	75.5	77.7	81.3	83.2	83.5	83.4	80.1	69.9	62.3	57.9	55.4
80°	58.2	59.8	60.9	61.5	61.8	58.5	54.9	48.7	46.1	43.5	40.6
82.5°	42.3	43.4	44.3	44.5	42.7	40.0	36.6	33.6	31.7	30.4	29.3
85°	22.9	23.2	22.9	21.3	18.9	18.0	17.3	16.7	16.4	16.0	16.0
87.5°	8.3	7.6	6.4	6.8	6.9	6.7	6.8	6.6	6.5	6.5	6.6
90°	0.6	1.2	1.8	2.4	3.0	3.4	4.0	4.2	4.9	5.2	5.5
92.5°	4.5	7.1	10.8	16.1	25.0	41.6	69.4	99.7	98.1	79.4	53.9
95°	10.3	12.7	16.1	22.8	36.5	69.1	136.0	220.0	269.6	263.8	218.8
97.5°	17.0	18.8	22.1	28.2	38.0	59.5	108.6	196.5	287.9	333.8	325.8
100°	21.9	23.2	26.4	32.3	41.4	59.1	98.6	175.3	274.7	350.9	374.3
102.5°	26.8	27.7	31.3	36.7	45.5	61.2	94.5	159.2	251.7	340.6	390.5
105°	34.4	35.9	38.9	43.8	52.3	65.7	92.8	143.6	220.6	308.0	381.0
107.5°	42.8	44.3	46.8	51.8	59.5	72.4	95.6	137.1	199.2	274.6	346.6
110°	48.4	49.6	52.3	56.9	64.8	77.3	98.3	135.1	189.2	255.6	321.3



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	54.0	54.9	57.7	62.3	69.9	81.9	101.7	135.1	183.4	241.5	301.4
115°	62.1	63.0	65.7	70.3	77.9	89.2	106.8	136.0	177.1	226.1	276.3
117.5°	69.7	70.7	73.4	78.6	85.9	96.6	112.6	138.0	174.0	216.9	260.1
120°	74.6	75.8	78.5	83.7	91.3	101.9	116.6	140.0	172.5	211.8	251.3
122.5°	79.4	80.4	83.2	88.8	96.4	107.0	120.9	141.6	171.3	207.4	244.8
125°	85.8	87.3	90.1	95.8	103.8	113.8	126.9	144.6	169.8	201.5	235.2
127.5°	91.2	93.1	96.6	102.7	110.6	120.3	132.3	147.7	169.1	196.0	225.5
130°	94.4	96.8	100.7	107.1	115.0	124.4	136.0	149.7	168.6	192.3	219.4
132.5°	97.0	100.0	104.4	111.0	118.9	128.4	139.2	151.9	168.6	189.4	213.3
135°	101.0	104.7	109.5	116.0	124.2	133.5	143.6	154.9	168.6	185.9	205.4
137.5°	105.7	109.1	114.0	120.3	128.7	137.3	146.9	157.6	168.9	182.8	198.7
140°	108.7	112.3	117.2	123.0	131.1	140.0	149.1	158.9	169.2	181.3	195.0
142.5°	111.8	115.2	120.1	125.6	133.4	141.6	150.3	159.5	169.4	180.1	191.9
145°	116.8	119.9	124.2	129.7	136.6	144.6	152.1	160.3	169.2	178.3	187.8
147.5°	121.9	124.6	128.5	133.3	139.4	146.4	153.3	160.7	168.4	176.4	183.8
150°	125.4	127.5	131.5	135.7	140.9	147.6	153.9	160.7	167.6	175.0	181.7
152.5°	128.5	130.4	133.9	137.9	142.6	148.8	154.5	160.4	166.7	173.2	179.3
155°	132.7	134.5	137.5	140.6	144.8	150.0	154.9	159.7	165.0	170.4	175.6
157.5°	136.6	138.1	140.7	143.4	146.6	151.0	155.2	158.9	163.1	167.7	171.9
160°	139.1	140.3	142.4	144.8	147.6	151.5	155.2	158.3	161.9	165.6	169.5
162.5°	141.3	142.5	144.4	146.3	148.5	152.1	155.0	157.5	160.4	163.6	166.8
165°	144.2	145.2	146.6	147.9	149.7	152.1	154.5	156.4	158.3	160.7	163.1
167.5°	146.7	147.3	148.1	149.0	150.2	152.1	153.9	154.7	156.1	157.8	159.5
170°	148.2	148.5	149.1	149.7	150.6	152.1	153.3	153.9	154.9	156.1	157.6
172.5°	149.0	149.2	149.8	150.2	150.6	151.9	152.9	153.0	153.4	154.4	155.4
175°	150.0	150.3	150.6	150.6	150.6	151.5	152.1	151.9	151.9	152.1	153.1
177.5°	150.7	150.7	150.9	150.7	150.7	151.2	151.4	150.9	150.9	151.2	151.4
180°	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	831.6	831.6	836.0	835.7	838.6	837.6	838.1
5°	893.9	899.4	904.3	907.6	912.5	913.9	913.2
7.5°	958.6	970.9	976.9	985.2	986.6	990.9	990.5
10°	998.5	1010.6	1019.8	1027.0	1030.6	1035.2	1035.5
12.5°	1029.9	1040.2	1048.4	1055.0	1059.4	1060.8	1061.7
15°	1054.5	1065.9	1075.4	1084.9	1090.5	1094.7	1097.0
17.5°	1079.2	1096.8	1113.6	1126.5	1134.2	1140.7	1140.7
20°	1098.3	1118.6	1139.5	1154.3	1169.2	1175.8	1176.8
22.5°	1118.7	1149.7	1176.6	1199.5	1219.3	1226.1	1228.6
25°	1161.1	1201.6	1243.2	1275.2	1298.1	1311.6	1313.5
27.5°	1212.3	1267.2	1310.9	1340.5	1359.5	1369.4	1371.6
30°	1248.4	1299.1	1338.3	1360.6	1369.4	1370.7	1365.8
32.5°	1264.6	1302.5	1318.2	1316.9	1299.6	1288.1	1283.7
35°	1244.8	1237.0	1198.7	1152.9	1117.9	1095.7	1089.8
37.5°	1132.8	1065.1	994.7	925.6	888.7	870.0	837.8
40°	1022.4	925.9	852.6	794.4	752.9	719.5	711.7
42.5°	897.9	798.2	725.0	675.1	642.0	619.1	609.2
45°	721.5	635.8	575.3	537.0	511.5	494.8	487.3
47.5°	577.0	510.7	466.7	438.3	418.9	404.4	400.4
50°	497.8	444.8	407.5	383.7	368.9	357.8	353.3
52.5°	432.4	389.6	360.9	341.3	327.4	320.4	316.6
55°	356.8	319.9	299.3	283.5	275.7	270.2	267.5
57.5°	291.8	265.1	250.0	239.2	232.0	228.4	227.1
60°	255.5	234.5	220.8	212.2	207.3	202.8	201.5
62.5°	223.3	206.8	196.1	188.7	183.8	181.8	181.1
65°	179.9	169.1	161.3	156.7	152.7	152.1	151.8
67.5°	143.0	136.6	132.5	127.8	126.4	124.1	123.6
70°	122.3	118.0	113.1	111.5	109.9	107.6	108.0
72.5°	103.8	99.5	96.2	94.0	93.4	92.5	93.2
75°	75.9	74.6	73.3	71.6	70.9	70.9	70.7
77.5°	54.2	53.0	51.6	50.6	50.5	49.1	49.6
80°	39.3	37.6	36.9	37.3	36.3	36.0	36.0
82.5°	29.0	28.4	27.8	27.9	27.6	27.4	27.6
85°	16.0	15.7	15.7	15.4	15.4	15.1	15.1
87.5°	6.9	7.2	6.8	6.5	6.5	6.9	7.1
90°	5.8	6.1	6.7	6.7	6.7	7.0	7.0
92.5°	39.1	29.4	25.0	21.1	20.3	19.9	19.4
95°	172.5	135.1	109.5	87.9	78.8	76.4	71.5
97.5°	293.4	256.9	221.4	202.6	185.5	176.8	172.8
100°	359.4	328.0	296.4	275.3	253.5	242.2	237.4
102.5°	399.8	384.8	363.3	340.9	325.3	313.1	309.4
105°	422.7	436.0	432.7	422.9	412.9	406.8	403.2
107.5°	402.3	436.6	452.5	457.4	457.4	455.4	453.0
110°	379.2	422.1	447.9	461.6	467.4	469.5	469.5



TEST NUMBER: P333522-935

CATALOG NUMBER: S125RDIP-S610D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	356.3	399.7	430.2	450.1	460.1	465.4	467.6
115°	323.5	365.2	398.3	422.1	436.6	445.1	449.1
117.5°	300.7	336.7	367.1	390.8	406.0	414.4	416.8
120°	287.8	321.3	348.1	370.7	385.2	393.5	395.9
122.5°	278.6	308.4	333.5	353.6	367.0	375.2	377.4
125°	266.2	292.7	314.6	331.7	344.1	350.9	353.9
127.5°	254.4	279.1	299.6	315.1	326.1	332.4	333.8
130°	246.2	269.9	289.7	304.9	315.0	321.1	322.9
132.5°	238.4	259.9	279.0	294.2	304.2	309.8	311.9
135°	226.4	245.9	263.2	276.6	286.6	292.1	293.9
137.5°	215.7	231.9	246.6	258.6	267.7	272.8	274.7
140°	209.3	223.3	236.1	247.4	255.3	259.8	261.4
142.5°	204.0	216.0	227.1	236.7	243.4	247.7	249.0
145°	197.2	206.6	214.8	222.1	227.3	230.7	231.9
147.5°	191.5	198.8	205.0	210.8	214.9	216.8	217.4
150°	188.4	194.2	199.6	204.1	207.8	209.1	209.3
152.5°	185.2	190.5	194.8	198.5	201.5	202.7	203.0
155°	180.5	184.7	188.0	191.1	193.2	194.2	194.4
157.5°	175.9	179.3	181.8	184.3	186.0	186.8	186.8
160°	172.5	175.6	177.7	179.9	181.3	181.9	181.7
162.5°	169.6	172.2	174.1	175.7	176.9	177.1	177.0
165°	165.2	167.0	168.6	169.8	170.4	170.4	170.4
167.5°	161.0	162.4	163.5	164.1	164.6	164.4	164.3
170°	158.5	159.5	160.1	160.7	161.0	161.0	160.7
172.5°	156.4	157.0	157.4	157.5	158.1	157.6	157.2
175°	153.1	153.7	153.7	153.7	153.9	153.3	153.1
177.5°	151.6	151.6	151.6	151.4	151.6	150.9	150.9
180°	150.9	150.9	150.9	150.9	150.9	150.9	150.9

(END OF REPORT)