

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333529-935

Luminaire Tested: **S125RDIP-S610D590U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333529-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D590U935-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4082.6 lumens  
Efficiency: N/A  
Efficacy: 124.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333529-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333529-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	83	81	73	71	69	61	60	58	50	49	48	43
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36
3	82	72	65	59	75	67	61	56	57	52	49	48	44	42	39	37	35	31
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	33	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	20
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	27	23	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5594	5594	5594
5°	5607	5543	5577
10°	5564	5491	5491
15°	5498	5380	5336
20°	5413	5225	5161
25°	5315	5072	4960
30°	5190	4894	4737
35°	5065	4709	4487
40°	4947	4517	4242
45°	4804	4302	3974
50°	4660	4068	3693
55°	4494	3845	3396
60°	4326	3574	3077
65°	4129	3260	2709
70°	3903	2866	2334
75°	3593	2415	1941
80°	3165	1901	1629
85°	2668	1549	1452



TEST NUMBER: P333529-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.4	2.0
10°-20°	227.6	5.6
20°-30°	330.1	8.1
30°-40°	376.2	9.2
40°-50°	366.7	9.0
50°-60°	308.6	7.6
60°-70°	216.4	5.3
70°-80°	111.2	2.7
80°-90°	29.5	0.7
90°-100°	24.1	0.6
100°-110°	148.4	3.6
110°-120°	269.2	6.6
120°-130°	345.5	8.5
130°-140°	371.6	9.1
140°-150°	348.8	8.5
150°-160°	282.1	6.9
160°-170°	182.5	4.5
170°-180°	62.9	1.5
0°-30°	639.1	15.7
0°-40°	1015.3	24.9
0°-60°	1690.5	41.4
0°-90°	2047.6	50.2
90°-120°	441.7	10.8
90°-150°	1507.5	36.9
90°-180°	2035.0	49.8
0°-180°	4082.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	865	862	855	861	860	82
15°	822	818	805	804	798	232
25°	746	735	712	703	696	343
35°	642	626	597	579	569	402
45°	526	506	471	446	435	406
55°	399	377	342	313	302	357
65°	270	247	213	188	177	268
75°	144	124	97	83	78	152
85°	36	25	21	20	20	40
90°	0	4	8	10	12	3
95°	28	26	8	10	10	36
105°	144	146	146	146	146	153
115°	271	274	274	272	269	269
125°	386	389	389	387	386	344
135°	481	484	483	482	479	371
145°	558	558	558	559	556	349
155°	614	611	612	613	610	283
165°	648	645	646	648	644	183
175°	663	660	660	664	660	63
180°	663	663	663	663	663	



TEST NUMBER: P333529-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2
2.5°	867.7	867.4	867.0	866.7	866.3	865.6	864.4	863.2	862.0	860.9	862.0
5°	864.8	864.3	863.7	863.1	862.5	861.4	859.8	858.2	856.6	855.0	856.4
7.5°	856.4	855.7	855.2	854.6	854.1	852.9	850.9	849.0	847.1	845.2	846.2
10°	848.4	848.0	847.6	847.1	846.7	845.5	843.4	841.5	839.4	837.3	837.8
12.5°	839.6	839.0	838.4	837.9	837.3	835.7	833.0	830.3	827.5	824.8	825.1
15°	822.3	821.4	820.5	819.7	818.8	816.8	813.8	810.7	807.7	804.6	804.5
17.5°	802.8	801.5	800.1	798.8	797.5	794.9	791.0	787.2	783.3	779.5	778.8
20°	787.6	786.2	784.7	783.3	781.8	778.8	774.1	769.5	764.8	760.2	759.4
22.5°	770.9	769.4	768.0	766.5	765.1	761.9	757.0	752.2	747.3	742.4	741.0
25°	745.8	743.6	741.4	739.3	737.0	733.2	727.9	722.5	717.1	711.7	709.9
27.5°	717.0	714.4	711.7	709.0	706.4	702.2	696.5	690.7	684.9	679.2	676.5
30°	696.0	693.3	690.5	687.8	685.0	680.5	674.4	668.4	662.3	656.2	652.8
32.5°	675.6	672.4	669.2	666.0	662.7	658.0	651.8	645.6	639.3	633.1	629.4
35°	642.4	638.9	635.4	632.0	628.4	623.5	616.9	610.4	603.8	597.3	593.1
37.5°	609.8	605.5	601.3	597.1	592.9	587.4	580.6	573.9	567.1	560.3	555.3
40°	586.8	582.5	578.1	573.7	569.4	563.7	556.7	549.7	542.8	535.8	530.3
42.5°	562.7	558.3	553.8	549.3	544.8	539.0	531.8	524.5	517.4	510.1	504.8
45°	526.0	521.8	517.5	513.3	509.1	503.0	495.0	487.0	479.0	471.0	465.2
47.5°	487.9	483.5	479.0	474.6	470.1	463.8	455.8	447.7	439.7	431.6	425.7
50°	463.8	459.0	454.2	449.4	444.6	438.1	429.8	421.5	413.2	404.9	398.8
52.5°	437.6	432.7	427.8	422.9	418.0	411.6	403.8	396.0	388.1	380.3	373.8
55°	399.1	394.4	389.8	385.1	380.5	374.0	365.9	357.7	349.7	341.5	334.9
57.5°	360.1	355.1	350.1	345.2	340.2	333.7	325.9	318.1	310.2	302.4	295.9
60°	334.9	329.8	324.8	319.7	314.6	308.2	300.2	292.4	284.6	276.7	270.4
62.5°	308.2	303.4	298.5	293.7	288.9	282.4	274.5	266.5	258.6	250.6	244.6
65°	270.2	265.3	260.3	255.4	250.4	244.1	236.3	228.7	220.9	213.3	207.4
67.5°	232.4	227.4	222.5	217.6	212.6	206.5	199.1	191.7	184.3	176.8	171.6
70°	206.7	201.8	196.8	191.9	186.9	180.8	173.6	166.3	159.0	151.8	147.2
72.5°	181.6	176.8	171.9	167.1	162.3	156.4	149.6	142.8	136.0	129.2	125.1
75°	144.0	139.6	135.2	130.9	126.5	121.2	115.1	109.0	102.9	96.8	93.6
77.5°	106.5	103.0	99.5	96.0	92.6	88.3	83.4	78.6	73.7	68.8	66.6
80°	85.1	81.5	78.1	74.6	71.1	67.3	63.2	59.2	55.1	51.1	49.7
82.5°	64.1	61.0	57.9	54.7	51.6	48.6	45.8	43.0	40.2	37.5	36.9
85°	36.0	33.3	30.7	28.2	25.5	23.8	23.1	22.4	21.7	20.9	20.8
87.5°	12.1	11.5	10.8	10.2	9.6	9.3	9.3	9.4	9.4	9.4	9.6
90°	0.5	1.4	2.2	3.1	4.0	4.8	5.6	6.4	7.1	7.8	8.4
92.5°	7.6	7.0	6.4	5.8	5.1	5.2	5.9	6.5	7.1	7.8	8.4
95°	28.0	27.6	27.4	27.0	26.7	24.5	20.3	16.2	12.0	7.8	8.4
97.5°	58.5	59.1	59.7	60.2	60.8	57.0	48.8	40.6	32.4	24.2	21.1
100°	82.1	82.4	82.7	83.0	83.3	83.7	84.2	84.6	85.1	85.5	69.2
102.5°	106.0	106.4	106.9	107.3	107.6	108.0	108.2	108.6	108.8	109.1	106.0
105°	144.4	144.8	145.3	145.8	146.2	146.4	146.4	146.4	146.4	146.4	146.4
107.5°	184.3	184.3	184.3	184.3	184.3	184.4	184.6	184.9	185.1	185.3	185.3
110°	210.3	210.3	210.3	210.3	210.3	210.3	210.6	210.8	211.0	211.2	210.9



TEST NUMBER: P333529-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	234.6	234.9	235.1	235.4	235.7	235.8	236.0	236.1	236.3	236.3	236.0
115°	271.1	271.7	272.2	272.8	273.4	273.7	273.8	273.9	274.0	274.1	273.7
117.5°	309.0	308.9	308.9	308.9	308.9	309.1	309.5	310.0	310.3	310.7	310.2
120°	332.6	332.4	332.3	332.3	332.1	332.3	332.6	332.9	333.2	333.6	333.3
122.5°	353.4	353.8	354.2	354.6	355.1	355.3	355.5	355.7	355.8	355.9	355.8
125°	385.6	386.4	387.1	387.9	388.7	389.1	389.1	389.1	389.1	389.1	388.7
127.5°	416.4	416.9	417.5	418.0	418.5	418.8	418.7	418.7	418.6	418.5	418.3
130°	435.2	435.8	436.4	436.9	437.4	437.7	437.8	438.0	438.1	438.2	437.8
132.5°	454.1	454.7	455.4	456.0	456.6	456.8	456.6	456.3	456.1	455.9	455.8
135°	481.0	481.6	482.2	482.8	483.5	483.8	483.5	483.3	483.1	482.8	482.7
137.5°	505.6	506.2	506.7	507.3	507.8	508.1	507.8	507.6	507.5	507.2	507.3
140°	521.7	521.9	522.1	522.4	522.5	522.6	522.5	522.4	522.3	522.2	522.4
142.5°	536.2	536.4	536.5	536.7	536.7	536.9	537.1	537.2	537.4	537.5	537.5
145°	557.6	557.8	558.0	558.2	558.4	558.5	558.5	558.5	558.5	558.5	558.6
147.5°	576.2	576.2	576.1	576.1	576.0	576.1	576.2	576.4	576.4	576.6	576.8
150°	588.0	587.8	587.5	587.4	587.1	587.1	587.4	587.5	587.8	588.0	588.2
152.5°	599.4	598.9	598.5	598.0	597.4	597.4	597.5	597.8	598.0	598.2	598.5
155°	614.1	613.4	612.8	612.1	611.4	611.2	611.4	611.7	611.8	612.1	612.4
157.5°	625.3	624.9	624.6	624.1	623.8	623.6	623.6	623.6	623.6	623.7	624.1
160°	633.2	632.6	631.9	631.2	630.6	630.3	630.4	630.5	630.6	630.8	631.2
162.5°	639.5	638.9	638.2	637.5	636.9	636.6	636.7	636.8	636.9	637.1	637.7
165°	647.9	647.3	646.6	646.0	645.3	645.1	645.1	645.2	645.4	645.5	646.1
167.5°	654.2	653.6	652.9	652.2	651.5	651.3	651.3	651.4	651.5	651.7	652.5
170°	657.8	657.0	656.3	655.5	654.7	654.4	654.4	654.6	654.7	654.8	655.7
172.5°	660.1	659.4	658.6	657.8	657.0	656.8	656.9	657.2	657.4	657.5	658.3
175°	662.7	662.0	661.3	660.7	660.0	659.8	659.9	660.0	660.1	660.2	661.1
177.5°	663.8	663.3	662.8	662.3	661.8	661.5	661.6	661.7	661.8	661.9	662.5
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7



TEST NUMBER: P333529-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2
2.5°	863.2	864.4	865.6	866.1	866.0	865.8	865.7	865.6
5°	857.9	859.4	860.8	861.4	861.1	860.8	860.6	860.2
7.5°	847.2	848.3	849.3	849.6	849.3	848.9	848.7	848.3
10°	838.2	838.6	839.1	839.1	838.6	838.2	837.8	837.3
12.5°	825.4	825.8	826.0	825.9	825.2	824.6	823.9	823.2
15°	804.3	804.2	804.1	803.3	802.0	800.7	799.4	798.1
17.5°	778.1	777.3	776.6	775.7	774.6	773.5	772.5	771.4
20°	758.7	757.9	757.2	756.2	754.9	753.6	752.3	751.0
22.5°	739.5	738.0	736.7	735.4	734.3	733.2	732.2	731.1
25°	708.0	706.1	704.2	702.4	700.9	699.2	697.7	696.0
27.5°	673.9	671.2	668.6	666.5	665.0	663.4	661.9	660.3
30°	649.5	646.1	642.7	640.4	639.1	637.8	636.5	635.2
32.5°	625.7	622.1	618.4	615.7	614.0	612.3	610.7	609.1
35°	588.8	584.6	580.4	577.3	575.2	573.2	571.2	569.1
37.5°	550.3	545.2	540.1	536.6	534.6	532.7	530.7	528.7
40°	524.7	519.2	513.7	510.1	508.3	506.5	504.8	503.1
42.5°	499.6	494.2	489.0	485.0	482.5	479.9	477.3	474.8
45°	459.3	453.6	447.7	443.8	441.6	439.4	437.2	435.1
47.5°	419.7	413.6	407.7	403.5	401.1	398.6	396.2	393.8
50°	392.7	386.6	380.5	376.3	374.2	372.0	369.8	367.6
52.5°	367.2	360.6	354.0	349.7	347.5	345.3	343.1	341.0
55°	328.4	321.8	315.3	310.9	308.6	306.3	303.9	301.6
57.5°	289.6	283.2	276.8	272.5	270.4	268.4	266.4	264.3
60°	263.9	257.5	251.2	246.8	244.7	242.5	240.3	238.2
62.5°	238.7	232.7	226.8	222.7	220.6	218.4	216.2	214.0
65°	201.6	195.8	190.0	186.0	183.8	181.7	179.4	177.3
67.5°	166.3	160.9	155.6	152.1	150.3	148.6	146.8	145.1
70°	142.8	138.3	133.7	130.6	128.9	127.2	125.4	123.6
72.5°	121.0	116.8	112.6	109.9	108.8	107.6	106.5	105.3
75°	90.4	87.2	84.0	81.9	80.9	79.9	78.9	77.8
77.5°	64.3	62.1	59.8	58.4	57.6	56.8	56.1	55.4
80°	48.4	47.1	45.8	45.0	44.7	44.4	44.1	43.8
82.5°	36.2	35.6	35.0	34.6	34.4	34.3	34.1	33.9
85°	20.7	20.5	20.3	20.2	20.1	19.9	19.8	19.6
87.5°	9.6	9.7	9.9	9.9	9.8	9.8	9.7	9.6
90°	9.0	9.5	10.1	10.5	10.8	11.1	11.5	11.8
92.5°	9.0	9.5	10.1	10.4	10.5	10.7	10.8	11.0
95°	9.0	9.5	10.1	10.3	10.3	10.3	10.3	10.3
97.5°	18.0	14.9	11.9	10.3	10.3	10.3	10.3	10.3
100°	53.0	36.7	20.4	12.1	11.6	11.2	10.8	10.3
102.5°	102.9	99.8	96.8	91.5	84.0	76.6	69.2	61.8
105°	146.4	146.4	146.4	146.4	146.2	146.1	146.0	145.9
107.5°	185.4	185.4	185.4	185.2	184.9	184.6	184.3	183.9
110°	210.6	210.3	209.9	209.8	209.9	210.0	210.2	210.3





TEST NUMBER: P333529-935

CATALOG NUMBER: S125RDIP-S610D590U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.6	235.1	234.7	234.5	234.3	234.1	234.0	233.8
115°	273.2	272.8	272.3	271.8	271.1	270.5	269.8	269.2
117.5°	309.6	309.0	308.5	308.1	307.8	307.5	307.2	306.9
120°	333.1	332.9	332.7	332.3	331.7	331.2	330.6	330.1
122.5°	355.5	355.3	355.1	354.6	354.0	353.4	352.8	352.1
125°	388.2	387.7	387.3	386.9	386.6	386.2	386.0	385.6
127.5°	418.0	417.8	417.6	417.1	416.2	415.4	414.7	413.8
130°	437.6	437.2	436.9	436.4	435.9	435.3	434.8	434.3
132.5°	455.7	455.6	455.6	455.3	454.8	454.2	453.7	453.1
135°	482.4	482.2	482.0	481.6	481.0	480.3	479.6	479.0
137.5°	507.3	507.4	507.4	507.1	506.6	506.0	505.5	504.9
140°	522.6	522.8	523.1	522.8	522.2	521.5	520.9	520.2
142.5°	537.6	537.6	537.7	537.4	536.7	536.1	535.4	534.8
145°	558.8	558.9	559.0	558.7	558.0	557.4	556.7	556.0
147.5°	576.9	577.0	577.1	576.8	576.0	575.2	574.5	573.7
150°	588.4	588.7	588.8	588.6	587.7	586.8	585.9	585.0
152.5°	598.7	598.9	599.1	598.8	598.1	597.3	596.4	595.6
155°	612.8	613.0	613.4	613.1	612.3	611.4	610.5	609.6
157.5°	624.4	624.7	625.1	624.8	624.0	623.0	622.2	621.3
160°	631.6	632.1	632.5	632.2	631.4	630.5	629.6	628.8
162.5°	638.3	638.9	639.5	639.3	638.3	637.4	636.5	635.4
165°	646.8	647.5	648.1	648.0	647.1	646.3	645.4	644.5
167.5°	653.2	654.0	654.8	654.7	653.8	652.7	651.8	650.7
170°	656.6	657.5	658.3	658.2	657.3	656.3	655.3	654.4
172.5°	659.1	660.0	660.7	660.6	659.6	658.7	657.6	656.7
175°	661.9	662.8	663.7	663.7	662.7	661.7	660.7	659.7
177.5°	663.1	663.7	664.3	664.3	663.6	662.9	662.2	661.5
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7

(END OF REPORT)