

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333534-935

Luminaire Tested: **S125RDIP-S610D810U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333534-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D810U935-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4570.1 lumens  
Efficiency: N/A  
Efficacy: 119.0 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	39	38	33				
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	28				
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	30	28	25				
5	68	57	49	43	62	53	46	41	45	39	35	37	33	30	30	27	25	22				
6	63	51	43	38	58	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15				
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	17	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5146	5146	5146	5146
5°	5920	5153	4550	5153
10°	6791	5126	4015	5126
15°	7335	5073	3569	5073
20°	8088	5013	3296	5013
25°	9360	4932	3058	4932
30°	10185	4847	2902	4847
35°	8592	4747	2759	4747
40°	6000	4569	2636	4569
45°	4451	4328	2515	4328
50°	3550	4078	2411	4078
55°	3012	3768	2320	3768
60°	2603	3490	2173	3490
65°	2320	3189	1869	3189
70°	2039	2921	1703	2921
75°	1764	2530	1599	2530
80°	1339	2131	1339	2131
85°	1119	1675	1260	1675



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.4	1.7
10°-20°	223.9	4.9
20°-30°	355.0	7.8
30°-40°	428.1	9.4
40°-50°	382.3	8.4
50°-60°	293.2	6.4
60°-70°	190.5	4.2
70°-80°	92.6	2.0
80°-90°	24.0	0.5
90°-100°	242.0	5.3
100°-110°	520.3	11.4
110°-120°	488.3	10.7
120°-130°	395.7	8.7
130°-140°	317.6	6.9
140°-150°	239.7	5.2
150°-160°	168.7	3.7
160°-170°	99.4	2.2
170°-180°	32.3	0.7
0°-30°	655.3	14.3
0°-40°	1083.4	23.7
0°-60°	1758.9	38.5
0°-90°	2066.1	45.2
90°-120°	1250.6	27.4
90°-150°	2203.6	48.2
90°-180°	2504.0	54.8
0°-180°	4570.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	797	797	797	797	797	
5°	913	795	702	795	913	91
15°	1097	759	534	759	1097	314
25°	1314	692	429	692	1314	603
35°	1090	602	350	602	1090	658
45°	487	474	275	474	487	389
55°	268	335	206	335	268	243
65°	152	209	122	209	152	151
75°	71	101	64	101	71	75
85°	15	23	17	23	15	18
90°	16	1	16	1	16	11
95°	158	22	158	22	158	224
105°	892	76	892	76	892	887
115°	994	136	994	136	994	971
125°	783	188	783	188	783	708
135°	650	221	650	221	650	504
145°	513	257	513	257	513	326
155°	430	294	430	294	430	201
165°	377	320	377	320	377	108
175°	339	333	339	333	339	33
180°	334	334	334	334	334	



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	838.1	837.6	838.6	835.7	836.0	831.6	831.6	828.1	823.7	820.3	818.7
5°	913.2	913.9	912.5	907.6	904.3	899.4	893.9	884.1	875.9	868.1	861.9
7.5°	990.5	990.9	986.6	985.2	976.9	970.9	958.6	945.2	933.3	918.3	906.8
10°	1035.5	1035.2	1030.6	1027.0	1019.8	1010.6	998.5	982.8	968.1	951.7	936.1
12.5°	1061.7	1060.8	1059.4	1055.0	1048.4	1040.2	1029.9	1014.5	996.3	978.4	960.2
15°	1097.0	1094.7	1090.5	1084.9	1075.4	1065.9	1054.5	1040.8	1023.4	1003.2	986.1
17.5°	1140.7	1140.7	1134.2	1126.5	1113.6	1096.8	1079.2	1057.0	1033.5	1011.2	993.1
20°	1176.8	1175.8	1169.2	1154.3	1139.5	1118.6	1098.3	1071.2	1042.4	1013.2	990.7
22.5°	1228.6	1226.1	1219.3	1199.5	1176.6	1149.7	1118.7	1085.5	1050.8	1017.7	988.1
25°	1313.5	1311.6	1298.1	1275.2	1243.2	1201.6	1161.1	1115.6	1065.6	1022.1	986.1
27.5°	1371.6	1369.4	1359.5	1340.5	1310.9	1267.2	1212.3	1151.6	1089.1	1029.2	977.3
30°	1365.8	1370.7	1369.4	1360.6	1338.3	1299.1	1248.4	1180.1	1105.8	1035.5	973.7
32.5°	1283.7	1288.1	1299.6	1316.9	1318.2	1302.5	1264.6	1201.5	1124.6	1044.7	970.8
35°	1089.8	1095.7	1117.9	1152.9	1198.7	1237.0	1244.8	1210.8	1141.8	1055.8	966.5
37.5°	837.8	870.0	888.7	925.6	994.7	1065.1	1132.8	1157.8	1128.4	1051.2	959.5
40°	711.7	719.5	752.9	794.4	852.6	925.9	1022.4	1092.1	1094.3	1040.8	948.5
42.5°	609.2	619.1	642.0	675.1	725.0	798.2	897.9	989.8	1032.3	1011.9	934.1
45°	487.3	494.8	511.5	537.0	575.3	635.8	721.5	827.9	912.2	945.2	895.5
47.5°	400.4	404.4	418.9	438.3	466.7	510.7	577.0	669.3	770.6	841.5	834.6
50°	353.3	357.8	368.9	383.7	407.5	444.8	497.8	574.6	679.0	765.7	783.0
52.5°	316.6	320.4	327.4	341.3	360.9	389.6	432.4	502.0	595.8	687.9	728.1
55°	267.5	270.2	275.7	283.5	299.3	319.9	356.8	404.9	480.8	573.7	632.6
57.5°	227.1	228.4	232.0	239.2	250.0	265.1	291.8	332.6	387.0	470.6	535.6
60°	201.5	202.8	207.3	212.2	220.8	234.5	255.5	283.9	336.2	405.3	471.0
62.5°	181.1	181.8	183.8	188.7	196.1	206.8	223.3	246.5	288.1	348.7	410.8
65°	151.8	152.1	152.7	156.7	161.3	169.1	179.9	196.2	227.6	273.5	328.4
67.5°	123.6	124.1	126.4	127.8	132.5	136.6	143.0	155.5	177.6	208.4	251.2
70°	108.0	107.6	109.9	111.5	113.1	118.0	122.3	132.4	146.2	169.8	205.4
72.5°	93.2	92.5	93.4	94.0	96.2	99.5	103.8	109.9	120.5	136.8	164.0
75°	70.7	70.9	70.9	71.6	73.3	74.6	75.9	79.1	85.1	95.8	110.6
77.5°	49.6	49.1	50.5	50.6	51.6	53.0	54.2	55.4	57.9	62.3	69.9
80°	36.0	36.0	36.3	37.3	36.9	37.6	39.3	40.6	43.5	46.1	48.7
82.5°	27.6	27.4	27.6	27.9	27.8	28.4	29.0	29.3	30.4	31.7	33.6
85°	15.1	15.1	15.4	15.4	15.7	15.7	16.0	16.0	16.0	16.4	16.7
87.5°	8.9	8.6	8.2	8.2	8.4	8.7	8.4	7.9	7.7	7.7	7.7
90°	15.5	15.5	14.8	14.8	14.8	13.4	12.8	12.1	11.5	10.8	9.4
92.5°	43.0	44.0	44.9	46.6	55.2	65.2	86.6	119.3	175.7	217.1	220.5
95°	158.2	169.0	174.4	194.6	242.4	298.9	381.7	484.1	583.7	596.5	486.7
97.5°	382.4	391.0	410.5	448.2	489.8	568.4	649.1	720.9	738.5	637.0	434.6
100°	525.1	535.9	560.8	609.2	655.7	725.7	795.0	828.0	776.2	608.0	387.8
102.5°	684.5	692.6	719.6	754.1	803.8	851.2	884.5	864.1	753.6	556.7	352.2
105°	892.0	900.1	913.5	935.7	957.3	964.8	935.1	842.8	681.3	488.1	317.8
107.5°	1002.1	1007.5	1011.9	1012.1	1001.2	966.0	890.0	766.9	607.5	440.8	303.2
110°	1038.8	1038.8	1034.1	1021.2	990.9	933.8	838.8	710.9	565.5	418.7	298.9



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1034.5	1029.6	1017.9	995.9	951.7	884.2	788.2	666.8	534.3	405.8	298.9
115°	993.7	984.9	966.0	933.8	881.2	807.9	715.7	611.3	500.2	391.8	300.9
117.5°	922.1	916.8	898.0	864.7	812.2	744.9	665.4	575.5	479.8	385.0	305.4
120°	875.8	870.5	852.3	819.9	770.2	710.9	636.9	556.0	468.6	381.7	309.7
122.5°	834.9	830.1	811.9	782.3	737.9	682.3	616.4	541.6	458.8	379.0	313.4
125°	782.9	776.2	761.4	733.8	696.1	647.6	589.1	520.4	445.7	375.7	319.8
127.5°	738.5	735.6	721.5	697.2	663.0	617.6	562.9	498.9	433.5	374.0	326.9
130°	714.3	710.2	696.8	674.6	640.9	597.1	544.7	485.3	425.5	373.0	331.2
132.5°	690.0	685.4	673.0	650.8	617.2	575.1	527.4	471.9	419.0	373.0	336.0
135°	650.3	646.3	634.1	611.9	582.3	544.0	500.8	454.4	411.3	373.0	342.7
137.5°	608.0	603.5	592.3	572.1	545.5	513.0	477.2	439.6	404.5	373.8	348.7
140°	578.2	574.9	564.8	547.3	522.4	494.1	463.1	431.5	401.2	374.3	351.4
142.5°	550.8	548.0	538.5	523.7	502.5	477.9	451.3	424.6	398.6	374.9	353.0
145°	513.0	510.3	502.9	491.5	475.3	457.1	436.3	415.3	394.5	374.3	354.8
147.5°	481.0	479.7	475.4	466.2	453.5	439.7	423.7	406.7	390.3	372.6	355.4
150°	463.1	462.5	459.8	451.8	441.6	429.5	416.7	401.9	387.1	370.9	355.4
152.5°	449.2	448.5	445.8	439.4	430.8	421.5	409.7	396.5	383.3	368.8	354.9
155°	430.2	429.5	427.5	422.8	416.0	408.6	399.2	388.5	377.0	364.9	353.4
157.5°	413.2	413.4	411.5	407.6	402.3	396.5	389.3	380.4	371.1	360.8	351.7
160°	401.9	402.6	401.2	397.9	393.1	388.5	381.7	375.0	366.3	358.2	350.1
162.5°	391.7	391.8	391.5	388.7	385.0	380.9	375.2	369.0	361.9	354.9	348.4
165°	377.0	377.0	377.0	375.7	373.0	369.6	365.6	360.8	355.4	350.1	346.0
167.5°	363.5	363.7	364.2	363.0	361.6	359.2	356.1	353.0	349.1	345.3	342.2
170°	355.4	356.1	356.1	355.4	354.1	352.8	350.8	348.7	345.3	342.7	340.6
172.5°	347.9	348.6	349.7	348.4	348.2	347.4	345.9	343.9	341.6	339.4	338.5
175°	338.6	339.3	340.6	340.0	340.0	340.0	338.6	338.6	336.6	336.0	336.0
177.5°	333.9	333.9	335.5	335.0	335.5	335.5	335.5	335.0	334.4	333.9	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	818.7	816.9	813.5	810.4	806.4	803.1	800.6	797.8	794.1	789.7	786.0
5°	855.0	847.7	838.3	830.1	819.7	811.5	803.0	794.8	786.6	776.1	767.0
7.5°	895.1	880.3	865.8	847.7	831.1	816.4	802.3	788.0	774.0	759.1	744.8
10°	919.7	901.7	881.8	858.8	837.9	818.0	799.7	781.7	762.8	746.1	728.1
12.5°	942.7	919.5	896.7	867.8	842.7	818.3	795.0	772.6	752.3	730.6	711.3
15°	963.5	940.6	915.2	879.9	844.8	815.4	787.9	758.8	733.7	709.4	687.9
17.5°	971.6	947.6	917.9	884.0	845.8	808.7	773.4	741.4	711.8	683.5	659.3
20°	968.5	945.2	914.8	882.4	841.5	803.0	764.7	729.4	696.3	666.6	640.8
22.5°	960.9	936.9	907.5	873.3	834.5	793.5	752.7	715.0	680.4	649.5	621.4
25°	949.5	916.8	886.7	853.3	816.4	775.8	733.7	692.1	655.1	623.7	593.0
27.5°	937.6	896.8	858.6	825.4	786.4	750.2	709.5	666.9	628.0	596.1	564.6
30°	927.0	881.1	839.0	801.3	764.4	730.0	691.4	649.9	610.0	577.0	544.9
32.5°	913.6	864.9	818.6	775.2	739.5	705.4	670.5	630.8	591.9	557.8	525.3
35°	896.8	834.7	784.3	738.2	698.6	665.6	634.2	602.1	563.2	527.9	496.2
37.5°	874.9	804.3	746.1	695.8	654.1	620.9	596.2	566.8	531.3	497.5	468.0
40°	861.5	782.4	718.6	668.8	625.0	590.0	566.8	541.9	509.5	477.9	448.4
42.5°	843.7	762.2	690.9	639.0	595.0	561.3	537.8	516.1	488.9	459.0	427.5
45°	808.8	723.2	648.2	592.6	548.2	515.1	493.2	473.9	453.3	425.9	398.4
47.5°	763.4	682.4	604.0	543.3	499.7	469.1	447.8	432.6	417.8	394.5	367.8
50°	727.1	648.9	572.4	513.5	467.1	437.9	418.0	405.9	392.4	371.3	349.0
52.5°	684.2	614.4	539.4	479.2	435.4	408.1	388.9	376.9	365.8	348.4	327.3
55°	616.6	555.3	486.6	432.0	391.8	364.4	346.0	334.6	328.0	313.3	296.6
57.5°	538.5	494.6	434.1	381.4	345.9	318.7	305.3	295.6	288.2	277.8	266.0
60°	484.1	453.3	399.0	349.0	316.2	290.4	278.4	270.2	263.3	254.4	245.3
62.5°	428.9	406.5	359.3	316.2	286.2	264.5	253.2	245.8	237.9	232.0	223.1
65°	354.9	334.9	302.2	268.5	240.7	223.4	215.2	208.7	203.8	197.3	191.0
67.5°	276.0	267.9	245.4	222.1	202.2	186.8	179.7	175.1	169.2	165.3	161.0
70°	227.6	223.7	207.7	192.3	173.7	163.2	156.7	154.7	147.5	143.6	140.6
72.5°	184.8	182.9	173.7	163.0	149.9	140.7	134.7	132.4	127.9	124.8	122.9
75°	126.6	127.3	125.6	118.7	113.8	108.0	102.7	101.4	98.2	95.5	93.8
77.5°	80.1	83.4	83.5	83.2	81.3	77.7	75.5	74.5	71.3	70.3	69.9
80°	54.9	58.5	61.8	61.5	60.9	59.8	58.2	57.3	55.6	54.6	54.0
82.5°	36.6	40.0	42.7	44.5	44.3	43.4	42.3	41.8	41.5	40.7	40.6
85°	17.3	18.0	18.9	21.3	22.9	23.2	22.9	22.6	21.6	22.0	22.2
87.5°	7.7	7.5	7.7	7.3	6.8	7.8	8.4	8.5	8.1	7.8	7.6
90°	8.8	7.4	6.7	5.4	4.0	2.7	1.4	0.7	1.4	2.7	4.0
92.5°	153.6	92.0	55.2	35.6	23.9	15.6	10.0	8.2	10.0	15.6	23.9
95°	300.9	152.8	80.8	50.5	35.6	28.2	22.9	22.2	22.9	28.2	35.6
97.5°	240.2	131.6	84.0	62.2	48.9	41.5	37.7	36.9	37.7	41.5	48.9
100°	218.1	130.6	91.5	71.4	58.5	51.1	48.5	47.1	48.5	51.1	58.5
102.5°	209.0	135.4	100.7	81.0	69.3	61.4	59.2	58.5	59.2	61.4	69.3
105°	205.3	145.4	115.8	96.9	86.2	79.5	76.1	76.1	76.1	79.5	86.2
107.5°	211.5	160.2	131.6	114.6	103.4	97.9	94.6	93.3	94.6	97.9	103.4
110°	217.5	171.0	143.4	125.9	115.8	109.7	107.0	105.7	107.0	109.7	115.8





TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	225.0	181.2	154.7	137.8	127.6	121.6	119.4	118.0	119.4	121.6	127.6
115°	236.3	197.3	172.4	155.5	145.4	139.4	137.3	136.0	137.3	139.4	145.4
117.5°	249.3	213.7	190.1	173.8	162.4	156.4	154.2	152.1	154.2	156.4	162.4
120°	257.9	225.5	202.0	185.1	173.7	167.6	165.0	162.9	165.0	167.6	173.7
122.5°	267.5	236.9	213.3	196.5	183.9	177.9	175.7	174.3	175.7	177.9	183.9
125°	280.7	251.8	229.5	212.1	199.2	193.2	189.9	188.5	189.9	193.2	199.2
127.5°	292.8	266.2	244.8	227.3	213.7	206.0	201.7	199.7	201.7	206.0	213.7
130°	300.9	275.3	254.5	236.9	222.8	214.0	208.7	206.6	208.7	214.0	222.8
132.5°	307.9	284.0	263.1	245.6	230.9	221.1	214.6	212.1	214.6	221.1	230.9
135°	317.8	295.6	274.7	256.5	242.4	231.6	223.5	220.8	223.5	231.6	242.4
137.5°	325.0	303.8	284.7	266.0	252.2	241.4	233.8	231.9	233.8	241.4	252.2
140°	329.8	309.7	290.2	272.0	259.2	248.4	240.3	238.3	240.3	248.4	259.2
142.5°	332.6	313.4	295.0	277.9	265.6	254.9	247.4	245.8	247.4	254.9	265.6
145°	336.6	319.8	302.3	286.8	274.7	265.3	258.5	257.2	258.5	265.3	274.7
147.5°	339.1	323.8	308.5	294.9	284.4	275.6	269.8	269.0	269.8	275.6	284.4
150°	340.6	326.5	311.7	300.2	290.8	282.1	277.3	276.0	277.3	282.1	290.8
152.5°	341.7	329.2	315.5	305.1	296.2	288.5	284.4	283.5	284.4	288.5	296.2
155°	342.7	331.9	320.5	311.0	304.3	297.6	293.5	293.5	293.5	297.6	304.3
157.5°	343.4	334.2	324.3	317.2	311.3	305.5	302.3	302.4	302.3	305.5	311.3
160°	343.4	335.3	326.5	320.5	315.0	310.4	307.6	308.3	307.6	310.4	315.0
162.5°	342.8	336.3	328.6	323.6	319.3	315.2	312.5	313.1	312.5	315.2	319.3
165°	342.0	336.6	331.2	327.2	324.5	321.2	319.1	320.5	319.1	321.2	324.5
167.5°	340.4	336.6	332.2	329.6	327.7	325.8	324.6	325.3	324.6	325.8	327.7
170°	339.3	336.6	333.2	331.2	329.8	328.6	327.9	328.6	327.9	328.6	329.8
172.5°	338.2	336.0	333.2	332.3	331.5	330.1	329.5	330.7	329.5	330.1	331.5
175°	336.6	335.3	333.2	333.2	333.2	332.6	331.9	333.2	331.9	332.6	333.2
177.5°	335.0	334.4	333.4	333.4	333.9	333.4	333.4	334.4	333.4	333.4	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	783.4	779.7	777.1	771.9	768.2	766.6	763.8	763.0	765.9	763.8	763.5
5°	760.1	750.6	743.1	735.6	727.4	722.2	714.3	713.0	711.0	708.1	707.5
7.5°	732.2	719.8	710.2	697.7	686.9	678.2	668.4	663.7	661.2	657.4	652.3
10°	713.3	698.6	685.5	673.1	659.7	648.9	639.1	631.5	626.6	622.1	620.1
12.5°	694.7	679.8	663.1	648.0	633.0	620.9	610.0	605.1	599.7	594.3	589.8
15°	665.9	645.9	627.7	610.3	597.5	584.4	574.0	566.8	558.6	556.4	547.5
17.5°	635.3	615.7	594.3	576.0	561.3	546.8	535.4	527.2	521.0	512.6	508.5
20°	616.2	593.0	572.0	555.3	539.0	522.0	510.2	503.3	497.5	490.6	487.3
22.5°	595.8	573.1	551.6	532.1	515.5	498.7	490.3	483.2	476.6	470.2	465.9
25°	565.8	542.9	520.4	500.1	482.8	470.6	460.8	452.6	449.1	442.8	438.2
27.5°	536.2	511.9	488.4	468.2	454.6	442.6	434.6	428.2	421.6	416.2	412.2
30°	517.1	492.2	466.7	450.7	436.3	424.9	416.0	409.8	404.9	400.0	397.1
32.5°	498.0	472.3	449.7	432.4	418.8	408.9	399.8	393.8	388.7	383.2	379.8
35°	467.4	441.2	422.9	405.9	392.4	383.3	377.1	368.6	364.4	360.4	356.8
37.5°	438.9	414.6	394.8	379.9	368.2	359.1	351.1	346.5	341.3	337.8	334.8
40°	418.0	395.7	377.8	362.1	353.5	343.5	335.9	330.0	326.1	321.5	318.2
42.5°	399.2	378.5	361.0	346.9	336.3	327.7	320.5	314.6	309.6	306.3	303.6
45°	372.6	351.9	334.9	321.8	312.0	303.8	296.4	293.3	286.8	282.9	281.6
47.5°	345.0	326.6	310.1	298.1	288.0	280.3	273.2	267.3	263.6	259.8	257.7
50°	326.4	308.8	293.3	281.6	271.8	263.3	256.8	252.8	247.9	244.4	241.7
52.5°	307.8	291.4	276.1	264.8	256.3	247.9	240.6	236.6	232.0	229.6	227.8
55°	281.3	264.0	250.9	239.7	230.9	223.1	216.2	212.2	209.3	207.1	206.4
57.5°	251.2	237.5	225.3	215.2	206.1	198.7	192.7	189.0	186.4	186.1	184.1
60°	231.5	219.1	208.0	197.3	189.3	182.5	177.3	173.1	170.4	170.0	169.4
62.5°	212.0	200.0	189.7	180.2	173.1	166.5	161.6	156.8	155.2	153.6	152.1
65°	182.8	172.0	163.5	156.0	148.5	142.9	138.0	135.1	131.5	129.5	126.0
67.5°	154.2	145.9	137.7	131.4	125.4	120.2	116.1	111.8	109.3	107.7	105.1
70°	135.4	128.9	120.7	113.8	109.3	105.0	101.7	96.8	95.1	93.8	92.6
72.5°	117.6	111.8	105.0	99.4	94.9	90.8	87.0	84.8	83.2	81.8	81.0
75°	92.6	87.0	81.1	77.1	74.0	70.7	68.7	67.1	66.4	66.0	64.7
77.5°	67.9	65.0	60.3	57.2	55.0	53.7	51.9	51.1	51.1	49.6	49.2
80°	52.0	50.4	46.4	45.1	43.5	42.2	41.2	39.6	38.0	37.3	36.3
82.5°	38.7	37.0	35.5	33.3	32.0	31.2	30.2	29.6	29.8	28.9	28.4
85°	20.6	18.9	18.3	18.0	17.3	18.0	17.7	17.3	17.0	16.7	17.0
87.5°	7.6	7.9	7.7	8.5	7.9	8.4	8.6	8.4	8.6	8.7	8.7
90°	5.4	6.7	7.4	8.8	9.4	10.8	11.5	12.1	12.8	13.4	14.8
92.5°	35.6	55.2	92.0	153.6	220.5	217.1	175.7	119.3	86.6	65.2	55.2
95°	50.5	80.8	152.8	300.9	486.7	596.5	583.7	484.1	381.7	298.9	242.4
97.5°	62.2	84.0	131.6	240.2	434.6	637.0	738.5	720.9	649.1	568.4	489.8
100°	71.4	91.5	130.6	218.1	387.8	608.0	776.2	828.0	795.0	725.7	655.7
102.5°	81.0	100.7	135.4	209.0	352.2	556.7	753.6	864.1	884.5	851.2	803.8
105°	96.9	115.8	145.4	205.3	317.8	488.1	681.3	842.8	935.1	964.8	957.3
107.5°	114.6	131.6	160.2	211.5	303.2	440.8	607.5	766.9	890.0	966.0	1001.2
110°	125.9	143.4	171.0	217.5	298.9	418.7	565.5	710.9	838.8	933.8	990.9



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	137.8	154.7	181.2	225.0	298.9	405.8	534.3	666.8	788.2	884.2	951.7
115°	155.5	172.4	197.3	236.3	300.9	391.8	500.2	611.3	715.7	807.9	881.2
117.5°	173.8	190.1	213.7	249.3	305.4	385.0	479.8	575.5	665.4	744.9	812.2
120°	185.1	202.0	225.5	257.9	309.7	381.7	468.6	556.0	636.9	710.9	770.2
122.5°	196.5	213.3	236.9	267.5	313.4	379.0	458.8	541.6	616.4	682.3	737.9
125°	212.1	229.5	251.8	280.7	319.8	375.7	445.7	520.4	589.1	647.6	696.1
127.5°	227.3	244.8	266.2	292.8	326.9	374.0	433.5	498.9	562.9	617.6	663.0
130°	236.9	254.5	275.3	300.9	331.2	373.0	425.5	485.3	544.7	597.1	640.9
132.5°	245.6	263.1	284.0	307.9	336.0	373.0	419.0	471.9	527.4	575.1	617.2
135°	256.5	274.7	295.6	317.8	342.7	373.0	411.3	454.4	500.8	544.0	582.3
137.5°	266.0	284.7	303.8	325.0	348.7	373.8	404.5	439.6	477.2	513.0	545.5
140°	272.0	290.2	309.7	329.8	351.4	374.3	401.2	431.5	463.1	494.1	522.4
142.5°	277.9	295.0	313.4	332.6	353.0	374.9	398.6	424.6	451.3	477.9	502.5
145°	286.8	302.3	319.8	336.6	354.8	374.3	394.5	415.3	436.3	457.1	475.3
147.5°	294.9	308.5	323.8	339.1	355.4	372.6	390.3	406.7	423.7	439.7	453.5
150°	300.2	311.7	326.5	340.6	355.4	370.9	387.1	401.9	416.7	429.5	441.6
152.5°	305.1	315.5	329.2	341.7	354.9	368.8	383.3	396.5	409.7	421.5	430.8
155°	311.0	320.5	331.9	342.7	353.4	364.9	377.0	388.5	399.2	408.6	416.0
157.5°	317.2	324.3	334.2	343.4	351.7	360.8	371.1	380.4	389.3	396.5	402.3
160°	320.5	326.5	335.3	343.4	350.1	358.2	366.3	375.0	381.7	388.5	393.1
162.5°	323.6	328.6	336.3	342.8	348.4	354.9	361.9	369.0	375.2	380.9	385.0
165°	327.2	331.2	336.6	342.0	346.0	350.1	355.4	360.8	365.6	369.6	373.0
167.5°	329.6	332.2	336.6	340.4	342.2	345.3	349.1	353.0	356.1	359.2	361.6
170°	331.2	333.2	336.6	339.3	340.6	342.7	345.3	348.7	350.8	352.8	354.1
172.5°	332.3	333.2	336.0	338.2	338.5	339.4	341.6	343.9	345.9	347.4	348.2
175°	333.2	333.2	335.3	336.6	336.0	336.0	336.6	338.6	338.6	340.0	340.0
177.5°	333.4	333.4	334.4	335.0	333.9	333.9	334.4	335.0	335.5	335.5	335.5
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	763.3	760.3	759.6	760.6	759.6	760.3	763.3	763.5	763.8	765.9	763.0
5°	704.2	700.9	702.6	701.9	702.6	700.9	704.2	707.5	708.1	711.0	713.0
7.5°	652.2	648.2	643.9	645.2	643.9	648.2	652.2	652.3	657.4	661.2	663.7
10°	615.9	612.6	610.6	612.3	610.6	612.6	615.9	620.1	622.1	626.6	631.5
12.5°	585.2	583.3	581.6	580.9	581.6	583.3	585.2	589.8	594.3	599.7	605.1
15°	543.5	539.7	538.0	533.8	538.0	539.7	543.5	547.5	556.4	558.6	566.8
17.5°	505.1	503.9	499.6	497.8	499.6	503.9	505.1	508.5	512.6	521.0	527.2
20°	482.4	481.1	476.9	479.5	476.9	481.1	482.4	487.3	490.6	497.5	503.3
22.5°	463.6	460.7	459.3	458.6	459.3	460.7	463.6	465.9	470.2	476.6	483.2
25°	437.0	432.7	431.1	429.1	431.1	432.7	437.0	438.2	442.8	449.1	452.6
27.5°	410.4	408.1	406.0	405.4	406.0	408.1	410.4	412.2	416.2	421.6	428.2
30°	393.1	390.8	389.2	389.2	389.2	390.8	393.1	397.1	400.0	404.9	409.8
32.5°	377.7	375.9	374.3	374.0	374.3	375.9	377.7	379.8	383.2	388.7	393.8
35°	355.2	352.6	351.9	350.0	351.9	352.6	355.2	356.8	360.4	364.4	368.6
37.5°	331.8	329.7	329.6	329.4	329.6	329.7	331.8	334.8	337.8	341.3	346.5
40°	316.9	315.3	315.0	312.7	315.0	315.3	316.9	318.2	321.5	326.1	330.0
42.5°	301.0	300.1	299.0	298.0	299.0	300.1	301.0	303.6	306.3	309.6	314.6
45°	279.3	277.1	277.1	275.4	277.1	277.1	279.3	281.6	282.9	286.8	293.3
47.5°	256.9	255.2	255.4	253.7	255.4	255.2	256.9	257.7	259.8	263.6	267.3
50°	242.0	241.1	240.7	240.0	240.7	241.1	242.0	241.7	244.4	247.9	252.8
52.5°	227.1	226.7	227.9	226.4	227.9	226.7	227.1	227.8	229.6	232.0	236.6
55°	207.1	206.0	208.0	206.0	208.0	206.0	207.1	206.4	207.1	209.3	212.2
57.5°	183.9	183.0	184.8	183.8	184.8	183.0	183.9	184.1	186.1	186.4	189.0
60°	168.8	166.8	167.8	168.2	167.8	166.8	168.8	169.4	170.0	170.4	173.1
62.5°	150.7	149.6	150.2	148.8	150.2	149.6	150.7	152.1	153.6	155.2	156.8
65°	125.3	124.3	123.0	122.3	123.0	124.3	125.3	126.0	129.5	131.5	135.1
67.5°	105.2	102.9	102.8	103.3	102.8	102.9	105.2	105.1	107.7	109.3	111.8
70°	90.6	90.6	90.2	90.2	90.2	90.6	90.6	92.6	93.8	95.1	96.8
72.5°	80.4	80.2	79.6	79.3	79.6	80.2	80.4	81.0	81.8	83.2	84.8
75°	64.7	65.1	64.4	64.1	64.4	65.1	64.7	64.7	66.0	66.4	67.1
77.5°	47.8	46.4	47.2	46.4	47.2	46.4	47.8	49.2	49.6	51.1	51.1
80°	36.3	36.0	36.9	36.0	36.9	36.0	36.3	36.3	37.3	38.0	39.6
82.5°	28.8	28.4	28.8	28.2	28.8	28.4	28.8	28.4	28.9	29.8	29.6
85°	17.3	17.0	16.7	17.0	16.7	17.0	17.3	17.0	16.7	17.0	17.3
87.5°	9.0	8.7	8.9	8.9	8.9	8.7	9.0	8.7	8.7	8.6	8.4
90°	14.8	14.8	15.5	15.5	15.5	14.8	14.8	14.8	13.4	12.8	12.1
92.5°	46.6	44.9	44.0	43.0	44.0	44.9	46.6	55.2	65.2	86.6	119.3
95°	194.6	174.4	169.0	158.2	169.0	174.4	194.6	242.4	298.9	381.7	484.1
97.5°	448.2	410.5	391.0	382.4	391.0	410.5	448.2	489.8	568.4	649.1	720.9
100°	609.2	560.8	535.9	525.1	535.9	560.8	609.2	655.7	725.7	795.0	828.0
102.5°	754.1	719.6	692.6	684.5	692.6	719.6	754.1	803.8	851.2	884.5	864.1
105°	935.7	913.5	900.1	892.0	900.1	913.5	935.7	957.3	964.8	935.1	842.8
107.5°	1012.1	1011.9	1007.5	1002.1	1007.5	1011.9	1012.1	1001.2	966.0	890.0	766.9
110°	1021.2	1034.1	1038.8	1038.8	1038.8	1034.1	1021.2	990.9	933.8	838.8	710.9



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	995.9	1017.9	1029.6	1034.5	1029.6	1017.9	995.9	951.7	884.2	788.2	666.8
115°	933.8	966.0	984.9	993.7	984.9	966.0	933.8	881.2	807.9	715.7	611.3
117.5°	864.7	898.0	916.8	922.1	916.8	898.0	864.7	812.2	744.9	665.4	575.5
120°	819.9	852.3	870.5	875.8	870.5	852.3	819.9	770.2	710.9	636.9	556.0
122.5°	782.3	811.9	830.1	834.9	830.1	811.9	782.3	737.9	682.3	616.4	541.6
125°	733.8	761.4	776.2	782.9	776.2	761.4	733.8	696.1	647.6	589.1	520.4
127.5°	697.2	721.5	735.6	738.5	735.6	721.5	697.2	663.0	617.6	562.9	498.9
130°	674.6	696.8	710.2	714.3	710.2	696.8	674.6	640.9	597.1	544.7	485.3
132.5°	650.8	673.0	685.4	690.0	685.4	673.0	650.8	617.2	575.1	527.4	471.9
135°	611.9	634.1	646.3	650.3	646.3	634.1	611.9	582.3	544.0	500.8	454.4
137.5°	572.1	592.3	603.5	608.0	603.5	592.3	572.1	545.5	513.0	477.2	439.6
140°	547.3	564.8	574.9	578.2	574.9	564.8	547.3	522.4	494.1	463.1	431.5
142.5°	523.7	538.5	548.0	550.8	548.0	538.5	523.7	502.5	477.9	451.3	424.6
145°	491.5	502.9	510.3	513.0	510.3	502.9	491.5	475.3	457.1	436.3	415.3
147.5°	466.2	475.4	479.7	481.0	479.7	475.4	466.2	453.5	439.7	423.7	406.7
150°	451.8	459.8	462.5	463.1	462.5	459.8	451.8	441.6	429.5	416.7	401.9
152.5°	439.4	445.8	448.5	449.2	448.5	445.8	439.4	430.8	421.5	409.7	396.5
155°	422.8	427.5	429.5	430.2	429.5	427.5	422.8	416.0	408.6	399.2	388.5
157.5°	407.6	411.5	413.4	413.2	413.4	411.5	407.6	402.3	396.5	389.3	380.4
160°	397.9	401.2	402.6	401.9	402.6	401.2	397.9	393.1	388.5	381.7	375.0
162.5°	388.7	391.5	391.8	391.7	391.8	391.5	388.7	385.0	380.9	375.2	369.0
165°	375.7	377.0	377.0	377.0	377.0	377.0	375.7	373.0	369.6	365.6	360.8
167.5°	363.0	364.2	363.7	363.5	363.7	364.2	363.0	361.6	359.2	356.1	353.0
170°	355.4	356.1	356.1	355.4	356.1	356.1	355.4	354.1	352.8	350.8	348.7
172.5°	348.4	349.7	348.6	347.9	348.6	349.7	348.4	348.2	347.4	345.9	343.9
175°	340.0	340.6	339.3	338.6	339.3	340.6	340.0	340.0	340.0	338.6	338.6
177.5°	335.0	335.5	333.9	333.9	333.9	335.5	335.0	335.5	335.5	335.5	335.0
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	763.8	766.6	768.2	771.9	777.1	779.7	783.4	786.0	789.7	794.1	797.8
5°	714.3	722.2	727.4	735.6	743.1	750.6	760.1	767.0	776.1	786.6	794.8
7.5°	668.4	678.2	686.9	697.7	710.2	719.8	732.2	744.8	759.1	774.0	788.0
10°	639.1	648.9	659.7	673.1	685.5	698.6	713.3	728.1	746.1	762.8	781.7
12.5°	610.0	620.9	633.0	648.0	663.1	679.8	694.7	711.3	730.6	752.3	772.6
15°	574.0	584.4	597.5	610.3	627.7	645.9	665.9	687.9	709.4	733.7	758.8
17.5°	535.4	546.8	561.3	576.0	594.3	615.7	635.3	659.3	683.5	711.8	741.4
20°	510.2	522.0	539.0	555.3	572.0	593.0	616.2	640.8	666.6	696.3	729.4
22.5°	490.3	498.7	515.5	532.1	551.6	573.1	595.8	621.4	649.5	680.4	715.0
25°	460.8	470.6	482.8	500.1	520.4	542.9	565.8	593.0	623.7	655.1	692.1
27.5°	434.6	442.6	454.6	468.2	488.4	511.9	536.2	564.6	596.1	628.0	666.9
30°	416.0	424.9	436.3	450.7	466.7	492.2	517.1	544.9	577.0	610.0	649.9
32.5°	399.8	408.9	418.8	432.4	449.7	472.3	498.0	525.3	557.8	591.9	630.8
35°	377.1	383.3	392.4	405.9	422.9	441.2	467.4	496.2	527.9	563.2	602.1
37.5°	351.1	359.1	368.2	379.9	394.8	414.6	438.9	468.0	497.5	531.3	566.8
40°	335.9	343.5	353.5	362.1	377.8	395.7	418.0	448.4	477.9	509.5	541.9
42.5°	320.5	327.7	336.3	346.9	361.0	378.5	399.2	427.5	459.0	488.9	516.1
45°	296.4	303.8	312.0	321.8	334.9	351.9	372.6	398.4	425.9	453.3	473.9
47.5°	273.2	280.3	288.0	298.1	310.1	326.6	345.0	367.8	394.5	417.8	432.6
50°	256.8	263.3	271.8	281.6	293.3	308.8	326.4	349.0	371.3	392.4	405.9
52.5°	240.6	247.9	256.3	264.8	276.1	291.4	307.8	327.3	348.4	365.8	376.9
55°	216.2	223.1	230.9	239.7	250.9	264.0	281.3	296.6	313.3	328.0	334.6
57.5°	192.7	198.7	206.1	215.2	225.3	237.5	251.2	266.0	277.8	288.2	295.6
60°	177.3	182.5	189.3	197.3	208.0	219.1	231.5	245.3	254.4	263.3	270.2
62.5°	161.6	166.5	173.1	180.2	189.7	200.0	212.0	223.1	232.0	237.9	245.8
65°	138.0	142.9	148.5	156.0	163.5	172.0	182.8	191.0	197.3	203.8	208.7
67.5°	116.1	120.2	125.4	131.4	137.7	145.9	154.2	161.0	165.3	169.2	175.1
70°	101.7	105.0	109.3	113.8	120.7	128.9	135.4	140.6	143.6	147.5	154.7
72.5°	87.0	90.8	94.9	99.4	105.0	111.8	117.6	122.9	124.8	127.9	132.4
75°	68.7	70.7	74.0	77.1	81.1	87.0	92.6	93.8	95.5	98.2	101.4
77.5°	51.9	53.7	55.0	57.2	60.3	65.0	67.9	69.9	70.3	71.3	74.5
80°	41.2	42.2	43.5	45.1	46.4	50.4	52.0	54.0	54.6	55.6	57.3
82.5°	30.2	31.2	32.0	33.3	35.5	37.0	38.7	40.6	40.7	41.5	41.8
85°	17.7	18.0	17.3	18.0	18.3	18.9	20.6	22.2	22.0	21.6	22.6
87.5°	8.6	8.4	7.9	8.5	7.7	7.9	7.6	7.6	7.8	8.1	8.5
90°	11.5	10.8	9.4	8.8	7.4	6.7	5.4	4.0	2.7	1.4	0.7
92.5°	175.7	217.1	220.5	153.6	92.0	55.2	35.6	23.9	15.6	10.0	8.2
95°	583.7	596.5	486.7	300.9	152.8	80.8	50.5	35.6	28.2	22.9	22.2
97.5°	738.5	637.0	434.6	240.2	131.6	84.0	62.2	48.9	41.5	37.7	36.9
100°	776.2	608.0	387.8	218.1	130.6	91.5	71.4	58.5	51.1	48.5	47.1
102.5°	753.6	556.7	352.2	209.0	135.4	100.7	81.0	69.3	61.4	59.2	58.5
105°	681.3	488.1	317.8	205.3	145.4	115.8	96.9	86.2	79.5	76.1	76.1
107.5°	607.5	440.8	303.2	211.5	160.2	131.6	114.6	103.4	97.9	94.6	93.3
110°	565.5	418.7	298.9	217.5	171.0	143.4	125.9	115.8	109.7	107.0	105.7



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	534.3	405.8	298.9	225.0	181.2	154.7	137.8	127.6	121.6	119.4	118.0
115°	500.2	391.8	300.9	236.3	197.3	172.4	155.5	145.4	139.4	137.3	136.0
117.5°	479.8	385.0	305.4	249.3	213.7	190.1	173.8	162.4	156.4	154.2	152.1
120°	468.6	381.7	309.7	257.9	225.5	202.0	185.1	173.7	167.6	165.0	162.9
122.5°	458.8	379.0	313.4	267.5	236.9	213.3	196.5	183.9	177.9	175.7	174.3
125°	445.7	375.7	319.8	280.7	251.8	229.5	212.1	199.2	193.2	189.9	188.5
127.5°	433.5	374.0	326.9	292.8	266.2	244.8	227.3	213.7	206.0	201.7	199.7
130°	425.5	373.0	331.2	300.9	275.3	254.5	236.9	222.8	214.0	208.7	206.6
132.5°	419.0	373.0	336.0	307.9	284.0	263.1	245.6	230.9	221.1	214.6	212.1
135°	411.3	373.0	342.7	317.8	295.6	274.7	256.5	242.4	231.6	223.5	220.8
137.5°	404.5	373.8	348.7	325.0	303.8	284.7	266.0	252.2	241.4	233.8	231.9
140°	401.2	374.3	351.4	329.8	309.7	290.2	272.0	259.2	248.4	240.3	238.3
142.5°	398.6	374.9	353.0	332.6	313.4	295.0	277.9	265.6	254.9	247.4	245.8
145°	394.5	374.3	354.8	336.6	319.8	302.3	286.8	274.7	265.3	258.5	257.2
147.5°	390.3	372.6	355.4	339.1	323.8	308.5	294.9	284.4	275.6	269.8	269.0
150°	387.1	370.9	355.4	340.6	326.5	311.7	300.2	290.8	282.1	277.3	276.0
152.5°	383.3	368.8	354.9	341.7	329.2	315.5	305.1	296.2	288.5	284.4	283.5
155°	377.0	364.9	353.4	342.7	331.9	320.5	311.0	304.3	297.6	293.5	293.5
157.5°	371.1	360.8	351.7	343.4	334.2	324.3	317.2	311.3	305.5	302.3	302.4
160°	366.3	358.2	350.1	343.4	335.3	326.5	320.5	315.0	310.4	307.6	308.3
162.5°	361.9	354.9	348.4	342.8	336.3	328.6	323.6	319.3	315.2	312.5	313.1
165°	355.4	350.1	346.0	342.0	336.6	331.2	327.2	324.5	321.2	319.1	320.5
167.5°	349.1	345.3	342.2	340.4	336.6	332.2	329.6	327.7	325.8	324.6	325.3
170°	345.3	342.7	340.6	339.3	336.6	333.2	331.2	329.8	328.6	327.9	328.6
172.5°	341.6	339.4	338.5	338.2	336.0	333.2	332.3	331.5	330.1	329.5	330.7
175°	336.6	336.0	336.0	336.6	335.3	333.2	333.2	333.2	332.6	331.9	333.2
177.5°	334.4	333.9	333.9	335.0	334.4	333.4	333.4	333.9	333.4	333.4	334.4
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	800.6	803.1	806.4	810.4	813.5	816.9	818.7	818.7	820.3	823.7	828.1
5°	803.0	811.5	819.7	830.1	838.3	847.7	855.0	861.9	868.1	875.9	884.1
7.5°	802.3	816.4	831.1	847.7	865.8	880.3	895.1	906.8	918.3	933.3	945.2
10°	799.7	818.0	837.9	858.8	881.8	901.7	919.7	936.1	951.7	968.1	982.8
12.5°	795.0	818.3	842.7	867.8	896.7	919.5	942.7	960.2	978.4	996.3	1014.5
15°	787.9	815.4	844.8	879.9	915.2	940.6	963.5	986.1	1003.2	1023.4	1040.8
17.5°	773.4	808.7	845.8	884.0	917.9	947.6	971.6	993.1	1011.2	1033.5	1057.0
20°	764.7	803.0	841.5	882.4	914.8	945.2	968.5	990.7	1013.2	1042.4	1071.2
22.5°	752.7	793.5	834.5	873.3	907.5	936.9	960.9	988.1	1017.7	1050.8	1085.5
25°	733.7	775.8	816.4	853.3	886.7	916.8	949.5	986.1	1022.1	1065.6	1115.6
27.5°	709.5	750.2	786.4	825.4	858.6	896.8	937.6	977.3	1029.2	1089.1	1151.6
30°	691.4	730.0	764.4	801.3	839.0	881.1	927.0	973.7	1035.5	1105.8	1180.1
32.5°	670.5	705.4	739.5	775.2	818.6	864.9	913.6	970.8	1044.7	1124.6	1201.5
35°	634.2	665.6	698.6	738.2	784.3	834.7	896.8	966.5	1055.8	1141.8	1210.8
37.5°	596.2	620.9	654.1	695.8	746.1	804.3	874.9	959.5	1051.2	1128.4	1157.8
40°	566.8	590.0	625.0	668.8	718.6	782.4	861.5	948.5	1040.8	1094.3	1092.1
42.5°	537.8	561.3	595.0	639.0	690.9	762.2	843.7	934.1	1011.9	1032.3	989.8
45°	493.2	515.1	548.2	592.6	648.2	723.2	808.8	895.5	945.2	912.2	827.9
47.5°	447.8	469.1	499.7	543.3	604.0	682.4	763.4	834.6	841.5	770.6	669.3
50°	418.0	437.9	467.1	513.5	572.4	648.9	727.1	783.0	765.7	679.0	574.6
52.5°	388.9	408.1	435.4	479.2	539.4	614.4	684.2	728.1	687.9	595.8	502.0
55°	346.0	364.4	391.8	432.0	486.6	555.3	616.6	632.6	573.7	480.8	404.9
57.5°	305.3	318.7	345.9	381.4	434.1	494.6	538.5	535.6	470.6	387.0	332.6
60°	278.4	290.4	316.2	349.0	399.0	453.3	484.1	471.0	405.3	336.2	283.9
62.5°	253.2	264.5	286.2	316.2	359.3	406.5	428.9	410.8	348.7	288.1	246.5
65°	215.2	223.4	240.7	268.5	302.2	334.9	354.9	328.4	273.5	227.6	196.2
67.5°	179.7	186.8	202.2	222.1	245.4	267.9	276.0	251.2	208.4	177.6	155.5
70°	156.7	163.2	173.7	192.3	207.7	223.7	227.6	205.4	169.8	146.2	132.4
72.5°	134.7	140.7	149.9	163.0	173.7	182.9	184.8	164.0	136.8	120.5	109.9
75°	102.7	108.0	113.8	118.7	125.6	127.3	126.6	110.6	95.8	85.1	79.1
77.5°	75.5	77.7	81.3	83.2	83.5	83.4	80.1	69.9	62.3	57.9	55.4
80°	58.2	59.8	60.9	61.5	61.8	58.5	54.9	48.7	46.1	43.5	40.6
82.5°	42.3	43.4	44.3	44.5	42.7	40.0	36.6	33.6	31.7	30.4	29.3
85°	22.9	23.2	22.9	21.3	18.9	18.0	17.3	16.7	16.4	16.0	16.0
87.5°	8.4	7.8	6.8	7.3	7.7	7.5	7.7	7.7	7.7	7.7	7.9
90°	1.4	2.7	4.0	5.4	6.7	7.4	8.8	9.4	10.8	11.5	12.1
92.5°	10.0	15.6	23.9	35.6	55.2	92.0	153.6	220.5	217.1	175.7	119.3
95°	22.9	28.2	35.6	50.5	80.8	152.8	300.9	486.7	596.5	583.7	484.1
97.5°	37.7	41.5	48.9	62.2	84.0	131.6	240.2	434.6	637.0	738.5	720.9
100°	48.5	51.1	58.5	71.4	91.5	130.6	218.1	387.8	608.0	776.2	828.0
102.5°	59.2	61.4	69.3	81.0	100.7	135.4	209.0	352.2	556.7	753.6	864.1
105°	76.1	79.5	86.2	96.9	115.8	145.4	205.3	317.8	488.1	681.3	842.8
107.5°	94.6	97.9	103.4	114.6	131.6	160.2	211.5	303.2	440.8	607.5	766.9
110°	107.0	109.7	115.8	125.9	143.4	171.0	217.5	298.9	418.7	565.5	710.9





TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	119.4	121.6	127.6	137.8	154.7	181.2	225.0	298.9	405.8	534.3	666.8
115°	137.3	139.4	145.4	155.5	172.4	197.3	236.3	300.9	391.8	500.2	611.3
117.5°	154.2	156.4	162.4	173.8	190.1	213.7	249.3	305.4	385.0	479.8	575.5
120°	165.0	167.6	173.7	185.1	202.0	225.5	257.9	309.7	381.7	468.6	556.0
122.5°	175.7	177.9	183.9	196.5	213.3	236.9	267.5	313.4	379.0	458.8	541.6
125°	189.9	193.2	199.2	212.1	229.5	251.8	280.7	319.8	375.7	445.7	520.4
127.5°	201.7	206.0	213.7	227.3	244.8	266.2	292.8	326.9	374.0	433.5	498.9
130°	208.7	214.0	222.8	236.9	254.5	275.3	300.9	331.2	373.0	425.5	485.3
132.5°	214.6	221.1	230.9	245.6	263.1	284.0	307.9	336.0	373.0	419.0	471.9
135°	223.5	231.6	242.4	256.5	274.7	295.6	317.8	342.7	373.0	411.3	454.4
137.5°	233.8	241.4	252.2	266.0	284.7	303.8	325.0	348.7	373.8	404.5	439.6
140°	240.3	248.4	259.2	272.0	290.2	309.7	329.8	351.4	374.3	401.2	431.5
142.5°	247.4	254.9	265.6	277.9	295.0	313.4	332.6	353.0	374.9	398.6	424.6
145°	258.5	265.3	274.7	286.8	302.3	319.8	336.6	354.8	374.3	394.5	415.3
147.5°	269.8	275.6	284.4	294.9	308.5	323.8	339.1	355.4	372.6	390.3	406.7
150°	277.3	282.1	290.8	300.2	311.7	326.5	340.6	355.4	370.9	387.1	401.9
152.5°	284.4	288.5	296.2	305.1	315.5	329.2	341.7	354.9	368.8	383.3	396.5
155°	293.5	297.6	304.3	311.0	320.5	331.9	342.7	353.4	364.9	377.0	388.5
157.5°	302.3	305.5	311.3	317.2	324.3	334.2	343.4	351.7	360.8	371.1	380.4
160°	307.6	310.4	315.0	320.5	326.5	335.3	343.4	350.1	358.2	366.3	375.0
162.5°	312.5	315.2	319.3	323.6	328.6	336.3	342.8	348.4	354.9	361.9	369.0
165°	319.1	321.2	324.5	327.2	331.2	336.6	342.0	346.0	350.1	355.4	360.8
167.5°	324.6	325.8	327.7	329.6	332.2	336.6	340.4	342.2	345.3	349.1	353.0
170°	327.9	328.6	329.8	331.2	333.2	336.6	339.3	340.6	342.7	345.3	348.7
172.5°	329.5	330.1	331.5	332.3	333.2	336.0	338.2	338.5	339.4	341.6	343.9
175°	331.9	332.6	333.2	333.2	333.2	335.3	336.6	336.0	336.0	336.6	338.6
177.5°	333.4	333.4	333.9	333.4	333.4	334.4	335.0	333.9	333.9	334.4	335.0
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9	333.9



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	796.8	796.8	796.8	796.8	796.8	796.8	796.8
2.5°	831.6	831.6	836.0	835.7	838.6	837.6	838.1
5°	893.9	899.4	904.3	907.6	912.5	913.9	913.2
7.5°	958.6	970.9	976.9	985.2	986.6	990.9	990.5
10°	998.5	1010.6	1019.8	1027.0	1030.6	1035.2	1035.5
12.5°	1029.9	1040.2	1048.4	1055.0	1059.4	1060.8	1061.7
15°	1054.5	1065.9	1075.4	1084.9	1090.5	1094.7	1097.0
17.5°	1079.2	1096.8	1113.6	1126.5	1134.2	1140.7	1140.7
20°	1098.3	1118.6	1139.5	1154.3	1169.2	1175.8	1176.8
22.5°	1118.7	1149.7	1176.6	1199.5	1219.3	1226.1	1228.6
25°	1161.1	1201.6	1243.2	1275.2	1298.1	1311.6	1313.5
27.5°	1212.3	1267.2	1310.9	1340.5	1359.5	1369.4	1371.6
30°	1248.4	1299.1	1338.3	1360.6	1369.4	1370.7	1365.8
32.5°	1264.6	1302.5	1318.2	1316.9	1299.6	1288.1	1283.7
35°	1244.8	1237.0	1198.7	1152.9	1117.9	1095.7	1089.8
37.5°	1132.8	1065.1	994.7	925.6	888.7	870.0	837.8
40°	1022.4	925.9	852.6	794.4	752.9	719.5	711.7
42.5°	897.9	798.2	725.0	675.1	642.0	619.1	609.2
45°	721.5	635.8	575.3	537.0	511.5	494.8	487.3
47.5°	577.0	510.7	466.7	438.3	418.9	404.4	400.4
50°	497.8	444.8	407.5	383.7	368.9	357.8	353.3
52.5°	432.4	389.6	360.9	341.3	327.4	320.4	316.6
55°	356.8	319.9	299.3	283.5	275.7	270.2	267.5
57.5°	291.8	265.1	250.0	239.2	232.0	228.4	227.1
60°	255.5	234.5	220.8	212.2	207.3	202.8	201.5
62.5°	223.3	206.8	196.1	188.7	183.8	181.8	181.1
65°	179.9	169.1	161.3	156.7	152.7	152.1	151.8
67.5°	143.0	136.6	132.5	127.8	126.4	124.1	123.6
70°	122.3	118.0	113.1	111.5	109.9	107.6	108.0
72.5°	103.8	99.5	96.2	94.0	93.4	92.5	93.2
75°	75.9	74.6	73.3	71.6	70.9	70.9	70.7
77.5°	54.2	53.0	51.6	50.6	50.5	49.1	49.6
80°	39.3	37.6	36.9	37.3	36.3	36.0	36.0
82.5°	29.0	28.4	27.8	27.9	27.6	27.4	27.6
85°	16.0	15.7	15.7	15.4	15.4	15.1	15.1
87.5°	8.4	8.7	8.4	8.2	8.2	8.6	8.9
90°	12.8	13.4	14.8	14.8	14.8	15.5	15.5
92.5°	86.6	65.2	55.2	46.6	44.9	44.0	43.0
95°	381.7	298.9	242.4	194.6	174.4	169.0	158.2
97.5°	649.1	568.4	489.8	448.2	410.5	391.0	382.4
100°	795.0	725.7	655.7	609.2	560.8	535.9	525.1
102.5°	884.5	851.2	803.8	754.1	719.6	692.6	684.5
105°	935.1	964.8	957.3	935.7	913.5	900.1	892.0
107.5°	890.0	966.0	1001.2	1012.1	1011.9	1007.5	1002.1
110°	838.8	933.8	990.9	1021.2	1034.1	1038.8	1038.8



TEST NUMBER: P333534-935

CATALOG NUMBER: S125RDIP-S610D810U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	788.2	884.2	951.7	995.9	1017.9	1029.6	1034.5
115°	715.7	807.9	881.2	933.8	966.0	984.9	993.7
117.5°	665.4	744.9	812.2	864.7	898.0	916.8	922.1
120°	636.9	710.9	770.2	819.9	852.3	870.5	875.8
122.5°	616.4	682.3	737.9	782.3	811.9	830.1	834.9
125°	589.1	647.6	696.1	733.8	761.4	776.2	782.9
127.5°	562.9	617.6	663.0	697.2	721.5	735.6	738.5
130°	544.7	597.1	640.9	674.6	696.8	710.2	714.3
132.5°	527.4	575.1	617.2	650.8	673.0	685.4	690.0
135°	500.8	544.0	582.3	611.9	634.1	646.3	650.3
137.5°	477.2	513.0	545.5	572.1	592.3	603.5	608.0
140°	463.1	494.1	522.4	547.3	564.8	574.9	578.2
142.5°	451.3	477.9	502.5	523.7	538.5	548.0	550.8
145°	436.3	457.1	475.3	491.5	502.9	510.3	513.0
147.5°	423.7	439.7	453.5	466.2	475.4	479.7	481.0
150°	416.7	429.5	441.6	451.8	459.8	462.5	463.1
152.5°	409.7	421.5	430.8	439.4	445.8	448.5	449.2
155°	399.2	408.6	416.0	422.8	427.5	429.5	430.2
157.5°	389.3	396.5	402.3	407.6	411.5	413.4	413.2
160°	381.7	388.5	393.1	397.9	401.2	402.6	401.9
162.5°	375.2	380.9	385.0	388.7	391.5	391.8	391.7
165°	365.6	369.6	373.0	375.7	377.0	377.0	377.0
167.5°	356.1	359.2	361.6	363.0	364.2	363.7	363.5
170°	350.8	352.8	354.1	355.4	356.1	356.1	355.4
172.5°	345.9	347.4	348.2	348.4	349.7	348.6	347.9
175°	338.6	340.0	340.0	340.0	340.6	339.3	338.6
177.5°	335.5	335.5	335.5	335.0	335.5	333.9	333.9
180°	333.9	333.9	333.9	333.9	333.9	333.9	333.9

(END OF REPORT)