

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333569-935

Luminaire Tested: **S125RDIP-S850D1035U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333569-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1035U935-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5906.2 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	48	48	48														
1	98	94	90	86	90	86	83	80	73	70	68	60	58	57	48	47	47	41	41	41	41	41	41	41														
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40	35	35	35	35	35	35	35														
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30	30	30	30	30	30	30														
4	75	64	57	51	69	60	53	48	51	46	41	42	39	36	35	32	30	26	26	26	26	26	26	26														
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23	23	23	23	23	23	23														
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20	20	20	20	20														
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21	18	18	18	18	18	18	18														
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	18	16	16	16	16	16	16	16														
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14	14	14	14	14	14	14														
10	47	35	28	24	44	33	27	22	29	23	20	24	20	17	20	17	15	13	13	13	13	13	13	13														

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7034	7034	7034	7034
5°	8092	7043	6220	7043
10°	9282	7007	5488	7007
15°	10026	6935	4878	6935
20°	11056	6852	4504	6852
25°	12794	6741	4180	6741
30°	13923	6624	3967	6624
35°	11744	6489	3772	6489
40°	8201	6246	3603	6246
45°	6085	5917	3438	5917
50°	4851	5574	3297	5574
55°	4118	5150	3171	5150
60°	3557	4770	2968	4770
65°	3169	4358	2555	4358
70°	2787	3994	2330	3994
75°	2410	3459	2186	3459
80°	1830	2912	1830	2912
85°	1526	2282	1719	2282



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	1.8
10°-20°	306.1	5.2
20°-30°	485.3	8.2
30°-40°	585.2	9.9
40°-50°	522.6	8.8
50°-60°	400.8	6.8
60°-70°	260.4	4.4
70°-80°	126.6	2.1
80°-90°	32.6	0.6
90°-100°	74.0	1.3
100°-110°	218.5	3.7
110°-120°	370.0	6.3
120°-130°	487.0	8.2
130°-140°	545.7	9.2
140°-150°	534.8	9.1
150°-160°	449.2	7.6
160°-170°	298.6	5.1
170°-180°	104.5	1.8
0°-30°	895.8	15.2
0°-40°	1481.0	25.1
0°-60°	2404.3	40.7
0°-90°	2824.0	47.8
90°-120°	662.5	11.2
90°-150°	2229.9	37.8
90°-180°	3082.0	52.2
0°-180°	5906.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1089	1089	1089	1089	1089	
5°	1248	1086	959	1086	1248	125
15°	1500	1037	730	1037	1500	430
25°	1795	946	587	946	1795	824
35°	1490	823	478	823	1490	900
45°	666	648	376	648	666	532
55°	366	457	282	457	366	332
65°	207	285	167	285	207	206
75°	97	139	88	139	97	103
85°	21	31	23	31	21	24
90°	21	1	21	1	21	13
95°	74	56	74	56	74	75
105°	213	196	213	196	213	226
115°	374	370	374	370	374	370
125°	544	541	544	541	544	486
135°	706	703	706	703	706	544
145°	855	852	855	852	855	534
155°	975	975	975	975	975	449
165°	1057	1060	1057	1060	1057	298
175°	1098	1102	1098	1102	1098	104
180°	1105	1105	1105	1105	1105	



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1145.6	1144.9	1146.3	1142.4	1142.7	1136.6	1136.6	1132.0	1125.9	1121.3	1119.1
5°	1248.2	1249.1	1247.3	1240.6	1236.1	1229.4	1221.8	1208.4	1197.2	1186.5	1178.0
7.5°	1353.9	1354.5	1348.7	1346.6	1335.3	1327.1	1310.2	1291.9	1275.7	1255.2	1239.5
10°	1415.4	1415.0	1408.8	1403.8	1394.0	1381.5	1364.9	1343.4	1323.4	1301.0	1279.5
12.5°	1451.2	1450.0	1448.0	1442.1	1433.0	1421.9	1407.8	1386.7	1361.9	1337.5	1312.4
15°	1499.5	1496.3	1490.6	1482.9	1470.0	1457.0	1441.4	1422.6	1398.9	1371.1	1347.9
17.5°	1559.2	1559.3	1550.4	1539.8	1522.2	1499.3	1475.2	1444.8	1412.6	1382.2	1357.4
20°	1608.6	1607.2	1598.3	1577.7	1557.6	1529.0	1501.2	1464.1	1424.8	1385.0	1354.2
22.5°	1679.4	1675.9	1666.6	1639.6	1608.4	1571.6	1529.1	1483.8	1436.2	1391.1	1350.7
25°	1795.4	1792.8	1774.4	1743.2	1699.4	1642.5	1587.1	1525.0	1456.6	1397.1	1347.9
27.5°	1874.8	1871.9	1858.3	1832.3	1791.9	1732.2	1657.1	1574.1	1488.7	1406.9	1335.9
30°	1867.0	1873.7	1871.9	1859.8	1829.5	1775.8	1706.5	1613.1	1511.6	1415.4	1330.9
32.5°	1754.6	1760.7	1776.4	1800.1	1801.9	1780.5	1728.6	1642.4	1537.3	1428.0	1327.0
35°	1489.6	1497.7	1528.1	1576.0	1638.5	1690.8	1701.6	1655.1	1560.7	1443.1	1321.1
37.5°	1145.2	1189.2	1214.8	1265.2	1359.7	1456.0	1548.5	1582.5	1542.4	1436.9	1311.6
40°	972.8	983.5	1029.2	1086.0	1165.5	1265.7	1397.6	1492.8	1495.9	1422.6	1296.5
42.5°	832.6	846.2	877.5	922.8	991.0	1091.1	1227.3	1353.0	1411.2	1383.3	1276.9
45°	666.2	676.4	699.2	734.1	786.4	869.1	986.3	1131.5	1246.9	1292.0	1224.1
47.5°	547.3	552.8	572.7	599.2	637.9	698.2	788.8	915.0	1053.3	1150.3	1140.7
50°	482.8	489.1	504.3	524.4	557.1	608.0	680.4	785.5	928.2	1046.6	1070.3
52.5°	432.7	438.0	447.5	466.5	493.4	532.5	591.0	686.0	814.4	940.4	995.1
55°	365.7	369.3	376.9	387.6	409.1	437.2	487.8	553.5	657.2	784.2	864.6
57.5°	310.5	312.2	317.1	327.0	341.8	362.4	398.9	454.6	529.0	643.3	732.1
60°	275.4	277.2	283.4	290.2	301.8	320.6	349.1	388.1	459.6	553.9	643.8
62.5°	247.5	248.6	251.2	258.0	268.1	282.7	305.1	336.9	393.8	476.6	561.5
65°	207.4	207.9	208.8	214.1	220.4	231.2	245.9	268.2	311.2	373.8	448.8
67.5°	169.0	169.6	172.7	174.6	181.2	186.8	195.4	212.6	242.8	285.0	343.4
70°	147.6	147.1	150.2	152.5	154.7	161.4	167.2	181.1	199.8	232.0	280.8
72.5°	127.5	126.3	127.7	128.5	131.5	136.0	141.8	150.3	164.8	186.9	224.3
75°	96.6	97.0	97.0	97.9	100.1	101.9	103.8	108.2	116.2	131.0	151.1
77.5°	67.8	67.1	69.0	69.2	70.5	72.5	74.0	75.9	79.1	85.2	95.6
80°	49.2	49.2	49.6	51.0	50.5	51.4	53.6	55.4	59.5	63.0	66.6
82.5°	37.7	37.4	37.8	38.1	38.0	38.9	39.7	40.0	41.6	43.4	45.9
85°	20.6	20.6	21.0	21.0	21.4	21.4	21.9	21.9	21.9	22.4	22.8
87.5°	12.0	11.5	11.0	10.9	11.2	11.7	11.2	10.7	10.4	10.2	10.3
90°	20.7	20.1	19.5	18.9	18.3	17.6	16.6	15.7	14.7	13.8	12.4
92.5°	40.6	40.1	39.7	39.3	38.9	38.1	36.8	35.6	34.3	33.0	31.3
95°	74.0	73.5	73.2	72.8	72.4	71.5	70.2	68.9	67.5	66.2	64.3
97.5°	112.1	111.8	111.7	111.4	111.2	110.5	109.2	107.9	106.7	105.4	102.7
100°	140.9	140.6	140.2	139.8	139.5	138.4	136.6	134.9	133.2	131.5	129.1
102.5°	169.9	169.4	168.8	168.2	167.7	166.5	164.6	162.7	160.9	159.0	157.7
105°	213.2	212.6	212.1	211.5	210.9	210.0	208.9	207.8	206.6	205.4	204.3
107.5°	257.5	257.6	257.6	257.6	257.7	257.4	256.8	256.2	255.7	255.1	254.3
110°	290.5	290.8	290.9	291.1	291.3	291.1	290.5	290.0	289.4	288.8	288.3



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	322.9	323.2	323.6	323.9	324.3	324.3	324.0	323.7	323.5	323.2	322.4
115°	373.9	374.1	374.3	374.4	374.7	374.9	375.1	375.2	375.5	375.7	375.2
117.5°	423.8	424.6	425.3	426.0	426.8	427.1	427.0	426.8	426.7	426.5	426.2
120°	458.1	458.9	459.7	460.5	461.2	461.6	461.6	461.6	461.6	461.6	461.4
122.5°	492.6	493.2	493.8	494.4	495.0	495.3	495.5	495.7	495.8	495.9	495.5
125°	544.2	544.3	544.5	544.7	544.8	545.2	545.5	546.0	546.3	546.7	546.5
127.5°	593.7	594.0	594.3	594.8	595.1	595.5	595.6	595.8	596.0	596.2	596.0
130°	626.6	627.0	627.4	627.8	628.2	628.4	628.6	628.8	629.0	629.2	628.8
132.5°	657.5	658.1	658.7	659.2	659.7	660.0	660.3	660.5	660.6	660.8	660.9
135°	705.7	706.5	707.2	708.0	708.8	709.1	709.1	709.1	709.1	709.1	708.9
137.5°	752.9	753.8	754.8	755.7	756.6	757.0	756.7	756.6	756.3	756.0	755.7
140°	783.1	784.0	785.0	785.9	786.9	787.2	786.8	786.4	786.0	785.7	785.1
142.5°	811.9	813.0	813.9	814.9	815.8	816.1	815.9	815.7	815.5	815.2	814.5
145°	855.3	855.8	856.4	857.0	857.6	857.9	857.9	857.9	857.9	857.9	857.3
147.5°	892.3	893.5	894.8	896.1	897.4	897.9	897.4	896.9	896.5	896.0	895.5
150°	919.7	920.2	920.5	920.9	921.3	921.4	921.4	921.4	921.4	921.4	920.7
152.5°	942.5	943.1	943.8	944.5	945.2	945.3	944.9	944.4	943.9	943.5	943.1
155°	974.7	975.7	976.6	977.7	978.6	978.7	977.9	977.1	976.4	975.6	975.4
157.5°	1001.8	1003.0	1004.3	1005.6	1006.8	1007.0	1006.3	1005.5	1004.8	1004.0	1003.8
160°	1020.3	1021.3	1022.3	1023.2	1024.2	1024.2	1023.5	1022.7	1021.9	1021.1	1021.0
162.5°	1036.1	1037.2	1038.4	1039.5	1040.6	1040.7	1039.7	1038.8	1037.9	1037.0	1037.0
165°	1057.3	1058.4	1059.5	1060.8	1061.9	1062.0	1061.3	1060.5	1059.8	1059.0	1058.8
167.5°	1074.1	1075.3	1076.5	1077.7	1078.8	1078.9	1077.7	1076.6	1075.5	1074.3	1074.3
170°	1083.1	1084.4	1085.7	1087.1	1088.4	1088.5	1087.4	1086.2	1085.1	1083.9	1083.9
172.5°	1090.6	1091.8	1093.0	1094.2	1095.4	1095.4	1094.2	1093.1	1091.9	1090.8	1090.8
175°	1097.7	1099.0	1100.4	1101.7	1103.0	1103.1	1102.0	1100.9	1099.7	1098.5	1098.5
177.5°	1101.8	1102.9	1104.0	1105.0	1106.1	1106.1	1105.3	1104.3	1103.5	1102.5	1102.7
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1119.1	1116.6	1112.0	1107.7	1102.3	1097.7	1094.4	1090.5	1085.5	1079.4	1074.4
5°	1168.6	1158.8	1145.8	1134.7	1120.3	1109.2	1097.6	1086.4	1075.2	1060.9	1048.4
7.5°	1223.6	1203.2	1183.5	1158.6	1136.1	1115.9	1096.7	1077.1	1058.0	1037.7	1018.0
10°	1257.1	1232.6	1205.3	1174.0	1145.4	1118.1	1093.1	1068.5	1042.6	1019.8	995.1
12.5°	1288.7	1256.9	1225.7	1186.2	1151.8	1118.5	1086.7	1056.0	1028.3	998.7	972.3
15°	1317.1	1285.8	1250.9	1202.6	1154.8	1114.6	1077.0	1037.2	1002.8	969.7	940.2
17.5°	1328.1	1295.3	1254.7	1208.3	1156.1	1105.4	1057.0	1013.4	972.9	934.4	901.2
20°	1323.8	1292.0	1250.4	1206.2	1150.3	1097.6	1045.3	997.0	951.8	911.1	875.8
22.5°	1313.4	1280.6	1240.4	1193.7	1140.7	1084.7	1028.8	977.3	930.0	887.9	849.4
25°	1297.9	1253.2	1212.0	1166.4	1115.9	1060.5	1002.8	946.0	895.5	852.6	810.5
27.5°	1281.7	1225.9	1173.5	1128.3	1074.9	1025.4	969.8	911.5	858.5	814.8	771.6
30°	1267.0	1204.5	1146.8	1095.4	1044.8	997.9	945.1	888.3	833.8	788.7	744.9
32.5°	1248.8	1182.2	1118.9	1059.5	1010.8	964.2	916.5	862.2	809.1	762.5	718.0
35°	1225.9	1140.9	1072.1	1009.0	954.9	909.8	866.9	823.0	769.8	721.6	678.2
37.5°	1195.8	1099.4	1019.8	951.1	894.1	848.7	814.9	774.8	726.3	680.0	639.7
40°	1177.6	1069.4	982.2	914.3	854.4	806.5	774.8	740.8	696.5	653.2	612.9
42.5°	1153.3	1041.9	944.3	873.5	813.2	767.2	735.0	705.4	668.3	627.4	584.4
45°	1105.6	988.5	886.1	810.1	749.3	704.1	674.2	647.8	619.7	582.1	544.5
47.5°	1043.5	932.8	825.6	742.7	683.1	641.2	612.2	591.3	571.2	539.2	502.7
50°	993.9	887.0	782.4	701.9	638.4	598.7	571.4	554.8	536.5	507.4	477.0
52.5°	935.2	839.8	737.3	655.0	595.1	557.8	531.7	515.1	500.0	476.3	447.4
55°	842.7	759.1	665.2	590.6	535.6	498.0	473.0	457.4	448.4	428.3	405.5
57.5°	736.1	676.1	593.3	521.3	472.8	435.7	417.3	404.0	393.9	379.6	363.6
60°	661.7	619.7	545.4	477.0	432.3	397.0	380.5	369.3	359.9	347.8	335.3
62.5°	586.2	555.6	491.0	432.3	391.2	361.6	346.1	336.0	325.2	317.1	304.9
65°	485.1	457.8	413.1	367.0	329.1	305.3	294.2	285.2	278.5	269.6	261.1
67.5°	377.3	366.3	335.4	303.7	276.4	255.3	245.6	239.4	231.4	225.9	220.2
70°	311.2	305.8	283.9	262.9	237.4	223.1	214.1	211.5	201.6	196.3	192.3
72.5°	252.5	250.0	237.4	222.8	204.8	192.3	184.1	181.1	174.8	170.5	167.9
75°	173.0	173.9	171.7	162.3	155.6	147.6	140.3	138.6	134.1	130.5	128.3
77.5°	109.4	114.0	114.2	113.7	111.1	106.2	103.1	101.9	97.5	96.1	95.6
80°	75.1	80.0	84.5	84.0	83.2	81.8	79.6	78.3	76.0	74.6	73.8
82.5°	50.1	54.7	58.4	60.8	60.6	59.3	57.8	57.2	56.7	55.7	55.5
85°	23.7	24.6	25.9	29.1	31.3	31.8	31.3	30.8	29.5	30.0	30.4
87.5°	10.4	10.2	10.2	10.0	9.3	10.8	11.5	11.6	11.2	10.8	10.4
90°	11.1	9.7	8.4	7.0	5.4	3.9	2.4	0.9	2.4	3.9	5.4
92.5°	29.7	28.1	26.4	25.1	24.0	22.9	21.9	20.8	21.9	22.9	24.0
95°	62.3	60.4	58.5	57.4	57.0	56.7	56.2	55.9	56.2	56.7	57.0
97.5°	100.1	97.5	94.9	93.4	93.3	93.2	93.0	92.8	93.0	93.2	93.3
100°	126.6	124.1	121.6	120.4	120.4	120.4	120.4	120.4	120.4	120.4	120.4
102.5°	156.5	155.2	153.9	153.0	152.2	151.4	150.7	149.9	150.7	151.4	152.2
105°	203.1	202.0	200.9	199.8	198.9	197.9	196.9	196.0	196.9	197.9	198.9
107.5°	253.4	252.4	251.6	250.7	249.8	248.7	247.8	246.8	247.8	248.7	249.8
110°	287.7	287.1	286.5	285.8	284.8	283.9	282.9	282.0	282.9	283.9	284.8



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	321.8	321.1	320.3	319.7	319.2	318.7	318.2	317.7	318.2	318.7	319.2
115°	374.9	374.4	374.1	373.5	372.8	372.0	371.3	370.5	371.3	372.0	372.8
117.5°	425.9	425.5	425.2	424.8	424.5	424.1	423.8	423.4	423.8	424.1	424.5
120°	461.2	461.0	460.8	460.3	459.3	458.3	457.4	456.4	457.4	458.3	459.3
122.5°	495.0	494.5	494.0	493.6	493.3	492.9	492.6	492.2	492.6	492.9	493.3
125°	546.3	546.1	546.0	545.3	544.2	542.9	541.8	540.7	541.8	542.9	544.2
127.5°	595.7	595.6	595.3	594.9	594.2	593.6	592.9	592.3	592.9	593.6	594.2
130°	628.4	628.1	627.7	627.0	626.0	625.1	624.1	623.2	624.1	625.1	626.0
132.5°	661.0	661.1	661.2	660.4	658.8	657.3	655.7	654.1	655.7	657.3	658.8
135°	708.8	708.6	708.4	707.7	706.5	705.4	704.3	703.2	704.3	705.4	706.5
137.5°	755.3	754.8	754.4	753.6	752.5	751.4	750.3	749.2	750.3	751.4	752.5
140°	784.5	783.9	783.3	782.6	781.6	780.7	779.7	778.8	779.7	780.7	781.6
142.5°	813.8	813.0	812.4	811.6	810.7	809.9	809.2	808.3	809.2	809.9	810.7
145°	856.7	856.2	855.6	854.9	854.1	853.3	852.6	851.9	852.6	853.3	854.1
147.5°	895.1	894.7	894.2	893.7	893.4	892.9	892.5	892.1	892.5	892.9	893.4
150°	920.0	919.2	918.4	918.2	918.3	918.5	918.7	918.9	918.7	918.5	918.3
152.5°	942.9	942.5	942.3	941.9	941.7	941.4	941.2	940.9	941.2	941.4	941.7
155°	975.3	975.1	974.8	974.7	974.7	974.7	974.7	974.7	974.7	974.7	974.7
157.5°	1003.6	1003.4	1003.2	1003.3	1003.8	1004.2	1004.6	1005.0	1004.6	1004.2	1003.8
160°	1020.8	1020.6	1020.5	1020.6	1021.1	1021.7	1022.4	1022.9	1022.4	1021.7	1021.1
162.5°	1036.9	1036.9	1036.8	1037.1	1037.4	1037.8	1038.3	1038.7	1038.3	1037.8	1037.4
165°	1058.6	1058.4	1058.3	1058.3	1058.7	1059.1	1059.5	1059.9	1059.5	1059.1	1058.7
167.5°	1074.3	1074.3	1074.3	1074.7	1075.5	1076.2	1076.9	1077.7	1076.9	1076.2	1075.5
170°	1083.9	1083.9	1083.9	1084.3	1085.1	1085.8	1086.6	1087.4	1086.6	1085.8	1085.1
172.5°	1090.8	1090.8	1090.8	1091.2	1091.9	1092.7	1093.5	1094.2	1093.5	1092.7	1091.9
175°	1098.5	1098.5	1098.5	1098.9	1099.7	1100.4	1101.2	1102.0	1101.2	1100.4	1099.7
177.5°	1102.8	1102.9	1103.1	1103.5	1104.1	1104.7	1105.4	1106.0	1105.4	1104.7	1104.1
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1070.8	1065.8	1062.2	1055.1	1050.1	1047.9	1044.0	1042.9	1046.9	1044.0	1043.6
5°	1039.0	1026.1	1015.7	1005.5	994.3	987.1	976.4	974.7	971.9	967.9	967.0
7.5°	1000.8	984.0	970.7	953.7	938.9	927.0	913.6	907.3	903.8	898.6	891.7
10°	975.1	954.9	937.0	920.1	901.7	887.0	873.6	863.3	856.6	850.3	847.7
12.5°	949.7	929.2	906.3	885.7	865.3	848.7	833.9	827.2	819.8	812.4	806.2
15°	910.2	883.0	857.9	834.2	816.8	798.9	784.6	774.8	763.6	760.4	748.4
17.5°	868.4	841.6	812.4	787.4	767.2	747.5	731.8	720.6	712.2	700.7	695.1
20°	842.3	810.5	782.0	759.1	736.8	713.5	697.4	688.0	680.0	670.6	666.2
22.5°	814.4	783.3	754.1	727.3	704.6	681.7	670.3	660.5	651.3	642.7	636.8
25°	773.4	742.2	711.3	683.5	659.9	643.3	629.9	618.7	613.8	605.4	599.1
27.5°	733.0	699.6	667.6	640.1	621.5	605.1	594.1	585.2	576.4	568.9	563.5
30°	706.8	672.9	638.0	616.0	596.4	580.7	568.7	560.2	553.5	546.7	542.8
32.5°	680.7	645.7	614.8	591.0	572.4	559.0	546.5	538.4	531.3	523.9	519.2
35°	638.9	603.1	578.1	554.8	536.5	524.0	515.5	503.9	498.0	492.7	487.8
37.5°	599.9	566.7	539.6	519.3	503.3	490.9	479.9	473.6	466.5	461.7	457.5
40°	571.4	541.0	516.3	494.9	483.3	469.4	459.2	451.1	445.7	439.5	435.0
42.5°	545.6	517.4	493.4	474.2	459.7	448.0	438.1	430.0	423.2	418.7	415.0
45°	509.2	481.0	457.8	439.9	426.5	415.3	405.0	401.1	392.1	386.8	385.0
47.5°	471.6	446.3	424.0	407.4	393.7	383.1	373.5	365.2	360.3	355.1	352.2
50°	446.2	422.1	401.1	385.0	371.5	359.9	350.9	345.6	338.9	334.0	330.4
52.5°	420.8	398.5	377.5	362.1	350.4	338.8	328.8	323.4	317.1	313.9	311.4
55°	384.5	360.8	342.9	327.7	315.6	304.9	295.5	290.2	286.1	283.0	282.1
57.5°	343.4	324.6	308.0	294.3	281.7	271.6	263.4	258.3	254.8	254.3	251.6
60°	316.5	299.5	284.3	269.6	258.8	249.4	242.3	236.5	232.9	232.5	231.6
62.5°	289.7	273.5	259.3	246.3	236.7	227.6	220.8	214.3	212.2	209.9	208.0
65°	249.9	235.1	223.5	213.3	202.9	195.4	188.6	184.6	179.7	177.0	172.1
67.5°	210.9	199.4	188.2	179.5	171.5	164.3	158.7	152.7	149.4	147.2	143.7
70°	185.1	176.2	165.0	155.6	149.3	143.5	139.1	132.3	130.1	128.3	126.5
72.5°	160.7	152.9	143.5	136.0	129.7	124.2	119.0	115.9	113.7	111.8	110.8
75°	126.5	118.9	110.9	105.5	101.1	96.6	93.8	91.6	90.7	90.3	88.5
77.5°	92.9	88.9	82.4	78.2	75.2	73.4	71.0	69.8	69.7	67.8	67.2
80°	71.1	68.9	63.5	61.7	59.5	57.7	56.3	54.1	51.8	51.0	49.6
82.5°	52.9	50.6	48.5	45.6	43.7	42.6	41.3	40.5	40.8	39.5	38.9
85°	28.2	25.9	25.1	24.6	23.7	24.6	24.1	23.7	23.2	22.8	23.2
87.5°	10.3	10.6	10.5	11.5	10.7	11.4	11.5	11.4	11.5	11.7	11.5
90°	7.0	8.4	9.7	11.1	12.4	13.8	14.7	15.7	16.6	17.6	18.3
92.5°	25.1	26.4	28.1	29.7	31.3	33.0	34.3	35.6	36.8	38.1	38.9
95°	57.4	58.5	60.4	62.3	64.3	66.2	67.5	68.9	70.2	71.5	72.4
97.5°	93.4	94.9	97.5	100.1	102.7	105.4	106.7	107.9	109.2	110.5	111.2
100°	120.4	121.6	124.1	126.6	129.1	131.5	133.2	134.9	136.6	138.4	139.5
102.5°	153.0	153.9	155.2	156.5	157.7	159.0	160.9	162.7	164.6	166.5	167.7
105°	199.8	200.9	202.0	203.1	204.3	205.4	206.6	207.8	208.9	210.0	210.9
107.5°	250.7	251.6	252.4	253.4	254.3	255.1	255.7	256.2	256.8	257.4	257.7
110°	285.8	286.5	287.1	287.7	288.3	288.8	289.4	290.0	290.5	291.1	291.3



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	319.7	320.3	321.1	321.8	322.4	323.2	323.5	323.7	324.0	324.3	324.3
115°	373.5	374.1	374.4	374.9	375.2	375.7	375.5	375.2	375.1	374.9	374.7
117.5°	424.8	425.2	425.5	425.9	426.2	426.5	426.7	426.8	427.0	427.1	426.8
120°	460.3	460.8	461.0	461.2	461.4	461.6	461.6	461.6	461.6	461.6	461.2
122.5°	493.6	494.0	494.5	495.0	495.5	495.9	495.8	495.7	495.5	495.3	495.0
125°	545.3	546.0	546.1	546.3	546.5	546.7	546.3	546.0	545.5	545.2	544.8
127.5°	594.9	595.3	595.6	595.7	596.0	596.2	596.0	595.8	595.6	595.5	595.1
130°	627.0	627.7	628.1	628.4	628.8	629.2	629.0	628.8	628.6	628.4	628.2
132.5°	660.4	661.2	661.1	661.0	660.9	660.8	660.6	660.5	660.3	660.0	659.7
135°	707.7	708.4	708.6	708.8	708.9	709.1	709.1	709.1	709.1	709.1	708.8
137.5°	753.6	754.4	754.8	755.3	755.7	756.0	756.3	756.6	756.7	757.0	756.6
140°	782.6	783.3	783.9	784.5	785.1	785.7	786.0	786.4	786.8	787.2	786.9
142.5°	811.6	812.4	813.0	813.8	814.5	815.2	815.5	815.7	815.9	816.1	815.8
145°	854.9	855.6	856.2	856.7	857.3	857.9	857.9	857.9	857.9	857.9	857.6
147.5°	893.7	894.2	894.7	895.1	895.5	896.0	896.5	896.9	897.4	897.9	897.4
150°	918.2	918.4	919.2	920.0	920.7	921.4	921.4	921.4	921.4	921.4	921.3
152.5°	941.9	942.3	942.5	942.9	943.1	943.5	943.9	944.4	944.9	945.3	945.2
155°	974.7	974.8	975.1	975.3	975.4	975.6	976.4	977.1	977.9	978.7	978.6
157.5°	1003.3	1003.2	1003.4	1003.6	1003.8	1004.0	1004.8	1005.5	1006.3	1007.0	1006.8
160°	1020.6	1020.5	1020.6	1020.8	1021.0	1021.1	1021.9	1022.7	1023.5	1024.2	1024.2
162.5°	1037.1	1036.8	1036.9	1036.9	1037.0	1037.0	1037.9	1038.8	1039.7	1040.7	1040.6
165°	1058.3	1058.3	1058.4	1058.6	1058.8	1059.0	1059.8	1060.5	1061.3	1062.0	1061.9
167.5°	1074.7	1074.3	1074.3	1074.3	1074.3	1074.3	1075.5	1076.6	1077.7	1078.9	1078.8
170°	1084.3	1083.9	1083.9	1083.9	1083.9	1083.9	1085.1	1086.2	1087.4	1088.5	1088.4
172.5°	1091.2	1090.8	1090.8	1090.8	1090.8	1090.8	1091.9	1093.1	1094.2	1095.4	1095.4
175°	1098.9	1098.5	1098.5	1098.5	1098.5	1098.5	1099.7	1100.9	1102.0	1103.1	1103.0
177.5°	1103.5	1103.1	1102.9	1102.8	1102.7	1102.5	1103.5	1104.3	1105.3	1106.1	1106.1
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1043.3	1039.4	1038.3	1039.7	1038.3	1039.4	1043.3	1043.6	1044.0	1046.9	1042.9
5°	962.5	958.1	960.3	959.4	960.3	958.1	962.5	967.0	967.9	971.9	974.7
7.5°	891.6	886.0	880.1	882.0	880.1	886.0	891.6	891.7	898.6	903.8	907.3
10°	841.8	837.4	834.7	836.9	834.7	837.4	841.8	847.7	850.3	856.6	863.3
12.5°	800.0	797.3	795.0	794.0	795.0	797.3	800.0	806.2	812.4	819.8	827.2
15°	743.0	737.7	735.5	729.6	735.5	737.7	743.0	748.4	760.4	763.6	774.8
17.5°	690.5	688.8	682.9	680.4	682.9	688.8	690.5	695.1	700.7	712.2	720.6
20°	659.4	657.6	651.9	655.4	651.9	657.6	659.4	666.2	670.6	680.0	688.0
22.5°	633.7	629.7	627.8	626.8	627.8	629.7	633.7	636.8	642.7	651.3	660.5
25°	597.3	591.5	589.3	586.6	589.3	591.5	597.3	599.1	605.4	613.8	618.7
27.5°	561.0	557.8	554.9	554.2	554.9	557.8	561.0	563.5	568.9	576.4	585.2
30°	537.4	534.3	532.0	532.0	532.0	534.3	537.4	542.8	546.7	553.5	560.2
32.5°	516.3	513.8	511.6	511.3	511.6	513.8	516.3	519.2	523.9	531.3	538.4
35°	485.5	482.0	481.0	478.4	481.0	482.0	485.5	487.8	492.7	498.0	503.9
37.5°	453.6	450.6	450.6	450.3	450.6	450.6	453.6	457.5	461.7	466.5	473.6
40°	433.3	431.0	430.5	427.4	430.5	431.0	433.3	435.0	439.5	445.7	451.1
42.5°	411.4	410.3	408.7	407.3	408.7	410.3	411.4	415.0	418.7	423.2	430.0
45°	381.8	378.7	378.7	376.4	378.7	378.7	381.8	385.0	386.8	392.1	401.1
47.5°	351.2	348.8	349.0	346.7	349.0	348.8	351.2	352.2	355.1	360.3	365.2
50°	330.8	329.5	329.1	328.1	329.1	329.5	330.8	330.4	334.0	338.9	345.6
52.5°	310.5	309.8	311.5	309.5	311.5	309.8	310.5	311.4	313.9	317.1	323.4
55°	283.0	281.6	284.3	281.6	284.3	281.6	283.0	282.1	283.0	286.1	290.2
57.5°	251.4	250.2	252.6	251.2	252.6	250.2	251.4	251.6	254.3	254.8	258.3
60°	230.7	228.0	229.4	229.8	229.4	228.0	230.7	231.6	232.5	232.9	236.5
62.5°	206.0	204.4	205.3	203.4	205.3	204.4	206.0	208.0	209.9	212.2	214.3
65°	171.3	169.9	168.1	167.2	168.1	169.9	171.3	172.1	177.0	179.7	184.6
67.5°	143.9	140.7	140.6	141.3	140.6	140.7	143.9	143.7	147.2	149.4	152.7
70°	123.8	123.8	123.4	123.4	123.4	123.8	123.8	126.5	128.3	130.1	132.3
72.5°	109.9	109.5	108.7	108.4	108.7	109.5	109.9	110.8	111.8	113.7	115.9
75°	88.5	88.9	88.1	87.6	88.1	88.9	88.5	88.5	90.3	90.7	91.6
77.5°	65.3	63.5	64.5	63.5	64.5	63.5	65.3	67.2	67.8	69.7	69.8
80°	49.6	49.2	50.5	49.2	50.5	49.2	49.6	49.6	51.0	51.8	54.1
82.5°	39.3	38.8	39.4	38.5	39.4	38.8	39.3	38.9	39.5	40.8	40.5
85°	23.7	23.2	22.8	23.2	22.8	23.2	23.7	23.2	22.8	23.2	23.7
87.5°	12.0	11.8	11.9	12.0	11.9	11.8	12.0	11.5	11.7	11.5	11.4
90°	18.9	19.5	20.1	20.7	20.1	19.5	18.9	18.3	17.6	16.6	15.7
92.5°	39.3	39.7	40.1	40.6	40.1	39.7	39.3	38.9	38.1	36.8	35.6
95°	72.8	73.2	73.5	74.0	73.5	73.2	72.8	72.4	71.5	70.2	68.9
97.5°	111.4	111.7	111.8	112.1	111.8	111.7	111.4	111.2	110.5	109.2	107.9
100°	139.8	140.2	140.6	140.9	140.6	140.2	139.8	139.5	138.4	136.6	134.9
102.5°	168.2	168.8	169.4	169.9	169.4	168.8	168.2	167.7	166.5	164.6	162.7
105°	211.5	212.1	212.6	213.2	212.6	212.1	211.5	210.9	210.0	208.9	207.8
107.5°	257.6	257.6	257.6	257.5	257.6	257.6	257.6	257.7	257.4	256.8	256.2
110°	291.1	290.9	290.8	290.5	290.8	290.9	291.1	291.3	291.1	290.5	290.0



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	323.9	323.6	323.2	322.9	323.2	323.6	323.9	324.3	324.3	324.0	323.7
115°	374.4	374.3	374.1	373.9	374.1	374.3	374.4	374.7	374.9	375.1	375.2
117.5°	426.0	425.3	424.6	423.8	424.6	425.3	426.0	426.8	427.1	427.0	426.8
120°	460.5	459.7	458.9	458.1	458.9	459.7	460.5	461.2	461.6	461.6	461.6
122.5°	494.4	493.8	493.2	492.6	493.2	493.8	494.4	495.0	495.3	495.5	495.7
125°	544.7	544.5	544.3	544.2	544.3	544.5	544.7	544.8	545.2	545.5	546.0
127.5°	594.8	594.3	594.0	593.7	594.0	594.3	594.8	595.1	595.5	595.6	595.8
130°	627.8	627.4	627.0	626.6	627.0	627.4	627.8	628.2	628.4	628.6	628.8
132.5°	659.2	658.7	658.1	657.5	658.1	658.7	659.2	659.7	660.0	660.3	660.5
135°	708.0	707.2	706.5	705.7	706.5	707.2	708.0	708.8	709.1	709.1	709.1
137.5°	755.7	754.8	753.8	752.9	753.8	754.8	755.7	756.6	757.0	756.7	756.6
140°	785.9	785.0	784.0	783.1	784.0	785.0	785.9	786.9	787.2	786.8	786.4
142.5°	814.9	813.9	813.0	811.9	813.0	813.9	814.9	815.8	816.1	815.9	815.7
145°	857.0	856.4	855.8	855.3	855.8	856.4	857.0	857.6	857.9	857.9	857.9
147.5°	896.1	894.8	893.5	892.3	893.5	894.8	896.1	897.4	897.9	897.4	896.9
150°	920.9	920.5	920.2	919.7	920.2	920.5	920.9	921.3	921.4	921.4	921.4
152.5°	944.5	943.8	943.1	942.5	943.1	943.8	944.5	945.2	945.3	944.9	944.4
155°	977.7	976.6	975.7	974.7	975.7	976.6	977.7	978.6	978.7	977.9	977.1
157.5°	1005.6	1004.3	1003.0	1001.8	1003.0	1004.3	1005.6	1006.8	1007.0	1006.3	1005.5
160°	1023.2	1022.3	1021.3	1020.3	1021.3	1022.3	1023.2	1024.2	1024.2	1023.5	1022.7
162.5°	1039.5	1038.4	1037.2	1036.1	1037.2	1038.4	1039.5	1040.6	1040.7	1039.7	1038.8
165°	1060.8	1059.5	1058.4	1057.3	1058.4	1059.5	1060.8	1061.9	1062.0	1061.3	1060.5
167.5°	1077.7	1076.5	1075.3	1074.1	1075.3	1076.5	1077.7	1078.8	1078.9	1077.7	1076.6
170°	1087.1	1085.7	1084.4	1083.1	1084.4	1085.7	1087.1	1088.4	1088.5	1087.4	1086.2
172.5°	1094.2	1093.0	1091.8	1090.6	1091.8	1093.0	1094.2	1095.4	1095.4	1094.2	1093.1
175°	1101.7	1100.4	1099.0	1097.7	1099.0	1100.4	1101.7	1103.0	1103.1	1102.0	1100.9
177.5°	1105.0	1104.0	1102.9	1101.8	1102.9	1104.0	1105.0	1106.1	1106.1	1105.3	1104.3
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1044.0	1047.9	1050.1	1055.1	1062.2	1065.8	1070.8	1074.4	1079.4	1085.5	1090.5
5°	976.4	987.1	994.3	1005.5	1015.7	1026.1	1039.0	1048.4	1060.9	1075.2	1086.4
7.5°	913.6	927.0	938.9	953.7	970.7	984.0	1000.8	1018.0	1037.7	1058.0	1077.1
10°	873.6	887.0	901.7	920.1	937.0	954.9	975.1	995.1	1019.8	1042.6	1068.5
12.5°	833.9	848.7	865.3	885.7	906.3	929.2	949.7	972.3	998.7	1028.3	1056.0
15°	784.6	798.9	816.8	834.2	857.9	883.0	910.2	940.2	969.7	1002.8	1037.2
17.5°	731.8	747.5	767.2	787.4	812.4	841.6	868.4	901.2	934.4	972.9	1013.4
20°	697.4	713.5	736.8	759.1	782.0	810.5	842.3	875.8	911.1	951.8	997.0
22.5°	670.3	681.7	704.6	727.3	754.1	783.3	814.4	849.4	887.9	930.0	977.3
25°	629.9	643.3	659.9	683.5	711.3	742.2	773.4	810.5	852.6	895.5	946.0
27.5°	594.1	605.1	621.5	640.1	667.6	699.6	733.0	771.6	814.8	858.5	911.5
30°	568.7	580.7	596.4	616.0	638.0	672.9	706.8	744.9	788.7	833.8	888.3
32.5°	546.5	559.0	572.4	591.0	614.8	645.7	680.7	718.0	762.5	809.1	862.2
35°	515.5	524.0	536.5	554.8	578.1	603.1	638.9	678.2	721.6	769.8	823.0
37.5°	479.9	490.9	503.3	519.3	539.6	566.7	599.9	639.7	680.0	726.3	774.8
40°	459.2	469.4	483.3	494.9	516.3	541.0	571.4	612.9	653.2	696.5	740.8
42.5°	438.1	448.0	459.7	474.2	493.4	517.4	545.6	584.4	627.4	668.3	705.4
45°	405.0	415.3	426.5	439.9	457.8	481.0	509.2	544.5	582.1	619.7	647.8
47.5°	373.5	383.1	393.7	407.4	424.0	446.3	471.6	502.7	539.2	571.2	591.3
50°	350.9	359.9	371.5	385.0	401.1	422.1	446.2	477.0	507.4	536.5	554.8
52.5°	328.8	338.8	350.4	362.1	377.5	398.5	420.8	447.4	476.3	500.0	515.1
55°	295.5	304.9	315.6	327.7	342.9	360.8	384.5	405.5	428.3	448.4	457.4
57.5°	263.4	271.6	281.7	294.3	308.0	324.6	343.4	363.6	379.6	393.9	404.0
60°	242.3	249.4	258.8	269.6	284.3	299.5	316.5	335.3	347.8	359.9	369.3
62.5°	220.8	227.6	236.7	246.3	259.3	273.5	289.7	304.9	317.1	325.2	336.0
65°	188.6	195.4	202.9	213.3	223.5	235.1	249.9	261.1	269.6	278.5	285.2
67.5°	158.7	164.3	171.5	179.5	188.2	199.4	210.9	220.2	225.9	231.4	239.4
70°	139.1	143.5	149.3	155.6	165.0	176.2	185.1	192.3	196.3	201.6	211.5
72.5°	119.0	124.2	129.7	136.0	143.5	152.9	160.7	167.9	170.5	174.8	181.1
75°	93.8	96.6	101.1	105.5	110.9	118.9	126.5	128.3	130.5	134.1	138.6
77.5°	71.0	73.4	75.2	78.2	82.4	88.9	92.9	95.6	96.1	97.5	101.9
80°	56.3	57.7	59.5	61.7	63.5	68.9	71.1	73.8	74.6	76.0	78.3
82.5°	41.3	42.6	43.7	45.6	48.5	50.6	52.9	55.5	55.7	56.7	57.2
85°	24.1	24.6	23.7	24.6	25.1	25.9	28.2	30.4	30.0	29.5	30.8
87.5°	11.5	11.4	10.7	11.5	10.5	10.6	10.3	10.4	10.8	11.2	11.6
90°	14.7	13.8	12.4	11.1	9.7	8.4	7.0	5.4	3.9	2.4	0.9
92.5°	34.3	33.0	31.3	29.7	28.1	26.4	25.1	24.0	22.9	21.9	20.8
95°	67.5	66.2	64.3	62.3	60.4	58.5	57.4	57.0	56.7	56.2	55.9
97.5°	106.7	105.4	102.7	100.1	97.5	94.9	93.4	93.3	93.2	93.0	92.8
100°	133.2	131.5	129.1	126.6	124.1	121.6	120.4	120.4	120.4	120.4	120.4
102.5°	160.9	159.0	157.7	156.5	155.2	153.9	153.0	152.2	151.4	150.7	149.9
105°	206.6	205.4	204.3	203.1	202.0	200.9	199.8	198.9	197.9	196.9	196.0
107.5°	255.7	255.1	254.3	253.4	252.4	251.6	250.7	249.8	248.7	247.8	246.8
110°	289.4	288.8	288.3	287.7	287.1	286.5	285.8	284.8	283.9	282.9	282.0



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	323.5	323.2	322.4	321.8	321.1	320.3	319.7	319.2	318.7	318.2	317.7
115°	375.5	375.7	375.2	374.9	374.4	374.1	373.5	372.8	372.0	371.3	370.5
117.5°	426.7	426.5	426.2	425.9	425.5	425.2	424.8	424.5	424.1	423.8	423.4
120°	461.6	461.6	461.4	461.2	461.0	460.8	460.3	459.3	458.3	457.4	456.4
122.5°	495.8	495.9	495.5	495.0	494.5	494.0	493.6	493.3	492.9	492.6	492.2
125°	546.3	546.7	546.5	546.3	546.1	546.0	545.3	544.2	542.9	541.8	540.7
127.5°	596.0	596.2	596.0	595.7	595.6	595.3	594.9	594.2	593.6	592.9	592.3
130°	629.0	629.2	628.8	628.4	628.1	627.7	627.0	626.0	625.1	624.1	623.2
132.5°	660.6	660.8	660.9	661.0	661.1	661.2	660.4	658.8	657.3	655.7	654.1
135°	709.1	709.1	708.9	708.8	708.6	708.4	707.7	706.5	705.4	704.3	703.2
137.5°	756.3	756.0	755.7	755.3	754.8	754.4	753.6	752.5	751.4	750.3	749.2
140°	786.0	785.7	785.1	784.5	783.9	783.3	782.6	781.6	780.7	779.7	778.8
142.5°	815.5	815.2	814.5	813.8	813.0	812.4	811.6	810.7	809.9	809.2	808.3
145°	857.9	857.9	857.3	856.7	856.2	855.6	854.9	854.1	853.3	852.6	851.9
147.5°	896.5	896.0	895.5	895.1	894.7	894.2	893.7	893.4	892.9	892.5	892.1
150°	921.4	921.4	920.7	920.0	919.2	918.4	918.2	918.3	918.5	918.7	918.9
152.5°	943.9	943.5	943.1	942.9	942.5	942.3	941.9	941.7	941.4	941.2	940.9
155°	976.4	975.6	975.4	975.3	975.1	974.8	974.7	974.7	974.7	974.7	974.7
157.5°	1004.8	1004.0	1003.8	1003.6	1003.4	1003.2	1003.3	1003.8	1004.2	1004.6	1005.0
160°	1021.9	1021.1	1021.0	1020.8	1020.6	1020.5	1020.6	1021.1	1021.7	1022.4	1022.9
162.5°	1037.9	1037.0	1037.0	1036.9	1036.9	1036.8	1037.1	1037.4	1037.8	1038.3	1038.7
165°	1059.8	1059.0	1058.8	1058.6	1058.4	1058.3	1058.3	1058.7	1059.1	1059.5	1059.9
167.5°	1075.5	1074.3	1074.3	1074.3	1074.3	1074.3	1074.7	1075.5	1076.2	1076.9	1077.7
170°	1085.1	1083.9	1083.9	1083.9	1083.9	1083.9	1084.3	1085.1	1085.8	1086.6	1087.4
172.5°	1091.9	1090.8	1090.8	1090.8	1090.8	1090.8	1091.2	1091.9	1092.7	1093.5	1094.2
175°	1099.7	1098.5	1098.5	1098.5	1098.5	1098.5	1098.9	1099.7	1100.4	1101.2	1102.0
177.5°	1103.5	1102.5	1102.7	1102.8	1102.9	1103.1	1103.5	1104.1	1104.7	1105.4	1106.0
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1094.4	1097.7	1102.3	1107.7	1112.0	1116.6	1119.1	1119.1	1121.3	1125.9	1132.0
5°	1097.6	1109.2	1120.3	1134.7	1145.8	1158.8	1168.6	1178.0	1186.5	1197.2	1208.4
7.5°	1096.7	1115.9	1136.1	1158.6	1183.5	1203.2	1223.6	1239.5	1255.2	1275.7	1291.9
10°	1093.1	1118.1	1145.4	1174.0	1205.3	1232.6	1257.1	1279.5	1301.0	1323.4	1343.4
12.5°	1086.7	1118.5	1151.8	1186.2	1225.7	1256.9	1288.7	1312.4	1337.5	1361.9	1386.7
15°	1077.0	1114.6	1154.8	1202.6	1250.9	1285.8	1317.1	1347.9	1371.1	1398.9	1422.6
17.5°	1057.0	1105.4	1156.1	1208.3	1254.7	1295.3	1328.1	1357.4	1382.2	1412.6	1444.8
20°	1045.3	1097.6	1150.3	1206.2	1250.4	1292.0	1323.8	1354.2	1385.0	1424.8	1464.1
22.5°	1028.8	1084.7	1140.7	1193.7	1240.4	1280.6	1313.4	1350.7	1391.1	1436.2	1483.8
25°	1002.8	1060.5	1115.9	1166.4	1212.0	1253.2	1297.9	1347.9	1397.1	1456.6	1525.0
27.5°	969.8	1025.4	1074.9	1128.3	1173.5	1225.9	1281.7	1335.9	1406.9	1488.7	1574.1
30°	945.1	997.9	1044.8	1095.4	1146.8	1204.5	1267.0	1330.9	1415.4	1511.6	1613.1
32.5°	916.5	964.2	1010.8	1059.5	1118.9	1182.2	1248.8	1327.0	1428.0	1537.3	1642.4
35°	866.9	909.8	954.9	1009.0	1072.1	1140.9	1225.9	1321.1	1443.1	1560.7	1655.1
37.5°	814.9	848.7	894.1	951.1	1019.8	1099.4	1195.8	1311.6	1436.9	1542.4	1582.5
40°	774.8	806.5	854.4	914.3	982.2	1069.4	1177.6	1296.5	1422.6	1495.9	1492.8
42.5°	735.0	767.2	813.2	873.5	944.3	1041.9	1153.3	1276.9	1383.3	1411.2	1353.0
45°	674.2	704.1	749.3	810.1	886.1	988.5	1105.6	1224.1	1292.0	1246.9	1131.5
47.5°	612.2	641.2	683.1	742.7	825.6	932.8	1043.5	1140.7	1150.3	1053.3	915.0
50°	571.4	598.7	638.4	701.9	782.4	887.0	993.9	1070.3	1046.6	928.2	785.5
52.5°	531.7	557.8	595.1	655.0	737.3	839.8	935.2	995.1	940.4	814.4	686.0
55°	473.0	498.0	535.6	590.6	665.2	759.1	842.7	864.6	784.2	657.2	553.5
57.5°	417.3	435.7	472.8	521.3	593.3	676.1	736.1	732.1	643.3	529.0	454.6
60°	380.5	397.0	432.3	477.0	545.4	619.7	661.7	643.8	553.9	459.6	388.1
62.5°	346.1	361.6	391.2	432.3	491.0	555.6	586.2	561.5	476.6	393.8	336.9
65°	294.2	305.3	329.1	367.0	413.1	457.8	485.1	448.8	373.8	311.2	268.2
67.5°	245.6	255.3	276.4	303.7	335.4	366.3	377.3	343.4	285.0	242.8	212.6
70°	214.1	223.1	237.4	262.9	283.9	305.8	311.2	280.8	232.0	199.8	181.1
72.5°	184.1	192.3	204.8	222.8	237.4	250.0	252.5	224.3	186.9	164.8	150.3
75°	140.3	147.6	155.6	162.3	171.7	173.9	173.0	151.1	131.0	116.2	108.2
77.5°	103.1	106.2	111.1	113.7	114.2	114.0	109.4	95.6	85.2	79.1	75.9
80°	79.6	81.8	83.2	84.0	84.5	80.0	75.1	66.6	63.0	59.5	55.4
82.5°	57.8	59.3	60.6	60.8	58.4	54.7	50.1	45.9	43.4	41.6	40.0
85°	31.3	31.8	31.3	29.1	25.9	24.6	23.7	22.8	22.4	21.9	21.9
87.5°	11.5	10.8	9.3	10.0	10.2	10.2	10.4	10.3	10.2	10.4	10.7
90°	2.4	3.9	5.4	7.0	8.4	9.7	11.1	12.4	13.8	14.7	15.7
92.5°	21.9	22.9	24.0	25.1	26.4	28.1	29.7	31.3	33.0	34.3	35.6
95°	56.2	56.7	57.0	57.4	58.5	60.4	62.3	64.3	66.2	67.5	68.9
97.5°	93.0	93.2	93.3	93.4	94.9	97.5	100.1	102.7	105.4	106.7	107.9
100°	120.4	120.4	120.4	120.4	121.6	124.1	126.6	129.1	131.5	133.2	134.9
102.5°	150.7	151.4	152.2	153.0	153.9	155.2	156.5	157.7	159.0	160.9	162.7
105°	196.9	197.9	198.9	199.8	200.9	202.0	203.1	204.3	205.4	206.6	207.8
107.5°	247.8	248.7	249.8	250.7	251.6	252.4	253.4	254.3	255.1	255.7	256.2
110°	282.9	283.9	284.8	285.8	286.5	287.1	287.7	288.3	288.8	289.4	290.0



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	318.2	318.7	319.2	319.7	320.3	321.1	321.8	322.4	323.2	323.5	323.7
115°	371.3	372.0	372.8	373.5	374.1	374.4	374.9	375.2	375.7	375.5	375.2
117.5°	423.8	424.1	424.5	424.8	425.2	425.5	425.9	426.2	426.5	426.7	426.8
120°	457.4	458.3	459.3	460.3	460.8	461.0	461.2	461.4	461.6	461.6	461.6
122.5°	492.6	492.9	493.3	493.6	494.0	494.5	495.0	495.5	495.9	495.8	495.7
125°	541.8	542.9	544.2	545.3	546.0	546.1	546.3	546.5	546.7	546.3	546.0
127.5°	592.9	593.6	594.2	594.9	595.3	595.6	595.7	596.0	596.2	596.0	595.8
130°	624.1	625.1	626.0	627.0	627.7	628.1	628.4	628.8	629.2	629.0	628.8
132.5°	655.7	657.3	658.8	660.4	661.2	661.1	661.0	660.9	660.8	660.6	660.5
135°	704.3	705.4	706.5	707.7	708.4	708.6	708.8	708.9	709.1	709.1	709.1
137.5°	750.3	751.4	752.5	753.6	754.4	754.8	755.3	755.7	756.0	756.3	756.6
140°	779.7	780.7	781.6	782.6	783.3	783.9	784.5	785.1	785.7	786.0	786.4
142.5°	809.2	809.9	810.7	811.6	812.4	813.0	813.8	814.5	815.2	815.5	815.7
145°	852.6	853.3	854.1	854.9	855.6	856.2	856.7	857.3	857.9	857.9	857.9
147.5°	892.5	892.9	893.4	893.7	894.2	894.7	895.1	895.5	896.0	896.5	896.9
150°	918.7	918.5	918.3	918.2	918.4	919.2	920.0	920.7	921.4	921.4	921.4
152.5°	941.2	941.4	941.7	941.9	942.3	942.5	942.9	943.1	943.5	943.9	944.4
155°	974.7	974.7	974.7	974.7	974.8	975.1	975.3	975.4	975.6	976.4	977.1
157.5°	1004.6	1004.2	1003.8	1003.3	1003.2	1003.4	1003.6	1003.8	1004.0	1004.8	1005.5
160°	1022.4	1021.7	1021.1	1020.6	1020.5	1020.6	1020.8	1021.0	1021.1	1021.9	1022.7
162.5°	1038.3	1037.8	1037.4	1037.1	1036.8	1036.9	1036.9	1037.0	1037.0	1037.9	1038.8
165°	1059.5	1059.1	1058.7	1058.3	1058.3	1058.4	1058.6	1058.8	1059.0	1059.8	1060.5
167.5°	1076.9	1076.2	1075.5	1074.7	1074.3	1074.3	1074.3	1074.3	1074.3	1075.5	1076.6
170°	1086.6	1085.8	1085.1	1084.3	1083.9	1083.9	1083.9	1083.9	1083.9	1085.1	1086.2
172.5°	1093.5	1092.7	1091.9	1091.2	1090.8	1090.8	1090.8	1090.8	1090.8	1091.9	1093.1
175°	1101.2	1100.4	1099.7	1098.9	1098.5	1098.5	1098.5	1098.5	1098.5	1099.7	1100.9
177.5°	1105.4	1104.7	1104.1	1103.5	1103.1	1102.9	1102.8	1102.7	1102.5	1103.5	1104.3
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1	1089.1
2.5°	1136.6	1136.6	1142.7	1142.4	1146.3	1144.9	1145.6
5°	1221.8	1229.4	1236.1	1240.6	1247.3	1249.1	1248.2
7.5°	1310.2	1327.1	1335.3	1346.6	1348.7	1354.5	1353.9
10°	1364.9	1381.5	1394.0	1403.8	1408.8	1415.0	1415.4
12.5°	1407.8	1421.9	1433.0	1442.1	1448.0	1450.0	1451.2
15°	1441.4	1457.0	1470.0	1482.9	1490.6	1496.3	1499.5
17.5°	1475.2	1499.3	1522.2	1539.8	1550.4	1559.3	1559.2
20°	1501.2	1529.0	1557.6	1577.7	1598.3	1607.2	1608.6
22.5°	1529.1	1571.6	1608.4	1639.6	1666.6	1675.9	1679.4
25°	1587.1	1642.5	1699.4	1743.2	1774.4	1792.8	1795.4
27.5°	1657.1	1732.2	1791.9	1832.3	1858.3	1871.9	1874.8
30°	1706.5	1775.8	1829.5	1859.8	1871.9	1873.7	1867.0
32.5°	1728.6	1780.5	1801.9	1800.1	1776.4	1760.7	1754.6
35°	1701.6	1690.8	1638.5	1576.0	1528.1	1497.7	1489.6
37.5°	1548.5	1456.0	1359.7	1265.2	1214.8	1189.2	1145.2
40°	1397.6	1265.7	1165.5	1086.0	1029.2	983.5	972.8
42.5°	1227.3	1091.1	991.0	922.8	877.5	846.2	832.6
45°	986.3	869.1	786.4	734.1	699.2	676.4	666.2
47.5°	788.8	698.2	637.9	599.2	572.7	552.8	547.3
50°	680.4	608.0	557.1	524.4	504.3	489.1	482.8
52.5°	591.0	532.5	493.4	466.5	447.5	438.0	432.7
55°	487.8	437.2	409.1	387.6	376.9	369.3	365.7
57.5°	398.9	362.4	341.8	327.0	317.1	312.2	310.5
60°	349.1	320.6	301.8	290.2	283.4	277.2	275.4
62.5°	305.1	282.7	268.1	258.0	251.2	248.6	247.5
65°	245.9	231.2	220.4	214.1	208.8	207.9	207.4
67.5°	195.4	186.8	181.2	174.6	172.7	169.6	169.0
70°	167.2	161.4	154.7	152.5	150.2	147.1	147.6
72.5°	141.8	136.0	131.5	128.5	127.7	126.3	127.5
75°	103.8	101.9	100.1	97.9	97.0	97.0	96.6
77.5°	74.0	72.5	70.5	69.2	69.0	67.1	67.8
80°	53.6	51.4	50.5	51.0	49.6	49.2	49.2
82.5°	39.7	38.9	38.0	38.1	37.8	37.4	37.7
85°	21.9	21.4	21.4	21.0	21.0	20.6	20.6
87.5°	11.2	11.7	11.2	10.9	11.0	11.5	12.0
90°	16.6	17.6	18.3	18.9	19.5	20.1	20.7
92.5°	36.8	38.1	38.9	39.3	39.7	40.1	40.6
95°	70.2	71.5	72.4	72.8	73.2	73.5	74.0
97.5°	109.2	110.5	111.2	111.4	111.7	111.8	112.1
100°	136.6	138.4	139.5	139.8	140.2	140.6	140.9
102.5°	164.6	166.5	167.7	168.2	168.8	169.4	169.9
105°	208.9	210.0	210.9	211.5	212.1	212.6	213.2
107.5°	256.8	257.4	257.7	257.6	257.6	257.6	257.5
110°	290.5	291.1	291.3	291.1	290.9	290.8	290.5



TEST NUMBER: P333569-935

CATALOG NUMBER: S125RDIP-S850D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	324.0	324.3	324.3	323.9	323.6	323.2	322.9
115°	375.1	374.9	374.7	374.4	374.3	374.1	373.9
117.5°	427.0	427.1	426.8	426.0	425.3	424.6	423.8
120°	461.6	461.6	461.2	460.5	459.7	458.9	458.1
122.5°	495.5	495.3	495.0	494.4	493.8	493.2	492.6
125°	545.5	545.2	544.8	544.7	544.5	544.3	544.2
127.5°	595.6	595.5	595.1	594.8	594.3	594.0	593.7
130°	628.6	628.4	628.2	627.8	627.4	627.0	626.6
132.5°	660.3	660.0	659.7	659.2	658.7	658.1	657.5
135°	709.1	709.1	708.8	708.0	707.2	706.5	705.7
137.5°	756.7	757.0	756.6	755.7	754.8	753.8	752.9
140°	786.8	787.2	786.9	785.9	785.0	784.0	783.1
142.5°	815.9	816.1	815.8	814.9	813.9	813.0	811.9
145°	857.9	857.9	857.6	857.0	856.4	855.8	855.3
147.5°	897.4	897.9	897.4	896.1	894.8	893.5	892.3
150°	921.4	921.4	921.3	920.9	920.5	920.2	919.7
152.5°	944.9	945.3	945.2	944.5	943.8	943.1	942.5
155°	977.9	978.7	978.6	977.7	976.6	975.7	974.7
157.5°	1006.3	1007.0	1006.8	1005.6	1004.3	1003.0	1001.8
160°	1023.5	1024.2	1024.2	1023.2	1022.3	1021.3	1020.3
162.5°	1039.7	1040.7	1040.6	1039.5	1038.4	1037.2	1036.1
165°	1061.3	1062.0	1061.9	1060.8	1059.5	1058.4	1057.3
167.5°	1077.7	1078.9	1078.8	1077.7	1076.5	1075.3	1074.1
170°	1087.4	1088.5	1088.4	1087.1	1085.7	1084.4	1083.1
172.5°	1094.2	1095.4	1095.4	1094.2	1093.0	1091.8	1090.6
175°	1102.0	1103.1	1103.0	1101.7	1100.4	1099.0	1097.7
177.5°	1105.3	1106.1	1106.1	1105.0	1104.0	1102.9	1101.8
180°	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6	1104.6

(END OF REPORT)