

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333266-840

Luminaire Tested: **S125DIP-S1090D590U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333266-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D590U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6551.4 lumens
Efficiency: N/A
Efficacy: 134.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333266-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333266-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	64	63	62	57
2	93	85	79	73	87	80	75	70	72	67	64	64	61	58	57	54	52	48
3	85	75	67	61	80	71	64	58	63	58	53	57	52	49	50	47	44	41
4	77	66	58	52	73	63	55	50	56	50	46	50	46	42	45	41	38	35
5	71	59	51	44	67	56	48	43	51	44	39	45	40	36	40	36	33	30
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	32	29	27
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26	24
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	28	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11129	11129	11129
5°	11154	11048	11119
10°	11086	10970	11032
15°	10965	10838	10884
20°	10794	10653	10672
25°	10608	10434	10424
30°	10380	10197	10147
35°	10136	9942	9802
40°	9885	9666	9528
45°	9613	9414	9227
50°	9315	9109	8835
55°	9026	8765	8519
60°	8681	8418	8117
65°	8270	8000	7728
70°	7878	7517	7260
75°	7177	6939	6700
80°	6390	6289	6133
85°	5550	5654	5350



TEST NUMBER: P333266-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.5
10°-20°	459.0	7.0
20°-30°	677.7	10.3
30°-40°	790.7	12.1
40°-50°	794.2	12.1
50°-60°	697.1	10.6
60°-70°	519.5	7.9
70°-80°	297.0	4.5
80°-90°	88.0	1.3
90°-100°	49.6	0.8
100°-110°	146.4	2.2
110°-120°	248.0	3.8
120°-130°	326.4	5.0
130°-140°	365.7	5.6
140°-150°	358.4	5.5
150°-160°	301.1	4.6
160°-170°	200.1	3.1
170°-180°	70.0	1.1
0°-30°	1299.1	19.8
0°-40°	2089.8	31.9
0°-60°	3581.2	54.7
0°-90°	4485.6	68.5
90°-120°	444.0	6.8
90°-150°	1494.5	22.8
90°-180°	2066.0	31.5
0°-180°	6551.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1720	1717	1704	1716	1715	163
15°	1640	1635	1621	1627	1628	462
25°	1489	1481	1464	1466	1463	685
35°	1286	1279	1261	1254	1243	804
45°	1052	1046	1031	1015	1010	811
55°	802	797	778	766	757	715
65°	541	538	524	512	506	537
75°	288	285	278	274	268	307
85°	75	76	76	75	72	84
90°	1	5	9	12	14	6
95°	38	39	44	48	50	40
105°	131	134	138	141	143	140
115°	248	250	252	251	251	245
125°	362	366	366	365	365	324
135°	471	474	475	475	473	363
145°	571	573	575	575	573	357
155°	653	653	654	656	653	301
165°	710	709	710	712	709	200
175°	738	736	736	739	736	70
180°	740	740	740	740	740	



TEST NUMBER: P333266-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1727.6	1726.9	1726.1	1725.4	1724.6	1723.0	1720.6	1718.2	1715.8	1713.3	1715.8
5°	1720.5	1719.9	1719.3	1718.7	1718.1	1716.3	1713.2	1710.2	1707.2	1704.1	1706.9
7.5°	1704.7	1704.0	1703.4	1702.8	1702.2	1700.2	1696.9	1693.5	1690.2	1686.9	1689.6
10°	1690.5	1689.9	1689.3	1688.7	1688.1	1686.1	1682.7	1679.4	1676.1	1672.7	1675.2
12.5°	1673.0	1671.9	1670.8	1669.7	1668.7	1666.6	1663.4	1660.4	1657.3	1654.2	1656.2
15°	1640.0	1639.1	1638.2	1637.3	1636.4	1634.3	1630.9	1627.6	1624.3	1620.9	1622.4
17.5°	1602.2	1600.8	1599.4	1598.1	1596.8	1594.4	1590.9	1587.5	1584.1	1580.5	1582.5
20°	1570.5	1569.9	1569.3	1568.7	1568.1	1565.8	1561.9	1557.9	1554.0	1550.0	1552.2
22.5°	1538.8	1537.8	1536.7	1535.6	1534.5	1532.1	1528.4	1524.7	1521.1	1517.3	1518.7
25°	1488.7	1487.2	1485.7	1484.2	1482.7	1480.0	1476.0	1472.1	1468.1	1464.2	1464.8
27.5°	1430.1	1429.2	1428.3	1427.3	1426.4	1424.0	1419.9	1415.8	1411.8	1407.8	1407.9
30°	1391.9	1391.0	1390.1	1389.2	1388.3	1385.5	1381.0	1376.4	1371.9	1367.4	1366.8
32.5°	1350.5	1349.1	1347.7	1346.3	1344.9	1342.2	1338.1	1334.0	1330.0	1326.0	1324.8
35°	1285.6	1284.3	1283.1	1281.9	1280.7	1278.0	1273.7	1269.5	1265.3	1261.0	1259.5
37.5°	1218.2	1216.7	1215.2	1213.7	1212.1	1209.4	1205.4	1201.4	1197.4	1193.5	1191.1
40°	1172.5	1170.9	1169.4	1167.9	1166.4	1163.5	1159.2	1155.0	1150.7	1146.5	1143.8
42.5°	1123.4	1122.1	1120.8	1119.5	1118.2	1115.5	1111.3	1107.0	1102.8	1098.5	1096.0
45°	1052.5	1051.3	1050.1	1048.8	1047.6	1045.2	1041.6	1037.9	1034.3	1030.7	1027.0
47.5°	976.1	976.1	976.2	976.3	976.3	974.2	969.9	965.4	961.1	956.7	953.0
50°	927.1	926.1	925.2	924.3	923.4	921.1	917.5	913.8	910.2	906.6	902.6
52.5°	876.9	876.2	875.6	874.8	874.2	871.9	868.1	864.1	860.3	856.4	852.9
55°	801.6	800.7	799.8	798.9	798.0	795.4	791.1	786.9	782.6	778.4	775.7
57.5°	722.3	721.8	721.3	720.8	720.3	718.3	714.7	711.1	707.6	704.0	700.4
60°	672.1	670.9	669.6	668.4	667.2	665.0	661.7	658.3	655.0	651.7	648.6
62.5°	619.8	618.7	617.8	616.8	615.9	614.0	611.1	608.2	605.4	602.6	599.3
65°	541.2	540.6	540.0	539.4	538.8	536.8	533.5	530.2	526.8	523.5	520.8
67.5°	465.1	463.8	462.6	461.3	460.1	458.2	455.7	453.2	450.7	448.3	446.0
70°	417.2	415.7	414.1	412.6	411.1	409.0	406.3	403.5	400.8	398.1	396.3
72.5°	364.9	363.8	362.7	361.7	360.7	359.3	357.6	355.8	354.1	352.2	350.2
75°	287.6	287.0	286.4	285.8	285.2	284.2	282.7	281.1	279.6	278.1	277.2
77.5°	216.5	216.2	216.0	215.8	215.5	215.0	214.1	213.3	212.5	211.6	211.1
80°	171.8	171.8	171.8	171.8	171.8	171.5	170.9	170.3	169.7	169.1	168.7
82.5°	132.5	132.0	131.6	131.1	130.6	130.3	130.2	130.1	129.9	129.8	129.3
85°	74.9	75.2	75.5	75.8	76.1	76.3	76.3	76.3	76.3	76.3	76.0
87.5°	29.6	29.8	30.0	30.2	30.4	30.5	30.4	30.3	30.3	30.2	30.3
90°	0.6	1.6	2.6	3.6	4.6	5.7	6.6	7.5	8.3	9.2	9.9
92.5°	13.9	14.6	15.3	16.1	16.8	17.7	18.8	19.9	21.0	22.1	22.9
95°	37.5	37.7	38.0	38.2	38.5	39.3	40.5	41.8	43.1	44.3	45.2
97.5°	62.2	62.3	62.4	62.5	62.6	63.5	65.3	67.1	68.9	70.6	71.5
100°	80.7	80.7	80.7	80.7	80.7	81.5	83.1	84.8	86.4	88.2	89.3
102.5°	100.5	101.0	101.5	102.0	102.5	103.2	104.0	104.9	105.7	106.5	107.9
105°	131.4	132.0	132.6	133.3	133.9	134.6	135.4	136.1	136.9	137.6	138.5
107.5°	165.4	166.1	166.7	167.3	168.0	168.6	169.3	169.8	170.4	171.0	171.4
110°	188.9	189.6	190.3	190.9	191.6	192.1	192.4	192.8	193.2	193.6	194.0



TEST NUMBER: P333266-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	212.9	213.3	213.6	213.9	214.3	214.7	215.2	215.6	216.1	216.6	216.8
115°	248.3	248.8	249.3	249.8	250.3	250.7	251.0	251.3	251.5	251.8	251.7
117.5°	283.8	284.0	284.3	284.5	284.7	285.0	285.2	285.4	285.6	285.9	286.0
120°	305.9	306.6	307.2	307.8	308.5	308.8	309.0	309.1	309.2	309.3	309.3
122.5°	329.9	330.1	330.3	330.5	330.8	331.0	331.4	331.7	332.0	332.4	332.3
125°	362.3	363.1	363.9	364.7	365.5	365.9	366.0	366.2	366.3	366.4	366.2
127.5°	397.0	397.4	397.8	398.2	398.7	399.0	399.1	399.3	399.4	399.6	399.5
130°	417.7	418.3	419.0	419.6	420.2	420.7	420.9	421.2	421.4	421.7	421.6
132.5°	438.4	439.5	440.5	441.5	442.6	443.1	443.0	443.0	442.9	442.9	442.8
135°	471.2	472.0	472.8	473.5	474.3	474.7	474.9	475.0	475.1	475.2	475.2
137.5°	502.1	502.9	503.6	504.3	505.1	505.6	505.9	506.1	506.4	506.8	506.9
140°	521.9	522.6	523.2	523.8	524.5	525.0	525.4	525.8	526.1	526.5	526.8
142.5°	541.8	542.3	542.8	543.4	543.9	544.4	544.9	545.4	545.9	546.3	546.5
145°	570.9	571.4	572.0	572.5	573.0	573.4	573.8	574.2	574.6	574.9	574.9
147.5°	597.8	598.1	598.4	598.7	599.1	599.3	599.6	600.0	600.3	600.6	600.9
150°	615.8	615.7	615.6	615.5	615.3	615.5	616.0	616.5	617.0	617.5	617.5
152.5°	630.6	630.8	631.0	631.2	631.3	631.5	631.7	631.9	632.1	632.4	632.7
155°	653.3	653.3	653.3	653.3	653.3	653.4	653.5	653.6	653.8	653.9	654.4
157.5°	673.6	673.3	673.0	672.8	672.5	672.4	672.5	672.7	672.8	672.9	673.4
160°	685.6	685.2	684.8	684.4	684.0	683.9	684.0	684.2	684.3	684.4	684.9
162.5°	696.2	695.9	695.6	695.3	695.0	694.9	694.9	695.0	695.0	695.0	695.6
165°	710.3	710.0	709.8	709.5	709.3	709.2	709.3	709.5	709.6	709.7	710.2
167.5°	722.4	721.9	721.2	720.7	720.2	720.0	720.0	720.0	720.0	720.0	720.7
170°	728.7	728.2	727.7	727.2	726.7	726.5	726.5	726.5	726.5	726.5	727.2
172.5°	733.4	732.9	732.4	731.8	731.3	731.0	731.0	731.0	731.0	731.0	731.8
175°	738.5	738.0	737.5	737.0	736.5	736.3	736.3	736.3	736.3	736.3	737.0
177.5°	741.2	740.8	740.4	740.0	739.5	739.3	739.2	739.1	739.0	738.9	739.5
180°	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3



TEST NUMBER: P333266-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1718.2	1720.6	1723.0	1724.1	1723.9	1723.6	1723.4	1723.2
5°	1709.6	1712.3	1715.1	1716.3	1716.0	1715.7	1715.4	1715.1
7.5°	1692.2	1695.0	1697.6	1698.8	1698.5	1698.2	1697.9	1697.6
10°	1677.6	1680.0	1682.4	1683.5	1683.2	1682.9	1682.6	1682.3
12.5°	1658.1	1660.0	1661.9	1662.9	1662.8	1662.7	1662.7	1662.6
15°	1624.0	1625.5	1627.0	1627.8	1627.8	1627.8	1627.8	1627.8
17.5°	1584.4	1586.2	1588.1	1588.3	1586.8	1585.3	1583.8	1582.3
20°	1554.3	1556.4	1558.5	1558.8	1557.3	1555.8	1554.3	1552.8
22.5°	1520.1	1521.6	1522.9	1523.1	1522.1	1521.1	1520.0	1518.9
25°	1465.4	1466.0	1466.6	1466.4	1465.5	1464.6	1463.7	1462.8
27.5°	1408.0	1408.1	1408.3	1407.9	1406.9	1406.0	1405.1	1404.2
30°	1366.1	1365.5	1364.9	1364.2	1363.3	1362.4	1361.5	1360.6
32.5°	1323.7	1322.6	1321.6	1320.2	1318.6	1317.0	1315.2	1313.6
35°	1258.0	1256.5	1255.0	1253.0	1250.6	1248.2	1245.8	1243.3
37.5°	1188.9	1186.7	1184.5	1182.7	1181.2	1179.8	1178.4	1177.1
40°	1141.0	1138.3	1135.6	1133.8	1132.9	1132.0	1131.0	1130.1
42.5°	1093.6	1091.1	1088.6	1086.6	1085.3	1083.9	1082.5	1081.1
45°	1023.4	1019.8	1016.1	1013.8	1012.9	1012.0	1011.1	1010.2
47.5°	949.4	945.6	942.0	939.1	937.0	934.8	932.7	930.6
50°	898.7	894.7	890.8	887.8	885.7	883.5	881.4	879.3
52.5°	849.5	846.1	842.6	839.7	837.3	835.0	832.6	830.2
55°	773.0	770.2	767.5	765.1	763.0	760.8	758.7	756.6
57.5°	697.0	693.5	689.9	687.6	686.5	685.3	684.2	683.0
60°	645.6	642.6	639.5	636.9	634.8	632.7	630.6	628.4
62.5°	596.0	592.8	589.5	587.0	585.4	583.8	582.1	580.5
65°	518.1	515.3	512.6	510.6	509.4	508.2	507.0	505.7
67.5°	443.6	441.3	439.0	437.5	436.8	436.1	435.4	434.6
70°	394.5	392.6	390.8	389.3	388.1	386.9	385.7	384.5
72.5°	348.2	346.1	344.1	342.4	341.2	340.0	338.8	337.6
75°	276.3	275.4	274.5	273.4	272.2	270.9	269.7	268.5
77.5°	210.5	210.0	209.4	208.7	207.8	207.0	206.1	205.3
80°	168.4	168.1	167.8	167.3	166.7	166.1	165.5	164.9
82.5°	128.7	128.2	127.6	127.2	127.1	127.0	126.9	126.7
85°	75.7	75.4	75.1	74.6	74.0	73.4	72.8	72.2
87.5°	30.5	30.6	30.7	30.6	30.2	29.8	29.4	29.0
90°	10.5	11.1	11.8	12.3	12.7	13.0	13.4	13.8
92.5°	23.8	24.6	25.5	26.1	26.4	26.7	26.9	27.2
95°	46.2	47.1	48.0	48.5	48.8	49.1	49.3	49.6
97.5°	72.3	73.2	74.0	74.5	74.6	74.8	74.9	75.1
100°	90.5	91.6	92.7	93.4	93.7	94.0	94.2	94.5
102.5°	109.1	110.4	111.6	112.4	112.8	113.1	113.5	113.8
105°	139.3	140.0	140.8	141.4	141.7	142.1	142.5	142.9
107.5°	171.8	172.2	172.5	172.7	172.7	172.7	172.6	172.6
110°	194.3	194.7	195.1	195.2	195.1	195.0	194.8	194.7



TEST NUMBER: P333266-840

CATALOG NUMBER: S125DIP-S1090D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	217.0	217.1	217.3	217.3	217.1	216.8	216.6	216.4
115°	251.5	251.4	251.3	251.2	251.0	250.9	250.7	250.6
117.5°	286.1	286.2	286.3	286.1	285.6	285.1	284.6	284.0
120°	309.3	309.3	309.3	309.1	308.6	308.1	307.6	307.1
122.5°	332.2	332.1	332.0	331.7	331.3	330.9	330.5	330.1
125°	365.9	365.7	365.4	365.2	365.1	365.0	364.8	364.7
127.5°	399.3	399.2	399.1	398.9	398.6	398.4	398.1	397.9
130°	421.4	421.3	421.2	421.0	420.7	420.5	420.2	420.0
132.5°	442.6	442.5	442.4	442.1	441.8	441.4	441.1	440.7
135°	475.2	475.2	475.2	475.0	474.5	474.0	473.5	473.0
137.5°	507.1	507.2	507.4	507.2	506.4	505.8	505.2	504.5
140°	527.0	527.4	527.6	527.4	526.7	526.1	525.4	524.8
142.5°	546.6	546.8	546.9	546.7	546.1	545.4	544.8	544.2
145°	574.9	574.9	574.9	574.7	574.4	574.0	573.6	573.2
147.5°	601.2	601.5	601.8	601.5	600.6	599.8	598.8	598.0
150°	617.5	617.5	617.5	617.4	617.2	616.9	616.7	616.4
152.5°	633.0	633.3	633.6	633.5	633.0	632.6	632.1	631.7
155°	654.9	655.4	655.9	655.9	655.2	654.6	653.9	653.3
157.5°	673.9	674.4	674.9	674.8	673.9	673.1	672.3	671.4
160°	685.4	685.9	686.4	686.4	685.8	685.1	684.5	683.9
162.5°	696.2	696.8	697.5	697.4	696.7	695.9	695.2	694.4
165°	710.7	711.2	711.9	711.7	710.9	710.1	709.3	708.6
167.5°	721.5	722.4	723.1	723.1	722.3	721.4	720.6	719.9
170°	728.0	728.7	729.5	729.4	728.6	727.7	726.8	725.9
172.5°	732.7	733.4	734.2	734.2	733.4	732.6	731.7	730.9
175°	737.8	738.5	739.3	739.2	738.4	737.5	736.6	735.7
177.5°	740.1	740.7	741.3	741.3	740.6	739.9	739.1	738.4
180°	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3

(END OF REPORT)