

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333274-840

Luminaire Tested: **S125DIP-S1090D810U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333274-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D810U840-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7757.9 lumens  
Efficiency: N/A  
Efficacy: 142.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333274-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333274-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	99	95	91	88	93	89	85	82	77	74	72	66	64	62	56	55	53	49
2	91	83	77	71	84	78	72	67	67	63	60	58	55	52	49	47	45	41
3	83	73	65	59	77	68	62	56	59	54	50	51	47	44	43	41	38	34
4	76	65	57	50	70	60	53	48	53	47	43	46	41	38	39	36	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29	26
6	64	52	43	38	59	49	41	36	43	37	32	37	32	29	32	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11129	11129	11129
5°	11154	11048	11119
10°	11086	10970	11032
15°	10965	10838	10884
20°	10794	10653	10672
25°	10608	10434	10424
30°	10380	10197	10147
35°	10136	9942	9802
40°	9885	9666	9528
45°	9613	9414	9227
50°	9315	9109	8835
55°	9026	8765	8519
60°	8681	8418	8117
65°	8270	8000	7728
70°	7878	7517	7260
75°	7177	6939	6700
80°	6390	6289	6133
85°	5550	5654	5350



TEST NUMBER: P333274-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.5	2.1
10°-20°	459.0	5.9
20°-30°	677.7	8.7
30°-40°	790.7	10.2
40°-50°	794.2	10.2
50°-60°	697.1	9.0
60°-70°	519.5	6.7
70°-80°	297.0	3.8
80°-90°	88.6	1.1
90°-100°	38.7	0.5
100°-110°	238.6	3.1
110°-120°	432.8	5.6
120°-130°	555.4	7.2
130°-140°	597.4	7.7
140°-150°	560.7	7.2
150°-160°	453.6	5.8
160°-170°	293.3	3.8
170°-180°	101.2	1.3
0°-30°	1299.1	16.7
0°-40°	2089.8	26.9
0°-60°	3581.2	46.2
0°-90°	4486.2	57.8
90°-120°	710.1	9.2
90°-150°	2423.5	31.2
90°-180°	3272.0	42.2
0°-180°	7757.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1720	1717	1704	1716	1715	163
15°	1640	1635	1621	1627	1628	462
25°	1489	1481	1464	1466	1463	685
35°	1286	1279	1261	1254	1243	804
45°	1052	1046	1031	1015	1010	811
55°	802	797	778	766	757	715
65°	541	538	524	512	506	537
75°	288	285	278	274	268	307
85°	75	76	76	75	72	84
90°	1	7	13	17	19	6
95°	45	41	13	16	17	57
105°	232	235	235	235	235	246
115°	436	440	441	437	433	432
125°	620	625	626	622	620	554
135°	773	778	776	775	770	596
145°	896	898	898	898	894	560
155°	987	983	984	986	980	455
165°	1042	1037	1038	1042	1036	294
175°	1065	1061	1062	1067	1061	101
180°	1065	1065	1065	1065	1065	



TEST NUMBER: P333274-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1727.6	1726.9	1726.1	1725.4	1724.6	1723.0	1720.6	1718.2	1715.8	1713.3	1715.8
5°	1720.5	1719.9	1719.3	1718.7	1718.1	1716.3	1713.2	1710.2	1707.2	1704.1	1706.9
7.5°	1704.7	1704.0	1703.4	1702.8	1702.2	1700.2	1696.9	1693.5	1690.2	1686.9	1689.6
10°	1690.5	1689.9	1689.3	1688.7	1688.1	1686.1	1682.7	1679.4	1676.1	1672.7	1675.2
12.5°	1673.0	1671.9	1670.8	1669.7	1668.7	1666.6	1663.4	1660.4	1657.3	1654.2	1656.2
15°	1640.0	1639.1	1638.2	1637.3	1636.4	1634.3	1630.9	1627.6	1624.3	1620.9	1622.4
17.5°	1602.2	1600.8	1599.4	1598.1	1596.8	1594.4	1590.9	1587.5	1584.1	1580.5	1582.5
20°	1570.5	1569.9	1569.3	1568.7	1568.1	1565.8	1561.9	1557.9	1554.0	1550.0	1552.2
22.5°	1538.8	1537.8	1536.7	1535.6	1534.5	1532.1	1528.4	1524.7	1521.1	1517.3	1518.7
25°	1488.7	1487.2	1485.7	1484.2	1482.7	1480.0	1476.0	1472.1	1468.1	1464.2	1464.8
27.5°	1430.1	1429.2	1428.3	1427.3	1426.4	1424.0	1419.9	1415.8	1411.8	1407.8	1407.9
30°	1391.9	1391.0	1390.1	1389.2	1388.3	1385.5	1381.0	1376.4	1371.9	1367.4	1366.8
32.5°	1350.5	1349.1	1347.7	1346.3	1344.9	1342.2	1338.1	1334.0	1330.0	1326.0	1324.8
35°	1285.6	1284.3	1283.1	1281.9	1280.7	1278.0	1273.7	1269.5	1265.3	1261.0	1259.5
37.5°	1218.2	1216.7	1215.2	1213.7	1212.1	1209.4	1205.4	1201.4	1197.4	1193.5	1191.1
40°	1172.5	1170.9	1169.4	1167.9	1166.4	1163.5	1159.2	1155.0	1150.7	1146.5	1143.8
42.5°	1123.4	1122.1	1120.8	1119.5	1118.2	1115.5	1111.3	1107.0	1102.8	1098.5	1096.0
45°	1052.5	1051.3	1050.1	1048.8	1047.6	1045.2	1041.6	1037.9	1034.3	1030.7	1027.0
47.5°	976.1	976.1	976.2	976.3	976.3	974.2	969.9	965.4	961.1	956.7	953.0
50°	927.1	926.1	925.2	924.3	923.4	921.1	917.5	913.8	910.2	906.6	902.6
52.5°	876.9	876.2	875.6	874.8	874.2	871.9	868.1	864.1	860.3	856.4	852.9
55°	801.6	800.7	799.8	798.9	798.0	795.4	791.1	786.9	782.6	778.4	775.7
57.5°	722.3	721.8	721.3	720.8	720.3	718.3	714.7	711.1	707.6	704.0	700.4
60°	672.1	670.9	669.6	668.4	667.2	665.0	661.7	658.3	655.0	651.7	648.6
62.5°	619.8	618.7	617.8	616.8	615.9	614.0	611.1	608.2	605.4	602.6	599.3
65°	541.2	540.6	540.0	539.4	538.8	536.8	533.5	530.2	526.8	523.5	520.8
67.5°	465.1	463.8	462.6	461.3	460.1	458.2	455.7	453.2	450.7	448.3	446.0
70°	417.2	415.7	414.1	412.6	411.1	409.0	406.3	403.5	400.8	398.1	396.3
72.5°	364.9	363.8	362.7	361.7	360.7	359.3	357.6	355.8	354.1	352.2	350.2
75°	287.6	287.0	286.4	285.8	285.2	284.2	282.7	281.1	279.6	278.1	277.2
77.5°	216.5	216.2	216.0	215.8	215.5	215.0	214.1	213.3	212.5	211.6	211.1
80°	171.8	171.8	171.8	171.8	171.8	171.5	170.9	170.3	169.7	169.1	168.7
82.5°	132.5	132.0	131.6	131.1	130.6	130.3	130.2	130.1	129.9	129.8	129.3
85°	74.9	75.2	75.5	75.8	76.1	76.3	76.3	76.3	76.3	76.3	76.0
87.5°	29.6	29.9	30.2	30.4	30.7	30.9	30.9	30.9	30.9	30.9	31.1
90°	0.8	2.2	3.6	5.0	6.4	7.7	9.0	10.2	11.4	12.6	13.5
92.5°	12.1	11.2	10.2	9.2	8.3	8.3	9.4	10.5	11.5	12.6	13.5
95°	45.0	44.5	43.9	43.4	42.9	39.3	32.6	26.0	19.3	12.6	13.5
97.5°	94.0	94.9	95.8	96.8	97.8	91.7	78.5	65.2	52.0	38.9	33.9
100°	131.9	132.4	132.9	133.5	134.0	134.6	135.3	136.0	136.7	137.4	111.3
102.5°	170.5	171.1	171.8	172.4	173.1	173.6	174.1	174.5	174.9	175.3	170.4
105°	232.2	232.9	233.6	234.3	235.0	235.3	235.3	235.3	235.3	235.3	235.3
107.5°	296.3	296.3	296.3	296.3	296.3	296.5	296.8	297.2	297.5	297.9	297.9
110°	338.0	338.0	338.0	338.0	338.0	338.2	338.5	338.9	339.2	339.6	339.1



TEST NUMBER: P333274-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	377.2	377.6	378.0	378.5	378.9	379.2	379.4	379.6	379.8	380.0	379.4
115°	436.0	436.9	437.7	438.6	439.5	440.0	440.2	440.3	440.5	440.7	440.0
117.5°	496.8	496.8	496.7	496.7	496.7	497.0	497.6	498.3	499.0	499.6	498.7
120°	534.6	534.5	534.3	534.1	533.9	534.1	534.6	535.2	535.7	536.2	535.9
122.5°	568.2	568.9	569.5	570.2	570.8	571.3	571.5	571.8	572.0	572.3	571.9
125°	620.0	621.2	622.4	623.7	624.9	625.5	625.5	625.5	625.5	625.5	624.8
127.5°	669.4	670.2	671.2	672.1	672.9	673.3	673.2	673.1	673.0	672.9	672.5
130°	699.7	700.6	701.5	702.4	703.3	703.8	704.0	704.1	704.3	704.5	704.0
132.5°	730.0	731.0	732.1	733.1	734.2	734.5	734.1	733.7	733.3	732.9	732.8
135°	773.2	774.3	775.3	776.4	777.4	777.7	777.4	777.0	776.7	776.4	776.0
137.5°	812.8	813.7	814.7	815.6	816.5	816.8	816.5	816.2	815.9	815.5	815.6
140°	838.7	839.1	839.4	839.8	840.1	840.2	840.0	839.9	839.7	839.5	839.9
142.5°	862.1	862.3	862.5	862.7	862.9	863.1	863.4	863.6	863.9	864.1	864.2
145°	896.4	896.8	897.1	897.5	897.8	898.0	898.0	898.0	898.0	898.0	898.2
147.5°	926.3	926.3	926.2	926.1	926.1	926.1	926.3	926.6	926.9	927.1	927.3
150°	945.3	945.0	944.6	944.3	943.9	943.9	944.3	944.6	945.0	945.3	945.7
152.5°	963.7	962.9	962.1	961.4	960.6	960.4	960.7	961.1	961.4	961.8	962.1
155°	987.2	986.1	985.1	984.0	983.0	982.6	983.0	983.3	983.7	984.0	984.5
157.5°	1005.3	1004.7	1004.1	1003.5	1002.8	1002.5	1002.6	1002.6	1002.6	1002.7	1003.2
160°	1018.0	1016.9	1015.9	1014.8	1013.8	1013.4	1013.5	1013.7	1013.9	1014.0	1014.7
162.5°	1028.1	1027.0	1026.0	1024.9	1023.9	1023.5	1023.6	1023.8	1024.0	1024.2	1025.1
165°	1041.7	1040.7	1039.6	1038.5	1037.4	1037.0	1037.2	1037.4	1037.5	1037.7	1038.8
167.5°	1051.8	1050.8	1049.7	1048.5	1047.4	1047.0	1047.1	1047.3	1047.5	1047.7	1048.9
170°	1057.5	1056.2	1055.0	1053.8	1052.6	1052.1	1052.2	1052.4	1052.6	1052.8	1054.2
172.5°	1061.3	1060.1	1058.8	1057.6	1056.3	1055.9	1056.2	1056.5	1056.8	1057.1	1058.4
175°	1065.4	1064.3	1063.3	1062.3	1061.2	1060.8	1060.9	1061.1	1061.3	1061.5	1062.9
177.5°	1067.3	1066.4	1065.6	1064.8	1063.9	1063.6	1063.7	1063.8	1064.0	1064.1	1065.1
180°	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4



TEST NUMBER: P333274-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1718.2	1720.6	1723.0	1724.1	1723.9	1723.6	1723.4	1723.2
5°	1709.6	1712.3	1715.1	1716.3	1716.0	1715.7	1715.4	1715.1
7.5°	1692.2	1695.0	1697.6	1698.8	1698.5	1698.2	1697.9	1697.6
10°	1677.6	1680.0	1682.4	1683.5	1683.2	1682.9	1682.6	1682.3
12.5°	1658.1	1660.0	1661.9	1662.9	1662.8	1662.7	1662.7	1662.6
15°	1624.0	1625.5	1627.0	1627.8	1627.8	1627.8	1627.8	1627.8
17.5°	1584.4	1586.2	1588.1	1588.3	1586.8	1585.3	1583.8	1582.3
20°	1554.3	1556.4	1558.5	1558.8	1557.3	1555.8	1554.3	1552.8
22.5°	1520.1	1521.6	1522.9	1523.1	1522.1	1521.1	1520.0	1518.9
25°	1465.4	1466.0	1466.6	1466.4	1465.5	1464.6	1463.7	1462.8
27.5°	1408.0	1408.1	1408.3	1407.9	1406.9	1406.0	1405.1	1404.2
30°	1366.1	1365.5	1364.9	1364.2	1363.3	1362.4	1361.5	1360.6
32.5°	1323.7	1322.6	1321.6	1320.2	1318.6	1317.0	1315.2	1313.6
35°	1258.0	1256.5	1255.0	1253.0	1250.6	1248.2	1245.8	1243.3
37.5°	1188.9	1186.7	1184.5	1182.7	1181.2	1179.8	1178.4	1177.1
40°	1141.0	1138.3	1135.6	1133.8	1132.9	1132.0	1131.0	1130.1
42.5°	1093.6	1091.1	1088.6	1086.6	1085.3	1083.9	1082.5	1081.1
45°	1023.4	1019.8	1016.1	1013.8	1012.9	1012.0	1011.1	1010.2
47.5°	949.4	945.6	942.0	939.1	937.0	934.8	932.7	930.6
50°	898.7	894.7	890.8	887.8	885.7	883.5	881.4	879.3
52.5°	849.5	846.1	842.6	839.7	837.3	835.0	832.6	830.2
55°	773.0	770.2	767.5	765.1	763.0	760.8	758.7	756.6
57.5°	697.0	693.5	689.9	687.6	686.5	685.3	684.2	683.0
60°	645.6	642.6	639.5	636.9	634.8	632.7	630.6	628.4
62.5°	596.0	592.8	589.5	587.0	585.4	583.8	582.1	580.5
65°	518.1	515.3	512.6	510.6	509.4	508.2	507.0	505.7
67.5°	443.6	441.3	439.0	437.5	436.8	436.1	435.4	434.6
70°	394.5	392.6	390.8	389.3	388.1	386.9	385.7	384.5
72.5°	348.2	346.1	344.1	342.4	341.2	340.0	338.8	337.6
75°	276.3	275.4	274.5	273.4	272.2	270.9	269.7	268.5
77.5°	210.5	210.0	209.4	208.7	207.8	207.0	206.1	205.3
80°	168.4	168.1	167.8	167.3	166.7	166.1	165.5	164.9
82.5°	128.7	128.2	127.6	127.2	127.1	127.0	126.9	126.7
85°	75.7	75.4	75.1	74.6	74.0	73.4	72.8	72.2
87.5°	31.2	31.4	31.6	31.5	31.1	30.7	30.3	30.0
90°	14.4	15.2	16.2	16.9	17.4	17.9	18.4	19.0
92.5°	14.4	15.2	16.2	16.7	17.0	17.2	17.5	17.7
95°	14.4	15.2	16.2	16.6	16.6	16.6	16.6	16.6
97.5°	29.0	24.0	19.1	16.6	16.6	16.6	16.6	16.6
100°	85.1	59.0	32.8	19.4	18.7	18.0	17.3	16.6
102.5°	165.4	160.5	155.5	147.1	135.1	123.2	111.3	99.4
105°	235.3	235.3	235.3	235.3	235.1	234.9	234.7	234.6
107.5°	298.0	298.0	298.0	297.8	297.3	296.7	296.2	295.7
110°	338.5	338.0	337.5	337.3	337.5	337.7	337.8	338.0





TEST NUMBER: P333274-840

CATALOG NUMBER: S125DIP-S1090D810U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	378.7	378.0	377.4	376.9	376.7	376.4	376.2	376.0
115°	439.3	438.6	437.9	437.0	436.0	434.8	433.8	432.8
117.5°	497.8	496.9	495.9	495.2	494.8	494.3	493.9	493.4
120°	535.5	535.2	534.8	534.2	533.3	532.5	531.6	530.7
122.5°	571.6	571.2	570.9	570.2	569.2	568.2	567.1	566.1
125°	624.1	623.4	622.7	622.1	621.6	621.0	620.5	620.0
127.5°	672.1	671.8	671.4	670.4	669.2	667.9	666.6	665.3
130°	703.4	702.9	702.4	701.7	700.7	699.9	699.0	698.1
132.5°	732.7	732.6	732.5	732.0	731.1	730.2	729.3	728.5
135°	775.7	775.3	775.0	774.3	773.2	772.1	771.0	770.0
137.5°	815.7	815.7	815.8	815.4	814.5	813.5	812.6	811.7
140°	840.2	840.6	840.9	840.6	839.5	838.5	837.4	836.4
142.5°	864.3	864.3	864.4	863.9	862.9	861.8	860.8	859.7
145°	898.3	898.5	898.7	898.2	897.2	896.2	895.0	894.0
147.5°	927.5	927.7	927.9	927.4	926.0	924.8	923.5	922.3
150°	946.0	946.4	946.7	946.2	944.8	943.4	942.0	940.6
152.5°	962.5	962.8	963.2	962.7	961.5	960.2	959.0	957.7
155°	985.1	985.6	986.1	985.7	984.3	982.9	981.5	980.1
157.5°	1003.8	1004.4	1004.9	1004.5	1003.1	1001.7	1000.3	998.9
160°	1015.4	1016.1	1016.8	1016.5	1015.1	1013.7	1012.3	1010.9
162.5°	1026.1	1027.1	1028.0	1027.8	1026.2	1024.7	1023.2	1021.7
165°	1039.9	1040.9	1042.0	1041.8	1040.4	1038.9	1037.5	1036.1
167.5°	1050.3	1051.5	1052.8	1052.6	1051.0	1049.5	1047.8	1046.3
170°	1055.5	1056.9	1058.3	1058.2	1056.7	1055.1	1053.5	1052.0
172.5°	1059.7	1061.0	1062.3	1062.1	1060.5	1058.9	1057.3	1055.7
175°	1064.2	1065.6	1067.0	1066.9	1065.4	1063.8	1062.3	1060.7
177.5°	1066.1	1067.0	1068.0	1068.0	1066.8	1065.7	1064.6	1063.5
180°	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4	1065.4

(END OF REPORT)