

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333134-840

Luminaire Tested: **S125DIP-S375D810U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333134-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D810U840-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4385.1 lumens
Efficiency: N/A
Efficacy: 140.5 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30
2	86	79	73	68	78	72	67	63	58	55	51	45	43	41	34	32	31	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	62	54	48	65	56	49	44	46	41	37	36	32	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	17	14
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	17	16	13
8	52	40	33	27	47	37	30	25	30	25	22	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	23	28	23	19	22	18	16	17	14	13	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3551	3551	3551	3551
5°	4112	3563	3120	3563
10°	4783	3545	2733	3545
15°	5295	3518	2521	3518
20°	5927	3477	2351	3477
25°	6944	3430	2268	3430
30°	7500	3384	2196	3384
35°	6166	3299	2149	3299
40°	4383	3179	2097	3179
45°	3368	3018	2067	3018
50°	2875	2817	2063	2817
55°	2559	2622	2081	2622
60°	2308	2408	2134	2408
65°	2133	2193	2190	2193
70°	1939	1969	2221	1969
75°	1712	1737	2201	1737
80°	1443	1417	2012	1417
85°	1149	1015	1623	1015



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.9	1.2
10°-20°	157.6	3.6
20°-30°	255.9	5.8
30°-40°	312.1	7.1
40°-50°	283.9	6.5
50°-60°	226.2	5.2
60°-70°	157.5	3.6
70°-80°	84.0	1.9
80°-90°	23.4	0.5
90°-100°	68.0	1.5
100°-110°	200.7	4.6
110°-120°	339.9	7.8
120°-130°	447.4	10.2
130°-140°	501.3	11.4
140°-150°	491.3	11.2
150°-160°	412.7	9.4
160°-170°	274.3	6.3
170°-180°	96.0	2.2
0°-30°	466.4	10.6
0°-40°	778.5	17.8
0°-60°	1288.6	29.4
0°-90°	1553.6	35.4
90°-120°	608.6	13.9
90°-150°	2048.6	46.7
90°-180°	2832.0	64.6
0°-180°	4385.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	550	550	550	550	550	
5°	634	550	481	550	634	64
15°	792	526	377	526	792	227
25°	974	481	318	481	974	445
35°	782	418	273	418	782	479
45°	369	330	226	330	369	295
55°	227	233	185	233	227	205
65°	140	144	143	144	140	138
75°	69	70	88	70	69	74
85°	16	14	22	14	16	18
90°	19	1	19	1	19	11
95°	68	51	68	51	68	69
105°	196	180	196	180	196	207
115°	344	340	344	340	344	340
125°	500	497	500	497	500	446
135°	648	646	648	646	648	500
145°	786	782	786	782	786	490
155°	895	895	895	895	895	412
165°	971	974	971	974	971	274
175°	1008	1012	1008	1012	1008	96
180°	1015	1015	1015	1015	1015	



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	581.5	580.8	580.0	578.6	579.7	576.4	575.0	572.4	569.2	568.0	566.7
5°	634.2	635.4	636.6	631.7	632.2	628.8	621.4	615.3	610.5	604.1	599.7
7.5°	697.7	695.0	694.7	691.6	686.1	681.7	673.9	663.9	654.2	643.2	634.1
10°	729.4	729.7	727.6	723.9	718.0	713.8	703.6	693.8	681.9	667.8	657.8
12.5°	753.4	754.4	751.6	746.6	743.8	734.4	726.3	714.7	700.5	689.3	674.1
15°	791.9	789.4	787.6	781.2	776.4	766.6	753.8	741.5	726.2	712.0	697.7
17.5°	829.2	831.3	827.8	822.0	806.8	795.4	778.2	761.5	742.4	723.3	706.3
20°	862.4	864.3	859.0	848.9	830.7	819.3	796.7	775.2	753.1	728.5	709.8
22.5°	903.9	902.4	895.1	879.9	864.1	843.0	818.5	792.3	764.6	736.9	712.1
25°	974.4	964.6	960.2	941.3	920.6	889.5	856.0	817.7	783.2	746.5	714.8
27.5°	1013.6	1010.5	1005.5	992.4	970.6	937.4	897.8	851.1	802.4	756.2	714.6
30°	1005.7	1006.2	1006.6	1002.5	988.5	963.5	924.0	873.9	816.0	764.0	715.9
32.5°	936.2	944.7	952.9	962.5	966.4	961.6	937.0	891.6	832.0	773.0	715.2
35°	782.1	784.8	811.1	837.3	872.7	900.3	918.7	898.6	848.5	780.5	714.3
37.5°	609.9	622.5	640.8	670.2	721.4	767.3	826.3	853.3	837.2	783.0	712.7
40°	519.9	531.6	543.5	573.6	616.7	672.3	739.2	796.4	809.7	775.2	707.0
42.5°	450.5	459.7	472.9	495.5	531.6	580.8	644.8	719.5	765.5	752.5	695.3
45°	368.7	374.6	384.8	402.7	428.9	467.4	523.8	605.5	676.7	700.2	667.4
47.5°	315.6	315.6	323.6	335.9	354.8	387.5	429.3	493.2	569.3	625.5	622.9
50°	286.1	284.9	291.2	301.9	316.9	338.6	378.5	429.6	502.6	566.3	584.1
52.5°	260.6	260.8	264.7	272.7	285.2	303.7	333.5	379.6	441.9	507.4	540.8
55°	227.3	226.3	230.8	236.1	245.3	257.4	278.8	314.1	364.8	429.1	472.5
57.5°	196.6	199.2	201.0	204.7	212.3	220.5	238.5	264.4	304.6	359.8	405.7
60°	178.7	181.3	182.7	186.4	192.5	199.5	213.5	234.5	268.3	316.0	361.4
62.5°	162.7	164.7	165.2	168.5	173.5	180.3	191.3	208.9	235.7	277.3	321.8
65°	139.6	139.6	140.5	144.0	146.3	152.4	160.8	173.6	195.1	227.5	265.6
67.5°	117.2	118.4	118.2	119.7	121.8	126.5	132.5	143.1	159.1	182.7	213.2
70°	102.7	103.6	103.4	104.5	106.8	109.9	114.8	124.8	136.2	156.5	182.7
72.5°	89.6	90.0	89.4	90.9	92.3	94.9	100.5	105.8	116.4	133.6	155.1
75°	68.6	69.1	69.6	70.5	71.9	73.3	76.0	81.4	88.5	101.3	115.0
77.5°	51.4	50.5	51.7	51.5	52.3	53.4	55.8	58.7	64.4	72.6	83.2
80°	38.8	39.0	39.0	39.2	40.4	41.1	43.1	45.2	49.7	55.7	63.2
82.5°	28.3	28.9	28.5	29.0	29.9	30.4	31.6	33.3	35.9	40.7	46.0
85°	15.5	14.2	14.7	15.1	15.1	15.5	16.4	17.1	18.5	20.3	22.4
87.5°	8.3	8.6	8.6	8.5	8.6	8.5	9.0	8.9	9.2	9.6	10.1
90°	19.0	18.4	17.9	17.4	16.9	16.2	15.2	14.3	13.5	12.6	11.4
92.5°	37.3	36.9	36.5	36.2	35.7	34.9	33.8	32.6	31.5	30.3	28.8
95°	67.9	67.6	67.3	66.9	66.6	65.7	64.5	63.2	62.0	60.8	59.1
97.5°	103.0	102.8	102.5	102.3	102.1	101.5	100.3	99.2	98.0	96.8	94.4
100°	129.5	129.2	128.8	128.5	128.2	127.1	125.5	124.0	122.4	120.8	118.6
102.5°	156.0	155.5	155.0	154.6	154.1	153.0	151.3	149.6	147.8	146.1	144.9
105°	195.8	195.3	194.8	194.3	193.7	193.0	191.9	190.9	189.8	188.7	187.6
107.5°	236.6	236.6	236.6	236.7	236.7	236.5	235.9	235.4	234.9	234.4	233.6
110°	266.9	267.1	267.2	267.4	267.6	267.4	266.9	266.4	265.9	265.3	264.8



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	296.6	296.9	297.2	297.5	297.9	297.9	297.6	297.4	297.2	296.9	296.3
115°	343.6	343.7	343.9	344.1	344.2	344.4	344.6	344.8	344.9	345.1	344.8
117.5°	389.3	390.0	390.7	391.4	392.1	392.4	392.2	392.1	391.9	391.8	391.5
120°	420.9	421.6	422.3	423.0	423.7	424.0	424.0	424.0	424.0	424.0	423.8
122.5°	452.5	453.0	453.6	454.1	454.7	455.0	455.2	455.3	455.4	455.7	455.1
125°	499.9	500.1	500.2	500.4	500.6	500.8	501.2	501.5	501.9	502.2	502.0
127.5°	545.3	545.7	546.0	546.4	546.7	547.0	547.1	547.3	547.5	547.8	547.5
130°	575.6	576.0	576.3	576.7	577.0	577.3	577.5	577.6	577.8	578.0	577.6
132.5°	604.1	604.6	605.1	605.6	606.0	606.4	606.5	606.7	606.9	607.1	607.1
135°	648.3	649.0	649.7	650.5	651.2	651.5	651.5	651.5	651.5	651.5	651.3
137.5°	691.6	692.5	693.4	694.2	695.1	695.4	695.2	695.0	694.8	694.6	694.2
140°	719.4	720.2	721.1	722.1	722.9	723.2	722.8	722.5	722.2	721.8	721.2
142.5°	745.9	746.8	747.7	748.5	749.4	749.7	749.5	749.3	749.1	748.9	748.2
145°	785.7	786.3	786.8	787.3	787.8	788.1	788.1	788.1	788.1	788.1	787.6
147.5°	819.7	820.9	822.0	823.2	824.5	824.9	824.5	823.9	823.5	823.1	822.7
150°	845.0	845.3	845.7	846.0	846.4	846.6	846.6	846.6	846.6	846.6	845.9
152.5°	865.8	866.5	867.1	867.7	868.3	868.4	868.0	867.6	867.2	866.8	866.5
155°	895.4	896.4	897.3	898.1	899.0	899.1	898.4	897.7	897.0	896.3	896.1
157.5°	920.3	921.4	922.6	923.7	924.9	925.1	924.4	923.7	923.0	922.3	922.1
160°	937.4	938.2	939.1	940.0	940.9	940.9	940.2	939.6	938.9	938.2	938.0
162.5°	951.9	952.9	953.9	954.9	955.9	956.0	955.2	954.3	953.5	952.7	952.6
165°	971.3	972.3	973.4	974.4	975.5	975.6	975.0	974.3	973.6	972.9	972.7
167.5°	986.7	987.8	989.0	990.1	991.1	991.2	990.1	989.1	988.0	986.9	986.9
170°	995.0	996.2	997.4	998.7	999.9	1000.0	999.0	997.8	996.8	995.7	995.7
172.5°	1001.9	1003.0	1004.1	1005.2	1006.3	1006.3	1005.2	1004.2	1003.1	1002.1	1002.1
175°	1008.5	1009.7	1010.9	1012.1	1013.3	1013.4	1012.4	1011.3	1010.3	1009.2	1009.2
177.5°	1012.2	1013.2	1014.2	1015.1	1016.1	1016.2	1015.3	1014.5	1013.7	1012.8	1013.0
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	565.6	564.3	562.8	560.2	557.0	555.3	552.8	551.1	547.8	544.9	541.9
5°	594.3	588.2	582.7	575.4	567.5	562.4	556.3	549.6	542.5	535.3	527.4
7.5°	624.1	613.3	601.7	589.2	576.8	565.5	554.7	544.2	534.3	522.3	512.2
10°	644.0	630.5	616.0	599.1	582.4	567.9	553.3	540.5	527.4	513.4	501.0
12.5°	664.0	646.0	625.5	606.8	586.9	569.5	552.2	535.7	519.4	503.8	489.4
15°	678.1	662.3	643.4	616.7	594.3	570.3	547.4	526.2	506.3	489.1	470.9
17.5°	687.4	666.9	646.6	621.2	591.8	564.9	539.0	514.6	492.3	470.4	452.9
20°	689.0	668.0	646.8	621.9	591.8	561.0	535.0	505.9	481.9	459.2	437.8
22.5°	688.5	664.7	641.6	615.9	586.5	558.2	526.8	497.2	471.0	448.8	426.4
25°	683.3	657.8	628.8	603.0	574.0	543.9	512.2	481.4	454.8	429.4	407.2
27.5°	678.8	645.9	613.1	582.9	554.9	527.4	497.0	465.4	436.0	410.2	389.3
30°	673.5	637.2	600.4	568.9	540.2	513.4	484.6	453.8	423.0	397.9	375.5
32.5°	668.6	626.4	587.5	553.2	522.8	496.8	470.3	441.0	410.7	385.2	362.7
35°	659.2	610.5	565.8	527.1	494.7	467.9	445.7	418.4	390.6	365.9	344.5
37.5°	647.3	589.5	541.6	501.0	465.4	437.2	416.6	395.6	368.9	345.1	325.7
40°	637.9	574.5	523.8	482.3	445.5	416.1	396.9	377.1	355.0	332.8	312.3
42.5°	626.2	561.1	505.9	461.2	424.7	396.1	376.0	359.2	339.6	318.9	299.9
45°	604.6	536.7	477.0	428.9	392.0	363.8	343.1	330.4	315.7	296.1	280.0
47.5°	572.8	507.5	445.7	396.1	358.0	331.8	312.4	300.2	289.9	275.4	260.7
50°	544.6	485.6	423.0	373.9	335.8	309.4	291.4	280.4	271.7	260.4	248.0
52.5°	513.1	458.2	400.8	352.1	314.5	288.5	270.9	261.3	253.9	245.9	233.7
55°	462.9	416.3	363.0	316.9	282.2	256.7	241.3	232.9	226.8	220.8	213.3
57.5°	407.8	371.2	324.2	281.9	249.8	226.7	212.4	204.2	199.4	196.3	192.0
60°	368.9	337.7	297.1	258.5	227.3	206.7	192.8	186.4	182.5	180.0	176.6
62.5°	332.9	307.2	269.6	234.5	207.1	187.7	175.2	169.1	165.3	164.0	161.4
65°	279.8	259.9	228.9	199.8	176.4	159.9	149.4	143.5	141.2	139.8	140.0
67.5°	227.4	215.4	190.5	165.6	146.9	133.1	124.6	120.2	119.0	117.1	117.1
70°	195.5	186.4	165.4	143.7	127.1	116.4	109.0	104.3	103.1	102.2	102.0
72.5°	167.3	159.4	141.2	123.8	108.9	99.5	93.3	90.5	88.6	88.1	88.0
75°	125.7	121.4	106.8	93.1	82.8	76.3	72.1	69.6	68.2	67.9	68.2
77.5°	89.4	85.5	76.3	66.6	60.1	55.1	51.6	50.7	49.2	49.2	49.0
80°	67.2	64.6	58.8	51.1	45.7	41.5	39.7	38.1	37.6	36.9	37.6
82.5°	48.7	45.9	42.0	37.1	32.6	30.2	28.3	27.8	27.5	27.2	27.3
85°	24.0	24.2	21.9	18.2	16.4	14.9	13.7	13.7	13.5	13.3	13.5
87.5°	10.2	9.6	8.7	7.8	6.6	5.8	5.3	5.2	4.9	5.0	5.5
90°	10.2	9.0	7.7	6.4	5.0	3.6	2.2	0.8	2.2	3.6	5.0
92.5°	27.3	25.8	24.2	23.0	22.0	21.1	20.1	19.1	20.1	21.1	22.0
95°	57.3	55.5	53.8	52.7	52.4	52.0	51.7	51.3	51.7	52.0	52.4
97.5°	92.0	89.6	87.2	85.8	85.7	85.5	85.4	85.3	85.4	85.5	85.7
100°	116.2	114.0	111.7	110.6	110.6	110.6	110.6	110.6	110.6	110.6	110.6
102.5°	143.8	142.6	141.5	140.6	139.9	139.2	138.5	137.7	138.5	139.2	139.9
105°	186.6	185.6	184.5	183.6	182.7	181.8	181.0	180.1	181.0	181.8	182.7
107.5°	232.8	232.0	231.2	230.4	229.4	228.5	227.6	226.8	227.6	228.5	229.4
110°	264.3	263.8	263.3	262.6	261.7	260.7	259.9	259.0	259.9	260.7	261.7



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	295.6	294.9	294.3	293.7	293.3	292.8	292.4	291.9	292.4	292.8	293.3
115°	344.4	344.1	343.7	343.2	342.4	341.7	341.0	340.3	341.0	341.7	342.4
117.5°	391.2	390.9	390.6	390.2	389.9	389.6	389.3	389.0	389.3	389.6	389.9
120°	423.7	423.5	423.3	422.8	421.9	421.1	420.2	419.3	420.2	421.1	421.9
122.5°	454.7	454.2	453.8	453.4	453.1	452.8	452.5	452.1	452.5	452.8	453.1
125°	501.9	501.7	501.5	500.9	499.9	498.8	497.8	496.7	497.8	498.8	499.9
127.5°	547.2	547.0	546.8	546.4	545.8	545.2	544.7	544.1	544.7	545.2	545.8
130°	577.3	576.9	576.6	576.0	575.1	574.3	573.4	572.5	573.4	574.3	575.1
132.5°	607.2	607.3	607.3	606.7	605.2	603.8	602.4	601.0	602.4	603.8	605.2
135°	651.2	651.0	650.8	650.2	649.1	648.0	647.0	645.9	647.0	648.0	649.1
137.5°	693.8	693.5	693.1	692.4	691.4	690.3	689.3	688.3	689.3	690.3	691.4
140°	720.7	720.1	719.6	718.9	718.1	717.2	716.3	715.5	716.3	717.2	718.1
142.5°	747.6	746.9	746.3	745.6	744.8	744.1	743.4	742.7	743.4	744.1	744.8
145°	787.0	786.5	786.0	785.4	784.7	784.0	783.3	782.5	783.3	784.0	784.7
147.5°	822.3	821.9	821.4	821.0	820.7	820.3	819.9	819.5	819.9	820.3	820.7
150°	845.2	844.4	843.7	843.4	843.6	843.8	843.9	844.1	843.9	843.8	843.6
152.5°	866.2	865.9	865.7	865.4	865.2	864.8	864.6	864.3	864.6	864.8	865.2
155°	896.0	895.8	895.5	895.4	895.4	895.4	895.4	895.4	895.4	895.4	895.4
157.5°	922.0	921.8	921.6	921.7	922.1	922.5	922.9	923.3	922.9	922.5	922.1
160°	937.8	937.6	937.5	937.6	938.2	938.7	939.2	939.7	939.2	938.7	938.2
162.5°	952.6	952.5	952.5	952.7	953.1	953.4	953.8	954.2	953.8	953.4	953.1
165°	972.5	972.3	972.2	972.3	972.6	973.0	973.3	973.7	973.3	973.0	972.6
167.5°	986.9	986.9	986.9	987.2	988.0	988.7	989.4	990.1	989.4	988.7	988.0
170°	995.7	995.7	995.7	996.1	996.8	997.5	998.3	999.0	998.3	997.5	996.8
172.5°	1002.1	1002.1	1002.1	1002.4	1003.1	1003.8	1004.5	1005.2	1004.5	1003.8	1003.1
175°	1009.2	1009.2	1009.2	1009.6	1010.3	1011.0	1011.7	1012.4	1011.7	1011.0	1010.3
177.5°	1013.1	1013.3	1013.4	1013.7	1014.3	1014.9	1015.4	1016.0	1015.4	1014.9	1014.3
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	540.3	538.2	536.5	532.8	530.7	528.0	525.7	528.2	525.5	526.6	524.9
5°	523.4	516.8	512.2	505.4	499.6	494.2	490.3	489.6	487.7	486.8	483.9
7.5°	503.1	494.9	487.0	478.1	470.6	463.0	458.2	454.1	451.5	448.0	445.6
10°	491.2	480.2	470.9	460.2	450.8	442.6	436.2	432.8	429.8	425.4	423.7
12.5°	476.5	465.1	453.7	442.2	433.2	424.1	418.6	413.6	411.5	406.6	406.1
15°	458.8	441.7	430.5	418.9	406.5	399.0	394.4	389.0	386.7	383.1	380.6
17.5°	437.7	422.4	408.5	396.4	385.8	379.5	373.7	370.0	366.0	363.7	359.5
20°	422.3	407.9	393.8	381.0	372.8	365.7	361.0	357.5	353.3	352.1	347.9
22.5°	409.5	393.5	380.1	369.3	360.4	352.2	347.2	344.8	341.9	338.3	337.5
25°	388.5	371.9	360.5	349.8	341.8	334.4	330.9	327.9	325.1	322.4	321.5
27.5°	370.4	355.6	342.0	332.3	325.4	318.6	315.6	311.8	309.8	307.7	305.2
30°	357.7	342.5	330.6	321.3	313.9	307.8	304.5	301.9	300.1	298.2	296.8
32.5°	344.7	330.6	319.1	309.9	302.5	297.9	295.0	293.2	291.1	288.9	287.1
35°	327.4	311.9	300.7	292.9	287.0	283.5	280.2	278.6	276.3	276.3	274.4
37.5°	307.9	294.6	284.7	277.5	272.3	269.1	265.6	264.5	263.0	262.0	261.4
40°	296.4	284.0	274.7	267.4	261.9	259.2	256.4	254.6	253.7	252.5	252.1
42.5°	284.4	272.6	263.7	257.0	252.1	249.9	247.3	246.0	244.1	242.6	242.3
45°	266.2	254.8	246.6	241.3	237.1	234.5	232.9	230.0	229.1	227.3	227.0
47.5°	249.0	238.0	230.0	225.6	222.0	219.8	217.3	214.5	213.4	212.5	212.4
50°	236.1	226.1	218.6	214.5	211.0	207.9	205.3	203.5	202.8	202.8	203.3
52.5°	223.1	214.5	208.2	203.1	199.8	196.5	194.1	193.0	192.0	193.1	193.9
55°	204.0	195.3	190.7	185.7	182.5	178.7	177.5	177.1	176.4	178.2	179.3
57.5°	183.7	177.6	172.2	167.3	164.4	162.2	160.7	160.4	161.7	162.6	165.6
60°	170.8	163.8	159.0	155.2	151.7	150.3	149.8	149.4	150.3	152.8	156.8
62.5°	156.6	151.0	145.6	142.9	140.3	137.9	137.8	138.1	140.0	143.0	146.9
65°	135.8	130.9	127.4	124.1	122.0	120.7	121.1	122.0	124.1	128.2	132.5
67.5°	114.6	111.3	108.2	105.5	103.5	103.5	104.0	105.4	107.9	112.4	116.4
70°	101.1	97.4	94.7	93.6	91.9	91.0	92.4	94.7	96.8	101.1	104.5
72.5°	87.5	84.2	82.2	81.4	80.7	80.0	80.5	83.0	85.8	90.0	94.1
75°	67.2	66.0	64.6	63.7	63.0	63.5	63.9	66.2	68.6	73.0	77.7
77.5°	49.1	47.9	47.0	46.8	46.4	46.7	48.0	49.7	51.9	55.1	58.7
80°	37.1	36.7	36.2	36.0	36.0	36.2	38.1	39.2	41.3	44.3	47.2
82.5°	27.1	26.8	26.7	26.6	26.8	26.9	28.0	29.5	31.2	33.5	36.0
85°	14.2	13.7	14.4	14.7	14.2	14.9	15.5	16.4	17.1	18.2	19.4
87.5°	6.0	6.6	6.7	7.1	7.4	8.0	8.0	8.9	9.4	10.0	9.9
90°	6.4	7.7	9.0	10.2	11.4	12.6	13.5	14.3	15.2	16.2	16.9
92.5°	23.0	24.2	25.8	27.3	28.8	30.3	31.5	32.6	33.8	34.9	35.7
95°	52.7	53.8	55.5	57.3	59.1	60.8	62.0	63.2	64.5	65.7	66.6
97.5°	85.8	87.2	89.6	92.0	94.4	96.8	98.0	99.2	100.3	101.5	102.1
100°	110.6	111.7	114.0	116.2	118.6	120.8	122.4	124.0	125.5	127.1	128.2
102.5°	140.6	141.5	142.6	143.8	144.9	146.1	147.8	149.6	151.3	153.0	154.1
105°	183.6	184.5	185.6	186.6	187.6	188.7	189.8	190.9	191.9	193.0	193.7
107.5°	230.4	231.2	232.0	232.8	233.6	234.4	234.9	235.4	235.9	236.5	236.7
110°	262.6	263.3	263.8	264.3	264.8	265.3	265.9	266.4	266.9	267.4	267.6



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	293.7	294.3	294.9	295.6	296.3	296.9	297.2	297.4	297.6	297.9	297.9
115°	343.2	343.7	344.1	344.4	344.8	345.1	344.9	344.8	344.6	344.4	344.2
117.5°	390.2	390.6	390.9	391.2	391.5	391.8	391.9	392.1	392.2	392.4	392.1
120°	422.8	423.3	423.5	423.7	423.8	424.0	424.0	424.0	424.0	424.0	423.7
122.5°	453.4	453.8	454.2	454.7	455.1	455.7	455.4	455.3	455.2	455.0	454.7
125°	500.9	501.5	501.7	501.9	502.0	502.2	501.9	501.5	501.2	500.8	500.6
127.5°	546.4	546.8	547.0	547.2	547.5	547.8	547.5	547.3	547.1	547.0	546.7
130°	576.0	576.6	576.9	577.3	577.6	578.0	577.8	577.6	577.5	577.3	577.0
132.5°	606.7	607.3	607.3	607.2	607.1	607.1	606.9	606.7	606.5	606.4	606.0
135°	650.2	650.8	651.0	651.2	651.3	651.5	651.5	651.5	651.5	651.5	651.2
137.5°	692.4	693.1	693.5	693.8	694.2	694.6	694.8	695.0	695.2	695.4	695.1
140°	718.9	719.6	720.1	720.7	721.2	721.8	722.2	722.5	722.8	723.2	722.9
142.5°	745.6	746.3	746.9	747.6	748.2	748.9	749.1	749.3	749.5	749.7	749.4
145°	785.4	786.0	786.5	787.0	787.6	788.1	788.1	788.1	788.1	788.1	787.8
147.5°	821.0	821.4	821.9	822.3	822.7	823.1	823.5	823.9	824.5	824.9	824.5
150°	843.4	843.7	844.4	845.2	845.9	846.6	846.6	846.6	846.6	846.6	846.4
152.5°	865.4	865.7	865.9	866.2	866.5	866.8	867.2	867.6	868.0	868.4	868.3
155°	895.4	895.5	895.8	896.0	896.1	896.3	897.0	897.7	898.4	899.1	899.0
157.5°	921.7	921.6	921.8	922.0	922.1	922.3	923.0	923.7	924.4	925.1	924.9
160°	937.6	937.5	937.6	937.8	938.0	938.2	938.9	939.6	940.2	940.9	940.9
162.5°	952.7	952.5	952.5	952.6	952.6	952.7	953.5	954.3	955.2	956.0	955.9
165°	972.3	972.2	972.3	972.5	972.7	972.9	973.6	974.3	975.0	975.6	975.5
167.5°	987.2	986.9	986.9	986.9	986.9	986.9	988.0	989.1	990.1	991.2	991.1
170°	996.1	995.7	995.7	995.7	995.7	995.7	996.8	997.8	999.0	1000.0	999.9
172.5°	1002.4	1002.1	1002.1	1002.1	1002.1	1002.1	1003.1	1004.2	1005.2	1006.3	1006.3
175°	1009.6	1009.2	1009.2	1009.2	1009.2	1009.2	1010.3	1011.3	1012.4	1013.4	1013.3
177.5°	1013.7	1013.4	1013.3	1013.1	1013.0	1012.8	1013.7	1014.5	1015.3	1016.2	1016.1
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	523.8	525.1	524.0	525.5	524.0	525.1	523.8	524.9	526.6	525.5	528.2
5°	482.8	480.7	482.1	481.2	482.1	480.7	482.8	483.9	486.8	487.7	489.6
7.5°	444.9	442.9	440.6	439.5	440.6	442.9	444.9	445.6	448.0	451.5	454.1
10°	421.2	418.6	418.4	416.8	418.4	418.6	421.2	423.7	425.4	429.8	432.8
12.5°	403.8	401.4	398.8	398.1	398.8	401.4	403.8	406.1	406.6	411.5	413.6
15°	379.2	377.3	375.7	377.1	375.7	377.3	379.2	380.6	383.1	386.7	389.0
17.5°	358.7	357.2	356.9	355.2	356.9	357.2	358.7	359.5	363.7	366.0	370.0
20°	345.8	344.7	345.2	342.0	345.2	344.7	345.8	347.9	352.1	353.3	357.5
22.5°	335.6	333.3	333.0	332.3	333.0	333.3	335.6	337.5	338.3	341.9	344.8
25°	319.4	318.3	317.1	318.3	317.1	318.3	319.4	321.5	322.4	325.1	327.9
27.5°	305.4	304.0	303.7	303.9	303.7	304.0	305.4	305.2	307.7	309.8	311.8
30°	296.8	294.5	294.7	294.5	294.7	294.5	296.8	296.8	298.2	300.1	301.9
32.5°	287.5	285.9	285.6	285.2	285.6	285.9	287.5	287.1	288.9	291.1	293.2
35°	273.7	273.7	272.6	272.6	272.6	273.7	273.7	274.4	276.3	276.3	278.6
37.5°	260.7	260.5	259.8	259.9	259.8	260.5	260.7	261.4	262.0	263.0	264.5
40°	251.1	250.9	250.1	248.7	250.1	250.9	251.1	252.1	252.5	253.7	254.6
42.5°	241.8	241.0	240.7	240.1	240.7	241.0	241.8	242.3	242.6	244.1	246.0
45°	227.0	227.0	226.6	226.3	226.6	227.0	227.0	227.0	227.3	229.1	230.0
47.5°	212.8	213.2	214.1	213.9	214.1	213.2	212.8	212.4	212.5	213.4	214.5
50°	204.2	204.4	205.1	205.3	205.1	204.4	204.2	203.3	202.8	202.8	203.5
52.5°	194.7	196.0	196.9	196.7	196.9	196.0	194.7	193.9	193.1	192.0	193.0
55°	181.3	183.0	184.6	184.8	184.6	183.0	181.3	179.3	178.2	176.4	177.1
57.5°	168.1	170.4	172.1	172.7	172.1	170.4	168.1	165.6	162.6	161.7	160.4
60°	159.2	162.2	164.3	165.2	164.3	162.2	159.2	156.8	152.8	150.3	149.4
62.5°	150.6	154.0	156.0	156.2	156.0	154.0	150.6	146.9	143.0	140.0	138.1
65°	136.5	140.0	141.9	143.3	141.9	140.0	136.5	132.5	128.2	124.1	122.0
67.5°	121.4	124.9	126.9	128.1	126.9	124.9	121.4	116.4	112.4	107.9	105.4
70°	110.4	113.9	116.6	117.6	116.6	113.9	110.4	104.5	101.1	96.8	94.7
72.5°	99.6	102.7	104.9	106.0	104.9	102.7	99.6	94.1	90.0	85.8	83.0
75°	80.7	84.9	87.1	88.2	87.1	84.9	80.7	77.7	73.0	68.6	66.2
77.5°	62.2	66.0	67.4	68.0	67.4	66.0	62.2	58.7	55.1	51.9	49.7
80°	49.9	52.3	53.9	54.1	53.9	52.3	49.9	47.2	44.3	41.3	39.2
82.5°	38.4	40.3	40.8	41.4	40.8	40.3	38.4	36.0	33.5	31.2	29.5
85°	21.0	21.9	22.2	21.9	22.2	21.9	21.0	19.4	18.2	17.1	16.4
87.5°	10.4	10.3	10.4	10.9	10.4	10.3	10.4	9.9	10.0	9.4	8.9
90°	17.4	17.9	18.4	19.0	18.4	17.9	17.4	16.9	16.2	15.2	14.3
92.5°	36.2	36.5	36.9	37.3	36.9	36.5	36.2	35.7	34.9	33.8	32.6
95°	66.9	67.3	67.6	67.9	67.6	67.3	66.9	66.6	65.7	64.5	63.2
97.5°	102.3	102.5	102.8	103.0	102.8	102.5	102.3	102.1	101.5	100.3	99.2
100°	128.5	128.8	129.2	129.5	129.2	128.8	128.5	128.2	127.1	125.5	124.0
102.5°	154.6	155.0	155.5	156.0	155.5	155.0	154.6	154.1	153.0	151.3	149.6
105°	194.3	194.8	195.3	195.8	195.3	194.8	194.3	193.7	193.0	191.9	190.9
107.5°	236.7	236.6	236.6	236.6	236.6	236.6	236.7	236.7	236.5	235.9	235.4
110°	267.4	267.2	267.1	266.9	267.1	267.2	267.4	267.6	267.4	266.9	266.4



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	297.5	297.2	296.9	296.6	296.9	297.2	297.5	297.9	297.9	297.6	297.4
115°	344.1	343.9	343.7	343.6	343.7	343.9	344.1	344.2	344.4	344.6	344.8
117.5°	391.4	390.7	390.0	389.3	390.0	390.7	391.4	392.1	392.4	392.2	392.1
120°	423.0	422.3	421.6	420.9	421.6	422.3	423.0	423.7	424.0	424.0	424.0
122.5°	454.1	453.6	453.0	452.5	453.0	453.6	454.1	454.7	455.0	455.2	455.3
125°	500.4	500.2	500.1	499.9	500.1	500.2	500.4	500.6	500.8	501.2	501.5
127.5°	546.4	546.0	545.7	545.3	545.7	546.0	546.4	546.7	547.0	547.1	547.3
130°	576.7	576.3	576.0	575.6	576.0	576.3	576.7	577.0	577.3	577.5	577.6
132.5°	605.6	605.1	604.6	604.1	604.6	605.1	605.6	606.0	606.4	606.5	606.7
135°	650.5	649.7	649.0	648.3	649.0	649.7	650.5	651.2	651.5	651.5	651.5
137.5°	694.2	693.4	692.5	691.6	692.5	693.4	694.2	695.1	695.4	695.2	695.0
140°	722.1	721.1	720.2	719.4	720.2	721.1	722.1	722.9	723.2	722.8	722.5
142.5°	748.5	747.7	746.8	745.9	746.8	747.7	748.5	749.4	749.7	749.5	749.3
145°	787.3	786.8	786.3	785.7	786.3	786.8	787.3	787.8	788.1	788.1	788.1
147.5°	823.2	822.0	820.9	819.7	820.9	822.0	823.2	824.5	824.9	824.5	823.9
150°	846.0	845.7	845.3	845.0	845.3	845.7	846.0	846.4	846.6	846.6	846.6
152.5°	867.7	867.1	866.5	865.8	866.5	867.1	867.7	868.3	868.4	868.0	867.6
155°	898.1	897.3	896.4	895.4	896.4	897.3	898.1	899.0	899.1	898.4	897.7
157.5°	923.7	922.6	921.4	920.3	921.4	922.6	923.7	924.9	925.1	924.4	923.7
160°	940.0	939.1	938.2	937.4	938.2	939.1	940.0	940.9	940.9	940.2	939.6
162.5°	954.9	953.9	952.9	951.9	952.9	953.9	954.9	955.9	956.0	955.2	954.3
165°	974.4	973.4	972.3	971.3	972.3	973.4	974.4	975.5	975.6	975.0	974.3
167.5°	990.1	989.0	987.8	986.7	987.8	989.0	990.1	991.1	991.2	990.1	989.1
170°	998.7	997.4	996.2	995.0	996.2	997.4	998.7	999.9	1000.0	999.0	997.8
172.5°	1005.2	1004.1	1003.0	1001.9	1003.0	1004.1	1005.2	1006.3	1006.3	1005.2	1004.2
175°	1012.1	1010.9	1009.7	1008.5	1009.7	1010.9	1012.1	1013.3	1013.4	1012.4	1011.3
177.5°	1015.1	1014.2	1013.2	1012.2	1013.2	1014.2	1015.1	1016.1	1016.2	1015.3	1014.5
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	525.7	528.0	530.7	532.8	536.5	538.2	540.3	541.9	544.9	547.8	551.1
5°	490.3	494.2	499.6	505.4	512.2	516.8	523.4	527.4	535.3	542.5	549.6
7.5°	458.2	463.0	470.6	478.1	487.0	494.9	503.1	512.2	522.3	534.3	544.2
10°	436.2	442.6	450.8	460.2	470.9	480.2	491.2	501.0	513.4	527.4	540.5
12.5°	418.6	424.1	433.2	442.2	453.7	465.1	476.5	489.4	503.8	519.4	535.7
15°	394.4	399.0	406.5	418.9	430.5	441.7	458.8	470.9	489.1	506.3	526.2
17.5°	373.7	379.5	385.8	396.4	408.5	422.4	437.7	452.9	470.4	492.3	514.6
20°	361.0	365.7	372.8	381.0	393.8	407.9	422.3	437.8	459.2	481.9	505.9
22.5°	347.2	352.2	360.4	369.3	380.1	393.5	409.5	426.4	448.8	471.0	497.2
25°	330.9	334.4	341.8	349.8	360.5	371.9	388.5	407.2	429.4	454.8	481.4
27.5°	315.6	318.6	325.4	332.3	342.0	355.6	370.4	389.3	410.2	436.0	465.4
30°	304.5	307.8	313.9	321.3	330.6	342.5	357.7	375.5	397.9	423.0	453.8
32.5°	295.0	297.9	302.5	309.9	319.1	330.6	344.7	362.7	385.2	410.7	441.0
35°	280.2	283.5	287.0	292.9	300.7	311.9	327.4	344.5	365.9	390.6	418.4
37.5°	265.6	269.1	272.3	277.5	284.7	294.6	307.9	325.7	345.1	368.9	395.6
40°	256.4	259.2	261.9	267.4	274.7	284.0	296.4	312.3	332.8	355.0	377.1
42.5°	247.3	249.9	252.1	257.0	263.7	272.6	284.4	299.9	318.9	339.6	359.2
45°	232.9	234.5	237.1	241.3	246.6	254.8	266.2	280.0	296.1	315.7	330.4
47.5°	217.3	219.8	222.0	225.6	230.0	238.0	249.0	260.7	275.4	289.9	300.2
50°	205.3	207.9	211.0	214.5	218.6	226.1	236.1	248.0	260.4	271.7	280.4
52.5°	194.1	196.5	199.8	203.1	208.2	214.5	223.1	233.7	245.9	253.9	261.3
55°	177.5	178.7	182.5	185.7	190.7	195.3	204.0	213.3	220.8	226.8	232.9
57.5°	160.7	162.2	164.4	167.3	172.2	177.6	183.7	192.0	196.3	199.4	204.2
60°	149.8	150.3	151.7	155.2	159.0	163.8	170.8	176.6	180.0	182.5	186.4
62.5°	137.8	137.9	140.3	142.9	145.6	151.0	156.6	161.4	164.0	165.3	169.1
65°	121.1	120.7	122.0	124.1	127.4	130.9	135.8	140.0	139.8	141.2	143.5
67.5°	104.0	103.5	103.5	105.5	108.2	111.3	114.6	117.1	117.1	119.0	120.2
70°	92.4	91.0	91.9	93.6	94.7	97.4	101.1	102.0	102.2	103.1	104.3
72.5°	80.5	80.0	80.7	81.4	82.2	84.2	87.5	88.0	88.1	88.6	90.5
75°	63.9	63.5	63.0	63.7	64.6	66.0	67.2	68.2	67.9	68.2	69.6
77.5°	48.0	46.7	46.4	46.8	47.0	47.9	49.1	49.0	49.2	49.2	50.7
80°	38.1	36.2	36.0	36.0	36.2	36.7	37.1	37.6	36.9	37.6	38.1
82.5°	28.0	26.9	26.8	26.6	26.7	26.8	27.1	27.3	27.2	27.5	27.8
85°	15.5	14.9	14.2	14.7	14.4	13.7	14.2	13.5	13.3	13.5	13.7
87.5°	8.0	8.0	7.4	7.1	6.7	6.6	6.0	5.5	5.0	4.9	5.2
90°	13.5	12.6	11.4	10.2	9.0	7.7	6.4	5.0	3.6	2.2	0.8
92.5°	31.5	30.3	28.8	27.3	25.8	24.2	23.0	22.0	21.1	20.1	19.1
95°	62.0	60.8	59.1	57.3	55.5	53.8	52.7	52.4	52.0	51.7	51.3
97.5°	98.0	96.8	94.4	92.0	89.6	87.2	85.8	85.7	85.5	85.4	85.3
100°	122.4	120.8	118.6	116.2	114.0	111.7	110.6	110.6	110.6	110.6	110.6
102.5°	147.8	146.1	144.9	143.8	142.6	141.5	140.6	139.9	139.2	138.5	137.7
105°	189.8	188.7	187.6	186.6	185.6	184.5	183.6	182.7	181.8	181.0	180.1
107.5°	234.9	234.4	233.6	232.8	232.0	231.2	230.4	229.4	228.5	227.6	226.8
110°	265.9	265.3	264.8	264.3	263.8	263.3	262.6	261.7	260.7	259.9	259.0



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	297.2	296.9	296.3	295.6	294.9	294.3	293.7	293.3	292.8	292.4	291.9
115°	344.9	345.1	344.8	344.4	344.1	343.7	343.2	342.4	341.7	341.0	340.3
117.5°	391.9	391.8	391.5	391.2	390.9	390.6	390.2	389.9	389.6	389.3	389.0
120°	424.0	424.0	423.8	423.7	423.5	423.3	422.8	421.9	421.1	420.2	419.3
122.5°	455.4	455.7	455.1	454.7	454.2	453.8	453.4	453.1	452.8	452.5	452.1
125°	501.9	502.2	502.0	501.9	501.7	501.5	500.9	499.9	498.8	497.8	496.7
127.5°	547.5	547.8	547.5	547.2	547.0	546.8	546.4	545.8	545.2	544.7	544.1
130°	577.8	578.0	577.6	577.3	576.9	576.6	576.0	575.1	574.3	573.4	572.5
132.5°	606.9	607.1	607.1	607.2	607.3	607.3	606.7	605.2	603.8	602.4	601.0
135°	651.5	651.5	651.3	651.2	651.0	650.8	650.2	649.1	648.0	647.0	645.9
137.5°	694.8	694.6	694.2	693.8	693.5	693.1	692.4	691.4	690.3	689.3	688.3
140°	722.2	721.8	721.2	720.7	720.1	719.6	718.9	718.1	717.2	716.3	715.5
142.5°	749.1	748.9	748.2	747.6	746.9	746.3	745.6	744.8	744.1	743.4	742.7
145°	788.1	788.1	787.6	787.0	786.5	786.0	785.4	784.7	784.0	783.3	782.5
147.5°	823.5	823.1	822.7	822.3	821.9	821.4	821.0	820.7	820.3	819.9	819.5
150°	846.6	846.6	845.9	845.2	844.4	843.7	843.4	843.6	843.8	843.9	844.1
152.5°	867.2	866.8	866.5	866.2	865.9	865.7	865.4	865.2	864.8	864.6	864.3
155°	897.0	896.3	896.1	896.0	895.8	895.5	895.4	895.4	895.4	895.4	895.4
157.5°	923.0	922.3	922.1	922.0	921.8	921.6	921.7	922.1	922.5	922.9	923.3
160°	938.9	938.2	938.0	937.8	937.6	937.5	937.6	938.2	938.7	939.2	939.7
162.5°	953.5	952.7	952.6	952.6	952.5	952.5	952.7	953.1	953.4	953.8	954.2
165°	973.6	972.9	972.7	972.5	972.3	972.2	972.3	972.6	973.0	973.3	973.7
167.5°	988.0	986.9	986.9	986.9	986.9	986.9	987.2	988.0	988.7	989.4	990.1
170°	996.8	995.7	995.7	995.7	995.7	995.7	996.1	996.8	997.5	998.3	999.0
172.5°	1003.1	1002.1	1002.1	1002.1	1002.1	1002.1	1002.4	1003.1	1003.8	1004.5	1005.2
175°	1010.3	1009.2	1009.2	1009.2	1009.2	1009.2	1009.6	1010.3	1011.0	1011.7	1012.4
177.5°	1013.7	1012.8	1013.0	1013.1	1013.3	1013.4	1013.7	1014.3	1014.9	1015.4	1016.0
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	552.8	555.3	557.0	560.2	562.8	564.3	565.6	566.7	568.0	569.2	572.4
5°	556.3	562.4	567.5	575.4	582.7	588.2	594.3	599.7	604.1	610.5	615.3
7.5°	554.7	565.5	576.8	589.2	601.7	613.3	624.1	634.1	643.2	654.2	663.9
10°	553.3	567.9	582.4	599.1	616.0	630.5	644.0	657.8	667.8	681.9	693.8
12.5°	552.2	569.5	586.9	606.8	625.5	646.0	664.0	674.1	689.3	700.5	714.7
15°	547.4	570.3	594.3	616.7	643.4	662.3	678.1	697.7	712.0	726.2	741.5
17.5°	539.0	564.9	591.8	621.2	646.6	666.9	687.4	706.3	723.3	742.4	761.5
20°	535.0	561.0	591.8	621.9	646.8	668.0	689.0	709.8	728.5	753.1	775.2
22.5°	526.8	558.2	586.5	615.9	641.6	664.7	688.5	712.1	736.9	764.6	792.3
25°	512.2	543.9	574.0	603.0	628.8	657.8	683.3	714.8	746.5	783.2	817.7
27.5°	497.0	527.4	554.9	582.9	613.1	645.9	678.8	714.6	756.2	802.4	851.1
30°	484.6	513.4	540.2	568.9	600.4	637.2	673.5	715.9	764.0	816.0	873.9
32.5°	470.3	496.8	522.8	553.2	587.5	626.4	668.6	715.2	773.0	832.0	891.6
35°	445.7	467.9	494.7	527.1	565.8	610.5	659.2	714.3	780.5	848.5	898.6
37.5°	416.6	437.2	465.4	501.0	541.6	589.5	647.3	712.7	783.0	837.2	853.3
40°	396.9	416.1	445.5	482.3	523.8	574.5	637.9	707.0	775.2	809.7	796.4
42.5°	376.0	396.1	424.7	461.2	505.9	561.1	626.2	695.3	752.5	765.5	719.5
45°	343.1	363.8	392.0	428.9	477.0	536.7	604.6	667.4	700.2	676.7	605.5
47.5°	312.4	331.8	358.0	396.1	445.7	507.5	572.8	622.9	625.5	569.3	493.2
50°	291.4	309.4	335.8	373.9	423.0	485.6	544.6	584.1	566.3	502.6	429.6
52.5°	270.9	288.5	314.5	352.1	400.8	458.2	513.1	540.8	507.4	441.9	379.6
55°	241.3	256.7	282.2	316.9	363.0	416.3	462.9	472.5	429.1	364.8	314.1
57.5°	212.4	226.7	249.8	281.9	324.2	371.2	407.8	405.7	359.8	304.6	264.4
60°	192.8	206.7	227.3	258.5	297.1	337.7	368.9	361.4	316.0	268.3	234.5
62.5°	175.2	187.7	207.1	234.5	269.6	307.2	332.9	321.8	277.3	235.7	208.9
65°	149.4	159.9	176.4	199.8	228.9	259.9	279.8	265.6	227.5	195.1	173.6
67.5°	124.6	133.1	146.9	165.6	190.5	215.4	227.4	213.2	182.7	159.1	143.1
70°	109.0	116.4	127.1	143.7	165.4	186.4	195.5	182.7	156.5	136.2	124.8
72.5°	93.3	99.5	108.9	123.8	141.2	159.4	167.3	155.1	133.6	116.4	105.8
75°	72.1	76.3	82.8	93.1	106.8	121.4	125.7	115.0	101.3	88.5	81.4
77.5°	51.6	55.1	60.1	66.6	76.3	85.5	89.4	83.2	72.6	64.4	58.7
80°	39.7	41.5	45.7	51.1	58.8	64.6	67.2	63.2	55.7	49.7	45.2
82.5°	28.3	30.2	32.6	37.1	42.0	45.9	48.7	46.0	40.7	35.9	33.3
85°	13.7	14.9	16.4	18.2	21.9	24.2	24.0	22.4	20.3	18.5	17.1
87.5°	5.3	5.8	6.6	7.8	8.7	9.6	10.2	10.1	9.6	9.2	8.9
90°	2.2	3.6	5.0	6.4	7.7	9.0	10.2	11.4	12.6	13.5	14.3
92.5°	20.1	21.1	22.0	23.0	24.2	25.8	27.3	28.8	30.3	31.5	32.6
95°	51.7	52.0	52.4	52.7	53.8	55.5	57.3	59.1	60.8	62.0	63.2
97.5°	85.4	85.5	85.7	85.8	87.2	89.6	92.0	94.4	96.8	98.0	99.2
100°	110.6	110.6	110.6	110.6	111.7	114.0	116.2	118.6	120.8	122.4	124.0
102.5°	138.5	139.2	139.9	140.6	141.5	142.6	143.8	144.9	146.1	147.8	149.6
105°	181.0	181.8	182.7	183.6	184.5	185.6	186.6	187.6	188.7	189.8	190.9
107.5°	227.6	228.5	229.4	230.4	231.2	232.0	232.8	233.6	234.4	234.9	235.4
110°	259.9	260.7	261.7	262.6	263.3	263.8	264.3	264.8	265.3	265.9	266.4



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	292.4	292.8	293.3	293.7	294.3	294.9	295.6	296.3	296.9	297.2	297.4
115°	341.0	341.7	342.4	343.2	343.7	344.1	344.4	344.8	345.1	344.9	344.8
117.5°	389.3	389.6	389.9	390.2	390.6	390.9	391.2	391.5	391.8	391.9	392.1
120°	420.2	421.1	421.9	422.8	423.3	423.5	423.7	423.8	424.0	424.0	424.0
122.5°	452.5	452.8	453.1	453.4	453.8	454.2	454.7	455.1	455.7	455.4	455.3
125°	497.8	498.8	499.9	500.9	501.5	501.7	501.9	502.0	502.2	501.9	501.5
127.5°	544.7	545.2	545.8	546.4	546.8	547.0	547.2	547.5	547.8	547.5	547.3
130°	573.4	574.3	575.1	576.0	576.6	576.9	577.3	577.6	578.0	577.8	577.6
132.5°	602.4	603.8	605.2	606.7	607.3	607.3	607.2	607.1	607.1	606.9	606.7
135°	647.0	648.0	649.1	650.2	650.8	651.0	651.2	651.3	651.5	651.5	651.5
137.5°	689.3	690.3	691.4	692.4	693.1	693.5	693.8	694.2	694.6	694.8	695.0
140°	716.3	717.2	718.1	718.9	719.6	720.1	720.7	721.2	721.8	722.2	722.5
142.5°	743.4	744.1	744.8	745.6	746.3	746.9	747.6	748.2	748.9	749.1	749.3
145°	783.3	784.0	784.7	785.4	786.0	786.5	787.0	787.6	788.1	788.1	788.1
147.5°	819.9	820.3	820.7	821.0	821.4	821.9	822.3	822.7	823.1	823.5	823.9
150°	843.9	843.8	843.6	843.4	843.7	844.4	845.2	845.9	846.6	846.6	846.6
152.5°	864.6	864.8	865.2	865.4	865.7	865.9	866.2	866.5	866.8	867.2	867.6
155°	895.4	895.4	895.4	895.4	895.5	895.8	896.0	896.1	896.3	897.0	897.7
157.5°	922.9	922.5	922.1	921.7	921.6	921.8	922.0	922.1	922.3	923.0	923.7
160°	939.2	938.7	938.2	937.6	937.5	937.6	937.8	938.0	938.2	938.9	939.6
162.5°	953.8	953.4	953.1	952.7	952.5	952.5	952.6	952.6	952.7	953.5	954.3
165°	973.3	973.0	972.6	972.3	972.2	972.3	972.5	972.7	972.9	973.6	974.3
167.5°	989.4	988.7	988.0	987.2	986.9	986.9	986.9	986.9	986.9	988.0	989.1
170°	998.3	997.5	996.8	996.1	995.7	995.7	995.7	995.7	995.7	996.8	997.8
172.5°	1004.5	1003.8	1003.1	1002.4	1002.1	1002.1	1002.1	1002.1	1002.1	1003.1	1004.2
175°	1011.7	1011.0	1010.3	1009.6	1009.2	1009.2	1009.2	1009.2	1009.2	1010.3	1011.3
177.5°	1015.4	1014.9	1014.3	1013.7	1013.4	1013.3	1013.1	1013.0	1012.8	1013.7	1014.5
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	575.0	576.4	579.7	578.6	580.0	580.8	581.5
5°	621.4	628.8	632.2	631.7	636.6	635.4	634.2
7.5°	673.9	681.7	686.1	691.6	694.7	695.0	697.7
10°	703.6	713.8	718.0	723.9	727.6	729.7	729.4
12.5°	726.3	734.4	743.8	746.6	751.6	754.4	753.4
15°	753.8	766.6	776.4	781.2	787.6	789.4	791.9
17.5°	778.2	795.4	806.8	822.0	827.8	831.3	829.2
20°	796.7	819.3	830.7	848.9	859.0	864.3	862.4
22.5°	818.5	843.0	864.1	879.9	895.1	902.4	903.9
25°	856.0	889.5	920.6	941.3	960.2	964.6	974.4
27.5°	897.8	937.4	970.6	992.4	1005.5	1010.5	1013.6
30°	924.0	963.5	988.5	1002.5	1006.6	1006.2	1005.7
32.5°	937.0	961.6	966.4	962.5	952.9	944.7	936.2
35°	918.7	900.3	872.7	837.3	811.1	784.8	782.1
37.5°	826.3	767.3	721.4	670.2	640.8	622.5	609.9
40°	739.2	672.3	616.7	573.6	543.5	531.6	519.9
42.5°	644.8	580.8	531.6	495.5	472.9	459.7	450.5
45°	523.8	467.4	428.9	402.7	384.8	374.6	368.7
47.5°	429.3	387.5	354.8	335.9	323.6	315.6	315.6
50°	378.5	338.6	316.9	301.9	291.2	284.9	286.1
52.5°	333.5	303.7	285.2	272.7	264.7	260.8	260.6
55°	278.8	257.4	245.3	236.1	230.8	226.3	227.3
57.5°	238.5	220.5	212.3	204.7	201.0	199.2	196.6
60°	213.5	199.5	192.5	186.4	182.7	181.3	178.7
62.5°	191.3	180.3	173.5	168.5	165.2	164.7	162.7
65°	160.8	152.4	146.3	144.0	140.5	139.6	139.6
67.5°	132.5	126.5	121.8	119.7	118.2	118.4	117.2
70°	114.8	109.9	106.8	104.5	103.4	103.6	102.7
72.5°	100.5	94.9	92.3	90.9	89.4	90.0	89.6
75°	76.0	73.3	71.9	70.5	69.6	69.1	68.6
77.5°	55.8	53.4	52.3	51.5	51.7	50.5	51.4
80°	43.1	41.1	40.4	39.2	39.0	39.0	38.8
82.5°	31.6	30.4	29.9	29.0	28.5	28.9	28.3
85°	16.4	15.5	15.1	15.1	14.7	14.2	15.5
87.5°	9.0	8.5	8.6	8.5	8.6	8.6	8.3
90°	15.2	16.2	16.9	17.4	17.9	18.4	19.0
92.5°	33.8	34.9	35.7	36.2	36.5	36.9	37.3
95°	64.5	65.7	66.6	66.9	67.3	67.6	67.9
97.5°	100.3	101.5	102.1	102.3	102.5	102.8	103.0
100°	125.5	127.1	128.2	128.5	128.8	129.2	129.5
102.5°	151.3	153.0	154.1	154.6	155.0	155.5	156.0
105°	191.9	193.0	193.7	194.3	194.8	195.3	195.8
107.5°	235.9	236.5	236.7	236.7	236.6	236.6	236.6
110°	266.9	267.4	267.6	267.4	267.2	267.1	266.9



TEST NUMBER: P333134-840

CATALOG NUMBER: S125DIP-S375D810U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	297.6	297.9	297.9	297.5	297.2	296.9	296.6
115°	344.6	344.4	344.2	344.1	343.9	343.7	343.6
117.5°	392.2	392.4	392.1	391.4	390.7	390.0	389.3
120°	424.0	424.0	423.7	423.0	422.3	421.6	420.9
122.5°	455.2	455.0	454.7	454.1	453.6	453.0	452.5
125°	501.2	500.8	500.6	500.4	500.2	500.1	499.9
127.5°	547.1	547.0	546.7	546.4	546.0	545.7	545.3
130°	577.5	577.3	577.0	576.7	576.3	576.0	575.6
132.5°	606.5	606.4	606.0	605.6	605.1	604.6	604.1
135°	651.5	651.5	651.2	650.5	649.7	649.0	648.3
137.5°	695.2	695.4	695.1	694.2	693.4	692.5	691.6
140°	722.8	723.2	722.9	722.1	721.1	720.2	719.4
142.5°	749.5	749.7	749.4	748.5	747.7	746.8	745.9
145°	788.1	788.1	787.8	787.3	786.8	786.3	785.7
147.5°	824.5	824.9	824.5	823.2	822.0	820.9	819.7
150°	846.6	846.6	846.4	846.0	845.7	845.3	845.0
152.5°	868.0	868.4	868.3	867.7	867.1	866.5	865.8
155°	898.4	899.1	899.0	898.1	897.3	896.4	895.4
157.5°	924.4	925.1	924.9	923.7	922.6	921.4	920.3
160°	940.2	940.9	940.9	940.0	939.1	938.2	937.4
162.5°	955.2	956.0	955.9	954.9	953.9	952.9	951.9
165°	975.0	975.6	975.5	974.4	973.4	972.3	971.3
167.5°	990.1	991.2	991.1	990.1	989.0	987.8	986.7
170°	999.0	1000.0	999.9	998.7	997.4	996.2	995.0
172.5°	1005.2	1006.3	1006.3	1005.2	1004.1	1003.0	1001.9
175°	1012.4	1013.4	1013.3	1012.1	1010.9	1009.7	1008.5
177.5°	1015.3	1016.2	1016.1	1015.1	1014.2	1013.2	1012.2
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7

(END OF REPORT)